

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333088-935

Luminaire Tested: **S124RDIW-S1020D1340U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333088-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S1020D1340U935-4F0-1E-UDD-A1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7744.3 lumens  
Efficiency: N/A  
Efficacy: 110.9 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 69.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333088-935

CATALOG NUMBER: S124RDIW-S1020D1340U935-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - · - · 90°-270°    - · - · 135°-315°



TEST NUMBER: P333088-935

CATALOG NUMBER: S124RDIW-S1020D1340U935-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55	48
1	98	94	90	87	90	86	83	80	73	71	69	60	59	57	49	48	47	42
2	89	82	76	71	82	76	71	67	64	61	57	54	51	49	44	42	40	36
3	82	73	66	60	75	67	61	56	57	53	49	48	44	42	39	37	35	31
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	35	32	30	27
5	69	58	50	44	63	54	47	41	46	40	36	39	35	31	32	29	27	23
6	64	52	44	38	59	48	41	36	41	36	32	35	31	28	29	26	24	21
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	17
9	51	39	32	27	47	36	30	25	31	26	23	27	23	20	23	19	17	15
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	11926	11926	11926	11926
5°	13834	11962	10573	11962
10°	16365	11910	9437	11910
15°	18904	11800	8109	11800
20°	21047	11649	7332	11649
25°	21727	11500	6807	11500
30°	19020	11320	6492	11320
35°	14807	11052	6300	11052
40°	11102	10745	6198	10745
45°	8766	10255	6142	10255
50°	7401	9688	5966	9688
55°	6450	9064	5645	9064
60°	5804	8418	4997	8418
65°	5117	7721	4298	7721
70°	4607	6996	3878	6996
75°	3862	6201	3306	6201
80°	3268	5286	3096	5286
85°	2760	4131	2760	4131



TEST NUMBER: P333088-935

CATALOG NUMBER: S124RDIW-S1020D1340U935-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	143.1	1.8
10°-20°	431.8	5.6
20°-30°	675.3	8.7
30°-40°	750.8	9.7
40°-50°	666.1	8.6
50°-60°	519.0	6.7
60°-70°	339.8	4.4
70°-80°	167.1	2.2
80°-90°	45.5	0.6
90°-100°	95.2	1.2
100°-110°	282.1	3.6
110°-120°	478.8	6.2
120°-130°	631.3	8.2
130°-140°	709.0	9.2
140°-150°	696.7	9.0
150°-160°	586.0	7.6
160°-170°	389.9	5.0
170°-180°	136.5	1.8
0°-30°	1250.3	16.1
0°-40°	2001.0	25.8
0°-60°	3186.1	41.1
0°-90°	3738.6	48.3
90°-120°	856.1	11.1
90°-150°	2893.2	37.4
90°-180°	4006.0	51.7
0°-180°	7744.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1477	1477	1477	1477	1477	
5°	1707	1476	1305	1476	1707	173
15°	2262	1412	970	1412	2262	643
25°	2439	1291	764	1291	2439	1082
35°	1502	1121	639	1121	1502	942
45°	768	898	538	898	768	608
55°	458	644	401	644	458	417
65°	268	404	225	404	268	269
75°	124	199	106	199	124	136
85°	30	45	30	45	30	34
90°	34	3	34	3	34	18
95°	88	67	88	67	88	92
105°	272	260	272	260	272	287
115°	482	487	482	487	482	477
125°	703	709	703	709	703	628
135°	916	914	916	914	916	707
145°	1112	1111	1112	1111	1112	696
155°	1272	1273	1272	1273	1272	585
165°	1382	1386	1382	1386	1382	389
175°	1435	1442	1435	1442	1435	136
180°	1444	1444	1444	1444	1444	



TEST NUMBER: P333088-935

CATALOG NUMBER: S124RDIW-S1020D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3
2.5°	1558.2	1562.5	1558.2	1557.8	1553.1	1551.6	1549.7	1543.5	1532.1	1525.4	1526.8
5°	1707.1	1721.9	1713.6	1712.4	1699.4	1686.3	1677.9	1658.9	1638.7	1625.0	1613.6
7.5°	1879.2	1887.7	1882.6	1874.2	1853.0	1841.0	1821.7	1796.6	1760.3	1732.5	1707.2
10°	1996.3	2003.5	2001.1	1985.6	1970.1	1938.6	1920.7	1885.7	1839.8	1803.5	1769.5
12.5°	2111.6	2119.2	2098.3	2098.9	2069.7	2044.8	2016.5	1972.3	1919.3	1872.5	1830.1
15°	2261.8	2252.3	2252.3	2240.4	2207.6	2173.2	2144.0	2097.6	2030.8	1974.9	1916.0
17.5°	2379.5	2382.7	2377.9	2349.8	2324.1	2288.4	2234.9	2180.7	2118.8	2043.8	1983.5
20°	2449.9	2449.9	2444.6	2425.5	2392.2	2354.1	2296.4	2237.4	2158.9	2083.3	2015.4
22.5°	2478.5	2480.4	2474.1	2458.3	2428.4	2391.2	2342.0	2282.2	2201.2	2116.1	2032.0
25°	2439.2	2450.5	2451.7	2447.5	2438.6	2416.0	2373.7	2312.4	2239.8	2147.5	2057.0
27.5°	2239.5	2253.8	2266.2	2286.8	2314.2	2328.5	2330.4	2299.2	2235.8	2147.1	2056.0
30°	2040.4	2052.3	2091.0	2141.6	2180.8	2216.6	2247.6	2255.8	2220.2	2140.4	2044.5
32.5°	1819.5	1835.7	1874.3	1928.7	1994.2	2054.7	2124.2	2159.6	2158.7	2110.8	2022.1
35°	1502.4	1514.2	1550.0	1607.1	1685.7	1775.6	1885.7	1971.3	2029.6	2025.5	1971.3
37.5°	1211.6	1225.0	1261.1	1308.5	1384.7	1496.0	1602.6	1720.6	1828.5	1889.1	1871.0
40°	1053.5	1054.1	1089.3	1138.1	1209.4	1306.5	1422.5	1553.5	1673.7	1771.9	1791.0
42.5°	928.8	928.8	952.1	1004.7	1056.2	1147.5	1258.3	1388.3	1529.0	1642.4	1692.9
45°	767.8	773.2	792.2	823.8	864.3	941.6	1030.3	1151.2	1308.9	1443.4	1527.3
47.5°	650.2	658.1	670.2	695.9	728.1	779.7	853.1	961.7	1089.9	1237.9	1357.4
50°	589.3	590.5	605.9	620.2	648.2	689.2	753.5	844.0	961.8	1104.1	1236.8
52.5°	536.9	536.7	546.0	564.0	586.8	618.8	670.7	753.0	857.6	985.1	1122.1
55°	458.3	461.3	468.5	482.7	500.0	522.6	563.7	625.6	707.7	816.7	941.1
57.5°	398.6	400.1	405.7	411.7	427.6	444.0	474.8	517.8	587.1	676.3	792.2
60°	359.5	360.1	361.9	370.8	383.3	398.8	419.7	455.9	514.3	595.8	687.5
62.5°	321.4	322.4	325.2	331.7	341.4	352.1	373.9	403.1	451.4	521.1	603.6
65°	267.9	268.5	272.6	275.0	282.8	292.2	308.3	328.0	361.3	419.7	482.2
67.5°	223.8	223.8	224.0	227.2	232.6	238.9	248.6	264.2	289.4	325.2	380.3
70°	195.2	195.2	196.4	198.2	201.2	206.6	211.9	223.8	242.3	271.4	313.7
72.5°	168.6	169.0	170.2	170.6	172.1	176.5	180.5	188.1	201.8	223.8	258.0
75°	123.8	125.6	128.5	131.0	133.9	133.4	137.5	142.2	146.5	159.5	179.2
77.5°	92.1	91.2	91.5	93.6	93.9	94.5	97.5	101.2	104.3	110.5	117.5
80°	70.3	70.3	72.0	72.6	72.0	72.6	75.6	77.4	78.6	80.9	87.5
82.5°	53.1	54.1	53.5	54.1	54.4	55.0	57.5	57.9	59.1	60.0	62.8
85°	29.8	30.4	30.9	29.8	29.8	29.8	30.9	31.5	32.7	32.1	33.3
87.5°	17.1	16.6	17.0	16.9	17.2	16.6	16.8	17.4	16.2	16.4	15.9
90°	33.5	33.0	32.5	32.0	31.5	30.5	29.0	27.6	26.1	24.5	22.6
92.5°	49.6	49.2	49.0	48.6	48.4	47.8	46.9	46.0	45.1	44.3	42.8
95°	88.3	88.3	88.3	88.3	88.3	87.8	87.1	86.4	85.6	84.9	83.1
97.5°	138.3	138.3	138.3	138.3	138.3	137.8	136.9	136.0	135.1	134.2	132.2
100°	173.1	173.1	173.1	173.1	173.1	172.8	172.4	171.9	171.3	170.8	168.6
102.5°	212.4	212.2	212.0	211.8	211.5	211.1	210.4	209.7	209.1	208.4	206.3
105°	272.4	271.7	271.0	270.2	269.5	268.7	268.0	267.3	266.5	265.8	264.8
107.5°	331.0	331.1	331.1	331.1	331.1	330.9	330.1	329.4	328.7	328.0	328.0
110°	373.0	372.2	371.4	370.7	370.0	369.9	370.3	370.8	371.3	371.9	372.1



TEST NUMBER: P333088-935

CATALOG NUMBER: S124RDIW-S1020D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	415.9	415.7	415.5	415.3	415.3	415.2	415.3	415.4	415.5	415.6	416.0
115°	482.4	482.6	482.8	483.1	483.4	483.6	483.9	484.1	484.4	484.6	485.1
117.5°	545.8	546.3	546.8	547.3	547.8	548.5	549.3	550.2	551.0	551.8	552.2
120°	594.0	593.6	593.1	592.5	592.0	592.5	593.7	595.0	596.2	597.4	598.1
122.5°	634.2	635.2	636.0	636.9	637.8	638.7	639.6	640.3	641.2	642.0	642.4
125°	703.4	704.0	704.5	705.0	705.4	705.9	706.5	707.0	707.4	707.9	708.2
127.5°	767.6	767.9	768.4	768.8	769.1	769.6	770.1	770.6	771.1	771.5	772.0
130°	809.5	810.5	811.5	812.5	813.6	814.2	814.8	815.3	815.7	816.2	816.2
132.5°	854.2	854.6	855.0	855.4	855.8	856.3	856.8	857.2	857.7	858.2	858.4
135°	915.6	916.4	917.1	917.8	918.6	919.2	919.7	920.2	920.8	921.2	921.2
137.5°	980.2	980.0	979.9	979.7	979.6	979.8	980.5	981.1	981.7	982.4	982.0
140°	1019.5	1019.7	1019.9	1020.2	1020.5	1020.7	1021.0	1021.2	1021.5	1021.7	1021.7
142.5°	1058.8	1058.9	1058.9	1058.9	1058.9	1059.0	1059.1	1059.1	1059.2	1059.2	1059.5
145°	1112.2	1112.9	1113.6	1114.4	1115.2	1115.6	1115.9	1116.1	1116.4	1116.6	1116.4
147.5°	1166.2	1166.5	1166.7	1166.9	1167.2	1167.4	1167.6	1167.8	1168.0	1168.2	1168.4
150°	1199.3	1199.5	1199.7	1200.0	1200.2	1200.3	1200.3	1200.3	1200.3	1200.3	1200.3
152.5°	1229.6	1230.3	1230.9	1231.6	1232.2	1232.3	1231.7	1231.1	1230.5	1229.9	1229.7
155°	1271.9	1272.8	1273.8	1274.8	1275.8	1275.8	1274.8	1273.8	1272.8	1271.9	1272.0
157.5°	1309.6	1310.4	1311.2	1312.1	1312.9	1313.0	1312.3	1311.5	1310.8	1310.0	1310.1
160°	1331.0	1332.2	1333.5	1334.7	1335.9	1336.2	1335.5	1334.7	1333.9	1333.3	1333.5
162.5°	1353.3	1354.6	1355.8	1357.0	1358.3	1358.2	1356.9	1355.6	1354.3	1352.9	1353.1
165°	1382.3	1383.4	1384.3	1385.3	1386.4	1386.1	1384.6	1383.1	1381.6	1380.1	1380.6
167.5°	1403.2	1404.7	1406.2	1407.7	1409.3	1409.3	1407.8	1406.4	1404.9	1403.3	1403.3
170°	1414.8	1416.5	1418.2	1420.0	1421.7	1421.9	1420.3	1418.8	1417.4	1415.8	1415.7
172.5°	1424.6	1426.3	1428.1	1429.8	1431.5	1431.6	1429.9	1428.1	1426.5	1424.8	1424.8
175°	1434.9	1436.6	1438.3	1440.0	1441.8	1441.8	1440.0	1438.3	1436.6	1434.9	1435.1
177.5°	1440.2	1441.8	1443.4	1445.0	1446.6	1446.7	1445.3	1443.9	1442.5	1441.1	1441.1
180°	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8



TEST NUMBER: P333088-935

CATALOG NUMBER: S124RDIW-S1020D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3
2.5°	1522.1	1515.4	1512.1	1504.4	1495.4	1490.6	1486.3	1480.1	1472.1	1463.5	1457.3
5°	1599.3	1585.0	1567.2	1545.8	1526.7	1508.3	1492.2	1476.1	1457.7	1438.6	1419.6
7.5°	1678.6	1650.5	1620.1	1585.0	1550.9	1519.8	1491.3	1463.9	1432.9	1405.2	1379.9
10°	1733.9	1695.7	1653.5	1608.9	1564.2	1525.5	1487.5	1452.9	1414.8	1380.9	1352.3
12.5°	1778.7	1733.9	1683.0	1627.5	1573.7	1527.0	1483.2	1438.1	1394.8	1358.1	1319.9
15°	1852.9	1791.6	1723.1	1656.5	1586.8	1523.1	1464.2	1411.9	1362.4	1310.7	1274.4
17.5°	1903.9	1831.3	1748.0	1667.9	1585.6	1510.5	1442.5	1380.2	1323.2	1270.3	1227.1
20°	1934.4	1854.1	1761.9	1670.8	1578.5	1498.1	1425.0	1355.9	1297.0	1239.8	1195.2
22.5°	1951.5	1862.7	1761.9	1666.5	1570.9	1483.8	1403.5	1331.6	1267.5	1210.3	1160.9
25°	1957.1	1861.8	1758.9	1649.3	1544.5	1452.3	1369.0	1291.0	1219.6	1162.4	1110.1
27.5°	1949.5	1837.3	1731.8	1619.5	1511.4	1414.1	1326.6	1244.7	1173.2	1111.9	1058.2
30°	1938.0	1817.7	1704.7	1588.0	1478.5	1385.1	1292.8	1214.3	1139.8	1076.2	1022.0
32.5°	1913.2	1794.0	1672.3	1552.8	1441.8	1345.6	1258.0	1179.0	1106.0	1040.9	983.4
35°	1864.2	1743.4	1611.3	1488.7	1379.7	1279.7	1197.6	1121.4	1051.7	982.1	921.4
37.5°	1799.6	1676.1	1544.7	1410.4	1301.4	1206.9	1131.6	1060.1	992.1	928.5	861.3
40°	1738.6	1626.1	1490.4	1357.1	1245.2	1154.1	1084.5	1019.6	951.1	888.0	820.8
42.5°	1664.8	1569.0	1431.8	1298.0	1187.6	1099.8	1034.9	971.5	909.2	848.1	777.9
45°	1541.6	1469.0	1340.4	1211.9	1100.5	1013.7	954.2	898.2	843.4	785.1	719.0
47.5°	1400.4	1351.3	1240.3	1108.6	1005.6	927.5	870.0	824.2	777.9	719.6	661.7
50°	1302.3	1270.7	1163.6	1043.4	945.2	873.1	814.2	771.4	732.7	676.7	625.0
52.5°	1197.6	1180.8	1090.3	975.3	880.5	809.9	759.5	720.9	681.7	635.3	586.9
55°	1038.0	1047.0	970.2	870.8	781.5	722.0	676.1	644.0	610.7	571.4	533.9
57.5°	874.9	907.6	856.0	768.8	685.1	630.1	595.6	568.5	540.5	508.0	476.0
60°	777.3	804.7	775.6	698.8	625.6	574.4	542.3	521.4	493.4	463.6	439.3
62.5°	682.1	711.4	694.1	632.1	564.1	520.1	491.8	472.3	451.5	425.6	400.2
65°	562.5	581.5	573.2	530.4	482.2	444.6	418.4	404.2	385.1	366.1	343.5
67.5°	430.8	467.6	462.7	440.0	398.3	369.0	351.9	339.2	321.9	307.7	292.4
70°	354.1	388.1	387.4	369.0	346.4	319.0	307.1	296.4	280.9	267.3	254.8
72.5°	289.9	321.0	325.5	311.4	295.9	275.3	263.8	256.4	241.4	232.0	221.9
75°	202.9	225.6	231.5	231.5	224.4	213.7	203.5	198.8	188.1	179.8	173.8
77.5°	133.1	147.4	156.7	158.8	159.9	156.3	148.0	144.6	136.4	133.5	127.8
80°	94.0	103.6	114.3	117.9	120.8	119.7	116.1	113.7	106.0	103.0	100.6
82.5°	65.0	70.3	79.0	86.9	86.1	89.2	86.1	84.2	78.4	77.2	74.9
85°	33.9	34.5	35.7	41.1	44.1	45.2	45.8	44.6	42.9	42.9	38.7
87.5°	15.6	14.6	15.2	14.7	14.7	16.0	17.0	16.9	16.0	15.1	14.2
90°	20.6	18.6	16.6	14.3	11.5	8.8	6.1	3.4	6.1	8.8	11.5
92.5°	41.4	40.0	38.7	36.4	33.2	30.1	27.0	23.9	27.0	30.1	33.2
95°	81.4	79.6	77.9	75.9	73.7	71.5	69.2	67.0	69.2	71.5	73.7
97.5°	130.2	128.1	126.1	124.2	122.3	120.6	118.8	117.0	118.8	120.6	122.3
100°	166.3	164.1	161.9	160.3	159.3	158.3	157.3	156.4	157.3	158.3	159.3
102.5°	204.3	202.2	200.2	199.0	198.6	198.2	197.9	197.4	197.9	198.2	198.6
105°	263.8	262.8	261.7	261.1	260.9	260.7	260.5	260.2	260.5	260.7	260.9
107.5°	327.8	327.6	327.4	327.3	326.9	326.7	326.3	326.1	326.3	326.7	326.9
110°	372.3	372.6	372.8	372.7	372.2	371.7	371.2	370.7	371.2	371.7	372.2





TEST NUMBER: P333088-935

CATALOG NUMBER: S124RDIW-S1020D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	416.5	417.0	417.4	417.6	417.5	417.3	417.2	417.2	417.2	417.3	417.5
115°	485.6	486.1	486.6	486.8	486.8	486.8	486.8	486.8	486.8	486.8	486.8
117.5°	552.5	552.8	553.2	553.3	553.1	552.9	552.7	552.5	552.7	552.9	553.1
120°	598.9	599.6	600.4	600.2	599.3	598.2	597.3	596.2	597.3	598.2	599.3
122.5°	642.7	643.1	643.4	643.4	643.0	642.7	642.2	641.8	642.2	642.7	643.0
125°	708.4	708.7	708.9	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0
127.5°	772.4	772.7	773.2	773.0	772.2	771.5	770.8	770.0	770.8	771.5	772.2
130°	816.2	816.2	816.2	815.9	815.1	814.4	813.6	812.9	813.6	814.4	815.1
132.5°	858.6	858.8	859.0	858.8	858.3	857.7	857.2	856.7	857.2	857.7	858.3
135°	921.2	921.2	921.2	920.5	918.9	917.5	916.0	914.5	916.0	917.5	918.9
137.5°	981.6	981.2	980.9	980.2	979.6	978.9	978.2	977.5	978.2	978.9	979.6
140°	1021.7	1021.7	1021.7	1021.5	1021.0	1020.5	1019.9	1019.5	1019.9	1020.5	1021.0
142.5°	1059.6	1059.8	1060.0	1059.9	1059.4	1058.9	1058.3	1057.9	1058.3	1058.9	1059.4
145°	1116.1	1115.9	1115.6	1115.0	1114.0	1113.0	1112.1	1111.0	1112.1	1113.0	1114.0
147.5°	1168.6	1168.8	1169.0	1168.5	1167.3	1166.1	1164.9	1163.7	1164.9	1166.1	1167.3
150°	1200.3	1200.3	1200.3	1199.9	1198.9	1197.9	1196.9	1195.9	1196.9	1197.9	1198.9
152.5°	1229.4	1229.2	1229.1	1228.6	1228.0	1227.4	1226.8	1226.2	1226.8	1227.4	1228.0
155°	1272.3	1272.6	1272.8	1272.9	1272.9	1272.9	1272.9	1272.9	1272.9	1272.9	1272.9
157.5°	1310.1	1310.2	1310.2	1310.4	1310.9	1311.4	1311.8	1312.3	1311.8	1311.4	1310.9
160°	1333.8	1333.9	1334.2	1334.5	1334.7	1335.0	1335.2	1335.5	1335.2	1335.0	1334.7
162.5°	1353.4	1353.7	1353.9	1354.4	1355.0	1355.6	1356.2	1356.9	1356.2	1355.6	1355.0
165°	1381.1	1381.6	1382.2	1382.8	1383.5	1384.2	1385.0	1385.7	1385.0	1384.2	1383.5
167.5°	1403.3	1403.3	1403.2	1403.7	1404.7	1405.8	1406.8	1407.8	1406.8	1405.8	1404.7
170°	1415.4	1415.1	1414.9	1415.4	1416.6	1417.9	1419.1	1420.3	1419.1	1417.9	1416.6
172.5°	1424.7	1424.7	1424.6	1425.1	1426.2	1427.2	1428.2	1429.3	1428.2	1427.2	1426.2
175°	1435.4	1435.6	1435.8	1436.6	1437.9	1439.1	1440.3	1441.6	1440.3	1439.1	1437.9
177.5°	1441.1	1441.1	1441.1	1441.6	1442.6	1443.6	1444.6	1445.5	1444.6	1443.6	1442.6
180°	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8



TEST NUMBER: P333088-935

CATALOG NUMBER: S124RDIW-S1020D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3
2.5°	1450.6	1445.9	1439.7	1432.5	1424.0	1416.3	1413.1	1415.9	1417.3	1413.5	1413.1
5°	1406.5	1391.6	1379.7	1361.8	1347.6	1335.7	1327.3	1323.8	1324.9	1315.4	1313.0
7.5°	1356.8	1339.2	1319.7	1298.5	1278.8	1261.3	1252.1	1247.1	1237.0	1232.7	1225.5
10°	1324.9	1301.1	1282.1	1257.1	1234.5	1213.7	1203.5	1195.2	1185.1	1180.3	1170.2
12.5°	1292.1	1264.5	1243.5	1217.5	1194.5	1169.3	1159.7	1144.3	1128.4	1118.4	1105.4
15°	1245.8	1212.5	1186.9	1155.9	1128.5	1099.9	1074.4	1045.8	1035.1	1012.4	999.4
17.5°	1191.6	1157.8	1126.1	1084.6	1042.3	1006.9	979.6	952.2	935.8	921.4	914.7
20°	1155.9	1125.0	1080.9	1032.7	985.7	946.4	924.4	906.5	888.6	878.6	871.4
22.5°	1122.1	1082.5	1031.4	979.4	932.4	901.6	883.0	864.6	850.1	840.4	831.0
25°	1065.4	1013.7	959.5	900.0	867.8	841.0	820.8	805.9	797.0	784.5	779.7
27.5°	1007.2	944.5	884.8	844.7	811.2	786.8	769.1	757.9	746.7	738.7	732.5
30°	962.4	898.8	845.2	807.1	773.2	752.9	738.7	725.6	716.6	710.1	705.3
32.5°	918.2	854.5	809.5	768.5	741.8	722.0	706.8	697.0	690.0	681.5	678.6
35°	854.1	797.5	758.3	721.4	694.1	676.1	664.3	654.1	648.2	645.8	644.0
37.5°	792.6	746.3	704.0	673.8	649.4	635.3	621.3	616.3	612.3	608.0	609.8
40°	753.5	710.1	672.6	640.4	620.8	605.4	597.0	591.1	587.5	587.5	587.5
42.5°	719.7	677.3	640.7	611.9	592.2	579.1	569.9	564.8	563.7	563.2	566.0
45°	667.3	627.9	591.1	567.2	550.6	537.4	532.1	528.0	528.0	530.4	530.9
47.5°	615.2	578.4	548.8	522.1	506.9	498.7	494.0	491.9	492.1	494.5	497.2
50°	583.3	547.0	517.8	494.0	479.7	472.0	467.9	466.7	467.9	467.9	472.0
52.5°	548.5	516.1	487.3	467.4	451.2	443.9	441.6	440.0	440.7	442.6	444.4
55°	497.6	468.5	441.1	422.0	410.1	405.4	400.0	400.5	399.4	400.5	400.5
57.5°	446.5	420.3	394.9	379.8	369.3	362.4	356.5	358.2	356.5	356.2	355.2
60°	413.7	385.1	364.9	351.2	339.2	333.3	328.0	329.2	327.4	326.1	323.8
62.5°	378.0	354.1	334.8	321.7	312.1	305.2	299.9	298.7	294.5	290.5	285.2
65°	326.1	306.5	289.3	276.8	267.9	262.5	258.3	254.8	245.8	236.3	231.5
67.5°	275.9	261.7	245.6	235.0	227.7	220.7	212.8	206.6	198.3	193.1	190.1
70°	243.4	229.7	216.0	206.0	198.2	191.7	182.7	178.6	172.6	170.2	167.3
72.5°	212.5	199.8	187.0	177.9	169.6	164.5	157.5	153.3	150.7	149.7	146.8
75°	165.5	155.3	145.9	137.5	131.0	127.3	124.4	121.4	120.2	114.9	111.9
77.5°	120.7	114.1	108.1	102.1	97.5	95.1	89.4	85.9	83.9	81.5	80.8
80°	94.0	89.3	83.3	79.7	73.2	70.9	68.4	67.8	67.2	66.6	66.0
82.5°	70.7	66.0	60.0	57.9	56.1	54.7	53.2	52.6	52.0	52.3	52.3
85°	35.7	33.3	33.3	32.7	32.1	31.5	30.9	30.9	30.4	30.9	30.4
87.5°	14.7	14.7	15.2	14.6	15.5	15.8	15.7	16.0	16.8	16.1	16.3
90°	14.3	16.6	18.6	20.6	22.6	24.5	26.1	27.6	29.0	30.5	31.5
92.5°	36.4	38.7	40.0	41.4	42.8	44.3	45.1	46.0	46.9	47.8	48.4
95°	75.9	77.9	79.6	81.4	83.1	84.9	85.6	86.4	87.1	87.8	88.3
97.5°	124.2	126.1	128.1	130.2	132.2	134.2	135.1	136.0	136.9	137.8	138.3
100°	160.3	161.9	164.1	166.3	168.6	170.8	171.3	171.9	172.4	172.8	173.1
102.5°	199.0	200.2	202.2	204.3	206.3	208.4	209.1	209.7	210.4	211.1	211.5
105°	261.1	261.7	262.8	263.8	264.8	265.8	266.5	267.3	268.0	268.7	269.5
107.5°	327.3	327.4	327.6	327.8	328.0	328.0	328.7	329.4	330.1	330.9	331.1
110°	372.7	372.8	372.6	372.3	372.1	371.9	371.3	370.8	370.3	369.9	370.0



TEST NUMBER: P333088-935

CATALOG NUMBER: S124RDIW-S1020D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	417.6	417.4	417.0	416.5	416.0	415.6	415.5	415.4	415.3	415.2	415.3
115°	486.8	486.6	486.1	485.6	485.1	484.6	484.4	484.1	483.9	483.6	483.4
117.5°	553.3	553.2	552.8	552.5	552.2	551.8	551.0	550.2	549.3	548.5	547.8
120°	600.2	600.4	599.6	598.9	598.1	597.4	596.2	595.0	593.7	592.5	592.0
122.5°	643.4	643.4	643.1	642.7	642.4	642.0	641.2	640.3	639.6	638.7	637.8
125°	709.0	708.9	708.7	708.4	708.2	707.9	707.4	707.0	706.5	705.9	705.4
127.5°	773.0	773.2	772.7	772.4	772.0	771.5	771.1	770.6	770.1	769.6	769.1
130°	815.9	816.2	816.2	816.2	816.2	816.2	815.7	815.3	814.8	814.2	813.6
132.5°	858.8	859.0	858.8	858.6	858.4	858.2	857.7	857.2	856.8	856.3	855.8
135°	920.5	921.2	921.2	921.2	921.2	921.2	920.8	920.2	919.7	919.2	918.6
137.5°	980.2	980.9	981.2	981.6	982.0	982.4	981.7	981.1	980.5	979.8	979.6
140°	1021.5	1021.7	1021.7	1021.7	1021.7	1021.7	1021.5	1021.2	1021.0	1020.7	1020.5
142.5°	1059.9	1060.0	1059.8	1059.6	1059.5	1059.2	1059.2	1059.1	1059.1	1059.0	1058.9
145°	1115.0	1115.6	1115.9	1116.1	1116.4	1116.6	1116.4	1116.1	1115.9	1115.6	1115.2
147.5°	1168.5	1169.0	1168.8	1168.6	1168.4	1168.2	1168.0	1167.8	1167.6	1167.4	1167.2
150°	1199.9	1200.3	1200.3	1200.3	1200.3	1200.3	1200.3	1200.3	1200.3	1200.3	1200.2
152.5°	1228.6	1229.1	1229.2	1229.4	1229.7	1229.9	1230.5	1231.1	1231.7	1232.3	1232.2
155°	1272.9	1272.8	1272.6	1272.3	1272.0	1271.9	1272.8	1273.8	1274.8	1275.8	1275.8
157.5°	1310.4	1310.2	1310.2	1310.1	1310.1	1310.0	1310.8	1311.5	1312.3	1313.0	1312.9
160°	1334.5	1334.2	1333.9	1333.8	1333.5	1333.3	1333.9	1334.7	1335.5	1336.2	1335.9
162.5°	1354.4	1353.9	1353.7	1353.4	1353.1	1352.9	1354.3	1355.6	1356.9	1358.2	1358.3
165°	1382.8	1382.2	1381.6	1381.1	1380.6	1380.1	1381.6	1383.1	1384.6	1386.1	1386.4
167.5°	1403.7	1403.2	1403.3	1403.3	1403.3	1403.3	1404.9	1406.4	1407.8	1409.3	1409.3
170°	1415.4	1414.9	1415.1	1415.4	1415.7	1415.8	1417.4	1418.8	1420.3	1421.9	1421.7
172.5°	1425.1	1424.6	1424.7	1424.7	1424.8	1424.8	1426.5	1428.1	1429.9	1431.6	1431.5
175°	1436.6	1435.8	1435.6	1435.4	1435.1	1434.9	1436.6	1438.3	1440.0	1441.8	1441.8
177.5°	1441.6	1441.1	1441.1	1441.1	1441.1	1441.1	1442.5	1443.9	1445.3	1446.7	1446.6
180°	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8



TEST NUMBER: P333088-935

CATALOG NUMBER: S124RDIW-S1020D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3
2.5°	1410.1	1411.1	1407.8	1406.9	1407.8	1411.1	1410.1	1413.1	1413.5	1417.3	1415.9
5°	1308.3	1307.1	1304.1	1304.7	1304.1	1307.1	1308.3	1313.0	1315.4	1324.9	1323.8
7.5°	1221.2	1216.5	1217.8	1213.1	1217.8	1216.5	1221.2	1225.5	1232.7	1237.0	1247.1
10°	1167.8	1161.2	1155.9	1151.2	1155.9	1161.2	1167.8	1170.2	1180.3	1185.1	1195.2
12.5°	1094.9	1089.3	1082.1	1083.6	1082.1	1089.3	1094.9	1105.4	1118.4	1128.4	1144.3
15°	991.6	982.7	968.5	970.2	968.5	982.7	991.6	999.4	1012.4	1035.1	1045.8
17.5°	904.1	904.2	897.7	899.2	897.7	904.2	904.1	914.7	921.4	935.8	952.2
20°	858.9	854.7	855.3	853.5	855.3	854.7	858.9	871.4	878.6	888.6	906.5
22.5°	827.5	822.3	818.2	814.5	818.2	822.3	827.5	831.0	840.4	850.1	864.6
25°	774.4	770.8	765.4	764.2	765.4	770.8	774.4	779.7	784.5	797.0	805.9
27.5°	727.7	727.0	724.9	722.1	724.9	727.0	727.7	732.5	738.7	746.7	757.9
30°	700.6	699.4	698.2	696.4	698.2	699.4	700.6	705.3	710.1	716.6	725.6
32.5°	676.3	675.5	674.3	674.5	674.3	675.5	676.3	678.6	681.5	690.0	697.0
35°	641.6	641.0	639.9	639.3	639.9	641.0	641.6	644.0	645.8	648.2	654.1
37.5°	609.2	610.8	610.1	609.9	610.1	610.8	609.2	609.8	608.0	612.3	616.3
40°	586.9	587.5	588.7	588.1	588.7	587.5	586.9	587.5	587.5	587.5	591.1
42.5°	568.3	568.4	570.1	568.1	570.1	568.4	568.3	566.0	563.2	563.7	564.8
45°	535.1	538.6	538.0	538.0	538.0	538.6	535.1	530.9	530.4	528.0	528.0
47.5°	498.8	501.9	502.7	502.6	502.7	501.9	498.8	497.2	494.5	492.1	491.9
50°	475.0	473.8	475.6	475.0	475.6	473.8	475.0	472.0	467.9	467.9	466.7
52.5°	445.9	446.2	446.1	445.5	446.1	446.2	445.9	444.4	442.6	440.7	440.0
55°	401.1	401.7	400.5	401.1	400.5	401.7	401.1	400.5	400.5	399.4	400.5
57.5°	352.6	349.7	350.9	349.5	350.9	349.7	352.6	355.2	356.2	356.5	358.2
60°	317.9	313.1	311.9	309.5	311.9	313.1	317.9	323.8	326.1	327.4	329.2
62.5°	278.8	275.4	271.4	273.3	271.4	275.4	278.8	285.2	290.5	294.5	298.7
65°	226.8	224.4	222.6	225.0	222.6	224.4	226.8	231.5	236.3	245.8	254.8
67.5°	187.7	186.4	186.4	185.2	186.4	186.4	187.7	190.1	193.1	198.3	206.6
70°	167.3	165.5	165.5	164.3	165.5	165.5	167.3	167.3	170.2	172.6	178.6
72.5°	146.3	144.5	145.0	144.3	145.0	144.5	146.3	146.8	149.7	150.7	153.3
75°	108.3	105.4	105.4	106.0	105.4	105.4	108.3	111.9	114.9	120.2	121.4
77.5°	80.8	80.2	81.1	80.0	81.1	80.2	80.8	80.8	81.5	83.9	85.9
80°	66.0	65.4	64.9	66.6	64.9	65.4	66.0	66.0	66.6	67.2	67.8
82.5°	51.3	51.2	51.1	53.3	51.1	51.2	51.3	52.3	52.3	52.0	52.6
85°	30.9	29.8	30.9	29.8	30.9	29.8	30.9	30.4	30.9	30.4	30.9
87.5°	17.4	17.0	16.6	17.1	16.6	17.0	17.4	16.3	16.1	16.8	16.0
90°	32.0	32.5	33.0	33.5	33.0	32.5	32.0	31.5	30.5	29.0	27.6
92.5°	48.6	49.0	49.2	49.6	49.2	49.0	48.6	48.4	47.8	46.9	46.0
95°	88.3	88.3	88.3	88.3	88.3	88.3	88.3	88.3	87.8	87.1	86.4
97.5°	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	137.8	136.9	136.0
100°	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	172.8	172.4	171.9
102.5°	211.8	212.0	212.2	212.4	212.2	212.0	211.8	211.5	211.1	210.4	209.7
105°	270.2	271.0	271.7	272.4	271.7	271.0	270.2	269.5	268.7	268.0	267.3
107.5°	331.1	331.1	331.1	331.0	331.1	331.1	331.1	331.1	330.9	330.1	329.4
110°	370.7	371.4	372.2	373.0	372.2	371.4	370.7	370.0	369.9	370.3	370.8



TEST NUMBER: P333088-935

CATALOG NUMBER: S124RDIW-S1020D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	415.3	415.5	415.7	415.9	415.7	415.5	415.3	415.3	415.2	415.3	415.4
115°	483.1	482.8	482.6	482.4	482.6	482.8	483.1	483.4	483.6	483.9	484.1
117.5°	547.3	546.8	546.3	545.8	546.3	546.8	547.3	547.8	548.5	549.3	550.2
120°	592.5	593.1	593.6	594.0	593.6	593.1	592.5	592.0	592.5	593.7	595.0
122.5°	636.9	636.0	635.2	634.2	635.2	636.0	636.9	637.8	638.7	639.6	640.3
125°	705.0	704.5	704.0	703.4	704.0	704.5	705.0	705.4	705.9	706.5	707.0
127.5°	768.8	768.4	767.9	767.6	767.9	768.4	768.8	769.1	769.6	770.1	770.6
130°	812.5	811.5	810.5	809.5	810.5	811.5	812.5	813.6	814.2	814.8	815.3
132.5°	855.4	855.0	854.6	854.2	854.6	855.0	855.4	855.8	856.3	856.8	857.2
135°	917.8	917.1	916.4	915.6	916.4	917.1	917.8	918.6	919.2	919.7	920.2
137.5°	979.7	979.9	980.0	980.2	980.0	979.9	979.7	979.6	979.8	980.5	981.1
140°	1020.2	1019.9	1019.7	1019.5	1019.7	1019.9	1020.2	1020.5	1020.7	1021.0	1021.2
142.5°	1058.9	1058.9	1058.9	1058.8	1058.9	1058.9	1058.9	1058.9	1059.0	1059.1	1059.1
145°	1114.4	1113.6	1112.9	1112.2	1112.9	1113.6	1114.4	1115.2	1115.6	1115.9	1116.1
147.5°	1166.9	1166.7	1166.5	1166.2	1166.5	1166.7	1166.9	1167.2	1167.4	1167.6	1167.8
150°	1200.0	1199.7	1199.5	1199.3	1199.5	1199.7	1200.0	1200.2	1200.3	1200.3	1200.3
152.5°	1231.6	1230.9	1230.3	1229.6	1230.3	1230.9	1231.6	1232.2	1232.3	1231.7	1231.1
155°	1274.8	1273.8	1272.8	1271.9	1272.8	1273.8	1274.8	1275.8	1275.8	1274.8	1273.8
157.5°	1312.1	1311.2	1310.4	1309.6	1310.4	1311.2	1312.1	1312.9	1313.0	1312.3	1311.5
160°	1334.7	1333.5	1332.2	1331.0	1332.2	1333.5	1334.7	1335.9	1336.2	1335.5	1334.7
162.5°	1357.0	1355.8	1354.6	1353.3	1354.6	1355.8	1357.0	1358.3	1358.2	1356.9	1355.6
165°	1385.3	1384.3	1383.4	1382.3	1383.4	1384.3	1385.3	1386.4	1386.1	1384.6	1383.1
167.5°	1407.7	1406.2	1404.7	1403.2	1404.7	1406.2	1407.7	1409.3	1409.3	1407.8	1406.4
170°	1420.0	1418.2	1416.5	1414.8	1416.5	1418.2	1420.0	1421.7	1421.9	1420.3	1418.8
172.5°	1429.8	1428.1	1426.3	1424.6	1426.3	1428.1	1429.8	1431.5	1431.6	1429.9	1428.1
175°	1440.0	1438.3	1436.6	1434.9	1436.6	1438.3	1440.0	1441.8	1441.8	1440.0	1438.3
177.5°	1445.0	1443.4	1441.8	1440.2	1441.8	1443.4	1445.0	1446.6	1446.7	1445.3	1443.9
180°	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8



TEST NUMBER: P333088-935

CATALOG NUMBER: S124RDIW-S1020D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3
2.5°	1413.1	1416.3	1424.0	1432.5	1439.7	1445.9	1450.6	1457.3	1463.5	1472.1	1480.1
5°	1327.3	1335.7	1347.6	1361.8	1379.7	1391.6	1406.5	1419.6	1438.6	1457.7	1476.1
7.5°	1252.1	1261.3	1278.8	1298.5	1319.7	1339.2	1356.8	1379.9	1405.2	1432.9	1463.9
10°	1203.5	1213.7	1234.5	1257.1	1282.1	1301.1	1324.9	1352.3	1380.9	1414.8	1452.9
12.5°	1159.7	1169.3	1194.5	1217.5	1243.5	1264.5	1292.1	1319.9	1358.1	1394.8	1438.1
15°	1074.4	1099.9	1128.5	1155.9	1186.9	1212.5	1245.8	1274.4	1310.7	1362.4	1411.9
17.5°	979.6	1006.9	1042.3	1084.6	1126.1	1157.8	1191.6	1227.1	1270.3	1323.2	1380.2
20°	924.4	946.4	985.7	1032.7	1080.9	1125.0	1155.9	1195.2	1239.8	1297.0	1355.9
22.5°	883.0	901.6	932.4	979.4	1031.4	1082.5	1122.1	1160.9	1210.3	1267.5	1331.6
25°	820.8	841.0	867.8	900.0	959.5	1013.7	1065.4	1110.1	1162.4	1219.6	1291.0
27.5°	769.1	786.8	811.2	844.7	884.8	944.5	1007.2	1058.2	1111.9	1173.2	1244.7
30°	738.7	752.9	773.2	807.1	845.2	898.8	962.4	1022.0	1076.2	1139.8	1214.3
32.5°	706.8	722.0	741.8	768.5	809.5	854.5	918.2	983.4	1040.9	1106.0	1179.0
35°	664.3	676.1	694.1	721.4	758.3	797.5	854.1	921.4	982.1	1051.7	1121.4
37.5°	621.3	635.3	649.4	673.8	704.0	746.3	792.6	861.3	928.5	992.1	1060.1
40°	597.0	605.4	620.8	640.4	672.6	710.1	753.5	820.8	888.0	951.1	1019.6
42.5°	569.9	579.1	592.2	611.9	640.7	677.3	719.7	777.9	848.1	909.2	971.5
45°	532.1	537.4	550.6	567.2	591.1	627.9	667.3	719.0	785.1	843.4	898.2
47.5°	494.0	498.7	506.9	522.1	548.8	578.4	615.2	661.7	719.6	777.9	824.2
50°	467.9	472.0	479.7	494.0	517.8	547.0	583.3	625.0	676.7	732.7	771.4
52.5°	441.6	443.9	451.2	467.4	487.3	516.1	548.5	586.9	635.3	681.7	720.9
55°	400.0	405.4	410.1	422.0	441.1	468.5	497.6	533.9	571.4	610.7	644.0
57.5°	356.5	362.4	369.3	379.8	394.9	420.3	446.5	476.0	508.0	540.5	568.5
60°	328.0	333.3	339.2	351.2	364.9	385.1	413.7	439.3	463.6	493.4	521.4
62.5°	299.9	305.2	312.1	321.7	334.8	354.1	378.0	400.2	425.6	451.5	472.3
65°	258.3	262.5	267.9	276.8	289.3	306.5	326.1	343.5	366.1	385.1	404.2
67.5°	212.8	220.7	227.7	235.0	245.6	261.7	275.9	292.4	307.7	321.9	339.2
70°	182.7	191.7	198.2	206.0	216.0	229.7	243.4	254.8	267.3	280.9	296.4
72.5°	157.5	164.5	169.6	177.9	187.0	199.8	212.5	221.9	232.0	241.4	256.4
75°	124.4	127.3	131.0	137.5	145.9	155.3	165.5	173.8	179.8	188.1	198.8
77.5°	89.4	95.1	97.5	102.1	108.1	114.1	120.7	127.8	133.5	136.4	144.6
80°	68.4	70.9	73.2	79.7	83.3	89.3	94.0	100.6	103.0	106.0	113.7
82.5°	53.2	54.7	56.1	57.9	60.0	66.0	70.7	74.9	77.2	78.4	84.2
85°	30.9	31.5	32.1	32.7	33.3	33.3	35.7	38.7	42.9	42.9	44.6
87.5°	15.7	15.8	15.5	14.6	15.2	14.7	14.7	14.2	15.1	16.0	16.9
90°	26.1	24.5	22.6	20.6	18.6	16.6	14.3	11.5	8.8	6.1	3.4
92.5°	45.1	44.3	42.8	41.4	40.0	38.7	36.4	33.2	30.1	27.0	23.9
95°	85.6	84.9	83.1	81.4	79.6	77.9	75.9	73.7	71.5	69.2	67.0
97.5°	135.1	134.2	132.2	130.2	128.1	126.1	124.2	122.3	120.6	118.8	117.0
100°	171.3	170.8	168.6	166.3	164.1	161.9	160.3	159.3	158.3	157.3	156.4
102.5°	209.1	208.4	206.3	204.3	202.2	200.2	199.0	198.6	198.2	197.9	197.4
105°	266.5	265.8	264.8	263.8	262.8	261.7	261.1	260.9	260.7	260.5	260.2
107.5°	328.7	328.0	328.0	327.8	327.6	327.4	327.3	326.9	326.7	326.3	326.1
110°	371.3	371.9	372.1	372.3	372.6	372.8	372.7	372.2	371.7	371.2	370.7



TEST NUMBER: P333088-935

CATALOG NUMBER: S124RDIW-S1020D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	415.5	415.6	416.0	416.5	417.0	417.4	417.6	417.5	417.3	417.2	417.2
115°	484.4	484.6	485.1	485.6	486.1	486.6	486.8	486.8	486.8	486.8	486.8
117.5°	551.0	551.8	552.2	552.5	552.8	553.2	553.3	553.1	552.9	552.7	552.5
120°	596.2	597.4	598.1	598.9	599.6	600.4	600.2	599.3	598.2	597.3	596.2
122.5°	641.2	642.0	642.4	642.7	643.1	643.4	643.4	643.0	642.7	642.2	641.8
125°	707.4	707.9	708.2	708.4	708.7	708.9	709.0	709.0	709.0	709.0	709.0
127.5°	771.1	771.5	772.0	772.4	772.7	773.2	773.0	772.2	771.5	770.8	770.0
130°	815.7	816.2	816.2	816.2	816.2	816.2	815.9	815.1	814.4	813.6	812.9
132.5°	857.7	858.2	858.4	858.6	858.8	859.0	858.8	858.3	857.7	857.2	856.7
135°	920.8	921.2	921.2	921.2	921.2	921.2	920.5	918.9	917.5	916.0	914.5
137.5°	981.7	982.4	982.0	981.6	981.2	980.9	980.2	979.6	978.9	978.2	977.5
140°	1021.5	1021.7	1021.7	1021.7	1021.7	1021.7	1021.5	1021.0	1020.5	1019.9	1019.5
142.5°	1059.2	1059.2	1059.5	1059.6	1059.8	1060.0	1059.9	1059.4	1058.9	1058.3	1057.9
145°	1116.4	1116.6	1116.4	1116.1	1115.9	1115.6	1115.0	1114.0	1113.0	1112.1	1111.0
147.5°	1168.0	1168.2	1168.4	1168.6	1168.8	1169.0	1168.5	1167.3	1166.1	1164.9	1163.7
150°	1200.3	1200.3	1200.3	1200.3	1200.3	1200.3	1199.9	1198.9	1197.9	1196.9	1195.9
152.5°	1230.5	1229.9	1229.7	1229.4	1229.2	1229.1	1228.6	1228.0	1227.4	1226.8	1226.2
155°	1272.8	1271.9	1272.0	1272.3	1272.6	1272.8	1272.9	1272.9	1272.9	1272.9	1272.9
157.5°	1310.8	1310.0	1310.1	1310.1	1310.2	1310.2	1310.4	1310.9	1311.4	1311.8	1312.3
160°	1333.9	1333.3	1333.5	1333.8	1333.9	1334.2	1334.5	1334.7	1335.0	1335.2	1335.5
162.5°	1354.3	1352.9	1353.1	1353.4	1353.7	1353.9	1354.4	1355.0	1355.6	1356.2	1356.9
165°	1381.6	1380.1	1380.6	1381.1	1381.6	1382.2	1382.8	1383.5	1384.2	1385.0	1385.7
167.5°	1404.9	1403.3	1403.3	1403.3	1403.3	1403.2	1403.7	1404.7	1405.8	1406.8	1407.8
170°	1417.4	1415.8	1415.7	1415.4	1415.1	1414.9	1415.4	1416.6	1417.9	1419.1	1420.3
172.5°	1426.5	1424.8	1424.8	1424.7	1424.7	1424.6	1425.1	1426.2	1427.2	1428.2	1429.3
175°	1436.6	1434.9	1435.1	1435.4	1435.6	1435.8	1436.6	1437.9	1439.1	1440.3	1441.6
177.5°	1442.5	1441.1	1441.1	1441.1	1441.1	1441.1	1441.6	1442.6	1443.6	1444.6	1445.5
180°	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8



TEST NUMBER: P333088-935

CATALOG NUMBER: S124RDIW-S1020D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3
2.5°	1486.3	1490.6	1495.4	1504.4	1512.1	1515.4	1522.1	1526.8	1525.4	1532.1	1543.5
5°	1492.2	1508.3	1526.7	1545.8	1567.2	1585.0	1599.3	1613.6	1625.0	1638.7	1658.9
7.5°	1491.3	1519.8	1550.9	1585.0	1620.1	1650.5	1678.6	1707.2	1732.5	1760.3	1796.6
10°	1487.5	1525.5	1564.2	1608.9	1653.5	1695.7	1733.9	1769.5	1803.5	1839.8	1885.7
12.5°	1483.2	1527.0	1573.7	1627.5	1683.0	1733.9	1778.7	1830.1	1872.5	1919.3	1972.3
15°	1464.2	1523.1	1586.8	1656.5	1723.1	1791.6	1852.9	1916.0	1974.9	2030.8	2097.6
17.5°	1442.5	1510.5	1585.6	1667.9	1748.0	1831.3	1903.9	1983.5	2043.8	2118.8	2180.7
20°	1425.0	1498.1	1578.5	1670.8	1761.9	1854.1	1934.4	2015.4	2083.3	2158.9	2237.4
22.5°	1403.5	1483.8	1570.9	1666.5	1761.9	1862.7	1951.5	2032.0	2116.1	2201.2	2282.2
25°	1369.0	1452.3	1544.5	1649.3	1758.9	1861.8	1957.1	2057.0	2147.5	2239.8	2312.4
27.5°	1326.6	1414.1	1511.4	1619.5	1731.8	1837.3	1949.5	2056.0	2147.1	2235.8	2299.2
30°	1292.8	1385.1	1478.5	1588.0	1704.7	1817.7	1938.0	2044.5	2140.4	2220.2	2255.8
32.5°	1258.0	1345.6	1441.8	1552.8	1672.3	1794.0	1913.2	2022.1	2110.8	2158.7	2159.6
35°	1197.6	1279.7	1379.7	1488.7	1611.3	1743.4	1864.2	1971.3	2025.5	2029.6	1971.3
37.5°	1131.6	1206.9	1301.4	1410.4	1544.7	1676.1	1799.6	1871.0	1889.1	1828.5	1720.6
40°	1084.5	1154.1	1245.2	1357.1	1490.4	1626.1	1738.6	1791.0	1771.9	1673.7	1553.5
42.5°	1034.9	1099.8	1187.6	1298.0	1431.8	1569.0	1664.8	1692.9	1642.4	1529.0	1388.3
45°	954.2	1013.7	1100.5	1211.9	1340.4	1469.0	1541.6	1527.3	1443.4	1308.9	1151.2
47.5°	870.0	927.5	1005.6	1108.6	1240.3	1351.3	1400.4	1357.4	1237.9	1089.9	961.7
50°	814.2	873.1	945.2	1043.4	1163.6	1270.7	1302.3	1236.8	1104.1	961.8	844.0
52.5°	759.5	809.9	880.5	975.3	1090.3	1180.8	1197.6	1122.1	985.1	857.6	753.0
55°	676.1	722.0	781.5	870.8	970.2	1047.0	1038.0	941.1	816.7	707.7	625.6
57.5°	595.6	630.1	685.1	768.8	856.0	907.6	874.9	792.2	676.3	587.1	517.8
60°	542.3	574.4	625.6	698.8	775.6	804.7	777.3	687.5	595.8	514.3	455.9
62.5°	491.8	520.1	564.1	632.1	694.1	711.4	682.1	603.6	521.1	451.4	403.1
65°	418.4	444.6	482.2	530.4	573.2	581.5	562.5	482.2	419.7	361.3	328.0
67.5°	351.9	369.0	398.3	440.0	462.7	467.6	430.8	380.3	325.2	289.4	264.2
70°	307.1	319.0	346.4	369.0	387.4	388.1	354.1	313.7	271.4	242.3	223.8
72.5°	263.8	275.3	295.9	311.4	325.5	321.0	289.9	258.0	223.8	201.8	188.1
75°	203.5	213.7	224.4	231.5	231.5	225.6	202.9	179.2	159.5	146.5	142.2
77.5°	148.0	156.3	159.9	158.8	156.7	147.4	133.1	117.5	110.5	104.3	101.2
80°	116.1	119.7	120.8	117.9	114.3	103.6	94.0	87.5	80.9	78.6	77.4
82.5°	86.1	89.2	86.1	86.9	79.0	70.3	65.0	62.8	60.0	59.1	57.9
85°	45.8	45.2	44.1	41.1	35.7	34.5	33.9	33.3	32.1	32.7	31.5
87.5°	17.0	16.0	14.7	14.7	15.2	14.6	15.6	15.9	16.4	16.2	17.4
90°	6.1	8.8	11.5	14.3	16.6	18.6	20.6	22.6	24.5	26.1	27.6
92.5°	27.0	30.1	33.2	36.4	38.7	40.0	41.4	42.8	44.3	45.1	46.0
95°	69.2	71.5	73.7	75.9	77.9	79.6	81.4	83.1	84.9	85.6	86.4
97.5°	118.8	120.6	122.3	124.2	126.1	128.1	130.2	132.2	134.2	135.1	136.0
100°	157.3	158.3	159.3	160.3	161.9	164.1	166.3	168.6	170.8	171.3	171.9
102.5°	197.9	198.2	198.6	199.0	200.2	202.2	204.3	206.3	208.4	209.1	209.7
105°	260.5	260.7	260.9	261.1	261.7	262.8	263.8	264.8	265.8	266.5	267.3
107.5°	326.3	326.7	326.9	327.3	327.4	327.6	327.8	328.0	328.0	328.7	329.4
110°	371.2	371.7	372.2	372.7	372.8	372.6	372.3	372.1	371.9	371.3	370.8





TEST NUMBER: P333088-935

CATALOG NUMBER: S124RDIW-S1020D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	417.2	417.3	417.5	417.6	417.4	417.0	416.5	416.0	415.6	415.5	415.4
115°	486.8	486.8	486.8	486.8	486.6	486.1	485.6	485.1	484.6	484.4	484.1
117.5°	552.7	552.9	553.1	553.3	553.2	552.8	552.5	552.2	551.8	551.0	550.2
120°	597.3	598.2	599.3	600.2	600.4	599.6	598.9	598.1	597.4	596.2	595.0
122.5°	642.2	642.7	643.0	643.4	643.4	643.1	642.7	642.4	642.0	641.2	640.3
125°	709.0	709.0	709.0	709.0	708.9	708.7	708.4	708.2	707.9	707.4	707.0
127.5°	770.8	771.5	772.2	773.0	773.2	772.7	772.4	772.0	771.5	771.1	770.6
130°	813.6	814.4	815.1	815.9	816.2	816.2	816.2	816.2	816.2	815.7	815.3
132.5°	857.2	857.7	858.3	858.8	859.0	858.8	858.6	858.4	858.2	857.7	857.2
135°	916.0	917.5	918.9	920.5	921.2	921.2	921.2	921.2	921.2	920.8	920.2
137.5°	978.2	978.9	979.6	980.2	980.9	981.2	981.6	982.0	982.4	981.7	981.1
140°	1019.9	1020.5	1021.0	1021.5	1021.7	1021.7	1021.7	1021.7	1021.7	1021.5	1021.2
142.5°	1058.3	1058.9	1059.4	1059.9	1060.0	1059.8	1059.6	1059.5	1059.2	1059.2	1059.1
145°	1112.1	1113.0	1114.0	1115.0	1115.6	1115.9	1116.1	1116.4	1116.6	1116.4	1116.1
147.5°	1164.9	1166.1	1167.3	1168.5	1169.0	1168.8	1168.6	1168.4	1168.2	1168.0	1167.8
150°	1196.9	1197.9	1198.9	1199.9	1200.3	1200.3	1200.3	1200.3	1200.3	1200.3	1200.3
152.5°	1226.8	1227.4	1228.0	1228.6	1229.1	1229.2	1229.4	1229.7	1229.9	1230.5	1231.1
155°	1272.9	1272.9	1272.9	1272.9	1272.8	1272.6	1272.3	1272.0	1271.9	1272.8	1273.8
157.5°	1311.8	1311.4	1310.9	1310.4	1310.2	1310.2	1310.1	1310.1	1310.0	1310.8	1311.5
160°	1335.2	1335.0	1334.7	1334.5	1334.2	1333.9	1333.8	1333.5	1333.3	1333.9	1334.7
162.5°	1356.2	1355.6	1355.0	1354.4	1353.9	1353.7	1353.4	1353.1	1352.9	1354.3	1355.6
165°	1385.0	1384.2	1383.5	1382.8	1382.2	1381.6	1381.1	1380.6	1380.1	1381.6	1383.1
167.5°	1406.8	1405.8	1404.7	1403.7	1403.2	1403.3	1403.3	1403.3	1403.3	1404.9	1406.4
170°	1419.1	1417.9	1416.6	1415.4	1414.9	1415.1	1415.4	1415.7	1415.8	1417.4	1418.8
172.5°	1428.2	1427.2	1426.2	1425.1	1424.6	1424.7	1424.7	1424.8	1424.8	1426.5	1428.1
175°	1440.3	1439.1	1437.9	1436.6	1435.8	1435.6	1435.4	1435.1	1434.9	1436.6	1438.3
177.5°	1444.6	1443.6	1442.6	1441.6	1441.1	1441.1	1441.1	1441.1	1441.1	1442.5	1443.9
180°	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8



TEST NUMBER: P333088-935

CATALOG NUMBER: S124RDIW-S1020D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3
2.5°	1549.7	1551.6	1553.1	1557.8	1558.2	1562.5	1558.2
5°	1677.9	1686.3	1699.4	1712.4	1713.6	1721.9	1707.1
7.5°	1821.7	1841.0	1853.0	1874.2	1882.6	1887.7	1879.2
10°	1920.7	1938.6	1970.1	1985.6	2001.1	2003.5	1996.3
12.5°	2016.5	2044.8	2069.7	2098.9	2098.3	2119.2	2111.6
15°	2144.0	2173.2	2207.6	2240.4	2252.3	2252.3	2261.8
17.5°	2234.9	2288.4	2324.1	2349.8	2377.9	2382.7	2379.5
20°	2296.4	2354.1	2392.2	2425.5	2444.6	2449.9	2449.9
22.5°	2342.0	2391.2	2428.4	2458.3	2474.1	2480.4	2478.5
25°	2373.7	2416.0	2438.6	2447.5	2451.7	2450.5	2439.2
27.5°	2330.4	2328.5	2314.2	2286.8	2266.2	2253.8	2239.5
30°	2247.6	2216.6	2180.8	2141.6	2091.0	2052.3	2040.4
32.5°	2124.2	2054.7	1994.2	1928.7	1874.3	1835.7	1819.5
35°	1885.7	1775.6	1685.7	1607.1	1550.0	1514.2	1502.4
37.5°	1602.6	1496.0	1384.7	1308.5	1261.1	1225.0	1211.6
40°	1422.5	1306.5	1209.4	1138.1	1089.3	1054.1	1053.5
42.5°	1258.3	1147.5	1056.2	1004.7	952.1	928.8	928.8
45°	1030.3	941.6	864.3	823.8	792.2	773.2	767.8
47.5°	853.1	779.7	728.1	695.9	670.2	658.1	650.2
50°	753.5	689.2	648.2	620.2	605.9	590.5	589.3
52.5°	670.7	618.8	586.8	564.0	546.0	536.7	536.9
55°	563.7	522.6	500.0	482.7	468.5	461.3	458.3
57.5°	474.8	444.0	427.6	411.7	405.7	400.1	398.6
60°	419.7	398.8	383.3	370.8	361.9	360.1	359.5
62.5°	373.9	352.1	341.4	331.7	325.2	322.4	321.4
65°	308.3	292.2	282.8	275.0	272.6	268.5	267.9
67.5°	248.6	238.9	232.6	227.2	224.0	223.8	223.8
70°	211.9	206.6	201.2	198.2	196.4	195.2	195.2
72.5°	180.5	176.5	172.1	170.6	170.2	169.0	168.6
75°	137.5	133.4	133.9	131.0	128.5	125.6	123.8
77.5°	97.5	94.5	93.9	93.6	91.5	91.2	92.1
80°	75.6	72.6	72.0	72.6	72.0	70.3	70.3
82.5°	57.5	55.0	54.4	54.1	53.5	54.1	53.1
85°	30.9	29.8	29.8	29.8	30.9	30.4	29.8
87.5°	16.8	16.6	17.2	16.9	17.0	16.6	17.1
90°	29.0	30.5	31.5	32.0	32.5	33.0	33.5
92.5°	46.9	47.8	48.4	48.6	49.0	49.2	49.6
95°	87.1	87.8	88.3	88.3	88.3	88.3	88.3
97.5°	136.9	137.8	138.3	138.3	138.3	138.3	138.3
100°	172.4	172.8	173.1	173.1	173.1	173.1	173.1
102.5°	210.4	211.1	211.5	211.8	212.0	212.2	212.4
105°	268.0	268.7	269.5	270.2	271.0	271.7	272.4
107.5°	330.1	330.9	331.1	331.1	331.1	331.1	331.0
110°	370.3	369.9	370.0	370.7	371.4	372.2	373.0



TEST NUMBER: P333088-935

CATALOG NUMBER: S124RDIW-S1020D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	415.3	415.2	415.3	415.3	415.5	415.7	415.9
115°	483.9	483.6	483.4	483.1	482.8	482.6	482.4
117.5°	549.3	548.5	547.8	547.3	546.8	546.3	545.8
120°	593.7	592.5	592.0	592.5	593.1	593.6	594.0
122.5°	639.6	638.7	637.8	636.9	636.0	635.2	634.2
125°	706.5	705.9	705.4	705.0	704.5	704.0	703.4
127.5°	770.1	769.6	769.1	768.8	768.4	767.9	767.6
130°	814.8	814.2	813.6	812.5	811.5	810.5	809.5
132.5°	856.8	856.3	855.8	855.4	855.0	854.6	854.2
135°	919.7	919.2	918.6	917.8	917.1	916.4	915.6
137.5°	980.5	979.8	979.6	979.7	979.9	980.0	980.2
140°	1021.0	1020.7	1020.5	1020.2	1019.9	1019.7	1019.5
142.5°	1059.1	1059.0	1058.9	1058.9	1058.9	1058.9	1058.8
145°	1115.9	1115.6	1115.2	1114.4	1113.6	1112.9	1112.2
147.5°	1167.6	1167.4	1167.2	1166.9	1166.7	1166.5	1166.2
150°	1200.3	1200.3	1200.2	1200.0	1199.7	1199.5	1199.3
152.5°	1231.7	1232.3	1232.2	1231.6	1230.9	1230.3	1229.6
155°	1274.8	1275.8	1275.8	1274.8	1273.8	1272.8	1271.9
157.5°	1312.3	1313.0	1312.9	1312.1	1311.2	1310.4	1309.6
160°	1335.5	1336.2	1335.9	1334.7	1333.5	1332.2	1331.0
162.5°	1356.9	1358.2	1358.3	1357.0	1355.8	1354.6	1353.3
165°	1384.6	1386.1	1386.4	1385.3	1384.3	1383.4	1382.3
167.5°	1407.8	1409.3	1409.3	1407.7	1406.2	1404.7	1403.2
170°	1420.3	1421.9	1421.7	1420.0	1418.2	1416.5	1414.8
172.5°	1429.9	1431.6	1431.5	1429.8	1428.1	1426.3	1424.6
175°	1440.0	1441.8	1441.8	1440.0	1438.3	1436.6	1434.9
177.5°	1445.3	1446.7	1446.6	1445.0	1443.4	1441.8	1440.2
180°	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8

(END OF REPORT)