

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333089-935

Luminaire Tested: **S124RDIW-S1020D1340U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333089-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1020D1340U935-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8215.0 lumens
Efficiency: N/A
Efficacy: 117.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333089-935

CATALOG NUMBER: S124RDIW-S1020D1340U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333089-935

CATALOG NUMBER: S124RDIW-S1020D1340U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	50	50	50	44
1	97	92	89	85	88	85	82	79	70	68	66	57	56	54	45	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	46	40	38	37	32
3	81	71	64	59	73	66	59	54	55	50	46	45	41	39	35	33	31	27
4	74	63	56	50	67	58	51	46	49	44	40	40	36	33	32	29	27	23
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	29	26	24	20
6	62	51	43	37	57	47	40	35	39	34	30	33	29	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	24	21	19	16
8	54	41	34	29	49	38	32	27	33	27	24	27	23	20	22	19	17	14
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13
10	47	35	28	23	43	32	26	22	28	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12551	12551	12551
5°	12580	12426	12503
10°	12500	12276	12276
15°	12357	12018	11929
20°	12160	11679	11465
25°	11908	11282	10996
30°	11663	10864	10409
35°	11392	10430	9819
40°	11065	9936	9183
45°	10764	9445	8535
50°	10420	8881	7850
55°	10054	8294	7104
60°	9649	7650	6344
65°	9278	6844	5593
70°	8738	5958	4749
75°	8057	4938	3862
80°	7029	3761	3543
85°	5956	3418	3196



TEST NUMBER: P333089-935

CATALOG NUMBER: S124RDIW-S1020D1340U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.0	1.8
10°-20°	407.3	5.0
20°-30°	588.1	7.2
30°-40°	666.6	8.1
40°-50°	643.7	7.8
50°-60°	535.3	6.5
60°-70°	369.6	4.5
70°-80°	187.4	2.3
80°-90°	52.4	0.6
90°-100°	51.1	0.6
100°-110°	325.6	4.0
110°-120°	622.9	7.6
120°-130°	790.7	9.6
130°-140°	846.0	10.3
140°-150°	791.1	9.6
150°-160°	638.0	7.8
160°-170°	411.5	5.0
170°-180°	141.8	1.7
0°-30°	1141.4	13.9
0°-40°	1808.0	22.0
0°-60°	2987.0	36.4
0°-90°	3596.3	43.8
90°-120°	999.5	12.2
90°-150°	3427.4	41.7
90°-180°	4619.0	56.2
0°-180°	8215.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1555	1555	1555	1555	1555	
5°	1552	1547	1533	1544	1543	147
15°	1478	1467	1438	1435	1427	416
25°	1337	1314	1267	1247	1234	616
35°	1156	1117	1058	1019	996	722
45°	943	897	827	771	748	727
55°	714	665	589	530	505	639
65°	486	433	358	309	293	479
75°	258	214	158	132	124	273
85°	64	42	37	35	34	72
90°	3	15	24	31	34	6
95°	61	26	24	31	32	79
105°	336	343	348	356	318	352
115°	628	631	630	632	632	617
125°	882	886	884	888	889	787
135°	1094	1094	1098	1100	1102	843
145°	1262	1265	1265	1266	1269	788
155°	1384	1385	1382	1385	1383	638
165°	1460	1454	1454	1462	1453	412
175°	1493	1487	1488	1496	1484	142
180°	1493	1493	1493	1493	1493	



TEST NUMBER: P333089-935

CATALOG NUMBER: S124RDIW-S1020D1340U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7
2.5°	1558.5	1557.6	1556.8	1556.0	1555.1	1553.5	1551.2	1548.9	1546.5	1544.2	1546.5
5°	1552.3	1551.3	1550.2	1549.1	1548.1	1545.9	1542.8	1539.6	1536.5	1533.3	1535.9
7.5°	1538.3	1537.1	1536.0	1534.9	1533.8	1531.2	1527.1	1522.9	1518.8	1514.7	1516.4
10°	1524.9	1523.6	1522.2	1521.0	1519.7	1516.6	1511.8	1507.1	1502.3	1497.5	1498.6
12.5°	1507.8	1506.2	1504.7	1503.2	1501.7	1498.1	1492.5	1486.9	1481.3	1475.7	1476.3
15°	1478.5	1476.1	1473.8	1471.4	1469.0	1464.5	1457.8	1451.2	1444.7	1438.0	1437.5
17.5°	1443.0	1439.6	1436.1	1432.7	1429.3	1423.6	1415.7	1407.7	1399.8	1391.8	1390.3
20°	1415.4	1412.0	1408.5	1405.1	1401.6	1395.4	1386.5	1377.4	1368.5	1359.4	1357.4
22.5°	1384.9	1381.0	1377.2	1373.4	1369.5	1362.7	1353.1	1343.5	1333.9	1324.2	1321.0
25°	1336.9	1332.1	1327.3	1322.6	1317.8	1310.0	1299.2	1288.3	1277.5	1266.6	1262.1
27.5°	1286.3	1280.4	1274.5	1268.4	1262.5	1253.7	1242.1	1230.5	1218.9	1207.3	1201.8
30°	1251.1	1244.5	1237.9	1231.3	1224.7	1215.1	1202.7	1190.2	1177.8	1165.4	1158.8
32.5°	1214.0	1206.5	1199.0	1191.6	1184.1	1174.0	1161.1	1148.3	1135.4	1122.6	1114.9
35°	1155.9	1147.5	1138.9	1130.5	1122.1	1111.2	1097.9	1084.8	1071.5	1058.3	1049.3
37.5°	1093.7	1085.0	1076.3	1067.6	1058.9	1047.1	1032.5	1017.9	1003.2	988.5	978.4
40°	1050.0	1041.2	1032.5	1023.7	1015.0	1003.2	988.1	972.9	957.9	942.8	931.7
42.5°	1008.1	998.9	989.7	980.6	971.5	959.0	943.3	927.6	911.9	896.1	884.8
45°	942.8	933.1	923.3	913.4	903.6	890.8	874.9	859.1	843.2	827.3	814.4
47.5°	875.5	865.3	855.2	845.2	835.0	821.7	805.2	788.7	772.1	755.7	742.3
50°	829.7	819.4	809.1	798.7	788.4	774.8	757.9	741.0	724.0	707.1	693.9
52.5°	783.1	772.9	762.8	752.8	742.6	728.9	711.5	694.2	676.8	659.5	646.1
55°	714.3	703.7	693.1	682.5	671.9	658.1	640.8	623.6	606.5	589.3	575.5
57.5°	646.2	635.2	624.1	613.1	602.2	588.1	571.3	554.3	537.4	520.5	506.5
60°	597.6	587.0	576.4	565.8	555.3	541.5	524.6	507.6	490.7	473.8	460.0
62.5°	553.8	542.8	531.8	520.7	509.8	495.6	478.2	460.9	443.5	426.2	413.5
65°	485.7	474.3	463.0	451.6	440.2	426.0	409.1	392.2	375.2	358.3	347.0
67.5°	415.0	404.1	393.2	382.3	371.3	358.1	342.3	326.7	310.9	295.2	285.4
70°	370.2	359.1	348.0	336.9	325.8	312.7	297.6	282.5	267.4	252.4	243.7
72.5°	322.6	312.5	302.5	292.5	282.4	270.3	256.1	241.8	227.6	213.4	205.9
75°	258.3	248.6	238.8	228.9	219.2	208.0	195.6	183.2	170.7	158.3	152.2
77.5°	193.1	184.8	176.5	168.2	159.9	150.7	140.6	130.6	120.5	110.5	106.9
80°	151.2	143.5	135.9	128.2	120.5	112.7	104.8	96.9	88.9	80.9	80.2
82.5°	115.0	108.0	100.9	93.8	86.9	81.0	76.5	72.0	67.4	62.9	62.3
85°	64.3	59.0	53.7	48.4	43.1	40.0	39.3	38.5	37.7	36.9	36.3
87.5°	22.6	21.4	20.3	19.1	18.0	17.5	17.7	17.9	18.1	18.3	18.3
90°	3.4	6.1	8.8	11.5	14.3	16.6	18.6	20.6	22.6	24.5	26.1
92.5°	14.0	14.2	14.4	14.6	14.6	15.8	17.7	19.7	21.7	23.7	25.1
95°	61.4	53.0	44.5	36.1	27.6	23.6	23.8	24.1	24.3	24.5	26.1
97.5°	130.4	135.7	140.9	146.2	151.4	140.3	112.5	84.9	57.2	29.4	29.6
100°	183.1	187.6	192.1	196.6	201.0	186.1	151.9	117.6	83.3	49.2	44.9
102.5°	242.1	245.4	248.7	251.9	255.2	254.6	250.1	245.7	241.3	236.8	191.2
105°	336.1	337.6	339.1	340.6	342.1	343.5	344.7	345.9	347.2	348.4	350.7
107.5°	423.4	424.2	425.0	425.7	426.5	427.7	429.4	431.0	432.7	434.5	435.5
110°	482.4	483.2	484.0	484.7	485.4	486.6	488.0	489.5	491.0	492.5	493.0



TEST NUMBER: P333089-935

CATALOG NUMBER: S124RDIW-S1020D1340U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	539.6	541.0	542.3	543.6	545.0	546.0	546.7	547.4	548.1	548.8	548.7
115°	627.6	628.4	629.1	629.8	630.6	630.9	630.6	630.3	630.1	629.8	630.3
117.5°	706.9	707.9	708.9	709.9	710.8	711.6	712.2	712.7	713.3	713.9	713.8
120°	760.5	761.5	762.5	763.5	764.5	764.8	764.7	764.4	764.1	763.9	764.4
122.5°	810.5	811.1	811.8	812.4	813.0	813.4	813.7	814.1	814.4	814.8	815.1
125°	882.3	883.2	884.2	885.2	886.2	886.5	886.0	885.5	884.9	884.5	885.2
127.5°	950.1	950.4	950.6	950.9	951.1	951.8	953.0	954.1	955.3	956.4	956.2
130°	993.9	994.2	994.5	994.6	994.9	995.4	996.2	996.9	997.6	998.4	998.7
132.5°	1034.1	1034.6	1035.0	1035.4	1035.9	1036.6	1037.6	1038.5	1039.4	1040.3	1040.6
135°	1094.4	1094.2	1093.9	1093.7	1093.5	1093.8	1094.8	1095.8	1096.8	1097.8	1098.3
137.5°	1147.8	1147.9	1148.0	1148.1	1148.2	1148.8	1149.9	1151.0	1152.1	1153.1	1153.7
140°	1182.7	1183.2	1183.6	1184.1	1184.6	1185.2	1185.6	1186.1	1186.6	1187.1	1187.8
142.5°	1213.9	1214.8	1215.7	1216.6	1217.5	1218.1	1218.4	1218.7	1219.0	1219.3	1219.9
145°	1262.0	1262.7	1263.4	1264.2	1264.9	1265.3	1265.3	1265.3	1265.3	1265.3	1265.6
147.5°	1300.1	1301.5	1303.0	1304.3	1305.7	1306.3	1306.1	1305.8	1305.5	1305.3	1305.4
150°	1327.8	1328.9	1329.8	1330.8	1331.8	1332.1	1332.0	1331.7	1331.5	1331.2	1331.2
152.5°	1351.1	1351.9	1352.6	1353.4	1354.3	1354.4	1354.0	1353.5	1353.1	1352.6	1353.1
155°	1383.7	1383.9	1384.1	1384.4	1384.7	1384.4	1383.7	1382.9	1382.2	1381.5	1382.4
157.5°	1411.2	1411.0	1410.8	1410.7	1410.6	1410.1	1409.2	1408.3	1407.6	1406.7	1408.0
160°	1427.2	1426.5	1425.7	1425.0	1424.3	1423.7	1423.5	1423.2	1423.0	1422.8	1424.3
162.5°	1441.5	1440.5	1439.7	1438.7	1437.8	1437.2	1436.9	1436.7	1436.4	1436.1	1437.6
165°	1459.7	1458.4	1457.2	1455.9	1454.7	1454.1	1454.1	1454.1	1454.1	1454.1	1456.0
167.5°	1473.9	1472.7	1471.4	1470.1	1468.8	1468.0	1467.9	1467.7	1467.6	1467.4	1469.6
170°	1482.0	1480.5	1478.9	1477.5	1476.0	1475.4	1475.6	1475.8	1476.1	1476.4	1478.3
172.5°	1487.3	1485.8	1484.4	1482.8	1481.4	1480.7	1481.0	1481.3	1481.4	1481.7	1483.7
175°	1493.1	1491.6	1490.1	1488.7	1487.1	1486.5	1486.8	1487.0	1487.3	1487.5	1489.8
177.5°	1495.8	1494.4	1493.0	1491.6	1490.2	1489.7	1490.1	1490.6	1490.9	1491.3	1492.9
180°	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1



TEST NUMBER: P333089-935

CATALOG NUMBER: S124RDIW-S1020D1340U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7
2.5°	1548.9	1551.2	1553.5	1554.6	1554.4	1554.2	1553.9	1553.8
5°	1538.5	1541.2	1543.9	1544.9	1544.4	1543.9	1543.3	1542.8
7.5°	1518.1	1519.8	1521.5	1521.9	1521.0	1520.2	1519.3	1518.5
10°	1499.7	1500.7	1501.8	1501.8	1500.7	1499.7	1498.6	1497.5
12.5°	1476.9	1477.6	1478.2	1477.7	1476.3	1474.8	1473.3	1471.9
15°	1437.0	1436.4	1435.9	1434.7	1432.9	1431.0	1429.2	1427.3
17.5°	1388.9	1387.4	1386.0	1383.8	1381.0	1378.2	1375.4	1372.5
20°	1355.2	1353.1	1351.0	1348.2	1344.8	1341.4	1337.9	1334.5
22.5°	1317.8	1314.7	1311.6	1308.5	1305.7	1303.0	1300.1	1297.4
25°	1257.6	1253.1	1248.6	1245.0	1242.4	1239.8	1237.1	1234.5
27.5°	1196.2	1190.7	1185.1	1180.4	1176.6	1172.8	1169.0	1165.2
30°	1152.2	1145.6	1138.9	1133.5	1129.3	1125.1	1120.8	1116.6
32.5°	1107.2	1099.6	1091.9	1086.1	1082.0	1078.0	1074.0	1070.0
35°	1040.3	1031.3	1022.3	1015.5	1010.6	1005.9	1001.2	996.3
37.5°	968.5	958.4	948.3	940.9	936.2	931.3	926.6	921.9
40°	920.6	909.5	898.4	890.4	885.7	880.9	876.2	871.4
42.5°	873.5	862.2	850.8	842.7	837.8	832.8	827.8	822.9
45°	801.4	788.4	775.5	766.6	761.9	757.1	752.3	747.6
47.5°	728.8	715.4	701.9	692.6	687.3	682.1	676.8	671.7
50°	680.6	667.4	654.2	645.1	640.1	635.0	630.0	625.0
52.5°	632.6	619.1	605.7	596.4	591.2	585.9	580.7	575.5
55°	561.7	548.0	534.3	524.9	519.8	514.8	509.8	504.7
57.5°	492.5	478.5	464.6	455.7	451.9	448.1	444.3	440.5
60°	446.3	432.5	418.8	409.7	405.5	401.3	397.1	392.9
62.5°	400.8	388.1	375.4	367.3	363.9	360.6	357.1	353.8
65°	335.5	324.2	312.8	305.6	302.4	299.2	296.0	292.8
67.5°	275.6	265.9	256.1	249.4	245.9	242.5	238.9	235.5
70°	234.9	226.2	217.5	211.7	209.1	206.5	203.8	201.2
72.5°	198.4	191.0	183.5	178.6	176.1	173.7	171.3	168.8
75°	146.2	140.1	134.0	130.2	128.5	127.0	125.4	123.8
77.5°	103.4	99.9	96.3	94.3	93.8	93.3	92.8	92.4
80°	79.4	78.6	77.7	77.2	77.0	76.7	76.5	76.2
82.5°	61.6	61.1	60.5	60.1	59.8	59.6	59.3	59.1
85°	35.8	35.3	34.8	34.5	34.5	34.5	34.5	34.5
87.5°	18.4	18.5	18.6	18.8	19.1	19.4	19.7	20.1
90°	27.6	29.0	30.6	31.5	32.0	32.5	33.0	33.5
92.5°	26.7	28.2	29.6	30.4	30.6	30.7	30.7	30.8
95°	27.6	29.0	30.6	31.4	31.6	31.9	32.1	32.4
97.5°	29.8	30.0	30.0	30.3	30.6	30.7	31.0	31.3
100°	40.7	36.5	32.3	30.3	30.6	30.7	31.0	31.3
102.5°	145.8	100.2	54.7	31.9	32.0	32.0	32.1	32.2
105°	352.9	355.2	357.4	354.0	345.1	336.1	327.2	318.3
107.5°	436.6	437.7	438.8	439.8	440.7	441.7	442.6	443.6
110°	493.5	494.0	494.5	495.1	495.8	496.6	497.3	498.1



TEST NUMBER: P333089-935

CATALOG NUMBER: S124RDIW-S1020D1340U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	548.5	548.5	548.4	548.8	549.7	550.7	551.6	552.6
115°	630.9	631.4	631.8	632.1	632.1	632.1	632.1	632.1
117.5°	713.6	713.5	713.4	713.3	713.3	713.2	713.1	712.9
120°	764.8	765.3	765.9	765.9	765.3	764.8	764.4	763.9
122.5°	815.4	815.7	816.0	815.9	815.4	814.9	814.4	813.9
125°	886.0	886.7	887.4	887.9	888.2	888.5	888.7	889.0
127.5°	956.1	956.0	955.8	955.6	955.5	955.2	955.0	954.8
130°	998.8	999.1	999.4	999.5	999.5	999.5	999.5	999.5
132.5°	1040.9	1041.1	1041.4	1041.4	1041.2	1041.0	1040.8	1040.6
135°	1098.8	1099.2	1099.8	1100.3	1100.8	1101.2	1101.7	1102.3
137.5°	1154.3	1154.8	1155.4	1155.5	1155.4	1155.3	1155.1	1154.9
140°	1188.6	1189.4	1190.1	1190.6	1190.8	1191.1	1191.4	1191.6
142.5°	1220.4	1220.9	1221.5	1221.8	1221.8	1221.8	1221.9	1221.9
145°	1265.8	1266.0	1266.3	1266.7	1267.1	1267.7	1268.2	1268.7
147.5°	1305.7	1305.9	1306.1	1306.3	1306.6	1306.8	1307.0	1307.3
150°	1331.2	1331.2	1331.2	1331.3	1331.5	1331.8	1332.1	1332.3
152.5°	1353.4	1353.8	1354.2	1354.4	1354.2	1354.0	1353.9	1353.8
155°	1383.5	1384.4	1385.4	1385.5	1384.8	1384.1	1383.3	1382.6
157.5°	1409.3	1410.6	1411.9	1411.9	1410.6	1409.3	1408.0	1406.7
160°	1425.7	1427.2	1428.7	1428.7	1427.2	1425.7	1424.3	1422.8
162.5°	1439.2	1440.6	1442.1	1442.0	1440.4	1438.6	1436.9	1435.3
165°	1458.0	1460.0	1462.0	1461.8	1459.7	1457.4	1455.2	1452.9
167.5°	1471.8	1473.9	1476.2	1476.0	1473.5	1471.0	1468.6	1466.1
170°	1480.3	1482.3	1484.3	1484.0	1481.6	1479.1	1476.6	1474.1
172.5°	1485.7	1487.7	1489.7	1489.4	1486.6	1483.9	1481.3	1478.6
175°	1492.0	1494.3	1496.5	1496.1	1493.1	1490.1	1487.1	1484.2
177.5°	1494.5	1496.1	1497.7	1497.3	1494.9	1492.5	1490.1	1487.7
180°	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1

(END OF REPORT)