

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333091-935

Luminaire Tested: **S124RDIW-S1020D1560U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333091-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1020D1560U935-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9109.3 lumens
Efficiency: N/A
Efficacy: 118.9 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333091-935

CATALOG NUMBER: S124RDIW-S1020D1560U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333091-935

CATALOG NUMBER: S124RDIW-S1020D1560U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	35
2	88	81	75	70	80	74	69	65	61	57	54	49	47	45	38	37	35	30
3	80	71	64	59	73	65	59	54	54	50	46	44	41	38	34	32	30	26
4	74	63	56	50	67	58	51	46	48	43	40	39	36	33	31	28	26	23
5	68	56	49	43	62	52	45	40	43	38	34	35	32	29	28	25	23	20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21	18
7	58	46	38	33	53	42	35	31	35	30	26	29	25	22	23	20	18	16
8	53	42	34	29	49	38	32	27	32	27	24	27	23	20	21	19	16	14
9	50	38	31	26	45	35	29	24	30	25	21	25	21	18	20	17	15	13
10	46	35	28	23	42	32	26	22	27	22	19	23	19	16	18	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11926	11926	11926	11926
5°	13834	11962	10573	11962
10°	16365	11910	9437	11910
15°	18904	11800	8109	11800
20°	21047	11649	7332	11649
25°	21727	11500	6807	11500
30°	19020	11320	6492	11320
35°	14807	11052	6300	11052
40°	11102	10745	6198	10745
45°	8766	10255	6142	10255
50°	7401	9688	5966	9688
55°	6450	9064	5645	9064
60°	5804	8418	4997	8418
65°	5117	7721	4298	7721
70°	4607	6996	3878	6996
75°	3862	6201	3306	6201
80°	3268	5286	3096	5286
85°	2760	4131	2760	4131



TEST NUMBER: P333091-935

CATALOG NUMBER: S124RDIW-S1020D1560U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.1	1.6
10°-20°	431.8	4.7
20°-30°	675.3	7.4
30°-40°	750.8	8.2
40°-50°	666.1	7.3
50°-60°	519.0	5.7
60°-70°	339.8	3.7
70°-80°	167.1	1.8
80°-90°	46.3	0.5
90°-100°	59.4	0.7
100°-110°	378.6	4.2
110°-120°	724.2	8.0
120°-130°	919.3	10.1
130°-140°	983.6	10.8
140°-150°	919.8	10.1
150°-160°	741.8	8.1
160°-170°	478.4	5.3
170°-180°	164.9	1.8
0°-30°	1250.3	13.7
0°-40°	2001.0	22.0
0°-60°	3186.1	35.0
0°-90°	3739.3	41.0
90°-120°	1162.1	12.8
90°-150°	3984.9	43.7
90°-180°	5370.0	59.0
0°-180°	9109.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1477	1477	1477	1477	1477	
5°	1707	1476	1305	1476	1707	173
15°	2262	1412	970	1412	2262	643
25°	2439	1291	764	1291	2439	1082
35°	1502	1121	639	1121	1502	942
45°	768	898	538	898	768	608
55°	458	644	401	644	458	417
65°	268	404	225	404	268	269
75°	124	199	106	199	124	136
85°	30	45	30	45	30	35
90°	39	4	39	4	39	18
95°	38	71	38	71	38	30
105°	370	391	370	391	370	323
115°	735	730	735	730	735	727
125°	1034	1026	1034	1026	1034	920
135°	1282	1272	1282	1272	1282	986
145°	1475	1467	1475	1467	1475	922
155°	1608	1609	1608	1609	1608	741
165°	1689	1697	1689	1697	1689	477
175°	1726	1736	1726	1736	1726	164
180°	1736	1736	1736	1736	1736	



TEST NUMBER: P333091-935

CATALOG NUMBER: S124RDIW-S1020D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3
2.5°	1558.2	1562.5	1558.2	1557.8	1553.1	1551.6	1549.7	1543.5	1532.1	1525.4	1526.8
5°	1707.1	1721.9	1713.6	1712.4	1699.4	1686.3	1677.9	1658.9	1638.7	1625.0	1613.6
7.5°	1879.2	1887.7	1882.6	1874.2	1853.0	1841.0	1821.7	1796.6	1760.3	1732.5	1707.2
10°	1996.3	2003.5	2001.1	1985.6	1970.1	1938.6	1920.7	1885.7	1839.8	1803.5	1769.5
12.5°	2111.6	2119.2	2098.3	2098.9	2069.7	2044.8	2016.5	1972.3	1919.3	1872.5	1830.1
15°	2261.8	2252.3	2252.3	2240.4	2207.6	2173.2	2144.0	2097.6	2030.8	1974.9	1916.0
17.5°	2379.5	2382.7	2377.9	2349.8	2324.1	2288.4	2234.9	2180.7	2118.8	2043.8	1983.5
20°	2449.9	2449.9	2444.6	2425.5	2392.2	2354.1	2296.4	2237.4	2158.9	2083.3	2015.4
22.5°	2478.5	2480.4	2474.1	2458.3	2428.4	2391.2	2342.0	2282.2	2201.2	2116.1	2032.0
25°	2439.2	2450.5	2451.7	2447.5	2438.6	2416.0	2373.7	2312.4	2239.8	2147.5	2057.0
27.5°	2239.5	2253.8	2266.2	2286.8	2314.2	2328.5	2330.4	2299.2	2235.8	2147.1	2056.0
30°	2040.4	2052.3	2091.0	2141.6	2180.8	2216.6	2247.6	2255.8	2220.2	2140.4	2044.5
32.5°	1819.5	1835.7	1874.3	1928.7	1994.2	2054.7	2124.2	2159.6	2158.7	2110.8	2022.1
35°	1502.4	1514.2	1550.0	1607.1	1685.7	1775.6	1885.7	1971.3	2029.6	2025.5	1971.3
37.5°	1211.6	1225.0	1261.1	1308.5	1384.7	1496.0	1602.6	1720.6	1828.5	1889.1	1871.0
40°	1053.5	1054.1	1089.3	1138.1	1209.4	1306.5	1422.5	1553.5	1673.7	1771.9	1791.0
42.5°	928.8	928.8	952.1	1004.7	1056.2	1147.5	1258.3	1388.3	1529.0	1642.4	1692.9
45°	767.8	773.2	792.2	823.8	864.3	941.6	1030.3	1151.2	1308.9	1443.4	1527.3
47.5°	650.2	658.1	670.2	695.9	728.1	779.7	853.1	961.7	1089.9	1237.9	1357.4
50°	589.3	590.5	605.9	620.2	648.2	689.2	753.5	844.0	961.8	1104.1	1236.8
52.5°	536.9	536.7	546.0	564.0	586.8	618.8	670.7	753.0	857.6	985.1	1122.1
55°	458.3	461.3	468.5	482.7	500.0	522.6	563.7	625.6	707.7	816.7	941.1
57.5°	398.6	400.1	405.7	411.7	427.6	444.0	474.8	517.8	587.1	676.3	792.2
60°	359.5	360.1	361.9	370.8	383.3	398.8	419.7	455.9	514.3	595.8	687.5
62.5°	321.4	322.4	325.2	331.7	341.4	352.1	373.9	403.1	451.4	521.1	603.6
65°	267.9	268.5	272.6	275.0	282.8	292.2	308.3	328.0	361.3	419.7	482.2
67.5°	223.8	223.8	224.0	227.2	232.6	238.9	248.6	264.2	289.4	325.2	380.3
70°	195.2	195.2	196.4	198.2	201.2	206.6	211.9	223.8	242.3	271.4	313.7
72.5°	168.6	169.0	170.2	170.6	172.1	176.5	180.5	188.1	201.8	223.8	258.0
75°	123.8	125.6	128.5	131.0	133.9	133.4	137.5	142.2	146.5	159.5	179.2
77.5°	92.1	91.2	91.5	93.6	93.9	94.5	97.5	101.2	104.3	110.5	117.5
80°	70.3	70.3	72.0	72.6	72.0	72.6	75.6	77.4	78.6	80.9	87.5
82.5°	53.1	54.1	53.5	54.1	54.4	55.0	57.5	57.9	59.1	60.0	62.8
85°	29.8	30.4	30.9	29.8	29.8	29.8	30.9	31.5	32.7	32.1	33.3
87.5°	18.3	17.7	18.0	17.9	18.3	17.6	17.7	18.3	17.0	17.1	16.7
90°	38.9	38.4	37.8	37.2	36.7	35.5	33.8	32.0	30.3	28.6	26.3
92.5°	35.8	35.7	35.6	35.5	35.4	34.4	32.7	31.0	29.3	27.6	25.2
95°	37.6	37.4	37.1	36.8	36.5	35.5	33.8	32.0	30.3	28.6	28.2
97.5°	36.3	36.1	35.8	35.5	35.2	35.0	34.8	34.6	34.4	34.3	66.5
100°	36.3	36.1	35.8	35.5	35.2	37.5	42.4	47.4	52.3	57.2	96.9
102.5°	37.4	37.4	37.3	37.2	37.2	63.6	116.5	169.4	222.3	275.3	280.4
105°	370.1	380.5	390.8	401.2	411.6	415.5	412.9	410.3	407.7	405.1	403.6
107.5°	515.7	514.6	513.5	512.5	511.3	510.1	508.9	507.6	506.4	505.1	503.1
110°	579.1	578.2	577.4	576.5	575.7	574.9	574.4	573.8	573.2	572.6	570.8



TEST NUMBER: P333091-935

CATALOG NUMBER: S124RDIW-S1020D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	642.5	641.4	640.2	639.2	638.1	637.6	637.7	637.8	637.9	638.1	637.2
115°	734.9	734.9	734.9	734.9	734.9	734.6	734.0	733.5	732.9	732.3	732.6
117.5°	828.9	829.1	829.1	829.2	829.4	829.5	829.6	829.7	829.8	829.9	829.3
120°	888.1	888.7	889.2	889.8	890.4	890.4	889.8	889.2	888.7	888.1	888.4
122.5°	946.3	946.8	947.4	948.0	948.6	948.7	948.4	948.0	947.7	947.4	946.9
125°	1033.5	1033.3	1032.9	1032.7	1032.4	1031.8	1031.0	1030.1	1029.2	1028.4	1028.9
127.5°	1110.2	1110.3	1110.6	1110.9	1111.0	1111.3	1111.5	1111.6	1111.8	1112.0	1110.6
130°	1162.1	1162.1	1162.1	1162.1	1162.1	1161.9	1161.7	1161.4	1161.1	1160.8	1159.9
132.5°	1209.9	1210.1	1210.3	1210.6	1210.8	1210.7	1210.5	1210.2	1209.9	1209.6	1208.5
135°	1281.5	1281.0	1280.4	1279.8	1279.3	1278.7	1278.1	1277.5	1276.9	1276.3	1275.2
137.5°	1342.8	1343.0	1343.2	1343.3	1343.5	1343.3	1342.6	1342.0	1341.4	1340.7	1339.5
140°	1385.4	1385.1	1384.8	1384.6	1384.2	1383.7	1382.9	1382.0	1381.1	1380.2	1379.7
142.5°	1420.7	1420.6	1420.6	1420.6	1420.5	1420.1	1419.5	1418.9	1418.2	1417.6	1417.3
145°	1475.0	1474.5	1473.9	1473.3	1472.7	1472.2	1472.0	1471.7	1471.4	1471.1	1471.1
147.5°	1519.9	1519.7	1519.3	1519.1	1518.8	1518.5	1518.3	1518.0	1517.9	1517.6	1517.9
150°	1549.0	1548.8	1548.4	1548.2	1547.9	1547.7	1547.7	1547.7	1547.7	1547.7	1548.0
152.5°	1573.9	1574.1	1574.3	1574.4	1574.6	1574.5	1574.0	1573.6	1573.1	1572.6	1573.1
155°	1607.5	1608.3	1609.2	1610.1	1610.9	1610.8	1609.6	1608.4	1607.3	1606.1	1607.1
157.5°	1635.5	1637.0	1638.5	1640.0	1641.5	1641.5	1640.0	1638.5	1637.0	1635.5	1636.5
160°	1654.2	1656.0	1657.7	1659.4	1661.1	1661.1	1659.4	1657.7	1656.0	1654.2	1654.5
162.5°	1668.7	1670.7	1672.7	1674.6	1676.5	1676.7	1675.0	1673.3	1671.5	1669.7	1670.1
165°	1689.3	1691.9	1694.4	1697.0	1699.6	1699.8	1697.5	1695.1	1692.8	1690.6	1690.6
167.5°	1704.6	1707.4	1710.4	1713.2	1716.1	1716.3	1713.7	1711.2	1708.7	1706.2	1706.3
170°	1713.9	1716.8	1719.7	1722.6	1725.4	1725.8	1723.5	1721.1	1718.8	1716.5	1716.2
172.5°	1719.1	1722.3	1725.4	1728.5	1731.6	1732.0	1729.7	1727.3	1725.0	1722.8	1722.4
175°	1725.6	1729.1	1732.5	1735.9	1739.5	1739.9	1737.3	1734.7	1732.1	1729.5	1729.2
177.5°	1729.7	1732.5	1735.3	1738.1	1740.9	1741.3	1739.5	1737.6	1735.8	1733.9	1733.5
180°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9



TEST NUMBER: P333091-935

CATALOG NUMBER: S124RDIW-S1020D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3
2.5°	1522.1	1515.4	1512.1	1504.4	1495.4	1490.6	1486.3	1480.1	1472.1	1463.5	1457.3
5°	1599.3	1585.0	1567.2	1545.8	1526.7	1508.3	1492.2	1476.1	1457.7	1438.6	1419.6
7.5°	1678.6	1650.5	1620.1	1585.0	1550.9	1519.8	1491.3	1463.9	1432.9	1405.2	1379.9
10°	1733.9	1695.7	1653.5	1608.9	1564.2	1525.5	1487.5	1452.9	1414.8	1380.9	1352.3
12.5°	1778.7	1733.9	1683.0	1627.5	1573.7	1527.0	1483.2	1438.1	1394.8	1358.1	1319.9
15°	1852.9	1791.6	1723.1	1656.5	1586.8	1523.1	1464.2	1411.9	1362.4	1310.7	1274.4
17.5°	1903.9	1831.3	1748.0	1667.9	1585.6	1510.5	1442.5	1380.2	1323.2	1270.3	1227.1
20°	1934.4	1854.1	1761.9	1670.8	1578.5	1498.1	1425.0	1355.9	1297.0	1239.8	1195.2
22.5°	1951.5	1862.7	1761.9	1666.5	1570.9	1483.8	1403.5	1331.6	1267.5	1210.3	1160.9
25°	1957.1	1861.8	1758.9	1649.3	1544.5	1452.3	1369.0	1291.0	1219.6	1162.4	1110.1
27.5°	1949.5	1837.3	1731.8	1619.5	1511.4	1414.1	1326.6	1244.7	1173.2	1111.9	1058.2
30°	1938.0	1817.7	1704.7	1588.0	1478.5	1385.1	1292.8	1214.3	1139.8	1076.2	1022.0
32.5°	1913.2	1794.0	1672.3	1552.8	1441.8	1345.6	1258.0	1179.0	1106.0	1040.9	983.4
35°	1864.2	1743.4	1611.3	1488.7	1379.7	1279.7	1197.6	1121.4	1051.7	982.1	921.4
37.5°	1799.6	1676.1	1544.7	1410.4	1301.4	1206.9	1131.6	1060.1	992.1	928.5	861.3
40°	1738.6	1626.1	1490.4	1357.1	1245.2	1154.1	1084.5	1019.6	951.1	888.0	820.8
42.5°	1664.8	1569.0	1431.8	1298.0	1187.6	1099.8	1034.9	971.5	909.2	848.1	777.9
45°	1541.6	1469.0	1340.4	1211.9	1100.5	1013.7	954.2	898.2	843.4	785.1	719.0
47.5°	1400.4	1351.3	1240.3	1108.6	1005.6	927.5	870.0	824.2	777.9	719.6	661.7
50°	1302.3	1270.7	1163.6	1043.4	945.2	873.1	814.2	771.4	732.7	676.7	625.0
52.5°	1197.6	1180.8	1090.3	975.3	880.5	809.9	759.5	720.9	681.7	635.3	586.9
55°	1038.0	1047.0	970.2	870.8	781.5	722.0	676.1	644.0	610.7	571.4	533.9
57.5°	874.9	907.6	856.0	768.8	685.1	630.1	595.6	568.5	540.5	508.0	476.0
60°	777.3	804.7	775.6	698.8	625.6	574.4	542.3	521.4	493.4	463.6	439.3
62.5°	682.1	711.4	694.1	632.1	564.1	520.1	491.8	472.3	451.5	425.6	400.2
65°	562.5	581.5	573.2	530.4	482.2	444.6	418.4	404.2	385.1	366.1	343.5
67.5°	430.8	467.6	462.7	440.0	398.3	369.0	351.9	339.2	321.9	307.7	292.4
70°	354.1	388.1	387.4	369.0	346.4	319.0	307.1	296.4	280.9	267.3	254.8
72.5°	289.9	321.0	325.5	311.4	295.9	275.3	263.8	256.4	241.4	232.0	221.9
75°	202.9	225.6	231.5	231.5	224.4	213.7	203.5	198.8	188.1	179.8	173.8
77.5°	133.1	147.4	156.7	158.8	159.9	156.3	148.0	144.6	136.4	133.5	127.8
80°	94.0	103.6	114.3	117.9	120.8	119.7	116.1	113.7	106.0	103.0	100.6
82.5°	65.0	70.3	79.0	86.9	86.1	89.2	86.1	84.2	78.4	77.2	74.9
85°	33.9	34.5	35.7	41.1	44.1	45.2	45.8	44.6	42.9	42.9	38.7
87.5°	16.2	15.2	15.8	15.2	15.1	16.4	17.1	17.0	16.2	15.4	14.6
90°	23.9	21.6	19.4	16.6	13.4	10.2	7.1	3.9	7.1	10.2	13.4
92.5°	22.9	20.6	18.3	17.0	16.9	16.7	16.5	16.4	16.5	16.7	16.9
95°	28.0	27.7	27.4	32.2	42.0	51.8	61.6	71.4	61.6	51.8	42.0
97.5°	98.7	130.9	163.1	176.2	170.0	163.8	157.7	151.6	157.7	163.8	170.0
100°	136.7	176.6	216.4	233.7	228.5	223.3	218.2	212.9	218.2	223.3	228.5
102.5°	285.7	290.8	296.0	296.7	292.9	289.1	285.3	281.5	285.3	289.1	292.9
105°	402.3	400.8	399.3	397.8	396.1	394.3	392.5	390.8	392.5	394.3	396.1
107.5°	501.2	499.2	497.2	495.8	495.0	494.1	493.3	492.3	493.3	494.1	495.0
110°	569.1	567.4	565.7	564.4	563.5	562.7	561.8	560.9	561.8	562.7	563.5



TEST NUMBER: P333091-935

CATALOG NUMBER: S124RDIW-S1020D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	636.5	635.6	634.8	633.6	632.1	630.5	629.0	627.4	629.0	630.5	632.1
115°	732.9	733.1	733.5	733.1	732.3	731.4	730.6	729.7	730.6	731.4	732.3
117.5°	828.7	828.0	827.4	826.6	825.4	824.2	823.0	821.9	823.0	824.2	825.4
120°	888.7	889.0	889.2	888.8	887.7	886.6	885.4	884.2	885.4	886.6	887.7
122.5°	946.5	946.2	945.7	945.2	944.4	943.7	943.1	942.4	943.1	943.7	944.4
125°	1029.5	1030.1	1030.6	1030.4	1029.2	1028.0	1026.9	1025.8	1026.9	1028.0	1029.2
127.5°	1109.3	1108.0	1106.6	1105.9	1105.5	1105.3	1105.0	1104.7	1105.0	1105.3	1105.5
130°	1159.1	1158.2	1157.4	1156.8	1156.5	1156.2	1155.9	1155.6	1155.9	1156.2	1156.5
132.5°	1207.4	1206.3	1205.2	1204.5	1203.9	1203.4	1202.8	1202.3	1202.8	1203.4	1203.9
135°	1274.0	1272.9	1271.7	1271.3	1271.6	1271.9	1272.1	1272.5	1272.1	1271.9	1271.6
137.5°	1338.3	1337.0	1335.7	1335.0	1334.9	1334.7	1334.6	1334.6	1334.6	1334.7	1334.9
140°	1379.1	1378.5	1377.9	1377.3	1376.7	1376.2	1375.6	1375.0	1375.6	1376.2	1376.7
142.5°	1416.9	1416.6	1416.3	1415.6	1414.5	1413.5	1412.4	1411.4	1412.4	1413.5	1414.5
145°	1471.1	1471.1	1471.1	1470.7	1469.8	1469.0	1468.1	1467.2	1468.1	1469.0	1469.8
147.5°	1518.2	1518.5	1518.7	1518.1	1516.5	1514.8	1513.2	1511.7	1513.2	1514.8	1516.5
150°	1548.3	1548.6	1548.9	1548.4	1547.3	1546.1	1545.0	1543.9	1545.0	1546.1	1547.3
152.5°	1573.6	1574.2	1574.8	1574.5	1573.6	1572.7	1571.8	1570.8	1571.8	1572.7	1573.6
155°	1607.9	1608.8	1609.6	1609.9	1609.6	1609.3	1609.0	1608.8	1609.0	1609.3	1609.6
157.5°	1637.4	1638.4	1639.4	1640.0	1640.2	1640.4	1640.5	1640.7	1640.5	1640.4	1640.2
160°	1654.8	1655.0	1655.4	1656.0	1656.8	1657.7	1658.5	1659.4	1658.5	1657.7	1656.8
162.5°	1670.3	1670.6	1670.9	1671.6	1672.8	1673.8	1674.9	1676.0	1674.9	1673.8	1672.8
165°	1690.6	1690.6	1690.6	1691.3	1692.7	1694.2	1695.6	1697.0	1695.6	1694.2	1692.7
167.5°	1706.5	1706.7	1706.8	1707.6	1709.2	1710.6	1712.2	1713.6	1712.2	1710.6	1709.2
170°	1716.0	1715.6	1715.4	1716.1	1717.8	1719.5	1721.3	1723.0	1721.3	1719.5	1717.8
172.5°	1722.2	1721.9	1721.6	1722.3	1724.1	1725.8	1727.5	1729.2	1727.5	1725.8	1724.1
175°	1728.9	1728.6	1728.4	1729.1	1730.8	1732.5	1734.2	1735.9	1734.2	1732.5	1730.8
177.5°	1733.0	1732.5	1732.1	1732.7	1734.2	1735.9	1737.5	1739.1	1737.5	1735.9	1734.2
180°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9



TEST NUMBER: P333091-935

CATALOG NUMBER: S124RDIW-S1020D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3
2.5°	1450.6	1445.9	1439.7	1432.5	1424.0	1416.3	1413.1	1415.9	1417.3	1413.5	1413.1
5°	1406.5	1391.6	1379.7	1361.8	1347.6	1335.7	1327.3	1323.8	1324.9	1315.4	1313.0
7.5°	1356.8	1339.2	1319.7	1298.5	1278.8	1261.3	1252.1	1247.1	1237.0	1232.7	1225.5
10°	1324.9	1301.1	1282.1	1257.1	1234.5	1213.7	1203.5	1195.2	1185.1	1180.3	1170.2
12.5°	1292.1	1264.5	1243.5	1217.5	1194.5	1169.3	1159.7	1144.3	1128.4	1118.4	1105.4
15°	1245.8	1212.5	1186.9	1155.9	1128.5	1099.9	1074.4	1045.8	1035.1	1012.4	999.4
17.5°	1191.6	1157.8	1126.1	1084.6	1042.3	1006.9	979.6	952.2	935.8	921.4	914.7
20°	1155.9	1125.0	1080.9	1032.7	985.7	946.4	924.4	906.5	888.6	878.6	871.4
22.5°	1122.1	1082.5	1031.4	979.4	932.4	901.6	883.0	864.6	850.1	840.4	831.0
25°	1065.4	1013.7	959.5	900.0	867.8	841.0	820.8	805.9	797.0	784.5	779.7
27.5°	1007.2	944.5	884.8	844.7	811.2	786.8	769.1	757.9	746.7	738.7	732.5
30°	962.4	898.8	845.2	807.1	773.2	752.9	738.7	725.6	716.6	710.1	705.3
32.5°	918.2	854.5	809.5	768.5	741.8	722.0	706.8	697.0	690.0	681.5	678.6
35°	854.1	797.5	758.3	721.4	694.1	676.1	664.3	654.1	648.2	645.8	644.0
37.5°	792.6	746.3	704.0	673.8	649.4	635.3	621.3	616.3	612.3	608.0	609.8
40°	753.5	710.1	672.6	640.4	620.8	605.4	597.0	591.1	587.5	587.5	587.5
42.5°	719.7	677.3	640.7	611.9	592.2	579.1	569.9	564.8	563.7	563.2	566.0
45°	667.3	627.9	591.1	567.2	550.6	537.4	532.1	528.0	528.0	530.4	530.9
47.5°	615.2	578.4	548.8	522.1	506.9	498.7	494.0	491.9	492.1	494.5	497.2
50°	583.3	547.0	517.8	494.0	479.7	472.0	467.9	466.7	467.9	467.9	472.0
52.5°	548.5	516.1	487.3	467.4	451.2	443.9	441.6	440.0	440.7	442.6	444.4
55°	497.6	468.5	441.1	422.0	410.1	405.4	400.0	400.5	399.4	400.5	400.5
57.5°	446.5	420.3	394.9	379.8	369.3	362.4	356.5	358.2	356.5	356.2	355.2
60°	413.7	385.1	364.9	351.2	339.2	333.3	328.0	329.2	327.4	326.1	323.8
62.5°	378.0	354.1	334.8	321.7	312.1	305.2	299.9	298.7	294.5	290.5	285.2
65°	326.1	306.5	289.3	276.8	267.9	262.5	258.3	254.8	245.8	236.3	231.5
67.5°	275.9	261.7	245.6	235.0	227.7	220.7	212.8	206.6	198.3	193.1	190.1
70°	243.4	229.7	216.0	206.0	198.2	191.7	182.7	178.6	172.6	170.2	167.3
72.5°	212.5	199.8	187.0	177.9	169.6	164.5	157.5	153.3	150.7	149.7	146.8
75°	165.5	155.3	145.9	137.5	131.0	127.3	124.4	121.4	120.2	114.9	111.9
77.5°	120.7	114.1	108.1	102.1	97.5	95.1	89.4	85.9	83.9	81.5	80.8
80°	94.0	89.3	83.3	79.7	73.2	70.9	68.4	67.8	67.2	66.6	66.0
82.5°	70.7	66.0	60.0	57.9	56.1	54.7	53.2	52.6	52.0	52.3	52.3
85°	35.7	33.3	33.3	32.7	32.1	31.5	30.9	30.9	30.4	30.9	30.4
87.5°	15.2	15.3	15.8	15.2	16.2	16.7	16.5	16.9	17.7	17.1	17.3
90°	16.6	19.4	21.6	23.9	26.3	28.6	30.3	32.0	33.8	35.5	36.7
92.5°	17.0	18.3	20.6	22.9	25.2	27.6	29.3	31.0	32.7	34.4	35.4
95°	32.2	27.4	27.7	28.0	28.2	28.6	30.3	32.0	33.8	35.5	36.5
97.5°	176.2	163.1	130.9	98.7	66.5	34.3	34.4	34.6	34.8	35.0	35.2
100°	233.7	216.4	176.6	136.7	96.9	57.2	52.3	47.4	42.4	37.5	35.2
102.5°	296.7	296.0	290.8	285.7	280.4	275.3	222.3	169.4	116.5	63.6	37.2
105°	397.8	399.3	400.8	402.3	403.6	405.1	407.7	410.3	412.9	415.5	411.6
107.5°	495.8	497.2	499.2	501.2	503.1	505.1	506.4	507.6	508.9	510.1	511.3
110°	564.4	565.7	567.4	569.1	570.8	572.6	573.2	573.8	574.4	574.9	575.7



TEST NUMBER: P333091-935

CATALOG NUMBER: S124RDIW-S1020D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	633.6	634.8	635.6	636.5	637.2	638.1	637.9	637.8	637.7	637.6	638.1
115°	733.1	733.5	733.1	732.9	732.6	732.3	732.9	733.5	734.0	734.6	734.9
117.5°	826.6	827.4	828.0	828.7	829.3	829.9	829.8	829.7	829.6	829.5	829.4
120°	888.8	889.2	889.0	888.7	888.4	888.1	888.7	889.2	889.8	890.4	890.4
122.5°	945.2	945.7	946.2	946.5	946.9	947.4	947.7	948.0	948.4	948.7	948.6
125°	1030.4	1030.6	1030.1	1029.5	1028.9	1028.4	1029.2	1030.1	1031.0	1031.8	1032.4
127.5°	1105.9	1106.6	1108.0	1109.3	1110.6	1112.0	1111.8	1111.6	1111.5	1111.3	1111.0
130°	1156.8	1157.4	1158.2	1159.1	1159.9	1160.8	1161.1	1161.4	1161.7	1161.9	1162.1
132.5°	1204.5	1205.2	1206.3	1207.4	1208.5	1209.6	1209.9	1210.2	1210.5	1210.7	1210.8
135°	1271.3	1271.7	1272.9	1274.0	1275.2	1276.3	1276.9	1277.5	1278.1	1278.7	1279.3
137.5°	1335.0	1335.7	1337.0	1338.3	1339.5	1340.7	1341.4	1342.0	1342.6	1343.3	1343.5
140°	1377.3	1377.9	1378.5	1379.1	1379.7	1380.2	1381.1	1382.0	1382.9	1383.7	1384.2
142.5°	1415.6	1416.3	1416.6	1416.9	1417.3	1417.6	1418.2	1418.9	1419.5	1420.1	1420.5
145°	1470.7	1471.1	1471.1	1471.1	1471.1	1471.1	1471.4	1471.7	1472.0	1472.2	1472.7
147.5°	1518.1	1518.7	1518.5	1518.2	1517.9	1517.6	1517.9	1518.0	1518.3	1518.5	1518.8
150°	1548.4	1548.9	1548.6	1548.3	1548.0	1547.7	1547.7	1547.7	1547.7	1547.7	1547.9
152.5°	1574.5	1574.8	1574.2	1573.6	1573.1	1572.6	1573.1	1573.6	1574.0	1574.5	1574.6
155°	1609.9	1609.6	1608.8	1607.9	1607.1	1606.1	1607.3	1608.4	1609.6	1610.8	1610.9
157.5°	1640.0	1639.4	1638.4	1637.4	1636.5	1635.5	1637.0	1638.5	1640.0	1641.5	1641.5
160°	1656.0	1655.4	1655.0	1654.8	1654.5	1654.2	1656.0	1657.7	1659.4	1661.1	1661.1
162.5°	1671.6	1670.9	1670.6	1670.3	1670.1	1669.7	1671.5	1673.3	1675.0	1676.7	1676.5
165°	1691.3	1690.6	1690.6	1690.6	1690.6	1690.6	1692.8	1695.1	1697.5	1699.8	1699.6
167.5°	1707.6	1706.8	1706.7	1706.5	1706.3	1706.2	1708.7	1711.2	1713.7	1716.3	1716.1
170°	1716.1	1715.4	1715.6	1716.0	1716.2	1716.5	1718.8	1721.1	1723.5	1725.8	1725.4
172.5°	1722.3	1721.6	1721.9	1722.2	1722.4	1722.8	1725.0	1727.3	1729.7	1732.0	1731.6
175°	1729.1	1728.4	1728.6	1728.9	1729.2	1729.5	1732.1	1734.7	1737.3	1739.9	1739.5
177.5°	1732.7	1732.1	1732.5	1733.0	1733.5	1733.9	1735.8	1737.6	1739.5	1741.3	1740.9
180°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9



TEST NUMBER: P333091-935

CATALOG NUMBER: S124RDIW-S1020D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3
2.5°	1410.1	1411.1	1407.8	1406.9	1407.8	1411.1	1410.1	1413.1	1413.5	1417.3	1415.9
5°	1308.3	1307.1	1304.1	1304.7	1304.1	1307.1	1308.3	1313.0	1315.4	1324.9	1323.8
7.5°	1221.2	1216.5	1217.8	1213.1	1217.8	1216.5	1221.2	1225.5	1232.7	1237.0	1247.1
10°	1167.8	1161.2	1155.9	1151.2	1155.9	1161.2	1167.8	1170.2	1180.3	1185.1	1195.2
12.5°	1094.9	1089.3	1082.1	1083.6	1082.1	1089.3	1094.9	1105.4	1118.4	1128.4	1144.3
15°	991.6	982.7	968.5	970.2	968.5	982.7	991.6	999.4	1012.4	1035.1	1045.8
17.5°	904.1	904.2	897.7	899.2	897.7	904.2	904.1	914.7	921.4	935.8	952.2
20°	858.9	854.7	855.3	853.5	855.3	854.7	858.9	871.4	878.6	888.6	906.5
22.5°	827.5	822.3	818.2	814.5	818.2	822.3	827.5	831.0	840.4	850.1	864.6
25°	774.4	770.8	765.4	764.2	765.4	770.8	774.4	779.7	784.5	797.0	805.9
27.5°	727.7	727.0	724.9	722.1	724.9	727.0	727.7	732.5	738.7	746.7	757.9
30°	700.6	699.4	698.2	696.4	698.2	699.4	700.6	705.3	710.1	716.6	725.6
32.5°	676.3	675.5	674.3	674.5	674.3	675.5	676.3	678.6	681.5	690.0	697.0
35°	641.6	641.0	639.9	639.3	639.9	641.0	641.6	644.0	645.8	648.2	654.1
37.5°	609.2	610.8	610.1	609.9	610.1	610.8	609.2	609.8	608.0	612.3	616.3
40°	586.9	587.5	588.7	588.1	588.7	587.5	586.9	587.5	587.5	587.5	591.1
42.5°	568.3	568.4	570.1	568.1	570.1	568.4	568.3	566.0	563.2	563.7	564.8
45°	535.1	538.6	538.0	538.0	538.0	538.6	535.1	530.9	530.4	528.0	528.0
47.5°	498.8	501.9	502.7	502.6	502.7	501.9	498.8	497.2	494.5	492.1	491.9
50°	475.0	473.8	475.6	475.0	475.6	473.8	475.0	472.0	467.9	467.9	466.7
52.5°	445.9	446.2	446.1	445.5	446.1	446.2	445.9	444.4	442.6	440.7	440.0
55°	401.1	401.7	400.5	401.1	400.5	401.7	401.1	400.5	400.5	399.4	400.5
57.5°	352.6	349.7	350.9	349.5	350.9	349.7	352.6	355.2	356.2	356.5	358.2
60°	317.9	313.1	311.9	309.5	311.9	313.1	317.9	323.8	326.1	327.4	329.2
62.5°	278.8	275.4	271.4	273.3	271.4	275.4	278.8	285.2	290.5	294.5	298.7
65°	226.8	224.4	222.6	225.0	222.6	224.4	226.8	231.5	236.3	245.8	254.8
67.5°	187.7	186.4	186.4	185.2	186.4	186.4	187.7	190.1	193.1	198.3	206.6
70°	167.3	165.5	165.5	164.3	165.5	165.5	167.3	167.3	170.2	172.6	178.6
72.5°	146.3	144.5	145.0	144.3	145.0	144.5	146.3	146.8	149.7	150.7	153.3
75°	108.3	105.4	105.4	106.0	105.4	105.4	108.3	111.9	114.9	120.2	121.4
77.5°	80.8	80.2	81.1	80.0	81.1	80.2	80.8	80.8	81.5	83.9	85.9
80°	66.0	65.4	64.9	66.6	64.9	65.4	66.0	66.0	66.6	67.2	67.8
82.5°	51.3	51.2	51.1	53.3	51.1	51.2	51.3	52.3	52.3	52.0	52.6
85°	30.9	29.8	30.9	29.8	30.9	29.8	30.9	30.4	30.9	30.4	30.9
87.5°	18.4	18.0	17.7	18.3	17.7	18.0	18.4	17.3	17.1	17.7	16.9
90°	37.2	37.8	38.4	38.9	38.4	37.8	37.2	36.7	35.5	33.8	32.0
92.5°	35.5	35.6	35.7	35.8	35.7	35.6	35.5	35.4	34.4	32.7	31.0
95°	36.8	37.1	37.4	37.6	37.4	37.1	36.8	36.5	35.5	33.8	32.0
97.5°	35.5	35.8	36.1	36.3	36.1	35.8	35.5	35.2	35.0	34.8	34.6
100°	35.5	35.8	36.1	36.3	36.1	35.8	35.5	35.2	37.5	42.4	47.4
102.5°	37.2	37.3	37.4	37.4	37.4	37.3	37.2	37.2	63.6	116.5	169.4
105°	401.2	390.8	380.5	370.1	380.5	390.8	401.2	411.6	415.5	412.9	410.3
107.5°	512.5	513.5	514.6	515.7	514.6	513.5	512.5	511.3	510.1	508.9	507.6
110°	576.5	577.4	578.2	579.1	578.2	577.4	576.5	575.7	574.9	574.4	573.8



TEST NUMBER: P333091-935

CATALOG NUMBER: S124RDIW-S1020D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	639.2	640.2	641.4	642.5	641.4	640.2	639.2	638.1	637.6	637.7	637.8
115°	734.9	734.9	734.9	734.9	734.9	734.9	734.9	734.9	734.6	734.0	733.5
117.5°	829.2	829.1	829.1	828.9	829.1	829.1	829.2	829.4	829.5	829.6	829.7
120°	889.8	889.2	888.7	888.1	888.7	889.2	889.8	890.4	890.4	889.8	889.2
122.5°	948.0	947.4	946.8	946.3	946.8	947.4	948.0	948.6	948.7	948.4	948.0
125°	1032.7	1032.9	1033.3	1033.5	1033.3	1032.9	1032.7	1032.4	1031.8	1031.0	1030.1
127.5°	1110.9	1110.6	1110.3	1110.2	1110.3	1110.6	1110.9	1111.0	1111.3	1111.5	1111.6
130°	1162.1	1162.1	1162.1	1162.1	1162.1	1162.1	1162.1	1162.1	1161.9	1161.7	1161.4
132.5°	1210.6	1210.3	1210.1	1209.9	1210.1	1210.3	1210.6	1210.8	1210.7	1210.5	1210.2
135°	1279.8	1280.4	1281.0	1281.5	1281.0	1280.4	1279.8	1279.3	1278.7	1278.1	1277.5
137.5°	1343.3	1343.2	1343.0	1342.8	1343.0	1343.2	1343.3	1343.5	1343.3	1342.6	1342.0
140°	1384.6	1384.8	1385.1	1385.4	1385.1	1384.8	1384.6	1384.2	1383.7	1382.9	1382.0
142.5°	1420.6	1420.6	1420.6	1420.7	1420.6	1420.6	1420.6	1420.5	1420.1	1419.5	1418.9
145°	1473.3	1473.9	1474.5	1475.0	1474.5	1473.9	1473.3	1472.7	1472.2	1472.0	1471.7
147.5°	1519.1	1519.3	1519.7	1519.9	1519.7	1519.3	1519.1	1518.8	1518.5	1518.3	1518.0
150°	1548.2	1548.4	1548.8	1549.0	1548.8	1548.4	1548.2	1547.9	1547.7	1547.7	1547.7
152.5°	1574.4	1574.3	1574.1	1573.9	1574.1	1574.3	1574.4	1574.6	1574.5	1574.0	1573.6
155°	1610.1	1609.2	1608.3	1607.5	1608.3	1609.2	1610.1	1610.9	1610.8	1609.6	1608.4
157.5°	1640.0	1638.5	1637.0	1635.5	1637.0	1638.5	1640.0	1641.5	1641.5	1640.0	1638.5
160°	1659.4	1657.7	1656.0	1654.2	1656.0	1657.7	1659.4	1661.1	1661.1	1659.4	1657.7
162.5°	1674.6	1672.7	1670.7	1668.7	1670.7	1672.7	1674.6	1676.5	1676.7	1675.0	1673.3
165°	1697.0	1694.4	1691.9	1689.3	1691.9	1694.4	1697.0	1699.6	1699.8	1697.5	1695.1
167.5°	1713.2	1710.4	1707.4	1704.6	1707.4	1710.4	1713.2	1716.1	1716.3	1713.7	1711.2
170°	1722.6	1719.7	1716.8	1713.9	1716.8	1719.7	1722.6	1725.4	1725.8	1723.5	1721.1
172.5°	1728.5	1725.4	1722.3	1719.1	1722.3	1725.4	1728.5	1731.6	1732.0	1729.7	1727.3
175°	1735.9	1732.5	1729.1	1725.6	1729.1	1732.5	1735.9	1739.5	1739.9	1737.3	1734.7
177.5°	1738.1	1735.3	1732.5	1729.7	1732.5	1735.3	1738.1	1740.9	1741.3	1739.5	1737.6
180°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9



TEST NUMBER: P333091-935

CATALOG NUMBER: S124RDIW-S1020D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3
2.5°	1413.1	1416.3	1424.0	1432.5	1439.7	1445.9	1450.6	1457.3	1463.5	1472.1	1480.1
5°	1327.3	1335.7	1347.6	1361.8	1379.7	1391.6	1406.5	1419.6	1438.6	1457.7	1476.1
7.5°	1252.1	1261.3	1278.8	1298.5	1319.7	1339.2	1356.8	1379.9	1405.2	1432.9	1463.9
10°	1203.5	1213.7	1234.5	1257.1	1282.1	1301.1	1324.9	1352.3	1380.9	1414.8	1452.9
12.5°	1159.7	1169.3	1194.5	1217.5	1243.5	1264.5	1292.1	1319.9	1358.1	1394.8	1438.1
15°	1074.4	1099.9	1128.5	1155.9	1186.9	1212.5	1245.8	1274.4	1310.7	1362.4	1411.9
17.5°	979.6	1006.9	1042.3	1084.6	1126.1	1157.8	1191.6	1227.1	1270.3	1323.2	1380.2
20°	924.4	946.4	985.7	1032.7	1080.9	1125.0	1155.9	1195.2	1239.8	1297.0	1355.9
22.5°	883.0	901.6	932.4	979.4	1031.4	1082.5	1122.1	1160.9	1210.3	1267.5	1331.6
25°	820.8	841.0	867.8	900.0	959.5	1013.7	1065.4	1110.1	1162.4	1219.6	1291.0
27.5°	769.1	786.8	811.2	844.7	884.8	944.5	1007.2	1058.2	1111.9	1173.2	1244.7
30°	738.7	752.9	773.2	807.1	845.2	898.8	962.4	1022.0	1076.2	1139.8	1214.3
32.5°	706.8	722.0	741.8	768.5	809.5	854.5	918.2	983.4	1040.9	1106.0	1179.0
35°	664.3	676.1	694.1	721.4	758.3	797.5	854.1	921.4	982.1	1051.7	1121.4
37.5°	621.3	635.3	649.4	673.8	704.0	746.3	792.6	861.3	928.5	992.1	1060.1
40°	597.0	605.4	620.8	640.4	672.6	710.1	753.5	820.8	888.0	951.1	1019.6
42.5°	569.9	579.1	592.2	611.9	640.7	677.3	719.7	777.9	848.1	909.2	971.5
45°	532.1	537.4	550.6	567.2	591.1	627.9	667.3	719.0	785.1	843.4	898.2
47.5°	494.0	498.7	506.9	522.1	548.8	578.4	615.2	661.7	719.6	777.9	824.2
50°	467.9	472.0	479.7	494.0	517.8	547.0	583.3	625.0	676.7	732.7	771.4
52.5°	441.6	443.9	451.2	467.4	487.3	516.1	548.5	586.9	635.3	681.7	720.9
55°	400.0	405.4	410.1	422.0	441.1	468.5	497.6	533.9	571.4	610.7	644.0
57.5°	356.5	362.4	369.3	379.8	394.9	420.3	446.5	476.0	508.0	540.5	568.5
60°	328.0	333.3	339.2	351.2	364.9	385.1	413.7	439.3	463.6	493.4	521.4
62.5°	299.9	305.2	312.1	321.7	334.8	354.1	378.0	400.2	425.6	451.5	472.3
65°	258.3	262.5	267.9	276.8	289.3	306.5	326.1	343.5	366.1	385.1	404.2
67.5°	212.8	220.7	227.7	235.0	245.6	261.7	275.9	292.4	307.7	321.9	339.2
70°	182.7	191.7	198.2	206.0	216.0	229.7	243.4	254.8	267.3	280.9	296.4
72.5°	157.5	164.5	169.6	177.9	187.0	199.8	212.5	221.9	232.0	241.4	256.4
75°	124.4	127.3	131.0	137.5	145.9	155.3	165.5	173.8	179.8	188.1	198.8
77.5°	89.4	95.1	97.5	102.1	108.1	114.1	120.7	127.8	133.5	136.4	144.6
80°	68.4	70.9	73.2	79.7	83.3	89.3	94.0	100.6	103.0	106.0	113.7
82.5°	53.2	54.7	56.1	57.9	60.0	66.0	70.7	74.9	77.2	78.4	84.2
85°	30.9	31.5	32.1	32.7	33.3	33.3	35.7	38.7	42.9	42.9	44.6
87.5°	16.5	16.7	16.2	15.2	15.8	15.3	15.2	14.6	15.4	16.2	17.0
90°	30.3	28.6	26.3	23.9	21.6	19.4	16.6	13.4	10.2	7.1	3.9
92.5°	29.3	27.6	25.2	22.9	20.6	18.3	17.0	16.9	16.7	16.5	16.4
95°	30.3	28.6	28.2	28.0	27.7	27.4	32.2	42.0	51.8	61.6	71.4
97.5°	34.4	34.3	66.5	98.7	130.9	163.1	176.2	170.0	163.8	157.7	151.6
100°	52.3	57.2	96.9	136.7	176.6	216.4	233.7	228.5	223.3	218.2	212.9
102.5°	222.3	275.3	280.4	285.7	290.8	296.0	296.7	292.9	289.1	285.3	281.5
105°	407.7	405.1	403.6	402.3	400.8	399.3	397.8	396.1	394.3	392.5	390.8
107.5°	506.4	505.1	503.1	501.2	499.2	497.2	495.8	495.0	494.1	493.3	492.3
110°	573.2	572.6	570.8	569.1	567.4	565.7	564.4	563.5	562.7	561.8	560.9



TEST NUMBER: P333091-935

CATALOG NUMBER: S124RDIW-S1020D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	637.9	638.1	637.2	636.5	635.6	634.8	633.6	632.1	630.5	629.0	627.4
115°	732.9	732.3	732.6	732.9	733.1	733.5	733.1	732.3	731.4	730.6	729.7
117.5°	829.8	829.9	829.3	828.7	828.0	827.4	826.6	825.4	824.2	823.0	821.9
120°	888.7	888.1	888.4	888.7	889.0	889.2	888.8	887.7	886.6	885.4	884.2
122.5°	947.7	947.4	946.9	946.5	946.2	945.7	945.2	944.4	943.7	943.1	942.4
125°	1029.2	1028.4	1028.9	1029.5	1030.1	1030.6	1030.4	1029.2	1028.0	1026.9	1025.8
127.5°	1111.8	1112.0	1110.6	1109.3	1108.0	1106.6	1105.9	1105.5	1105.3	1105.0	1104.7
130°	1161.1	1160.8	1159.9	1159.1	1158.2	1157.4	1156.8	1156.5	1156.2	1155.9	1155.6
132.5°	1209.9	1209.6	1208.5	1207.4	1206.3	1205.2	1204.5	1203.9	1203.4	1202.8	1202.3
135°	1276.9	1276.3	1275.2	1274.0	1272.9	1271.7	1271.3	1271.6	1271.9	1272.1	1272.5
137.5°	1341.4	1340.7	1339.5	1338.3	1337.0	1335.7	1335.0	1334.9	1334.7	1334.6	1334.6
140°	1381.1	1380.2	1379.7	1379.1	1378.5	1377.9	1377.3	1376.7	1376.2	1375.6	1375.0
142.5°	1418.2	1417.6	1417.3	1416.9	1416.6	1416.3	1415.6	1414.5	1413.5	1412.4	1411.4
145°	1471.4	1471.1	1471.1	1471.1	1471.1	1471.1	1470.7	1469.8	1469.0	1468.1	1467.2
147.5°	1517.9	1517.6	1517.9	1518.2	1518.5	1518.7	1518.1	1516.5	1514.8	1513.2	1511.7
150°	1547.7	1547.7	1548.0	1548.3	1548.6	1548.9	1548.4	1547.3	1546.1	1545.0	1543.9
152.5°	1573.1	1572.6	1573.1	1573.6	1574.2	1574.8	1574.5	1573.6	1572.7	1571.8	1570.8
155°	1607.3	1606.1	1607.1	1607.9	1608.8	1609.6	1609.9	1609.6	1609.3	1609.0	1608.8
157.5°	1637.0	1635.5	1636.5	1637.4	1638.4	1639.4	1640.0	1640.2	1640.4	1640.5	1640.7
160°	1656.0	1654.2	1654.5	1654.8	1655.0	1655.4	1656.0	1656.8	1657.7	1658.5	1659.4
162.5°	1671.5	1669.7	1670.1	1670.3	1670.6	1670.9	1671.6	1672.8	1673.8	1674.9	1676.0
165°	1692.8	1690.6	1690.6	1690.6	1690.6	1690.6	1691.3	1692.7	1694.2	1695.6	1697.0
167.5°	1708.7	1706.2	1706.3	1706.5	1706.7	1706.8	1707.6	1709.2	1710.6	1712.2	1713.6
170°	1718.8	1716.5	1716.2	1716.0	1715.6	1715.4	1716.1	1717.8	1719.5	1721.3	1723.0
172.5°	1725.0	1722.8	1722.4	1722.2	1721.9	1721.6	1722.3	1724.1	1725.8	1727.5	1729.2
175°	1732.1	1729.5	1729.2	1728.9	1728.6	1728.4	1729.1	1730.8	1732.5	1734.2	1735.9
177.5°	1735.8	1733.9	1733.5	1733.0	1732.5	1732.1	1732.7	1734.2	1735.9	1737.5	1739.1
180°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9



TEST NUMBER: P333091-935

CATALOG NUMBER: S124RDIW-S1020D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3
2.5°	1486.3	1490.6	1495.4	1504.4	1512.1	1515.4	1522.1	1526.8	1525.4	1532.1	1543.5
5°	1492.2	1508.3	1526.7	1545.8	1567.2	1585.0	1599.3	1613.6	1625.0	1638.7	1658.9
7.5°	1491.3	1519.8	1550.9	1585.0	1620.1	1650.5	1678.6	1707.2	1732.5	1760.3	1796.6
10°	1487.5	1525.5	1564.2	1608.9	1653.5	1695.7	1733.9	1769.5	1803.5	1839.8	1885.7
12.5°	1483.2	1527.0	1573.7	1627.5	1683.0	1733.9	1778.7	1830.1	1872.5	1919.3	1972.3
15°	1464.2	1523.1	1586.8	1656.5	1723.1	1791.6	1852.9	1916.0	1974.9	2030.8	2097.6
17.5°	1442.5	1510.5	1585.6	1667.9	1748.0	1831.3	1903.9	1983.5	2043.8	2118.8	2180.7
20°	1425.0	1498.1	1578.5	1670.8	1761.9	1854.1	1934.4	2015.4	2083.3	2158.9	2237.4
22.5°	1403.5	1483.8	1570.9	1666.5	1761.9	1862.7	1951.5	2032.0	2116.1	2201.2	2282.2
25°	1369.0	1452.3	1544.5	1649.3	1758.9	1861.8	1957.1	2057.0	2147.5	2239.8	2312.4
27.5°	1326.6	1414.1	1511.4	1619.5	1731.8	1837.3	1949.5	2056.0	2147.1	2235.8	2299.2
30°	1292.8	1385.1	1478.5	1588.0	1704.7	1817.7	1938.0	2044.5	2140.4	2220.2	2255.8
32.5°	1258.0	1345.6	1441.8	1552.8	1672.3	1794.0	1913.2	2022.1	2110.8	2158.7	2159.6
35°	1197.6	1279.7	1379.7	1488.7	1611.3	1743.4	1864.2	1971.3	2025.5	2029.6	1971.3
37.5°	1131.6	1206.9	1301.4	1410.4	1544.7	1676.1	1799.6	1871.0	1889.1	1828.5	1720.6
40°	1084.5	1154.1	1245.2	1357.1	1490.4	1626.1	1738.6	1791.0	1771.9	1673.7	1553.5
42.5°	1034.9	1099.8	1187.6	1298.0	1431.8	1569.0	1664.8	1692.9	1642.4	1529.0	1388.3
45°	954.2	1013.7	1100.5	1211.9	1340.4	1469.0	1541.6	1527.3	1443.4	1308.9	1151.2
47.5°	870.0	927.5	1005.6	1108.6	1240.3	1351.3	1400.4	1357.4	1237.9	1089.9	961.7
50°	814.2	873.1	945.2	1043.4	1163.6	1270.7	1302.3	1236.8	1104.1	961.8	844.0
52.5°	759.5	809.9	880.5	975.3	1090.3	1180.8	1197.6	1122.1	985.1	857.6	753.0
55°	676.1	722.0	781.5	870.8	970.2	1047.0	1038.0	941.1	816.7	707.7	625.6
57.5°	595.6	630.1	685.1	768.8	856.0	907.6	874.9	792.2	676.3	587.1	517.8
60°	542.3	574.4	625.6	698.8	775.6	804.7	777.3	687.5	595.8	514.3	455.9
62.5°	491.8	520.1	564.1	632.1	694.1	711.4	682.1	603.6	521.1	451.4	403.1
65°	418.4	444.6	482.2	530.4	573.2	581.5	562.5	482.2	419.7	361.3	328.0
67.5°	351.9	369.0	398.3	440.0	462.7	467.6	430.8	380.3	325.2	289.4	264.2
70°	307.1	319.0	346.4	369.0	387.4	388.1	354.1	313.7	271.4	242.3	223.8
72.5°	263.8	275.3	295.9	311.4	325.5	321.0	289.9	258.0	223.8	201.8	188.1
75°	203.5	213.7	224.4	231.5	231.5	225.6	202.9	179.2	159.5	146.5	142.2
77.5°	148.0	156.3	159.9	158.8	156.7	147.4	133.1	117.5	110.5	104.3	101.2
80°	116.1	119.7	120.8	117.9	114.3	103.6	94.0	87.5	80.9	78.6	77.4
82.5°	86.1	89.2	86.1	86.9	79.0	70.3	65.0	62.8	60.0	59.1	57.9
85°	45.8	45.2	44.1	41.1	35.7	34.5	33.9	33.3	32.1	32.7	31.5
87.5°	17.1	16.4	15.1	15.2	15.8	15.2	16.2	16.7	17.1	17.0	18.3
90°	7.1	10.2	13.4	16.6	19.4	21.6	23.9	26.3	28.6	30.3	32.0
92.5°	16.5	16.7	16.9	17.0	18.3	20.6	22.9	25.2	27.6	29.3	31.0
95°	61.6	51.8	42.0	32.2	27.4	27.7	28.0	28.2	28.6	30.3	32.0
97.5°	157.7	163.8	170.0	176.2	163.1	130.9	98.7	66.5	34.3	34.4	34.6
100°	218.2	223.3	228.5	233.7	216.4	176.6	136.7	96.9	57.2	52.3	47.4
102.5°	285.3	289.1	292.9	296.7	296.0	290.8	285.7	280.4	275.3	222.3	169.4
105°	392.5	394.3	396.1	397.8	399.3	400.8	402.3	403.6	405.1	407.7	410.3
107.5°	493.3	494.1	495.0	495.8	497.2	499.2	501.2	503.1	505.1	506.4	507.6
110°	561.8	562.7	563.5	564.4	565.7	567.4	569.1	570.8	572.6	573.2	573.8



TEST NUMBER: P333091-935

CATALOG NUMBER: S124RDIW-S1020D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	629.0	630.5	632.1	633.6	634.8	635.6	636.5	637.2	638.1	637.9	637.8
115°	730.6	731.4	732.3	733.1	733.5	733.1	732.9	732.6	732.3	732.9	733.5
117.5°	823.0	824.2	825.4	826.6	827.4	828.0	828.7	829.3	829.9	829.8	829.7
120°	885.4	886.6	887.7	888.8	889.2	889.0	888.7	888.4	888.1	888.7	889.2
122.5°	943.1	943.7	944.4	945.2	945.7	946.2	946.5	946.9	947.4	947.7	948.0
125°	1026.9	1028.0	1029.2	1030.4	1030.6	1030.1	1029.5	1028.9	1028.4	1029.2	1030.1
127.5°	1105.0	1105.3	1105.5	1105.9	1106.6	1108.0	1109.3	1110.6	1112.0	1111.8	1111.6
130°	1155.9	1156.2	1156.5	1156.8	1157.4	1158.2	1159.1	1159.9	1160.8	1161.1	1161.4
132.5°	1202.8	1203.4	1203.9	1204.5	1205.2	1206.3	1207.4	1208.5	1209.6	1209.9	1210.2
135°	1272.1	1271.9	1271.6	1271.3	1271.7	1272.9	1274.0	1275.2	1276.3	1276.9	1277.5
137.5°	1334.6	1334.7	1334.9	1335.0	1335.7	1337.0	1338.3	1339.5	1340.7	1341.4	1342.0
140°	1375.6	1376.2	1376.7	1377.3	1377.9	1378.5	1379.1	1379.7	1380.2	1381.1	1382.0
142.5°	1412.4	1413.5	1414.5	1415.6	1416.3	1416.6	1416.9	1417.3	1417.6	1418.2	1418.9
145°	1468.1	1469.0	1469.8	1470.7	1471.1	1471.1	1471.1	1471.1	1471.1	1471.4	1471.7
147.5°	1513.2	1514.8	1516.5	1518.1	1518.7	1518.5	1518.2	1517.9	1517.6	1517.9	1518.0
150°	1545.0	1546.1	1547.3	1548.4	1548.9	1548.6	1548.3	1548.0	1547.7	1547.7	1547.7
152.5°	1571.8	1572.7	1573.6	1574.5	1574.8	1574.2	1573.6	1573.1	1572.6	1573.1	1573.6
155°	1609.0	1609.3	1609.6	1609.9	1609.6	1608.8	1607.9	1607.1	1606.1	1607.3	1608.4
157.5°	1640.5	1640.4	1640.2	1640.0	1639.4	1638.4	1637.4	1636.5	1635.5	1637.0	1638.5
160°	1658.5	1657.7	1656.8	1656.0	1655.4	1655.0	1654.8	1654.5	1654.2	1656.0	1657.7
162.5°	1674.9	1673.8	1672.8	1671.6	1670.9	1670.6	1670.3	1670.1	1669.7	1671.5	1673.3
165°	1695.6	1694.2	1692.7	1691.3	1690.6	1690.6	1690.6	1690.6	1690.6	1692.8	1695.1
167.5°	1712.2	1710.6	1709.2	1707.6	1706.8	1706.7	1706.5	1706.3	1706.2	1708.7	1711.2
170°	1721.3	1719.5	1717.8	1716.1	1715.4	1715.6	1716.0	1716.2	1716.5	1718.8	1721.1
172.5°	1727.5	1725.8	1724.1	1722.3	1721.6	1721.9	1722.2	1722.4	1722.8	1725.0	1727.3
175°	1734.2	1732.5	1730.8	1729.1	1728.4	1728.6	1728.9	1729.2	1729.5	1732.1	1734.7
177.5°	1737.5	1735.9	1734.2	1732.7	1732.1	1732.5	1733.0	1733.5	1733.9	1735.8	1737.6
180°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9



TEST NUMBER: P333091-935

CATALOG NUMBER: S124RDIW-S1020D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3
2.5°	1549.7	1551.6	1553.1	1557.8	1558.2	1562.5	1558.2
5°	1677.9	1686.3	1699.4	1712.4	1713.6	1721.9	1707.1
7.5°	1821.7	1841.0	1853.0	1874.2	1882.6	1887.7	1879.2
10°	1920.7	1938.6	1970.1	1985.6	2001.1	2003.5	1996.3
12.5°	2016.5	2044.8	2069.7	2098.9	2098.3	2119.2	2111.6
15°	2144.0	2173.2	2207.6	2240.4	2252.3	2252.3	2261.8
17.5°	2234.9	2288.4	2324.1	2349.8	2377.9	2382.7	2379.5
20°	2296.4	2354.1	2392.2	2425.5	2444.6	2449.9	2449.9
22.5°	2342.0	2391.2	2428.4	2458.3	2474.1	2480.4	2478.5
25°	2373.7	2416.0	2438.6	2447.5	2451.7	2450.5	2439.2
27.5°	2330.4	2328.5	2314.2	2286.8	2266.2	2253.8	2239.5
30°	2247.6	2216.6	2180.8	2141.6	2091.0	2052.3	2040.4
32.5°	2124.2	2054.7	1994.2	1928.7	1874.3	1835.7	1819.5
35°	1885.7	1775.6	1685.7	1607.1	1550.0	1514.2	1502.4
37.5°	1602.6	1496.0	1384.7	1308.5	1261.1	1225.0	1211.6
40°	1422.5	1306.5	1209.4	1138.1	1089.3	1054.1	1053.5
42.5°	1258.3	1147.5	1056.2	1004.7	952.1	928.8	928.8
45°	1030.3	941.6	864.3	823.8	792.2	773.2	767.8
47.5°	853.1	779.7	728.1	695.9	670.2	658.1	650.2
50°	753.5	689.2	648.2	620.2	605.9	590.5	589.3
52.5°	670.7	618.8	586.8	564.0	546.0	536.7	536.9
55°	563.7	522.6	500.0	482.7	468.5	461.3	458.3
57.5°	474.8	444.0	427.6	411.7	405.7	400.1	398.6
60°	419.7	398.8	383.3	370.8	361.9	360.1	359.5
62.5°	373.9	352.1	341.4	331.7	325.2	322.4	321.4
65°	308.3	292.2	282.8	275.0	272.6	268.5	267.9
67.5°	248.6	238.9	232.6	227.2	224.0	223.8	223.8
70°	211.9	206.6	201.2	198.2	196.4	195.2	195.2
72.5°	180.5	176.5	172.1	170.6	170.2	169.0	168.6
75°	137.5	133.4	133.9	131.0	128.5	125.6	123.8
77.5°	97.5	94.5	93.9	93.6	91.5	91.2	92.1
80°	75.6	72.6	72.0	72.6	72.0	70.3	70.3
82.5°	57.5	55.0	54.4	54.1	53.5	54.1	53.1
85°	30.9	29.8	29.8	29.8	30.9	30.4	29.8
87.5°	17.7	17.6	18.3	17.9	18.0	17.7	18.3
90°	33.8	35.5	36.7	37.2	37.8	38.4	38.9
92.5°	32.7	34.4	35.4	35.5	35.6	35.7	35.8
95°	33.8	35.5	36.5	36.8	37.1	37.4	37.6
97.5°	34.8	35.0	35.2	35.5	35.8	36.1	36.3
100°	42.4	37.5	35.2	35.5	35.8	36.1	36.3
102.5°	116.5	63.6	37.2	37.2	37.3	37.4	37.4
105°	412.9	415.5	411.6	401.2	390.8	380.5	370.1
107.5°	508.9	510.1	511.3	512.5	513.5	514.6	515.7
110°	574.4	574.9	575.7	576.5	577.4	578.2	579.1



TEST NUMBER: P333091-935

CATALOG NUMBER: S124RDIW-S1020D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	637.7	637.6	638.1	639.2	640.2	641.4	642.5
115°	734.0	734.6	734.9	734.9	734.9	734.9	734.9
117.5°	829.6	829.5	829.4	829.2	829.1	829.1	828.9
120°	889.8	890.4	890.4	889.8	889.2	888.7	888.1
122.5°	948.4	948.7	948.6	948.0	947.4	946.8	946.3
125°	1031.0	1031.8	1032.4	1032.7	1032.9	1033.3	1033.5
127.5°	1111.5	1111.3	1111.0	1110.9	1110.6	1110.3	1110.2
130°	1161.7	1161.9	1162.1	1162.1	1162.1	1162.1	1162.1
132.5°	1210.5	1210.7	1210.8	1210.6	1210.3	1210.1	1209.9
135°	1278.1	1278.7	1279.3	1279.8	1280.4	1281.0	1281.5
137.5°	1342.6	1343.3	1343.5	1343.3	1343.2	1343.0	1342.8
140°	1382.9	1383.7	1384.2	1384.6	1384.8	1385.1	1385.4
142.5°	1419.5	1420.1	1420.5	1420.6	1420.6	1420.6	1420.7
145°	1472.0	1472.2	1472.7	1473.3	1473.9	1474.5	1475.0
147.5°	1518.3	1518.5	1518.8	1519.1	1519.3	1519.7	1519.9
150°	1547.7	1547.7	1547.9	1548.2	1548.4	1548.8	1549.0
152.5°	1574.0	1574.5	1574.6	1574.4	1574.3	1574.1	1573.9
155°	1609.6	1610.8	1610.9	1610.1	1609.2	1608.3	1607.5
157.5°	1640.0	1641.5	1641.5	1640.0	1638.5	1637.0	1635.5
160°	1659.4	1661.1	1661.1	1659.4	1657.7	1656.0	1654.2
162.5°	1675.0	1676.7	1676.5	1674.6	1672.7	1670.7	1668.7
165°	1697.5	1699.8	1699.6	1697.0	1694.4	1691.9	1689.3
167.5°	1713.7	1716.3	1716.1	1713.2	1710.4	1707.4	1704.6
170°	1723.5	1725.8	1725.4	1722.6	1719.7	1716.8	1713.9
172.5°	1729.7	1732.0	1731.6	1728.5	1725.4	1722.3	1719.1
175°	1737.3	1739.9	1739.5	1735.9	1732.5	1729.1	1725.6
177.5°	1739.5	1741.3	1740.9	1738.1	1735.3	1732.5	1729.7
180°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9

(END OF REPORT)