

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333104-935

Luminaire Tested: **S124RDIW-S1195D1050U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333104-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1195D1050U935-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7445.2 lumens
Efficiency: N/A
Efficacy: 110.5 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 67.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333104-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333104-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63	58
1	100	96	92	89	93	90	86	83	78	75	73	67	65	64	57	56	55	50
2	92	84	78	73	85	79	74	69	69	65	62	59	57	54	51	49	47	43
3	84	75	67	62	78	70	64	59	61	56	52	53	49	46	45	43	40	37
4	77	66	59	53	72	62	55	50	55	49	45	48	43	40	41	38	35	32
5	71	59	51	46	66	56	49	43	49	43	39	43	38	35	37	34	31	28
6	65	54	46	40	61	50	43	38	44	39	34	39	34	31	34	30	27	25
7	61	48	41	35	56	46	39	34	40	35	31	36	31	28	31	27	25	22
8	56	44	36	31	53	42	35	30	37	31	27	33	28	25	28	25	22	20
9	53	40	33	28	49	38	31	27	34	28	25	30	26	22	26	23	20	18
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13774	13774	13774	13774
5°	15977	13816	12211	13816
10°	18901	13755	10899	13755
15°	21833	13628	9365	13628
20°	24308	13454	8469	13454
25°	25093	13281	7863	13281
30°	21967	13073	7498	13073
35°	17100	12764	7276	12764
40°	12823	12410	7158	12410
45°	10123	11843	7096	11843
50°	8547	11189	6889	11189
55°	7450	10469	6521	10469
60°	6704	9723	5772	9723
65°	5910	8915	4963	8915
70°	5323	8080	4480	8080
75°	4460	7162	3815	7162
80°	3770	6104	3580	6104
85°	3186	4780	3186	4780



TEST NUMBER: P333104-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.3	2.2
10°-20°	498.7	6.7
20°-30°	780.0	10.5
30°-40°	867.1	11.6
40°-50°	769.3	10.3
50°-60°	599.5	8.1
60°-70°	392.5	5.3
70°-80°	193.0	2.6
80°-90°	51.0	0.7
90°-100°	74.4	1.0
100°-110°	220.4	3.0
110°-120°	374.0	5.0
120°-130°	493.2	6.6
130°-140°	553.9	7.4
140°-150°	544.3	7.3
150°-160°	457.8	6.1
160°-170°	304.6	4.1
170°-180°	106.6	1.4
0°-30°	1444.0	19.4
0°-40°	2311.0	31.0
0°-60°	3679.8	49.4
0°-90°	4316.2	58.0
90°-120°	668.7	9.0
90°-150°	2260.0	30.4
90°-180°	3129.0	42.0
0°-180°	7445.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1706	1706	1706	1706	1706	
5°	1972	1705	1507	1705	1972	199
15°	2612	1631	1120	1631	2612	743
25°	2817	1491	883	1491	2817	1250
35°	1735	1295	738	1295	1735	1088
45°	887	1037	622	1037	887	702
55°	529	744	463	744	529	481
65°	309	467	260	467	309	311
75°	143	230	122	230	143	157
85°	34	52	34	52	34	39
90°	26	3	26	3	26	15
95°	69	52	69	52	69	72
105°	213	203	213	203	213	224
115°	377	380	377	380	377	373
125°	550	554	550	554	550	490
135°	715	714	715	714	715	552
145°	869	868	869	868	869	544
155°	994	994	994	994	994	457
165°	1080	1082	1080	1082	1080	304
175°	1121	1126	1121	1126	1121	106
180°	1128	1128	1128	1128	1128	



TEST NUMBER: P333104-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2
2.5°	1799.7	1804.7	1799.7	1799.1	1793.6	1792.0	1789.8	1782.6	1769.4	1761.8	1763.4
5°	1971.5	1988.7	1979.1	1977.7	1962.6	1947.5	1937.9	1915.9	1892.5	1876.7	1863.6
7.5°	2170.3	2180.2	2174.2	2164.6	2140.1	2126.2	2103.9	2074.9	2033.0	2001.0	1971.7
10°	2305.7	2313.9	2311.2	2293.3	2275.4	2238.9	2218.4	2177.8	2124.9	2082.9	2043.8
12.5°	2438.7	2447.6	2423.4	2424.1	2390.3	2361.6	2328.9	2277.9	2216.7	2162.7	2113.6
15°	2612.3	2601.3	2601.3	2587.5	2549.7	2509.8	2476.1	2422.5	2345.5	2280.9	2212.9
17.5°	2748.1	2751.9	2746.2	2713.9	2684.2	2642.9	2581.2	2518.6	2447.1	2360.3	2290.8
20°	2829.5	2829.5	2823.3	2801.3	2762.8	2718.8	2652.1	2584.0	2493.3	2406.0	2327.6
22.5°	2862.5	2864.6	2857.4	2839.2	2804.6	2761.7	2704.9	2635.8	2542.3	2443.9	2346.9
25°	2817.1	2830.2	2831.5	2826.7	2816.4	2790.2	2741.5	2670.6	2586.8	2480.3	2375.8
27.5°	2586.4	2602.9	2617.4	2641.1	2672.7	2689.2	2691.4	2655.4	2582.2	2479.7	2374.6
30°	2356.5	2370.2	2414.9	2473.4	2518.8	2560.0	2595.7	2605.4	2564.1	2472.0	2361.3
32.5°	2101.4	2120.0	2164.7	2227.6	2303.2	2373.0	2453.3	2494.2	2493.2	2437.9	2335.5
35°	1735.1	1748.9	1790.1	1856.1	1946.8	2050.6	2177.8	2276.7	2344.2	2339.3	2276.7
37.5°	1399.3	1414.9	1456.6	1511.2	1599.2	1727.8	1850.8	1987.2	2111.8	2181.8	2160.9
40°	1216.8	1217.5	1258.0	1314.4	1396.9	1508.9	1643.0	1794.2	1933.0	2046.5	2068.5
42.5°	1072.6	1072.8	1099.6	1160.4	1219.8	1325.3	1453.2	1603.4	1765.9	1896.9	1955.2
45°	886.7	892.9	915.0	951.4	998.2	1087.5	1189.9	1329.5	1511.7	1667.0	1763.9
47.5°	751.0	760.0	774.0	803.7	841.0	900.5	985.2	1110.6	1258.8	1429.7	1567.6
50°	680.5	681.9	699.8	716.3	748.6	796.1	870.3	974.7	1110.9	1275.1	1428.5
52.5°	620.1	619.7	630.5	651.4	677.7	714.6	774.6	869.7	990.4	1137.7	1296.0
55°	529.3	532.8	541.0	557.5	577.5	603.6	651.0	722.5	817.3	943.1	1086.8
57.5°	460.3	462.1	468.6	475.5	493.9	512.8	548.5	598.1	678.1	781.1	915.0
60°	415.2	415.9	417.9	428.3	442.7	460.5	484.7	526.6	593.9	688.1	794.0
62.5°	371.2	372.5	375.7	383.1	394.3	406.7	431.9	465.5	521.3	601.8	697.2
65°	309.4	310.0	314.9	317.6	326.5	337.5	356.1	378.8	417.2	484.7	556.8
67.5°	258.5	258.5	258.7	262.4	268.6	276.0	287.1	305.2	334.2	375.7	439.3
70°	225.5	225.5	226.9	228.9	232.4	238.5	244.7	258.5	279.8	313.5	362.3
72.5°	194.7	195.2	196.6	197.0	198.8	203.9	208.4	217.2	233.1	258.5	297.9
75°	143.0	145.1	148.5	151.3	154.6	153.9	158.8	164.3	169.1	184.3	206.9
77.5°	106.4	105.3	105.7	108.1	108.5	109.2	112.6	116.8	120.5	127.6	135.7
80°	81.1	81.1	83.2	83.9	83.2	83.9	87.3	89.4	90.7	93.5	101.1
82.5°	61.3	62.4	61.7	62.4	62.9	63.5	66.4	66.8	68.2	69.3	72.5
85°	34.4	35.0	35.7	34.4	34.4	34.4	35.7	36.4	37.8	37.1	38.5
87.5°	17.3	16.7	17.2	17.1	17.6	16.9	17.2	18.1	16.7	17.0	16.7
90°	26.2	25.7	25.4	25.0	24.6	23.8	22.6	21.5	20.3	19.2	17.7
92.5°	38.7	38.5	38.2	38.1	37.8	37.4	36.6	35.9	35.2	34.5	33.5
95°	68.9	68.9	68.9	68.9	68.9	68.6	68.0	67.4	66.9	66.3	64.9
97.5°	108.0	108.0	108.0	108.0	108.0	107.6	106.9	106.2	105.6	104.9	103.2
100°	135.2	135.2	135.2	135.2	135.2	135.0	134.6	134.2	133.8	133.5	131.7
102.5°	165.9	165.7	165.6	165.4	165.3	165.0	164.4	163.8	163.3	162.7	161.2
105°	212.8	212.2	211.6	211.1	210.5	209.9	209.3	208.8	208.2	207.6	206.8
107.5°	258.6	258.6	258.6	258.6	258.6	258.5	257.9	257.4	256.8	256.2	256.1
110°	291.4	290.8	290.2	289.6	289.0	288.9	289.3	289.6	290.1	290.4	290.7



TEST NUMBER: P333104-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	324.9	324.7	324.6	324.5	324.3	324.3	324.4	324.5	324.6	324.7	325.0
115°	376.8	377.0	377.2	377.4	377.5	377.8	378.0	378.2	378.3	378.6	378.9
117.5°	426.4	426.7	427.1	427.5	427.9	428.4	429.0	429.7	430.4	431.0	431.4
120°	464.0	463.6	463.2	462.9	462.4	462.8	463.7	464.7	465.7	466.7	467.3
122.5°	495.4	496.1	496.8	497.5	498.2	498.9	499.6	500.2	500.8	501.5	501.8
125°	549.5	549.9	550.3	550.7	551.0	551.5	551.8	552.2	552.6	553.0	553.2
127.5°	599.6	599.9	600.2	600.5	600.8	601.2	601.6	601.9	602.4	602.7	603.0
130°	632.4	633.2	634.0	634.7	635.5	636.0	636.5	636.8	637.2	637.6	637.6
132.5°	667.3	667.5	667.9	668.2	668.5	668.8	669.3	669.6	670.0	670.4	670.5
135°	715.2	715.8	716.4	717.0	717.6	718.1	718.4	718.8	719.2	719.6	719.6
137.5°	765.6	765.5	765.4	765.3	765.2	765.3	765.9	766.4	766.9	767.4	767.1
140°	796.3	796.5	796.8	796.9	797.1	797.3	797.5	797.7	797.9	798.1	798.1
142.5°	827.1	827.1	827.2	827.2	827.2	827.2	827.2	827.3	827.3	827.4	827.6
145°	868.7	869.4	869.9	870.5	871.1	871.4	871.7	871.8	872.0	872.2	872.0
147.5°	910.9	911.1	911.4	911.5	911.7	911.9	912.1	912.2	912.4	912.5	912.7
150°	936.8	936.9	937.2	937.4	937.5	937.6	937.6	937.6	937.6	937.6	937.6
152.5°	960.5	961.0	961.5	962.0	962.5	962.5	962.1	961.6	961.1	960.7	960.5
155°	993.5	994.3	995.1	995.8	996.6	996.6	995.8	995.1	994.3	993.5	993.7
157.5°	1023.0	1023.6	1024.2	1024.9	1025.6	1025.6	1025.0	1024.5	1023.9	1023.3	1023.3
160°	1039.7	1040.7	1041.6	1042.6	1043.5	1043.8	1043.2	1042.6	1042.0	1041.5	1041.6
162.5°	1057.1	1058.1	1059.1	1060.1	1061.0	1061.0	1059.9	1058.9	1057.8	1056.8	1057.0
165°	1079.8	1080.6	1081.3	1082.1	1082.9	1082.7	1081.6	1080.4	1079.3	1078.1	1078.5
167.5°	1096.1	1097.3	1098.5	1099.7	1100.9	1100.9	1099.7	1098.5	1097.3	1096.2	1096.1
170°	1105.1	1106.5	1107.8	1109.2	1110.5	1110.6	1109.5	1108.3	1107.2	1106.0	1105.8
172.5°	1112.8	1114.1	1115.5	1116.9	1118.2	1118.3	1116.9	1115.6	1114.3	1112.9	1112.9
175°	1120.8	1122.1	1123.5	1124.9	1126.3	1126.3	1124.9	1123.5	1122.1	1120.8	1121.0
177.5°	1125.0	1126.3	1127.5	1128.7	1130.0	1130.1	1128.9	1127.9	1126.8	1125.7	1125.7
180°	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8



TEST NUMBER: P333104-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2
2.5°	1757.9	1750.2	1746.4	1737.6	1727.1	1721.6	1716.7	1709.5	1700.1	1690.2	1683.1
5°	1847.1	1830.7	1810.0	1785.3	1763.2	1742.0	1723.4	1704.9	1683.5	1661.6	1639.5
7.5°	1938.7	1906.3	1871.2	1830.7	1791.1	1755.3	1722.3	1690.7	1654.9	1622.9	1593.7
10°	2002.5	1958.5	1909.7	1858.1	1806.6	1761.9	1717.9	1678.0	1634.0	1594.8	1561.9
12.5°	2054.2	2002.5	1943.8	1879.6	1817.6	1763.5	1713.0	1661.0	1610.9	1568.5	1524.5
15°	2139.9	2069.2	1990.1	1913.1	1832.7	1759.1	1691.1	1630.6	1573.6	1513.7	1471.8
17.5°	2199.0	2115.0	2018.9	1926.3	1831.3	1744.6	1666.0	1594.1	1528.2	1467.1	1417.2
20°	2234.1	2141.3	2034.8	1929.6	1823.1	1730.3	1645.7	1566.0	1497.9	1431.9	1380.4
22.5°	2253.9	2151.2	2034.8	1924.7	1814.3	1713.7	1620.9	1537.9	1463.8	1397.8	1340.7
25°	2260.3	2150.3	2031.4	1904.9	1783.9	1677.3	1581.1	1491.0	1408.5	1342.6	1282.0
27.5°	2251.5	2121.9	2000.2	1870.4	1745.5	1633.2	1532.1	1437.5	1355.0	1284.1	1222.1
30°	2238.3	2099.4	1968.8	1834.1	1707.5	1599.7	1493.1	1402.4	1316.5	1242.9	1180.3
32.5°	2209.7	2071.9	1931.4	1793.4	1665.3	1554.0	1452.9	1361.7	1277.4	1202.2	1135.7
35°	2153.0	2013.4	1860.9	1719.2	1593.5	1478.0	1383.1	1295.1	1214.7	1134.3	1064.1
37.5°	2078.4	1935.8	1784.0	1628.9	1503.0	1394.0	1306.9	1224.3	1145.8	1072.4	994.7
40°	2008.0	1878.1	1721.3	1567.4	1438.1	1332.9	1252.5	1177.6	1098.5	1025.6	948.0
42.5°	1922.8	1812.1	1653.7	1499.2	1371.6	1270.2	1195.3	1122.1	1050.2	979.5	898.5
45°	1780.5	1696.6	1548.1	1399.6	1271.1	1170.7	1102.0	1037.3	974.0	906.7	830.4
47.5°	1617.4	1560.6	1432.4	1280.4	1161.5	1071.2	1004.8	951.9	898.5	831.1	764.1
50°	1504.1	1467.7	1343.9	1205.1	1091.7	1008.5	940.4	890.9	846.2	781.6	721.8
52.5°	1383.1	1363.7	1259.2	1126.4	1016.8	935.3	877.2	832.6	787.4	733.7	677.8
55°	1198.9	1209.2	1120.5	1005.7	902.6	833.9	780.9	743.8	705.3	660.0	616.6
57.5°	1010.6	1048.2	988.7	887.9	791.3	727.7	687.9	656.6	624.3	586.7	549.7
60°	897.8	929.4	895.7	807.0	722.5	663.4	626.3	602.2	569.9	535.5	507.3
62.5°	787.8	821.7	801.7	730.0	651.5	600.7	567.9	545.5	521.5	491.5	462.3
65°	649.6	671.6	662.0	612.5	556.8	513.5	483.3	466.7	444.8	422.8	396.7
67.5°	497.6	540.0	534.4	508.2	460.0	426.2	406.4	391.8	371.8	355.4	337.7
70°	409.1	448.2	447.5	426.2	400.1	368.4	354.7	342.3	324.4	308.7	294.2
72.5°	334.8	370.7	376.0	359.6	341.8	317.9	304.7	296.2	278.8	267.9	256.2
75°	234.5	260.5	267.4	267.4	259.2	246.8	235.1	229.6	217.2	207.6	200.7
77.5°	153.7	170.2	180.9	183.4	184.7	180.6	170.9	167.0	157.6	154.1	147.5
80°	108.6	119.6	132.0	136.1	139.6	138.2	134.1	131.3	122.3	118.9	116.1
82.5°	75.1	81.1	91.3	100.4	99.4	103.0	99.4	97.2	90.5	89.2	86.4
85°	39.2	39.9	41.2	47.4	50.9	52.3	53.0	51.6	49.5	49.5	44.7
87.5°	16.4	15.6	16.4	16.0	16.1	17.9	19.1	19.2	18.0	16.8	15.6
90°	16.1	14.6	13.0	11.1	9.0	6.9	4.7	2.6	4.7	6.9	9.0
92.5°	32.4	31.3	30.2	28.4	26.0	23.6	21.1	18.7	21.1	23.6	26.0
95°	63.5	62.3	60.9	59.3	57.6	55.8	54.1	52.3	54.1	55.8	57.6
97.5°	101.7	100.0	98.5	97.0	95.6	94.2	92.8	91.4	92.8	94.2	95.6
100°	129.9	128.2	126.5	125.2	124.4	123.6	122.9	122.1	122.9	123.6	124.4
102.5°	159.5	158.0	156.4	155.4	155.2	154.8	154.5	154.2	154.5	154.8	155.2
105°	206.0	205.3	204.5	204.0	203.8	203.6	203.5	203.2	203.5	203.6	203.8
107.5°	256.1	255.9	255.8	255.6	255.4	255.1	254.9	254.7	254.9	255.1	255.4
110°	290.8	291.0	291.2	291.1	290.8	290.3	290.0	289.6	290.0	290.3	290.8



TEST NUMBER: P333104-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	325.4	325.7	326.1	326.1	326.1	326.1	326.0	325.9	326.0	326.1	326.1
115°	379.4	379.7	380.1	380.3	380.3	380.3	380.3	380.3	380.3	380.3	380.3
117.5°	431.6	431.9	432.1	432.2	432.0	431.9	431.7	431.6	431.7	431.9	432.0
120°	467.8	468.4	469.0	468.9	468.1	467.4	466.6	465.8	466.6	467.4	468.1
122.5°	502.0	502.3	502.7	502.6	502.3	502.0	501.7	501.4	501.7	502.0	502.3
125°	553.4	553.5	553.8	553.9	553.9	553.9	553.9	553.9	553.9	553.9	553.9
127.5°	603.3	603.6	604.0	603.8	603.2	602.6	602.1	601.5	602.1	602.6	603.2
130°	637.6	637.6	637.6	637.3	636.7	636.1	635.6	635.0	635.6	636.1	636.7
132.5°	670.7	670.9	671.0	670.9	670.5	670.0	669.6	669.2	669.6	670.0	670.5
135°	719.6	719.6	719.6	719.0	717.8	716.7	715.5	714.4	715.5	716.7	717.8
137.5°	766.8	766.5	766.1	765.7	765.2	764.7	764.1	763.5	764.1	764.7	765.2
140°	798.1	798.1	798.1	797.9	797.5	797.1	796.8	796.3	796.8	797.1	797.5
142.5°	827.7	827.9	828.0	827.9	827.5	827.2	826.7	826.4	826.7	827.2	827.5
145°	871.8	871.7	871.4	871.0	870.2	869.4	868.7	867.9	868.7	869.4	870.2
147.5°	912.8	913.0	913.2	912.7	911.8	910.9	910.0	909.0	910.0	910.9	911.8
150°	937.6	937.6	937.6	937.3	936.5	935.7	935.0	934.2	935.0	935.7	936.5
152.5°	960.4	960.2	960.0	959.8	959.2	958.8	958.4	957.9	958.4	958.8	959.2
155°	993.9	994.0	994.3	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4
157.5°	1023.4	1023.4	1023.5	1023.6	1024.0	1024.3	1024.7	1025.0	1024.7	1024.3	1024.0
160°	1041.8	1042.0	1042.2	1042.4	1042.6	1042.8	1043.0	1043.2	1043.0	1042.8	1042.6
162.5°	1057.2	1057.4	1057.6	1057.9	1058.4	1058.9	1059.5	1059.9	1059.5	1058.9	1058.4
165°	1078.8	1079.3	1079.6	1080.1	1080.7	1081.2	1081.8	1082.4	1081.8	1081.2	1080.7
167.5°	1096.1	1096.1	1096.1	1096.5	1097.3	1098.1	1098.9	1099.7	1098.9	1098.1	1097.3
170°	1105.6	1105.4	1105.2	1105.6	1106.6	1107.5	1108.5	1109.5	1108.5	1107.5	1106.6
172.5°	1112.9	1112.8	1112.8	1113.2	1114.0	1114.8	1115.6	1116.5	1115.6	1114.8	1114.0
175°	1121.2	1121.4	1121.6	1122.1	1123.2	1124.1	1125.1	1126.0	1125.1	1124.1	1123.2
177.5°	1125.7	1125.7	1125.7	1126.1	1126.9	1127.7	1128.4	1129.2	1128.4	1127.7	1126.9
180°	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8



TEST NUMBER: P333104-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2
2.5°	1675.4	1669.9	1662.8	1654.5	1644.6	1635.8	1631.9	1635.3	1636.9	1632.5	1631.9
5°	1624.4	1607.2	1593.5	1572.9	1556.3	1542.6	1533.0	1528.9	1530.3	1519.2	1516.5
7.5°	1567.1	1546.7	1524.1	1499.7	1476.9	1456.6	1446.0	1440.3	1428.7	1423.7	1415.3
10°	1530.3	1502.7	1480.7	1451.8	1425.7	1401.7	1390.0	1380.4	1368.6	1363.1	1351.5
12.5°	1492.3	1460.3	1436.1	1406.2	1379.5	1350.6	1339.4	1321.5	1303.2	1291.7	1276.7
15°	1438.8	1400.3	1370.7	1335.0	1303.4	1270.4	1240.8	1207.8	1195.4	1169.3	1154.2
17.5°	1376.2	1337.2	1300.6	1252.7	1203.9	1162.9	1131.4	1099.8	1080.8	1064.1	1056.4
20°	1335.0	1299.2	1248.4	1192.7	1138.4	1093.0	1067.6	1047.0	1026.3	1014.7	1006.4
22.5°	1296.0	1250.3	1191.2	1131.1	1076.8	1041.3	1019.8	998.6	981.8	970.7	959.7
25°	1230.5	1170.7	1108.1	1039.4	1002.3	971.4	948.0	930.7	920.5	906.0	900.5
27.5°	1163.3	1090.8	1021.8	975.6	936.9	908.6	888.3	875.4	862.3	853.1	845.9
30°	1111.6	1038.0	976.1	932.1	892.9	869.6	853.1	838.0	827.7	820.1	814.6
32.5°	1060.4	986.9	934.9	887.6	856.7	833.9	816.2	804.9	796.9	787.1	783.8
35°	986.4	921.2	875.8	833.2	801.5	780.9	767.2	755.5	748.6	745.9	743.8
37.5°	915.4	861.9	813.1	778.2	750.0	733.7	717.6	711.8	707.1	702.1	704.4
40°	870.3	820.1	776.8	739.7	717.0	699.1	689.5	682.6	678.5	678.5	678.5
42.5°	831.2	782.1	739.9	706.7	684.0	668.9	658.1	652.4	651.0	650.5	653.8
45°	770.6	725.2	682.6	655.1	635.8	620.8	614.6	609.8	609.8	612.5	613.2
47.5°	710.5	668.0	633.8	603.0	585.4	575.9	570.6	568.1	568.3	571.1	574.3
50°	673.6	631.7	598.1	570.6	554.1	545.1	540.3	539.0	540.3	540.3	545.1
52.5°	633.5	596.0	562.8	539.8	521.1	512.7	510.1	508.2	508.9	511.2	513.2
55°	574.7	541.0	509.4	487.4	473.6	468.1	461.9	462.6	461.2	462.6	462.6
57.5°	515.7	485.4	456.1	438.6	426.5	418.5	411.7	413.7	411.6	411.4	410.3
60°	477.8	444.8	421.4	405.6	391.8	385.0	378.8	380.1	378.1	376.7	373.9
62.5°	436.5	409.1	386.8	371.5	360.5	352.5	346.3	344.9	340.2	335.4	329.4
65°	376.7	354.0	334.1	319.7	309.4	303.2	298.3	294.2	283.9	272.9	267.4
67.5°	318.6	302.2	283.6	271.4	263.0	254.9	245.7	238.7	229.0	223.0	219.6
70°	281.1	265.4	249.5	237.8	228.9	221.4	211.0	206.2	199.3	196.6	193.2
72.5°	245.4	230.7	216.0	205.4	195.9	190.0	181.9	177.1	174.1	173.0	169.5
75°	191.1	179.4	168.4	158.8	151.3	147.1	143.7	140.3	138.9	132.7	129.2
77.5°	139.4	131.7	124.8	118.0	112.6	109.9	103.2	99.3	96.9	94.0	93.3
80°	108.6	103.1	96.3	92.1	84.6	81.8	79.0	78.4	77.7	77.0	76.3
82.5°	81.7	76.2	69.3	66.8	64.7	63.1	61.5	60.8	60.1	60.5	60.4
85°	41.2	38.5	38.5	37.8	37.1	36.4	35.7	35.7	35.0	35.7	35.0
87.5°	16.0	15.8	16.1	15.3	16.2	16.4	16.2	16.4	17.2	16.4	16.4
90°	11.1	13.0	14.6	16.1	17.7	19.2	20.3	21.5	22.6	23.8	24.6
92.5°	28.4	30.2	31.3	32.4	33.5	34.5	35.2	35.9	36.6	37.4	37.8
95°	59.3	60.9	62.3	63.5	64.9	66.3	66.9	67.4	68.0	68.6	68.9
97.5°	97.0	98.5	100.0	101.7	103.2	104.9	105.6	106.2	106.9	107.6	108.0
100°	125.2	126.5	128.2	129.9	131.7	133.5	133.8	134.2	134.6	135.0	135.2
102.5°	155.4	156.4	158.0	159.5	161.2	162.7	163.3	163.8	164.4	165.0	165.3
105°	204.0	204.5	205.3	206.0	206.8	207.6	208.2	208.8	209.3	209.9	210.5
107.5°	255.6	255.8	255.9	256.1	256.1	256.2	256.8	257.4	257.9	258.5	258.6
110°	291.1	291.2	291.0	290.8	290.7	290.4	290.1	289.6	289.3	288.9	289.0



TEST NUMBER: P333104-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	326.1	326.1	325.7	325.4	325.0	324.7	324.6	324.5	324.4	324.3	324.3
115°	380.3	380.1	379.7	379.4	378.9	378.6	378.3	378.2	378.0	377.8	377.5
117.5°	432.2	432.1	431.9	431.6	431.4	431.0	430.4	429.7	429.0	428.4	427.9
120°	468.9	469.0	468.4	467.8	467.3	466.7	465.7	464.7	463.7	462.8	462.4
122.5°	502.6	502.7	502.3	502.0	501.8	501.5	500.8	500.2	499.6	498.9	498.2
125°	553.9	553.8	553.5	553.4	553.2	553.0	552.6	552.2	551.8	551.5	551.0
127.5°	603.8	604.0	603.6	603.3	603.0	602.7	602.4	601.9	601.6	601.2	600.8
130°	637.3	637.6	637.6	637.6	637.6	637.6	637.2	636.8	636.5	636.0	635.5
132.5°	670.9	671.0	670.9	670.7	670.5	670.4	670.0	669.6	669.3	668.8	668.5
135°	719.0	719.6	719.6	719.6	719.6	719.6	719.2	718.8	718.4	718.1	717.6
137.5°	765.7	766.1	766.5	766.8	767.1	767.4	766.9	766.4	765.9	765.3	765.2
140°	797.9	798.1	798.1	798.1	798.1	798.1	797.9	797.7	797.5	797.3	797.1
142.5°	827.9	828.0	827.9	827.7	827.6	827.4	827.3	827.3	827.2	827.2	827.2
145°	871.0	871.4	871.7	871.8	872.0	872.2	872.0	871.8	871.7	871.4	871.1
147.5°	912.7	913.2	913.0	912.8	912.7	912.5	912.4	912.2	912.1	911.9	911.7
150°	937.3	937.6	937.6	937.6	937.6	937.6	937.6	937.6	937.6	937.6	937.5
152.5°	959.8	960.0	960.2	960.4	960.5	960.7	961.1	961.6	962.1	962.5	962.5
155°	994.4	994.3	994.0	993.9	993.7	993.5	994.3	995.1	995.8	996.6	996.6
157.5°	1023.6	1023.5	1023.4	1023.4	1023.3	1023.3	1023.9	1024.5	1025.0	1025.6	1025.6
160°	1042.4	1042.2	1042.0	1041.8	1041.6	1041.5	1042.0	1042.6	1043.2	1043.8	1043.5
162.5°	1057.9	1057.6	1057.4	1057.2	1057.0	1056.8	1057.8	1058.9	1059.9	1061.0	1061.0
165°	1080.1	1079.6	1079.3	1078.8	1078.5	1078.1	1079.3	1080.4	1081.6	1082.7	1082.9
167.5°	1096.5	1096.1	1096.1	1096.1	1096.1	1096.2	1097.3	1098.5	1099.7	1100.9	1100.9
170°	1105.6	1105.2	1105.4	1105.6	1105.8	1106.0	1107.2	1108.3	1109.5	1110.6	1110.5
172.5°	1113.2	1112.8	1112.8	1112.9	1112.9	1112.9	1114.3	1115.6	1116.9	1118.3	1118.2
175°	1122.1	1121.6	1121.4	1121.2	1121.0	1120.8	1122.1	1123.5	1124.9	1126.3	1126.3
177.5°	1126.1	1125.7	1125.7	1125.7	1125.7	1125.7	1126.8	1127.9	1128.9	1130.1	1130.0
180°	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8



TEST NUMBER: P333104-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2
2.5°	1628.7	1629.8	1625.9	1624.8	1625.9	1629.8	1628.7	1631.9	1632.5	1636.9	1635.3
5°	1511.0	1509.6	1506.1	1506.8	1506.1	1509.6	1511.0	1516.5	1519.2	1530.3	1528.9
7.5°	1410.3	1405.0	1406.4	1401.0	1406.4	1405.0	1410.3	1415.3	1423.7	1428.7	1440.3
10°	1348.8	1341.2	1335.0	1329.5	1335.0	1341.2	1348.8	1351.5	1363.1	1368.6	1380.4
12.5°	1264.6	1258.1	1249.7	1251.4	1249.7	1258.1	1264.6	1276.7	1291.7	1303.2	1321.5
15°	1145.2	1135.0	1118.4	1120.5	1118.4	1135.0	1145.2	1154.2	1169.3	1195.4	1207.8
17.5°	1044.2	1044.3	1036.8	1038.5	1036.8	1044.3	1044.2	1056.4	1064.1	1080.8	1099.8
20°	992.0	987.1	987.8	985.8	987.8	987.1	992.0	1006.4	1014.7	1026.3	1047.0
22.5°	955.6	949.8	944.9	940.6	944.9	949.8	955.6	959.7	970.7	981.8	998.6
25°	894.3	890.2	884.1	882.7	884.1	890.2	894.3	900.5	906.0	920.5	930.7
27.5°	840.4	839.6	837.2	834.0	837.2	839.6	840.4	845.9	853.1	862.3	875.4
30°	809.1	807.7	806.3	804.3	806.3	807.7	809.1	814.6	820.1	827.7	838.0
32.5°	781.1	780.2	778.9	779.0	778.9	780.2	781.1	783.8	787.1	796.9	804.9
35°	741.1	740.4	739.0	738.3	739.0	740.4	741.1	743.8	745.9	748.6	755.5
37.5°	703.7	705.4	704.6	704.5	704.6	705.4	703.7	704.4	702.1	707.1	711.8
40°	677.8	678.5	679.8	679.2	679.8	678.5	677.8	678.5	678.5	678.5	682.6
42.5°	656.3	656.5	658.4	656.1	658.4	656.5	656.3	653.8	650.5	651.0	652.4
45°	618.0	622.2	621.5	621.5	621.5	622.2	618.0	613.2	612.5	609.8	609.8
47.5°	576.1	579.6	580.6	580.5	580.6	579.6	576.1	574.3	571.1	568.3	568.1
50°	548.5	547.2	549.2	548.5	549.2	547.2	548.5	545.1	540.3	540.3	539.0
52.5°	515.1	515.3	515.1	514.4	515.1	515.3	515.1	513.2	511.2	508.9	508.2
55°	463.3	464.0	462.6	463.3	462.6	464.0	463.3	462.6	462.6	461.2	462.6
57.5°	407.3	403.9	405.3	403.6	405.3	403.9	407.3	410.3	411.4	411.6	413.7
60°	367.1	361.6	360.2	357.5	360.2	361.6	367.1	373.9	376.7	378.1	380.1
62.5°	322.0	318.1	313.5	315.6	313.5	318.1	322.0	329.4	335.4	340.2	344.9
65°	261.9	259.2	257.1	259.8	257.1	259.2	261.9	267.4	272.9	283.9	294.2
67.5°	216.8	215.3	215.3	214.0	215.3	215.3	216.8	219.6	223.0	229.0	238.7
70°	193.2	191.1	191.1	189.8	191.1	191.1	193.2	193.2	196.6	199.3	206.2
72.5°	168.9	166.9	167.5	166.6	167.5	166.9	168.9	169.5	173.0	174.1	177.1
75°	125.1	121.7	121.7	122.3	121.7	121.7	125.1	129.2	132.7	138.9	140.3
77.5°	93.3	92.6	93.6	92.4	93.6	92.6	93.3	93.3	94.0	96.9	99.3
80°	76.3	75.6	74.9	77.0	74.9	75.6	76.3	76.3	77.0	77.7	78.4
82.5°	59.2	59.2	59.0	61.6	59.0	59.2	59.2	60.4	60.5	60.1	60.8
85°	35.7	34.4	35.7	34.4	35.7	34.4	35.7	35.0	35.7	35.0	35.7
87.5°	17.7	17.2	16.7	17.3	16.7	17.2	17.7	16.4	16.4	17.2	16.4
90°	25.0	25.4	25.7	26.2	25.7	25.4	25.0	24.6	23.8	22.6	21.5
92.5°	38.1	38.2	38.5	38.7	38.5	38.2	38.1	37.8	37.4	36.6	35.9
95°	68.9	68.9	68.9	68.9	68.9	68.9	68.9	68.9	68.6	68.0	67.4
97.5°	108.0	108.0	108.0	108.0	108.0	108.0	108.0	108.0	107.6	106.9	106.2
100°	135.2	135.2	135.2	135.2	135.2	135.2	135.2	135.2	135.0	134.6	134.2
102.5°	165.4	165.6	165.7	165.9	165.7	165.6	165.4	165.3	165.0	164.4	163.8
105°	211.1	211.6	212.2	212.8	212.2	211.6	211.1	210.5	209.9	209.3	208.8
107.5°	258.6	258.6	258.6	258.6	258.6	258.6	258.6	258.6	258.5	257.9	257.4
110°	289.6	290.2	290.8	291.4	290.8	290.2	289.6	289.0	288.9	289.3	289.6



TEST NUMBER: P333104-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	324.5	324.6	324.7	324.9	324.7	324.6	324.5	324.3	324.3	324.4	324.5
115°	377.4	377.2	377.0	376.8	377.0	377.2	377.4	377.5	377.8	378.0	378.2
117.5°	427.5	427.1	426.7	426.4	426.7	427.1	427.5	427.9	428.4	429.0	429.7
120°	462.9	463.2	463.6	464.0	463.6	463.2	462.9	462.4	462.8	463.7	464.7
122.5°	497.5	496.8	496.1	495.4	496.1	496.8	497.5	498.2	498.9	499.6	500.2
125°	550.7	550.3	549.9	549.5	549.9	550.3	550.7	551.0	551.5	551.8	552.2
127.5°	600.5	600.2	599.9	599.6	599.9	600.2	600.5	600.8	601.2	601.6	601.9
130°	634.7	634.0	633.2	632.4	633.2	634.0	634.7	635.5	636.0	636.5	636.8
132.5°	668.2	667.9	667.5	667.3	667.5	667.9	668.2	668.5	668.8	669.3	669.6
135°	717.0	716.4	715.8	715.2	715.8	716.4	717.0	717.6	718.1	718.4	718.8
137.5°	765.3	765.4	765.5	765.6	765.5	765.4	765.3	765.2	765.3	765.9	766.4
140°	796.9	796.8	796.5	796.3	796.5	796.8	796.9	797.1	797.3	797.5	797.7
142.5°	827.2	827.2	827.1	827.1	827.1	827.2	827.2	827.2	827.2	827.2	827.3
145°	870.5	869.9	869.4	868.7	869.4	869.9	870.5	871.1	871.4	871.7	871.8
147.5°	911.5	911.4	911.1	910.9	911.1	911.4	911.5	911.7	911.9	912.1	912.2
150°	937.4	937.2	936.9	936.8	936.9	937.2	937.4	937.5	937.6	937.6	937.6
152.5°	962.0	961.5	961.0	960.5	961.0	961.5	962.0	962.5	962.5	962.1	961.6
155°	995.8	995.1	994.3	993.5	994.3	995.1	995.8	996.6	996.6	995.8	995.1
157.5°	1024.9	1024.2	1023.6	1023.0	1023.6	1024.2	1024.9	1025.6	1025.6	1025.0	1024.5
160°	1042.6	1041.6	1040.7	1039.7	1040.7	1041.6	1042.6	1043.5	1043.8	1043.2	1042.6
162.5°	1060.1	1059.1	1058.1	1057.1	1058.1	1059.1	1060.1	1061.0	1061.0	1059.9	1058.9
165°	1082.1	1081.3	1080.6	1079.8	1080.6	1081.3	1082.1	1082.9	1082.7	1081.6	1080.4
167.5°	1099.7	1098.5	1097.3	1096.1	1097.3	1098.5	1099.7	1100.9	1100.9	1099.7	1098.5
170°	1109.2	1107.8	1106.5	1105.1	1106.5	1107.8	1109.2	1110.5	1110.6	1109.5	1108.3
172.5°	1116.9	1115.5	1114.1	1112.8	1114.1	1115.5	1116.9	1118.2	1118.3	1116.9	1115.6
175°	1124.9	1123.5	1122.1	1120.8	1122.1	1123.5	1124.9	1126.3	1126.3	1124.9	1123.5
177.5°	1128.7	1127.5	1126.3	1125.0	1126.3	1127.5	1128.7	1130.0	1130.1	1128.9	1127.9
180°	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8



TEST NUMBER: P333104-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2
2.5°	1631.9	1635.8	1644.6	1654.5	1662.8	1669.9	1675.4	1683.1	1690.2	1700.1	1709.5
5°	1533.0	1542.6	1556.3	1572.9	1593.5	1607.2	1624.4	1639.5	1661.6	1683.5	1704.9
7.5°	1446.0	1456.6	1476.9	1499.7	1524.1	1546.7	1567.1	1593.7	1622.9	1654.9	1690.7
10°	1390.0	1401.7	1425.7	1451.8	1480.7	1502.7	1530.3	1561.9	1594.8	1634.0	1678.0
12.5°	1339.4	1350.6	1379.5	1406.2	1436.1	1460.3	1492.3	1524.5	1568.5	1610.9	1661.0
15°	1240.8	1270.4	1303.4	1335.0	1370.7	1400.3	1438.8	1471.8	1513.7	1573.6	1630.6
17.5°	1131.4	1162.9	1203.9	1252.7	1300.6	1337.2	1376.2	1417.2	1467.1	1528.2	1594.1
20°	1067.6	1093.0	1138.4	1192.7	1248.4	1299.2	1335.0	1380.4	1431.9	1497.9	1566.0
22.5°	1019.8	1041.3	1076.8	1131.1	1191.2	1250.3	1296.0	1340.7	1397.8	1463.8	1537.9
25°	948.0	971.4	1002.3	1039.4	1108.1	1170.7	1230.5	1282.0	1342.6	1408.5	1491.0
27.5°	888.3	908.6	936.9	975.6	1021.8	1090.8	1163.3	1222.1	1284.1	1355.0	1437.5
30°	853.1	869.6	892.9	932.1	976.1	1038.0	1111.6	1180.3	1242.9	1316.5	1402.4
32.5°	816.2	833.9	856.7	887.6	934.9	986.9	1060.4	1135.7	1202.2	1277.4	1361.7
35°	767.2	780.9	801.5	833.2	875.8	921.2	986.4	1064.1	1134.3	1214.7	1295.1
37.5°	717.6	733.7	750.0	778.2	813.1	861.9	915.4	994.7	1072.4	1145.8	1224.3
40°	689.5	699.1	717.0	739.7	776.8	820.1	870.3	948.0	1025.6	1098.5	1177.6
42.5°	658.1	668.9	684.0	706.7	739.9	782.1	831.2	898.5	979.5	1050.2	1122.1
45°	614.6	620.8	635.8	655.1	682.6	725.2	770.6	830.4	906.7	974.0	1037.3
47.5°	570.6	575.9	585.4	603.0	633.8	668.0	710.5	764.1	831.1	898.5	951.9
50°	540.3	545.1	554.1	570.6	598.1	631.7	673.6	721.8	781.6	846.2	890.9
52.5°	510.1	512.7	521.1	539.8	562.8	596.0	633.5	677.8	733.7	787.4	832.6
55°	461.9	468.1	473.6	487.4	509.4	541.0	574.7	616.6	660.0	705.3	743.8
57.5°	411.7	418.5	426.5	438.6	456.1	485.4	515.7	549.7	586.7	624.3	656.6
60°	378.8	385.0	391.8	405.6	421.4	444.8	477.8	507.3	535.5	569.9	602.2
62.5°	346.3	352.5	360.5	371.5	386.8	409.1	436.5	462.3	491.5	521.5	545.5
65°	298.3	303.2	309.4	319.7	334.1	354.0	376.7	396.7	422.8	444.8	466.7
67.5°	245.7	254.9	263.0	271.4	283.6	302.2	318.6	337.7	355.4	371.8	391.8
70°	211.0	221.4	228.9	237.8	249.5	265.4	281.1	294.2	308.7	324.4	342.3
72.5°	181.9	190.0	195.9	205.4	216.0	230.7	245.4	256.2	267.9	278.8	296.2
75°	143.7	147.1	151.3	158.8	168.4	179.4	191.1	200.7	207.6	217.2	229.6
77.5°	103.2	109.9	112.6	118.0	124.8	131.7	139.4	147.5	154.1	157.6	167.0
80°	79.0	81.8	84.6	92.1	96.3	103.1	108.6	116.1	118.9	122.3	131.3
82.5°	61.5	63.1	64.7	66.8	69.3	76.2	81.7	86.4	89.2	90.5	97.2
85°	35.7	36.4	37.1	37.8	38.5	38.5	41.2	44.7	49.5	49.5	51.6
87.5°	16.2	16.4	16.2	15.3	16.1	15.8	16.0	15.6	16.8	18.0	19.2
90°	20.3	19.2	17.7	16.1	14.6	13.0	11.1	9.0	6.9	4.7	2.6
92.5°	35.2	34.5	33.5	32.4	31.3	30.2	28.4	26.0	23.6	21.1	18.7
95°	66.9	66.3	64.9	63.5	62.3	60.9	59.3	57.6	55.8	54.1	52.3
97.5°	105.6	104.9	103.2	101.7	100.0	98.5	97.0	95.6	94.2	92.8	91.4
100°	133.8	133.5	131.7	129.9	128.2	126.5	125.2	124.4	123.6	122.9	122.1
102.5°	163.3	162.7	161.2	159.5	158.0	156.4	155.4	155.2	154.8	154.5	154.2
105°	208.2	207.6	206.8	206.0	205.3	204.5	204.0	203.8	203.6	203.5	203.2
107.5°	256.8	256.2	256.1	256.1	255.9	255.8	255.6	255.4	255.1	254.9	254.7
110°	290.1	290.4	290.7	290.8	291.0	291.2	291.1	290.8	290.3	290.0	289.6



TEST NUMBER: P333104-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	324.6	324.7	325.0	325.4	325.7	326.1	326.1	326.1	326.1	326.0	325.9
115°	378.3	378.6	378.9	379.4	379.7	380.1	380.3	380.3	380.3	380.3	380.3
117.5°	430.4	431.0	431.4	431.6	431.9	432.1	432.2	432.0	431.9	431.7	431.6
120°	465.7	466.7	467.3	467.8	468.4	469.0	468.9	468.1	467.4	466.6	465.8
122.5°	500.8	501.5	501.8	502.0	502.3	502.7	502.6	502.3	502.0	501.7	501.4
125°	552.6	553.0	553.2	553.4	553.5	553.8	553.9	553.9	553.9	553.9	553.9
127.5°	602.4	602.7	603.0	603.3	603.6	604.0	603.8	603.2	602.6	602.1	601.5
130°	637.2	637.6	637.6	637.6	637.6	637.6	637.3	636.7	636.1	635.6	635.0
132.5°	670.0	670.4	670.5	670.7	670.9	671.0	670.9	670.5	670.0	669.6	669.2
135°	719.2	719.6	719.6	719.6	719.6	719.6	719.0	717.8	716.7	715.5	714.4
137.5°	766.9	767.4	767.1	766.8	766.5	766.1	765.7	765.2	764.7	764.1	763.5
140°	797.9	798.1	798.1	798.1	798.1	798.1	797.9	797.5	797.1	796.8	796.3
142.5°	827.3	827.4	827.6	827.7	827.9	828.0	827.9	827.5	827.2	826.7	826.4
145°	872.0	872.2	872.0	871.8	871.7	871.4	871.0	870.2	869.4	868.7	867.9
147.5°	912.4	912.5	912.7	912.8	913.0	913.2	912.7	911.8	910.9	910.0	909.0
150°	937.6	937.6	937.6	937.6	937.6	937.6	937.3	936.5	935.7	935.0	934.2
152.5°	961.1	960.7	960.5	960.4	960.2	960.0	959.8	959.2	958.8	958.4	957.9
155°	994.3	993.5	993.7	993.9	994.0	994.3	994.4	994.4	994.4	994.4	994.4
157.5°	1023.9	1023.3	1023.3	1023.4	1023.4	1023.5	1023.6	1024.0	1024.3	1024.7	1025.0
160°	1042.0	1041.5	1041.6	1041.8	1042.0	1042.2	1042.4	1042.6	1042.8	1043.0	1043.2
162.5°	1057.8	1056.8	1057.0	1057.2	1057.4	1057.6	1057.9	1058.4	1058.9	1059.5	1059.9
165°	1079.3	1078.1	1078.5	1078.8	1079.3	1079.6	1080.1	1080.7	1081.2	1081.8	1082.4
167.5°	1097.3	1096.2	1096.1	1096.1	1096.1	1096.1	1096.5	1097.3	1098.1	1098.9	1099.7
170°	1107.2	1106.0	1105.8	1105.6	1105.4	1105.2	1105.6	1106.6	1107.5	1108.5	1109.5
172.5°	1114.3	1112.9	1112.9	1112.9	1112.8	1112.8	1113.2	1114.0	1114.8	1115.6	1116.5
175°	1122.1	1120.8	1121.0	1121.2	1121.4	1121.6	1122.1	1123.2	1124.1	1125.1	1126.0
177.5°	1126.8	1125.7	1125.7	1125.7	1125.7	1125.7	1126.1	1126.9	1127.7	1128.4	1129.2
180°	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8



TEST NUMBER: P333104-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2
2.5°	1716.7	1721.6	1727.1	1737.6	1746.4	1750.2	1757.9	1763.4	1761.8	1769.4	1782.6
5°	1723.4	1742.0	1763.2	1785.3	1810.0	1830.7	1847.1	1863.6	1876.7	1892.5	1915.9
7.5°	1722.3	1755.3	1791.1	1830.7	1871.2	1906.3	1938.7	1971.7	2001.0	2033.0	2074.9
10°	1717.9	1761.9	1806.6	1858.1	1909.7	1958.5	2002.5	2043.8	2082.9	2124.9	2177.8
12.5°	1713.0	1763.5	1817.6	1879.6	1943.8	2002.5	2054.2	2113.6	2162.7	2216.7	2277.9
15°	1691.1	1759.1	1832.7	1913.1	1990.1	2069.2	2139.9	2212.9	2280.9	2345.5	2422.5
17.5°	1666.0	1744.6	1831.3	1926.3	2018.9	2115.0	2199.0	2290.8	2360.3	2447.1	2518.6
20°	1645.7	1730.3	1823.1	1929.6	2034.8	2141.3	2234.1	2327.6	2406.0	2493.3	2584.0
22.5°	1620.9	1713.7	1814.3	1924.7	2034.8	2151.2	2253.9	2346.9	2443.9	2542.3	2635.8
25°	1581.1	1677.3	1783.9	1904.9	2031.4	2150.3	2260.3	2375.8	2480.3	2586.8	2670.6
27.5°	1532.1	1633.2	1745.5	1870.4	2000.2	2121.9	2251.5	2374.6	2479.7	2582.2	2655.4
30°	1493.1	1599.7	1707.5	1834.1	1968.8	2099.4	2238.3	2361.3	2472.0	2564.1	2605.4
32.5°	1452.9	1554.0	1665.3	1793.4	1931.4	2071.9	2209.7	2335.5	2437.9	2493.2	2494.2
35°	1383.1	1478.0	1593.5	1719.2	1860.9	2013.4	2153.0	2276.7	2339.3	2344.2	2276.7
37.5°	1306.9	1394.0	1503.0	1628.9	1784.0	1935.8	2078.4	2160.9	2181.8	2111.8	1987.2
40°	1252.5	1332.9	1438.1	1567.4	1721.3	1878.1	2008.0	2068.5	2046.5	1933.0	1794.2
42.5°	1195.3	1270.2	1371.6	1499.2	1653.7	1812.1	1922.8	1955.2	1896.9	1765.9	1603.4
45°	1102.0	1170.7	1271.1	1399.6	1548.1	1696.6	1780.5	1763.9	1667.0	1511.7	1329.5
47.5°	1004.8	1071.2	1161.5	1280.4	1432.4	1560.6	1617.4	1567.6	1429.7	1258.8	1110.6
50°	940.4	1008.5	1091.7	1205.1	1343.9	1467.7	1504.1	1428.5	1275.1	1110.9	974.7
52.5°	877.2	935.3	1016.8	1126.4	1259.2	1363.7	1383.1	1296.0	1137.7	990.4	869.7
55°	780.9	833.9	902.6	1005.7	1120.5	1209.2	1198.9	1086.8	943.1	817.3	722.5
57.5°	687.9	727.7	791.3	887.9	988.7	1048.2	1010.6	915.0	781.1	678.1	598.1
60°	626.3	663.4	722.5	807.0	895.7	929.4	897.8	794.0	688.1	593.9	526.6
62.5°	567.9	600.7	651.5	730.0	801.7	821.7	787.8	697.2	601.8	521.3	465.5
65°	483.3	513.5	556.8	612.5	662.0	671.6	649.6	556.8	484.7	417.2	378.8
67.5°	406.4	426.2	460.0	508.2	534.4	540.0	497.6	439.3	375.7	334.2	305.2
70°	354.7	368.4	400.1	426.2	447.5	448.2	409.1	362.3	313.5	279.8	258.5
72.5°	304.7	317.9	341.8	359.6	376.0	370.7	334.8	297.9	258.5	233.1	217.2
75°	235.1	246.8	259.2	267.4	267.4	260.5	234.5	206.9	184.3	169.1	164.3
77.5°	170.9	180.6	184.7	183.4	180.9	170.2	153.7	135.7	127.6	120.5	116.8
80°	134.1	138.2	139.6	136.1	132.0	119.6	108.6	101.1	93.5	90.7	89.4
82.5°	99.4	103.0	99.4	100.4	91.3	81.1	75.1	72.5	69.3	68.2	66.8
85°	53.0	52.3	50.9	47.4	41.2	39.9	39.2	38.5	37.1	37.8	36.4
87.5°	19.1	17.9	16.1	16.0	16.4	15.6	16.4	16.7	17.0	16.7	18.1
90°	4.7	6.9	9.0	11.1	13.0	14.6	16.1	17.7	19.2	20.3	21.5
92.5°	21.1	23.6	26.0	28.4	30.2	31.3	32.4	33.5	34.5	35.2	35.9
95°	54.1	55.8	57.6	59.3	60.9	62.3	63.5	64.9	66.3	66.9	67.4
97.5°	92.8	94.2	95.6	97.0	98.5	100.0	101.7	103.2	104.9	105.6	106.2
100°	122.9	123.6	124.4	125.2	126.5	128.2	129.9	131.7	133.5	133.8	134.2
102.5°	154.5	154.8	155.2	155.4	156.4	158.0	159.5	161.2	162.7	163.3	163.8
105°	203.5	203.6	203.8	204.0	204.5	205.3	206.0	206.8	207.6	208.2	208.8
107.5°	254.9	255.1	255.4	255.6	255.8	255.9	256.1	256.1	256.2	256.8	257.4
110°	290.0	290.3	290.8	291.1	291.2	291.0	290.8	290.7	290.4	290.1	289.6



TEST NUMBER: P333104-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	326.0	326.1	326.1	326.1	326.1	325.7	325.4	325.0	324.7	324.6	324.5
115°	380.3	380.3	380.3	380.3	380.1	379.7	379.4	378.9	378.6	378.3	378.2
117.5°	431.7	431.9	432.0	432.2	432.1	431.9	431.6	431.4	431.0	430.4	429.7
120°	466.6	467.4	468.1	468.9	469.0	468.4	467.8	467.3	466.7	465.7	464.7
122.5°	501.7	502.0	502.3	502.6	502.7	502.3	502.0	501.8	501.5	500.8	500.2
125°	553.9	553.9	553.9	553.9	553.8	553.5	553.4	553.2	553.0	552.6	552.2
127.5°	602.1	602.6	603.2	603.8	604.0	603.6	603.3	603.0	602.7	602.4	601.9
130°	635.6	636.1	636.7	637.3	637.6	637.6	637.6	637.6	637.6	637.2	636.8
132.5°	669.6	670.0	670.5	670.9	671.0	670.9	670.7	670.5	670.4	670.0	669.6
135°	715.5	716.7	717.8	719.0	719.6	719.6	719.6	719.6	719.6	719.2	718.8
137.5°	764.1	764.7	765.2	765.7	766.1	766.5	766.8	767.1	767.4	766.9	766.4
140°	796.8	797.1	797.5	797.9	798.1	798.1	798.1	798.1	798.1	797.9	797.7
142.5°	826.7	827.2	827.5	827.9	828.0	827.9	827.7	827.6	827.4	827.3	827.3
145°	868.7	869.4	870.2	871.0	871.4	871.7	871.8	872.0	872.2	872.0	871.8
147.5°	910.0	910.9	911.8	912.7	913.2	913.0	912.8	912.7	912.5	912.4	912.2
150°	935.0	935.7	936.5	937.3	937.6	937.6	937.6	937.6	937.6	937.6	937.6
152.5°	958.4	958.8	959.2	959.8	960.0	960.2	960.4	960.5	960.7	961.1	961.6
155°	994.4	994.4	994.4	994.4	994.3	994.0	993.9	993.7	993.5	994.3	995.1
157.5°	1024.7	1024.3	1024.0	1023.6	1023.5	1023.4	1023.4	1023.3	1023.3	1023.9	1024.5
160°	1043.0	1042.8	1042.6	1042.4	1042.2	1042.0	1041.8	1041.6	1041.5	1042.0	1042.6
162.5°	1059.5	1058.9	1058.4	1057.9	1057.6	1057.4	1057.2	1057.0	1056.8	1057.8	1058.9
165°	1081.8	1081.2	1080.7	1080.1	1079.6	1079.3	1078.8	1078.5	1078.1	1079.3	1080.4
167.5°	1098.9	1098.1	1097.3	1096.5	1096.1	1096.1	1096.1	1096.1	1096.2	1097.3	1098.5
170°	1108.5	1107.5	1106.6	1105.6	1105.2	1105.4	1105.6	1105.8	1106.0	1107.2	1108.3
172.5°	1115.6	1114.8	1114.0	1113.2	1112.8	1112.8	1112.9	1112.9	1112.9	1114.3	1115.6
175°	1125.1	1124.1	1123.2	1122.1	1121.6	1121.4	1121.2	1121.0	1120.8	1122.1	1123.5
177.5°	1128.4	1127.7	1126.9	1126.1	1125.7	1125.7	1125.7	1125.7	1125.7	1126.8	1127.9
180°	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8



TEST NUMBER: P333104-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2
2.5°	1789.8	1792.0	1793.6	1799.1	1799.7	1804.7	1799.7
5°	1937.9	1947.5	1962.6	1977.7	1979.1	1988.7	1971.5
7.5°	2103.9	2126.2	2140.1	2164.6	2174.2	2180.2	2170.3
10°	2218.4	2238.9	2275.4	2293.3	2311.2	2313.9	2305.7
12.5°	2328.9	2361.6	2390.3	2424.1	2423.4	2447.6	2438.7
15°	2476.1	2509.8	2549.7	2587.5	2601.3	2601.3	2612.3
17.5°	2581.2	2642.9	2684.2	2713.9	2746.2	2751.9	2748.1
20°	2652.1	2718.8	2762.8	2801.3	2823.3	2829.5	2829.5
22.5°	2704.9	2761.7	2804.6	2839.2	2857.4	2864.6	2862.5
25°	2741.5	2790.2	2816.4	2826.7	2831.5	2830.2	2817.1
27.5°	2691.4	2689.2	2672.7	2641.1	2617.4	2602.9	2586.4
30°	2595.7	2560.0	2518.8	2473.4	2414.9	2370.2	2356.5
32.5°	2453.3	2373.0	2303.2	2227.6	2164.7	2120.0	2101.4
35°	2177.8	2050.6	1946.8	1856.1	1790.1	1748.9	1735.1
37.5°	1850.8	1727.8	1599.2	1511.2	1456.6	1414.9	1399.3
40°	1643.0	1508.9	1396.9	1314.4	1258.0	1217.5	1216.8
42.5°	1453.2	1325.3	1219.8	1160.4	1099.6	1072.8	1072.6
45°	1189.9	1087.5	998.2	951.4	915.0	892.9	886.7
47.5°	985.2	900.5	841.0	803.7	774.0	760.0	751.0
50°	870.3	796.1	748.6	716.3	699.8	681.9	680.5
52.5°	774.6	714.6	677.7	651.4	630.5	619.7	620.1
55°	651.0	603.6	577.5	557.5	541.0	532.8	529.3
57.5°	548.5	512.8	493.9	475.5	468.6	462.1	460.3
60°	484.7	460.5	442.7	428.3	417.9	415.9	415.2
62.5°	431.9	406.7	394.3	383.1	375.7	372.5	371.2
65°	356.1	337.5	326.5	317.6	314.9	310.0	309.4
67.5°	287.1	276.0	268.6	262.4	258.7	258.5	258.5
70°	244.7	238.5	232.4	228.9	226.9	225.5	225.5
72.5°	208.4	203.9	198.8	197.0	196.6	195.2	194.7
75°	158.8	153.9	154.6	151.3	148.5	145.1	143.0
77.5°	112.6	109.2	108.5	108.1	105.7	105.3	106.4
80°	87.3	83.9	83.2	83.9	83.2	81.1	81.1
82.5°	66.4	63.5	62.9	62.4	61.7	62.4	61.3
85°	35.7	34.4	34.4	34.4	35.7	35.0	34.4
87.5°	17.2	16.9	17.6	17.1	17.2	16.7	17.3
90°	22.6	23.8	24.6	25.0	25.4	25.7	26.2
92.5°	36.6	37.4	37.8	38.1	38.2	38.5	38.7
95°	68.0	68.6	68.9	68.9	68.9	68.9	68.9
97.5°	106.9	107.6	108.0	108.0	108.0	108.0	108.0
100°	134.6	135.0	135.2	135.2	135.2	135.2	135.2
102.5°	164.4	165.0	165.3	165.4	165.6	165.7	165.9
105°	209.3	209.9	210.5	211.1	211.6	212.2	212.8
107.5°	257.9	258.5	258.6	258.6	258.6	258.6	258.6
110°	289.3	288.9	289.0	289.6	290.2	290.8	291.4



TEST NUMBER: P333104-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	324.4	324.3	324.3	324.5	324.6	324.7	324.9
115°	378.0	377.8	377.5	377.4	377.2	377.0	376.8
117.5°	429.0	428.4	427.9	427.5	427.1	426.7	426.4
120°	463.7	462.8	462.4	462.9	463.2	463.6	464.0
122.5°	499.6	498.9	498.2	497.5	496.8	496.1	495.4
125°	551.8	551.5	551.0	550.7	550.3	549.9	549.5
127.5°	601.6	601.2	600.8	600.5	600.2	599.9	599.6
130°	636.5	636.0	635.5	634.7	634.0	633.2	632.4
132.5°	669.3	668.8	668.5	668.2	667.9	667.5	667.3
135°	718.4	718.1	717.6	717.0	716.4	715.8	715.2
137.5°	765.9	765.3	765.2	765.3	765.4	765.5	765.6
140°	797.5	797.3	797.1	796.9	796.8	796.5	796.3
142.5°	827.2	827.2	827.2	827.2	827.2	827.1	827.1
145°	871.7	871.4	871.1	870.5	869.9	869.4	868.7
147.5°	912.1	911.9	911.7	911.5	911.4	911.1	910.9
150°	937.6	937.6	937.5	937.4	937.2	936.9	936.8
152.5°	962.1	962.5	962.5	962.0	961.5	961.0	960.5
155°	995.8	996.6	996.6	995.8	995.1	994.3	993.5
157.5°	1025.0	1025.6	1025.6	1024.9	1024.2	1023.6	1023.0
160°	1043.2	1043.8	1043.5	1042.6	1041.6	1040.7	1039.7
162.5°	1059.9	1061.0	1061.0	1060.1	1059.1	1058.1	1057.1
165°	1081.6	1082.7	1082.9	1082.1	1081.3	1080.6	1079.8
167.5°	1099.7	1100.9	1100.9	1099.7	1098.5	1097.3	1096.1
170°	1109.5	1110.6	1110.5	1109.2	1107.8	1106.5	1105.1
172.5°	1116.9	1118.3	1118.2	1116.9	1115.5	1114.1	1112.8
175°	1124.9	1126.3	1126.3	1124.9	1123.5	1122.1	1120.8
177.5°	1128.9	1130.1	1130.0	1128.7	1127.5	1126.3	1125.0
180°	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8

(END OF REPORT)