

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333055-940

Luminaire Tested: **S124RDIW-S795D470U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333055-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S795D470U940-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4648.3 lumens
Efficiency: N/A
Efficacy: 123.3 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333055-940

CATALOG NUMBER: S124RDIW-S795D470U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333055-940

CATALOG NUMBER: S124RDIW-S795D470U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	104	104	104	104	91	91	91	80	80	80	69	69	69	64
1	102	97	94	90	95	92	88	85	81	78	76	71	69	68	62	61	60	55
2	93	86	80	75	87	81	76	71	72	68	64	63	60	57	55	53	51	47
3	85	76	69	63	80	72	65	60	64	59	55	56	52	49	49	47	44	41
4	78	68	60	54	73	64	57	51	57	51	47	51	46	43	45	41	38	35
5	72	61	52	47	68	57	50	45	51	45	41	46	41	37	40	37	34	31
6	67	55	46	41	62	52	44	39	46	40	36	41	37	33	37	33	30	27
7	62	49	42	36	58	47	40	35	42	36	32	38	33	29	34	30	27	24
8	57	45	37	32	54	43	36	31	39	33	29	35	30	26	31	27	24	22
9	54	41	34	29	50	39	32	28	36	30	26	32	27	24	29	25	22	20
10	50	38	31	26	47	36	30	25	33	27	23	30	25	22	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9503	9503	9503	9503
5°	11022	9532	8425	9532
10°	13039	9489	7519	9489
15°	15061	9402	6461	9402
20°	16770	9281	5843	9281
25°	17312	9163	5424	9163
30°	15155	9018	5172	9018
35°	11797	8806	5019	8806
40°	8847	8560	4938	8560
45°	6985	8170	4894	8170
50°	5897	7720	4752	7720
55°	5140	7222	4500	7222
60°	4624	6707	3982	6707
65°	4076	6151	3423	6151
70°	3670	5575	3090	5575
75°	3075	4941	2633	4941
80°	2603	4212	2469	4212
85°	2195	3298	2195	3298



TEST NUMBER: P333055-940

CATALOG NUMBER: S124RDIW-S795D470U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.1	2.5
10°-20°	344.0	7.4
20°-30°	538.1	11.6
30°-40°	598.2	12.9
40°-50°	530.7	11.4
50°-60°	413.6	8.9
60°-70°	270.8	5.8
70°-80°	133.1	2.9
80°-90°	34.4	0.7
90°-100°	18.5	0.4
100°-110°	117.8	2.5
110°-120°	225.4	4.8
120°-130°	286.1	6.2
130°-140°	306.1	6.6
140°-150°	286.3	6.2
150°-160°	230.9	5.0
160°-170°	148.9	3.2
170°-180°	51.3	1.1
0°-30°	996.2	21.4
0°-40°	1594.3	34.3
0°-60°	2538.6	54.6
0°-90°	2976.9	64.0
90°-120°	361.7	7.8
90°-150°	1240.3	26.7
90°-180°	1671.0	35.9
0°-180°	4648.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1177	1177	1177	1177	1177	
5°	1360	1176	1040	1176	1360	138
15°	1802	1125	773	1125	1802	512
25°	1944	1029	609	1029	1944	862
35°	1197	894	509	894	1197	750
45°	612	716	429	716	612	485
55°	365	513	320	513	365	332
65°	213	322	179	322	213	215
75°	99	158	84	158	99	109
85°	24	36	24	36	24	27
90°	12	1	12	1	12	6
95°	12	22	12	22	12	9
105°	115	122	115	122	115	100
115°	229	227	229	227	229	226
125°	322	319	322	319	322	286
135°	399	396	399	396	399	307
145°	459	457	459	457	459	287
155°	500	501	500	501	500	231
165°	526	528	526	528	526	149
175°	537	540	537	540	537	51
180°	540	540	540	540	540	



TEST NUMBER: P333055-940

CATALOG NUMBER: S124RDIW-S795D470U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1
2.5°	1241.5	1245.0	1241.5	1241.2	1237.4	1236.3	1234.8	1229.8	1220.7	1215.4	1216.6
5°	1360.1	1372.0	1365.4	1364.4	1354.0	1343.5	1336.9	1321.7	1305.6	1294.7	1285.7
7.5°	1497.3	1504.1	1499.9	1493.3	1476.4	1466.9	1451.4	1431.5	1402.6	1380.5	1360.2
10°	1590.6	1596.3	1594.4	1582.1	1569.8	1544.6	1530.4	1502.4	1465.9	1437.0	1410.0
12.5°	1682.4	1688.5	1671.8	1672.4	1649.0	1629.2	1606.7	1571.5	1529.3	1492.0	1458.1
15°	1802.1	1794.6	1794.6	1785.0	1759.0	1731.4	1708.3	1671.2	1618.1	1573.5	1526.6
17.5°	1895.9	1898.5	1894.6	1872.2	1851.7	1823.3	1780.7	1737.5	1688.2	1628.4	1580.4
20°	1952.0	1952.0	1947.8	1932.5	1906.0	1875.6	1829.6	1782.7	1720.1	1659.8	1605.8
22.5°	1974.8	1976.3	1971.2	1958.7	1934.8	1905.2	1866.1	1818.4	1753.8	1686.0	1619.1
25°	1943.5	1952.5	1953.4	1950.1	1942.9	1924.9	1891.3	1842.5	1784.6	1711.1	1639.0
27.5°	1784.3	1795.6	1805.6	1822.0	1843.9	1855.2	1856.7	1831.9	1781.5	1710.7	1638.2
30°	1625.7	1635.2	1666.0	1706.3	1737.7	1766.1	1790.7	1797.4	1769.0	1705.4	1629.1
32.5°	1449.7	1462.6	1493.4	1536.8	1588.9	1637.1	1692.5	1720.7	1720.0	1681.9	1611.2
35°	1197.0	1206.5	1234.9	1280.5	1343.1	1414.7	1502.4	1570.7	1617.2	1613.8	1570.7
37.5°	965.4	976.1	1004.9	1042.6	1103.3	1191.9	1276.8	1370.9	1456.9	1505.1	1490.8
40°	839.5	839.9	867.9	906.8	963.7	1041.0	1133.5	1237.8	1333.6	1411.8	1427.0
42.5°	740.0	740.1	758.6	800.5	841.5	914.3	1002.6	1106.2	1218.3	1308.7	1348.9
45°	611.8	616.1	631.2	656.4	688.6	750.3	820.9	917.2	1042.9	1150.0	1216.9
47.5°	518.1	524.3	534.0	554.5	580.1	621.3	679.7	766.2	868.4	986.3	1081.5
50°	469.5	470.5	482.8	494.2	516.5	549.2	600.4	672.4	766.3	879.8	985.5
52.5°	427.8	427.6	435.0	449.4	467.5	493.0	534.4	600.0	683.3	784.9	894.0
55°	365.2	367.6	373.3	384.6	398.3	416.4	449.1	498.5	563.9	650.7	749.8
57.5°	317.5	318.8	323.2	328.1	340.7	353.8	378.4	412.6	467.8	538.9	631.2
60°	286.4	287.0	288.4	295.4	305.4	317.7	334.3	363.3	409.7	474.7	547.8
62.5°	256.1	256.9	259.1	264.3	272.1	280.5	297.9	321.2	359.6	415.2	481.0
65°	213.4	213.9	217.2	219.1	225.2	232.8	245.7	261.3	287.8	334.3	384.1
67.5°	178.3	178.3	178.5	181.1	185.3	190.4	198.0	210.5	230.6	259.1	303.0
70°	155.5	155.5	156.5	157.9	160.3	164.5	168.8	178.3	193.1	216.2	249.9
72.5°	134.3	134.6	135.6	135.9	137.1	140.6	143.8	149.9	160.8	178.3	205.5
75°	98.6	100.0	102.5	104.3	106.7	106.2	109.6	113.3	116.6	127.1	142.8
77.5°	73.4	72.7	72.9	74.5	74.8	75.3	77.7	80.6	83.1	88.0	93.6
80°	56.0	56.0	57.4	57.9	57.4	57.9	60.2	61.6	62.6	64.5	69.7
82.5°	42.3	43.1	42.6	43.1	43.3	43.8	45.8	46.1	47.1	47.8	50.0
85°	23.7	24.2	24.7	23.7	23.7	23.7	24.7	25.1	26.1	25.6	26.6
87.5°	10.8	10.3	10.7	10.7	11.0	10.5	10.8	11.5	10.6	10.9	10.7
90°	12.1	11.9	11.8	11.6	11.4	11.1	10.5	10.0	9.5	8.9	8.2
92.5°	11.1	11.1	11.1	11.1	11.0	10.7	10.2	9.6	9.1	8.6	7.8
95°	11.7	11.6	11.5	11.4	11.3	11.1	10.5	10.0	9.5	8.9	8.8
97.5°	11.3	11.2	11.1	11.1	11.0	10.9	10.8	10.8	10.7	10.7	20.7
100°	11.3	11.2	11.1	11.1	11.0	11.7	13.2	14.7	16.2	17.7	30.1
102.5°	11.7	11.6	11.6	11.6	11.6	19.8	36.3	52.7	69.2	85.7	87.3
105°	115.2	118.4	121.6	124.8	128.1	129.3	128.5	127.7	126.9	126.1	125.6
107.5°	160.5	160.2	159.8	159.5	159.2	158.8	158.4	158.0	157.6	157.2	156.6
110°	180.2	179.9	179.7	179.4	179.1	179.0	178.8	178.6	178.4	178.3	177.7



TEST NUMBER: P333055-940

CATALOG NUMBER: S124RDIW-S795D470U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	199.9	199.7	199.3	198.9	198.6	198.4	198.5	198.5	198.6	198.6	198.3
115°	228.7	228.7	228.7	228.7	228.7	228.6	228.5	228.3	228.1	227.9	228.0
117.5°	258.0	258.1	258.1	258.1	258.2	258.2	258.2	258.2	258.2	258.3	258.2
120°	276.4	276.6	276.8	277.0	277.1	277.1	277.0	276.8	276.6	276.4	276.5
122.5°	294.5	294.7	294.9	295.1	295.2	295.2	295.2	295.1	295.0	294.9	294.7
125°	321.6	321.6	321.5	321.4	321.3	321.1	320.8	320.6	320.3	320.0	320.2
127.5°	345.5	345.6	345.6	345.7	345.8	345.9	345.9	346.0	346.1	346.1	345.7
130°	361.7	361.7	361.7	361.7	361.7	361.7	361.6	361.5	361.4	361.3	361.1
132.5°	376.6	376.7	376.7	376.7	376.8	376.8	376.7	376.7	376.6	376.5	376.1
135°	398.9	398.7	398.5	398.3	398.1	398.0	397.8	397.6	397.4	397.3	396.9
137.5°	417.9	418.0	418.0	418.1	418.1	418.1	417.9	417.7	417.5	417.3	416.9
140°	431.2	431.1	431.1	431.0	430.9	430.7	430.4	430.2	429.9	429.6	429.4
142.5°	442.2	442.2	442.2	442.1	442.1	442.0	441.8	441.6	441.4	441.2	441.1
145°	459.1	458.9	458.7	458.5	458.3	458.3	458.2	458.1	458.0	457.9	457.9
147.5°	473.1	473.0	472.9	472.8	472.7	472.6	472.5	472.5	472.4	472.3	472.4
150°	482.1	482.1	482.0	481.9	481.8	481.7	481.7	481.7	481.7	481.7	481.8
152.5°	489.9	489.9	490.0	490.1	490.1	490.1	489.9	489.7	489.6	489.5	489.6
155°	500.3	500.6	500.9	501.1	501.4	501.3	501.0	500.6	500.2	499.9	500.2
157.5°	509.1	509.5	510.0	510.4	510.9	510.9	510.4	510.0	509.5	509.1	509.3
160°	514.9	515.4	515.9	516.5	517.0	517.0	516.5	515.9	515.4	514.9	515.0
162.5°	519.4	520.0	520.6	521.2	521.8	521.8	521.3	520.8	520.2	519.7	519.8
165°	525.8	526.6	527.4	528.2	529.0	529.1	528.3	527.6	526.9	526.2	526.2
167.5°	530.6	531.5	532.4	533.2	534.1	534.2	533.4	532.6	531.8	531.0	531.1
170°	533.4	534.3	535.2	536.1	537.1	537.2	536.4	535.7	534.9	534.2	534.1
172.5°	535.0	536.0	537.0	538.0	539.0	539.0	538.3	537.6	536.9	536.2	536.1
175°	537.1	538.1	539.2	540.3	541.4	541.5	540.7	539.9	539.1	538.3	538.2
177.5°	538.4	539.2	540.1	541.0	541.8	542.0	541.4	540.8	540.2	539.7	539.5
180°	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3



TEST NUMBER: P333055-940

CATALOG NUMBER: S124RDIW-S795D470U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1
2.5°	1212.7	1207.5	1204.8	1198.7	1191.5	1187.7	1184.3	1179.4	1172.9	1166.1	1161.1
5°	1274.3	1262.9	1248.7	1231.6	1216.5	1201.8	1188.9	1176.2	1161.5	1146.2	1131.0
7.5°	1337.5	1315.1	1290.9	1262.9	1235.7	1210.9	1188.2	1166.4	1141.7	1119.6	1099.5
10°	1381.4	1351.1	1317.4	1281.9	1246.3	1215.5	1185.2	1157.6	1127.3	1100.3	1077.5
12.5°	1417.1	1381.4	1341.0	1296.6	1253.9	1216.7	1181.7	1145.8	1111.3	1082.0	1051.7
15°	1476.3	1427.5	1373.0	1319.8	1264.4	1213.6	1166.6	1124.9	1085.6	1044.3	1015.4
17.5°	1517.0	1459.0	1392.8	1328.9	1263.4	1203.5	1149.4	1099.7	1054.3	1012.1	977.7
20°	1541.3	1477.3	1403.7	1331.2	1257.7	1193.6	1135.3	1080.3	1033.4	987.8	952.3
22.5°	1555.0	1484.1	1403.7	1327.8	1251.6	1182.3	1118.3	1061.0	1009.9	964.3	925.0
25°	1559.3	1483.5	1401.4	1314.1	1230.7	1157.2	1090.7	1028.7	971.7	926.2	884.5
27.5°	1553.3	1463.9	1379.8	1290.3	1204.2	1126.7	1057.0	991.8	934.8	885.9	843.1
30°	1544.2	1448.3	1358.3	1265.2	1178.0	1103.6	1030.0	967.4	908.2	857.5	814.3
32.5°	1524.4	1429.4	1332.4	1237.2	1148.8	1072.1	1002.4	939.4	881.3	829.4	783.5
35°	1485.3	1389.1	1283.8	1186.1	1099.3	1019.6	954.2	893.5	838.0	782.5	734.1
37.5°	1433.9	1335.5	1230.7	1123.7	1036.9	961.7	901.6	844.6	790.5	739.9	686.3
40°	1385.3	1295.7	1187.5	1081.3	992.1	919.5	864.1	812.3	757.9	707.6	654.0
42.5°	1326.4	1250.1	1140.9	1034.2	946.2	876.3	824.7	774.1	724.4	675.7	619.8
45°	1228.3	1170.5	1068.0	965.5	876.9	807.6	760.2	715.6	672.0	625.5	572.9
47.5°	1115.8	1076.7	988.2	883.3	801.3	739.0	693.1	656.7	619.8	573.4	527.2
50°	1037.7	1012.5	927.1	831.3	753.1	695.7	648.8	614.7	583.8	539.2	497.9
52.5°	954.2	940.8	868.7	777.1	701.5	645.2	605.1	574.4	543.2	506.2	467.6
55°	827.1	834.2	773.0	693.8	622.7	575.2	538.8	513.1	486.6	455.3	425.4
57.5°	697.1	723.1	682.1	612.5	545.8	502.0	474.6	453.0	430.7	404.7	379.2
60°	619.4	641.1	618.0	556.8	498.5	457.6	432.0	415.4	393.2	369.4	350.0
62.5°	543.5	566.9	553.0	503.6	449.5	414.4	391.8	376.4	359.8	339.1	318.9
65°	448.2	463.3	456.7	422.6	384.1	354.3	333.4	322.0	306.8	291.7	273.7
67.5°	343.2	372.6	368.7	350.5	317.4	294.0	280.4	270.3	256.5	245.2	232.9
70°	282.1	309.2	308.7	294.0	276.0	254.2	244.7	236.2	223.8	212.9	203.0
72.5°	231.0	255.7	259.4	248.2	235.8	219.3	210.2	204.3	192.3	184.9	176.8
75°	161.8	179.8	184.5	184.5	178.8	170.2	162.2	158.4	149.9	143.2	138.5
77.5°	106.0	117.4	124.8	126.5	127.4	124.6	117.9	115.2	108.7	106.3	101.7
80°	74.9	82.5	91.0	93.9	96.3	95.3	92.5	90.6	84.4	82.0	80.2
82.5°	51.8	56.0	63.0	69.2	68.6	71.1	68.6	67.1	62.4	61.5	59.7
85°	27.0	27.5	28.4	32.7	35.1	36.0	36.6	35.6	34.2	34.2	30.9
87.5°	10.6	10.1	10.7	10.5	10.7	12.0	12.9	13.1	12.2	11.2	10.3
90°	7.5	6.8	6.0	5.2	4.2	3.2	2.2	1.2	2.2	3.2	4.2
92.5°	7.1	6.4	5.7	5.4	5.3	5.2	5.2	5.1	5.2	5.2	5.3
95°	8.7	8.6	8.6	10.0	13.1	16.1	19.2	22.2	19.2	16.1	13.1
97.5°	30.7	40.8	50.7	54.8	52.9	51.0	49.1	47.2	49.1	51.0	52.9
100°	42.5	54.9	67.3	72.8	71.2	69.6	67.9	66.3	67.9	69.6	71.2
102.5°	88.9	90.5	92.1	92.4	91.1	90.0	88.8	87.7	88.8	90.0	91.1
105°	125.2	124.8	124.3	123.8	123.2	122.7	122.2	121.6	122.2	122.7	123.2
107.5°	156.0	155.3	154.8	154.4	154.1	153.8	153.6	153.3	153.6	153.8	154.1
110°	177.2	176.6	176.0	175.7	175.4	175.1	174.9	174.6	174.9	175.1	175.4



TEST NUMBER: P333055-940

CATALOG NUMBER: S124RDIW-S795D470U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	198.0	197.9	197.6	197.2	196.7	196.3	195.7	195.3	195.7	196.3	196.7
115°	228.1	228.2	228.3	228.2	227.9	227.7	227.4	227.1	227.4	227.7	227.9
117.5°	257.9	257.7	257.5	257.3	256.9	256.5	256.2	255.8	256.2	256.5	256.9
120°	276.6	276.7	276.8	276.6	276.3	275.9	275.5	275.2	275.5	275.9	276.3
122.5°	294.6	294.4	294.4	294.2	294.0	293.7	293.6	293.3	293.6	293.7	294.0
125°	320.4	320.6	320.7	320.7	320.3	319.9	319.6	319.2	319.6	319.9	320.3
127.5°	345.3	344.8	344.5	344.2	344.1	344.0	343.9	343.8	343.9	344.0	344.1
130°	360.8	360.5	360.3	360.1	360.0	359.9	359.7	359.6	359.7	359.9	360.0
132.5°	375.8	375.5	375.1	374.9	374.7	374.5	374.3	374.3	374.3	374.5	374.7
135°	396.5	396.2	395.8	395.7	395.7	395.8	395.9	396.0	395.9	395.8	395.7
137.5°	416.5	416.1	415.7	415.5	415.4	415.4	415.4	415.4	415.4	415.4	415.4
140°	429.3	429.0	428.8	428.6	428.5	428.3	428.1	427.9	428.1	428.3	428.5
142.5°	441.0	440.9	440.8	440.6	440.2	440.0	439.6	439.3	439.6	440.0	440.2
145°	457.9	457.9	457.9	457.7	457.4	457.2	456.9	456.6	456.9	457.2	457.4
147.5°	472.5	472.6	472.7	472.5	472.0	471.4	471.0	470.5	471.0	471.4	472.0
150°	481.9	482.0	482.1	482.0	481.6	481.3	480.9	480.5	480.9	481.3	481.6
152.5°	489.8	490.0	490.1	490.1	489.7	489.5	489.2	488.9	489.2	489.5	489.7
155°	500.4	500.7	501.0	501.1	501.0	500.9	500.8	500.7	500.8	500.9	501.0
157.5°	509.6	510.0	510.2	510.4	510.5	510.5	510.6	510.7	510.6	510.5	510.5
160°	515.1	515.1	515.2	515.4	515.7	515.9	516.2	516.5	516.2	515.9	515.7
162.5°	519.9	520.0	520.0	520.3	520.6	520.9	521.3	521.7	521.3	520.9	520.6
165°	526.2	526.2	526.2	526.4	526.8	527.3	527.7	528.2	527.7	527.3	526.8
167.5°	531.1	531.2	531.2	531.5	532.0	532.4	532.9	533.3	532.9	532.4	532.0
170°	534.0	534.0	533.9	534.1	534.7	535.2	535.7	536.3	535.7	535.2	534.7
172.5°	536.0	535.9	535.8	536.1	536.6	537.2	537.7	538.2	537.7	537.2	536.6
175°	538.1	538.1	538.0	538.1	538.7	539.2	539.8	540.3	539.8	539.2	538.7
177.5°	539.4	539.2	539.1	539.3	539.8	540.3	540.8	541.3	540.8	540.3	539.8
180°	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3



TEST NUMBER: P333055-940

CATALOG NUMBER: S124RDIW-S795D470U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1
2.5°	1155.8	1152.0	1147.1	1141.4	1134.6	1128.5	1125.9	1128.1	1129.3	1126.2	1125.9
5°	1120.6	1108.8	1099.3	1085.0	1073.7	1064.2	1057.6	1054.7	1055.7	1048.1	1046.2
7.5°	1081.1	1067.0	1051.5	1034.7	1018.9	1005.0	997.6	993.6	985.6	982.1	976.3
10°	1055.7	1036.7	1021.5	1001.6	983.6	967.0	958.9	952.3	944.2	940.4	932.4
12.5°	1029.5	1007.5	990.8	970.1	951.7	931.7	924.0	911.7	899.1	891.1	880.7
15°	992.6	966.1	945.7	921.0	899.2	876.4	856.0	833.2	824.7	806.7	796.3
17.5°	949.4	922.5	897.2	864.2	830.5	802.3	780.5	758.7	745.6	734.1	728.8
20°	921.0	896.3	861.2	822.8	785.3	754.0	736.5	722.3	708.0	700.0	694.3
22.5°	894.0	862.6	821.8	780.3	742.9	718.4	703.5	688.8	677.3	669.7	662.0
25°	848.9	807.6	764.5	717.0	691.4	670.1	654.0	642.1	635.0	625.1	621.3
27.5°	802.5	752.5	704.9	673.1	646.4	626.9	612.8	603.9	594.9	588.5	583.6
30°	766.9	716.1	673.4	643.1	616.1	599.9	588.5	578.1	571.0	565.8	562.0
32.5°	731.6	680.8	645.0	612.3	591.0	575.2	563.1	555.4	549.7	543.1	540.7
35°	680.6	635.5	604.2	574.8	552.9	538.8	529.2	521.2	516.5	514.5	513.1
37.5°	631.5	594.6	561.0	536.8	517.4	506.2	495.0	491.1	487.8	484.4	485.9
40°	600.4	565.8	535.9	510.3	494.6	482.3	475.6	470.9	468.1	468.1	468.1
42.5°	573.5	539.6	510.5	487.5	471.9	461.5	454.1	450.0	449.1	448.7	451.0
45°	531.6	500.3	470.9	451.9	438.6	428.2	424.0	420.6	420.6	422.6	423.0
47.5°	490.2	460.8	437.3	416.0	403.9	397.3	393.6	391.9	392.1	394.0	396.2
50°	464.8	435.9	412.6	393.6	382.3	376.0	372.7	371.8	372.7	372.7	376.0
52.5°	437.0	411.2	388.3	372.4	359.4	353.7	351.9	350.5	351.2	352.7	354.1
55°	396.5	373.3	351.4	336.3	326.7	323.0	318.7	319.1	318.3	319.1	319.1
57.5°	355.8	334.9	314.6	302.6	294.3	288.7	284.1	285.4	284.0	283.8	283.0
60°	329.6	306.8	290.7	279.8	270.3	265.6	261.3	262.3	260.8	259.8	258.0
62.5°	301.1	282.1	266.8	256.3	248.7	243.2	238.9	238.0	234.7	231.4	227.3
65°	259.8	244.2	230.5	220.5	213.4	209.1	205.8	203.0	195.8	188.2	184.5
67.5°	219.8	208.5	195.6	187.3	181.5	175.8	169.5	164.7	158.0	153.8	151.5
70°	193.9	183.1	172.2	164.1	157.9	152.8	145.6	142.3	137.5	135.6	133.2
72.5°	169.3	159.2	149.0	141.7	135.2	131.1	125.5	122.2	120.1	119.3	117.0
75°	131.9	123.8	116.2	109.6	104.3	101.5	99.2	96.8	95.8	91.5	89.2
77.5°	96.2	90.9	86.1	81.4	77.7	75.8	71.2	68.5	66.9	64.9	64.4
80°	74.9	71.2	66.4	63.6	58.3	56.4	54.6	54.0	53.6	53.1	52.6
82.5°	56.4	52.5	47.8	46.1	44.7	43.5	42.4	41.9	41.5	41.7	41.6
85°	28.4	26.6	26.6	26.1	25.6	25.1	24.7	24.7	24.2	24.7	24.2
87.5°	10.5	10.3	10.4	9.8	10.3	10.5	10.3	10.3	10.8	10.2	10.3
90°	5.2	6.0	6.8	7.5	8.2	8.9	9.5	10.0	10.5	11.1	11.4
92.5°	5.4	5.7	6.4	7.1	7.8	8.6	9.1	9.6	10.2	10.7	11.0
95°	10.0	8.6	8.6	8.7	8.8	8.9	9.5	10.0	10.5	11.1	11.3
97.5°	54.8	50.7	40.8	30.7	20.7	10.7	10.7	10.8	10.8	10.9	11.0
100°	72.8	67.3	54.9	42.5	30.1	17.7	16.2	14.7	13.2	11.7	11.0
102.5°	92.4	92.1	90.5	88.9	87.3	85.7	69.2	52.7	36.3	19.8	11.6
105°	123.8	124.3	124.8	125.2	125.6	126.1	126.9	127.7	128.5	129.3	128.1
107.5°	154.4	154.8	155.3	156.0	156.6	157.2	157.6	158.0	158.4	158.8	159.2
110°	175.7	176.0	176.6	177.2	177.7	178.3	178.4	178.6	178.8	179.0	179.1



TEST NUMBER: P333055-940

CATALOG NUMBER: S124RDIW-S795D470U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	197.2	197.6	197.9	198.0	198.3	198.6	198.6	198.5	198.5	198.4	198.6
115°	228.2	228.3	228.2	228.1	228.0	227.9	228.1	228.3	228.5	228.6	228.7
117.5°	257.3	257.5	257.7	257.9	258.2	258.3	258.2	258.2	258.2	258.2	258.2
120°	276.6	276.8	276.7	276.6	276.5	276.4	276.6	276.8	277.0	277.1	277.1
122.5°	294.2	294.4	294.4	294.6	294.7	294.9	295.0	295.1	295.2	295.2	295.2
125°	320.7	320.7	320.6	320.4	320.2	320.0	320.3	320.6	320.8	321.1	321.3
127.5°	344.2	344.5	344.8	345.3	345.7	346.1	346.1	346.0	345.9	345.9	345.8
130°	360.1	360.3	360.5	360.8	361.1	361.3	361.4	361.5	361.6	361.7	361.7
132.5°	374.9	375.1	375.5	375.8	376.1	376.5	376.6	376.7	376.7	376.8	376.8
135°	395.7	395.8	396.2	396.5	396.9	397.3	397.4	397.6	397.8	398.0	398.1
137.5°	415.5	415.7	416.1	416.5	416.9	417.3	417.5	417.7	417.9	418.1	418.1
140°	428.6	428.8	429.0	429.3	429.4	429.6	429.9	430.2	430.4	430.7	430.9
142.5°	440.6	440.8	440.9	441.0	441.1	441.2	441.4	441.6	441.8	442.0	442.1
145°	457.7	457.9	457.9	457.9	457.9	457.9	458.0	458.1	458.2	458.3	458.3
147.5°	472.5	472.7	472.6	472.5	472.4	472.3	472.4	472.5	472.5	472.6	472.7
150°	482.0	482.1	482.0	481.9	481.8	481.7	481.7	481.7	481.7	481.7	481.8
152.5°	490.1	490.1	490.0	489.8	489.6	489.5	489.6	489.7	489.9	490.1	490.1
155°	501.1	501.0	500.7	500.4	500.2	499.9	500.2	500.6	501.0	501.3	501.4
157.5°	510.4	510.2	510.0	509.6	509.3	509.1	509.5	510.0	510.4	510.9	510.9
160°	515.4	515.2	515.1	515.1	515.0	514.9	515.4	515.9	516.5	517.0	517.0
162.5°	520.3	520.0	520.0	519.9	519.8	519.7	520.2	520.8	521.3	521.8	521.8
165°	526.4	526.2	526.2	526.2	526.2	526.2	526.9	527.6	528.3	529.1	529.0
167.5°	531.5	531.2	531.2	531.1	531.1	531.0	531.8	532.6	533.4	534.2	534.1
170°	534.1	533.9	534.0	534.0	534.1	534.2	534.9	535.7	536.4	537.2	537.1
172.5°	536.1	535.8	535.9	536.0	536.1	536.2	536.9	537.6	538.3	539.0	539.0
175°	538.1	538.0	538.1	538.1	538.2	538.3	539.1	539.9	540.7	541.5	541.4
177.5°	539.3	539.1	539.2	539.4	539.5	539.7	540.2	540.8	541.4	542.0	541.8
180°	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3



TEST NUMBER: P333055-940

CATALOG NUMBER: S124RDIW-S795D470U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1
2.5°	1123.6	1124.4	1121.7	1120.9	1121.7	1124.4	1123.6	1125.9	1126.2	1129.3	1128.1
5°	1042.4	1041.4	1039.1	1039.6	1039.1	1041.4	1042.4	1046.2	1048.1	1055.7	1054.7
7.5°	972.9	969.3	970.3	966.5	970.3	969.3	972.9	976.3	982.1	985.6	993.6
10°	930.5	925.2	921.0	917.2	921.0	925.2	930.5	932.4	940.4	944.2	952.3
12.5°	872.4	868.0	862.2	863.4	862.2	868.0	872.4	880.7	891.1	899.1	911.7
15°	790.1	783.0	771.6	773.0	771.6	783.0	790.1	796.3	806.7	824.7	833.2
17.5°	720.4	720.5	715.2	716.5	715.2	720.5	720.4	728.8	734.1	745.6	758.7
20°	684.3	681.0	681.4	680.1	681.4	681.0	684.3	694.3	700.0	708.0	722.3
22.5°	659.3	655.2	651.9	649.0	651.9	655.2	659.3	662.0	669.7	677.3	688.8
25°	617.0	614.1	609.8	608.9	609.8	614.1	617.0	621.3	625.1	635.0	642.1
27.5°	579.8	579.3	577.6	575.3	577.6	579.3	579.8	583.6	588.5	594.9	603.9
30°	558.2	557.2	556.2	554.8	556.2	557.2	558.2	562.0	565.8	571.0	578.1
32.5°	538.9	538.2	537.3	537.4	537.3	538.2	538.9	540.7	543.1	549.7	555.4
35°	511.2	510.8	509.8	509.3	509.8	510.8	511.2	513.1	514.5	516.5	521.2
37.5°	485.4	486.7	486.1	486.0	486.1	486.7	485.4	485.9	484.4	487.8	491.1
40°	467.6	468.1	469.0	468.6	469.0	468.1	467.6	468.1	468.1	468.1	470.9
42.5°	452.8	452.9	454.2	452.6	454.2	452.9	452.8	451.0	448.7	449.1	450.0
45°	426.3	429.2	428.7	428.7	428.7	429.2	426.3	423.0	422.6	420.6	420.6
47.5°	397.4	399.8	400.6	400.5	400.6	399.8	397.4	396.2	394.0	392.1	391.9
50°	378.4	377.5	378.9	378.4	378.9	377.5	378.4	376.0	372.7	372.7	371.8
52.5°	355.3	355.5	355.4	354.9	355.4	355.5	355.3	354.1	352.7	351.2	350.5
55°	319.7	320.1	319.1	319.7	319.1	320.1	319.7	319.1	319.1	318.3	319.1
57.5°	281.0	278.7	279.6	278.5	279.6	278.7	281.0	283.0	283.8	284.0	285.4
60°	253.2	249.4	248.5	246.6	248.5	249.4	253.2	258.0	259.8	260.8	262.3
62.5°	222.1	219.5	216.2	217.8	216.2	219.5	222.1	227.3	231.4	234.7	238.0
65°	180.7	178.8	177.4	179.2	177.4	178.8	180.7	184.5	188.2	195.8	203.0
67.5°	149.5	148.6	148.6	147.6	148.6	148.6	149.5	151.5	153.8	158.0	164.7
70°	133.2	131.9	131.9	130.9	131.9	131.9	133.2	133.2	135.6	137.5	142.3
72.5°	116.5	115.1	115.6	114.9	115.6	115.1	116.5	117.0	119.3	120.1	122.2
75°	86.3	83.9	83.9	84.4	83.9	83.9	86.3	89.2	91.5	95.8	96.8
77.5°	64.4	63.9	64.6	63.8	64.6	63.9	64.4	64.4	64.9	66.9	68.5
80°	52.6	52.2	51.7	53.1	51.7	52.2	52.6	52.6	53.1	53.6	54.0
82.5°	40.8	40.8	40.7	42.5	40.7	40.8	40.8	41.6	41.7	41.5	41.9
85°	24.7	23.7	24.7	23.7	24.7	23.7	24.7	24.2	24.7	24.2	24.7
87.5°	11.1	10.7	10.3	10.8	10.3	10.7	11.1	10.3	10.2	10.8	10.3
90°	11.6	11.8	11.9	12.1	11.9	11.8	11.6	11.4	11.1	10.5	10.0
92.5°	11.1	11.1	11.1	11.1	11.1	11.1	11.1	11.0	10.7	10.2	9.6
95°	11.4	11.5	11.6	11.7	11.6	11.5	11.4	11.3	11.1	10.5	10.0
97.5°	11.1	11.1	11.2	11.3	11.2	11.1	11.1	11.0	10.9	10.8	10.8
100°	11.1	11.1	11.2	11.3	11.2	11.1	11.1	11.0	11.7	13.2	14.7
102.5°	11.6	11.6	11.6	11.7	11.6	11.6	11.6	11.6	19.8	36.3	52.7
105°	124.8	121.6	118.4	115.2	118.4	121.6	124.8	128.1	129.3	128.5	127.7
107.5°	159.5	159.8	160.2	160.5	160.2	159.8	159.5	159.2	158.8	158.4	158.0
110°	179.4	179.7	179.9	180.2	179.9	179.7	179.4	179.1	179.0	178.8	178.6



TEST NUMBER: P333055-940

CATALOG NUMBER: S124RDIW-S795D470U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	198.9	199.3	199.7	199.9	199.7	199.3	198.9	198.6	198.4	198.5	198.5
115°	228.7	228.7	228.7	228.7	228.7	228.7	228.7	228.7	228.6	228.5	228.3
117.5°	258.1	258.1	258.1	258.0	258.1	258.1	258.1	258.2	258.2	258.2	258.2
120°	277.0	276.8	276.6	276.4	276.6	276.8	277.0	277.1	277.1	277.0	276.8
122.5°	295.1	294.9	294.7	294.5	294.7	294.9	295.1	295.2	295.2	295.2	295.1
125°	321.4	321.5	321.6	321.6	321.6	321.5	321.4	321.3	321.1	320.8	320.6
127.5°	345.7	345.6	345.6	345.5	345.6	345.6	345.7	345.8	345.9	345.9	346.0
130°	361.7	361.7	361.7	361.7	361.7	361.7	361.7	361.7	361.7	361.6	361.5
132.5°	376.7	376.7	376.7	376.6	376.7	376.7	376.7	376.8	376.8	376.7	376.7
135°	398.3	398.5	398.7	398.9	398.7	398.5	398.3	398.1	398.0	397.8	397.6
137.5°	418.1	418.0	418.0	417.9	418.0	418.0	418.1	418.1	418.1	417.9	417.7
140°	431.0	431.1	431.1	431.2	431.1	431.1	431.0	430.9	430.7	430.4	430.2
142.5°	442.1	442.2	442.2	442.2	442.2	442.2	442.1	442.1	442.0	441.8	441.6
145°	458.5	458.7	458.9	459.1	458.9	458.7	458.5	458.3	458.3	458.2	458.1
147.5°	472.8	472.9	473.0	473.1	473.0	472.9	472.8	472.7	472.6	472.5	472.5
150°	481.9	482.0	482.1	482.1	482.1	482.0	481.9	481.8	481.7	481.7	481.7
152.5°	490.1	490.0	489.9	489.9	489.9	490.0	490.1	490.1	490.1	489.9	489.7
155°	501.1	500.9	500.6	500.3	500.6	500.9	501.1	501.4	501.3	501.0	500.6
157.5°	510.4	510.0	509.5	509.1	509.5	510.0	510.4	510.9	510.9	510.4	510.0
160°	516.5	515.9	515.4	514.9	515.4	515.9	516.5	517.0	517.0	516.5	515.9
162.5°	521.2	520.6	520.0	519.4	520.0	520.6	521.2	521.8	521.8	521.3	520.8
165°	528.2	527.4	526.6	525.8	526.6	527.4	528.2	529.0	529.1	528.3	527.6
167.5°	533.2	532.4	531.5	530.6	531.5	532.4	533.2	534.1	534.2	533.4	532.6
170°	536.1	535.2	534.3	533.4	534.3	535.2	536.1	537.1	537.2	536.4	535.7
172.5°	538.0	537.0	536.0	535.0	536.0	537.0	538.0	539.0	539.0	538.3	537.6
175°	540.3	539.2	538.1	537.1	538.1	539.2	540.3	541.4	541.5	540.7	539.9
177.5°	541.0	540.1	539.2	538.4	539.2	540.1	541.0	541.8	542.0	541.4	540.8
180°	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3



TEST NUMBER: P333055-940

CATALOG NUMBER: S124RDIW-S795D470U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1
2.5°	1125.9	1128.5	1134.6	1141.4	1147.1	1152.0	1155.8	1161.1	1166.1	1172.9	1179.4
5°	1057.6	1064.2	1073.7	1085.0	1099.3	1108.8	1120.6	1131.0	1146.2	1161.5	1176.2
7.5°	997.6	1005.0	1018.9	1034.7	1051.5	1067.0	1081.1	1099.5	1119.6	1141.7	1166.4
10°	958.9	967.0	983.6	1001.6	1021.5	1036.7	1055.7	1077.5	1100.3	1127.3	1157.6
12.5°	924.0	931.7	951.7	970.1	990.8	1007.5	1029.5	1051.7	1082.0	1111.3	1145.8
15°	856.0	876.4	899.2	921.0	945.7	966.1	992.6	1015.4	1044.3	1085.6	1124.9
17.5°	780.5	802.3	830.5	864.2	897.2	922.5	949.4	977.7	1012.1	1054.3	1099.7
20°	736.5	754.0	785.3	822.8	861.2	896.3	921.0	952.3	987.8	1033.4	1080.3
22.5°	703.5	718.4	742.9	780.3	821.8	862.6	894.0	925.0	964.3	1009.9	1061.0
25°	654.0	670.1	691.4	717.0	764.5	807.6	848.9	884.5	926.2	971.7	1028.7
27.5°	612.8	626.9	646.4	673.1	704.9	752.5	802.5	843.1	885.9	934.8	991.8
30°	588.5	599.9	616.1	643.1	673.4	716.1	766.9	814.3	857.5	908.2	967.4
32.5°	563.1	575.2	591.0	612.3	645.0	680.8	731.6	783.5	829.4	881.3	939.4
35°	529.2	538.8	552.9	574.8	604.2	635.5	680.6	734.1	782.5	838.0	893.5
37.5°	495.0	506.2	517.4	536.8	561.0	594.6	631.5	686.3	739.9	790.5	844.6
40°	475.6	482.3	494.6	510.3	535.9	565.8	600.4	654.0	707.6	757.9	812.3
42.5°	454.1	461.5	471.9	487.5	510.5	539.6	573.5	619.8	675.7	724.4	774.1
45°	424.0	428.2	438.6	451.9	470.9	500.3	531.6	572.9	625.5	672.0	715.6
47.5°	393.6	397.3	403.9	416.0	437.3	460.8	490.2	527.2	573.4	619.8	656.7
50°	372.7	376.0	382.3	393.6	412.6	435.9	464.8	497.9	539.2	583.8	614.7
52.5°	351.9	353.7	359.4	372.4	388.3	411.2	437.0	467.6	506.2	543.2	574.4
55°	318.7	323.0	326.7	336.3	351.4	373.3	396.5	425.4	455.3	486.6	513.1
57.5°	284.1	288.7	294.3	302.6	314.6	334.9	355.8	379.2	404.7	430.7	453.0
60°	261.3	265.6	270.3	279.8	290.7	306.8	329.6	350.0	369.4	393.2	415.4
62.5°	238.9	243.2	248.7	256.3	266.8	282.1	301.1	318.9	339.1	359.8	376.4
65°	205.8	209.1	213.4	220.5	230.5	244.2	259.8	273.7	291.7	306.8	322.0
67.5°	169.5	175.8	181.5	187.3	195.6	208.5	219.8	232.9	245.2	256.5	270.3
70°	145.6	152.8	157.9	164.1	172.2	183.1	193.9	203.0	212.9	223.8	236.2
72.5°	125.5	131.1	135.2	141.7	149.0	159.2	169.3	176.8	184.9	192.3	204.3
75°	99.2	101.5	104.3	109.6	116.2	123.8	131.9	138.5	143.2	149.9	158.4
77.5°	71.2	75.8	77.7	81.4	86.1	90.9	96.2	101.7	106.3	108.7	115.2
80°	54.6	56.4	58.3	63.6	66.4	71.2	74.9	80.2	82.0	84.4	90.6
82.5°	42.4	43.5	44.7	46.1	47.8	52.5	56.4	59.7	61.5	62.4	67.1
85°	24.7	25.1	25.6	26.1	26.6	26.6	28.4	30.9	34.2	34.2	35.6
87.5°	10.3	10.5	10.3	9.8	10.4	10.3	10.5	10.3	11.2	12.2	13.1
90°	9.5	8.9	8.2	7.5	6.8	6.0	5.2	4.2	3.2	2.2	1.2
92.5°	9.1	8.6	7.8	7.1	6.4	5.7	5.4	5.3	5.2	5.2	5.1
95°	9.5	8.9	8.8	8.7	8.6	8.6	10.0	13.1	16.1	19.2	22.2
97.5°	10.7	10.7	20.7	30.7	40.8	50.7	54.8	52.9	51.0	49.1	47.2
100°	16.2	17.7	30.1	42.5	54.9	67.3	72.8	71.2	69.6	67.9	66.3
102.5°	69.2	85.7	87.3	88.9	90.5	92.1	92.4	91.1	90.0	88.8	87.7
105°	126.9	126.1	125.6	125.2	124.8	124.3	123.8	123.2	122.7	122.2	121.6
107.5°	157.6	157.2	156.6	156.0	155.3	154.8	154.4	154.1	153.8	153.6	153.3
110°	178.4	178.3	177.7	177.2	176.6	176.0	175.7	175.4	175.1	174.9	174.6



TEST NUMBER: P333055-940

CATALOG NUMBER: S124RDIW-S795D470U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	198.6	198.6	198.3	198.0	197.9	197.6	197.2	196.7	196.3	195.7	195.3
115°	228.1	227.9	228.0	228.1	228.2	228.3	228.2	227.9	227.7	227.4	227.1
117.5°	258.2	258.3	258.2	257.9	257.7	257.5	257.3	256.9	256.5	256.2	255.8
120°	276.6	276.4	276.5	276.6	276.7	276.8	276.6	276.3	275.9	275.5	275.2
122.5°	295.0	294.9	294.7	294.6	294.4	294.4	294.2	294.0	293.7	293.6	293.3
125°	320.3	320.0	320.2	320.4	320.6	320.7	320.7	320.3	319.9	319.6	319.2
127.5°	346.1	346.1	345.7	345.3	344.8	344.5	344.2	344.1	344.0	343.9	343.8
130°	361.4	361.3	361.1	360.8	360.5	360.3	360.1	360.0	359.9	359.7	359.6
132.5°	376.6	376.5	376.1	375.8	375.5	375.1	374.9	374.7	374.5	374.3	374.3
135°	397.4	397.3	396.9	396.5	396.2	395.8	395.7	395.7	395.8	395.9	396.0
137.5°	417.5	417.3	416.9	416.5	416.1	415.7	415.5	415.4	415.4	415.4	415.4
140°	429.9	429.6	429.4	429.3	429.0	428.8	428.6	428.5	428.3	428.1	427.9
142.5°	441.4	441.2	441.1	441.0	440.9	440.8	440.6	440.2	440.0	439.6	439.3
145°	458.0	457.9	457.9	457.9	457.9	457.9	457.7	457.4	457.2	456.9	456.6
147.5°	472.4	472.3	472.4	472.5	472.6	472.7	472.5	472.0	471.4	471.0	470.5
150°	481.7	481.7	481.8	481.9	482.0	482.1	482.0	481.6	481.3	480.9	480.5
152.5°	489.6	489.5	489.6	489.8	490.0	490.1	490.1	489.7	489.5	489.2	488.9
155°	500.2	499.9	500.2	500.4	500.7	501.0	501.1	501.0	500.9	500.8	500.7
157.5°	509.5	509.1	509.3	509.6	510.0	510.2	510.4	510.5	510.5	510.6	510.7
160°	515.4	514.9	515.0	515.1	515.1	515.2	515.4	515.7	515.9	516.2	516.5
162.5°	520.2	519.7	519.8	519.9	520.0	520.0	520.3	520.6	520.9	521.3	521.7
165°	526.9	526.2	526.2	526.2	526.2	526.2	526.4	526.8	527.3	527.7	528.2
167.5°	531.8	531.0	531.1	531.1	531.2	531.2	531.5	532.0	532.4	532.9	533.3
170°	534.9	534.2	534.1	534.0	534.0	533.9	534.1	534.7	535.2	535.7	536.3
172.5°	536.9	536.2	536.1	536.0	535.9	535.8	536.1	536.6	537.2	537.7	538.2
175°	539.1	538.3	538.2	538.1	538.1	538.0	538.1	538.7	539.2	539.8	540.3
177.5°	540.2	539.7	539.5	539.4	539.2	539.1	539.3	539.8	540.3	540.8	541.3
180°	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3



TEST NUMBER: P333055-940

CATALOG NUMBER: S124RDIW-S795D470U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1
2.5°	1184.3	1187.7	1191.5	1198.7	1204.8	1207.5	1212.7	1216.6	1215.4	1220.7	1229.8
5°	1188.9	1201.8	1216.5	1231.6	1248.7	1262.9	1274.3	1285.7	1294.7	1305.6	1321.7
7.5°	1188.2	1210.9	1235.7	1262.9	1290.9	1315.1	1337.5	1360.2	1380.5	1402.6	1431.5
10°	1185.2	1215.5	1246.3	1281.9	1317.4	1351.1	1381.4	1410.0	1437.0	1465.9	1502.4
12.5°	1181.7	1216.7	1253.9	1296.6	1341.0	1381.4	1417.1	1458.1	1492.0	1529.3	1571.5
15°	1166.6	1213.6	1264.4	1319.8	1373.0	1427.5	1476.3	1526.6	1573.5	1618.1	1671.2
17.5°	1149.4	1203.5	1263.4	1328.9	1392.8	1459.0	1517.0	1580.4	1628.4	1688.2	1737.5
20°	1135.3	1193.6	1257.7	1331.2	1403.7	1477.3	1541.3	1605.8	1659.8	1720.1	1782.7
22.5°	1118.3	1182.3	1251.6	1327.8	1403.7	1484.1	1555.0	1619.1	1686.0	1753.8	1818.4
25°	1090.7	1157.2	1230.7	1314.1	1401.4	1483.5	1559.3	1639.0	1711.1	1784.6	1842.5
27.5°	1057.0	1126.7	1204.2	1290.3	1379.8	1463.9	1553.3	1638.2	1710.7	1781.5	1831.9
30°	1030.0	1103.6	1178.0	1265.2	1358.3	1448.3	1544.2	1629.1	1705.4	1769.0	1797.4
32.5°	1002.4	1072.1	1148.8	1237.2	1332.4	1429.4	1524.4	1611.2	1681.9	1720.0	1720.7
35°	954.2	1019.6	1099.3	1186.1	1283.8	1389.1	1485.3	1570.7	1613.8	1617.2	1570.7
37.5°	901.6	961.7	1036.9	1123.7	1230.7	1335.5	1433.9	1490.8	1505.1	1456.9	1370.9
40°	864.1	919.5	992.1	1081.3	1187.5	1295.7	1385.3	1427.0	1411.8	1333.6	1237.8
42.5°	824.7	876.3	946.2	1034.2	1140.9	1250.1	1326.4	1348.9	1308.7	1218.3	1106.2
45°	760.2	807.6	876.9	965.5	1068.0	1170.5	1228.3	1216.9	1150.0	1042.9	917.2
47.5°	693.1	739.0	801.3	883.3	988.2	1076.7	1115.8	1081.5	986.3	868.4	766.2
50°	648.8	695.7	753.1	831.3	927.1	1012.5	1037.7	985.5	879.8	766.3	672.4
52.5°	605.1	645.2	701.5	777.1	868.7	940.8	954.2	894.0	784.9	683.3	600.0
55°	538.8	575.2	622.7	693.8	773.0	834.2	827.1	749.8	650.7	563.9	498.5
57.5°	474.6	502.0	545.8	612.5	682.1	723.1	697.1	631.2	538.9	467.8	412.6
60°	432.0	457.6	498.5	556.8	618.0	641.1	619.4	547.8	474.7	409.7	363.3
62.5°	391.8	414.4	449.5	503.6	553.0	566.9	543.5	481.0	415.2	359.6	321.2
65°	333.4	354.3	384.1	422.6	456.7	463.3	448.2	384.1	334.3	287.8	261.3
67.5°	280.4	294.0	317.4	350.5	368.7	372.6	343.2	303.0	259.1	230.6	210.5
70°	244.7	254.2	276.0	294.0	308.7	309.2	282.1	249.9	216.2	193.1	178.3
72.5°	210.2	219.3	235.8	248.2	259.4	255.7	231.0	205.5	178.3	160.8	149.9
75°	162.2	170.2	178.8	184.5	184.5	179.8	161.8	142.8	127.1	116.6	113.3
77.5°	117.9	124.6	127.4	126.5	124.8	117.4	106.0	93.6	88.0	83.1	80.6
80°	92.5	95.3	96.3	93.9	91.0	82.5	74.9	69.7	64.5	62.6	61.6
82.5°	68.6	71.1	68.6	69.2	63.0	56.0	51.8	50.0	47.8	47.1	46.1
85°	36.6	36.0	35.1	32.7	28.4	27.5	27.0	26.6	25.6	26.1	25.1
87.5°	12.9	12.0	10.7	10.5	10.7	10.1	10.6	10.7	10.9	10.6	11.5
90°	2.2	3.2	4.2	5.2	6.0	6.8	7.5	8.2	8.9	9.5	10.0
92.5°	5.2	5.2	5.3	5.4	5.7	6.4	7.1	7.8	8.6	9.1	9.6
95°	19.2	16.1	13.1	10.0	8.6	8.6	8.7	8.8	8.9	9.5	10.0
97.5°	49.1	51.0	52.9	54.8	50.7	40.8	30.7	20.7	10.7	10.7	10.8
100°	67.9	69.6	71.2	72.8	67.3	54.9	42.5	30.1	17.7	16.2	14.7
102.5°	88.8	90.0	91.1	92.4	92.1	90.5	88.9	87.3	85.7	69.2	52.7
105°	122.2	122.7	123.2	123.8	124.3	124.8	125.2	125.6	126.1	126.9	127.7
107.5°	153.6	153.8	154.1	154.4	154.8	155.3	156.0	156.6	157.2	157.6	158.0
110°	174.9	175.1	175.4	175.7	176.0	176.6	177.2	177.7	178.3	178.4	178.6



TEST NUMBER: P333055-940

CATALOG NUMBER: S124RDIW-S795D470U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	195.7	196.3	196.7	197.2	197.6	197.9	198.0	198.3	198.6	198.6	198.5
115°	227.4	227.7	227.9	228.2	228.3	228.2	228.1	228.0	227.9	228.1	228.3
117.5°	256.2	256.5	256.9	257.3	257.5	257.7	257.9	258.2	258.3	258.2	258.2
120°	275.5	275.9	276.3	276.6	276.8	276.7	276.6	276.5	276.4	276.6	276.8
122.5°	293.6	293.7	294.0	294.2	294.4	294.4	294.6	294.7	294.9	295.0	295.1
125°	319.6	319.9	320.3	320.7	320.7	320.6	320.4	320.2	320.0	320.3	320.6
127.5°	343.9	344.0	344.1	344.2	344.5	344.8	345.3	345.7	346.1	346.1	346.0
130°	359.7	359.9	360.0	360.1	360.3	360.5	360.8	361.1	361.3	361.4	361.5
132.5°	374.3	374.5	374.7	374.9	375.1	375.5	375.8	376.1	376.5	376.6	376.7
135°	395.9	395.8	395.7	395.7	395.8	396.2	396.5	396.9	397.3	397.4	397.6
137.5°	415.4	415.4	415.4	415.5	415.7	416.1	416.5	416.9	417.3	417.5	417.7
140°	428.1	428.3	428.5	428.6	428.8	429.0	429.3	429.4	429.6	429.9	430.2
142.5°	439.6	440.0	440.2	440.6	440.8	440.9	441.0	441.1	441.2	441.4	441.6
145°	456.9	457.2	457.4	457.7	457.9	457.9	457.9	457.9	457.9	458.0	458.1
147.5°	471.0	471.4	472.0	472.5	472.7	472.6	472.5	472.4	472.3	472.4	472.5
150°	480.9	481.3	481.6	482.0	482.1	482.0	481.9	481.8	481.7	481.7	481.7
152.5°	489.2	489.5	489.7	490.1	490.1	490.0	489.8	489.6	489.5	489.6	489.7
155°	500.8	500.9	501.0	501.1	501.0	500.7	500.4	500.2	499.9	500.2	500.6
157.5°	510.6	510.5	510.5	510.4	510.2	510.0	509.6	509.3	509.1	509.5	510.0
160°	516.2	515.9	515.7	515.4	515.2	515.1	515.1	515.0	514.9	515.4	515.9
162.5°	521.3	520.9	520.6	520.3	520.0	520.0	519.9	519.8	519.7	520.2	520.8
165°	527.7	527.3	526.8	526.4	526.2	526.2	526.2	526.2	526.2	526.9	527.6
167.5°	532.9	532.4	532.0	531.5	531.2	531.2	531.1	531.1	531.0	531.8	532.6
170°	535.7	535.2	534.7	534.1	533.9	534.0	534.0	534.1	534.2	534.9	535.7
172.5°	537.7	537.2	536.6	536.1	535.8	535.9	536.0	536.1	536.2	536.9	537.6
175°	539.8	539.2	538.7	538.1	538.0	538.1	538.1	538.2	538.3	539.1	539.9
177.5°	540.8	540.3	539.8	539.3	539.1	539.2	539.4	539.5	539.7	540.2	540.8
180°	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3



TEST NUMBER: P333055-940

CATALOG NUMBER: S124RDIW-S795D470U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1
2.5°	1234.8	1236.3	1237.4	1241.2	1241.5	1245.0	1241.5
5°	1336.9	1343.5	1354.0	1364.4	1365.4	1372.0	1360.1
7.5°	1451.4	1466.9	1476.4	1493.3	1499.9	1504.1	1497.3
10°	1530.4	1544.6	1569.8	1582.1	1594.4	1596.3	1590.6
12.5°	1606.7	1629.2	1649.0	1672.4	1671.8	1688.5	1682.4
15°	1708.3	1731.4	1759.0	1785.0	1794.6	1794.6	1802.1
17.5°	1780.7	1823.3	1851.7	1872.2	1894.6	1898.5	1895.9
20°	1829.6	1875.6	1906.0	1932.5	1947.8	1952.0	1952.0
22.5°	1866.1	1905.2	1934.8	1958.7	1971.2	1976.3	1974.8
25°	1891.3	1924.9	1942.9	1950.1	1953.4	1952.5	1943.5
27.5°	1856.7	1855.2	1843.9	1822.0	1805.6	1795.6	1784.3
30°	1790.7	1766.1	1737.7	1706.3	1666.0	1635.2	1625.7
32.5°	1692.5	1637.1	1588.9	1536.8	1493.4	1462.6	1449.7
35°	1502.4	1414.7	1343.1	1280.5	1234.9	1206.5	1197.0
37.5°	1276.8	1191.9	1103.3	1042.6	1004.9	976.1	965.4
40°	1133.5	1041.0	963.7	906.8	867.9	839.9	839.5
42.5°	1002.6	914.3	841.5	800.5	758.6	740.1	740.0
45°	820.9	750.3	688.6	656.4	631.2	616.1	611.8
47.5°	679.7	621.3	580.1	554.5	534.0	524.3	518.1
50°	600.4	549.2	516.5	494.2	482.8	470.5	469.5
52.5°	534.4	493.0	467.5	449.4	435.0	427.6	427.8
55°	449.1	416.4	398.3	384.6	373.3	367.6	365.2
57.5°	378.4	353.8	340.7	328.1	323.2	318.8	317.5
60°	334.3	317.7	305.4	295.4	288.4	287.0	286.4
62.5°	297.9	280.5	272.1	264.3	259.1	256.9	256.1
65°	245.7	232.8	225.2	219.1	217.2	213.9	213.4
67.5°	198.0	190.4	185.3	181.1	178.5	178.3	178.3
70°	168.8	164.5	160.3	157.9	156.5	155.5	155.5
72.5°	143.8	140.6	137.1	135.9	135.6	134.6	134.3
75°	109.6	106.2	106.7	104.3	102.5	100.0	98.6
77.5°	77.7	75.3	74.8	74.5	72.9	72.7	73.4
80°	60.2	57.9	57.4	57.9	57.4	56.0	56.0
82.5°	45.8	43.8	43.3	43.1	42.6	43.1	42.3
85°	24.7	23.7	23.7	23.7	24.7	24.2	23.7
87.5°	10.8	10.5	11.0	10.7	10.7	10.3	10.8
90°	10.5	11.1	11.4	11.6	11.8	11.9	12.1
92.5°	10.2	10.7	11.0	11.1	11.1	11.1	11.1
95°	10.5	11.1	11.3	11.4	11.5	11.6	11.7
97.5°	10.8	10.9	11.0	11.1	11.1	11.2	11.3
100°	13.2	11.7	11.0	11.1	11.1	11.2	11.3
102.5°	36.3	19.8	11.6	11.6	11.6	11.6	11.7
105°	128.5	129.3	128.1	124.8	121.6	118.4	115.2
107.5°	158.4	158.8	159.2	159.5	159.8	160.2	160.5
110°	178.8	179.0	179.1	179.4	179.7	179.9	180.2



TEST NUMBER: P333055-940

CATALOG NUMBER: S124RDIW-S795D470U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	198.5	198.4	198.6	198.9	199.3	199.7	199.9
115°	228.5	228.6	228.7	228.7	228.7	228.7	228.7
117.5°	258.2	258.2	258.2	258.1	258.1	258.1	258.0
120°	277.0	277.1	277.1	277.0	276.8	276.6	276.4
122.5°	295.2	295.2	295.2	295.1	294.9	294.7	294.5
125°	320.8	321.1	321.3	321.4	321.5	321.6	321.6
127.5°	345.9	345.9	345.8	345.7	345.6	345.6	345.5
130°	361.6	361.7	361.7	361.7	361.7	361.7	361.7
132.5°	376.7	376.8	376.8	376.7	376.7	376.7	376.6
135°	397.8	398.0	398.1	398.3	398.5	398.7	398.9
137.5°	417.9	418.1	418.1	418.1	418.0	418.0	417.9
140°	430.4	430.7	430.9	431.0	431.1	431.1	431.2
142.5°	441.8	442.0	442.1	442.1	442.2	442.2	442.2
145°	458.2	458.3	458.3	458.5	458.7	458.9	459.1
147.5°	472.5	472.6	472.7	472.8	472.9	473.0	473.1
150°	481.7	481.7	481.8	481.9	482.0	482.1	482.1
152.5°	489.9	490.1	490.1	490.1	490.0	489.9	489.9
155°	501.0	501.3	501.4	501.1	500.9	500.6	500.3
157.5°	510.4	510.9	510.9	510.4	510.0	509.5	509.1
160°	516.5	517.0	517.0	516.5	515.9	515.4	514.9
162.5°	521.3	521.8	521.8	521.2	520.6	520.0	519.4
165°	528.3	529.1	529.0	528.2	527.4	526.6	525.8
167.5°	533.4	534.2	534.1	533.2	532.4	531.5	530.6
170°	536.4	537.2	537.1	536.1	535.2	534.3	533.4
172.5°	538.3	539.0	539.0	538.0	537.0	536.0	535.0
175°	540.7	541.5	541.4	540.3	539.2	538.1	537.1
177.5°	541.4	542.0	541.8	541.0	540.1	539.2	538.4
180°	540.3	540.3	540.3	540.3	540.3	540.3	540.3

(END OF REPORT)