

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333106-935

Luminaire Tested: **S124RDIW-S1195D1050U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333106-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S1195D1050U935-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7280.8 lumens  
Efficiency: N/A  
Efficacy: 108.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 67.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333106-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333106-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63	57
1	100	95	92	88	93	89	86	83	77	75	72	66	64	63	56	55	53	49
2	91	84	78	73	85	78	73	68	68	64	60	58	55	53	49	47	45	41
3	83	74	67	61	77	69	63	57	60	55	51	52	48	45	44	41	39	35
4	76	66	58	52	71	61	54	49	54	48	44	46	42	39	40	36	34	30
5	70	59	50	44	65	55	48	42	48	42	38	42	37	34	36	32	30	27
6	65	53	45	39	60	49	42	37	43	38	33	38	33	30	33	29	26	24
7	60	48	40	34	56	45	38	33	40	34	29	35	30	26	30	26	23	21
8	56	43	36	30	52	41	34	29	36	30	26	32	27	24	27	24	21	19
9	52	40	32	27	48	37	31	26	33	28	24	29	25	21	25	22	19	17
10	49	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	17	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14495	14495	14495
5°	14528	14350	14439
10°	14437	14178	14178
15°	14271	13881	13778
20°	14044	13489	13241
25°	13752	13030	12699
30°	13470	12547	12021
35°	13157	12046	11340
40°	12779	11475	10606
45°	12432	10909	9857
50°	12036	10257	9065
55°	11610	9578	8204
60°	11144	8835	7325
65°	10714	7904	6460
70°	10093	6878	5486
75°	9304	5705	4460
80°	8117	4347	4091
85°	6873	3946	3696



TEST NUMBER: P333106-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	168.7	2.3
10°-20°	470.4	6.5
20°-30°	679.2	9.3
30°-40°	769.9	10.6
40°-50°	743.4	10.2
50°-60°	618.2	8.5
60°-70°	426.9	5.9
70°-80°	216.4	3.0
80°-90°	58.9	0.8
90°-100°	74.4	1.0
100°-110°	220.4	3.0
110°-120°	374.0	5.1
120°-130°	493.2	6.8
130°-140°	553.9	7.6
140°-150°	544.3	7.5
150°-160°	457.8	6.3
160°-170°	304.6	4.2
170°-180°	106.6	1.5
0°-30°	1318.2	18.1
0°-40°	2088.1	28.7
0°-60°	3449.7	47.4
0°-90°	4151.9	57.0
90°-120°	668.7	9.2
90°-150°	2260.0	31.0
90°-180°	3129.0	43.0
0°-180°	7280.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1796	1796	1796	1796	1796	
5°	1793	1787	1771	1784	1782	170
15°	1708	1694	1661	1658	1648	481
25°	1544	1517	1463	1440	1426	711
35°	1335	1290	1222	1177	1151	834
45°	1089	1036	956	890	863	839
55°	825	768	680	612	583	738
65°	561	500	414	357	338	554
75°	298	247	183	152	143	315
85°	74	48	43	40	40	84
90°	3	12	19	24	26	7
95°	52	60	66	69	69	58
105°	203	204	208	210	213	216
115°	380	380	379	378	377	375
125°	554	554	553	551	550	493
135°	714	719	720	718	715	552
145°	868	871	872	871	869	543
155°	994	994	994	997	994	457
165°	1082	1080	1078	1083	1080	305
175°	1126	1122	1121	1126	1121	107
180°	1128	1128	1128	1128	1128	



TEST NUMBER: P333106-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5
2.5°	1799.9	1799.0	1798.0	1797.0	1796.0	1794.2	1791.6	1788.8	1786.1	1783.5	1786.1
5°	1792.8	1791.6	1790.4	1789.2	1788.0	1785.5	1781.8	1778.1	1774.5	1770.8	1773.8
7.5°	1776.6	1775.3	1774.0	1772.7	1771.4	1768.4	1763.7	1758.9	1754.1	1749.4	1751.4
10°	1761.2	1759.6	1758.2	1756.6	1755.1	1751.5	1746.1	1740.6	1735.1	1729.6	1730.8
12.5°	1741.4	1739.7	1737.8	1736.0	1734.3	1730.2	1723.7	1717.3	1710.7	1704.3	1705.0
15°	1707.5	1704.8	1702.1	1699.4	1696.6	1691.3	1683.8	1676.1	1668.4	1660.8	1660.2
17.5°	1666.6	1662.6	1658.6	1654.7	1650.7	1644.2	1635.0	1625.8	1616.6	1607.5	1605.8
20°	1634.7	1630.7	1626.8	1622.8	1618.9	1611.6	1601.3	1590.9	1580.5	1570.1	1567.6
22.5°	1599.5	1595.1	1590.6	1586.1	1581.7	1573.9	1562.7	1551.6	1540.5	1529.4	1525.7
25°	1543.9	1538.4	1532.9	1527.5	1522.0	1512.9	1500.5	1487.9	1475.4	1462.8	1457.7
27.5°	1485.7	1478.8	1471.9	1465.0	1458.0	1447.9	1434.5	1421.2	1407.7	1394.4	1387.9
30°	1445.0	1437.4	1429.7	1422.0	1414.5	1403.4	1389.1	1374.7	1360.4	1346.0	1338.3
32.5°	1402.1	1393.4	1384.8	1376.2	1367.6	1355.9	1341.0	1326.2	1311.3	1296.5	1287.6
35°	1335.0	1325.2	1315.4	1305.6	1295.9	1283.3	1268.1	1252.8	1237.5	1222.3	1211.9
37.5°	1263.3	1253.1	1243.0	1233.0	1222.9	1209.4	1192.5	1175.5	1158.6	1141.7	1130.1
40°	1212.6	1202.6	1192.5	1182.4	1172.3	1158.6	1141.2	1123.7	1106.3	1088.9	1076.1
42.5°	1164.2	1153.7	1143.1	1132.5	1122.0	1107.6	1089.4	1071.3	1053.2	1035.0	1021.9
45°	1088.9	1077.5	1066.3	1055.0	1043.7	1028.8	1010.6	992.2	973.9	955.5	940.6
47.5°	1011.1	999.4	987.7	976.0	964.4	949.0	930.0	910.9	891.8	872.8	857.2
50°	958.3	946.3	934.4	922.6	910.6	894.8	875.3	855.7	836.2	816.7	801.4
52.5°	904.4	892.7	881.1	869.4	857.7	841.8	821.8	801.8	781.7	761.6	746.1
55°	824.9	812.7	800.5	788.2	776.0	760.0	740.1	720.3	700.4	680.5	664.7
57.5°	746.2	733.6	720.8	708.2	695.4	679.3	659.8	640.2	620.6	601.1	585.0
60°	690.2	678.0	665.7	653.5	641.3	625.4	605.9	586.3	566.7	547.2	531.3
62.5°	639.6	626.9	614.2	601.5	588.8	572.4	552.3	532.3	512.2	492.2	477.5
65°	560.9	547.8	534.7	521.5	508.4	492.1	472.5	453.0	433.4	413.8	400.7
67.5°	479.2	466.7	454.1	441.5	429.0	413.5	395.4	377.3	359.1	341.0	329.7
70°	427.6	414.7	401.9	389.1	376.3	361.1	343.7	326.3	308.9	291.4	281.4
72.5°	372.6	361.0	349.4	337.8	326.1	312.1	295.7	279.2	262.8	246.3	237.7
75°	298.3	287.1	275.7	264.4	253.1	240.3	225.9	211.5	197.3	182.9	175.8
77.5°	223.0	213.4	203.8	194.2	184.6	174.0	162.4	150.8	139.2	127.6	123.5
80°	174.6	165.7	156.9	148.0	139.1	130.2	121.0	111.8	102.6	93.5	92.6
82.5°	132.9	124.7	116.6	108.4	100.3	93.6	88.3	83.1	77.8	72.6	71.9
85°	74.2	68.1	62.0	55.9	49.8	46.3	45.4	44.4	43.6	42.6	42.0
87.5°	25.8	24.3	22.7	21.3	19.7	18.9	19.0	19.1	19.2	19.2	19.2
90°	2.6	4.7	6.9	9.0	11.1	13.0	14.6	16.1	17.7	19.2	20.3
92.5°	18.7	21.1	23.6	26.0	28.4	30.2	31.3	32.4	33.5	34.5	35.2
95°	52.3	54.1	55.8	57.6	59.3	60.9	62.3	63.5	64.9	66.3	66.9
97.5°	91.4	92.8	94.2	95.6	97.0	98.5	100.0	101.7	103.2	104.9	105.6
100°	122.1	122.9	123.6	124.4	125.2	126.5	128.2	129.9	131.7	133.5	133.8
102.5°	154.2	154.5	154.8	155.2	155.4	156.4	158.0	159.5	161.2	162.7	163.3
105°	203.2	203.5	203.6	203.8	204.0	204.5	205.3	206.0	206.8	207.6	208.2
107.5°	254.7	254.9	255.1	255.4	255.6	255.8	255.9	256.1	256.1	256.2	256.8
110°	289.6	290.0	290.3	290.8	291.1	291.2	291.0	290.8	290.7	290.4	290.1



TEST NUMBER: P333106-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	325.9	326.0	326.1	326.1	326.1	326.1	325.7	325.4	325.0	324.7	324.6
115°	380.3	380.3	380.3	380.3	380.3	380.1	379.7	379.4	378.9	378.6	378.3
117.5°	431.6	431.7	431.9	432.0	432.2	432.1	431.9	431.6	431.4	431.0	430.4
120°	465.8	466.6	467.4	468.1	468.9	469.0	468.4	467.8	467.3	466.7	465.7
122.5°	501.4	501.7	502.0	502.3	502.6	502.7	502.3	502.0	501.8	501.5	500.8
125°	553.9	553.9	553.9	553.9	553.9	553.8	553.5	553.4	553.2	553.0	552.6
127.5°	601.5	602.1	602.6	603.2	603.8	604.0	603.6	603.3	603.0	602.7	602.4
130°	635.0	635.6	636.1	636.7	637.3	637.6	637.6	637.6	637.6	637.6	637.2
132.5°	669.2	669.6	670.0	670.5	670.9	671.0	670.9	670.7	670.5	670.4	670.0
135°	714.4	715.5	716.7	717.8	719.0	719.6	719.6	719.6	719.6	719.6	719.2
137.5°	763.5	764.1	764.7	765.2	765.7	766.1	766.5	766.8	767.1	767.4	766.9
140°	796.3	796.8	797.1	797.5	797.9	798.1	798.1	798.1	798.1	798.1	797.9
142.5°	826.4	826.7	827.2	827.5	827.9	828.0	827.9	827.7	827.6	827.4	827.3
145°	867.9	868.7	869.4	870.2	871.0	871.4	871.7	871.8	872.0	872.2	872.0
147.5°	909.0	910.0	910.9	911.8	912.7	913.2	913.0	912.8	912.7	912.5	912.4
150°	934.2	935.0	935.7	936.5	937.3	937.6	937.6	937.6	937.6	937.6	937.6
152.5°	957.9	958.4	958.8	959.2	959.8	960.0	960.2	960.4	960.5	960.7	961.1
155°	994.4	994.4	994.4	994.4	994.4	994.3	994.0	993.9	993.7	993.5	994.3
157.5°	1025.0	1024.7	1024.3	1024.0	1023.6	1023.5	1023.4	1023.4	1023.3	1023.3	1023.9
160°	1043.2	1043.0	1042.8	1042.6	1042.4	1042.2	1042.0	1041.8	1041.6	1041.5	1042.0
162.5°	1059.9	1059.5	1058.9	1058.4	1057.9	1057.6	1057.4	1057.2	1057.0	1056.8	1057.8
165°	1082.4	1081.8	1081.2	1080.7	1080.1	1079.6	1079.3	1078.8	1078.5	1078.1	1079.3
167.5°	1099.7	1098.9	1098.1	1097.3	1096.5	1096.1	1096.1	1096.1	1096.1	1096.2	1097.3
170°	1109.5	1108.5	1107.5	1106.6	1105.6	1105.2	1105.4	1105.6	1105.8	1106.0	1107.2
172.5°	1116.5	1115.6	1114.8	1114.0	1113.2	1112.8	1112.8	1112.9	1112.9	1112.9	1114.3
175°	1126.0	1125.1	1124.1	1123.2	1122.1	1121.6	1121.4	1121.2	1121.0	1120.8	1122.1
177.5°	1129.2	1128.4	1127.7	1126.9	1126.1	1125.7	1125.7	1125.7	1125.7	1125.7	1126.8
180°	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8



TEST NUMBER: P333106-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5
2.5°	1788.8	1791.6	1794.2	1795.4	1795.2	1794.9	1794.7	1794.5
5°	1776.9	1779.9	1783.0	1784.3	1783.6	1783.0	1782.4	1781.8
7.5°	1753.3	1755.2	1757.2	1757.6	1756.7	1755.8	1754.7	1753.8
10°	1732.0	1733.2	1734.5	1734.5	1733.2	1732.0	1730.8	1729.6
12.5°	1705.7	1706.5	1707.2	1706.7	1705.0	1703.3	1701.6	1699.9
15°	1659.6	1659.0	1658.4	1657.0	1654.8	1652.7	1650.6	1648.5
17.5°	1604.0	1602.3	1600.6	1598.2	1594.9	1591.6	1588.5	1585.2
20°	1565.2	1562.7	1560.3	1557.1	1553.2	1549.2	1545.2	1541.2
22.5°	1522.1	1518.4	1514.8	1511.3	1508.0	1504.8	1501.6	1498.3
25°	1452.4	1447.3	1442.1	1438.0	1434.9	1431.8	1428.7	1425.7
27.5°	1381.6	1375.1	1368.7	1363.3	1358.9	1354.5	1350.1	1345.7
30°	1330.7	1323.1	1315.4	1309.2	1304.2	1299.4	1294.5	1289.6
32.5°	1278.8	1269.9	1261.0	1254.3	1249.7	1245.0	1240.4	1235.7
35°	1201.4	1191.1	1180.7	1172.8	1167.3	1161.7	1156.2	1150.7
37.5°	1118.4	1106.8	1095.3	1086.7	1081.2	1075.6	1070.2	1064.7
40°	1063.2	1050.4	1037.6	1028.4	1022.9	1017.4	1011.9	1006.4
42.5°	1008.8	995.7	982.7	973.3	967.5	961.8	956.1	950.3
45°	925.6	910.6	895.6	885.4	879.9	874.4	868.9	863.4
47.5°	841.7	826.2	810.7	799.9	793.8	787.8	781.7	775.7
50°	786.1	770.9	755.5	745.0	739.3	733.4	727.6	721.8
52.5°	730.6	715.1	699.6	688.8	682.8	676.7	670.6	664.6
55°	648.8	632.9	617.0	606.1	600.4	594.5	588.8	582.9
57.5°	568.9	552.7	536.6	526.3	521.9	517.5	513.1	508.7
60°	515.4	499.6	483.6	473.3	468.4	463.5	458.6	453.7
62.5°	462.9	448.2	433.5	424.2	420.3	416.5	412.5	408.6
65°	387.5	374.4	361.3	352.8	349.2	345.5	341.9	338.2
67.5°	318.4	307.0	295.8	288.1	284.0	280.0	276.0	271.9
70°	271.3	261.2	251.2	244.6	241.5	238.5	235.4	232.4
72.5°	229.1	220.5	211.9	206.2	203.4	200.6	197.8	194.9
75°	168.8	161.8	154.7	150.3	148.5	146.6	144.8	143.0
77.5°	119.4	115.3	111.2	108.9	108.3	107.8	107.3	106.7
80°	91.7	90.7	89.8	89.2	88.9	88.6	88.3	88.0
82.5°	71.3	70.6	69.9	69.4	69.1	68.8	68.5	68.2
85°	41.4	40.8	40.2	39.9	39.9	39.9	39.9	39.9
87.5°	19.2	19.2	19.2	19.4	19.6	20.0	20.3	20.7
90°	21.5	22.6	23.8	24.6	25.0	25.4	25.7	26.2
92.5°	35.9	36.6	37.4	37.8	38.1	38.2	38.5	38.7
95°	67.4	68.0	68.6	68.9	68.9	68.9	68.9	68.9
97.5°	106.2	106.9	107.6	108.0	108.0	108.0	108.0	108.0
100°	134.2	134.6	135.0	135.2	135.2	135.2	135.2	135.2
102.5°	163.8	164.4	165.0	165.3	165.4	165.6	165.7	165.9
105°	208.8	209.3	209.9	210.5	211.1	211.6	212.2	212.8
107.5°	257.4	257.9	258.5	258.6	258.6	258.6	258.6	258.6
110°	289.6	289.3	288.9	289.0	289.6	290.2	290.8	291.4





TEST NUMBER: P333106-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	324.5	324.4	324.3	324.3	324.5	324.6	324.7	324.9
115°	378.2	378.0	377.8	377.5	377.4	377.2	377.0	376.8
117.5°	429.7	429.0	428.4	427.9	427.5	427.1	426.7	426.4
120°	464.7	463.7	462.8	462.4	462.9	463.2	463.6	464.0
122.5°	500.2	499.6	498.9	498.2	497.5	496.8	496.1	495.4
125°	552.2	551.8	551.5	551.0	550.7	550.3	549.9	549.5
127.5°	601.9	601.6	601.2	600.8	600.5	600.2	599.9	599.6
130°	636.8	636.5	636.0	635.5	634.7	634.0	633.2	632.4
132.5°	669.6	669.3	668.8	668.5	668.2	667.9	667.5	667.3
135°	718.8	718.4	718.1	717.6	717.0	716.4	715.8	715.2
137.5°	766.4	765.9	765.3	765.2	765.3	765.4	765.5	765.6
140°	797.7	797.5	797.3	797.1	796.9	796.8	796.5	796.3
142.5°	827.3	827.2	827.2	827.2	827.2	827.2	827.1	827.1
145°	871.8	871.7	871.4	871.1	870.5	869.9	869.4	868.7
147.5°	912.2	912.1	911.9	911.7	911.5	911.4	911.1	910.9
150°	937.6	937.6	937.6	937.5	937.4	937.2	936.9	936.8
152.5°	961.6	962.1	962.5	962.5	962.0	961.5	961.0	960.5
155°	995.1	995.8	996.6	996.6	995.8	995.1	994.3	993.5
157.5°	1024.5	1025.0	1025.6	1025.6	1024.9	1024.2	1023.6	1023.0
160°	1042.6	1043.2	1043.8	1043.5	1042.6	1041.6	1040.7	1039.7
162.5°	1058.9	1059.9	1061.0	1061.0	1060.1	1059.1	1058.1	1057.1
165°	1080.4	1081.6	1082.7	1082.9	1082.1	1081.3	1080.6	1079.8
167.5°	1098.5	1099.7	1100.9	1100.9	1099.7	1098.5	1097.3	1096.1
170°	1108.3	1109.5	1110.6	1110.5	1109.2	1107.8	1106.5	1105.1
172.5°	1115.6	1116.9	1118.3	1118.2	1116.9	1115.5	1114.1	1112.8
175°	1123.5	1124.9	1126.3	1126.3	1124.9	1123.5	1122.1	1120.8
177.5°	1127.9	1128.9	1130.1	1130.0	1128.7	1127.5	1126.3	1125.0
180°	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8

(END OF REPORT)