

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333058-940

Luminaire Tested: **S124RDIW-S795D470U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333058-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S795D470U940-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4313.0 lumens
Efficiency: N/A
Efficacy: 114.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333058-940

CATALOG NUMBER: S124RDIW-S795D470U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333058-940

CATALOG NUMBER: S124RDIW-S795D470U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	92	92	92	81	81	81	71	71	71	66
1	102	98	94	90	96	92	89	86	82	79	77	72	70	69	64	62	61	57
2	93	86	79	74	87	81	75	71	72	68	64	64	61	58	56	54	52	48
3	85	76	68	62	80	72	65	60	64	59	54	57	53	49	50	47	44	41
4	78	67	59	53	73	64	56	51	57	51	47	51	46	43	45	42	39	35
5	72	60	52	46	67	57	50	44	51	45	41	46	41	37	41	37	34	31
6	66	54	46	40	62	51	44	39	46	40	36	42	37	33	37	33	30	27
7	61	49	41	35	58	47	39	34	42	36	32	38	33	29	34	30	27	24
8	57	45	37	31	54	43	35	30	39	33	28	35	30	26	31	27	24	22
9	53	41	33	28	50	39	32	27	36	30	25	32	27	24	29	25	22	20
10	50	38	30	26	47	36	29	25	33	27	23	30	25	22	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10001	10001	10001
5°	10023	9900	9961
10°	9960	9781	9781
15°	9845	9576	9504
20°	9688	9306	9135
25°	9487	8989	8761
30°	9292	8655	8294
35°	9077	8310	7824
40°	8816	7917	7317
45°	8576	7526	6801
50°	8303	7076	6253
55°	8010	6608	5661
60°	7689	6095	5054
65°	7393	5454	4458
70°	6963	4747	3784
75°	6419	3936	3075
80°	5602	2999	2822
85°	4742	2723	2547



TEST NUMBER: P333058-940

CATALOG NUMBER: S124RDIW-S795D470U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.4	2.7
10°-20°	324.5	7.5
20°-30°	468.6	10.9
30°-40°	531.1	12.3
40°-50°	512.9	11.9
50°-60°	426.5	9.9
60°-70°	294.5	6.8
70°-80°	149.3	3.5
80°-90°	39.9	0.9
90°-100°	34.5	0.8
100°-110°	102.1	2.4
110°-120°	173.3	4.0
120°-130°	228.5	5.3
130°-140°	256.6	5.9
140°-150°	252.1	5.8
150°-160°	212.1	4.9
160°-170°	141.1	3.3
170°-180°	49.4	1.1
0°-30°	909.4	21.1
0°-40°	1440.5	33.4
0°-60°	2379.9	55.2
0°-90°	2863.5	66.4
90°-120°	309.8	7.2
90°-150°	1047.0	24.3
90°-180°	1450.0	33.6
0°-180°	4313.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1239	1239	1239	1239	1239	
5°	1237	1233	1222	1230	1229	117
15°	1178	1169	1146	1144	1137	332
25°	1065	1047	1009	993	984	491
35°	921	890	843	812	794	575
45°	751	715	659	614	596	579
55°	569	530	470	422	402	509
65°	387	345	286	246	233	382
75°	206	170	126	105	99	217
85°	51	33	29	28	28	58
90°	1	6	9	11	12	4
95°	24	28	31	32	32	27
105°	94	95	96	97	99	100
115°	176	176	175	175	175	174
125°	256	256	256	255	255	229
135°	331	333	333	332	331	256
145°	402	404	404	404	402	252
155°	461	461	460	462	460	212
165°	501	500	499	502	500	141
175°	522	520	519	522	519	49
180°	522	522	522	522	522	



TEST NUMBER: P333058-940

CATALOG NUMBER: S124RDIW-S795D470U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8
2.5°	1241.8	1241.1	1240.4	1239.7	1239.0	1237.8	1235.9	1234.1	1232.3	1230.4	1232.3
5°	1236.8	1236.0	1235.1	1234.3	1233.4	1231.8	1229.2	1226.7	1224.1	1221.6	1223.8
7.5°	1225.7	1224.8	1223.9	1223.0	1222.1	1220.0	1216.7	1213.4	1210.1	1206.8	1208.2
10°	1215.0	1214.0	1212.9	1211.8	1210.8	1208.4	1204.6	1200.8	1197.0	1193.2	1194.0
12.5°	1201.3	1200.2	1198.9	1197.7	1196.5	1193.6	1189.2	1184.6	1180.2	1175.7	1176.3
15°	1178.0	1176.2	1174.2	1172.3	1170.5	1166.9	1161.5	1156.3	1151.0	1145.8	1145.3
17.5°	1149.8	1147.0	1144.2	1141.6	1138.8	1134.3	1127.9	1121.6	1115.3	1108.9	1107.8
20°	1127.7	1125.0	1122.3	1119.5	1116.8	1111.9	1104.7	1097.5	1090.3	1083.2	1081.5
22.5°	1103.5	1100.4	1097.3	1094.2	1091.2	1085.7	1078.1	1070.4	1062.7	1055.1	1052.6
25°	1065.1	1061.3	1057.6	1053.7	1050.0	1043.7	1035.1	1026.4	1017.8	1009.1	1005.6
27.5°	1024.9	1020.2	1015.4	1010.7	1005.8	998.9	989.6	980.4	971.2	962.0	957.5
30°	996.8	991.6	986.3	981.1	975.8	968.2	958.3	948.4	938.4	928.5	923.3
32.5°	967.2	961.4	955.4	949.4	943.5	935.4	925.1	914.9	904.6	894.4	888.3
35°	921.0	914.3	907.5	900.7	894.0	885.4	874.9	864.2	853.7	843.2	836.1
37.5°	871.5	864.5	857.6	850.6	843.6	834.4	822.7	811.0	799.3	787.6	779.6
40°	836.6	829.6	822.7	815.7	808.8	799.2	787.2	775.3	763.2	751.2	742.3
42.5°	803.2	795.9	788.6	781.3	774.0	764.1	751.6	739.0	726.6	714.0	705.0
45°	751.2	743.4	735.6	727.8	720.0	709.8	697.1	684.5	671.8	659.2	648.9
47.5°	697.5	689.5	681.4	673.3	665.3	654.7	641.6	628.4	615.3	602.1	591.4
50°	661.1	652.9	644.6	636.4	628.2	617.3	603.9	590.4	576.8	563.4	552.9
52.5°	623.9	615.9	607.8	599.8	591.7	580.8	566.9	553.1	539.3	525.5	514.8
55°	569.1	560.6	552.2	543.8	535.4	524.3	510.6	496.9	483.2	469.5	458.5
57.5°	514.9	506.0	497.3	488.6	479.7	468.6	455.1	441.7	428.2	414.6	403.6
60°	476.2	467.7	459.3	450.8	442.4	431.5	417.9	404.5	391.0	377.5	366.5
62.5°	441.2	432.5	423.7	414.9	406.2	394.8	381.0	367.2	353.4	339.6	329.4
65°	387.0	377.9	368.8	359.8	350.7	339.5	325.9	312.5	299.0	285.5	276.4
67.5°	330.6	322.0	313.3	304.6	295.9	285.3	272.8	260.3	247.7	235.2	227.4
70°	295.0	286.1	277.2	268.4	259.6	249.1	237.1	225.1	213.1	201.1	194.1
72.5°	257.1	249.1	241.0	233.0	225.0	215.3	204.0	192.6	181.3	170.0	164.0
75°	205.8	198.0	190.2	182.4	174.6	165.8	155.9	146.0	136.1	126.2	121.3
77.5°	153.8	147.2	140.6	134.0	127.3	120.0	112.1	104.1	96.0	88.0	85.2
80°	120.5	114.3	108.3	102.1	96.0	89.8	83.5	77.1	70.8	64.5	63.8
82.5°	91.7	86.1	80.4	74.8	69.2	64.6	61.0	57.3	53.7	50.1	49.6
85°	51.2	47.0	42.8	38.6	34.3	31.9	31.3	30.7	30.1	29.4	29.0
87.5°	17.7	16.6	15.4	14.3	13.1	12.5	12.5	12.5	12.4	12.4	12.3
90°	1.2	2.2	3.2	4.2	5.2	6.0	6.8	7.5	8.2	8.9	9.5
92.5°	8.6	9.8	10.9	12.0	13.2	14.0	14.5	15.0	15.5	16.0	16.3
95°	24.3	25.1	25.9	26.7	27.5	28.2	28.8	29.4	30.1	30.7	30.9
97.5°	42.4	43.0	43.6	44.3	44.9	45.7	46.4	47.1	47.8	48.6	48.9
100°	56.5	56.9	57.2	57.6	58.1	58.6	59.4	60.2	61.0	61.8	62.0
102.5°	71.4	71.6	71.7	71.9	72.1	72.5	73.2	73.9	74.6	75.4	75.6
105°	94.2	94.3	94.3	94.4	94.5	94.7	95.1	95.4	95.8	96.1	96.4
107.5°	118.0	118.1	118.2	118.3	118.4	118.5	118.6	118.6	118.7	118.7	119.0
110°	134.1	134.3	134.5	134.6	134.8	134.9	134.8	134.7	134.6	134.6	134.4



TEST NUMBER: P333058-940

CATALOG NUMBER: S124RDIW-S795D470U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	151.0	151.0	151.1	151.1	151.1	151.1	150.9	150.7	150.5	150.4	150.3
115°	176.2	176.2	176.2	176.2	176.2	176.1	175.9	175.8	175.6	175.4	175.3
117.5°	199.9	200.0	200.1	200.2	200.2	200.2	200.1	199.9	199.8	199.7	199.4
120°	215.8	216.2	216.5	216.9	217.2	217.2	217.0	216.7	216.4	216.2	215.7
122.5°	232.3	232.4	232.6	232.6	232.8	232.8	232.7	232.6	232.5	232.4	232.0
125°	256.5	256.5	256.5	256.5	256.5	256.5	256.5	256.4	256.3	256.2	256.0
127.5°	278.7	278.9	279.2	279.5	279.7	279.8	279.6	279.5	279.4	279.2	279.0
130°	294.2	294.4	294.7	295.0	295.2	295.3	295.3	295.3	295.3	295.3	295.2
132.5°	310.0	310.2	310.4	310.6	310.8	310.9	310.8	310.7	310.7	310.6	310.4
135°	330.9	331.4	332.0	332.5	333.1	333.3	333.3	333.3	333.3	333.3	333.1
137.5°	353.7	354.0	354.2	354.5	354.7	354.9	355.1	355.3	355.3	355.5	355.3
140°	368.9	369.1	369.3	369.4	369.6	369.7	369.7	369.7	369.7	369.7	369.6
142.5°	382.8	383.0	383.2	383.3	383.5	383.6	383.5	383.4	383.3	383.3	383.3
145°	402.1	402.4	402.8	403.1	403.5	403.7	403.8	403.9	403.9	404.0	403.9
147.5°	421.2	421.5	422.0	422.4	422.8	423.0	422.9	422.8	422.8	422.8	422.7
150°	432.7	433.1	433.5	433.8	434.2	434.4	434.4	434.4	434.4	434.4	434.4
152.5°	443.7	444.0	444.2	444.4	444.6	444.8	444.8	444.9	445.0	445.1	445.2
155°	460.7	460.7	460.7	460.7	460.7	460.6	460.5	460.4	460.3	460.2	460.6
157.5°	474.8	474.7	474.6	474.4	474.2	474.1	474.1	474.1	474.0	474.0	474.3
160°	483.3	483.2	483.1	483.0	483.0	482.9	482.8	482.7	482.6	482.5	482.8
162.5°	491.1	490.8	490.5	490.4	490.1	489.9	489.8	489.7	489.6	489.5	490.1
165°	501.4	501.1	500.9	500.6	500.3	500.2	500.0	499.8	499.6	499.4	500.0
167.5°	509.4	509.1	508.7	508.4	507.9	507.7	507.7	507.8	507.8	507.8	508.4
170°	514.0	513.5	513.1	512.6	512.2	512.0	512.1	512.2	512.3	512.4	512.9
172.5°	517.2	516.8	516.5	516.1	515.7	515.5	515.5	515.6	515.6	515.6	516.2
175°	521.7	521.2	520.8	520.3	519.9	519.6	519.5	519.4	519.3	519.2	519.9
177.5°	523.1	522.7	522.4	522.0	521.7	521.5	521.5	521.5	521.5	521.5	522.0
180°	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5



TEST NUMBER: P333058-940

CATALOG NUMBER: S124RDIW-S795D470U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8
2.5°	1234.1	1235.9	1237.8	1238.7	1238.5	1238.3	1238.1	1238.0
5°	1225.8	1228.0	1230.1	1230.9	1230.5	1230.1	1229.7	1229.2
7.5°	1209.5	1210.9	1212.3	1212.5	1211.9	1211.2	1210.6	1209.9
10°	1194.9	1195.7	1196.6	1196.6	1195.7	1194.9	1194.0	1193.2
12.5°	1176.8	1177.2	1177.8	1177.4	1176.3	1175.1	1173.8	1172.7
15°	1145.0	1144.5	1144.1	1143.2	1141.7	1140.1	1138.7	1137.2
17.5°	1106.6	1105.5	1104.2	1102.5	1100.3	1098.1	1095.8	1093.6
20°	1079.8	1078.1	1076.4	1074.2	1071.5	1068.7	1066.0	1063.3
22.5°	1050.1	1047.5	1045.0	1042.6	1040.4	1038.1	1035.9	1033.7
25°	1002.0	998.4	994.9	992.0	989.9	987.8	985.7	983.6
27.5°	953.1	948.7	944.2	940.5	937.5	934.4	931.4	928.4
30°	918.0	912.8	907.5	903.1	899.8	896.4	893.0	889.7
32.5°	882.2	876.1	870.0	865.3	862.1	858.9	855.7	852.5
35°	828.8	821.7	814.6	809.0	805.3	801.5	797.6	793.9
37.5°	771.6	763.6	755.5	749.7	745.9	742.1	738.3	734.5
40°	733.5	724.6	715.8	709.4	705.7	701.9	698.1	694.3
42.5°	696.0	687.0	678.0	671.5	667.4	663.5	659.6	655.6
45°	638.6	628.2	617.9	610.8	607.0	603.2	599.4	595.7
47.5°	580.7	570.0	559.3	551.8	547.7	543.5	539.3	535.1
50°	542.3	531.8	521.2	514.0	510.0	506.0	501.9	497.9
52.5°	504.1	493.4	482.6	475.2	471.0	466.8	462.7	458.5
55°	447.5	436.6	425.7	418.2	414.2	410.2	406.2	402.2
57.5°	392.4	381.3	370.1	363.1	360.1	357.0	354.0	351.0
60°	355.6	344.6	333.7	326.5	323.2	319.8	316.4	313.0
62.5°	319.3	309.2	299.1	292.7	290.0	287.3	284.5	281.9
65°	267.3	258.3	249.2	243.4	240.9	238.4	235.9	233.4
67.5°	219.6	211.9	204.0	198.8	196.0	193.1	190.4	187.6
70°	187.2	180.2	173.3	168.7	166.7	164.5	162.4	160.3
72.5°	158.1	152.1	146.2	142.2	140.4	138.4	136.4	134.5
75°	116.5	111.6	106.7	103.7	102.5	101.2	99.9	98.6
77.5°	82.4	79.5	76.7	75.1	74.7	74.4	74.0	73.6
80°	63.2	62.6	62.0	61.5	61.3	61.1	60.9	60.7
82.5°	49.1	48.7	48.2	47.9	47.7	47.4	47.3	47.1
85°	28.5	28.2	27.7	27.5	27.5	27.5	27.5	27.5
87.5°	12.3	12.2	12.1	12.2	12.4	12.7	12.8	13.0
90°	10.0	10.5	11.1	11.4	11.6	11.8	11.9	12.1
92.5°	16.7	16.9	17.3	17.5	17.7	17.7	17.8	17.9
95°	31.2	31.5	31.7	31.9	31.9	31.9	31.9	31.9
97.5°	49.2	49.6	49.8	50.0	50.0	50.0	50.0	50.0
100°	62.2	62.3	62.5	62.6	62.6	62.6	62.6	62.6
102.5°	75.9	76.2	76.4	76.6	76.6	76.7	76.8	76.9
105°	96.8	97.0	97.3	97.6	97.8	98.1	98.4	98.6
107.5°	119.2	119.5	119.8	119.8	119.8	119.8	119.8	119.8
110°	134.2	134.0	133.8	133.8	134.1	134.4	134.6	134.9



TEST NUMBER: P333058-940

CATALOG NUMBER: S124RDIW-S795D470U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	150.3	150.3	150.3	150.3	150.3	150.3	150.4	150.4
115°	175.2	175.1	175.0	175.0	174.9	174.8	174.7	174.6
117.5°	199.1	198.8	198.5	198.2	198.0	197.9	197.7	197.5
120°	215.3	214.8	214.4	214.3	214.5	214.6	214.8	215.0
122.5°	231.8	231.4	231.1	230.8	230.5	230.2	229.8	229.5
125°	255.8	255.7	255.5	255.3	255.1	254.9	254.8	254.6
127.5°	278.8	278.7	278.5	278.3	278.2	278.0	277.9	277.8
130°	295.0	294.8	294.6	294.4	294.0	293.6	293.3	292.9
132.5°	310.2	310.0	309.9	309.7	309.5	309.4	309.2	309.2
135°	333.0	332.8	332.6	332.4	332.2	331.9	331.6	331.4
137.5°	355.0	354.8	354.5	354.5	354.5	354.5	354.6	354.7
140°	369.5	369.4	369.3	369.3	369.2	369.1	369.0	368.9
142.5°	383.3	383.3	383.3	383.2	383.2	383.2	383.2	383.2
145°	403.9	403.8	403.7	403.5	403.2	403.0	402.7	402.4
147.5°	422.6	422.5	422.5	422.4	422.3	422.2	422.1	422.0
150°	434.4	434.4	434.4	434.4	434.3	434.2	434.1	434.0
152.5°	445.5	445.7	445.9	445.9	445.7	445.4	445.2	445.0
155°	460.9	461.3	461.6	461.6	461.3	460.9	460.6	460.2
157.5°	474.6	474.8	475.1	475.1	474.8	474.5	474.2	473.9
160°	483.0	483.3	483.6	483.5	483.0	482.6	482.1	481.6
162.5°	490.5	491.1	491.5	491.5	491.1	490.6	490.2	489.7
165°	500.5	501.1	501.6	501.7	501.3	501.0	500.6	500.2
167.5°	508.9	509.4	510.0	510.0	509.4	508.9	508.3	507.7
170°	513.4	514.0	514.5	514.4	513.8	513.2	512.6	511.9
172.5°	516.8	517.5	518.0	518.0	517.4	516.7	516.1	515.5
175°	520.5	521.1	521.7	521.7	521.1	520.5	519.9	519.2
177.5°	522.5	523.0	523.5	523.4	522.9	522.4	521.7	521.2
180°	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5

(END OF REPORT)