

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333107-935

Luminaire Tested: **S124RDIW-S1195D1340U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333107-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S1195D1340U935-4F0-1E-UDD-A  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1340 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8935.9 lumens  
Efficiency: N/A  
Efficacy: 117.3 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 76.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333107-935

CATALOG NUMBER: S124RDIW-S1195D1340U935-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333107-935

CATALOG NUMBER: S124RDIW-S1195D1340U935-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55	48
1	98	94	90	87	90	86	83	80	73	71	69	60	59	57	49	48	47	42
2	89	82	76	71	82	76	71	67	64	61	57	54	51	49	44	42	40	36
3	82	73	66	60	75	67	61	56	57	53	49	48	44	42	39	37	35	31
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	35	32	30	27
5	69	58	50	44	63	54	47	41	46	40	36	39	35	31	32	29	27	23
6	64	52	44	38	59	48	41	36	41	36	32	35	31	28	29	26	24	21
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	17
9	51	39	32	27	47	36	30	25	32	26	23	27	23	20	23	19	17	15
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	13774	13774	13774	13774
5°	15977	13816	12211	13816
10°	18901	13755	10899	13755
15°	21833	13628	9365	13628
20°	24308	13454	8469	13454
25°	25093	13281	7863	13281
30°	21967	13073	7498	13073
35°	17100	12764	7276	12764
40°	12823	12410	7158	12410
45°	10123	11843	7096	11843
50°	8547	11189	6889	11189
55°	7450	10469	6521	10469
60°	6704	9723	5772	9723
65°	5910	8915	4963	8915
70°	5323	8080	4480	8080
75°	4460	7162	3815	7162
80°	3770	6104	3580	6104
85°	3186	4780	3186	4780



TEST NUMBER: P333107-935

CATALOG NUMBER: S124RDIW-S1195D1340U935-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	165.3	1.9
10°-20°	498.7	5.6
20°-30°	780.0	8.7
30°-40°	867.1	9.7
40°-50°	769.3	8.6
50°-60°	599.5	6.7
60°-70°	392.5	4.4
70°-80°	193.0	2.2
80°-90°	51.9	0.6
90°-100°	51.1	0.6
100°-110°	325.6	3.6
110°-120°	622.9	7.0
120°-130°	790.7	8.8
130°-140°	846.0	9.5
140°-150°	791.1	8.9
150°-160°	638.0	7.1
160°-170°	411.5	4.6
170°-180°	141.8	1.6
0°-30°	1444.0	16.2
0°-40°	2311.0	25.9
0°-60°	3679.8	41.2
0°-90°	4317.2	48.3
90°-120°	999.5	11.2
90°-150°	3427.4	38.4
90°-180°	4619.0	51.7
0°-180°	8935.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1706	1706	1706	1706	1706	
5°	1972	1705	1507	1705	1972	199
15°	2612	1631	1120	1631	2612	743
25°	2817	1491	883	1491	2817	1250
35°	1735	1295	738	1295	1735	1088
45°	887	1037	622	1037	887	702
55°	529	744	463	744	529	481
65°	309	467	260	467	309	311
75°	143	230	122	230	143	157
85°	34	52	34	52	34	40
90°	34	3	34	3	34	16
95°	32	61	32	61	32	26
105°	318	336	318	336	318	278
115°	632	628	632	628	632	626
125°	889	882	889	882	889	792
135°	1102	1094	1102	1094	1102	848
145°	1269	1262	1269	1262	1269	793
155°	1383	1384	1383	1384	1383	638
165°	1453	1460	1453	1460	1453	410
175°	1484	1493	1484	1493	1484	141
180°	1493	1493	1493	1493	1493	



TEST NUMBER: P333107-935

CATALOG NUMBER: S124RDIW-S1195D1340U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2
2.5°	1799.7	1804.7	1799.7	1799.1	1793.6	1792.0	1789.8	1782.6	1769.4	1761.8	1763.4
5°	1971.5	1988.7	1979.1	1977.7	1962.6	1947.5	1937.9	1915.9	1892.5	1876.7	1863.6
7.5°	2170.3	2180.2	2174.2	2164.6	2140.1	2126.2	2103.9	2074.9	2033.0	2001.0	1971.7
10°	2305.7	2313.9	2311.2	2293.3	2275.4	2238.9	2218.4	2177.8	2124.9	2082.9	2043.8
12.5°	2438.7	2447.6	2423.4	2424.1	2390.3	2361.6	2328.9	2277.9	2216.7	2162.7	2113.6
15°	2612.3	2601.3	2601.3	2587.5	2549.7	2509.8	2476.1	2422.5	2345.5	2280.9	2212.9
17.5°	2748.1	2751.9	2746.2	2713.9	2684.2	2642.9	2581.2	2518.6	2447.1	2360.3	2290.8
20°	2829.5	2829.5	2823.3	2801.3	2762.8	2718.8	2652.1	2584.0	2493.3	2406.0	2327.6
22.5°	2862.5	2864.6	2857.4	2839.2	2804.6	2761.7	2704.9	2635.8	2542.3	2443.9	2346.9
25°	2817.1	2830.2	2831.5	2826.7	2816.4	2790.2	2741.5	2670.6	2586.8	2480.3	2375.8
27.5°	2586.4	2602.9	2617.4	2641.1	2672.7	2689.2	2691.4	2655.4	2582.2	2479.7	2374.6
30°	2356.5	2370.2	2414.9	2473.4	2518.8	2560.0	2595.7	2605.4	2564.1	2472.0	2361.3
32.5°	2101.4	2120.0	2164.7	2227.6	2303.2	2373.0	2453.3	2494.2	2493.2	2437.9	2335.5
35°	1735.1	1748.9	1790.1	1856.1	1946.8	2050.6	2177.8	2276.7	2344.2	2339.3	2276.7
37.5°	1399.3	1414.9	1456.6	1511.2	1599.2	1727.8	1850.8	1987.2	2111.8	2181.8	2160.9
40°	1216.8	1217.5	1258.0	1314.4	1396.9	1508.9	1643.0	1794.2	1933.0	2046.5	2068.5
42.5°	1072.6	1072.8	1099.6	1160.4	1219.8	1325.3	1453.2	1603.4	1765.9	1896.9	1955.2
45°	886.7	892.9	915.0	951.4	998.2	1087.5	1189.9	1329.5	1511.7	1667.0	1763.9
47.5°	751.0	760.0	774.0	803.7	841.0	900.5	985.2	1110.6	1258.8	1429.7	1567.6
50°	680.5	681.9	699.8	716.3	748.6	796.1	870.3	974.7	1110.9	1275.1	1428.5
52.5°	620.1	619.7	630.5	651.4	677.7	714.6	774.6	869.7	990.4	1137.7	1296.0
55°	529.3	532.8	541.0	557.5	577.5	603.6	651.0	722.5	817.3	943.1	1086.8
57.5°	460.3	462.1	468.6	475.5	493.9	512.8	548.5	598.1	678.1	781.1	915.0
60°	415.2	415.9	417.9	428.3	442.7	460.5	484.7	526.6	593.9	688.1	794.0
62.5°	371.2	372.5	375.7	383.1	394.3	406.7	431.9	465.5	521.3	601.8	697.2
65°	309.4	310.0	314.9	317.6	326.5	337.5	356.1	378.8	417.2	484.7	556.8
67.5°	258.5	258.5	258.7	262.4	268.6	276.0	287.1	305.2	334.2	375.7	439.3
70°	225.5	225.5	226.9	228.9	232.4	238.5	244.7	258.5	279.8	313.5	362.3
72.5°	194.7	195.2	196.6	197.0	198.8	203.9	208.4	217.2	233.1	258.5	297.9
75°	143.0	145.1	148.5	151.3	154.6	153.9	158.8	164.3	169.1	184.3	206.9
77.5°	106.4	105.3	105.7	108.1	108.5	109.2	112.6	116.8	120.5	127.6	135.7
80°	81.1	81.1	83.2	83.9	83.2	83.9	87.3	89.4	90.7	93.5	101.1
82.5°	61.3	62.4	61.7	62.4	62.9	63.5	66.4	66.8	68.2	69.3	72.5
85°	34.4	35.0	35.7	34.4	34.4	34.4	35.7	36.4	37.8	37.1	38.5
87.5°	18.8	18.2	18.6	18.5	18.9	18.2	18.4	19.3	17.8	18.1	17.7
90°	33.5	33.0	32.5	32.0	31.5	30.6	29.0	27.6	26.1	24.5	22.6
92.5°	30.8	30.7	30.7	30.6	30.4	29.6	28.2	26.7	25.1	23.7	21.7
95°	32.4	32.1	31.9	31.6	31.4	30.6	29.0	27.6	26.1	24.5	24.3
97.5°	31.3	31.0	30.7	30.6	30.3	30.0	30.0	29.8	29.6	29.4	57.2
100°	31.3	31.0	30.7	30.6	30.3	32.3	36.5	40.7	44.9	49.2	83.3
102.5°	32.2	32.1	32.0	32.0	31.9	54.7	100.2	145.8	191.2	236.8	241.3
105°	318.3	327.2	336.1	345.1	354.0	357.4	355.2	352.9	350.7	348.4	347.2
107.5°	443.6	442.6	441.7	440.7	439.8	438.8	437.7	436.6	435.5	434.5	432.7
110°	498.1	497.3	496.6	495.8	495.1	494.5	494.0	493.5	493.0	492.5	491.0



TEST NUMBER: P333107-935

CATALOG NUMBER: S124RDIW-S1195D1340U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	552.6	551.6	550.7	549.7	548.8	548.4	548.5	548.5	548.7	548.8	548.1
115°	632.1	632.1	632.1	632.1	632.1	631.8	631.4	630.9	630.3	629.8	630.1
117.5°	712.9	713.1	713.2	713.3	713.3	713.4	713.5	713.6	713.8	713.9	713.3
120°	763.9	764.4	764.8	765.3	765.9	765.9	765.3	764.8	764.4	763.9	764.1
122.5°	813.9	814.4	814.9	815.4	815.9	816.0	815.7	815.4	815.1	814.8	814.4
125°	889.0	888.7	888.5	888.2	887.9	887.4	886.7	886.0	885.2	884.5	884.9
127.5°	954.8	955.0	955.2	955.5	955.6	955.8	956.0	956.1	956.2	956.4	955.3
130°	999.5	999.5	999.5	999.5	999.5	999.4	999.1	998.8	998.7	998.4	997.6
132.5°	1040.6	1040.8	1041.0	1041.2	1041.4	1041.4	1041.1	1040.9	1040.6	1040.3	1039.4
135°	1102.3	1101.7	1101.2	1100.8	1100.3	1099.8	1099.2	1098.8	1098.3	1097.8	1096.8
137.5°	1154.9	1155.1	1155.3	1155.4	1155.5	1155.4	1154.8	1154.3	1153.7	1153.1	1152.1
140°	1191.6	1191.4	1191.1	1190.8	1190.6	1190.1	1189.4	1188.6	1187.8	1187.1	1186.6
142.5°	1221.9	1221.9	1221.8	1221.8	1221.8	1221.5	1220.9	1220.4	1219.9	1219.3	1219.0
145°	1268.7	1268.2	1267.7	1267.1	1266.7	1266.3	1266.0	1265.8	1265.6	1265.3	1265.3
147.5°	1307.3	1307.0	1306.8	1306.6	1306.3	1306.1	1305.9	1305.7	1305.4	1305.3	1305.5
150°	1332.3	1332.1	1331.8	1331.5	1331.3	1331.2	1331.2	1331.2	1331.2	1331.2	1331.5
152.5°	1353.8	1353.9	1354.0	1354.2	1354.4	1354.2	1353.8	1353.4	1353.1	1352.6	1353.1
155°	1382.6	1383.3	1384.1	1384.8	1385.5	1385.4	1384.4	1383.5	1382.4	1381.5	1382.2
157.5°	1406.7	1408.0	1409.3	1410.6	1411.9	1411.9	1410.6	1409.3	1408.0	1406.7	1407.6
160°	1422.8	1424.3	1425.7	1427.2	1428.7	1428.7	1427.2	1425.7	1424.3	1422.8	1423.0
162.5°	1435.3	1436.9	1438.6	1440.4	1442.0	1442.1	1440.6	1439.2	1437.6	1436.1	1436.4
165°	1452.9	1455.2	1457.4	1459.7	1461.8	1462.0	1460.0	1458.0	1456.0	1454.1	1454.1
167.5°	1466.1	1468.6	1471.0	1473.5	1476.0	1476.2	1473.9	1471.8	1469.6	1467.4	1467.6
170°	1474.1	1476.6	1479.1	1481.6	1484.0	1484.3	1482.3	1480.3	1478.3	1476.4	1476.1
172.5°	1478.6	1481.3	1483.9	1486.6	1489.4	1489.7	1487.7	1485.7	1483.7	1481.7	1481.4
175°	1484.2	1487.1	1490.1	1493.1	1496.1	1496.5	1494.3	1492.0	1489.8	1487.5	1487.3
177.5°	1487.7	1490.1	1492.5	1494.9	1497.3	1497.7	1496.1	1494.5	1492.9	1491.3	1490.9
180°	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1



TEST NUMBER: P333107-935

CATALOG NUMBER: S124RDIW-S1195D1340U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2
2.5°	1757.9	1750.2	1746.4	1737.6	1727.1	1721.6	1716.7	1709.5	1700.1	1690.2	1683.1
5°	1847.1	1830.7	1810.0	1785.3	1763.2	1742.0	1723.4	1704.9	1683.5	1661.6	1639.5
7.5°	1938.7	1906.3	1871.2	1830.7	1791.1	1755.3	1722.3	1690.7	1654.9	1622.9	1593.7
10°	2002.5	1958.5	1909.7	1858.1	1806.6	1761.9	1717.9	1678.0	1634.0	1594.8	1561.9
12.5°	2054.2	2002.5	1943.8	1879.6	1817.6	1763.5	1713.0	1661.0	1610.9	1568.5	1524.5
15°	2139.9	2069.2	1990.1	1913.1	1832.7	1759.1	1691.1	1630.6	1573.6	1513.7	1471.8
17.5°	2199.0	2115.0	2018.9	1926.3	1831.3	1744.6	1666.0	1594.1	1528.2	1467.1	1417.2
20°	2234.1	2141.3	2034.8	1929.6	1823.1	1730.3	1645.7	1566.0	1497.9	1431.9	1380.4
22.5°	2253.9	2151.2	2034.8	1924.7	1814.3	1713.7	1620.9	1537.9	1463.8	1397.8	1340.7
25°	2260.3	2150.3	2031.4	1904.9	1783.9	1677.3	1581.1	1491.0	1408.5	1342.6	1282.0
27.5°	2251.5	2121.9	2000.2	1870.4	1745.5	1633.2	1532.1	1437.5	1355.0	1284.1	1222.1
30°	2238.3	2099.4	1968.8	1834.1	1707.5	1599.7	1493.1	1402.4	1316.5	1242.9	1180.3
32.5°	2209.7	2071.9	1931.4	1793.4	1665.3	1554.0	1452.9	1361.7	1277.4	1202.2	1135.7
35°	2153.0	2013.4	1860.9	1719.2	1593.5	1478.0	1383.1	1295.1	1214.7	1134.3	1064.1
37.5°	2078.4	1935.8	1784.0	1628.9	1503.0	1394.0	1306.9	1224.3	1145.8	1072.4	994.7
40°	2008.0	1878.1	1721.3	1567.4	1438.1	1332.9	1252.5	1177.6	1098.5	1025.6	948.0
42.5°	1922.8	1812.1	1653.7	1499.2	1371.6	1270.2	1195.3	1122.1	1050.2	979.5	898.5
45°	1780.5	1696.6	1548.1	1399.6	1271.1	1170.7	1102.0	1037.3	974.0	906.7	830.4
47.5°	1617.4	1560.6	1432.4	1280.4	1161.5	1071.2	1004.8	951.9	898.5	831.1	764.1
50°	1504.1	1467.7	1343.9	1205.1	1091.7	1008.5	940.4	890.9	846.2	781.6	721.8
52.5°	1383.1	1363.7	1259.2	1126.4	1016.8	935.3	877.2	832.6	787.4	733.7	677.8
55°	1198.9	1209.2	1120.5	1005.7	902.6	833.9	780.9	743.8	705.3	660.0	616.6
57.5°	1010.6	1048.2	988.7	887.9	791.3	727.7	687.9	656.6	624.3	586.7	549.7
60°	897.8	929.4	895.7	807.0	722.5	663.4	626.3	602.2	569.9	535.5	507.3
62.5°	787.8	821.7	801.7	730.0	651.5	600.7	567.9	545.5	521.5	491.5	462.3
65°	649.6	671.6	662.0	612.5	556.8	513.5	483.3	466.7	444.8	422.8	396.7
67.5°	497.6	540.0	534.4	508.2	460.0	426.2	406.4	391.8	371.8	355.4	337.7
70°	409.1	448.2	447.5	426.2	400.1	368.4	354.7	342.3	324.4	308.7	294.2
72.5°	334.8	370.7	376.0	359.6	341.8	317.9	304.7	296.2	278.8	267.9	256.2
75°	234.5	260.5	267.4	267.4	259.2	246.8	235.1	229.6	217.2	207.6	200.7
77.5°	153.7	170.2	180.9	183.4	184.7	180.6	170.9	167.0	157.6	154.1	147.5
80°	108.6	119.6	132.0	136.1	139.6	138.2	134.1	131.3	122.3	118.9	116.1
82.5°	75.1	81.1	91.3	100.4	99.4	103.0	99.4	97.2	90.5	89.2	86.4
85°	39.2	39.9	41.2	47.4	50.9	52.3	53.0	51.6	49.5	49.5	44.7
87.5°	17.3	16.4	17.0	16.6	16.6	18.3	19.4	19.4	18.3	17.1	16.0
90°	20.6	18.6	16.6	14.3	11.5	8.8	6.1	3.4	6.1	8.8	11.5
92.5°	19.7	17.7	15.8	14.6	14.6	14.4	14.2	14.0	14.2	14.4	14.6
95°	24.1	23.8	23.6	27.6	36.1	44.5	53.0	61.4	53.0	44.5	36.1
97.5°	84.9	112.5	140.3	151.4	146.2	140.9	135.7	130.4	135.7	140.9	146.2
100°	117.6	151.9	186.1	201.0	196.6	192.1	187.6	183.1	187.6	192.1	196.6
102.5°	245.7	250.1	254.6	255.2	251.9	248.7	245.4	242.1	245.4	248.7	251.9
105°	345.9	344.7	343.5	342.1	340.6	339.1	337.6	336.1	337.6	339.1	340.6
107.5°	431.0	429.4	427.7	426.5	425.7	425.0	424.2	423.4	424.2	425.0	425.7
110°	489.5	488.0	486.6	485.4	484.7	484.0	483.2	482.4	483.2	484.0	484.7





TEST NUMBER: P333107-935

CATALOG NUMBER: S124RDIW-S1195D1340U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	547.4	546.7	546.0	545.0	543.6	542.3	541.0	539.6	541.0	542.3	543.6
115°	630.3	630.6	630.9	630.6	629.8	629.1	628.4	627.6	628.4	629.1	629.8
117.5°	712.7	712.2	711.6	710.8	709.9	708.9	707.9	706.9	707.9	708.9	709.9
120°	764.4	764.7	764.8	764.5	763.5	762.5	761.5	760.5	761.5	762.5	763.5
122.5°	814.1	813.7	813.4	813.0	812.4	811.8	811.1	810.5	811.1	811.8	812.4
125°	885.5	886.0	886.5	886.2	885.2	884.2	883.2	882.3	883.2	884.2	885.2
127.5°	954.1	953.0	951.8	951.1	950.9	950.6	950.4	950.1	950.4	950.6	950.9
130°	996.9	996.2	995.4	994.9	994.6	994.5	994.2	993.9	994.2	994.5	994.6
132.5°	1038.5	1037.6	1036.6	1035.9	1035.4	1035.0	1034.6	1034.1	1034.6	1035.0	1035.4
135°	1095.8	1094.8	1093.8	1093.5	1093.7	1093.9	1094.2	1094.4	1094.2	1093.9	1093.7
137.5°	1151.0	1149.9	1148.8	1148.2	1148.1	1148.0	1147.9	1147.8	1147.9	1148.0	1148.1
140°	1186.1	1185.6	1185.2	1184.6	1184.1	1183.6	1183.2	1182.7	1183.2	1183.6	1184.1
142.5°	1218.7	1218.4	1218.1	1217.5	1216.6	1215.7	1214.8	1213.9	1214.8	1215.7	1216.6
145°	1265.3	1265.3	1265.3	1264.9	1264.2	1263.4	1262.7	1262.0	1262.7	1263.4	1264.2
147.5°	1305.8	1306.1	1306.3	1305.7	1304.3	1303.0	1301.5	1300.1	1301.5	1303.0	1304.3
150°	1331.7	1332.0	1332.1	1331.8	1330.8	1329.8	1328.9	1327.8	1328.9	1329.8	1330.8
152.5°	1353.5	1354.0	1354.4	1354.3	1353.4	1352.6	1351.9	1351.1	1351.9	1352.6	1353.4
155°	1382.9	1383.7	1384.4	1384.7	1384.4	1384.1	1383.9	1383.7	1383.9	1384.1	1384.4
157.5°	1408.3	1409.2	1410.1	1410.6	1410.7	1410.8	1411.0	1411.2	1411.0	1410.8	1410.7
160°	1423.2	1423.5	1423.7	1424.3	1425.0	1425.7	1426.5	1427.2	1426.5	1425.7	1425.0
162.5°	1436.7	1436.9	1437.2	1437.8	1438.7	1439.7	1440.5	1441.5	1440.5	1439.7	1438.7
165°	1454.1	1454.1	1454.1	1454.7	1455.9	1457.2	1458.4	1459.7	1458.4	1457.2	1455.9
167.5°	1467.7	1467.9	1468.0	1468.8	1470.1	1471.4	1472.7	1473.9	1472.7	1471.4	1470.1
170°	1475.8	1475.6	1475.4	1476.0	1477.5	1478.9	1480.5	1482.0	1480.5	1478.9	1477.5
172.5°	1481.3	1481.0	1480.7	1481.4	1482.8	1484.4	1485.8	1487.3	1485.8	1484.4	1482.8
175°	1487.0	1486.8	1486.5	1487.1	1488.7	1490.1	1491.6	1493.1	1491.6	1490.1	1488.7
177.5°	1490.6	1490.1	1489.7	1490.2	1491.6	1493.0	1494.4	1495.8	1494.4	1493.0	1491.6
180°	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1



TEST NUMBER: P333107-935

CATALOG NUMBER: S124RDIW-S1195D1340U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2
2.5°	1675.4	1669.9	1662.8	1654.5	1644.6	1635.8	1631.9	1635.3	1636.9	1632.5	1631.9
5°	1624.4	1607.2	1593.5	1572.9	1556.3	1542.6	1533.0	1528.9	1530.3	1519.2	1516.5
7.5°	1567.1	1546.7	1524.1	1499.7	1476.9	1456.6	1446.0	1440.3	1428.7	1423.7	1415.3
10°	1530.3	1502.7	1480.7	1451.8	1425.7	1401.7	1390.0	1380.4	1368.6	1363.1	1351.5
12.5°	1492.3	1460.3	1436.1	1406.2	1379.5	1350.6	1339.4	1321.5	1303.2	1291.7	1276.7
15°	1438.8	1400.3	1370.7	1335.0	1303.4	1270.4	1240.8	1207.8	1195.4	1169.3	1154.2
17.5°	1376.2	1337.2	1300.6	1252.7	1203.9	1162.9	1131.4	1099.8	1080.8	1064.1	1056.4
20°	1335.0	1299.2	1248.4	1192.7	1138.4	1093.0	1067.6	1047.0	1026.3	1014.7	1006.4
22.5°	1296.0	1250.3	1191.2	1131.1	1076.8	1041.3	1019.8	998.6	981.8	970.7	959.7
25°	1230.5	1170.7	1108.1	1039.4	1002.3	971.4	948.0	930.7	920.5	906.0	900.5
27.5°	1163.3	1090.8	1021.8	975.6	936.9	908.6	888.3	875.4	862.3	853.1	845.9
30°	1111.6	1038.0	976.1	932.1	892.9	869.6	853.1	838.0	827.7	820.1	814.6
32.5°	1060.4	986.9	934.9	887.6	856.7	833.9	816.2	804.9	796.9	787.1	783.8
35°	986.4	921.2	875.8	833.2	801.5	780.9	767.2	755.5	748.6	745.9	743.8
37.5°	915.4	861.9	813.1	778.2	750.0	733.7	717.6	711.8	707.1	702.1	704.4
40°	870.3	820.1	776.8	739.7	717.0	699.1	689.5	682.6	678.5	678.5	678.5
42.5°	831.2	782.1	739.9	706.7	684.0	668.9	658.1	652.4	651.0	650.5	653.8
45°	770.6	725.2	682.6	655.1	635.8	620.8	614.6	609.8	609.8	612.5	613.2
47.5°	710.5	668.0	633.8	603.0	585.4	575.9	570.6	568.1	568.3	571.1	574.3
50°	673.6	631.7	598.1	570.6	554.1	545.1	540.3	539.0	540.3	540.3	545.1
52.5°	633.5	596.0	562.8	539.8	521.1	512.7	510.1	508.2	508.9	511.2	513.2
55°	574.7	541.0	509.4	487.4	473.6	468.1	461.9	462.6	461.2	462.6	462.6
57.5°	515.7	485.4	456.1	438.6	426.5	418.5	411.7	413.7	411.6	411.4	410.3
60°	477.8	444.8	421.4	405.6	391.8	385.0	378.8	380.1	378.1	376.7	373.9
62.5°	436.5	409.1	386.8	371.5	360.5	352.5	346.3	344.9	340.2	335.4	329.4
65°	376.7	354.0	334.1	319.7	309.4	303.2	298.3	294.2	283.9	272.9	267.4
67.5°	318.6	302.2	283.6	271.4	263.0	254.9	245.7	238.7	229.0	223.0	219.6
70°	281.1	265.4	249.5	237.8	228.9	221.4	211.0	206.2	199.3	196.6	193.2
72.5°	245.4	230.7	216.0	205.4	195.9	190.0	181.9	177.1	174.1	173.0	169.5
75°	191.1	179.4	168.4	158.8	151.3	147.1	143.7	140.3	138.9	132.7	129.2
77.5°	139.4	131.7	124.8	118.0	112.6	109.9	103.2	99.3	96.9	94.0	93.3
80°	108.6	103.1	96.3	92.1	84.6	81.8	79.0	78.4	77.7	77.0	76.3
82.5°	81.7	76.2	69.3	66.8	64.7	63.1	61.5	60.8	60.1	60.5	60.4
85°	41.2	38.5	38.5	37.8	37.1	36.4	35.7	35.7	35.0	35.7	35.0
87.5°	16.6	16.5	17.0	16.2	17.1	17.6	17.3	17.7	18.4	17.7	17.8
90°	14.3	16.6	18.6	20.6	22.6	24.5	26.1	27.6	29.0	30.6	31.5
92.5°	14.6	15.8	17.7	19.7	21.7	23.7	25.1	26.7	28.2	29.6	30.4
95°	27.6	23.6	23.8	24.1	24.3	24.5	26.1	27.6	29.0	30.6	31.4
97.5°	151.4	140.3	112.5	84.9	57.2	29.4	29.6	29.8	30.0	30.0	30.3
100°	201.0	186.1	151.9	117.6	83.3	49.2	44.9	40.7	36.5	32.3	30.3
102.5°	255.2	254.6	250.1	245.7	241.3	236.8	191.2	145.8	100.2	54.7	31.9
105°	342.1	343.5	344.7	345.9	347.2	348.4	350.7	352.9	355.2	357.4	354.0
107.5°	426.5	427.7	429.4	431.0	432.7	434.5	435.5	436.6	437.7	438.8	439.8
110°	485.4	486.6	488.0	489.5	491.0	492.5	493.0	493.5	494.0	494.5	495.1



TEST NUMBER: P333107-935

CATALOG NUMBER: S124RDIW-S1195D1340U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	545.0	546.0	546.7	547.4	548.1	548.8	548.7	548.5	548.5	548.4	548.8
115°	630.6	630.9	630.6	630.3	630.1	629.8	630.3	630.9	631.4	631.8	632.1
117.5°	710.8	711.6	712.2	712.7	713.3	713.9	713.8	713.6	713.5	713.4	713.3
120°	764.5	764.8	764.7	764.4	764.1	763.9	764.4	764.8	765.3	765.9	765.9
122.5°	813.0	813.4	813.7	814.1	814.4	814.8	815.1	815.4	815.7	816.0	815.9
125°	886.2	886.5	886.0	885.5	884.9	884.5	885.2	886.0	886.7	887.4	887.9
127.5°	951.1	951.8	953.0	954.1	955.3	956.4	956.2	956.1	956.0	955.8	955.6
130°	994.9	995.4	996.2	996.9	997.6	998.4	998.7	998.8	999.1	999.4	999.5
132.5°	1035.9	1036.6	1037.6	1038.5	1039.4	1040.3	1040.6	1040.9	1041.1	1041.4	1041.4
135°	1093.5	1093.8	1094.8	1095.8	1096.8	1097.8	1098.3	1098.8	1099.2	1099.8	1100.3
137.5°	1148.2	1148.8	1149.9	1151.0	1152.1	1153.1	1153.7	1154.3	1154.8	1155.4	1155.5
140°	1184.6	1185.2	1185.6	1186.1	1186.6	1187.1	1187.8	1188.6	1189.4	1190.1	1190.6
142.5°	1217.5	1218.1	1218.4	1218.7	1219.0	1219.3	1219.9	1220.4	1220.9	1221.5	1221.8
145°	1264.9	1265.3	1265.3	1265.3	1265.3	1265.3	1265.6	1265.8	1266.0	1266.3	1266.7
147.5°	1305.7	1306.3	1306.1	1305.8	1305.5	1305.3	1305.4	1305.7	1305.9	1306.1	1306.3
150°	1331.8	1332.1	1332.0	1331.7	1331.5	1331.2	1331.2	1331.2	1331.2	1331.2	1331.3
152.5°	1354.3	1354.4	1354.0	1353.5	1353.1	1352.6	1353.1	1353.4	1353.8	1354.2	1354.4
155°	1384.7	1384.4	1383.7	1382.9	1382.2	1381.5	1382.4	1383.5	1384.4	1385.4	1385.5
157.5°	1410.6	1410.1	1409.2	1408.3	1407.6	1406.7	1408.0	1409.3	1410.6	1411.9	1411.9
160°	1424.3	1423.7	1423.5	1423.2	1423.0	1422.8	1424.3	1425.7	1427.2	1428.7	1428.7
162.5°	1437.8	1437.2	1436.9	1436.7	1436.4	1436.1	1437.6	1439.2	1440.6	1442.1	1442.0
165°	1454.7	1454.1	1454.1	1454.1	1454.1	1454.1	1456.0	1458.0	1460.0	1462.0	1461.8
167.5°	1468.8	1468.0	1467.9	1467.7	1467.6	1467.4	1469.6	1471.8	1473.9	1476.2	1476.0
170°	1476.0	1475.4	1475.6	1475.8	1476.1	1476.4	1478.3	1480.3	1482.3	1484.3	1484.0
172.5°	1481.4	1480.7	1481.0	1481.3	1481.4	1481.7	1483.7	1485.7	1487.7	1489.7	1489.4
175°	1487.1	1486.5	1486.8	1487.0	1487.3	1487.5	1489.8	1492.0	1494.3	1496.5	1496.1
177.5°	1490.2	1489.7	1490.1	1490.6	1490.9	1491.3	1492.9	1494.5	1496.1	1497.7	1497.3
180°	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1



TEST NUMBER: P333107-935

CATALOG NUMBER: S124RDIW-S1195D1340U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2
2.5°	1628.7	1629.8	1625.9	1624.8	1625.9	1629.8	1628.7	1631.9	1632.5	1636.9	1635.3
5°	1511.0	1509.6	1506.1	1506.8	1506.1	1509.6	1511.0	1516.5	1519.2	1530.3	1528.9
7.5°	1410.3	1405.0	1406.4	1401.0	1406.4	1405.0	1410.3	1415.3	1423.7	1428.7	1440.3
10°	1348.8	1341.2	1335.0	1329.5	1335.0	1341.2	1348.8	1351.5	1363.1	1368.6	1380.4
12.5°	1264.6	1258.1	1249.7	1251.4	1249.7	1258.1	1264.6	1276.7	1291.7	1303.2	1321.5
15°	1145.2	1135.0	1118.4	1120.5	1118.4	1135.0	1145.2	1154.2	1169.3	1195.4	1207.8
17.5°	1044.2	1044.3	1036.8	1038.5	1036.8	1044.3	1044.2	1056.4	1064.1	1080.8	1099.8
20°	992.0	987.1	987.8	985.8	987.8	987.1	992.0	1006.4	1014.7	1026.3	1047.0
22.5°	955.6	949.8	944.9	940.6	944.9	949.8	955.6	959.7	970.7	981.8	998.6
25°	894.3	890.2	884.1	882.7	884.1	890.2	894.3	900.5	906.0	920.5	930.7
27.5°	840.4	839.6	837.2	834.0	837.2	839.6	840.4	845.9	853.1	862.3	875.4
30°	809.1	807.7	806.3	804.3	806.3	807.7	809.1	814.6	820.1	827.7	838.0
32.5°	781.1	780.2	778.9	779.0	778.9	780.2	781.1	783.8	787.1	796.9	804.9
35°	741.1	740.4	739.0	738.3	739.0	740.4	741.1	743.8	745.9	748.6	755.5
37.5°	703.7	705.4	704.6	704.5	704.6	705.4	703.7	704.4	702.1	707.1	711.8
40°	677.8	678.5	679.8	679.2	679.8	678.5	677.8	678.5	678.5	678.5	682.6
42.5°	656.3	656.5	658.4	656.1	658.4	656.5	656.3	653.8	650.5	651.0	652.4
45°	618.0	622.2	621.5	621.5	621.5	622.2	618.0	613.2	612.5	609.8	609.8
47.5°	576.1	579.6	580.6	580.5	580.6	579.6	576.1	574.3	571.1	568.3	568.1
50°	548.5	547.2	549.2	548.5	549.2	547.2	548.5	545.1	540.3	540.3	539.0
52.5°	515.1	515.3	515.1	514.4	515.1	515.3	515.1	513.2	511.2	508.9	508.2
55°	463.3	464.0	462.6	463.3	462.6	464.0	463.3	462.6	462.6	461.2	462.6
57.5°	407.3	403.9	405.3	403.6	405.3	403.9	407.3	410.3	411.4	411.6	413.7
60°	367.1	361.6	360.2	357.5	360.2	361.6	367.1	373.9	376.7	378.1	380.1
62.5°	322.0	318.1	313.5	315.6	313.5	318.1	322.0	329.4	335.4	340.2	344.9
65°	261.9	259.2	257.1	259.8	257.1	259.2	261.9	267.4	272.9	283.9	294.2
67.5°	216.8	215.3	215.3	214.0	215.3	215.3	216.8	219.6	223.0	229.0	238.7
70°	193.2	191.1	191.1	189.8	191.1	191.1	193.2	193.2	196.6	199.3	206.2
72.5°	168.9	166.9	167.5	166.6	167.5	166.9	168.9	169.5	173.0	174.1	177.1
75°	125.1	121.7	121.7	122.3	121.7	121.7	125.1	129.2	132.7	138.9	140.3
77.5°	93.3	92.6	93.6	92.4	93.6	92.6	93.3	93.3	94.0	96.9	99.3
80°	76.3	75.6	74.9	77.0	74.9	75.6	76.3	76.3	77.0	77.7	78.4
82.5°	59.2	59.2	59.0	61.6	59.0	59.2	59.2	60.4	60.5	60.1	60.8
85°	35.7	34.4	35.7	34.4	35.7	34.4	35.7	35.0	35.7	35.0	35.7
87.5°	19.0	18.6	18.2	18.8	18.2	18.6	19.0	17.8	17.7	18.4	17.7
90°	32.0	32.5	33.0	33.5	33.0	32.5	32.0	31.5	30.6	29.0	27.6
92.5°	30.6	30.7	30.7	30.8	30.7	30.7	30.6	30.4	29.6	28.2	26.7
95°	31.6	31.9	32.1	32.4	32.1	31.9	31.6	31.4	30.6	29.0	27.6
97.5°	30.6	30.7	31.0	31.3	31.0	30.7	30.6	30.3	30.0	30.0	29.8
100°	30.6	30.7	31.0	31.3	31.0	30.7	30.6	30.3	32.3	36.5	40.7
102.5°	32.0	32.0	32.1	32.2	32.1	32.0	32.0	31.9	54.7	100.2	145.8
105°	345.1	336.1	327.2	318.3	327.2	336.1	345.1	354.0	357.4	355.2	352.9
107.5°	440.7	441.7	442.6	443.6	442.6	441.7	440.7	439.8	438.8	437.7	436.6
110°	495.8	496.6	497.3	498.1	497.3	496.6	495.8	495.1	494.5	494.0	493.5



TEST NUMBER: P333107-935

CATALOG NUMBER: S124RDIW-S1195D1340U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	549.7	550.7	551.6	552.6	551.6	550.7	549.7	548.8	548.4	548.5	548.5
115°	632.1	632.1	632.1	632.1	632.1	632.1	632.1	632.1	631.8	631.4	630.9
117.5°	713.3	713.2	713.1	712.9	713.1	713.2	713.3	713.3	713.4	713.5	713.6
120°	765.3	764.8	764.4	763.9	764.4	764.8	765.3	765.9	765.9	765.3	764.8
122.5°	815.4	814.9	814.4	813.9	814.4	814.9	815.4	815.9	816.0	815.7	815.4
125°	888.2	888.5	888.7	889.0	888.7	888.5	888.2	887.9	887.4	886.7	886.0
127.5°	955.5	955.2	955.0	954.8	955.0	955.2	955.5	955.6	955.8	956.0	956.1
130°	999.5	999.5	999.5	999.5	999.5	999.5	999.5	999.5	999.4	999.1	998.8
132.5°	1041.2	1041.0	1040.8	1040.6	1040.8	1041.0	1041.2	1041.4	1041.4	1041.1	1040.9
135°	1100.8	1101.2	1101.7	1102.3	1101.7	1101.2	1100.8	1100.3	1099.8	1099.2	1098.8
137.5°	1155.4	1155.3	1155.1	1154.9	1155.1	1155.3	1155.4	1155.5	1155.4	1154.8	1154.3
140°	1190.8	1191.1	1191.4	1191.6	1191.4	1191.1	1190.8	1190.6	1190.1	1189.4	1188.6
142.5°	1221.8	1221.8	1221.9	1221.9	1221.9	1221.8	1221.8	1221.8	1221.5	1220.9	1220.4
145°	1267.1	1267.7	1268.2	1268.7	1268.2	1267.7	1267.1	1266.7	1266.3	1266.0	1265.8
147.5°	1306.6	1306.8	1307.0	1307.3	1307.0	1306.8	1306.6	1306.3	1306.1	1305.9	1305.7
150°	1331.5	1331.8	1332.1	1332.3	1332.1	1331.8	1331.5	1331.3	1331.2	1331.2	1331.2
152.5°	1354.2	1354.0	1353.9	1353.8	1353.9	1354.0	1354.2	1354.4	1354.2	1353.8	1353.4
155°	1384.8	1384.1	1383.3	1382.6	1383.3	1384.1	1384.8	1385.5	1385.4	1384.4	1383.5
157.5°	1410.6	1409.3	1408.0	1406.7	1408.0	1409.3	1410.6	1411.9	1411.9	1410.6	1409.3
160°	1427.2	1425.7	1424.3	1422.8	1424.3	1425.7	1427.2	1428.7	1428.7	1427.2	1425.7
162.5°	1440.4	1438.6	1436.9	1435.3	1436.9	1438.6	1440.4	1442.0	1442.1	1440.6	1439.2
165°	1459.7	1457.4	1455.2	1452.9	1455.2	1457.4	1459.7	1461.8	1462.0	1460.0	1458.0
167.5°	1473.5	1471.0	1468.6	1466.1	1468.6	1471.0	1473.5	1476.0	1476.2	1473.9	1471.8
170°	1481.6	1479.1	1476.6	1474.1	1476.6	1479.1	1481.6	1484.0	1484.3	1482.3	1480.3
172.5°	1486.6	1483.9	1481.3	1478.6	1481.3	1483.9	1486.6	1489.4	1489.7	1487.7	1485.7
175°	1493.1	1490.1	1487.1	1484.2	1487.1	1490.1	1493.1	1496.1	1496.5	1494.3	1492.0
177.5°	1494.9	1492.5	1490.1	1487.7	1490.1	1492.5	1494.9	1497.3	1497.7	1496.1	1494.5
180°	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1



TEST NUMBER: P333107-935

CATALOG NUMBER: S124RDIW-S1195D1340U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2
2.5°	1631.9	1635.8	1644.6	1654.5	1662.8	1669.9	1675.4	1683.1	1690.2	1700.1	1709.5
5°	1533.0	1542.6	1556.3	1572.9	1593.5	1607.2	1624.4	1639.5	1661.6	1683.5	1704.9
7.5°	1446.0	1456.6	1476.9	1499.7	1524.1	1546.7	1567.1	1593.7	1622.9	1654.9	1690.7
10°	1390.0	1401.7	1425.7	1451.8	1480.7	1502.7	1530.3	1561.9	1594.8	1634.0	1678.0
12.5°	1339.4	1350.6	1379.5	1406.2	1436.1	1460.3	1492.3	1524.5	1568.5	1610.9	1661.0
15°	1240.8	1270.4	1303.4	1335.0	1370.7	1400.3	1438.8	1471.8	1513.7	1573.6	1630.6
17.5°	1131.4	1162.9	1203.9	1252.7	1300.6	1337.2	1376.2	1417.2	1467.1	1528.2	1594.1
20°	1067.6	1093.0	1138.4	1192.7	1248.4	1299.2	1335.0	1380.4	1431.9	1497.9	1566.0
22.5°	1019.8	1041.3	1076.8	1131.1	1191.2	1250.3	1296.0	1340.7	1397.8	1463.8	1537.9
25°	948.0	971.4	1002.3	1039.4	1108.1	1170.7	1230.5	1282.0	1342.6	1408.5	1491.0
27.5°	888.3	908.6	936.9	975.6	1021.8	1090.8	1163.3	1222.1	1284.1	1355.0	1437.5
30°	853.1	869.6	892.9	932.1	976.1	1038.0	1111.6	1180.3	1242.9	1316.5	1402.4
32.5°	816.2	833.9	856.7	887.6	934.9	986.9	1060.4	1135.7	1202.2	1277.4	1361.7
35°	767.2	780.9	801.5	833.2	875.8	921.2	986.4	1064.1	1134.3	1214.7	1295.1
37.5°	717.6	733.7	750.0	778.2	813.1	861.9	915.4	994.7	1072.4	1145.8	1224.3
40°	689.5	699.1	717.0	739.7	776.8	820.1	870.3	948.0	1025.6	1098.5	1177.6
42.5°	658.1	668.9	684.0	706.7	739.9	782.1	831.2	898.5	979.5	1050.2	1122.1
45°	614.6	620.8	635.8	655.1	682.6	725.2	770.6	830.4	906.7	974.0	1037.3
47.5°	570.6	575.9	585.4	603.0	633.8	668.0	710.5	764.1	831.1	898.5	951.9
50°	540.3	545.1	554.1	570.6	598.1	631.7	673.6	721.8	781.6	846.2	890.9
52.5°	510.1	512.7	521.1	539.8	562.8	596.0	633.5	677.8	733.7	787.4	832.6
55°	461.9	468.1	473.6	487.4	509.4	541.0	574.7	616.6	660.0	705.3	743.8
57.5°	411.7	418.5	426.5	438.6	456.1	485.4	515.7	549.7	586.7	624.3	656.6
60°	378.8	385.0	391.8	405.6	421.4	444.8	477.8	507.3	535.5	569.9	602.2
62.5°	346.3	352.5	360.5	371.5	386.8	409.1	436.5	462.3	491.5	521.5	545.5
65°	298.3	303.2	309.4	319.7	334.1	354.0	376.7	396.7	422.8	444.8	466.7
67.5°	245.7	254.9	263.0	271.4	283.6	302.2	318.6	337.7	355.4	371.8	391.8
70°	211.0	221.4	228.9	237.8	249.5	265.4	281.1	294.2	308.7	324.4	342.3
72.5°	181.9	190.0	195.9	205.4	216.0	230.7	245.4	256.2	267.9	278.8	296.2
75°	143.7	147.1	151.3	158.8	168.4	179.4	191.1	200.7	207.6	217.2	229.6
77.5°	103.2	109.9	112.6	118.0	124.8	131.7	139.4	147.5	154.1	157.6	167.0
80°	79.0	81.8	84.6	92.1	96.3	103.1	108.6	116.1	118.9	122.3	131.3
82.5°	61.5	63.1	64.7	66.8	69.3	76.2	81.7	86.4	89.2	90.5	97.2
85°	35.7	36.4	37.1	37.8	38.5	38.5	41.2	44.7	49.5	49.5	51.6
87.5°	17.3	17.6	17.1	16.2	17.0	16.5	16.6	16.0	17.1	18.3	19.4
90°	26.1	24.5	22.6	20.6	18.6	16.6	14.3	11.5	8.8	6.1	3.4
92.5°	25.1	23.7	21.7	19.7	17.7	15.8	14.6	14.6	14.4	14.2	14.0
95°	26.1	24.5	24.3	24.1	23.8	23.6	27.6	36.1	44.5	53.0	61.4
97.5°	29.6	29.4	57.2	84.9	112.5	140.3	151.4	146.2	140.9	135.7	130.4
100°	44.9	49.2	83.3	117.6	151.9	186.1	201.0	196.6	192.1	187.6	183.1
102.5°	191.2	236.8	241.3	245.7	250.1	254.6	255.2	251.9	248.7	245.4	242.1
105°	350.7	348.4	347.2	345.9	344.7	343.5	342.1	340.6	339.1	337.6	336.1
107.5°	435.5	434.5	432.7	431.0	429.4	427.7	426.5	425.7	425.0	424.2	423.4
110°	493.0	492.5	491.0	489.5	488.0	486.6	485.4	484.7	484.0	483.2	482.4



TEST NUMBER: P333107-935

CATALOG NUMBER: S124RDIW-S1195D1340U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	548.7	548.8	548.1	547.4	546.7	546.0	545.0	543.6	542.3	541.0	539.6
115°	630.3	629.8	630.1	630.3	630.6	630.9	630.6	629.8	629.1	628.4	627.6
117.5°	713.8	713.9	713.3	712.7	712.2	711.6	710.8	709.9	708.9	707.9	706.9
120°	764.4	763.9	764.1	764.4	764.7	764.8	764.5	763.5	762.5	761.5	760.5
122.5°	815.1	814.8	814.4	814.1	813.7	813.4	813.0	812.4	811.8	811.1	810.5
125°	885.2	884.5	884.9	885.5	886.0	886.5	886.2	885.2	884.2	883.2	882.3
127.5°	956.2	956.4	955.3	954.1	953.0	951.8	951.1	950.9	950.6	950.4	950.1
130°	998.7	998.4	997.6	996.9	996.2	995.4	994.9	994.6	994.5	994.2	993.9
132.5°	1040.6	1040.3	1039.4	1038.5	1037.6	1036.6	1035.9	1035.4	1035.0	1034.6	1034.1
135°	1098.3	1097.8	1096.8	1095.8	1094.8	1093.8	1093.5	1093.7	1093.9	1094.2	1094.4
137.5°	1153.7	1153.1	1152.1	1151.0	1149.9	1148.8	1148.2	1148.1	1148.0	1147.9	1147.8
140°	1187.8	1187.1	1186.6	1186.1	1185.6	1185.2	1184.6	1184.1	1183.6	1183.2	1182.7
142.5°	1219.9	1219.3	1219.0	1218.7	1218.4	1218.1	1217.5	1216.6	1215.7	1214.8	1213.9
145°	1265.6	1265.3	1265.3	1265.3	1265.3	1265.3	1264.9	1264.2	1263.4	1262.7	1262.0
147.5°	1305.4	1305.3	1305.5	1305.8	1306.1	1306.3	1305.7	1304.3	1303.0	1301.5	1300.1
150°	1331.2	1331.2	1331.5	1331.7	1332.0	1332.1	1331.8	1330.8	1329.8	1328.9	1327.8
152.5°	1353.1	1352.6	1353.1	1353.5	1354.0	1354.4	1354.3	1353.4	1352.6	1351.9	1351.1
155°	1382.4	1381.5	1382.2	1382.9	1383.7	1384.4	1384.7	1384.4	1384.1	1383.9	1383.7
157.5°	1408.0	1406.7	1407.6	1408.3	1409.2	1410.1	1410.6	1410.7	1410.8	1411.0	1411.2
160°	1424.3	1422.8	1423.0	1423.2	1423.5	1423.7	1424.3	1425.0	1425.7	1426.5	1427.2
162.5°	1437.6	1436.1	1436.4	1436.7	1436.9	1437.2	1437.8	1438.7	1439.7	1440.5	1441.5
165°	1456.0	1454.1	1454.1	1454.1	1454.1	1454.1	1454.7	1455.9	1457.2	1458.4	1459.7
167.5°	1469.6	1467.4	1467.6	1467.7	1467.9	1468.0	1468.8	1470.1	1471.4	1472.7	1473.9
170°	1478.3	1476.4	1476.1	1475.8	1475.6	1475.4	1476.0	1477.5	1478.9	1480.5	1482.0
172.5°	1483.7	1481.7	1481.4	1481.3	1481.0	1480.7	1481.4	1482.8	1484.4	1485.8	1487.3
175°	1489.8	1487.5	1487.3	1487.0	1486.8	1486.5	1487.1	1488.7	1490.1	1491.6	1493.1
177.5°	1492.9	1491.3	1490.9	1490.6	1490.1	1489.7	1490.2	1491.6	1493.0	1494.4	1495.8
180°	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1



TEST NUMBER: P333107-935

CATALOG NUMBER: S124RDIW-S1195D1340U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2
2.5°	1716.7	1721.6	1727.1	1737.6	1746.4	1750.2	1757.9	1763.4	1761.8	1769.4	1782.6
5°	1723.4	1742.0	1763.2	1785.3	1810.0	1830.7	1847.1	1863.6	1876.7	1892.5	1915.9
7.5°	1722.3	1755.3	1791.1	1830.7	1871.2	1906.3	1938.7	1971.7	2001.0	2033.0	2074.9
10°	1717.9	1761.9	1806.6	1858.1	1909.7	1958.5	2002.5	2043.8	2082.9	2124.9	2177.8
12.5°	1713.0	1763.5	1817.6	1879.6	1943.8	2002.5	2054.2	2113.6	2162.7	2216.7	2277.9
15°	1691.1	1759.1	1832.7	1913.1	1990.1	2069.2	2139.9	2212.9	2280.9	2345.5	2422.5
17.5°	1666.0	1744.6	1831.3	1926.3	2018.9	2115.0	2199.0	2290.8	2360.3	2447.1	2518.6
20°	1645.7	1730.3	1823.1	1929.6	2034.8	2141.3	2234.1	2327.6	2406.0	2493.3	2584.0
22.5°	1620.9	1713.7	1814.3	1924.7	2034.8	2151.2	2253.9	2346.9	2443.9	2542.3	2635.8
25°	1581.1	1677.3	1783.9	1904.9	2031.4	2150.3	2260.3	2375.8	2480.3	2586.8	2670.6
27.5°	1532.1	1633.2	1745.5	1870.4	2000.2	2121.9	2251.5	2374.6	2479.7	2582.2	2655.4
30°	1493.1	1599.7	1707.5	1834.1	1968.8	2099.4	2238.3	2361.3	2472.0	2564.1	2605.4
32.5°	1452.9	1554.0	1665.3	1793.4	1931.4	2071.9	2209.7	2335.5	2437.9	2493.2	2494.2
35°	1383.1	1478.0	1593.5	1719.2	1860.9	2013.4	2153.0	2276.7	2339.3	2344.2	2276.7
37.5°	1306.9	1394.0	1503.0	1628.9	1784.0	1935.8	2078.4	2160.9	2181.8	2111.8	1987.2
40°	1252.5	1332.9	1438.1	1567.4	1721.3	1878.1	2008.0	2068.5	2046.5	1933.0	1794.2
42.5°	1195.3	1270.2	1371.6	1499.2	1653.7	1812.1	1922.8	1955.2	1896.9	1765.9	1603.4
45°	1102.0	1170.7	1271.1	1399.6	1548.1	1696.6	1780.5	1763.9	1667.0	1511.7	1329.5
47.5°	1004.8	1071.2	1161.5	1280.4	1432.4	1560.6	1617.4	1567.6	1429.7	1258.8	1110.6
50°	940.4	1008.5	1091.7	1205.1	1343.9	1467.7	1504.1	1428.5	1275.1	1110.9	974.7
52.5°	877.2	935.3	1016.8	1126.4	1259.2	1363.7	1383.1	1296.0	1137.7	990.4	869.7
55°	780.9	833.9	902.6	1005.7	1120.5	1209.2	1198.9	1086.8	943.1	817.3	722.5
57.5°	687.9	727.7	791.3	887.9	988.7	1048.2	1010.6	915.0	781.1	678.1	598.1
60°	626.3	663.4	722.5	807.0	895.7	929.4	897.8	794.0	688.1	593.9	526.6
62.5°	567.9	600.7	651.5	730.0	801.7	821.7	787.8	697.2	601.8	521.3	465.5
65°	483.3	513.5	556.8	612.5	662.0	671.6	649.6	556.8	484.7	417.2	378.8
67.5°	406.4	426.2	460.0	508.2	534.4	540.0	497.6	439.3	375.7	334.2	305.2
70°	354.7	368.4	400.1	426.2	447.5	448.2	409.1	362.3	313.5	279.8	258.5
72.5°	304.7	317.9	341.8	359.6	376.0	370.7	334.8	297.9	258.5	233.1	217.2
75°	235.1	246.8	259.2	267.4	267.4	260.5	234.5	206.9	184.3	169.1	164.3
77.5°	170.9	180.6	184.7	183.4	180.9	170.2	153.7	135.7	127.6	120.5	116.8
80°	134.1	138.2	139.6	136.1	132.0	119.6	108.6	101.1	93.5	90.7	89.4
82.5°	99.4	103.0	99.4	100.4	91.3	81.1	75.1	72.5	69.3	68.2	66.8
85°	53.0	52.3	50.9	47.4	41.2	39.9	39.2	38.5	37.1	37.8	36.4
87.5°	19.4	18.3	16.6	16.6	17.0	16.4	17.3	17.7	18.1	17.8	19.3
90°	6.1	8.8	11.5	14.3	16.6	18.6	20.6	22.6	24.5	26.1	27.6
92.5°	14.2	14.4	14.6	14.6	15.8	17.7	19.7	21.7	23.7	25.1	26.7
95°	53.0	44.5	36.1	27.6	23.6	23.8	24.1	24.3	24.5	26.1	27.6
97.5°	135.7	140.9	146.2	151.4	140.3	112.5	84.9	57.2	29.4	29.6	29.8
100°	187.6	192.1	196.6	201.0	186.1	151.9	117.6	83.3	49.2	44.9	40.7
102.5°	245.4	248.7	251.9	255.2	254.6	250.1	245.7	241.3	236.8	191.2	145.8
105°	337.6	339.1	340.6	342.1	343.5	344.7	345.9	347.2	348.4	350.7	352.9
107.5°	424.2	425.0	425.7	426.5	427.7	429.4	431.0	432.7	434.5	435.5	436.6
110°	483.2	484.0	484.7	485.4	486.6	488.0	489.5	491.0	492.5	493.0	493.5





TEST NUMBER: P333107-935

CATALOG NUMBER: S124RDIW-S1195D1340U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	541.0	542.3	543.6	545.0	546.0	546.7	547.4	548.1	548.8	548.7	548.5
115°	628.4	629.1	629.8	630.6	630.9	630.6	630.3	630.1	629.8	630.3	630.9
117.5°	707.9	708.9	709.9	710.8	711.6	712.2	712.7	713.3	713.9	713.8	713.6
120°	761.5	762.5	763.5	764.5	764.8	764.7	764.4	764.1	763.9	764.4	764.8
122.5°	811.1	811.8	812.4	813.0	813.4	813.7	814.1	814.4	814.8	815.1	815.4
125°	883.2	884.2	885.2	886.2	886.5	886.0	885.5	884.9	884.5	885.2	886.0
127.5°	950.4	950.6	950.9	951.1	951.8	953.0	954.1	955.3	956.4	956.2	956.1
130°	994.2	994.5	994.6	994.9	995.4	996.2	996.9	997.6	998.4	998.7	998.8
132.5°	1034.6	1035.0	1035.4	1035.9	1036.6	1037.6	1038.5	1039.4	1040.3	1040.6	1040.9
135°	1094.2	1093.9	1093.7	1093.5	1093.8	1094.8	1095.8	1096.8	1097.8	1098.3	1098.8
137.5°	1147.9	1148.0	1148.1	1148.2	1148.8	1149.9	1151.0	1152.1	1153.1	1153.7	1154.3
140°	1183.2	1183.6	1184.1	1184.6	1185.2	1185.6	1186.1	1186.6	1187.1	1187.8	1188.6
142.5°	1214.8	1215.7	1216.6	1217.5	1218.1	1218.4	1218.7	1219.0	1219.3	1219.9	1220.4
145°	1262.7	1263.4	1264.2	1264.9	1265.3	1265.3	1265.3	1265.3	1265.3	1265.6	1265.8
147.5°	1301.5	1303.0	1304.3	1305.7	1306.3	1306.1	1305.8	1305.5	1305.3	1305.4	1305.7
150°	1328.9	1329.8	1330.8	1331.8	1332.1	1332.0	1331.7	1331.5	1331.2	1331.2	1331.2
152.5°	1351.9	1352.6	1353.4	1354.3	1354.4	1354.0	1353.5	1353.1	1352.6	1353.1	1353.4
155°	1383.9	1384.1	1384.4	1384.7	1384.4	1383.7	1382.9	1382.2	1381.5	1382.4	1383.5
157.5°	1411.0	1410.8	1410.7	1410.6	1410.1	1409.2	1408.3	1407.6	1406.7	1408.0	1409.3
160°	1426.5	1425.7	1425.0	1424.3	1423.7	1423.5	1423.2	1423.0	1422.8	1424.3	1425.7
162.5°	1440.5	1439.7	1438.7	1437.8	1437.2	1436.9	1436.7	1436.4	1436.1	1437.6	1439.2
165°	1458.4	1457.2	1455.9	1454.7	1454.1	1454.1	1454.1	1454.1	1454.1	1456.0	1458.0
167.5°	1472.7	1471.4	1470.1	1468.8	1468.0	1467.9	1467.7	1467.6	1467.4	1469.6	1471.8
170°	1480.5	1478.9	1477.5	1476.0	1475.4	1475.6	1475.8	1476.1	1476.4	1478.3	1480.3
172.5°	1485.8	1484.4	1482.8	1481.4	1480.7	1481.0	1481.3	1481.4	1481.7	1483.7	1485.7
175°	1491.6	1490.1	1488.7	1487.1	1486.5	1486.8	1487.0	1487.3	1487.5	1489.8	1492.0
177.5°	1494.4	1493.0	1491.6	1490.2	1489.7	1490.1	1490.6	1490.9	1491.3	1492.9	1494.5
180°	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1



TEST NUMBER: P333107-935

CATALOG NUMBER: S124RDIW-S1195D1340U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2
2.5°	1789.8	1792.0	1793.6	1799.1	1799.7	1804.7	1799.7
5°	1937.9	1947.5	1962.6	1977.7	1979.1	1988.7	1971.5
7.5°	2103.9	2126.2	2140.1	2164.6	2174.2	2180.2	2170.3
10°	2218.4	2238.9	2275.4	2293.3	2311.2	2313.9	2305.7
12.5°	2328.9	2361.6	2390.3	2424.1	2423.4	2447.6	2438.7
15°	2476.1	2509.8	2549.7	2587.5	2601.3	2601.3	2612.3
17.5°	2581.2	2642.9	2684.2	2713.9	2746.2	2751.9	2748.1
20°	2652.1	2718.8	2762.8	2801.3	2823.3	2829.5	2829.5
22.5°	2704.9	2761.7	2804.6	2839.2	2857.4	2864.6	2862.5
25°	2741.5	2790.2	2816.4	2826.7	2831.5	2830.2	2817.1
27.5°	2691.4	2689.2	2672.7	2641.1	2617.4	2602.9	2586.4
30°	2595.7	2560.0	2518.8	2473.4	2414.9	2370.2	2356.5
32.5°	2453.3	2373.0	2303.2	2227.6	2164.7	2120.0	2101.4
35°	2177.8	2050.6	1946.8	1856.1	1790.1	1748.9	1735.1
37.5°	1850.8	1727.8	1599.2	1511.2	1456.6	1414.9	1399.3
40°	1643.0	1508.9	1396.9	1314.4	1258.0	1217.5	1216.8
42.5°	1453.2	1325.3	1219.8	1160.4	1099.6	1072.8	1072.6
45°	1189.9	1087.5	998.2	951.4	915.0	892.9	886.7
47.5°	985.2	900.5	841.0	803.7	774.0	760.0	751.0
50°	870.3	796.1	748.6	716.3	699.8	681.9	680.5
52.5°	774.6	714.6	677.7	651.4	630.5	619.7	620.1
55°	651.0	603.6	577.5	557.5	541.0	532.8	529.3
57.5°	548.5	512.8	493.9	475.5	468.6	462.1	460.3
60°	484.7	460.5	442.7	428.3	417.9	415.9	415.2
62.5°	431.9	406.7	394.3	383.1	375.7	372.5	371.2
65°	356.1	337.5	326.5	317.6	314.9	310.0	309.4
67.5°	287.1	276.0	268.6	262.4	258.7	258.5	258.5
70°	244.7	238.5	232.4	228.9	226.9	225.5	225.5
72.5°	208.4	203.9	198.8	197.0	196.6	195.2	194.7
75°	158.8	153.9	154.6	151.3	148.5	145.1	143.0
77.5°	112.6	109.2	108.5	108.1	105.7	105.3	106.4
80°	87.3	83.9	83.2	83.9	83.2	81.1	81.1
82.5°	66.4	63.5	62.9	62.4	61.7	62.4	61.3
85°	35.7	34.4	34.4	34.4	35.7	35.0	34.4
87.5°	18.4	18.2	18.9	18.5	18.6	18.2	18.8
90°	29.0	30.6	31.5	32.0	32.5	33.0	33.5
92.5°	28.2	29.6	30.4	30.6	30.7	30.7	30.8
95°	29.0	30.6	31.4	31.6	31.9	32.1	32.4
97.5°	30.0	30.0	30.3	30.6	30.7	31.0	31.3
100°	36.5	32.3	30.3	30.6	30.7	31.0	31.3
102.5°	100.2	54.7	31.9	32.0	32.0	32.1	32.2
105°	355.2	357.4	354.0	345.1	336.1	327.2	318.3
107.5°	437.7	438.8	439.8	440.7	441.7	442.6	443.6
110°	494.0	494.5	495.1	495.8	496.6	497.3	498.1



TEST NUMBER: P333107-935

CATALOG NUMBER: S124RDIW-S1195D1340U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	548.5	548.4	548.8	549.7	550.7	551.6	552.6
115°	631.4	631.8	632.1	632.1	632.1	632.1	632.1
117.5°	713.5	713.4	713.3	713.3	713.2	713.1	712.9
120°	765.3	765.9	765.9	765.3	764.8	764.4	763.9
122.5°	815.7	816.0	815.9	815.4	814.9	814.4	813.9
125°	886.7	887.4	887.9	888.2	888.5	888.7	889.0
127.5°	956.0	955.8	955.6	955.5	955.2	955.0	954.8
130°	999.1	999.4	999.5	999.5	999.5	999.5	999.5
132.5°	1041.1	1041.4	1041.4	1041.2	1041.0	1040.8	1040.6
135°	1099.2	1099.8	1100.3	1100.8	1101.2	1101.7	1102.3
137.5°	1154.8	1155.4	1155.5	1155.4	1155.3	1155.1	1154.9
140°	1189.4	1190.1	1190.6	1190.8	1191.1	1191.4	1191.6
142.5°	1220.9	1221.5	1221.8	1221.8	1221.8	1221.9	1221.9
145°	1266.0	1266.3	1266.7	1267.1	1267.7	1268.2	1268.7
147.5°	1305.9	1306.1	1306.3	1306.6	1306.8	1307.0	1307.3
150°	1331.2	1331.2	1331.3	1331.5	1331.8	1332.1	1332.3
152.5°	1353.8	1354.2	1354.4	1354.2	1354.0	1353.9	1353.8
155°	1384.4	1385.4	1385.5	1384.8	1384.1	1383.3	1382.6
157.5°	1410.6	1411.9	1411.9	1410.6	1409.3	1408.0	1406.7
160°	1427.2	1428.7	1428.7	1427.2	1425.7	1424.3	1422.8
162.5°	1440.6	1442.1	1442.0	1440.4	1438.6	1436.9	1435.3
165°	1460.0	1462.0	1461.8	1459.7	1457.4	1455.2	1452.9
167.5°	1473.9	1476.2	1476.0	1473.5	1471.0	1468.6	1466.1
170°	1482.3	1484.3	1484.0	1481.6	1479.1	1476.6	1474.1
172.5°	1487.7	1489.7	1489.4	1486.6	1483.9	1481.3	1478.6
175°	1494.3	1496.5	1496.1	1493.1	1490.1	1487.1	1484.2
177.5°	1496.1	1497.7	1497.3	1494.9	1492.5	1490.1	1487.7
180°	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1

(END OF REPORT)