

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333110-935

Luminaire Tested: **S124RDIW-S1195D1340U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333110-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1195D1340U935-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8158.5 lumens
Efficiency: N/A
Efficacy: 107.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333110-935

CATALOG NUMBER: S124RDIW-S1195D1340U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333110-935

CATALOG NUMBER: S124RDIW-S1195D1340U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84		70	70	70		57	57	57	51
1	98	94	90	87	91	87	84	81	74	72	69		62	60	59		51	50	49	43
2	90	82	76	71	83	76	71	67	65	61	58		55	52	49		45	43	41	37
3	82	73	65	60	75	67	61	56	58	53	49		49	45	42		40	38	35	31
4	75	64	57	51	69	60	53	48	51	46	42		43	39	36		36	33	31	27
5	69	58	50	44	64	54	46	41	46	41	36		39	35	32		33	29	27	24
6	64	52	44	38	59	48	41	36	42	36	32		35	31	28		30	26	24	21
7	59	47	39	33	54	44	37	32	38	32	28		32	28	25		27	24	21	19
8	55	43	35	30	51	40	33	28	34	29	25		30	25	22		25	22	19	17
9	51	39	31	26	47	36	30	25	32	26	22		27	23	20		23	20	17	15
10	48	36	29	24	44	33	27	23	29	24	20		25	21	18		21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14495	14495	14495
5°	14528	14350	14439
10°	14437	14178	14178
15°	14271	13881	13778
20°	14044	13489	13241
25°	13752	13030	12699
30°	13470	12547	12021
35°	13157	12046	11340
40°	12779	11475	10606
45°	12432	10909	9857
50°	12036	10257	9065
55°	11610	9578	8204
60°	11144	8835	7325
65°	10714	7904	6460
70°	10093	6878	5486
75°	9304	5705	4460
80°	8117	4347	4091
85°	6873	3946	3696



TEST NUMBER: P333110-935

CATALOG NUMBER: S124RDIW-S1195D1340U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	168.7	2.1
10°-20°	470.4	5.8
20°-30°	679.2	8.3
30°-40°	769.9	9.4
40°-50°	743.4	9.1
50°-60°	618.2	7.6
60°-70°	426.9	5.2
70°-80°	216.4	2.7
80°-90°	59.8	0.7
90°-100°	95.2	1.2
100°-110°	282.1	3.5
110°-120°	478.8	5.9
120°-130°	631.3	7.7
130°-140°	709.0	8.7
140°-150°	696.7	8.5
150°-160°	586.0	7.2
160°-170°	389.9	4.8
170°-180°	136.5	1.7
0°-30°	1318.2	16.2
0°-40°	2088.1	25.6
0°-60°	3449.7	42.3
0°-90°	4152.8	50.9
90°-120°	856.1	10.5
90°-150°	2893.2	35.5
90°-180°	4006.0	49.1
0°-180°	8158.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1796	1796	1796	1796	1796	
5°	1793	1787	1771	1784	1782	170
15°	1708	1694	1661	1658	1648	481
25°	1544	1517	1463	1440	1426	711
35°	1335	1290	1222	1177	1151	834
45°	1089	1036	956	890	863	839
55°	825	768	680	612	583	738
65°	561	500	414	357	338	554
75°	298	247	183	152	143	315
85°	74	48	43	40	40	84
90°	3	15	24	31	34	8
95°	67	77	85	88	88	75
105°	260	261	266	269	272	276
115°	487	487	485	484	482	480
125°	709	709	708	706	703	632
135°	914	921	921	919	916	707
145°	1111	1115	1117	1115	1112	695
155°	1273	1273	1272	1276	1272	585
165°	1386	1382	1380	1386	1382	390
175°	1442	1436	1435	1442	1435	137
180°	1444	1444	1444	1444	1444	



TEST NUMBER: P333110-935

CATALOG NUMBER: S124RDIW-S1195D1340U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5
2.5°	1799.9	1799.0	1798.0	1797.0	1796.0	1794.2	1791.6	1788.8	1786.1	1783.5	1786.1
5°	1792.8	1791.6	1790.4	1789.2	1788.0	1785.5	1781.8	1778.1	1774.5	1770.8	1773.8
7.5°	1776.6	1775.3	1774.0	1772.7	1771.4	1768.4	1763.7	1758.9	1754.1	1749.4	1751.4
10°	1761.2	1759.6	1758.2	1756.6	1755.1	1751.5	1746.1	1740.6	1735.1	1729.6	1730.8
12.5°	1741.4	1739.7	1737.8	1736.0	1734.3	1730.2	1723.7	1717.3	1710.7	1704.3	1705.0
15°	1707.5	1704.8	1702.1	1699.4	1696.6	1691.3	1683.8	1676.1	1668.4	1660.8	1660.2
17.5°	1666.6	1662.6	1658.6	1654.7	1650.7	1644.2	1635.0	1625.8	1616.6	1607.5	1605.8
20°	1634.7	1630.7	1626.8	1622.8	1618.9	1611.6	1601.3	1590.9	1580.5	1570.1	1567.6
22.5°	1599.5	1595.1	1590.6	1586.1	1581.7	1573.9	1562.7	1551.6	1540.5	1529.4	1525.7
25°	1543.9	1538.4	1532.9	1527.5	1522.0	1512.9	1500.5	1487.9	1475.4	1462.8	1457.7
27.5°	1485.7	1478.8	1471.9	1465.0	1458.0	1447.9	1434.5	1421.2	1407.7	1394.4	1387.9
30°	1445.0	1437.4	1429.7	1422.0	1414.5	1403.4	1389.1	1374.7	1360.4	1346.0	1338.3
32.5°	1402.1	1393.4	1384.8	1376.2	1367.6	1355.9	1341.0	1326.2	1311.3	1296.5	1287.6
35°	1335.0	1325.2	1315.4	1305.6	1295.9	1283.3	1268.1	1252.8	1237.5	1222.3	1211.9
37.5°	1263.3	1253.1	1243.0	1233.0	1222.9	1209.4	1192.5	1175.5	1158.6	1141.7	1130.1
40°	1212.6	1202.6	1192.5	1182.4	1172.3	1158.6	1141.2	1123.7	1106.3	1088.9	1076.1
42.5°	1164.2	1153.7	1143.1	1132.5	1122.0	1107.6	1089.4	1071.3	1053.2	1035.0	1021.9
45°	1088.9	1077.5	1066.3	1055.0	1043.7	1028.8	1010.6	992.2	973.9	955.5	940.6
47.5°	1011.1	999.4	987.7	976.0	964.4	949.0	930.0	910.9	891.8	872.8	857.2
50°	958.3	946.3	934.4	922.6	910.6	894.8	875.3	855.7	836.2	816.7	801.4
52.5°	904.4	892.7	881.1	869.4	857.7	841.8	821.8	801.8	781.7	761.6	746.1
55°	824.9	812.7	800.5	788.2	776.0	760.0	740.1	720.3	700.4	680.5	664.7
57.5°	746.2	733.6	720.8	708.2	695.4	679.3	659.8	640.2	620.6	601.1	585.0
60°	690.2	678.0	665.7	653.5	641.3	625.4	605.9	586.3	566.7	547.2	531.3
62.5°	639.6	626.9	614.2	601.5	588.8	572.4	552.3	532.3	512.2	492.2	477.5
65°	560.9	547.8	534.7	521.5	508.4	492.1	472.5	453.0	433.4	413.8	400.7
67.5°	479.2	466.7	454.1	441.5	429.0	413.5	395.4	377.3	359.1	341.0	329.7
70°	427.6	414.7	401.9	389.1	376.3	361.1	343.7	326.3	308.9	291.4	281.4
72.5°	372.6	361.0	349.4	337.8	326.1	312.1	295.7	279.2	262.8	246.3	237.7
75°	298.3	287.1	275.7	264.4	253.1	240.3	225.9	211.5	197.3	182.9	175.8
77.5°	223.0	213.4	203.8	194.2	184.6	174.0	162.4	150.8	139.2	127.6	123.5
80°	174.6	165.7	156.9	148.0	139.1	130.2	121.0	111.8	102.6	93.5	92.6
82.5°	132.9	124.7	116.6	108.4	100.3	93.6	88.3	83.1	77.8	72.6	71.9
85°	74.2	68.1	62.0	55.9	49.8	46.3	45.4	44.4	43.6	42.6	42.0
87.5°	26.0	24.5	23.2	21.7	20.3	19.7	19.9	20.0	20.1	20.3	20.4
90°	3.4	6.1	8.8	11.5	14.3	16.6	18.6	20.6	22.6	24.5	26.1
92.5°	23.9	27.0	30.1	33.2	36.4	38.7	40.0	41.4	42.8	44.3	45.1
95°	67.0	69.2	71.5	73.7	75.9	77.9	79.6	81.4	83.1	84.9	85.6
97.5°	117.0	118.8	120.6	122.3	124.2	126.1	128.1	130.2	132.2	134.2	135.1
100°	156.4	157.3	158.3	159.3	160.3	161.9	164.1	166.3	168.6	170.8	171.3
102.5°	197.4	197.9	198.2	198.6	199.0	200.2	202.2	204.3	206.3	208.4	209.1
105°	260.2	260.5	260.7	260.9	261.1	261.7	262.8	263.8	264.8	265.8	266.5
107.5°	326.1	326.3	326.7	326.9	327.3	327.4	327.6	327.8	328.0	328.0	328.7
110°	370.7	371.2	371.7	372.2	372.7	372.8	372.6	372.3	372.1	371.9	371.3



TEST NUMBER: P333110-935

CATALOG NUMBER: S124RDIW-S1195D1340U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	417.2	417.2	417.3	417.5	417.6	417.4	417.0	416.5	416.0	415.6	415.5
115°	486.8	486.8	486.8	486.8	486.8	486.6	486.1	485.6	485.1	484.6	484.4
117.5°	552.5	552.7	552.9	553.1	553.3	553.2	552.8	552.5	552.2	551.8	551.0
120°	596.2	597.3	598.2	599.3	600.2	600.4	599.6	598.9	598.1	597.4	596.2
122.5°	641.8	642.2	642.7	643.0	643.4	643.4	643.1	642.7	642.4	642.0	641.2
125°	709.0	709.0	709.0	709.0	709.0	708.9	708.7	708.4	708.2	707.9	707.4
127.5°	770.0	770.8	771.5	772.2	773.0	773.2	772.7	772.4	772.0	771.5	771.1
130°	812.9	813.6	814.4	815.1	815.9	816.2	816.2	816.2	816.2	816.2	815.7
132.5°	856.7	857.2	857.7	858.3	858.8	859.0	858.8	858.6	858.4	858.2	857.7
135°	914.5	916.0	917.5	918.9	920.5	921.2	921.2	921.2	921.2	921.2	920.8
137.5°	977.5	978.2	978.9	979.6	980.2	980.9	981.2	981.6	982.0	982.4	981.7
140°	1019.5	1019.9	1020.5	1021.0	1021.5	1021.7	1021.7	1021.7	1021.7	1021.7	1021.5
142.5°	1057.9	1058.3	1058.9	1059.4	1059.9	1060.0	1059.8	1059.6	1059.5	1059.2	1059.2
145°	1111.0	1112.1	1113.0	1114.0	1115.0	1115.6	1115.9	1116.1	1116.4	1116.6	1116.4
147.5°	1163.7	1164.9	1166.1	1167.3	1168.5	1169.0	1168.8	1168.6	1168.4	1168.2	1168.0
150°	1195.9	1196.9	1197.9	1198.9	1199.9	1200.3	1200.3	1200.3	1200.3	1200.3	1200.3
152.5°	1226.2	1226.8	1227.4	1228.0	1228.6	1229.1	1229.2	1229.4	1229.7	1229.9	1230.5
155°	1272.9	1272.9	1272.9	1272.9	1272.9	1272.8	1272.6	1272.3	1272.0	1271.9	1272.8
157.5°	1312.3	1311.8	1311.4	1310.9	1310.4	1310.2	1310.2	1310.1	1310.1	1310.0	1310.8
160°	1335.5	1335.2	1335.0	1334.7	1334.5	1334.2	1333.9	1333.8	1333.5	1333.3	1333.9
162.5°	1356.9	1356.2	1355.6	1355.0	1354.4	1353.9	1353.7	1353.4	1353.1	1352.9	1354.3
165°	1385.7	1385.0	1384.2	1383.5	1382.8	1382.2	1381.6	1381.1	1380.6	1380.1	1381.6
167.5°	1407.8	1406.8	1405.8	1404.7	1403.7	1403.2	1403.3	1403.3	1403.3	1403.3	1404.9
170°	1420.3	1419.1	1417.9	1416.6	1415.4	1414.9	1415.1	1415.4	1415.7	1415.8	1417.4
172.5°	1429.3	1428.2	1427.2	1426.2	1425.1	1424.6	1424.7	1424.7	1424.8	1424.8	1426.5
175°	1441.6	1440.3	1439.1	1437.9	1436.6	1435.8	1435.6	1435.4	1435.1	1434.9	1436.6
177.5°	1445.5	1444.6	1443.6	1442.6	1441.6	1441.1	1441.1	1441.1	1441.1	1441.1	1442.5
180°	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8



TEST NUMBER: P333110-935

CATALOG NUMBER: S124RDIW-S1195D1340U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5
2.5°	1788.8	1791.6	1794.2	1795.4	1795.2	1794.9	1794.7	1794.5
5°	1776.9	1779.9	1783.0	1784.3	1783.6	1783.0	1782.4	1781.8
7.5°	1753.3	1755.2	1757.2	1757.6	1756.7	1755.8	1754.7	1753.8
10°	1732.0	1733.2	1734.5	1734.5	1733.2	1732.0	1730.8	1729.6
12.5°	1705.7	1706.5	1707.2	1706.7	1705.0	1703.3	1701.6	1699.9
15°	1659.6	1659.0	1658.4	1657.0	1654.8	1652.7	1650.6	1648.5
17.5°	1604.0	1602.3	1600.6	1598.2	1594.9	1591.6	1588.5	1585.2
20°	1565.2	1562.7	1560.3	1557.1	1553.2	1549.2	1545.2	1541.2
22.5°	1522.1	1518.4	1514.8	1511.3	1508.0	1504.8	1501.6	1498.3
25°	1452.4	1447.3	1442.1	1438.0	1434.9	1431.8	1428.7	1425.7
27.5°	1381.6	1375.1	1368.7	1363.3	1358.9	1354.5	1350.1	1345.7
30°	1330.7	1323.1	1315.4	1309.2	1304.2	1299.4	1294.5	1289.6
32.5°	1278.8	1269.9	1261.0	1254.3	1249.7	1245.0	1240.4	1235.7
35°	1201.4	1191.1	1180.7	1172.8	1167.3	1161.7	1156.2	1150.7
37.5°	1118.4	1106.8	1095.3	1086.7	1081.2	1075.6	1070.2	1064.7
40°	1063.2	1050.4	1037.6	1028.4	1022.9	1017.4	1011.9	1006.4
42.5°	1008.8	995.7	982.7	973.3	967.5	961.8	956.1	950.3
45°	925.6	910.6	895.6	885.4	879.9	874.4	868.9	863.4
47.5°	841.7	826.2	810.7	799.9	793.8	787.8	781.7	775.7
50°	786.1	770.9	755.5	745.0	739.3	733.4	727.6	721.8
52.5°	730.6	715.1	699.6	688.8	682.8	676.7	670.6	664.6
55°	648.8	632.9	617.0	606.1	600.4	594.5	588.8	582.9
57.5°	568.9	552.7	536.6	526.3	521.9	517.5	513.1	508.7
60°	515.4	499.6	483.6	473.3	468.4	463.5	458.6	453.7
62.5°	462.9	448.2	433.5	424.2	420.3	416.5	412.5	408.6
65°	387.5	374.4	361.3	352.8	349.2	345.5	341.9	338.2
67.5°	318.4	307.0	295.8	288.1	284.0	280.0	276.0	271.9
70°	271.3	261.2	251.2	244.6	241.5	238.5	235.4	232.4
72.5°	229.1	220.5	211.9	206.2	203.4	200.6	197.8	194.9
75°	168.8	161.8	154.7	150.3	148.5	146.6	144.8	143.0
77.5°	119.4	115.3	111.2	108.9	108.3	107.8	107.3	106.7
80°	91.7	90.7	89.8	89.2	88.9	88.6	88.3	88.0
82.5°	71.3	70.6	69.9	69.4	69.1	68.8	68.5	68.2
85°	41.4	40.8	40.2	39.9	39.9	39.9	39.9	39.9
87.5°	20.4	20.5	20.5	20.8	21.1	21.4	21.8	22.1
90°	27.6	29.0	30.5	31.5	32.0	32.5	33.0	33.5
92.5°	46.0	46.9	47.8	48.4	48.6	49.0	49.2	49.6
95°	86.4	87.1	87.8	88.3	88.3	88.3	88.3	88.3
97.5°	136.0	136.9	137.8	138.3	138.3	138.3	138.3	138.3
100°	171.9	172.4	172.8	173.1	173.1	173.1	173.1	173.1
102.5°	209.7	210.4	211.1	211.5	211.8	212.0	212.2	212.4
105°	267.3	268.0	268.7	269.5	270.2	271.0	271.7	272.4
107.5°	329.4	330.1	330.9	331.1	331.1	331.1	331.1	331.0
110°	370.8	370.3	369.9	370.0	370.7	371.4	372.2	373.0



TEST NUMBER: P333110-935

CATALOG NUMBER: S124RDIW-S1195D1340U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	415.4	415.3	415.2	415.3	415.3	415.5	415.7	415.9
115°	484.1	483.9	483.6	483.4	483.1	482.8	482.6	482.4
117.5°	550.2	549.3	548.5	547.8	547.3	546.8	546.3	545.8
120°	595.0	593.7	592.5	592.0	592.5	593.1	593.6	594.0
122.5°	640.3	639.6	638.7	637.8	636.9	636.0	635.2	634.2
125°	707.0	706.5	705.9	705.4	705.0	704.5	704.0	703.4
127.5°	770.6	770.1	769.6	769.1	768.8	768.4	767.9	767.6
130°	815.3	814.8	814.2	813.6	812.5	811.5	810.5	809.5
132.5°	857.2	856.8	856.3	855.8	855.4	855.0	854.6	854.2
135°	920.2	919.7	919.2	918.6	917.8	917.1	916.4	915.6
137.5°	981.1	980.5	979.8	979.6	979.7	979.9	980.0	980.2
140°	1021.2	1021.0	1020.7	1020.5	1020.2	1019.9	1019.7	1019.5
142.5°	1059.1	1059.1	1059.0	1058.9	1058.9	1058.9	1058.9	1058.8
145°	1116.1	1115.9	1115.6	1115.2	1114.4	1113.6	1112.9	1112.2
147.5°	1167.8	1167.6	1167.4	1167.2	1166.9	1166.7	1166.5	1166.2
150°	1200.3	1200.3	1200.3	1200.2	1200.0	1199.7	1199.5	1199.3
152.5°	1231.1	1231.7	1232.3	1232.2	1231.6	1230.9	1230.3	1229.6
155°	1273.8	1274.8	1275.8	1275.8	1274.8	1273.8	1272.8	1271.9
157.5°	1311.5	1312.3	1313.0	1312.9	1312.1	1311.2	1310.4	1309.6
160°	1334.7	1335.5	1336.2	1335.9	1334.7	1333.5	1332.2	1331.0
162.5°	1355.6	1356.9	1358.2	1358.3	1357.0	1355.8	1354.6	1353.3
165°	1383.1	1384.6	1386.1	1386.4	1385.3	1384.3	1383.4	1382.3
167.5°	1406.4	1407.8	1409.3	1409.3	1407.7	1406.2	1404.7	1403.2
170°	1418.8	1420.3	1421.9	1421.7	1420.0	1418.2	1416.5	1414.8
172.5°	1428.1	1429.9	1431.6	1431.5	1429.8	1428.1	1426.3	1424.6
175°	1438.3	1440.0	1441.8	1441.8	1440.0	1438.3	1436.6	1434.9
177.5°	1443.9	1445.3	1446.7	1446.6	1445.0	1443.4	1441.8	1440.2
180°	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8

(END OF REPORT)