

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333034-935

Luminaire Tested: **S124RDIW-S350D1560U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333034-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S350D1560U935-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5892.0 lumens
Efficiency: N/A
Efficacy: 110.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333034-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333034-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	29	29	29	21
1	91	87	84	80	81	77	74	72	59	57	55	42	41	40	26	26	25	18
2	83	76	70	66	73	68	63	59	52	48	46	37	35	33	23	22	21	15
3	76	67	60	55	67	60	54	49	46	42	38	33	30	28	21	19	18	13
4	69	59	52	46	61	53	46	42	40	36	33	29	26	24	18	17	16	11
5	64	53	45	39	56	47	40	36	36	32	28	26	23	21	17	15	14	10
6	58	47	39	34	52	42	35	31	32	28	24	23	20	18	15	13	12	9
7	54	42	35	30	48	38	31	27	29	25	21	21	18	16	14	12	11	8
8	50	38	31	26	44	34	28	24	27	22	19	19	16	14	13	11	10	7
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	6
10	43	32	25	20	38	28	23	19	22	18	15	16	13	11	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4297	4297	4297
5°	4306	4254	4280
10°	4279	4203	4203
15°	4231	4115	4084
20°	4163	3998	3924
25°	4077	3862	3764
30°	3993	3719	3564
35°	3900	3571	3362
40°	3789	3402	3144
45°	3685	3234	2923
50°	3567	3041	2688
55°	3441	2839	2432
60°	3303	2619	2172
65°	3177	2344	1914
70°	2991	2039	1626
75°	2757	1691	1323
80°	2404	1288	1213
85°	2038	1176	1093



TEST NUMBER: P333034-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.0	0.8
10°-20°	139.4	2.4
20°-30°	201.3	3.4
30°-40°	228.2	3.9
40°-50°	220.4	3.7
50°-60°	183.2	3.1
60°-70°	126.5	2.1
70°-80°	64.1	1.1
80°-90°	21.5	0.4
90°-100°	110.7	1.9
100°-110°	328.0	5.6
110°-120°	556.7	9.4
120°-130°	734.0	12.5
130°-140°	824.4	14.0
140°-150°	810.1	13.7
150°-160°	681.3	11.6
160°-170°	453.3	7.7
170°-180°	158.7	2.7
0°-30°	390.7	6.6
0°-40°	619.0	10.5
0°-60°	1022.6	17.4
0°-90°	1234.7	21.0
90°-120°	995.4	16.9
90°-150°	3363.9	57.1
90°-180°	4657.0	79.0
0°-180°	5892.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	532	532	532	532	532	
5°	531	530	525	529	528	50
15°	506	502	492	491	489	143
25°	458	450	434	427	423	211
35°	396	382	362	349	341	247
45°	323	307	283	264	256	249
55°	244	228	202	181	173	219
65°	166	148	123	106	100	164
75°	88	73	54	45	42	93
85°	22	14	13	12	12	25
90°	4	18	29	36	39	6
95°	78	89	99	102	102	87
105°	302	304	309	313	317	321
115°	566	566	563	562	561	558
125°	824	824	823	820	818	734
135°	1063	1071	1071	1068	1064	822
145°	1292	1297	1298	1297	1293	808
155°	1480	1480	1479	1483	1479	681
165°	1611	1607	1605	1612	1607	454
175°	1676	1670	1668	1676	1668	159
180°	1679	1679	1679	1679	1679	



TEST NUMBER: P333034-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3
2.5°	533.6	533.2	533.0	532.7	532.4	531.8	531.1	530.3	529.4	528.7	529.4
5°	531.4	531.1	530.7	530.4	529.9	529.3	528.1	527.1	526.0	525.0	525.8
7.5°	526.6	526.2	525.9	525.5	525.1	524.2	522.8	521.3	520.0	518.6	519.1
10°	522.0	521.6	521.2	520.7	520.2	519.2	517.5	515.9	514.3	512.7	513.1
12.5°	516.2	515.7	515.1	514.6	514.1	512.9	510.9	509.0	507.1	505.1	505.4
15°	506.2	505.3	504.5	503.7	502.9	501.4	499.1	496.8	494.6	492.3	492.1
17.5°	494.0	492.8	491.6	490.5	489.3	487.3	484.7	481.9	479.2	476.5	476.0
20°	484.6	483.4	482.2	481.0	479.8	477.8	474.7	471.6	468.5	465.4	464.7
22.5°	474.2	472.8	471.5	470.2	468.8	466.5	463.2	459.9	456.7	453.3	452.3
25°	457.7	456.1	454.4	452.8	451.2	448.5	444.8	441.1	437.3	433.6	432.0
27.5°	440.4	438.3	436.3	434.3	432.2	429.2	425.2	421.3	417.3	413.4	411.4
30°	428.3	426.0	423.8	421.5	419.3	416.0	411.7	407.5	403.2	399.0	396.7
32.5°	415.6	413.0	410.5	407.9	405.4	401.9	397.5	393.1	388.7	384.4	381.7
35°	395.7	392.8	389.9	387.0	384.1	380.4	375.9	371.3	366.9	362.3	359.2
37.5°	374.4	371.4	368.5	365.5	362.5	358.5	353.4	348.4	343.5	338.5	335.0
40°	359.5	356.5	353.4	350.5	347.5	343.5	338.3	333.1	328.0	322.8	319.0
42.5°	345.1	342.0	338.8	335.7	332.6	328.3	323.0	317.5	312.2	306.8	302.9
45°	322.8	319.4	316.1	312.7	309.4	305.0	299.5	294.1	288.7	283.3	278.8
47.5°	299.7	296.3	292.8	289.3	285.9	281.3	275.7	270.0	264.3	258.7	254.1
50°	284.0	280.5	277.0	273.5	269.9	265.3	259.5	253.7	247.9	242.1	237.5
52.5°	268.1	264.6	261.1	257.7	254.3	249.5	243.6	237.6	231.7	225.8	221.2
55°	244.5	240.9	237.3	233.7	230.1	225.2	219.4	213.5	207.6	201.7	197.0
57.5°	221.2	217.4	213.7	209.9	206.1	201.4	195.5	189.8	184.0	178.1	173.4
60°	204.6	201.0	197.3	193.7	190.1	185.4	179.6	173.7	168.0	162.2	157.5
62.5°	189.6	185.8	182.0	178.3	174.5	169.7	163.8	157.8	151.9	145.9	141.5
65°	166.3	162.4	158.5	154.6	150.7	145.9	140.1	134.2	128.5	122.7	118.8
67.5°	142.1	138.4	134.6	130.9	127.2	122.6	117.2	111.8	106.4	101.1	97.7
70°	126.7	123.0	119.2	115.4	111.5	107.0	101.9	96.7	91.5	86.4	83.4
72.5°	110.5	107.0	103.6	100.1	96.7	92.6	87.6	82.7	77.9	73.0	70.5
75°	88.4	85.1	81.7	78.4	75.0	71.2	67.0	62.7	58.5	54.2	52.1
77.5°	66.1	63.3	60.4	57.6	54.8	51.6	48.1	44.7	41.2	37.8	36.6
80°	51.7	49.2	46.5	43.9	41.2	38.6	35.9	33.1	30.4	27.7	27.5
82.5°	39.3	36.9	34.5	32.1	29.7	27.7	26.2	24.6	23.1	21.5	21.4
85°	22.0	20.2	18.4	16.5	14.7	13.7	13.4	13.2	12.9	12.7	12.5
87.5°	8.3	8.4	8.4	8.4	8.5	8.7	9.1	9.5	9.9	10.2	10.6
90°	3.9	7.1	10.2	13.4	16.6	19.4	21.6	23.9	26.3	28.6	30.3
92.5°	27.8	31.4	35.0	38.7	42.4	44.9	46.6	48.2	49.8	51.4	52.4
95°	77.9	80.5	83.1	85.7	88.3	90.6	92.6	94.6	96.7	98.7	99.5
97.5°	136.0	138.1	140.2	142.3	144.4	146.6	149.0	151.3	153.7	156.0	157.0
100°	181.8	182.9	184.1	185.2	186.4	188.2	190.9	193.5	196.0	198.6	199.2
102.5°	229.5	230.0	230.5	230.9	231.4	232.8	235.1	237.5	239.9	242.3	243.1
105°	302.5	302.8	303.1	303.3	303.7	304.4	305.5	306.7	307.8	309.0	309.9
107.5°	379.1	379.4	379.8	380.1	380.5	380.7	380.9	381.1	381.3	381.4	382.2
110°	431.0	431.6	432.1	432.7	433.3	433.5	433.2	432.9	432.6	432.3	431.7



TEST NUMBER: P333034-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	485.0	485.2	485.3	485.3	485.5	485.3	484.7	484.2	483.7	483.2	483.1
115°	566.0	566.0	566.0	566.0	566.0	565.8	565.2	564.6	564.0	563.4	563.2
117.5°	642.4	642.6	642.8	643.1	643.3	643.3	642.8	642.4	642.0	641.6	640.6
120°	693.3	694.4	695.6	696.7	697.8	698.0	697.2	696.3	695.4	694.6	693.1
122.5°	746.2	746.7	747.2	747.6	748.0	748.1	747.7	747.3	746.9	746.5	745.5
125°	824.4	824.4	824.4	824.4	824.4	824.2	824.0	823.6	823.4	823.1	822.5
127.5°	895.3	896.1	897.0	897.9	898.7	899.0	898.5	898.0	897.6	897.1	896.5
130°	945.1	946.0	946.8	947.7	948.6	949.0	949.0	949.0	949.0	949.0	948.5
132.5°	996.0	996.7	997.3	997.9	998.6	998.8	998.5	998.3	998.1	997.8	997.3
135°	1063.2	1065.0	1066.7	1068.5	1070.2	1071.1	1071.1	1071.1	1071.1	1071.1	1070.5
137.5°	1136.5	1137.3	1138.1	1138.9	1139.7	1140.4	1140.8	1141.3	1141.8	1142.2	1141.4
140°	1185.3	1185.9	1186.5	1187.1	1187.6	1187.9	1187.9	1187.9	1187.9	1187.9	1187.6
142.5°	1229.9	1230.5	1231.1	1231.7	1232.3	1232.4	1232.2	1232.0	1231.7	1231.5	1231.5
145°	1291.8	1292.9	1294.1	1295.2	1296.4	1297.1	1297.4	1297.7	1298.0	1298.2	1298.0
147.5°	1353.1	1354.4	1355.8	1357.2	1358.6	1359.2	1358.9	1358.7	1358.5	1358.2	1358.0
150°	1390.4	1391.5	1392.8	1393.9	1395.1	1395.6	1395.6	1395.6	1395.6	1395.6	1395.6
152.5°	1425.7	1426.4	1427.1	1427.8	1428.5	1429.0	1429.2	1429.4	1429.7	1429.9	1430.6
155°	1480.0	1480.0	1480.0	1480.0	1480.0	1479.9	1479.5	1479.3	1479.0	1478.7	1479.9
157.5°	1525.7	1525.2	1524.7	1524.1	1523.6	1523.4	1523.3	1523.2	1523.2	1523.1	1524.0
160°	1552.7	1552.4	1552.1	1551.9	1551.5	1551.3	1551.0	1550.7	1550.4	1550.1	1551.0
162.5°	1577.6	1576.9	1576.1	1575.4	1574.6	1574.1	1573.8	1573.6	1573.2	1573.0	1574.5
165°	1611.1	1610.2	1609.4	1608.5	1607.7	1607.0	1606.4	1605.8	1605.2	1604.6	1606.4
167.5°	1636.8	1635.6	1634.4	1633.2	1632.0	1631.4	1631.5	1631.5	1631.6	1631.7	1633.4
170°	1651.4	1649.9	1648.5	1647.0	1645.6	1645.0	1645.3	1645.6	1645.9	1646.1	1647.9
172.5°	1661.7	1660.5	1659.3	1658.1	1656.9	1656.3	1656.4	1656.5	1656.5	1656.6	1658.5
175°	1676.0	1674.6	1673.2	1671.7	1670.3	1669.4	1669.1	1668.8	1668.5	1668.3	1670.3
177.5°	1680.7	1679.6	1678.4	1677.2	1676.1	1675.5	1675.5	1675.5	1675.5	1675.5	1677.1
180°	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6



TEST NUMBER: P333034-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3
2.5°	530.3	531.1	531.8	532.2	532.1	532.1	532.0	531.9
5°	526.8	527.6	528.6	528.9	528.7	528.6	528.3	528.1
7.5°	519.7	520.3	520.9	521.0	520.7	520.5	520.1	519.9
10°	513.4	513.8	514.1	514.1	513.8	513.4	513.1	512.7
12.5°	505.6	505.8	506.1	505.9	505.4	504.9	504.4	503.9
15°	492.0	491.8	491.5	491.2	490.5	489.9	489.3	488.6
17.5°	475.4	475.0	474.5	473.7	472.8	471.8	470.9	469.9
20°	464.0	463.2	462.5	461.6	460.4	459.2	458.1	456.8
22.5°	451.2	450.0	449.0	448.0	447.0	446.1	445.1	444.1
25°	430.5	429.0	427.5	426.3	425.3	424.4	423.5	422.6
27.5°	409.5	407.6	405.7	404.2	402.8	401.5	400.2	398.9
30°	394.4	392.2	389.9	388.1	386.6	385.2	383.7	382.3
32.5°	379.1	376.4	373.8	371.8	370.4	369.0	367.6	366.3
35°	356.1	353.1	350.0	347.7	346.0	344.4	342.8	341.1
37.5°	331.6	328.1	324.7	322.1	320.5	318.8	317.2	315.6
40°	315.1	311.3	307.5	304.9	303.2	301.6	300.0	298.3
42.5°	299.0	295.2	291.3	288.5	286.8	285.1	283.4	281.7
45°	274.4	269.9	265.4	262.4	260.8	259.2	257.5	256.0
47.5°	249.5	244.9	240.3	237.1	235.3	233.5	231.7	230.0
50°	233.0	228.5	223.9	220.8	219.1	217.4	215.7	214.0
52.5°	216.5	212.0	207.4	204.1	202.4	200.6	198.8	197.0
55°	192.3	187.6	182.9	179.7	178.0	176.2	174.5	172.8
57.5°	168.6	163.8	159.0	156.0	154.7	153.4	152.1	150.8
60°	152.7	148.1	143.4	140.3	138.8	137.4	136.0	134.5
62.5°	137.2	132.9	128.5	125.8	124.6	123.5	122.3	121.1
65°	114.9	111.0	107.1	104.6	103.5	102.5	101.3	100.2
67.5°	94.4	91.0	87.6	85.4	84.2	83.0	81.8	80.6
70°	80.4	77.4	74.5	72.5	71.5	70.7	69.7	68.9
72.5°	67.9	65.3	62.9	61.1	60.3	59.5	58.6	57.8
75°	50.0	48.0	45.9	44.6	44.0	43.5	43.0	42.4
77.5°	35.4	34.2	33.0	32.3	32.1	31.9	31.8	31.6
80°	27.2	26.9	26.6	26.4	26.3	26.3	26.2	26.1
82.5°	21.1	20.9	20.8	20.6	20.5	20.4	20.3	20.2
85°	12.3	12.1	11.9	11.8	11.8	11.8	11.8	11.8
87.5°	10.8	11.1	11.4	11.6	11.8	12.0	12.1	12.3
90°	32.0	33.8	35.5	36.7	37.2	37.8	38.4	38.9
92.5°	53.5	54.5	55.5	56.2	56.6	56.9	57.3	57.6
95°	100.4	101.3	102.1	102.5	102.5	102.5	102.5	102.5
97.5°	158.2	159.2	160.2	160.7	160.7	160.7	160.7	160.7
100°	199.8	200.4	201.0	201.2	201.2	201.2	201.2	201.2
102.5°	243.8	244.7	245.5	246.0	246.2	246.5	246.7	246.9
105°	310.7	311.6	312.5	313.3	314.2	315.0	315.9	316.8
107.5°	383.1	383.8	384.7	385.0	385.0	385.0	384.9	384.8
110°	431.2	430.6	430.0	430.2	431.0	431.9	432.7	433.6



TEST NUMBER: P333034-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	482.9	482.8	482.8	482.8	482.9	483.1	483.3	483.5
115°	562.8	562.6	562.3	562.0	561.7	561.5	561.1	560.9
117.5°	639.6	638.7	637.7	636.9	636.3	635.8	635.2	634.6
120°	691.6	690.3	688.8	688.4	689.0	689.5	690.1	690.7
122.5°	744.5	743.6	742.6	741.6	740.5	739.5	738.5	737.4
125°	821.9	821.4	820.8	820.2	819.6	819.1	818.5	817.9
127.5°	896.0	895.4	894.8	894.2	893.8	893.4	892.9	892.4
130°	947.9	947.3	946.7	945.8	944.7	943.6	942.4	941.2
132.5°	996.7	996.1	995.5	995.0	994.5	994.1	993.6	993.2
135°	1069.9	1069.4	1068.8	1068.0	1067.1	1066.3	1065.4	1064.5
137.5°	1140.7	1140.0	1139.2	1138.9	1139.1	1139.3	1139.4	1139.6
140°	1187.3	1187.1	1186.7	1186.5	1186.2	1185.9	1185.6	1185.3
142.5°	1231.4	1231.3	1231.3	1231.2	1231.1	1231.1	1231.1	1231.0
145°	1297.7	1297.4	1297.1	1296.5	1295.6	1294.8	1293.9	1293.0
147.5°	1357.8	1357.5	1357.3	1357.0	1356.8	1356.5	1356.2	1355.9
150°	1395.6	1395.6	1395.6	1395.5	1395.2	1394.9	1394.6	1394.3
152.5°	1431.2	1431.9	1432.6	1432.6	1431.8	1431.2	1430.4	1429.6
155°	1481.0	1482.1	1483.3	1483.3	1482.1	1481.0	1479.9	1478.7
157.5°	1524.8	1525.7	1526.6	1526.5	1525.5	1524.6	1523.5	1522.6
160°	1551.9	1552.7	1553.6	1553.2	1551.9	1550.4	1548.9	1547.5
162.5°	1576.1	1577.6	1579.2	1579.2	1577.8	1576.4	1574.9	1573.5
165°	1608.1	1609.8	1611.5	1611.9	1610.7	1609.6	1608.3	1607.2
167.5°	1635.1	1636.8	1638.6	1638.6	1636.8	1635.0	1633.1	1631.3
170°	1649.7	1651.4	1653.1	1652.9	1651.0	1648.9	1646.9	1644.9
172.5°	1660.5	1662.4	1664.4	1664.4	1662.3	1660.4	1658.3	1656.3
175°	1672.3	1674.3	1676.4	1676.4	1674.3	1672.3	1670.3	1668.3
177.5°	1678.8	1680.3	1682.0	1681.9	1680.0	1678.2	1676.4	1674.5
180°	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6

(END OF REPORT)