

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333018-935

Luminaire Tested: **S124RDIW-S350D470U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333018-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S350D470U935-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2630.8 lumens
Efficiency: N/A
Efficacy: 114.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 23
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333018-935

CATALOG NUMBER: S124RDIW-S350D470U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333018-935

CATALOG NUMBER: S124RDIW-S350D470U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47
1	97	93	89	86	89	86	82	80	72	70	67	59	58	56	47	46	45	40
2	89	82	76	71	81	75	70	66	63	59	56	52	50	47	42	40	39	34
3	81	72	65	59	74	66	60	55	56	51	48	46	43	40	37	35	33	29
4	74	64	56	50	68	59	52	47	50	45	41	41	38	35	34	31	29	25
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	30	27	25	22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22	19
7	58	46	38	33	53	43	36	31	37	31	27	31	27	23	25	22	20	17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16	14
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4297	4297	4297
5°	4306	4254	4280
10°	4279	4203	4203
15°	4231	4115	4084
20°	4163	3998	3924
25°	4077	3862	3764
30°	3993	3719	3564
35°	3900	3571	3362
40°	3789	3402	3144
45°	3685	3234	2923
50°	3567	3041	2688
55°	3441	2839	2432
60°	3303	2619	2172
65°	3177	2344	1914
70°	2991	2039	1626
75°	2757	1691	1323
80°	2404	1288	1213
85°	2038	1176	1093



TEST NUMBER: P333018-935

CATALOG NUMBER: S124RDIW-S350D470U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.0	1.9
10°-20°	139.4	5.3
20°-30°	201.3	7.7
30°-40°	228.2	8.7
40°-50°	220.4	8.4
50°-60°	183.2	7.0
60°-70°	126.5	4.8
70°-80°	64.1	2.4
80°-90°	18.0	0.7
90°-100°	33.3	1.3
100°-110°	98.6	3.7
110°-120°	167.3	6.4
120°-130°	220.6	8.4
130°-140°	247.7	9.4
140°-150°	243.4	9.3
150°-160°	204.8	7.8
160°-170°	136.2	5.2
170°-180°	47.7	1.8
0°-30°	390.7	14.9
0°-40°	619.0	23.5
0°-60°	1022.6	38.9
0°-90°	1231.2	46.8
90°-120°	299.1	11.4
90°-150°	1010.9	38.4
90°-180°	1400.0	53.2
0°-180°	2630.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	532	532	532	532	532	
5°	531	530	525	529	528	50
15°	506	502	492	491	489	143
25°	458	450	434	427	423	211
35°	396	382	362	349	341	247
45°	323	307	283	264	256	249
55°	244	228	202	181	173	219
65°	166	148	123	106	100	164
75°	88	73	54	45	42	93
85°	22	14	13	12	12	25
90°	1	5	9	11	12	3
95°	23	27	30	31	31	26
105°	91	91	93	94	95	96
115°	170	170	169	169	169	168
125°	248	248	247	247	246	221
135°	320	322	322	321	320	247
145°	388	390	390	390	389	243
155°	445	445	444	446	444	205
165°	484	483	482	484	483	136
175°	504	502	501	504	501	48
180°	504	504	504	504	504	



TEST NUMBER: P333018-935

CATALOG NUMBER: S124RDIW-S350D470U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3
2.5°	533.6	533.2	533.0	532.7	532.4	531.8	531.1	530.3	529.4	528.7	529.4
5°	531.4	531.1	530.7	530.4	529.9	529.3	528.1	527.1	526.0	525.0	525.8
7.5°	526.6	526.2	525.9	525.5	525.1	524.2	522.8	521.3	520.0	518.6	519.1
10°	522.0	521.6	521.2	520.7	520.2	519.2	517.5	515.9	514.3	512.7	513.1
12.5°	516.2	515.7	515.1	514.6	514.1	512.9	510.9	509.0	507.1	505.1	505.4
15°	506.2	505.3	504.5	503.7	502.9	501.4	499.1	496.8	494.6	492.3	492.1
17.5°	494.0	492.8	491.6	490.5	489.3	487.3	484.7	481.9	479.2	476.5	476.0
20°	484.6	483.4	482.2	481.0	479.8	477.8	474.7	471.6	468.5	465.4	464.7
22.5°	474.2	472.8	471.5	470.2	468.8	466.5	463.2	459.9	456.7	453.3	452.3
25°	457.7	456.1	454.4	452.8	451.2	448.5	444.8	441.1	437.3	433.6	432.0
27.5°	440.4	438.3	436.3	434.3	432.2	429.2	425.2	421.3	417.3	413.4	411.4
30°	428.3	426.0	423.8	421.5	419.3	416.0	411.7	407.5	403.2	399.0	396.7
32.5°	415.6	413.0	410.5	407.9	405.4	401.9	397.5	393.1	388.7	384.4	381.7
35°	395.7	392.8	389.9	387.0	384.1	380.4	375.9	371.3	366.9	362.3	359.2
37.5°	374.4	371.4	368.5	365.5	362.5	358.5	353.4	348.4	343.5	338.5	335.0
40°	359.5	356.5	353.4	350.5	347.5	343.5	338.3	333.1	328.0	322.8	319.0
42.5°	345.1	342.0	338.8	335.7	332.6	328.3	323.0	317.5	312.2	306.8	302.9
45°	322.8	319.4	316.1	312.7	309.4	305.0	299.5	294.1	288.7	283.3	278.8
47.5°	299.7	296.3	292.8	289.3	285.9	281.3	275.7	270.0	264.3	258.7	254.1
50°	284.0	280.5	277.0	273.5	269.9	265.3	259.5	253.7	247.9	242.1	237.5
52.5°	268.1	264.6	261.1	257.7	254.3	249.5	243.6	237.6	231.7	225.8	221.2
55°	244.5	240.9	237.3	233.7	230.1	225.2	219.4	213.5	207.6	201.7	197.0
57.5°	221.2	217.4	213.7	209.9	206.1	201.4	195.5	189.8	184.0	178.1	173.4
60°	204.6	201.0	197.3	193.7	190.1	185.4	179.6	173.7	168.0	162.2	157.5
62.5°	189.6	185.8	182.0	178.3	174.5	169.7	163.8	157.8	151.9	145.9	141.5
65°	166.3	162.4	158.5	154.6	150.7	145.9	140.1	134.2	128.5	122.7	118.8
67.5°	142.1	138.4	134.6	130.9	127.2	122.6	117.2	111.8	106.4	101.1	97.7
70°	126.7	123.0	119.2	115.4	111.5	107.0	101.9	96.7	91.5	86.4	83.4
72.5°	110.5	107.0	103.6	100.1	96.7	92.6	87.6	82.7	77.9	73.0	70.5
75°	88.4	85.1	81.7	78.4	75.0	71.2	67.0	62.7	58.5	54.2	52.1
77.5°	66.1	63.3	60.4	57.6	54.8	51.6	48.1	44.7	41.2	37.8	36.6
80°	51.7	49.2	46.5	43.9	41.2	38.6	35.9	33.1	30.4	27.7	27.5
82.5°	39.3	36.9	34.5	32.1	29.7	27.7	26.2	24.6	23.1	21.5	21.4
85°	22.0	20.2	18.4	16.5	14.7	13.7	13.4	13.2	12.9	12.7	12.5
87.5°	7.7	7.3	7.0	6.5	6.2	6.0	6.1	6.1	6.2	6.3	6.3
90°	1.2	2.2	3.1	4.0	5.0	5.8	6.5	7.2	7.9	8.6	9.1
92.5°	8.4	9.5	10.5	11.6	12.7	13.5	14.0	14.5	15.0	15.4	15.8
95°	23.4	24.2	25.0	25.7	26.5	27.2	27.8	28.4	29.0	29.6	29.9
97.5°	40.9	41.5	42.1	42.8	43.4	44.1	44.8	45.5	46.1	46.9	47.2
100°	54.6	54.9	55.3	55.6	56.1	56.6	57.3	58.1	58.9	59.7	59.8
102.5°	69.0	69.1	69.2	69.4	69.6	70.0	70.7	71.4	72.1	72.8	73.0
105°	90.9	91.0	91.1	91.2	91.3	91.4	91.8	92.1	92.5	92.8	93.1
107.5°	113.9	114.0	114.2	114.3	114.3	114.4	114.5	114.5	114.6	114.6	114.9
110°	129.5	129.7	129.8	130.0	130.2	130.3	130.2	130.1	130.0	129.9	129.8



TEST NUMBER: P333018-935

CATALOG NUMBER: S124RDIW-S350D470U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	145.8	145.8	145.9	145.9	145.9	145.9	145.7	145.5	145.3	145.3	145.2
115°	170.1	170.1	170.1	170.1	170.1	170.0	169.9	169.7	169.5	169.4	169.3
117.5°	193.0	193.1	193.2	193.3	193.3	193.3	193.2	193.0	193.0	192.8	192.5
120°	208.4	208.7	209.1	209.4	209.7	209.7	209.5	209.2	209.0	208.7	208.3
122.5°	224.3	224.4	224.5	224.6	224.8	224.8	224.7	224.5	224.5	224.4	224.0
125°	247.7	247.7	247.7	247.7	247.7	247.7	247.6	247.5	247.5	247.4	247.2
127.5°	269.1	269.3	269.6	269.8	270.1	270.2	270.0	269.8	269.8	269.6	269.4
130°	284.0	284.3	284.6	284.8	285.1	285.2	285.2	285.2	285.2	285.2	285.0
132.5°	299.3	299.5	299.7	299.9	300.1	300.1	300.1	300.0	300.0	299.9	299.7
135°	319.5	320.0	320.6	321.1	321.6	321.8	321.8	321.8	321.8	321.8	321.7
137.5°	341.6	341.8	342.0	342.2	342.5	342.7	342.9	343.0	343.1	343.3	343.0
140°	356.2	356.4	356.5	356.7	356.9	357.0	357.0	357.0	357.0	357.0	356.9
142.5°	369.6	369.8	370.0	370.1	370.3	370.4	370.3	370.2	370.1	370.1	370.1
145°	388.2	388.6	388.9	389.3	389.6	389.8	389.9	389.9	390.0	390.1	390.0
147.5°	406.7	407.0	407.4	407.9	408.3	408.5	408.4	408.3	408.3	408.2	408.1
150°	417.8	418.2	418.5	418.9	419.2	419.4	419.4	419.4	419.4	419.4	419.4
152.5°	428.4	428.7	428.9	429.1	429.3	429.5	429.5	429.6	429.6	429.7	429.9
155°	444.8	444.8	444.8	444.8	444.8	444.7	444.6	444.5	444.4	444.4	444.7
157.5°	458.5	458.3	458.2	458.1	457.9	457.8	457.8	457.8	457.7	457.7	458.0
160°	466.7	466.6	466.5	466.4	466.3	466.2	466.1	466.1	466.0	465.9	466.1
162.5°	474.2	473.9	473.6	473.5	473.2	473.0	472.9	472.9	472.8	472.7	473.2
165°	484.1	483.9	483.6	483.4	483.1	482.9	482.8	482.6	482.4	482.2	482.8
167.5°	491.9	491.5	491.2	490.9	490.4	490.3	490.3	490.3	490.3	490.3	490.9
170°	496.3	495.8	495.4	495.0	494.6	494.4	494.5	494.6	494.6	494.7	495.2
172.5°	499.4	499.0	498.7	498.3	497.9	497.7	497.7	497.8	497.8	497.8	498.4
175°	503.7	503.3	502.8	502.4	502.0	501.7	501.6	501.5	501.4	501.4	502.0
177.5°	505.1	504.7	504.4	504.0	503.7	503.5	503.5	503.5	503.5	503.5	504.0
180°	504.5	504.5	504.5	504.5	504.5	504.5	504.5	504.5	504.5	504.5	504.5



TEST NUMBER: P333018-935

CATALOG NUMBER: S124RDIW-S350D470U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3
2.5°	530.3	531.1	531.8	532.2	532.1	532.1	532.0	531.9
5°	526.8	527.6	528.6	528.9	528.7	528.6	528.3	528.1
7.5°	519.7	520.3	520.9	521.0	520.7	520.5	520.1	519.9
10°	513.4	513.8	514.1	514.1	513.8	513.4	513.1	512.7
12.5°	505.6	505.8	506.1	505.9	505.4	504.9	504.4	503.9
15°	492.0	491.8	491.5	491.2	490.5	489.9	489.3	488.6
17.5°	475.4	475.0	474.5	473.7	472.8	471.8	470.9	469.9
20°	464.0	463.2	462.5	461.6	460.4	459.2	458.1	456.8
22.5°	451.2	450.0	449.0	448.0	447.0	446.1	445.1	444.1
25°	430.5	429.0	427.5	426.3	425.3	424.4	423.5	422.6
27.5°	409.5	407.6	405.7	404.2	402.8	401.5	400.2	398.9
30°	394.4	392.2	389.9	388.1	386.6	385.2	383.7	382.3
32.5°	379.1	376.4	373.8	371.8	370.4	369.0	367.6	366.3
35°	356.1	353.1	350.0	347.7	346.0	344.4	342.8	341.1
37.5°	331.6	328.1	324.7	322.1	320.5	318.8	317.2	315.6
40°	315.1	311.3	307.5	304.9	303.2	301.6	300.0	298.3
42.5°	299.0	295.2	291.3	288.5	286.8	285.1	283.4	281.7
45°	274.4	269.9	265.4	262.4	260.8	259.2	257.5	256.0
47.5°	249.5	244.9	240.3	237.1	235.3	233.5	231.7	230.0
50°	233.0	228.5	223.9	220.8	219.1	217.4	215.7	214.0
52.5°	216.5	212.0	207.4	204.1	202.4	200.6	198.8	197.0
55°	192.3	187.6	182.9	179.7	178.0	176.2	174.5	172.8
57.5°	168.6	163.8	159.0	156.0	154.7	153.4	152.1	150.8
60°	152.7	148.1	143.4	140.3	138.8	137.4	136.0	134.5
62.5°	137.2	132.9	128.5	125.8	124.6	123.5	122.3	121.1
65°	114.9	111.0	107.1	104.6	103.5	102.5	101.3	100.2
67.5°	94.4	91.0	87.6	85.4	84.2	83.0	81.8	80.6
70°	80.4	77.4	74.5	72.5	71.5	70.7	69.7	68.9
72.5°	67.9	65.3	62.9	61.1	60.3	59.5	58.6	57.8
75°	50.0	48.0	45.9	44.6	44.0	43.5	43.0	42.4
77.5°	35.4	34.2	33.0	32.3	32.1	31.9	31.8	31.6
80°	27.2	26.9	26.6	26.4	26.3	26.3	26.2	26.1
82.5°	21.1	20.9	20.8	20.6	20.5	20.4	20.3	20.2
85°	12.3	12.1	11.9	11.8	11.8	11.8	11.8	11.8
87.5°	6.4	6.4	6.4	6.5	6.5	6.7	6.8	6.9
90°	9.6	10.2	10.7	11.0	11.2	11.4	11.5	11.7
92.5°	16.1	16.4	16.7	16.9	17.0	17.1	17.2	17.3
95°	30.1	30.4	30.7	30.8	30.8	30.8	30.8	30.8
97.5°	47.5	47.9	48.1	48.3	48.3	48.3	48.3	48.3
100°	60.0	60.2	60.4	60.4	60.4	60.4	60.4	60.4
102.5°	73.3	73.5	73.8	74.0	74.0	74.0	74.1	74.2
105°	93.4	93.7	93.9	94.2	94.5	94.7	95.0	95.2
107.5°	115.1	115.4	115.6	115.7	115.7	115.7	115.6	115.6
110°	129.6	129.4	129.2	129.2	129.5	129.8	130.0	130.3



TEST NUMBER: P333018-935

CATALOG NUMBER: S124RDIW-S350D470U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	145.2	145.1	145.1	145.1	145.2	145.2	145.3	145.3
115°	169.2	169.1	169.0	168.9	168.8	168.8	168.7	168.6
117.5°	192.3	191.9	191.7	191.4	191.2	191.1	190.9	190.7
120°	207.8	207.4	207.0	206.9	207.1	207.2	207.4	207.6
122.5°	223.8	223.4	223.2	222.8	222.6	222.2	221.9	221.6
125°	247.0	246.8	246.7	246.5	246.3	246.2	246.0	245.8
127.5°	269.2	269.1	268.9	268.7	268.6	268.5	268.4	268.2
130°	284.8	284.6	284.5	284.2	283.9	283.5	283.2	282.8
132.5°	299.5	299.4	299.2	299.0	298.9	298.8	298.6	298.5
135°	321.5	321.3	321.2	321.0	320.7	320.5	320.2	319.9
137.5°	342.8	342.6	342.3	342.2	342.3	342.3	342.4	342.5
140°	356.8	356.7	356.6	356.5	356.5	356.4	356.3	356.2
142.5°	370.1	370.1	370.1	370.0	370.0	370.0	370.0	370.0
145°	389.9	389.9	389.8	389.6	389.3	389.1	388.8	388.6
147.5°	408.0	407.9	407.9	407.9	407.8	407.7	407.6	407.5
150°	419.4	419.4	419.4	419.4	419.3	419.2	419.1	419.0
152.5°	430.2	430.3	430.6	430.5	430.3	430.1	429.9	429.6
155°	445.1	445.4	445.7	445.7	445.4	445.1	444.7	444.4
157.5°	458.2	458.5	458.7	458.7	458.5	458.1	457.9	457.5
160°	466.4	466.7	466.9	466.8	466.4	466.0	465.5	465.0
162.5°	473.6	474.2	474.6	474.6	474.2	473.7	473.3	472.9
165°	483.3	483.8	484.3	484.4	484.1	483.7	483.4	483.0
167.5°	491.4	491.9	492.4	492.4	491.9	491.4	490.8	490.3
170°	495.8	496.3	496.8	496.7	496.1	495.5	494.9	494.3
172.5°	499.0	499.6	500.2	500.2	499.6	498.9	498.3	497.7
175°	502.6	503.2	503.8	503.8	503.2	502.6	502.0	501.4
177.5°	504.5	505.0	505.5	505.4	504.9	504.4	503.8	503.3
180°	504.5	504.5	504.5	504.5	504.5	504.5	504.5	504.5

(END OF REPORT)