

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333067-935

Luminaire Tested: **S124RDIW-S795D1340U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333067-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S795D1340U935-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7495.9 lumens
Efficiency: N/A
Efficacy: 122.1 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333067-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333067-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38								
1	96	91	88	84	87	83	80	77	68	66	64	54	52	51	41	40	39	33								
2	87	80	74	69	79	73	68	64	60	56	53	48	45	43	36	35	33	28								
3	80	71	64	58	72	65	59	54	53	49	45	42	39	37	32	30	29	24								
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25	21								
5	67	56	48	42	61	51	44	39	42	37	33	34	30	28	26	24	22	19								
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16								
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17	15								
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	18	16	13								
9	49	38	30	25	45	35	28	24	29	24	20	24	20	17	19	16	14	12								
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	17	15	13	11								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9175	9175	9175	9175
5°	10643	9203	8135	9203
10°	12591	9163	7260	9163
15°	14543	9078	6238	9078
20°	16192	8961	5642	8961
25°	16715	8847	5238	8847
30°	14632	8708	4994	8708
35°	11391	8502	4847	8502
40°	8541	8266	4769	8266
45°	6744	7889	4727	7889
50°	5693	7454	4589	7454
55°	4963	6973	4345	6973
60°	4466	6476	3846	6476
65°	3935	5939	3307	5939
70°	3545	5384	2984	5384
75°	2969	4769	2542	4769
80°	2515	4068	2385	4068
85°	2121	3186	2121	3186



TEST NUMBER: P333067-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.1	1.5
10°-20°	332.2	4.4
20°-30°	519.5	6.9
30°-40°	577.6	7.7
40°-50°	512.4	6.8
50°-60°	399.3	5.3
60°-70°	261.4	3.5
70°-80°	128.6	1.7
80°-90°	36.0	0.5
90°-100°	51.1	0.7
100°-110°	325.6	4.3
110°-120°	622.9	8.3
120°-130°	790.7	10.5
130°-140°	846.0	11.3
140°-150°	791.1	10.6
150°-160°	638.0	8.5
160°-170°	411.5	5.5
170°-180°	141.8	1.9
0°-30°	961.8	12.8
0°-40°	1539.4	20.5
0°-60°	2451.2	32.7
0°-90°	2877.2	38.4
90°-120°	999.5	13.3
90°-150°	3427.4	45.7
90°-180°	4619.0	61.6
0°-180°	7495.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1136	1136	1136	1136	1136	
5°	1313	1136	1004	1136	1313	133
15°	1740	1086	746	1086	1740	495
25°	1876	993	588	993	1876	832
35°	1156	863	492	863	1156	724
45°	591	691	414	691	591	468
55°	353	495	309	495	353	321
65°	206	311	173	311	206	207
75°	95	153	82	153	95	105
85°	23	34	23	34	23	27
90°	34	3	34	3	34	15
95°	32	61	32	61	32	26
105°	318	336	318	336	318	278
115°	632	628	632	628	632	626
125°	889	882	889	882	889	792
135°	1102	1094	1102	1094	1102	848
145°	1269	1262	1269	1262	1269	793
155°	1383	1384	1383	1384	1383	638
165°	1453	1460	1453	1460	1453	410
175°	1484	1493	1484	1493	1484	141
180°	1493	1493	1493	1493	1493	



TEST NUMBER: P333067-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1198.8	1202.1	1198.8	1198.4	1194.8	1193.7	1192.2	1187.5	1178.6	1173.5	1174.7
5°	1313.3	1324.7	1318.4	1317.4	1307.3	1297.3	1290.8	1276.2	1260.6	1250.1	1241.4
7.5°	1445.7	1452.3	1448.3	1441.8	1425.6	1416.3	1401.4	1382.2	1354.3	1332.9	1313.4
10°	1535.9	1541.4	1539.5	1527.6	1515.7	1491.4	1477.6	1450.7	1415.4	1387.5	1361.4
12.5°	1624.4	1630.4	1614.2	1614.8	1592.2	1573.1	1551.3	1517.3	1476.6	1440.6	1407.9
15°	1740.1	1732.8	1732.8	1723.5	1698.4	1671.8	1649.4	1613.7	1562.4	1519.3	1474.0
17.5°	1830.6	1833.1	1829.4	1807.8	1788.0	1760.5	1719.3	1677.7	1630.0	1572.3	1526.0
20°	1884.7	1884.7	1880.7	1866.0	1840.4	1811.0	1766.6	1721.3	1660.9	1602.7	1550.5
22.5°	1906.8	1908.2	1903.3	1891.3	1868.2	1839.6	1801.8	1755.8	1693.4	1628.0	1563.3
25°	1876.5	1885.2	1886.1	1882.9	1876.0	1858.6	1826.2	1779.0	1723.1	1652.2	1582.5
27.5°	1722.9	1733.8	1743.4	1759.3	1780.4	1791.3	1792.8	1768.8	1720.1	1651.7	1581.7
30°	1569.7	1578.9	1608.6	1647.5	1677.8	1705.3	1729.1	1735.5	1708.1	1646.7	1573.0
32.5°	1399.7	1412.2	1442.0	1483.8	1534.2	1580.7	1634.2	1661.5	1660.8	1623.9	1555.7
35°	1155.8	1164.9	1192.4	1236.4	1296.8	1366.0	1450.7	1516.6	1561.5	1558.2	1516.6
37.5°	932.1	942.5	970.3	1006.7	1065.3	1150.9	1232.9	1323.7	1406.7	1453.3	1439.4
40°	810.5	811.0	838.0	875.6	930.5	1005.1	1094.4	1195.2	1287.6	1363.2	1377.9
42.5°	714.5	714.6	732.5	772.9	812.5	882.8	968.0	1068.1	1176.3	1263.6	1302.4
45°	590.7	594.9	609.5	633.8	664.9	724.4	792.6	885.6	1006.9	1110.4	1175.0
47.5°	500.2	506.3	515.6	535.4	560.2	599.9	656.3	739.8	838.5	952.4	1044.2
50°	453.3	454.3	466.1	477.2	498.7	530.3	579.7	649.3	739.9	849.5	951.6
52.5°	413.0	412.8	420.0	433.9	451.4	476.0	516.0	579.4	659.8	757.9	863.2
55°	352.6	354.9	360.4	371.3	384.6	402.1	433.6	481.3	544.5	628.3	723.9
57.5°	306.6	307.8	312.1	316.8	329.0	341.6	365.3	398.4	451.7	520.3	609.5
60°	276.6	277.1	278.4	285.2	294.9	306.8	322.8	350.8	395.6	458.4	528.9
62.5°	247.3	248.1	250.2	255.2	262.7	270.9	287.7	310.1	347.2	400.9	464.4
65°	206.0	206.6	209.7	211.5	217.5	224.8	237.2	252.3	277.9	322.8	370.9
67.5°	172.2	172.2	172.4	174.9	178.9	183.8	191.2	203.3	222.7	250.2	292.6
70°	150.2	150.2	151.1	152.5	154.8	158.9	163.0	172.2	186.4	208.8	241.3
72.5°	129.7	130.0	131.0	131.2	132.4	135.8	138.9	144.7	155.2	172.2	198.5
75°	95.2	96.6	98.9	100.7	103.1	102.5	105.8	109.4	112.6	122.7	137.8
77.5°	70.9	70.2	70.4	72.0	72.2	72.8	75.0	77.8	80.2	85.0	90.4
80°	54.1	54.1	55.4	55.9	55.4	55.9	58.1	59.5	60.4	62.3	67.3
82.5°	40.8	41.6	41.2	41.6	41.8	42.3	44.3	44.5	45.5	46.1	48.3
85°	22.9	23.3	23.8	22.9	22.9	22.9	23.8	24.3	25.2	24.7	25.7
87.5°	14.7	14.3	14.6	14.5	14.7	14.2	14.2	14.6	13.6	13.7	13.3
90°	33.5	33.0	32.5	32.0	31.5	30.6	29.0	27.6	26.1	24.5	22.6
92.5°	30.8	30.7	30.7	30.6	30.4	29.6	28.2	26.7	25.1	23.7	21.7
95°	32.4	32.1	31.9	31.6	31.4	30.6	29.0	27.6	26.1	24.5	24.3
97.5°	31.3	31.0	30.7	30.6	30.3	30.0	30.0	29.8	29.6	29.4	57.2
100°	31.3	31.0	30.7	30.6	30.3	32.3	36.5	40.7	44.9	49.2	83.3
102.5°	32.2	32.1	32.0	32.0	31.9	54.7	100.2	145.8	191.2	236.8	241.3
105°	318.3	327.2	336.1	345.1	354.0	357.4	355.2	352.9	350.7	348.4	347.2
107.5°	443.6	442.6	441.7	440.7	439.8	438.8	437.7	436.6	435.5	434.5	432.7
110°	498.1	497.3	496.6	495.8	495.1	494.5	494.0	493.5	493.0	492.5	491.0



TEST NUMBER: P333067-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	552.6	551.6	550.7	549.7	548.8	548.4	548.5	548.5	548.7	548.8	548.1
115°	632.1	632.1	632.1	632.1	632.1	631.8	631.4	630.9	630.3	629.8	630.1
117.5°	712.9	713.1	713.2	713.3	713.3	713.4	713.5	713.6	713.8	713.9	713.3
120°	763.9	764.4	764.8	765.3	765.9	765.9	765.3	764.8	764.4	763.9	764.1
122.5°	813.9	814.4	814.9	815.4	815.9	816.0	815.7	815.4	815.1	814.8	814.4
125°	889.0	888.7	888.5	888.2	887.9	887.4	886.7	886.0	885.2	884.5	884.9
127.5°	954.8	955.0	955.2	955.5	955.6	955.8	956.0	956.1	956.2	956.4	955.3
130°	999.5	999.5	999.5	999.5	999.5	999.4	999.1	998.8	998.7	998.4	997.6
132.5°	1040.6	1040.8	1041.0	1041.2	1041.4	1041.4	1041.1	1040.9	1040.6	1040.3	1039.4
135°	1102.3	1101.7	1101.2	1100.8	1100.3	1099.8	1099.2	1098.8	1098.3	1097.8	1096.8
137.5°	1154.9	1155.1	1155.3	1155.4	1155.5	1155.4	1154.8	1154.3	1153.7	1153.1	1152.1
140°	1191.6	1191.4	1191.1	1190.8	1190.6	1190.1	1189.4	1188.6	1187.8	1187.1	1186.6
142.5°	1221.9	1221.9	1221.8	1221.8	1221.8	1221.5	1220.9	1220.4	1219.9	1219.3	1219.0
145°	1268.7	1268.2	1267.7	1267.1	1266.7	1266.3	1266.0	1265.8	1265.6	1265.3	1265.3
147.5°	1307.3	1307.0	1306.8	1306.6	1306.3	1306.1	1305.9	1305.7	1305.4	1305.3	1305.5
150°	1332.3	1332.1	1331.8	1331.5	1331.3	1331.2	1331.2	1331.2	1331.2	1331.2	1331.5
152.5°	1353.8	1353.9	1354.0	1354.2	1354.4	1354.2	1353.8	1353.4	1353.1	1352.6	1353.1
155°	1382.6	1383.3	1384.1	1384.8	1385.5	1385.4	1384.4	1383.5	1382.4	1381.5	1382.2
157.5°	1406.7	1408.0	1409.3	1410.6	1411.9	1411.9	1410.6	1409.3	1408.0	1406.7	1407.6
160°	1422.8	1424.3	1425.7	1427.2	1428.7	1428.7	1427.2	1425.7	1424.3	1422.8	1423.0
162.5°	1435.3	1436.9	1438.6	1440.4	1442.0	1442.1	1440.6	1439.2	1437.6	1436.1	1436.4
165°	1452.9	1455.2	1457.4	1459.7	1461.8	1462.0	1460.0	1458.0	1456.0	1454.1	1454.1
167.5°	1466.1	1468.6	1471.0	1473.5	1476.0	1476.2	1473.9	1471.8	1469.6	1467.4	1467.6
170°	1474.1	1476.6	1479.1	1481.6	1484.0	1484.3	1482.3	1480.3	1478.3	1476.4	1476.1
172.5°	1478.6	1481.3	1483.9	1486.6	1489.4	1489.7	1487.7	1485.7	1483.7	1481.7	1481.4
175°	1484.2	1487.1	1490.1	1493.1	1496.1	1496.5	1494.3	1492.0	1489.8	1487.5	1487.3
177.5°	1487.7	1490.1	1492.5	1494.9	1497.3	1497.7	1496.1	1494.5	1492.9	1491.3	1490.9
180°	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1



TEST NUMBER: P333067-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1171.0	1165.9	1163.3	1157.4	1150.5	1146.8	1143.5	1138.8	1132.5	1125.9	1121.1
5°	1230.4	1219.4	1205.7	1189.2	1174.6	1160.4	1148.0	1135.7	1121.5	1106.7	1092.1
7.5°	1291.4	1269.8	1246.5	1219.4	1193.2	1169.2	1147.3	1126.2	1102.3	1081.1	1061.6
10°	1333.9	1304.6	1272.0	1237.8	1203.4	1173.6	1144.4	1117.8	1088.5	1062.4	1040.3
12.5°	1368.3	1333.9	1294.8	1252.0	1210.7	1174.7	1141.0	1106.4	1073.1	1044.7	1015.5
15°	1425.5	1378.3	1325.7	1274.4	1220.8	1171.8	1126.4	1086.2	1048.2	1008.3	980.4
17.5°	1464.7	1408.8	1344.8	1283.1	1219.9	1162.1	1109.8	1061.8	1018.0	977.2	944.0
20°	1488.2	1426.4	1355.4	1285.4	1214.4	1152.5	1096.2	1043.1	997.8	953.8	919.5
22.5°	1501.4	1433.0	1355.4	1282.0	1208.5	1141.6	1079.8	1024.4	975.1	931.1	893.1
25°	1505.6	1432.4	1353.1	1268.9	1188.3	1117.3	1053.2	993.2	938.2	894.3	854.0
27.5°	1499.8	1413.5	1332.3	1245.9	1162.7	1087.9	1020.6	957.6	902.6	855.4	814.1
30°	1491.0	1398.4	1311.5	1221.7	1137.5	1065.6	994.5	934.1	876.9	827.9	786.3
32.5°	1471.9	1380.2	1286.5	1194.6	1109.2	1035.2	967.9	907.1	850.9	800.8	756.6
35°	1434.2	1341.3	1239.6	1145.2	1061.4	984.5	921.4	862.7	809.2	755.5	708.9
37.5°	1384.5	1289.5	1188.4	1085.0	1001.2	928.6	870.6	815.5	763.3	714.4	662.6
40°	1337.6	1251.0	1146.6	1044.0	957.9	887.9	834.3	784.4	731.8	683.2	631.5
42.5°	1280.7	1207.0	1101.6	998.6	913.6	846.1	796.3	747.4	699.5	652.5	598.5
45°	1186.0	1130.1	1031.2	932.3	846.7	779.8	734.0	691.0	648.8	604.0	553.2
47.5°	1077.4	1039.6	954.2	852.9	773.7	713.5	669.3	634.1	598.5	553.6	509.0
50°	1001.9	977.7	895.2	802.7	727.2	671.8	626.5	593.5	563.7	520.6	480.8
52.5°	921.4	908.4	838.8	750.4	677.3	623.0	584.3	554.7	524.5	488.8	451.5
55°	798.6	805.5	746.4	669.9	601.2	555.4	520.2	495.4	469.8	439.6	410.8
57.5°	673.1	698.2	658.6	591.4	527.0	484.7	458.2	437.4	415.9	390.8	366.2
60°	598.1	619.1	596.7	537.6	481.3	441.9	417.2	401.1	379.6	356.7	337.9
62.5°	524.8	547.3	534.0	486.3	434.0	400.1	378.3	363.4	347.4	327.4	307.9
65°	432.7	447.4	441.0	408.0	370.9	342.1	321.9	310.9	296.3	281.6	264.2
67.5°	331.4	359.7	356.0	338.5	306.4	283.9	270.7	261.0	247.6	236.8	224.9
70°	272.4	298.6	298.1	283.9	266.5	245.5	236.3	228.1	216.1	205.6	196.0
72.5°	223.0	246.9	250.5	239.6	227.6	211.7	202.9	197.3	185.7	178.5	170.7
75°	156.2	173.6	178.1	178.1	172.6	164.4	156.6	152.9	144.7	138.3	133.7
77.5°	102.4	113.4	120.5	122.2	123.0	120.3	113.8	111.2	105.0	102.6	98.2
80°	72.3	79.6	87.9	90.7	93.0	92.0	89.3	87.5	81.5	79.2	77.4
82.5°	50.0	54.1	60.8	66.8	66.2	68.6	66.2	64.7	60.3	59.4	57.6
85°	26.1	26.5	27.5	31.6	33.9	34.8	35.3	34.4	33.0	33.0	29.8
87.5°	12.9	12.1	12.5	12.1	11.8	12.7	13.3	13.1	12.6	12.1	11.5
90°	20.6	18.6	16.6	14.3	11.5	8.8	6.1	3.4	6.1	8.8	11.5
92.5°	19.7	17.7	15.8	14.6	14.6	14.4	14.2	14.0	14.2	14.4	14.6
95°	24.1	23.8	23.6	27.6	36.1	44.5	53.0	61.4	53.0	44.5	36.1
97.5°	84.9	112.5	140.3	151.4	146.2	140.9	135.7	130.4	135.7	140.9	146.2
100°	117.6	151.9	186.1	201.0	196.6	192.1	187.6	183.1	187.6	192.1	196.6
102.5°	245.7	250.1	254.6	255.2	251.9	248.7	245.4	242.1	245.4	248.7	251.9
105°	345.9	344.7	343.5	342.1	340.6	339.1	337.6	336.1	337.6	339.1	340.6
107.5°	431.0	429.4	427.7	426.5	425.7	425.0	424.2	423.4	424.2	425.0	425.7
110°	489.5	488.0	486.6	485.4	484.7	484.0	483.2	482.4	483.2	484.0	484.7



TEST NUMBER: P333067-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	547.4	546.7	546.0	545.0	543.6	542.3	541.0	539.6	541.0	542.3	543.6
115°	630.3	630.6	630.9	630.6	629.8	629.1	628.4	627.6	628.4	629.1	629.8
117.5°	712.7	712.2	711.6	710.8	709.9	708.9	707.9	706.9	707.9	708.9	709.9
120°	764.4	764.7	764.8	764.5	763.5	762.5	761.5	760.5	761.5	762.5	763.5
122.5°	814.1	813.7	813.4	813.0	812.4	811.8	811.1	810.5	811.1	811.8	812.4
125°	885.5	886.0	886.5	886.2	885.2	884.2	883.2	882.3	883.2	884.2	885.2
127.5°	954.1	953.0	951.8	951.1	950.9	950.6	950.4	950.1	950.4	950.6	950.9
130°	996.9	996.2	995.4	994.9	994.6	994.5	994.2	993.9	994.2	994.5	994.6
132.5°	1038.5	1037.6	1036.6	1035.9	1035.4	1035.0	1034.6	1034.1	1034.6	1035.0	1035.4
135°	1095.8	1094.8	1093.8	1093.5	1093.7	1093.9	1094.2	1094.4	1094.2	1093.9	1093.7
137.5°	1151.0	1149.9	1148.8	1148.2	1148.1	1148.0	1147.9	1147.8	1147.9	1148.0	1148.1
140°	1186.1	1185.6	1185.2	1184.6	1184.1	1183.6	1183.2	1182.7	1183.2	1183.6	1184.1
142.5°	1218.7	1218.4	1218.1	1217.5	1216.6	1215.7	1214.8	1213.9	1214.8	1215.7	1216.6
145°	1265.3	1265.3	1265.3	1264.9	1264.2	1263.4	1262.7	1262.0	1262.7	1263.4	1264.2
147.5°	1305.8	1306.1	1306.3	1305.7	1304.3	1303.0	1301.5	1300.1	1301.5	1303.0	1304.3
150°	1331.7	1332.0	1332.1	1331.8	1330.8	1329.8	1328.9	1327.8	1328.9	1329.8	1330.8
152.5°	1353.5	1354.0	1354.4	1354.3	1353.4	1352.6	1351.9	1351.1	1351.9	1352.6	1353.4
155°	1382.9	1383.7	1384.4	1384.7	1384.4	1384.1	1383.9	1383.7	1383.9	1384.1	1384.4
157.5°	1408.3	1409.2	1410.1	1410.6	1410.7	1410.8	1411.0	1411.2	1411.0	1410.8	1410.7
160°	1423.2	1423.5	1423.7	1424.3	1425.0	1425.7	1426.5	1427.2	1426.5	1425.7	1425.0
162.5°	1436.7	1436.9	1437.2	1437.8	1438.7	1439.7	1440.5	1441.5	1440.5	1439.7	1438.7
165°	1454.1	1454.1	1454.1	1454.7	1455.9	1457.2	1458.4	1459.7	1458.4	1457.2	1455.9
167.5°	1467.7	1467.9	1468.0	1468.8	1470.1	1471.4	1472.7	1473.9	1472.7	1471.4	1470.1
170°	1475.8	1475.6	1475.4	1476.0	1477.5	1478.9	1480.5	1482.0	1480.5	1478.9	1477.5
172.5°	1481.3	1481.0	1480.7	1481.4	1482.8	1484.4	1485.8	1487.3	1485.8	1484.4	1482.8
175°	1487.0	1486.8	1486.5	1487.1	1488.7	1490.1	1491.6	1493.1	1491.6	1490.1	1488.7
177.5°	1490.6	1490.1	1489.7	1490.2	1491.6	1493.0	1494.4	1495.8	1494.4	1493.0	1491.6
180°	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1



TEST NUMBER: P333067-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1116.0	1112.3	1107.6	1102.1	1095.5	1089.7	1087.1	1089.3	1090.4	1087.4	1087.1
5°	1082.0	1070.6	1061.4	1047.7	1036.7	1027.5	1021.1	1018.4	1019.3	1012.0	1010.1
7.5°	1043.9	1030.3	1015.3	999.0	983.8	970.3	963.3	959.4	951.7	948.3	942.7
10°	1019.3	1001.0	986.4	967.1	949.7	933.7	925.9	919.5	911.7	908.0	900.3
12.5°	994.0	972.8	956.7	936.7	918.9	899.6	892.2	880.3	868.1	860.4	850.4
15°	958.4	932.8	913.1	889.2	868.2	846.2	826.6	804.5	796.3	778.9	768.9
17.5°	916.7	890.7	866.3	834.4	801.9	774.6	753.6	732.5	720.0	708.9	703.7
20°	889.2	865.5	831.6	794.4	758.3	728.1	711.1	697.4	683.6	675.9	670.4
22.5°	863.2	832.8	793.5	753.5	717.3	693.6	679.2	665.1	654.0	646.6	639.2
25°	819.7	779.8	738.1	692.3	667.6	647.0	631.5	620.0	613.1	603.6	599.9
27.5°	774.9	726.6	680.6	649.9	624.1	605.3	591.7	583.1	574.4	568.3	563.5
30°	740.5	691.5	650.2	621.0	594.9	579.3	568.3	558.2	551.3	546.3	542.6
32.5°	706.4	657.4	622.8	591.2	570.7	555.4	543.7	536.2	530.8	524.3	522.1
35°	657.1	613.6	583.4	555.0	533.9	520.2	511.0	503.3	498.7	496.8	495.4
37.5°	609.8	574.1	541.7	518.3	499.6	488.8	477.9	474.2	471.0	467.7	469.2
40°	579.7	546.3	517.5	492.8	477.6	465.7	459.3	454.7	451.9	451.9	451.9
42.5°	553.7	521.0	492.9	470.7	455.6	445.6	438.4	434.5	433.6	433.3	435.5
45°	513.3	483.1	454.7	436.4	423.5	413.5	409.4	406.1	406.1	408.0	408.5
47.5°	473.3	445.0	422.2	401.7	389.9	383.7	380.0	378.4	378.6	380.5	382.5
50°	448.8	420.9	398.4	380.0	369.1	363.1	359.9	359.0	359.9	359.9	363.1
52.5°	422.0	397.0	375.0	359.6	347.1	341.5	339.8	338.5	339.1	340.5	341.9
55°	382.8	360.4	339.3	324.7	315.5	311.9	307.7	308.2	307.3	308.2	308.2
57.5°	343.5	323.4	303.8	292.1	284.1	278.8	274.3	275.6	274.2	274.1	273.3
60°	318.2	296.3	280.7	270.2	261.0	256.4	252.3	253.2	251.8	250.9	249.1
62.5°	290.8	272.4	257.6	247.5	240.1	234.8	230.7	229.8	226.6	223.4	219.5
65°	250.9	235.8	222.6	212.9	206.0	201.9	198.7	196.0	189.1	181.8	178.1
67.5°	212.2	201.3	188.9	180.8	175.2	169.8	163.7	159.0	152.6	148.5	146.3
70°	187.3	176.8	166.3	158.4	152.5	147.5	140.6	137.4	132.8	131.0	128.6
72.5°	163.5	153.7	143.9	136.8	130.5	126.6	121.1	118.0	116.0	115.2	113.0
75°	127.3	119.5	112.2	105.8	100.7	98.0	95.7	93.4	92.5	88.3	86.1
77.5°	92.9	87.7	83.2	78.6	75.0	73.2	68.8	66.1	64.6	62.7	62.2
80°	72.3	68.7	64.1	61.4	56.3	54.5	52.7	52.2	51.7	51.3	50.8
82.5°	54.4	50.7	46.1	44.5	43.1	42.0	40.9	40.5	40.0	40.3	40.2
85°	27.5	25.7	25.7	25.2	24.7	24.3	23.8	23.8	23.3	23.8	23.3
87.5°	12.1	12.1	12.5	12.1	12.9	13.3	13.3	13.6	14.2	13.8	14.0
90°	14.3	16.6	18.6	20.6	22.6	24.5	26.1	27.6	29.0	30.6	31.5
92.5°	14.6	15.8	17.7	19.7	21.7	23.7	25.1	26.7	28.2	29.6	30.4
95°	27.6	23.6	23.8	24.1	24.3	24.5	26.1	27.6	29.0	30.6	31.4
97.5°	151.4	140.3	112.5	84.9	57.2	29.4	29.6	29.8	30.0	30.0	30.3
100°	201.0	186.1	151.9	117.6	83.3	49.2	44.9	40.7	36.5	32.3	30.3
102.5°	255.2	254.6	250.1	245.7	241.3	236.8	191.2	145.8	100.2	54.7	31.9
105°	342.1	343.5	344.7	345.9	347.2	348.4	350.7	352.9	355.2	357.4	354.0
107.5°	426.5	427.7	429.4	431.0	432.7	434.5	435.5	436.6	437.7	438.8	439.8
110°	485.4	486.6	488.0	489.5	491.0	492.5	493.0	493.5	494.0	494.5	495.1



TEST NUMBER: P333067-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	545.0	546.0	546.7	547.4	548.1	548.8	548.7	548.5	548.5	548.4	548.8
115°	630.6	630.9	630.6	630.3	630.1	629.8	630.3	630.9	631.4	631.8	632.1
117.5°	710.8	711.6	712.2	712.7	713.3	713.9	713.8	713.6	713.5	713.4	713.3
120°	764.5	764.8	764.7	764.4	764.1	763.9	764.4	764.8	765.3	765.9	765.9
122.5°	813.0	813.4	813.7	814.1	814.4	814.8	815.1	815.4	815.7	816.0	815.9
125°	886.2	886.5	886.0	885.5	884.9	884.5	885.2	886.0	886.7	887.4	887.9
127.5°	951.1	951.8	953.0	954.1	955.3	956.4	956.2	956.1	956.0	955.8	955.6
130°	994.9	995.4	996.2	996.9	997.6	998.4	998.7	998.8	999.1	999.4	999.5
132.5°	1035.9	1036.6	1037.6	1038.5	1039.4	1040.3	1040.6	1040.9	1041.1	1041.4	1041.4
135°	1093.5	1093.8	1094.8	1095.8	1096.8	1097.8	1098.3	1098.8	1099.2	1099.8	1100.3
137.5°	1148.2	1148.8	1149.9	1151.0	1152.1	1153.1	1153.7	1154.3	1154.8	1155.4	1155.5
140°	1184.6	1185.2	1185.6	1186.1	1186.6	1187.1	1187.8	1188.6	1189.4	1190.1	1190.6
142.5°	1217.5	1218.1	1218.4	1218.7	1219.0	1219.3	1219.9	1220.4	1220.9	1221.5	1221.8
145°	1264.9	1265.3	1265.3	1265.3	1265.3	1265.3	1265.6	1265.8	1266.0	1266.3	1266.7
147.5°	1305.7	1306.3	1306.1	1305.8	1305.5	1305.3	1305.4	1305.7	1305.9	1306.1	1306.3
150°	1331.8	1332.1	1332.0	1331.7	1331.5	1331.2	1331.2	1331.2	1331.2	1331.2	1331.3
152.5°	1354.3	1354.4	1354.0	1353.5	1353.1	1352.6	1353.1	1353.4	1353.8	1354.2	1354.4
155°	1384.7	1384.4	1383.7	1382.9	1382.2	1381.5	1382.4	1383.5	1384.4	1385.4	1385.5
157.5°	1410.6	1410.1	1409.2	1408.3	1407.6	1406.7	1408.0	1409.3	1410.6	1411.9	1411.9
160°	1424.3	1423.7	1423.5	1423.2	1423.0	1422.8	1424.3	1425.7	1427.2	1428.7	1428.7
162.5°	1437.8	1437.2	1436.9	1436.7	1436.4	1436.1	1437.6	1439.2	1440.6	1442.1	1442.0
165°	1454.7	1454.1	1454.1	1454.1	1454.1	1454.1	1456.0	1458.0	1460.0	1462.0	1461.8
167.5°	1468.8	1468.0	1467.9	1467.7	1467.6	1467.4	1469.6	1471.8	1473.9	1476.2	1476.0
170°	1476.0	1475.4	1475.6	1475.8	1476.1	1476.4	1478.3	1480.3	1482.3	1484.3	1484.0
172.5°	1481.4	1480.7	1481.0	1481.3	1481.4	1481.7	1483.7	1485.7	1487.7	1489.7	1489.4
175°	1487.1	1486.5	1486.8	1487.0	1487.3	1487.5	1489.8	1492.0	1494.3	1496.5	1496.1
177.5°	1490.2	1489.7	1490.1	1490.6	1490.9	1491.3	1492.9	1494.5	1496.1	1497.7	1497.3
180°	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1



TEST NUMBER: P333067-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1084.9	1085.6	1083.1	1082.3	1083.1	1085.6	1084.9	1087.1	1087.4	1090.4	1089.3
5°	1006.5	1005.6	1003.3	1003.8	1003.3	1005.6	1006.5	1010.1	1012.0	1019.3	1018.4
7.5°	939.4	935.9	936.9	933.2	936.9	935.9	939.4	942.7	948.3	951.7	959.4
10°	898.5	893.4	889.2	885.6	889.2	893.4	898.5	900.3	908.0	911.7	919.5
12.5°	842.4	838.1	832.5	833.6	832.5	838.1	842.4	850.4	860.4	868.1	880.3
15°	762.8	756.0	745.0	746.4	745.0	756.0	762.8	768.9	778.9	796.3	804.5
17.5°	695.6	695.7	690.6	691.8	690.6	695.7	695.6	703.7	708.9	720.0	732.5
20°	660.7	657.5	658.0	656.7	658.0	657.5	660.7	670.4	675.9	683.6	697.4
22.5°	636.6	632.7	629.5	626.6	629.5	632.7	636.6	639.2	646.6	654.0	665.1
25°	595.7	593.0	588.8	588.0	588.8	593.0	595.7	599.9	603.6	613.1	620.0
27.5°	559.8	559.3	557.7	555.5	557.7	559.3	559.8	563.5	568.3	574.4	583.1
30°	539.0	538.0	537.1	535.7	537.1	538.0	539.0	542.6	546.3	551.3	558.2
32.5°	520.3	519.7	518.8	518.9	518.8	519.7	520.3	522.1	524.3	530.8	536.2
35°	493.6	493.2	492.2	491.8	492.2	493.2	493.6	495.4	496.8	498.7	503.3
37.5°	468.7	469.9	469.3	469.2	469.3	469.9	468.7	469.2	467.7	471.0	474.2
40°	451.5	451.9	452.9	452.5	452.9	451.9	451.5	451.9	451.9	451.9	454.7
42.5°	437.2	437.3	438.6	437.0	438.6	437.3	437.2	435.5	433.3	433.6	434.5
45°	411.6	414.4	414.0	414.0	414.0	414.4	411.6	408.5	408.0	406.1	406.1
47.5°	383.7	386.1	386.8	386.7	386.8	386.1	383.7	382.5	380.5	378.6	378.4
50°	365.4	364.5	365.8	365.4	365.8	364.5	365.4	363.1	359.9	359.9	359.0
52.5°	343.1	343.3	343.2	342.7	343.2	343.3	343.1	341.9	340.5	339.1	338.5
55°	308.7	309.1	308.2	308.7	308.2	309.1	308.7	308.2	308.2	307.3	308.2
57.5°	271.3	269.1	270.0	268.9	270.0	269.1	271.3	273.3	274.1	274.2	275.6
60°	244.5	240.8	240.0	238.2	240.0	240.8	244.5	249.1	250.9	251.8	253.2
62.5°	214.5	211.9	208.8	210.3	208.8	211.9	214.5	219.5	223.4	226.6	229.8
65°	174.4	172.6	171.3	173.1	171.3	172.6	174.4	178.1	181.8	189.1	196.0
67.5°	144.4	143.4	143.4	142.5	143.4	143.4	144.4	146.3	148.5	152.6	159.0
70°	128.6	127.3	127.3	126.4	127.3	127.3	128.6	128.6	131.0	132.8	137.4
72.5°	112.5	111.2	111.6	111.0	111.6	111.2	112.5	113.0	115.2	116.0	118.0
75°	83.3	81.0	81.0	81.5	81.0	81.0	83.3	86.1	88.3	92.5	93.4
77.5°	62.2	61.7	62.3	61.6	62.3	61.7	62.2	62.2	62.7	64.6	66.1
80°	50.8	50.4	49.9	51.3	49.9	50.4	50.8	50.8	51.3	51.7	52.2
82.5°	39.4	39.3	39.3	41.1	39.3	39.3	39.4	40.2	40.3	40.0	40.5
85°	23.8	22.9	23.8	22.9	23.8	22.9	23.8	23.3	23.8	23.3	23.8
87.5°	14.8	14.6	14.3	14.7	14.3	14.6	14.8	14.0	13.8	14.2	13.6
90°	32.0	32.5	33.0	33.5	33.0	32.5	32.0	31.5	30.6	29.0	27.6
92.5°	30.6	30.7	30.7	30.8	30.7	30.7	30.6	30.4	29.6	28.2	26.7
95°	31.6	31.9	32.1	32.4	32.1	31.9	31.6	31.4	30.6	29.0	27.6
97.5°	30.6	30.7	31.0	31.3	31.0	30.7	30.6	30.3	30.0	30.0	29.8
100°	30.6	30.7	31.0	31.3	31.0	30.7	30.6	30.3	32.3	36.5	40.7
102.5°	32.0	32.0	32.1	32.2	32.1	32.0	32.0	31.9	54.7	100.2	145.8
105°	345.1	336.1	327.2	318.3	327.2	336.1	345.1	354.0	357.4	355.2	352.9
107.5°	440.7	441.7	442.6	443.6	442.6	441.7	440.7	439.8	438.8	437.7	436.6
110°	495.8	496.6	497.3	498.1	497.3	496.6	495.8	495.1	494.5	494.0	493.5



TEST NUMBER: P333067-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	549.7	550.7	551.6	552.6	551.6	550.7	549.7	548.8	548.4	548.5	548.5
115°	632.1	632.1	632.1	632.1	632.1	632.1	632.1	632.1	631.8	631.4	630.9
117.5°	713.3	713.2	713.1	712.9	713.1	713.2	713.3	713.3	713.4	713.5	713.6
120°	765.3	764.8	764.4	763.9	764.4	764.8	765.3	765.9	765.9	765.3	764.8
122.5°	815.4	814.9	814.4	813.9	814.4	814.9	815.4	815.9	816.0	815.7	815.4
125°	888.2	888.5	888.7	889.0	888.7	888.5	888.2	887.9	887.4	886.7	886.0
127.5°	955.5	955.2	955.0	954.8	955.0	955.2	955.5	955.6	955.8	956.0	956.1
130°	999.5	999.5	999.5	999.5	999.5	999.5	999.5	999.5	999.4	999.1	998.8
132.5°	1041.2	1041.0	1040.8	1040.6	1040.8	1041.0	1041.2	1041.4	1041.4	1041.1	1040.9
135°	1100.8	1101.2	1101.7	1102.3	1101.7	1101.2	1100.8	1100.3	1099.8	1099.2	1098.8
137.5°	1155.4	1155.3	1155.1	1154.9	1155.1	1155.3	1155.4	1155.5	1155.4	1154.8	1154.3
140°	1190.8	1191.1	1191.4	1191.6	1191.4	1191.1	1190.8	1190.6	1190.1	1189.4	1188.6
142.5°	1221.8	1221.8	1221.9	1221.9	1221.9	1221.8	1221.8	1221.8	1221.5	1220.9	1220.4
145°	1267.1	1267.7	1268.2	1268.7	1268.2	1267.7	1267.1	1266.7	1266.3	1266.0	1265.8
147.5°	1306.6	1306.8	1307.0	1307.3	1307.0	1306.8	1306.6	1306.3	1306.1	1305.9	1305.7
150°	1331.5	1331.8	1332.1	1332.3	1332.1	1331.8	1331.5	1331.3	1331.2	1331.2	1331.2
152.5°	1354.2	1354.0	1353.9	1353.8	1353.9	1354.0	1354.2	1354.4	1354.2	1353.8	1353.4
155°	1384.8	1384.1	1383.3	1382.6	1383.3	1384.1	1384.8	1385.5	1385.4	1384.4	1383.5
157.5°	1410.6	1409.3	1408.0	1406.7	1408.0	1409.3	1410.6	1411.9	1411.9	1410.6	1409.3
160°	1427.2	1425.7	1424.3	1422.8	1424.3	1425.7	1427.2	1428.7	1428.7	1427.2	1425.7
162.5°	1440.4	1438.6	1436.9	1435.3	1436.9	1438.6	1440.4	1442.0	1442.1	1440.6	1439.2
165°	1459.7	1457.4	1455.2	1452.9	1455.2	1457.4	1459.7	1461.8	1462.0	1460.0	1458.0
167.5°	1473.5	1471.0	1468.6	1466.1	1468.6	1471.0	1473.5	1476.0	1476.2	1473.9	1471.8
170°	1481.6	1479.1	1476.6	1474.1	1476.6	1479.1	1481.6	1484.0	1484.3	1482.3	1480.3
172.5°	1486.6	1483.9	1481.3	1478.6	1481.3	1483.9	1486.6	1489.4	1489.7	1487.7	1485.7
175°	1493.1	1490.1	1487.1	1484.2	1487.1	1490.1	1493.1	1496.1	1496.5	1494.3	1492.0
177.5°	1494.9	1492.5	1490.1	1487.7	1490.1	1492.5	1494.9	1497.3	1497.7	1496.1	1494.5
180°	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1



TEST NUMBER: P333067-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1087.1	1089.7	1095.5	1102.1	1107.6	1112.3	1116.0	1121.1	1125.9	1132.5	1138.8
5°	1021.1	1027.5	1036.7	1047.7	1061.4	1070.6	1082.0	1092.1	1106.7	1121.5	1135.7
7.5°	963.3	970.3	983.8	999.0	1015.3	1030.3	1043.9	1061.6	1081.1	1102.3	1126.2
10°	925.9	933.7	949.7	967.1	986.4	1001.0	1019.3	1040.3	1062.4	1088.5	1117.8
12.5°	892.2	899.6	918.9	936.7	956.7	972.8	994.0	1015.5	1044.7	1073.1	1106.4
15°	826.6	846.2	868.2	889.2	913.1	932.8	958.4	980.4	1008.3	1048.2	1086.2
17.5°	753.6	774.6	801.9	834.4	866.3	890.7	916.7	944.0	977.2	1018.0	1061.8
20°	711.1	728.1	758.3	794.4	831.6	865.5	889.2	919.5	953.8	997.8	1043.1
22.5°	679.2	693.6	717.3	753.5	793.5	832.8	863.2	893.1	931.1	975.1	1024.4
25°	631.5	647.0	667.6	692.3	738.1	779.8	819.7	854.0	894.3	938.2	993.2
27.5°	591.7	605.3	624.1	649.9	680.6	726.6	774.9	814.1	855.4	902.6	957.6
30°	568.3	579.3	594.9	621.0	650.2	691.5	740.5	786.3	827.9	876.9	934.1
32.5°	543.7	555.4	570.7	591.2	622.8	657.4	706.4	756.6	800.8	850.9	907.1
35°	511.0	520.2	533.9	555.0	583.4	613.6	657.1	708.9	755.5	809.2	862.7
37.5°	477.9	488.8	499.6	518.3	541.7	574.1	609.8	662.6	714.4	763.3	815.5
40°	459.3	465.7	477.6	492.8	517.5	546.3	579.7	631.5	683.2	731.8	784.4
42.5°	438.4	445.6	455.6	470.7	492.9	521.0	553.7	598.5	652.5	699.5	747.4
45°	409.4	413.5	423.5	436.4	454.7	483.1	513.3	553.2	604.0	648.8	691.0
47.5°	380.0	383.7	389.9	401.7	422.2	445.0	473.3	509.0	553.6	598.5	634.1
50°	359.9	363.1	369.1	380.0	398.4	420.9	448.8	480.8	520.6	563.7	593.5
52.5°	339.8	341.5	347.1	359.6	375.0	397.0	422.0	451.5	488.8	524.5	554.7
55°	307.7	311.9	315.5	324.7	339.3	360.4	382.8	410.8	439.6	469.8	495.4
57.5°	274.3	278.8	284.1	292.1	303.8	323.4	343.5	366.2	390.8	415.9	437.4
60°	252.3	256.4	261.0	270.2	280.7	296.3	318.2	337.9	356.7	379.6	401.1
62.5°	230.7	234.8	240.1	247.5	257.6	272.4	290.8	307.9	327.4	347.4	363.4
65°	198.7	201.9	206.0	212.9	222.6	235.8	250.9	264.2	281.6	296.3	310.9
67.5°	163.7	169.8	175.2	180.8	188.9	201.3	212.2	224.9	236.8	247.6	261.0
70°	140.6	147.5	152.5	158.4	166.3	176.8	187.3	196.0	205.6	216.1	228.1
72.5°	121.1	126.6	130.5	136.8	143.9	153.7	163.5	170.7	178.5	185.7	197.3
75°	95.7	98.0	100.7	105.8	112.2	119.5	127.3	133.7	138.3	144.7	152.9
77.5°	68.8	73.2	75.0	78.6	83.2	87.7	92.9	98.2	102.6	105.0	111.2
80°	52.7	54.5	56.3	61.4	64.1	68.7	72.3	77.4	79.2	81.5	87.5
82.5°	40.9	42.0	43.1	44.5	46.1	50.7	54.4	57.6	59.4	60.3	64.7
85°	23.8	24.3	24.7	25.2	25.7	25.7	27.5	29.8	33.0	33.0	34.4
87.5°	13.3	13.3	12.9	12.1	12.5	12.1	12.1	11.5	12.1	12.6	13.1
90°	26.1	24.5	22.6	20.6	18.6	16.6	14.3	11.5	8.8	6.1	3.4
92.5°	25.1	23.7	21.7	19.7	17.7	15.8	14.6	14.6	14.4	14.2	14.0
95°	26.1	24.5	24.3	24.1	23.8	23.6	27.6	36.1	44.5	53.0	61.4
97.5°	29.6	29.4	57.2	84.9	112.5	140.3	151.4	146.2	140.9	135.7	130.4
100°	44.9	49.2	83.3	117.6	151.9	186.1	201.0	196.6	192.1	187.6	183.1
102.5°	191.2	236.8	241.3	245.7	250.1	254.6	255.2	251.9	248.7	245.4	242.1
105°	350.7	348.4	347.2	345.9	344.7	343.5	342.1	340.6	339.1	337.6	336.1
107.5°	435.5	434.5	432.7	431.0	429.4	427.7	426.5	425.7	425.0	424.2	423.4
110°	493.0	492.5	491.0	489.5	488.0	486.6	485.4	484.7	484.0	483.2	482.4



TEST NUMBER: P333067-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	548.7	548.8	548.1	547.4	546.7	546.0	545.0	543.6	542.3	541.0	539.6
115°	630.3	629.8	630.1	630.3	630.6	630.9	630.6	629.8	629.1	628.4	627.6
117.5°	713.8	713.9	713.3	712.7	712.2	711.6	710.8	709.9	708.9	707.9	706.9
120°	764.4	763.9	764.1	764.4	764.7	764.8	764.5	763.5	762.5	761.5	760.5
122.5°	815.1	814.8	814.4	814.1	813.7	813.4	813.0	812.4	811.8	811.1	810.5
125°	885.2	884.5	884.9	885.5	886.0	886.5	886.2	885.2	884.2	883.2	882.3
127.5°	956.2	956.4	955.3	954.1	953.0	951.8	951.1	950.9	950.6	950.4	950.1
130°	998.7	998.4	997.6	996.9	996.2	995.4	994.9	994.6	994.5	994.2	993.9
132.5°	1040.6	1040.3	1039.4	1038.5	1037.6	1036.6	1035.9	1035.4	1035.0	1034.6	1034.1
135°	1098.3	1097.8	1096.8	1095.8	1094.8	1093.8	1093.5	1093.7	1093.9	1094.2	1094.4
137.5°	1153.7	1153.1	1152.1	1151.0	1149.9	1148.8	1148.2	1148.1	1148.0	1147.9	1147.8
140°	1187.8	1187.1	1186.6	1186.1	1185.6	1185.2	1184.6	1184.1	1183.6	1183.2	1182.7
142.5°	1219.9	1219.3	1219.0	1218.7	1218.4	1218.1	1217.5	1216.6	1215.7	1214.8	1213.9
145°	1265.6	1265.3	1265.3	1265.3	1265.3	1265.3	1264.9	1264.2	1263.4	1262.7	1262.0
147.5°	1305.4	1305.3	1305.5	1305.8	1306.1	1306.3	1305.7	1304.3	1303.0	1301.5	1300.1
150°	1331.2	1331.2	1331.5	1331.7	1332.0	1332.1	1331.8	1330.8	1329.8	1328.9	1327.8
152.5°	1353.1	1352.6	1353.1	1353.5	1354.0	1354.4	1354.3	1353.4	1352.6	1351.9	1351.1
155°	1382.4	1381.5	1382.2	1382.9	1383.7	1384.4	1384.7	1384.4	1384.1	1383.9	1383.7
157.5°	1408.0	1406.7	1407.6	1408.3	1409.2	1410.1	1410.6	1410.7	1410.8	1411.0	1411.2
160°	1424.3	1422.8	1423.0	1423.2	1423.5	1423.7	1424.3	1425.0	1425.7	1426.5	1427.2
162.5°	1437.6	1436.1	1436.4	1436.7	1436.9	1437.2	1437.8	1438.7	1439.7	1440.5	1441.5
165°	1456.0	1454.1	1454.1	1454.1	1454.1	1454.1	1454.7	1455.9	1457.2	1458.4	1459.7
167.5°	1469.6	1467.4	1467.6	1467.7	1467.9	1468.0	1468.8	1470.1	1471.4	1472.7	1473.9
170°	1478.3	1476.4	1476.1	1475.8	1475.6	1475.4	1476.0	1477.5	1478.9	1480.5	1482.0
172.5°	1483.7	1481.7	1481.4	1481.3	1481.0	1480.7	1481.4	1482.8	1484.4	1485.8	1487.3
175°	1489.8	1487.5	1487.3	1487.0	1486.8	1486.5	1487.1	1488.7	1490.1	1491.6	1493.1
177.5°	1492.9	1491.3	1490.9	1490.6	1490.1	1489.7	1490.2	1491.6	1493.0	1494.4	1495.8
180°	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1



TEST NUMBER: P333067-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1143.5	1146.8	1150.5	1157.4	1163.3	1165.9	1171.0	1174.7	1173.5	1178.6	1187.5
5°	1148.0	1160.4	1174.6	1189.2	1205.7	1219.4	1230.4	1241.4	1250.1	1260.6	1276.2
7.5°	1147.3	1169.2	1193.2	1219.4	1246.5	1269.8	1291.4	1313.4	1332.9	1354.3	1382.2
10°	1144.4	1173.6	1203.4	1237.8	1272.0	1304.6	1333.9	1361.4	1387.5	1415.4	1450.7
12.5°	1141.0	1174.7	1210.7	1252.0	1294.8	1333.9	1368.3	1407.9	1440.6	1476.6	1517.3
15°	1126.4	1171.8	1220.8	1274.4	1325.7	1378.3	1425.5	1474.0	1519.3	1562.4	1613.7
17.5°	1109.8	1162.1	1219.9	1283.1	1344.8	1408.8	1464.7	1526.0	1572.3	1630.0	1677.7
20°	1096.2	1152.5	1214.4	1285.4	1355.4	1426.4	1488.2	1550.5	1602.7	1660.9	1721.3
22.5°	1079.8	1141.6	1208.5	1282.0	1355.4	1433.0	1501.4	1563.3	1628.0	1693.4	1755.8
25°	1053.2	1117.3	1188.3	1268.9	1353.1	1432.4	1505.6	1582.5	1652.2	1723.1	1779.0
27.5°	1020.6	1087.9	1162.7	1245.9	1332.3	1413.5	1499.8	1581.7	1651.7	1720.1	1768.8
30°	994.5	1065.6	1137.5	1221.7	1311.5	1398.4	1491.0	1573.0	1646.7	1708.1	1735.5
32.5°	967.9	1035.2	1109.2	1194.6	1286.5	1380.2	1471.9	1555.7	1623.9	1660.8	1661.5
35°	921.4	984.5	1061.4	1145.2	1239.6	1341.3	1434.2	1516.6	1558.2	1561.5	1516.6
37.5°	870.6	928.6	1001.2	1085.0	1188.4	1289.5	1384.5	1439.4	1453.3	1406.7	1323.7
40°	834.3	887.9	957.9	1044.0	1146.6	1251.0	1337.6	1377.9	1363.2	1287.6	1195.2
42.5°	796.3	846.1	913.6	998.6	1101.6	1207.0	1280.7	1302.4	1263.6	1176.3	1068.1
45°	734.0	779.8	846.7	932.3	1031.2	1130.1	1186.0	1175.0	1110.4	1006.9	885.6
47.5°	669.3	713.5	773.7	852.9	954.2	1039.6	1077.4	1044.2	952.4	838.5	739.8
50°	626.5	671.8	727.2	802.7	895.2	977.7	1001.9	951.6	849.5	739.9	649.3
52.5°	584.3	623.0	677.3	750.4	838.8	908.4	921.4	863.2	757.9	659.8	579.4
55°	520.2	555.4	601.2	669.9	746.4	805.5	798.6	723.9	628.3	544.5	481.3
57.5°	458.2	484.7	527.0	591.4	658.6	698.2	673.1	609.5	520.3	451.7	398.4
60°	417.2	441.9	481.3	537.6	596.7	619.1	598.1	528.9	458.4	395.6	350.8
62.5°	378.3	400.1	434.0	486.3	534.0	547.3	524.8	464.4	400.9	347.2	310.1
65°	321.9	342.1	370.9	408.0	441.0	447.4	432.7	370.9	322.8	277.9	252.3
67.5°	270.7	283.9	306.4	338.5	356.0	359.7	331.4	292.6	250.2	222.7	203.3
70°	236.3	245.5	266.5	283.9	298.1	298.6	272.4	241.3	208.8	186.4	172.2
72.5°	202.9	211.7	227.6	239.6	250.5	246.9	223.0	198.5	172.2	155.2	144.7
75°	156.6	164.4	172.6	178.1	178.1	173.6	156.2	137.8	122.7	112.6	109.4
77.5°	113.8	120.3	123.0	122.2	120.5	113.4	102.4	90.4	85.0	80.2	77.8
80°	89.3	92.0	93.0	90.7	87.9	79.6	72.3	67.3	62.3	60.4	59.5
82.5°	66.2	68.6	66.2	66.8	60.8	54.1	50.0	48.3	46.1	45.5	44.5
85°	35.3	34.8	33.9	31.6	27.5	26.5	26.1	25.7	24.7	25.2	24.3
87.5°	13.3	12.7	11.8	12.1	12.5	12.1	12.9	13.3	13.7	13.6	14.6
90°	6.1	8.8	11.5	14.3	16.6	18.6	20.6	22.6	24.5	26.1	27.6
92.5°	14.2	14.4	14.6	14.6	15.8	17.7	19.7	21.7	23.7	25.1	26.7
95°	53.0	44.5	36.1	27.6	23.6	23.8	24.1	24.3	24.5	26.1	27.6
97.5°	135.7	140.9	146.2	151.4	140.3	112.5	84.9	57.2	29.4	29.6	29.8
100°	187.6	192.1	196.6	201.0	186.1	151.9	117.6	83.3	49.2	44.9	40.7
102.5°	245.4	248.7	251.9	255.2	254.6	250.1	245.7	241.3	236.8	191.2	145.8
105°	337.6	339.1	340.6	342.1	343.5	344.7	345.9	347.2	348.4	350.7	352.9
107.5°	424.2	425.0	425.7	426.5	427.7	429.4	431.0	432.7	434.5	435.5	436.6
110°	483.2	484.0	484.7	485.4	486.6	488.0	489.5	491.0	492.5	493.0	493.5



TEST NUMBER: P333067-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	541.0	542.3	543.6	545.0	546.0	546.7	547.4	548.1	548.8	548.7	548.5
115°	628.4	629.1	629.8	630.6	630.9	630.6	630.3	630.1	629.8	630.3	630.9
117.5°	707.9	708.9	709.9	710.8	711.6	712.2	712.7	713.3	713.9	713.8	713.6
120°	761.5	762.5	763.5	764.5	764.8	764.7	764.4	764.1	763.9	764.4	764.8
122.5°	811.1	811.8	812.4	813.0	813.4	813.7	814.1	814.4	814.8	815.1	815.4
125°	883.2	884.2	885.2	886.2	886.5	886.0	885.5	884.9	884.5	885.2	886.0
127.5°	950.4	950.6	950.9	951.1	951.8	953.0	954.1	955.3	956.4	956.2	956.1
130°	994.2	994.5	994.6	994.9	995.4	996.2	996.9	997.6	998.4	998.7	998.8
132.5°	1034.6	1035.0	1035.4	1035.9	1036.6	1037.6	1038.5	1039.4	1040.3	1040.6	1040.9
135°	1094.2	1093.9	1093.7	1093.5	1093.8	1094.8	1095.8	1096.8	1097.8	1098.3	1098.8
137.5°	1147.9	1148.0	1148.1	1148.2	1148.8	1149.9	1151.0	1152.1	1153.1	1153.7	1154.3
140°	1183.2	1183.6	1184.1	1184.6	1185.2	1185.6	1186.1	1186.6	1187.1	1187.8	1188.6
142.5°	1214.8	1215.7	1216.6	1217.5	1218.1	1218.4	1218.7	1219.0	1219.3	1219.9	1220.4
145°	1262.7	1263.4	1264.2	1264.9	1265.3	1265.3	1265.3	1265.3	1265.3	1265.6	1265.8
147.5°	1301.5	1303.0	1304.3	1305.7	1306.3	1306.1	1305.8	1305.5	1305.3	1305.4	1305.7
150°	1328.9	1329.8	1330.8	1331.8	1332.1	1332.0	1331.7	1331.5	1331.2	1331.2	1331.2
152.5°	1351.9	1352.6	1353.4	1354.3	1354.4	1354.0	1353.5	1353.1	1352.6	1353.1	1353.4
155°	1383.9	1384.1	1384.4	1384.7	1384.4	1383.7	1382.9	1382.2	1381.5	1382.4	1383.5
157.5°	1411.0	1410.8	1410.7	1410.6	1410.1	1409.2	1408.3	1407.6	1406.7	1408.0	1409.3
160°	1426.5	1425.7	1425.0	1424.3	1423.7	1423.5	1423.2	1423.0	1422.8	1424.3	1425.7
162.5°	1440.5	1439.7	1438.7	1437.8	1437.2	1436.9	1436.7	1436.4	1436.1	1437.6	1439.2
165°	1458.4	1457.2	1455.9	1454.7	1454.1	1454.1	1454.1	1454.1	1454.1	1456.0	1458.0
167.5°	1472.7	1471.4	1470.1	1468.8	1468.0	1467.9	1467.7	1467.6	1467.4	1469.6	1471.8
170°	1480.5	1478.9	1477.5	1476.0	1475.4	1475.6	1475.8	1476.1	1476.4	1478.3	1480.3
172.5°	1485.8	1484.4	1482.8	1481.4	1480.7	1481.0	1481.3	1481.4	1481.7	1483.7	1485.7
175°	1491.6	1490.1	1488.7	1487.1	1486.5	1486.8	1487.0	1487.3	1487.5	1489.8	1492.0
177.5°	1494.4	1493.0	1491.6	1490.2	1489.7	1490.1	1490.6	1490.9	1491.3	1492.9	1494.5
180°	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1



TEST NUMBER: P333067-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1192.2	1193.7	1194.8	1198.4	1198.8	1202.1	1198.8
5°	1290.8	1297.3	1307.3	1317.4	1318.4	1324.7	1313.3
7.5°	1401.4	1416.3	1425.6	1441.8	1448.3	1452.3	1445.7
10°	1477.6	1491.4	1515.7	1527.6	1539.5	1541.4	1535.9
12.5°	1551.3	1573.1	1592.2	1614.8	1614.2	1630.4	1624.4
15°	1649.4	1671.8	1698.4	1723.5	1732.8	1732.8	1740.1
17.5°	1719.3	1760.5	1788.0	1807.8	1829.4	1833.1	1830.6
20°	1766.6	1811.0	1840.4	1866.0	1880.7	1884.7	1884.7
22.5°	1801.8	1839.6	1868.2	1891.3	1903.3	1908.2	1906.8
25°	1826.2	1858.6	1876.0	1882.9	1886.1	1885.2	1876.5
27.5°	1792.8	1791.3	1780.4	1759.3	1743.4	1733.8	1722.9
30°	1729.1	1705.3	1677.8	1647.5	1608.6	1578.9	1569.7
32.5°	1634.2	1580.7	1534.2	1483.8	1442.0	1412.2	1399.7
35°	1450.7	1366.0	1296.8	1236.4	1192.4	1164.9	1155.8
37.5°	1232.9	1150.9	1065.3	1006.7	970.3	942.5	932.1
40°	1094.4	1005.1	930.5	875.6	838.0	811.0	810.5
42.5°	968.0	882.8	812.5	772.9	732.5	714.6	714.5
45°	792.6	724.4	664.9	633.8	609.5	594.9	590.7
47.5°	656.3	599.9	560.2	535.4	515.6	506.3	500.2
50°	579.7	530.3	498.7	477.2	466.1	454.3	453.3
52.5°	516.0	476.0	451.4	433.9	420.0	412.8	413.0
55°	433.6	402.1	384.6	371.3	360.4	354.9	352.6
57.5°	365.3	341.6	329.0	316.8	312.1	307.8	306.6
60°	322.8	306.8	294.9	285.2	278.4	277.1	276.6
62.5°	287.7	270.9	262.7	255.2	250.2	248.1	247.3
65°	237.2	224.8	217.5	211.5	209.7	206.6	206.0
67.5°	191.2	183.8	178.9	174.9	172.4	172.2	172.2
70°	163.0	158.9	154.8	152.5	151.1	150.2	150.2
72.5°	138.9	135.8	132.4	131.2	131.0	130.0	129.7
75°	105.8	102.5	103.1	100.7	98.9	96.6	95.2
77.5°	75.0	72.8	72.2	72.0	70.4	70.2	70.9
80°	58.1	55.9	55.4	55.9	55.4	54.1	54.1
82.5°	44.3	42.3	41.8	41.6	41.2	41.6	40.8
85°	23.8	22.9	22.9	22.9	23.8	23.3	22.9
87.5°	14.2	14.2	14.7	14.5	14.6	14.3	14.7
90°	29.0	30.6	31.5	32.0	32.5	33.0	33.5
92.5°	28.2	29.6	30.4	30.6	30.7	30.7	30.8
95°	29.0	30.6	31.4	31.6	31.9	32.1	32.4
97.5°	30.0	30.0	30.3	30.6	30.7	31.0	31.3
100°	36.5	32.3	30.3	30.6	30.7	31.0	31.3
102.5°	100.2	54.7	31.9	32.0	32.0	32.1	32.2
105°	355.2	357.4	354.0	345.1	336.1	327.2	318.3
107.5°	437.7	438.8	439.8	440.7	441.7	442.6	443.6
110°	494.0	494.5	495.1	495.8	496.6	497.3	498.1



TEST NUMBER: P333067-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	548.5	548.4	548.8	549.7	550.7	551.6	552.6
115°	631.4	631.8	632.1	632.1	632.1	632.1	632.1
117.5°	713.5	713.4	713.3	713.3	713.2	713.1	712.9
120°	765.3	765.9	765.9	765.3	764.8	764.4	763.9
122.5°	815.7	816.0	815.9	815.4	814.9	814.4	813.9
125°	886.7	887.4	887.9	888.2	888.5	888.7	889.0
127.5°	956.0	955.8	955.6	955.5	955.2	955.0	954.8
130°	999.1	999.4	999.5	999.5	999.5	999.5	999.5
132.5°	1041.1	1041.4	1041.4	1041.2	1041.0	1040.8	1040.6
135°	1099.2	1099.8	1100.3	1100.8	1101.2	1101.7	1102.3
137.5°	1154.8	1155.4	1155.5	1155.4	1155.3	1155.1	1154.9
140°	1189.4	1190.1	1190.6	1190.8	1191.1	1191.4	1191.6
142.5°	1220.9	1221.5	1221.8	1221.8	1221.8	1221.9	1221.9
145°	1266.0	1266.3	1266.7	1267.1	1267.7	1268.2	1268.7
147.5°	1305.9	1306.1	1306.3	1306.6	1306.8	1307.0	1307.3
150°	1331.2	1331.2	1331.3	1331.5	1331.8	1332.1	1332.3
152.5°	1353.8	1354.2	1354.4	1354.2	1354.0	1353.9	1353.8
155°	1384.4	1385.4	1385.5	1384.8	1384.1	1383.3	1382.6
157.5°	1410.6	1411.9	1411.9	1410.6	1409.3	1408.0	1406.7
160°	1427.2	1428.7	1428.7	1427.2	1425.7	1424.3	1422.8
162.5°	1440.6	1442.1	1442.0	1440.4	1438.6	1436.9	1435.3
165°	1460.0	1462.0	1461.8	1459.7	1457.4	1455.2	1452.9
167.5°	1473.9	1476.2	1476.0	1473.5	1471.0	1468.6	1466.1
170°	1482.3	1484.3	1484.0	1481.6	1479.1	1476.6	1474.1
172.5°	1487.7	1489.7	1489.4	1486.6	1483.9	1481.3	1478.6
175°	1494.3	1496.5	1496.1	1493.1	1490.1	1487.1	1484.2
177.5°	1496.1	1497.7	1497.3	1494.9	1492.5	1490.1	1487.7
180°	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1

(END OF REPORT)