

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333069-935

Luminaire Tested: **S124RDIW-S795D1340U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333069-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S795D1340U935-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7386.4 lumens
Efficiency: N/A
Efficacy: 120.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333069-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333069-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	104	104	104	104	94	94	94	94	76	76	76		60	60	60		45	45	45	37
1	95	91	87	84	86	83	80	77	67	65	63		53	51	50		40	39	38	32
2	87	80	74	69	79	72	67	63	59	55	52		47	44	42		35	34	32	27
3	79	70	63	57	72	64	58	53	52	48	44		41	38	36		31	29	28	23
4	73	62	54	49	66	57	50	45	46	42	38		37	34	31		28	26	24	20
5	67	55	47	42	60	51	44	39	42	37	33		33	30	27		25	23	21	17
6	61	50	42	36	55	45	39	34	37	32	28		30	26	23		23	21	19	15
7	57	45	37	32	51	41	34	29	34	29	25		27	24	21		21	18	17	14
8	53	41	33	28	48	37	31	26	31	26	22		25	21	19		19	17	15	12
9	49	37	30	25	44	34	28	23	28	23	20		23	19	17		18	15	13	11
10	46	34	27	22	41	31	25	21	26	21	18		21	18	15		17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9656	9656	9656
5°	9678	9559	9618
10°	9617	9444	9444
15°	9507	9246	9177
20°	9355	8985	8820
25°	9161	8679	8459
30°	8972	8358	8007
35°	8763	8024	7554
40°	8513	7644	7065
45°	8281	7267	6566
50°	8017	6832	6038
55°	7734	6380	5465
60°	7424	5885	4879
65°	7138	5266	4304
70°	6722	4584	3654
75°	6198	3799	2969
80°	5407	2896	2724
85°	4576	2631	2455



TEST NUMBER: P333069-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.4	1.5
10°-20°	313.3	4.2
20°-30°	452.4	6.1
30°-40°	512.8	6.9
40°-50°	495.2	6.7
50°-60°	411.8	5.6
60°-70°	284.4	3.8
70°-80°	144.1	2.0
80°-90°	41.3	0.6
90°-100°	51.1	0.7
100°-110°	325.6	4.4
110°-120°	622.9	8.4
120°-130°	790.7	10.7
130°-140°	846.0	11.5
140°-150°	791.1	10.7
150°-160°	638.0	8.6
160°-170°	411.5	5.6
170°-180°	141.8	1.9
0°-30°	878.1	11.9
0°-40°	1390.9	18.8
0°-60°	2297.9	31.1
0°-90°	2767.7	37.5
90°-120°	999.5	13.5
90°-150°	3427.4	46.4
90°-180°	4619.0	62.5
0°-180°	7386.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1196	1196	1196	1196	1196	
5°	1194	1190	1180	1188	1187	113
15°	1138	1128	1106	1104	1098	320
25°	1028	1011	974	959	950	474
35°	889	859	814	784	766	555
45°	725	690	636	593	575	559
55°	550	512	453	407	388	491
65°	374	333	276	238	225	369
75°	199	164	122	102	95	210
85°	49	32	28	27	26	56
90°	3	15	24	31	34	5
95°	61	26	24	31	32	79
105°	336	343	348	356	318	352
115°	628	631	630	632	632	617
125°	882	886	884	888	889	787
135°	1094	1094	1098	1100	1102	843
145°	1262	1265	1265	1266	1269	788
155°	1384	1385	1382	1385	1383	638
165°	1460	1454	1454	1462	1453	412
175°	1493	1487	1488	1496	1484	142
180°	1493	1493	1493	1493	1493	



TEST NUMBER: P333069-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1
2.5°	1199.0	1198.3	1197.7	1197.0	1196.4	1195.2	1193.3	1191.6	1189.8	1188.0	1189.8
5°	1194.2	1193.4	1192.6	1191.8	1190.9	1189.4	1186.9	1184.5	1182.0	1179.6	1181.6
7.5°	1183.4	1182.6	1181.7	1180.9	1180.0	1178.0	1174.8	1171.6	1168.5	1165.3	1166.6
10°	1173.2	1172.2	1171.1	1170.1	1169.1	1166.7	1163.1	1159.4	1155.8	1152.1	1152.9
12.5°	1159.9	1158.8	1157.6	1156.4	1155.3	1152.5	1148.2	1143.8	1139.5	1135.2	1135.7
15°	1137.5	1135.7	1133.8	1132.0	1130.1	1126.7	1121.5	1116.5	1111.4	1106.3	1105.9
17.5°	1110.2	1107.5	1104.8	1102.3	1099.6	1095.2	1089.1	1083.0	1076.9	1070.7	1069.6
20°	1088.9	1086.2	1083.7	1081.0	1078.3	1073.6	1066.6	1059.7	1052.7	1045.9	1044.2
22.5°	1065.5	1062.5	1059.5	1056.5	1053.6	1048.4	1040.9	1033.5	1026.1	1018.7	1016.3
25°	1028.5	1024.8	1021.1	1017.4	1013.8	1007.8	999.4	991.1	982.7	974.4	970.9
27.5°	989.6	985.1	980.4	975.9	971.2	964.5	955.5	946.7	937.7	928.8	924.5
30°	962.5	957.4	952.4	947.3	942.2	934.9	925.3	915.8	906.1	896.6	891.5
32.5°	933.9	928.2	922.5	916.7	911.0	903.2	893.3	883.4	873.5	863.6	857.7
35°	889.2	882.8	876.2	869.7	863.2	854.9	844.7	834.5	824.3	814.2	807.3
37.5°	841.5	834.7	828.0	821.3	814.6	805.6	794.4	783.1	771.8	760.5	752.8
40°	807.8	801.1	794.4	787.6	780.9	771.7	760.1	748.6	736.9	725.3	716.8
42.5°	775.5	768.4	761.5	754.4	747.3	737.8	725.7	713.6	701.5	689.4	680.7
45°	725.3	717.8	710.2	702.7	695.2	685.4	673.1	660.9	648.7	636.5	626.5
47.5°	673.5	665.7	658.0	650.1	642.4	632.1	619.5	606.7	594.1	581.3	571.0
50°	638.3	630.4	622.4	614.5	606.6	596.1	583.1	570.1	557.0	544.0	533.8
52.5°	602.4	594.7	586.9	579.1	571.4	560.8	547.4	534.1	520.7	507.4	497.1
55°	549.5	541.3	533.2	525.0	516.9	506.3	493.0	479.7	466.6	453.3	442.7
57.5°	497.1	488.6	480.2	471.7	463.2	452.5	439.5	426.5	413.5	400.4	389.7
60°	459.8	451.6	443.5	435.3	427.1	416.6	403.6	390.5	377.5	364.5	353.9
62.5°	426.0	417.6	409.1	400.6	392.2	381.3	367.9	354.6	341.2	327.9	318.1
65°	373.7	364.9	356.1	347.4	338.6	327.8	314.7	301.7	288.7	275.7	266.9
67.5°	319.3	310.9	302.5	294.1	285.7	275.5	263.4	251.3	239.2	227.1	219.6
70°	284.8	276.3	267.7	259.2	250.6	240.6	228.9	217.3	205.8	194.2	187.4
72.5°	248.2	240.5	232.7	225.0	217.2	207.9	197.0	186.0	175.0	164.1	158.3
75°	198.7	191.2	183.7	176.2	168.6	160.1	150.5	140.9	131.4	121.8	117.1
77.5°	148.5	142.2	135.8	129.4	123.0	115.9	108.2	100.5	92.7	85.0	82.2
80°	116.3	110.4	104.5	98.6	92.7	86.7	80.6	74.5	68.4	62.3	61.6
82.5°	88.5	83.1	77.7	72.2	66.8	62.3	58.9	55.4	51.8	48.4	47.9
85°	49.4	45.4	41.3	37.3	33.1	30.8	30.2	29.6	29.0	28.4	28.0
87.5°	17.5	16.8	16.0	15.2	14.5	14.2	14.5	14.7	14.9	15.2	15.3
90°	3.4	6.1	8.8	11.5	14.3	16.6	18.6	20.6	22.6	24.5	26.1
92.5°	14.0	14.2	14.4	14.6	14.6	15.8	17.7	19.7	21.7	23.7	25.1
95°	61.4	53.0	44.5	36.1	27.6	23.6	23.8	24.1	24.3	24.5	26.1
97.5°	130.4	135.7	140.9	146.2	151.4	140.3	112.5	84.9	57.2	29.4	29.6
100°	183.1	187.6	192.1	196.6	201.0	186.1	151.9	117.6	83.3	49.2	44.9
102.5°	242.1	245.4	248.7	251.9	255.2	254.6	250.1	245.7	241.3	236.8	191.2
105°	336.1	337.6	339.1	340.6	342.1	343.5	344.7	345.9	347.2	348.4	350.7
107.5°	423.4	424.2	425.0	425.7	426.5	427.7	429.4	431.0	432.7	434.5	435.5
110°	482.4	483.2	484.0	484.7	485.4	486.6	488.0	489.5	491.0	492.5	493.0



TEST NUMBER: P333069-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	539.6	541.0	542.3	543.6	545.0	546.0	546.7	547.4	548.1	548.8	548.7
115°	627.6	628.4	629.1	629.8	630.6	630.9	630.6	630.3	630.1	629.8	630.3
117.5°	706.9	707.9	708.9	709.9	710.8	711.6	712.2	712.7	713.3	713.9	713.8
120°	760.5	761.5	762.5	763.5	764.5	764.8	764.7	764.4	764.1	763.9	764.4
122.5°	810.5	811.1	811.8	812.4	813.0	813.4	813.7	814.1	814.4	814.8	815.1
125°	882.3	883.2	884.2	885.2	886.2	886.5	886.0	885.5	884.9	884.5	885.2
127.5°	950.1	950.4	950.6	950.9	951.1	951.8	953.0	954.1	955.3	956.4	956.2
130°	993.9	994.2	994.5	994.6	994.9	995.4	996.2	996.9	997.6	998.4	998.7
132.5°	1034.1	1034.6	1035.0	1035.4	1035.9	1036.6	1037.6	1038.5	1039.4	1040.3	1040.6
135°	1094.4	1094.2	1093.9	1093.7	1093.5	1093.8	1094.8	1095.8	1096.8	1097.8	1098.3
137.5°	1147.8	1147.9	1148.0	1148.1	1148.2	1148.8	1149.9	1151.0	1152.1	1153.1	1153.7
140°	1182.7	1183.2	1183.6	1184.1	1184.6	1185.2	1185.6	1186.1	1186.6	1187.1	1187.8
142.5°	1213.9	1214.8	1215.7	1216.6	1217.5	1218.1	1218.4	1218.7	1219.0	1219.3	1219.9
145°	1262.0	1262.7	1263.4	1264.2	1264.9	1265.3	1265.3	1265.3	1265.3	1265.3	1265.6
147.5°	1300.1	1301.5	1303.0	1304.3	1305.7	1306.3	1306.1	1305.8	1305.5	1305.3	1305.4
150°	1327.8	1328.9	1329.8	1330.8	1331.8	1332.1	1332.0	1331.7	1331.5	1331.2	1331.2
152.5°	1351.1	1351.9	1352.6	1353.4	1354.3	1354.4	1354.0	1353.5	1353.1	1352.6	1353.1
155°	1383.7	1383.9	1384.1	1384.4	1384.7	1384.4	1383.7	1382.9	1382.2	1381.5	1382.4
157.5°	1411.2	1411.0	1410.8	1410.7	1410.6	1410.1	1409.2	1408.3	1407.6	1406.7	1408.0
160°	1427.2	1426.5	1425.7	1425.0	1424.3	1423.7	1423.5	1423.2	1423.0	1422.8	1424.3
162.5°	1441.5	1440.5	1439.7	1438.7	1437.8	1437.2	1436.9	1436.7	1436.4	1436.1	1437.6
165°	1459.7	1458.4	1457.2	1455.9	1454.7	1454.1	1454.1	1454.1	1454.1	1454.1	1456.0
167.5°	1473.9	1472.7	1471.4	1470.1	1468.8	1468.0	1467.9	1467.7	1467.6	1467.4	1469.6
170°	1482.0	1480.5	1478.9	1477.5	1476.0	1475.4	1475.6	1475.8	1476.1	1476.4	1478.3
172.5°	1487.3	1485.8	1484.4	1482.8	1481.4	1480.7	1481.0	1481.3	1481.4	1481.7	1483.7
175°	1493.1	1491.6	1490.1	1488.7	1487.1	1486.5	1486.8	1487.0	1487.3	1487.5	1489.8
177.5°	1495.8	1494.4	1493.0	1491.6	1490.2	1489.7	1490.1	1490.6	1490.9	1491.3	1492.9
180°	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1



TEST NUMBER: P333069-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1
2.5°	1191.6	1193.3	1195.2	1196.0	1195.8	1195.7	1195.5	1195.3
5°	1183.6	1185.7	1187.7	1188.5	1188.1	1187.7	1187.3	1186.9
7.5°	1167.9	1169.2	1170.5	1170.8	1170.2	1169.5	1168.9	1168.2
10°	1153.7	1154.5	1155.4	1155.4	1154.5	1153.7	1152.9	1152.1
12.5°	1136.3	1136.7	1137.2	1136.9	1135.7	1134.6	1133.4	1132.3
15°	1105.5	1105.1	1104.7	1103.8	1102.3	1100.9	1099.5	1098.0
17.5°	1068.5	1067.4	1066.2	1064.5	1062.4	1060.2	1058.1	1055.9
20°	1042.6	1040.9	1039.3	1037.2	1034.6	1031.9	1029.2	1026.7
22.5°	1013.9	1011.4	1009.0	1006.7	1004.5	1002.4	1000.2	998.1
25°	967.5	964.1	960.6	957.9	955.8	953.8	951.7	949.7
27.5°	920.2	916.0	911.7	908.1	905.2	902.2	899.3	896.4
30°	886.4	881.3	876.2	872.0	868.8	865.6	862.3	859.0
32.5°	851.8	845.9	840.0	835.5	832.4	829.3	826.2	823.1
35°	800.3	793.4	786.5	781.2	777.6	773.9	770.2	766.5
37.5°	745.0	737.3	729.5	723.8	720.2	716.5	712.9	709.2
40°	708.3	699.6	691.1	685.0	681.4	677.7	674.1	670.4
42.5°	672.0	663.3	654.6	648.3	644.5	640.7	636.9	633.0
45°	616.6	606.6	596.6	589.8	586.1	582.5	578.8	575.1
47.5°	560.7	550.4	540.0	532.8	528.8	524.8	520.7	516.7
50°	523.7	513.5	503.3	496.3	492.4	488.5	484.7	480.8
52.5°	486.7	476.4	466.0	458.8	454.8	450.7	446.8	442.7
55°	432.1	421.5	411.0	403.8	399.9	396.1	392.2	388.3
57.5°	378.9	368.2	357.4	350.6	347.7	344.7	341.8	338.9
60°	343.4	332.8	322.2	315.2	312.0	308.8	305.5	302.2
62.5°	308.3	298.6	288.8	282.6	280.0	277.4	274.7	272.2
65°	258.1	249.4	240.6	235.1	232.6	230.1	227.7	225.3
67.5°	212.1	204.6	197.0	191.9	189.2	186.5	183.8	181.2
70°	180.7	174.0	167.3	162.9	160.9	158.9	156.8	154.8
72.5°	152.7	146.9	141.1	137.3	135.5	133.6	131.7	129.8
75°	112.4	107.8	103.1	100.1	98.9	97.7	96.4	95.2
77.5°	79.6	76.8	74.0	72.5	72.2	71.8	71.5	71.0
80°	61.0	60.4	59.8	59.4	59.2	59.0	58.8	58.6
82.5°	47.4	47.0	46.6	46.2	46.1	45.8	45.6	45.5
85°	27.6	27.2	26.8	26.5	26.5	26.5	26.5	26.5
87.5°	15.4	15.6	15.7	15.9	16.2	16.4	16.7	17.0
90°	27.6	29.0	30.6	31.5	32.0	32.5	33.0	33.5
92.5°	26.7	28.2	29.6	30.4	30.6	30.7	30.7	30.8
95°	27.6	29.0	30.6	31.4	31.6	31.9	32.1	32.4
97.5°	29.8	30.0	30.0	30.3	30.6	30.7	31.0	31.3
100°	40.7	36.5	32.3	30.3	30.6	30.7	31.0	31.3
102.5°	145.8	100.2	54.7	31.9	32.0	32.0	32.1	32.2
105°	352.9	355.2	357.4	354.0	345.1	336.1	327.2	318.3
107.5°	436.6	437.7	438.8	439.8	440.7	441.7	442.6	443.6
110°	493.5	494.0	494.5	495.1	495.8	496.6	497.3	498.1



TEST NUMBER: P333069-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	548.5	548.5	548.4	548.8	549.7	550.7	551.6	552.6
115°	630.9	631.4	631.8	632.1	632.1	632.1	632.1	632.1
117.5°	713.6	713.5	713.4	713.3	713.3	713.2	713.1	712.9
120°	764.8	765.3	765.9	765.9	765.3	764.8	764.4	763.9
122.5°	815.4	815.7	816.0	815.9	815.4	814.9	814.4	813.9
125°	886.0	886.7	887.4	887.9	888.2	888.5	888.7	889.0
127.5°	956.1	956.0	955.8	955.6	955.5	955.2	955.0	954.8
130°	998.8	999.1	999.4	999.5	999.5	999.5	999.5	999.5
132.5°	1040.9	1041.1	1041.4	1041.4	1041.2	1041.0	1040.8	1040.6
135°	1098.8	1099.2	1099.8	1100.3	1100.8	1101.2	1101.7	1102.3
137.5°	1154.3	1154.8	1155.4	1155.5	1155.4	1155.3	1155.1	1154.9
140°	1188.6	1189.4	1190.1	1190.6	1190.8	1191.1	1191.4	1191.6
142.5°	1220.4	1220.9	1221.5	1221.8	1221.8	1221.8	1221.9	1221.9
145°	1265.8	1266.0	1266.3	1266.7	1267.1	1267.7	1268.2	1268.7
147.5°	1305.7	1305.9	1306.1	1306.3	1306.6	1306.8	1307.0	1307.3
150°	1331.2	1331.2	1331.2	1331.3	1331.5	1331.8	1332.1	1332.3
152.5°	1353.4	1353.8	1354.2	1354.4	1354.2	1354.0	1353.9	1353.8
155°	1383.5	1384.4	1385.4	1385.5	1384.8	1384.1	1383.3	1382.6
157.5°	1409.3	1410.6	1411.9	1411.9	1410.6	1409.3	1408.0	1406.7
160°	1425.7	1427.2	1428.7	1428.7	1427.2	1425.7	1424.3	1422.8
162.5°	1439.2	1440.6	1442.1	1442.0	1440.4	1438.6	1436.9	1435.3
165°	1458.0	1460.0	1462.0	1461.8	1459.7	1457.4	1455.2	1452.9
167.5°	1471.8	1473.9	1476.2	1476.0	1473.5	1471.0	1468.6	1466.1
170°	1480.3	1482.3	1484.3	1484.0	1481.6	1479.1	1476.6	1474.1
172.5°	1485.7	1487.7	1489.7	1489.4	1486.6	1483.9	1481.3	1478.6
175°	1492.0	1494.3	1496.5	1496.1	1493.1	1490.1	1487.1	1484.2
177.5°	1494.5	1496.1	1497.7	1497.3	1494.9	1492.5	1490.1	1487.7
180°	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1

(END OF REPORT)