

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333055-935

Luminaire Tested: **S124RDIW-S795D470U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333055-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S795D470U935-4F0-1E-UDD-A  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 470 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4488.2 lumens  
Efficiency: N/A  
Efficacy: 119.1 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 37.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333055-935

CATALOG NUMBER: S124RDIW-S795D470U935-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333055-935

CATALOG NUMBER: S124RDIW-S795D470U935-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	104	104	104	104	91	91	91	80	80	80	69	69	69	64
1	102	97	94	90	95	92	88	85	81	78	76	71	69	68	62	61	60	55
2	93	86	80	75	87	81	76	71	72	68	64	63	60	57	55	53	51	47
3	85	76	69	63	80	72	65	60	64	59	55	56	52	49	49	47	44	41
4	78	68	60	54	73	64	57	51	57	51	47	51	46	43	45	41	38	35
5	72	61	52	47	68	57	50	45	51	45	41	46	41	37	40	37	34	31
6	67	55	46	41	62	52	44	39	46	40	36	41	37	33	37	33	30	27
7	62	49	42	36	58	47	40	35	42	36	32	38	33	29	34	30	27	24
8	57	45	37	32	54	43	36	31	39	33	29	35	30	26	31	27	24	22
9	54	41	34	29	50	39	32	28	36	30	26	32	27	24	29	25	22	20
10	50	38	31	26	47	36	30	25	33	27	23	30	25	22	27	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9175	9175	9175	9175
5°	10643	9203	8135	9203
10°	12591	9163	7260	9163
15°	14543	9078	6238	9078
20°	16192	8961	5642	8961
25°	16715	8847	5238	8847
30°	14632	8708	4994	8708
35°	11391	8502	4847	8502
40°	8541	8266	4769	8266
45°	6744	7889	4727	7889
50°	5693	7454	4589	7454
55°	4963	6973	4345	6973
60°	4466	6476	3846	6476
65°	3935	5939	3307	5939
70°	3545	5384	2984	5384
75°	2969	4769	2542	4769
80°	2515	4068	2385	4068
85°	2121	3186	2121	3186



TEST NUMBER: P333055-935

CATALOG NUMBER: S124RDIW-S795D470U935-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	110.1	2.5
10°-20°	332.2	7.4
20°-30°	519.5	11.6
30°-40°	577.6	12.9
40°-50°	512.4	11.4
50°-60°	399.3	8.9
60°-70°	261.4	5.8
70°-80°	128.6	2.9
80°-90°	33.2	0.7
90°-100°	17.8	0.4
100°-110°	113.8	2.5
110°-120°	217.6	4.8
120°-130°	276.3	6.2
130°-140°	295.6	6.6
140°-150°	276.4	6.2
150°-160°	222.9	5.0
160°-170°	143.8	3.2
170°-180°	49.6	1.1
0°-30°	961.8	21.4
0°-40°	1539.4	34.3
0°-60°	2451.2	54.6
0°-90°	2874.4	64.0
90°-120°	349.2	7.8
90°-150°	1197.5	26.7
90°-180°	1614.0	36.0
0°-180°	4488.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1136	1136	1136	1136	1136	
5°	1313	1136	1004	1136	1313	133
15°	1740	1086	746	1086	1740	495
25°	1876	993	588	993	1876	832
35°	1156	863	492	863	1156	724
45°	591	691	414	691	591	468
55°	353	495	309	495	353	321
65°	206	311	173	311	206	207
75°	95	153	82	153	95	105
85°	23	34	23	34	23	26
90°	12	1	12	1	12	6
95°	11	21	11	21	11	9
105°	111	117	111	117	111	97
115°	221	219	221	219	221	219
125°	311	308	311	308	311	277
135°	385	382	385	382	385	296
145°	443	441	443	441	443	277
155°	483	484	483	484	483	223
165°	508	510	508	510	508	143
175°	519	522	519	522	519	49
180°	522	522	522	522	522	



TEST NUMBER: P333055-935

CATALOG NUMBER: S124RDIW-S795D470U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1198.8	1202.1	1198.8	1198.4	1194.8	1193.7	1192.2	1187.5	1178.6	1173.5	1174.7
5°	1313.3	1324.7	1318.4	1317.4	1307.3	1297.3	1290.8	1276.2	1260.6	1250.1	1241.4
7.5°	1445.7	1452.3	1448.3	1441.8	1425.6	1416.3	1401.4	1382.2	1354.3	1332.9	1313.4
10°	1535.9	1541.4	1539.5	1527.6	1515.7	1491.4	1477.6	1450.7	1415.4	1387.5	1361.4
12.5°	1624.4	1630.4	1614.2	1614.8	1592.2	1573.1	1551.3	1517.3	1476.6	1440.6	1407.9
15°	1740.1	1732.8	1732.8	1723.5	1698.4	1671.8	1649.4	1613.7	1562.4	1519.3	1474.0
17.5°	1830.6	1833.1	1829.4	1807.8	1788.0	1760.5	1719.3	1677.7	1630.0	1572.3	1526.0
20°	1884.7	1884.7	1880.7	1866.0	1840.4	1811.0	1766.6	1721.3	1660.9	1602.7	1550.5
22.5°	1906.8	1908.2	1903.3	1891.3	1868.2	1839.6	1801.8	1755.8	1693.4	1628.0	1563.3
25°	1876.5	1885.2	1886.1	1882.9	1876.0	1858.6	1826.2	1779.0	1723.1	1652.2	1582.5
27.5°	1722.9	1733.8	1743.4	1759.3	1780.4	1791.3	1792.8	1768.8	1720.1	1651.7	1581.7
30°	1569.7	1578.9	1608.6	1647.5	1677.8	1705.3	1729.1	1735.5	1708.1	1646.7	1573.0
32.5°	1399.7	1412.2	1442.0	1483.8	1534.2	1580.7	1634.2	1661.5	1660.8	1623.9	1555.7
35°	1155.8	1164.9	1192.4	1236.4	1296.8	1366.0	1450.7	1516.6	1561.5	1558.2	1516.6
37.5°	932.1	942.5	970.3	1006.7	1065.3	1150.9	1232.9	1323.7	1406.7	1453.3	1439.4
40°	810.5	811.0	838.0	875.6	930.5	1005.1	1094.4	1195.2	1287.6	1363.2	1377.9
42.5°	714.5	714.6	732.5	772.9	812.5	882.8	968.0	1068.1	1176.3	1263.6	1302.4
45°	590.7	594.9	609.5	633.8	664.9	724.4	792.6	885.6	1006.9	1110.4	1175.0
47.5°	500.2	506.3	515.6	535.4	560.2	599.9	656.3	739.8	838.5	952.4	1044.2
50°	453.3	454.3	466.1	477.2	498.7	530.3	579.7	649.3	739.9	849.5	951.6
52.5°	413.0	412.8	420.0	433.9	451.4	476.0	516.0	579.4	659.8	757.9	863.2
55°	352.6	354.9	360.4	371.3	384.6	402.1	433.6	481.3	544.5	628.3	723.9
57.5°	306.6	307.8	312.1	316.8	329.0	341.6	365.3	398.4	451.7	520.3	609.5
60°	276.6	277.1	278.4	285.2	294.9	306.8	322.8	350.8	395.6	458.4	528.9
62.5°	247.3	248.1	250.2	255.2	262.7	270.9	287.7	310.1	347.2	400.9	464.4
65°	206.0	206.6	209.7	211.5	217.5	224.8	237.2	252.3	277.9	322.8	370.9
67.5°	172.2	172.2	172.4	174.9	178.9	183.8	191.2	203.3	222.7	250.2	292.6
70°	150.2	150.2	151.1	152.5	154.8	158.9	163.0	172.2	186.4	208.8	241.3
72.5°	129.7	130.0	131.0	131.2	132.4	135.8	138.9	144.7	155.2	172.2	198.5
75°	95.2	96.6	98.9	100.7	103.1	102.5	105.8	109.4	112.6	122.7	137.8
77.5°	70.9	70.2	70.4	72.0	72.2	72.8	75.0	77.8	80.2	85.0	90.4
80°	54.1	54.1	55.4	55.9	55.4	55.9	58.1	59.5	60.4	62.3	67.3
82.5°	40.8	41.6	41.2	41.6	41.8	42.3	44.3	44.5	45.5	46.1	48.3
85°	22.9	23.3	23.8	22.9	22.9	22.9	23.8	24.3	25.2	24.7	25.7
87.5°	10.4	10.0	10.3	10.3	10.6	10.2	10.4	11.1	10.2	10.5	10.3
90°	11.7	11.5	11.4	11.2	11.0	10.7	10.2	9.6	9.1	8.6	7.9
92.5°	10.8	10.8	10.7	10.7	10.6	10.3	9.8	9.3	8.8	8.3	7.6
95°	11.3	11.2	11.1	11.0	10.9	10.7	10.2	9.6	9.1	8.6	8.5
97.5°	10.9	10.8	10.8	10.7	10.6	10.5	10.4	10.4	10.3	10.3	20.0
100°	10.9	10.8	10.8	10.7	10.6	11.3	12.7	14.2	15.7	17.1	29.1
102.5°	11.3	11.2	11.2	11.2	11.2	19.1	35.0	50.9	66.8	82.7	84.3
105°	111.2	114.3	117.4	120.5	123.7	124.8	124.1	123.3	122.5	121.7	121.3
107.5°	155.0	154.6	154.3	154.0	153.7	153.3	152.9	152.6	152.1	151.8	151.2
110°	174.0	173.7	173.5	173.2	173.0	172.8	172.6	172.5	172.3	172.1	171.6



TEST NUMBER: P333055-935

CATALOG NUMBER: S124RDIW-S795D470U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	193.0	192.8	192.4	192.1	191.7	191.6	191.7	191.7	191.7	191.7	191.5
115°	220.8	220.8	220.8	220.8	220.8	220.8	220.6	220.4	220.2	220.1	220.2
117.5°	249.1	249.2	249.2	249.2	249.3	249.3	249.3	249.3	249.3	249.4	249.3
120°	266.9	267.1	267.3	267.4	267.6	267.6	267.4	267.3	267.1	266.9	267.0
122.5°	284.4	284.6	284.7	284.9	285.1	285.1	285.0	284.9	284.8	284.7	284.6
125°	310.6	310.5	310.4	310.3	310.2	310.0	309.8	309.5	309.3	309.0	309.2
127.5°	333.6	333.7	333.7	333.8	333.9	334.0	334.0	334.1	334.2	334.2	333.8
130°	349.2	349.2	349.2	349.2	349.2	349.2	349.1	349.0	349.0	348.9	348.6
132.5°	363.6	363.7	363.8	363.8	363.9	363.9	363.8	363.7	363.6	363.5	363.2
135°	385.1	385.0	384.8	384.6	384.4	384.3	384.1	383.9	383.7	383.6	383.2
137.5°	403.6	403.6	403.6	403.7	403.7	403.7	403.5	403.3	403.1	402.9	402.5
140°	416.4	416.3	416.2	416.1	416.0	415.9	415.6	415.3	415.1	414.8	414.7
142.5°	427.0	427.0	427.0	426.9	426.9	426.8	426.6	426.4	426.2	426.0	425.9
145°	443.2	443.1	442.9	442.7	442.6	442.5	442.4	442.3	442.2	442.1	442.1
147.5°	456.8	456.7	456.6	456.5	456.4	456.3	456.2	456.2	456.2	456.1	456.2
150°	465.5	465.5	465.4	465.3	465.2	465.1	465.1	465.1	465.1	465.1	465.2
152.5°	473.0	473.0	473.1	473.2	473.2	473.2	473.0	472.9	472.8	472.6	472.8
155°	483.1	483.4	483.6	483.9	484.1	484.1	483.7	483.4	483.0	482.7	482.9
157.5°	491.5	492.0	492.4	492.8	493.3	493.3	492.8	492.4	492.0	491.5	491.8
160°	497.1	497.7	498.2	498.7	499.2	499.2	498.7	498.2	497.7	497.1	497.2
162.5°	501.5	502.0	502.7	503.3	503.9	503.9	503.3	502.8	502.3	501.8	501.9
165°	507.6	508.4	509.2	510.0	510.7	510.8	510.1	509.5	508.8	508.1	508.1
167.5°	512.3	513.2	514.0	514.9	515.7	515.8	515.1	514.3	513.5	512.7	512.8
170°	515.1	515.9	516.8	517.6	518.6	518.7	517.9	517.2	516.5	515.8	515.7
172.5°	516.6	517.5	518.5	519.4	520.4	520.5	519.8	519.1	518.4	517.7	517.6
175°	518.6	519.6	520.6	521.7	522.7	522.9	522.1	521.3	520.6	519.8	519.7
177.5°	519.9	520.6	521.5	522.4	523.1	523.3	522.7	522.2	521.6	521.1	520.9
180°	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7



TEST NUMBER: P333055-935

CATALOG NUMBER: S124RDIW-S795D470U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1171.0	1165.9	1163.3	1157.4	1150.5	1146.8	1143.5	1138.8	1132.5	1125.9	1121.1
5°	1230.4	1219.4	1205.7	1189.2	1174.6	1160.4	1148.0	1135.7	1121.5	1106.7	1092.1
7.5°	1291.4	1269.8	1246.5	1219.4	1193.2	1169.2	1147.3	1126.2	1102.3	1081.1	1061.6
10°	1333.9	1304.6	1272.0	1237.8	1203.4	1173.6	1144.4	1117.8	1088.5	1062.4	1040.3
12.5°	1368.3	1333.9	1294.8	1252.0	1210.7	1174.7	1141.0	1106.4	1073.1	1044.7	1015.5
15°	1425.5	1378.3	1325.7	1274.4	1220.8	1171.8	1126.4	1086.2	1048.2	1008.3	980.4
17.5°	1464.7	1408.8	1344.8	1283.1	1219.9	1162.1	1109.8	1061.8	1018.0	977.2	944.0
20°	1488.2	1426.4	1355.4	1285.4	1214.4	1152.5	1096.2	1043.1	997.8	953.8	919.5
22.5°	1501.4	1433.0	1355.4	1282.0	1208.5	1141.6	1079.8	1024.4	975.1	931.1	893.1
25°	1505.6	1432.4	1353.1	1268.9	1188.3	1117.3	1053.2	993.2	938.2	894.3	854.0
27.5°	1499.8	1413.5	1332.3	1245.9	1162.7	1087.9	1020.6	957.6	902.6	855.4	814.1
30°	1491.0	1398.4	1311.5	1221.7	1137.5	1065.6	994.5	934.1	876.9	827.9	786.3
32.5°	1471.9	1380.2	1286.5	1194.6	1109.2	1035.2	967.9	907.1	850.9	800.8	756.6
35°	1434.2	1341.3	1239.6	1145.2	1061.4	984.5	921.4	862.7	809.2	755.5	708.9
37.5°	1384.5	1289.5	1188.4	1085.0	1001.2	928.6	870.6	815.5	763.3	714.4	662.6
40°	1337.6	1251.0	1146.6	1044.0	957.9	887.9	834.3	784.4	731.8	683.2	631.5
42.5°	1280.7	1207.0	1101.6	998.6	913.6	846.1	796.3	747.4	699.5	652.5	598.5
45°	1186.0	1130.1	1031.2	932.3	846.7	779.8	734.0	691.0	648.8	604.0	553.2
47.5°	1077.4	1039.6	954.2	852.9	773.7	713.5	669.3	634.1	598.5	553.6	509.0
50°	1001.9	977.7	895.2	802.7	727.2	671.8	626.5	593.5	563.7	520.6	480.8
52.5°	921.4	908.4	838.8	750.4	677.3	623.0	584.3	554.7	524.5	488.8	451.5
55°	798.6	805.5	746.4	669.9	601.2	555.4	520.2	495.4	469.8	439.6	410.8
57.5°	673.1	698.2	658.6	591.4	527.0	484.7	458.2	437.4	415.9	390.8	366.2
60°	598.1	619.1	596.7	537.6	481.3	441.9	417.2	401.1	379.6	356.7	337.9
62.5°	524.8	547.3	534.0	486.3	434.0	400.1	378.3	363.4	347.4	327.4	307.9
65°	432.7	447.4	441.0	408.0	370.9	342.1	321.9	310.9	296.3	281.6	264.2
67.5°	331.4	359.7	356.0	338.5	306.4	283.9	270.7	261.0	247.6	236.8	224.9
70°	272.4	298.6	298.1	283.9	266.5	245.5	236.3	228.1	216.1	205.6	196.0
72.5°	223.0	246.9	250.5	239.6	227.6	211.7	202.9	197.3	185.7	178.5	170.7
75°	156.2	173.6	178.1	178.1	172.6	164.4	156.6	152.9	144.7	138.3	133.7
77.5°	102.4	113.4	120.5	122.2	123.0	120.3	113.8	111.2	105.0	102.6	98.2
80°	72.3	79.6	87.9	90.7	93.0	92.0	89.3	87.5	81.5	79.2	77.4
82.5°	50.0	54.1	60.8	66.8	66.2	68.6	66.2	64.7	60.3	59.4	57.6
85°	26.1	26.5	27.5	31.6	33.9	34.8	35.3	34.4	33.0	33.0	29.8
87.5°	10.2	9.7	10.3	10.2	10.3	11.6	12.5	12.7	11.8	10.8	10.0
90°	7.2	6.5	5.8	5.0	4.0	3.1	2.2	1.2	2.2	3.1	4.0
92.5°	6.9	6.2	5.5	5.2	5.1	5.0	5.0	4.9	5.0	5.0	5.1
95°	8.4	8.4	8.3	9.6	12.7	15.6	18.5	21.4	18.5	15.6	12.7
97.5°	29.6	39.3	49.0	53.0	51.1	49.2	47.4	45.5	47.4	49.2	51.1
100°	41.1	53.0	65.0	70.3	68.7	67.2	65.5	64.0	65.5	67.2	68.7
102.5°	85.8	87.4	88.9	89.2	88.0	86.9	85.8	84.6	85.8	86.9	88.0
105°	120.9	120.5	120.0	119.5	119.0	118.5	118.0	117.4	118.0	118.5	119.0
107.5°	150.6	150.0	149.5	149.0	148.8	148.5	148.3	148.0	148.3	148.5	148.8
110°	171.1	170.5	170.0	169.6	169.4	169.1	168.8	168.6	168.8	169.1	169.4





TEST NUMBER: P333055-935

CATALOG NUMBER: S124RDIW-S795D470U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	191.2	191.1	190.8	190.5	189.9	189.5	189.0	188.6	189.0	189.5	189.9
115°	220.2	220.3	220.4	220.3	220.1	219.8	219.6	219.3	219.6	219.8	220.1
117.5°	249.0	248.8	248.7	248.4	248.1	247.7	247.4	247.0	247.4	247.7	248.1
120°	267.1	267.2	267.3	267.1	266.7	266.4	266.0	265.7	266.0	266.4	266.7
122.5°	284.5	284.3	284.2	284.0	283.9	283.6	283.4	283.2	283.4	283.6	283.9
125°	309.4	309.5	309.7	309.6	309.3	308.9	308.6	308.2	308.6	308.9	309.3
127.5°	333.4	332.9	332.6	332.3	332.3	332.2	332.1	332.0	332.1	332.2	332.3
130°	348.4	348.1	347.8	347.7	347.6	347.5	347.3	347.2	347.3	347.5	347.6
132.5°	362.8	362.6	362.2	362.0	361.8	361.6	361.4	361.4	361.4	361.6	361.8
135°	382.9	382.5	382.2	382.0	382.1	382.2	382.3	382.4	382.3	382.2	382.1
137.5°	402.2	401.7	401.4	401.2	401.1	401.1	401.1	401.1	401.1	401.1	401.1
140°	414.5	414.2	414.1	413.9	413.7	413.5	413.4	413.2	413.4	413.5	413.7
142.5°	425.9	425.7	425.6	425.4	425.1	424.8	424.5	424.1	424.5	424.8	425.1
145°	442.1	442.1	442.1	442.0	441.7	441.4	441.2	440.9	441.2	441.4	441.7
147.5°	456.2	456.3	456.4	456.2	455.7	455.2	454.8	454.3	454.8	455.2	455.7
150°	465.3	465.4	465.5	465.4	465.0	464.7	464.3	464.0	464.3	464.7	465.0
152.5°	472.9	473.1	473.2	473.2	472.9	472.6	472.3	472.1	472.3	472.6	472.9
155°	483.2	483.5	483.7	483.8	483.7	483.6	483.5	483.5	483.5	483.6	483.7
157.5°	492.1	492.4	492.7	492.8	492.9	492.9	493.0	493.1	493.0	492.9	492.9
160°	497.3	497.4	497.5	497.7	497.9	498.2	498.4	498.7	498.4	498.2	497.9
162.5°	502.0	502.0	502.1	502.4	502.7	503.0	503.3	503.7	503.3	503.0	502.7
165°	508.1	508.1	508.1	508.2	508.7	509.1	509.5	510.0	509.5	509.1	508.7
167.5°	512.8	512.9	512.9	513.2	513.7	514.1	514.5	515.0	514.5	514.1	513.7
170°	515.7	515.6	515.5	515.7	516.3	516.8	517.3	517.8	517.3	516.8	516.3
172.5°	517.5	517.5	517.4	517.6	518.1	518.7	519.2	519.7	519.2	518.7	518.1
175°	519.6	519.5	519.4	519.6	520.1	520.6	521.2	521.7	521.2	520.6	520.1
177.5°	520.8	520.6	520.6	520.7	521.2	521.7	522.2	522.6	522.2	521.7	521.2
180°	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7



TEST NUMBER: P333055-935

CATALOG NUMBER: S124RDIW-S795D470U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1116.0	1112.3	1107.6	1102.1	1095.5	1089.7	1087.1	1089.3	1090.4	1087.4	1087.1
5°	1082.0	1070.6	1061.4	1047.7	1036.7	1027.5	1021.1	1018.4	1019.3	1012.0	1010.1
7.5°	1043.9	1030.3	1015.3	999.0	983.8	970.3	963.3	959.4	951.7	948.3	942.7
10°	1019.3	1001.0	986.4	967.1	949.7	933.7	925.9	919.5	911.7	908.0	900.3
12.5°	994.0	972.8	956.7	936.7	918.9	899.6	892.2	880.3	868.1	860.4	850.4
15°	958.4	932.8	913.1	889.2	868.2	846.2	826.6	804.5	796.3	778.9	768.9
17.5°	916.7	890.7	866.3	834.4	801.9	774.6	753.6	732.5	720.0	708.9	703.7
20°	889.2	865.5	831.6	794.4	758.3	728.1	711.1	697.4	683.6	675.9	670.4
22.5°	863.2	832.8	793.5	753.5	717.3	693.6	679.2	665.1	654.0	646.6	639.2
25°	819.7	779.8	738.1	692.3	667.6	647.0	631.5	620.0	613.1	603.6	599.9
27.5°	774.9	726.6	680.6	649.9	624.1	605.3	591.7	583.1	574.4	568.3	563.5
30°	740.5	691.5	650.2	621.0	594.9	579.3	568.3	558.2	551.3	546.3	542.6
32.5°	706.4	657.4	622.8	591.2	570.7	555.4	543.7	536.2	530.8	524.3	522.1
35°	657.1	613.6	583.4	555.0	533.9	520.2	511.0	503.3	498.7	496.8	495.4
37.5°	609.8	574.1	541.7	518.3	499.6	488.8	477.9	474.2	471.0	467.7	469.2
40°	579.7	546.3	517.5	492.8	477.6	465.7	459.3	454.7	451.9	451.9	451.9
42.5°	553.7	521.0	492.9	470.7	455.6	445.6	438.4	434.5	433.6	433.3	435.5
45°	513.3	483.1	454.7	436.4	423.5	413.5	409.4	406.1	406.1	408.0	408.5
47.5°	473.3	445.0	422.2	401.7	389.9	383.7	380.0	378.4	378.6	380.5	382.5
50°	448.8	420.9	398.4	380.0	369.1	363.1	359.9	359.0	359.9	359.9	363.1
52.5°	422.0	397.0	375.0	359.6	347.1	341.5	339.8	338.5	339.1	340.5	341.9
55°	382.8	360.4	339.3	324.7	315.5	311.9	307.7	308.2	307.3	308.2	308.2
57.5°	343.5	323.4	303.8	292.1	284.1	278.8	274.3	275.6	274.2	274.1	273.3
60°	318.2	296.3	280.7	270.2	261.0	256.4	252.3	253.2	251.8	250.9	249.1
62.5°	290.8	272.4	257.6	247.5	240.1	234.8	230.7	229.8	226.6	223.4	219.5
65°	250.9	235.8	222.6	212.9	206.0	201.9	198.7	196.0	189.1	181.8	178.1
67.5°	212.2	201.3	188.9	180.8	175.2	169.8	163.7	159.0	152.6	148.5	146.3
70°	187.3	176.8	166.3	158.4	152.5	147.5	140.6	137.4	132.8	131.0	128.6
72.5°	163.5	153.7	143.9	136.8	130.5	126.6	121.1	118.0	116.0	115.2	113.0
75°	127.3	119.5	112.2	105.8	100.7	98.0	95.7	93.4	92.5	88.3	86.1
77.5°	92.9	87.7	83.2	78.6	75.0	73.2	68.8	66.1	64.6	62.7	62.2
80°	72.3	68.7	64.1	61.4	56.3	54.5	52.7	52.2	51.7	51.3	50.8
82.5°	54.4	50.7	46.1	44.5	43.1	42.0	40.9	40.5	40.0	40.3	40.2
85°	27.5	25.7	25.7	25.2	24.7	24.3	23.8	23.8	23.3	23.8	23.3
87.5°	10.2	10.0	10.1	9.5	10.0	10.2	9.9	10.0	10.4	9.8	9.9
90°	5.0	5.8	6.5	7.2	7.9	8.6	9.1	9.6	10.2	10.7	11.0
92.5°	5.2	5.5	6.2	6.9	7.6	8.3	8.8	9.3	9.8	10.3	10.6
95°	9.6	8.3	8.4	8.4	8.5	8.6	9.1	9.6	10.2	10.7	10.9
97.5°	53.0	49.0	39.3	29.6	20.0	10.3	10.3	10.4	10.4	10.5	10.6
100°	70.3	65.0	53.0	41.1	29.1	17.1	15.7	14.2	12.7	11.3	10.6
102.5°	89.2	88.9	87.4	85.8	84.3	82.7	66.8	50.9	35.0	19.1	11.2
105°	119.5	120.0	120.5	120.9	121.3	121.7	122.5	123.3	124.1	124.8	123.7
107.5°	149.0	149.5	150.0	150.6	151.2	151.8	152.1	152.6	152.9	153.3	153.7
110°	169.6	170.0	170.5	171.1	171.6	172.1	172.3	172.5	172.6	172.8	173.0



TEST NUMBER: P333055-935

CATALOG NUMBER: S124RDIW-S795D470U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	190.5	190.8	191.1	191.2	191.5	191.7	191.7	191.7	191.7	191.6	191.7
115°	220.3	220.4	220.3	220.2	220.2	220.1	220.2	220.4	220.6	220.8	220.8
117.5°	248.4	248.7	248.8	249.0	249.3	249.4	249.3	249.3	249.3	249.3	249.3
120°	267.1	267.3	267.2	267.1	267.0	266.9	267.1	267.3	267.4	267.6	267.6
122.5°	284.0	284.2	284.3	284.5	284.6	284.7	284.8	284.9	285.0	285.1	285.1
125°	309.6	309.7	309.5	309.4	309.2	309.0	309.3	309.5	309.8	310.0	310.2
127.5°	332.3	332.6	332.9	333.4	333.8	334.2	334.2	334.1	334.0	334.0	333.9
130°	347.7	347.8	348.1	348.4	348.6	348.9	349.0	349.0	349.1	349.2	349.2
132.5°	362.0	362.2	362.6	362.8	363.2	363.5	363.6	363.7	363.8	363.9	363.9
135°	382.0	382.2	382.5	382.9	383.2	383.6	383.7	383.9	384.1	384.3	384.4
137.5°	401.2	401.4	401.7	402.2	402.5	402.9	403.1	403.3	403.5	403.7	403.7
140°	413.9	414.1	414.2	414.5	414.7	414.8	415.1	415.3	415.6	415.9	416.0
142.5°	425.4	425.6	425.7	425.9	425.9	426.0	426.2	426.4	426.6	426.8	426.9
145°	442.0	442.1	442.1	442.1	442.1	442.1	442.2	442.3	442.4	442.5	442.6
147.5°	456.2	456.4	456.3	456.2	456.2	456.1	456.2	456.2	456.2	456.3	456.4
150°	465.4	465.5	465.4	465.3	465.2	465.1	465.1	465.1	465.1	465.1	465.2
152.5°	473.2	473.2	473.1	472.9	472.8	472.6	472.8	472.9	473.0	473.2	473.2
155°	483.8	483.7	483.5	483.2	482.9	482.7	483.0	483.4	483.7	484.1	484.1
157.5°	492.8	492.7	492.4	492.1	491.8	491.5	492.0	492.4	492.8	493.3	493.3
160°	497.7	497.5	497.4	497.3	497.2	497.1	497.7	498.2	498.7	499.2	499.2
162.5°	502.4	502.1	502.0	502.0	501.9	501.8	502.3	502.8	503.3	503.9	503.9
165°	508.2	508.1	508.1	508.1	508.1	508.1	508.8	509.5	510.1	510.8	510.7
167.5°	513.2	512.9	512.9	512.8	512.8	512.7	513.5	514.3	515.1	515.8	515.7
170°	515.7	515.5	515.6	515.7	515.7	515.8	516.5	517.2	517.9	518.7	518.6
172.5°	517.6	517.4	517.5	517.5	517.6	517.7	518.4	519.1	519.8	520.5	520.4
175°	519.6	519.4	519.5	519.6	519.7	519.8	520.6	521.3	522.1	522.9	522.7
177.5°	520.7	520.6	520.6	520.8	520.9	521.1	521.6	522.2	522.7	523.3	523.1
180°	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7



TEST NUMBER: P333055-935

CATALOG NUMBER: S124RDIW-S795D470U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1084.9	1085.6	1083.1	1082.3	1083.1	1085.6	1084.9	1087.1	1087.4	1090.4	1089.3
5°	1006.5	1005.6	1003.3	1003.8	1003.3	1005.6	1006.5	1010.1	1012.0	1019.3	1018.4
7.5°	939.4	935.9	936.9	933.2	936.9	935.9	939.4	942.7	948.3	951.7	959.4
10°	898.5	893.4	889.2	885.6	889.2	893.4	898.5	900.3	908.0	911.7	919.5
12.5°	842.4	838.1	832.5	833.6	832.5	838.1	842.4	850.4	860.4	868.1	880.3
15°	762.8	756.0	745.0	746.4	745.0	756.0	762.8	768.9	778.9	796.3	804.5
17.5°	695.6	695.7	690.6	691.8	690.6	695.7	695.6	703.7	708.9	720.0	732.5
20°	660.7	657.5	658.0	656.7	658.0	657.5	660.7	670.4	675.9	683.6	697.4
22.5°	636.6	632.7	629.5	626.6	629.5	632.7	636.6	639.2	646.6	654.0	665.1
25°	595.7	593.0	588.8	588.0	588.8	593.0	595.7	599.9	603.6	613.1	620.0
27.5°	559.8	559.3	557.7	555.5	557.7	559.3	559.8	563.5	568.3	574.4	583.1
30°	539.0	538.0	537.1	535.7	537.1	538.0	539.0	542.6	546.3	551.3	558.2
32.5°	520.3	519.7	518.8	518.9	518.8	519.7	520.3	522.1	524.3	530.8	536.2
35°	493.6	493.2	492.2	491.8	492.2	493.2	493.6	495.4	496.8	498.7	503.3
37.5°	468.7	469.9	469.3	469.2	469.3	469.9	468.7	469.2	467.7	471.0	474.2
40°	451.5	451.9	452.9	452.5	452.9	451.9	451.5	451.9	451.9	451.9	454.7
42.5°	437.2	437.3	438.6	437.0	438.6	437.3	437.2	435.5	433.3	433.6	434.5
45°	411.6	414.4	414.0	414.0	414.0	414.4	411.6	408.5	408.0	406.1	406.1
47.5°	383.7	386.1	386.8	386.7	386.8	386.1	383.7	382.5	380.5	378.6	378.4
50°	365.4	364.5	365.8	365.4	365.8	364.5	365.4	363.1	359.9	359.9	359.0
52.5°	343.1	343.3	343.2	342.7	343.2	343.3	343.1	341.9	340.5	339.1	338.5
55°	308.7	309.1	308.2	308.7	308.2	309.1	308.7	308.2	308.2	307.3	308.2
57.5°	271.3	269.1	270.0	268.9	270.0	269.1	271.3	273.3	274.1	274.2	275.6
60°	244.5	240.8	240.0	238.2	240.0	240.8	244.5	249.1	250.9	251.8	253.2
62.5°	214.5	211.9	208.8	210.3	208.8	211.9	214.5	219.5	223.4	226.6	229.8
65°	174.4	172.6	171.3	173.1	171.3	172.6	174.4	178.1	181.8	189.1	196.0
67.5°	144.4	143.4	143.4	142.5	143.4	143.4	144.4	146.3	148.5	152.6	159.0
70°	128.6	127.3	127.3	126.4	127.3	127.3	128.6	128.6	131.0	132.8	137.4
72.5°	112.5	111.2	111.6	111.0	111.6	111.2	112.5	113.0	115.2	116.0	118.0
75°	83.3	81.0	81.0	81.5	81.0	81.0	83.3	86.1	88.3	92.5	93.4
77.5°	62.2	61.7	62.3	61.6	62.3	61.7	62.2	62.2	62.7	64.6	66.1
80°	50.8	50.4	49.9	51.3	49.9	50.4	50.8	50.8	51.3	51.7	52.2
82.5°	39.4	39.3	39.3	41.1	39.3	39.3	39.4	40.2	40.3	40.0	40.5
85°	23.8	22.9	23.8	22.9	23.8	22.9	23.8	23.3	23.8	23.3	23.8
87.5°	10.7	10.3	10.0	10.4	10.0	10.3	10.7	9.9	9.8	10.4	10.0
90°	11.2	11.4	11.5	11.7	11.5	11.4	11.2	11.0	10.7	10.2	9.6
92.5°	10.7	10.7	10.8	10.8	10.8	10.7	10.7	10.6	10.3	9.8	9.3
95°	11.0	11.1	11.2	11.3	11.2	11.1	11.0	10.9	10.7	10.2	9.6
97.5°	10.7	10.8	10.8	10.9	10.8	10.8	10.7	10.6	10.5	10.4	10.4
100°	10.7	10.8	10.8	10.9	10.8	10.8	10.7	10.6	11.3	12.7	14.2
102.5°	11.2	11.2	11.2	11.3	11.2	11.2	11.2	11.2	19.1	35.0	50.9
105°	120.5	117.4	114.3	111.2	114.3	117.4	120.5	123.7	124.8	124.1	123.3
107.5°	154.0	154.3	154.6	155.0	154.6	154.3	154.0	153.7	153.3	152.9	152.6
110°	173.2	173.5	173.7	174.0	173.7	173.5	173.2	173.0	172.8	172.6	172.5



TEST NUMBER: P333055-935

CATALOG NUMBER: S124RDIW-S795D470U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	192.1	192.4	192.8	193.0	192.8	192.4	192.1	191.7	191.6	191.7	191.7
115°	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.6	220.4
117.5°	249.2	249.2	249.2	249.1	249.2	249.2	249.2	249.3	249.3	249.3	249.3
120°	267.4	267.3	267.1	266.9	267.1	267.3	267.4	267.6	267.6	267.4	267.3
122.5°	284.9	284.7	284.6	284.4	284.6	284.7	284.9	285.1	285.1	285.0	284.9
125°	310.3	310.4	310.5	310.6	310.5	310.4	310.3	310.2	310.0	309.8	309.5
127.5°	333.8	333.7	333.7	333.6	333.7	333.7	333.8	333.9	334.0	334.0	334.1
130°	349.2	349.2	349.2	349.2	349.2	349.2	349.2	349.2	349.2	349.1	349.0
132.5°	363.8	363.8	363.7	363.6	363.7	363.8	363.8	363.9	363.9	363.8	363.7
135°	384.6	384.8	385.0	385.1	385.0	384.8	384.6	384.4	384.3	384.1	383.9
137.5°	403.7	403.6	403.6	403.6	403.6	403.6	403.7	403.7	403.7	403.5	403.3
140°	416.1	416.2	416.3	416.4	416.3	416.2	416.1	416.0	415.9	415.6	415.3
142.5°	426.9	427.0	427.0	427.0	427.0	427.0	426.9	426.9	426.8	426.6	426.4
145°	442.7	442.9	443.1	443.2	443.1	442.9	442.7	442.6	442.5	442.4	442.3
147.5°	456.5	456.6	456.7	456.8	456.7	456.6	456.5	456.4	456.3	456.2	456.2
150°	465.3	465.4	465.5	465.5	465.5	465.4	465.3	465.2	465.1	465.1	465.1
152.5°	473.2	473.1	473.0	473.0	473.0	473.1	473.2	473.2	473.2	473.0	472.9
155°	483.9	483.6	483.4	483.1	483.4	483.6	483.9	484.1	484.1	483.7	483.4
157.5°	492.8	492.4	492.0	491.5	492.0	492.4	492.8	493.3	493.3	492.8	492.4
160°	498.7	498.2	497.7	497.1	497.7	498.2	498.7	499.2	499.2	498.7	498.2
162.5°	503.3	502.7	502.0	501.5	502.0	502.7	503.3	503.9	503.9	503.3	502.8
165°	510.0	509.2	508.4	507.6	508.4	509.2	510.0	510.7	510.8	510.1	509.5
167.5°	514.9	514.0	513.2	512.3	513.2	514.0	514.9	515.7	515.8	515.1	514.3
170°	517.6	516.8	515.9	515.1	515.9	516.8	517.6	518.6	518.7	517.9	517.2
172.5°	519.4	518.5	517.5	516.6	517.5	518.5	519.4	520.4	520.5	519.8	519.1
175°	521.7	520.6	519.6	518.6	519.6	520.6	521.7	522.7	522.9	522.1	521.3
177.5°	522.4	521.5	520.6	519.9	520.6	521.5	522.4	523.1	523.3	522.7	522.2
180°	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7



TEST NUMBER: P333055-935

CATALOG NUMBER: S124RDIW-S795D470U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1087.1	1089.7	1095.5	1102.1	1107.6	1112.3	1116.0	1121.1	1125.9	1132.5	1138.8
5°	1021.1	1027.5	1036.7	1047.7	1061.4	1070.6	1082.0	1092.1	1106.7	1121.5	1135.7
7.5°	963.3	970.3	983.8	999.0	1015.3	1030.3	1043.9	1061.6	1081.1	1102.3	1126.2
10°	925.9	933.7	949.7	967.1	986.4	1001.0	1019.3	1040.3	1062.4	1088.5	1117.8
12.5°	892.2	899.6	918.9	936.7	956.7	972.8	994.0	1015.5	1044.7	1073.1	1106.4
15°	826.6	846.2	868.2	889.2	913.1	932.8	958.4	980.4	1008.3	1048.2	1086.2
17.5°	753.6	774.6	801.9	834.4	866.3	890.7	916.7	944.0	977.2	1018.0	1061.8
20°	711.1	728.1	758.3	794.4	831.6	865.5	889.2	919.5	953.8	997.8	1043.1
22.5°	679.2	693.6	717.3	753.5	793.5	832.8	863.2	893.1	931.1	975.1	1024.4
25°	631.5	647.0	667.6	692.3	738.1	779.8	819.7	854.0	894.3	938.2	993.2
27.5°	591.7	605.3	624.1	649.9	680.6	726.6	774.9	814.1	855.4	902.6	957.6
30°	568.3	579.3	594.9	621.0	650.2	691.5	740.5	786.3	827.9	876.9	934.1
32.5°	543.7	555.4	570.7	591.2	622.8	657.4	706.4	756.6	800.8	850.9	907.1
35°	511.0	520.2	533.9	555.0	583.4	613.6	657.1	708.9	755.5	809.2	862.7
37.5°	477.9	488.8	499.6	518.3	541.7	574.1	609.8	662.6	714.4	763.3	815.5
40°	459.3	465.7	477.6	492.8	517.5	546.3	579.7	631.5	683.2	731.8	784.4
42.5°	438.4	445.6	455.6	470.7	492.9	521.0	553.7	598.5	652.5	699.5	747.4
45°	409.4	413.5	423.5	436.4	454.7	483.1	513.3	553.2	604.0	648.8	691.0
47.5°	380.0	383.7	389.9	401.7	422.2	445.0	473.3	509.0	553.6	598.5	634.1
50°	359.9	363.1	369.1	380.0	398.4	420.9	448.8	480.8	520.6	563.7	593.5
52.5°	339.8	341.5	347.1	359.6	375.0	397.0	422.0	451.5	488.8	524.5	554.7
55°	307.7	311.9	315.5	324.7	339.3	360.4	382.8	410.8	439.6	469.8	495.4
57.5°	274.3	278.8	284.1	292.1	303.8	323.4	343.5	366.2	390.8	415.9	437.4
60°	252.3	256.4	261.0	270.2	280.7	296.3	318.2	337.9	356.7	379.6	401.1
62.5°	230.7	234.8	240.1	247.5	257.6	272.4	290.8	307.9	327.4	347.4	363.4
65°	198.7	201.9	206.0	212.9	222.6	235.8	250.9	264.2	281.6	296.3	310.9
67.5°	163.7	169.8	175.2	180.8	188.9	201.3	212.2	224.9	236.8	247.6	261.0
70°	140.6	147.5	152.5	158.4	166.3	176.8	187.3	196.0	205.6	216.1	228.1
72.5°	121.1	126.6	130.5	136.8	143.9	153.7	163.5	170.7	178.5	185.7	197.3
75°	95.7	98.0	100.7	105.8	112.2	119.5	127.3	133.7	138.3	144.7	152.9
77.5°	68.8	73.2	75.0	78.6	83.2	87.7	92.9	98.2	102.6	105.0	111.2
80°	52.7	54.5	56.3	61.4	64.1	68.7	72.3	77.4	79.2	81.5	87.5
82.5°	40.9	42.0	43.1	44.5	46.1	50.7	54.4	57.6	59.4	60.3	64.7
85°	23.8	24.3	24.7	25.2	25.7	25.7	27.5	29.8	33.0	33.0	34.4
87.5°	9.9	10.2	10.0	9.5	10.1	10.0	10.2	10.0	10.8	11.8	12.7
90°	9.1	8.6	7.9	7.2	6.5	5.8	5.0	4.0	3.1	2.2	1.2
92.5°	8.8	8.3	7.6	6.9	6.2	5.5	5.2	5.1	5.0	5.0	4.9
95°	9.1	8.6	8.5	8.4	8.4	8.3	9.6	12.7	15.6	18.5	21.4
97.5°	10.3	10.3	20.0	29.6	39.3	49.0	53.0	51.1	49.2	47.4	45.5
100°	15.7	17.1	29.1	41.1	53.0	65.0	70.3	68.7	67.2	65.5	64.0
102.5°	66.8	82.7	84.3	85.8	87.4	88.9	89.2	88.0	86.9	85.8	84.6
105°	122.5	121.7	121.3	120.9	120.5	120.0	119.5	119.0	118.5	118.0	117.4
107.5°	152.1	151.8	151.2	150.6	150.0	149.5	149.0	148.8	148.5	148.3	148.0
110°	172.3	172.1	171.6	171.1	170.5	170.0	169.6	169.4	169.1	168.8	168.6



TEST NUMBER: P333055-935

CATALOG NUMBER: S124RDIW-S795D470U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	191.7	191.7	191.5	191.2	191.1	190.8	190.5	189.9	189.5	189.0	188.6
115°	220.2	220.1	220.2	220.2	220.3	220.4	220.3	220.1	219.8	219.6	219.3
117.5°	249.3	249.4	249.3	249.0	248.8	248.7	248.4	248.1	247.7	247.4	247.0
120°	267.1	266.9	267.0	267.1	267.2	267.3	267.1	266.7	266.4	266.0	265.7
122.5°	284.8	284.7	284.6	284.5	284.3	284.2	284.0	283.9	283.6	283.4	283.2
125°	309.3	309.0	309.2	309.4	309.5	309.7	309.6	309.3	308.9	308.6	308.2
127.5°	334.2	334.2	333.8	333.4	332.9	332.6	332.3	332.3	332.2	332.1	332.0
130°	349.0	348.9	348.6	348.4	348.1	347.8	347.7	347.6	347.5	347.3	347.2
132.5°	363.6	363.5	363.2	362.8	362.6	362.2	362.0	361.8	361.6	361.4	361.4
135°	383.7	383.6	383.2	382.9	382.5	382.2	382.0	382.1	382.2	382.3	382.4
137.5°	403.1	402.9	402.5	402.2	401.7	401.4	401.2	401.1	401.1	401.1	401.1
140°	415.1	414.8	414.7	414.5	414.2	414.1	413.9	413.7	413.5	413.4	413.2
142.5°	426.2	426.0	425.9	425.9	425.7	425.6	425.4	425.1	424.8	424.5	424.1
145°	442.2	442.1	442.1	442.1	442.1	442.1	442.0	441.7	441.4	441.2	440.9
147.5°	456.2	456.1	456.2	456.2	456.3	456.4	456.2	455.7	455.2	454.8	454.3
150°	465.1	465.1	465.2	465.3	465.4	465.5	465.4	465.0	464.7	464.3	464.0
152.5°	472.8	472.6	472.8	472.9	473.1	473.2	473.2	472.9	472.6	472.3	472.1
155°	483.0	482.7	482.9	483.2	483.5	483.7	483.8	483.7	483.6	483.5	483.5
157.5°	492.0	491.5	491.8	492.1	492.4	492.7	492.8	492.9	492.9	493.0	493.1
160°	497.7	497.1	497.2	497.3	497.4	497.5	497.7	497.9	498.2	498.4	498.7
162.5°	502.3	501.8	501.9	502.0	502.0	502.1	502.4	502.7	503.0	503.3	503.7
165°	508.8	508.1	508.1	508.1	508.1	508.1	508.2	508.7	509.1	509.5	510.0
167.5°	513.5	512.7	512.8	512.8	512.9	512.9	513.2	513.7	514.1	514.5	515.0
170°	516.5	515.8	515.7	515.7	515.6	515.5	515.7	516.3	516.8	517.3	517.8
172.5°	518.4	517.7	517.6	517.5	517.5	517.4	517.6	518.1	518.7	519.2	519.7
175°	520.6	519.8	519.7	519.6	519.5	519.4	519.6	520.1	520.6	521.2	521.7
177.5°	521.6	521.1	520.9	520.8	520.6	520.6	520.7	521.2	521.7	522.2	522.6
180°	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7



TEST NUMBER: P333055-935

CATALOG NUMBER: S124RDIW-S795D470U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1143.5	1146.8	1150.5	1157.4	1163.3	1165.9	1171.0	1174.7	1173.5	1178.6	1187.5
5°	1148.0	1160.4	1174.6	1189.2	1205.7	1219.4	1230.4	1241.4	1250.1	1260.6	1276.2
7.5°	1147.3	1169.2	1193.2	1219.4	1246.5	1269.8	1291.4	1313.4	1332.9	1354.3	1382.2
10°	1144.4	1173.6	1203.4	1237.8	1272.0	1304.6	1333.9	1361.4	1387.5	1415.4	1450.7
12.5°	1141.0	1174.7	1210.7	1252.0	1294.8	1333.9	1368.3	1407.9	1440.6	1476.6	1517.3
15°	1126.4	1171.8	1220.8	1274.4	1325.7	1378.3	1425.5	1474.0	1519.3	1562.4	1613.7
17.5°	1109.8	1162.1	1219.9	1283.1	1344.8	1408.8	1464.7	1526.0	1572.3	1630.0	1677.7
20°	1096.2	1152.5	1214.4	1285.4	1355.4	1426.4	1488.2	1550.5	1602.7	1660.9	1721.3
22.5°	1079.8	1141.6	1208.5	1282.0	1355.4	1433.0	1501.4	1563.3	1628.0	1693.4	1755.8
25°	1053.2	1117.3	1188.3	1268.9	1353.1	1432.4	1505.6	1582.5	1652.2	1723.1	1779.0
27.5°	1020.6	1087.9	1162.7	1245.9	1332.3	1413.5	1499.8	1581.7	1651.7	1720.1	1768.8
30°	994.5	1065.6	1137.5	1221.7	1311.5	1398.4	1491.0	1573.0	1646.7	1708.1	1735.5
32.5°	967.9	1035.2	1109.2	1194.6	1286.5	1380.2	1471.9	1555.7	1623.9	1660.8	1661.5
35°	921.4	984.5	1061.4	1145.2	1239.6	1341.3	1434.2	1516.6	1558.2	1561.5	1516.6
37.5°	870.6	928.6	1001.2	1085.0	1188.4	1289.5	1384.5	1439.4	1453.3	1406.7	1323.7
40°	834.3	887.9	957.9	1044.0	1146.6	1251.0	1337.6	1377.9	1363.2	1287.6	1195.2
42.5°	796.3	846.1	913.6	998.6	1101.6	1207.0	1280.7	1302.4	1263.6	1176.3	1068.1
45°	734.0	779.8	846.7	932.3	1031.2	1130.1	1186.0	1175.0	1110.4	1006.9	885.6
47.5°	669.3	713.5	773.7	852.9	954.2	1039.6	1077.4	1044.2	952.4	838.5	739.8
50°	626.5	671.8	727.2	802.7	895.2	977.7	1001.9	951.6	849.5	739.9	649.3
52.5°	584.3	623.0	677.3	750.4	838.8	908.4	921.4	863.2	757.9	659.8	579.4
55°	520.2	555.4	601.2	669.9	746.4	805.5	798.6	723.9	628.3	544.5	481.3
57.5°	458.2	484.7	527.0	591.4	658.6	698.2	673.1	609.5	520.3	451.7	398.4
60°	417.2	441.9	481.3	537.6	596.7	619.1	598.1	528.9	458.4	395.6	350.8
62.5°	378.3	400.1	434.0	486.3	534.0	547.3	524.8	464.4	400.9	347.2	310.1
65°	321.9	342.1	370.9	408.0	441.0	447.4	432.7	370.9	322.8	277.9	252.3
67.5°	270.7	283.9	306.4	338.5	356.0	359.7	331.4	292.6	250.2	222.7	203.3
70°	236.3	245.5	266.5	283.9	298.1	298.6	272.4	241.3	208.8	186.4	172.2
72.5°	202.9	211.7	227.6	239.6	250.5	246.9	223.0	198.5	172.2	155.2	144.7
75°	156.6	164.4	172.6	178.1	178.1	173.6	156.2	137.8	122.7	112.6	109.4
77.5°	113.8	120.3	123.0	122.2	120.5	113.4	102.4	90.4	85.0	80.2	77.8
80°	89.3	92.0	93.0	90.7	87.9	79.6	72.3	67.3	62.3	60.4	59.5
82.5°	66.2	68.6	66.2	66.8	60.8	54.1	50.0	48.3	46.1	45.5	44.5
85°	35.3	34.8	33.9	31.6	27.5	26.5	26.1	25.7	24.7	25.2	24.3
87.5°	12.5	11.6	10.3	10.2	10.3	9.7	10.2	10.3	10.5	10.2	11.1
90°	2.2	3.1	4.0	5.0	5.8	6.5	7.2	7.9	8.6	9.1	9.6
92.5°	5.0	5.0	5.1	5.2	5.5	6.2	6.9	7.6	8.3	8.8	9.3
95°	18.5	15.6	12.7	9.6	8.3	8.4	8.4	8.5	8.6	9.1	9.6
97.5°	47.4	49.2	51.1	53.0	49.0	39.3	29.6	20.0	10.3	10.3	10.4
100°	65.5	67.2	68.7	70.3	65.0	53.0	41.1	29.1	17.1	15.7	14.2
102.5°	85.8	86.9	88.0	89.2	88.9	87.4	85.8	84.3	82.7	66.8	50.9
105°	118.0	118.5	119.0	119.5	120.0	120.5	120.9	121.3	121.7	122.5	123.3
107.5°	148.3	148.5	148.8	149.0	149.5	150.0	150.6	151.2	151.8	152.1	152.6
110°	168.8	169.1	169.4	169.6	170.0	170.5	171.1	171.6	172.1	172.3	172.5





TEST NUMBER: P333055-935

CATALOG NUMBER: S124RDIW-S795D470U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	189.0	189.5	189.9	190.5	190.8	191.1	191.2	191.5	191.7	191.7	191.7
115°	219.6	219.8	220.1	220.3	220.4	220.3	220.2	220.2	220.1	220.2	220.4
117.5°	247.4	247.7	248.1	248.4	248.7	248.8	249.0	249.3	249.4	249.3	249.3
120°	266.0	266.4	266.7	267.1	267.3	267.2	267.1	267.0	266.9	267.1	267.3
122.5°	283.4	283.6	283.9	284.0	284.2	284.3	284.5	284.6	284.7	284.8	284.9
125°	308.6	308.9	309.3	309.6	309.7	309.5	309.4	309.2	309.0	309.3	309.5
127.5°	332.1	332.2	332.3	332.3	332.6	332.9	333.4	333.8	334.2	334.2	334.1
130°	347.3	347.5	347.6	347.7	347.8	348.1	348.4	348.6	348.9	349.0	349.0
132.5°	361.4	361.6	361.8	362.0	362.2	362.6	362.8	363.2	363.5	363.6	363.7
135°	382.3	382.2	382.1	382.0	382.2	382.5	382.9	383.2	383.6	383.7	383.9
137.5°	401.1	401.1	401.1	401.2	401.4	401.7	402.2	402.5	402.9	403.1	403.3
140°	413.4	413.5	413.7	413.9	414.1	414.2	414.5	414.7	414.8	415.1	415.3
142.5°	424.5	424.8	425.1	425.4	425.6	425.7	425.9	425.9	426.0	426.2	426.4
145°	441.2	441.4	441.7	442.0	442.1	442.1	442.1	442.1	442.1	442.2	442.3
147.5°	454.8	455.2	455.7	456.2	456.4	456.3	456.2	456.2	456.1	456.2	456.2
150°	464.3	464.7	465.0	465.4	465.5	465.4	465.3	465.2	465.1	465.1	465.1
152.5°	472.3	472.6	472.9	473.2	473.2	473.1	472.9	472.8	472.6	472.8	472.9
155°	483.5	483.6	483.7	483.8	483.7	483.5	483.2	482.9	482.7	483.0	483.4
157.5°	493.0	492.9	492.9	492.8	492.7	492.4	492.1	491.8	491.5	492.0	492.4
160°	498.4	498.2	497.9	497.7	497.5	497.4	497.3	497.2	497.1	497.7	498.2
162.5°	503.3	503.0	502.7	502.4	502.1	502.0	502.0	501.9	501.8	502.3	502.8
165°	509.5	509.1	508.7	508.2	508.1	508.1	508.1	508.1	508.1	508.8	509.5
167.5°	514.5	514.1	513.7	513.2	512.9	512.9	512.8	512.8	512.7	513.5	514.3
170°	517.3	516.8	516.3	515.7	515.5	515.6	515.7	515.7	515.8	516.5	517.2
172.5°	519.2	518.7	518.1	517.6	517.4	517.5	517.5	517.6	517.7	518.4	519.1
175°	521.2	520.6	520.1	519.6	519.4	519.5	519.6	519.7	519.8	520.6	521.3
177.5°	522.2	521.7	521.2	520.7	520.6	520.6	520.8	520.9	521.1	521.6	522.2
180°	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7



TEST NUMBER: P333055-935

CATALOG NUMBER: S124RDIW-S795D470U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1192.2	1193.7	1194.8	1198.4	1198.8	1202.1	1198.8
5°	1290.8	1297.3	1307.3	1317.4	1318.4	1324.7	1313.3
7.5°	1401.4	1416.3	1425.6	1441.8	1448.3	1452.3	1445.7
10°	1477.6	1491.4	1515.7	1527.6	1539.5	1541.4	1535.9
12.5°	1551.3	1573.1	1592.2	1614.8	1614.2	1630.4	1624.4
15°	1649.4	1671.8	1698.4	1723.5	1732.8	1732.8	1740.1
17.5°	1719.3	1760.5	1788.0	1807.8	1829.4	1833.1	1830.6
20°	1766.6	1811.0	1840.4	1866.0	1880.7	1884.7	1884.7
22.5°	1801.8	1839.6	1868.2	1891.3	1903.3	1908.2	1906.8
25°	1826.2	1858.6	1876.0	1882.9	1886.1	1885.2	1876.5
27.5°	1792.8	1791.3	1780.4	1759.3	1743.4	1733.8	1722.9
30°	1729.1	1705.3	1677.8	1647.5	1608.6	1578.9	1569.7
32.5°	1634.2	1580.7	1534.2	1483.8	1442.0	1412.2	1399.7
35°	1450.7	1366.0	1296.8	1236.4	1192.4	1164.9	1155.8
37.5°	1232.9	1150.9	1065.3	1006.7	970.3	942.5	932.1
40°	1094.4	1005.1	930.5	875.6	838.0	811.0	810.5
42.5°	968.0	882.8	812.5	772.9	732.5	714.6	714.5
45°	792.6	724.4	664.9	633.8	609.5	594.9	590.7
47.5°	656.3	599.9	560.2	535.4	515.6	506.3	500.2
50°	579.7	530.3	498.7	477.2	466.1	454.3	453.3
52.5°	516.0	476.0	451.4	433.9	420.0	412.8	413.0
55°	433.6	402.1	384.6	371.3	360.4	354.9	352.6
57.5°	365.3	341.6	329.0	316.8	312.1	307.8	306.6
60°	322.8	306.8	294.9	285.2	278.4	277.1	276.6
62.5°	287.7	270.9	262.7	255.2	250.2	248.1	247.3
65°	237.2	224.8	217.5	211.5	209.7	206.6	206.0
67.5°	191.2	183.8	178.9	174.9	172.4	172.2	172.2
70°	163.0	158.9	154.8	152.5	151.1	150.2	150.2
72.5°	138.9	135.8	132.4	131.2	131.0	130.0	129.7
75°	105.8	102.5	103.1	100.7	98.9	96.6	95.2
77.5°	75.0	72.8	72.2	72.0	70.4	70.2	70.9
80°	58.1	55.9	55.4	55.9	55.4	54.1	54.1
82.5°	44.3	42.3	41.8	41.6	41.2	41.6	40.8
85°	23.8	22.9	22.9	22.9	23.8	23.3	22.9
87.5°	10.4	10.2	10.6	10.3	10.3	10.0	10.4
90°	10.2	10.7	11.0	11.2	11.4	11.5	11.7
92.5°	9.8	10.3	10.6	10.7	10.7	10.8	10.8
95°	10.2	10.7	10.9	11.0	11.1	11.2	11.3
97.5°	10.4	10.5	10.6	10.7	10.8	10.8	10.9
100°	12.7	11.3	10.6	10.7	10.8	10.8	10.9
102.5°	35.0	19.1	11.2	11.2	11.2	11.2	11.3
105°	124.1	124.8	123.7	120.5	117.4	114.3	111.2
107.5°	152.9	153.3	153.7	154.0	154.3	154.6	155.0
110°	172.6	172.8	173.0	173.2	173.5	173.7	174.0



TEST NUMBER: P333055-935

CATALOG NUMBER: S124RDIW-S795D470U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	191.7	191.6	191.7	192.1	192.4	192.8	193.0
115°	220.6	220.8	220.8	220.8	220.8	220.8	220.8
117.5°	249.3	249.3	249.3	249.2	249.2	249.2	249.1
120°	267.4	267.6	267.6	267.4	267.3	267.1	266.9
122.5°	285.0	285.1	285.1	284.9	284.7	284.6	284.4
125°	309.8	310.0	310.2	310.3	310.4	310.5	310.6
127.5°	334.0	334.0	333.9	333.8	333.7	333.7	333.6
130°	349.1	349.2	349.2	349.2	349.2	349.2	349.2
132.5°	363.8	363.9	363.9	363.8	363.8	363.7	363.6
135°	384.1	384.3	384.4	384.6	384.8	385.0	385.1
137.5°	403.5	403.7	403.7	403.7	403.6	403.6	403.6
140°	415.6	415.9	416.0	416.1	416.2	416.3	416.4
142.5°	426.6	426.8	426.9	426.9	427.0	427.0	427.0
145°	442.4	442.5	442.6	442.7	442.9	443.1	443.2
147.5°	456.2	456.3	456.4	456.5	456.6	456.7	456.8
150°	465.1	465.1	465.2	465.3	465.4	465.5	465.5
152.5°	473.0	473.2	473.2	473.2	473.1	473.0	473.0
155°	483.7	484.1	484.1	483.9	483.6	483.4	483.1
157.5°	492.8	493.3	493.3	492.8	492.4	492.0	491.5
160°	498.7	499.2	499.2	498.7	498.2	497.7	497.1
162.5°	503.3	503.9	503.9	503.3	502.7	502.0	501.5
165°	510.1	510.8	510.7	510.0	509.2	508.4	507.6
167.5°	515.1	515.8	515.7	514.9	514.0	513.2	512.3
170°	517.9	518.7	518.6	517.6	516.8	515.9	515.1
172.5°	519.8	520.5	520.4	519.4	518.5	517.5	516.6
175°	522.1	522.9	522.7	521.7	520.6	519.6	518.6
177.5°	522.7	523.3	523.1	522.4	521.5	520.6	519.9
180°	521.7	521.7	521.7	521.7	521.7	521.7	521.7

(END OF REPORT)