

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333057-935

Luminaire Tested: **S124RDIW-S795D470U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333057-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S795D470U935-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4378.7 lumens
Efficiency: N/A
Efficacy: 116.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333057-935

CATALOG NUMBER: S124RDIW-S795D470U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333057-935

CATALOG NUMBER: S124RDIW-S795D470U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68	63
1	101	97	93	90	95	91	88	85	80	78	75	70	68	67	61	60	58	54
2	92	85	79	74	86	80	75	70	71	66	63	62	59	56	54	52	50	46
3	84	75	68	62	79	71	64	59	63	57	53	55	51	48	48	45	43	39
4	77	67	59	53	72	63	56	50	56	50	46	49	45	41	43	40	37	34
5	71	60	51	45	67	56	49	43	50	44	40	44	40	36	39	35	32	29
6	66	54	45	40	62	51	43	38	45	39	35	40	35	32	36	32	29	26
7	61	49	41	35	57	46	39	34	41	35	31	37	32	28	33	29	26	23
8	57	44	36	31	53	42	35	30	38	32	28	34	29	25	30	26	23	21
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	28	24	21	19
10	49	37	30	25	47	36	29	24	32	26	23	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9656	9656	9656
5°	9678	9559	9618
10°	9617	9444	9444
15°	9507	9246	9177
20°	9355	8985	8820
25°	9161	8679	8459
30°	8972	8358	8007
35°	8763	8024	7554
40°	8513	7644	7065
45°	8281	7267	6566
50°	8017	6832	6038
55°	7734	6380	5465
60°	7424	5885	4879
65°	7138	5266	4304
70°	6722	4584	3654
75°	6198	3799	2969
80°	5407	2896	2724
85°	4576	2631	2455



TEST NUMBER: P333057-935

CATALOG NUMBER: S124RDIW-S795D470U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.4	2.6
10°-20°	313.3	7.2
20°-30°	452.4	10.3
30°-40°	512.8	11.7
40°-50°	495.2	11.3
50°-60°	411.8	9.4
60°-70°	284.4	6.5
70°-80°	144.1	3.3
80°-90°	38.5	0.9
90°-100°	17.8	0.4
100°-110°	113.8	2.6
110°-120°	217.6	5.0
120°-130°	276.3	6.3
130°-140°	295.6	6.8
140°-150°	276.4	6.3
150°-160°	222.9	5.1
160°-170°	143.8	3.3
170°-180°	49.6	1.1
0°-30°	878.1	20.1
0°-40°	1390.9	31.8
0°-60°	2297.9	52.5
0°-90°	2764.9	63.1
90°-120°	349.2	8.0
90°-150°	1197.5	27.3
90°-180°	1614.0	36.9
0°-180°	4378.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1196	1196	1196	1196	1196	
5°	1194	1190	1180	1188	1187	113
15°	1138	1128	1106	1104	1098	320
25°	1028	1011	974	959	950	474
35°	889	859	814	784	766	555
45°	725	690	636	593	575	559
55°	550	512	453	407	388	491
65°	374	333	276	238	225	369
75°	199	164	122	102	95	210
85°	49	32	28	27	26	56
90°	1	5	9	11	12	3
95°	21	9	9	11	11	28
105°	117	120	122	124	111	123
115°	219	220	220	221	221	216
125°	308	310	309	310	311	275
135°	382	382	384	384	385	295
145°	441	442	442	443	443	275
155°	484	484	483	484	483	223
165°	510	508	508	511	508	144
175°	522	520	520	523	519	50
180°	522	522	522	522	522	



TEST NUMBER: P333057-935

CATALOG NUMBER: S124RDIW-S795D470U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1
2.5°	1199.0	1198.3	1197.7	1197.0	1196.4	1195.2	1193.3	1191.6	1189.8	1188.0	1189.8
5°	1194.2	1193.4	1192.6	1191.8	1190.9	1189.4	1186.9	1184.5	1182.0	1179.6	1181.6
7.5°	1183.4	1182.6	1181.7	1180.9	1180.0	1178.0	1174.8	1171.6	1168.5	1165.3	1166.6
10°	1173.2	1172.2	1171.1	1170.1	1169.1	1166.7	1163.1	1159.4	1155.8	1152.1	1152.9
12.5°	1159.9	1158.8	1157.6	1156.4	1155.3	1152.5	1148.2	1143.8	1139.5	1135.2	1135.7
15°	1137.5	1135.7	1133.8	1132.0	1130.1	1126.7	1121.5	1116.5	1111.4	1106.3	1105.9
17.5°	1110.2	1107.5	1104.8	1102.3	1099.6	1095.2	1089.1	1083.0	1076.9	1070.7	1069.6
20°	1088.9	1086.2	1083.7	1081.0	1078.3	1073.6	1066.6	1059.7	1052.7	1045.9	1044.2
22.5°	1065.5	1062.5	1059.5	1056.5	1053.6	1048.4	1040.9	1033.5	1026.1	1018.7	1016.3
25°	1028.5	1024.8	1021.1	1017.4	1013.8	1007.8	999.4	991.1	982.7	974.4	970.9
27.5°	989.6	985.1	980.4	975.9	971.2	964.5	955.5	946.7	937.7	928.8	924.5
30°	962.5	957.4	952.4	947.3	942.2	934.9	925.3	915.8	906.1	896.6	891.5
32.5°	933.9	928.2	922.5	916.7	911.0	903.2	893.3	883.4	873.5	863.6	857.7
35°	889.2	882.8	876.2	869.7	863.2	854.9	844.7	834.5	824.3	814.2	807.3
37.5°	841.5	834.7	828.0	821.3	814.6	805.6	794.4	783.1	771.8	760.5	752.8
40°	807.8	801.1	794.4	787.6	780.9	771.7	760.1	748.6	736.9	725.3	716.8
42.5°	775.5	768.4	761.5	754.4	747.3	737.8	725.7	713.6	701.5	689.4	680.7
45°	725.3	717.8	710.2	702.7	695.2	685.4	673.1	660.9	648.7	636.5	626.5
47.5°	673.5	665.7	658.0	650.1	642.4	632.1	619.5	606.7	594.1	581.3	571.0
50°	638.3	630.4	622.4	614.5	606.6	596.1	583.1	570.1	557.0	544.0	533.8
52.5°	602.4	594.7	586.9	579.1	571.4	560.8	547.4	534.1	520.7	507.4	497.1
55°	549.5	541.3	533.2	525.0	516.9	506.3	493.0	479.7	466.6	453.3	442.7
57.5°	497.1	488.6	480.2	471.7	463.2	452.5	439.5	426.5	413.5	400.4	389.7
60°	459.8	451.6	443.5	435.3	427.1	416.6	403.6	390.5	377.5	364.5	353.9
62.5°	426.0	417.6	409.1	400.6	392.2	381.3	367.9	354.6	341.2	327.9	318.1
65°	373.7	364.9	356.1	347.4	338.6	327.8	314.7	301.7	288.7	275.7	266.9
67.5°	319.3	310.9	302.5	294.1	285.7	275.5	263.4	251.3	239.2	227.1	219.6
70°	284.8	276.3	267.7	259.2	250.6	240.6	228.9	217.3	205.8	194.2	187.4
72.5°	248.2	240.5	232.7	225.0	217.2	207.9	197.0	186.0	175.0	164.1	158.3
75°	198.7	191.2	183.7	176.2	168.6	160.1	150.5	140.9	131.4	121.8	117.1
77.5°	148.5	142.2	135.8	129.4	123.0	115.9	108.2	100.5	92.7	85.0	82.2
80°	116.3	110.4	104.5	98.6	92.7	86.7	80.6	74.5	68.4	62.3	61.6
82.5°	88.5	83.1	77.7	72.2	66.8	62.3	58.9	55.4	51.8	48.4	47.9
85°	49.4	45.4	41.3	37.3	33.1	30.8	30.2	29.6	29.0	28.4	28.0
87.5°	17.0	16.0	14.9	13.8	12.7	12.1	12.1	12.1	12.0	12.0	11.9
90°	1.2	2.2	3.1	4.0	5.0	5.8	6.5	7.2	7.9	8.6	9.1
92.5°	4.9	5.0	5.0	5.1	5.2	5.5	6.2	6.9	7.6	8.3	8.8
95°	21.4	18.5	15.6	12.7	9.6	8.3	8.4	8.4	8.5	8.6	9.1
97.5°	45.5	47.4	49.2	51.1	53.0	49.0	39.3	29.6	20.0	10.3	10.3
100°	64.0	65.5	67.2	68.7	70.3	65.0	53.0	41.1	29.1	17.1	15.7
102.5°	84.6	85.8	86.9	88.0	89.2	88.9	87.4	85.8	84.3	82.7	66.8
105°	117.4	118.0	118.5	119.0	119.5	120.0	120.5	120.9	121.3	121.7	122.5
107.5°	148.0	148.3	148.5	148.8	149.0	149.5	150.0	150.6	151.2	151.8	152.1
110°	168.6	168.8	169.1	169.4	169.6	170.0	170.5	171.1	171.6	172.1	172.3



TEST NUMBER: P333057-935

CATALOG NUMBER: S124RDIW-S795D470U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	188.6	189.0	189.5	189.9	190.5	190.8	191.1	191.2	191.5	191.7	191.7
115°	219.3	219.6	219.8	220.1	220.3	220.4	220.3	220.2	220.2	220.1	220.2
117.5°	247.0	247.4	247.7	248.1	248.4	248.7	248.8	249.0	249.3	249.4	249.3
120°	265.7	266.0	266.4	266.7	267.1	267.3	267.2	267.1	267.0	266.9	267.1
122.5°	283.2	283.4	283.6	283.9	284.0	284.2	284.3	284.5	284.6	284.7	284.8
125°	308.2	308.6	308.9	309.3	309.6	309.7	309.5	309.4	309.2	309.0	309.3
127.5°	332.0	332.1	332.2	332.3	332.3	332.6	332.9	333.4	333.8	334.2	334.2
130°	347.2	347.3	347.5	347.6	347.7	347.8	348.1	348.4	348.6	348.9	349.0
132.5°	361.4	361.4	361.6	361.8	362.0	362.2	362.6	362.8	363.2	363.5	363.6
135°	382.4	382.3	382.2	382.1	382.0	382.2	382.5	382.9	383.2	383.6	383.7
137.5°	401.1	401.1	401.1	401.1	401.2	401.4	401.7	402.2	402.5	402.9	403.1
140°	413.2	413.4	413.5	413.7	413.9	414.1	414.2	414.5	414.7	414.8	415.1
142.5°	424.1	424.5	424.8	425.1	425.4	425.6	425.7	425.9	425.9	426.0	426.2
145°	440.9	441.2	441.4	441.7	442.0	442.1	442.1	442.1	442.1	442.1	442.2
147.5°	454.3	454.8	455.2	455.7	456.2	456.4	456.3	456.2	456.2	456.1	456.2
150°	464.0	464.3	464.7	465.0	465.4	465.5	465.4	465.3	465.2	465.1	465.1
152.5°	472.1	472.3	472.6	472.9	473.2	473.2	473.1	472.9	472.8	472.6	472.8
155°	483.5	483.5	483.6	483.7	483.8	483.7	483.5	483.2	482.9	482.7	483.0
157.5°	493.1	493.0	492.9	492.9	492.8	492.7	492.4	492.1	491.8	491.5	492.0
160°	498.7	498.4	498.2	497.9	497.7	497.5	497.4	497.3	497.2	497.1	497.7
162.5°	503.7	503.3	503.0	502.7	502.4	502.1	502.0	502.0	501.9	501.8	502.3
165°	510.0	509.5	509.1	508.7	508.2	508.1	508.1	508.1	508.1	508.1	508.8
167.5°	515.0	514.5	514.1	513.7	513.2	512.9	512.9	512.8	512.8	512.7	513.5
170°	517.8	517.3	516.8	516.3	515.7	515.5	515.6	515.7	515.7	515.8	516.5
172.5°	519.7	519.2	518.7	518.1	517.6	517.4	517.5	517.5	517.6	517.7	518.4
175°	521.7	521.2	520.6	520.1	519.6	519.4	519.5	519.6	519.7	519.8	520.6
177.5°	522.6	522.2	521.7	521.2	520.7	520.6	520.6	520.8	520.9	521.1	521.6
180°	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7



TEST NUMBER: P333057-935

CATALOG NUMBER: S124RDIW-S795D470U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1
2.5°	1191.6	1193.3	1195.2	1196.0	1195.8	1195.7	1195.5	1195.3
5°	1183.6	1185.7	1187.7	1188.5	1188.1	1187.7	1187.3	1186.9
7.5°	1167.9	1169.2	1170.5	1170.8	1170.2	1169.5	1168.9	1168.2
10°	1153.7	1154.5	1155.4	1155.4	1154.5	1153.7	1152.9	1152.1
12.5°	1136.3	1136.7	1137.2	1136.9	1135.7	1134.6	1133.4	1132.3
15°	1105.5	1105.1	1104.7	1103.8	1102.3	1100.9	1099.5	1098.0
17.5°	1068.5	1067.4	1066.2	1064.5	1062.4	1060.2	1058.1	1055.9
20°	1042.6	1040.9	1039.3	1037.2	1034.6	1031.9	1029.2	1026.7
22.5°	1013.9	1011.4	1009.0	1006.7	1004.5	1002.4	1000.2	998.1
25°	967.5	964.1	960.6	957.9	955.8	953.8	951.7	949.7
27.5°	920.2	916.0	911.7	908.1	905.2	902.2	899.3	896.4
30°	886.4	881.3	876.2	872.0	868.8	865.6	862.3	859.0
32.5°	851.8	845.9	840.0	835.5	832.4	829.3	826.2	823.1
35°	800.3	793.4	786.5	781.2	777.6	773.9	770.2	766.5
37.5°	745.0	737.3	729.5	723.8	720.2	716.5	712.9	709.2
40°	708.3	699.6	691.1	685.0	681.4	677.7	674.1	670.4
42.5°	672.0	663.3	654.6	648.3	644.5	640.7	636.9	633.0
45°	616.6	606.6	596.6	589.8	586.1	582.5	578.8	575.1
47.5°	560.7	550.4	540.0	532.8	528.8	524.8	520.7	516.7
50°	523.7	513.5	503.3	496.3	492.4	488.5	484.7	480.8
52.5°	486.7	476.4	466.0	458.8	454.8	450.7	446.8	442.7
55°	432.1	421.5	411.0	403.8	399.9	396.1	392.2	388.3
57.5°	378.9	368.2	357.4	350.6	347.7	344.7	341.8	338.9
60°	343.4	332.8	322.2	315.2	312.0	308.8	305.5	302.2
62.5°	308.3	298.6	288.8	282.6	280.0	277.4	274.7	272.2
65°	258.1	249.4	240.6	235.1	232.6	230.1	227.7	225.3
67.5°	212.1	204.6	197.0	191.9	189.2	186.5	183.8	181.2
70°	180.7	174.0	167.3	162.9	160.9	158.9	156.8	154.8
72.5°	152.7	146.9	141.1	137.3	135.5	133.6	131.7	129.8
75°	112.4	107.8	103.1	100.1	98.9	97.7	96.4	95.2
77.5°	79.6	76.8	74.0	72.5	72.2	71.8	71.5	71.0
80°	61.0	60.4	59.8	59.4	59.2	59.0	58.8	58.6
82.5°	47.4	47.0	46.6	46.2	46.1	45.8	45.6	45.5
85°	27.6	27.2	26.8	26.5	26.5	26.5	26.5	26.5
87.5°	11.9	11.8	11.7	11.8	12.0	12.2	12.4	12.6
90°	9.6	10.2	10.7	11.0	11.2	11.4	11.5	11.7
92.5°	9.3	9.8	10.3	10.6	10.7	10.7	10.8	10.8
95°	9.6	10.2	10.7	10.9	11.0	11.1	11.2	11.3
97.5°	10.4	10.4	10.5	10.6	10.7	10.8	10.8	10.9
100°	14.2	12.7	11.3	10.6	10.7	10.8	10.8	10.9
102.5°	50.9	35.0	19.1	11.2	11.2	11.2	11.2	11.3
105°	123.3	124.1	124.8	123.7	120.5	117.4	114.3	111.2
107.5°	152.6	152.9	153.3	153.7	154.0	154.3	154.6	155.0
110°	172.5	172.6	172.8	173.0	173.2	173.5	173.7	174.0



TEST NUMBER: P333057-935

CATALOG NUMBER: S124RDIW-S795D470U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	191.7	191.7	191.6	191.7	192.1	192.4	192.8	193.0
115°	220.4	220.6	220.8	220.8	220.8	220.8	220.8	220.8
117.5°	249.3	249.3	249.3	249.3	249.2	249.2	249.2	249.1
120°	267.3	267.4	267.6	267.6	267.4	267.3	267.1	266.9
122.5°	284.9	285.0	285.1	285.1	284.9	284.7	284.6	284.4
125°	309.5	309.8	310.0	310.2	310.3	310.4	310.5	310.6
127.5°	334.1	334.0	334.0	333.9	333.8	333.7	333.7	333.6
130°	349.0	349.1	349.2	349.2	349.2	349.2	349.2	349.2
132.5°	363.7	363.8	363.9	363.9	363.8	363.8	363.7	363.6
135°	383.9	384.1	384.3	384.4	384.6	384.8	385.0	385.1
137.5°	403.3	403.5	403.7	403.7	403.7	403.6	403.6	403.6
140°	415.3	415.6	415.9	416.0	416.1	416.2	416.3	416.4
142.5°	426.4	426.6	426.8	426.9	426.9	427.0	427.0	427.0
145°	442.3	442.4	442.5	442.6	442.7	442.9	443.1	443.2
147.5°	456.2	456.2	456.3	456.4	456.5	456.6	456.7	456.8
150°	465.1	465.1	465.1	465.2	465.3	465.4	465.5	465.5
152.5°	472.9	473.0	473.2	473.2	473.2	473.1	473.0	473.0
155°	483.4	483.7	484.1	484.1	483.9	483.6	483.4	483.1
157.5°	492.4	492.8	493.3	493.3	492.8	492.4	492.0	491.5
160°	498.2	498.7	499.2	499.2	498.7	498.2	497.7	497.1
162.5°	502.8	503.3	503.9	503.9	503.3	502.7	502.0	501.5
165°	509.5	510.1	510.8	510.7	510.0	509.2	508.4	507.6
167.5°	514.3	515.1	515.8	515.7	514.9	514.0	513.2	512.3
170°	517.2	517.9	518.7	518.6	517.6	516.8	515.9	515.1
172.5°	519.1	519.8	520.5	520.4	519.4	518.5	517.5	516.6
175°	521.3	522.1	522.9	522.7	521.7	520.6	519.6	518.6
177.5°	522.2	522.7	523.3	523.1	522.4	521.5	520.6	519.9
180°	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7

(END OF REPORT)