

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332817-840

Luminaire Tested: **S124DIW-S1020D1050U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332817-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1020D1050U840-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8885.3 lumens
Efficiency: N/A
Efficacy: 145.2 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332817-840

CATALOG NUMBER: S124DIW-S1020D1050U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332817-840

CATALOG NUMBER: S124DIW-S1020D1050U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	52
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	52	51	50	45
2	90	83	77	71	83	77	71	67	66	62	58	55	53	50	46	44	42	38
3	82	73	66	60	76	68	61	56	58	53	49	49	46	43	41	38	36	32
4	75	65	57	51	69	60	53	48	52	46	42	44	40	37	37	34	31	28
5	69	58	50	44	64	54	47	41	46	41	37	40	35	32	33	30	27	24
6	64	52	44	38	59	48	41	36	42	36	32	36	31	28	30	27	24	21
7	59	47	39	33	55	44	37	32	38	32	28	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	25	22	19	17
9	51	39	31	26	47	37	30	25	32	26	23	28	23	20	23	20	18	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13605	13605	13605	13605
5°	16022	13639	12039	13639
10°	19184	13581	10839	13581
15°	22697	13443	9954	13443
20°	25274	13302	9164	13302
25°	25683	13097	8620	13097
30°	21853	12899	8447	12899
35°	16802	12577	8449	12577
40°	13095	12198	8608	12198
45°	10919	11628	8752	11628
50°	9610	10934	9048	10934
55°	8804	10101	9413	10101
60°	8251	9357	9852	9357
65°	7681	8521	10214	8521
70°	7020	7695	10447	7695
75°	6273	6772	10321	6772
80°	5258	5551	9995	5551
85°	3881	4011	9568	4011



TEST NUMBER: P332817-840

CATALOG NUMBER: S124DIW-S1020D1050U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.2	1.8
10°-20°	506.1	5.7
20°-30°	802.5	9.0
30°-40°	893.1	10.1
40°-50°	812.9	9.1
50°-60°	664.3	7.5
60°-70°	474.2	5.3
70°-80°	261.1	2.9
80°-90°	75.2	0.8
90°-100°	46.8	0.5
100°-110°	298.3	3.4
110°-120°	570.7	6.4
120°-130°	724.4	8.2
130°-140°	775.1	8.7
140°-150°	724.8	8.2
150°-160°	584.5	6.6
160°-170°	377.0	4.2
170°-180°	129.9	1.5
0°-30°	1472.7	16.6
0°-40°	2365.8	26.6
0°-60°	3843.0	43.3
0°-90°	4653.7	52.4
90°-120°	915.8	10.3
90°-150°	3140.1	35.3
90°-180°	4232.0	47.6
0°-180°	8885.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1685	1685	1685	1685	1685	
5°	1977	1683	1486	1683	1977	201
15°	2716	1608	1191	1608	2716	767
25°	2883	1470	968	1470	2883	1271
35°	1705	1276	857	1276	1705	1082
45°	956	1018	767	1018	956	753
55°	626	718	669	718	626	565
65°	402	446	535	446	402	398
75°	201	217	331	217	201	214
85°	42	43	103	43	42	52
90°	31	3	31	3	31	15
95°	30	56	30	56	30	24
105°	292	308	292	308	292	254
115°	579	575	579	575	579	573
125°	814	808	814	808	814	725
135°	1010	1003	1010	1003	1010	777
145°	1162	1156	1162	1156	1162	726
155°	1267	1268	1267	1268	1267	584
165°	1331	1337	1331	1337	1331	376
175°	1360	1368	1360	1368	1360	129
180°	1368	1368	1368	1368	1368	



TEST NUMBER: P332817-840

CATALOG NUMBER: S124DIW-S1020D1050U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3
2.5°	1793.6	1793.1	1787.5	1786.4	1782.4	1777.5	1776.4	1767.4	1749.5	1741.1	1738.9
5°	1977.1	1991.0	1972.9	1969.4	1967.3	1944.3	1932.4	1918.4	1886.3	1867.4	1852.8
7.5°	2196.1	2197.7	2189.8	2183.3	2165.6	2145.5	2115.4	2083.3	2045.0	2005.2	1975.1
10°	2340.2	2345.7	2336.6	2335.2	2299.7	2277.2	2232.6	2194.9	2151.6	2103.4	2059.5
12.5°	2492.0	2484.2	2479.6	2449.7	2443.2	2402.4	2350.5	2311.7	2244.9	2189.5	2130.9
15°	2715.7	2700.4	2690.6	2649.4	2629.2	2572.6	2517.4	2474.9	2387.6	2304.5	2241.7
17.5°	2846.9	2862.4	2839.7	2822.8	2770.5	2730.8	2674.4	2585.1	2516.8	2413.6	2334.3
20°	2941.9	2943.3	2930.7	2913.3	2872.1	2821.9	2760.4	2662.6	2581.0	2478.3	2369.4
22.5°	2967.6	2967.9	2962.5	2946.2	2915.1	2874.3	2812.4	2730.8	2631.8	2520.2	2411.4
25°	2883.3	2880.4	2886.8	2904.9	2893.1	2880.4	2844.9	2784.1	2692.0	2573.9	2456.7
27.5°	2569.9	2589.2	2624.6	2669.4	2712.4	2745.2	2754.4	2742.0	2684.8	2587.8	2465.0
30°	2344.3	2368.0	2394.6	2439.2	2525.8	2575.4	2629.9	2671.0	2648.0	2570.5	2456.0
32.5°	2096.4	2102.2	2141.6	2192.4	2271.7	2367.0	2453.4	2537.0	2564.8	2524.2	2428.6
35°	1704.9	1714.5	1757.2	1807.5	1904.5	2021.0	2150.9	2266.8	2362.5	2400.9	2352.0
37.5°	1391.2	1419.3	1449.4	1503.4	1588.8	1693.7	1828.7	1978.6	2121.2	2216.7	2232.9
40°	1242.6	1260.1	1281.7	1322.9	1395.5	1498.8	1614.8	1786.6	1938.0	2074.9	2119.5
42.5°	1125.4	1135.6	1148.8	1186.1	1241.4	1344.1	1450.0	1601.0	1753.1	1916.7	1991.7
45°	956.4	966.9	989.3	1010.9	1052.8	1124.0	1222.4	1346.7	1499.5	1657.4	1795.5
47.5°	834.4	841.1	854.3	877.6	913.1	960.1	1040.2	1144.0	1285.7	1438.9	1586.1
50°	765.2	770.7	781.2	802.1	829.4	871.2	936.9	1033.9	1144.9	1299.2	1443.7
52.5°	710.4	712.7	720.3	734.6	756.2	791.4	845.3	925.5	1028.7	1166.3	1310.2
55°	625.5	628.3	635.3	645.8	664.6	686.9	728.1	788.2	878.3	997.6	1122.6
57.5°	555.7	557.6	563.5	567.5	583.1	601.3	632.9	675.8	744.1	845.3	956.8
60°	511.0	509.7	516.6	520.1	530.6	545.9	570.4	611.6	670.9	752.6	855.2
62.5°	467.5	465.5	471.4	475.9	482.0	495.1	515.0	547.3	595.5	669.3	758.0
65°	402.1	399.3	402.8	408.4	413.9	421.0	435.7	464.2	502.6	555.7	623.4
67.5°	336.5	339.4	340.0	342.7	346.0	355.5	365.6	385.8	412.8	455.3	512.7
70°	297.4	298.1	300.9	300.9	303.0	311.3	319.7	331.6	358.1	397.3	444.0
72.5°	258.3	261.3	260.1	262.4	263.9	269.4	275.6	286.9	309.5	338.6	378.1
75°	201.1	203.2	203.2	203.9	205.9	208.0	212.9	221.3	237.3	259.0	286.2
77.5°	146.6	146.9	147.8	150.4	150.4	153.7	157.3	164.1	172.0	186.8	203.4
80°	113.1	114.5	113.8	115.2	115.2	118.0	119.4	127.7	131.3	141.0	154.3
82.5°	82.9	84.3	84.2	86.1	87.3	87.9	89.8	93.1	96.6	105.2	110.7
85°	41.9	43.3	41.9	43.3	45.3	46.0	48.2	48.9	51.7	53.7	58.7
87.5°	18.4	20.0	19.9	20.4	21.4	21.8	22.1	21.2	23.2	23.5	25.3
90°	30.7	30.2	29.8	29.3	28.9	28.0	26.6	25.2	23.8	22.5	20.7
92.5°	28.3	28.2	28.1	28.0	27.9	27.2	25.8	24.4	23.0	21.7	19.9
95°	29.7	29.5	29.2	29.0	28.8	28.0	26.6	25.2	23.8	22.5	22.3
97.5°	28.7	28.4	28.2	28.0	27.8	27.6	27.5	27.3	27.2	27.0	52.4
100°	28.7	28.4	28.2	28.0	27.8	29.6	33.4	37.3	41.2	45.0	76.4
102.5°	29.5	29.4	29.4	29.3	29.3	50.1	91.8	133.5	175.2	216.9	221.0
105°	291.6	299.8	308.0	316.2	324.4	327.4	325.4	323.4	321.2	319.2	318.1
107.5°	406.4	405.6	404.7	403.8	402.9	402.0	401.0	400.0	399.0	398.0	396.5
110°	456.4	455.7	454.9	454.3	453.6	453.0	452.6	452.1	451.7	451.2	449.9



TEST NUMBER: P332817-840

CATALOG NUMBER: S124DIW-S1020D1050U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	506.2	505.4	504.5	503.7	502.8	502.4	502.5	502.6	502.7	502.8	502.1
115°	579.2	579.2	579.2	579.2	579.2	578.9	578.5	577.9	577.5	577.0	577.3
117.5°	653.2	653.3	653.4	653.5	653.6	653.7	653.8	653.8	653.9	654.0	653.5
120°	699.8	700.3	700.7	701.3	701.7	701.7	701.3	700.7	700.3	699.8	700.0
122.5°	745.7	746.2	746.6	747.1	747.5	747.6	747.3	747.1	746.8	746.5	746.2
125°	814.5	814.3	814.0	813.7	813.5	813.0	812.4	811.7	811.0	810.3	810.8
127.5°	874.8	874.9	875.1	875.4	875.6	875.7	875.9	876.0	876.2	876.3	875.1
130°	915.7	915.7	915.7	915.7	915.7	915.6	915.4	915.1	914.9	914.7	914.0
132.5°	953.4	953.6	953.7	953.9	954.1	954.1	953.9	953.6	953.4	953.2	952.3
135°	1009.9	1009.5	1009.0	1008.6	1008.0	1007.6	1007.1	1006.7	1006.2	1005.8	1004.9
137.5°	1058.1	1058.3	1058.4	1058.5	1058.7	1058.5	1058.0	1057.5	1057.0	1056.5	1055.5
140°	1091.8	1091.5	1091.3	1091.1	1090.9	1090.4	1089.6	1089.0	1088.3	1087.6	1087.2
142.5°	1119.5	1119.5	1119.4	1119.4	1119.3	1119.1	1118.6	1118.1	1117.6	1117.1	1116.8
145°	1162.4	1161.8	1161.4	1160.9	1160.5	1160.1	1159.9	1159.7	1159.5	1159.2	1159.2
147.5°	1197.7	1197.5	1197.3	1197.1	1196.8	1196.6	1196.4	1196.3	1196.1	1195.9	1196.1
150°	1220.6	1220.4	1220.2	1219.9	1219.7	1219.6	1219.6	1219.6	1219.6	1219.6	1219.8
152.5°	1240.3	1240.4	1240.5	1240.7	1240.8	1240.7	1240.3	1240.0	1239.6	1239.3	1239.7
155°	1266.7	1267.4	1268.1	1268.7	1269.4	1269.3	1268.4	1267.5	1266.6	1265.7	1266.4
157.5°	1288.8	1290.0	1291.1	1292.3	1293.5	1293.5	1292.3	1291.1	1290.0	1288.8	1289.6
160°	1303.5	1304.8	1306.3	1307.6	1309.0	1309.0	1307.6	1306.3	1304.8	1303.5	1303.7
162.5°	1314.9	1316.6	1318.1	1319.6	1321.2	1321.2	1319.9	1318.5	1317.2	1315.8	1316.1
165°	1331.1	1333.2	1335.2	1337.3	1339.3	1339.5	1337.7	1335.8	1334.0	1332.2	1332.2
167.5°	1343.2	1345.5	1347.8	1350.1	1352.3	1352.4	1350.5	1348.5	1346.5	1344.4	1344.6
170°	1350.6	1352.8	1355.1	1357.4	1359.7	1359.9	1358.1	1356.2	1354.4	1352.6	1352.4
172.5°	1354.6	1357.2	1359.6	1362.0	1364.5	1364.8	1363.0	1361.2	1359.4	1357.6	1357.4
175°	1359.8	1362.5	1365.2	1368.0	1370.7	1371.1	1369.0	1367.0	1364.9	1362.9	1362.6
177.5°	1363.1	1365.2	1367.5	1369.6	1371.8	1372.2	1370.7	1369.3	1367.8	1366.3	1365.9
180°	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0



TEST NUMBER: P332817-840

CATALOG NUMBER: S124DIW-S1020D1050U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3
2.5°	1739.5	1731.6	1726.1	1721.6	1709.3	1702.0	1696.5	1688.6	1679.7	1670.2	1658.5
5°	1838.2	1814.4	1797.0	1770.5	1745.3	1724.3	1702.7	1683.1	1659.4	1633.7	1614.8
7.5°	1941.9	1906.6	1861.4	1822.1	1778.0	1739.6	1705.3	1670.0	1633.5	1598.0	1565.5
10°	2007.8	1962.5	1912.2	1852.8	1797.0	1747.4	1701.3	1656.7	1613.4	1570.0	1533.1
12.5°	2078.7	2022.2	1947.9	1878.6	1815.9	1749.7	1694.0	1639.3	1587.1	1541.6	1498.4
15°	2173.9	2092.2	2006.4	1913.6	1831.2	1753.7	1677.6	1608.5	1549.8	1489.8	1447.9
17.5°	2232.5	2131.4	2033.3	1936.2	1836.4	1738.8	1656.7	1576.9	1503.5	1443.9	1391.1
20°	2271.0	2170.5	2048.3	1951.3	1832.6	1732.0	1637.1	1548.4	1471.7	1408.2	1353.6
22.5°	2304.5	2188.4	2066.2	1938.4	1820.3	1713.6	1609.7	1520.6	1442.1	1375.1	1322.9
25°	2322.7	2189.3	2056.7	1929.7	1795.5	1669.2	1575.0	1470.3	1386.4	1316.0	1260.1
27.5°	2324.6	2182.0	2031.9	1890.8	1752.4	1634.8	1515.8	1422.2	1335.2	1260.7	1207.1
30°	2318.4	2169.8	2008.5	1855.6	1716.7	1588.9	1485.6	1383.7	1295.1	1221.0	1165.2
32.5°	2299.0	2144.0	1978.3	1816.5	1672.5	1547.6	1441.0	1344.0	1257.6	1184.7	1126.1
35°	2242.4	2089.5	1912.9	1744.6	1597.3	1471.0	1374.6	1276.2	1189.6	1120.4	1064.0
37.5°	2154.0	2015.8	1836.2	1662.1	1517.4	1390.5	1295.1	1206.1	1128.0	1057.8	999.9
40°	2076.9	1955.4	1775.3	1605.7	1449.4	1328.6	1239.2	1157.5	1080.1	1013.7	958.6
42.5°	1988.1	1882.3	1716.2	1536.4	1385.6	1264.4	1177.2	1103.9	1030.9	969.6	914.4
45°	1829.8	1760.0	1603.6	1437.4	1280.4	1165.9	1082.8	1018.5	957.2	897.1	851.0
47.5°	1647.7	1613.1	1481.5	1323.6	1174.6	1061.7	989.7	930.3	876.5	825.6	785.0
50°	1525.4	1508.6	1394.8	1242.6	1100.2	994.1	921.5	870.6	824.5	779.8	741.4
52.5°	1404.7	1404.2	1301.6	1162.3	1030.5	928.3	856.2	808.6	768.6	732.4	697.8
55°	1220.3	1239.9	1159.6	1035.3	917.4	825.2	760.2	717.7	689.7	659.7	633.9
57.5°	1051.0	1083.4	1017.1	907.7	809.3	724.4	667.8	635.8	606.1	587.9	569.2
60°	940.4	971.1	919.5	827.3	734.5	661.9	608.0	579.5	553.6	541.1	527.8
62.5°	842.1	869.5	831.2	745.8	665.2	595.3	550.0	522.5	505.0	491.3	482.5
65°	701.7	724.7	691.9	629.8	560.6	504.7	467.8	446.1	429.4	423.7	413.9
67.5°	567.1	588.1	570.4	517.6	462.1	419.9	390.9	370.1	360.2	355.4	348.4
70°	487.3	508.3	489.4	443.3	400.7	365.2	337.9	326.0	315.6	313.5	303.7
72.5°	419.7	433.9	415.2	379.1	342.6	312.7	291.5	279.1	273.7	269.9	264.6
75°	314.9	327.4	314.9	286.9	261.1	240.1	222.0	217.1	210.9	208.7	205.2
77.5°	222.9	233.7	224.1	206.6	187.3	171.2	161.4	155.1	153.7	150.1	151.8
80°	170.4	177.3	168.2	156.4	141.0	129.9	122.9	119.4	115.2	113.8	116.5
82.5°	122.3	125.4	120.8	112.8	101.4	94.1	89.4	85.3	84.4	84.7	84.7
85°	63.5	62.8	62.1	55.1	51.7	46.8	44.0	43.3	42.6	44.0	45.3
87.5°	25.0	25.1	24.2	21.6	19.4	17.3	16.2	15.1	16.2	17.3	18.3
90°	18.9	17.1	15.2	13.0	10.6	8.1	5.6	3.0	5.6	8.1	10.6
92.5°	18.1	16.3	14.4	13.4	13.3	13.1	13.0	12.9	13.0	13.1	13.3
95°	22.0	21.8	21.6	25.3	33.1	40.8	48.6	56.2	48.6	40.8	33.1
97.5°	77.8	103.1	128.6	138.8	134.0	129.2	124.3	119.5	124.3	129.2	134.0
100°	107.8	139.2	170.6	184.2	180.1	176.0	171.9	167.8	171.9	176.0	180.1
102.5°	225.1	229.2	233.3	233.8	230.9	227.8	224.8	221.9	224.8	227.8	230.9
105°	317.0	315.8	314.7	313.5	312.0	310.7	309.3	308.0	309.3	310.7	312.0
107.5°	395.0	393.3	391.8	390.7	390.0	389.3	388.7	388.0	388.7	389.3	390.0
110°	448.5	447.2	445.8	444.7	444.0	443.3	442.7	442.0	442.7	443.3	444.0



TEST NUMBER: P332817-840

CATALOG NUMBER: S124DIW-S1020D1050U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	501.5	500.9	500.3	499.3	498.1	496.9	495.6	494.4	495.6	496.9	498.1
115°	577.5	577.7	577.9	577.7	577.0	576.4	575.7	575.0	575.7	576.4	577.0
117.5°	653.0	652.5	652.0	651.3	650.4	649.4	648.5	647.6	648.5	649.4	650.4
120°	700.3	700.5	700.7	700.4	699.5	698.6	697.7	696.8	697.7	698.6	699.5
122.5°	745.9	745.6	745.3	744.8	744.3	743.7	743.2	742.7	743.2	743.7	744.3
125°	811.2	811.7	812.1	811.9	811.0	810.1	809.2	808.3	809.2	810.1	811.0
127.5°	874.1	873.1	872.0	871.4	871.2	871.0	870.7	870.5	870.7	871.0	871.2
130°	913.3	912.7	912.0	911.5	911.3	911.1	910.9	910.6	910.9	911.1	911.3
132.5°	951.5	950.6	949.8	949.1	948.7	948.3	947.9	947.5	947.9	948.3	948.7
135°	1004.0	1003.1	1002.2	1001.8	1002.0	1002.3	1002.5	1002.7	1002.5	1002.3	1002.0
137.5°	1054.5	1053.5	1052.5	1052.0	1051.9	1051.8	1051.7	1051.6	1051.7	1051.8	1051.9
140°	1086.7	1086.3	1085.8	1085.4	1084.9	1084.5	1084.0	1083.6	1084.0	1084.5	1084.9
142.5°	1116.5	1116.3	1116.0	1115.5	1114.7	1113.8	1113.0	1112.2	1113.0	1113.8	1114.7
145°	1159.2	1159.2	1159.2	1158.9	1158.2	1157.5	1156.9	1156.2	1156.9	1157.5	1158.2
147.5°	1196.4	1196.6	1196.8	1196.3	1195.0	1193.8	1192.4	1191.1	1192.4	1193.8	1195.0
150°	1220.1	1220.3	1220.5	1220.2	1219.3	1218.4	1217.5	1216.6	1217.5	1218.4	1219.3
152.5°	1240.1	1240.5	1240.9	1240.7	1240.0	1239.3	1238.6	1237.8	1238.6	1239.3	1240.0
155°	1267.1	1267.7	1268.4	1268.6	1268.4	1268.2	1268.0	1267.7	1268.0	1268.2	1268.4
157.5°	1290.3	1291.1	1291.9	1292.3	1292.4	1292.6	1292.7	1292.9	1292.7	1292.6	1292.4
160°	1303.9	1304.2	1304.4	1304.8	1305.6	1306.3	1307.0	1307.6	1307.0	1306.3	1305.6
162.5°	1316.3	1316.5	1316.7	1317.3	1318.1	1319.0	1319.9	1320.7	1319.9	1319.0	1318.1
165°	1332.2	1332.2	1332.2	1332.7	1333.8	1335.0	1336.2	1337.3	1336.2	1335.0	1333.8
167.5°	1344.7	1344.8	1345.0	1345.6	1346.9	1348.1	1349.2	1350.4	1349.2	1348.1	1346.9
170°	1352.2	1351.9	1351.7	1352.3	1353.6	1355.0	1356.3	1357.8	1356.3	1355.0	1353.6
172.5°	1357.1	1356.9	1356.7	1357.2	1358.6	1359.9	1361.3	1362.6	1361.3	1359.9	1358.6
175°	1362.4	1362.2	1362.0	1362.5	1363.9	1365.2	1366.7	1368.0	1366.7	1365.2	1363.9
177.5°	1365.6	1365.2	1364.9	1365.3	1366.7	1367.9	1369.2	1370.4	1369.2	1367.9	1366.7
180°	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0



TEST NUMBER: P332817-840

CATALOG NUMBER: S124DIW-S1020D1050U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3
2.5°	1652.8	1647.9	1640.6	1630.5	1622.1	1613.3	1611.0	1607.6	1614.4	1608.7	1607.1
5°	1598.7	1584.1	1565.2	1543.6	1531.0	1512.9	1509.3	1502.4	1495.4	1494.7	1487.7
7.5°	1541.4	1519.8	1495.1	1473.1	1452.7	1432.8	1419.9	1417.0	1406.7	1400.7	1393.7
10°	1504.5	1477.9	1449.4	1428.4	1404.6	1383.7	1369.1	1360.7	1353.6	1345.9	1339.0
12.5°	1460.9	1432.7	1409.1	1386.4	1358.3	1342.3	1318.2	1303.6	1302.3	1302.4	1284.2
15°	1410.2	1382.3	1345.9	1313.8	1298.5	1267.8	1254.6	1237.8	1227.3	1216.8	1208.5
17.5°	1352.3	1317.5	1289.2	1252.3	1222.9	1198.5	1181.1	1171.0	1155.3	1140.4	1129.7
20°	1316.0	1279.0	1248.9	1209.8	1177.7	1147.7	1133.1	1119.1	1107.2	1094.7	1082.8
22.5°	1279.1	1240.4	1203.7	1165.7	1135.9	1104.2	1090.0	1071.1	1059.8	1052.8	1040.9
25°	1221.0	1179.1	1137.2	1101.0	1070.3	1042.3	1023.5	1008.8	996.2	990.7	983.0
27.5°	1157.9	1116.3	1075.8	1034.6	999.8	979.5	964.4	953.3	946.1	938.7	935.2
30°	1117.7	1074.4	1031.2	992.7	960.6	940.4	926.5	918.8	913.1	909.7	906.2
32.5°	1076.9	1034.2	988.7	953.6	924.8	906.9	896.3	888.6	885.8	884.5	883.2
35°	1011.6	968.3	926.5	895.0	867.8	860.8	851.7	847.5	846.2	851.0	853.1
37.5°	948.4	908.2	869.6	839.1	821.3	811.1	808.0	808.2	813.1	817.5	822.5
40°	907.6	868.5	832.1	805.7	788.9	782.6	781.2	784.7	790.3	795.2	800.7
42.5°	867.9	829.4	796.4	771.5	759.8	754.1	755.0	758.4	766.3	772.2	780.6
45°	806.4	774.3	742.1	721.9	712.1	713.5	713.5	719.7	727.4	736.5	745.6
47.5°	748.4	716.0	689.6	672.6	667.5	666.3	670.2	678.4	689.4	700.6	713.4
50°	709.3	678.5	655.5	640.2	634.6	636.7	642.3	649.9	663.2	677.2	690.4
52.5°	669.6	641.7	620.4	606.1	602.2	606.0	611.6	623.7	635.3	650.4	666.4
55°	608.0	584.3	567.5	557.1	555.7	557.8	564.1	577.3	594.1	613.0	628.3
57.5°	546.7	526.9	511.6	504.3	505.0	507.0	517.4	533.1	551.0	571.1	590.9
60°	505.4	487.3	474.7	469.2	469.8	474.0	486.6	501.3	523.6	543.1	564.1
62.5°	466.4	450.4	438.4	433.4	432.4	441.6	453.6	468.9	491.2	513.0	535.6
65°	403.5	390.9	381.2	378.4	380.5	387.5	402.8	423.0	441.9	464.9	488.7
67.5°	342.0	331.7	325.1	326.3	328.8	339.1	352.0	369.4	390.8	414.7	438.2
70°	303.0	293.2	287.6	288.3	292.6	305.1	316.3	333.7	356.8	381.2	400.7
72.5°	262.8	256.3	251.4	254.3	258.4	267.1	281.0	298.5	318.8	341.5	362.1
75°	201.8	201.8	198.9	201.1	207.3	215.7	226.2	244.4	264.6	282.8	299.5
77.5°	149.7	148.1	150.0	152.5	156.1	166.0	178.0	191.0	206.2	224.4	238.2
80°	114.5	115.2	118.7	122.9	124.3	132.0	144.5	156.4	168.2	183.6	196.8
82.5°	86.0	86.7	88.6	93.8	95.2	103.5	111.6	123.4	134.2	144.5	155.5
85°	46.8	46.8	50.3	52.3	55.8	61.4	66.3	73.3	83.1	90.1	100.5
87.5°	20.5	20.9	23.5	25.0	27.1	30.2	31.6	38.0	40.5	43.5	48.8
90°	13.0	15.2	17.1	18.9	20.7	22.5	23.8	25.2	26.6	28.0	28.9
92.5°	13.4	14.4	16.3	18.1	19.9	21.7	23.0	24.4	25.8	27.2	27.9
95°	25.3	21.6	21.8	22.0	22.3	22.5	23.8	25.2	26.6	28.0	28.8
97.5°	138.8	128.6	103.1	77.8	52.4	27.0	27.2	27.3	27.5	27.6	27.8
100°	184.2	170.6	139.2	107.8	76.4	45.0	41.2	37.3	33.4	29.6	27.8
102.5°	233.8	233.3	229.2	225.1	221.0	216.9	175.2	133.5	91.8	50.1	29.3
105°	313.5	314.7	315.8	317.0	318.1	319.2	321.2	323.4	325.4	327.4	324.4
107.5°	390.7	391.8	393.3	395.0	396.5	398.0	399.0	400.0	401.0	402.0	402.9
110°	444.7	445.8	447.2	448.5	449.9	451.2	451.7	452.1	452.6	453.0	453.6



TEST NUMBER: P332817-840

CATALOG NUMBER: S124DIW-S1020D1050U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	499.3	500.3	500.9	501.5	502.1	502.8	502.7	502.6	502.5	502.4	502.8
115°	577.7	577.9	577.7	577.5	577.3	577.0	577.5	577.9	578.5	578.9	579.2
117.5°	651.3	652.0	652.5	653.0	653.5	654.0	653.9	653.8	653.8	653.7	653.6
120°	700.4	700.7	700.5	700.3	700.0	699.8	700.3	700.7	701.3	701.7	701.7
122.5°	744.8	745.3	745.6	745.9	746.2	746.5	746.8	747.1	747.3	747.6	747.5
125°	811.9	812.1	811.7	811.2	810.8	810.3	811.0	811.7	812.4	813.0	813.5
127.5°	871.4	872.0	873.1	874.1	875.1	876.3	876.2	876.0	875.9	875.7	875.6
130°	911.5	912.0	912.7	913.3	914.0	914.7	914.9	915.1	915.4	915.6	915.7
132.5°	949.1	949.8	950.6	951.5	952.3	953.2	953.4	953.6	953.9	954.1	954.1
135°	1001.8	1002.2	1003.1	1004.0	1004.9	1005.8	1006.2	1006.7	1007.1	1007.6	1008.0
137.5°	1052.0	1052.5	1053.5	1054.5	1055.5	1056.5	1057.0	1057.5	1058.0	1058.5	1058.7
140°	1085.4	1085.8	1086.3	1086.7	1087.2	1087.6	1088.3	1089.0	1089.6	1090.4	1090.9
142.5°	1115.5	1116.0	1116.3	1116.5	1116.8	1117.1	1117.6	1118.1	1118.6	1119.1	1119.3
145°	1158.9	1159.2	1159.2	1159.2	1159.2	1159.2	1159.5	1159.7	1159.9	1160.1	1160.5
147.5°	1196.3	1196.8	1196.6	1196.4	1196.1	1195.9	1196.1	1196.3	1196.4	1196.6	1196.8
150°	1220.2	1220.5	1220.3	1220.1	1219.8	1219.6	1219.6	1219.6	1219.6	1219.6	1219.7
152.5°	1240.7	1240.9	1240.5	1240.1	1239.7	1239.3	1239.6	1240.0	1240.3	1240.7	1240.8
155°	1268.6	1268.4	1267.7	1267.1	1266.4	1265.7	1266.6	1267.5	1268.4	1269.3	1269.4
157.5°	1292.3	1291.9	1291.1	1290.3	1289.6	1288.8	1290.0	1291.1	1292.3	1293.5	1293.5
160°	1304.8	1304.4	1304.2	1303.9	1303.7	1303.5	1304.8	1306.3	1307.6	1309.0	1309.0
162.5°	1317.3	1316.7	1316.5	1316.3	1316.1	1315.8	1317.2	1318.5	1319.9	1321.2	1321.2
165°	1332.7	1332.2	1332.2	1332.2	1332.2	1332.2	1334.0	1335.8	1337.7	1339.5	1339.3
167.5°	1345.6	1345.0	1344.8	1344.7	1344.6	1344.4	1346.5	1348.5	1350.5	1352.4	1352.3
170°	1352.3	1351.7	1351.9	1352.2	1352.4	1352.6	1354.4	1356.2	1358.1	1359.9	1359.7
172.5°	1357.2	1356.7	1356.9	1357.1	1357.4	1357.6	1359.4	1361.2	1363.0	1364.8	1364.5
175°	1362.5	1362.0	1362.2	1362.4	1362.6	1362.9	1364.9	1367.0	1369.0	1371.1	1370.7
177.5°	1365.3	1364.9	1365.2	1365.6	1365.9	1366.3	1367.8	1369.3	1370.7	1372.2	1371.8
180°	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0



TEST NUMBER: P332817-840

CATALOG NUMBER: S124DIW-S1020D1050U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3
2.5°	1606.0	1604.9	1600.9	1600.4	1600.9	1604.9	1606.0	1607.1	1608.7	1614.4	1607.6
5°	1483.5	1480.1	1477.9	1485.6	1477.9	1480.1	1483.5	1487.7	1494.7	1495.4	1502.4
7.5°	1391.2	1388.5	1382.3	1380.4	1382.3	1388.5	1391.2	1393.7	1400.7	1406.7	1417.0
10°	1332.0	1329.2	1323.6	1322.2	1323.6	1329.2	1332.0	1339.0	1345.9	1353.6	1360.7
12.5°	1275.1	1269.5	1268.4	1269.7	1268.4	1269.5	1275.1	1284.2	1302.4	1302.3	1303.6
15°	1199.4	1196.6	1188.9	1191.0	1188.9	1196.6	1199.4	1208.5	1216.8	1227.3	1237.8
17.5°	1124.8	1121.5	1112.2	1120.3	1112.2	1121.5	1124.8	1129.7	1140.4	1155.3	1171.0
20°	1077.9	1072.3	1067.4	1066.7	1067.4	1072.3	1077.9	1082.8	1094.7	1107.2	1119.1
22.5°	1033.2	1028.2	1027.7	1023.2	1027.7	1028.2	1033.2	1040.9	1052.8	1059.8	1071.1
25°	977.3	972.5	971.1	967.7	971.1	972.5	977.3	983.0	990.7	996.2	1008.8
27.5°	934.5	932.1	929.6	930.7	929.6	932.1	934.5	935.2	938.7	946.1	953.3
30°	908.3	907.6	906.2	906.2	906.2	907.6	908.3	906.2	909.7	913.1	918.8
32.5°	886.5	886.4	887.2	887.2	887.2	886.4	886.5	883.2	884.5	885.8	888.6
35°	855.9	858.0	859.4	857.3	859.4	858.0	855.9	853.1	851.0	846.2	847.5
37.5°	828.3	830.3	832.3	834.7	832.3	830.3	828.3	822.5	817.5	813.1	808.2
40°	807.0	811.9	813.3	816.8	813.3	811.9	807.0	800.7	795.2	790.3	784.7
42.5°	786.9	792.3	796.0	796.7	796.0	792.3	786.9	780.6	772.2	766.3	758.4
45°	756.1	761.6	766.6	766.6	766.6	761.6	756.1	745.6	736.5	727.4	719.7
47.5°	724.1	732.2	737.1	738.3	737.1	732.2	724.1	713.4	700.6	689.4	678.4
50°	702.4	712.1	717.0	720.4	717.0	712.1	702.4	690.4	677.2	663.2	649.9
52.5°	681.1	690.8	697.4	699.2	697.4	690.8	681.1	666.4	650.4	635.3	623.7
55°	644.4	658.3	666.0	668.8	666.0	658.3	644.4	628.3	613.0	594.1	577.3
57.5°	609.8	622.6	631.6	633.6	631.6	622.6	609.8	590.9	571.1	551.0	533.1
60°	582.9	596.9	608.0	610.2	608.0	596.9	582.9	564.1	543.1	523.6	501.3
62.5°	555.5	570.1	580.2	585.6	580.2	570.1	555.5	535.6	513.0	491.2	468.9
65°	508.3	522.9	532.7	534.7	532.7	522.9	508.3	488.7	464.9	441.9	423.0
67.5°	456.6	471.2	477.7	481.7	477.7	471.2	456.6	438.2	414.7	390.8	369.4
70°	420.3	432.1	439.1	442.6	439.1	432.1	420.3	400.7	381.2	356.8	333.7
72.5°	378.9	391.3	399.5	400.2	399.5	391.3	378.9	362.1	341.5	318.8	298.5
75°	315.6	326.7	330.9	330.9	330.9	326.7	315.6	299.5	282.8	264.6	244.4
77.5°	249.7	255.5	260.8	262.0	260.8	255.5	249.7	238.2	224.4	206.2	191.0
80°	207.3	210.9	215.0	215.0	215.0	210.9	207.3	196.8	183.6	168.2	156.4
82.5°	163.8	166.7	170.9	170.4	170.9	166.7	163.8	155.5	144.5	134.2	123.4
85°	99.2	105.4	104.7	103.3	104.7	105.4	99.2	100.5	90.1	83.1	73.3
87.5°	50.6	51.2	52.9	54.1	52.9	51.2	50.6	48.8	43.5	40.5	38.0
90°	29.3	29.8	30.2	30.7	30.2	29.8	29.3	28.9	28.0	26.6	25.2
92.5°	28.0	28.1	28.2	28.3	28.2	28.1	28.0	27.9	27.2	25.8	24.4
95°	29.0	29.2	29.5	29.7	29.5	29.2	29.0	28.8	28.0	26.6	25.2
97.5°	28.0	28.2	28.4	28.7	28.4	28.2	28.0	27.8	27.6	27.5	27.3
100°	28.0	28.2	28.4	28.7	28.4	28.2	28.0	27.8	29.6	33.4	37.3
102.5°	29.3	29.4	29.4	29.5	29.4	29.4	29.3	29.3	50.1	91.8	133.5
105°	316.2	308.0	299.8	291.6	299.8	308.0	316.2	324.4	327.4	325.4	323.4
107.5°	403.8	404.7	405.6	406.4	405.6	404.7	403.8	402.9	402.0	401.0	400.0
110°	454.3	454.9	455.7	456.4	455.7	454.9	454.3	453.6	453.0	452.6	452.1



TEST NUMBER: P332817-840

CATALOG NUMBER: S124DIW-S1020D1050U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	503.7	504.5	505.4	506.2	505.4	504.5	503.7	502.8	502.4	502.5	502.6
115°	579.2	579.2	579.2	579.2	579.2	579.2	579.2	579.2	578.9	578.5	577.9
117.5°	653.5	653.4	653.3	653.2	653.3	653.4	653.5	653.6	653.7	653.8	653.8
120°	701.3	700.7	700.3	699.8	700.3	700.7	701.3	701.7	701.7	701.3	700.7
122.5°	747.1	746.6	746.2	745.7	746.2	746.6	747.1	747.5	747.6	747.3	747.1
125°	813.7	814.0	814.3	814.5	814.3	814.0	813.7	813.5	813.0	812.4	811.7
127.5°	875.4	875.1	874.9	874.8	874.9	875.1	875.4	875.6	875.7	875.9	876.0
130°	915.7	915.7	915.7	915.7	915.7	915.7	915.7	915.7	915.6	915.4	915.1
132.5°	953.9	953.7	953.6	953.4	953.6	953.7	953.9	954.1	954.1	953.9	953.6
135°	1008.6	1009.0	1009.5	1009.9	1009.5	1009.0	1008.6	1008.0	1007.6	1007.1	1006.7
137.5°	1058.5	1058.4	1058.3	1058.1	1058.3	1058.4	1058.5	1058.7	1058.5	1058.0	1057.5
140°	1091.1	1091.3	1091.5	1091.8	1091.5	1091.3	1091.1	1090.9	1090.4	1089.6	1089.0
142.5°	1119.4	1119.4	1119.5	1119.5	1119.5	1119.4	1119.4	1119.3	1119.1	1118.6	1118.1
145°	1160.9	1161.4	1161.8	1162.4	1161.8	1161.4	1160.9	1160.5	1160.1	1159.9	1159.7
147.5°	1197.1	1197.3	1197.5	1197.7	1197.5	1197.3	1197.1	1196.8	1196.6	1196.4	1196.3
150°	1219.9	1220.2	1220.4	1220.6	1220.4	1220.2	1219.9	1219.7	1219.6	1219.6	1219.6
152.5°	1240.7	1240.5	1240.4	1240.3	1240.4	1240.5	1240.7	1240.8	1240.7	1240.3	1240.0
155°	1268.7	1268.1	1267.4	1266.7	1267.4	1268.1	1268.7	1269.4	1269.3	1268.4	1267.5
157.5°	1292.3	1291.1	1290.0	1288.8	1290.0	1291.1	1292.3	1293.5	1293.5	1292.3	1291.1
160°	1307.6	1306.3	1304.8	1303.5	1304.8	1306.3	1307.6	1309.0	1309.0	1307.6	1306.3
162.5°	1319.6	1318.1	1316.6	1314.9	1316.6	1318.1	1319.6	1321.2	1321.2	1319.9	1318.5
165°	1337.3	1335.2	1333.2	1331.1	1333.2	1335.2	1337.3	1339.3	1339.5	1337.7	1335.8
167.5°	1350.1	1347.8	1345.5	1343.2	1345.5	1347.8	1350.1	1352.3	1352.4	1350.5	1348.5
170°	1357.4	1355.1	1352.8	1350.6	1352.8	1355.1	1357.4	1359.7	1359.9	1358.1	1356.2
172.5°	1362.0	1359.6	1357.2	1354.6	1357.2	1359.6	1362.0	1364.5	1364.8	1363.0	1361.2
175°	1368.0	1365.2	1362.5	1359.8	1362.5	1365.2	1368.0	1370.7	1371.1	1369.0	1367.0
177.5°	1369.6	1367.5	1365.2	1363.1	1365.2	1367.5	1369.6	1371.8	1372.2	1370.7	1369.3
180°	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0



TEST NUMBER: P332817-840

CATALOG NUMBER: S124DIW-S1020D1050U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3
2.5°	1611.0	1613.3	1622.1	1630.5	1640.6	1647.9	1652.8	1658.5	1670.2	1679.7	1688.6
5°	1509.3	1512.9	1531.0	1543.6	1565.2	1584.1	1598.7	1614.8	1633.7	1659.4	1683.1
7.5°	1419.9	1432.8	1452.7	1473.1	1495.1	1519.8	1541.4	1565.5	1598.0	1633.5	1670.0
10°	1369.1	1383.7	1404.6	1428.4	1449.4	1477.9	1504.5	1533.1	1570.0	1613.4	1656.7
12.5°	1318.2	1342.3	1358.3	1386.4	1409.1	1432.7	1460.9	1498.4	1541.6	1587.1	1639.3
15°	1254.6	1267.8	1298.5	1313.8	1345.9	1382.3	1410.2	1447.9	1489.8	1549.8	1608.5
17.5°	1181.1	1198.5	1222.9	1252.3	1289.2	1317.5	1352.3	1391.1	1443.9	1503.5	1576.9
20°	1133.1	1147.7	1177.7	1209.8	1248.9	1279.0	1316.0	1353.6	1408.2	1471.7	1548.4
22.5°	1090.0	1104.2	1135.9	1165.7	1203.7	1240.4	1279.1	1322.9	1375.1	1442.1	1520.6
25°	1023.5	1042.3	1070.3	1101.0	1137.2	1179.1	1221.0	1260.1	1316.0	1386.4	1470.3
27.5°	964.4	979.5	999.8	1034.6	1075.8	1116.3	1157.9	1207.1	1260.7	1335.2	1422.2
30°	926.5	940.4	960.6	992.7	1031.2	1074.4	1117.7	1165.2	1221.0	1295.1	1383.7
32.5°	896.3	906.9	924.8	953.6	988.7	1034.2	1076.9	1126.1	1184.7	1257.6	1344.0
35°	851.7	860.8	867.8	895.0	926.5	968.3	1011.6	1064.0	1120.4	1189.6	1276.2
37.5°	808.0	811.1	821.3	839.1	869.6	908.2	948.4	999.9	1057.8	1128.0	1206.1
40°	781.2	782.6	788.9	805.7	832.1	868.5	907.6	958.6	1013.7	1080.1	1157.5
42.5°	755.0	754.1	759.8	771.5	796.4	829.4	867.9	914.4	969.6	1030.9	1103.9
45°	713.5	713.5	712.1	721.9	742.1	774.3	806.4	851.0	897.1	957.2	1018.5
47.5°	670.2	666.3	667.5	672.6	689.6	716.0	748.4	785.0	825.6	876.5	930.3
50°	642.3	636.7	634.6	640.2	655.5	678.5	709.3	741.4	779.8	824.5	870.6
52.5°	611.6	606.0	602.2	606.1	620.4	641.7	669.6	697.8	732.4	768.6	808.6
55°	564.1	557.8	555.7	557.1	567.5	584.3	608.0	633.9	659.7	689.7	717.7
57.5°	517.4	507.0	505.0	504.3	511.6	526.9	546.7	569.2	587.9	606.1	635.8
60°	486.6	474.0	469.8	469.2	474.7	487.3	505.4	527.8	541.1	553.6	579.5
62.5°	453.6	441.6	432.4	433.4	438.4	450.4	466.4	482.5	491.3	505.0	522.5
65°	402.8	387.5	380.5	378.4	381.2	390.9	403.5	413.9	423.7	429.4	446.1
67.5°	352.0	339.1	328.8	326.3	325.1	331.7	342.0	348.4	355.4	360.2	370.1
70°	316.3	305.1	292.6	288.3	287.6	293.2	303.0	303.7	313.5	315.6	326.0
72.5°	281.0	267.1	258.4	254.3	251.4	256.3	262.8	264.6	269.9	273.7	279.1
75°	226.2	215.7	207.3	201.1	198.9	201.8	201.8	205.2	208.7	210.9	217.1
77.5°	178.0	166.0	156.1	152.5	150.0	148.1	149.7	151.8	150.1	153.7	155.1
80°	144.5	132.0	124.3	122.9	118.7	115.2	114.5	116.5	113.8	115.2	119.4
82.5°	111.6	103.5	95.2	93.8	88.6	86.7	86.0	84.7	84.7	84.4	85.3
85°	66.3	61.4	55.8	52.3	50.3	46.8	46.8	45.3	44.0	42.6	43.3
87.5°	31.6	30.2	27.1	25.0	23.5	20.9	20.5	18.3	17.3	16.2	15.1
90°	23.8	22.5	20.7	18.9	17.1	15.2	13.0	10.6	8.1	5.6	3.0
92.5°	23.0	21.7	19.9	18.1	16.3	14.4	13.4	13.3	13.1	13.0	12.9
95°	23.8	22.5	22.3	22.0	21.8	21.6	25.3	33.1	40.8	48.6	56.2
97.5°	27.2	27.0	52.4	77.8	103.1	128.6	138.8	134.0	129.2	124.3	119.5
100°	41.2	45.0	76.4	107.8	139.2	170.6	184.2	180.1	176.0	171.9	167.8
102.5°	175.2	216.9	221.0	225.1	229.2	233.3	233.8	230.9	227.8	224.8	221.9
105°	321.2	319.2	318.1	317.0	315.8	314.7	313.5	312.0	310.7	309.3	308.0
107.5°	399.0	398.0	396.5	395.0	393.3	391.8	390.7	390.0	389.3	388.7	388.0
110°	451.7	451.2	449.9	448.5	447.2	445.8	444.7	444.0	443.3	442.7	442.0



TEST NUMBER: P332817-840

CATALOG NUMBER: S124DIW-S1020D1050U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	502.7	502.8	502.1	501.5	500.9	500.3	499.3	498.1	496.9	495.6	494.4
115°	577.5	577.0	577.3	577.5	577.7	577.9	577.7	577.0	576.4	575.7	575.0
117.5°	653.9	654.0	653.5	653.0	652.5	652.0	651.3	650.4	649.4	648.5	647.6
120°	700.3	699.8	700.0	700.3	700.5	700.7	700.4	699.5	698.6	697.7	696.8
122.5°	746.8	746.5	746.2	745.9	745.6	745.3	744.8	744.3	743.7	743.2	742.7
125°	811.0	810.3	810.8	811.2	811.7	812.1	811.9	811.0	810.1	809.2	808.3
127.5°	876.2	876.3	875.1	874.1	873.1	872.0	871.4	871.2	871.0	870.7	870.5
130°	914.9	914.7	914.0	913.3	912.7	912.0	911.5	911.3	911.1	910.9	910.6
132.5°	953.4	953.2	952.3	951.5	950.6	949.8	949.1	948.7	948.3	947.9	947.5
135°	1006.2	1005.8	1004.9	1004.0	1003.1	1002.2	1001.8	1002.0	1002.3	1002.5	1002.7
137.5°	1057.0	1056.5	1055.5	1054.5	1053.5	1052.5	1052.0	1051.9	1051.8	1051.7	1051.6
140°	1088.3	1087.6	1087.2	1086.7	1086.3	1085.8	1085.4	1084.9	1084.5	1084.0	1083.6
142.5°	1117.6	1117.1	1116.8	1116.5	1116.3	1116.0	1115.5	1114.7	1113.8	1113.0	1112.2
145°	1159.5	1159.2	1159.2	1159.2	1159.2	1159.2	1158.9	1158.2	1157.5	1156.9	1156.2
147.5°	1196.1	1195.9	1196.1	1196.4	1196.6	1196.8	1196.3	1195.0	1193.8	1192.4	1191.1
150°	1219.6	1219.6	1219.8	1220.1	1220.3	1220.5	1220.2	1219.3	1218.4	1217.5	1216.6
152.5°	1239.6	1239.3	1239.7	1240.1	1240.5	1240.9	1240.7	1240.0	1239.3	1238.6	1237.8
155°	1266.6	1265.7	1266.4	1267.1	1267.7	1268.4	1268.6	1268.4	1268.2	1268.0	1267.7
157.5°	1290.0	1288.8	1289.6	1290.3	1291.1	1291.9	1292.3	1292.4	1292.6	1292.7	1292.9
160°	1304.8	1303.5	1303.7	1303.9	1304.2	1304.4	1304.8	1305.6	1306.3	1307.0	1307.6
162.5°	1317.2	1315.8	1316.1	1316.3	1316.5	1316.7	1317.3	1318.1	1319.0	1319.9	1320.7
165°	1334.0	1332.2	1332.2	1332.2	1332.2	1332.2	1332.7	1333.8	1335.0	1336.2	1337.3
167.5°	1346.5	1344.4	1344.6	1344.7	1344.8	1345.0	1345.6	1346.9	1348.1	1349.2	1350.4
170°	1354.4	1352.6	1352.4	1352.2	1351.9	1351.7	1352.3	1353.6	1355.0	1356.3	1357.8
172.5°	1359.4	1357.6	1357.4	1357.1	1356.9	1356.7	1357.2	1358.6	1359.9	1361.3	1362.6
175°	1364.9	1362.9	1362.6	1362.4	1362.2	1362.0	1362.5	1363.9	1365.2	1366.7	1368.0
177.5°	1367.8	1366.3	1365.9	1365.6	1365.2	1364.9	1365.3	1366.7	1367.9	1369.2	1370.4
180°	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0



TEST NUMBER: P332817-840

CATALOG NUMBER: S124DIW-S1020D1050U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3
2.5°	1696.5	1702.0	1709.3	1721.6	1726.1	1731.6	1739.5	1738.9	1741.1	1749.5	1767.4
5°	1702.7	1724.3	1745.3	1770.5	1797.0	1814.4	1838.2	1852.8	1867.4	1886.3	1918.4
7.5°	1705.3	1739.6	1778.0	1822.1	1861.4	1906.6	1941.9	1975.1	2005.2	2045.0	2083.3
10°	1701.3	1747.4	1797.0	1852.8	1912.2	1962.5	2007.8	2059.5	2103.4	2151.6	2194.9
12.5°	1694.0	1749.7	1815.9	1878.6	1947.9	2022.2	2078.7	2130.9	2189.5	2244.9	2311.7
15°	1677.6	1753.7	1831.2	1913.6	2006.4	2092.2	2173.9	2241.7	2304.5	2387.6	2474.9
17.5°	1656.7	1738.8	1836.4	1936.2	2033.3	2131.4	2232.5	2334.3	2413.6	2516.8	2585.1
20°	1637.1	1732.0	1832.6	1951.3	2048.3	2170.5	2271.0	2369.4	2478.3	2581.0	2662.6
22.5°	1609.7	1713.6	1820.3	1938.4	2066.2	2188.4	2304.5	2411.4	2520.2	2631.8	2730.8
25°	1575.0	1669.2	1795.5	1929.7	2056.7	2189.3	2322.7	2456.7	2573.9	2692.0	2784.1
27.5°	1515.8	1634.8	1752.4	1890.8	2031.9	2182.0	2324.6	2465.0	2587.8	2684.8	2742.0
30°	1485.6	1588.9	1716.7	1855.6	2008.5	2169.8	2318.4	2456.0	2570.5	2648.0	2671.0
32.5°	1441.0	1547.6	1672.5	1816.5	1978.3	2144.0	2299.0	2428.6	2524.2	2564.8	2537.0
35°	1374.6	1471.0	1597.3	1744.6	1912.9	2089.5	2242.4	2352.0	2400.9	2362.5	2266.8
37.5°	1295.1	1390.5	1517.4	1662.1	1836.2	2015.8	2154.0	2232.9	2216.7	2121.2	1978.6
40°	1239.2	1328.6	1449.4	1605.7	1775.3	1955.4	2076.9	2119.5	2074.9	1938.0	1786.6
42.5°	1177.2	1264.4	1385.6	1536.4	1716.2	1882.3	1988.1	1991.7	1916.7	1753.1	1601.0
45°	1082.8	1165.9	1280.4	1437.4	1603.6	1760.0	1829.8	1795.5	1657.4	1499.5	1346.7
47.5°	989.7	1061.7	1174.6	1323.6	1481.5	1613.1	1647.7	1586.1	1438.9	1285.7	1144.0
50°	921.5	994.1	1100.2	1242.6	1394.8	1508.6	1525.4	1443.7	1299.2	1144.9	1033.9
52.5°	856.2	928.3	1030.5	1162.3	1301.6	1404.2	1404.7	1310.2	1166.3	1028.7	925.5
55°	760.2	825.2	917.4	1035.3	1159.6	1239.9	1220.3	1122.6	997.6	878.3	788.2
57.5°	667.8	724.4	809.3	907.7	1017.1	1083.4	1051.0	956.8	845.3	744.1	675.8
60°	608.0	661.9	734.5	827.3	919.5	971.1	940.4	855.2	752.6	670.9	611.6
62.5°	550.0	595.3	665.2	745.8	831.2	869.5	842.1	758.0	669.3	595.5	547.3
65°	467.8	504.7	560.6	629.8	691.9	724.7	701.7	623.4	555.7	502.6	464.2
67.5°	390.9	419.9	462.1	517.6	570.4	588.1	567.1	512.7	455.3	412.8	385.8
70°	337.9	365.2	400.7	443.3	489.4	508.3	487.3	444.0	397.3	358.1	331.6
72.5°	291.5	312.7	342.6	379.1	415.2	433.9	419.7	378.1	338.6	309.5	286.9
75°	222.0	240.1	261.1	286.9	314.9	327.4	314.9	286.2	259.0	237.3	221.3
77.5°	161.4	171.2	187.3	206.6	224.1	233.7	222.9	203.4	186.8	172.0	164.1
80°	122.9	129.9	141.0	156.4	168.2	177.3	170.4	154.3	141.0	131.3	127.7
82.5°	89.4	94.1	101.4	112.8	120.8	125.4	122.3	110.7	105.2	96.6	93.1
85°	44.0	46.8	51.7	55.1	62.1	62.8	63.5	58.7	53.7	51.7	48.9
87.5°	16.2	17.3	19.4	21.6	24.2	25.1	25.0	25.3	23.5	23.2	21.2
90°	5.6	8.1	10.6	13.0	15.2	17.1	18.9	20.7	22.5	23.8	25.2
92.5°	13.0	13.1	13.3	13.4	14.4	16.3	18.1	19.9	21.7	23.0	24.4
95°	48.6	40.8	33.1	25.3	21.6	21.8	22.0	22.3	22.5	23.8	25.2
97.5°	124.3	129.2	134.0	138.8	128.6	103.1	77.8	52.4	27.0	27.2	27.3
100°	171.9	176.0	180.1	184.2	170.6	139.2	107.8	76.4	45.0	41.2	37.3
102.5°	224.8	227.8	230.9	233.8	233.3	229.2	225.1	221.0	216.9	175.2	133.5
105°	309.3	310.7	312.0	313.5	314.7	315.8	317.0	318.1	319.2	321.2	323.4
107.5°	388.7	389.3	390.0	390.7	391.8	393.3	395.0	396.5	398.0	399.0	400.0
110°	442.7	443.3	444.0	444.7	445.8	447.2	448.5	449.9	451.2	451.7	452.1



TEST NUMBER: P332817-840

CATALOG NUMBER: S124DIW-S1020D1050U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	495.6	496.9	498.1	499.3	500.3	500.9	501.5	502.1	502.8	502.7	502.6
115°	575.7	576.4	577.0	577.7	577.9	577.7	577.5	577.3	577.0	577.5	577.9
117.5°	648.5	649.4	650.4	651.3	652.0	652.5	653.0	653.5	654.0	653.9	653.8
120°	697.7	698.6	699.5	700.4	700.7	700.5	700.3	700.0	699.8	700.3	700.7
122.5°	743.2	743.7	744.3	744.8	745.3	745.6	745.9	746.2	746.5	746.8	747.1
125°	809.2	810.1	811.0	811.9	812.1	811.7	811.2	810.8	810.3	811.0	811.7
127.5°	870.7	871.0	871.2	871.4	872.0	873.1	874.1	875.1	876.3	876.2	876.0
130°	910.9	911.1	911.3	911.5	912.0	912.7	913.3	914.0	914.7	914.9	915.1
132.5°	947.9	948.3	948.7	949.1	949.8	950.6	951.5	952.3	953.2	953.4	953.6
135°	1002.5	1002.3	1002.0	1001.8	1002.2	1003.1	1004.0	1004.9	1005.8	1006.2	1006.7
137.5°	1051.7	1051.8	1051.9	1052.0	1052.5	1053.5	1054.5	1055.5	1056.5	1057.0	1057.5
140°	1084.0	1084.5	1084.9	1085.4	1085.8	1086.3	1086.7	1087.2	1087.6	1088.3	1089.0
142.5°	1113.0	1113.8	1114.7	1115.5	1116.0	1116.3	1116.5	1116.8	1117.1	1117.6	1118.1
145°	1156.9	1157.5	1158.2	1158.9	1159.2	1159.2	1159.2	1159.2	1159.2	1159.5	1159.7
147.5°	1192.4	1193.8	1195.0	1196.3	1196.8	1196.6	1196.4	1196.1	1195.9	1196.1	1196.3
150°	1217.5	1218.4	1219.3	1220.2	1220.5	1220.3	1220.1	1219.8	1219.6	1219.6	1219.6
152.5°	1238.6	1239.3	1240.0	1240.7	1240.9	1240.5	1240.1	1239.7	1239.3	1239.6	1240.0
155°	1268.0	1268.2	1268.4	1268.6	1268.4	1267.7	1267.1	1266.4	1265.7	1266.6	1267.5
157.5°	1292.7	1292.6	1292.4	1292.3	1291.9	1291.1	1290.3	1289.6	1288.8	1290.0	1291.1
160°	1307.0	1306.3	1305.6	1304.8	1304.4	1304.2	1303.9	1303.7	1303.5	1304.8	1306.3
162.5°	1319.9	1319.0	1318.1	1317.3	1316.7	1316.5	1316.3	1316.1	1315.8	1317.2	1318.5
165°	1336.2	1335.0	1333.8	1332.7	1332.2	1332.2	1332.2	1332.2	1332.2	1334.0	1335.8
167.5°	1349.2	1348.1	1346.9	1345.6	1345.0	1344.8	1344.7	1344.6	1344.4	1346.5	1348.5
170°	1356.3	1355.0	1353.6	1352.3	1351.7	1351.9	1352.2	1352.4	1352.6	1354.4	1356.2
172.5°	1361.3	1359.9	1358.6	1357.2	1356.7	1356.9	1357.1	1357.4	1357.6	1359.4	1361.2
175°	1366.7	1365.2	1363.9	1362.5	1362.0	1362.2	1362.4	1362.6	1362.9	1364.9	1367.0
177.5°	1369.2	1367.9	1366.7	1365.3	1364.9	1365.2	1365.6	1365.9	1366.3	1367.8	1369.3
180°	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0



TEST NUMBER: P332817-840

CATALOG NUMBER: S124DIW-S1020D1050U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3
2.5°	1776.4	1777.5	1782.4	1786.4	1787.5	1793.1	1793.6
5°	1932.4	1944.3	1967.3	1969.4	1972.9	1991.0	1977.1
7.5°	2115.4	2145.5	2165.6	2183.3	2189.8	2197.7	2196.1
10°	2232.6	2277.2	2299.7	2335.2	2336.6	2345.7	2340.2
12.5°	2350.5	2402.4	2443.2	2449.7	2479.6	2484.2	2492.0
15°	2517.4	2572.6	2629.2	2649.4	2690.6	2700.4	2715.7
17.5°	2674.4	2730.8	2770.5	2822.8	2839.7	2862.4	2846.9
20°	2760.4	2821.9	2872.1	2913.3	2930.7	2943.3	2941.9
22.5°	2812.4	2874.3	2915.1	2946.2	2962.5	2967.9	2967.6
25°	2844.9	2880.4	2893.1	2904.9	2886.8	2880.4	2883.3
27.5°	2754.4	2745.2	2712.4	2669.4	2624.6	2589.2	2569.9
30°	2629.9	2575.4	2525.8	2439.2	2394.6	2368.0	2344.3
32.5°	2453.4	2367.0	2271.7	2192.4	2141.6	2102.2	2096.4
35°	2150.9	2021.0	1904.5	1807.5	1757.2	1714.5	1704.9
37.5°	1828.7	1693.7	1588.8	1503.4	1449.4	1419.3	1391.2
40°	1614.8	1498.8	1395.5	1322.9	1281.7	1260.1	1242.6
42.5°	1450.0	1344.1	1241.4	1186.1	1148.8	1135.6	1125.4
45°	1222.4	1124.0	1052.8	1010.9	989.3	966.9	956.4
47.5°	1040.2	960.1	913.1	877.6	854.3	841.1	834.4
50°	936.9	871.2	829.4	802.1	781.2	770.7	765.2
52.5°	845.3	791.4	756.2	734.6	720.3	712.7	710.4
55°	728.1	686.9	664.6	645.8	635.3	628.3	625.5
57.5°	632.9	601.3	583.1	567.5	563.5	557.6	555.7
60°	570.4	545.9	530.6	520.1	516.6	509.7	511.0
62.5°	515.0	495.1	482.0	475.9	471.4	465.5	467.5
65°	435.7	421.0	413.9	408.4	402.8	399.3	402.1
67.5°	365.6	355.5	346.0	342.7	340.0	339.4	336.5
70°	319.7	311.3	303.0	300.9	300.9	298.1	297.4
72.5°	275.6	269.4	263.9	262.4	260.1	261.3	258.3
75°	212.9	208.0	205.9	203.9	203.2	203.2	201.1
77.5°	157.3	153.7	150.4	150.4	147.8	146.9	146.6
80°	119.4	118.0	115.2	115.2	113.8	114.5	113.1
82.5°	89.8	87.9	87.3	86.1	84.2	84.3	82.9
85°	48.2	46.0	45.3	43.3	41.9	43.3	41.9
87.5°	22.1	21.8	21.4	20.4	19.9	20.0	18.4
90°	26.6	28.0	28.9	29.3	29.8	30.2	30.7
92.5°	25.8	27.2	27.9	28.0	28.1	28.2	28.3
95°	26.6	28.0	28.8	29.0	29.2	29.5	29.7
97.5°	27.5	27.6	27.8	28.0	28.2	28.4	28.7
100°	33.4	29.6	27.8	28.0	28.2	28.4	28.7
102.5°	91.8	50.1	29.3	29.3	29.4	29.4	29.5
105°	325.4	327.4	324.4	316.2	308.0	299.8	291.6
107.5°	401.0	402.0	402.9	403.8	404.7	405.6	406.4
110°	452.6	453.0	453.6	454.3	454.9	455.7	456.4



TEST NUMBER: P332817-840

CATALOG NUMBER: S124DIW-S1020D1050U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	502.5	502.4	502.8	503.7	504.5	505.4	506.2
115°	578.5	578.9	579.2	579.2	579.2	579.2	579.2
117.5°	653.8	653.7	653.6	653.5	653.4	653.3	653.2
120°	701.3	701.7	701.7	701.3	700.7	700.3	699.8
122.5°	747.3	747.6	747.5	747.1	746.6	746.2	745.7
125°	812.4	813.0	813.5	813.7	814.0	814.3	814.5
127.5°	875.9	875.7	875.6	875.4	875.1	874.9	874.8
130°	915.4	915.6	915.7	915.7	915.7	915.7	915.7
132.5°	953.9	954.1	954.1	953.9	953.7	953.6	953.4
135°	1007.1	1007.6	1008.0	1008.6	1009.0	1009.5	1009.9
137.5°	1058.0	1058.5	1058.7	1058.5	1058.4	1058.3	1058.1
140°	1089.6	1090.4	1090.9	1091.1	1091.3	1091.5	1091.8
142.5°	1118.6	1119.1	1119.3	1119.4	1119.4	1119.5	1119.5
145°	1159.9	1160.1	1160.5	1160.9	1161.4	1161.8	1162.4
147.5°	1196.4	1196.6	1196.8	1197.1	1197.3	1197.5	1197.7
150°	1219.6	1219.6	1219.7	1219.9	1220.2	1220.4	1220.6
152.5°	1240.3	1240.7	1240.8	1240.7	1240.5	1240.4	1240.3
155°	1268.4	1269.3	1269.4	1268.7	1268.1	1267.4	1266.7
157.5°	1292.3	1293.5	1293.5	1292.3	1291.1	1290.0	1288.8
160°	1307.6	1309.0	1309.0	1307.6	1306.3	1304.8	1303.5
162.5°	1319.9	1321.2	1321.2	1319.6	1318.1	1316.6	1314.9
165°	1337.7	1339.5	1339.3	1337.3	1335.2	1333.2	1331.1
167.5°	1350.5	1352.4	1352.3	1350.1	1347.8	1345.5	1343.2
170°	1358.1	1359.9	1359.7	1357.4	1355.1	1352.8	1350.6
172.5°	1363.0	1364.8	1364.5	1362.0	1359.6	1357.2	1354.6
175°	1369.0	1371.1	1370.7	1368.0	1365.2	1362.5	1359.8
177.5°	1370.7	1372.2	1371.8	1369.6	1367.5	1365.2	1363.1
180°	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0

(END OF REPORT)