

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332822-840

Luminaire Tested: **S124DIW-S1020D1050U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332822-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1020D1050U840-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8145.4 lumens
Efficiency: N/A
Efficacy: 133.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332822-840

CATALOG NUMBER: S124DIW-S1020D1050U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332822-840

CATALOG NUMBER: S124DIW-S1020D1050U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55																												
1	99	94	91	87	92	88	84	81	75	73	71	64	62	61	54	52	51	46																												
2	90	82	76	71	83	77	71	67	66	62	58	56	53	51	47	45	43	39																												
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33																												
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	32	28																												
5	69	57	49	43	64	53	46	41	46	41	36	40	35	32	34	30	28	24																												
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	31	27	24	21																												
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	22	19																												
8	55	42	34	29	51	40	32	28	35	29	25	30	25	22	26	22	19	17																												
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	17	15																												
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	18	16	14																												

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14067	14067	14067
5°	14109	13940	14041
10°	14021	13827	13896
15°	13852	13630	13665
20°	13626	13387	13399
25°	13370	13109	13071
30°	13055	12781	12665
35°	12728	12439	12275
40°	12390	12052	11830
45°	12036	11669	11445
50°	11645	11328	10977
55°	11222	10888	10534
60°	10798	10393	10077
65°	10323	9922	9522
70°	9788	9293	8932
75°	8971	8537	8319
80°	7987	7657	7466
85°	6984	6725	6595



TEST NUMBER: P332822-840

CATALOG NUMBER: S124DIW-S1020D1050U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.1	2.0
10°-20°	462.4	5.7
20°-30°	680.5	8.4
30°-40°	791.1	9.7
40°-50°	791.2	9.7
50°-60°	692.1	8.5
60°-70°	514.0	6.3
70°-80°	292.0	3.6
80°-90°	88.2	1.1
90°-100°	87.2	1.1
100°-110°	258.4	3.2
110°-120°	438.7	5.4
120°-130°	578.4	7.1
130°-140°	649.6	8.0
140°-150°	638.4	7.8
150°-160°	536.9	6.6
160°-170°	357.2	4.4
170°-180°	125.1	1.5
0°-30°	1307.0	16.0
0°-40°	2098.1	25.8
0°-60°	3581.3	44.0
0°-90°	4475.5	54.9
90°-120°	784.3	9.6
90°-150°	2650.7	32.5
90°-180°	3670.0	45.1
0°-180°	8145.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1742	1742	1742	1742	1742	
5°	1741	1735	1720	1735	1733	165
15°	1657	1651	1631	1638	1635	467
25°	1501	1491	1472	1473	1467	690
35°	1292	1281	1262	1253	1246	807
45°	1054	1044	1022	1007	1002	812
55°	797	792	774	757	748	714
65°	540	533	519	506	498	535
75°	288	281	274	268	267	306
85°	75	75	73	72	71	83
90°	3	14	22	28	31	8
95°	61	70	78	81	81	68
105°	238	240	244	247	250	253
115°	446	446	444	443	442	440
125°	650	650	649	647	644	579
135°	838	844	844	842	839	648
145°	1018	1022	1023	1022	1019	637
155°	1166	1166	1165	1169	1165	536
165°	1270	1267	1264	1270	1266	358
175°	1321	1316	1315	1321	1315	125
180°	1323	1323	1323	1323	1323	



TEST NUMBER: P332822-840

CATALOG NUMBER: S124DIW-S1020D1050U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5
2.5°	1747.0	1746.3	1745.5	1744.7	1744.0	1742.2	1739.5	1736.8	1734.0	1731.3	1733.8
5°	1741.1	1739.9	1738.7	1737.4	1736.2	1733.8	1730.4	1727.0	1723.6	1720.2	1723.6
7.5°	1725.0	1723.6	1722.4	1721.2	1720.0	1717.5	1713.6	1709.9	1706.1	1702.3	1705.1
10°	1710.4	1709.2	1707.9	1706.7	1705.5	1702.8	1698.8	1694.8	1690.7	1686.7	1689.1
12.5°	1691.4	1690.2	1688.9	1687.7	1686.5	1683.6	1679.4	1675.2	1670.8	1666.6	1669.3
15°	1657.4	1656.1	1654.9	1653.7	1652.3	1649.4	1644.8	1640.1	1635.5	1630.8	1632.6
17.5°	1616.3	1614.8	1613.2	1611.6	1610.1	1607.1	1602.7	1598.3	1593.9	1589.5	1590.6
20°	1586.1	1584.6	1583.1	1581.4	1579.9	1576.8	1572.2	1567.5	1562.9	1558.2	1559.1
22.5°	1553.8	1551.7	1549.6	1547.6	1545.6	1542.2	1537.5	1532.9	1528.2	1523.6	1525.3
25°	1501.0	1498.8	1496.6	1494.4	1492.3	1489.0	1484.7	1480.4	1476.0	1471.7	1472.0
27.5°	1440.7	1438.5	1436.1	1433.9	1431.7	1428.6	1424.5	1420.5	1416.4	1412.4	1411.7
30°	1400.5	1398.0	1395.4	1393.0	1390.5	1387.3	1383.2	1379.2	1375.1	1371.1	1369.9
32.5°	1358.0	1355.7	1353.5	1351.3	1349.1	1345.7	1341.5	1337.3	1332.9	1328.7	1327.2
35°	1291.5	1289.4	1287.2	1285.1	1282.8	1279.6	1275.3	1270.9	1266.6	1262.2	1260.0
37.5°	1221.4	1219.4	1217.5	1215.5	1213.5	1210.2	1205.5	1200.8	1196.2	1191.5	1189.2
40°	1175.7	1173.2	1170.6	1168.2	1165.7	1162.2	1157.5	1152.9	1148.2	1143.6	1140.4
42.5°	1126.5	1125.0	1123.5	1122.1	1120.5	1117.2	1112.1	1106.9	1101.8	1096.6	1093.0
45°	1054.2	1052.0	1049.9	1047.6	1045.5	1041.9	1036.9	1032.0	1027.0	1022.1	1018.7
47.5°	978.5	977.0	975.5	974.0	972.5	969.5	964.9	960.3	955.7	951.1	947.3
50°	927.2	925.8	924.6	923.4	922.1	919.4	915.0	910.7	906.4	902.0	897.7
52.5°	876.9	875.4	873.8	872.4	870.9	867.9	863.2	858.7	854.0	849.5	845.7
55°	797.3	796.3	795.4	794.5	793.6	790.9	786.6	782.2	777.9	773.6	769.8
57.5°	721.3	720.2	719.2	718.1	717.1	714.4	710.1	705.9	701.6	697.3	693.8
60°	668.8	667.2	665.7	664.2	662.6	659.8	655.8	651.8	647.7	643.7	640.9
62.5°	617.4	616.1	614.8	613.5	612.2	609.5	605.1	600.9	596.5	592.3	589.8
65°	540.4	538.8	537.2	535.7	534.1	531.8	528.7	525.6	522.5	519.4	516.3
67.5°	462.7	461.3	459.9	458.5	457.0	454.8	451.8	448.9	445.9	442.9	439.9
70°	414.7	412.5	410.3	408.2	406.0	403.6	401.2	398.7	396.3	393.7	391.2
72.5°	363.3	361.1	359.0	356.8	354.7	352.5	350.5	348.6	346.6	344.6	342.6
75°	287.6	286.1	284.5	283.0	281.4	279.8	278.3	276.8	275.2	273.7	272.5
77.5°	215.3	214.6	213.9	213.3	212.6	211.6	210.2	208.8	207.4	206.1	205.7
80°	171.8	170.8	169.9	169.0	168.0	167.2	166.6	166.0	165.4	164.7	164.1
82.5°	129.3	128.9	128.5	127.9	127.5	127.2	127.1	127.0	126.9	126.7	126.4
85°	75.4	75.4	75.4	75.4	75.4	75.1	74.4	73.8	73.2	72.6	72.6
87.5°	29.7	29.9	30.2	30.4	30.7	30.8	31.0	31.1	31.2	31.3	31.6
90°	3.0	5.6	8.1	10.6	13.0	15.2	17.1	18.9	20.7	22.5	23.8
92.5°	21.9	24.7	27.7	30.5	33.3	35.4	36.7	38.0	39.3	40.5	41.3
95°	61.4	63.4	65.4	67.6	69.6	71.4	73.0	74.5	76.1	77.8	78.5
97.5°	107.2	108.9	110.5	112.1	113.8	115.5	117.3	119.3	121.1	123.0	123.8
100°	143.2	144.1	145.0	145.9	146.8	148.3	150.4	152.4	154.5	156.5	156.9
102.5°	180.9	181.3	181.6	182.0	182.3	183.4	185.3	187.1	189.0	190.9	191.6
105°	238.3	238.6	238.8	239.0	239.2	239.8	240.8	241.7	242.6	243.5	244.2
107.5°	298.7	299.0	299.2	299.5	299.8	300.0	300.1	300.3	300.4	300.5	301.2
110°	339.6	340.1	340.5	341.0	341.4	341.5	341.3	341.1	340.9	340.6	340.2



TEST NUMBER: P332822-840

CATALOG NUMBER: S124DIW-S1020D1050U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	382.2	382.3	382.4	382.4	382.5	382.4	382.0	381.6	381.2	380.8	380.7
115°	446.1	446.1	446.1	446.1	446.1	445.9	445.4	444.9	444.4	444.0	443.7
117.5°	506.2	506.3	506.5	506.8	507.0	506.9	506.5	506.2	505.9	505.5	504.8
120°	546.3	547.2	548.2	549.1	550.0	550.1	549.4	548.7	548.1	547.3	546.2
122.5°	588.0	588.4	588.8	589.2	589.5	589.6	589.2	588.9	588.5	588.2	587.4
125°	649.6	649.6	649.6	649.6	649.6	649.5	649.2	649.0	648.8	648.6	648.1
127.5°	705.5	706.2	706.8	707.5	708.2	708.4	708.0	707.6	707.3	706.9	706.5
130°	744.8	745.5	746.1	746.8	747.5	747.8	747.8	747.8	747.8	747.8	747.4
132.5°	784.9	785.4	785.9	786.4	786.9	787.0	786.9	786.7	786.5	786.3	785.9
135°	837.9	839.2	840.6	841.9	843.3	844.0	844.0	844.0	844.0	844.0	843.5
137.5°	895.5	896.2	896.9	897.5	898.1	898.6	899.0	899.4	899.7	900.1	899.5
140°	934.0	934.5	934.9	935.4	935.8	936.0	936.0	936.0	936.0	936.0	935.8
142.5°	969.3	969.7	970.2	970.6	971.1	971.2	971.0	970.8	970.7	970.5	970.4
145°	1017.9	1018.9	1019.8	1020.7	1021.6	1022.1	1022.4	1022.6	1022.8	1023.0	1022.8
147.5°	1066.2	1067.3	1068.4	1069.4	1070.6	1071.1	1070.9	1070.7	1070.5	1070.3	1070.2
150°	1095.7	1096.6	1097.5	1098.4	1099.3	1099.7	1099.7	1099.7	1099.7	1099.7	1099.7
152.5°	1123.5	1124.1	1124.6	1125.1	1125.7	1126.0	1126.2	1126.4	1126.6	1126.8	1127.3
155°	1166.3	1166.3	1166.3	1166.3	1166.3	1166.2	1165.9	1165.7	1165.5	1165.3	1166.2
157.5°	1202.2	1201.8	1201.4	1201.0	1200.6	1200.4	1200.3	1200.3	1200.2	1200.2	1200.9
160°	1223.6	1223.4	1223.0	1222.8	1222.6	1222.4	1222.1	1221.9	1221.7	1221.5	1222.1
162.5°	1243.1	1242.6	1242.0	1241.4	1240.8	1240.4	1240.2	1240.0	1239.7	1239.5	1240.7
165°	1269.6	1268.9	1268.2	1267.6	1266.9	1266.3	1265.9	1265.4	1265.0	1264.5	1265.9
167.5°	1289.8	1288.9	1288.0	1287.0	1286.1	1285.6	1285.7	1285.7	1285.7	1285.8	1287.1
170°	1301.3	1300.2	1299.0	1297.9	1296.8	1296.3	1296.6	1296.8	1297.0	1297.2	1298.6
172.5°	1309.5	1308.5	1307.6	1306.7	1305.7	1305.3	1305.3	1305.4	1305.4	1305.4	1307.0
175°	1320.7	1319.6	1318.5	1317.4	1316.2	1315.6	1315.2	1315.0	1314.8	1314.6	1316.2
177.5°	1324.4	1323.5	1322.6	1321.7	1320.8	1320.3	1320.3	1320.3	1320.3	1320.3	1321.6
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8



TEST NUMBER: P332822-840

CATALOG NUMBER: S124DIW-S1020D1050U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5
2.5°	1736.3	1738.8	1741.3	1742.4	1742.1	1741.9	1741.6	1741.4
5°	1727.0	1730.4	1733.8	1735.3	1734.6	1733.9	1733.3	1732.7
7.5°	1707.8	1710.5	1713.2	1714.4	1714.0	1713.6	1713.2	1712.9
10°	1691.6	1694.1	1696.6	1697.5	1696.9	1696.3	1695.7	1695.1
12.5°	1672.0	1674.8	1677.5	1678.4	1677.6	1676.7	1675.8	1675.0
15°	1634.6	1636.4	1638.3	1638.7	1637.8	1636.9	1636.0	1635.0
17.5°	1591.9	1593.1	1594.2	1594.5	1593.9	1593.3	1592.7	1592.0
20°	1560.0	1561.0	1562.0	1562.1	1561.5	1560.8	1560.2	1559.6
22.5°	1526.9	1528.6	1530.2	1530.6	1529.4	1528.3	1527.2	1526.1
25°	1472.3	1472.6	1472.9	1472.4	1471.2	1470.0	1468.6	1467.4
27.5°	1411.0	1410.2	1409.5	1408.4	1406.7	1405.2	1403.6	1402.1
30°	1368.7	1367.4	1366.1	1364.7	1363.2	1361.6	1360.1	1358.6
32.5°	1325.6	1324.2	1322.7	1321.2	1319.6	1318.1	1316.6	1314.9
35°	1257.9	1255.7	1253.5	1251.6	1250.1	1248.6	1247.0	1245.5
37.5°	1186.8	1184.5	1182.1	1179.9	1177.9	1175.8	1173.8	1171.7
40°	1137.3	1134.2	1131.1	1128.8	1127.2	1125.7	1124.2	1122.6
42.5°	1089.4	1085.8	1082.2	1079.8	1078.8	1077.7	1076.7	1075.7
45°	1015.2	1011.8	1008.4	1006.2	1005.3	1004.4	1003.4	1002.5
47.5°	943.4	939.6	935.7	932.6	930.3	927.9	925.5	923.2
50°	893.3	889.0	884.6	881.5	879.6	877.8	876.0	874.0
52.5°	841.8	837.9	834.0	831.0	828.6	826.3	823.9	821.5
55°	766.1	762.3	758.6	755.9	754.0	752.1	750.2	748.4
57.5°	690.2	686.7	683.2	680.4	678.6	676.9	675.1	673.3
60°	638.1	635.3	632.5	630.4	628.7	627.2	625.7	624.1
62.5°	587.2	584.6	582.1	580.1	578.6	576.9	575.4	573.9
65°	513.2	510.1	507.0	504.6	503.1	501.6	500.0	498.5
67.5°	437.0	433.9	431.0	429.3	428.8	428.4	428.0	427.6
70°	388.8	386.3	383.8	382.1	381.2	380.2	379.3	378.4
72.5°	340.6	338.6	336.7	335.2	334.3	333.4	332.4	331.4
75°	271.1	269.9	268.7	267.9	267.6	267.3	267.0	266.7
77.5°	205.3	205.0	204.6	204.0	203.2	202.4	201.6	200.8
80°	163.5	162.9	162.3	161.8	161.5	161.2	160.9	160.6
82.5°	126.0	125.6	125.3	124.9	124.6	124.3	124.0	123.7
85°	72.6	72.6	72.6	72.4	72.1	71.8	71.5	71.2
87.5°	31.8	32.1	32.4	32.6	32.7	32.7	32.8	32.9
90°	25.2	26.6	28.0	28.9	29.3	29.8	30.2	30.7
92.5°	42.1	42.9	43.8	44.3	44.6	44.8	45.1	45.4
95°	79.1	79.8	80.5	80.8	80.8	80.8	80.8	80.8
97.5°	124.6	125.4	126.2	126.6	126.6	126.6	126.6	126.6
100°	157.4	157.8	158.3	158.5	158.5	158.5	158.5	158.5
102.5°	192.2	192.8	193.5	193.9	194.0	194.2	194.4	194.6
105°	244.9	245.5	246.2	246.9	247.6	248.2	248.9	249.6
107.5°	301.8	302.5	303.2	303.4	303.4	303.4	303.3	303.3
110°	339.7	339.3	338.8	339.0	339.6	340.3	341.0	341.7



TEST NUMBER: P332822-840

CATALOG NUMBER: S124DIW-S1020D1050U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	380.6	380.5	380.4	380.4	380.6	380.7	380.8	381.0
115°	443.5	443.3	443.1	442.8	442.6	442.4	442.2	441.9
117.5°	504.0	503.2	502.5	501.9	501.4	501.0	500.5	500.1
120°	545.0	543.9	542.8	542.4	542.9	543.3	543.8	544.2
122.5°	586.7	585.9	585.1	584.3	583.5	582.7	581.9	581.1
125°	647.7	647.2	646.8	646.3	645.9	645.4	645.0	644.5
127.5°	706.0	705.6	705.1	704.7	704.3	704.0	703.6	703.3
130°	746.9	746.5	746.0	745.4	744.5	743.6	742.7	741.7
132.5°	785.4	785.0	784.5	784.1	783.8	783.4	782.9	782.6
135°	843.1	842.6	842.2	841.6	840.9	840.2	839.6	838.9
137.5°	898.9	898.3	897.7	897.5	897.6	897.8	897.9	898.0
140°	935.6	935.4	935.1	934.9	934.7	934.5	934.2	934.0
142.5°	970.4	970.3	970.3	970.2	970.2	970.2	970.1	970.1
145°	1022.6	1022.4	1022.1	1021.7	1021.0	1020.3	1019.7	1019.0
147.5°	1070.0	1069.8	1069.5	1069.3	1069.1	1068.9	1068.6	1068.4
150°	1099.7	1099.7	1099.7	1099.6	1099.4	1099.2	1098.9	1098.7
152.5°	1127.8	1128.4	1128.9	1128.9	1128.3	1127.7	1127.1	1126.6
155°	1167.1	1168.0	1168.9	1168.9	1168.0	1167.1	1166.2	1165.3
157.5°	1201.6	1202.2	1203.0	1203.0	1202.1	1201.3	1200.6	1199.8
160°	1222.8	1223.6	1224.3	1224.0	1222.8	1221.7	1220.6	1219.4
162.5°	1241.9	1243.1	1244.5	1244.5	1243.3	1242.2	1241.0	1239.9
165°	1267.2	1268.6	1269.9	1270.1	1269.2	1268.3	1267.4	1266.5
167.5°	1288.5	1289.8	1291.2	1291.2	1289.8	1288.4	1287.0	1285.6
170°	1299.9	1301.3	1302.6	1302.5	1301.0	1299.4	1297.8	1296.2
172.5°	1308.5	1310.0	1311.6	1311.5	1310.0	1308.4	1306.8	1305.1
175°	1317.8	1319.4	1321.0	1321.0	1319.4	1317.8	1316.2	1314.6
177.5°	1322.9	1324.1	1325.4	1325.3	1323.8	1322.4	1321.0	1319.5
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8

(END OF REPORT)