

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332828-840

Luminaire Tested: **S124DIW-S1020D1340U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332828-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1020D1340U840-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9174.9 lumens
Efficiency: N/A
Efficacy: 131.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332828-840

CATALOG NUMBER: S124DIW-S1020D1340U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332828-840

CATALOG NUMBER: S124DIW-S1020D1340U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	49	47	46	41
2	89	81	75	70	81	75	70	65	63	59	56	53	50	47	43	41	39	34
3	81	71	64	58	74	66	60	54	56	51	47	47	43	40	38	35	33	29
4	74	63	55	49	68	59	52	46	50	44	40	41	38	34	34	31	29	25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	22
6	63	51	42	37	57	47	40	34	40	34	30	34	29	26	28	24	22	19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20	17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14067	14067	14067
5°	14109	13940	14041
10°	14021	13827	13896
15°	13852	13630	13665
20°	13626	13387	13399
25°	13370	13109	13071
30°	13055	12781	12665
35°	12728	12439	12275
40°	12390	12052	11830
45°	12036	11669	11445
50°	11645	11328	10977
55°	11222	10888	10534
60°	10798	10393	10077
65°	10323	9922	9522
70°	9788	9293	8932
75°	8971	8537	8319
80°	7987	7657	7466
85°	6984	6725	6595



TEST NUMBER: P332828-840

CATALOG NUMBER: S124DIW-S1020D1340U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.1	1.8
10°-20°	462.4	5.0
20°-30°	680.5	7.4
30°-40°	791.1	8.6
40°-50°	791.2	8.6
50°-60°	692.1	7.5
60°-70°	514.0	5.6
70°-80°	292.0	3.2
80°-90°	89.3	1.0
90°-100°	111.7	1.2
100°-110°	330.9	3.6
110°-120°	561.6	6.1
120°-130°	740.5	8.1
130°-140°	831.6	9.1
140°-150°	817.2	8.9
150°-160°	687.3	7.5
160°-170°	457.3	5.0
170°-180°	160.1	1.7
0°-30°	1307.0	14.2
0°-40°	2098.1	22.9
0°-60°	3581.3	39.0
0°-90°	4476.6	48.8
90°-120°	1004.2	10.9
90°-150°	3393.5	37.0
90°-180°	4698.0	51.2
0°-180°	9174.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1742	1742	1742	1742	1742	
5°	1741	1735	1720	1735	1733	165
15°	1657	1651	1631	1638	1635	467
25°	1501	1491	1472	1473	1467	690
35°	1292	1281	1262	1253	1246	807
45°	1054	1044	1022	1007	1002	812
55°	797	792	774	757	748	714
65°	540	533	519	506	498	535
75°	288	281	274	268	267	306
85°	75	75	73	72	71	83
90°	4	18	29	36	39	9
95°	79	90	100	103	104	87
105°	305	307	312	316	320	324
115°	571	571	568	567	566	563
125°	832	832	830	828	825	741
135°	1073	1080	1080	1078	1074	830
145°	1303	1308	1310	1308	1304	815
155°	1493	1493	1492	1496	1492	687
165°	1625	1621	1619	1626	1621	458
175°	1691	1685	1683	1691	1683	160
180°	1693	1693	1693	1693	1693	



TEST NUMBER: P332828-840

CATALOG NUMBER: S124DIW-S1020D1340U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5
2.5°	1747.0	1746.3	1745.5	1744.7	1744.0	1742.2	1739.5	1736.8	1734.0	1731.3	1733.8
5°	1741.1	1739.9	1738.7	1737.4	1736.2	1733.8	1730.4	1727.0	1723.6	1720.2	1723.6
7.5°	1725.0	1723.6	1722.4	1721.2	1720.0	1717.5	1713.6	1709.9	1706.1	1702.3	1705.1
10°	1710.4	1709.2	1707.9	1706.7	1705.5	1702.8	1698.8	1694.8	1690.7	1686.7	1689.1
12.5°	1691.4	1690.2	1688.9	1687.7	1686.5	1683.6	1679.4	1675.2	1670.8	1666.6	1669.3
15°	1657.4	1656.1	1654.9	1653.7	1652.3	1649.4	1644.8	1640.1	1635.5	1630.8	1632.6
17.5°	1616.3	1614.8	1613.2	1611.6	1610.1	1607.1	1602.7	1598.3	1593.9	1589.5	1590.6
20°	1586.1	1584.6	1583.1	1581.4	1579.9	1576.8	1572.2	1567.5	1562.9	1558.2	1559.1
22.5°	1553.8	1551.7	1549.6	1547.6	1545.6	1542.2	1537.5	1532.9	1528.2	1523.6	1525.3
25°	1501.0	1498.8	1496.6	1494.4	1492.3	1489.0	1484.7	1480.4	1476.0	1471.7	1472.0
27.5°	1440.7	1438.5	1436.1	1433.9	1431.7	1428.6	1424.5	1420.5	1416.4	1412.4	1411.7
30°	1400.5	1398.0	1395.4	1393.0	1390.5	1387.3	1383.2	1379.2	1375.1	1371.1	1369.9
32.5°	1358.0	1355.7	1353.5	1351.3	1349.1	1345.7	1341.5	1337.3	1332.9	1328.7	1327.2
35°	1291.5	1289.4	1287.2	1285.1	1282.8	1279.6	1275.3	1270.9	1266.6	1262.2	1260.0
37.5°	1221.4	1219.4	1217.5	1215.5	1213.5	1210.2	1205.5	1200.8	1196.2	1191.5	1189.2
40°	1175.7	1173.2	1170.6	1168.2	1165.7	1162.2	1157.5	1152.9	1148.2	1143.6	1140.4
42.5°	1126.5	1125.0	1123.5	1122.1	1120.5	1117.2	1112.1	1106.9	1101.8	1096.6	1093.0
45°	1054.2	1052.0	1049.9	1047.6	1045.5	1041.9	1036.9	1032.0	1027.0	1022.1	1018.7
47.5°	978.5	977.0	975.5	974.0	972.5	969.5	964.9	960.3	955.7	951.1	947.3
50°	927.2	925.8	924.6	923.4	922.1	919.4	915.0	910.7	906.4	902.0	897.7
52.5°	876.9	875.4	873.8	872.4	870.9	867.9	863.2	858.7	854.0	849.5	845.7
55°	797.3	796.3	795.4	794.5	793.6	790.9	786.6	782.2	777.9	773.6	769.8
57.5°	721.3	720.2	719.2	718.1	717.1	714.4	710.1	705.9	701.6	697.3	693.8
60°	668.8	667.2	665.7	664.2	662.6	659.8	655.8	651.8	647.7	643.7	640.9
62.5°	617.4	616.1	614.8	613.5	612.2	609.5	605.1	600.9	596.5	592.3	589.8
65°	540.4	538.8	537.2	535.7	534.1	531.8	528.7	525.6	522.5	519.4	516.3
67.5°	462.7	461.3	459.9	458.5	457.0	454.8	451.8	448.9	445.9	442.9	439.9
70°	414.7	412.5	410.3	408.2	406.0	403.6	401.2	398.7	396.3	393.7	391.2
72.5°	363.3	361.1	359.0	356.8	354.7	352.5	350.5	348.6	346.6	344.6	342.6
75°	287.6	286.1	284.5	283.0	281.4	279.8	278.3	276.8	275.2	273.7	272.5
77.5°	215.3	214.6	213.9	213.3	212.6	211.6	210.2	208.8	207.4	206.1	205.7
80°	171.8	170.8	169.9	169.0	168.0	167.2	166.6	166.0	165.4	164.7	164.1
82.5°	129.3	128.9	128.5	127.9	127.5	127.2	127.1	127.0	126.9	126.7	126.4
85°	75.4	75.4	75.4	75.4	75.4	75.1	74.4	73.8	73.2	72.6	72.6
87.5°	29.8	30.2	30.6	31.0	31.4	31.7	31.9	32.1	32.3	32.6	32.9
90°	3.9	7.2	10.3	13.5	16.8	19.5	21.8	24.1	26.5	28.8	30.6
92.5°	28.1	31.7	35.3	39.0	42.7	45.3	47.0	48.6	50.2	51.9	52.9
95°	78.6	81.2	83.8	86.4	89.1	91.4	93.4	95.4	97.5	99.6	100.4
97.5°	137.2	139.4	141.5	143.5	145.6	147.8	150.3	152.7	155.0	157.4	158.4
100°	183.4	184.5	185.7	186.8	188.0	189.9	192.5	195.1	197.7	200.4	201.0
102.5°	231.6	232.1	232.5	233.0	233.4	234.8	237.2	239.6	242.0	244.4	245.2
105°	305.2	305.5	305.8	306.0	306.3	307.0	308.2	309.4	310.5	311.7	312.6
107.5°	382.4	382.7	383.1	383.4	383.8	384.1	384.3	384.5	384.7	384.8	385.6
110°	434.8	435.4	436.0	436.6	437.2	437.3	437.0	436.7	436.5	436.2	435.6



TEST NUMBER: P332828-840

CATALOG NUMBER: S124DIW-S1020D1340U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	489.3	489.4	489.5	489.7	489.8	489.6	489.1	488.5	488.0	487.5	487.4
115°	571.0	571.0	571.0	571.0	571.0	570.8	570.2	569.6	569.0	568.4	568.2
117.5°	648.0	648.2	648.5	648.7	648.9	648.8	648.4	648.0	647.6	647.2	646.2
120°	699.3	700.5	701.7	702.9	704.0	704.2	703.3	702.5	701.6	700.6	699.2
122.5°	752.8	753.3	753.8	754.2	754.7	754.7	754.3	753.9	753.5	753.1	752.0
125°	831.6	831.6	831.6	831.6	831.6	831.5	831.2	830.9	830.6	830.3	829.7
127.5°	903.1	904.0	904.9	905.7	906.7	906.9	906.4	905.9	905.4	904.9	904.4
130°	953.4	954.3	955.2	956.0	956.9	957.4	957.4	957.4	957.4	957.4	956.7
132.5°	1004.8	1005.4	1006.0	1006.7	1007.3	1007.5	1007.3	1007.0	1006.8	1006.6	1006.0
135°	1072.6	1074.4	1076.1	1077.8	1079.6	1080.5	1080.5	1080.5	1080.5	1080.5	1079.9
137.5°	1146.5	1147.3	1148.1	1148.9	1149.7	1150.4	1150.8	1151.3	1151.8	1152.3	1151.4
140°	1195.8	1196.3	1196.9	1197.5	1198.1	1198.3	1198.3	1198.3	1198.3	1198.3	1198.1
142.5°	1240.8	1241.3	1241.9	1242.5	1243.1	1243.2	1243.0	1242.8	1242.6	1242.3	1242.3
145°	1303.1	1304.3	1305.5	1306.7	1307.8	1308.5	1308.8	1309.1	1309.4	1309.7	1309.4
147.5°	1364.9	1366.3	1367.8	1369.2	1370.5	1371.1	1370.9	1370.7	1370.4	1370.2	1370.0
150°	1402.7	1403.8	1405.0	1406.1	1407.3	1407.9	1407.9	1407.9	1407.9	1407.9	1407.9
152.5°	1438.2	1439.0	1439.7	1440.4	1441.1	1441.6	1441.8	1442.0	1442.3	1442.5	1443.2
155°	1493.0	1493.0	1493.0	1493.0	1493.0	1492.9	1492.6	1492.3	1492.0	1491.8	1492.9
157.5°	1539.1	1538.6	1538.1	1537.5	1537.0	1536.7	1536.7	1536.6	1536.6	1536.5	1537.4
160°	1566.4	1566.1	1565.8	1565.5	1565.2	1564.9	1564.6	1564.4	1564.1	1563.8	1564.6
162.5°	1591.5	1590.7	1590.0	1589.2	1588.5	1588.0	1587.7	1587.4	1587.1	1586.8	1588.4
165°	1625.3	1624.5	1623.6	1622.7	1621.8	1621.1	1620.5	1619.9	1619.3	1618.7	1620.5
167.5°	1651.2	1650.0	1648.8	1647.6	1646.4	1645.8	1645.9	1645.9	1646.0	1646.0	1647.8
170°	1665.9	1664.5	1663.0	1661.5	1660.1	1659.5	1659.8	1660.1	1660.4	1660.6	1662.4
172.5°	1676.4	1675.2	1674.0	1672.7	1671.5	1670.9	1671.0	1671.0	1671.1	1671.1	1673.1
175°	1690.8	1689.3	1687.9	1686.5	1685.0	1684.1	1683.8	1683.5	1683.2	1682.9	1685.0
177.5°	1695.5	1694.4	1693.1	1692.0	1690.8	1690.3	1690.3	1690.3	1690.3	1690.3	1691.9
180°	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4



TEST NUMBER: P332828-840

CATALOG NUMBER: S124DIW-S1020D1340U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5
2.5°	1736.3	1738.8	1741.3	1742.4	1742.1	1741.9	1741.6	1741.4
5°	1727.0	1730.4	1733.8	1735.3	1734.6	1733.9	1733.3	1732.7
7.5°	1707.8	1710.5	1713.2	1714.4	1714.0	1713.6	1713.2	1712.9
10°	1691.6	1694.1	1696.6	1697.5	1696.9	1696.3	1695.7	1695.1
12.5°	1672.0	1674.8	1677.5	1678.4	1677.6	1676.7	1675.8	1675.0
15°	1634.6	1636.4	1638.3	1638.7	1637.8	1636.9	1636.0	1635.0
17.5°	1591.9	1593.1	1594.2	1594.5	1593.9	1593.3	1592.7	1592.0
20°	1560.0	1561.0	1562.0	1562.1	1561.5	1560.8	1560.2	1559.6
22.5°	1526.9	1528.6	1530.2	1530.6	1529.4	1528.3	1527.2	1526.1
25°	1472.3	1472.6	1472.9	1472.4	1471.2	1470.0	1468.6	1467.4
27.5°	1411.0	1410.2	1409.5	1408.4	1406.7	1405.2	1403.6	1402.1
30°	1368.7	1367.4	1366.1	1364.7	1363.2	1361.6	1360.1	1358.6
32.5°	1325.6	1324.2	1322.7	1321.2	1319.6	1318.1	1316.6	1314.9
35°	1257.9	1255.7	1253.5	1251.6	1250.1	1248.6	1247.0	1245.5
37.5°	1186.8	1184.5	1182.1	1179.9	1177.9	1175.8	1173.8	1171.7
40°	1137.3	1134.2	1131.1	1128.8	1127.2	1125.7	1124.2	1122.6
42.5°	1089.4	1085.8	1082.2	1079.8	1078.8	1077.7	1076.7	1075.7
45°	1015.2	1011.8	1008.4	1006.2	1005.3	1004.4	1003.4	1002.5
47.5°	943.4	939.6	935.7	932.6	930.3	927.9	925.5	923.2
50°	893.3	889.0	884.6	881.5	879.6	877.8	876.0	874.0
52.5°	841.8	837.9	834.0	831.0	828.6	826.3	823.9	821.5
55°	766.1	762.3	758.6	755.9	754.0	752.1	750.2	748.4
57.5°	690.2	686.7	683.2	680.4	678.6	676.9	675.1	673.3
60°	638.1	635.3	632.5	630.4	628.7	627.2	625.7	624.1
62.5°	587.2	584.6	582.1	580.1	578.6	576.9	575.4	573.9
65°	513.2	510.1	507.0	504.6	503.1	501.6	500.0	498.5
67.5°	437.0	433.9	431.0	429.3	428.8	428.4	428.0	427.6
70°	388.8	386.3	383.8	382.1	381.2	380.2	379.3	378.4
72.5°	340.6	338.6	336.7	335.2	334.3	333.4	332.4	331.4
75°	271.1	269.9	268.7	267.9	267.6	267.3	267.0	266.7
77.5°	205.3	205.0	204.6	204.0	203.2	202.4	201.6	200.8
80°	163.5	162.9	162.3	161.8	161.5	161.2	160.9	160.6
82.5°	126.0	125.6	125.3	124.9	124.6	124.3	124.0	123.7
85°	72.6	72.6	72.6	72.4	72.1	71.8	71.5	71.2
87.5°	33.2	33.6	33.9	34.2	34.3	34.4	34.5	34.6
90°	32.3	34.0	35.7	37.0	37.6	38.2	38.7	39.3
92.5°	53.9	55.0	56.0	56.8	57.1	57.5	57.8	58.2
95°	101.3	102.2	103.0	103.5	103.5	103.5	103.5	103.5
97.5°	159.6	160.6	161.6	162.2	162.2	162.2	162.2	162.2
100°	201.6	202.2	202.7	203.0	203.0	203.0	203.0	203.0
102.5°	246.0	246.8	247.6	248.1	248.4	248.6	248.8	249.1
105°	313.5	314.4	315.2	316.1	316.9	317.8	318.7	319.5
107.5°	386.4	387.2	388.1	388.4	388.4	388.3	388.3	388.2
110°	434.9	434.3	433.8	433.9	434.8	435.7	436.6	437.5



TEST NUMBER: P332828-840

CATALOG NUMBER: S124DIW-S1020D1340U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	487.3	487.2	487.0	487.1	487.2	487.4	487.6	487.8
115°	567.8	567.5	567.2	566.9	566.6	566.3	566.0	565.8
117.5°	645.3	644.3	643.3	642.5	641.9	641.4	640.8	640.2
120°	697.8	696.3	694.9	694.4	695.0	695.6	696.2	696.7
122.5°	751.0	750.1	749.1	748.1	747.0	746.0	745.0	743.9
125°	829.2	828.6	828.0	827.4	826.9	826.3	825.7	825.1
127.5°	903.8	903.2	902.6	902.1	901.7	901.2	900.7	900.3
130°	956.2	955.6	955.0	954.2	953.0	951.8	950.7	949.5
132.5°	1005.4	1004.9	1004.3	1003.8	1003.3	1002.8	1002.4	1001.9
135°	1079.3	1078.7	1078.1	1077.4	1076.5	1075.7	1074.8	1073.9
137.5°	1150.7	1150.0	1149.2	1148.9	1149.1	1149.3	1149.4	1149.6
140°	1197.8	1197.5	1197.2	1196.9	1196.6	1196.3	1196.0	1195.8
142.5°	1242.2	1242.2	1242.1	1242.0	1242.0	1241.9	1241.9	1241.8
145°	1309.1	1308.8	1308.5	1308.0	1307.1	1306.2	1305.4	1304.4
147.5°	1369.7	1369.5	1369.3	1369.0	1368.7	1368.4	1368.2	1367.9
150°	1407.9	1407.9	1407.9	1407.8	1407.4	1407.1	1406.8	1406.6
152.5°	1443.9	1444.6	1445.3	1445.2	1444.5	1443.7	1443.0	1442.2
155°	1494.1	1495.2	1496.4	1496.4	1495.2	1494.1	1492.9	1491.8
157.5°	1538.2	1539.1	1540.0	1539.9	1538.9	1537.9	1537.0	1536.0
160°	1565.5	1566.4	1567.2	1566.9	1565.5	1564.1	1562.6	1561.2
162.5°	1589.9	1591.5	1593.1	1593.2	1591.6	1590.2	1588.8	1587.3
165°	1622.2	1624.0	1625.8	1626.1	1624.9	1623.7	1622.6	1621.3
167.5°	1649.5	1651.2	1652.9	1652.9	1651.1	1649.3	1647.6	1645.8
170°	1664.2	1665.9	1667.7	1667.5	1665.5	1663.4	1661.4	1659.4
172.5°	1675.1	1677.1	1679.1	1679.0	1677.0	1675.0	1672.9	1670.9
175°	1687.0	1689.0	1691.1	1691.1	1689.0	1687.0	1685.0	1682.9
177.5°	1693.5	1695.2	1696.8	1696.7	1694.9	1692.9	1691.1	1689.2
180°	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4

(END OF REPORT)