

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332829-840

Luminaire Tested: **S124DIW-S1020D1560U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332829-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1020D1560U840-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10954.0 lumens
Efficiency: N/A
Efficacy: 143.0 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332829-840

CATALOG NUMBER: S124DIW-S1020D1560U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332829-840

CATALOG NUMBER: S124DIW-S1020D1560U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49	43					43			
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42	36					36			
2	88	81	75	70	80	74	69	64	61	58	54	50	47	45	39	37	36	31					31			
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	34	32	30	26					26			
4	73	63	55	49	67	58	51	46	48	43	39	39	36	33	31	28	26	23					23			
5	67	56	48	42	61	52	45	39	43	38	34	35	31	28	28	25	23	20					20			
6	62	50	42	37	57	46	39	34	39	34	30	32	28	25	25	23	20	17					17			
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15					15			
8	53	41	34	28	49	38	31	27	32	27	23	27	23	20	21	18	16	14					14			
9	50	38	30	25	45	35	28	24	29	24	21	24	21	18	20	17	15	13					13			
10	46	34	27	23	42	32	26	21	27	22	19	23	19	16	18	15	13	11					11			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13605	13605	13605	13605
5°	16022	13639	12039	13639
10°	19184	13581	10839	13581
15°	22697	13443	9954	13443
20°	25274	13302	9164	13302
25°	25683	13097	8620	13097
30°	21853	12899	8447	12899
35°	16802	12577	8449	12577
40°	13095	12198	8608	12198
45°	10919	11628	8752	11628
50°	9610	10934	9048	10934
55°	8804	10101	9413	10101
60°	8251	9357	9852	9357
65°	7681	8521	10214	8521
70°	7020	7695	10447	7695
75°	6273	6772	10321	6772
80°	5258	5551	9995	5551
85°	3881	4011	9568	4011



TEST NUMBER: P332829-840

CATALOG NUMBER: S124DIW-S1020D1560U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.2	1.5
10°-20°	506.1	4.6
20°-30°	802.5	7.3
30°-40°	893.1	8.2
40°-50°	812.9	7.4
50°-60°	664.3	6.1
60°-70°	474.2	4.3
70°-80°	261.1	2.4
80°-90°	77.2	0.7
90°-100°	69.6	0.6
100°-110°	444.0	4.1
110°-120°	849.4	7.8
120°-130°	1078.3	9.8
130°-140°	1153.7	10.5
140°-150°	1078.8	9.8
150°-160°	870.0	7.9
160°-170°	561.1	5.1
170°-180°	193.4	1.8
0°-30°	1472.7	13.4
0°-40°	2365.8	21.6
0°-60°	3843.0	35.1
0°-90°	4655.6	42.5
90°-120°	1363.1	12.4
90°-150°	4673.9	42.7
90°-180°	6298.0	57.5
0°-180°	10954.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1685	1685	1685	1685	1685	
5°	1977	1683	1486	1683	1977	201
15°	2716	1608	1191	1608	2716	767
25°	2883	1470	968	1470	2883	1271
35°	1705	1276	857	1276	1705	1082
45°	956	1018	767	1018	956	753
55°	626	718	669	718	626	565
65°	402	446	535	446	402	398
75°	201	217	331	217	201	214
85°	42	43	103	43	42	52
90°	46	4	46	4	46	21
95°	44	84	44	84	44	35
105°	434	458	434	458	434	379
115°	862	856	862	856	862	853
125°	1212	1203	1212	1203	1212	1080
135°	1503	1492	1503	1492	1503	1157
145°	1730	1721	1730	1721	1730	1081
155°	1885	1887	1885	1887	1885	869
165°	1981	1990	1981	1990	1981	560
175°	2024	2036	2024	2036	2024	193
180°	2036	2036	2036	2036	2036	



TEST NUMBER: P332829-840

CATALOG NUMBER: S124DIW-S1020D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3
2.5°	1793.6	1793.1	1787.5	1786.4	1782.4	1777.5	1776.4	1767.4	1749.5	1741.1	1738.9
5°	1977.1	1991.0	1972.9	1969.4	1967.3	1944.3	1932.4	1918.4	1886.3	1867.4	1852.8
7.5°	2196.1	2197.7	2189.8	2183.3	2165.6	2145.5	2115.4	2083.3	2045.0	2005.2	1975.1
10°	2340.2	2345.7	2336.6	2335.2	2299.7	2277.2	2232.6	2194.9	2151.6	2103.4	2059.5
12.5°	2492.0	2484.2	2479.6	2449.7	2443.2	2402.4	2350.5	2311.7	2244.9	2189.5	2130.9
15°	2715.7	2700.4	2690.6	2649.4	2629.2	2572.6	2517.4	2474.9	2387.6	2304.5	2241.7
17.5°	2846.9	2862.4	2839.7	2822.8	2770.5	2730.8	2674.4	2585.1	2516.8	2413.6	2334.3
20°	2941.9	2943.3	2930.7	2913.3	2872.1	2821.9	2760.4	2662.6	2581.0	2478.3	2369.4
22.5°	2967.6	2967.9	2962.5	2946.2	2915.1	2874.3	2812.4	2730.8	2631.8	2520.2	2411.4
25°	2883.3	2880.4	2886.8	2904.9	2893.1	2880.4	2844.9	2784.1	2692.0	2573.9	2456.7
27.5°	2569.9	2589.2	2624.6	2669.4	2712.4	2745.2	2754.4	2742.0	2684.8	2587.8	2465.0
30°	2344.3	2368.0	2394.6	2439.2	2525.8	2575.4	2629.9	2671.0	2648.0	2570.5	2456.0
32.5°	2096.4	2102.2	2141.6	2192.4	2271.7	2367.0	2453.4	2537.0	2564.8	2524.2	2428.6
35°	1704.9	1714.5	1757.2	1807.5	1904.5	2021.0	2150.9	2266.8	2362.5	2400.9	2352.0
37.5°	1391.2	1419.3	1449.4	1503.4	1588.8	1693.7	1828.7	1978.6	2121.2	2216.7	2232.9
40°	1242.6	1260.1	1281.7	1322.9	1395.5	1498.8	1614.8	1786.6	1938.0	2074.9	2119.5
42.5°	1125.4	1135.6	1148.8	1186.1	1241.4	1344.1	1450.0	1601.0	1753.1	1916.7	1991.7
45°	956.4	966.9	989.3	1010.9	1052.8	1124.0	1222.4	1346.7	1499.5	1657.4	1795.5
47.5°	834.4	841.1	854.3	877.6	913.1	960.1	1040.2	1144.0	1285.7	1438.9	1586.1
50°	765.2	770.7	781.2	802.1	829.4	871.2	936.9	1033.9	1144.9	1299.2	1443.7
52.5°	710.4	712.7	720.3	734.6	756.2	791.4	845.3	925.5	1028.7	1166.3	1310.2
55°	625.5	628.3	635.3	645.8	664.6	686.9	728.1	788.2	878.3	997.6	1122.6
57.5°	555.7	557.6	563.5	567.5	583.1	601.3	632.9	675.8	744.1	845.3	956.8
60°	511.0	509.7	516.6	520.1	530.6	545.9	570.4	611.6	670.9	752.6	855.2
62.5°	467.5	465.5	471.4	475.9	482.0	495.1	515.0	547.3	595.5	669.3	758.0
65°	402.1	399.3	402.8	408.4	413.9	421.0	435.7	464.2	502.6	555.7	623.4
67.5°	336.5	339.4	340.0	342.7	346.0	355.5	365.6	385.8	412.8	455.3	512.7
70°	297.4	298.1	300.9	300.9	303.0	311.3	319.7	331.6	358.1	397.3	444.0
72.5°	258.3	261.3	260.1	262.4	263.9	269.4	275.6	286.9	309.5	338.6	378.1
75°	201.1	203.2	203.2	203.9	205.9	208.0	212.9	221.3	237.3	259.0	286.2
77.5°	146.6	146.9	147.8	150.4	150.4	153.7	157.3	164.1	172.0	186.8	203.4
80°	113.1	114.5	113.8	115.2	115.2	118.0	119.4	127.7	131.3	141.0	154.3
82.5°	82.9	84.3	84.2	86.1	87.3	87.9	89.8	93.1	96.6	105.2	110.7
85°	41.9	43.3	41.9	43.3	45.3	46.0	48.2	48.9	51.7	53.7	58.7
87.5°	21.4	22.9	22.8	23.2	24.2	24.5	24.6	23.7	25.5	25.7	27.4
90°	45.6	45.0	44.3	43.6	43.0	41.6	39.6	37.6	35.5	33.5	30.8
92.5°	42.0	41.9	41.8	41.6	41.5	40.4	38.4	36.4	34.3	32.3	29.6
95°	44.1	43.8	43.5	43.1	42.8	41.6	39.6	37.6	35.5	33.5	33.1
97.5°	42.6	42.3	42.0	41.6	41.3	41.0	40.8	40.6	40.4	40.2	78.0
100°	42.6	42.3	42.0	41.6	41.3	44.0	49.8	55.5	61.3	67.1	113.7
102.5°	43.8	43.8	43.7	43.6	43.6	74.6	136.6	198.7	260.7	322.9	328.9
105°	434.0	446.3	458.4	470.6	482.7	487.4	484.3	481.2	478.2	475.1	473.4
107.5°	604.9	603.6	602.3	601.1	599.8	598.3	596.9	595.4	593.9	592.4	590.1
110°	679.2	678.2	677.2	676.2	675.2	674.3	673.7	673.0	672.3	671.6	669.5



TEST NUMBER: P332829-840

CATALOG NUMBER: S124DIW-S1020D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	753.6	752.2	750.9	749.7	748.4	747.8	747.9	748.1	748.2	748.4	747.4
115°	862.0	862.0	862.0	862.0	862.0	861.6	860.9	860.3	859.6	858.9	859.3
117.5°	972.2	972.4	972.5	972.6	972.8	972.9	973.0	973.2	973.3	973.4	972.7
120°	1041.7	1042.4	1043.0	1043.7	1044.4	1044.4	1043.7	1043.0	1042.4	1041.7	1042.0
122.5°	1109.9	1110.5	1111.3	1112.0	1112.6	1112.8	1112.4	1112.0	1111.6	1111.2	1110.6
125°	1212.2	1211.9	1211.5	1211.2	1210.9	1210.2	1209.2	1208.2	1207.2	1206.2	1206.8
127.5°	1302.1	1302.3	1302.6	1302.9	1303.1	1303.4	1303.6	1303.8	1304.0	1304.2	1302.6
130°	1363.0	1363.0	1363.0	1363.0	1363.0	1362.8	1362.5	1362.2	1361.8	1361.5	1360.5
132.5°	1419.1	1419.4	1419.6	1419.9	1420.2	1420.1	1419.8	1419.5	1419.1	1418.8	1417.4
135°	1503.1	1502.5	1501.8	1501.1	1500.5	1499.8	1499.0	1498.3	1497.7	1497.0	1495.7
137.5°	1575.0	1575.2	1575.4	1575.6	1575.8	1575.6	1574.8	1574.1	1573.3	1572.6	1571.0
140°	1625.0	1624.6	1624.3	1624.0	1623.6	1623.0	1621.9	1620.9	1619.9	1618.8	1618.2
142.5°	1666.4	1666.3	1666.3	1666.2	1666.1	1665.7	1665.0	1664.3	1663.4	1662.7	1662.3
145°	1730.0	1729.4	1728.7	1728.0	1727.4	1726.8	1726.5	1726.2	1725.8	1725.5	1725.5
147.5°	1782.7	1782.4	1782.0	1781.7	1781.4	1781.1	1780.8	1780.5	1780.3	1780.0	1780.3
150°	1816.8	1816.5	1816.1	1815.8	1815.5	1815.3	1815.3	1815.3	1815.3	1815.3	1815.6
152.5°	1846.0	1846.2	1846.4	1846.6	1846.8	1846.7	1846.1	1845.6	1845.1	1844.5	1845.1
155°	1885.4	1886.4	1887.4	1888.4	1889.5	1889.3	1887.9	1886.5	1885.2	1883.8	1884.9
157.5°	1918.2	1920.1	1921.8	1923.6	1925.3	1925.3	1923.6	1921.8	1920.1	1918.2	1919.5
160°	1940.2	1942.3	1944.3	1946.3	1948.3	1948.3	1946.3	1944.3	1942.3	1940.2	1940.6
162.5°	1957.2	1959.5	1961.9	1964.2	1966.4	1966.6	1964.6	1962.6	1960.5	1958.4	1958.8
165°	1981.4	1984.4	1987.4	1990.4	1993.5	1993.7	1990.9	1988.2	1985.5	1982.9	1982.9
167.5°	1999.3	2002.7	2006.1	2009.4	2012.9	2013.1	2010.0	2007.1	2004.1	2001.1	2001.4
170°	2010.2	2013.7	2017.0	2020.4	2023.8	2024.2	2021.4	2018.7	2016.0	2013.3	2013.0
172.5°	2016.3	2020.0	2023.7	2027.3	2030.9	2031.4	2028.7	2026.0	2023.3	2020.6	2020.2
175°	2024.0	2028.0	2032.1	2036.1	2040.2	2040.7	2037.7	2034.6	2031.5	2028.5	2028.2
177.5°	2028.8	2032.1	2035.3	2038.6	2041.8	2042.4	2040.2	2038.0	2035.9	2033.7	2033.2
180°	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1



TEST NUMBER: P332829-840

CATALOG NUMBER: S124DIW-S1020D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3
2.5°	1739.5	1731.6	1726.1	1721.6	1709.3	1702.0	1696.5	1688.6	1679.7	1670.2	1658.5
5°	1838.2	1814.4	1797.0	1770.5	1745.3	1724.3	1702.7	1683.1	1659.4	1633.7	1614.8
7.5°	1941.9	1906.6	1861.4	1822.1	1778.0	1739.6	1705.3	1670.0	1633.5	1598.0	1565.5
10°	2007.8	1962.5	1912.2	1852.8	1797.0	1747.4	1701.3	1656.7	1613.4	1570.0	1533.1
12.5°	2078.7	2022.2	1947.9	1878.6	1815.9	1749.7	1694.0	1639.3	1587.1	1541.6	1498.4
15°	2173.9	2092.2	2006.4	1913.6	1831.2	1753.7	1677.6	1608.5	1549.8	1489.8	1447.9
17.5°	2232.5	2131.4	2033.3	1936.2	1836.4	1738.8	1656.7	1576.9	1503.5	1443.9	1391.1
20°	2271.0	2170.5	2048.3	1951.3	1832.6	1732.0	1637.1	1548.4	1471.7	1408.2	1353.6
22.5°	2304.5	2188.4	2066.2	1938.4	1820.3	1713.6	1609.7	1520.6	1442.1	1375.1	1322.9
25°	2322.7	2189.3	2056.7	1929.7	1795.5	1669.2	1575.0	1470.3	1386.4	1316.0	1260.1
27.5°	2324.6	2182.0	2031.9	1890.8	1752.4	1634.8	1515.8	1422.2	1335.2	1260.7	1207.1
30°	2318.4	2169.8	2008.5	1855.6	1716.7	1588.9	1485.6	1383.7	1295.1	1221.0	1165.2
32.5°	2299.0	2144.0	1978.3	1816.5	1672.5	1547.6	1441.0	1344.0	1257.6	1184.7	1126.1
35°	2242.4	2089.5	1912.9	1744.6	1597.3	1471.0	1374.6	1276.2	1189.6	1120.4	1064.0
37.5°	2154.0	2015.8	1836.2	1662.1	1517.4	1390.5	1295.1	1206.1	1128.0	1057.8	999.9
40°	2076.9	1955.4	1775.3	1605.7	1449.4	1328.6	1239.2	1157.5	1080.1	1013.7	958.6
42.5°	1988.1	1882.3	1716.2	1536.4	1385.6	1264.4	1177.2	1103.9	1030.9	969.6	914.4
45°	1829.8	1760.0	1603.6	1437.4	1280.4	1165.9	1082.8	1018.5	957.2	897.1	851.0
47.5°	1647.7	1613.1	1481.5	1323.6	1174.6	1061.7	989.7	930.3	876.5	825.6	785.0
50°	1525.4	1508.6	1394.8	1242.6	1100.2	994.1	921.5	870.6	824.5	779.8	741.4
52.5°	1404.7	1404.2	1301.6	1162.3	1030.5	928.3	856.2	808.6	768.6	732.4	697.8
55°	1220.3	1239.9	1159.6	1035.3	917.4	825.2	760.2	717.7	689.7	659.7	633.9
57.5°	1051.0	1083.4	1017.1	907.7	809.3	724.4	667.8	635.8	606.1	587.9	569.2
60°	940.4	971.1	919.5	827.3	734.5	661.9	608.0	579.5	553.6	541.1	527.8
62.5°	842.1	869.5	831.2	745.8	665.2	595.3	550.0	522.5	505.0	491.3	482.5
65°	701.7	724.7	691.9	629.8	560.6	504.7	467.8	446.1	429.4	423.7	413.9
67.5°	567.1	588.1	570.4	517.6	462.1	419.9	390.9	370.1	360.2	355.4	348.4
70°	487.3	508.3	489.4	443.3	400.7	365.2	337.9	326.0	315.6	313.5	303.7
72.5°	419.7	433.9	415.2	379.1	342.6	312.7	291.5	279.1	273.7	269.9	264.6
75°	314.9	327.4	314.9	286.9	261.1	240.1	222.0	217.1	210.9	208.7	205.2
77.5°	222.9	233.7	224.1	206.6	187.3	171.2	161.4	155.1	153.7	150.1	151.8
80°	170.4	177.3	168.2	156.4	141.0	129.9	122.9	119.4	115.2	113.8	116.5
82.5°	122.3	125.4	120.8	112.8	101.4	94.1	89.4	85.3	84.4	84.7	84.7
85°	63.5	62.8	62.1	55.1	51.7	46.8	44.0	43.3	42.6	44.0	45.3
87.5°	26.9	26.9	25.8	22.9	20.5	18.1	16.8	15.5	16.8	18.1	19.4
90°	28.1	25.3	22.7	19.5	15.8	12.0	8.3	4.5	8.3	12.0	15.8
92.5°	26.9	24.1	21.4	20.0	19.8	19.6	19.4	19.2	19.4	19.6	19.8
95°	32.8	32.5	32.1	37.8	49.3	60.8	72.2	83.7	72.2	60.8	49.3
97.5°	115.7	153.5	191.3	206.6	199.4	192.2	185.0	177.8	185.0	192.2	199.4
100°	160.4	207.1	253.8	274.1	268.0	262.0	255.9	249.7	255.9	262.0	268.0
102.5°	335.1	341.1	347.2	348.0	343.6	339.1	334.7	330.1	334.7	339.1	343.6
105°	471.8	470.1	468.4	466.6	464.5	462.4	460.4	458.4	460.4	462.4	464.5
107.5°	587.8	585.5	583.2	581.6	580.6	579.6	578.6	577.4	578.6	579.6	580.6
110°	667.5	665.5	663.5	662.0	661.0	659.9	658.9	657.9	658.9	659.9	661.0



TEST NUMBER: P332829-840

CATALOG NUMBER: S124DIW-S1020D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	746.5	745.5	744.6	743.2	741.3	739.5	737.7	735.9	737.7	739.5	741.3
115°	859.6	859.9	860.3	859.9	858.9	857.9	856.9	855.9	856.9	857.9	858.9
117.5°	972.0	971.2	970.5	969.5	968.1	966.7	965.3	964.0	965.3	966.7	968.1
120°	1042.4	1042.7	1043.0	1042.5	1041.2	1039.9	1038.4	1037.1	1038.4	1039.9	1041.2
122.5°	1110.1	1109.7	1109.2	1108.6	1107.7	1106.9	1106.1	1105.3	1106.1	1106.9	1107.7
125°	1207.5	1208.2	1208.8	1208.5	1207.2	1205.8	1204.5	1203.2	1204.5	1205.8	1207.2
127.5°	1301.1	1299.6	1298.0	1297.1	1296.7	1296.4	1296.1	1295.7	1296.1	1296.4	1296.7
130°	1359.5	1358.5	1357.5	1356.8	1356.5	1356.0	1355.7	1355.4	1355.7	1356.0	1356.5
132.5°	1416.1	1414.9	1413.6	1412.7	1412.1	1411.5	1410.8	1410.2	1410.8	1411.5	1412.1
135°	1494.3	1493.0	1491.6	1491.1	1491.5	1491.8	1492.1	1492.5	1492.1	1491.8	1491.5
137.5°	1569.6	1568.1	1566.6	1565.8	1565.7	1565.5	1565.4	1565.3	1565.4	1565.5	1565.7
140°	1617.5	1616.8	1616.2	1615.5	1614.8	1614.2	1613.5	1612.8	1613.5	1614.2	1614.8
142.5°	1661.9	1661.5	1661.1	1660.3	1659.1	1657.9	1656.6	1655.4	1656.6	1657.9	1659.1
145°	1725.5	1725.5	1725.5	1725.0	1723.9	1722.9	1721.9	1720.9	1721.9	1722.9	1723.9
147.5°	1780.7	1781.0	1781.3	1780.6	1778.7	1776.8	1774.8	1773.0	1774.8	1776.8	1778.7
150°	1816.0	1816.3	1816.6	1816.1	1814.8	1813.4	1812.1	1810.8	1812.1	1813.4	1814.8
152.5°	1845.7	1846.3	1847.0	1846.7	1845.6	1844.6	1843.5	1842.4	1843.5	1844.6	1845.6
155°	1885.9	1886.9	1887.9	1888.2	1887.9	1887.5	1887.2	1886.9	1887.2	1887.5	1887.9
157.5°	1920.6	1921.7	1922.9	1923.6	1923.8	1924.0	1924.2	1924.4	1924.2	1924.0	1923.8
160°	1940.9	1941.2	1941.6	1942.3	1943.3	1944.3	1945.3	1946.3	1945.3	1944.3	1943.3
162.5°	1959.1	1959.4	1959.8	1960.7	1962.0	1963.2	1964.5	1965.8	1964.5	1963.2	1962.0
165°	1982.9	1982.9	1982.9	1983.7	1985.4	1987.1	1988.7	1990.4	1988.7	1987.1	1985.4
167.5°	2001.6	2001.8	2002.0	2002.9	2004.7	2006.4	2008.2	2009.9	2008.2	2006.4	2004.7
170°	2012.7	2012.3	2012.0	2012.8	2014.8	2016.8	2018.9	2020.9	2018.9	2016.8	2014.8
172.5°	2019.9	2019.6	2019.2	2020.1	2022.2	2024.2	2026.2	2028.2	2026.2	2024.2	2022.2
175°	2027.8	2027.5	2027.2	2028.0	2030.0	2032.1	2034.1	2036.1	2034.1	2032.1	2030.0
177.5°	2032.7	2032.1	2031.5	2032.3	2034.1	2036.0	2037.9	2039.8	2037.9	2036.0	2034.1
180°	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1



TEST NUMBER: P332829-840

CATALOG NUMBER: S124DIW-S1020D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3
2.5°	1652.8	1647.9	1640.6	1630.5	1622.1	1613.3	1611.0	1607.6	1614.4	1608.7	1607.1
5°	1598.7	1584.1	1565.2	1543.6	1531.0	1512.9	1509.3	1502.4	1495.4	1494.7	1487.7
7.5°	1541.4	1519.8	1495.1	1473.1	1452.7	1432.8	1419.9	1417.0	1406.7	1400.7	1393.7
10°	1504.5	1477.9	1449.4	1428.4	1404.6	1383.7	1369.1	1360.7	1353.6	1345.9	1339.0
12.5°	1460.9	1432.7	1409.1	1386.4	1358.3	1342.3	1318.2	1303.6	1302.3	1302.4	1284.2
15°	1410.2	1382.3	1345.9	1313.8	1298.5	1267.8	1254.6	1237.8	1227.3	1216.8	1208.5
17.5°	1352.3	1317.5	1289.2	1252.3	1222.9	1198.5	1181.1	1171.0	1155.3	1140.4	1129.7
20°	1316.0	1279.0	1248.9	1209.8	1177.7	1147.7	1133.1	1119.1	1107.2	1094.7	1082.8
22.5°	1279.1	1240.4	1203.7	1165.7	1135.9	1104.2	1090.0	1071.1	1059.8	1052.8	1040.9
25°	1221.0	1179.1	1137.2	1101.0	1070.3	1042.3	1023.5	1008.8	996.2	990.7	983.0
27.5°	1157.9	1116.3	1075.8	1034.6	999.8	979.5	964.4	953.3	946.1	938.7	935.2
30°	1117.7	1074.4	1031.2	992.7	960.6	940.4	926.5	918.8	913.1	909.7	906.2
32.5°	1076.9	1034.2	988.7	953.6	924.8	906.9	896.3	888.6	885.8	884.5	883.2
35°	1011.6	968.3	926.5	895.0	867.8	860.8	851.7	847.5	846.2	851.0	853.1
37.5°	948.4	908.2	869.6	839.1	821.3	811.1	808.0	808.2	813.1	817.5	822.5
40°	907.6	868.5	832.1	805.7	788.9	782.6	781.2	784.7	790.3	795.2	800.7
42.5°	867.9	829.4	796.4	771.5	759.8	754.1	755.0	758.4	766.3	772.2	780.6
45°	806.4	774.3	742.1	721.9	712.1	713.5	713.5	719.7	727.4	736.5	745.6
47.5°	748.4	716.0	689.6	672.6	667.5	666.3	670.2	678.4	689.4	700.6	713.4
50°	709.3	678.5	655.5	640.2	634.6	636.7	642.3	649.9	663.2	677.2	690.4
52.5°	669.6	641.7	620.4	606.1	602.2	606.0	611.6	623.7	635.3	650.4	666.4
55°	608.0	584.3	567.5	557.1	555.7	557.8	564.1	577.3	594.1	613.0	628.3
57.5°	546.7	526.9	511.6	504.3	505.0	507.0	517.4	533.1	551.0	571.1	590.9
60°	505.4	487.3	474.7	469.2	469.8	474.0	486.6	501.3	523.6	543.1	564.1
62.5°	466.4	450.4	438.4	433.4	432.4	441.6	453.6	468.9	491.2	513.0	535.6
65°	403.5	390.9	381.2	378.4	380.5	387.5	402.8	423.0	441.9	464.9	488.7
67.5°	342.0	331.7	325.1	326.3	328.8	339.1	352.0	369.4	390.8	414.7	438.2
70°	303.0	293.2	287.6	288.3	292.6	305.1	316.3	333.7	356.8	381.2	400.7
72.5°	262.8	256.3	251.4	254.3	258.4	267.1	281.0	298.5	318.8	341.5	362.1
75°	201.8	201.8	198.9	201.1	207.3	215.7	226.2	244.4	264.6	282.8	299.5
77.5°	149.7	148.1	150.0	152.5	156.1	166.0	178.0	191.0	206.2	224.4	238.2
80°	114.5	115.2	118.7	122.9	124.3	132.0	144.5	156.4	168.2	183.6	196.8
82.5°	86.0	86.7	88.6	93.8	95.2	103.5	111.6	123.4	134.2	144.5	155.5
85°	46.8	46.8	50.3	52.3	55.8	61.4	66.3	73.3	83.1	90.1	100.5
87.5°	21.8	22.4	25.1	26.9	29.1	32.4	33.9	40.5	43.1	46.4	51.6
90°	19.5	22.7	25.3	28.1	30.8	33.5	35.5	37.6	39.6	41.6	43.0
92.5°	20.0	21.4	24.1	26.9	29.6	32.3	34.3	36.4	38.4	40.4	41.5
95°	37.8	32.1	32.5	32.8	33.1	33.5	35.5	37.6	39.6	41.6	42.8
97.5°	206.6	191.3	153.5	115.7	78.0	40.2	40.4	40.6	40.8	41.0	41.3
100°	274.1	253.8	207.1	160.4	113.7	67.1	61.3	55.5	49.8	44.0	41.3
102.5°	348.0	347.2	341.1	335.1	328.9	322.9	260.7	198.7	136.6	74.6	43.6
105°	466.6	468.4	470.1	471.8	473.4	475.1	478.2	481.2	484.3	487.4	482.7
107.5°	581.6	583.2	585.5	587.8	590.1	592.4	593.9	595.4	596.9	598.3	599.8
110°	662.0	663.5	665.5	667.5	669.5	671.6	672.3	673.0	673.7	674.3	675.2



TEST NUMBER: P332829-840

CATALOG NUMBER: S124DIW-S1020D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	743.2	744.6	745.5	746.5	747.4	748.4	748.2	748.1	747.9	747.8	748.4
115°	859.9	860.3	859.9	859.6	859.3	858.9	859.6	860.3	860.9	861.6	862.0
117.5°	969.5	970.5	971.2	972.0	972.7	973.4	973.3	973.2	973.0	972.9	972.8
120°	1042.5	1043.0	1042.7	1042.4	1042.0	1041.7	1042.4	1043.0	1043.7	1044.4	1044.4
122.5°	1108.6	1109.2	1109.7	1110.1	1110.6	1111.2	1111.6	1112.0	1112.4	1112.8	1112.6
125°	1208.5	1208.8	1208.2	1207.5	1206.8	1206.2	1207.2	1208.2	1209.2	1210.2	1210.9
127.5°	1297.1	1298.0	1299.6	1301.1	1302.6	1304.2	1304.0	1303.8	1303.6	1303.4	1303.1
130°	1356.8	1357.5	1358.5	1359.5	1360.5	1361.5	1361.8	1362.2	1362.5	1362.8	1363.0
132.5°	1412.7	1413.6	1414.9	1416.1	1417.4	1418.8	1419.1	1419.5	1419.8	1420.1	1420.2
135°	1491.1	1491.6	1493.0	1494.3	1495.7	1497.0	1497.7	1498.3	1499.0	1499.8	1500.5
137.5°	1565.8	1566.6	1568.1	1569.6	1571.0	1572.6	1573.3	1574.1	1574.8	1575.6	1575.8
140°	1615.5	1616.2	1616.8	1617.5	1618.2	1618.8	1619.9	1620.9	1621.9	1623.0	1623.6
142.5°	1660.3	1661.1	1661.5	1661.9	1662.3	1662.7	1663.4	1664.3	1665.0	1665.7	1666.1
145°	1725.0	1725.5	1725.5	1725.5	1725.5	1725.5	1725.8	1726.2	1726.5	1726.8	1727.4
147.5°	1780.6	1781.3	1781.0	1780.7	1780.3	1780.0	1780.3	1780.5	1780.8	1781.1	1781.4
150°	1816.1	1816.6	1816.3	1816.0	1815.6	1815.3	1815.3	1815.3	1815.3	1815.3	1815.5
152.5°	1846.7	1847.0	1846.3	1845.7	1845.1	1844.5	1845.1	1845.6	1846.1	1846.7	1846.8
155°	1888.2	1887.9	1886.9	1885.9	1884.9	1883.8	1885.2	1886.5	1887.9	1889.3	1889.5
157.5°	1923.6	1922.9	1921.7	1920.6	1919.5	1918.2	1920.1	1921.8	1923.6	1925.3	1925.3
160°	1942.3	1941.6	1941.2	1940.9	1940.6	1940.2	1942.3	1944.3	1946.3	1948.3	1948.3
162.5°	1960.7	1959.8	1959.4	1959.1	1958.8	1958.4	1960.5	1962.6	1964.6	1966.6	1966.4
165°	1983.7	1982.9	1982.9	1982.9	1982.9	1982.9	1985.5	1988.2	1990.9	1993.7	1993.5
167.5°	2002.9	2002.0	2001.8	2001.6	2001.4	2001.1	2004.1	2007.1	2010.0	2013.1	2012.9
170°	2012.8	2012.0	2012.3	2012.7	2013.0	2013.3	2016.0	2018.7	2021.4	2024.2	2023.8
172.5°	2020.1	2019.2	2019.6	2019.9	2020.2	2020.6	2023.3	2026.0	2028.7	2031.4	2030.9
175°	2028.0	2027.2	2027.5	2027.8	2028.2	2028.5	2031.5	2034.6	2037.7	2040.7	2040.2
177.5°	2032.3	2031.5	2032.1	2032.7	2033.2	2033.7	2035.9	2038.0	2040.2	2042.4	2041.8
180°	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1



TEST NUMBER: P332829-840

CATALOG NUMBER: S124DIW-S1020D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3
2.5°	1606.0	1604.9	1600.9	1600.4	1600.9	1604.9	1606.0	1607.1	1608.7	1614.4	1607.6
5°	1483.5	1480.1	1477.9	1485.6	1477.9	1480.1	1483.5	1487.7	1494.7	1495.4	1502.4
7.5°	1391.2	1388.5	1382.3	1380.4	1382.3	1388.5	1391.2	1393.7	1400.7	1406.7	1417.0
10°	1332.0	1329.2	1323.6	1322.2	1323.6	1329.2	1332.0	1339.0	1345.9	1353.6	1360.7
12.5°	1275.1	1269.5	1268.4	1269.7	1268.4	1269.5	1275.1	1284.2	1302.4	1302.3	1303.6
15°	1199.4	1196.6	1188.9	1191.0	1188.9	1196.6	1199.4	1208.5	1216.8	1227.3	1237.8
17.5°	1124.8	1121.5	1112.2	1120.3	1112.2	1121.5	1124.8	1129.7	1140.4	1155.3	1171.0
20°	1077.9	1072.3	1067.4	1066.7	1067.4	1072.3	1077.9	1082.8	1094.7	1107.2	1119.1
22.5°	1033.2	1028.2	1027.7	1023.2	1027.7	1028.2	1033.2	1040.9	1052.8	1059.8	1071.1
25°	977.3	972.5	971.1	967.7	971.1	972.5	977.3	983.0	990.7	996.2	1008.8
27.5°	934.5	932.1	929.6	930.7	929.6	932.1	934.5	935.2	938.7	946.1	953.3
30°	908.3	907.6	906.2	906.2	906.2	907.6	908.3	906.2	909.7	913.1	918.8
32.5°	886.5	886.4	887.2	887.2	887.2	886.4	886.5	883.2	884.5	885.8	888.6
35°	855.9	858.0	859.4	857.3	859.4	858.0	855.9	853.1	851.0	846.2	847.5
37.5°	828.3	830.3	832.3	834.7	832.3	830.3	828.3	822.5	817.5	813.1	808.2
40°	807.0	811.9	813.3	816.8	813.3	811.9	807.0	800.7	795.2	790.3	784.7
42.5°	786.9	792.3	796.0	796.7	796.0	792.3	786.9	780.6	772.2	766.3	758.4
45°	756.1	761.6	766.6	766.6	766.6	761.6	756.1	745.6	736.5	727.4	719.7
47.5°	724.1	732.2	737.1	738.3	737.1	732.2	724.1	713.4	700.6	689.4	678.4
50°	702.4	712.1	717.0	720.4	717.0	712.1	702.4	690.4	677.2	663.2	649.9
52.5°	681.1	690.8	697.4	699.2	697.4	690.8	681.1	666.4	650.4	635.3	623.7
55°	644.4	658.3	666.0	668.8	666.0	658.3	644.4	628.3	613.0	594.1	577.3
57.5°	609.8	622.6	631.6	633.6	631.6	622.6	609.8	590.9	571.1	551.0	533.1
60°	582.9	596.9	608.0	610.2	608.0	596.9	582.9	564.1	543.1	523.6	501.3
62.5°	555.5	570.1	580.2	585.6	580.2	570.1	555.5	535.6	513.0	491.2	468.9
65°	508.3	522.9	532.7	534.7	532.7	522.9	508.3	488.7	464.9	441.9	423.0
67.5°	456.6	471.2	477.7	481.7	477.7	471.2	456.6	438.2	414.7	390.8	369.4
70°	420.3	432.1	439.1	442.6	439.1	432.1	420.3	400.7	381.2	356.8	333.7
72.5°	378.9	391.3	399.5	400.2	399.5	391.3	378.9	362.1	341.5	318.8	298.5
75°	315.6	326.7	330.9	330.9	330.9	326.7	315.6	299.5	282.8	264.6	244.4
77.5°	249.7	255.5	260.8	262.0	260.8	255.5	249.7	238.2	224.4	206.2	191.0
80°	207.3	210.9	215.0	215.0	215.0	210.9	207.3	196.8	183.6	168.2	156.4
82.5°	163.8	166.7	170.9	170.4	170.9	166.7	163.8	155.5	144.5	134.2	123.4
85°	99.2	105.4	104.7	103.3	104.7	105.4	99.2	100.5	90.1	83.1	73.3
87.5°	53.4	54.1	55.9	57.2	55.9	54.1	53.4	51.6	46.4	43.1	40.5
90°	43.6	44.3	45.0	45.6	45.0	44.3	43.6	43.0	41.6	39.6	37.6
92.5°	41.6	41.8	41.9	42.0	41.9	41.8	41.6	41.5	40.4	38.4	36.4
95°	43.1	43.5	43.8	44.1	43.8	43.5	43.1	42.8	41.6	39.6	37.6
97.5°	41.6	42.0	42.3	42.6	42.3	42.0	41.6	41.3	41.0	40.8	40.6
100°	41.6	42.0	42.3	42.6	42.3	42.0	41.6	41.3	44.0	49.8	55.5
102.5°	43.6	43.7	43.8	43.8	43.8	43.7	43.6	43.6	74.6	136.6	198.7
105°	470.6	458.4	446.3	434.0	446.3	458.4	470.6	482.7	487.4	484.3	481.2
107.5°	601.1	602.3	603.6	604.9	603.6	602.3	601.1	599.8	598.3	596.9	595.4
110°	676.2	677.2	678.2	679.2	678.2	677.2	676.2	675.2	674.3	673.7	673.0



TEST NUMBER: P332829-840

CATALOG NUMBER: S124DIW-S1020D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	749.7	750.9	752.2	753.6	752.2	750.9	749.7	748.4	747.8	747.9	748.1
115°	862.0	862.0	862.0	862.0	862.0	862.0	862.0	862.0	861.6	860.9	860.3
117.5°	972.6	972.5	972.4	972.2	972.4	972.5	972.6	972.8	972.9	973.0	973.2
120°	1043.7	1043.0	1042.4	1041.7	1042.4	1043.0	1043.7	1044.4	1044.4	1043.7	1043.0
122.5°	1112.0	1111.3	1110.5	1109.9	1110.5	1111.3	1112.0	1112.6	1112.8	1112.4	1112.0
125°	1211.2	1211.5	1211.9	1212.2	1211.9	1211.5	1211.2	1210.9	1210.2	1209.2	1208.2
127.5°	1302.9	1302.6	1302.3	1302.1	1302.3	1302.6	1302.9	1303.1	1303.4	1303.6	1303.8
130°	1363.0	1363.0	1363.0	1363.0	1363.0	1363.0	1363.0	1363.0	1362.8	1362.5	1362.2
132.5°	1419.9	1419.6	1419.4	1419.1	1419.4	1419.6	1419.9	1420.2	1420.1	1419.8	1419.5
135°	1501.1	1501.8	1502.5	1503.1	1502.5	1501.8	1501.1	1500.5	1499.8	1499.0	1498.3
137.5°	1575.6	1575.4	1575.2	1575.0	1575.2	1575.4	1575.6	1575.8	1575.6	1574.8	1574.1
140°	1624.0	1624.3	1624.6	1625.0	1624.6	1624.3	1624.0	1623.6	1623.0	1621.9	1620.9
142.5°	1666.2	1666.3	1666.3	1666.4	1666.3	1666.3	1666.2	1666.1	1665.7	1665.0	1664.3
145°	1728.0	1728.7	1729.4	1730.0	1729.4	1728.7	1728.0	1727.4	1726.8	1726.5	1726.2
147.5°	1781.7	1782.0	1782.4	1782.7	1782.4	1782.0	1781.7	1781.4	1781.1	1780.8	1780.5
150°	1815.8	1816.1	1816.5	1816.8	1816.5	1816.1	1815.8	1815.5	1815.3	1815.3	1815.3
152.5°	1846.6	1846.4	1846.2	1846.0	1846.2	1846.4	1846.6	1846.8	1846.7	1846.1	1845.6
155°	1888.4	1887.4	1886.4	1885.4	1886.4	1887.4	1888.4	1889.5	1889.3	1887.9	1886.5
157.5°	1923.6	1921.8	1920.1	1918.2	1920.1	1921.8	1923.6	1925.3	1925.3	1923.6	1921.8
160°	1946.3	1944.3	1942.3	1940.2	1942.3	1944.3	1946.3	1948.3	1948.3	1946.3	1944.3
162.5°	1964.2	1961.9	1959.5	1957.2	1959.5	1961.9	1964.2	1966.4	1966.6	1964.6	1962.6
165°	1990.4	1987.4	1984.4	1981.4	1984.4	1987.4	1990.4	1993.5	1993.7	1990.9	1988.2
167.5°	2009.4	2006.1	2002.7	1999.3	2002.7	2006.1	2009.4	2012.9	2013.1	2010.0	2007.1
170°	2020.4	2017.0	2013.7	2010.2	2013.7	2017.0	2020.4	2023.8	2024.2	2021.4	2018.7
172.5°	2027.3	2023.7	2020.0	2016.3	2020.0	2023.7	2027.3	2030.9	2031.4	2028.7	2026.0
175°	2036.1	2032.1	2028.0	2024.0	2028.0	2032.1	2036.1	2040.2	2040.7	2037.7	2034.6
177.5°	2038.6	2035.3	2032.1	2028.8	2032.1	2035.3	2038.6	2041.8	2042.4	2040.2	2038.0
180°	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1



TEST NUMBER: P332829-840

CATALOG NUMBER: S124DIW-S1020D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3
2.5°	1611.0	1613.3	1622.1	1630.5	1640.6	1647.9	1652.8	1658.5	1670.2	1679.7	1688.6
5°	1509.3	1512.9	1531.0	1543.6	1565.2	1584.1	1598.7	1614.8	1633.7	1659.4	1683.1
7.5°	1419.9	1432.8	1452.7	1473.1	1495.1	1519.8	1541.4	1565.5	1598.0	1633.5	1670.0
10°	1369.1	1383.7	1404.6	1428.4	1449.4	1477.9	1504.5	1533.1	1570.0	1613.4	1656.7
12.5°	1318.2	1342.3	1358.3	1386.4	1409.1	1432.7	1460.9	1498.4	1541.6	1587.1	1639.3
15°	1254.6	1267.8	1298.5	1313.8	1345.9	1382.3	1410.2	1447.9	1489.8	1549.8	1608.5
17.5°	1181.1	1198.5	1222.9	1252.3	1289.2	1317.5	1352.3	1391.1	1443.9	1503.5	1576.9
20°	1133.1	1147.7	1177.7	1209.8	1248.9	1279.0	1316.0	1353.6	1408.2	1471.7	1548.4
22.5°	1090.0	1104.2	1135.9	1165.7	1203.7	1240.4	1279.1	1322.9	1375.1	1442.1	1520.6
25°	1023.5	1042.3	1070.3	1101.0	1137.2	1179.1	1221.0	1260.1	1316.0	1386.4	1470.3
27.5°	964.4	979.5	999.8	1034.6	1075.8	1116.3	1157.9	1207.1	1260.7	1335.2	1422.2
30°	926.5	940.4	960.6	992.7	1031.2	1074.4	1117.7	1165.2	1221.0	1295.1	1383.7
32.5°	896.3	906.9	924.8	953.6	988.7	1034.2	1076.9	1126.1	1184.7	1257.6	1344.0
35°	851.7	860.8	867.8	895.0	926.5	968.3	1011.6	1064.0	1120.4	1189.6	1276.2
37.5°	808.0	811.1	821.3	839.1	869.6	908.2	948.4	999.9	1057.8	1128.0	1206.1
40°	781.2	782.6	788.9	805.7	832.1	868.5	907.6	958.6	1013.7	1080.1	1157.5
42.5°	755.0	754.1	759.8	771.5	796.4	829.4	867.9	914.4	969.6	1030.9	1103.9
45°	713.5	713.5	712.1	721.9	742.1	774.3	806.4	851.0	897.1	957.2	1018.5
47.5°	670.2	666.3	667.5	672.6	689.6	716.0	748.4	785.0	825.6	876.5	930.3
50°	642.3	636.7	634.6	640.2	655.5	678.5	709.3	741.4	779.8	824.5	870.6
52.5°	611.6	606.0	602.2	606.1	620.4	641.7	669.6	697.8	732.4	768.6	808.6
55°	564.1	557.8	555.7	557.1	567.5	584.3	608.0	633.9	659.7	689.7	717.7
57.5°	517.4	507.0	505.0	504.3	511.6	526.9	546.7	569.2	587.9	606.1	635.8
60°	486.6	474.0	469.8	469.2	474.7	487.3	505.4	527.8	541.1	553.6	579.5
62.5°	453.6	441.6	432.4	433.4	438.4	450.4	466.4	482.5	491.3	505.0	522.5
65°	402.8	387.5	380.5	378.4	381.2	390.9	403.5	413.9	423.7	429.4	446.1
67.5°	352.0	339.1	328.8	326.3	325.1	331.7	342.0	348.4	355.4	360.2	370.1
70°	316.3	305.1	292.6	288.3	287.6	293.2	303.0	303.7	313.5	315.6	326.0
72.5°	281.0	267.1	258.4	254.3	251.4	256.3	262.8	264.6	269.9	273.7	279.1
75°	226.2	215.7	207.3	201.1	198.9	201.8	201.8	205.2	208.7	210.9	217.1
77.5°	178.0	166.0	156.1	152.5	150.0	148.1	149.7	151.8	150.1	153.7	155.1
80°	144.5	132.0	124.3	122.9	118.7	115.2	114.5	116.5	113.8	115.2	119.4
82.5°	111.6	103.5	95.2	93.8	88.6	86.7	86.0	84.7	84.7	84.4	85.3
85°	66.3	61.4	55.8	52.3	50.3	46.8	46.8	45.3	44.0	42.6	43.3
87.5°	33.9	32.4	29.1	26.9	25.1	22.4	21.8	19.4	18.1	16.8	15.5
90°	35.5	33.5	30.8	28.1	25.3	22.7	19.5	15.8	12.0	8.3	4.5
92.5°	34.3	32.3	29.6	26.9	24.1	21.4	20.0	19.8	19.6	19.4	19.2
95°	35.5	33.5	33.1	32.8	32.5	32.1	37.8	49.3	60.8	72.2	83.7
97.5°	40.4	40.2	78.0	115.7	153.5	191.3	206.6	199.4	192.2	185.0	177.8
100°	61.3	67.1	113.7	160.4	207.1	253.8	274.1	268.0	262.0	255.9	249.7
102.5°	260.7	322.9	328.9	335.1	341.1	347.2	348.0	343.6	339.1	334.7	330.1
105°	478.2	475.1	473.4	471.8	470.1	468.4	466.6	464.5	462.4	460.4	458.4
107.5°	593.9	592.4	590.1	587.8	585.5	583.2	581.6	580.6	579.6	578.6	577.4
110°	672.3	671.6	669.5	667.5	665.5	663.5	662.0	661.0	659.9	658.9	657.9



TEST NUMBER: P332829-840

CATALOG NUMBER: S124DIW-S1020D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	748.2	748.4	747.4	746.5	745.5	744.6	743.2	741.3	739.5	737.7	735.9
115°	859.6	858.9	859.3	859.6	859.9	860.3	859.9	858.9	857.9	856.9	855.9
117.5°	973.3	973.4	972.7	972.0	971.2	970.5	969.5	968.1	966.7	965.3	964.0
120°	1042.4	1041.7	1042.0	1042.4	1042.7	1043.0	1042.5	1041.2	1039.9	1038.4	1037.1
122.5°	1111.6	1111.2	1110.6	1110.1	1109.7	1109.2	1108.6	1107.7	1106.9	1106.1	1105.3
125°	1207.2	1206.2	1206.8	1207.5	1208.2	1208.8	1208.5	1207.2	1205.8	1204.5	1203.2
127.5°	1304.0	1304.2	1302.6	1301.1	1299.6	1298.0	1297.1	1296.7	1296.4	1296.1	1295.7
130°	1361.8	1361.5	1360.5	1359.5	1358.5	1357.5	1356.8	1356.5	1356.0	1355.7	1355.4
132.5°	1419.1	1418.8	1417.4	1416.1	1414.9	1413.6	1412.7	1412.1	1411.5	1410.8	1410.2
135°	1497.7	1497.0	1495.7	1494.3	1493.0	1491.6	1491.1	1491.5	1491.8	1492.1	1492.5
137.5°	1573.3	1572.6	1571.0	1569.6	1568.1	1566.6	1565.8	1565.7	1565.5	1565.4	1565.3
140°	1619.9	1618.8	1618.2	1617.5	1616.8	1616.2	1615.5	1614.8	1614.2	1613.5	1612.8
142.5°	1663.4	1662.7	1662.3	1661.9	1661.5	1661.1	1660.3	1659.1	1657.9	1656.6	1655.4
145°	1725.8	1725.5	1725.5	1725.5	1725.5	1725.5	1725.0	1723.9	1722.9	1721.9	1720.9
147.5°	1780.3	1780.0	1780.3	1780.7	1781.0	1781.3	1780.6	1778.7	1776.8	1774.8	1773.0
150°	1815.3	1815.3	1815.6	1816.0	1816.3	1816.6	1816.1	1814.8	1813.4	1812.1	1810.8
152.5°	1845.1	1844.5	1845.1	1845.7	1846.3	1847.0	1846.7	1845.6	1844.6	1843.5	1842.4
155°	1885.2	1883.8	1884.9	1885.9	1886.9	1887.9	1888.2	1887.9	1887.5	1887.2	1886.9
157.5°	1920.1	1918.2	1919.5	1920.6	1921.7	1922.9	1923.6	1923.8	1924.0	1924.2	1924.4
160°	1942.3	1940.2	1940.6	1940.9	1941.2	1941.6	1942.3	1943.3	1944.3	1945.3	1946.3
162.5°	1960.5	1958.4	1958.8	1959.1	1959.4	1959.8	1960.7	1962.0	1963.2	1964.5	1965.8
165°	1985.5	1982.9	1982.9	1982.9	1982.9	1982.9	1983.7	1985.4	1987.1	1988.7	1990.4
167.5°	2004.1	2001.1	2001.4	2001.6	2001.8	2002.0	2002.9	2004.7	2006.4	2008.2	2009.9
170°	2016.0	2013.3	2013.0	2012.7	2012.3	2012.0	2012.8	2014.8	2016.8	2018.9	2020.9
172.5°	2023.3	2020.6	2020.2	2019.9	2019.6	2019.2	2020.1	2022.2	2024.2	2026.2	2028.2
175°	2031.5	2028.5	2028.2	2027.8	2027.5	2027.2	2028.0	2030.0	2032.1	2034.1	2036.1
177.5°	2035.9	2033.7	2033.2	2032.7	2032.1	2031.5	2032.3	2034.1	2036.0	2037.9	2039.8
180°	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1



TEST NUMBER: P332829-840

CATALOG NUMBER: S124DIW-S1020D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3
2.5°	1696.5	1702.0	1709.3	1721.6	1726.1	1731.6	1739.5	1738.9	1741.1	1749.5	1767.4
5°	1702.7	1724.3	1745.3	1770.5	1797.0	1814.4	1838.2	1852.8	1867.4	1886.3	1918.4
7.5°	1705.3	1739.6	1778.0	1822.1	1861.4	1906.6	1941.9	1975.1	2005.2	2045.0	2083.3
10°	1701.3	1747.4	1797.0	1852.8	1912.2	1962.5	2007.8	2059.5	2103.4	2151.6	2194.9
12.5°	1694.0	1749.7	1815.9	1878.6	1947.9	2022.2	2078.7	2130.9	2189.5	2244.9	2311.7
15°	1677.6	1753.7	1831.2	1913.6	2006.4	2092.2	2173.9	2241.7	2304.5	2387.6	2474.9
17.5°	1656.7	1738.8	1836.4	1936.2	2033.3	2131.4	2232.5	2334.3	2413.6	2516.8	2585.1
20°	1637.1	1732.0	1832.6	1951.3	2048.3	2170.5	2271.0	2369.4	2478.3	2581.0	2662.6
22.5°	1609.7	1713.6	1820.3	1938.4	2066.2	2188.4	2304.5	2411.4	2520.2	2631.8	2730.8
25°	1575.0	1669.2	1795.5	1929.7	2056.7	2189.3	2322.7	2456.7	2573.9	2692.0	2784.1
27.5°	1515.8	1634.8	1752.4	1890.8	2031.9	2182.0	2324.6	2465.0	2587.8	2684.8	2742.0
30°	1485.6	1588.9	1716.7	1855.6	2008.5	2169.8	2318.4	2456.0	2570.5	2648.0	2671.0
32.5°	1441.0	1547.6	1672.5	1816.5	1978.3	2144.0	2299.0	2428.6	2524.2	2564.8	2537.0
35°	1374.6	1471.0	1597.3	1744.6	1912.9	2089.5	2242.4	2352.0	2400.9	2362.5	2266.8
37.5°	1295.1	1390.5	1517.4	1662.1	1836.2	2015.8	2154.0	2232.9	2216.7	2121.2	1978.6
40°	1239.2	1328.6	1449.4	1605.7	1775.3	1955.4	2076.9	2119.5	2074.9	1938.0	1786.6
42.5°	1177.2	1264.4	1385.6	1536.4	1716.2	1882.3	1988.1	1991.7	1916.7	1753.1	1601.0
45°	1082.8	1165.9	1280.4	1437.4	1603.6	1760.0	1829.8	1795.5	1657.4	1499.5	1346.7
47.5°	989.7	1061.7	1174.6	1323.6	1481.5	1613.1	1647.7	1586.1	1438.9	1285.7	1144.0
50°	921.5	994.1	1100.2	1242.6	1394.8	1508.6	1525.4	1443.7	1299.2	1144.9	1033.9
52.5°	856.2	928.3	1030.5	1162.3	1301.6	1404.2	1404.7	1310.2	1166.3	1028.7	925.5
55°	760.2	825.2	917.4	1035.3	1159.6	1239.9	1220.3	1122.6	997.6	878.3	788.2
57.5°	667.8	724.4	809.3	907.7	1017.1	1083.4	1051.0	956.8	845.3	744.1	675.8
60°	608.0	661.9	734.5	827.3	919.5	971.1	940.4	855.2	752.6	670.9	611.6
62.5°	550.0	595.3	665.2	745.8	831.2	869.5	842.1	758.0	669.3	595.5	547.3
65°	467.8	504.7	560.6	629.8	691.9	724.7	701.7	623.4	555.7	502.6	464.2
67.5°	390.9	419.9	462.1	517.6	570.4	588.1	567.1	512.7	455.3	412.8	385.8
70°	337.9	365.2	400.7	443.3	489.4	508.3	487.3	444.0	397.3	358.1	331.6
72.5°	291.5	312.7	342.6	379.1	415.2	433.9	419.7	378.1	338.6	309.5	286.9
75°	222.0	240.1	261.1	286.9	314.9	327.4	314.9	286.2	259.0	237.3	221.3
77.5°	161.4	171.2	187.3	206.6	224.1	233.7	222.9	203.4	186.8	172.0	164.1
80°	122.9	129.9	141.0	156.4	168.2	177.3	170.4	154.3	141.0	131.3	127.7
82.5°	89.4	94.1	101.4	112.8	120.8	125.4	122.3	110.7	105.2	96.6	93.1
85°	44.0	46.8	51.7	55.1	62.1	62.8	63.5	58.7	53.7	51.7	48.9
87.5°	16.8	18.1	20.5	22.9	25.8	26.9	26.9	27.4	25.7	25.5	23.7
90°	8.3	12.0	15.8	19.5	22.7	25.3	28.1	30.8	33.5	35.5	37.6
92.5°	19.4	19.6	19.8	20.0	21.4	24.1	26.9	29.6	32.3	34.3	36.4
95°	72.2	60.8	49.3	37.8	32.1	32.5	32.8	33.1	33.5	35.5	37.6
97.5°	185.0	192.2	199.4	206.6	191.3	153.5	115.7	78.0	40.2	40.4	40.6
100°	255.9	262.0	268.0	274.1	253.8	207.1	160.4	113.7	67.1	61.3	55.5
102.5°	334.7	339.1	343.6	348.0	347.2	341.1	335.1	328.9	322.9	260.7	198.7
105°	460.4	462.4	464.5	466.6	468.4	470.1	471.8	473.4	475.1	478.2	481.2
107.5°	578.6	579.6	580.6	581.6	583.2	585.5	587.8	590.1	592.4	593.9	595.4
110°	658.9	659.9	661.0	662.0	663.5	665.5	667.5	669.5	671.6	672.3	673.0



TEST NUMBER: P332829-840

CATALOG NUMBER: S124DIW-S1020D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	737.7	739.5	741.3	743.2	744.6	745.5	746.5	747.4	748.4	748.2	748.1
115°	856.9	857.9	858.9	859.9	860.3	859.9	859.6	859.3	858.9	859.6	860.3
117.5°	965.3	966.7	968.1	969.5	970.5	971.2	972.0	972.7	973.4	973.3	973.2
120°	1038.4	1039.9	1041.2	1042.5	1043.0	1042.7	1042.4	1042.0	1041.7	1042.4	1043.0
122.5°	1106.1	1106.9	1107.7	1108.6	1109.2	1109.7	1110.1	1110.6	1111.2	1111.6	1112.0
125°	1204.5	1205.8	1207.2	1208.5	1208.8	1208.2	1207.5	1206.8	1206.2	1207.2	1208.2
127.5°	1296.1	1296.4	1296.7	1297.1	1298.0	1299.6	1301.1	1302.6	1304.2	1304.0	1303.8
130°	1355.7	1356.0	1356.5	1356.8	1357.5	1358.5	1359.5	1360.5	1361.5	1361.8	1362.2
132.5°	1410.8	1411.5	1412.1	1412.7	1413.6	1414.9	1416.1	1417.4	1418.8	1419.1	1419.5
135°	1492.1	1491.8	1491.5	1491.1	1491.6	1493.0	1494.3	1495.7	1497.0	1497.7	1498.3
137.5°	1565.4	1565.5	1565.7	1565.8	1566.6	1568.1	1569.6	1571.0	1572.6	1573.3	1574.1
140°	1613.5	1614.2	1614.8	1615.5	1616.2	1616.8	1617.5	1618.2	1618.8	1619.9	1620.9
142.5°	1656.6	1657.9	1659.1	1660.3	1661.1	1661.5	1661.9	1662.3	1662.7	1663.4	1664.3
145°	1721.9	1722.9	1723.9	1725.0	1725.5	1725.5	1725.5	1725.5	1725.5	1725.8	1726.2
147.5°	1774.8	1776.8	1778.7	1780.6	1781.3	1781.0	1780.7	1780.3	1780.0	1780.3	1780.5
150°	1812.1	1813.4	1814.8	1816.1	1816.6	1816.3	1816.0	1815.6	1815.3	1815.3	1815.3
152.5°	1843.5	1844.6	1845.6	1846.7	1847.0	1846.3	1845.7	1845.1	1844.5	1845.1	1845.6
155°	1887.2	1887.5	1887.9	1888.2	1887.9	1886.9	1885.9	1884.9	1883.8	1885.2	1886.5
157.5°	1924.2	1924.0	1923.8	1923.6	1922.9	1921.7	1920.6	1919.5	1918.2	1920.1	1921.8
160°	1945.3	1944.3	1943.3	1942.3	1941.6	1941.2	1940.9	1940.6	1940.2	1942.3	1944.3
162.5°	1964.5	1963.2	1962.0	1960.7	1959.8	1959.4	1959.1	1958.8	1958.4	1960.5	1962.6
165°	1988.7	1987.1	1985.4	1983.7	1982.9	1982.9	1982.9	1982.9	1982.9	1985.5	1988.2
167.5°	2008.2	2006.4	2004.7	2002.9	2002.0	2001.8	2001.6	2001.4	2001.1	2004.1	2007.1
170°	2018.9	2016.8	2014.8	2012.8	2012.0	2012.3	2012.7	2013.0	2013.3	2016.0	2018.7
172.5°	2026.2	2024.2	2022.2	2020.1	2019.2	2019.6	2019.9	2020.2	2020.6	2023.3	2026.0
175°	2034.1	2032.1	2030.0	2028.0	2027.2	2027.5	2027.8	2028.2	2028.5	2031.5	2034.6
177.5°	2037.9	2036.0	2034.1	2032.3	2031.5	2032.1	2032.7	2033.2	2033.7	2035.9	2038.0
180°	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1



TEST NUMBER: P332829-840

CATALOG NUMBER: S124DIW-S1020D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3
2.5°	1776.4	1777.5	1782.4	1786.4	1787.5	1793.1	1793.6
5°	1932.4	1944.3	1967.3	1969.4	1972.9	1991.0	1977.1
7.5°	2115.4	2145.5	2165.6	2183.3	2189.8	2197.7	2196.1
10°	2232.6	2277.2	2299.7	2335.2	2336.6	2345.7	2340.2
12.5°	2350.5	2402.4	2443.2	2449.7	2479.6	2484.2	2492.0
15°	2517.4	2572.6	2629.2	2649.4	2690.6	2700.4	2715.7
17.5°	2674.4	2730.8	2770.5	2822.8	2839.7	2862.4	2846.9
20°	2760.4	2821.9	2872.1	2913.3	2930.7	2943.3	2941.9
22.5°	2812.4	2874.3	2915.1	2946.2	2962.5	2967.9	2967.6
25°	2844.9	2880.4	2893.1	2904.9	2886.8	2880.4	2883.3
27.5°	2754.4	2745.2	2712.4	2669.4	2624.6	2589.2	2569.9
30°	2629.9	2575.4	2525.8	2439.2	2394.6	2368.0	2344.3
32.5°	2453.4	2367.0	2271.7	2192.4	2141.6	2102.2	2096.4
35°	2150.9	2021.0	1904.5	1807.5	1757.2	1714.5	1704.9
37.5°	1828.7	1693.7	1588.8	1503.4	1449.4	1419.3	1391.2
40°	1614.8	1498.8	1395.5	1322.9	1281.7	1260.1	1242.6
42.5°	1450.0	1344.1	1241.4	1186.1	1148.8	1135.6	1125.4
45°	1222.4	1124.0	1052.8	1010.9	989.3	966.9	956.4
47.5°	1040.2	960.1	913.1	877.6	854.3	841.1	834.4
50°	936.9	871.2	829.4	802.1	781.2	770.7	765.2
52.5°	845.3	791.4	756.2	734.6	720.3	712.7	710.4
55°	728.1	686.9	664.6	645.8	635.3	628.3	625.5
57.5°	632.9	601.3	583.1	567.5	563.5	557.6	555.7
60°	570.4	545.9	530.6	520.1	516.6	509.7	511.0
62.5°	515.0	495.1	482.0	475.9	471.4	465.5	467.5
65°	435.7	421.0	413.9	408.4	402.8	399.3	402.1
67.5°	365.6	355.5	346.0	342.7	340.0	339.4	336.5
70°	319.7	311.3	303.0	300.9	300.9	298.1	297.4
72.5°	275.6	269.4	263.9	262.4	260.1	261.3	258.3
75°	212.9	208.0	205.9	203.9	203.2	203.2	201.1
77.5°	157.3	153.7	150.4	150.4	147.8	146.9	146.6
80°	119.4	118.0	115.2	115.2	113.8	114.5	113.1
82.5°	89.8	87.9	87.3	86.1	84.2	84.3	82.9
85°	48.2	46.0	45.3	43.3	41.9	43.3	41.9
87.5°	24.6	24.5	24.2	23.2	22.8	22.9	21.4
90°	39.6	41.6	43.0	43.6	44.3	45.0	45.6
92.5°	38.4	40.4	41.5	41.6	41.8	41.9	42.0
95°	39.6	41.6	42.8	43.1	43.5	43.8	44.1
97.5°	40.8	41.0	41.3	41.6	42.0	42.3	42.6
100°	49.8	44.0	41.3	41.6	42.0	42.3	42.6
102.5°	136.6	74.6	43.6	43.6	43.7	43.8	43.8
105°	484.3	487.4	482.7	470.6	458.4	446.3	434.0
107.5°	596.9	598.3	599.8	601.1	602.3	603.6	604.9
110°	673.7	674.3	675.2	676.2	677.2	678.2	679.2



TEST NUMBER: P332829-840

CATALOG NUMBER: S124DIW-S1020D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	747.9	747.8	748.4	749.7	750.9	752.2	753.6
115°	860.9	861.6	862.0	862.0	862.0	862.0	862.0
117.5°	973.0	972.9	972.8	972.6	972.5	972.4	972.2
120°	1043.7	1044.4	1044.4	1043.7	1043.0	1042.4	1041.7
122.5°	1112.4	1112.8	1112.6	1112.0	1111.3	1110.5	1109.9
125°	1209.2	1210.2	1210.9	1211.2	1211.5	1211.9	1212.2
127.5°	1303.6	1303.4	1303.1	1302.9	1302.6	1302.3	1302.1
130°	1362.5	1362.8	1363.0	1363.0	1363.0	1363.0	1363.0
132.5°	1419.8	1420.1	1420.2	1419.9	1419.6	1419.4	1419.1
135°	1499.0	1499.8	1500.5	1501.1	1501.8	1502.5	1503.1
137.5°	1574.8	1575.6	1575.8	1575.6	1575.4	1575.2	1575.0
140°	1621.9	1623.0	1623.6	1624.0	1624.3	1624.6	1625.0
142.5°	1665.0	1665.7	1666.1	1666.2	1666.3	1666.3	1666.4
145°	1726.5	1726.8	1727.4	1728.0	1728.7	1729.4	1730.0
147.5°	1780.8	1781.1	1781.4	1781.7	1782.0	1782.4	1782.7
150°	1815.3	1815.3	1815.5	1815.8	1816.1	1816.5	1816.8
152.5°	1846.1	1846.7	1846.8	1846.6	1846.4	1846.2	1846.0
155°	1887.9	1889.3	1889.5	1888.4	1887.4	1886.4	1885.4
157.5°	1923.6	1925.3	1925.3	1923.6	1921.8	1920.1	1918.2
160°	1946.3	1948.3	1948.3	1946.3	1944.3	1942.3	1940.2
162.5°	1964.6	1966.6	1966.4	1964.2	1961.9	1959.5	1957.2
165°	1990.9	1993.7	1993.5	1990.4	1987.4	1984.4	1981.4
167.5°	2010.0	2013.1	2012.9	2009.4	2006.1	2002.7	1999.3
170°	2021.4	2024.2	2023.8	2020.4	2017.0	2013.7	2010.2
172.5°	2028.7	2031.4	2030.9	2027.3	2023.7	2020.0	2016.3
175°	2037.7	2040.7	2040.2	2036.1	2032.1	2028.0	2024.0
177.5°	2040.2	2042.4	2041.8	2038.6	2035.3	2032.1	2028.8
180°	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1

(END OF REPORT)