

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332858-840

Luminaire Tested: **S124DIW-S1195D1340U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332858-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S1195D1340U840-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9867.6 lumens  
Efficiency: N/A  
Efficacy: 129.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 76.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332858-840

CATALOG NUMBER: S124DIW-S1195D1340U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332858-840

CATALOG NUMBER: S124DIW-S1195D1340U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	52
1	98	94	90	86	91	87	84	81	74	72	69	62	61	59	51	50	49	44
2	89	82	76	71	83	76	71	66	65	61	57	55	52	49	45	43	41	37
3	82	72	65	59	75	67	60	55	57	52	48	48	45	42	40	37	35	31
4	75	64	56	50	69	59	52	47	51	45	41	43	39	36	36	33	30	27
5	69	57	49	43	63	53	46	40	46	40	36	39	34	31	32	29	26	23
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	29	26	23	20
7	58	46	38	32	54	43	36	31	37	32	27	32	27	24	27	23	21	18
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	19	16
9	50	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	20	17	21	18	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16247	16247	16247
5°	16295	16100	16216
10°	16193	15969	16047
15°	15998	15742	15782
20°	15738	15460	15474
25°	15441	15139	15097
30°	15077	14762	14626
35°	14701	14366	14177
40°	14309	13918	13663
45°	13900	13476	13218
50°	13448	13083	12679
55°	12960	12573	12165
60°	12471	12003	11638
65°	11922	11459	10997
70°	11306	10733	10315
75°	10359	9860	9607
80°	9219	8847	8619
85°	8068	7762	7614



TEST NUMBER: P332858-840

CATALOG NUMBER: S124DIW-S1195D1340U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	189.5	1.9
10°-20°	534.0	5.4
20°-30°	786.0	8.0
30°-40°	913.7	9.3
40°-50°	913.7	9.3
50°-60°	799.3	8.1
60°-70°	593.6	6.0
70°-80°	337.2	3.4
80°-90°	102.4	1.0
90°-100°	111.7	1.1
100°-110°	330.9	3.4
110°-120°	561.6	5.7
120°-130°	740.5	7.5
130°-140°	831.6	8.4
140°-150°	817.2	8.3
150°-160°	687.3	7.0
160°-170°	457.3	4.6
170°-180°	160.1	1.6
0°-30°	1509.5	15.3
0°-40°	2423.2	24.6
0°-60°	4136.2	41.9
0°-90°	5169.4	52.4
90°-120°	1004.2	10.2
90°-150°	3393.5	34.4
90°-180°	4698.0	47.6
0°-180°	9867.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2012	2012	2012	2012	2012	
5°	2011	2004	1987	2003	2001	191
15°	1914	1907	1884	1892	1888	539
25°	1734	1722	1700	1701	1695	797
35°	1492	1480	1458	1447	1438	932
45°	1218	1205	1180	1163	1158	938
55°	921	915	893	875	864	824
65°	624	616	600	584	576	618
75°	332	324	316	310	308	353
85°	87	87	84	84	82	96
90°	4	18	29	36	39	10
95°	79	90	100	103	104	87
105°	305	307	312	316	320	324
115°	571	571	568	567	566	563
125°	832	832	830	828	825	741
135°	1073	1080	1080	1078	1074	830
145°	1303	1308	1310	1308	1304	815
155°	1493	1493	1492	1496	1492	687
165°	1625	1621	1619	1626	1621	458
175°	1691	1685	1683	1691	1683	160
180°	1693	1693	1693	1693	1693	



TEST NUMBER: P332858-840

CATALOG NUMBER: S124DIW-S1195D1340U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5
2.5°	2017.6	2016.8	2015.9	2015.1	2014.2	2012.2	2009.0	2005.9	2002.8	1999.6	2002.5
5°	2010.8	2009.4	2008.0	2006.6	2005.2	2002.5	1998.5	1994.6	1990.6	1986.7	1990.6
7.5°	1992.2	1990.7	1989.3	1987.8	1986.4	1983.6	1979.1	1974.8	1970.4	1966.0	1969.2
10°	1975.4	1974.0	1972.6	1971.1	1969.6	1966.6	1962.0	1957.3	1952.7	1948.0	1950.9
12.5°	1953.5	1952.1	1950.6	1949.1	1947.7	1944.5	1939.6	1934.7	1929.8	1924.8	1927.9
15°	1914.1	1912.7	1911.3	1909.9	1908.3	1905.0	1899.6	1894.2	1888.9	1883.5	1885.6
17.5°	1866.7	1864.9	1863.1	1861.4	1859.6	1856.1	1851.0	1845.9	1840.9	1835.7	1837.1
20°	1831.9	1830.1	1828.3	1826.5	1824.7	1821.1	1815.7	1810.4	1805.0	1799.6	1800.7
22.5°	1794.4	1792.1	1789.8	1787.4	1785.0	1781.1	1775.7	1770.4	1765.0	1759.6	1761.6
25°	1733.5	1731.0	1728.5	1726.0	1723.4	1719.7	1714.6	1709.7	1704.7	1699.6	1700.0
27.5°	1663.9	1661.2	1658.7	1656.1	1653.6	1649.9	1645.3	1640.6	1636.0	1631.2	1630.4
30°	1617.4	1614.6	1611.6	1608.8	1606.0	1602.2	1597.5	1592.9	1588.2	1583.6	1582.2
32.5°	1568.4	1565.8	1563.3	1560.6	1558.0	1554.3	1549.3	1544.4	1539.4	1534.5	1532.8
35°	1491.7	1489.1	1486.6	1484.1	1481.6	1477.8	1472.8	1467.8	1462.8	1457.7	1455.2
37.5°	1410.7	1408.4	1406.1	1403.8	1401.5	1397.7	1392.3	1386.9	1381.5	1376.1	1373.4
40°	1357.8	1354.9	1352.0	1349.2	1346.4	1342.2	1336.9	1331.4	1326.1	1320.7	1317.1
42.5°	1301.0	1299.3	1297.6	1295.9	1294.1	1290.3	1284.3	1278.4	1272.4	1266.5	1262.3
45°	1217.5	1215.0	1212.4	1209.9	1207.5	1203.4	1197.6	1191.8	1186.1	1180.4	1176.5
47.5°	1130.0	1128.3	1126.6	1124.9	1123.2	1119.7	1114.4	1109.1	1103.8	1098.5	1094.1
50°	1070.8	1069.3	1067.8	1066.4	1065.0	1061.8	1056.7	1051.8	1046.7	1041.7	1036.7
52.5°	1012.7	1011.0	1009.3	1007.5	1005.8	1002.3	997.0	991.7	986.4	981.1	976.6
55°	920.8	919.7	918.7	917.6	916.5	913.4	908.4	903.4	898.4	893.3	889.1
57.5°	833.0	831.8	830.6	829.4	828.2	825.1	820.1	815.2	810.2	805.3	801.2
60°	772.4	770.6	768.8	767.1	765.3	762.0	757.4	752.8	748.0	743.4	740.1
62.5°	713.1	711.6	710.0	708.5	707.1	703.9	698.9	694.0	689.0	684.1	681.2
65°	624.1	622.3	620.5	618.6	616.9	614.2	610.7	607.0	603.5	599.9	596.3
67.5°	534.4	532.8	531.1	529.5	527.9	525.2	521.8	518.4	514.9	511.5	508.1
70°	479.0	476.5	473.9	471.4	468.9	466.3	463.3	460.5	457.6	454.7	451.9
72.5°	419.6	417.1	414.5	412.0	409.6	407.2	404.9	402.5	400.3	398.0	395.7
75°	332.1	330.4	328.6	326.8	325.0	323.3	321.4	319.6	317.9	316.1	314.7
77.5°	248.6	247.8	247.1	246.3	245.5	244.3	242.8	241.2	239.6	238.0	237.6
80°	198.3	197.2	196.2	195.1	194.1	193.2	192.5	191.7	191.0	190.3	189.6
82.5°	149.4	148.9	148.3	147.8	147.3	147.0	146.8	146.7	146.5	146.4	146.0
85°	87.1	87.1	87.1	87.1	87.1	86.7	86.0	85.3	84.5	83.8	83.8
87.5°	34.3	34.6	35.0	35.3	35.7	36.1	36.2	36.4	36.6	36.8	37.1
90°	3.9	7.2	10.3	13.5	16.8	19.5	21.8	24.1	26.5	28.8	30.6
92.5°	28.1	31.7	35.3	39.0	42.7	45.3	47.0	48.6	50.2	51.9	52.9
95°	78.6	81.2	83.8	86.4	89.1	91.4	93.4	95.4	97.5	99.6	100.4
97.5°	137.2	139.4	141.5	143.5	145.6	147.8	150.3	152.7	155.0	157.4	158.4
100°	183.4	184.5	185.7	186.8	188.0	189.9	192.5	195.1	197.7	200.4	201.0
102.5°	231.6	232.1	232.5	233.0	233.4	234.8	237.2	239.6	242.0	244.4	245.2
105°	305.2	305.5	305.8	306.0	306.3	307.0	308.2	309.4	310.5	311.7	312.6
107.5°	382.4	382.7	383.1	383.4	383.8	384.1	384.3	384.5	384.7	384.8	385.6
110°	434.8	435.4	436.0	436.6	437.2	437.3	437.0	436.7	436.5	436.2	435.6



TEST NUMBER: P332858-840

CATALOG NUMBER: S124DIW-S1195D1340U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	489.3	489.4	489.5	489.7	489.8	489.6	489.1	488.5	488.0	487.5	487.4
115°	571.0	571.0	571.0	571.0	571.0	570.8	570.2	569.6	569.0	568.4	568.2
117.5°	648.0	648.2	648.5	648.7	648.9	648.8	648.4	648.0	647.6	647.2	646.2
120°	699.3	700.5	701.7	702.9	704.0	704.2	703.3	702.5	701.6	700.6	699.2
122.5°	752.8	753.3	753.8	754.2	754.7	754.7	754.3	753.9	753.5	753.1	752.0
125°	831.6	831.6	831.6	831.6	831.6	831.5	831.2	830.9	830.6	830.3	829.7
127.5°	903.1	904.0	904.9	905.7	906.7	906.9	906.4	905.9	905.4	904.9	904.4
130°	953.4	954.3	955.2	956.0	956.9	957.4	957.4	957.4	957.4	957.4	956.7
132.5°	1004.8	1005.4	1006.0	1006.7	1007.3	1007.5	1007.3	1007.0	1006.8	1006.6	1006.0
135°	1072.6	1074.4	1076.1	1077.8	1079.6	1080.5	1080.5	1080.5	1080.5	1080.5	1079.9
137.5°	1146.5	1147.3	1148.1	1148.9	1149.7	1150.4	1150.8	1151.3	1151.8	1152.3	1151.4
140°	1195.8	1196.3	1196.9	1197.5	1198.1	1198.3	1198.3	1198.3	1198.3	1198.3	1198.1
142.5°	1240.8	1241.3	1241.9	1242.5	1243.1	1243.2	1243.0	1242.8	1242.6	1242.3	1242.3
145°	1303.1	1304.3	1305.5	1306.7	1307.8	1308.5	1308.8	1309.1	1309.4	1309.7	1309.4
147.5°	1364.9	1366.3	1367.8	1369.2	1370.5	1371.1	1370.9	1370.7	1370.4	1370.2	1370.0
150°	1402.7	1403.8	1405.0	1406.1	1407.3	1407.9	1407.9	1407.9	1407.9	1407.9	1407.9
152.5°	1438.2	1439.0	1439.7	1440.4	1441.1	1441.6	1441.8	1442.0	1442.3	1442.5	1443.2
155°	1493.0	1493.0	1493.0	1493.0	1493.0	1492.9	1492.6	1492.3	1492.0	1491.8	1492.9
157.5°	1539.1	1538.6	1538.1	1537.5	1537.0	1536.7	1536.7	1536.6	1536.6	1536.5	1537.4
160°	1566.4	1566.1	1565.8	1565.5	1565.2	1564.9	1564.6	1564.4	1564.1	1563.8	1564.6
162.5°	1591.5	1590.7	1590.0	1589.2	1588.5	1588.0	1587.7	1587.4	1587.1	1586.8	1588.4
165°	1625.3	1624.5	1623.6	1622.7	1621.8	1621.1	1620.5	1619.9	1619.3	1618.7	1620.5
167.5°	1651.2	1650.0	1648.8	1647.6	1646.4	1645.8	1645.9	1645.9	1646.0	1646.0	1647.8
170°	1665.9	1664.5	1663.0	1661.5	1660.1	1659.5	1659.8	1660.1	1660.4	1660.6	1662.4
172.5°	1676.4	1675.2	1674.0	1672.7	1671.5	1670.9	1671.0	1671.0	1671.1	1671.1	1673.1
175°	1690.8	1689.3	1687.9	1686.5	1685.0	1684.1	1683.8	1683.5	1683.2	1682.9	1685.0
177.5°	1695.5	1694.4	1693.1	1692.0	1690.8	1690.3	1690.3	1690.3	1690.3	1690.3	1691.9
180°	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4



TEST NUMBER: P332858-840

CATALOG NUMBER: S124DIW-S1195D1340U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5
2.5°	2005.3	2008.2	2011.0	2012.4	2012.1	2011.8	2011.4	2011.1
5°	1994.6	1998.5	2002.5	2004.1	2003.4	2002.7	2002.0	2001.1
7.5°	1972.4	1975.5	1978.6	1980.0	1979.6	1979.1	1978.7	1978.3
10°	1953.7	1956.6	1959.4	1960.6	1959.8	1959.1	1958.3	1957.6
12.5°	1931.1	1934.2	1937.4	1938.4	1937.4	1936.4	1935.4	1934.4
15°	1887.7	1890.0	1892.1	1892.6	1891.6	1890.5	1889.4	1888.3
17.5°	1838.5	1839.9	1841.2	1841.5	1840.8	1840.1	1839.4	1838.7
20°	1801.8	1802.8	1803.9	1804.1	1803.4	1802.7	1802.0	1801.2
22.5°	1763.5	1765.4	1767.4	1767.7	1766.5	1765.1	1763.8	1762.5
25°	1700.4	1700.7	1701.1	1700.5	1699.1	1697.7	1696.3	1694.9
27.5°	1629.5	1628.7	1627.8	1626.5	1624.7	1623.0	1621.1	1619.3
30°	1580.6	1579.2	1577.8	1576.2	1574.4	1572.7	1570.8	1569.0
32.5°	1531.1	1529.3	1527.6	1525.9	1524.1	1522.3	1520.6	1518.7
35°	1452.8	1450.3	1447.7	1445.6	1443.8	1442.0	1440.2	1438.5
37.5°	1370.7	1368.0	1365.2	1362.7	1360.4	1358.0	1355.6	1353.2
40°	1313.5	1309.9	1306.4	1303.6	1301.9	1300.1	1298.3	1296.5
42.5°	1258.2	1254.1	1249.9	1247.2	1246.0	1244.8	1243.5	1242.3
45°	1172.6	1168.6	1164.7	1162.2	1161.0	1159.9	1158.9	1157.8
47.5°	1089.6	1085.2	1080.8	1077.1	1074.4	1071.7	1068.9	1066.2
50°	1031.7	1026.6	1021.7	1018.0	1015.9	1013.8	1011.6	1009.5
52.5°	972.2	967.8	963.3	959.8	957.0	954.3	951.6	948.9
55°	884.7	880.5	876.2	872.9	870.8	868.7	866.5	864.3
57.5°	797.2	793.0	789.0	785.9	783.9	781.7	779.6	777.6
60°	736.9	733.8	730.5	728.0	726.2	724.4	722.7	720.8
62.5°	678.1	675.2	672.3	669.9	668.1	666.3	664.6	662.8
65°	592.7	589.2	585.5	582.9	581.1	579.3	577.4	575.7
67.5°	504.6	501.2	497.8	495.7	495.2	494.7	494.2	493.7
70°	449.0	446.2	443.2	441.3	440.2	439.2	438.1	437.0
72.5°	393.4	391.1	388.8	387.1	386.1	385.0	383.8	382.8
75°	313.2	311.7	310.3	309.4	309.1	308.7	308.3	308.0
77.5°	237.1	236.7	236.3	235.6	234.7	233.8	232.8	231.9
80°	188.8	188.1	187.4	186.9	186.5	186.1	185.8	185.4
82.5°	145.5	145.1	144.7	144.3	143.9	143.6	143.2	142.9
85°	83.8	83.8	83.8	83.7	83.3	82.9	82.6	82.2
87.5°	37.5	37.8	38.1	38.4	38.5	38.6	38.7	38.8
90°	32.3	34.0	35.7	37.0	37.6	38.2	38.7	39.3
92.5°	53.9	55.0	56.0	56.8	57.1	57.5	57.8	58.2
95°	101.3	102.2	103.0	103.5	103.5	103.5	103.5	103.5
97.5°	159.6	160.6	161.6	162.2	162.2	162.2	162.2	162.2
100°	201.6	202.2	202.7	203.0	203.0	203.0	203.0	203.0
102.5°	246.0	246.8	247.6	248.1	248.4	248.6	248.8	249.1
105°	313.5	314.4	315.2	316.1	316.9	317.8	318.7	319.5
107.5°	386.4	387.2	388.1	388.4	388.4	388.3	388.3	388.2
110°	434.9	434.3	433.8	433.9	434.8	435.7	436.6	437.5





TEST NUMBER: P332858-840

CATALOG NUMBER: S124DIW-S1195D1340U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	487.3	487.2	487.0	487.1	487.2	487.4	487.6	487.8
115°	567.8	567.5	567.2	566.9	566.6	566.3	566.0	565.8
117.5°	645.3	644.3	643.3	642.5	641.9	641.4	640.8	640.2
120°	697.8	696.3	694.9	694.4	695.0	695.6	696.2	696.7
122.5°	751.0	750.1	749.1	748.1	747.0	746.0	745.0	743.9
125°	829.2	828.6	828.0	827.4	826.9	826.3	825.7	825.1
127.5°	903.8	903.2	902.6	902.1	901.7	901.2	900.7	900.3
130°	956.2	955.6	955.0	954.2	953.0	951.8	950.7	949.5
132.5°	1005.4	1004.9	1004.3	1003.8	1003.3	1002.8	1002.4	1001.9
135°	1079.3	1078.7	1078.1	1077.4	1076.5	1075.7	1074.8	1073.9
137.5°	1150.7	1150.0	1149.2	1148.9	1149.1	1149.3	1149.4	1149.6
140°	1197.8	1197.5	1197.2	1196.9	1196.6	1196.3	1196.0	1195.8
142.5°	1242.2	1242.2	1242.1	1242.0	1242.0	1241.9	1241.9	1241.8
145°	1309.1	1308.8	1308.5	1308.0	1307.1	1306.2	1305.4	1304.4
147.5°	1369.7	1369.5	1369.3	1369.0	1368.7	1368.4	1368.2	1367.9
150°	1407.9	1407.9	1407.9	1407.8	1407.4	1407.1	1406.8	1406.6
152.5°	1443.9	1444.6	1445.3	1445.2	1444.5	1443.7	1443.0	1442.2
155°	1494.1	1495.2	1496.4	1496.4	1495.2	1494.1	1492.9	1491.8
157.5°	1538.2	1539.1	1540.0	1539.9	1538.9	1537.9	1537.0	1536.0
160°	1565.5	1566.4	1567.2	1566.9	1565.5	1564.1	1562.6	1561.2
162.5°	1589.9	1591.5	1593.1	1593.2	1591.6	1590.2	1588.8	1587.3
165°	1622.2	1624.0	1625.8	1626.1	1624.9	1623.7	1622.6	1621.3
167.5°	1649.5	1651.2	1652.9	1652.9	1651.1	1649.3	1647.6	1645.8
170°	1664.2	1665.9	1667.7	1667.5	1665.5	1663.4	1661.4	1659.4
172.5°	1675.1	1677.1	1679.1	1679.0	1677.0	1675.0	1672.9	1670.9
175°	1687.0	1689.0	1691.1	1691.1	1689.0	1687.0	1685.0	1682.9
177.5°	1693.5	1695.2	1696.8	1696.7	1694.9	1692.9	1691.1	1689.2
180°	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4

(END OF REPORT)