

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333471-927

Luminaire Tested: **S125DIW-S1270D770U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333471-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1270D770U927-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6172.8 lumens
Efficiency: N/A
Efficacy: 103.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333471-927

CATALOG NUMBER: S125DIW-S1270D770U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333471-927

CATALOG NUMBER: S125DIW-S1270D770U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66
1	101	97	93	89	95	91	88	84	81	78	76	71	69	67	62	61	60	55
2	92	84	78	73	86	80	74	69	71	66	63	62	59	56	55	52	50	46
3	84	74	67	61	79	70	63	58	62	57	53	55	51	48	49	45	43	39
4	77	66	58	51	72	62	55	49	55	50	45	49	45	41	43	40	37	34
5	71	59	50	44	66	56	48	42	50	44	39	44	39	35	39	35	32	29
6	65	53	44	38	61	50	42	37	45	39	34	40	35	31	36	31	28	26
7	60	48	40	34	57	45	38	32	41	35	30	36	31	28	32	28	25	23
8	56	43	35	30	53	41	34	29	37	31	27	33	28	25	30	26	22	20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	23	20	18
10	49	37	29	24	46	35	28	23	32	26	22	28	24	20	26	21	18	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10083	10083	10083
5°	10105	10009	10073
10°	10044	9938	9996
15°	9934	9819	9860
20°	9779	9652	9669
25°	9612	9453	9443
30°	9405	9238	9192
35°	9183	9008	8881
40°	8955	8757	8632
45°	8709	8528	8359
50°	8439	8252	8004
55°	8178	7942	7719
60°	7865	7626	7355
65°	7494	7248	7002
70°	7138	6811	6577
75°	6503	6288	6071
80°	5787	5694	5560
85°	5039	5128	4846



TEST NUMBER: P333471-927

CATALOG NUMBER: S125DIW-S1270D770U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.2	2.4
10°-20°	415.8	6.7
20°-30°	613.9	9.9
30°-40°	716.4	11.6
40°-50°	719.5	11.7
50°-60°	631.6	10.2
60°-70°	470.6	7.6
70°-80°	269.1	4.4
80°-90°	79.9	1.3
90°-100°	50.6	0.8
100°-110°	149.5	2.4
110°-120°	253.2	4.1
120°-130°	333.2	5.4
130°-140°	373.3	6.0
140°-150°	365.9	5.9
150°-160°	307.3	5.0
160°-170°	204.3	3.3
170°-180°	71.5	1.2
0°-30°	1177.0	19.1
0°-40°	1893.4	30.7
0°-60°	3244.5	52.6
0°-90°	4064.1	65.8
90°-120°	453.2	7.3
90°-150°	1525.6	24.7
90°-180°	2109.0	34.2
0°-180°	6172.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1561	1561	1561	1561	1561	
5°	1559	1556	1544	1554	1554	148
15°	1486	1482	1468	1474	1475	419
25°	1349	1342	1326	1329	1325	620
35°	1165	1159	1142	1136	1126	728
45°	954	948	934	920	915	734
55°	726	722	705	694	686	648
65°	490	487	474	464	458	486
75°	261	258	252	248	243	278
85°	68	69	69	68	65	76
90°	1	5	9	12	14	6
95°	38	40	45	49	50	41
105°	134	137	140	144	146	143
115°	254	256	257	256	256	251
125°	370	373	374	373	372	331
135°	481	484	485	485	483	371
145°	583	585	587	587	585	364
155°	667	667	668	670	667	307
165°	725	724	724	726	723	204
175°	754	752	752	755	751	72
180°	756	756	756	756	756	



TEST NUMBER: P333471-927

CATALOG NUMBER: S125DIW-S1270D770U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1561.2	1561.2	1561.2	1561.2	1561.2	1561.2	1561.2	1561.2	1561.2	1561.2	1561.2
2.5°	1565.1	1564.5	1563.8	1563.1	1562.5	1561.1	1558.9	1556.6	1554.5	1552.3	1554.5
5°	1558.7	1558.1	1557.6	1557.0	1556.5	1554.9	1552.1	1549.4	1546.7	1543.9	1546.3
7.5°	1544.4	1543.8	1543.3	1542.7	1542.1	1540.4	1537.4	1534.4	1531.4	1528.4	1530.7
10°	1531.5	1531.0	1530.4	1529.9	1529.3	1527.6	1524.6	1521.5	1518.5	1515.4	1517.7
12.5°	1515.7	1514.7	1513.8	1512.8	1511.8	1509.9	1507.0	1504.3	1501.5	1498.7	1500.5
15°	1485.8	1485.0	1484.2	1483.4	1482.6	1480.6	1477.6	1474.6	1471.6	1468.5	1469.9
17.5°	1451.5	1450.3	1449.1	1447.9	1446.7	1444.5	1441.4	1438.2	1435.1	1431.9	1433.7
20°	1422.8	1422.3	1421.7	1421.2	1420.6	1418.6	1415.0	1411.4	1407.9	1404.3	1406.2
22.5°	1394.2	1393.2	1392.2	1391.2	1390.2	1388.1	1384.7	1381.4	1378.0	1374.7	1375.9
25°	1348.8	1347.3	1346.0	1344.7	1343.2	1340.8	1337.2	1333.6	1330.1	1326.5	1327.1
27.5°	1295.6	1294.8	1294.0	1293.2	1292.4	1290.1	1286.4	1282.7	1279.1	1275.3	1275.5
30°	1261.1	1260.2	1259.4	1258.5	1257.7	1255.3	1251.2	1247.1	1242.9	1238.8	1238.3
32.5°	1223.5	1222.3	1221.0	1219.7	1218.5	1216.0	1212.3	1208.6	1204.9	1201.3	1200.3
35°	1164.7	1163.6	1162.5	1161.4	1160.3	1157.9	1154.0	1150.2	1146.3	1142.5	1141.1
37.5°	1103.7	1102.3	1101.0	1099.5	1098.2	1095.7	1092.1	1088.5	1084.8	1081.2	1079.2
40°	1062.2	1060.8	1059.5	1058.0	1056.7	1054.1	1050.3	1046.4	1042.6	1038.7	1036.3
42.5°	1017.7	1016.6	1015.4	1014.2	1013.1	1010.6	1006.8	1002.9	999.1	995.2	993.0
45°	953.5	952.4	951.3	950.2	949.1	946.9	943.6	940.3	937.1	933.7	930.4
47.5°	884.3	884.4	884.5	884.5	884.6	882.6	878.7	874.7	870.8	866.8	863.5
50°	839.9	839.1	838.2	837.4	836.5	834.5	831.2	827.9	824.7	821.3	817.8
52.5°	794.4	793.8	793.2	792.6	792.0	790.0	786.4	782.9	779.4	775.9	772.8
55°	726.3	725.4	724.6	723.7	722.9	720.6	716.8	713.0	709.1	705.3	702.7
57.5°	654.3	653.9	653.5	653.1	652.6	650.8	647.5	644.3	641.0	637.8	634.6
60°	608.9	607.8	606.7	605.6	604.5	602.5	599.4	596.4	593.4	590.4	587.6
62.5°	561.5	560.6	559.8	558.8	557.9	556.3	553.7	551.0	548.5	545.9	543.0
65°	490.4	489.8	489.3	488.7	488.1	486.3	483.3	480.3	477.3	474.3	471.8
67.5°	421.4	420.3	419.1	418.0	416.8	415.1	412.9	410.6	408.4	406.1	404.0
70°	378.0	376.6	375.2	373.8	372.5	370.5	368.0	365.6	363.1	360.7	359.0
72.5°	330.5	329.5	328.7	327.7	326.8	325.5	323.9	322.3	320.8	319.2	317.3
75°	260.6	260.1	259.5	259.0	258.4	257.5	256.1	254.7	253.3	252.0	251.1
77.5°	196.1	195.9	195.7	195.5	195.3	194.8	194.0	193.2	192.4	191.7	191.2
80°	155.6	155.6	155.6	155.6	155.6	155.3	154.8	154.2	153.7	153.1	152.9
82.5°	120.0	119.6	119.1	118.7	118.3	118.0	117.9	117.8	117.7	117.6	117.1
85°	68.0	68.2	68.4	68.8	69.0	69.2	69.2	69.2	69.2	69.2	68.9
87.5°	26.8	27.0	27.3	27.4	27.6	27.7	27.6	27.6	27.6	27.6	27.7
90°	0.6	1.7	2.7	3.7	4.8	5.8	6.7	7.6	8.5	9.4	10.1
92.5°	14.3	15.0	15.7	16.4	17.2	18.1	19.3	20.4	21.5	22.6	23.4
95°	38.3	38.5	38.7	39.0	39.3	40.1	41.4	42.7	44.0	45.3	46.2
97.5°	63.5	63.6	63.7	63.8	63.9	64.9	66.7	68.5	70.3	72.1	73.0
100°	82.3	82.3	82.3	82.3	82.3	83.2	84.8	86.6	88.2	90.0	91.2
102.5°	102.6	103.1	103.6	104.1	104.6	105.4	106.2	107.1	107.9	108.8	110.1
105°	134.1	134.8	135.4	136.0	136.7	137.4	138.2	138.9	139.7	140.5	141.3
107.5°	168.9	169.5	170.2	170.9	171.5	172.1	172.8	173.3	174.0	174.5	174.9
110°	192.9	193.5	194.2	194.9	195.5	196.0	196.4	196.8	197.2	197.6	198.0



TEST NUMBER: P333471-927

CATALOG NUMBER: S125DIW-S1270D770U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	217.4	217.7	218.0	218.4	218.7	219.1	219.6	220.1	220.6	221.1	221.3
115°	253.5	254.0	254.5	255.0	255.6	256.0	256.2	256.4	256.7	257.0	256.8
117.5°	289.7	289.9	290.2	290.4	290.7	290.9	291.1	291.4	291.6	291.8	291.9
120°	312.3	312.9	313.5	314.3	314.9	315.3	315.4	315.5	315.7	315.8	315.8
122.5°	336.8	337.0	337.2	337.5	337.7	337.9	338.3	338.7	339.0	339.3	339.2
125°	369.9	370.7	371.5	372.2	373.0	373.5	373.6	373.8	373.9	374.0	373.8
127.5°	405.2	405.6	406.1	406.5	406.9	407.3	407.4	407.6	407.7	407.9	407.7
130°	426.4	427.0	427.7	428.3	429.0	429.4	429.7	429.9	430.2	430.5	430.3
132.5°	447.5	448.6	449.6	450.8	451.8	452.3	452.3	452.2	452.2	452.1	452.0
135°	481.0	481.8	482.6	483.4	484.2	484.7	484.7	484.9	485.1	485.1	485.1
137.5°	512.5	513.3	514.0	514.8	515.6	516.1	516.4	516.7	517.0	517.3	517.5
140°	532.8	533.5	534.1	534.7	535.4	535.9	536.3	536.7	537.1	537.5	537.7
142.5°	553.0	553.6	554.1	554.7	555.2	555.7	556.3	556.7	557.2	557.7	557.9
145°	582.8	583.3	583.8	584.3	584.9	585.3	585.7	586.1	586.5	586.9	586.9
147.5°	610.3	610.6	610.9	611.2	611.5	611.7	612.0	612.4	612.7	613.0	613.3
150°	628.7	628.5	628.4	628.3	628.1	628.4	628.8	629.4	629.9	630.4	630.4
152.5°	643.7	643.9	644.0	644.3	644.4	644.6	644.8	645.1	645.2	645.5	645.8
155°	666.9	666.9	666.9	666.9	666.9	666.9	667.1	667.2	667.3	667.5	668.0
157.5°	687.6	687.3	687.0	686.7	686.4	686.3	686.5	686.6	686.7	686.9	687.4
160°	699.8	699.4	699.0	698.6	698.2	698.1	698.2	698.4	698.5	698.6	699.2
162.5°	710.7	710.3	710.0	709.8	709.5	709.3	709.4	709.4	709.4	709.5	710.1
165°	725.1	724.8	724.6	724.3	724.1	724.0	724.1	724.2	724.4	724.5	725.0
167.5°	737.4	736.8	736.3	735.8	735.2	735.0	735.0	735.0	735.0	735.0	735.8
170°	743.9	743.4	742.8	742.4	741.8	741.6	741.6	741.6	741.6	741.6	742.4
172.5°	748.6	748.1	747.6	747.0	746.6	746.2	746.2	746.2	746.2	746.2	747.0
175°	753.9	753.4	752.9	752.3	751.8	751.5	751.5	751.5	751.5	751.5	752.3
177.5°	756.6	756.2	755.7	755.3	754.9	754.7	754.6	754.5	754.4	754.2	754.9
180°	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7



TEST NUMBER: P333471-927

CATALOG NUMBER: S125DIW-S1270D770U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1561.2	1561.2	1561.2	1561.2	1561.2	1561.2	1561.2	1561.2
2.5°	1556.6	1558.9	1561.1	1562.0	1561.9	1561.6	1561.4	1561.2
5°	1548.8	1551.3	1553.8	1554.9	1554.6	1554.3	1554.0	1553.8
7.5°	1533.1	1535.6	1537.9	1539.1	1538.8	1538.5	1538.3	1537.9
10°	1519.9	1522.1	1524.2	1525.2	1525.0	1524.6	1524.4	1524.2
12.5°	1502.2	1504.0	1505.7	1506.6	1506.5	1506.4	1506.4	1506.3
15°	1471.3	1472.7	1474.0	1474.7	1474.7	1474.7	1474.7	1474.7
17.5°	1435.4	1437.1	1438.8	1438.9	1437.6	1436.2	1434.8	1433.5
20°	1408.2	1410.1	1412.0	1412.3	1410.9	1409.5	1408.2	1406.8
22.5°	1377.2	1378.5	1379.7	1379.9	1379.0	1378.0	1377.1	1376.2
25°	1327.6	1328.2	1328.7	1328.6	1327.8	1326.9	1326.1	1325.2
27.5°	1275.6	1275.7	1275.8	1275.4	1274.6	1273.8	1273.0	1272.2
30°	1237.7	1237.2	1236.6	1236.0	1235.1	1234.3	1233.4	1232.6
32.5°	1199.3	1198.3	1197.3	1196.0	1194.6	1193.1	1191.6	1190.2
35°	1139.7	1138.4	1137.0	1135.2	1133.0	1130.8	1128.6	1126.4
37.5°	1077.1	1075.1	1073.1	1071.4	1070.2	1068.9	1067.6	1066.4
40°	1033.8	1031.3	1028.8	1027.2	1026.4	1025.6	1024.7	1023.9
42.5°	990.8	988.5	986.3	984.5	983.3	982.0	980.7	979.5
45°	927.2	923.8	920.6	918.5	917.7	916.9	916.0	915.2
47.5°	860.1	856.7	853.4	850.8	848.8	846.9	845.0	843.1
50°	814.2	810.6	807.1	804.3	802.4	800.5	798.6	796.6
52.5°	769.6	766.5	763.3	760.7	758.6	756.5	754.3	752.2
55°	700.3	697.8	695.4	693.2	691.3	689.4	687.4	685.5
57.5°	631.4	628.3	625.1	623.0	621.9	620.9	619.8	618.8
60°	584.9	582.2	579.4	577.1	575.1	573.2	571.3	569.4
62.5°	540.0	537.0	534.1	531.9	530.4	528.9	527.4	525.9
65°	469.4	466.8	464.4	462.6	461.5	460.4	459.3	458.2
67.5°	402.0	399.8	397.8	396.4	395.7	395.1	394.4	393.7
70°	357.4	355.7	354.0	352.7	351.6	350.5	349.4	348.3
72.5°	315.4	313.5	311.7	310.2	309.1	308.0	306.9	305.8
75°	250.3	249.5	248.7	247.7	246.6	245.5	244.4	243.3
77.5°	190.7	190.2	189.7	189.1	188.3	187.5	186.8	186.0
80°	152.6	152.3	152.0	151.6	151.1	150.5	150.0	149.5
82.5°	116.6	116.1	115.6	115.3	115.2	115.1	114.9	114.9
85°	68.6	68.4	68.0	67.7	67.1	66.5	66.0	65.4
87.5°	27.8	28.0	28.1	28.0	27.6	27.3	26.9	26.5
90°	10.7	11.4	12.0	12.5	12.9	13.3	13.7	14.1
92.5°	24.3	25.2	26.1	26.6	26.9	27.2	27.5	27.7
95°	47.1	48.0	49.0	49.5	49.8	50.1	50.3	50.5
97.5°	73.8	74.7	75.6	76.0	76.2	76.4	76.5	76.7
100°	92.3	93.5	94.7	95.4	95.7	95.9	96.2	96.4
102.5°	111.4	112.6	113.9	114.7	115.1	115.5	115.8	116.2
105°	142.1	142.9	143.7	144.3	144.7	145.0	145.4	145.8
107.5°	175.3	175.7	176.1	176.3	176.3	176.3	176.2	176.2
110°	198.4	198.8	199.2	199.3	199.2	199.0	198.9	198.8



TEST NUMBER: P333471-927

CATALOG NUMBER: S125DIW-S1270D770U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	221.5	221.7	221.8	221.8	221.6	221.3	221.1	220.9
115°	256.7	256.6	256.4	256.4	256.2	256.1	256.0	255.8
117.5°	292.0	292.1	292.2	292.0	291.5	291.0	290.4	289.9
120°	315.8	315.8	315.8	315.5	315.1	314.5	313.9	313.5
122.5°	339.1	339.0	338.9	338.7	338.2	337.8	337.4	337.0
125°	373.5	373.2	373.0	372.8	372.6	372.5	372.4	372.2
127.5°	407.7	407.5	407.3	407.2	406.9	406.6	406.4	406.2
130°	430.2	430.1	429.9	429.8	429.5	429.2	429.0	428.7
132.5°	451.9	451.7	451.6	451.3	451.0	450.6	450.3	449.9
135°	485.1	485.1	485.1	484.9	484.3	483.9	483.3	482.8
137.5°	517.6	517.8	517.9	517.6	517.0	516.3	515.7	515.0
140°	538.1	538.3	538.5	538.4	537.7	537.0	536.4	535.8
142.5°	558.0	558.2	558.3	558.1	557.5	556.8	556.1	555.5
145°	586.9	586.9	586.9	586.7	586.3	585.9	585.5	585.1
147.5°	613.6	613.9	614.3	613.9	613.1	612.2	611.3	610.5
150°	630.4	630.4	630.4	630.3	630.0	629.8	629.5	629.2
152.5°	646.1	646.4	646.7	646.7	646.2	645.7	645.2	644.8
155°	668.5	669.0	669.6	669.5	668.8	668.2	667.5	666.9
157.5°	687.9	688.4	689.0	688.8	687.9	687.1	686.2	685.3
160°	699.7	700.2	700.7	700.7	700.0	699.3	698.7	698.1
162.5°	710.7	711.3	711.9	711.9	711.1	710.3	709.6	708.8
165°	725.6	726.1	726.6	726.4	725.7	724.9	724.1	723.3
167.5°	736.6	737.4	738.1	738.1	737.3	736.5	735.7	734.8
170°	743.1	743.9	744.7	744.7	743.7	742.8	741.9	741.0
172.5°	747.8	748.6	749.4	749.4	748.6	747.7	746.9	746.2
175°	753.1	753.9	754.7	754.6	753.7	752.8	751.9	751.0
177.5°	755.5	756.1	756.8	756.7	756.0	755.3	754.6	753.8
180°	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7

(END OF REPORT)