

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332725-840

Luminaire Tested: **S124DIW-S350D770U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332725-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S350D770U840-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4633.9 lumens
Efficiency: N/A
Efficacy: 152.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332725-840

CATALOG NUMBER: S124DIW-S350D770U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332725-840

CATALOG NUMBER: S124DIW-S350D770U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33
1	94	90	86	82	85	81	78	75	65	62	60	50	48	47	36	35	34	28
2	86	78	72	67	77	71	66	61	57	53	50	44	41	39	31	30	29	23
3	78	69	62	56	70	62	56	51	50	46	42	38	36	33	28	26	24	20
4	71	61	53	47	64	55	48	43	44	39	36	34	31	28	25	23	21	17
5	65	54	46	40	59	49	42	37	40	34	31	31	27	24	22	20	18	15
6	60	48	40	35	54	44	37	32	36	30	27	28	24	21	20	18	16	13
7	55	44	36	30	50	40	33	28	32	27	23	25	21	19	19	16	14	11
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13	10
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	16	13	12	9
10	45	33	26	21	40	30	24	20	25	20	16	19	16	13	15	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4816	4816	4816
5°	4830	4772	4807
10°	4800	4733	4757
15°	4741	4667	4679
20°	4665	4582	4587
25°	4577	4488	4475
30°	4470	4376	4336
35°	4357	4258	4202
40°	4241	4126	4051
45°	4120	3995	3919
50°	3986	3878	3758
55°	3842	3727	3606
60°	3696	3559	3450
65°	3534	3396	3261
70°	3352	3182	3059
75°	3072	2923	2848
80°	2734	2627	2552
85°	2399	2297	2251



TEST NUMBER: P332725-840

CATALOG NUMBER: S124DIW-S350D770U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.2	1.2
10°-20°	158.3	3.4
20°-30°	233.0	5.0
30°-40°	270.8	5.8
40°-50°	270.9	5.8
50°-60°	236.9	5.1
60°-70°	175.9	3.8
70°-80°	100.0	2.2
80°-90°	31.7	0.7
90°-100°	34.3	0.7
100°-110°	218.6	4.7
110°-120°	418.1	9.0
120°-130°	530.7	11.5
130°-140°	567.9	12.3
140°-150°	531.0	11.5
150°-160°	428.2	9.2
160°-170°	276.2	6.0
170°-180°	95.2	2.1
0°-30°	447.4	9.7
0°-40°	718.3	15.5
0°-60°	1226.1	26.5
0°-90°	1533.7	33.1
90°-120°	670.9	14.5
90°-150°	2300.6	49.6
90°-180°	3100.0	66.9
0°-180°	4633.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	596	596	596	596	596	
5°	596	594	589	594	593	57
15°	567	565	558	561	560	160
25°	514	510	504	504	502	236
35°	442	439	432	429	426	276
45°	361	357	350	345	343	278
55°	273	271	265	259	256	244
65°	185	182	178	173	171	183
75°	98	96	94	92	91	105
85°	26	26	25	25	24	28
90°	2	10	16	21	22	3
95°	41	17	16	21	22	53
105°	226	230	234	239	214	236
115°	421	423	423	424	424	414
125°	592	595	594	596	597	529
135°	735	734	737	738	740	566
145°	847	849	849	850	852	529
155°	929	929	927	930	928	428
165°	980	976	976	981	975	277
175°	1002	998	998	1004	996	95
180°	1002	1002	1002	1002	1002	



TEST NUMBER: P332725-840

CATALOG NUMBER: S124DIW-S350D770U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5
2.5°	598.0	597.8	597.5	597.3	597.0	596.4	595.5	594.6	593.7	592.7	593.6
5°	596.0	595.6	595.2	594.8	594.4	593.6	592.4	591.3	590.1	588.9	590.1
7.5°	590.6	590.1	589.7	589.3	588.9	587.9	586.6	585.4	584.1	582.8	583.7
10°	585.5	585.1	584.7	584.3	583.9	583.0	581.6	580.2	578.9	577.4	578.2
12.5°	579.1	578.7	578.2	577.7	577.3	576.4	574.9	573.5	572.0	570.6	571.5
15°	567.3	566.9	566.5	566.1	565.7	564.7	563.1	561.5	559.9	558.4	559.0
17.5°	553.3	552.8	552.3	551.8	551.2	550.2	548.7	547.1	545.6	544.1	544.5
20°	543.0	542.5	542.0	541.4	540.9	539.9	538.3	536.6	535.0	533.4	533.8
22.5°	531.9	531.2	530.5	529.8	529.1	528.0	526.3	524.8	523.2	521.6	522.2
25°	513.8	513.1	512.4	511.6	510.9	509.8	508.3	506.8	505.3	503.8	503.9
27.5°	493.2	492.4	491.7	490.9	490.2	489.1	487.7	486.4	484.9	483.5	483.3
30°	479.5	478.6	477.8	476.9	476.1	474.9	473.5	472.1	470.8	469.4	469.0
32.5°	464.9	464.1	463.3	462.6	461.8	460.7	459.3	457.8	456.4	454.8	454.3
35°	442.1	441.4	440.7	439.9	439.2	438.1	436.6	435.0	433.6	432.1	431.4
37.5°	418.2	417.5	416.8	416.2	415.5	414.3	412.7	411.1	409.5	407.9	407.1
40°	402.4	401.6	400.8	399.9	399.1	397.9	396.3	394.7	393.0	391.5	390.4
42.5°	385.7	385.2	384.7	384.2	383.6	382.4	380.7	378.9	377.2	375.5	374.2
45°	360.9	360.1	359.4	358.7	357.9	356.7	355.0	353.3	351.6	349.9	348.7
47.5°	335.0	334.5	334.0	333.5	333.0	331.9	330.3	328.7	327.2	325.6	324.3
50°	317.4	317.0	316.6	316.1	315.7	314.8	313.3	311.7	310.2	308.8	307.3
52.5°	300.2	299.6	299.1	298.6	298.1	297.1	295.5	294.0	292.4	290.8	289.5
55°	273.0	272.7	272.3	272.0	271.7	270.7	269.2	267.8	266.3	264.8	263.6
57.5°	246.9	246.6	246.2	245.9	245.5	244.6	243.1	241.7	240.1	238.7	237.5
60°	228.9	228.4	227.9	227.3	226.8	225.9	224.5	223.1	221.8	220.4	219.4
62.5°	211.4	211.0	210.5	210.1	209.5	208.6	207.1	205.7	204.2	202.8	201.9
65°	185.0	184.5	183.9	183.4	182.9	182.1	181.0	180.0	178.8	177.8	176.7
67.5°	158.4	157.9	157.4	156.9	156.4	155.7	154.7	153.7	152.7	151.6	150.6
70°	142.0	141.2	140.5	139.8	139.0	138.1	137.3	136.5	135.6	134.8	133.9
72.5°	124.4	123.6	122.9	122.2	121.4	120.7	120.0	119.4	118.7	118.0	117.2
75°	98.5	98.0	97.5	96.8	96.3	95.8	95.3	94.7	94.2	93.7	93.3
77.5°	73.7	73.5	73.2	73.0	72.8	72.4	72.0	71.5	71.0	70.6	70.4
80°	58.8	58.5	58.2	57.9	57.6	57.3	57.1	56.9	56.7	56.5	56.1
82.5°	44.2	44.1	43.9	43.8	43.6	43.5	43.5	43.5	43.4	43.4	43.3
85°	25.9	25.9	25.9	25.9	25.9	25.8	25.4	25.2	25.0	24.8	24.8
87.5°	10.4	10.7	10.9	11.2	11.5	11.7	11.9	12.1	12.3	12.5	12.7
90°	2.2	4.0	6.0	7.8	9.6	11.2	12.5	13.8	15.1	16.5	17.5
92.5°	9.5	9.6	9.7	9.7	9.8	10.6	11.9	13.2	14.5	15.9	16.9
95°	41.2	35.5	29.9	24.2	18.6	15.9	16.0	16.2	16.4	16.5	17.5
97.5°	87.6	91.1	94.6	98.2	101.7	94.1	75.5	57.0	38.4	19.8	19.9
100°	122.9	125.9	129.0	131.9	134.9	124.9	102.0	79.0	55.9	33.0	30.2
102.5°	162.5	164.7	166.9	169.2	171.3	170.9	167.9	164.9	161.9	159.0	128.4
105°	225.6	226.6	227.6	228.6	229.6	230.6	231.4	232.2	233.1	233.9	235.4
107.5°	284.3	284.8	285.3	285.8	286.3	287.1	288.2	289.3	290.4	291.5	292.4
110°	323.9	324.4	324.9	325.4	325.8	326.6	327.6	328.6	329.6	330.5	330.9



TEST NUMBER: P332725-840

CATALOG NUMBER: S124DIW-S350D770U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	362.2	363.1	364.1	364.9	365.8	366.5	367.0	367.4	367.9	368.4	368.3
115°	421.3	421.8	422.3	422.7	423.2	423.4	423.2	423.1	422.9	422.7	423.1
117.5°	474.5	475.1	475.8	476.5	477.2	477.7	478.1	478.4	478.8	479.2	479.1
120°	510.5	511.2	511.8	512.5	513.1	513.4	513.2	513.1	512.9	512.7	513.1
122.5°	544.1	544.4	544.8	545.2	545.6	545.9	546.2	546.4	546.6	546.9	547.1
125°	592.2	592.9	593.5	594.2	594.8	595.0	594.7	594.4	594.0	593.7	594.2
127.5°	637.7	637.9	638.1	638.2	638.4	638.9	639.6	640.5	641.2	642.0	641.9
130°	667.1	667.3	667.5	667.6	667.8	668.1	668.6	669.1	669.6	670.1	670.3
132.5°	694.2	694.5	694.8	695.0	695.3	695.8	696.4	697.1	697.7	698.3	698.5
135°	734.6	734.5	734.3	734.1	734.0	734.2	734.9	735.5	736.2	736.9	737.2
137.5°	770.4	770.5	770.6	770.6	770.7	771.1	771.8	772.5	773.4	774.1	774.4
140°	793.9	794.2	794.5	794.9	795.2	795.5	795.9	796.2	796.5	796.9	797.3
142.5°	814.9	815.5	816.1	816.6	817.2	817.6	817.8	818.0	818.2	818.4	818.8
145°	847.1	847.6	848.1	848.6	849.1	849.3	849.3	849.3	849.3	849.3	849.5
147.5°	872.7	873.6	874.5	875.5	876.5	876.8	876.7	876.5	876.3	876.2	876.3
150°	891.3	891.9	892.6	893.3	893.9	894.2	894.0	893.8	893.7	893.5	893.5
152.5°	906.9	907.4	908.0	908.5	909.0	909.1	908.8	908.6	908.3	908.0	908.2
155°	928.8	929.0	929.1	929.3	929.5	929.3	928.8	928.3	927.8	927.3	928.0
157.5°	947.3	947.2	947.1	947.0	946.8	946.4	945.9	945.3	944.7	944.2	945.0
160°	958.0	957.5	957.0	956.5	956.0	955.6	955.5	955.3	955.1	955.0	956.0
162.5°	967.6	966.9	966.3	965.7	965.0	964.6	964.5	964.3	964.1	964.0	965.0
165°	979.8	978.9	978.1	977.2	976.4	976.0	976.0	976.0	976.0	976.0	977.3
167.5°	989.4	988.5	987.6	986.7	985.8	985.4	985.3	985.2	985.1	985.0	986.4
170°	994.7	993.7	992.7	991.7	990.8	990.3	990.5	990.7	990.8	991.0	992.3
172.5°	998.4	997.3	996.3	995.3	994.3	993.9	994.1	994.2	994.4	994.6	995.9
175°	1002.2	1001.2	1000.3	999.3	998.3	997.8	997.9	998.2	998.4	998.5	1000.0
177.5°	1004.0	1003.1	1002.2	1001.2	1000.3	1000.0	1000.3	1000.5	1000.8	1001.0	1002.1
180°	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2



TEST NUMBER: P332725-840

CATALOG NUMBER: S124DIW-S350D770U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5
2.5°	594.4	595.3	596.1	596.5	596.4	596.3	596.2	596.1
5°	591.3	592.4	593.6	594.0	593.8	593.6	593.4	593.2
7.5°	584.6	585.6	586.5	586.9	586.8	586.6	586.5	586.4
10°	579.2	580.0	580.9	581.2	581.0	580.7	580.5	580.3
12.5°	572.4	573.3	574.3	574.6	574.3	574.0	573.7	573.4
15°	559.6	560.2	560.9	561.0	560.7	560.4	560.1	559.8
17.5°	544.9	545.3	545.7	545.8	545.6	545.4	545.2	545.0
20°	534.1	534.4	534.7	534.8	534.5	534.3	534.1	533.9
22.5°	522.7	523.3	523.9	524.0	523.6	523.2	522.8	522.5
25°	504.0	504.1	504.2	504.1	503.6	503.2	502.8	502.4
27.5°	483.0	482.8	482.5	482.1	481.6	481.1	480.5	480.0
30°	468.6	468.2	467.7	467.3	466.7	466.2	465.6	465.1
32.5°	453.8	453.3	452.8	452.3	451.8	451.2	450.7	450.2
35°	430.6	429.9	429.1	428.5	428.0	427.5	426.9	426.4
37.5°	406.3	405.5	404.7	403.9	403.2	402.5	401.8	401.1
40°	389.4	388.3	387.3	386.5	385.9	385.4	384.9	384.4
42.5°	372.9	371.7	370.5	369.7	369.3	369.0	368.6	368.3
45°	347.6	346.4	345.3	344.5	344.2	343.9	343.6	343.3
47.5°	323.0	321.6	320.3	319.3	318.5	317.7	316.9	316.1
50°	305.8	304.4	302.9	301.7	301.1	300.5	299.8	299.2
52.5°	288.2	286.9	285.6	284.5	283.7	282.9	282.1	281.2
55°	262.3	260.9	259.7	258.7	258.1	257.5	256.8	256.2
57.5°	236.3	235.1	233.9	233.0	232.4	231.8	231.2	230.5
60°	218.4	217.5	216.5	215.8	215.3	214.7	214.2	213.7
62.5°	201.1	200.2	199.2	198.5	198.0	197.5	197.0	196.4
65°	175.7	174.6	173.6	172.8	172.3	171.7	171.2	170.7
67.5°	149.6	148.6	147.5	146.9	146.8	146.6	146.5	146.3
70°	133.1	132.3	131.4	130.8	130.5	130.2	129.9	129.6
72.5°	116.6	115.9	115.2	114.7	114.4	114.1	113.8	113.5
75°	92.8	92.4	92.0	91.7	91.6	91.5	91.4	91.3
77.5°	70.3	70.2	70.1	69.9	69.6	69.3	69.0	68.8
80°	55.9	55.7	55.5	55.4	55.2	55.1	55.0	54.9
82.5°	43.1	43.0	42.9	42.8	42.7	42.5	42.4	42.3
85°	24.8	24.8	24.8	24.8	24.7	24.6	24.4	24.3
87.5°	12.8	13.0	13.2	13.4	13.4	13.5	13.6	13.6
90°	18.5	19.5	20.5	21.1	21.5	21.8	22.1	22.5
92.5°	17.9	18.9	19.9	20.4	20.5	20.6	20.6	20.7
95°	18.5	19.5	20.5	21.1	21.2	21.4	21.6	21.7
97.5°	20.0	20.1	20.2	20.3	20.5	20.7	20.8	21.0
100°	27.4	24.4	21.6	20.3	20.5	20.7	20.8	21.0
102.5°	97.9	67.3	36.8	21.4	21.5	21.5	21.5	21.6
105°	236.9	238.3	239.8	237.6	231.7	225.6	219.6	213.7
107.5°	293.1	293.8	294.6	295.2	295.9	296.5	297.1	297.7
110°	331.2	331.5	331.9	332.3	332.9	333.4	333.9	334.4



TEST NUMBER: P332725-840

CATALOG NUMBER: S124DIW-S350D770U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	368.2	368.2	368.1	368.4	369.0	369.6	370.3	370.9
115°	423.4	423.7	424.1	424.2	424.2	424.2	424.2	424.2
117.5°	479.0	479.0	478.9	478.8	478.8	478.7	478.6	478.6
120°	513.4	513.7	514.0	514.0	513.7	513.4	513.1	512.7
122.5°	547.3	547.5	547.8	547.6	547.3	546.9	546.6	546.3
125°	594.7	595.2	595.7	596.0	596.2	596.3	596.5	596.7
127.5°	641.8	641.7	641.6	641.5	641.4	641.2	641.1	641.0
130°	670.4	670.7	670.9	670.9	670.9	670.9	670.9	670.9
132.5°	698.6	698.8	699.0	699.0	698.9	698.7	698.6	698.5
135°	737.5	737.9	738.2	738.5	738.8	739.2	739.5	739.8
137.5°	774.8	775.2	775.5	775.7	775.6	775.5	775.4	775.3
140°	797.8	798.3	798.8	799.2	799.3	799.5	799.7	799.8
142.5°	819.2	819.5	819.9	820.1	820.1	820.1	820.2	820.2
145°	849.6	849.8	850.0	850.2	850.5	850.9	851.2	851.5
147.5°	876.4	876.6	876.7	876.9	877.0	877.2	877.4	877.5
150°	893.5	893.5	893.5	893.6	893.8	893.9	894.1	894.2
152.5°	908.5	908.7	909.0	909.1	909.0	908.9	908.8	908.7
155°	928.6	929.3	929.9	930.0	929.5	929.0	928.5	928.1
157.5°	945.9	946.8	947.7	947.7	946.8	945.9	945.0	944.2
160°	957.0	958.0	959.0	959.0	958.0	957.0	956.0	955.0
162.5°	966.0	966.9	968.0	968.0	966.8	965.6	964.5	963.4
165°	978.7	980.0	981.3	981.3	979.8	978.3	976.7	975.2
167.5°	988.0	989.4	990.9	990.8	989.1	987.4	985.7	984.1
170°	993.6	995.0	996.3	996.1	994.5	992.8	991.2	989.5
172.5°	997.2	998.6	999.9	999.7	997.8	996.1	994.3	992.5
175°	1001.5	1003.0	1004.5	1004.2	1002.2	1000.3	998.3	996.2
177.5°	1003.2	1004.2	1005.3	1005.0	1003.4	1001.8	1000.3	998.7
180°	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2

(END OF REPORT)