

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333358-927

Luminaire Tested: **S125DIW-S375D1340U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333358-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S375D1340U927-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5468.7 lumens
Efficiency: N/A
Efficacy: 117.4 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333358-927

CATALOG NUMBER: S125DIW-S375D1340U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333358-927

CATALOG NUMBER: S125DIW-S375D1340U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31	22
1	92	88	84	81	81	78	75	72	60	58	56	43	42	40	27	27	26	19
2	83	77	71	66	74	68	63	59	52	49	46	38	36	34	24	23	22	16
3	76	67	60	55	67	60	54	49	46	42	39	33	31	29	21	20	19	14
4	70	59	52	46	61	53	47	42	41	36	33	30	27	24	19	18	16	12
5	64	53	45	39	56	47	41	36	36	32	28	26	23	21	17	15	14	10
6	59	47	39	34	52	42	36	31	33	28	25	24	21	18	16	14	12	9
7	54	42	35	30	48	38	31	27	29	25	21	22	18	16	14	12	11	8
8	50	38	31	26	44	34	28	24	27	22	19	20	17	14	13	11	10	7
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	6
10	43	32	25	20	38	29	23	18	22	18	15	17	14	11	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	2785	2785	2785	2785
5°	3225	2795	2447	2795
10°	3752	2781	2144	2781
15°	4153	2760	1978	2760
20°	4649	2728	1844	2728
25°	5447	2691	1779	2691
30°	5883	2655	1723	2655
35°	4837	2588	1686	2588
40°	3438	2494	1645	2494
45°	2641	2367	1621	2367
50°	2255	2210	1619	2210
55°	2008	2057	1633	2057
60°	1811	1888	1674	1888
65°	1673	1721	1718	1721
70°	1522	1545	1743	1545
75°	1342	1362	1727	1362
80°	1131	1112	1581	1112
85°	897	800	1275	800



TEST NUMBER: P333358-927

CATALOG NUMBER: S125DIW-S375D1340U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.5	0.8
10°-20°	123.6	2.3
20°-30°	200.7	3.7
30°-40°	244.8	4.5
40°-50°	222.7	4.1
50°-60°	177.4	3.2
60°-70°	123.6	2.3
70°-80°	65.9	1.2
80°-90°	19.5	0.4
90°-100°	50.3	0.9
100°-110°	309.9	5.7
110°-120°	562.0	10.3
120°-130°	721.3	13.2
130°-140°	775.8	14.2
140°-150°	728.2	13.3
150°-160°	589.1	10.8
160°-170°	381.0	7.0
170°-180°	131.4	2.4
0°-30°	365.9	6.7
0°-40°	610.7	11.2
0°-60°	1010.8	18.5
0°-90°	1219.8	22.3
90°-120°	922.2	16.9
90°-150°	3147.5	57.6
90°-180°	4249.0	77.7
0°-180°	5468.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	431	431	431	431	431	
5°	498	431	378	431	498	50
15°	621	413	296	413	621	178
25°	764	378	250	378	764	349
35°	614	328	214	328	614	375
45°	289	259	178	259	289	231
55°	178	183	145	183	178	161
65°	110	113	112	113	110	109
75°	54	55	69	55	54	58
85°	12	11	17	11	12	15
90°	25	1	25	1	25	11
95°	22	58	22	58	22	18
105°	305	302	305	302	305	275
115°	562	566	562	566	562	558
125°	805	805	805	805	805	716
135°	1000	1004	1000	1004	1000	772
145°	1161	1164	1161	1164	1161	725
155°	1273	1282	1273	1282	1273	587
165°	1346	1353	1346	1353	1346	380
175°	1377	1384	1377	1384	1377	131
180°	1384	1384	1384	1384	1384	



TEST NUMBER: P333358-927

CATALOG NUMBER: S125DIW-S375D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3
2.5°	456.1	455.6	455.0	453.8	454.7	452.2	451.1	449.0	446.5	445.6	444.6
5°	497.5	498.4	499.4	495.5	495.9	493.3	487.4	482.7	478.9	473.9	470.4
7.5°	547.3	545.2	544.9	542.5	538.2	534.7	528.6	520.8	513.2	504.5	497.4
10°	572.2	572.4	570.8	567.8	563.2	559.9	551.9	544.2	534.9	523.9	516.0
12.5°	591.0	591.8	589.6	585.7	583.4	576.1	569.7	560.6	549.5	540.7	528.8
15°	621.2	619.2	617.8	612.8	609.0	601.3	591.3	581.7	569.7	558.5	547.3
17.5°	650.5	652.1	649.4	644.8	632.9	623.9	610.5	597.4	582.3	567.4	554.1
20°	676.5	678.0	673.8	665.9	651.6	642.7	625.0	608.1	590.7	571.5	556.8
22.5°	709.1	707.9	702.2	690.2	677.9	661.3	642.1	621.5	599.8	578.1	558.6
25°	764.4	756.7	753.2	738.4	722.2	697.8	671.5	641.4	614.3	585.6	560.7
27.5°	795.1	792.7	788.8	778.5	761.4	735.3	704.3	667.7	629.5	593.2	560.5
30°	788.9	789.3	789.6	786.4	775.4	755.8	724.8	685.6	640.1	599.3	561.6
32.5°	734.4	741.1	747.5	755.0	758.1	754.3	735.0	699.4	652.7	606.3	561.0
35°	613.5	615.6	636.3	656.8	684.6	706.2	720.6	704.9	665.6	612.3	560.3
37.5°	478.4	488.3	502.6	525.8	565.9	601.9	648.2	669.4	656.7	614.3	559.0
40°	407.8	417.0	426.4	450.0	483.8	527.4	579.9	624.7	635.2	608.1	554.6
42.5°	353.4	360.6	371.0	388.7	417.0	455.6	505.8	564.4	600.5	590.3	545.4
45°	289.2	293.8	301.8	315.9	336.4	366.6	410.9	475.0	530.8	549.3	523.6
47.5°	247.6	247.6	253.8	263.5	278.3	304.0	336.8	386.9	446.6	490.7	488.6
50°	224.4	223.5	228.5	236.9	248.6	265.6	296.9	337.0	394.3	444.3	458.2
52.5°	204.5	204.6	207.6	213.9	223.7	238.2	261.6	297.8	346.7	398.0	424.2
55°	178.3	177.5	181.0	185.2	192.4	201.9	218.7	246.4	286.1	336.6	370.7
57.5°	154.2	156.3	157.6	160.6	166.5	172.9	187.1	207.4	238.9	282.3	318.2
60°	140.2	142.2	143.3	146.2	151.0	156.5	167.5	183.9	210.5	247.9	283.5
62.5°	127.6	129.2	129.6	132.2	136.1	141.4	150.0	163.9	184.9	217.5	252.5
65°	109.5	109.5	110.2	113.0	114.8	119.5	126.1	136.2	153.0	178.5	208.3
67.5°	92.0	92.8	92.7	93.9	95.5	99.3	103.9	112.3	124.8	143.3	167.2
70°	80.6	81.3	81.1	82.0	83.8	86.2	90.1	97.9	106.9	122.8	143.3
72.5°	70.3	70.6	70.1	71.3	72.4	74.5	78.8	83.0	91.3	104.8	121.7
75°	53.8	54.2	54.6	55.3	56.4	57.5	59.7	63.8	69.4	79.5	90.2
77.5°	40.3	39.6	40.6	40.4	41.0	41.9	43.8	46.0	50.5	57.0	65.3
80°	30.4	30.6	30.6	30.7	31.7	32.2	33.8	35.5	39.0	43.7	49.6
82.5°	22.2	22.7	22.3	22.7	23.4	23.8	24.8	26.1	28.1	31.9	36.1
85°	12.1	11.2	11.6	11.9	11.9	12.1	12.8	13.4	14.5	15.9	17.6
87.5°	8.5	8.6	8.6	8.5	8.5	8.3	8.6	8.4	8.6	8.9	9.1
90°	24.6	23.9	23.2	22.6	21.9	21.0	19.8	18.7	17.6	16.4	14.8
92.5°	23.0	22.7	22.3	22.0	21.7	21.0	19.8	18.7	17.6	16.4	15.0
95°	21.5	21.5	21.5	21.5	21.5	21.0	19.8	18.7	17.6	16.4	25.0
97.5°	21.5	21.5	21.5	21.5	21.5	24.7	31.2	37.6	44.0	50.5	67.6
100°	21.5	22.4	23.4	24.2	25.2	42.6	76.6	110.5	144.5	178.5	177.5
102.5°	129.0	144.5	160.0	175.5	191.0	202.0	208.4	214.8	221.3	227.7	227.1
105°	304.6	304.8	305.1	305.3	305.5	305.6	305.6	305.6	305.6	305.6	305.6
107.5°	384.0	384.7	385.4	386.0	386.7	387.1	387.1	387.0	386.9	386.9	386.4
110°	439.0	438.8	438.6	438.3	438.1	438.3	439.0	439.7	440.4	441.0	440.6



TEST NUMBER: P333358-927

CATALOG NUMBER: S125DIW-S375D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	488.2	488.5	488.9	489.2	489.5	490.1	491.0	491.8	492.7	493.5	493.3
115°	562.1	563.4	564.8	566.2	567.5	568.7	569.6	570.5	571.4	572.4	572.1
117.5°	640.9	641.4	642.1	642.6	643.2	644.1	645.3	646.5	647.7	648.9	648.0
120°	689.3	690.4	691.5	692.7	693.8	694.6	695.1	695.5	696.0	696.4	695.8
122.5°	735.2	736.5	737.8	739.2	740.5	741.4	741.8	742.3	742.8	743.2	742.9
125°	805.2	805.8	806.5	807.2	807.9	808.7	809.6	810.5	811.4	812.3	812.3
127.5°	864.0	865.7	867.4	869.1	870.8	871.9	872.4	872.9	873.4	873.9	874.0
130°	906.7	907.8	908.9	910.1	911.2	912.2	912.8	913.5	914.3	914.9	914.7
132.5°	946.1	947.2	948.4	949.5	950.6	951.3	951.4	951.6	951.7	951.8	952.4
135°	1000.1	1001.4	1002.7	1004.2	1005.5	1006.4	1006.9	1007.3	1007.8	1008.2	1008.7
137.5°	1054.2	1055.3	1056.5	1057.7	1058.9	1059.5	1059.4	1059.3	1059.2	1059.1	1059.5
140°	1086.2	1087.6	1088.9	1090.3	1091.6	1092.1	1091.6	1091.2	1090.8	1090.3	1090.5
142.5°	1116.6	1117.9	1119.3	1120.6	1122.0	1122.7	1122.6	1122.4	1122.4	1122.3	1122.0
145°	1161.1	1162.4	1163.8	1165.1	1166.6	1167.1	1166.9	1166.6	1166.4	1166.2	1166.2
147.5°	1197.8	1199.4	1201.0	1202.7	1204.4	1205.1	1204.8	1204.5	1204.2	1204.0	1203.6
150°	1221.5	1223.4	1225.2	1227.0	1228.8	1229.5	1229.1	1228.7	1228.2	1227.7	1227.2
152.5°	1243.7	1245.4	1247.1	1248.6	1250.3	1250.9	1250.5	1250.0	1249.5	1249.0	1248.6
155°	1272.9	1274.7	1276.5	1278.3	1280.2	1280.7	1280.0	1279.4	1278.7	1278.0	1277.6
157.5°	1297.3	1299.1	1300.9	1302.7	1304.6	1305.1	1304.4	1303.7	1302.9	1302.2	1302.2
160°	1312.9	1314.7	1316.5	1318.3	1320.2	1320.6	1319.7	1318.8	1317.9	1317.0	1316.8
162.5°	1326.8	1328.8	1330.8	1332.8	1334.8	1335.2	1334.0	1332.6	1331.3	1330.1	1329.8
165°	1345.7	1347.5	1349.3	1351.1	1353.0	1353.2	1351.9	1350.4	1349.1	1347.7	1347.5
167.5°	1358.8	1360.9	1362.9	1364.9	1367.0	1367.2	1365.6	1364.0	1362.3	1360.7	1360.4
170°	1366.2	1368.3	1370.3	1372.4	1374.4	1374.5	1372.7	1370.9	1369.0	1367.2	1367.0
172.5°	1371.1	1373.2	1375.2	1377.3	1379.3	1379.5	1377.9	1376.3	1374.6	1372.9	1372.5
175°	1377.4	1379.5	1381.6	1383.6	1385.7	1385.8	1383.9	1382.1	1380.3	1378.5	1378.3
177.5°	1381.2	1382.6	1384.1	1385.5	1387.0	1387.1	1385.8	1384.6	1383.3	1382.0	1381.8
180°	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6



TEST NUMBER: P333358-927

CATALOG NUMBER: S125DIW-S375D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3
2.5°	443.7	442.7	441.5	439.4	437.0	435.6	433.6	432.3	429.7	427.5	425.1
5°	466.2	461.4	457.1	451.4	445.2	441.2	436.4	431.1	425.6	419.9	413.7
7.5°	489.6	481.1	472.0	462.2	452.5	443.6	435.1	426.9	419.1	409.7	401.8
10°	505.2	494.6	483.2	469.9	456.9	445.5	434.0	424.0	413.7	402.7	393.0
12.5°	520.9	506.8	490.7	476.0	460.4	446.7	433.2	420.3	407.4	395.2	383.9
15°	532.0	519.5	504.7	483.8	466.2	447.3	429.4	412.8	397.2	383.7	369.4
17.5°	539.2	523.2	507.2	487.3	464.2	443.1	422.8	403.7	386.2	369.0	355.3
20°	540.5	524.0	507.4	487.8	464.2	440.1	419.7	396.9	378.0	360.2	343.4
22.5°	540.1	521.4	503.3	483.2	460.1	437.8	413.3	390.0	369.5	352.0	334.5
25°	536.0	516.0	493.3	473.0	450.3	426.7	401.8	377.6	356.8	336.8	319.4
27.5°	532.5	506.7	480.9	457.2	435.3	413.7	389.8	365.1	342.0	321.8	305.4
30°	528.3	499.9	471.0	446.2	423.7	402.7	380.2	356.0	331.8	312.1	294.5
32.5°	524.5	491.4	460.9	434.0	410.1	389.7	368.9	345.9	322.2	302.1	284.6
35°	517.1	478.9	443.9	413.5	388.1	367.0	349.6	328.2	306.4	287.0	270.2
37.5°	507.8	462.4	424.8	393.0	365.1	342.9	326.8	310.3	289.4	270.7	255.5
40°	500.4	450.7	410.9	378.3	349.4	326.4	311.3	295.8	278.5	261.0	244.9
42.5°	491.2	440.1	396.9	361.8	333.2	310.7	294.9	281.8	266.4	250.2	235.3
45°	474.3	421.0	374.1	336.4	307.5	285.3	269.1	259.2	247.6	232.3	219.7
47.5°	449.3	398.1	349.6	310.7	280.8	260.3	245.0	235.5	227.4	216.0	204.5
50°	427.2	381.0	331.8	293.3	263.4	242.7	228.6	220.0	213.1	204.3	194.6
52.5°	402.5	359.4	314.4	276.2	246.7	226.3	212.5	204.9	199.2	192.9	183.3
55°	363.1	326.5	284.8	248.6	221.3	201.4	189.3	182.7	177.9	173.2	167.3
57.5°	319.9	291.2	254.3	221.1	196.0	177.8	166.6	160.2	156.5	154.0	150.6
60°	289.4	264.9	233.1	202.8	178.3	162.2	151.2	146.2	143.1	141.2	138.6
62.5°	261.1	241.0	211.5	183.9	162.5	147.3	137.4	132.6	129.7	128.7	126.6
65°	219.5	203.9	179.6	156.7	138.4	125.4	117.2	112.6	110.7	109.6	109.8
67.5°	178.4	169.0	149.4	129.9	115.3	104.4	97.8	94.3	93.3	91.9	91.9
70°	153.4	146.2	129.8	112.7	99.7	91.3	85.5	81.8	80.9	80.2	80.0
72.5°	131.3	125.0	110.7	97.1	85.4	78.0	73.2	71.0	69.5	69.1	69.0
75°	98.6	95.2	83.8	73.0	65.0	59.9	56.6	54.6	53.5	53.2	53.5
77.5°	70.1	67.1	59.9	52.2	47.1	43.3	40.5	39.8	38.6	38.6	38.4
80°	52.7	50.7	46.1	40.1	35.9	32.6	31.1	29.9	29.5	28.9	29.5
82.5°	38.2	36.0	33.0	29.1	25.6	23.7	22.2	21.8	21.5	21.3	21.4
85°	18.9	19.0	17.2	14.3	12.8	11.7	10.8	10.8	10.6	10.5	10.6
87.5°	9.1	8.5	7.6	6.8	5.7	4.9	4.4	4.2	4.1	4.3	4.8
90°	13.2	11.6	10.1	8.3	6.5	4.7	2.9	1.0	2.9	4.7	6.5
92.5°	13.5	12.2	10.8	10.7	12.0	13.2	14.5	15.8	14.5	13.2	12.0
95°	33.7	42.4	51.0	55.7	56.4	57.1	57.8	58.5	57.8	57.1	56.4
97.5°	84.8	101.9	119.0	127.0	125.7	124.5	123.3	122.1	123.3	124.5	125.7
100°	176.7	175.7	174.8	174.0	173.3	172.6	172.0	171.3	172.0	172.6	173.3
102.5°	226.6	226.1	225.5	224.8	223.9	223.1	222.2	221.3	222.2	223.1	223.9
105°	305.6	305.6	305.6	305.2	304.3	303.4	302.5	301.6	302.5	303.4	304.3
107.5°	386.0	385.6	385.1	384.8	384.8	384.8	384.8	384.8	384.8	384.8	384.8
110°	440.1	439.7	439.2	439.0	439.0	439.0	439.0	439.0	439.0	439.0	439.0



TEST NUMBER: P333358-927

CATALOG NUMBER: S125DIW-S375D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	493.0	492.7	492.5	492.0	491.5	491.0	490.4	489.9	490.4	491.0	491.5
115°	571.9	571.6	571.4	570.8	569.6	568.5	567.3	566.2	567.3	568.5	569.6
117.5°	647.1	646.3	645.4	645.0	645.0	645.1	645.1	645.2	645.1	645.1	645.0
120°	695.1	694.3	693.7	693.5	693.7	694.0	694.2	694.3	694.2	694.0	693.7
122.5°	742.6	742.3	742.0	741.3	740.5	739.6	738.7	737.8	738.7	739.6	740.5
125°	812.3	812.3	812.3	811.5	809.9	808.3	806.8	805.2	806.8	808.3	809.9
127.5°	874.2	874.3	874.4	873.9	872.7	871.6	870.5	869.3	870.5	871.6	872.7
130°	914.4	914.3	914.0	913.3	912.2	911.0	909.9	908.7	909.9	911.0	912.2
132.5°	952.8	953.3	953.9	953.4	952.1	950.8	949.4	948.2	949.4	950.8	952.1
135°	1009.2	1009.6	1010.0	1009.6	1008.2	1006.9	1005.5	1004.2	1005.5	1006.9	1008.2
137.5°	1059.9	1060.3	1060.7	1060.3	1059.1	1058.0	1056.8	1055.7	1056.8	1058.0	1059.1
140°	1090.8	1091.0	1091.2	1091.1	1090.6	1090.2	1089.7	1089.3	1089.7	1090.2	1090.6
142.5°	1121.7	1121.3	1121.0	1120.7	1120.5	1120.1	1119.9	1119.6	1119.9	1120.1	1120.5
145°	1166.2	1166.2	1166.2	1165.9	1165.5	1165.1	1164.6	1164.1	1164.6	1165.1	1165.5
147.5°	1203.4	1203.1	1202.8	1202.8	1202.8	1202.9	1203.0	1203.1	1203.0	1202.9	1202.8
150°	1226.9	1226.4	1225.9	1225.9	1226.4	1226.9	1227.2	1227.7	1227.2	1226.9	1226.4
152.5°	1248.2	1247.7	1247.2	1247.5	1248.6	1249.5	1250.5	1251.5	1250.5	1249.5	1248.6
155°	1277.1	1276.6	1276.2	1276.6	1278.0	1279.4	1280.7	1282.1	1280.7	1279.4	1278.0
157.5°	1302.1	1302.0	1302.0	1302.4	1303.2	1304.0	1304.9	1305.7	1304.9	1304.0	1303.2
160°	1316.5	1316.3	1316.1	1316.6	1318.0	1319.4	1320.7	1322.1	1320.7	1319.4	1318.0
162.5°	1329.7	1329.4	1329.2	1329.8	1331.1	1332.5	1333.9	1335.2	1333.9	1332.5	1331.1
165°	1347.3	1347.0	1346.8	1347.4	1348.8	1350.1	1351.5	1352.9	1351.5	1350.1	1348.8
167.5°	1360.2	1359.9	1359.8	1360.3	1361.8	1363.2	1364.6	1366.0	1364.6	1363.2	1361.8
170°	1366.8	1366.5	1366.3	1367.0	1368.6	1370.2	1371.8	1373.4	1371.8	1370.2	1368.6
172.5°	1372.1	1371.7	1371.3	1371.9	1373.5	1375.1	1376.7	1378.3	1376.7	1375.1	1373.5
175°	1378.1	1377.8	1377.6	1378.2	1379.5	1380.9	1382.3	1383.6	1382.3	1380.9	1379.5
177.5°	1381.6	1381.5	1381.2	1381.7	1382.8	1383.9	1385.0	1386.1	1385.0	1383.9	1382.8
180°	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6



TEST NUMBER: P333358-927

CATALOG NUMBER: S125DIW-S375D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3
2.5°	423.8	422.2	420.9	418.0	416.3	414.2	412.4	414.3	412.3	413.1	411.8
5°	410.6	405.4	401.8	396.5	391.9	387.7	384.6	384.0	382.5	381.8	379.6
7.5°	394.7	388.2	382.0	375.0	369.2	363.2	359.4	356.2	354.2	351.4	349.5
10°	385.3	376.7	369.4	361.0	353.6	347.2	342.1	339.5	337.2	333.7	332.4
12.5°	373.8	364.9	355.9	346.9	339.8	332.7	328.4	324.5	322.8	318.9	318.5
15°	359.9	346.5	337.7	328.6	318.9	313.0	309.3	305.1	303.3	300.6	298.6
17.5°	343.3	331.4	320.4	310.9	302.6	297.7	293.1	290.3	287.1	285.3	282.0
20°	331.3	320.0	309.0	298.9	292.5	286.8	283.2	280.4	277.1	276.2	272.9
22.5°	321.2	308.7	298.2	289.7	282.7	276.3	272.4	270.5	268.2	265.4	264.7
25°	304.8	291.8	282.8	274.4	268.2	262.3	259.6	257.2	255.0	252.9	252.2
27.5°	290.6	278.9	268.3	260.7	255.2	249.9	247.6	244.6	243.0	241.4	239.4
30°	280.6	268.7	259.4	252.1	246.2	241.5	238.8	236.9	235.4	233.9	232.8
32.5°	270.4	259.4	250.3	243.1	237.3	233.7	231.4	230.0	228.4	226.6	225.2
35°	256.8	244.7	235.9	229.7	225.1	222.4	219.8	218.6	216.7	216.7	215.2
37.5°	241.5	231.1	223.3	217.7	213.6	211.1	208.3	207.5	206.3	205.5	205.0
40°	232.5	222.8	215.5	209.8	205.4	203.4	201.1	199.7	199.0	198.0	197.7
42.5°	223.1	213.8	206.8	201.6	197.7	196.1	194.0	193.0	191.5	190.3	190.0
45°	208.8	199.9	193.5	189.3	186.0	183.9	182.7	180.5	179.7	178.3	178.1
47.5°	195.4	186.7	180.5	177.0	174.1	172.5	170.5	168.3	167.4	166.7	166.6
50°	185.2	177.4	171.5	168.3	165.5	163.1	161.1	159.6	159.1	159.1	159.5
52.5°	175.0	168.3	163.3	159.3	156.7	154.2	152.3	151.4	150.6	151.5	152.1
55°	160.0	153.2	149.6	145.7	143.1	140.2	139.3	138.9	138.4	139.8	140.6
57.5°	144.1	139.3	135.1	131.3	129.0	127.2	126.0	125.8	126.8	127.5	129.9
60°	134.0	128.5	124.7	121.8	119.0	117.9	117.5	117.2	117.9	119.9	123.0
62.5°	122.9	118.4	114.2	112.1	110.0	108.2	108.1	108.4	109.8	112.2	115.3
65°	106.5	102.7	100.0	97.4	95.7	94.7	95.0	95.7	97.4	100.5	103.9
67.5°	89.9	87.3	84.8	82.8	81.2	81.2	81.6	82.7	84.6	88.2	91.3
70°	79.3	76.4	74.3	73.4	72.1	71.4	72.5	74.3	76.0	79.3	82.0
72.5°	68.6	66.1	64.5	63.8	63.3	62.7	63.1	65.1	67.3	70.6	73.8
75°	52.7	51.8	50.7	50.0	49.4	49.8	50.1	52.0	53.8	57.3	60.9
77.5°	38.5	37.5	36.8	36.7	36.4	36.6	37.6	39.0	40.7	43.3	46.0
80°	29.1	28.8	28.4	28.2	28.2	28.4	29.9	30.7	32.4	34.8	37.0
82.5°	21.2	21.0	20.9	20.8	21.0	21.1	21.9	23.1	24.5	26.3	28.2
85°	11.2	10.8	11.3	11.6	11.2	11.7	12.1	12.8	13.4	14.3	15.2
87.5°	5.3	5.9	6.1	6.6	6.9	7.5	7.6	8.4	9.0	9.4	9.5
90°	8.3	10.1	11.6	13.2	14.8	16.4	17.6	18.7	19.8	21.0	21.9
92.5°	10.7	10.8	12.2	13.5	15.0	16.4	17.6	18.7	19.8	21.0	21.7
95°	55.7	51.0	42.4	33.7	25.0	16.4	17.6	18.7	19.8	21.0	21.5
97.5°	127.0	119.0	101.9	84.8	67.6	50.5	44.0	37.6	31.2	24.7	21.5
100°	174.0	174.8	175.7	176.7	177.5	178.5	144.5	110.5	76.6	42.6	25.2
102.5°	224.8	225.5	226.1	226.6	227.1	227.7	221.3	214.8	208.4	202.0	191.0
105°	305.2	305.6	305.6	305.6	305.6	305.6	305.6	305.6	305.6	305.6	305.5
107.5°	384.8	385.1	385.6	386.0	386.4	386.9	386.9	387.0	387.1	387.1	386.7
110°	439.0	439.2	439.7	440.1	440.6	441.0	440.4	439.7	439.0	438.3	438.1



TEST NUMBER: P333358-927

CATALOG NUMBER: S125DIW-S375D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	492.0	492.5	492.7	493.0	493.3	493.5	492.7	491.8	491.0	490.1	489.5
115°	570.8	571.4	571.6	571.9	572.1	572.4	571.4	570.5	569.6	568.7	567.5
117.5°	645.0	645.4	646.3	647.1	648.0	648.9	647.7	646.5	645.3	644.1	643.2
120°	693.5	693.7	694.3	695.1	695.8	696.4	696.0	695.5	695.1	694.6	693.8
122.5°	741.3	742.0	742.3	742.6	742.9	743.2	742.8	742.3	741.8	741.4	740.5
125°	811.5	812.3	812.3	812.3	812.3	812.3	811.4	810.5	809.6	808.7	807.9
127.5°	873.9	874.4	874.3	874.2	874.0	873.9	873.4	872.9	872.4	871.9	870.8
130°	913.3	914.0	914.3	914.4	914.7	914.9	914.3	913.5	912.8	912.2	911.2
132.5°	953.4	953.9	953.3	952.8	952.4	951.8	951.7	951.6	951.4	951.3	950.6
135°	1009.6	1010.0	1009.6	1009.2	1008.7	1008.2	1007.8	1007.3	1006.9	1006.4	1005.5
137.5°	1060.3	1060.7	1060.3	1059.9	1059.5	1059.1	1059.2	1059.3	1059.4	1059.5	1058.9
140°	1091.1	1091.2	1091.0	1090.8	1090.5	1090.3	1090.8	1091.2	1091.6	1092.1	1091.6
142.5°	1120.7	1121.0	1121.3	1121.7	1122.0	1122.3	1122.4	1122.4	1122.6	1122.7	1122.0
145°	1165.9	1166.2	1166.2	1166.2	1166.2	1166.2	1166.4	1166.6	1166.9	1167.1	1166.6
147.5°	1202.8	1202.8	1203.1	1203.4	1203.6	1204.0	1204.2	1204.5	1204.8	1205.1	1204.4
150°	1225.9	1225.9	1226.4	1226.9	1227.2	1227.7	1228.2	1228.7	1229.1	1229.5	1228.8
152.5°	1247.5	1247.2	1247.7	1248.2	1248.6	1249.0	1249.5	1250.0	1250.5	1250.9	1250.3
155°	1276.6	1276.2	1276.6	1277.1	1277.6	1278.0	1278.7	1279.4	1280.0	1280.7	1280.2
157.5°	1302.4	1302.0	1302.0	1302.1	1302.2	1302.2	1302.9	1303.7	1304.4	1305.1	1304.6
160°	1316.6	1316.1	1316.3	1316.5	1316.8	1317.0	1317.9	1318.8	1319.7	1320.6	1320.2
162.5°	1329.8	1329.2	1329.4	1329.7	1329.8	1330.1	1331.3	1332.6	1334.0	1335.2	1334.8
165°	1347.4	1346.8	1347.0	1347.3	1347.5	1347.7	1349.1	1350.4	1351.9	1353.2	1353.0
167.5°	1360.3	1359.8	1359.9	1360.2	1360.4	1360.7	1362.3	1364.0	1365.6	1367.2	1367.0
170°	1367.0	1366.3	1366.5	1366.8	1367.0	1367.2	1369.0	1370.9	1372.7	1374.5	1374.4
172.5°	1371.9	1371.3	1371.7	1372.1	1372.5	1372.9	1374.6	1376.3	1377.9	1379.5	1379.3
175°	1378.2	1377.6	1377.8	1378.1	1378.3	1378.5	1380.3	1382.1	1383.9	1385.8	1385.7
177.5°	1381.7	1381.2	1381.5	1381.6	1381.8	1382.0	1383.3	1384.6	1385.8	1387.1	1387.0
180°	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6



TEST NUMBER: P333358-927

CATALOG NUMBER: S125DIW-S375D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3
2.5°	410.9	411.9	411.1	412.3	411.1	411.9	410.9	411.8	413.1	412.3	414.3
5°	378.7	377.1	378.2	377.5	378.2	377.1	378.7	379.6	381.8	382.5	384.0
7.5°	349.0	347.5	345.6	344.8	345.6	347.5	349.0	349.5	351.4	354.2	356.2
10°	330.4	328.4	328.2	326.9	328.2	328.4	330.4	332.4	333.7	337.2	339.5
12.5°	316.8	314.9	312.8	312.3	312.8	314.9	316.8	318.5	318.9	322.8	324.5
15°	297.5	296.0	294.7	295.8	294.7	296.0	297.5	298.6	300.6	303.3	305.1
17.5°	281.4	280.2	280.0	278.6	280.0	280.2	281.4	282.0	285.3	287.1	290.3
20°	271.2	270.4	270.8	268.3	270.8	270.4	271.2	272.9	276.2	277.1	280.4
22.5°	263.2	261.4	261.2	260.7	261.2	261.4	263.2	264.7	265.4	268.2	270.5
25°	250.6	249.7	248.7	249.7	248.7	249.7	250.6	252.2	252.9	255.0	257.2
27.5°	239.6	238.4	238.2	238.4	238.2	238.4	239.6	239.4	241.4	243.0	244.6
30°	232.8	231.0	231.2	231.0	231.2	231.0	232.8	232.8	233.9	235.4	236.9
32.5°	225.5	224.3	224.0	223.7	224.0	224.3	225.5	225.2	226.6	228.4	230.0
35°	214.7	214.7	213.8	213.8	213.8	214.7	214.7	215.2	216.7	216.7	218.6
37.5°	204.5	204.4	203.8	203.9	203.8	204.4	204.5	205.0	205.5	206.3	207.5
40°	196.9	196.8	196.2	195.1	196.2	196.8	196.9	197.7	198.0	199.0	199.7
42.5°	189.6	189.0	188.8	188.4	188.8	189.0	189.6	190.0	190.3	191.5	193.0
45°	178.1	178.1	177.8	177.5	177.8	178.1	178.1	178.1	178.3	179.7	180.5
47.5°	166.9	167.2	167.9	167.8	167.9	167.2	166.9	166.6	166.7	167.4	168.3
50°	160.2	160.3	160.9	161.1	160.9	160.3	160.2	159.5	159.1	159.1	159.6
52.5°	152.7	153.8	154.5	154.3	154.5	153.8	152.7	152.1	151.5	150.6	151.4
55°	142.2	143.5	144.8	145.0	144.8	143.5	142.2	140.6	139.8	138.4	138.9
57.5°	131.9	133.6	135.0	135.5	135.0	133.6	131.9	129.9	127.5	126.8	125.8
60°	124.8	127.2	128.9	129.6	128.9	127.2	124.8	123.0	119.9	117.9	117.2
62.5°	118.1	120.8	122.4	122.6	122.4	120.8	118.1	115.3	112.2	109.8	108.4
65°	107.1	109.8	111.3	112.4	111.3	109.8	107.1	103.9	100.5	97.4	95.7
67.5°	95.2	98.0	99.6	100.4	99.6	98.0	95.2	91.3	88.2	84.6	82.7
70°	86.6	89.4	91.5	92.3	91.5	89.4	86.6	82.0	79.3	76.0	74.3
72.5°	78.1	80.6	82.3	83.2	82.3	80.6	78.1	73.8	70.6	67.3	65.1
75°	63.3	66.6	68.3	69.2	68.3	66.6	63.3	60.9	57.3	53.8	52.0
77.5°	48.8	51.8	52.8	53.3	52.8	51.8	48.8	46.0	43.3	40.7	39.0
80°	39.1	41.0	42.3	42.5	42.3	41.0	39.1	37.0	34.8	32.4	30.7
82.5°	30.1	31.6	32.0	32.5	32.0	31.6	30.1	28.2	26.3	24.5	23.1
85°	16.5	17.2	17.4	17.2	17.4	17.2	16.5	15.2	14.3	13.4	12.8
87.5°	9.9	9.9	10.1	10.5	10.1	9.9	9.9	9.5	9.4	9.0	8.4
90°	22.6	23.2	23.9	24.6	23.9	23.2	22.6	21.9	21.0	19.8	18.7
92.5°	22.0	22.3	22.7	23.0	22.7	22.3	22.0	21.7	21.0	19.8	18.7
95°	21.5	21.5	21.5	21.5	21.5	21.5	21.5	21.5	21.0	19.8	18.7
97.5°	21.5	21.5	21.5	21.5	21.5	21.5	21.5	21.5	24.7	31.2	37.6
100°	24.2	23.4	22.4	21.5	22.4	23.4	24.2	25.2	42.6	76.6	110.5
102.5°	175.5	160.0	144.5	129.0	144.5	160.0	175.5	191.0	202.0	208.4	214.8
105°	305.3	305.1	304.8	304.6	304.8	305.1	305.3	305.5	305.6	305.6	305.6
107.5°	386.0	385.4	384.7	384.0	384.7	385.4	386.0	386.7	387.1	387.1	387.0
110°	438.3	438.6	438.8	439.0	438.8	438.6	438.3	438.1	438.3	439.0	439.7



TEST NUMBER: P333358-927

CATALOG NUMBER: S125DIW-S375D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	489.2	488.9	488.5	488.2	488.5	488.9	489.2	489.5	490.1	491.0	491.8
115°	566.2	564.8	563.4	562.1	563.4	564.8	566.2	567.5	568.7	569.6	570.5
117.5°	642.6	642.1	641.4	640.9	641.4	642.1	642.6	643.2	644.1	645.3	646.5
120°	692.7	691.5	690.4	689.3	690.4	691.5	692.7	693.8	694.6	695.1	695.5
122.5°	739.2	737.8	736.5	735.2	736.5	737.8	739.2	740.5	741.4	741.8	742.3
125°	807.2	806.5	805.8	805.2	805.8	806.5	807.2	807.9	808.7	809.6	810.5
127.5°	869.1	867.4	865.7	864.0	865.7	867.4	869.1	870.8	871.9	872.4	872.9
130°	910.1	908.9	907.8	906.7	907.8	908.9	910.1	911.2	912.2	912.8	913.5
132.5°	949.5	948.4	947.2	946.1	947.2	948.4	949.5	950.6	951.3	951.4	951.6
135°	1004.2	1002.7	1001.4	1000.1	1001.4	1002.7	1004.2	1005.5	1006.4	1006.9	1007.3
137.5°	1057.7	1056.5	1055.3	1054.2	1055.3	1056.5	1057.7	1058.9	1059.5	1059.4	1059.3
140°	1090.3	1088.9	1087.6	1086.2	1087.6	1088.9	1090.3	1091.6	1092.1	1091.6	1091.2
142.5°	1120.6	1119.3	1117.9	1116.6	1117.9	1119.3	1120.6	1122.0	1122.7	1122.6	1122.4
145°	1165.1	1163.8	1162.4	1161.1	1162.4	1163.8	1165.1	1166.6	1167.1	1166.9	1166.6
147.5°	1202.7	1201.0	1199.4	1197.8	1199.4	1201.0	1202.7	1204.4	1205.1	1204.8	1204.5
150°	1227.0	1225.2	1223.4	1221.5	1223.4	1225.2	1227.0	1228.8	1229.5	1229.1	1228.7
152.5°	1248.6	1247.1	1245.4	1243.7	1245.4	1247.1	1248.6	1250.3	1250.9	1250.5	1250.0
155°	1278.3	1276.5	1274.7	1272.9	1274.7	1276.5	1278.3	1280.2	1280.7	1280.0	1279.4
157.5°	1302.7	1300.9	1299.1	1297.3	1299.1	1300.9	1302.7	1304.6	1305.1	1304.4	1303.7
160°	1318.3	1316.5	1314.7	1312.9	1314.7	1316.5	1318.3	1320.2	1320.6	1319.7	1318.8
162.5°	1332.8	1330.8	1328.8	1326.8	1328.8	1330.8	1332.8	1334.8	1335.2	1334.0	1332.6
165°	1351.1	1349.3	1347.5	1345.7	1347.5	1349.3	1351.1	1353.0	1353.2	1351.9	1350.4
167.5°	1364.9	1362.9	1360.9	1358.8	1360.9	1362.9	1364.9	1367.0	1367.2	1365.6	1364.0
170°	1372.4	1370.3	1368.3	1366.2	1368.3	1370.3	1372.4	1374.4	1374.5	1372.7	1370.9
172.5°	1377.3	1375.2	1373.2	1371.1	1373.2	1375.2	1377.3	1379.3	1379.5	1377.9	1376.3
175°	1383.6	1381.6	1379.5	1377.4	1379.5	1381.6	1383.6	1385.7	1385.8	1383.9	1382.1
177.5°	1385.5	1384.1	1382.6	1381.2	1382.6	1384.1	1385.5	1387.0	1387.1	1385.8	1384.6
180°	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6



TEST NUMBER: P333358-927

CATALOG NUMBER: S125DIW-S375D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3
2.5°	412.4	414.2	416.3	418.0	420.9	422.2	423.8	425.1	427.5	429.7	432.3
5°	384.6	387.7	391.9	396.5	401.8	405.4	410.6	413.7	419.9	425.6	431.1
7.5°	359.4	363.2	369.2	375.0	382.0	388.2	394.7	401.8	409.7	419.1	426.9
10°	342.1	347.2	353.6	361.0	369.4	376.7	385.3	393.0	402.7	413.7	424.0
12.5°	328.4	332.7	339.8	346.9	355.9	364.9	373.8	383.9	395.2	407.4	420.3
15°	309.3	313.0	318.9	328.6	337.7	346.5	359.9	369.4	383.7	397.2	412.8
17.5°	293.1	297.7	302.6	310.9	320.4	331.4	343.3	355.3	369.0	386.2	403.7
20°	283.2	286.8	292.5	298.9	309.0	320.0	331.3	343.4	360.2	378.0	396.9
22.5°	272.4	276.3	282.7	289.7	298.2	308.7	321.2	334.5	352.0	369.5	390.0
25°	259.6	262.3	268.2	274.4	282.8	291.8	304.8	319.4	336.8	356.8	377.6
27.5°	247.6	249.9	255.2	260.7	268.3	278.9	290.6	305.4	321.8	342.0	365.1
30°	238.8	241.5	246.2	252.1	259.4	268.7	280.6	294.5	312.1	331.8	356.0
32.5°	231.4	233.7	237.3	243.1	250.3	259.4	270.4	284.6	302.1	322.2	345.9
35°	219.8	222.4	225.1	229.7	235.9	244.7	256.8	270.2	287.0	306.4	328.2
37.5°	208.3	211.1	213.6	217.7	223.3	231.1	241.5	255.5	270.7	289.4	310.3
40°	201.1	203.4	205.4	209.8	215.5	222.8	232.5	244.9	261.0	278.5	295.8
42.5°	194.0	196.1	197.7	201.6	206.8	213.8	223.1	235.3	250.2	266.4	281.8
45°	182.7	183.9	186.0	189.3	193.5	199.9	208.8	219.7	232.3	247.6	259.2
47.5°	170.5	172.5	174.1	177.0	180.5	186.7	195.4	204.5	216.0	227.4	235.5
50°	161.1	163.1	165.5	168.3	171.5	177.4	185.2	194.6	204.3	213.1	220.0
52.5°	152.3	154.2	156.7	159.3	163.3	168.3	175.0	183.3	192.9	199.2	204.9
55°	139.3	140.2	143.1	145.7	149.6	153.2	160.0	167.3	173.2	177.9	182.7
57.5°	126.0	127.2	129.0	131.3	135.1	139.3	144.1	150.6	154.0	156.5	160.2
60°	117.5	117.9	119.0	121.8	124.7	128.5	134.0	138.6	141.2	143.1	146.2
62.5°	108.1	108.2	110.0	112.1	114.2	118.4	122.9	126.6	128.7	129.7	132.6
65°	95.0	94.7	95.7	97.4	100.0	102.7	106.5	109.8	109.6	110.7	112.6
67.5°	81.6	81.2	81.2	82.8	84.8	87.3	89.9	91.9	91.9	93.3	94.3
70°	72.5	71.4	72.1	73.4	74.3	76.4	79.3	80.0	80.2	80.9	81.8
72.5°	63.1	62.7	63.3	63.8	64.5	66.1	68.6	69.0	69.1	69.5	71.0
75°	50.1	49.8	49.4	50.0	50.7	51.8	52.7	53.5	53.2	53.5	54.6
77.5°	37.6	36.6	36.4	36.7	36.8	37.5	38.5	38.4	38.6	38.6	39.8
80°	29.9	28.4	28.2	28.2	28.4	28.8	29.1	29.5	28.9	29.5	29.9
82.5°	21.9	21.1	21.0	20.8	20.9	21.0	21.2	21.4	21.3	21.5	21.8
85°	12.1	11.7	11.2	11.6	11.3	10.8	11.2	10.6	10.5	10.6	10.8
87.5°	7.6	7.5	6.9	6.6	6.1	5.9	5.3	4.8	4.3	4.1	4.2
90°	17.6	16.4	14.8	13.2	11.6	10.1	8.3	6.5	4.7	2.9	1.0
92.5°	17.6	16.4	15.0	13.5	12.2	10.8	10.7	12.0	13.2	14.5	15.8
95°	17.6	16.4	25.0	33.7	42.4	51.0	55.7	56.4	57.1	57.8	58.5
97.5°	44.0	50.5	67.6	84.8	101.9	119.0	127.0	125.7	124.5	123.3	122.1
100°	144.5	178.5	177.5	176.7	175.7	174.8	174.0	173.3	172.6	172.0	171.3
102.5°	221.3	227.7	227.1	226.6	226.1	225.5	224.8	223.9	223.1	222.2	221.3
105°	305.6	305.6	305.6	305.6	305.6	305.6	305.2	304.3	303.4	302.5	301.6
107.5°	386.9	386.9	386.4	386.0	385.6	385.1	384.8	384.8	384.8	384.8	384.8
110°	440.4	441.0	440.6	440.1	439.7	439.2	439.0	439.0	439.0	439.0	439.0



TEST NUMBER: P333358-927

CATALOG NUMBER: S125DIW-S375D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	492.7	493.5	493.3	493.0	492.7	492.5	492.0	491.5	491.0	490.4	489.9
115°	571.4	572.4	572.1	571.9	571.6	571.4	570.8	569.6	568.5	567.3	566.2
117.5°	647.7	648.9	648.0	647.1	646.3	645.4	645.0	645.0	645.1	645.1	645.2
120°	696.0	696.4	695.8	695.1	694.3	693.7	693.5	693.7	694.0	694.2	694.3
122.5°	742.8	743.2	742.9	742.6	742.3	742.0	741.3	740.5	739.6	738.7	737.8
125°	811.4	812.3	812.3	812.3	812.3	812.3	811.5	809.9	808.3	806.8	805.2
127.5°	873.4	873.9	874.0	874.2	874.3	874.4	873.9	872.7	871.6	870.5	869.3
130°	914.3	914.9	914.7	914.4	914.3	914.0	913.3	912.2	911.0	909.9	908.7
132.5°	951.7	951.8	952.4	952.8	953.3	953.9	953.4	952.1	950.8	949.4	948.2
135°	1007.8	1008.2	1008.7	1009.2	1009.6	1010.0	1009.6	1008.2	1006.9	1005.5	1004.2
137.5°	1059.2	1059.1	1059.5	1059.9	1060.3	1060.7	1060.3	1059.1	1058.0	1056.8	1055.7
140°	1090.8	1090.3	1090.5	1090.8	1091.0	1091.2	1091.1	1090.6	1090.2	1089.7	1089.3
142.5°	1122.4	1122.3	1122.0	1121.7	1121.3	1121.0	1120.7	1120.5	1120.1	1119.9	1119.6
145°	1166.4	1166.2	1166.2	1166.2	1166.2	1166.2	1165.9	1165.5	1165.1	1164.6	1164.1
147.5°	1204.2	1204.0	1203.6	1203.4	1203.1	1202.8	1202.8	1202.8	1202.9	1203.0	1203.1
150°	1228.2	1227.7	1227.2	1226.9	1226.4	1225.9	1225.9	1226.4	1226.9	1227.2	1227.7
152.5°	1249.5	1249.0	1248.6	1248.2	1247.7	1247.2	1247.5	1248.6	1249.5	1250.5	1251.5
155°	1278.7	1278.0	1277.6	1277.1	1276.6	1276.2	1276.6	1278.0	1279.4	1280.7	1282.1
157.5°	1302.9	1302.2	1302.2	1302.1	1302.0	1302.0	1302.4	1303.2	1304.0	1304.9	1305.7
160°	1317.9	1317.0	1316.8	1316.5	1316.3	1316.1	1316.6	1318.0	1319.4	1320.7	1322.1
162.5°	1331.3	1330.1	1329.8	1329.7	1329.4	1329.2	1329.8	1331.1	1332.5	1333.9	1335.2
165°	1349.1	1347.7	1347.5	1347.3	1347.0	1346.8	1347.4	1348.8	1350.1	1351.5	1352.9
167.5°	1362.3	1360.7	1360.4	1360.2	1359.9	1359.8	1360.3	1361.8	1363.2	1364.6	1366.0
170°	1369.0	1367.2	1367.0	1366.8	1366.5	1366.3	1367.0	1368.6	1370.2	1371.8	1373.4
172.5°	1374.6	1372.9	1372.5	1372.1	1371.7	1371.3	1371.9	1373.5	1375.1	1376.7	1378.3
175°	1380.3	1378.5	1378.3	1378.1	1377.8	1377.6	1378.2	1379.5	1380.9	1382.3	1383.6
177.5°	1383.3	1382.0	1381.8	1381.6	1381.5	1381.2	1381.7	1382.8	1383.9	1385.0	1386.1
180°	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6



TEST NUMBER: P333358-927

CATALOG NUMBER: S125DIW-S375D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3
2.5°	433.6	435.6	437.0	439.4	441.5	442.7	443.7	444.6	445.6	446.5	449.0
5°	436.4	441.2	445.2	451.4	457.1	461.4	466.2	470.4	473.9	478.9	482.7
7.5°	435.1	443.6	452.5	462.2	472.0	481.1	489.6	497.4	504.5	513.2	520.8
10°	434.0	445.5	456.9	469.9	483.2	494.6	505.2	516.0	523.9	534.9	544.2
12.5°	433.2	446.7	460.4	476.0	490.7	506.8	520.9	528.8	540.7	549.5	560.6
15°	429.4	447.3	466.2	483.8	504.7	519.5	532.0	547.3	558.5	569.7	581.7
17.5°	422.8	443.1	464.2	487.3	507.2	523.2	539.2	554.1	567.4	582.3	597.4
20°	419.7	440.1	464.2	487.8	507.4	524.0	540.5	556.8	571.5	590.7	608.1
22.5°	413.3	437.8	460.1	483.2	503.3	521.4	540.1	558.6	578.1	599.8	621.5
25°	401.8	426.7	450.3	473.0	493.3	516.0	536.0	560.7	585.6	614.3	641.4
27.5°	389.8	413.7	435.3	457.2	480.9	506.7	532.5	560.5	593.2	629.5	667.7
30°	380.2	402.7	423.7	446.2	471.0	499.9	528.3	561.6	599.3	640.1	685.6
32.5°	368.9	389.7	410.1	434.0	460.9	491.4	524.5	561.0	606.3	652.7	699.4
35°	349.6	367.0	388.1	413.5	443.9	478.9	517.1	560.3	612.3	665.6	704.9
37.5°	326.8	342.9	365.1	393.0	424.8	462.4	507.8	559.0	614.3	656.7	669.4
40°	311.3	326.4	349.4	378.3	410.9	450.7	500.4	554.6	608.1	635.2	624.7
42.5°	294.9	310.7	333.2	361.8	396.9	440.1	491.2	545.4	590.3	600.5	564.4
45°	269.1	285.3	307.5	336.4	374.1	421.0	474.3	523.6	549.3	530.8	475.0
47.5°	245.0	260.3	280.8	310.7	349.6	398.1	449.3	488.6	490.7	446.6	386.9
50°	228.6	242.7	263.4	293.3	331.8	381.0	427.2	458.2	444.3	394.3	337.0
52.5°	212.5	226.3	246.7	276.2	314.4	359.4	402.5	424.2	398.0	346.7	297.8
55°	189.3	201.4	221.3	248.6	284.8	326.5	363.1	370.7	336.6	286.1	246.4
57.5°	166.6	177.8	196.0	221.1	254.3	291.2	319.9	318.2	282.3	238.9	207.4
60°	151.2	162.2	178.3	202.8	233.1	264.9	289.4	283.5	247.9	210.5	183.9
62.5°	137.4	147.3	162.5	183.9	211.5	241.0	261.1	252.5	217.5	184.9	163.9
65°	117.2	125.4	138.4	156.7	179.6	203.9	219.5	208.3	178.5	153.0	136.2
67.5°	97.8	104.4	115.3	129.9	149.4	169.0	178.4	167.2	143.3	124.8	112.3
70°	85.5	91.3	99.7	112.7	129.8	146.2	153.4	143.3	122.8	106.9	97.9
72.5°	73.2	78.0	85.4	97.1	110.7	125.0	131.3	121.7	104.8	91.3	83.0
75°	56.6	59.9	65.0	73.0	83.8	95.2	98.6	90.2	79.5	69.4	63.8
77.5°	40.5	43.3	47.1	52.2	59.9	67.1	70.1	65.3	57.0	50.5	46.0
80°	31.1	32.6	35.9	40.1	46.1	50.7	52.7	49.6	43.7	39.0	35.5
82.5°	22.2	23.7	25.6	29.1	33.0	36.0	38.2	36.1	31.9	28.1	26.1
85°	10.8	11.7	12.8	14.3	17.2	19.0	18.9	17.6	15.9	14.5	13.4
87.5°	4.4	4.9	5.7	6.8	7.6	8.5	9.1	9.1	8.9	8.6	8.4
90°	2.9	4.7	6.5	8.3	10.1	11.6	13.2	14.8	16.4	17.6	18.7
92.5°	14.5	13.2	12.0	10.7	10.8	12.2	13.5	15.0	16.4	17.6	18.7
95°	57.8	57.1	56.4	55.7	51.0	42.4	33.7	25.0	16.4	17.6	18.7
97.5°	123.3	124.5	125.7	127.0	119.0	101.9	84.8	67.6	50.5	44.0	37.6
100°	172.0	172.6	173.3	174.0	174.8	175.7	176.7	177.5	178.5	144.5	110.5
102.5°	222.2	223.1	223.9	224.8	225.5	226.1	226.6	227.1	227.7	221.3	214.8
105°	302.5	303.4	304.3	305.2	305.6	305.6	305.6	305.6	305.6	305.6	305.6
107.5°	384.8	384.8	384.8	384.8	385.1	385.6	386.0	386.4	386.9	386.9	387.0
110°	439.0	439.0	439.0	439.0	439.2	439.7	440.1	440.6	441.0	440.4	439.7



TEST NUMBER: P333358-927

CATALOG NUMBER: S125DIW-S375D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	490.4	491.0	491.5	492.0	492.5	492.7	493.0	493.3	493.5	492.7	491.8
115°	567.3	568.5	569.6	570.8	571.4	571.6	571.9	572.1	572.4	571.4	570.5
117.5°	645.1	645.1	645.0	645.0	645.4	646.3	647.1	648.0	648.9	647.7	646.5
120°	694.2	694.0	693.7	693.5	693.7	694.3	695.1	695.8	696.4	696.0	695.5
122.5°	738.7	739.6	740.5	741.3	742.0	742.3	742.6	742.9	743.2	742.8	742.3
125°	806.8	808.3	809.9	811.5	812.3	812.3	812.3	812.3	812.3	811.4	810.5
127.5°	870.5	871.6	872.7	873.9	874.4	874.3	874.2	874.0	873.9	873.4	872.9
130°	909.9	911.0	912.2	913.3	914.0	914.3	914.4	914.7	914.9	914.3	913.5
132.5°	949.4	950.8	952.1	953.4	953.9	953.3	952.8	952.4	951.8	951.7	951.6
135°	1005.5	1006.9	1008.2	1009.6	1010.0	1009.6	1009.2	1008.7	1008.2	1007.8	1007.3
137.5°	1056.8	1058.0	1059.1	1060.3	1060.7	1060.3	1059.9	1059.5	1059.1	1059.2	1059.3
140°	1089.7	1090.2	1090.6	1091.1	1091.2	1091.0	1090.8	1090.5	1090.3	1090.8	1091.2
142.5°	1119.9	1120.1	1120.5	1120.7	1121.0	1121.3	1121.7	1122.0	1122.3	1122.4	1122.4
145°	1164.6	1165.1	1165.5	1165.9	1166.2	1166.2	1166.2	1166.2	1166.2	1166.4	1166.6
147.5°	1203.0	1202.9	1202.8	1202.8	1202.8	1203.1	1203.4	1203.6	1204.0	1204.2	1204.5
150°	1227.2	1226.9	1226.4	1225.9	1225.9	1226.4	1226.9	1227.2	1227.7	1228.2	1228.7
152.5°	1250.5	1249.5	1248.6	1247.5	1247.2	1247.7	1248.2	1248.6	1249.0	1249.5	1250.0
155°	1280.7	1279.4	1278.0	1276.6	1276.2	1276.6	1277.1	1277.6	1278.0	1278.7	1279.4
157.5°	1304.9	1304.0	1303.2	1302.4	1302.0	1302.0	1302.1	1302.2	1302.2	1302.9	1303.7
160°	1320.7	1319.4	1318.0	1316.6	1316.1	1316.3	1316.5	1316.8	1317.0	1317.9	1318.8
162.5°	1333.9	1332.5	1331.1	1329.8	1329.2	1329.4	1329.7	1329.8	1330.1	1331.3	1332.6
165°	1351.5	1350.1	1348.8	1347.4	1346.8	1347.0	1347.3	1347.5	1347.7	1349.1	1350.4
167.5°	1364.6	1363.2	1361.8	1360.3	1359.8	1359.9	1360.2	1360.4	1360.7	1362.3	1364.0
170°	1371.8	1370.2	1368.6	1367.0	1366.3	1366.5	1366.8	1367.0	1367.2	1369.0	1370.9
172.5°	1376.7	1375.1	1373.5	1371.9	1371.3	1371.7	1372.1	1372.5	1372.9	1374.6	1376.3
175°	1382.3	1380.9	1379.5	1378.2	1377.6	1377.8	1378.1	1378.3	1378.5	1380.3	1382.1
177.5°	1385.0	1383.9	1382.8	1381.7	1381.2	1381.5	1381.6	1381.8	1382.0	1383.3	1384.6
180°	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6



TEST NUMBER: P333358-927

CATALOG NUMBER: S125DIW-S375D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	431.3	431.3	431.3	431.3	431.3	431.3	431.3
2.5°	451.1	452.2	454.7	453.8	455.0	455.6	456.1
5°	487.4	493.3	495.9	495.5	499.4	498.4	497.5
7.5°	528.6	534.7	538.2	542.5	544.9	545.2	547.3
10°	551.9	559.9	563.2	567.8	570.8	572.4	572.2
12.5°	569.7	576.1	583.4	585.7	589.6	591.8	591.0
15°	591.3	601.3	609.0	612.8	617.8	619.2	621.2
17.5°	610.5	623.9	632.9	644.8	649.4	652.1	650.5
20°	625.0	642.7	651.6	665.9	673.8	678.0	676.5
22.5°	642.1	661.3	677.9	690.2	702.2	707.9	709.1
25°	671.5	697.8	722.2	738.4	753.2	756.7	764.4
27.5°	704.3	735.3	761.4	778.5	788.8	792.7	795.1
30°	724.8	755.8	775.4	786.4	789.6	789.3	788.9
32.5°	735.0	754.3	758.1	755.0	747.5	741.1	734.4
35°	720.6	706.2	684.6	656.8	636.3	615.6	613.5
37.5°	648.2	601.9	565.9	525.8	502.6	488.3	478.4
40°	579.9	527.4	483.8	450.0	426.4	417.0	407.8
42.5°	505.8	455.6	417.0	388.7	371.0	360.6	353.4
45°	410.9	366.6	336.4	315.9	301.8	293.8	289.2
47.5°	336.8	304.0	278.3	263.5	253.8	247.6	247.6
50°	296.9	265.6	248.6	236.9	228.5	223.5	224.4
52.5°	261.6	238.2	223.7	213.9	207.6	204.6	204.5
55°	218.7	201.9	192.4	185.2	181.0	177.5	178.3
57.5°	187.1	172.9	166.5	160.6	157.6	156.3	154.2
60°	167.5	156.5	151.0	146.2	143.3	142.2	140.2
62.5°	150.0	141.4	136.1	132.2	129.6	129.2	127.6
65°	126.1	119.5	114.8	113.0	110.2	109.5	109.5
67.5°	103.9	99.3	95.5	93.9	92.7	92.8	92.0
70°	90.1	86.2	83.8	82.0	81.1	81.3	80.6
72.5°	78.8	74.5	72.4	71.3	70.1	70.6	70.3
75°	59.7	57.5	56.4	55.3	54.6	54.2	53.8
77.5°	43.8	41.9	41.0	40.4	40.6	39.6	40.3
80°	33.8	32.2	31.7	30.7	30.6	30.6	30.4
82.5°	24.8	23.8	23.4	22.7	22.3	22.7	22.2
85°	12.8	12.1	11.9	11.9	11.6	11.2	12.1
87.5°	8.6	8.3	8.5	8.5	8.6	8.6	8.5
90°	19.8	21.0	21.9	22.6	23.2	23.9	24.6
92.5°	19.8	21.0	21.7	22.0	22.3	22.7	23.0
95°	19.8	21.0	21.5	21.5	21.5	21.5	21.5
97.5°	31.2	24.7	21.5	21.5	21.5	21.5	21.5
100°	76.6	42.6	25.2	24.2	23.4	22.4	21.5
102.5°	208.4	202.0	191.0	175.5	160.0	144.5	129.0
105°	305.6	305.6	305.5	305.3	305.1	304.8	304.6
107.5°	387.1	387.1	386.7	386.0	385.4	384.7	384.0
110°	439.0	438.3	438.1	438.3	438.6	438.8	439.0



TEST NUMBER: P333358-927

CATALOG NUMBER: S125DIW-S375D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	491.0	490.1	489.5	489.2	488.9	488.5	488.2
115°	569.6	568.7	567.5	566.2	564.8	563.4	562.1
117.5°	645.3	644.1	643.2	642.6	642.1	641.4	640.9
120°	695.1	694.6	693.8	692.7	691.5	690.4	689.3
122.5°	741.8	741.4	740.5	739.2	737.8	736.5	735.2
125°	809.6	808.7	807.9	807.2	806.5	805.8	805.2
127.5°	872.4	871.9	870.8	869.1	867.4	865.7	864.0
130°	912.8	912.2	911.2	910.1	908.9	907.8	906.7
132.5°	951.4	951.3	950.6	949.5	948.4	947.2	946.1
135°	1006.9	1006.4	1005.5	1004.2	1002.7	1001.4	1000.1
137.5°	1059.4	1059.5	1058.9	1057.7	1056.5	1055.3	1054.2
140°	1091.6	1092.1	1091.6	1090.3	1088.9	1087.6	1086.2
142.5°	1122.6	1122.7	1122.0	1120.6	1119.3	1117.9	1116.6
145°	1166.9	1167.1	1166.6	1165.1	1163.8	1162.4	1161.1
147.5°	1204.8	1205.1	1204.4	1202.7	1201.0	1199.4	1197.8
150°	1229.1	1229.5	1228.8	1227.0	1225.2	1223.4	1221.5
152.5°	1250.5	1250.9	1250.3	1248.6	1247.1	1245.4	1243.7
155°	1280.0	1280.7	1280.2	1278.3	1276.5	1274.7	1272.9
157.5°	1304.4	1305.1	1304.6	1302.7	1300.9	1299.1	1297.3
160°	1319.7	1320.6	1320.2	1318.3	1316.5	1314.7	1312.9
162.5°	1334.0	1335.2	1334.8	1332.8	1330.8	1328.8	1326.8
165°	1351.9	1353.2	1353.0	1351.1	1349.3	1347.5	1345.7
167.5°	1365.6	1367.2	1367.0	1364.9	1362.9	1360.9	1358.8
170°	1372.7	1374.5	1374.4	1372.4	1370.3	1368.3	1366.2
172.5°	1377.9	1379.5	1379.3	1377.3	1375.2	1373.2	1371.1
175°	1383.9	1385.8	1385.7	1383.6	1381.6	1379.5	1377.4
177.5°	1385.8	1387.1	1387.0	1385.5	1384.1	1382.6	1381.2
180°	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6

(END OF REPORT)