

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332726-840

Luminaire Tested: **S124DIW-S350D770U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332726-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S350D770U840-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4222.4 lumens  
Efficiency: N/A  
Efficacy: 138.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 30.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332726-840

CATALOG NUMBER: S124DIW-S350D770U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332726-840

CATALOG NUMBER: S124DIW-S350D770U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36
1	95	90	87	83	86	82	79	76	66	64	62	52	50	49	38	37	37	30
2	86	79	73	68	78	72	67	62	58	54	51	45	43	41	34	32	31	26
3	79	69	62	56	71	63	57	52	51	47	43	40	37	34	30	28	26	22
4	72	61	54	48	65	56	49	44	45	40	37	36	32	29	27	24	23	19
5	66	54	47	41	59	50	43	38	41	35	31	32	28	25	24	22	20	16
6	61	49	41	35	55	45	38	33	36	31	27	29	25	22	22	19	17	14
7	56	44	36	31	51	40	33	28	33	28	24	26	22	20	20	17	15	13
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	16	14	11
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12	10
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4816	4816	4816
5°	4830	4772	4807
10°	4800	4733	4757
15°	4741	4667	4679
20°	4665	4582	4587
25°	4577	4488	4475
30°	4470	4376	4336
35°	4357	4258	4202
40°	4241	4126	4051
45°	4120	3995	3919
50°	3986	3878	3758
55°	3842	3727	3606
60°	3696	3559	3450
65°	3534	3396	3261
70°	3352	3182	3059
75°	3072	2923	2848
80°	2734	2627	2552
85°	2399	2297	2251



TEST NUMBER: P332726-840

CATALOG NUMBER: S124DIW-S350D770U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	56.2	1.3
10°-20°	158.3	3.7
20°-30°	233.0	5.5
30°-40°	270.8	6.4
40°-50°	270.9	6.4
50°-60°	236.9	5.6
60°-70°	175.9	4.2
70°-80°	100.0	2.4
80°-90°	31.7	0.8
90°-100°	63.9	1.5
100°-110°	189.3	4.5
110°-120°	321.4	7.6
120°-130°	423.8	10.0
130°-140°	475.9	11.3
140°-150°	467.7	11.1
150°-160°	393.4	9.3
160°-170°	261.7	6.2
170°-180°	91.6	2.2
0°-30°	447.4	10.6
0°-40°	718.3	17.0
0°-60°	1226.1	29.0
0°-90°	1533.7	36.3
90°-120°	574.6	13.6
90°-150°	1942.0	46.0
90°-180°	2689.0	63.7
0°-180°	4222.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	596	596	596	596	596	
5°	596	594	589	594	593	57
15°	567	565	558	561	560	160
25°	514	510	504	504	502	236
35°	442	439	432	429	426	276
45°	361	357	350	345	343	278
55°	273	271	265	259	256	244
65°	185	182	178	173	171	183
75°	98	96	94	92	91	105
85°	26	26	25	25	24	28
90°	2	10	16	21	22	4
95°	45	52	57	59	59	50
105°	175	176	178	181	183	185
115°	327	327	325	325	324	322
125°	476	476	475	474	472	424
135°	614	618	618	617	615	475
145°	746	749	750	749	746	467
155°	854	854	854	856	854	393
165°	930	928	926	930	928	262
175°	968	964	963	968	963	92
180°	969	969	969	969	969	



TEST NUMBER: P332726-840

CATALOG NUMBER: S124DIW-S350D770U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5
2.5°	598.0	597.8	597.5	597.3	597.0	596.4	595.5	594.6	593.7	592.7	593.6
5°	596.0	595.6	595.2	594.8	594.4	593.6	592.4	591.3	590.1	588.9	590.1
7.5°	590.6	590.1	589.7	589.3	588.9	587.9	586.6	585.4	584.1	582.8	583.7
10°	585.5	585.1	584.7	584.3	583.9	583.0	581.6	580.2	578.9	577.4	578.2
12.5°	579.1	578.7	578.2	577.7	577.3	576.4	574.9	573.5	572.0	570.6	571.5
15°	567.3	566.9	566.5	566.1	565.7	564.7	563.1	561.5	559.9	558.4	559.0
17.5°	553.3	552.8	552.3	551.8	551.2	550.2	548.7	547.1	545.6	544.1	544.5
20°	543.0	542.5	542.0	541.4	540.9	539.9	538.3	536.6	535.0	533.4	533.8
22.5°	531.9	531.2	530.5	529.8	529.1	528.0	526.3	524.8	523.2	521.6	522.2
25°	513.8	513.1	512.4	511.6	510.9	509.8	508.3	506.8	505.3	503.8	503.9
27.5°	493.2	492.4	491.7	490.9	490.2	489.1	487.7	486.4	484.9	483.5	483.3
30°	479.5	478.6	477.8	476.9	476.1	474.9	473.5	472.1	470.8	469.4	469.0
32.5°	464.9	464.1	463.3	462.6	461.8	460.7	459.3	457.8	456.4	454.8	454.3
35°	442.1	441.4	440.7	439.9	439.2	438.1	436.6	435.0	433.6	432.1	431.4
37.5°	418.2	417.5	416.8	416.2	415.5	414.3	412.7	411.1	409.5	407.9	407.1
40°	402.4	401.6	400.8	399.9	399.1	397.9	396.3	394.7	393.0	391.5	390.4
42.5°	385.7	385.2	384.7	384.2	383.6	382.4	380.7	378.9	377.2	375.5	374.2
45°	360.9	360.1	359.4	358.7	357.9	356.7	355.0	353.3	351.6	349.9	348.7
47.5°	335.0	334.5	334.0	333.5	333.0	331.9	330.3	328.7	327.2	325.6	324.3
50°	317.4	317.0	316.6	316.1	315.7	314.8	313.3	311.7	310.2	308.8	307.3
52.5°	300.2	299.6	299.1	298.6	298.1	297.1	295.5	294.0	292.4	290.8	289.5
55°	273.0	272.7	272.3	272.0	271.7	270.7	269.2	267.8	266.3	264.8	263.6
57.5°	246.9	246.6	246.2	245.9	245.5	244.6	243.1	241.7	240.1	238.7	237.5
60°	228.9	228.4	227.9	227.3	226.8	225.9	224.5	223.1	221.8	220.4	219.4
62.5°	211.4	211.0	210.5	210.1	209.5	208.6	207.1	205.7	204.2	202.8	201.9
65°	185.0	184.5	183.9	183.4	182.9	182.1	181.0	180.0	178.8	177.8	176.7
67.5°	158.4	157.9	157.4	156.9	156.4	155.7	154.7	153.7	152.7	151.6	150.6
70°	142.0	141.2	140.5	139.8	139.0	138.1	137.3	136.5	135.6	134.8	133.9
72.5°	124.4	123.6	122.9	122.2	121.4	120.7	120.0	119.4	118.7	118.0	117.2
75°	98.5	98.0	97.5	96.8	96.3	95.8	95.3	94.7	94.2	93.7	93.3
77.5°	73.7	73.5	73.2	73.0	72.8	72.4	72.0	71.5	71.0	70.6	70.4
80°	58.8	58.5	58.2	57.9	57.6	57.3	57.1	56.9	56.7	56.5	56.1
82.5°	44.2	44.1	43.9	43.8	43.6	43.5	43.5	43.5	43.4	43.4	43.3
85°	25.9	25.9	25.9	25.9	25.9	25.8	25.4	25.2	25.0	24.8	24.8
87.5°	10.4	10.7	10.9	11.2	11.5	11.7	11.9	12.1	12.3	12.5	12.7
90°	2.2	4.0	6.0	7.8	9.6	11.2	12.5	13.8	15.1	16.5	17.5
92.5°	16.1	18.2	20.2	22.3	24.4	26.0	26.9	27.8	28.8	29.7	30.3
95°	44.9	46.5	48.0	49.5	51.0	52.3	53.4	54.6	55.8	57.0	57.5
97.5°	78.6	79.8	81.0	82.1	83.3	84.6	86.0	87.4	88.8	90.1	90.7
100°	104.9	105.6	106.2	106.9	107.6	108.7	110.2	111.7	113.2	114.7	115.0
102.5°	132.5	132.8	133.0	133.3	133.6	134.4	135.7	137.1	138.5	139.9	140.4
105°	174.6	174.8	175.0	175.1	175.3	175.7	176.4	177.0	177.7	178.3	178.8
107.5°	218.8	219.0	219.2	219.4	219.6	219.8	219.9	220.0	220.2	220.3	220.7
110°	248.8	249.1	249.5	249.8	250.1	250.2	250.0	249.9	249.7	249.5	249.2



TEST NUMBER: P332726-840

CATALOG NUMBER: S124DIW-S350D770U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	280.0	280.0	280.1	280.2	280.2	280.1	279.8	279.5	279.2	278.9	278.9
115°	326.8	326.8	326.8	326.8	326.8	326.6	326.3	326.0	325.6	325.3	325.1
117.5°	370.8	371.0	371.1	371.2	371.4	371.3	371.1	370.9	370.6	370.4	369.8
120°	400.2	400.9	401.5	402.2	402.9	402.9	402.5	402.0	401.5	401.0	400.1
122.5°	430.8	431.1	431.3	431.6	431.9	431.9	431.7	431.4	431.2	431.0	430.4
125°	475.9	475.9	475.9	475.9	475.9	475.8	475.6	475.5	475.3	475.1	474.8
127.5°	516.8	517.4	517.9	518.4	518.9	519.0	518.7	518.5	518.2	518.0	517.6
130°	545.6	546.1	546.6	547.1	547.6	547.9	547.9	547.9	547.9	547.9	547.5
132.5°	575.0	575.4	575.7	576.1	576.5	576.6	576.4	576.3	576.2	576.0	575.7
135°	613.9	614.8	615.8	616.8	617.8	618.3	618.3	618.3	618.3	618.3	618.0
137.5°	656.1	656.6	657.0	657.5	658.0	658.3	658.6	658.8	659.1	659.4	658.9
140°	684.3	684.6	685.0	685.3	685.6	685.8	685.8	685.8	685.8	685.8	685.6
142.5°	710.0	710.4	710.7	711.0	711.4	711.6	711.3	711.2	711.1	710.9	710.9
145°	745.8	746.4	747.1	747.8	748.4	748.8	749.0	749.2	749.3	749.5	749.3
147.5°	781.1	781.9	782.7	783.6	784.4	784.7	784.6	784.4	784.3	784.2	784.0
150°	802.7	803.3	804.1	804.8	805.4	805.8	805.8	805.8	805.8	805.8	805.8
152.5°	823.1	823.5	823.9	824.4	824.8	825.0	825.1	825.3	825.4	825.5	825.9
155°	854.4	854.4	854.4	854.4	854.4	854.3	854.1	854.0	853.8	853.7	854.3
157.5°	880.8	880.5	880.2	879.9	879.6	879.5	879.4	879.4	879.4	879.3	879.8
160°	896.5	896.3	896.1	896.0	895.8	895.5	895.4	895.2	895.0	894.9	895.4
162.5°	910.8	910.4	909.9	909.5	909.1	908.8	908.6	908.5	908.3	908.1	909.0
165°	930.2	929.7	929.2	928.7	928.2	927.8	927.4	927.1	926.8	926.3	927.4
167.5°	944.9	944.3	943.6	942.9	942.2	941.8	941.9	941.9	941.9	942.0	943.0
170°	953.4	952.5	951.7	950.9	950.1	949.7	949.9	950.1	950.2	950.4	951.4
172.5°	959.4	958.7	958.0	957.3	956.5	956.2	956.2	956.3	956.3	956.3	957.6
175°	967.7	966.7	965.9	965.1	964.3	963.8	963.6	963.4	963.3	963.1	964.3
177.5°	970.3	969.7	969.0	968.4	967.7	967.3	967.3	967.3	967.3	967.3	968.3
180°	969.1	969.1	969.1	969.1	969.1	969.1	969.1	969.1	969.1	969.1	969.1



TEST NUMBER: P332726-840

CATALOG NUMBER: S124DIW-S350D770U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5
2.5°	594.4	595.3	596.1	596.5	596.4	596.3	596.2	596.1
5°	591.3	592.4	593.6	594.0	593.8	593.6	593.4	593.2
7.5°	584.6	585.6	586.5	586.9	586.8	586.6	586.5	586.4
10°	579.2	580.0	580.9	581.2	581.0	580.7	580.5	580.3
12.5°	572.4	573.3	574.3	574.6	574.3	574.0	573.7	573.4
15°	559.6	560.2	560.9	561.0	560.7	560.4	560.1	559.8
17.5°	544.9	545.3	545.7	545.8	545.6	545.4	545.2	545.0
20°	534.1	534.4	534.7	534.8	534.5	534.3	534.1	533.9
22.5°	522.7	523.3	523.9	524.0	523.6	523.2	522.8	522.5
25°	504.0	504.1	504.2	504.1	503.6	503.2	502.8	502.4
27.5°	483.0	482.8	482.5	482.1	481.6	481.1	480.5	480.0
30°	468.6	468.2	467.7	467.3	466.7	466.2	465.6	465.1
32.5°	453.8	453.3	452.8	452.3	451.8	451.2	450.7	450.2
35°	430.6	429.9	429.1	428.5	428.0	427.5	426.9	426.4
37.5°	406.3	405.5	404.7	403.9	403.2	402.5	401.8	401.1
40°	389.4	388.3	387.3	386.5	385.9	385.4	384.9	384.4
42.5°	372.9	371.7	370.5	369.7	369.3	369.0	368.6	368.3
45°	347.6	346.4	345.3	344.5	344.2	343.9	343.6	343.3
47.5°	323.0	321.6	320.3	319.3	318.5	317.7	316.9	316.1
50°	305.8	304.4	302.9	301.7	301.1	300.5	299.8	299.2
52.5°	288.2	286.9	285.6	284.5	283.7	282.9	282.1	281.2
55°	262.3	260.9	259.7	258.7	258.1	257.5	256.8	256.2
57.5°	236.3	235.1	233.9	233.0	232.4	231.8	231.2	230.5
60°	218.4	217.5	216.5	215.8	215.3	214.7	214.2	213.7
62.5°	201.1	200.2	199.2	198.5	198.0	197.5	197.0	196.4
65°	175.7	174.6	173.6	172.8	172.3	171.7	171.2	170.7
67.5°	149.6	148.6	147.5	146.9	146.8	146.6	146.5	146.3
70°	133.1	132.3	131.4	130.8	130.5	130.2	129.9	129.6
72.5°	116.6	115.9	115.2	114.7	114.4	114.1	113.8	113.5
75°	92.8	92.4	92.0	91.7	91.6	91.5	91.4	91.3
77.5°	70.3	70.2	70.1	69.9	69.6	69.3	69.0	68.8
80°	55.9	55.7	55.5	55.4	55.2	55.1	55.0	54.9
82.5°	43.1	43.0	42.9	42.8	42.7	42.5	42.4	42.3
85°	24.8	24.8	24.8	24.8	24.7	24.6	24.4	24.3
87.5°	12.8	13.0	13.2	13.4	13.4	13.5	13.6	13.6
90°	18.5	19.5	20.5	21.1	21.5	21.8	22.1	22.5
92.5°	30.9	31.5	32.1	32.5	32.7	32.9	33.1	33.3
95°	58.0	58.5	59.0	59.2	59.2	59.2	59.2	59.2
97.5°	91.3	91.9	92.5	92.8	92.8	92.8	92.8	92.8
100°	115.3	115.6	116.0	116.1	116.1	116.1	116.1	116.1
102.5°	140.8	141.3	141.7	142.0	142.2	142.3	142.4	142.6
105°	179.4	179.9	180.4	180.9	181.4	181.9	182.4	182.9
107.5°	221.2	221.6	222.1	222.3	222.3	222.3	222.2	222.2
110°	248.9	248.6	248.2	248.3	248.8	249.3	249.8	250.3





TEST NUMBER: P332726-840

CATALOG NUMBER: S124DIW-S350D770U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	278.8	278.7	278.7	278.7	278.8	278.9	279.0	279.1
115°	325.0	324.8	324.6	324.5	324.3	324.2	324.0	323.8
117.5°	369.3	368.7	368.1	367.7	367.4	367.0	366.7	366.4
120°	399.3	398.5	397.7	397.4	397.8	398.1	398.4	398.7
122.5°	429.8	429.3	428.7	428.1	427.5	426.9	426.4	425.8
125°	474.5	474.2	473.8	473.5	473.2	472.8	472.5	472.2
127.5°	517.3	516.9	516.5	516.2	516.0	515.7	515.4	515.2
130°	547.2	546.8	546.5	546.0	545.4	544.7	544.0	543.4
132.5°	575.4	575.1	574.7	574.4	574.2	573.9	573.6	573.4
135°	617.6	617.3	617.0	616.6	616.1	615.6	615.1	614.6
137.5°	658.5	658.1	657.7	657.5	657.6	657.7	657.8	657.9
140°	685.5	685.3	685.1	685.0	684.8	684.6	684.5	684.3
142.5°	710.9	710.8	710.8	710.8	710.7	710.7	710.7	710.6
145°	749.2	749.0	748.8	748.5	748.0	747.5	747.0	746.5
147.5°	783.9	783.8	783.6	783.5	783.3	783.2	782.9	782.7
150°	805.8	805.8	805.8	805.7	805.5	805.3	805.2	805.0
152.5°	826.3	826.7	827.1	827.1	826.7	826.3	825.8	825.4
155°	855.1	855.7	856.4	856.4	855.7	855.1	854.3	853.7
157.5°	880.3	880.8	881.3	881.3	880.7	880.2	879.6	879.0
160°	896.0	896.5	897.0	896.8	896.0	895.0	894.2	893.4
162.5°	909.9	910.8	911.7	911.7	910.9	910.1	909.3	908.4
165°	928.4	929.4	930.4	930.6	929.9	929.2	928.6	927.9
167.5°	944.0	944.9	945.9	945.9	944.9	943.9	942.9	941.8
170°	952.4	953.4	954.4	954.3	953.1	952.0	950.8	949.7
172.5°	958.7	959.8	960.9	960.9	959.7	958.6	957.4	956.2
175°	965.4	966.6	967.8	967.8	966.6	965.4	964.3	963.1
177.5°	969.2	970.1	971.1	971.0	969.9	968.9	967.8	966.7
180°	969.1	969.1	969.1	969.1	969.1	969.1	969.1	969.1

(END OF REPORT)