

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332767-840

Luminaire Tested: **S124DIW-S575D1340U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332767-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S575D1340U840-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7939.0 lumens
Efficiency: N/A
Efficacy: 147.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332767-840

CATALOG NUMBER: S124DIW-S575D1340U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332767-840

CATALOG NUMBER: S124DIW-S575D1340U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	56	56	56	39	39	39	32
1	94	89	86	82	84	81	77	75	64	62	60	49	47	46	35	34	33	27
2	85	78	72	67	76	70	65	61	56	53	49	43	40	38	31	29	28	22
3	78	69	61	56	70	62	56	51	49	45	42	38	35	32	27	25	24	19
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20	16
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	20	18	14
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16	12
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14	11
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12	10
9	48	36	28	24	43	33	26	22	26	22	18	21	17	15	15	13	11	9
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7917	7917	7917
5°	7942	7846	7903
10°	7891	7782	7820
15°	7796	7672	7691
20°	7669	7534	7541
25°	7525	7378	7357
30°	7347	7194	7127
35°	7164	7001	6908
40°	6973	6783	6658
45°	6774	6567	6441
50°	6553	6376	6178
55°	6315	6128	5928
60°	6077	5848	5670
65°	5809	5585	5358
70°	5509	5231	5028
75°	5050	4803	4682
80°	4491	4310	4203
85°	3927	3788	3714



TEST NUMBER: P332767-840

CATALOG NUMBER: S124DIW-S575D1340U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.4	1.2
10°-20°	260.2	3.3
20°-30°	383.0	4.8
30°-40°	445.3	5.6
40°-50°	445.3	5.6
50°-60°	389.5	4.9
60°-70°	289.3	3.6
70°-80°	164.3	2.1
80°-90°	52.5	0.7
90°-100°	59.9	0.8
100°-110°	381.9	4.8
110°-120°	730.6	9.2
120°-130°	927.4	11.7
130°-140°	992.3	12.5
140°-150°	927.9	11.7
150°-160°	748.3	9.4
160°-170°	482.6	6.1
170°-180°	166.3	2.1
0°-30°	735.6	9.3
0°-40°	1180.9	14.9
0°-60°	2015.7	25.4
0°-90°	2521.7	31.8
90°-120°	1172.4	14.8
90°-150°	4020.0	50.6
90°-180°	5417.0	68.2
0°-180°	7939.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	981	981	981	981	981	
5°	980	976	968	976	975	93
15°	933	929	918	922	920	263
25°	845	839	828	829	826	388
35°	727	721	710	705	701	454
45°	593	587	575	567	564	457
55°	449	446	435	426	421	402
65°	304	300	292	285	280	301
75°	162	158	154	151	150	172
85°	42	42	41	41	40	47
90°	4	18	29	36	39	6
95°	72	30	29	36	38	93
105°	394	402	409	417	373	413
115°	736	740	739	741	741	724
125°	1035	1040	1037	1041	1043	924
135°	1284	1283	1288	1290	1293	989
145°	1480	1484	1484	1485	1488	925
155°	1623	1624	1620	1625	1622	748
165°	1712	1706	1706	1715	1704	484
175°	1751	1744	1745	1755	1741	167
180°	1751	1751	1751	1751	1751	



TEST NUMBER: P332767-840

CATALOG NUMBER: S124DIW-S575D1340U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	980.7	980.7	980.7	980.7	980.7	980.7	980.7	980.7	980.7	980.7	980.7
2.5°	983.2	982.8	982.4	982.0	981.6	980.6	979.1	977.5	975.9	974.4	975.8
5°	980.0	979.3	978.6	977.9	977.1	975.8	973.9	972.0	970.1	968.2	970.1
7.5°	970.8	970.1	969.5	968.8	968.1	966.6	964.5	962.4	960.2	958.1	959.7
10°	962.6	962.0	961.3	960.6	959.9	958.4	956.1	953.8	951.6	949.3	950.7
12.5°	952.0	951.3	950.6	949.9	949.2	947.7	945.2	942.8	940.4	938.0	939.5
15°	932.8	932.1	931.4	930.7	930.0	928.4	925.7	923.1	920.5	917.9	918.9
17.5°	909.7	908.8	908.0	907.1	906.2	904.5	902.0	899.6	897.1	894.6	895.2
20°	892.7	891.8	891.0	890.1	889.2	887.5	884.8	882.2	879.6	877.0	877.5
22.5°	874.4	873.3	872.2	871.0	869.9	868.0	865.4	862.7	860.1	857.5	858.5
25°	844.8	843.5	842.3	841.1	839.9	838.1	835.6	833.1	830.7	828.3	828.5
27.5°	810.8	809.6	808.3	807.1	805.8	804.1	801.7	799.5	797.2	795.0	794.6
30°	788.2	786.8	785.4	784.0	782.6	780.7	778.5	776.2	774.0	771.7	771.0
32.5°	764.3	763.1	761.7	760.5	759.3	757.4	755.1	752.7	750.2	747.8	747.0
35°	726.9	725.7	724.5	723.3	722.1	720.1	717.7	715.3	712.9	710.4	709.1
37.5°	687.4	686.3	685.2	684.1	683.0	681.2	678.5	675.9	673.3	670.7	669.3
40°	661.7	660.2	658.8	657.5	656.1	654.1	651.5	648.8	646.2	643.6	641.9
42.5°	634.0	633.2	632.4	631.5	630.7	628.7	625.9	623.0	620.1	617.2	615.2
45°	593.3	592.1	590.9	589.7	588.4	586.4	583.6	580.8	578.0	575.2	573.3
47.5°	550.7	549.9	549.1	548.2	547.3	545.6	543.1	540.5	537.9	535.3	533.1
50°	521.8	521.1	520.4	519.7	519.0	517.5	515.0	512.5	510.1	507.7	505.2
52.5°	493.5	492.7	491.8	491.0	490.2	488.5	485.8	483.3	480.7	478.1	475.9
55°	448.7	448.2	447.7	447.2	446.7	445.1	442.7	440.2	437.8	435.4	433.2
57.5°	406.0	405.4	404.8	404.1	403.5	402.1	399.7	397.3	394.9	392.4	390.4
60°	376.4	375.6	374.7	373.8	372.9	371.3	369.1	366.8	364.6	362.2	360.7
62.5°	347.5	346.8	346.0	345.3	344.6	343.0	340.6	338.2	335.8	333.4	331.9
65°	304.1	303.3	302.4	301.5	300.6	299.3	297.6	295.8	294.1	292.4	290.5
67.5°	260.4	259.6	258.8	258.0	257.2	256.0	254.3	252.7	251.0	249.2	247.6
70°	233.4	232.2	231.0	229.7	228.5	227.2	225.8	224.4	223.0	221.6	220.3
72.5°	204.5	203.3	202.1	200.8	199.5	198.4	197.3	196.2	195.1	193.9	192.8
75°	161.9	161.0	160.2	159.3	158.3	157.5	156.6	155.7	154.9	154.0	153.3
77.5°	121.2	120.8	120.4	120.1	119.7	119.1	118.3	117.5	116.7	116.0	115.7
80°	96.6	96.1	95.6	95.1	94.5	94.1	93.8	93.4	93.1	92.7	92.4
82.5°	72.8	72.5	72.3	72.0	71.8	71.6	71.6	71.5	71.4	71.4	71.1
85°	42.4	42.4	42.4	42.4	42.4	42.2	41.9	41.6	41.2	40.9	40.9
87.5°	17.2	17.7	18.2	18.7	19.1	19.6	19.9	20.2	20.5	20.8	21.2
90°	3.9	7.2	10.3	13.5	16.8	19.5	21.8	24.1	26.5	28.8	30.6
92.5°	16.5	16.7	16.9	17.1	17.2	18.5	20.8	23.1	25.4	27.8	29.5
95°	72.0	62.1	52.2	42.3	32.4	27.7	28.0	28.3	28.5	28.8	30.6
97.5°	153.0	159.2	165.3	171.5	177.6	164.5	132.0	99.6	67.1	34.5	34.7
100°	214.8	220.0	225.3	230.6	235.8	218.3	178.1	137.9	97.8	57.7	52.7
102.5°	284.0	287.8	291.6	295.5	299.3	298.6	293.4	288.2	283.0	277.7	224.3
105°	394.3	396.0	397.8	399.5	401.2	402.8	404.3	405.8	407.2	408.7	411.3
107.5°	496.7	497.6	498.5	499.3	500.2	501.6	503.6	505.5	507.6	509.6	510.8
110°	565.8	566.7	567.6	568.5	569.4	570.7	572.4	574.1	575.9	577.6	578.2



TEST NUMBER: P332767-840

CATALOG NUMBER: S124DIW-S575D1340U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	632.9	634.5	636.1	637.6	639.2	640.4	641.3	642.1	642.9	643.7	643.6
115°	736.1	737.0	737.9	738.7	739.6	739.9	739.6	739.3	739.0	738.7	739.3
117.5°	829.1	830.3	831.4	832.6	833.7	834.7	835.4	836.0	836.6	837.3	837.2
120°	892.0	893.1	894.3	895.5	896.7	897.1	896.9	896.6	896.3	896.0	896.6
122.5°	950.7	951.4	952.1	952.8	953.5	954.0	954.4	954.8	955.2	955.6	956.0
125°	1034.8	1035.9	1037.1	1038.2	1039.5	1039.8	1039.2	1038.5	1037.9	1037.4	1038.2
127.5°	1114.4	1114.7	1115.0	1115.3	1115.6	1116.4	1117.7	1119.0	1120.4	1121.8	1121.6
130°	1165.8	1166.1	1166.4	1166.6	1166.9	1167.5	1168.4	1169.2	1170.1	1171.0	1171.3
132.5°	1212.9	1213.5	1214.0	1214.5	1215.0	1215.9	1217.0	1218.0	1219.1	1220.2	1220.5
135°	1283.6	1283.3	1283.0	1282.8	1282.5	1282.9	1284.0	1285.3	1286.5	1287.6	1288.2
137.5°	1346.3	1346.4	1346.5	1346.7	1346.8	1347.5	1348.7	1350.0	1351.3	1352.5	1353.2
140°	1387.2	1387.8	1388.3	1388.9	1389.5	1390.1	1390.6	1391.2	1391.8	1392.4	1393.2
142.5°	1423.8	1424.8	1425.9	1426.9	1428.1	1428.7	1429.1	1429.4	1429.8	1430.1	1430.8
145°	1480.2	1481.0	1481.9	1482.8	1483.6	1484.1	1484.1	1484.1	1484.1	1484.1	1484.4
147.5°	1524.9	1526.5	1528.2	1529.8	1531.5	1532.2	1531.9	1531.6	1531.3	1531.0	1531.2
150°	1557.4	1558.6	1559.7	1560.9	1562.1	1562.5	1562.3	1562.0	1561.7	1561.4	1561.4
152.5°	1584.7	1585.6	1586.5	1587.4	1588.4	1588.6	1588.1	1587.5	1587.0	1586.5	1587.0
155°	1623.0	1623.2	1623.5	1623.8	1624.1	1623.8	1623.0	1622.0	1621.1	1620.3	1621.4
157.5°	1655.2	1655.0	1654.8	1654.6	1654.5	1653.9	1652.8	1651.8	1650.9	1649.9	1651.4
160°	1674.0	1673.1	1672.2	1671.3	1670.5	1669.9	1669.6	1669.3	1669.0	1668.8	1670.5
162.5°	1690.7	1689.6	1688.6	1687.5	1686.4	1685.7	1685.4	1685.1	1684.8	1684.5	1686.2
165°	1712.0	1710.5	1709.1	1707.6	1706.2	1705.5	1705.5	1705.5	1705.5	1705.5	1707.8
167.5°	1728.8	1727.3	1725.8	1724.2	1722.7	1721.8	1721.7	1721.5	1721.3	1721.1	1723.7
170°	1738.2	1736.5	1734.6	1732.9	1731.2	1730.5	1730.7	1731.0	1731.3	1731.6	1733.9
172.5°	1744.4	1742.7	1741.0	1739.2	1737.5	1736.8	1737.1	1737.4	1737.6	1737.9	1740.2
175°	1751.3	1749.5	1747.8	1746.1	1744.2	1743.5	1743.8	1744.1	1744.4	1744.7	1747.4
177.5°	1754.4	1752.8	1751.1	1749.5	1747.9	1747.3	1747.8	1748.3	1748.7	1749.2	1751.0
180°	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3



TEST NUMBER: P332767-840

CATALOG NUMBER: S124DIW-S575D1340U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	980.7	980.7	980.7	980.7	980.7	980.7	980.7	980.7
2.5°	977.2	978.7	980.1	980.7	980.5	980.4	980.3	980.1
5°	972.0	973.9	975.8	976.6	976.2	975.9	975.5	975.2
7.5°	961.2	962.7	964.2	964.9	964.7	964.5	964.3	964.0
10°	952.1	953.5	954.9	955.4	955.0	954.7	954.3	954.0
12.5°	941.1	942.6	944.1	944.6	944.1	943.6	943.2	942.7
15°	920.0	921.0	922.0	922.3	921.8	921.3	920.7	920.2
17.5°	896.0	896.6	897.3	897.4	897.1	896.7	896.4	896.1
20°	878.1	878.6	879.1	879.2	878.8	878.5	878.2	877.8
22.5°	859.4	860.3	861.3	861.4	860.8	860.2	859.6	858.9
25°	828.6	828.8	829.0	828.7	828.0	827.3	826.6	825.9
27.5°	794.2	793.7	793.2	792.6	791.7	790.9	790.0	789.1
30°	770.3	769.6	768.9	768.1	767.2	766.4	765.5	764.6
32.5°	746.1	745.3	744.5	743.6	742.8	741.8	740.9	740.1
35°	707.9	706.7	705.5	704.5	703.6	702.7	701.9	700.9
37.5°	668.0	666.6	665.3	664.1	663.0	661.8	660.7	659.4
40°	640.2	638.3	636.6	635.3	634.4	633.6	632.7	631.8
42.5°	613.2	611.1	609.0	607.7	607.2	606.6	606.0	605.4
45°	571.4	569.5	567.5	566.3	565.8	565.3	564.7	564.2
47.5°	531.0	528.8	526.6	524.9	523.6	522.2	520.9	519.6
50°	502.7	500.3	497.9	496.1	495.0	494.0	493.0	491.9
52.5°	473.7	471.6	469.5	467.7	466.4	465.0	463.7	462.4
55°	431.2	429.1	427.0	425.4	424.3	423.3	422.2	421.2
57.5°	388.5	386.5	384.5	382.9	381.9	380.9	379.9	378.9
60°	359.1	357.6	356.0	354.8	353.9	353.0	352.1	351.2
62.5°	330.5	329.0	327.6	326.5	325.6	324.8	323.9	323.0
65°	288.8	287.1	285.4	284.1	283.2	282.3	281.4	280.5
67.5°	245.9	244.3	242.6	241.6	241.4	241.2	240.9	240.7
70°	218.8	217.4	216.0	215.1	214.5	214.0	213.5	213.0
72.5°	191.7	190.6	189.5	188.6	188.1	187.6	187.1	186.5
75°	152.6	151.9	151.3	150.8	150.6	150.5	150.3	150.1
77.5°	115.5	115.3	115.1	114.8	114.3	113.9	113.4	113.0
80°	92.0	91.7	91.3	91.1	90.9	90.7	90.6	90.4
82.5°	70.9	70.7	70.5	70.3	70.2	70.0	69.8	69.6
85°	40.9	40.9	40.9	40.8	40.6	40.4	40.3	40.1
87.5°	21.5	21.9	22.2	22.5	22.6	22.7	22.8	22.9
90°	32.3	34.0	35.9	37.0	37.6	38.2	38.7	39.3
92.5°	31.3	33.0	34.7	35.6	35.9	36.0	36.1	36.2
95°	32.3	34.0	35.9	36.9	37.1	37.4	37.7	38.0
97.5°	34.9	35.1	35.2	35.5	35.9	36.1	36.4	36.7
100°	47.8	42.8	37.9	35.5	35.9	36.1	36.4	36.7
102.5°	171.0	117.5	64.1	37.5	37.6	37.6	37.7	37.8
105°	413.9	416.6	419.2	415.3	404.8	394.3	383.7	373.3
107.5°	512.1	513.4	514.6	515.8	516.9	518.1	519.2	520.3
110°	578.9	579.4	580.0	580.7	581.6	582.5	583.3	584.2



TEST NUMBER: P332767-840

CATALOG NUMBER: S124DIW-S575D1340U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	643.4	643.3	643.2	643.7	644.8	645.9	647.0	648.1
115°	739.9	740.5	741.0	741.3	741.3	741.3	741.3	741.3
117.5°	837.0	836.9	836.8	836.7	836.6	836.5	836.4	836.2
120°	897.1	897.7	898.3	898.3	897.7	897.1	896.6	896.0
122.5°	956.3	956.7	957.0	956.9	956.3	955.7	955.2	954.6
125°	1039.2	1040.1	1040.9	1041.5	1041.8	1042.1	1042.4	1042.7
127.5°	1121.5	1121.3	1121.1	1120.8	1120.6	1120.3	1120.1	1119.9
130°	1171.5	1171.8	1172.2	1172.4	1172.4	1172.4	1172.4	1172.4
132.5°	1220.8	1221.1	1221.4	1221.4	1221.2	1221.0	1220.7	1220.5
135°	1288.8	1289.3	1289.9	1290.5	1291.1	1291.6	1292.2	1292.8
137.5°	1353.8	1354.4	1355.1	1355.3	1355.1	1355.0	1354.8	1354.6
140°	1394.1	1395.0	1395.8	1396.4	1396.7	1397.0	1397.4	1397.7
142.5°	1431.4	1432.0	1432.7	1433.0	1433.1	1433.1	1433.2	1433.2
145°	1484.6	1484.9	1485.2	1485.7	1486.2	1486.8	1487.4	1488.0
147.5°	1531.5	1531.7	1531.9	1532.2	1532.5	1532.8	1533.0	1533.3
150°	1561.4	1561.4	1561.4	1561.5	1561.8	1562.1	1562.4	1562.7
152.5°	1587.4	1587.9	1588.3	1588.5	1588.3	1588.1	1588.0	1587.8
155°	1622.7	1623.8	1625.0	1625.1	1624.3	1623.4	1622.4	1621.6
157.5°	1652.9	1654.5	1656.0	1656.0	1654.5	1652.9	1651.4	1649.9
160°	1672.2	1674.0	1675.8	1675.8	1674.0	1672.2	1670.5	1668.8
162.5°	1688.0	1689.7	1691.4	1691.3	1689.4	1687.4	1685.4	1683.4
165°	1710.1	1712.4	1714.8	1714.5	1712.0	1709.4	1706.8	1704.1
167.5°	1726.3	1728.8	1731.4	1731.2	1728.3	1725.4	1722.5	1719.6
170°	1736.3	1738.6	1740.9	1740.6	1737.8	1734.8	1731.9	1729.0
172.5°	1742.5	1744.9	1747.3	1746.9	1743.6	1740.5	1737.4	1734.2
175°	1750.0	1752.6	1755.2	1754.7	1751.3	1747.8	1744.2	1740.8
177.5°	1752.9	1754.7	1756.7	1756.2	1753.3	1750.6	1747.8	1744.9
180°	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3

(END OF REPORT)