

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333368-927

Luminaire Tested: **S125DIW-S375D1560U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333368-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S375D1560U927-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6147.6 lumens
Efficiency: N/A
Efficacy: 115.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333368-927

CATALOG NUMBER: S125DIW-S375D1560U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333368-927

CATALOG NUMBER: S125DIW-S375D1560U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	88	88	88	88	66	66	66	47	47	47	28	28	28	20
1	91	87	83	80	80	77	74	71	58	56	54	41	40	38	25	24	24	16
2	83	76	70	65	73	67	62	58	51	48	45	36	34	32	22	21	20	14
3	75	66	60	54	66	59	53	48	45	41	38	32	29	27	19	18	17	12
4	69	59	51	45	61	52	46	41	40	35	32	28	25	23	17	16	15	10
5	63	52	44	39	55	46	40	35	35	31	27	25	22	20	15	14	13	9
6	58	46	39	33	51	41	35	30	32	27	24	22	20	17	14	12	11	8
7	53	42	34	29	47	37	31	26	28	24	21	20	17	15	13	11	10	7
8	49	38	30	25	43	34	27	23	26	21	18	19	16	13	12	10	9	6
9	46	34	27	22	40	31	24	20	24	19	16	17	14	12	11	9	8	5
10	43	31	24	20	38	28	22	18	22	17	14	16	13	11	10	8	7	5

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2989	2989	2989
5°	2995	2967	2986
10°	2977	2946	2963
15°	2945	2910	2923
20°	2899	2861	2866
25°	2849	2802	2799
30°	2788	2738	2725
35°	2722	2670	2633
40°	2655	2596	2559
45°	2582	2528	2478
50°	2502	2446	2372
55°	2423	2354	2288
60°	2331	2260	2180
65°	2222	2149	2077
70°	2115	2019	1949
75°	1926	1864	1799
80°	1715	1689	1648
85°	1489	1519	1438



TEST NUMBER: P333368-927

CATALOG NUMBER: S125DIW-S375D1560U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.6	0.7
10°-20°	123.3	2.0
20°-30°	182.0	3.0
30°-40°	212.4	3.5
40°-50°	213.3	3.5
50°-60°	187.2	3.0
60°-70°	139.5	2.3
70°-80°	79.8	1.3
80°-90°	26.5	0.4
90°-100°	58.5	1.0
100°-110°	360.3	5.9
110°-120°	653.4	10.6
120°-130°	838.6	13.6
130°-140°	902.0	14.7
140°-150°	846.7	13.8
150°-160°	684.9	11.1
160°-170°	442.9	7.2
170°-180°	152.8	2.5
0°-30°	348.9	5.7
0°-40°	561.2	9.1
0°-60°	961.7	15.6
0°-90°	1207.5	19.6
90°-120°	1072.2	17.4
90°-150°	3659.5	59.5
90°-180°	4940.0	80.4
0°-180°	6147.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	463	463	463	463	463	
5°	462	461	458	461	461	44
15°	440	439	435	437	437	124
25°	400	398	393	394	393	184
35°	345	344	339	337	334	216
45°	283	281	277	273	271	218
55°	215	214	209	206	203	192
65°	145	144	141	137	136	144
75°	77	76	75	74	72	82
85°	20	20	20	20	19	23
90°	1	11	19	25	29	4
95°	68	62	19	25	25	87
105°	351	355	355	355	354	372
115°	658	664	665	661	654	652
125°	936	944	944	940	936	836
135°	1167	1174	1172	1170	1163	900
145°	1354	1356	1356	1357	1350	846
155°	1491	1484	1486	1489	1480	686
165°	1573	1566	1567	1573	1565	444
175°	1609	1602	1603	1611	1602	153
180°	1609	1609	1609	1609	1609	



TEST NUMBER: P333368-927

CATALOG NUMBER: S125DIW-S375D1560U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8
2.5°	463.9	463.7	463.6	463.3	463.2	462.7	462.1	461.4	460.8	460.1	460.8
5°	462.0	461.8	461.7	461.5	461.4	460.9	460.1	459.3	458.4	457.6	458.4
7.5°	457.8	457.6	457.5	457.3	457.2	456.6	455.7	454.8	453.9	453.0	453.8
10°	454.0	453.8	453.7	453.5	453.4	452.8	451.9	451.0	450.1	449.2	449.9
12.5°	449.3	449.0	448.7	448.5	448.1	447.6	446.7	445.9	445.0	444.3	444.7
15°	440.5	440.2	440.0	439.7	439.4	438.9	438.0	437.1	436.2	435.3	435.7
17.5°	430.2	429.9	429.5	429.2	428.8	428.2	427.2	426.4	425.4	424.5	425.0
20°	421.8	421.6	421.4	421.3	421.1	420.5	419.5	418.4	417.3	416.3	416.8
22.5°	413.3	413.0	412.6	412.4	412.1	411.5	410.4	409.5	408.4	407.5	407.9
25°	399.8	399.4	398.9	398.5	398.2	397.4	396.4	395.3	394.3	393.2	393.4
27.5°	384.0	383.8	383.6	383.3	383.1	382.4	381.4	380.2	379.1	378.0	378.1
30°	373.8	373.6	373.3	373.0	372.8	372.1	370.9	369.6	368.4	367.2	367.0
32.5°	362.7	362.3	361.9	361.6	361.2	360.4	359.3	358.2	357.2	356.1	355.8
35°	345.2	344.9	344.6	344.3	344.0	343.2	342.1	341.0	339.8	338.7	338.3
37.5°	327.2	326.8	326.4	325.9	325.5	324.8	323.7	322.7	321.5	320.5	319.9
40°	314.9	314.4	314.0	313.6	313.2	312.4	311.3	310.2	309.0	307.9	307.2
42.5°	301.7	301.3	301.0	300.6	300.3	299.6	298.4	297.3	296.1	295.0	294.4
45°	282.7	282.3	282.0	281.7	281.3	280.7	279.7	278.8	277.7	276.8	275.8
47.5°	262.1	262.1	262.1	262.2	262.2	261.7	260.5	259.3	258.1	256.9	256.0
50°	249.0	248.7	248.5	248.2	248.0	247.4	246.4	245.4	244.5	243.4	242.4
52.5°	235.5	235.3	235.1	235.0	234.8	234.2	233.1	232.1	231.0	230.0	229.1
55°	215.2	215.0	214.8	214.5	214.3	213.6	212.5	211.4	210.2	209.1	208.3
57.5°	194.0	193.8	193.7	193.6	193.5	192.9	191.9	191.0	190.0	189.1	188.1
60°	180.5	180.1	179.8	179.5	179.2	178.6	177.7	176.8	175.9	175.0	174.2
62.5°	166.4	166.2	165.9	165.6	165.4	164.9	164.1	163.3	162.6	161.8	161.0
65°	145.4	145.2	145.0	144.9	144.7	144.2	143.3	142.4	141.5	140.6	139.8
67.5°	124.9	124.6	124.2	123.9	123.6	123.0	122.4	121.7	121.0	120.4	119.8
70°	112.0	111.6	111.2	110.8	110.4	109.8	109.1	108.4	107.7	106.9	106.4
72.5°	98.0	97.7	97.4	97.1	96.9	96.5	96.0	95.5	95.1	94.6	94.0
75°	77.2	77.1	76.9	76.8	76.6	76.3	75.9	75.5	75.1	74.7	74.5
77.5°	58.1	58.1	58.0	57.9	57.9	57.8	57.5	57.3	57.0	56.8	56.6
80°	46.1	46.1	46.1	46.1	46.1	46.0	45.9	45.7	45.6	45.4	45.3
82.5°	35.6	35.5	35.3	35.2	35.1	35.0	34.9	34.9	34.9	34.9	34.7
85°	20.1	20.2	20.3	20.4	20.4	20.5	20.5	20.5	20.5	20.5	20.4
87.5°	8.2	8.6	9.0	9.4	9.8	10.2	10.5	10.9	11.1	11.4	11.7
90°	1.2	3.3	5.5	7.5	9.7	11.6	13.5	15.4	17.2	19.1	20.4
92.5°	18.4	16.9	15.4	13.9	12.4	12.5	14.2	15.8	17.4	19.1	20.4
95°	68.0	67.2	66.4	65.6	64.8	59.3	49.3	39.2	29.2	19.1	20.4
97.5°	141.9	143.3	144.7	146.2	147.7	138.4	118.4	98.5	78.6	58.7	51.2
100°	199.2	199.9	200.7	201.5	202.3	203.3	204.3	205.4	206.4	207.5	168.0
102.5°	257.4	258.3	259.4	260.4	261.3	262.2	262.8	263.5	264.1	264.7	257.3
105°	350.6	351.6	352.8	353.8	354.8	355.4	355.4	355.4	355.4	355.4	355.4
107.5°	447.4	447.4	447.4	447.4	447.4	447.7	448.2	448.8	449.3	449.8	449.9
110°	510.4	510.4	510.4	510.4	510.4	510.6	511.2	511.7	512.2	512.8	512.0



TEST NUMBER: P333368-927

CATALOG NUMBER: S125DIW-S375D1560U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	569.6	570.2	570.8	571.5	572.1	572.6	572.9	573.2	573.5	573.9	572.8
115°	658.3	659.6	660.9	662.3	663.5	664.3	664.6	664.9	665.2	665.4	664.3
117.5°	750.1	750.0	750.0	750.0	749.9	750.4	751.4	752.3	753.4	754.4	753.0
120°	807.3	807.1	806.8	806.5	806.3	806.5	807.3	808.1	808.9	809.7	809.2
122.5°	857.9	858.9	859.9	860.9	861.9	862.6	863.0	863.3	863.7	864.1	863.6
125°	936.1	937.9	939.8	941.7	943.6	944.4	944.4	944.4	944.4	944.4	943.4
127.5°	1010.7	1012.1	1013.4	1014.8	1016.1	1016.7	1016.5	1016.4	1016.2	1016.1	1015.4
130°	1056.5	1057.9	1059.2	1060.6	1061.8	1062.6	1063.0	1063.2	1063.4	1063.7	1063.0
132.5°	1102.3	1103.9	1105.4	1107.0	1108.5	1109.0	1108.4	1107.8	1107.2	1106.7	1106.5
135°	1167.4	1169.0	1170.7	1172.3	1173.9	1174.3	1173.9	1173.3	1172.7	1172.3	1171.7
137.5°	1227.3	1228.7	1230.1	1231.4	1232.9	1233.3	1232.8	1232.3	1231.8	1231.4	1231.5
140°	1266.5	1267.0	1267.5	1268.0	1268.6	1268.7	1268.4	1268.2	1267.9	1267.7	1268.2
142.5°	1301.7	1302.0	1302.3	1302.7	1303.0	1303.4	1303.8	1304.1	1304.5	1304.9	1305.0
145°	1353.5	1354.0	1354.6	1355.1	1355.7	1355.9	1355.9	1355.9	1355.9	1355.9	1356.1
147.5°	1398.8	1398.7	1398.6	1398.5	1398.4	1398.5	1398.8	1399.2	1399.5	1399.8	1400.1
150°	1427.4	1426.9	1426.4	1425.8	1425.3	1425.3	1425.8	1426.4	1426.9	1427.4	1428.0
152.5°	1455.1	1454.0	1452.8	1451.6	1450.4	1450.1	1450.6	1451.2	1451.8	1452.2	1452.8
155°	1490.6	1489.1	1487.5	1485.9	1484.3	1483.8	1484.3	1484.8	1485.3	1485.9	1486.7
157.5°	1518.1	1517.1	1516.2	1515.2	1514.3	1513.8	1513.9	1513.9	1513.9	1514.0	1514.9
160°	1537.2	1535.6	1534.0	1532.4	1530.8	1530.1	1530.4	1530.7	1530.9	1531.2	1532.2
162.5°	1552.4	1550.9	1549.3	1547.6	1546.0	1545.4	1545.6	1545.9	1546.2	1546.4	1547.9
165°	1573.0	1571.4	1569.7	1568.1	1566.5	1565.9	1566.1	1566.5	1566.7	1566.9	1568.5
167.5°	1588.2	1586.6	1584.9	1583.3	1581.6	1581.0	1581.2	1581.4	1581.8	1582.0	1583.9
170°	1596.8	1594.9	1593.1	1591.2	1589.4	1588.6	1588.8	1589.1	1589.4	1589.6	1591.7
172.5°	1602.5	1600.7	1598.8	1597.0	1595.1	1594.4	1594.9	1595.4	1595.9	1596.3	1598.2
175°	1608.7	1607.1	1605.5	1603.9	1602.3	1601.7	1602.0	1602.2	1602.5	1602.7	1604.9
177.5°	1611.5	1610.3	1609.0	1607.7	1606.5	1605.9	1606.1	1606.4	1606.5	1606.8	1608.3
180°	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7



TEST NUMBER: P333368-927

CATALOG NUMBER: S125DIW-S375D1560U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8
2.5°	461.4	462.1	462.7	463.0	463.0	462.9	462.9	462.8
5°	459.1	459.9	460.6	460.9	460.8	460.7	460.7	460.6
7.5°	454.5	455.2	455.9	456.2	456.1	456.1	456.0	455.9
10°	450.5	451.1	451.9	452.1	452.0	451.9	451.9	451.8
12.5°	445.3	445.8	446.3	446.6	446.6	446.6	446.6	446.5
15°	436.1	436.5	437.0	437.1	437.1	437.1	437.1	437.1
17.5°	425.5	426.0	426.5	426.5	426.1	425.7	425.3	424.9
20°	417.4	418.0	418.5	418.7	418.2	417.8	417.4	417.0
22.5°	408.2	408.6	409.0	409.0	408.8	408.4	408.2	407.9
25°	393.6	393.7	393.9	393.8	393.6	393.3	393.1	392.8
27.5°	378.1	378.1	378.2	378.1	377.8	377.6	377.3	377.1
30°	366.9	366.7	366.5	366.4	366.1	365.9	365.6	365.4
32.5°	355.5	355.2	354.9	354.6	354.1	353.6	353.2	352.8
35°	337.9	337.5	337.0	336.5	335.9	335.2	334.5	333.9
37.5°	319.3	318.7	318.1	317.6	317.2	316.9	316.5	316.1
40°	306.4	305.7	305.0	304.5	304.3	304.0	303.7	303.5
42.5°	293.7	293.0	292.3	291.8	291.4	291.0	290.7	290.3
45°	274.8	273.9	272.9	272.3	272.0	271.8	271.6	271.3
47.5°	254.9	254.0	252.9	252.2	251.6	251.0	250.5	249.9
50°	241.4	240.3	239.2	238.4	237.8	237.3	236.7	236.1
52.5°	228.1	227.2	226.2	225.5	224.9	224.3	223.6	223.0
55°	207.6	206.8	206.1	205.5	204.9	204.3	203.7	203.2
57.5°	187.2	186.2	185.3	184.7	184.3	184.0	183.7	183.4
60°	173.4	172.5	171.7	171.0	170.5	169.9	169.4	168.8
62.5°	160.1	159.1	158.3	157.6	157.2	156.8	156.3	155.9
65°	139.1	138.4	137.7	137.1	136.8	136.5	136.2	135.9
67.5°	119.1	118.5	117.9	117.5	117.3	117.1	116.9	116.7
70°	105.9	105.4	105.0	104.6	104.3	103.9	103.5	103.2
72.5°	93.5	92.9	92.4	92.0	91.7	91.3	90.9	90.6
75°	74.2	74.0	73.7	73.4	73.1	72.8	72.5	72.1
77.5°	56.6	56.4	56.2	56.1	55.8	55.6	55.4	55.1
80°	45.2	45.2	45.1	44.9	44.8	44.6	44.4	44.3
82.5°	34.5	34.4	34.3	34.1	34.1	34.1	34.1	34.1
85°	20.4	20.3	20.2	20.0	19.9	19.7	19.6	19.4
87.5°	12.0	12.2	12.5	12.7	12.7	12.7	12.8	12.8
90°	21.7	23.1	24.4	25.4	26.2	27.0	27.8	28.6
92.5°	21.7	23.1	24.4	25.2	25.6	26.0	26.4	26.7
95°	21.7	23.1	24.4	25.0	25.0	25.0	25.0	25.0
97.5°	43.7	36.3	28.8	25.0	25.0	25.0	25.0	25.0
100°	128.5	89.0	49.6	29.3	28.2	27.2	26.1	25.0
102.5°	249.8	242.3	234.9	222.1	204.1	186.1	168.0	150.0
105°	355.4	355.4	355.4	355.2	355.0	354.7	354.4	354.2
107.5°	450.0	450.0	450.0	449.6	448.9	448.1	447.3	446.5
110°	511.2	510.4	509.6	509.4	509.6	509.8	510.2	510.4



TEST NUMBER: P333368-927

CATALOG NUMBER: S125DIW-S375D1560U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	571.8	570.8	569.8	569.1	568.8	568.4	568.0	567.6
115°	663.3	662.3	661.2	659.9	658.3	656.6	655.1	653.5
117.5°	751.6	750.3	748.8	747.8	747.2	746.5	745.8	745.0
120°	808.7	808.1	807.6	806.7	805.3	804.0	802.7	801.4
122.5°	863.0	862.5	862.0	860.9	859.4	857.9	856.3	854.8
125°	942.4	941.3	940.2	939.3	938.5	937.7	936.9	936.1
127.5°	1014.9	1014.3	1013.7	1012.4	1010.4	1008.5	1006.5	1004.6
130°	1062.2	1061.4	1060.6	1059.5	1058.2	1056.9	1055.5	1054.2
132.5°	1106.4	1106.2	1106.0	1105.3	1104.0	1102.6	1101.3	1099.9
135°	1171.2	1170.7	1170.1	1169.0	1167.4	1165.9	1164.3	1162.7
137.5°	1231.6	1231.7	1231.8	1231.2	1229.8	1228.4	1227.0	1225.7
140°	1268.7	1269.2	1269.8	1269.2	1267.7	1266.1	1264.5	1262.9
142.5°	1305.0	1305.2	1305.3	1304.6	1302.9	1301.3	1299.7	1298.1
145°	1356.5	1356.7	1356.9	1356.3	1354.7	1353.1	1351.5	1350.0
147.5°	1400.4	1400.7	1401.1	1400.3	1398.4	1396.5	1394.6	1392.7
150°	1428.5	1429.0	1429.6	1428.8	1426.6	1424.5	1422.4	1420.3
152.5°	1453.3	1453.8	1454.4	1453.7	1451.8	1449.9	1448.0	1446.0
155°	1487.5	1488.3	1489.1	1488.4	1486.3	1484.2	1482.0	1479.9
157.5°	1515.7	1516.6	1517.4	1516.8	1514.7	1512.5	1510.4	1508.3
160°	1533.3	1534.4	1535.4	1534.9	1532.8	1530.7	1528.5	1526.5
162.5°	1549.4	1550.9	1552.4	1552.0	1549.7	1547.3	1545.0	1542.6
165°	1570.1	1571.8	1573.4	1573.0	1571.0	1568.8	1566.7	1564.6
167.5°	1585.8	1587.7	1589.6	1589.4	1587.0	1584.6	1582.2	1579.8
170°	1593.9	1596.0	1598.1	1598.0	1595.6	1593.2	1590.8	1588.4
172.5°	1600.1	1602.0	1603.9	1603.7	1601.3	1598.9	1596.6	1594.2
175°	1606.9	1609.1	1611.2	1611.1	1608.7	1606.3	1603.9	1601.6
177.5°	1609.8	1611.2	1612.7	1612.6	1610.9	1609.2	1607.5	1605.8
180°	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7

(END OF REPORT)