

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332774-840

Luminaire Tested: **S124DIW-S575D1560U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332774-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S575D1560U840-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7985.1 lumens
Efficiency: N/A
Efficacy: 131.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332774-840

CATALOG NUMBER: S124DIW-S575D1560U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332774-840

CATALOG NUMBER: S124DIW-S575D1560U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	32
1	94	89	86	82	84	81	77	74	64	62	60	49	47	46	35	34	33	27
2	85	78	72	67	76	70	65	61	56	52	49	43	40	38	30	29	28	22
3	78	69	61	56	70	62	56	51	49	45	41	38	35	32	27	25	24	19
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20	16
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	19	18	14
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16	12
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14	11
8	51	39	32	27	46	36	29	24	29	24	20	22	19	16	16	14	12	10
9	48	36	28	24	43	32	26	22	26	22	18	21	17	15	15	13	11	9
10	44	33	26	21	40	30	24	19	24	19	16	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7917	7917	7917
5°	7942	7846	7903
10°	7891	7782	7820
15°	7796	7672	7691
20°	7669	7534	7541
25°	7525	7378	7357
30°	7347	7194	7127
35°	7164	7001	6908
40°	6973	6783	6658
45°	6774	6567	6441
50°	6553	6376	6178
55°	6315	6128	5928
60°	6077	5848	5670
65°	5809	5585	5358
70°	5509	5231	5028
75°	5050	4803	4682
80°	4491	4310	4203
85°	3927	3788	3714



TEST NUMBER: P332774-840

CATALOG NUMBER: S124DIW-S575D1560U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.4	1.2
10°-20°	260.2	3.3
20°-30°	383.0	4.8
30°-40°	445.3	5.6
40°-50°	445.3	5.6
50°-60°	389.5	4.9
60°-70°	289.3	3.6
70°-80°	164.3	2.1
80°-90°	53.3	0.7
90°-100°	129.9	1.6
100°-110°	384.7	4.8
110°-120°	652.9	8.2
120°-130°	861.0	10.8
130°-140°	966.9	12.1
140°-150°	950.1	11.9
150°-160°	799.1	10.0
160°-170°	531.7	6.7
170°-180°	186.2	2.3
0°-30°	735.6	9.2
0°-40°	1180.9	14.8
0°-60°	2015.7	25.2
0°-90°	2522.6	31.6
90°-120°	1167.5	14.6
90°-150°	3945.5	49.4
90°-180°	5463.0	68.4
0°-180°	7985.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	981	981	981	981	981	
5°	980	976	968	976	975	93
15°	933	929	918	922	920	263
25°	845	839	828	829	826	388
35°	727	721	710	705	701	454
45°	593	587	575	567	564	457
55°	449	446	435	426	421	402
65°	304	300	292	285	280	301
75°	162	158	154	151	150	172
85°	42	42	41	41	40	47
90°	4	21	34	42	46	8
95°	91	105	116	120	120	102
105°	355	357	362	367	372	376
115°	664	664	661	659	658	654
125°	967	967	965	962	959	861
135°	1247	1256	1256	1253	1249	964
145°	1515	1521	1523	1521	1517	948
155°	1736	1736	1734	1740	1734	798
165°	1890	1885	1882	1890	1885	532
175°	1966	1958	1957	1966	1957	187
180°	1969	1969	1969	1969	1969	



TEST NUMBER: P332774-840

CATALOG NUMBER: S124DIW-S575D1560U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	980.7	980.7	980.7	980.7	980.7	980.7	980.7	980.7	980.7	980.7	980.7
2.5°	983.2	982.8	982.4	982.0	981.6	980.6	979.1	977.5	975.9	974.4	975.8
5°	980.0	979.3	978.6	977.9	977.1	975.8	973.9	972.0	970.1	968.2	970.1
7.5°	970.8	970.1	969.5	968.8	968.1	966.6	964.5	962.4	960.2	958.1	959.7
10°	962.6	962.0	961.3	960.6	959.9	958.4	956.1	953.8	951.6	949.3	950.7
12.5°	952.0	951.3	950.6	949.9	949.2	947.7	945.2	942.8	940.4	938.0	939.5
15°	932.8	932.1	931.4	930.7	930.0	928.4	925.7	923.1	920.5	917.9	918.9
17.5°	909.7	908.8	908.0	907.1	906.2	904.5	902.0	899.6	897.1	894.6	895.2
20°	892.7	891.8	891.0	890.1	889.2	887.5	884.8	882.2	879.6	877.0	877.5
22.5°	874.4	873.3	872.2	871.0	869.9	868.0	865.4	862.7	860.1	857.5	858.5
25°	844.8	843.5	842.3	841.1	839.9	838.1	835.6	833.1	830.7	828.3	828.5
27.5°	810.8	809.6	808.3	807.1	805.8	804.1	801.7	799.5	797.2	795.0	794.6
30°	788.2	786.8	785.4	784.0	782.6	780.7	778.5	776.2	774.0	771.7	771.0
32.5°	764.3	763.1	761.7	760.5	759.3	757.4	755.1	752.7	750.2	747.8	747.0
35°	726.9	725.7	724.5	723.3	722.1	720.1	717.7	715.3	712.9	710.4	709.1
37.5°	687.4	686.3	685.2	684.1	683.0	681.2	678.5	675.9	673.3	670.7	669.3
40°	661.7	660.2	658.8	657.5	656.1	654.1	651.5	648.8	646.2	643.6	641.9
42.5°	634.0	633.2	632.4	631.5	630.7	628.7	625.9	623.0	620.1	617.2	615.2
45°	593.3	592.1	590.9	589.7	588.4	586.4	583.6	580.8	578.0	575.2	573.3
47.5°	550.7	549.9	549.1	548.2	547.3	545.6	543.1	540.5	537.9	535.3	533.1
50°	521.8	521.1	520.4	519.7	519.0	517.5	515.0	512.5	510.1	507.7	505.2
52.5°	493.5	492.7	491.8	491.0	490.2	488.5	485.8	483.3	480.7	478.1	475.9
55°	448.7	448.2	447.7	447.2	446.7	445.1	442.7	440.2	437.8	435.4	433.2
57.5°	406.0	405.4	404.8	404.1	403.5	402.1	399.7	397.3	394.9	392.4	390.4
60°	376.4	375.6	374.7	373.8	372.9	371.3	369.1	366.8	364.6	362.2	360.7
62.5°	347.5	346.8	346.0	345.3	344.6	343.0	340.6	338.2	335.8	333.4	331.9
65°	304.1	303.3	302.4	301.5	300.6	299.3	297.6	295.8	294.1	292.4	290.5
67.5°	260.4	259.6	258.8	258.0	257.2	256.0	254.3	252.7	251.0	249.2	247.6
70°	233.4	232.2	231.0	229.7	228.5	227.2	225.8	224.4	223.0	221.6	220.3
72.5°	204.5	203.3	202.1	200.8	199.5	198.4	197.3	196.2	195.1	193.9	192.8
75°	161.9	161.0	160.2	159.3	158.3	157.5	156.6	155.7	154.9	154.0	153.3
77.5°	121.2	120.8	120.4	120.1	119.7	119.1	118.3	117.5	116.7	116.0	115.7
80°	96.6	96.1	95.6	95.1	94.5	94.1	93.8	93.4	93.1	92.7	92.4
82.5°	72.8	72.5	72.3	72.0	71.8	71.6	71.6	71.5	71.4	71.4	71.1
85°	42.4	42.4	42.4	42.4	42.4	42.2	41.9	41.6	41.2	40.9	40.9
87.5°	17.3	17.9	18.5	19.1	19.7	20.2	20.6	21.0	21.4	21.8	22.2
90°	4.5	8.3	12.0	15.8	19.5	22.7	25.3	28.1	30.8	33.5	35.5
92.5°	32.6	36.9	41.1	45.3	49.7	52.7	54.6	56.6	58.4	60.3	61.5
95°	91.4	94.4	97.5	100.5	103.5	106.2	108.7	111.0	113.4	115.7	116.7
97.5°	159.6	162.0	164.4	166.9	169.4	172.0	174.7	177.4	180.3	183.0	184.2
100°	213.2	214.5	215.9	217.2	218.6	220.8	223.9	226.9	229.9	233.0	233.7
102.5°	269.2	269.7	270.3	270.8	271.4	273.1	275.8	278.6	281.3	284.2	285.1
105°	354.8	355.2	355.5	355.8	356.2	357.0	358.3	359.7	361.0	362.4	363.5
107.5°	444.6	445.0	445.5	445.9	446.3	446.6	446.8	447.0	447.2	447.4	448.3
110°	505.5	506.2	506.9	507.6	508.3	508.5	508.1	507.8	507.4	507.1	506.3



TEST NUMBER: P332774-840

CATALOG NUMBER: S124DIW-S575D1560U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	568.9	569.1	569.2	569.3	569.5	569.2	568.6	567.9	567.3	566.7	566.6
115°	663.9	663.9	663.9	663.9	663.9	663.6	662.9	662.2	661.6	660.9	660.6
117.5°	753.5	753.7	754.0	754.3	754.6	754.5	754.0	753.5	753.0	752.6	751.3
120°	813.1	814.5	815.9	817.2	818.5	818.7	817.7	816.7	815.7	814.7	812.9
122.5°	875.3	875.8	876.4	876.9	877.4	877.5	877.0	876.5	876.1	875.6	874.4
125°	966.9	966.9	966.9	966.9	966.9	966.7	966.4	966.0	965.7	965.4	964.7
127.5°	1050.1	1051.1	1052.1	1053.1	1054.1	1054.4	1053.8	1053.3	1052.8	1052.2	1051.5
130°	1108.5	1109.5	1110.5	1111.6	1112.6	1113.1	1113.1	1113.1	1113.1	1113.1	1112.5
132.5°	1168.2	1169.0	1169.7	1170.4	1171.2	1171.4	1171.1	1170.9	1170.6	1170.3	1169.7
135°	1247.1	1249.1	1251.1	1253.2	1255.3	1256.3	1256.3	1256.3	1256.3	1256.3	1255.6
137.5°	1333.0	1333.9	1334.8	1335.8	1336.8	1337.6	1338.1	1338.6	1339.2	1339.7	1338.8
140°	1390.3	1390.9	1391.6	1392.3	1392.9	1393.3	1393.3	1393.3	1393.3	1393.3	1392.9
142.5°	1442.6	1443.3	1444.0	1444.6	1445.3	1445.5	1445.2	1445.0	1444.7	1444.4	1444.4
145°	1515.1	1516.4	1517.8	1519.1	1520.6	1521.4	1521.7	1522.1	1522.4	1522.7	1522.4
147.5°	1587.0	1588.6	1590.2	1591.9	1593.5	1594.2	1593.9	1593.6	1593.4	1593.1	1592.8
150°	1630.8	1632.1	1633.6	1634.9	1636.3	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9
152.5°	1672.2	1673.0	1673.9	1674.7	1675.5	1676.1	1676.3	1676.6	1676.9	1677.1	1677.9
155°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.8	1735.4	1735.0	1734.7	1734.3	1735.8
157.5°	1789.5	1788.9	1788.3	1787.7	1787.1	1786.8	1786.7	1786.6	1786.6	1786.5	1787.5
160°	1821.2	1820.8	1820.5	1820.2	1819.8	1819.5	1819.2	1818.8	1818.5	1818.2	1819.2
162.5°	1850.4	1849.6	1848.7	1847.8	1846.8	1846.2	1845.9	1845.6	1845.2	1844.9	1846.7
165°	1889.7	1888.6	1887.6	1886.6	1885.6	1884.8	1884.1	1883.4	1882.8	1882.1	1884.1
167.5°	1919.9	1918.4	1917.0	1915.6	1914.2	1913.5	1913.6	1913.6	1913.7	1913.8	1915.8
170°	1936.9	1935.2	1933.5	1931.8	1930.2	1929.4	1929.8	1930.2	1930.5	1930.8	1932.8
172.5°	1949.0	1947.6	1946.2	1944.8	1943.4	1942.7	1942.8	1942.9	1942.9	1943.0	1945.3
175°	1965.8	1964.1	1962.5	1960.8	1959.0	1958.0	1957.7	1957.3	1957.0	1956.7	1959.0
177.5°	1971.3	1969.9	1968.6	1967.2	1965.9	1965.2	1965.2	1965.2	1965.2	1965.2	1967.1
180°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8



TEST NUMBER: P332774-840

CATALOG NUMBER: S124DIW-S575D1560U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	980.7	980.7	980.7	980.7	980.7	980.7	980.7	980.7
2.5°	977.2	978.7	980.1	980.7	980.5	980.4	980.3	980.1
5°	972.0	973.9	975.8	976.6	976.2	975.9	975.5	975.2
7.5°	961.2	962.7	964.2	964.9	964.7	964.5	964.3	964.0
10°	952.1	953.5	954.9	955.4	955.0	954.7	954.3	954.0
12.5°	941.1	942.6	944.1	944.6	944.1	943.6	943.2	942.7
15°	920.0	921.0	922.0	922.3	921.8	921.3	920.7	920.2
17.5°	896.0	896.6	897.3	897.4	897.1	896.7	896.4	896.1
20°	878.1	878.6	879.1	879.2	878.8	878.5	878.2	877.8
22.5°	859.4	860.3	861.3	861.4	860.8	860.2	859.6	858.9
25°	828.6	828.8	829.0	828.7	828.0	827.3	826.6	825.9
27.5°	794.2	793.7	793.2	792.6	791.7	790.9	790.0	789.1
30°	770.3	769.6	768.9	768.1	767.2	766.4	765.5	764.6
32.5°	746.1	745.3	744.5	743.6	742.8	741.8	740.9	740.1
35°	707.9	706.7	705.5	704.5	703.6	702.7	701.9	700.9
37.5°	668.0	666.6	665.3	664.1	663.0	661.8	660.7	659.4
40°	640.2	638.3	636.6	635.3	634.4	633.6	632.7	631.8
42.5°	613.2	611.1	609.0	607.7	607.2	606.6	606.0	605.4
45°	571.4	569.5	567.5	566.3	565.8	565.3	564.7	564.2
47.5°	531.0	528.8	526.6	524.9	523.6	522.2	520.9	519.6
50°	502.7	500.3	497.9	496.1	495.0	494.0	493.0	491.9
52.5°	473.7	471.6	469.5	467.7	466.4	465.0	463.7	462.4
55°	431.2	429.1	427.0	425.4	424.3	423.3	422.2	421.2
57.5°	388.5	386.5	384.5	382.9	381.9	380.9	379.9	378.9
60°	359.1	357.6	356.0	354.8	353.9	353.0	352.1	351.2
62.5°	330.5	329.0	327.6	326.5	325.6	324.8	323.9	323.0
65°	288.8	287.1	285.4	284.1	283.2	282.3	281.4	280.5
67.5°	245.9	244.3	242.6	241.6	241.4	241.2	240.9	240.7
70°	218.8	217.4	216.0	215.1	214.5	214.0	213.5	213.0
72.5°	191.7	190.6	189.5	188.6	188.1	187.6	187.1	186.5
75°	152.6	151.9	151.3	150.8	150.6	150.5	150.3	150.1
77.5°	115.5	115.3	115.1	114.8	114.3	113.9	113.4	113.0
80°	92.0	91.7	91.3	91.1	90.9	90.7	90.6	90.4
82.5°	70.9	70.7	70.5	70.3	70.2	70.0	69.8	69.6
85°	40.9	40.9	40.9	40.8	40.6	40.4	40.3	40.1
87.5°	22.6	23.0	23.4	23.7	23.8	23.9	24.1	24.2
90°	37.6	39.6	41.6	43.0	43.6	44.3	45.0	45.6
92.5°	62.7	63.9	65.1	65.9	66.3	66.8	67.2	67.6
95°	117.8	118.8	119.8	120.3	120.3	120.3	120.3	120.3
97.5°	185.5	186.7	187.9	188.5	188.5	188.5	188.5	188.5
100°	234.3	235.0	235.7	236.0	236.0	236.0	236.0	236.0
102.5°	286.0	287.0	287.9	288.5	288.8	289.1	289.3	289.6
105°	364.5	365.5	366.5	367.5	368.5	369.5	370.5	371.5
107.5°	449.3	450.2	451.2	451.6	451.5	451.5	451.4	451.3
110°	505.7	505.0	504.3	504.5	505.5	506.5	507.6	508.6



TEST NUMBER: P332774-840

CATALOG NUMBER: S124DIW-S575D1560U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	566.4	566.3	566.2	566.2	566.4	566.6	566.8	567.0
115°	660.1	659.8	659.5	659.1	658.8	658.5	658.1	657.8
117.5°	750.2	749.1	747.9	747.0	746.3	745.7	745.0	744.3
120°	811.2	809.6	807.9	807.4	808.1	808.7	809.4	810.1
122.5°	873.2	872.1	871.0	869.8	868.6	867.4	866.2	864.9
125°	964.0	963.4	962.7	962.0	961.3	960.7	960.0	959.3
127.5°	1050.9	1050.2	1049.5	1048.8	1048.3	1047.8	1047.2	1046.7
130°	1111.8	1111.1	1110.3	1109.3	1108.0	1106.7	1105.3	1104.0
132.5°	1169.0	1168.3	1167.6	1167.0	1166.5	1166.0	1165.4	1164.9
135°	1254.9	1254.3	1253.5	1252.6	1251.6	1250.6	1249.6	1248.6
137.5°	1338.0	1337.1	1336.2	1335.8	1336.1	1336.3	1336.5	1336.7
140°	1392.6	1392.3	1391.9	1391.6	1391.3	1390.9	1390.6	1390.3
142.5°	1444.3	1444.2	1444.2	1444.1	1444.0	1444.0	1443.9	1443.8
145°	1522.1	1521.7	1521.4	1520.7	1519.6	1518.6	1517.6	1516.6
147.5°	1592.6	1592.3	1592.0	1591.6	1591.3	1591.0	1590.6	1590.3
150°	1636.9	1636.9	1636.9	1636.8	1636.4	1636.1	1635.8	1635.4
152.5°	1678.7	1679.5	1680.3	1680.3	1679.4	1678.6	1677.7	1676.8
155°	1737.1	1738.4	1739.8	1739.8	1738.4	1737.1	1735.8	1734.3
157.5°	1788.5	1789.5	1790.5	1790.4	1789.3	1788.2	1787.0	1785.8
160°	1820.2	1821.2	1822.2	1821.8	1820.2	1818.5	1816.7	1815.0
162.5°	1848.6	1850.4	1852.2	1852.3	1850.6	1849.0	1847.2	1845.5
165°	1886.1	1888.1	1890.2	1890.6	1889.2	1887.8	1886.4	1885.1
167.5°	1917.8	1919.9	1921.9	1921.9	1919.8	1917.6	1915.5	1913.4
170°	1934.9	1936.9	1938.9	1938.7	1936.4	1934.0	1931.7	1929.2
172.5°	1947.6	1949.8	1952.2	1952.2	1949.7	1947.4	1945.0	1942.7
175°	1961.5	1963.8	1966.2	1966.2	1963.8	1961.5	1959.0	1956.7
177.5°	1969.0	1970.9	1972.8	1972.7	1970.4	1968.3	1966.2	1964.0
180°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8

(END OF REPORT)