

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333344-927

Luminaire Tested: **S125DIW-S375D470U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333344-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S375D470U927-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2689.8 lumens
Efficiency: N/A
Efficacy: 116.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 23
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333344-927

CATALOG NUMBER: S125DIW-S375D470U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333344-927

CATALOG NUMBER: S125DIW-S375D470U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	97	92	88	85	88	85	81	78	70	68	66	57	56	54	45	44	43	38
2	88	80	74	69	80	74	69	64	62	58	54	50	48	45	40	38	36	31
3	80	71	63	58	73	65	59	54	54	50	46	44	41	38	35	33	31	27
4	73	63	55	49	67	58	51	45	48	43	39	40	36	33	31	29	27	23
5	67	56	48	42	61	51	44	39	43	38	34	35	31	28	28	25	23	20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	20	17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	33	28	49	38	31	26	32	27	23	27	22	19	22	18	16	14
9	49	37	30	25	45	35	28	23	29	24	20	24	20	17	20	17	15	12
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2989	2989	2989
5°	2995	2967	2986
10°	2977	2946	2963
15°	2945	2910	2923
20°	2899	2861	2866
25°	2849	2802	2799
30°	2788	2738	2725
35°	2722	2670	2633
40°	2655	2596	2559
45°	2582	2528	2478
50°	2502	2446	2372
55°	2423	2354	2288
60°	2331	2260	2180
65°	2222	2149	2077
70°	2115	2019	1949
75°	1926	1864	1799
80°	1715	1689	1648
85°	1489	1519	1438



TEST NUMBER: P333344-927

CATALOG NUMBER: S125DIW-S375D470U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.6	1.6
10°-20°	123.3	4.6
20°-30°	182.0	6.8
30°-40°	212.4	7.9
40°-50°	213.3	7.9
50°-60°	187.2	7.0
60°-70°	139.5	5.2
70°-80°	79.8	3.0
80°-90°	24.2	0.9
90°-100°	17.6	0.7
100°-110°	108.3	4.0
110°-120°	196.4	7.3
120°-130°	252.0	9.4
130°-140°	271.1	10.1
140°-150°	254.4	9.5
150°-160°	205.8	7.7
160°-170°	133.1	4.9
170°-180°	45.9	1.7
0°-30°	348.9	13.0
0°-40°	561.2	20.9
0°-60°	961.7	35.8
0°-90°	1205.2	44.8
90°-120°	322.2	12.0
90°-150°	1099.7	40.9
90°-180°	1485.0	55.2
0°-180°	2689.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	463	463	463	463	463	
5°	462	461	458	461	461	44
15°	440	439	435	437	437	124
25°	400	398	393	394	393	184
35°	345	344	339	337	334	216
45°	283	281	277	273	271	218
55°	215	214	209	206	203	192
65°	145	144	141	137	136	144
75°	77	76	75	74	72	82
85°	20	20	20	20	19	23
90°	0	3	6	8	9	2
95°	20	19	6	7	8	26
105°	105	107	107	107	106	112
115°	198	200	200	198	196	196
125°	281	284	284	282	281	251
135°	351	353	352	351	349	270
145°	407	407	408	408	406	254
155°	448	446	447	447	445	206
165°	473	471	471	473	470	133
175°	484	481	482	484	481	46
180°	484	484	484	484	484	



TEST NUMBER: P333344-927

CATALOG NUMBER: S125DIW-S375D470U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8
2.5°	463.9	463.7	463.6	463.3	463.2	462.7	462.1	461.4	460.8	460.1	460.8
5°	462.0	461.8	461.7	461.5	461.4	460.9	460.1	459.3	458.4	457.6	458.4
7.5°	457.8	457.6	457.5	457.3	457.2	456.6	455.7	454.8	453.9	453.0	453.8
10°	454.0	453.8	453.7	453.5	453.4	452.8	451.9	451.0	450.1	449.2	449.9
12.5°	449.3	449.0	448.7	448.5	448.1	447.6	446.7	445.9	445.0	444.3	444.7
15°	440.5	440.2	440.0	439.7	439.4	438.9	438.0	437.1	436.2	435.3	435.7
17.5°	430.2	429.9	429.5	429.2	428.8	428.2	427.2	426.4	425.4	424.5	425.0
20°	421.8	421.6	421.4	421.3	421.1	420.5	419.5	418.4	417.3	416.3	416.8
22.5°	413.3	413.0	412.6	412.4	412.1	411.5	410.4	409.5	408.4	407.5	407.9
25°	399.8	399.4	398.9	398.5	398.2	397.4	396.4	395.3	394.3	393.2	393.4
27.5°	384.0	383.8	383.6	383.3	383.1	382.4	381.4	380.2	379.1	378.0	378.1
30°	373.8	373.6	373.3	373.0	372.8	372.1	370.9	369.6	368.4	367.2	367.0
32.5°	362.7	362.3	361.9	361.6	361.2	360.4	359.3	358.2	357.2	356.1	355.8
35°	345.2	344.9	344.6	344.3	344.0	343.2	342.1	341.0	339.8	338.7	338.3
37.5°	327.2	326.8	326.4	325.9	325.5	324.8	323.7	322.7	321.5	320.5	319.9
40°	314.9	314.4	314.0	313.6	313.2	312.4	311.3	310.2	309.0	307.9	307.2
42.5°	301.7	301.3	301.0	300.6	300.3	299.6	298.4	297.3	296.1	295.0	294.4
45°	282.7	282.3	282.0	281.7	281.3	280.7	279.7	278.8	277.7	276.8	275.8
47.5°	262.1	262.1	262.1	262.2	262.2	261.7	260.5	259.3	258.1	256.9	256.0
50°	249.0	248.7	248.5	248.2	248.0	247.4	246.4	245.4	244.5	243.4	242.4
52.5°	235.5	235.3	235.1	235.0	234.8	234.2	233.1	232.1	231.0	230.0	229.1
55°	215.2	215.0	214.8	214.5	214.3	213.6	212.5	211.4	210.2	209.1	208.3
57.5°	194.0	193.8	193.7	193.6	193.5	192.9	191.9	191.0	190.0	189.1	188.1
60°	180.5	180.1	179.8	179.5	179.2	178.6	177.7	176.8	175.9	175.0	174.2
62.5°	166.4	166.2	165.9	165.6	165.4	164.9	164.1	163.3	162.6	161.8	161.0
65°	145.4	145.2	145.0	144.9	144.7	144.2	143.3	142.4	141.5	140.6	139.8
67.5°	124.9	124.6	124.2	123.9	123.6	123.0	122.4	121.7	121.0	120.4	119.8
70°	112.0	111.6	111.2	110.8	110.4	109.8	109.1	108.4	107.7	106.9	106.4
72.5°	98.0	97.7	97.4	97.1	96.9	96.5	96.0	95.5	95.1	94.6	94.0
75°	77.2	77.1	76.9	76.8	76.6	76.3	75.9	75.5	75.1	74.7	74.5
77.5°	58.1	58.1	58.0	57.9	57.9	57.8	57.5	57.3	57.0	56.8	56.6
80°	46.1	46.1	46.1	46.1	46.1	46.0	45.9	45.7	45.6	45.4	45.3
82.5°	35.6	35.5	35.3	35.2	35.1	35.0	34.9	34.9	34.9	34.9	34.7
85°	20.1	20.2	20.3	20.4	20.4	20.5	20.5	20.5	20.5	20.5	20.4
87.5°	8.0	8.1	8.2	8.4	8.5	8.6	8.6	8.6	8.7	8.8	8.9
90°	0.4	1.0	1.7	2.3	2.9	3.5	4.0	4.6	5.1	5.7	6.1
92.5°	5.5	5.1	4.6	4.2	3.7	3.7	4.3	4.8	5.2	5.7	6.1
95°	20.4	20.2	20.0	19.7	19.5	17.8	14.8	11.8	8.8	5.7	6.1
97.5°	42.6	43.1	43.5	44.0	44.4	41.6	35.6	29.6	23.6	17.7	15.4
100°	59.8	60.1	60.4	60.6	60.8	61.1	61.4	61.7	62.0	62.3	50.5
102.5°	77.3	77.6	78.0	78.3	78.6	78.8	79.0	79.1	79.4	79.5	77.3
105°	105.4	105.7	106.0	106.3	106.6	106.8	106.8	106.8	106.8	106.8	106.8
107.5°	134.4	134.4	134.4	134.4	134.4	134.5	134.7	134.8	135.0	135.1	135.2
110°	153.4	153.4	153.4	153.4	153.4	153.4	153.6	153.8	153.9	154.1	153.8



TEST NUMBER: P333344-927

CATALOG NUMBER: S125DIW-S375D470U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	171.2	171.3	171.5	171.7	171.9	172.1	172.1	172.3	172.4	172.5	172.1
115°	197.8	198.2	198.6	199.0	199.4	199.6	199.7	199.8	199.9	199.9	199.6
117.5°	225.5	225.4	225.4	225.4	225.4	225.5	225.8	226.1	226.4	226.7	226.3
120°	242.6	242.6	242.5	242.4	242.3	242.4	242.6	242.9	243.1	243.4	243.2
122.5°	257.9	258.1	258.4	258.7	259.0	259.2	259.4	259.4	259.6	259.7	259.5
125°	281.3	281.9	282.4	283.0	283.5	283.8	283.8	283.8	283.8	283.8	283.5
127.5°	303.7	304.2	304.6	305.0	305.4	305.5	305.5	305.5	305.4	305.3	305.1
130°	317.5	317.9	318.3	318.7	319.1	319.3	319.4	319.5	319.6	319.6	319.4
132.5°	331.3	331.8	332.2	332.6	333.1	333.3	333.1	333.0	332.7	332.6	332.6
135°	350.9	351.3	351.8	352.3	352.8	352.9	352.8	352.6	352.4	352.3	352.1
137.5°	368.8	369.2	369.6	370.1	370.5	370.7	370.5	370.3	370.2	370.0	370.1
140°	380.6	380.7	380.9	381.0	381.2	381.3	381.2	381.1	381.0	381.0	381.1
142.5°	391.2	391.3	391.4	391.5	391.6	391.7	391.8	391.9	392.1	392.1	392.1
145°	406.8	406.9	407.1	407.3	407.4	407.5	407.5	407.5	407.5	407.5	407.6
147.5°	420.4	420.3	420.3	420.3	420.3	420.3	420.4	420.5	420.6	420.6	420.7
150°	429.0	428.8	428.6	428.5	428.3	428.3	428.5	428.6	428.8	429.0	429.1
152.5°	437.3	437.0	436.6	436.3	435.9	435.8	435.9	436.1	436.3	436.4	436.6
155°	448.0	447.5	447.0	446.6	446.1	445.9	446.1	446.2	446.4	446.6	446.8
157.5°	456.2	455.9	455.7	455.3	455.0	455.0	455.0	455.0	455.0	455.0	455.3
160°	461.9	461.4	461.0	460.5	460.0	459.9	459.9	460.0	460.1	460.2	460.5
162.5°	466.5	466.0	465.6	465.1	464.6	464.5	464.5	464.6	464.7	464.8	465.2
165°	472.7	472.2	471.7	471.3	470.8	470.6	470.6	470.7	470.8	470.9	471.3
167.5°	477.3	476.8	476.3	475.8	475.3	475.1	475.2	475.2	475.3	475.4	476.0
170°	479.9	479.3	478.7	478.2	477.6	477.4	477.4	477.5	477.6	477.7	478.3
172.5°	481.6	481.0	480.5	479.9	479.3	479.2	479.3	479.4	479.6	479.7	480.3
175°	483.5	483.0	482.5	482.0	481.6	481.3	481.4	481.5	481.6	481.6	482.3
177.5°	484.3	483.9	483.5	483.2	482.8	482.6	482.7	482.8	482.8	482.9	483.3
180°	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5



TEST NUMBER: P333344-927

CATALOG NUMBER: S125DIW-S375D470U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8
2.5°	461.4	462.1	462.7	463.0	463.0	462.9	462.9	462.8
5°	459.1	459.9	460.6	460.9	460.8	460.7	460.7	460.6
7.5°	454.5	455.2	455.9	456.2	456.1	456.1	456.0	455.9
10°	450.5	451.1	451.9	452.1	452.0	451.9	451.9	451.8
12.5°	445.3	445.8	446.3	446.6	446.6	446.6	446.6	446.5
15°	436.1	436.5	437.0	437.1	437.1	437.1	437.1	437.1
17.5°	425.5	426.0	426.5	426.5	426.1	425.7	425.3	424.9
20°	417.4	418.0	418.5	418.7	418.2	417.8	417.4	417.0
22.5°	408.2	408.6	409.0	409.0	408.8	408.4	408.2	407.9
25°	393.6	393.7	393.9	393.8	393.6	393.3	393.1	392.8
27.5°	378.1	378.1	378.2	378.1	377.8	377.6	377.3	377.1
30°	366.9	366.7	366.5	366.4	366.1	365.9	365.6	365.4
32.5°	355.5	355.2	354.9	354.6	354.1	353.6	353.2	352.8
35°	337.9	337.5	337.0	336.5	335.9	335.2	334.5	333.9
37.5°	319.3	318.7	318.1	317.6	317.2	316.9	316.5	316.1
40°	306.4	305.7	305.0	304.5	304.3	304.0	303.7	303.5
42.5°	293.7	293.0	292.3	291.8	291.4	291.0	290.7	290.3
45°	274.8	273.9	272.9	272.3	272.0	271.8	271.6	271.3
47.5°	254.9	254.0	252.9	252.2	251.6	251.0	250.5	249.9
50°	241.4	240.3	239.2	238.4	237.8	237.3	236.7	236.1
52.5°	228.1	227.2	226.2	225.5	224.9	224.3	223.6	223.0
55°	207.6	206.8	206.1	205.5	204.9	204.3	203.7	203.2
57.5°	187.2	186.2	185.3	184.7	184.3	184.0	183.7	183.4
60°	173.4	172.5	171.7	171.0	170.5	169.9	169.4	168.8
62.5°	160.1	159.1	158.3	157.6	157.2	156.8	156.3	155.9
65°	139.1	138.4	137.7	137.1	136.8	136.5	136.2	135.9
67.5°	119.1	118.5	117.9	117.5	117.3	117.1	116.9	116.7
70°	105.9	105.4	105.0	104.6	104.3	103.9	103.5	103.2
72.5°	93.5	92.9	92.4	92.0	91.7	91.3	90.9	90.6
75°	74.2	74.0	73.7	73.4	73.1	72.8	72.5	72.1
77.5°	56.6	56.4	56.2	56.1	55.8	55.6	55.4	55.1
80°	45.2	45.2	45.1	44.9	44.8	44.6	44.4	44.3
82.5°	34.5	34.4	34.3	34.1	34.1	34.1	34.1	34.1
85°	20.4	20.3	20.2	20.0	19.9	19.7	19.6	19.4
87.5°	9.0	9.0	9.1	9.1	9.0	9.0	8.8	8.7
90°	6.5	6.9	7.3	7.7	7.9	8.2	8.4	8.6
92.5°	6.5	6.9	7.3	7.6	7.7	7.8	7.9	8.0
95°	6.5	6.9	7.3	7.5	7.5	7.5	7.5	7.5
97.5°	13.2	10.9	8.6	7.5	7.5	7.5	7.5	7.5
100°	38.7	26.8	14.9	8.8	8.5	8.2	7.8	7.5
102.5°	75.1	72.8	70.6	66.8	61.3	55.9	50.5	45.1
105°	106.8	106.8	106.8	106.8	106.7	106.6	106.5	106.5
107.5°	135.2	135.2	135.2	135.1	134.9	134.7	134.4	134.2
110°	153.6	153.4	153.1	153.0	153.1	153.2	153.3	153.4



TEST NUMBER: P333344-927

CATALOG NUMBER: S125DIW-S375D470U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	171.8	171.5	171.3	171.0	171.0	170.8	170.7	170.6
115°	199.3	199.0	198.7	198.3	197.8	197.3	196.9	196.4
117.5°	225.9	225.5	225.1	224.7	224.5	224.3	224.1	223.9
120°	243.0	242.9	242.7	242.4	242.0	241.6	241.2	240.8
122.5°	259.4	259.2	259.0	258.7	258.3	257.8	257.4	256.9
125°	283.2	282.9	282.6	282.3	282.0	281.8	281.5	281.3
127.5°	305.0	304.8	304.7	304.3	303.6	303.1	302.5	301.9
130°	319.2	318.9	318.7	318.4	318.0	317.6	317.2	316.8
132.5°	332.5	332.4	332.4	332.2	331.8	331.4	331.0	330.6
135°	352.0	351.8	351.6	351.3	350.9	350.4	349.9	349.4
137.5°	370.1	370.2	370.2	370.0	369.6	369.2	368.8	368.4
140°	381.3	381.4	381.6	381.4	381.0	380.5	380.0	379.5
142.5°	392.2	392.2	392.3	392.1	391.6	391.1	390.6	390.1
145°	407.7	407.7	407.8	407.6	407.1	406.6	406.2	405.7
147.5°	420.9	421.0	421.0	420.8	420.3	419.7	419.1	418.5
150°	429.3	429.4	429.6	429.4	428.7	428.1	427.5	426.8
152.5°	436.7	436.9	437.0	436.9	436.3	435.7	435.1	434.6
155°	447.0	447.3	447.5	447.3	446.6	446.0	445.4	444.7
157.5°	455.5	455.7	456.0	455.8	455.2	454.6	453.9	453.3
160°	460.8	461.1	461.4	461.3	460.7	460.0	459.4	458.8
162.5°	465.6	466.1	466.5	466.4	465.7	465.0	464.3	463.6
165°	471.9	472.4	472.9	472.8	472.1	471.4	470.8	470.2
167.5°	476.6	477.1	477.7	477.7	476.9	476.2	475.5	474.8
170°	479.0	479.7	480.3	480.2	479.5	478.8	478.1	477.4
172.5°	480.9	481.4	482.0	482.0	481.3	480.5	479.8	479.1
175°	482.9	483.5	484.2	484.2	483.5	482.8	482.0	481.3
177.5°	483.8	484.2	484.7	484.7	484.1	483.6	483.1	482.6
180°	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5

(END OF REPORT)