

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332755-840

Luminaire Tested: **S124DIW-S575D770U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332755-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S575D770U840-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5619.8 lumens
Efficiency: N/A
Efficacy: 149.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332755-840

CATALOG NUMBER: S124DIW-S575D770U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332755-840

CATALOG NUMBER: S124DIW-S575D770U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	97	92	88	85	88	85	81	78	70	68	66	57	56	54	45	44	43	38
2	88	81	74	69	80	74	69	64	62	58	55	50	48	45	40	38	36	32
3	80	71	63	58	73	65	59	54	54	50	46	45	41	38	35	33	31	27
4	73	63	55	49	67	58	51	45	48	43	39	40	36	33	32	29	27	23
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	28	26	23	20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	20	17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	49	37	30	25	45	35	28	23	29	24	20	25	20	18	20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7917	7917	7917
5°	7942	7846	7903
10°	7891	7782	7820
15°	7796	7672	7691
20°	7669	7534	7541
25°	7525	7378	7357
30°	7347	7194	7127
35°	7164	7001	6908
40°	6973	6783	6658
45°	6774	6567	6441
50°	6553	6376	6178
55°	6315	6128	5928
60°	6077	5848	5670
65°	5809	5585	5358
70°	5509	5231	5028
75°	5050	4803	4682
80°	4491	4310	4203
85°	3927	3788	3714



TEST NUMBER: P332755-840

CATALOG NUMBER: S124DIW-S575D770U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.4	1.6
10°-20°	260.2	4.6
20°-30°	383.0	6.8
30°-40°	445.3	7.9
40°-50°	445.3	7.9
50°-60°	389.5	6.9
60°-70°	289.3	5.1
70°-80°	164.3	2.9
80°-90°	50.3	0.9
90°-100°	34.3	0.6
100°-110°	218.6	3.9
110°-120°	418.1	7.4
120°-130°	530.7	9.4
130°-140°	567.9	10.1
140°-150°	531.0	9.4
150°-160°	428.2	7.6
160°-170°	276.2	4.9
170°-180°	95.2	1.7
0°-30°	735.6	13.1
0°-40°	1180.9	21.0
0°-60°	2015.7	35.9
0°-90°	2519.6	44.8
90°-120°	670.9	11.9
90°-150°	2300.6	40.9
90°-180°	3100.0	55.2
0°-180°	5619.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	981	981	981	981	981	
5°	980	976	968	976	975	93
15°	933	929	918	922	920	263
25°	845	839	828	829	826	388
35°	727	721	710	705	701	454
45°	593	587	575	567	564	457
55°	449	446	435	426	421	402
65°	304	300	292	285	280	301
75°	162	158	154	151	150	172
85°	42	42	41	41	40	47
90°	2	10	16	21	22	4
95°	41	17	16	21	22	53
105°	226	230	234	239	214	236
115°	421	423	423	424	424	414
125°	592	595	594	596	597	529
135°	735	734	737	738	740	566
145°	847	849	849	850	852	529
155°	929	929	927	930	928	428
165°	980	976	976	981	975	277
175°	1002	998	998	1004	996	95
180°	1002	1002	1002	1002	1002	



TEST NUMBER: P332755-840

CATALOG NUMBER: S124DIW-S575D770U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	980.7	980.7	980.7	980.7	980.7	980.7	980.7	980.7	980.7	980.7	980.7
2.5°	983.2	982.8	982.4	982.0	981.6	980.6	979.1	977.5	975.9	974.4	975.8
5°	980.0	979.3	978.6	977.9	977.1	975.8	973.9	972.0	970.1	968.2	970.1
7.5°	970.8	970.1	969.5	968.8	968.1	966.6	964.5	962.4	960.2	958.1	959.7
10°	962.6	962.0	961.3	960.6	959.9	958.4	956.1	953.8	951.6	949.3	950.7
12.5°	952.0	951.3	950.6	949.9	949.2	947.7	945.2	942.8	940.4	938.0	939.5
15°	932.8	932.1	931.4	930.7	930.0	928.4	925.7	923.1	920.5	917.9	918.9
17.5°	909.7	908.8	908.0	907.1	906.2	904.5	902.0	899.6	897.1	894.6	895.2
20°	892.7	891.8	891.0	890.1	889.2	887.5	884.8	882.2	879.6	877.0	877.5
22.5°	874.4	873.3	872.2	871.0	869.9	868.0	865.4	862.7	860.1	857.5	858.5
25°	844.8	843.5	842.3	841.1	839.9	838.1	835.6	833.1	830.7	828.3	828.5
27.5°	810.8	809.6	808.3	807.1	805.8	804.1	801.7	799.5	797.2	795.0	794.6
30°	788.2	786.8	785.4	784.0	782.6	780.7	778.5	776.2	774.0	771.7	771.0
32.5°	764.3	763.1	761.7	760.5	759.3	757.4	755.1	752.7	750.2	747.8	747.0
35°	726.9	725.7	724.5	723.3	722.1	720.1	717.7	715.3	712.9	710.4	709.1
37.5°	687.4	686.3	685.2	684.1	683.0	681.2	678.5	675.9	673.3	670.7	669.3
40°	661.7	660.2	658.8	657.5	656.1	654.1	651.5	648.8	646.2	643.6	641.9
42.5°	634.0	633.2	632.4	631.5	630.7	628.7	625.9	623.0	620.1	617.2	615.2
45°	593.3	592.1	590.9	589.7	588.4	586.4	583.6	580.8	578.0	575.2	573.3
47.5°	550.7	549.9	549.1	548.2	547.3	545.6	543.1	540.5	537.9	535.3	533.1
50°	521.8	521.1	520.4	519.7	519.0	517.5	515.0	512.5	510.1	507.7	505.2
52.5°	493.5	492.7	491.8	491.0	490.2	488.5	485.8	483.3	480.7	478.1	475.9
55°	448.7	448.2	447.7	447.2	446.7	445.1	442.7	440.2	437.8	435.4	433.2
57.5°	406.0	405.4	404.8	404.1	403.5	402.1	399.7	397.3	394.9	392.4	390.4
60°	376.4	375.6	374.7	373.8	372.9	371.3	369.1	366.8	364.6	362.2	360.7
62.5°	347.5	346.8	346.0	345.3	344.6	343.0	340.6	338.2	335.8	333.4	331.9
65°	304.1	303.3	302.4	301.5	300.6	299.3	297.6	295.8	294.1	292.4	290.5
67.5°	260.4	259.6	258.8	258.0	257.2	256.0	254.3	252.7	251.0	249.2	247.6
70°	233.4	232.2	231.0	229.7	228.5	227.2	225.8	224.4	223.0	221.6	220.3
72.5°	204.5	203.3	202.1	200.8	199.5	198.4	197.3	196.2	195.1	193.9	192.8
75°	161.9	161.0	160.2	159.3	158.3	157.5	156.6	155.7	154.9	154.0	153.3
77.5°	121.2	120.8	120.4	120.1	119.7	119.1	118.3	117.5	116.7	116.0	115.7
80°	96.6	96.1	95.6	95.1	94.5	94.1	93.8	93.4	93.1	92.7	92.4
82.5°	72.8	72.5	72.3	72.0	71.8	71.6	71.6	71.5	71.4	71.4	71.1
85°	42.4	42.4	42.4	42.4	42.4	42.2	41.9	41.6	41.2	40.9	40.9
87.5°	16.8	17.1	17.3	17.5	17.7	17.9	18.0	18.2	18.3	18.4	18.6
90°	2.2	4.0	6.0	7.8	9.6	11.2	12.5	13.8	15.1	16.5	17.5
92.5°	9.5	9.6	9.7	9.7	9.8	10.6	11.9	13.2	14.5	15.9	16.9
95°	41.2	35.5	29.9	24.2	18.6	15.9	16.0	16.2	16.4	16.5	17.5
97.5°	87.6	91.1	94.6	98.2	101.7	94.1	75.5	57.0	38.4	19.8	19.9
100°	122.9	125.9	129.0	131.9	134.9	124.9	102.0	79.0	55.9	33.0	30.2
102.5°	162.5	164.7	166.9	169.2	171.3	170.9	167.9	164.9	161.9	159.0	128.4
105°	225.6	226.6	227.6	228.6	229.6	230.6	231.4	232.2	233.1	233.9	235.4
107.5°	284.3	284.8	285.3	285.8	286.3	287.1	288.2	289.3	290.4	291.5	292.4
110°	323.9	324.4	324.9	325.4	325.8	326.6	327.6	328.6	329.6	330.5	330.9



TEST NUMBER: P332755-840

CATALOG NUMBER: S124DIW-S575D770U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	362.2	363.1	364.1	364.9	365.8	366.5	367.0	367.4	367.9	368.4	368.3
115°	421.3	421.8	422.3	422.7	423.2	423.4	423.2	423.1	422.9	422.7	423.1
117.5°	474.5	475.1	475.8	476.5	477.2	477.7	478.1	478.4	478.8	479.2	479.1
120°	510.5	511.2	511.8	512.5	513.1	513.4	513.2	513.1	512.9	512.7	513.1
122.5°	544.1	544.4	544.8	545.2	545.6	545.9	546.2	546.4	546.6	546.9	547.1
125°	592.2	592.9	593.5	594.2	594.8	595.0	594.7	594.4	594.0	593.7	594.2
127.5°	637.7	637.9	638.1	638.2	638.4	638.9	639.6	640.5	641.2	642.0	641.9
130°	667.1	667.3	667.5	667.6	667.8	668.1	668.6	669.1	669.6	670.1	670.3
132.5°	694.2	694.5	694.8	695.0	695.3	695.8	696.4	697.1	697.7	698.3	698.5
135°	734.6	734.5	734.3	734.1	734.0	734.2	734.9	735.5	736.2	736.9	737.2
137.5°	770.4	770.5	770.6	770.6	770.7	771.1	771.8	772.5	773.4	774.1	774.4
140°	793.9	794.2	794.5	794.9	795.2	795.5	795.9	796.2	796.5	796.9	797.3
142.5°	814.9	815.5	816.1	816.6	817.2	817.6	817.8	818.0	818.2	818.4	818.8
145°	847.1	847.6	848.1	848.6	849.1	849.3	849.3	849.3	849.3	849.3	849.5
147.5°	872.7	873.6	874.5	875.5	876.5	876.8	876.7	876.5	876.3	876.2	876.3
150°	891.3	891.9	892.6	893.3	893.9	894.2	894.0	893.8	893.7	893.5	893.5
152.5°	906.9	907.4	908.0	908.5	909.0	909.1	908.8	908.6	908.3	908.0	908.2
155°	928.8	929.0	929.1	929.3	929.5	929.3	928.8	928.3	927.8	927.3	928.0
157.5°	947.3	947.2	947.1	947.0	946.8	946.4	945.9	945.3	944.7	944.2	945.0
160°	958.0	957.5	957.0	956.5	956.0	955.6	955.5	955.3	955.1	955.0	956.0
162.5°	967.6	966.9	966.3	965.7	965.0	964.6	964.5	964.3	964.1	964.0	965.0
165°	979.8	978.9	978.1	977.2	976.4	976.0	976.0	976.0	976.0	976.0	977.3
167.5°	989.4	988.5	987.6	986.7	985.8	985.4	985.3	985.2	985.1	985.0	986.4
170°	994.7	993.7	992.7	991.7	990.8	990.3	990.5	990.7	990.8	991.0	992.3
172.5°	998.4	997.3	996.3	995.3	994.3	993.9	994.1	994.2	994.4	994.6	995.9
175°	1002.2	1001.2	1000.3	999.3	998.3	997.8	997.9	998.2	998.4	998.5	1000.0
177.5°	1004.0	1003.1	1002.2	1001.2	1000.3	1000.0	1000.3	1000.5	1000.8	1001.0	1002.1
180°	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2



TEST NUMBER: P332755-840

CATALOG NUMBER: S124DIW-S575D770U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	980.7	980.7	980.7	980.7	980.7	980.7	980.7	980.7
2.5°	977.2	978.7	980.1	980.7	980.5	980.4	980.3	980.1
5°	972.0	973.9	975.8	976.6	976.2	975.9	975.5	975.2
7.5°	961.2	962.7	964.2	964.9	964.7	964.5	964.3	964.0
10°	952.1	953.5	954.9	955.4	955.0	954.7	954.3	954.0
12.5°	941.1	942.6	944.1	944.6	944.1	943.6	943.2	942.7
15°	920.0	921.0	922.0	922.3	921.8	921.3	920.7	920.2
17.5°	896.0	896.6	897.3	897.4	897.1	896.7	896.4	896.1
20°	878.1	878.6	879.1	879.2	878.8	878.5	878.2	877.8
22.5°	859.4	860.3	861.3	861.4	860.8	860.2	859.6	858.9
25°	828.6	828.8	829.0	828.7	828.0	827.3	826.6	825.9
27.5°	794.2	793.7	793.2	792.6	791.7	790.9	790.0	789.1
30°	770.3	769.6	768.9	768.1	767.2	766.4	765.5	764.6
32.5°	746.1	745.3	744.5	743.6	742.8	741.8	740.9	740.1
35°	707.9	706.7	705.5	704.5	703.6	702.7	701.9	700.9
37.5°	668.0	666.6	665.3	664.1	663.0	661.8	660.7	659.4
40°	640.2	638.3	636.6	635.3	634.4	633.6	632.7	631.8
42.5°	613.2	611.1	609.0	607.7	607.2	606.6	606.0	605.4
45°	571.4	569.5	567.5	566.3	565.8	565.3	564.7	564.2
47.5°	531.0	528.8	526.6	524.9	523.6	522.2	520.9	519.6
50°	502.7	500.3	497.9	496.1	495.0	494.0	493.0	491.9
52.5°	473.7	471.6	469.5	467.7	466.4	465.0	463.7	462.4
55°	431.2	429.1	427.0	425.4	424.3	423.3	422.2	421.2
57.5°	388.5	386.5	384.5	382.9	381.9	380.9	379.9	378.9
60°	359.1	357.6	356.0	354.8	353.9	353.0	352.1	351.2
62.5°	330.5	329.0	327.6	326.5	325.6	324.8	323.9	323.0
65°	288.8	287.1	285.4	284.1	283.2	282.3	281.4	280.5
67.5°	245.9	244.3	242.6	241.6	241.4	241.2	240.9	240.7
70°	218.8	217.4	216.0	215.1	214.5	214.0	213.5	213.0
72.5°	191.7	190.6	189.5	188.6	188.1	187.6	187.1	186.5
75°	152.6	151.9	151.3	150.8	150.6	150.5	150.3	150.1
77.5°	115.5	115.3	115.1	114.8	114.3	113.9	113.4	113.0
80°	92.0	91.7	91.3	91.1	90.9	90.7	90.6	90.4
82.5°	70.9	70.7	70.5	70.3	70.2	70.0	69.8	69.6
85°	40.9	40.9	40.9	40.8	40.6	40.4	40.3	40.1
87.5°	18.8	19.0	19.2	19.3	19.4	19.5	19.5	19.6
90°	18.5	19.5	20.5	21.1	21.5	21.8	22.1	22.5
92.5°	17.9	18.9	19.9	20.4	20.5	20.6	20.6	20.7
95°	18.5	19.5	20.5	21.1	21.2	21.4	21.6	21.7
97.5°	20.0	20.1	20.2	20.3	20.5	20.7	20.8	21.0
100°	27.4	24.4	21.6	20.3	20.5	20.7	20.8	21.0
102.5°	97.9	67.3	36.8	21.4	21.5	21.5	21.5	21.6
105°	236.9	238.3	239.8	237.6	231.7	225.6	219.6	213.7
107.5°	293.1	293.8	294.6	295.2	295.9	296.5	297.1	297.7
110°	331.2	331.5	331.9	332.3	332.9	333.4	333.9	334.4



TEST NUMBER: P332755-840

CATALOG NUMBER: S124DIW-S575D770U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	368.2	368.2	368.1	368.4	369.0	369.6	370.3	370.9
115°	423.4	423.7	424.1	424.2	424.2	424.2	424.2	424.2
117.5°	479.0	479.0	478.9	478.8	478.8	478.7	478.6	478.6
120°	513.4	513.7	514.0	514.0	513.7	513.4	513.1	512.7
122.5°	547.3	547.5	547.8	547.6	547.3	546.9	546.6	546.3
125°	594.7	595.2	595.7	596.0	596.2	596.3	596.5	596.7
127.5°	641.8	641.7	641.6	641.5	641.4	641.2	641.1	641.0
130°	670.4	670.7	670.9	670.9	670.9	670.9	670.9	670.9
132.5°	698.6	698.8	699.0	699.0	698.9	698.7	698.6	698.5
135°	737.5	737.9	738.2	738.5	738.8	739.2	739.5	739.8
137.5°	774.8	775.2	775.5	775.7	775.6	775.5	775.4	775.3
140°	797.8	798.3	798.8	799.2	799.3	799.5	799.7	799.8
142.5°	819.2	819.5	819.9	820.1	820.1	820.1	820.2	820.2
145°	849.6	849.8	850.0	850.2	850.5	850.9	851.2	851.5
147.5°	876.4	876.6	876.7	876.9	877.0	877.2	877.4	877.5
150°	893.5	893.5	893.5	893.6	893.8	893.9	894.1	894.2
152.5°	908.5	908.7	909.0	909.1	909.0	908.9	908.8	908.7
155°	928.6	929.3	929.9	930.0	929.5	929.0	928.5	928.1
157.5°	945.9	946.8	947.7	947.7	946.8	945.9	945.0	944.2
160°	957.0	958.0	959.0	959.0	958.0	957.0	956.0	955.0
162.5°	966.0	966.9	968.0	968.0	966.8	965.6	964.5	963.4
165°	978.7	980.0	981.3	981.3	979.8	978.3	976.7	975.2
167.5°	988.0	989.4	990.9	990.8	989.1	987.4	985.7	984.1
170°	993.6	995.0	996.3	996.1	994.5	992.8	991.2	989.5
172.5°	997.2	998.6	999.9	999.7	997.8	996.1	994.3	992.5
175°	1001.5	1003.0	1004.5	1004.2	1002.2	1000.3	998.3	996.2
177.5°	1003.2	1004.2	1005.3	1005.0	1003.4	1001.8	1000.3	998.7
180°	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2

(END OF REPORT)