

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332793-840

Luminaire Tested: **S124DIW-S795D1340U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332793-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S795D1340U840-4F0-1E-UDD-A  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1340 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8999.5 lumens  
Efficiency: N/A  
Efficacy: 146.6 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 61.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332793-840

CATALOG NUMBER: S124DIW-S795D1340U840-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332793-840

CATALOG NUMBER: S124DIW-S795D1340U840-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40																												
1	96	91	88	84	87	83	80	77	68	66	64	54	53	52	42	41	40	34																												
2	87	80	74	69	79	73	68	64	60	56	53	48	45	43	37	35	34	29																												
3	80	70	63	58	72	64	58	53	53	49	45	43	39	37	33	31	29	24																												
4	73	62	55	49	66	57	51	45	47	42	38	38	34	32	29	27	25	21																												
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	27	24	22	18																												
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	21	19	16																												
7	57	45	37	32	52	41	35	30	35	29	25	28	24	21	22	19	17	14																												
8	53	41	33	28	48	38	31	26	31	26	23	26	22	19	20	18	15	13																												
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12																												
10	46	34	27	22	42	31	25	21	26	22	18	22	18	15	17	15	13	11																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10467	10467	10467	10467
5°	12327	10494	9263	10494
10°	14758	10449	8338	10449
15°	17462	10343	7658	10343
20°	19444	10234	7050	10234
25°	19759	10075	6631	10075
30°	16812	9923	6498	9923
35°	12925	9676	6500	9676
40°	10075	9385	6622	9385
45°	8401	8947	6734	8947
50°	7394	8411	6962	8411
55°	6773	7771	7241	7771
60°	6347	7198	7579	7198
65°	5908	6556	7859	6556
70°	5401	5922	8037	5922
75°	4825	5209	7941	5209
80°	4049	4268	7689	4268
85°	2983	3084	7364	3084



TEST NUMBER: P332793-840

CATALOG NUMBER: S124DIW-S795D1340U840-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	126.3	1.4
10°-20°	389.3	4.3
20°-30°	617.4	6.9
30°-40°	687.1	7.6
40°-50°	625.4	6.9
50°-60°	511.1	5.7
60°-70°	364.8	4.1
70°-80°	200.9	2.2
80°-90°	59.9	0.7
90°-100°	59.9	0.7
100°-110°	381.9	4.2
110°-120°	730.6	8.1
120°-130°	927.4	10.3
130°-140°	992.3	11.0
140°-150°	927.9	10.3
150°-160°	748.3	8.3
160°-170°	482.6	5.4
170°-180°	166.3	1.8
0°-30°	1133.0	12.6
0°-40°	1820.1	20.2
0°-60°	2956.5	32.9
0°-90°	3582.2	39.8
90°-120°	1172.4	13.0
90°-150°	4020.0	44.7
90°-180°	5417.0	60.2
0°-180°	8999.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1297	1297	1297	1297	1297	
5°	1521	1295	1143	1295	1521	155
15°	2089	1238	916	1238	2089	590
25°	2218	1131	744	1131	2218	978
35°	1312	982	660	982	1312	832
45°	736	784	590	784	736	580
55°	481	552	514	552	481	435
65°	309	343	411	343	309	306
75°	155	167	255	167	155	164
85°	32	33	80	33	32	40
90°	39	4	39	4	39	18
95°	38	72	38	72	38	30
105°	373	394	373	394	373	326
115°	741	736	741	736	741	734
125°	1043	1035	1043	1035	1043	929
135°	1293	1284	1293	1284	1293	995
145°	1488	1480	1488	1480	1488	930
155°	1622	1623	1622	1623	1622	748
165°	1704	1712	1704	1712	1704	481
175°	1741	1751	1741	1751	1741	166
180°	1751	1751	1751	1751	1751	



TEST NUMBER: P332793-840

CATALOG NUMBER: S124DIW-S795D1340U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6
2.5°	1379.9	1379.5	1375.1	1374.3	1371.3	1367.5	1366.5	1359.7	1345.9	1339.5	1337.8
5°	1521.1	1531.8	1517.8	1515.1	1513.5	1495.8	1486.6	1475.9	1451.2	1436.7	1425.4
7.5°	1689.5	1690.7	1684.7	1679.7	1666.1	1650.5	1627.4	1602.7	1573.3	1542.6	1519.5
10°	1800.3	1804.6	1797.7	1796.5	1769.2	1752.0	1717.6	1688.6	1655.3	1618.2	1584.4
12.5°	1917.2	1911.2	1907.6	1884.6	1879.6	1848.3	1808.3	1778.4	1727.1	1684.5	1639.4
15°	2089.3	2077.5	2069.9	2038.2	2022.7	1979.1	1936.7	1904.0	1836.8	1772.9	1724.5
17.5°	2190.2	2202.0	2184.6	2171.6	2131.3	2100.8	2057.5	1988.7	1936.2	1856.8	1795.8
20°	2263.3	2264.3	2254.7	2241.3	2209.6	2170.9	2123.6	2048.4	1985.6	1906.6	1822.9
22.5°	2283.0	2283.3	2279.2	2266.6	2242.6	2211.3	2163.6	2100.8	2024.7	1938.8	1855.1
25°	2218.2	2216.0	2220.9	2234.8	2225.6	2216.0	2188.6	2141.9	2071.0	1980.2	1890.0
27.5°	1977.1	1992.0	2019.2	2053.6	2086.7	2111.9	2119.0	2109.4	2065.5	1990.8	1896.3
30°	1803.5	1821.8	1842.2	1876.5	1943.2	1981.4	2023.2	2054.9	2037.2	1977.5	1889.5
32.5°	1612.8	1617.3	1647.6	1686.7	1747.7	1821.1	1887.4	1951.8	1973.2	1941.9	1868.5
35°	1311.5	1319.1	1351.8	1390.5	1465.2	1554.9	1654.8	1743.9	1817.5	1847.0	1809.5
37.5°	1070.3	1091.9	1115.0	1156.6	1222.3	1303.0	1406.8	1522.2	1631.8	1705.4	1717.8
40°	956.0	969.5	986.1	1017.7	1073.6	1153.2	1242.2	1374.4	1491.0	1596.2	1630.6
42.5°	865.8	873.6	883.8	912.5	955.0	1034.1	1115.5	1231.7	1348.8	1474.6	1532.2
45°	735.8	743.9	761.0	777.7	809.9	864.7	940.4	1036.0	1153.7	1275.1	1381.4
47.5°	642.0	647.1	657.3	675.1	702.5	738.6	800.2	880.1	989.1	1106.9	1220.2
50°	588.7	592.9	601.0	617.1	638.0	670.2	720.7	795.5	880.8	999.6	1110.6
52.5°	546.5	548.3	554.2	565.1	581.8	608.8	650.3	712.1	791.4	897.3	1008.0
55°	481.2	483.4	488.8	496.9	511.3	528.5	560.2	606.3	675.7	767.5	863.6
57.5°	427.5	429.0	433.5	436.7	448.6	462.5	487.0	519.9	572.4	650.3	736.1
60°	393.1	392.0	397.5	400.1	408.2	420.0	438.8	470.5	516.1	579.0	657.9
62.5°	359.6	358.1	362.6	366.2	370.8	380.9	396.3	421.1	458.2	514.9	583.2
65°	309.3	307.2	309.9	314.2	318.5	323.9	335.2	357.2	386.7	427.5	479.6
67.5°	258.8	261.2	261.6	263.7	266.2	273.5	281.2	296.8	317.6	350.3	394.5
70°	228.8	229.3	231.5	231.5	233.1	239.5	246.0	255.1	275.5	305.6	341.5
72.5°	198.7	201.0	200.2	201.9	203.0	207.3	212.1	220.8	238.1	260.4	290.8
75°	154.7	156.3	156.3	156.8	158.4	160.1	163.8	170.3	182.6	199.2	220.3
77.5°	112.8	113.0	113.7	115.7	115.7	118.3	121.1	126.2	132.3	143.7	156.5
80°	87.1	88.1	87.6	88.7	88.7	90.8	91.8	98.3	101.0	108.5	118.7
82.5°	63.8	64.8	64.7	66.2	67.2	67.6	69.1	71.6	74.3	81.0	85.1
85°	32.2	33.3	32.2	33.3	34.9	35.4	37.1	37.6	39.8	41.4	45.1
87.5°	17.3	18.5	18.4	18.7	19.4	19.6	19.7	18.9	20.3	20.4	21.6
90°	39.3	38.7	38.2	37.6	37.0	35.9	34.0	32.3	30.6	28.8	26.5
92.5°	36.2	36.1	36.0	35.9	35.6	34.7	33.0	31.3	29.5	27.8	25.4
95°	38.0	37.7	37.4	37.1	36.9	35.9	34.0	32.3	30.6	28.8	28.5
97.5°	36.7	36.4	36.1	35.9	35.5	35.2	35.1	34.9	34.7	34.5	67.1
100°	36.7	36.4	36.1	35.9	35.5	37.9	42.8	47.8	52.7	57.7	97.8
102.5°	37.8	37.7	37.6	37.6	37.5	64.1	117.5	171.0	224.3	277.7	283.0
105°	373.3	383.7	394.3	404.8	415.3	419.2	416.6	413.9	411.3	408.7	407.2
107.5°	520.3	519.2	518.1	516.9	515.8	514.6	513.4	512.1	510.8	509.6	507.6
110°	584.2	583.3	582.5	581.6	580.7	580.0	579.4	578.9	578.2	577.6	575.9



TEST NUMBER: P332793-840

CATALOG NUMBER: S124DIW-S795D1340U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	648.1	647.0	645.9	644.8	643.7	643.2	643.3	643.4	643.6	643.7	642.9
115°	741.3	741.3	741.3	741.3	741.3	741.0	740.5	739.9	739.3	738.7	739.0
117.5°	836.2	836.4	836.5	836.6	836.7	836.8	836.9	837.0	837.2	837.3	836.6
120°	896.0	896.6	897.1	897.7	898.3	898.3	897.7	897.1	896.6	896.0	896.3
122.5°	954.6	955.2	955.7	956.3	956.9	957.0	956.7	956.3	956.0	955.6	955.2
125°	1042.7	1042.4	1042.1	1041.8	1041.5	1040.9	1040.1	1039.2	1038.2	1037.4	1037.9
127.5°	1119.9	1120.1	1120.3	1120.6	1120.8	1121.1	1121.3	1121.5	1121.6	1121.8	1120.4
130°	1172.4	1172.4	1172.4	1172.4	1172.4	1172.2	1171.8	1171.5	1171.3	1171.0	1170.1
132.5°	1220.5	1220.7	1221.0	1221.2	1221.4	1221.4	1221.1	1220.8	1220.5	1220.2	1219.1
135°	1292.8	1292.2	1291.6	1291.1	1290.5	1289.9	1289.3	1288.8	1288.2	1287.6	1286.5
137.5°	1354.6	1354.8	1355.0	1355.1	1355.3	1355.1	1354.4	1353.8	1353.2	1352.5	1351.3
140°	1397.7	1397.4	1397.0	1396.7	1396.4	1395.8	1395.0	1394.1	1393.2	1392.4	1391.8
142.5°	1433.2	1433.2	1433.1	1433.1	1433.0	1432.7	1432.0	1431.4	1430.8	1430.1	1429.8
145°	1488.0	1487.4	1486.8	1486.2	1485.7	1485.2	1484.9	1484.6	1484.4	1484.1	1484.1
147.5°	1533.3	1533.0	1532.8	1532.5	1532.2	1531.9	1531.7	1531.5	1531.2	1531.0	1531.3
150°	1562.7	1562.4	1562.1	1561.8	1561.5	1561.4	1561.4	1561.4	1561.4	1561.4	1561.7
152.5°	1587.8	1588.0	1588.1	1588.3	1588.5	1588.3	1587.9	1587.4	1587.0	1586.5	1587.0
155°	1621.6	1622.4	1623.4	1624.3	1625.1	1625.0	1623.8	1622.7	1621.4	1620.3	1621.1
157.5°	1649.9	1651.4	1652.9	1654.5	1656.0	1656.0	1654.5	1652.9	1651.4	1649.9	1650.9
160°	1668.8	1670.5	1672.2	1674.0	1675.8	1675.8	1674.0	1672.2	1670.5	1668.8	1669.0
162.5°	1683.4	1685.4	1687.4	1689.4	1691.3	1691.4	1689.7	1688.0	1686.2	1684.5	1684.8
165°	1704.1	1706.8	1709.4	1712.0	1714.5	1714.8	1712.4	1710.1	1707.8	1705.5	1705.5
167.5°	1719.6	1722.5	1725.4	1728.3	1731.2	1731.4	1728.8	1726.3	1723.7	1721.1	1721.3
170°	1729.0	1731.9	1734.8	1737.8	1740.6	1740.9	1738.6	1736.3	1733.9	1731.6	1731.3
172.5°	1734.2	1737.4	1740.5	1743.6	1746.9	1747.3	1744.9	1742.5	1740.2	1737.9	1737.6
175°	1740.8	1744.2	1747.8	1751.3	1754.7	1755.2	1752.6	1750.0	1747.4	1744.7	1744.4
177.5°	1744.9	1747.8	1750.6	1753.3	1756.2	1756.7	1754.7	1752.9	1751.0	1749.2	1748.7
180°	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3



TEST NUMBER: P332793-840

CATALOG NUMBER: S124DIW-S795D1340U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6
2.5°	1338.2	1332.2	1327.9	1324.4	1315.0	1309.4	1305.1	1299.1	1292.2	1285.0	1275.9
5°	1414.1	1395.8	1382.5	1362.0	1342.7	1326.6	1310.0	1294.9	1276.7	1256.8	1242.2
7.5°	1494.0	1466.8	1432.0	1401.8	1367.9	1338.3	1311.9	1284.9	1256.7	1229.4	1204.4
10°	1544.7	1509.7	1471.1	1425.4	1382.5	1344.3	1308.9	1274.6	1241.2	1207.9	1179.4
12.5°	1599.2	1555.7	1498.5	1445.2	1397.0	1346.0	1303.3	1261.2	1221.0	1186.0	1152.8
15°	1672.4	1609.6	1543.6	1472.2	1408.8	1349.2	1290.6	1237.5	1192.3	1146.1	1113.9
17.5°	1717.5	1639.7	1564.2	1489.6	1412.9	1337.7	1274.6	1213.2	1156.7	1110.8	1070.2
20°	1747.2	1669.8	1575.8	1501.2	1409.9	1332.5	1259.5	1191.2	1132.2	1083.3	1041.4
22.5°	1772.9	1683.5	1589.5	1491.3	1400.4	1318.4	1238.4	1169.7	1109.4	1057.9	1017.7
25°	1786.9	1684.3	1582.3	1484.5	1381.4	1284.1	1211.6	1131.1	1066.6	1012.4	969.5
27.5°	1788.4	1678.7	1563.3	1454.6	1348.2	1257.7	1166.1	1094.2	1027.2	969.9	928.6
30°	1783.6	1669.3	1545.2	1427.5	1320.7	1222.4	1143.0	1064.5	996.3	939.4	896.4
32.5°	1768.6	1649.5	1522.0	1397.5	1286.8	1190.6	1108.5	1034.0	967.6	911.4	866.4
35°	1725.2	1607.5	1471.6	1342.2	1228.8	1131.7	1057.5	981.8	915.2	862.0	818.5
37.5°	1657.1	1550.7	1412.6	1278.7	1167.4	1069.8	996.3	927.9	867.8	813.7	769.2
40°	1597.8	1504.4	1365.8	1235.3	1115.0	1022.1	953.3	890.5	830.9	779.8	737.4
42.5°	1529.5	1448.0	1320.3	1182.0	1066.0	972.7	905.6	849.2	793.0	745.9	703.5
45°	1407.7	1354.0	1233.7	1105.9	985.0	897.0	833.0	783.7	736.4	690.1	654.7
47.5°	1267.6	1241.0	1139.7	1018.3	903.6	816.8	761.3	715.7	674.3	635.2	603.9
50°	1173.6	1160.6	1073.1	956.0	846.5	764.8	708.9	669.7	634.3	600.0	570.4
52.5°	1080.8	1080.3	1001.4	894.1	792.7	714.1	658.6	622.1	591.4	563.4	536.8
55°	938.9	953.8	892.1	796.5	705.7	634.8	584.9	552.1	530.7	507.6	487.7
57.5°	808.5	833.4	782.5	698.3	622.6	557.2	513.8	489.2	466.3	452.3	437.9
60°	723.5	747.1	707.3	636.4	565.0	509.2	467.8	445.8	425.9	416.3	406.1
62.5°	647.8	668.9	639.4	573.7	511.7	458.1	423.1	401.9	388.5	378.0	371.2
65°	539.8	557.4	532.3	484.4	431.3	388.3	359.8	343.2	330.3	326.0	318.5
67.5°	436.4	452.4	438.8	398.2	355.6	323.0	300.7	284.8	277.1	273.4	268.0
70°	374.9	391.0	376.5	341.0	308.3	280.9	259.9	250.9	242.8	241.2	233.6
72.5°	322.9	333.9	319.3	291.6	263.6	240.5	224.3	214.7	210.6	207.6	203.6
75°	242.3	251.9	242.3	220.8	200.9	184.8	170.8	167.0	162.2	160.6	157.9
77.5°	171.5	179.9	172.4	159.0	144.1	131.7	124.2	119.4	118.3	115.4	116.7
80°	131.1	136.4	129.5	120.3	108.5	99.9	94.5	91.8	88.7	87.6	89.7
82.5°	94.1	96.4	92.9	86.7	78.0	72.4	68.8	65.6	65.0	65.2	65.2
85°	48.9	48.4	47.8	42.4	39.8	36.0	33.8	33.3	32.7	33.8	34.9
87.5°	21.2	21.1	20.2	18.0	16.1	14.1	13.0	11.9	13.0	14.1	15.1
90°	24.1	21.8	19.5	16.8	13.5	10.3	7.2	3.9	7.2	10.3	13.5
92.5°	23.1	20.8	18.5	17.2	17.1	16.9	16.7	16.5	16.7	16.9	17.1
95°	28.3	28.0	27.7	32.4	42.3	52.2	62.1	72.0	62.1	52.2	42.3
97.5°	99.6	132.0	164.5	177.6	171.5	165.3	159.2	153.0	159.2	165.3	171.5
100°	137.9	178.1	218.3	235.8	230.6	225.3	220.0	214.8	220.0	225.3	230.6
102.5°	288.2	293.4	298.6	299.3	295.5	291.6	287.8	284.0	287.8	291.6	295.5
105°	405.8	404.3	402.8	401.2	399.5	397.8	396.0	394.3	396.0	397.8	399.5
107.5°	505.5	503.6	501.6	500.2	499.3	498.5	497.6	496.7	497.6	498.5	499.3
110°	574.1	572.4	570.7	569.4	568.5	567.6	566.7	565.8	566.7	567.6	568.5





TEST NUMBER: P332793-840

CATALOG NUMBER: S124DIW-S795D1340U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	642.1	641.3	640.4	639.2	637.6	636.1	634.5	632.9	634.5	636.1	637.6
115°	739.3	739.6	739.9	739.6	738.7	737.9	737.0	736.1	737.0	737.9	738.7
117.5°	836.0	835.4	834.7	833.7	832.6	831.4	830.3	829.1	830.3	831.4	832.6
120°	896.6	896.9	897.1	896.7	895.5	894.3	893.1	892.0	893.1	894.3	895.5
122.5°	954.8	954.4	954.0	953.5	952.8	952.1	951.4	950.7	951.4	952.1	952.8
125°	1038.5	1039.2	1039.8	1039.5	1038.2	1037.1	1035.9	1034.8	1035.9	1037.1	1038.2
127.5°	1119.0	1117.7	1116.4	1115.6	1115.3	1115.0	1114.7	1114.4	1114.7	1115.0	1115.3
130°	1169.2	1168.4	1167.5	1166.9	1166.6	1166.4	1166.1	1165.8	1166.1	1166.4	1166.6
132.5°	1218.0	1217.0	1215.9	1215.0	1214.5	1214.0	1213.5	1212.9	1213.5	1214.0	1214.5
135°	1285.3	1284.0	1282.9	1282.5	1282.8	1283.0	1283.3	1283.6	1283.3	1283.0	1282.8
137.5°	1350.0	1348.7	1347.5	1346.8	1346.7	1346.5	1346.4	1346.3	1346.4	1346.5	1346.7
140°	1391.2	1390.6	1390.1	1389.5	1388.9	1388.3	1387.8	1387.2	1387.8	1388.3	1388.9
142.5°	1429.4	1429.1	1428.7	1428.1	1426.9	1425.9	1424.8	1423.8	1424.8	1425.9	1426.9
145°	1484.1	1484.1	1484.1	1483.6	1482.8	1481.9	1481.0	1480.2	1481.0	1481.9	1482.8
147.5°	1531.6	1531.9	1532.2	1531.5	1529.8	1528.2	1526.5	1524.9	1526.5	1528.2	1529.8
150°	1562.0	1562.3	1562.5	1562.1	1560.9	1559.7	1558.6	1557.4	1558.6	1559.7	1560.9
152.5°	1587.5	1588.1	1588.6	1588.4	1587.4	1586.5	1585.6	1584.7	1585.6	1586.5	1587.4
155°	1622.0	1623.0	1623.8	1624.1	1623.8	1623.5	1623.2	1623.0	1623.2	1623.5	1623.8
157.5°	1651.8	1652.8	1653.9	1654.5	1654.6	1654.8	1655.0	1655.2	1655.0	1654.8	1654.6
160°	1669.3	1669.6	1669.9	1670.5	1671.3	1672.2	1673.1	1674.0	1673.1	1672.2	1671.3
162.5°	1685.1	1685.4	1685.7	1686.4	1687.5	1688.6	1689.6	1690.7	1689.6	1688.6	1687.5
165°	1705.5	1705.5	1705.5	1706.2	1707.6	1709.1	1710.5	1712.0	1710.5	1709.1	1707.6
167.5°	1721.5	1721.7	1721.8	1722.7	1724.2	1725.8	1727.3	1728.8	1727.3	1725.8	1724.2
170°	1731.0	1730.7	1730.5	1731.2	1732.9	1734.6	1736.5	1738.2	1736.5	1734.6	1732.9
172.5°	1737.4	1737.1	1736.8	1737.5	1739.2	1741.0	1742.7	1744.4	1742.7	1741.0	1739.2
175°	1744.1	1743.8	1743.5	1744.2	1746.1	1747.8	1749.5	1751.3	1749.5	1747.8	1746.1
177.5°	1748.3	1747.8	1747.3	1747.9	1749.5	1751.1	1752.8	1754.4	1752.8	1751.1	1749.5
180°	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3



TEST NUMBER: P332793-840

CATALOG NUMBER: S124DIW-S795D1340U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6
2.5°	1271.6	1267.8	1262.1	1254.5	1248.0	1241.1	1239.4	1236.8	1241.9	1237.7	1236.4
5°	1229.9	1218.6	1204.2	1187.5	1177.8	1163.9	1161.1	1155.8	1150.4	1149.9	1144.5
7.5°	1185.8	1169.2	1150.2	1133.3	1117.5	1102.3	1092.4	1090.1	1082.3	1077.6	1072.3
10°	1157.4	1137.0	1115.0	1098.8	1080.7	1064.5	1053.2	1046.8	1041.4	1035.5	1030.2
12.5°	1123.9	1102.2	1084.1	1066.6	1044.9	1032.7	1014.1	1003.0	1001.9	1002.0	988.1
15°	1084.9	1063.4	1035.5	1010.8	999.0	975.3	965.1	952.2	944.2	936.1	929.7
17.5°	1040.4	1013.6	991.8	963.4	940.9	922.1	908.7	900.9	888.8	877.4	869.1
20°	1012.4	983.9	960.9	930.8	906.1	882.9	871.7	860.9	851.8	842.1	833.0
22.5°	984.0	954.3	926.0	896.9	873.8	849.5	838.6	823.9	815.3	809.9	800.8
25°	939.4	907.2	874.9	847.0	823.3	801.8	787.4	776.1	766.4	762.1	756.2
27.5°	890.8	858.8	827.7	796.0	769.1	753.6	741.9	733.5	727.8	722.2	719.5
30°	859.9	826.6	793.2	763.8	739.0	723.5	712.7	706.8	702.5	699.8	697.1
32.5°	828.5	795.7	760.6	733.7	711.6	697.7	689.5	683.6	681.5	680.4	679.5
35°	778.2	745.0	712.7	688.5	667.6	662.3	655.2	652.1	651.0	654.7	656.3
37.5°	729.5	698.6	669.0	645.6	631.9	624.0	621.6	621.8	625.6	628.9	632.8
40°	698.2	668.1	640.3	619.8	606.9	602.1	601.0	603.7	607.9	611.8	616.0
42.5°	667.7	638.0	612.7	593.6	584.6	580.2	580.8	583.5	589.5	594.1	600.6
45°	620.4	595.6	570.9	555.3	547.9	548.9	548.9	553.7	559.7	566.6	573.6
47.5°	575.7	550.9	530.5	517.5	513.5	512.6	515.6	521.9	530.4	539.1	548.8
50°	545.6	522.0	504.3	492.5	488.2	489.8	494.1	500.0	510.2	521.0	531.2
52.5°	515.1	493.7	477.3	466.3	463.3	466.2	470.5	479.8	488.8	500.4	512.7
55°	467.8	449.5	436.7	428.6	427.5	429.1	433.9	444.1	457.1	471.6	483.4
57.5°	420.6	405.4	393.5	388.0	388.5	390.0	398.0	410.1	423.8	439.3	454.5
60°	388.9	374.9	365.3	360.9	361.4	364.7	374.4	385.7	402.8	417.9	433.9
62.5°	358.8	346.5	337.3	333.5	332.6	339.7	349.0	360.7	377.9	394.7	412.0
65°	310.4	300.7	293.3	291.1	292.8	298.1	309.9	325.5	340.0	357.7	376.0
67.5°	263.2	255.2	250.0	251.1	253.0	260.9	270.8	284.2	300.6	319.0	337.1
70°	233.1	225.6	221.3	221.8	225.0	234.7	243.3	256.7	274.5	293.3	308.3
72.5°	202.2	197.2	193.4	195.6	198.8	205.5	216.2	229.6	245.2	262.8	278.6
75°	155.2	155.2	153.1	154.7	159.6	165.9	174.0	187.9	203.6	217.5	230.5
77.5°	115.1	114.0	115.3	117.3	120.1	127.7	136.9	146.9	158.6	172.6	183.3
80°	88.1	88.7	91.3	94.5	95.6	101.5	111.2	120.3	129.5	141.3	151.5
82.5°	66.1	66.8	68.1	72.2	73.2	79.6	85.8	94.9	103.2	111.2	119.7
85°	36.0	36.0	38.7	40.3	42.9	47.3	51.0	56.4	63.9	69.3	77.4
87.5°	17.1	17.7	19.8	21.2	22.9	25.5	26.8	31.8	33.8	36.4	40.5
90°	16.8	19.5	21.8	24.1	26.5	28.8	30.6	32.3	34.0	35.9	37.0
92.5°	17.2	18.5	20.8	23.1	25.4	27.8	29.5	31.3	33.0	34.7	35.6
95°	32.4	27.7	28.0	28.3	28.5	28.8	30.6	32.3	34.0	35.9	36.9
97.5°	177.6	164.5	132.0	99.6	67.1	34.5	34.7	34.9	35.1	35.2	35.5
100°	235.8	218.3	178.1	137.9	97.8	57.7	52.7	47.8	42.8	37.9	35.5
102.5°	299.3	298.6	293.4	288.2	283.0	277.7	224.3	171.0	117.5	64.1	37.5
105°	401.2	402.8	404.3	405.8	407.2	408.7	411.3	413.9	416.6	419.2	415.3
107.5°	500.2	501.6	503.6	505.5	507.6	509.6	510.8	512.1	513.4	514.6	515.8
110°	569.4	570.7	572.4	574.1	575.9	577.6	578.2	578.9	579.4	580.0	580.7



TEST NUMBER: P332793-840

CATALOG NUMBER: S124DIW-S795D1340U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	639.2	640.4	641.3	642.1	642.9	643.7	643.6	643.4	643.3	643.2	643.7
115°	739.6	739.9	739.6	739.3	739.0	738.7	739.3	739.9	740.5	741.0	741.3
117.5°	833.7	834.7	835.4	836.0	836.6	837.3	837.2	837.0	836.9	836.8	836.7
120°	896.7	897.1	896.9	896.6	896.3	896.0	896.6	897.1	897.7	898.3	898.3
122.5°	953.5	954.0	954.4	954.8	955.2	955.6	956.0	956.3	956.7	957.0	956.9
125°	1039.5	1039.8	1039.2	1038.5	1037.9	1037.4	1038.2	1039.2	1040.1	1040.9	1041.5
127.5°	1115.6	1116.4	1117.7	1119.0	1120.4	1121.8	1121.6	1121.5	1121.3	1121.1	1120.8
130°	1166.9	1167.5	1168.4	1169.2	1170.1	1171.0	1171.3	1171.5	1171.8	1172.2	1172.4
132.5°	1215.0	1215.9	1217.0	1218.0	1219.1	1220.2	1220.5	1220.8	1221.1	1221.4	1221.4
135°	1282.5	1282.9	1284.0	1285.3	1286.5	1287.6	1288.2	1288.8	1289.3	1289.9	1290.5
137.5°	1346.8	1347.5	1348.7	1350.0	1351.3	1352.5	1353.2	1353.8	1354.4	1355.1	1355.3
140°	1389.5	1390.1	1390.6	1391.2	1391.8	1392.4	1393.2	1394.1	1395.0	1395.8	1396.4
142.5°	1428.1	1428.7	1429.1	1429.4	1429.8	1430.1	1430.8	1431.4	1432.0	1432.7	1433.0
145°	1483.6	1484.1	1484.1	1484.1	1484.1	1484.1	1484.4	1484.6	1484.9	1485.2	1485.7
147.5°	1531.5	1532.2	1531.9	1531.6	1531.3	1531.0	1531.2	1531.5	1531.7	1531.9	1532.2
150°	1562.1	1562.5	1562.3	1562.0	1561.7	1561.4	1561.4	1561.4	1561.4	1561.4	1561.5
152.5°	1588.4	1588.6	1588.1	1587.5	1587.0	1586.5	1587.0	1587.4	1587.9	1588.3	1588.5
155°	1624.1	1623.8	1623.0	1622.0	1621.1	1620.3	1621.4	1622.7	1623.8	1625.0	1625.1
157.5°	1654.5	1653.9	1652.8	1651.8	1650.9	1649.9	1651.4	1652.9	1654.5	1656.0	1656.0
160°	1670.5	1669.9	1669.6	1669.3	1669.0	1668.8	1670.5	1672.2	1674.0	1675.8	1675.8
162.5°	1686.4	1685.7	1685.4	1685.1	1684.8	1684.5	1686.2	1688.0	1689.7	1691.4	1691.3
165°	1706.2	1705.5	1705.5	1705.5	1705.5	1705.5	1707.8	1710.1	1712.4	1714.8	1714.5
167.5°	1722.7	1721.8	1721.7	1721.5	1721.3	1721.1	1723.7	1726.3	1728.8	1731.4	1731.2
170°	1731.2	1730.5	1730.7	1731.0	1731.3	1731.6	1733.9	1736.3	1738.6	1740.9	1740.6
172.5°	1737.5	1736.8	1737.1	1737.4	1737.6	1737.9	1740.2	1742.5	1744.9	1747.3	1746.9
175°	1744.2	1743.5	1743.8	1744.1	1744.4	1744.7	1747.4	1750.0	1752.6	1755.2	1754.7
177.5°	1747.9	1747.3	1747.8	1748.3	1748.7	1749.2	1751.0	1752.9	1754.7	1756.7	1756.2
180°	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3



TEST NUMBER: P332793-840

CATALOG NUMBER: S124DIW-S795D1340U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6
2.5°	1235.5	1234.7	1231.6	1231.2	1231.6	1234.7	1235.5	1236.4	1237.7	1241.9	1236.8
5°	1141.3	1138.6	1137.0	1143.0	1137.0	1138.6	1141.3	1144.5	1149.9	1150.4	1155.8
7.5°	1070.3	1068.1	1063.4	1062.0	1063.4	1068.1	1070.3	1072.3	1077.6	1082.3	1090.1
10°	1024.7	1022.6	1018.3	1017.2	1018.3	1022.6	1024.7	1030.2	1035.5	1041.4	1046.8
12.5°	980.9	976.6	975.7	976.8	975.7	976.6	980.9	988.1	1002.0	1001.9	1003.0
15°	922.7	920.6	914.6	916.3	914.6	920.6	922.7	929.7	936.1	944.2	952.2
17.5°	865.4	862.7	855.6	861.9	855.6	862.7	865.4	869.1	877.4	888.8	900.9
20°	829.3	825.0	821.2	820.6	821.2	825.0	829.3	833.0	842.1	851.8	860.9
22.5°	794.9	791.0	790.7	787.2	790.7	791.0	794.9	800.8	809.9	815.3	823.9
25°	751.9	748.2	747.1	744.4	747.1	748.2	751.9	756.2	762.1	766.4	776.1
27.5°	718.9	717.1	715.2	716.0	715.2	717.1	718.9	719.5	722.2	727.8	733.5
30°	698.7	698.2	697.1	697.1	697.1	698.2	698.7	697.1	699.8	702.5	706.8
32.5°	682.0	681.9	682.6	682.6	682.6	681.9	682.0	679.5	680.4	681.5	683.6
35°	658.4	660.0	661.2	659.5	661.2	660.0	658.4	656.3	654.7	651.0	652.1
37.5°	637.2	638.8	640.4	642.2	640.4	638.8	637.2	632.8	628.9	625.6	621.8
40°	620.9	624.6	625.7	628.4	625.7	624.6	620.9	616.0	611.8	607.9	603.7
42.5°	605.4	609.6	612.4	612.9	612.4	609.6	605.4	600.6	594.1	589.5	583.5
45°	581.7	585.9	589.8	589.8	589.8	585.9	581.7	573.6	566.6	559.7	553.7
47.5°	557.0	563.3	567.0	568.0	567.0	563.3	557.0	548.8	539.1	530.4	521.9
50°	540.3	547.9	551.6	554.3	551.6	547.9	540.3	531.2	521.0	510.2	500.0
52.5°	524.0	531.5	536.5	538.0	536.5	531.5	524.0	512.7	500.4	488.8	479.8
55°	495.7	506.4	512.4	514.5	512.4	506.4	495.7	483.4	471.6	457.1	444.1
57.5°	469.1	479.0	485.8	487.5	485.8	479.0	469.1	454.5	439.3	423.8	410.1
60°	448.5	459.2	467.8	469.4	467.8	459.2	448.5	433.9	417.9	402.8	385.7
62.5°	427.4	438.6	446.4	450.5	446.4	438.6	427.4	412.0	394.7	377.9	360.7
65°	391.0	402.2	409.8	411.4	409.8	402.2	391.0	376.0	357.7	340.0	325.5
67.5°	351.2	362.5	367.5	370.6	367.5	362.5	351.2	337.1	319.0	300.6	284.2
70°	323.4	332.4	337.8	340.5	337.8	332.4	323.4	308.3	293.3	274.5	256.7
72.5°	291.5	301.0	307.3	307.8	307.3	301.0	291.5	278.6	262.8	245.2	229.6
75°	242.8	251.4	254.6	254.6	254.6	251.4	242.8	230.5	217.5	203.6	187.9
77.5°	192.2	196.6	200.7	201.5	200.7	196.6	192.2	183.3	172.6	158.6	146.9
80°	159.6	162.2	165.4	165.4	165.4	162.2	159.6	151.5	141.3	129.5	120.3
82.5°	126.0	128.3	131.5	131.1	131.5	128.3	126.0	119.7	111.2	103.2	94.9
85°	76.2	81.1	80.6	79.5	80.6	81.1	76.2	77.4	69.3	63.9	56.4
87.5°	41.9	42.4	43.8	44.8	43.8	42.4	41.9	40.5	36.4	33.8	31.8
90°	37.6	38.2	38.7	39.3	38.7	38.2	37.6	37.0	35.9	34.0	32.3
92.5°	35.9	36.0	36.1	36.2	36.1	36.0	35.9	35.6	34.7	33.0	31.3
95°	37.1	37.4	37.7	38.0	37.7	37.4	37.1	36.9	35.9	34.0	32.3
97.5°	35.9	36.1	36.4	36.7	36.4	36.1	35.9	35.5	35.2	35.1	34.9
100°	35.9	36.1	36.4	36.7	36.4	36.1	35.9	35.5	37.9	42.8	47.8
102.5°	37.6	37.6	37.7	37.8	37.7	37.6	37.6	37.5	64.1	117.5	171.0
105°	404.8	394.3	383.7	373.3	383.7	394.3	404.8	415.3	419.2	416.6	413.9
107.5°	516.9	518.1	519.2	520.3	519.2	518.1	516.9	515.8	514.6	513.4	512.1
110°	581.6	582.5	583.3	584.2	583.3	582.5	581.6	580.7	580.0	579.4	578.9



TEST NUMBER: P332793-840

CATALOG NUMBER: S124DIW-S795D1340U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	644.8	645.9	647.0	648.1	647.0	645.9	644.8	643.7	643.2	643.3	643.4
115°	741.3	741.3	741.3	741.3	741.3	741.3	741.3	741.3	741.0	740.5	739.9
117.5°	836.6	836.5	836.4	836.2	836.4	836.5	836.6	836.7	836.8	836.9	837.0
120°	897.7	897.1	896.6	896.0	896.6	897.1	897.7	898.3	898.3	897.7	897.1
122.5°	956.3	955.7	955.2	954.6	955.2	955.7	956.3	956.9	957.0	956.7	956.3
125°	1041.8	1042.1	1042.4	1042.7	1042.4	1042.1	1041.8	1041.5	1040.9	1040.1	1039.2
127.5°	1120.6	1120.3	1120.1	1119.9	1120.1	1120.3	1120.6	1120.8	1121.1	1121.3	1121.5
130°	1172.4	1172.4	1172.4	1172.4	1172.4	1172.4	1172.4	1172.4	1172.2	1171.8	1171.5
132.5°	1221.2	1221.0	1220.7	1220.5	1220.7	1221.0	1221.2	1221.4	1221.4	1221.1	1220.8
135°	1291.1	1291.6	1292.2	1292.8	1292.2	1291.6	1291.1	1290.5	1289.9	1289.3	1288.8
137.5°	1355.1	1355.0	1354.8	1354.6	1354.8	1355.0	1355.1	1355.3	1355.1	1354.4	1353.8
140°	1396.7	1397.0	1397.4	1397.7	1397.4	1397.0	1396.7	1396.4	1395.8	1395.0	1394.1
142.5°	1433.1	1433.1	1433.2	1433.2	1433.2	1433.1	1433.1	1433.0	1432.7	1432.0	1431.4
145°	1486.2	1486.8	1487.4	1488.0	1487.4	1486.8	1486.2	1485.7	1485.2	1484.9	1484.6
147.5°	1532.5	1532.8	1533.0	1533.3	1533.0	1532.8	1532.5	1532.2	1531.9	1531.7	1531.5
150°	1561.8	1562.1	1562.4	1562.7	1562.4	1562.1	1561.8	1561.5	1561.4	1561.4	1561.4
152.5°	1588.3	1588.1	1588.0	1587.8	1588.0	1588.1	1588.3	1588.5	1588.3	1587.9	1587.4
155°	1624.3	1623.4	1622.4	1621.6	1622.4	1623.4	1624.3	1625.1	1625.0	1623.8	1622.7
157.5°	1654.5	1652.9	1651.4	1649.9	1651.4	1652.9	1654.5	1656.0	1656.0	1654.5	1652.9
160°	1674.0	1672.2	1670.5	1668.8	1670.5	1672.2	1674.0	1675.8	1675.8	1674.0	1672.2
162.5°	1689.4	1687.4	1685.4	1683.4	1685.4	1687.4	1689.4	1691.3	1691.4	1689.7	1688.0
165°	1712.0	1709.4	1706.8	1704.1	1706.8	1709.4	1712.0	1714.5	1714.8	1712.4	1710.1
167.5°	1728.3	1725.4	1722.5	1719.6	1722.5	1725.4	1728.3	1731.2	1731.4	1728.8	1726.3
170°	1737.8	1734.8	1731.9	1729.0	1731.9	1734.8	1737.8	1740.6	1740.9	1738.6	1736.3
172.5°	1743.6	1740.5	1737.4	1734.2	1737.4	1740.5	1743.6	1746.9	1747.3	1744.9	1742.5
175°	1751.3	1747.8	1744.2	1740.8	1744.2	1747.8	1751.3	1754.7	1755.2	1752.6	1750.0
177.5°	1753.3	1750.6	1747.8	1744.9	1747.8	1750.6	1753.3	1756.2	1756.7	1754.7	1752.9
180°	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3



TEST NUMBER: P332793-840

CATALOG NUMBER: S124DIW-S795D1340U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6
2.5°	1239.4	1241.1	1248.0	1254.5	1262.1	1267.8	1271.6	1275.9	1285.0	1292.2	1299.1
5°	1161.1	1163.9	1177.8	1187.5	1204.2	1218.6	1229.9	1242.2	1256.8	1276.7	1294.9
7.5°	1092.4	1102.3	1117.5	1133.3	1150.2	1169.2	1185.8	1204.4	1229.4	1256.7	1284.9
10°	1053.2	1064.5	1080.7	1098.8	1115.0	1137.0	1157.4	1179.4	1207.9	1241.2	1274.6
12.5°	1014.1	1032.7	1044.9	1066.6	1084.1	1102.2	1123.9	1152.8	1186.0	1221.0	1261.2
15°	965.1	975.3	999.0	1010.8	1035.5	1063.4	1084.9	1113.9	1146.1	1192.3	1237.5
17.5°	908.7	922.1	940.9	963.4	991.8	1013.6	1040.4	1070.2	1110.8	1156.7	1213.2
20°	871.7	882.9	906.1	930.8	960.9	983.9	1012.4	1041.4	1083.3	1132.2	1191.2
22.5°	838.6	849.5	873.8	896.9	926.0	954.3	984.0	1017.7	1057.9	1109.4	1169.7
25°	787.4	801.8	823.3	847.0	874.9	907.2	939.4	969.5	1012.4	1066.6	1131.1
27.5°	741.9	753.6	769.1	796.0	827.7	858.8	890.8	928.6	969.9	1027.2	1094.2
30°	712.7	723.5	739.0	763.8	793.2	826.6	859.9	896.4	939.4	996.3	1064.5
32.5°	689.5	697.7	711.6	733.7	760.6	795.7	828.5	866.4	911.4	967.6	1034.0
35°	655.2	662.3	667.6	688.5	712.7	745.0	778.2	818.5	862.0	915.2	981.8
37.5°	621.6	624.0	631.9	645.6	669.0	698.6	729.5	769.2	813.7	867.8	927.9
40°	601.0	602.1	606.9	619.8	640.3	668.1	698.2	737.4	779.8	830.9	890.5
42.5°	580.8	580.2	584.6	593.6	612.7	638.0	667.7	703.5	745.9	793.0	849.2
45°	548.9	548.9	547.9	555.3	570.9	595.6	620.4	654.7	690.1	736.4	783.7
47.5°	515.6	512.6	513.5	517.5	530.5	550.9	575.7	603.9	635.2	674.3	715.7
50°	494.1	489.8	488.2	492.5	504.3	522.0	545.6	570.4	600.0	634.3	669.7
52.5°	470.5	466.2	463.3	466.3	477.3	493.7	515.1	536.8	563.4	591.4	622.1
55°	433.9	429.1	427.5	428.6	436.7	449.5	467.8	487.7	507.6	530.7	552.1
57.5°	398.0	390.0	388.5	388.0	393.5	405.4	420.6	437.9	452.3	466.3	489.2
60°	374.4	364.7	361.4	360.9	365.3	374.9	388.9	406.1	416.3	425.9	445.8
62.5°	349.0	339.7	332.6	333.5	337.3	346.5	358.8	371.2	378.0	388.5	401.9
65°	309.9	298.1	292.8	291.1	293.3	300.7	310.4	318.5	326.0	330.3	343.2
67.5°	270.8	260.9	253.0	251.1	250.0	255.2	263.2	268.0	273.4	277.1	284.8
70°	243.3	234.7	225.0	221.8	221.3	225.6	233.1	233.6	241.2	242.8	250.9
72.5°	216.2	205.5	198.8	195.6	193.4	197.2	202.2	203.6	207.6	210.6	214.7
75°	174.0	165.9	159.6	154.7	153.1	155.2	155.2	157.9	160.6	162.2	167.0
77.5°	136.9	127.7	120.1	117.3	115.3	114.0	115.1	116.7	115.4	118.3	119.4
80°	111.2	101.5	95.6	94.5	91.3	88.7	88.1	89.7	87.6	88.7	91.8
82.5°	85.8	79.6	73.2	72.2	68.1	66.8	66.1	65.2	65.2	65.0	65.6
85°	51.0	47.3	42.9	40.3	38.7	36.0	36.0	34.9	33.8	32.7	33.3
87.5°	26.8	25.5	22.9	21.2	19.8	17.7	17.1	15.1	14.1	13.0	11.9
90°	30.6	28.8	26.5	24.1	21.8	19.5	16.8	13.5	10.3	7.2	3.9
92.5°	29.5	27.8	25.4	23.1	20.8	18.5	17.2	17.1	16.9	16.7	16.5
95°	30.6	28.8	28.5	28.3	28.0	27.7	32.4	42.3	52.2	62.1	72.0
97.5°	34.7	34.5	67.1	99.6	132.0	164.5	177.6	171.5	165.3	159.2	153.0
100°	52.7	57.7	97.8	137.9	178.1	218.3	235.8	230.6	225.3	220.0	214.8
102.5°	224.3	277.7	283.0	288.2	293.4	298.6	299.3	295.5	291.6	287.8	284.0
105°	411.3	408.7	407.2	405.8	404.3	402.8	401.2	399.5	397.8	396.0	394.3
107.5°	510.8	509.6	507.6	505.5	503.6	501.6	500.2	499.3	498.5	497.6	496.7
110°	578.2	577.6	575.9	574.1	572.4	570.7	569.4	568.5	567.6	566.7	565.8



TEST NUMBER: P332793-840

CATALOG NUMBER: S124DIW-S795D1340U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	643.6	643.7	642.9	642.1	641.3	640.4	639.2	637.6	636.1	634.5	632.9
115°	739.3	738.7	739.0	739.3	739.6	739.9	739.6	738.7	737.9	737.0	736.1
117.5°	837.2	837.3	836.6	836.0	835.4	834.7	833.7	832.6	831.4	830.3	829.1
120°	896.6	896.0	896.3	896.6	896.9	897.1	896.7	895.5	894.3	893.1	892.0
122.5°	956.0	955.6	955.2	954.8	954.4	954.0	953.5	952.8	952.1	951.4	950.7
125°	1038.2	1037.4	1037.9	1038.5	1039.2	1039.8	1039.5	1038.2	1037.1	1035.9	1034.8
127.5°	1121.6	1121.8	1120.4	1119.0	1117.7	1116.4	1115.6	1115.3	1115.0	1114.7	1114.4
130°	1171.3	1171.0	1170.1	1169.2	1168.4	1167.5	1166.9	1166.6	1166.4	1166.1	1165.8
132.5°	1220.5	1220.2	1219.1	1218.0	1217.0	1215.9	1215.0	1214.5	1214.0	1213.5	1212.9
135°	1288.2	1287.6	1286.5	1285.3	1284.0	1282.9	1282.5	1282.8	1283.0	1283.3	1283.6
137.5°	1353.2	1352.5	1351.3	1350.0	1348.7	1347.5	1346.8	1346.7	1346.5	1346.4	1346.3
140°	1393.2	1392.4	1391.8	1391.2	1390.6	1390.1	1389.5	1388.9	1388.3	1387.8	1387.2
142.5°	1430.8	1430.1	1429.8	1429.4	1429.1	1428.7	1428.1	1426.9	1425.9	1424.8	1423.8
145°	1484.4	1484.1	1484.1	1484.1	1484.1	1484.1	1483.6	1482.8	1481.9	1481.0	1480.2
147.5°	1531.2	1531.0	1531.3	1531.6	1531.9	1532.2	1531.5	1529.8	1528.2	1526.5	1524.9
150°	1561.4	1561.4	1561.7	1562.0	1562.3	1562.5	1562.1	1560.9	1559.7	1558.6	1557.4
152.5°	1587.0	1586.5	1587.0	1587.5	1588.1	1588.6	1588.4	1587.4	1586.5	1585.6	1584.7
155°	1621.4	1620.3	1621.1	1622.0	1623.0	1623.8	1624.1	1623.8	1623.5	1623.2	1623.0
157.5°	1651.4	1649.9	1650.9	1651.8	1652.8	1653.9	1654.5	1654.6	1654.8	1655.0	1655.2
160°	1670.5	1668.8	1669.0	1669.3	1669.6	1669.9	1670.5	1671.3	1672.2	1673.1	1674.0
162.5°	1686.2	1684.5	1684.8	1685.1	1685.4	1685.7	1686.4	1687.5	1688.6	1689.6	1690.7
165°	1707.8	1705.5	1705.5	1705.5	1705.5	1705.5	1706.2	1707.6	1709.1	1710.5	1712.0
167.5°	1723.7	1721.1	1721.3	1721.5	1721.7	1721.8	1722.7	1724.2	1725.8	1727.3	1728.8
170°	1733.9	1731.6	1731.3	1731.0	1730.7	1730.5	1731.2	1732.9	1734.6	1736.5	1738.2
172.5°	1740.2	1737.9	1737.6	1737.4	1737.1	1736.8	1737.5	1739.2	1741.0	1742.7	1744.4
175°	1747.4	1744.7	1744.4	1744.1	1743.8	1743.5	1744.2	1746.1	1747.8	1749.5	1751.3
177.5°	1751.0	1749.2	1748.7	1748.3	1747.8	1747.3	1747.9	1749.5	1751.1	1752.8	1754.4
180°	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3



TEST NUMBER: P332793-840

CATALOG NUMBER: S124DIW-S795D1340U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6
2.5°	1305.1	1309.4	1315.0	1324.4	1327.9	1332.2	1338.2	1337.8	1339.5	1345.9	1359.7
5°	1310.0	1326.6	1342.7	1362.0	1382.5	1395.8	1414.1	1425.4	1436.7	1451.2	1475.9
7.5°	1311.9	1338.3	1367.9	1401.8	1432.0	1466.8	1494.0	1519.5	1542.6	1573.3	1602.7
10°	1308.9	1344.3	1382.5	1425.4	1471.1	1509.7	1544.7	1584.4	1618.2	1655.3	1688.6
12.5°	1303.3	1346.0	1397.0	1445.2	1498.5	1555.7	1599.2	1639.4	1684.5	1727.1	1778.4
15°	1290.6	1349.2	1408.8	1472.2	1543.6	1609.6	1672.4	1724.5	1772.9	1836.8	1904.0
17.5°	1274.6	1337.7	1412.9	1489.6	1564.2	1639.7	1717.5	1795.8	1856.8	1936.2	1988.7
20°	1259.5	1332.5	1409.9	1501.2	1575.8	1669.8	1747.2	1822.9	1906.6	1985.6	2048.4
22.5°	1238.4	1318.4	1400.4	1491.3	1589.5	1683.5	1772.9	1855.1	1938.8	2024.7	2100.8
25°	1211.6	1284.1	1381.4	1484.5	1582.3	1684.3	1786.9	1890.0	1980.2	2071.0	2141.9
27.5°	1166.1	1257.7	1348.2	1454.6	1563.3	1678.7	1788.4	1896.3	1990.8	2065.5	2109.4
30°	1143.0	1222.4	1320.7	1427.5	1545.2	1669.3	1783.6	1889.5	1977.5	2037.2	2054.9
32.5°	1108.5	1190.6	1286.8	1397.5	1522.0	1649.5	1768.6	1868.5	1941.9	1973.2	1951.8
35°	1057.5	1131.7	1228.8	1342.2	1471.6	1607.5	1725.2	1809.5	1847.0	1817.5	1743.9
37.5°	996.3	1069.8	1167.4	1278.7	1412.6	1550.7	1657.1	1717.8	1705.4	1631.8	1522.2
40°	953.3	1022.1	1115.0	1235.3	1365.8	1504.4	1597.8	1630.6	1596.2	1491.0	1374.4
42.5°	905.6	972.7	1066.0	1182.0	1320.3	1448.0	1529.5	1532.2	1474.6	1348.8	1231.7
45°	833.0	897.0	985.0	1105.9	1233.7	1354.0	1407.7	1381.4	1275.1	1153.7	1036.0
47.5°	761.3	816.8	903.6	1018.3	1139.7	1241.0	1267.6	1220.2	1106.9	989.1	880.1
50°	708.9	764.8	846.5	956.0	1073.1	1160.6	1173.6	1110.6	999.6	880.8	795.5
52.5°	658.6	714.1	792.7	894.1	1001.4	1080.3	1080.8	1008.0	897.3	791.4	712.1
55°	584.9	634.8	705.7	796.5	892.1	953.8	938.9	863.6	767.5	675.7	606.3
57.5°	513.8	557.2	622.6	698.3	782.5	833.4	808.5	736.1	650.3	572.4	519.9
60°	467.8	509.2	565.0	636.4	707.3	747.1	723.5	657.9	579.0	516.1	470.5
62.5°	423.1	458.1	511.7	573.7	639.4	668.9	647.8	583.2	514.9	458.2	421.1
65°	359.8	388.3	431.3	484.4	532.3	557.4	539.8	479.6	427.5	386.7	357.2
67.5°	300.7	323.0	355.6	398.2	438.8	452.4	436.4	394.5	350.3	317.6	296.8
70°	259.9	280.9	308.3	341.0	376.5	391.0	374.9	341.5	305.6	275.5	255.1
72.5°	224.3	240.5	263.6	291.6	319.3	333.9	322.9	290.8	260.4	238.1	220.8
75°	170.8	184.8	200.9	220.8	242.3	251.9	242.3	220.3	199.2	182.6	170.3
77.5°	124.2	131.7	144.1	159.0	172.4	179.9	171.5	156.5	143.7	132.3	126.2
80°	94.5	99.9	108.5	120.3	129.5	136.4	131.1	118.7	108.5	101.0	98.3
82.5°	68.8	72.4	78.0	86.7	92.9	96.4	94.1	85.1	81.0	74.3	71.6
85°	33.8	36.0	39.8	42.4	47.8	48.4	48.9	45.1	41.4	39.8	37.6
87.5°	13.0	14.1	16.1	18.0	20.2	21.1	21.2	21.6	20.4	20.3	18.9
90°	7.2	10.3	13.5	16.8	19.5	21.8	24.1	26.5	28.8	30.6	32.3
92.5°	16.7	16.9	17.1	17.2	18.5	20.8	23.1	25.4	27.8	29.5	31.3
95°	62.1	52.2	42.3	32.4	27.7	28.0	28.3	28.5	28.8	30.6	32.3
97.5°	159.2	165.3	171.5	177.6	164.5	132.0	99.6	67.1	34.5	34.7	34.9
100°	220.0	225.3	230.6	235.8	218.3	178.1	137.9	97.8	57.7	52.7	47.8
102.5°	287.8	291.6	295.5	299.3	298.6	293.4	288.2	283.0	277.7	224.3	171.0
105°	396.0	397.8	399.5	401.2	402.8	404.3	405.8	407.2	408.7	411.3	413.9
107.5°	497.6	498.5	499.3	500.2	501.6	503.6	505.5	507.6	509.6	510.8	512.1
110°	566.7	567.6	568.5	569.4	570.7	572.4	574.1	575.9	577.6	578.2	578.9





TEST NUMBER: P332793-840

CATALOG NUMBER: S124DIW-S795D1340U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	634.5	636.1	637.6	639.2	640.4	641.3	642.1	642.9	643.7	643.6	643.4
115°	737.0	737.9	738.7	739.6	739.9	739.6	739.3	739.0	738.7	739.3	739.9
117.5°	830.3	831.4	832.6	833.7	834.7	835.4	836.0	836.6	837.3	837.2	837.0
120°	893.1	894.3	895.5	896.7	897.1	896.9	896.6	896.3	896.0	896.6	897.1
122.5°	951.4	952.1	952.8	953.5	954.0	954.4	954.8	955.2	955.6	956.0	956.3
125°	1035.9	1037.1	1038.2	1039.5	1039.8	1039.2	1038.5	1037.9	1037.4	1038.2	1039.2
127.5°	1114.7	1115.0	1115.3	1115.6	1116.4	1117.7	1119.0	1120.4	1121.8	1121.6	1121.5
130°	1166.1	1166.4	1166.6	1166.9	1167.5	1168.4	1169.2	1170.1	1171.0	1171.3	1171.5
132.5°	1213.5	1214.0	1214.5	1215.0	1215.9	1217.0	1218.0	1219.1	1220.2	1220.5	1220.8
135°	1283.3	1283.0	1282.8	1282.5	1282.9	1284.0	1285.3	1286.5	1287.6	1288.2	1288.8
137.5°	1346.4	1346.5	1346.7	1346.8	1347.5	1348.7	1350.0	1351.3	1352.5	1353.2	1353.8
140°	1387.8	1388.3	1388.9	1389.5	1390.1	1390.6	1391.2	1391.8	1392.4	1393.2	1394.1
142.5°	1424.8	1425.9	1426.9	1428.1	1428.7	1429.1	1429.4	1429.8	1430.1	1430.8	1431.4
145°	1481.0	1481.9	1482.8	1483.6	1484.1	1484.1	1484.1	1484.1	1484.1	1484.4	1484.6
147.5°	1526.5	1528.2	1529.8	1531.5	1532.2	1531.9	1531.6	1531.3	1531.0	1531.2	1531.5
150°	1558.6	1559.7	1560.9	1562.1	1562.5	1562.3	1562.0	1561.7	1561.4	1561.4	1561.4
152.5°	1585.6	1586.5	1587.4	1588.4	1588.6	1588.1	1587.5	1587.0	1586.5	1587.0	1587.4
155°	1623.2	1623.5	1623.8	1624.1	1623.8	1623.0	1622.0	1621.1	1620.3	1621.4	1622.7
157.5°	1655.0	1654.8	1654.6	1654.5	1653.9	1652.8	1651.8	1650.9	1649.9	1651.4	1652.9
160°	1673.1	1672.2	1671.3	1670.5	1669.9	1669.6	1669.3	1669.0	1668.8	1670.5	1672.2
162.5°	1689.6	1688.6	1687.5	1686.4	1685.7	1685.4	1685.1	1684.8	1684.5	1686.2	1688.0
165°	1710.5	1709.1	1707.6	1706.2	1705.5	1705.5	1705.5	1705.5	1705.5	1707.8	1710.1
167.5°	1727.3	1725.8	1724.2	1722.7	1721.8	1721.7	1721.5	1721.3	1721.1	1723.7	1726.3
170°	1736.5	1734.6	1732.9	1731.2	1730.5	1730.7	1731.0	1731.3	1731.6	1733.9	1736.3
172.5°	1742.7	1741.0	1739.2	1737.5	1736.8	1737.1	1737.4	1737.6	1737.9	1740.2	1742.5
175°	1749.5	1747.8	1746.1	1744.2	1743.5	1743.8	1744.1	1744.4	1744.7	1747.4	1750.0
177.5°	1752.8	1751.1	1749.5	1747.9	1747.3	1747.8	1748.3	1748.7	1749.2	1751.0	1752.9
180°	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3



TEST NUMBER: P332793-840

CATALOG NUMBER: S124DIW-S795D1340U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6
2.5°	1366.5	1367.5	1371.3	1374.3	1375.1	1379.5	1379.9
5°	1486.6	1495.8	1513.5	1515.1	1517.8	1531.8	1521.1
7.5°	1627.4	1650.5	1666.1	1679.7	1684.7	1690.7	1689.5
10°	1717.6	1752.0	1769.2	1796.5	1797.7	1804.6	1800.3
12.5°	1808.3	1848.3	1879.6	1884.6	1907.6	1911.2	1917.2
15°	1936.7	1979.1	2022.7	2038.2	2069.9	2077.5	2089.3
17.5°	2057.5	2100.8	2131.3	2171.6	2184.6	2202.0	2190.2
20°	2123.6	2170.9	2209.6	2241.3	2254.7	2264.3	2263.3
22.5°	2163.6	2211.3	2242.6	2266.6	2279.2	2283.3	2283.0
25°	2188.6	2216.0	2225.6	2234.8	2220.9	2216.0	2218.2
27.5°	2119.0	2111.9	2086.7	2053.6	2019.2	1992.0	1977.1
30°	2023.2	1981.4	1943.2	1876.5	1842.2	1821.8	1803.5
32.5°	1887.4	1821.1	1747.7	1686.7	1647.6	1617.3	1612.8
35°	1654.8	1554.9	1465.2	1390.5	1351.8	1319.1	1311.5
37.5°	1406.8	1303.0	1222.3	1156.6	1115.0	1091.9	1070.3
40°	1242.2	1153.2	1073.6	1017.7	986.1	969.5	956.0
42.5°	1115.5	1034.1	955.0	912.5	883.8	873.6	865.8
45°	940.4	864.7	809.9	777.7	761.0	743.9	735.8
47.5°	800.2	738.6	702.5	675.1	657.3	647.1	642.0
50°	720.7	670.2	638.0	617.1	601.0	592.9	588.7
52.5°	650.3	608.8	581.8	565.1	554.2	548.3	546.5
55°	560.2	528.5	511.3	496.9	488.8	483.4	481.2
57.5°	487.0	462.5	448.6	436.7	433.5	429.0	427.5
60°	438.8	420.0	408.2	400.1	397.5	392.0	393.1
62.5°	396.3	380.9	370.8	366.2	362.6	358.1	359.6
65°	335.2	323.9	318.5	314.2	309.9	307.2	309.3
67.5°	281.2	273.5	266.2	263.7	261.6	261.2	258.8
70°	246.0	239.5	233.1	231.5	231.5	229.3	228.8
72.5°	212.1	207.3	203.0	201.9	200.2	201.0	198.7
75°	163.8	160.1	158.4	156.8	156.3	156.3	154.7
77.5°	121.1	118.3	115.7	115.7	113.7	113.0	112.8
80°	91.8	90.8	88.7	88.7	87.6	88.1	87.1
82.5°	69.1	67.6	67.2	66.2	64.7	64.8	63.8
85°	37.1	35.4	34.9	33.3	32.2	33.3	32.2
87.5°	19.7	19.6	19.4	18.7	18.4	18.5	17.3
90°	34.0	35.9	37.0	37.6	38.2	38.7	39.3
92.5°	33.0	34.7	35.6	35.9	36.0	36.1	36.2
95°	34.0	35.9	36.9	37.1	37.4	37.7	38.0
97.5°	35.1	35.2	35.5	35.9	36.1	36.4	36.7
100°	42.8	37.9	35.5	35.9	36.1	36.4	36.7
102.5°	117.5	64.1	37.5	37.6	37.6	37.7	37.8
105°	416.6	419.2	415.3	404.8	394.3	383.7	373.3
107.5°	513.4	514.6	515.8	516.9	518.1	519.2	520.3
110°	579.4	580.0	580.7	581.6	582.5	583.3	584.2



TEST NUMBER: P332793-840

CATALOG NUMBER: S124DIW-S795D1340U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	643.3	643.2	643.7	644.8	645.9	647.0	648.1
115°	740.5	741.0	741.3	741.3	741.3	741.3	741.3
117.5°	836.9	836.8	836.7	836.6	836.5	836.4	836.2
120°	897.7	898.3	898.3	897.7	897.1	896.6	896.0
122.5°	956.7	957.0	956.9	956.3	955.7	955.2	954.6
125°	1040.1	1040.9	1041.5	1041.8	1042.1	1042.4	1042.7
127.5°	1121.3	1121.1	1120.8	1120.6	1120.3	1120.1	1119.9
130°	1171.8	1172.2	1172.4	1172.4	1172.4	1172.4	1172.4
132.5°	1221.1	1221.4	1221.4	1221.2	1221.0	1220.7	1220.5
135°	1289.3	1289.9	1290.5	1291.1	1291.6	1292.2	1292.8
137.5°	1354.4	1355.1	1355.3	1355.1	1355.0	1354.8	1354.6
140°	1395.0	1395.8	1396.4	1396.7	1397.0	1397.4	1397.7
142.5°	1432.0	1432.7	1433.0	1433.1	1433.1	1433.2	1433.2
145°	1484.9	1485.2	1485.7	1486.2	1486.8	1487.4	1488.0
147.5°	1531.7	1531.9	1532.2	1532.5	1532.8	1533.0	1533.3
150°	1561.4	1561.4	1561.5	1561.8	1562.1	1562.4	1562.7
152.5°	1587.9	1588.3	1588.5	1588.3	1588.1	1588.0	1587.8
155°	1623.8	1625.0	1625.1	1624.3	1623.4	1622.4	1621.6
157.5°	1654.5	1656.0	1656.0	1654.5	1652.9	1651.4	1649.9
160°	1674.0	1675.8	1675.8	1674.0	1672.2	1670.5	1668.8
162.5°	1689.7	1691.4	1691.3	1689.4	1687.4	1685.4	1683.4
165°	1712.4	1714.8	1714.5	1712.0	1709.4	1706.8	1704.1
167.5°	1728.8	1731.4	1731.2	1728.3	1725.4	1722.5	1719.6
170°	1738.6	1740.9	1740.6	1737.8	1734.8	1731.9	1729.0
172.5°	1744.9	1747.3	1746.9	1743.6	1740.5	1737.4	1734.2
175°	1752.6	1755.2	1754.7	1751.3	1747.8	1744.2	1740.8
177.5°	1754.7	1756.7	1756.2	1753.3	1750.6	1747.8	1744.9
180°	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3

(END OF REPORT)