

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332775-840

Luminaire Tested: **S124DIW-S795D470U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332775-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S795D470U840-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5471.7 lumens
Efficiency: N/A
Efficacy: 145.1 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332775-840

CATALOG NUMBER: S124DIW-S795D470U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332775-840

CATALOG NUMBER: S124DIW-S795D470U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	70	70	70	65
1	102	97	93	90	95	92	88	85	81	79	76	71	70	68	63	61	60	56
2	93	85	79	74	87	80	75	70	71	67	64	63	60	57	55	53	51	47
3	85	75	68	62	79	71	65	59	63	58	54	56	52	49	49	46	44	40
4	78	67	59	53	73	63	56	51	56	51	46	50	46	42	44	41	38	35
5	72	60	52	46	67	57	49	44	51	45	40	45	40	37	40	36	33	30
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	33	29	27
7	61	49	41	35	57	46	39	34	42	36	31	37	32	29	33	29	26	24
8	57	44	37	31	53	42	35	30	38	32	28	34	29	26	31	27	24	21
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	28	24	21	19
10	50	37	30	25	47	36	29	24	32	27	23	29	24	21	26	22	19	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10467	10467	10467	10467
5°	12327	10494	9263	10494
10°	14758	10449	8338	10449
15°	17462	10343	7658	10343
20°	19444	10234	7050	10234
25°	19759	10075	6631	10075
30°	16812	9923	6498	9923
35°	12925	9676	6500	9676
40°	10075	9385	6622	9385
45°	8401	8947	6734	8947
50°	7394	8411	6962	8411
55°	6773	7771	7241	7771
60°	6347	7198	7579	7198
65°	5908	6556	7859	6556
70°	5401	5922	8037	5922
75°	4825	5209	7941	5209
80°	4049	4268	7689	4268
85°	2983	3084	7364	3084



TEST NUMBER: P332775-840

CATALOG NUMBER: S124DIW-S795D470U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	2.3
10°-20°	389.3	7.1
20°-30°	617.4	11.3
30°-40°	687.1	12.6
40°-50°	625.4	11.4
50°-60°	511.1	9.3
60°-70°	364.8	6.7
70°-80°	200.9	3.7
80°-90°	56.6	1.0
90°-100°	20.9	0.4
100°-110°	133.4	2.4
110°-120°	255.3	4.7
120°-130°	324.0	5.9
130°-140°	346.7	6.3
140°-150°	324.2	5.9
150°-160°	261.4	4.8
160°-170°	168.6	3.1
170°-180°	58.1	1.1
0°-30°	1133.0	20.7
0°-40°	1820.1	33.3
0°-60°	2956.5	54.0
0°-90°	3578.9	65.4
90°-120°	409.6	7.5
90°-150°	1404.6	25.7
90°-180°	1893.0	34.6
0°-180°	5471.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1297	1297	1297	1297	1297	
5°	1521	1295	1143	1295	1521	155
15°	2089	1238	916	1238	2089	590
25°	2218	1131	744	1131	2218	978
35°	1312	982	660	982	1312	832
45°	736	784	590	784	736	580
55°	481	552	514	552	481	435
65°	309	343	411	343	309	306
75°	155	167	255	167	155	164
85°	32	33	80	33	32	40
90°	14	1	14	1	14	7
95°	13	25	13	25	13	11
105°	130	138	130	138	130	114
115°	259	257	259	257	259	256
125°	364	362	364	362	364	324
135°	452	448	452	448	452	348
145°	520	517	520	517	520	325
155°	567	567	567	567	567	261
165°	595	598	595	598	595	168
175°	608	612	608	612	608	58
180°	612	612	612	612	612	



TEST NUMBER: P332775-840

CATALOG NUMBER: S124DIW-S795D470U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6
2.5°	1379.9	1379.5	1375.1	1374.3	1371.3	1367.5	1366.5	1359.7	1345.9	1339.5	1337.8
5°	1521.1	1531.8	1517.8	1515.1	1513.5	1495.8	1486.6	1475.9	1451.2	1436.7	1425.4
7.5°	1689.5	1690.7	1684.7	1679.7	1666.1	1650.5	1627.4	1602.7	1573.3	1542.6	1519.5
10°	1800.3	1804.6	1797.7	1796.5	1769.2	1752.0	1717.6	1688.6	1655.3	1618.2	1584.4
12.5°	1917.2	1911.2	1907.6	1884.6	1879.6	1848.3	1808.3	1778.4	1727.1	1684.5	1639.4
15°	2089.3	2077.5	2069.9	2038.2	2022.7	1979.1	1936.7	1904.0	1836.8	1772.9	1724.5
17.5°	2190.2	2202.0	2184.6	2171.6	2131.3	2100.8	2057.5	1988.7	1936.2	1856.8	1795.8
20°	2263.3	2264.3	2254.7	2241.3	2209.6	2170.9	2123.6	2048.4	1985.6	1906.6	1822.9
22.5°	2283.0	2283.3	2279.2	2266.6	2242.6	2211.3	2163.6	2100.8	2024.7	1938.8	1855.1
25°	2218.2	2216.0	2220.9	2234.8	2225.6	2216.0	2188.6	2141.9	2071.0	1980.2	1890.0
27.5°	1977.1	1992.0	2019.2	2053.6	2086.7	2111.9	2119.0	2109.4	2065.5	1990.8	1896.3
30°	1803.5	1821.8	1842.2	1876.5	1943.2	1981.4	2023.2	2054.9	2037.2	1977.5	1889.5
32.5°	1612.8	1617.3	1647.6	1686.7	1747.7	1821.1	1887.4	1951.8	1973.2	1941.9	1868.5
35°	1311.5	1319.1	1351.8	1390.5	1465.2	1554.9	1654.8	1743.9	1817.5	1847.0	1809.5
37.5°	1070.3	1091.9	1115.0	1156.6	1222.3	1303.0	1406.8	1522.2	1631.8	1705.4	1717.8
40°	956.0	969.5	986.1	1017.7	1073.6	1153.2	1242.2	1374.4	1491.0	1596.2	1630.6
42.5°	865.8	873.6	883.8	912.5	955.0	1034.1	1115.5	1231.7	1348.8	1474.6	1532.2
45°	735.8	743.9	761.0	777.7	809.9	864.7	940.4	1036.0	1153.7	1275.1	1381.4
47.5°	642.0	647.1	657.3	675.1	702.5	738.6	800.2	880.1	989.1	1106.9	1220.2
50°	588.7	592.9	601.0	617.1	638.0	670.2	720.7	795.5	880.8	999.6	1110.6
52.5°	546.5	548.3	554.2	565.1	581.8	608.8	650.3	712.1	791.4	897.3	1008.0
55°	481.2	483.4	488.8	496.9	511.3	528.5	560.2	606.3	675.7	767.5	863.6
57.5°	427.5	429.0	433.5	436.7	448.6	462.5	487.0	519.9	572.4	650.3	736.1
60°	393.1	392.0	397.5	400.1	408.2	420.0	438.8	470.5	516.1	579.0	657.9
62.5°	359.6	358.1	362.6	366.2	370.8	380.9	396.3	421.1	458.2	514.9	583.2
65°	309.3	307.2	309.9	314.2	318.5	323.9	335.2	357.2	386.7	427.5	479.6
67.5°	258.8	261.2	261.6	263.7	266.2	273.5	281.2	296.8	317.6	350.3	394.5
70°	228.8	229.3	231.5	231.5	233.1	239.5	246.0	255.1	275.5	305.6	341.5
72.5°	198.7	201.0	200.2	201.9	203.0	207.3	212.1	220.8	238.1	260.4	290.8
75°	154.7	156.3	156.3	156.8	158.4	160.1	163.8	170.3	182.6	199.2	220.3
77.5°	112.8	113.0	113.7	115.7	115.7	118.3	121.1	126.2	132.3	143.7	156.5
80°	87.1	88.1	87.6	88.7	88.7	90.8	91.8	98.3	101.0	108.5	118.7
82.5°	63.8	64.8	64.7	66.2	67.2	67.6	69.1	71.6	74.3	81.0	85.1
85°	32.2	33.3	32.2	33.3	34.9	35.4	37.1	37.6	39.8	41.4	45.1
87.5°	12.2	13.4	13.4	13.8	14.6	14.9	15.2	14.7	16.4	16.7	18.2
90°	13.7	13.5	13.3	13.1	12.9	12.5	11.9	11.3	10.7	10.1	9.3
92.5°	12.6	12.6	12.5	12.5	12.4	12.1	11.5	10.9	10.3	9.7	8.9
95°	13.2	13.1	13.0	12.9	12.8	12.5	11.9	11.3	10.7	10.1	10.0
97.5°	12.8	12.7	12.6	12.5	12.4	12.3	12.2	12.2	12.1	12.1	23.4
100°	12.8	12.7	12.6	12.5	12.4	13.2	14.9	16.7	18.4	20.1	34.1
102.5°	13.2	13.1	13.1	13.1	13.1	22.4	41.1	59.7	78.4	97.0	98.9
105°	130.5	134.1	137.7	141.4	145.1	146.4	145.5	144.6	143.7	142.8	142.3
107.5°	181.8	181.4	181.0	180.7	180.3	179.9	179.4	178.9	178.4	178.0	177.3
110°	204.1	203.8	203.5	203.2	202.9	202.7	202.5	202.3	202.1	201.9	201.3



TEST NUMBER: P332775-840

CATALOG NUMBER: S124DIW-S795D470U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	226.4	226.1	225.7	225.3	224.9	224.7	224.8	224.8	224.9	224.9	224.6
115°	259.0	259.0	259.0	259.0	259.0	258.9	258.7	258.5	258.3	258.1	258.2
117.5°	292.2	292.3	292.3	292.3	292.4	292.4	292.5	292.5	292.5	292.6	292.4
120°	313.1	313.3	313.5	313.7	313.9	313.9	313.7	313.5	313.3	313.1	313.2
122.5°	333.6	333.8	334.0	334.2	334.4	334.4	334.3	334.2	334.1	334.0	333.8
125°	364.3	364.2	364.1	364.0	363.9	363.7	363.3	363.0	362.7	362.4	362.6
127.5°	391.3	391.4	391.4	391.5	391.6	391.7	391.7	391.8	391.9	391.9	391.5
130°	409.6	409.6	409.6	409.6	409.6	409.6	409.5	409.4	409.3	409.2	408.9
132.5°	426.5	426.6	426.7	426.7	426.8	426.8	426.7	426.6	426.5	426.4	426.0
135°	451.7	451.5	451.3	451.1	450.9	450.7	450.5	450.3	450.1	449.9	449.5
137.5°	473.3	473.4	473.4	473.5	473.5	473.5	473.2	473.0	472.8	472.6	472.1
140°	488.4	488.3	488.2	488.1	488.0	487.8	487.5	487.2	486.9	486.6	486.4
142.5°	500.8	500.8	500.8	500.7	500.7	500.6	500.4	500.1	499.9	499.7	499.6
145°	519.9	519.7	519.5	519.3	519.1	519.0	518.9	518.8	518.7	518.6	518.6
147.5°	535.7	535.6	535.5	535.4	535.3	535.2	535.1	535.1	535.0	534.9	535.0
150°	546.0	545.9	545.8	545.7	545.6	545.5	545.5	545.5	545.5	545.5	545.6
152.5°	554.8	554.8	554.9	555.0	555.0	555.0	554.8	554.6	554.5	554.3	554.5
155°	566.6	566.9	567.2	567.5	567.8	567.7	567.3	566.9	566.5	566.1	566.4
157.5°	576.5	577.0	577.5	578.0	578.6	578.6	578.0	577.5	577.0	576.5	576.8
160°	583.1	583.7	584.3	584.9	585.5	585.5	584.9	584.3	583.7	583.1	583.2
162.5°	588.2	588.9	589.6	590.3	591.0	591.0	590.4	589.8	589.2	588.5	588.7
165°	595.4	596.3	597.2	598.1	599.1	599.2	598.3	597.5	596.7	595.9	595.9
167.5°	600.9	601.9	602.9	603.9	604.9	605.0	604.1	603.2	602.3	601.4	601.5
170°	604.1	605.1	606.1	607.1	608.2	608.3	607.4	606.6	605.8	605.0	604.9
172.5°	605.9	607.0	608.1	609.3	610.4	610.5	609.7	608.8	608.0	607.2	607.1
175°	608.2	609.5	610.7	611.9	613.1	613.3	612.4	611.5	610.6	609.7	609.6
177.5°	609.8	610.7	611.7	612.7	613.6	613.8	613.1	612.5	611.8	611.2	611.0
180°	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9



TEST NUMBER: P332775-840

CATALOG NUMBER: S124DIW-S795D470U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6
2.5°	1338.2	1332.2	1327.9	1324.4	1315.0	1309.4	1305.1	1299.1	1292.2	1285.0	1275.9
5°	1414.1	1395.8	1382.5	1362.0	1342.7	1326.6	1310.0	1294.9	1276.7	1256.8	1242.2
7.5°	1494.0	1466.8	1432.0	1401.8	1367.9	1338.3	1311.9	1284.9	1256.7	1229.4	1204.4
10°	1544.7	1509.7	1471.1	1425.4	1382.5	1344.3	1308.9	1274.6	1241.2	1207.9	1179.4
12.5°	1599.2	1555.7	1498.5	1445.2	1397.0	1346.0	1303.3	1261.2	1221.0	1186.0	1152.8
15°	1672.4	1609.6	1543.6	1472.2	1408.8	1349.2	1290.6	1237.5	1192.3	1146.1	1113.9
17.5°	1717.5	1639.7	1564.2	1489.6	1412.9	1337.7	1274.6	1213.2	1156.7	1110.8	1070.2
20°	1747.2	1669.8	1575.8	1501.2	1409.9	1332.5	1259.5	1191.2	1132.2	1083.3	1041.4
22.5°	1772.9	1683.5	1589.5	1491.3	1400.4	1318.4	1238.4	1169.7	1109.4	1057.9	1017.7
25°	1786.9	1684.3	1582.3	1484.5	1381.4	1284.1	1211.6	1131.1	1066.6	1012.4	969.5
27.5°	1788.4	1678.7	1563.3	1454.6	1348.2	1257.7	1166.1	1094.2	1027.2	969.9	928.6
30°	1783.6	1669.3	1545.2	1427.5	1320.7	1222.4	1143.0	1064.5	996.3	939.4	896.4
32.5°	1768.6	1649.5	1522.0	1397.5	1286.8	1190.6	1108.5	1034.0	967.6	911.4	866.4
35°	1725.2	1607.5	1471.6	1342.2	1228.8	1131.7	1057.5	981.8	915.2	862.0	818.5
37.5°	1657.1	1550.7	1412.6	1278.7	1167.4	1069.8	996.3	927.9	867.8	813.7	769.2
40°	1597.8	1504.4	1365.8	1235.3	1115.0	1022.1	953.3	890.5	830.9	779.8	737.4
42.5°	1529.5	1448.0	1320.3	1182.0	1066.0	972.7	905.6	849.2	793.0	745.9	703.5
45°	1407.7	1354.0	1233.7	1105.9	985.0	897.0	833.0	783.7	736.4	690.1	654.7
47.5°	1267.6	1241.0	1139.7	1018.3	903.6	816.8	761.3	715.7	674.3	635.2	603.9
50°	1173.6	1160.6	1073.1	956.0	846.5	764.8	708.9	669.7	634.3	600.0	570.4
52.5°	1080.8	1080.3	1001.4	894.1	792.7	714.1	658.6	622.1	591.4	563.4	536.8
55°	938.9	953.8	892.1	796.5	705.7	634.8	584.9	552.1	530.7	507.6	487.7
57.5°	808.5	833.4	782.5	698.3	622.6	557.2	513.8	489.2	466.3	452.3	437.9
60°	723.5	747.1	707.3	636.4	565.0	509.2	467.8	445.8	425.9	416.3	406.1
62.5°	647.8	668.9	639.4	573.7	511.7	458.1	423.1	401.9	388.5	378.0	371.2
65°	539.8	557.4	532.3	484.4	431.3	388.3	359.8	343.2	330.3	326.0	318.5
67.5°	436.4	452.4	438.8	398.2	355.6	323.0	300.7	284.8	277.1	273.4	268.0
70°	374.9	391.0	376.5	341.0	308.3	280.9	259.9	250.9	242.8	241.2	233.6
72.5°	322.9	333.9	319.3	291.6	263.6	240.5	224.3	214.7	210.6	207.6	203.6
75°	242.3	251.9	242.3	220.8	200.9	184.8	170.8	167.0	162.2	160.6	157.9
77.5°	171.5	179.9	172.4	159.0	144.1	131.7	124.2	119.4	118.3	115.4	116.7
80°	131.1	136.4	129.5	120.3	108.5	99.9	94.5	91.8	88.7	87.6	89.7
82.5°	94.1	96.4	92.9	86.7	78.0	72.4	68.8	65.6	65.0	65.2	65.2
85°	48.9	48.4	47.8	42.4	39.8	36.0	33.8	33.3	32.7	33.8	34.9
87.5°	18.0	18.3	17.7	15.8	14.2	12.7	12.1	11.4	12.1	12.7	13.4
90°	8.5	7.7	6.8	5.9	4.7	3.6	2.5	1.4	2.5	3.6	4.7
92.5°	8.1	7.3	6.5	6.1	6.0	5.9	5.9	5.8	5.9	5.9	6.0
95°	9.9	9.8	9.7	11.3	14.8	18.3	21.7	25.1	21.7	18.3	14.8
97.5°	34.7	46.2	57.5	62.1	59.9	57.8	55.6	53.4	55.6	57.8	59.9
100°	48.2	62.2	76.2	82.4	80.6	78.8	76.9	75.0	76.9	78.8	80.6
102.5°	100.7	102.5	104.3	104.6	103.2	101.9	100.6	99.3	100.6	101.9	103.2
105°	141.8	141.3	140.8	140.2	139.6	139.0	138.4	137.7	138.4	139.0	139.6
107.5°	176.6	175.9	175.3	174.8	174.5	174.2	173.9	173.6	173.9	174.2	174.5
110°	200.7	200.0	199.3	198.9	198.6	198.3	198.0	197.7	198.0	198.3	198.6



TEST NUMBER: P332775-840

CATALOG NUMBER: S124DIW-S795D470U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	224.3	224.1	223.8	223.4	222.8	222.3	221.7	221.2	221.7	222.3	222.8
115°	258.3	258.4	258.5	258.4	258.1	257.8	257.5	257.2	257.5	257.8	258.1
117.5°	292.1	291.9	291.6	291.3	290.9	290.5	290.1	289.7	290.1	290.5	290.9
120°	313.3	313.4	313.5	313.3	312.9	312.5	312.0	311.6	312.0	312.5	312.9
122.5°	333.7	333.5	333.4	333.2	333.0	332.6	332.4	332.1	332.4	332.6	333.0
125°	362.8	363.0	363.2	363.1	362.7	362.3	361.9	361.5	361.9	362.3	362.7
127.5°	391.0	390.5	390.1	389.8	389.7	389.6	389.5	389.4	389.5	389.6	389.7
130°	408.6	408.3	408.0	407.8	407.7	407.6	407.4	407.3	407.4	407.6	407.7
132.5°	425.6	425.3	424.9	424.5	424.3	424.1	423.9	423.8	423.9	424.1	424.3
135°	449.1	448.7	448.3	448.1	448.2	448.3	448.4	448.5	448.4	448.3	448.2
137.5°	471.7	471.2	470.8	470.6	470.5	470.5	470.4	470.4	470.4	470.5	470.5
140°	486.1	485.8	485.6	485.4	485.2	485.0	484.8	484.6	484.8	485.0	485.2
142.5°	499.5	499.3	499.2	499.0	498.6	498.3	497.9	497.5	497.9	498.3	498.6
145°	518.6	518.6	518.6	518.4	518.1	517.8	517.5	517.2	517.5	517.8	518.1
147.5°	535.1	535.2	535.3	535.1	534.5	533.9	533.4	532.8	533.4	533.9	534.5
150°	545.7	545.8	545.9	545.8	545.4	545.0	544.6	544.2	544.6	545.0	545.4
152.5°	554.7	554.9	555.0	555.0	554.6	554.3	554.0	553.7	554.0	554.3	554.6
155°	566.7	567.0	567.3	567.4	567.3	567.2	567.1	567.0	567.1	567.2	567.3
157.5°	577.1	577.5	577.8	578.0	578.1	578.1	578.2	578.3	578.2	578.1	578.1
160°	583.3	583.4	583.5	583.7	584.0	584.3	584.6	584.9	584.6	584.3	584.0
162.5°	588.8	588.9	589.0	589.3	589.6	590.0	590.4	590.8	590.4	590.0	589.6
165°	595.9	595.9	595.9	596.1	596.6	597.1	597.6	598.1	597.6	597.1	596.6
167.5°	601.5	601.6	601.6	601.9	602.5	603.0	603.5	604.0	603.5	603.0	602.5
170°	604.8	604.7	604.6	604.9	605.5	606.1	606.7	607.3	606.7	606.1	605.5
172.5°	607.0	606.9	606.8	607.1	607.7	608.3	608.9	609.6	608.9	608.3	607.7
175°	609.5	609.4	609.3	609.5	610.1	610.7	611.3	611.9	611.3	610.7	610.1
177.5°	610.9	610.7	610.6	610.8	611.3	611.9	612.5	613.0	612.5	611.9	611.3
180°	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9



TEST NUMBER: P332775-840

CATALOG NUMBER: S124DIW-S795D470U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6
2.5°	1271.6	1267.8	1262.1	1254.5	1248.0	1241.1	1239.4	1236.8	1241.9	1237.7	1236.4
5°	1229.9	1218.6	1204.2	1187.5	1177.8	1163.9	1161.1	1155.8	1150.4	1149.9	1144.5
7.5°	1185.8	1169.2	1150.2	1133.3	1117.5	1102.3	1092.4	1090.1	1082.3	1077.6	1072.3
10°	1157.4	1137.0	1115.0	1098.8	1080.7	1064.5	1053.2	1046.8	1041.4	1035.5	1030.2
12.5°	1123.9	1102.2	1084.1	1066.6	1044.9	1032.7	1014.1	1003.0	1001.9	1002.0	988.1
15°	1084.9	1063.4	1035.5	1010.8	999.0	975.3	965.1	952.2	944.2	936.1	929.7
17.5°	1040.4	1013.6	991.8	963.4	940.9	922.1	908.7	900.9	888.8	877.4	869.1
20°	1012.4	983.9	960.9	930.8	906.1	882.9	871.7	860.9	851.8	842.1	833.0
22.5°	984.0	954.3	926.0	896.9	873.8	849.5	838.6	823.9	815.3	809.9	800.8
25°	939.4	907.2	874.9	847.0	823.3	801.8	787.4	776.1	766.4	762.1	756.2
27.5°	890.8	858.8	827.7	796.0	769.1	753.6	741.9	733.5	727.8	722.2	719.5
30°	859.9	826.6	793.2	763.8	739.0	723.5	712.7	706.8	702.5	699.8	697.1
32.5°	828.5	795.7	760.6	733.7	711.6	697.7	689.5	683.6	681.5	680.4	679.5
35°	778.2	745.0	712.7	688.5	667.6	662.3	655.2	652.1	651.0	654.7	656.3
37.5°	729.5	698.6	669.0	645.6	631.9	624.0	621.6	621.8	625.6	628.9	632.8
40°	698.2	668.1	640.3	619.8	606.9	602.1	601.0	603.7	607.9	611.8	616.0
42.5°	667.7	638.0	612.7	593.6	584.6	580.2	580.8	583.5	589.5	594.1	600.6
45°	620.4	595.6	570.9	555.3	547.9	548.9	548.9	553.7	559.7	566.6	573.6
47.5°	575.7	550.9	530.5	517.5	513.5	512.6	515.6	521.9	530.4	539.1	548.8
50°	545.6	522.0	504.3	492.5	488.2	489.8	494.1	500.0	510.2	521.0	531.2
52.5°	515.1	493.7	477.3	466.3	463.3	466.2	470.5	479.8	488.8	500.4	512.7
55°	467.8	449.5	436.7	428.6	427.5	429.1	433.9	444.1	457.1	471.6	483.4
57.5°	420.6	405.4	393.5	388.0	388.5	390.0	398.0	410.1	423.8	439.3	454.5
60°	388.9	374.9	365.3	360.9	361.4	364.7	374.4	385.7	402.8	417.9	433.9
62.5°	358.8	346.5	337.3	333.5	332.6	339.7	349.0	360.7	377.9	394.7	412.0
65°	310.4	300.7	293.3	291.1	292.8	298.1	309.9	325.5	340.0	357.7	376.0
67.5°	263.2	255.2	250.0	251.1	253.0	260.9	270.8	284.2	300.6	319.0	337.1
70°	233.1	225.6	221.3	221.8	225.0	234.7	243.3	256.7	274.5	293.3	308.3
72.5°	202.2	197.2	193.4	195.6	198.8	205.5	216.2	229.6	245.2	262.8	278.6
75°	155.2	155.2	153.1	154.7	159.6	165.9	174.0	187.9	203.6	217.5	230.5
77.5°	115.1	114.0	115.3	117.3	120.1	127.7	136.9	146.9	158.6	172.6	183.3
80°	88.1	88.7	91.3	94.5	95.6	101.5	111.2	120.3	129.5	141.3	151.5
82.5°	66.1	66.8	68.1	72.2	73.2	79.6	85.8	94.9	103.2	111.2	119.7
85°	36.0	36.0	38.7	40.3	42.9	47.3	51.0	56.4	63.9	69.3	77.4
87.5°	14.9	15.1	17.0	18.0	19.5	21.8	22.7	27.6	29.5	31.7	35.6
90°	5.9	6.8	7.7	8.5	9.3	10.1	10.7	11.3	11.9	12.5	12.9
92.5°	6.1	6.5	7.3	8.1	8.9	9.7	10.3	10.9	11.5	12.1	12.4
95°	11.3	9.7	9.8	9.9	10.0	10.1	10.7	11.3	11.9	12.5	12.8
97.5°	62.1	57.5	46.2	34.7	23.4	12.1	12.1	12.2	12.2	12.3	12.4
100°	82.4	76.2	62.2	48.2	34.1	20.1	18.4	16.7	14.9	13.2	12.4
102.5°	104.6	104.3	102.5	100.7	98.9	97.0	78.4	59.7	41.1	22.4	13.1
105°	140.2	140.8	141.3	141.8	142.3	142.8	143.7	144.6	145.5	146.4	145.1
107.5°	174.8	175.3	175.9	176.6	177.3	178.0	178.4	178.9	179.4	179.9	180.3
110°	198.9	199.3	200.0	200.7	201.3	201.9	202.1	202.3	202.5	202.7	202.9



TEST NUMBER: P332775-840

CATALOG NUMBER: S124DIW-S795D470U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	223.4	223.8	224.1	224.3	224.6	224.9	224.9	224.8	224.8	224.7	224.9
115°	258.4	258.5	258.4	258.3	258.2	258.1	258.3	258.5	258.7	258.9	259.0
117.5°	291.3	291.6	291.9	292.1	292.4	292.6	292.5	292.5	292.5	292.4	292.4
120°	313.3	313.5	313.4	313.3	313.2	313.1	313.3	313.5	313.7	313.9	313.9
122.5°	333.2	333.4	333.5	333.7	333.8	334.0	334.1	334.2	334.3	334.4	334.4
125°	363.1	363.2	363.0	362.8	362.6	362.4	362.7	363.0	363.3	363.7	363.9
127.5°	389.8	390.1	390.5	391.0	391.5	391.9	391.9	391.8	391.7	391.7	391.6
130°	407.8	408.0	408.3	408.6	408.9	409.2	409.3	409.4	409.5	409.6	409.6
132.5°	424.5	424.9	425.3	425.6	426.0	426.4	426.5	426.6	426.7	426.8	426.8
135°	448.1	448.3	448.7	449.1	449.5	449.9	450.1	450.3	450.5	450.7	450.9
137.5°	470.6	470.8	471.2	471.7	472.1	472.6	472.8	473.0	473.2	473.5	473.5
140°	485.4	485.6	485.8	486.1	486.4	486.6	486.9	487.2	487.5	487.8	488.0
142.5°	499.0	499.2	499.3	499.5	499.6	499.7	499.9	500.1	500.4	500.6	500.7
145°	518.4	518.6	518.6	518.6	518.6	518.6	518.7	518.8	518.9	519.0	519.1
147.5°	535.1	535.3	535.2	535.1	535.0	534.9	535.0	535.1	535.1	535.2	535.3
150°	545.8	545.9	545.8	545.7	545.6	545.5	545.5	545.5	545.5	545.5	545.6
152.5°	555.0	555.0	554.9	554.7	554.5	554.3	554.5	554.6	554.8	555.0	555.0
155°	567.4	567.3	567.0	566.7	566.4	566.1	566.5	566.9	567.3	567.7	567.8
157.5°	578.0	577.8	577.5	577.1	576.8	576.5	577.0	577.5	578.0	578.6	578.6
160°	583.7	583.5	583.4	583.3	583.2	583.1	583.7	584.3	584.9	585.5	585.5
162.5°	589.3	589.0	588.9	588.8	588.7	588.5	589.2	589.8	590.4	591.0	591.0
165°	596.1	595.9	595.9	595.9	595.9	595.9	596.7	597.5	598.3	599.2	599.1
167.5°	601.9	601.6	601.6	601.5	601.5	601.4	602.3	603.2	604.1	605.0	604.9
170°	604.9	604.6	604.7	604.8	604.9	605.0	605.8	606.6	607.4	608.3	608.2
172.5°	607.1	606.8	606.9	607.0	607.1	607.2	608.0	608.8	609.7	610.5	610.4
175°	609.5	609.3	609.4	609.5	609.6	609.7	610.6	611.5	612.4	613.3	613.1
177.5°	610.8	610.6	610.7	610.9	611.0	611.2	611.8	612.5	613.1	613.8	613.6
180°	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9



TEST NUMBER: P332775-840

CATALOG NUMBER: S124DIW-S795D470U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6
2.5°	1235.5	1234.7	1231.6	1231.2	1231.6	1234.7	1235.5	1236.4	1237.7	1241.9	1236.8
5°	1141.3	1138.6	1137.0	1143.0	1137.0	1138.6	1141.3	1144.5	1149.9	1150.4	1155.8
7.5°	1070.3	1068.1	1063.4	1062.0	1063.4	1068.1	1070.3	1072.3	1077.6	1082.3	1090.1
10°	1024.7	1022.6	1018.3	1017.2	1018.3	1022.6	1024.7	1030.2	1035.5	1041.4	1046.8
12.5°	980.9	976.6	975.7	976.8	975.7	976.6	980.9	988.1	1002.0	1001.9	1003.0
15°	922.7	920.6	914.6	916.3	914.6	920.6	922.7	929.7	936.1	944.2	952.2
17.5°	865.4	862.7	855.6	861.9	855.6	862.7	865.4	869.1	877.4	888.8	900.9
20°	829.3	825.0	821.2	820.6	821.2	825.0	829.3	833.0	842.1	851.8	860.9
22.5°	794.9	791.0	790.7	787.2	790.7	791.0	794.9	800.8	809.9	815.3	823.9
25°	751.9	748.2	747.1	744.4	747.1	748.2	751.9	756.2	762.1	766.4	776.1
27.5°	718.9	717.1	715.2	716.0	715.2	717.1	718.9	719.5	722.2	727.8	733.5
30°	698.7	698.2	697.1	697.1	697.1	698.2	698.7	697.1	699.8	702.5	706.8
32.5°	682.0	681.9	682.6	682.6	682.6	681.9	682.0	679.5	680.4	681.5	683.6
35°	658.4	660.0	661.2	659.5	661.2	660.0	658.4	656.3	654.7	651.0	652.1
37.5°	637.2	638.8	640.4	642.2	640.4	638.8	637.2	632.8	628.9	625.6	621.8
40°	620.9	624.6	625.7	628.4	625.7	624.6	620.9	616.0	611.8	607.9	603.7
42.5°	605.4	609.6	612.4	612.9	612.4	609.6	605.4	600.6	594.1	589.5	583.5
45°	581.7	585.9	589.8	589.8	589.8	585.9	581.7	573.6	566.6	559.7	553.7
47.5°	557.0	563.3	567.0	568.0	567.0	563.3	557.0	548.8	539.1	530.4	521.9
50°	540.3	547.9	551.6	554.3	551.6	547.9	540.3	531.2	521.0	510.2	500.0
52.5°	524.0	531.5	536.5	538.0	536.5	531.5	524.0	512.7	500.4	488.8	479.8
55°	495.7	506.4	512.4	514.5	512.4	506.4	495.7	483.4	471.6	457.1	444.1
57.5°	469.1	479.0	485.8	487.5	485.8	479.0	469.1	454.5	439.3	423.8	410.1
60°	448.5	459.2	467.8	469.4	467.8	459.2	448.5	433.9	417.9	402.8	385.7
62.5°	427.4	438.6	446.4	450.5	446.4	438.6	427.4	412.0	394.7	377.9	360.7
65°	391.0	402.2	409.8	411.4	409.8	402.2	391.0	376.0	357.7	340.0	325.5
67.5°	351.2	362.5	367.5	370.6	367.5	362.5	351.2	337.1	319.0	300.6	284.2
70°	323.4	332.4	337.8	340.5	337.8	332.4	323.4	308.3	293.3	274.5	256.7
72.5°	291.5	301.0	307.3	307.8	307.3	301.0	291.5	278.6	262.8	245.2	229.6
75°	242.8	251.4	254.6	254.6	254.6	251.4	242.8	230.5	217.5	203.6	187.9
77.5°	192.2	196.6	200.7	201.5	200.7	196.6	192.2	183.3	172.6	158.6	146.9
80°	159.6	162.2	165.4	165.4	165.4	162.2	159.6	151.5	141.3	129.5	120.3
82.5°	126.0	128.3	131.5	131.1	131.5	128.3	126.0	119.7	111.2	103.2	94.9
85°	76.2	81.1	80.6	79.5	80.6	81.1	76.2	77.4	69.3	63.9	56.4
87.5°	37.0	37.5	38.8	39.7	38.8	37.5	37.0	35.6	31.7	29.5	27.6
90°	13.1	13.3	13.5	13.7	13.5	13.3	13.1	12.9	12.5	11.9	11.3
92.5°	12.5	12.5	12.6	12.6	12.6	12.5	12.5	12.4	12.1	11.5	10.9
95°	12.9	13.0	13.1	13.2	13.1	13.0	12.9	12.8	12.5	11.9	11.3
97.5°	12.5	12.6	12.7	12.8	12.7	12.6	12.5	12.4	12.3	12.2	12.2
100°	12.5	12.6	12.7	12.8	12.7	12.6	12.5	12.4	13.2	14.9	16.7
102.5°	13.1	13.1	13.1	13.2	13.1	13.1	13.1	13.1	22.4	41.1	59.7
105°	141.4	137.7	134.1	130.5	134.1	137.7	141.4	145.1	146.4	145.5	144.6
107.5°	180.7	181.0	181.4	181.8	181.4	181.0	180.7	180.3	179.9	179.4	178.9
110°	203.2	203.5	203.8	204.1	203.8	203.5	203.2	202.9	202.7	202.5	202.3



TEST NUMBER: P332775-840

CATALOG NUMBER: S124DIW-S795D470U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	225.3	225.7	226.1	226.4	226.1	225.7	225.3	224.9	224.7	224.8	224.8
115°	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	258.9	258.7	258.5
117.5°	292.3	292.3	292.3	292.2	292.3	292.3	292.3	292.4	292.4	292.5	292.5
120°	313.7	313.5	313.3	313.1	313.3	313.5	313.7	313.9	313.9	313.7	313.5
122.5°	334.2	334.0	333.8	333.6	333.8	334.0	334.2	334.4	334.4	334.3	334.2
125°	364.0	364.1	364.2	364.3	364.2	364.1	364.0	363.9	363.7	363.3	363.0
127.5°	391.5	391.4	391.4	391.3	391.4	391.4	391.5	391.6	391.7	391.7	391.8
130°	409.6	409.6	409.6	409.6	409.6	409.6	409.6	409.6	409.6	409.5	409.4
132.5°	426.7	426.7	426.6	426.5	426.6	426.7	426.7	426.8	426.8	426.7	426.6
135°	451.1	451.3	451.5	451.7	451.5	451.3	451.1	450.9	450.7	450.5	450.3
137.5°	473.5	473.4	473.4	473.3	473.4	473.4	473.5	473.5	473.5	473.2	473.0
140°	488.1	488.2	488.3	488.4	488.3	488.2	488.1	488.0	487.8	487.5	487.2
142.5°	500.7	500.8	500.8	500.8	500.8	500.8	500.7	500.7	500.6	500.4	500.1
145°	519.3	519.5	519.7	519.9	519.7	519.5	519.3	519.1	519.0	518.9	518.8
147.5°	535.4	535.5	535.6	535.7	535.6	535.5	535.4	535.3	535.2	535.1	535.1
150°	545.7	545.8	545.9	546.0	545.9	545.8	545.7	545.6	545.5	545.5	545.5
152.5°	555.0	554.9	554.8	554.8	554.8	554.9	555.0	555.0	555.0	554.8	554.6
155°	567.5	567.2	566.9	566.6	566.9	567.2	567.5	567.8	567.7	567.3	566.9
157.5°	578.0	577.5	577.0	576.5	577.0	577.5	578.0	578.6	578.6	578.0	577.5
160°	584.9	584.3	583.7	583.1	583.7	584.3	584.9	585.5	585.5	584.9	584.3
162.5°	590.3	589.6	588.9	588.2	588.9	589.6	590.3	591.0	591.0	590.4	589.8
165°	598.1	597.2	596.3	595.4	596.3	597.2	598.1	599.1	599.2	598.3	597.5
167.5°	603.9	602.9	601.9	600.9	601.9	602.9	603.9	604.9	605.0	604.1	603.2
170°	607.1	606.1	605.1	604.1	605.1	606.1	607.1	608.2	608.3	607.4	606.6
172.5°	609.3	608.1	607.0	605.9	607.0	608.1	609.3	610.4	610.5	609.7	608.8
175°	611.9	610.7	609.5	608.2	609.5	610.7	611.9	613.1	613.3	612.4	611.5
177.5°	612.7	611.7	610.7	609.8	610.7	611.7	612.7	613.6	613.8	613.1	612.5
180°	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9



TEST NUMBER: P332775-840

CATALOG NUMBER: S124DIW-S795D470U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6
2.5°	1239.4	1241.1	1248.0	1254.5	1262.1	1267.8	1271.6	1275.9	1285.0	1292.2	1299.1
5°	1161.1	1163.9	1177.8	1187.5	1204.2	1218.6	1229.9	1242.2	1256.8	1276.7	1294.9
7.5°	1092.4	1102.3	1117.5	1133.3	1150.2	1169.2	1185.8	1204.4	1229.4	1256.7	1284.9
10°	1053.2	1064.5	1080.7	1098.8	1115.0	1137.0	1157.4	1179.4	1207.9	1241.2	1274.6
12.5°	1014.1	1032.7	1044.9	1066.6	1084.1	1102.2	1123.9	1152.8	1186.0	1221.0	1261.2
15°	965.1	975.3	999.0	1010.8	1035.5	1063.4	1084.9	1113.9	1146.1	1192.3	1237.5
17.5°	908.7	922.1	940.9	963.4	991.8	1013.6	1040.4	1070.2	1110.8	1156.7	1213.2
20°	871.7	882.9	906.1	930.8	960.9	983.9	1012.4	1041.4	1083.3	1132.2	1191.2
22.5°	838.6	849.5	873.8	896.9	926.0	954.3	984.0	1017.7	1057.9	1109.4	1169.7
25°	787.4	801.8	823.3	847.0	874.9	907.2	939.4	969.5	1012.4	1066.6	1131.1
27.5°	741.9	753.6	769.1	796.0	827.7	858.8	890.8	928.6	969.9	1027.2	1094.2
30°	712.7	723.5	739.0	763.8	793.2	826.6	859.9	896.4	939.4	996.3	1064.5
32.5°	689.5	697.7	711.6	733.7	760.6	795.7	828.5	866.4	911.4	967.6	1034.0
35°	655.2	662.3	667.6	688.5	712.7	745.0	778.2	818.5	862.0	915.2	981.8
37.5°	621.6	624.0	631.9	645.6	669.0	698.6	729.5	769.2	813.7	867.8	927.9
40°	601.0	602.1	606.9	619.8	640.3	668.1	698.2	737.4	779.8	830.9	890.5
42.5°	580.8	580.2	584.6	593.6	612.7	638.0	667.7	703.5	745.9	793.0	849.2
45°	548.9	548.9	547.9	555.3	570.9	595.6	620.4	654.7	690.1	736.4	783.7
47.5°	515.6	512.6	513.5	517.5	530.5	550.9	575.7	603.9	635.2	674.3	715.7
50°	494.1	489.8	488.2	492.5	504.3	522.0	545.6	570.4	600.0	634.3	669.7
52.5°	470.5	466.2	463.3	466.3	477.3	493.7	515.1	536.8	563.4	591.4	622.1
55°	433.9	429.1	427.5	428.6	436.7	449.5	467.8	487.7	507.6	530.7	552.1
57.5°	398.0	390.0	388.5	388.0	393.5	405.4	420.6	437.9	452.3	466.3	489.2
60°	374.4	364.7	361.4	360.9	365.3	374.9	388.9	406.1	416.3	425.9	445.8
62.5°	349.0	339.7	332.6	333.5	337.3	346.5	358.8	371.2	378.0	388.5	401.9
65°	309.9	298.1	292.8	291.1	293.3	300.7	310.4	318.5	326.0	330.3	343.2
67.5°	270.8	260.9	253.0	251.1	250.0	255.2	263.2	268.0	273.4	277.1	284.8
70°	243.3	234.7	225.0	221.8	221.3	225.6	233.1	233.6	241.2	242.8	250.9
72.5°	216.2	205.5	198.8	195.6	193.4	197.2	202.2	203.6	207.6	210.6	214.7
75°	174.0	165.9	159.6	154.7	153.1	155.2	155.2	157.9	160.6	162.2	167.0
77.5°	136.9	127.7	120.1	117.3	115.3	114.0	115.1	116.7	115.4	118.3	119.4
80°	111.2	101.5	95.6	94.5	91.3	88.7	88.1	89.7	87.6	88.7	91.8
82.5°	85.8	79.6	73.2	72.2	68.1	66.8	66.1	65.2	65.2	65.0	65.6
85°	51.0	47.3	42.9	40.3	38.7	36.0	36.0	34.9	33.8	32.7	33.3
87.5°	22.7	21.8	19.5	18.0	17.0	15.1	14.9	13.4	12.7	12.1	11.4
90°	10.7	10.1	9.3	8.5	7.7	6.8	5.9	4.7	3.6	2.5	1.4
92.5°	10.3	9.7	8.9	8.1	7.3	6.5	6.1	6.0	5.9	5.9	5.8
95°	10.7	10.1	10.0	9.9	9.8	9.7	11.3	14.8	18.3	21.7	25.1
97.5°	12.1	12.1	23.4	34.7	46.2	57.5	62.1	59.9	57.8	55.6	53.4
100°	18.4	20.1	34.1	48.2	62.2	76.2	82.4	80.6	78.8	76.9	75.0
102.5°	78.4	97.0	98.9	100.7	102.5	104.3	104.6	103.2	101.9	100.6	99.3
105°	143.7	142.8	142.3	141.8	141.3	140.8	140.2	139.6	139.0	138.4	137.7
107.5°	178.4	178.0	177.3	176.6	175.9	175.3	174.8	174.5	174.2	173.9	173.6
110°	202.1	201.9	201.3	200.7	200.0	199.3	198.9	198.6	198.3	198.0	197.7



TEST NUMBER: P332775-840

CATALOG NUMBER: S124DIW-S795D470U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	224.9	224.9	224.6	224.3	224.1	223.8	223.4	222.8	222.3	221.7	221.2
115°	258.3	258.1	258.2	258.3	258.4	258.5	258.4	258.1	257.8	257.5	257.2
117.5°	292.5	292.6	292.4	292.1	291.9	291.6	291.3	290.9	290.5	290.1	289.7
120°	313.3	313.1	313.2	313.3	313.4	313.5	313.3	312.9	312.5	312.0	311.6
122.5°	334.1	334.0	333.8	333.7	333.5	333.4	333.2	333.0	332.6	332.4	332.1
125°	362.7	362.4	362.6	362.8	363.0	363.2	363.1	362.7	362.3	361.9	361.5
127.5°	391.9	391.9	391.5	391.0	390.5	390.1	389.8	389.7	389.6	389.5	389.4
130°	409.3	409.2	408.9	408.6	408.3	408.0	407.8	407.7	407.6	407.4	407.3
132.5°	426.5	426.4	426.0	425.6	425.3	424.9	424.5	424.3	424.1	423.9	423.8
135°	450.1	449.9	449.5	449.1	448.7	448.3	448.1	448.2	448.3	448.4	448.5
137.5°	472.8	472.6	472.1	471.7	471.2	470.8	470.6	470.5	470.5	470.4	470.4
140°	486.9	486.6	486.4	486.1	485.8	485.6	485.4	485.2	485.0	484.8	484.6
142.5°	499.9	499.7	499.6	499.5	499.3	499.2	499.0	498.6	498.3	497.9	497.5
145°	518.7	518.6	518.6	518.6	518.6	518.6	518.4	518.1	517.8	517.5	517.2
147.5°	535.0	534.9	535.0	535.1	535.2	535.3	535.1	534.5	533.9	533.4	532.8
150°	545.5	545.5	545.6	545.7	545.8	545.9	545.8	545.4	545.0	544.6	544.2
152.5°	554.5	554.3	554.5	554.7	554.9	555.0	555.0	554.6	554.3	554.0	553.7
155°	566.5	566.1	566.4	566.7	567.0	567.3	567.4	567.3	567.2	567.1	567.0
157.5°	577.0	576.5	576.8	577.1	577.5	577.8	578.0	578.1	578.1	578.2	578.3
160°	583.7	583.1	583.2	583.3	583.4	583.5	583.7	584.0	584.3	584.6	584.9
162.5°	589.2	588.5	588.7	588.8	588.9	589.0	589.3	589.6	590.0	590.4	590.8
165°	596.7	595.9	595.9	595.9	595.9	595.9	596.1	596.6	597.1	597.6	598.1
167.5°	602.3	601.4	601.5	601.5	601.6	601.6	601.9	602.5	603.0	603.5	604.0
170°	605.8	605.0	604.9	604.8	604.7	604.6	604.9	605.5	606.1	606.7	607.3
172.5°	608.0	607.2	607.1	607.0	606.9	606.8	607.1	607.7	608.3	608.9	609.6
175°	610.6	609.7	609.6	609.5	609.4	609.3	609.5	610.1	610.7	611.3	611.9
177.5°	611.8	611.2	611.0	610.9	610.7	610.6	610.8	611.3	611.9	612.5	613.0
180°	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9



TEST NUMBER: P332775-840

CATALOG NUMBER: S124DIW-S795D470U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6
2.5°	1305.1	1309.4	1315.0	1324.4	1327.9	1332.2	1338.2	1337.8	1339.5	1345.9	1359.7
5°	1310.0	1326.6	1342.7	1362.0	1382.5	1395.8	1414.1	1425.4	1436.7	1451.2	1475.9
7.5°	1311.9	1338.3	1367.9	1401.8	1432.0	1466.8	1494.0	1519.5	1542.6	1573.3	1602.7
10°	1308.9	1344.3	1382.5	1425.4	1471.1	1509.7	1544.7	1584.4	1618.2	1655.3	1688.6
12.5°	1303.3	1346.0	1397.0	1445.2	1498.5	1555.7	1599.2	1639.4	1684.5	1727.1	1778.4
15°	1290.6	1349.2	1408.8	1472.2	1543.6	1609.6	1672.4	1724.5	1772.9	1836.8	1904.0
17.5°	1274.6	1337.7	1412.9	1489.6	1564.2	1639.7	1717.5	1795.8	1856.8	1936.2	1988.7
20°	1259.5	1332.5	1409.9	1501.2	1575.8	1669.8	1747.2	1822.9	1906.6	1985.6	2048.4
22.5°	1238.4	1318.4	1400.4	1491.3	1589.5	1683.5	1772.9	1855.1	1938.8	2024.7	2100.8
25°	1211.6	1284.1	1381.4	1484.5	1582.3	1684.3	1786.9	1890.0	1980.2	2071.0	2141.9
27.5°	1166.1	1257.7	1348.2	1454.6	1563.3	1678.7	1788.4	1896.3	1990.8	2065.5	2109.4
30°	1143.0	1222.4	1320.7	1427.5	1545.2	1669.3	1783.6	1889.5	1977.5	2037.2	2054.9
32.5°	1108.5	1190.6	1286.8	1397.5	1522.0	1649.5	1768.6	1868.5	1941.9	1973.2	1951.8
35°	1057.5	1131.7	1228.8	1342.2	1471.6	1607.5	1725.2	1809.5	1847.0	1817.5	1743.9
37.5°	996.3	1069.8	1167.4	1278.7	1412.6	1550.7	1657.1	1717.8	1705.4	1631.8	1522.2
40°	953.3	1022.1	1115.0	1235.3	1365.8	1504.4	1597.8	1630.6	1596.2	1491.0	1374.4
42.5°	905.6	972.7	1066.0	1182.0	1320.3	1448.0	1529.5	1532.2	1474.6	1348.8	1231.7
45°	833.0	897.0	985.0	1105.9	1233.7	1354.0	1407.7	1381.4	1275.1	1153.7	1036.0
47.5°	761.3	816.8	903.6	1018.3	1139.7	1241.0	1267.6	1220.2	1106.9	989.1	880.1
50°	708.9	764.8	846.5	956.0	1073.1	1160.6	1173.6	1110.6	999.6	880.8	795.5
52.5°	658.6	714.1	792.7	894.1	1001.4	1080.3	1080.8	1008.0	897.3	791.4	712.1
55°	584.9	634.8	705.7	796.5	892.1	953.8	938.9	863.6	767.5	675.7	606.3
57.5°	513.8	557.2	622.6	698.3	782.5	833.4	808.5	736.1	650.3	572.4	519.9
60°	467.8	509.2	565.0	636.4	707.3	747.1	723.5	657.9	579.0	516.1	470.5
62.5°	423.1	458.1	511.7	573.7	639.4	668.9	647.8	583.2	514.9	458.2	421.1
65°	359.8	388.3	431.3	484.4	532.3	557.4	539.8	479.6	427.5	386.7	357.2
67.5°	300.7	323.0	355.6	398.2	438.8	452.4	436.4	394.5	350.3	317.6	296.8
70°	259.9	280.9	308.3	341.0	376.5	391.0	374.9	341.5	305.6	275.5	255.1
72.5°	224.3	240.5	263.6	291.6	319.3	333.9	322.9	290.8	260.4	238.1	220.8
75°	170.8	184.8	200.9	220.8	242.3	251.9	242.3	220.3	199.2	182.6	170.3
77.5°	124.2	131.7	144.1	159.0	172.4	179.9	171.5	156.5	143.7	132.3	126.2
80°	94.5	99.9	108.5	120.3	129.5	136.4	131.1	118.7	108.5	101.0	98.3
82.5°	68.8	72.4	78.0	86.7	92.9	96.4	94.1	85.1	81.0	74.3	71.6
85°	33.8	36.0	39.8	42.4	47.8	48.4	48.9	45.1	41.4	39.8	37.6
87.5°	12.1	12.7	14.2	15.8	17.7	18.3	18.0	18.2	16.7	16.4	14.7
90°	2.5	3.6	4.7	5.9	6.8	7.7	8.5	9.3	10.1	10.7	11.3
92.5°	5.9	5.9	6.0	6.1	6.5	7.3	8.1	8.9	9.7	10.3	10.9
95°	21.7	18.3	14.8	11.3	9.7	9.8	9.9	10.0	10.1	10.7	11.3
97.5°	55.6	57.8	59.9	62.1	57.5	46.2	34.7	23.4	12.1	12.1	12.2
100°	76.9	78.8	80.6	82.4	76.2	62.2	48.2	34.1	20.1	18.4	16.7
102.5°	100.6	101.9	103.2	104.6	104.3	102.5	100.7	98.9	97.0	78.4	59.7
105°	138.4	139.0	139.6	140.2	140.8	141.3	141.8	142.3	142.8	143.7	144.6
107.5°	173.9	174.2	174.5	174.8	175.3	175.9	176.6	177.3	178.0	178.4	178.9
110°	198.0	198.3	198.6	198.9	199.3	200.0	200.7	201.3	201.9	202.1	202.3



TEST NUMBER: P332775-840

CATALOG NUMBER: S124DIW-S795D470U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	221.7	222.3	222.8	223.4	223.8	224.1	224.3	224.6	224.9	224.9	224.8
115°	257.5	257.8	258.1	258.4	258.5	258.4	258.3	258.2	258.1	258.3	258.5
117.5°	290.1	290.5	290.9	291.3	291.6	291.9	292.1	292.4	292.6	292.5	292.5
120°	312.0	312.5	312.9	313.3	313.5	313.4	313.3	313.2	313.1	313.3	313.5
122.5°	332.4	332.6	333.0	333.2	333.4	333.5	333.7	333.8	334.0	334.1	334.2
125°	361.9	362.3	362.7	363.1	363.2	363.0	362.8	362.6	362.4	362.7	363.0
127.5°	389.5	389.6	389.7	389.8	390.1	390.5	391.0	391.5	391.9	391.9	391.8
130°	407.4	407.6	407.7	407.8	408.0	408.3	408.6	408.9	409.2	409.3	409.4
132.5°	423.9	424.1	424.3	424.5	424.9	425.3	425.6	426.0	426.4	426.5	426.6
135°	448.4	448.3	448.2	448.1	448.3	448.7	449.1	449.5	449.9	450.1	450.3
137.5°	470.4	470.5	470.5	470.6	470.8	471.2	471.7	472.1	472.6	472.8	473.0
140°	484.8	485.0	485.2	485.4	485.6	485.8	486.1	486.4	486.6	486.9	487.2
142.5°	497.9	498.3	498.6	499.0	499.2	499.3	499.5	499.6	499.7	499.9	500.1
145°	517.5	517.8	518.1	518.4	518.6	518.6	518.6	518.6	518.6	518.7	518.8
147.5°	533.4	533.9	534.5	535.1	535.3	535.2	535.1	535.0	534.9	535.0	535.1
150°	544.6	545.0	545.4	545.8	545.9	545.8	545.7	545.6	545.5	545.5	545.5
152.5°	554.0	554.3	554.6	555.0	555.0	554.9	554.7	554.5	554.3	554.5	554.6
155°	567.1	567.2	567.3	567.4	567.3	567.0	566.7	566.4	566.1	566.5	566.9
157.5°	578.2	578.1	578.1	578.0	577.8	577.5	577.1	576.8	576.5	577.0	577.5
160°	584.6	584.3	584.0	583.7	583.5	583.4	583.3	583.2	583.1	583.7	584.3
162.5°	590.4	590.0	589.6	589.3	589.0	588.9	588.8	588.7	588.5	589.2	589.8
165°	597.6	597.1	596.6	596.1	595.9	595.9	595.9	595.9	595.9	596.7	597.5
167.5°	603.5	603.0	602.5	601.9	601.6	601.6	601.5	601.5	601.4	602.3	603.2
170°	606.7	606.1	605.5	604.9	604.6	604.7	604.8	604.9	605.0	605.8	606.6
172.5°	608.9	608.3	607.7	607.1	606.8	606.9	607.0	607.1	607.2	608.0	608.8
175°	611.3	610.7	610.1	609.5	609.3	609.4	609.5	609.6	609.7	610.6	611.5
177.5°	612.5	611.9	611.3	610.8	610.6	610.7	610.9	611.0	611.2	611.8	612.5
180°	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9



TEST NUMBER: P332775-840

CATALOG NUMBER: S124DIW-S795D470U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6
2.5°	1366.5	1367.5	1371.3	1374.3	1375.1	1379.5	1379.9
5°	1486.6	1495.8	1513.5	1515.1	1517.8	1531.8	1521.1
7.5°	1627.4	1650.5	1666.1	1679.7	1684.7	1690.7	1689.5
10°	1717.6	1752.0	1769.2	1796.5	1797.7	1804.6	1800.3
12.5°	1808.3	1848.3	1879.6	1884.6	1907.6	1911.2	1917.2
15°	1936.7	1979.1	2022.7	2038.2	2069.9	2077.5	2089.3
17.5°	2057.5	2100.8	2131.3	2171.6	2184.6	2202.0	2190.2
20°	2123.6	2170.9	2209.6	2241.3	2254.7	2264.3	2263.3
22.5°	2163.6	2211.3	2242.6	2266.6	2279.2	2283.3	2283.0
25°	2188.6	2216.0	2225.6	2234.8	2220.9	2216.0	2218.2
27.5°	2119.0	2111.9	2086.7	2053.6	2019.2	1992.0	1977.1
30°	2023.2	1981.4	1943.2	1876.5	1842.2	1821.8	1803.5
32.5°	1887.4	1821.1	1747.7	1686.7	1647.6	1617.3	1612.8
35°	1654.8	1554.9	1465.2	1390.5	1351.8	1319.1	1311.5
37.5°	1406.8	1303.0	1222.3	1156.6	1115.0	1091.9	1070.3
40°	1242.2	1153.2	1073.6	1017.7	986.1	969.5	956.0
42.5°	1115.5	1034.1	955.0	912.5	883.8	873.6	865.8
45°	940.4	864.7	809.9	777.7	761.0	743.9	735.8
47.5°	800.2	738.6	702.5	675.1	657.3	647.1	642.0
50°	720.7	670.2	638.0	617.1	601.0	592.9	588.7
52.5°	650.3	608.8	581.8	565.1	554.2	548.3	546.5
55°	560.2	528.5	511.3	496.9	488.8	483.4	481.2
57.5°	487.0	462.5	448.6	436.7	433.5	429.0	427.5
60°	438.8	420.0	408.2	400.1	397.5	392.0	393.1
62.5°	396.3	380.9	370.8	366.2	362.6	358.1	359.6
65°	335.2	323.9	318.5	314.2	309.9	307.2	309.3
67.5°	281.2	273.5	266.2	263.7	261.6	261.2	258.8
70°	246.0	239.5	233.1	231.5	231.5	229.3	228.8
72.5°	212.1	207.3	203.0	201.9	200.2	201.0	198.7
75°	163.8	160.1	158.4	156.8	156.3	156.3	154.7
77.5°	121.1	118.3	115.7	115.7	113.7	113.0	112.8
80°	91.8	90.8	88.7	88.7	87.6	88.1	87.1
82.5°	69.1	67.6	67.2	66.2	64.7	64.8	63.8
85°	37.1	35.4	34.9	33.3	32.2	33.3	32.2
87.5°	15.2	14.9	14.6	13.8	13.4	13.4	12.2
90°	11.9	12.5	12.9	13.1	13.3	13.5	13.7
92.5°	11.5	12.1	12.4	12.5	12.5	12.6	12.6
95°	11.9	12.5	12.8	12.9	13.0	13.1	13.2
97.5°	12.2	12.3	12.4	12.5	12.6	12.7	12.8
100°	14.9	13.2	12.4	12.5	12.6	12.7	12.8
102.5°	41.1	22.4	13.1	13.1	13.1	13.1	13.2
105°	145.5	146.4	145.1	141.4	137.7	134.1	130.5
107.5°	179.4	179.9	180.3	180.7	181.0	181.4	181.8
110°	202.5	202.7	202.9	203.2	203.5	203.8	204.1



TEST NUMBER: P332775-840

CATALOG NUMBER: S124DIW-S795D470U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	224.8	224.7	224.9	225.3	225.7	226.1	226.4
115°	258.7	258.9	259.0	259.0	259.0	259.0	259.0
117.5°	292.5	292.4	292.4	292.3	292.3	292.3	292.2
120°	313.7	313.9	313.9	313.7	313.5	313.3	313.1
122.5°	334.3	334.4	334.4	334.2	334.0	333.8	333.6
125°	363.3	363.7	363.9	364.0	364.1	364.2	364.3
127.5°	391.7	391.7	391.6	391.5	391.4	391.4	391.3
130°	409.5	409.6	409.6	409.6	409.6	409.6	409.6
132.5°	426.7	426.8	426.8	426.7	426.7	426.6	426.5
135°	450.5	450.7	450.9	451.1	451.3	451.5	451.7
137.5°	473.2	473.5	473.5	473.5	473.4	473.4	473.3
140°	487.5	487.8	488.0	488.1	488.2	488.3	488.4
142.5°	500.4	500.6	500.7	500.7	500.8	500.8	500.8
145°	518.9	519.0	519.1	519.3	519.5	519.7	519.9
147.5°	535.1	535.2	535.3	535.4	535.5	535.6	535.7
150°	545.5	545.5	545.6	545.7	545.8	545.9	546.0
152.5°	554.8	555.0	555.0	555.0	554.9	554.8	554.8
155°	567.3	567.7	567.8	567.5	567.2	566.9	566.6
157.5°	578.0	578.6	578.6	578.0	577.5	577.0	576.5
160°	584.9	585.5	585.5	584.9	584.3	583.7	583.1
162.5°	590.4	591.0	591.0	590.3	589.6	588.9	588.2
165°	598.3	599.2	599.1	598.1	597.2	596.3	595.4
167.5°	604.1	605.0	604.9	603.9	602.9	601.9	600.9
170°	607.4	608.3	608.2	607.1	606.1	605.1	604.1
172.5°	609.7	610.5	610.4	609.3	608.1	607.0	605.9
175°	612.4	613.3	613.1	611.9	610.7	609.5	608.2
177.5°	613.1	613.8	613.6	612.7	611.7	610.7	609.8
180°	611.9	611.9	611.9	611.9	611.9	611.9	611.9

(END OF REPORT)