

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332779-840

Luminaire Tested: **S124DIW-S795D470U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332779-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S795D470U840-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 470 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5334.6 lumens  
Efficiency: N/A  
Efficacy: 141.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 37.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332779-840

CATALOG NUMBER: S124DIW-S795D470U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332779-840

CATALOG NUMBER: S124DIW-S795D470U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	65
1	101	97	93	89	95	91	87	84	80	78	75	70	68	67	61	60	59	54
2	92	84	78	73	86	79	74	69	70	66	62	62	59	56	54	52	49	45
3	84	74	67	61	79	70	63	58	62	57	52	55	51	47	48	45	42	38
4	77	66	58	51	72	62	55	49	55	49	45	49	44	40	43	39	36	33
5	71	59	50	44	66	55	48	42	49	43	39	44	39	35	39	35	32	29
6	65	53	44	38	61	50	42	37	45	38	34	40	35	31	35	31	28	25
7	60	48	39	34	56	45	38	32	40	34	30	36	31	27	32	28	25	22
8	56	43	35	30	53	41	34	29	37	31	27	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	26	22	27	23	20	18
10	49	36	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10823	10823	10823
5°	10855	10724	10802
10°	10787	10637	10690
15°	10657	10486	10513
20°	10483	10299	10308
25°	10286	10085	10056
30°	10043	9833	9743
35°	9792	9570	9443
40°	9531	9271	9101
45°	9259	8977	8805
50°	8959	8715	8446
55°	8633	8376	8103
60°	8307	7995	7753
65°	7941	7633	7324
70°	7530	7152	6871
75°	6903	6569	6400
80°	6141	5890	5742
85°	5372	5169	5067



TEST NUMBER: P332779-840

CATALOG NUMBER: S124DIW-S795D470U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	126.2	2.4
10°-20°	355.7	6.7
20°-30°	523.5	9.8
30°-40°	608.6	11.4
40°-50°	608.7	11.4
50°-60°	532.4	10.0
60°-70°	395.4	7.4
70°-80°	224.6	4.2
80°-90°	66.6	1.2
90°-100°	20.9	0.4
100°-110°	133.4	2.5
110°-120°	255.3	4.8
120°-130°	324.0	6.1
130°-140°	346.7	6.5
140°-150°	324.2	6.1
150°-160°	261.4	4.9
160°-170°	168.6	3.2
170°-180°	58.1	1.1
0°-30°	1005.5	18.8
0°-40°	1614.1	30.3
0°-60°	2755.2	51.6
0°-90°	3441.8	64.5
90°-120°	409.6	7.7
90°-150°	1404.6	26.3
90°-180°	1893.0	35.5
0°-180°	5334.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1341	1341	1341	1341	1341	
5°	1340	1335	1323	1334	1333	127
15°	1275	1270	1255	1260	1258	359
25°	1155	1147	1132	1133	1129	531
35°	994	986	971	964	958	621
45°	811	803	786	775	771	625
55°	613	609	595	583	576	549
65°	416	410	400	389	383	411
75°	221	216	211	206	205	235
85°	58	58	56	56	55	64
90°	1	6	10	13	14	4
95°	25	10	10	13	13	32
105°	138	140	143	146	130	144
115°	257	258	258	259	259	253
125°	362	363	362	364	364	323
135°	448	448	450	451	452	345
145°	517	518	519	519	520	323
155°	567	567	566	568	567	261
165°	598	596	596	599	595	169
175°	612	609	610	613	608	58
180°	612	612	612	612	612	



TEST NUMBER: P332779-840

CATALOG NUMBER: S124DIW-S795D470U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6
2.5°	1344.0	1343.4	1342.8	1342.3	1341.7	1340.4	1338.3	1336.2	1334.0	1332.0	1333.8
5°	1339.5	1338.6	1337.6	1336.7	1335.6	1333.8	1331.2	1328.6	1326.0	1323.3	1326.0
7.5°	1327.1	1326.1	1325.1	1324.1	1323.2	1321.3	1318.4	1315.5	1312.5	1309.6	1311.7
10°	1315.9	1314.9	1313.9	1313.0	1312.0	1310.0	1306.9	1303.8	1300.7	1297.6	1299.5
12.5°	1301.2	1300.3	1299.3	1298.4	1297.5	1295.3	1292.0	1288.7	1285.5	1282.1	1284.2
15°	1275.1	1274.0	1273.1	1272.1	1271.2	1269.0	1265.4	1261.8	1258.2	1254.7	1256.1
17.5°	1243.4	1242.2	1241.0	1239.9	1238.7	1236.4	1233.0	1229.6	1226.2	1222.8	1223.8
20°	1220.2	1219.0	1217.9	1216.7	1215.5	1213.0	1209.5	1205.9	1202.3	1198.8	1199.5
22.5°	1195.4	1193.8	1192.1	1190.6	1189.0	1186.5	1182.9	1179.3	1175.7	1172.2	1173.5
25°	1154.7	1153.1	1151.3	1149.7	1148.0	1145.5	1142.2	1138.8	1135.5	1132.2	1132.4
27.5°	1108.3	1106.6	1104.9	1103.2	1101.5	1099.0	1095.9	1092.9	1089.7	1086.6	1086.0
30°	1077.4	1075.5	1073.6	1071.7	1069.8	1067.2	1064.1	1061.1	1057.9	1054.8	1053.9
32.5°	1044.7	1043.0	1041.3	1039.6	1037.8	1035.3	1032.1	1028.7	1025.5	1022.2	1021.1
35°	993.6	991.9	990.3	988.6	986.9	984.4	981.1	977.8	974.4	971.1	969.4
37.5°	939.7	938.2	936.6	935.1	933.5	931.0	927.5	923.8	920.3	916.7	914.8
40°	904.4	902.5	900.6	898.7	896.8	894.0	890.5	886.9	883.3	879.7	877.4
42.5°	866.7	865.5	864.3	863.2	862.0	859.5	855.6	851.6	847.6	843.6	840.9
45°	811.0	809.3	807.7	806.0	804.4	801.5	797.8	794.0	790.1	786.3	783.7
47.5°	752.8	751.6	750.5	749.3	748.2	745.9	742.4	738.8	735.3	731.7	728.7
50°	713.3	712.3	711.3	710.3	709.4	707.3	704.0	700.6	697.2	693.9	690.5
52.5°	674.6	673.5	672.3	671.2	669.9	667.6	664.1	660.6	657.0	653.5	650.6
55°	613.4	612.6	611.9	611.2	610.5	608.4	605.1	601.8	598.4	595.1	592.2
57.5°	554.9	554.1	553.3	552.5	551.7	549.6	546.3	543.0	539.8	536.4	533.7
60°	514.5	513.3	512.1	511.0	509.8	507.6	504.5	501.4	498.3	495.2	493.0
62.5°	475.0	474.0	473.0	472.0	471.0	468.9	465.5	462.2	459.0	455.7	453.7
65°	415.7	414.5	413.3	412.1	410.9	409.1	406.8	404.3	401.9	399.6	397.2
67.5°	356.0	354.9	353.8	352.6	351.6	349.9	347.6	345.3	343.1	340.7	338.4
70°	319.0	317.4	315.7	314.0	312.4	310.5	308.6	306.7	304.8	303.0	301.0
72.5°	279.5	277.8	276.2	274.5	272.8	271.2	269.7	268.1	266.6	265.1	263.6
75°	221.3	220.0	218.9	217.7	216.5	215.3	214.1	212.9	211.8	210.6	209.5
77.5°	165.6	165.1	164.6	164.1	163.5	162.8	161.7	160.7	159.6	158.5	158.2
80°	132.1	131.4	130.7	130.0	129.3	128.7	128.2	127.7	127.2	126.7	126.2
82.5°	99.5	99.2	98.8	98.5	98.2	98.0	97.9	97.8	97.7	97.6	97.3
85°	58.0	58.0	58.0	58.0	58.0	57.8	57.3	56.9	56.4	55.8	55.8
87.5°	22.6	22.6	22.7	22.7	22.7	22.7	22.7	22.7	22.6	22.6	22.7
90°	1.4	2.5	3.6	4.7	5.9	6.8	7.7	8.5	9.3	10.1	10.7
92.5°	5.8	5.9	5.9	6.0	6.1	6.5	7.3	8.1	8.9	9.7	10.3
95°	25.1	21.7	18.3	14.8	11.3	9.7	9.8	9.9	10.0	10.1	10.7
97.5°	53.4	55.6	57.8	59.9	62.1	57.5	46.2	34.7	23.4	12.1	12.1
100°	75.0	76.9	78.8	80.6	82.4	76.2	62.2	48.2	34.1	20.1	18.4
102.5°	99.3	100.6	101.9	103.2	104.6	104.3	102.5	100.7	98.9	97.0	78.4
105°	137.7	138.4	139.0	139.6	140.2	140.8	141.3	141.8	142.3	142.8	143.7
107.5°	173.6	173.9	174.2	174.5	174.8	175.3	175.9	176.6	177.3	178.0	178.4
110°	197.7	198.0	198.3	198.6	198.9	199.3	200.0	200.7	201.3	201.9	202.1



TEST NUMBER: P332779-840

CATALOG NUMBER: S124DIW-S795D470U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	221.2	221.7	222.3	222.8	223.4	223.8	224.1	224.3	224.6	224.9	224.9
115°	257.2	257.5	257.8	258.1	258.4	258.5	258.4	258.3	258.2	258.1	258.3
117.5°	289.7	290.1	290.5	290.9	291.3	291.6	291.9	292.1	292.4	292.6	292.5
120°	311.6	312.0	312.5	312.9	313.3	313.5	313.4	313.3	313.2	313.1	313.3
122.5°	332.1	332.4	332.6	333.0	333.2	333.4	333.5	333.7	333.8	334.0	334.1
125°	361.5	361.9	362.3	362.7	363.1	363.2	363.0	362.8	362.6	362.4	362.7
127.5°	389.4	389.5	389.6	389.7	389.8	390.1	390.5	391.0	391.5	391.9	391.9
130°	407.3	407.4	407.6	407.7	407.8	408.0	408.3	408.6	408.9	409.2	409.3
132.5°	423.8	423.9	424.1	424.3	424.5	424.9	425.3	425.6	426.0	426.4	426.5
135°	448.5	448.4	448.3	448.2	448.1	448.3	448.7	449.1	449.5	449.9	450.1
137.5°	470.4	470.4	470.5	470.5	470.6	470.8	471.2	471.7	472.1	472.6	472.8
140°	484.6	484.8	485.0	485.2	485.4	485.6	485.8	486.1	486.4	486.6	486.9
142.5°	497.5	497.9	498.3	498.6	499.0	499.2	499.3	499.5	499.6	499.7	499.9
145°	517.2	517.5	517.8	518.1	518.4	518.6	518.6	518.6	518.6	518.6	518.7
147.5°	532.8	533.4	533.9	534.5	535.1	535.3	535.2	535.1	535.0	534.9	535.0
150°	544.2	544.6	545.0	545.4	545.8	545.9	545.8	545.7	545.6	545.5	545.5
152.5°	553.7	554.0	554.3	554.6	555.0	555.0	554.9	554.7	554.5	554.3	554.5
155°	567.0	567.1	567.2	567.3	567.4	567.3	567.0	566.7	566.4	566.1	566.5
157.5°	578.3	578.2	578.1	578.1	578.0	577.8	577.5	577.1	576.8	576.5	577.0
160°	584.9	584.6	584.3	584.0	583.7	583.5	583.4	583.3	583.2	583.1	583.7
162.5°	590.8	590.4	590.0	589.6	589.3	589.0	588.9	588.8	588.7	588.5	589.2
165°	598.1	597.6	597.1	596.6	596.1	595.9	595.9	595.9	595.9	595.9	596.7
167.5°	604.0	603.5	603.0	602.5	601.9	601.6	601.6	601.5	601.5	601.4	602.3
170°	607.3	606.7	606.1	605.5	604.9	604.6	604.7	604.8	604.9	605.0	605.8
172.5°	609.6	608.9	608.3	607.7	607.1	606.8	606.9	607.0	607.1	607.2	608.0
175°	611.9	611.3	610.7	610.1	609.5	609.3	609.4	609.5	609.6	609.7	610.6
177.5°	613.0	612.5	611.9	611.3	610.8	610.6	610.7	610.9	611.0	611.2	611.8
180°	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9



TEST NUMBER: P332779-840

CATALOG NUMBER: S124DIW-S795D470U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6
2.5°	1335.7	1337.7	1339.6	1340.5	1340.3	1340.1	1339.9	1339.7
5°	1328.6	1331.2	1333.8	1334.9	1334.4	1334.0	1333.5	1333.0
7.5°	1313.8	1316.0	1318.0	1318.9	1318.7	1318.4	1318.1	1317.8
10°	1301.4	1303.3	1305.3	1306.0	1305.5	1304.9	1304.5	1304.0
12.5°	1286.4	1288.4	1290.5	1291.2	1290.6	1289.9	1289.2	1288.6
15°	1257.5	1258.9	1260.3	1260.7	1260.0	1259.3	1258.6	1257.9
17.5°	1224.7	1225.6	1226.5	1226.7	1226.2	1225.7	1225.3	1224.8
20°	1200.2	1200.9	1201.6	1201.7	1201.2	1200.8	1200.3	1199.8
22.5°	1174.7	1176.0	1177.3	1177.5	1176.6	1175.8	1174.9	1174.1
25°	1132.7	1132.9	1133.2	1132.8	1131.9	1130.8	1129.9	1128.9
27.5°	1085.5	1084.9	1084.3	1083.5	1082.3	1081.1	1079.8	1078.6
30°	1052.9	1052.0	1051.0	1050.0	1048.7	1047.5	1046.3	1045.2
32.5°	1019.9	1018.8	1017.6	1016.4	1015.2	1014.0	1012.8	1011.7
35°	967.8	966.0	964.3	962.9	961.7	960.6	959.4	958.2
37.5°	913.0	911.2	909.5	907.8	906.2	904.6	903.0	901.4
40°	874.9	872.6	870.2	868.4	867.2	866.1	864.8	863.6
42.5°	838.1	835.4	832.5	830.8	830.0	829.2	828.4	827.6
45°	781.0	778.4	775.8	774.2	773.4	772.6	771.9	771.2
47.5°	725.8	722.9	719.8	717.5	715.7	713.9	712.1	710.2
50°	687.2	683.9	680.5	678.1	676.7	675.3	673.9	672.5
52.5°	647.6	644.6	641.7	639.3	637.5	635.7	633.9	632.1
55°	589.4	586.5	583.6	581.5	580.1	578.7	577.1	575.7
57.5°	531.0	528.3	525.5	523.5	522.1	520.7	519.4	518.0
60°	490.9	488.8	486.6	484.9	483.7	482.5	481.3	480.2
62.5°	451.7	449.8	447.9	446.3	445.0	443.8	442.7	441.5
65°	394.9	392.4	390.0	388.3	387.1	385.9	384.7	383.4
67.5°	336.2	333.9	331.5	330.2	329.9	329.6	329.2	328.9
70°	299.1	297.2	295.3	294.0	293.3	292.6	291.9	291.1
72.5°	262.1	260.5	259.0	257.9	257.1	256.4	255.7	255.0
75°	208.6	207.6	206.7	206.1	205.9	205.6	205.4	205.2
77.5°	157.9	157.6	157.4	156.9	156.3	155.7	155.1	154.5
80°	125.8	125.3	124.8	124.5	124.2	124.0	123.8	123.5
82.5°	96.9	96.6	96.3	96.1	95.9	95.6	95.4	95.1
85°	55.8	55.8	55.8	55.7	55.5	55.2	55.0	54.7
87.5°	22.9	23.0	23.1	23.2	23.2	23.3	23.3	23.3
90°	11.3	11.9	12.5	12.9	13.1	13.3	13.5	13.7
92.5°	10.9	11.5	12.1	12.4	12.5	12.5	12.6	12.6
95°	11.3	11.9	12.5	12.8	12.9	13.0	13.1	13.2
97.5°	12.2	12.2	12.3	12.4	12.5	12.6	12.7	12.8
100°	16.7	14.9	13.2	12.4	12.5	12.6	12.7	12.8
102.5°	59.7	41.1	22.4	13.1	13.1	13.1	13.1	13.2
105°	144.6	145.5	146.4	145.1	141.4	137.7	134.1	130.5
107.5°	178.9	179.4	179.9	180.3	180.7	181.0	181.4	181.8
110°	202.3	202.5	202.7	202.9	203.2	203.5	203.8	204.1





TEST NUMBER: P332779-840

CATALOG NUMBER: S124DIW-S795D470U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	224.8	224.8	224.7	224.9	225.3	225.7	226.1	226.4
115°	258.5	258.7	258.9	259.0	259.0	259.0	259.0	259.0
117.5°	292.5	292.5	292.4	292.4	292.3	292.3	292.3	292.2
120°	313.5	313.7	313.9	313.9	313.7	313.5	313.3	313.1
122.5°	334.2	334.3	334.4	334.4	334.2	334.0	333.8	333.6
125°	363.0	363.3	363.7	363.9	364.0	364.1	364.2	364.3
127.5°	391.8	391.7	391.7	391.6	391.5	391.4	391.4	391.3
130°	409.4	409.5	409.6	409.6	409.6	409.6	409.6	409.6
132.5°	426.6	426.7	426.8	426.8	426.7	426.7	426.6	426.5
135°	450.3	450.5	450.7	450.9	451.1	451.3	451.5	451.7
137.5°	473.0	473.2	473.5	473.5	473.5	473.4	473.4	473.3
140°	487.2	487.5	487.8	488.0	488.1	488.2	488.3	488.4
142.5°	500.1	500.4	500.6	500.7	500.7	500.8	500.8	500.8
145°	518.8	518.9	519.0	519.1	519.3	519.5	519.7	519.9
147.5°	535.1	535.1	535.2	535.3	535.4	535.5	535.6	535.7
150°	545.5	545.5	545.5	545.6	545.7	545.8	545.9	546.0
152.5°	554.6	554.8	555.0	555.0	555.0	554.9	554.8	554.8
155°	566.9	567.3	567.7	567.8	567.5	567.2	566.9	566.6
157.5°	577.5	578.0	578.6	578.6	578.0	577.5	577.0	576.5
160°	584.3	584.9	585.5	585.5	584.9	584.3	583.7	583.1
162.5°	589.8	590.4	591.0	591.0	590.3	589.6	588.9	588.2
165°	597.5	598.3	599.2	599.1	598.1	597.2	596.3	595.4
167.5°	603.2	604.1	605.0	604.9	603.9	602.9	601.9	600.9
170°	606.6	607.4	608.3	608.2	607.1	606.1	605.1	604.1
172.5°	608.8	609.7	610.5	610.4	609.3	608.1	607.0	605.9
175°	611.5	612.4	613.3	613.1	611.9	610.7	609.5	608.2
177.5°	612.5	613.1	613.8	613.6	612.7	611.7	610.7	609.8
180°	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9

(END OF REPORT)