

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333375-927

Luminaire Tested: **S125DIW-S610D470U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333375-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S610D470U927-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3268.2 lumens
Efficiency: N/A
Efficacy: 108.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333375-927

CATALOG NUMBER: S125DIW-S610D470U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333375-927

CATALOG NUMBER: S125DIW-S610D470U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	100	96	92	88	93	90	86	83	78	76	73	68	66	64	58	57	55	51
2	91	83	77	72	85	78	73	68	68	64	61	59	56	53	51	49	47	43
3	83	73	66	60	77	69	62	57	60	55	51	53	49	45	45	42	40	36
4	76	65	57	51	71	61	54	48	54	48	43	47	42	39	40	37	34	31
5	70	58	50	44	65	55	47	41	48	42	37	42	37	34	36	33	30	27
6	64	52	44	38	60	49	42	36	43	37	33	38	33	29	33	29	26	24
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23	21
8	55	43	35	29	52	40	33	28	36	30	26	32	27	23	28	24	21	19
9	52	39	31	26	48	37	30	25	33	27	23	29	24	21	26	22	19	17
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4914	4914	4914
5°	4924	4877	4909
10°	4894	4844	4871
15°	4841	4785	4805
20°	4766	4704	4712
25°	4684	4606	4603
30°	4583	4502	4480
35°	4475	4389	4328
40°	4364	4268	4207
45°	4244	4156	4074
50°	4112	4022	3900
55°	3985	3869	3762
60°	3834	3716	3584
65°	3651	3533	3412
70°	3478	3320	3206
75°	3169	3064	2959
80°	2819	2775	2708
85°	2453	2497	2364



TEST NUMBER: P333375-927

CATALOG NUMBER: S125DIW-S610D470U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.7	2.2
10°-20°	202.6	6.2
20°-30°	299.2	9.2
30°-40°	349.1	10.7
40°-50°	350.6	10.7
50°-60°	307.8	9.4
60°-70°	229.3	7.0
70°-80°	131.1	4.0
80°-90°	39.2	1.2
90°-100°	30.9	0.9
100°-110°	91.2	2.8
110°-120°	154.6	4.7
120°-130°	203.4	6.2
130°-140°	227.9	7.0
140°-150°	223.4	6.8
150°-160°	187.6	5.7
160°-170°	124.7	3.8
170°-180°	43.6	1.3
0°-30°	573.6	17.5
0°-40°	922.7	28.2
0°-60°	1581.1	48.4
0°-90°	1980.7	60.6
90°-120°	276.7	8.5
90°-150°	931.5	28.5
90°-180°	1287.0	39.4
0°-180°	3268.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	761	761	761	761	761	
5°	760	758	752	757	757	72
15°	724	722	716	719	719	204
25°	657	654	646	648	646	302
35°	568	565	557	554	549	355
45°	465	462	455	448	446	358
55°	354	352	344	338	334	316
65°	239	237	231	226	223	237
75°	127	126	123	121	119	135
85°	33	34	34	33	32	37
90°	0	3	6	8	9	3
95°	23	24	28	30	31	25
105°	82	84	86	88	89	87
115°	155	156	157	157	156	153
125°	226	228	228	228	227	202
135°	294	296	296	296	295	226
145°	356	357	358	358	357	222
155°	407	407	408	409	407	187
165°	443	442	442	444	442	125
175°	460	459	459	461	458	44
180°	461	461	461	461	461	



TEST NUMBER: P333375-927

CATALOG NUMBER: S125DIW-S610D470U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	760.8	760.8	760.8	760.8	760.8	760.8	760.8	760.8	760.8	760.8	760.8
2.5°	762.7	762.4	762.1	761.8	761.4	760.7	759.7	758.6	757.6	756.5	757.6
5°	759.6	759.3	759.1	758.8	758.5	757.7	756.4	755.0	753.7	752.3	753.6
7.5°	752.6	752.3	752.1	751.8	751.5	750.7	749.2	747.7	746.2	744.8	745.9
10°	746.3	746.1	745.8	745.5	745.3	744.4	742.9	741.5	740.0	738.6	739.6
12.5°	738.6	738.2	737.7	737.2	736.7	735.8	734.4	733.1	731.7	730.3	731.2
15°	724.1	723.7	723.3	722.9	722.5	721.5	720.1	718.6	717.1	715.7	716.3
17.5°	707.3	706.8	706.2	705.6	705.0	703.9	702.4	700.8	699.3	697.8	698.6
20°	693.4	693.1	692.8	692.6	692.3	691.3	689.6	687.9	686.1	684.4	685.3
22.5°	679.4	678.9	678.4	677.9	677.5	676.4	674.8	673.2	671.5	669.9	670.5
25°	657.3	656.6	655.9	655.3	654.6	653.4	651.6	649.9	648.2	646.4	646.7
27.5°	631.4	631.0	630.6	630.2	629.8	628.7	626.9	625.1	623.3	621.5	621.5
30°	614.5	614.1	613.7	613.3	612.9	611.7	609.7	607.7	605.7	603.7	603.4
32.5°	596.2	595.6	595.0	594.4	593.7	592.6	590.8	589.0	587.2	585.4	584.9
35°	567.6	567.0	566.5	566.0	565.5	564.3	562.4	560.5	558.6	556.7	556.1
37.5°	537.8	537.2	536.5	535.8	535.2	533.9	532.2	530.4	528.6	526.9	525.9
40°	517.6	517.0	516.3	515.6	514.9	513.7	511.8	509.9	508.0	506.2	505.0
42.5°	496.0	495.4	494.8	494.2	493.7	492.5	490.6	488.8	486.9	485.0	483.9
45°	464.7	464.1	463.6	463.0	462.6	461.4	459.9	458.3	456.6	455.0	453.4
47.5°	430.9	430.9	431.0	431.0	431.0	430.1	428.2	426.3	424.4	422.4	420.8
50°	409.3	408.8	408.4	408.1	407.7	406.7	405.0	403.5	401.9	400.3	398.5
52.5°	387.1	386.8	386.6	386.3	386.0	384.9	383.3	381.5	379.9	378.1	376.6
55°	353.9	353.5	353.1	352.7	352.3	351.2	349.3	347.5	345.5	343.6	342.5
57.5°	318.9	318.7	318.5	318.2	318.1	317.1	315.5	313.9	312.4	310.9	309.3
60°	296.8	296.2	295.6	295.1	294.6	293.6	292.2	290.7	289.1	287.7	286.4
62.5°	273.6	273.2	272.7	272.4	271.9	271.1	269.8	268.5	267.3	266.0	264.6
65°	238.9	238.7	238.4	238.1	237.9	237.0	235.5	234.1	232.6	231.2	229.9
67.5°	205.3	204.8	204.2	203.7	203.1	202.3	201.2	200.1	199.0	197.9	196.9
70°	184.2	183.5	182.8	182.2	181.5	180.5	179.4	178.2	177.0	175.8	174.9
72.5°	161.1	160.6	160.2	159.7	159.2	158.6	157.9	157.1	156.3	155.5	154.6
75°	127.0	126.7	126.4	126.2	126.0	125.5	124.8	124.1	123.4	122.8	122.4
77.5°	95.6	95.5	95.4	95.2	95.1	94.9	94.5	94.2	93.8	93.4	93.2
80°	75.8	75.8	75.8	75.8	75.8	75.7	75.4	75.2	74.9	74.6	74.5
82.5°	58.5	58.3	58.1	57.8	57.7	57.5	57.4	57.4	57.4	57.3	57.0
85°	33.1	33.3	33.4	33.5	33.7	33.7	33.7	33.7	33.7	33.7	33.6
87.5°	13.1	13.2	13.3	13.5	13.5	13.6	13.6	13.6	13.6	13.7	13.8
90°	0.4	1.0	1.7	2.3	2.9	3.5	4.0	4.6	5.1	5.8	6.2
92.5°	8.7	9.1	9.6	10.1	10.5	11.0	11.7	12.4	13.1	13.8	14.3
95°	23.4	23.5	23.7	23.8	24.0	24.5	25.3	26.1	26.9	27.6	28.2
97.5°	38.7	38.8	38.9	39.0	39.1	39.6	40.7	41.8	42.9	44.0	44.5
100°	50.3	50.3	50.3	50.3	50.3	50.8	51.8	52.8	53.9	54.9	55.7
102.5°	62.6	62.9	63.3	63.6	63.9	64.3	64.9	65.4	65.9	66.4	67.2
105°	81.8	82.2	82.6	83.0	83.5	83.9	84.4	84.8	85.3	85.8	86.3
107.5°	103.1	103.5	103.9	104.3	104.7	105.1	105.4	105.8	106.2	106.5	106.8
110°	117.8	118.2	118.6	119.0	119.4	119.7	119.9	120.2	120.4	120.6	120.9



TEST NUMBER: P333375-927

CATALOG NUMBER: S125DIW-S610D470U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	132.7	132.9	133.1	133.3	133.6	133.8	134.1	134.4	134.7	135.0	135.1
115°	154.7	155.0	155.4	155.7	156.1	156.3	156.5	156.6	156.8	156.9	156.9
117.5°	176.9	177.0	177.1	177.3	177.4	177.6	177.8	177.8	178.0	178.2	178.2
120°	190.7	191.1	191.5	191.9	192.3	192.5	192.6	192.7	192.7	192.8	192.8
122.5°	205.6	205.7	205.9	206.0	206.1	206.4	206.5	206.8	207.0	207.2	207.1
125°	225.9	226.3	226.8	227.3	227.8	228.1	228.1	228.2	228.3	228.4	228.2
127.5°	247.4	247.6	248.0	248.2	248.5	248.7	248.7	248.8	248.9	249.1	249.0
130°	260.3	260.7	261.1	261.5	261.9	262.2	262.4	262.5	262.7	262.8	262.8
132.5°	273.2	273.9	274.6	275.2	275.8	276.2	276.2	276.1	276.1	276.0	275.9
135°	293.7	294.2	294.7	295.2	295.6	295.9	296.0	296.0	296.1	296.2	296.2
137.5°	312.9	313.4	313.9	314.3	314.8	315.1	315.3	315.4	315.6	315.8	315.9
140°	325.3	325.7	326.1	326.5	326.9	327.3	327.5	327.7	328.0	328.2	328.4
142.5°	337.6	337.9	338.3	338.7	339.0	339.3	339.6	339.9	340.2	340.6	340.6
145°	355.8	356.2	356.5	356.8	357.1	357.4	357.6	357.8	358.1	358.3	358.3
147.5°	372.6	372.8	373.0	373.1	373.4	373.5	373.7	373.9	374.1	374.3	374.5
150°	383.8	383.7	383.7	383.6	383.5	383.7	384.0	384.3	384.6	384.9	384.9
152.5°	393.0	393.2	393.2	393.3	393.5	393.6	393.7	393.9	394.0	394.1	394.3
155°	407.2	407.2	407.2	407.2	407.2	407.2	407.3	407.3	407.4	407.5	407.8
157.5°	419.8	419.6	419.5	419.3	419.1	419.1	419.1	419.2	419.3	419.4	419.7
160°	427.3	427.1	426.7	426.5	426.3	426.2	426.3	426.4	426.4	426.5	426.9
162.5°	433.9	433.7	433.6	433.3	433.2	433.1	433.1	433.1	433.2	433.2	433.6
165°	442.7	442.5	442.4	442.2	442.0	442.0	442.1	442.2	442.3	442.4	442.7
167.5°	450.2	449.9	449.6	449.2	448.9	448.8	448.8	448.8	448.8	448.8	449.2
170°	454.2	453.8	453.5	453.2	452.9	452.7	452.7	452.7	452.7	452.7	453.2
172.5°	457.1	456.8	456.5	456.1	455.8	455.7	455.7	455.7	455.7	455.7	456.1
175°	460.3	459.9	459.6	459.3	459.0	458.8	458.8	458.8	458.8	458.8	459.3
177.5°	461.9	461.7	461.4	461.2	460.9	460.7	460.7	460.7	460.6	460.5	460.9
180°	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4



TEST NUMBER: P333375-927

CATALOG NUMBER: S125DIW-S610D470U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	760.8	760.8	760.8	760.8	760.8	760.8	760.8	760.8
2.5°	758.6	759.7	760.7	761.2	761.1	761.0	760.9	760.8
5°	754.8	756.0	757.2	757.7	757.6	757.5	757.3	757.2
7.5°	747.1	748.3	749.5	750.0	749.9	749.7	749.6	749.5
10°	740.7	741.7	742.8	743.3	743.1	743.0	742.8	742.8
12.5°	732.1	732.9	733.7	734.2	734.1	734.1	734.1	734.0
15°	717.0	717.6	718.4	718.7	718.7	718.7	718.7	718.7
17.5°	699.5	700.3	701.2	701.2	700.5	699.9	699.3	698.5
20°	686.2	687.1	688.1	688.2	687.5	686.9	686.2	685.6
22.5°	671.1	671.8	672.4	672.5	672.0	671.5	671.1	670.7
25°	647.0	647.2	647.5	647.5	647.1	646.7	646.3	645.9
27.5°	621.6	621.7	621.7	621.5	621.2	620.8	620.4	620.0
30°	603.2	602.9	602.6	602.3	601.9	601.5	601.1	600.7
32.5°	584.5	583.9	583.4	582.9	582.2	581.5	580.7	580.0
35°	555.4	554.8	554.1	553.2	552.2	551.0	550.0	548.9
37.5°	524.9	523.9	522.9	522.1	521.5	520.9	520.3	519.7
40°	503.7	502.6	501.4	500.6	500.2	499.8	499.4	499.0
42.5°	482.8	481.7	480.6	479.7	479.1	478.6	477.9	477.3
45°	451.8	450.2	448.6	447.6	447.2	446.8	446.4	446.0
47.5°	419.1	417.5	415.9	414.6	413.7	412.7	411.8	410.8
50°	396.8	395.1	393.3	392.0	391.0	390.1	389.1	388.2
52.5°	375.0	373.5	372.0	370.7	369.7	368.6	367.6	366.5
55°	341.3	340.1	338.9	337.8	336.8	335.9	335.0	334.1
57.5°	307.7	306.2	304.6	303.6	303.1	302.5	302.1	301.6
60°	285.0	283.7	282.3	281.2	280.3	279.3	278.4	277.5
62.5°	263.2	261.7	260.2	259.2	258.5	257.7	257.0	256.3
65°	228.7	227.5	226.3	225.5	224.9	224.3	223.9	223.3
67.5°	195.9	194.9	193.8	193.1	192.8	192.5	192.2	191.9
70°	174.1	173.3	172.5	171.9	171.3	170.8	170.2	169.8
72.5°	153.7	152.8	151.9	151.1	150.6	150.1	149.6	149.0
75°	122.0	121.6	121.2	120.7	120.2	119.6	119.1	118.6
77.5°	92.9	92.7	92.4	92.1	91.7	91.4	91.0	90.6
80°	74.4	74.2	74.1	73.9	73.6	73.4	73.1	72.8
82.5°	56.8	56.6	56.3	56.2	56.2	56.1	56.0	56.0
85°	33.4	33.3	33.2	33.0	32.7	32.4	32.2	31.9
87.5°	13.9	13.9	14.0	13.9	13.8	13.6	13.5	13.3
90°	6.6	7.0	7.4	7.7	7.9	8.2	8.4	8.6
92.5°	14.8	15.4	15.9	16.2	16.4	16.6	16.8	17.0
95°	28.8	29.3	29.9	30.3	30.4	30.6	30.7	30.9
97.5°	45.1	45.6	46.1	46.4	46.5	46.7	46.7	46.8
100°	56.4	57.1	57.8	58.2	58.4	58.5	58.7	58.9
102.5°	68.0	68.8	69.6	70.0	70.3	70.5	70.7	71.0
105°	86.7	87.2	87.7	88.1	88.3	88.6	88.8	89.0
107.5°	107.0	107.3	107.5	107.7	107.7	107.6	107.6	107.6
110°	121.1	121.4	121.6	121.7	121.6	121.5	121.4	121.4



TEST NUMBER: P333375-927

CATALOG NUMBER: S125DIW-S610D470U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	135.2	135.3	135.5	135.5	135.3	135.1	135.0	134.8
115°	156.8	156.7	156.6	156.5	156.5	156.4	156.3	156.2
117.5°	178.3	178.3	178.4	178.3	178.0	177.7	177.3	177.0
120°	192.8	192.8	192.8	192.7	192.3	192.0	191.7	191.4
122.5°	207.1	207.0	206.9	206.8	206.5	206.3	206.0	205.7
125°	228.1	227.9	227.8	227.6	227.5	227.4	227.4	227.3
127.5°	248.9	248.8	248.7	248.6	248.4	248.3	248.1	248.0
130°	262.7	262.6	262.5	262.4	262.2	262.1	261.9	261.7
132.5°	275.8	275.8	275.7	275.6	275.4	275.1	274.9	274.6
135°	296.2	296.2	296.2	296.0	295.7	295.4	295.1	294.8
137.5°	316.0	316.1	316.2	316.1	315.7	315.3	314.8	314.4
140°	328.5	328.7	328.8	328.7	328.3	327.9	327.5	327.1
142.5°	340.7	340.8	340.9	340.7	340.3	339.9	339.5	339.1
145°	358.3	358.3	358.3	358.2	358.0	357.7	357.5	357.3
147.5°	374.6	374.9	375.0	374.9	374.3	373.8	373.2	372.7
150°	384.9	384.9	384.9	384.8	384.7	384.5	384.4	384.2
152.5°	394.5	394.7	394.8	394.8	394.5	394.3	394.0	393.6
155°	408.1	408.4	408.8	408.8	408.4	408.0	407.6	407.2
157.5°	420.0	420.3	420.6	420.6	420.0	419.5	419.0	418.4
160°	427.2	427.5	427.9	427.8	427.4	427.0	426.6	426.2
162.5°	434.0	434.3	434.7	434.7	434.2	433.7	433.2	432.8
165°	443.0	443.3	443.6	443.5	443.1	442.6	442.1	441.6
167.5°	449.7	450.2	450.7	450.7	450.1	449.6	449.2	448.7
170°	453.7	454.2	454.7	454.6	454.1	453.5	453.0	452.4
172.5°	456.6	457.1	457.6	457.6	457.0	456.5	456.1	455.6
175°	459.8	460.3	460.8	460.7	460.2	459.6	459.1	458.5
177.5°	461.3	461.7	462.1	462.0	461.6	461.1	460.7	460.3
180°	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4

(END OF REPORT)