

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333090-840

Luminaire Tested: **S124RDIW-S1020D1340U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333090-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1020D1340U840-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8916.3 lumens
Efficiency: N/A
Efficacy: 127.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333090-840

CATALOG NUMBER: S124RDIW-S1020D1340U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333090-840

CATALOG NUMBER: S124RDIW-S1020D1340U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47					47			
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	48	47	46					40				
2	89	82	76	71	82	75	70	66	63	60	56	52	50	47	42	41	39					34				
3	81	72	65	59	74	67	60	55	56	52	48	47	43	40	38	35	33					29				
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29					25				
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	31	28	25					22				
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	22					19				
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	25	22	20					17				
8	54	42	34	29	50	39	32	28	34	28	24	28	24	21	23	20	18					16				
9	50	38	31	26	46	36	29	25	31	25	22	26	22	19	22	19	16					14				
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15					13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14721	14721	14721
5°	14755	14574	14665
10°	14662	14399	14399
15°	14493	14097	13992
20°	14262	13698	13447
25°	13967	13233	12897
30°	13679	12743	12209
35°	13361	12232	11517
40°	12978	11653	10771
45°	12625	11079	10011
50°	12223	10417	9207
55°	11792	9728	8332
60°	11317	8972	7440
65°	10883	8029	6562
70°	10249	6987	5570
75°	9451	5792	4529
80°	8243	4412	4156
85°	6984	4011	3751



TEST NUMBER: P333090-840

CATALOG NUMBER: S124RDIW-S1020D1340U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.3	1.9
10°-20°	477.7	5.4
20°-30°	689.8	7.7
30°-40°	781.8	8.8
40°-50°	755.0	8.5
50°-60°	627.8	7.0
60°-70°	433.5	4.9
70°-80°	219.7	2.5
80°-90°	61.4	0.7
90°-100°	111.7	1.3
100°-110°	330.9	3.7
110°-120°	561.6	6.3
120°-130°	740.5	8.3
130°-140°	831.6	9.3
140°-150°	817.2	9.2
150°-160°	687.3	7.7
160°-170°	457.3	5.1
170°-180°	160.1	1.8
0°-30°	1338.7	15.0
0°-40°	2120.6	23.8
0°-60°	3503.4	39.3
0°-90°	4218.1	47.3
90°-120°	1004.2	11.3
90°-150°	3393.5	38.1
90°-180°	4698.0	52.7
0°-180°	8916.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1824	1824	1824	1824	1824	
5°	1821	1814	1798	1811	1810	173
15°	1734	1720	1687	1683	1674	488
25°	1568	1541	1486	1462	1448	722
35°	1356	1310	1241	1195	1169	847
45°	1106	1052	970	904	877	852
55°	838	780	691	621	592	749
65°	570	508	420	363	344	562
75°	303	251	186	155	145	320
85°	75	49	43	41	40	85
90°	4	18	29	36	39	9
95°	79	90	100	103	104	87
105°	305	307	312	316	320	324
115°	571	571	568	567	566	563
125°	832	832	830	828	825	741
135°	1073	1080	1080	1078	1074	830
145°	1303	1308	1310	1308	1304	815
155°	1493	1493	1492	1496	1492	687
165°	1625	1621	1619	1626	1621	458
175°	1691	1685	1683	1691	1683	160
180°	1693	1693	1693	1693	1693	



TEST NUMBER: P333090-840

CATALOG NUMBER: S124RDIW-S1020D1340U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5
2.5°	1828.0	1826.9	1825.9	1825.0	1824.0	1822.1	1819.4	1816.6	1813.9	1811.2	1813.9
5°	1820.7	1819.5	1818.3	1816.9	1815.7	1813.2	1809.6	1805.8	1802.1	1798.4	1801.5
7.5°	1804.2	1802.9	1801.6	1800.3	1799.0	1795.9	1791.1	1786.2	1781.4	1776.6	1778.6
10°	1788.6	1787.1	1785.4	1783.9	1782.4	1778.8	1773.2	1767.7	1762.0	1756.5	1757.7
12.5°	1768.5	1766.7	1764.8	1763.1	1761.3	1757.1	1750.5	1743.9	1737.4	1730.8	1731.5
15°	1734.1	1731.3	1728.6	1725.8	1722.9	1717.7	1709.9	1702.1	1694.5	1686.7	1686.1
17.5°	1692.5	1688.5	1684.5	1680.4	1676.4	1669.7	1660.4	1651.1	1641.8	1632.4	1630.7
20°	1660.1	1656.1	1652.0	1648.0	1644.0	1636.7	1626.2	1615.6	1605.1	1594.5	1592.1
22.5°	1624.4	1619.8	1615.3	1610.8	1606.3	1598.3	1587.1	1575.8	1564.5	1553.2	1549.4
25°	1568.0	1562.4	1556.8	1551.3	1545.6	1536.5	1523.8	1511.1	1498.3	1485.6	1480.4
27.5°	1508.7	1501.8	1494.8	1487.7	1480.8	1470.5	1456.8	1443.3	1429.7	1416.0	1409.6
30°	1467.4	1459.7	1452.0	1444.2	1436.4	1425.2	1410.7	1396.0	1381.5	1367.0	1359.2
32.5°	1423.9	1415.1	1406.3	1397.7	1388.9	1377.0	1361.9	1346.9	1331.7	1316.7	1307.7
35°	1355.7	1345.8	1335.8	1326.0	1316.1	1303.3	1287.8	1272.3	1256.8	1241.2	1230.7
37.5°	1282.8	1272.6	1262.4	1252.1	1241.9	1228.2	1211.0	1193.9	1176.6	1159.4	1147.6
40°	1231.5	1221.2	1211.0	1200.7	1190.5	1176.6	1158.9	1141.1	1123.5	1105.8	1092.8
42.5°	1182.3	1171.6	1160.8	1150.1	1139.4	1124.8	1106.4	1087.9	1069.5	1051.1	1037.8
45°	1105.8	1094.4	1082.9	1071.4	1059.9	1044.8	1026.2	1007.6	989.0	970.4	955.2
47.5°	1026.8	1014.9	1003.1	991.3	979.4	963.8	944.4	925.0	905.6	886.4	870.6
50°	973.2	961.1	949.0	936.9	924.7	908.8	889.0	869.1	849.2	829.4	813.9
52.5°	918.5	906.6	894.7	882.9	871.0	855.0	834.6	814.3	793.9	773.6	757.8
55°	837.8	825.4	812.9	800.5	788.1	771.8	751.6	731.4	711.3	691.2	675.0
57.5°	757.9	745.0	732.1	719.1	706.3	689.8	670.0	650.2	630.3	610.5	594.1
60°	700.9	688.5	676.1	663.7	651.3	635.1	615.3	595.4	575.5	555.7	539.6
62.5°	649.5	636.6	623.7	610.8	597.9	581.3	560.9	540.6	520.2	499.9	484.9
65°	569.7	556.3	543.0	529.7	516.3	499.7	479.9	460.0	440.1	420.3	407.0
67.5°	486.8	473.9	461.2	448.4	435.6	420.0	401.5	383.1	364.7	346.3	334.8
70°	434.2	421.2	408.2	395.2	382.1	366.8	349.1	331.3	313.7	296.0	285.8
72.5°	378.4	366.6	354.8	343.1	331.2	317.0	300.3	283.6	266.9	250.2	241.5
75°	303.0	291.5	280.0	268.5	257.1	244.0	229.4	214.9	200.3	185.7	178.5
77.5°	226.5	216.7	207.0	197.2	187.5	176.7	164.9	153.2	141.4	129.6	125.4
80°	177.3	168.3	159.4	150.4	141.4	132.2	122.9	113.6	104.2	94.9	94.0
82.5°	134.9	126.6	118.4	110.1	101.9	95.0	89.8	84.4	79.1	73.7	73.0
85°	75.4	69.2	63.0	56.8	50.6	47.0	46.0	45.1	44.2	43.3	42.6
87.5°	26.5	25.1	23.8	22.4	21.1	20.5	20.7	21.0	21.2	21.4	21.5
90°	3.9	7.2	10.3	13.5	16.8	19.5	21.8	24.1	26.5	28.8	30.6
92.5°	28.1	31.7	35.3	39.0	42.7	45.3	47.0	48.6	50.2	51.9	52.9
95°	78.6	81.2	83.8	86.4	89.1	91.4	93.4	95.4	97.5	99.6	100.4
97.5°	137.2	139.4	141.5	143.5	145.6	147.8	150.3	152.7	155.0	157.4	158.4
100°	183.4	184.5	185.7	186.8	188.0	189.9	192.5	195.1	197.7	200.4	201.0
102.5°	231.6	232.1	232.5	233.0	233.4	234.8	237.2	239.6	242.0	244.4	245.2
105°	305.2	305.5	305.8	306.0	306.3	307.0	308.2	309.4	310.5	311.7	312.6
107.5°	382.4	382.7	383.1	383.4	383.8	384.1	384.3	384.5	384.7	384.8	385.6
110°	434.8	435.4	436.0	436.6	437.2	437.3	437.0	436.7	436.5	436.2	435.6



TEST NUMBER: P333090-840

CATALOG NUMBER: S124RDIW-S1020D1340U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	489.3	489.4	489.5	489.7	489.8	489.6	489.1	488.5	488.0	487.5	487.4
115°	571.0	571.0	571.0	571.0	571.0	570.8	570.2	569.6	569.0	568.4	568.2
117.5°	648.0	648.2	648.5	648.7	648.9	648.8	648.4	648.0	647.6	647.2	646.2
120°	699.3	700.5	701.7	702.9	704.0	704.2	703.3	702.5	701.6	700.6	699.2
122.5°	752.8	753.3	753.8	754.2	754.7	754.7	754.3	753.9	753.5	753.1	752.0
125°	831.6	831.6	831.6	831.6	831.6	831.5	831.2	830.9	830.6	830.3	829.7
127.5°	903.1	904.0	904.9	905.7	906.7	906.9	906.4	905.9	905.4	904.9	904.4
130°	953.4	954.3	955.2	956.0	956.9	957.4	957.4	957.4	957.4	957.4	956.7
132.5°	1004.8	1005.4	1006.0	1006.7	1007.3	1007.5	1007.3	1007.0	1006.8	1006.6	1006.0
135°	1072.6	1074.4	1076.1	1077.8	1079.6	1080.5	1080.5	1080.5	1080.5	1080.5	1079.9
137.5°	1146.5	1147.3	1148.1	1148.9	1149.7	1150.4	1150.8	1151.3	1151.8	1152.3	1151.4
140°	1195.8	1196.3	1196.9	1197.5	1198.1	1198.3	1198.3	1198.3	1198.3	1198.3	1198.1
142.5°	1240.8	1241.3	1241.9	1242.5	1243.1	1243.2	1243.0	1242.8	1242.6	1242.3	1242.3
145°	1303.1	1304.3	1305.5	1306.7	1307.8	1308.5	1308.8	1309.1	1309.4	1309.7	1309.4
147.5°	1364.9	1366.3	1367.8	1369.2	1370.5	1371.1	1370.9	1370.7	1370.4	1370.2	1370.0
150°	1402.7	1403.8	1405.0	1406.1	1407.3	1407.9	1407.9	1407.9	1407.9	1407.9	1407.9
152.5°	1438.2	1439.0	1439.7	1440.4	1441.1	1441.6	1441.8	1442.0	1442.3	1442.5	1443.2
155°	1493.0	1493.0	1493.0	1493.0	1493.0	1492.9	1492.6	1492.3	1492.0	1491.8	1492.9
157.5°	1539.1	1538.6	1538.1	1537.5	1537.0	1536.7	1536.7	1536.6	1536.6	1536.5	1537.4
160°	1566.4	1566.1	1565.8	1565.5	1565.2	1564.9	1564.6	1564.4	1564.1	1563.8	1564.6
162.5°	1591.5	1590.7	1590.0	1589.2	1588.5	1588.0	1587.7	1587.4	1587.1	1586.8	1588.4
165°	1625.3	1624.5	1623.6	1622.7	1621.8	1621.1	1620.5	1619.9	1619.3	1618.7	1620.5
167.5°	1651.2	1650.0	1648.8	1647.6	1646.4	1645.8	1645.9	1645.9	1646.0	1646.0	1647.8
170°	1665.9	1664.5	1663.0	1661.5	1660.1	1659.5	1659.8	1660.1	1660.4	1660.6	1662.4
172.5°	1676.4	1675.2	1674.0	1672.7	1671.5	1670.9	1671.0	1671.0	1671.1	1671.1	1673.1
175°	1690.8	1689.3	1687.9	1686.5	1685.0	1684.1	1683.8	1683.5	1683.2	1682.9	1685.0
177.5°	1695.5	1694.4	1693.1	1692.0	1690.8	1690.3	1690.3	1690.3	1690.3	1690.3	1691.9
180°	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4



TEST NUMBER: P333090-840

CATALOG NUMBER: S124RDIW-S1020D1340U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5
2.5°	1816.6	1819.4	1822.1	1823.4	1823.1	1822.9	1822.6	1822.4
5°	1804.5	1807.7	1810.8	1812.0	1811.4	1810.8	1810.2	1809.6
7.5°	1780.6	1782.5	1784.5	1785.0	1784.0	1783.0	1782.0	1781.0
10°	1759.0	1760.2	1761.4	1761.4	1760.2	1759.0	1757.7	1756.5
12.5°	1732.2	1733.0	1733.7	1733.2	1731.5	1729.8	1728.1	1726.4
15°	1685.5	1684.8	1684.2	1682.7	1680.6	1678.4	1676.3	1674.1
17.5°	1629.0	1627.3	1625.6	1623.1	1619.7	1616.5	1613.2	1609.8
20°	1589.5	1587.1	1584.6	1581.3	1577.3	1573.3	1569.2	1565.2
22.5°	1545.7	1542.0	1538.3	1534.8	1531.5	1528.2	1524.9	1521.7
25°	1475.0	1469.8	1464.5	1460.3	1457.2	1454.1	1451.0	1447.9
27.5°	1403.0	1396.5	1390.0	1384.5	1380.1	1375.5	1371.1	1366.7
30°	1351.4	1343.6	1335.8	1329.5	1324.5	1319.6	1314.6	1309.7
32.5°	1298.7	1289.7	1280.7	1273.8	1269.1	1264.4	1259.7	1255.0
35°	1220.1	1209.6	1199.0	1191.0	1185.4	1179.8	1174.3	1168.6
37.5°	1135.9	1124.1	1112.3	1103.6	1098.0	1092.4	1086.8	1081.3
40°	1079.7	1066.7	1053.7	1044.4	1038.8	1033.2	1027.6	1022.1
42.5°	1024.5	1011.3	997.9	988.5	982.6	976.7	970.9	965.1
45°	940.0	924.7	909.6	899.2	893.6	888.0	882.4	876.9
47.5°	854.9	839.1	823.2	812.3	806.2	800.0	793.9	787.8
50°	798.3	782.8	767.3	756.6	750.7	744.8	738.9	733.1
52.5°	741.9	726.2	710.4	699.5	693.4	687.2	681.1	675.0
55°	658.8	642.8	626.6	615.6	609.7	603.8	597.9	592.0
57.5°	577.6	561.3	544.9	534.5	530.0	525.5	521.1	516.6
60°	523.4	507.3	491.2	480.6	475.6	470.7	465.7	460.8
62.5°	470.1	455.1	440.3	430.8	426.9	422.9	418.9	415.0
65°	393.5	380.2	366.9	358.4	354.7	350.9	347.2	343.5
67.5°	323.3	311.8	300.3	292.6	288.4	284.4	280.2	276.2
70°	275.5	265.3	255.1	248.3	245.3	242.2	239.0	236.0
72.5°	232.7	224.0	215.2	209.4	206.5	203.7	200.9	198.0
75°	171.5	164.3	157.1	152.7	150.8	149.0	147.0	145.2
77.5°	121.3	117.1	112.9	110.6	110.0	109.5	108.9	108.4
80°	93.1	92.2	91.2	90.6	90.3	90.0	89.7	89.4
82.5°	72.3	71.7	71.0	70.5	70.2	69.9	69.6	69.3
85°	42.0	41.4	40.8	40.5	40.5	40.5	40.5	40.5
87.5°	21.6	21.7	21.8	22.0	22.4	22.7	23.1	23.5
90°	32.3	34.0	35.7	37.0	37.6	38.2	38.7	39.3
92.5°	53.9	55.0	56.0	56.8	57.1	57.5	57.8	58.2
95°	101.3	102.2	103.0	103.5	103.5	103.5	103.5	103.5
97.5°	159.6	160.6	161.6	162.2	162.2	162.2	162.2	162.2
100°	201.6	202.2	202.7	203.0	203.0	203.0	203.0	203.0
102.5°	246.0	246.8	247.6	248.1	248.4	248.6	248.8	249.1
105°	313.5	314.4	315.2	316.1	316.9	317.8	318.7	319.5
107.5°	386.4	387.2	388.1	388.4	388.4	388.3	388.3	388.2
110°	434.9	434.3	433.8	433.9	434.8	435.7	436.6	437.5



TEST NUMBER: P333090-840

CATALOG NUMBER: S124RDIW-S1020D1340U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	487.3	487.2	487.0	487.1	487.2	487.4	487.6	487.8
115°	567.8	567.5	567.2	566.9	566.6	566.3	566.0	565.8
117.5°	645.3	644.3	643.3	642.5	641.9	641.4	640.8	640.2
120°	697.8	696.3	694.9	694.4	695.0	695.6	696.2	696.7
122.5°	751.0	750.1	749.1	748.1	747.0	746.0	745.0	743.9
125°	829.2	828.6	828.0	827.4	826.9	826.3	825.7	825.1
127.5°	903.8	903.2	902.6	902.1	901.7	901.2	900.7	900.3
130°	956.2	955.6	955.0	954.2	953.0	951.8	950.7	949.5
132.5°	1005.4	1004.9	1004.3	1003.8	1003.3	1002.8	1002.4	1001.9
135°	1079.3	1078.7	1078.1	1077.4	1076.5	1075.7	1074.8	1073.9
137.5°	1150.7	1150.0	1149.2	1148.9	1149.1	1149.3	1149.4	1149.6
140°	1197.8	1197.5	1197.2	1196.9	1196.6	1196.3	1196.0	1195.8
142.5°	1242.2	1242.2	1242.1	1242.0	1242.0	1241.9	1241.9	1241.8
145°	1309.1	1308.8	1308.5	1308.0	1307.1	1306.2	1305.4	1304.4
147.5°	1369.7	1369.5	1369.3	1369.0	1368.7	1368.4	1368.2	1367.9
150°	1407.9	1407.9	1407.9	1407.8	1407.4	1407.1	1406.8	1406.6
152.5°	1443.9	1444.6	1445.3	1445.2	1444.5	1443.7	1443.0	1442.2
155°	1494.1	1495.2	1496.4	1496.4	1495.2	1494.1	1492.9	1491.8
157.5°	1538.2	1539.1	1540.0	1539.9	1538.9	1537.9	1537.0	1536.0
160°	1565.5	1566.4	1567.2	1566.9	1565.5	1564.1	1562.6	1561.2
162.5°	1589.9	1591.5	1593.1	1593.2	1591.6	1590.2	1588.8	1587.3
165°	1622.2	1624.0	1625.8	1626.1	1624.9	1623.7	1622.6	1621.3
167.5°	1649.5	1651.2	1652.9	1652.9	1651.1	1649.3	1647.6	1645.8
170°	1664.2	1665.9	1667.7	1667.5	1665.5	1663.4	1661.4	1659.4
172.5°	1675.1	1677.1	1679.1	1679.0	1677.0	1675.0	1672.9	1670.9
175°	1687.0	1689.0	1691.1	1691.1	1689.0	1687.0	1685.0	1682.9
177.5°	1693.5	1695.2	1696.8	1696.7	1694.9	1692.9	1691.1	1689.2
180°	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4

(END OF REPORT)