

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333422-927

Luminaire Tested: **S125DIW-S850D1340U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333422-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S850D1340U927-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6957.9 lumens
Efficiency: N/A
Efficacy: 113.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333422-927

CATALOG NUMBER: S125DIW-S850D1340U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333422-927

CATALOG NUMBER: S125DIW-S850D1340U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	91	87	84	86	83	80	77	68	65	63	53	52	51	41	40	39	33
2	87	79	73	68	79	72	67	63	59	55	52	47	44	42	36	34	33	27
3	79	70	63	57	72	64	57	52	52	48	44	41	38	36	32	29	28	23
4	72	62	54	48	65	56	50	44	46	41	37	37	33	30	28	26	24	20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21	17
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18	15
7	56	44	36	31	51	41	34	29	34	28	24	27	23	20	21	18	16	13
8	52	40	32	27	47	37	30	25	31	25	22	25	21	18	19	16	14	12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11
10	45	33	26	22	41	31	24	20	26	21	17	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6716	6716	6716
5°	6731	6667	6710
10°	6690	6620	6658
15°	6618	6540	6568
20°	6514	6429	6441
25°	6402	6297	6291
30°	6264	6154	6123
35°	6117	6000	5916
40°	5966	5833	5751
45°	5802	5681	5569
50°	5621	5497	5332
55°	5447	5290	5141
60°	5239	5079	4899
65°	4991	4828	4664
70°	4755	4538	4381
75°	4332	4190	4045
80°	3857	3794	3704
85°	3349	3416	3231



TEST NUMBER: P333422-927

CATALOG NUMBER: S125DIW-S850D1340U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.1	1.4
10°-20°	277.0	4.0
20°-30°	409.0	5.9
30°-40°	477.2	6.9
40°-50°	479.3	6.9
50°-60°	420.7	6.0
60°-70°	313.5	4.5
70°-80°	179.3	2.6
80°-90°	55.0	0.8
90°-100°	50.3	0.7
100°-110°	309.9	4.5
110°-120°	562.0	8.1
120°-130°	721.3	10.4
130°-140°	775.8	11.1
140°-150°	728.2	10.5
150°-160°	589.1	8.5
160°-170°	381.0	5.5
170°-180°	131.4	1.9
0°-30°	784.0	11.3
0°-40°	1261.2	18.1
0°-60°	2161.2	31.1
0°-90°	2709.0	38.9
90°-120°	922.2	13.3
90°-150°	3147.5	45.2
90°-180°	4249.0	61.1
0°-180°	6957.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1040	1040	1040	1040	1040	
5°	1038	1036	1028	1035	1035	98
15°	990	987	978	982	982	279
25°	898	894	884	885	883	413
35°	776	772	761	757	750	485
45°	635	631	622	612	610	489
55°	484	481	470	462	457	432
65°	327	325	316	309	305	324
75°	174	172	168	165	162	185
85°	45	46	46	45	44	51
90°	1	9	16	21	25	5
95°	58	53	16	21	22	75
105°	302	305	306	306	305	320
115°	566	571	572	568	562	561
125°	805	812	812	808	805	719
135°	1004	1010	1008	1006	1000	774
145°	1164	1166	1166	1167	1161	728
155°	1282	1276	1278	1280	1273	590
165°	1353	1347	1348	1353	1346	382
175°	1384	1378	1378	1386	1377	132
180°	1384	1384	1384	1384	1384	



TEST NUMBER: P333422-927

CATALOG NUMBER: S125DIW-S850D1340U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9
2.5°	1042.6	1042.1	1041.7	1041.2	1040.8	1039.8	1038.4	1037.0	1035.5	1034.0	1035.5
5°	1038.3	1037.9	1037.5	1037.2	1036.8	1035.7	1033.9	1032.1	1030.2	1028.4	1030.1
7.5°	1028.7	1028.4	1028.0	1027.6	1027.3	1026.1	1024.1	1022.1	1020.1	1018.0	1019.6
10°	1020.2	1019.9	1019.5	1019.1	1018.7	1017.6	1015.5	1013.5	1011.5	1009.5	1011.0
12.5°	1009.6	1009.0	1008.4	1007.7	1007.0	1005.8	1003.9	1002.0	1000.1	998.3	999.5
15°	989.8	989.2	988.6	988.1	987.5	986.3	984.3	982.2	980.2	978.2	979.1
17.5°	966.9	966.1	965.3	964.5	963.7	962.2	960.1	958.1	955.9	953.9	955.0
20°	947.8	947.5	947.1	946.7	946.3	944.9	942.5	940.2	937.8	935.4	936.8
22.5°	928.7	928.0	927.4	926.7	926.1	924.6	922.4	920.1	917.9	915.7	916.6
25°	898.4	897.5	896.6	895.6	894.8	893.1	890.7	888.4	886.0	883.6	884.0
27.5°	863.0	862.5	862.0	861.4	860.9	859.4	856.9	854.4	852.0	849.5	849.6
30°	840.0	839.5	838.9	838.4	837.8	836.1	833.5	830.7	827.9	825.2	824.8
32.5°	815.0	814.1	813.3	812.5	811.7	810.0	807.6	805.1	802.6	800.2	799.5
35°	775.9	775.1	774.4	773.6	772.9	771.3	768.7	766.1	763.6	761.0	760.1
37.5°	735.2	734.3	733.3	732.5	731.5	729.8	727.5	725.0	722.6	720.3	718.8
40°	707.6	706.6	705.8	704.8	703.9	702.2	699.6	697.0	694.5	691.9	690.3
42.5°	677.9	677.2	676.4	675.7	674.9	673.2	670.7	668.0	665.5	663.0	661.5
45°	635.2	634.4	633.7	633.0	632.2	630.7	628.6	626.4	624.2	622.0	619.8
47.5°	589.1	589.1	589.1	589.1	589.2	588.0	585.3	582.7	580.0	577.4	575.1
50°	559.4	558.9	558.3	557.8	557.3	555.9	553.7	551.5	549.3	547.1	544.7
52.5°	529.2	528.8	528.4	528.0	527.6	526.2	523.9	521.5	519.2	516.8	514.8
55°	483.8	483.2	482.7	482.1	481.6	480.0	477.4	474.9	472.3	469.8	468.1
57.5°	435.9	435.6	435.3	435.0	434.7	433.5	431.3	429.2	427.0	424.8	422.7
60°	405.6	404.9	404.2	403.4	402.7	401.3	399.3	397.3	395.3	393.2	391.4
62.5°	374.0	373.4	372.9	372.2	371.7	370.5	368.8	367.1	365.4	363.6	361.7
65°	326.6	326.2	325.9	325.5	325.2	324.0	321.9	320.0	317.9	315.9	314.3
67.5°	280.7	280.0	279.2	278.4	277.7	276.5	275.0	273.5	272.0	270.5	269.1
70°	251.8	250.8	249.9	249.0	248.1	246.8	245.2	243.5	241.9	240.3	239.2
72.5°	220.1	219.5	218.9	218.3	217.7	216.8	215.8	214.7	213.7	212.6	211.4
75°	173.6	173.3	172.9	172.5	172.1	171.5	170.6	169.7	168.7	167.9	167.3
77.5°	130.6	130.5	130.4	130.2	130.1	129.8	129.2	128.7	128.2	127.7	127.4
80°	103.7	103.7	103.7	103.7	103.7	103.5	103.1	102.7	102.3	102.0	101.9
82.5°	79.9	79.7	79.4	79.1	78.8	78.6	78.5	78.5	78.4	78.3	78.0
85°	45.2	45.5	45.6	45.8	45.9	46.1	46.1	46.1	46.1	46.1	45.9
87.5°	18.0	18.4	18.7	19.1	19.4	19.7	19.9	20.0	20.2	20.4	20.6
90°	1.0	2.9	4.7	6.5	8.3	10.1	11.6	13.2	14.8	16.4	17.6
92.5°	15.8	14.5	13.2	12.0	10.7	10.8	12.2	13.5	15.0	16.4	17.6
95°	58.5	57.8	57.1	56.4	55.7	51.0	42.4	33.7	25.0	16.4	17.6
97.5°	122.1	123.3	124.5	125.7	127.0	119.0	101.9	84.8	67.6	50.5	44.0
100°	171.3	172.0	172.6	173.3	174.0	174.8	175.7	176.7	177.5	178.5	144.5
102.5°	221.3	222.2	223.1	223.9	224.8	225.5	226.1	226.6	227.1	227.7	221.3
105°	301.6	302.5	303.4	304.3	305.2	305.6	305.6	305.6	305.6	305.6	305.6
107.5°	384.8	384.8	384.8	384.8	384.8	385.1	385.6	386.0	386.4	386.9	386.9
110°	439.0	439.0	439.0	439.0	439.0	439.2	439.7	440.1	440.6	441.0	440.4



TEST NUMBER: P333422-927

CATALOG NUMBER: S125DIW-S850D1340U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	489.9	490.4	491.0	491.5	492.0	492.5	492.7	493.0	493.3	493.5	492.7
115°	566.2	567.3	568.5	569.6	570.8	571.4	571.6	571.9	572.1	572.4	571.4
117.5°	645.2	645.1	645.1	645.0	645.0	645.4	646.3	647.1	648.0	648.9	647.7
120°	694.3	694.2	694.0	693.7	693.5	693.7	694.3	695.1	695.8	696.4	696.0
122.5°	737.8	738.7	739.6	740.5	741.3	742.0	742.3	742.6	742.9	743.2	742.8
125°	805.2	806.8	808.3	809.9	811.5	812.3	812.3	812.3	812.3	812.3	811.4
127.5°	869.3	870.5	871.6	872.7	873.9	874.4	874.3	874.2	874.0	873.9	873.4
130°	908.7	909.9	911.0	912.2	913.3	914.0	914.3	914.4	914.7	914.9	914.3
132.5°	948.2	949.4	950.8	952.1	953.4	953.9	953.3	952.8	952.4	951.8	951.7
135°	1004.2	1005.5	1006.9	1008.2	1009.6	1010.0	1009.6	1009.2	1008.7	1008.2	1007.8
137.5°	1055.7	1056.8	1058.0	1059.1	1060.3	1060.7	1060.3	1059.9	1059.5	1059.1	1059.2
140°	1089.3	1089.7	1090.2	1090.6	1091.1	1091.2	1091.0	1090.8	1090.5	1090.3	1090.8
142.5°	1119.6	1119.9	1120.1	1120.5	1120.7	1121.0	1121.3	1121.7	1122.0	1122.3	1122.4
145°	1164.1	1164.6	1165.1	1165.5	1165.9	1166.2	1166.2	1166.2	1166.2	1166.2	1166.4
147.5°	1203.1	1203.0	1202.9	1202.8	1202.8	1202.8	1203.1	1203.4	1203.6	1204.0	1204.2
150°	1227.7	1227.2	1226.9	1226.4	1225.9	1225.9	1226.4	1226.9	1227.2	1227.7	1228.2
152.5°	1251.5	1250.5	1249.5	1248.6	1247.5	1247.2	1247.7	1248.2	1248.6	1249.0	1249.5
155°	1282.1	1280.7	1279.4	1278.0	1276.6	1276.2	1276.6	1277.1	1277.6	1278.0	1278.7
157.5°	1305.7	1304.9	1304.0	1303.2	1302.4	1302.0	1302.0	1302.1	1302.2	1302.2	1302.9
160°	1322.1	1320.7	1319.4	1318.0	1316.6	1316.1	1316.3	1316.5	1316.8	1317.0	1317.9
162.5°	1335.2	1333.9	1332.5	1331.1	1329.8	1329.2	1329.4	1329.7	1329.8	1330.1	1331.3
165°	1352.9	1351.5	1350.1	1348.8	1347.4	1346.8	1347.0	1347.3	1347.5	1347.7	1349.1
167.5°	1366.0	1364.6	1363.2	1361.8	1360.3	1359.8	1359.9	1360.2	1360.4	1360.7	1362.3
170°	1373.4	1371.8	1370.2	1368.6	1367.0	1366.3	1366.5	1366.8	1367.0	1367.2	1369.0
172.5°	1378.3	1376.7	1375.1	1373.5	1371.9	1371.3	1371.7	1372.1	1372.5	1372.9	1374.6
175°	1383.6	1382.3	1380.9	1379.5	1378.2	1377.6	1377.8	1378.1	1378.3	1378.5	1380.3
177.5°	1386.1	1385.0	1383.9	1382.8	1381.7	1381.2	1381.5	1381.6	1381.8	1382.0	1383.3
180°	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6



TEST NUMBER: P333422-927

CATALOG NUMBER: S125DIW-S850D1340U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9
2.5°	1037.0	1038.4	1039.8	1040.5	1040.4	1040.2	1040.1	1039.9
5°	1031.7	1033.3	1035.0	1035.7	1035.5	1035.4	1035.1	1035.0
7.5°	1021.3	1022.9	1024.5	1025.2	1025.0	1024.8	1024.6	1024.5
10°	1012.4	1013.9	1015.3	1016.0	1015.8	1015.6	1015.4	1015.3
12.5°	1000.6	1001.8	1003.0	1003.5	1003.5	1003.5	1003.5	1003.4
15°	980.1	981.0	981.9	982.3	982.3	982.3	982.3	982.3
17.5°	956.2	957.3	958.4	958.5	957.6	956.7	955.8	954.9
20°	938.0	939.3	940.6	940.7	939.8	938.9	938.0	937.1
22.5°	917.3	918.2	919.1	919.2	918.5	917.9	917.3	916.7
25°	884.3	884.7	885.1	884.9	884.5	883.9	883.4	882.8
27.5°	849.7	849.8	849.9	849.6	849.1	848.5	848.0	847.4
30°	824.5	824.1	823.7	823.3	822.8	822.2	821.7	821.1
32.5°	798.8	798.2	797.6	796.7	795.7	794.7	793.8	792.8
35°	759.2	758.3	757.4	756.2	754.7	753.3	751.8	750.4
37.5°	717.5	716.1	714.8	713.7	712.9	712.0	711.2	710.3
40°	688.6	687.0	685.3	684.2	683.7	683.2	682.6	682.1
42.5°	660.0	658.5	657.0	655.8	655.0	654.1	653.2	652.4
45°	617.6	615.4	613.2	611.8	611.3	610.8	610.2	609.7
47.5°	572.9	570.7	568.5	566.7	565.5	564.2	562.8	561.6
50°	542.3	540.0	537.6	535.8	534.5	533.2	532.0	530.7
52.5°	512.7	510.6	508.5	506.8	505.3	503.9	502.5	501.1
55°	466.5	464.9	463.2	461.8	460.4	459.1	457.9	456.6
57.5°	420.6	418.5	416.4	414.9	414.2	413.6	412.9	412.2
60°	389.6	387.8	386.0	384.4	383.1	381.8	380.6	379.3
62.5°	359.7	357.7	355.8	354.3	353.3	352.3	351.3	350.3
65°	312.7	311.0	309.3	308.2	307.4	306.7	305.9	305.2
67.5°	267.8	266.3	265.0	264.0	263.6	263.2	262.7	262.3
70°	238.1	236.9	235.8	235.0	234.2	233.5	232.7	232.0
72.5°	210.1	208.9	207.6	206.6	205.9	205.2	204.5	203.7
75°	166.8	166.2	165.6	165.0	164.3	163.5	162.8	162.1
77.5°	127.1	126.7	126.4	126.0	125.4	124.9	124.5	123.9
80°	101.6	101.5	101.3	101.0	100.7	100.3	99.9	99.6
82.5°	77.6	77.3	77.0	76.8	76.8	76.7	76.6	76.5
85°	45.7	45.6	45.3	45.1	44.7	44.4	44.0	43.6
87.5°	20.8	21.1	21.3	21.3	21.2	21.0	20.9	20.8
90°	18.7	19.8	21.0	21.9	22.6	23.2	23.9	24.6
92.5°	18.7	19.8	21.0	21.7	22.0	22.3	22.7	23.0
95°	18.7	19.8	21.0	21.5	21.5	21.5	21.5	21.5
97.5°	37.6	31.2	24.7	21.5	21.5	21.5	21.5	21.5
100°	110.5	76.6	42.6	25.2	24.2	23.4	22.4	21.5
102.5°	214.8	208.4	202.0	191.0	175.5	160.0	144.5	129.0
105°	305.6	305.6	305.6	305.5	305.3	305.1	304.8	304.6
107.5°	387.0	387.1	387.1	386.7	386.0	385.4	384.7	384.0
110°	439.7	439.0	438.3	438.1	438.3	438.6	438.8	439.0



TEST NUMBER: P333422-927

CATALOG NUMBER: S125DIW-S850D1340U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	491.8	491.0	490.1	489.5	489.2	488.9	488.5	488.2
115°	570.5	569.6	568.7	567.5	566.2	564.8	563.4	562.1
117.5°	646.5	645.3	644.1	643.2	642.6	642.1	641.4	640.9
120°	695.5	695.1	694.6	693.8	692.7	691.5	690.4	689.3
122.5°	742.3	741.8	741.4	740.5	739.2	737.8	736.5	735.2
125°	810.5	809.6	808.7	807.9	807.2	806.5	805.8	805.2
127.5°	872.9	872.4	871.9	870.8	869.1	867.4	865.7	864.0
130°	913.5	912.8	912.2	911.2	910.1	908.9	907.8	906.7
132.5°	951.6	951.4	951.3	950.6	949.5	948.4	947.2	946.1
135°	1007.3	1006.9	1006.4	1005.5	1004.2	1002.7	1001.4	1000.1
137.5°	1059.3	1059.4	1059.5	1058.9	1057.7	1056.5	1055.3	1054.2
140°	1091.2	1091.6	1092.1	1091.6	1090.3	1088.9	1087.6	1086.2
142.5°	1122.4	1122.6	1122.7	1122.0	1120.6	1119.3	1117.9	1116.6
145°	1166.6	1166.9	1167.1	1166.6	1165.1	1163.8	1162.4	1161.1
147.5°	1204.5	1204.8	1205.1	1204.4	1202.7	1201.0	1199.4	1197.8
150°	1228.7	1229.1	1229.5	1228.8	1227.0	1225.2	1223.4	1221.5
152.5°	1250.0	1250.5	1250.9	1250.3	1248.6	1247.1	1245.4	1243.7
155°	1279.4	1280.0	1280.7	1280.2	1278.3	1276.5	1274.7	1272.9
157.5°	1303.7	1304.4	1305.1	1304.6	1302.7	1300.9	1299.1	1297.3
160°	1318.8	1319.7	1320.6	1320.2	1318.3	1316.5	1314.7	1312.9
162.5°	1332.6	1334.0	1335.2	1334.8	1332.8	1330.8	1328.8	1326.8
165°	1350.4	1351.9	1353.2	1353.0	1351.1	1349.3	1347.5	1345.7
167.5°	1364.0	1365.6	1367.2	1367.0	1364.9	1362.9	1360.9	1358.8
170°	1370.9	1372.7	1374.5	1374.4	1372.4	1370.3	1368.3	1366.2
172.5°	1376.3	1377.9	1379.5	1379.3	1377.3	1375.2	1373.2	1371.1
175°	1382.1	1383.9	1385.8	1385.7	1383.6	1381.6	1379.5	1377.4
177.5°	1384.6	1385.8	1387.1	1387.0	1385.5	1384.1	1382.6	1381.2
180°	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6

(END OF REPORT)