

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333094-840

Luminaire Tested: **S124RDIW-S1020D1560U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333094-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1020D1560U840-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9681.4 lumens
Efficiency: N/A
Efficacy: 126.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333094-840

CATALOG NUMBER: S124RDIW-S1020D1560U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333094-840

CATALOG NUMBER: S124RDIW-S1020D1560U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44			44
1	97	92	89	85	88	85	81	79	70	68	66	57	55	54	45	44	43	37			37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	40	38	36	31			31
3	80	71	64	58	73	66	59	54	55	50	46	45	41	39	35	33	31	27			27
4	74	63	55	50	67	58	51	46	49	44	40	40	36	33	32	29	27	23			23
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	29	26	24	20			20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18			18
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	24	21	19	16			16
8	54	41	34	29	49	38	32	27	33	27	24	27	23	20	22	19	17	14			14
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13			13
10	47	35	28	23	43	32	26	22	27	22	19	23	19	16	19	16	14	12			12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14721	14721	14721
5°	14755	14574	14665
10°	14662	14399	14399
15°	14493	14097	13992
20°	14262	13698	13447
25°	13967	13233	12897
30°	13679	12743	12209
35°	13361	12232	11517
40°	12978	11653	10771
45°	12625	11079	10011
50°	12223	10417	9207
55°	11792	9728	8332
60°	11317	8972	7440
65°	10883	8029	6562
70°	10249	6987	5570
75°	9451	5792	4529
80°	8243	4412	4156
85°	6984	4011	3751



TEST NUMBER: P333094-840

CATALOG NUMBER: S124RDIW-S1020D1560U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.3	1.8
10°-20°	477.7	4.9
20°-30°	689.8	7.1
30°-40°	781.8	8.1
40°-50°	755.0	7.8
50°-60°	627.8	6.5
60°-70°	433.5	4.5
70°-80°	219.7	2.3
80°-90°	62.2	0.6
90°-100°	129.9	1.3
100°-110°	384.7	4.0
110°-120°	652.9	6.7
120°-130°	861.0	8.9
130°-140°	966.9	10.0
140°-150°	950.1	9.8
150°-160°	799.1	8.3
160°-170°	531.7	5.5
170°-180°	186.2	1.9
0°-30°	1338.7	13.8
0°-40°	2120.6	21.9
0°-60°	3503.4	36.2
0°-90°	4218.9	43.6
90°-120°	1167.5	12.1
90°-150°	3945.5	40.8
90°-180°	5463.0	56.4
0°-180°	9681.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1824	1824	1824	1824	1824	
5°	1821	1814	1798	1811	1810	173
15°	1734	1720	1687	1683	1674	488
25°	1568	1541	1486	1462	1448	722
35°	1356	1310	1241	1195	1169	847
45°	1106	1052	970	904	877	852
55°	838	780	691	621	592	749
65°	570	508	420	363	344	562
75°	303	251	186	155	145	320
85°	75	49	43	41	40	85
90°	4	21	34	42	46	9
95°	91	105	116	120	120	102
105°	355	357	362	367	372	376
115°	664	664	661	659	658	654
125°	967	967	965	962	959	861
135°	1247	1256	1256	1253	1249	964
145°	1515	1521	1523	1521	1517	948
155°	1736	1736	1734	1740	1734	798
165°	1890	1885	1882	1890	1885	532
175°	1966	1958	1957	1966	1957	187
180°	1969	1969	1969	1969	1969	



TEST NUMBER: P333094-840

CATALOG NUMBER: S124RDIW-S1020D1560U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5
2.5°	1828.0	1826.9	1825.9	1825.0	1824.0	1822.1	1819.4	1816.6	1813.9	1811.2	1813.9
5°	1820.7	1819.5	1818.3	1816.9	1815.7	1813.2	1809.6	1805.8	1802.1	1798.4	1801.5
7.5°	1804.2	1802.9	1801.6	1800.3	1799.0	1795.9	1791.1	1786.2	1781.4	1776.6	1778.6
10°	1788.6	1787.1	1785.4	1783.9	1782.4	1778.8	1773.2	1767.7	1762.0	1756.5	1757.7
12.5°	1768.5	1766.7	1764.8	1763.1	1761.3	1757.1	1750.5	1743.9	1737.4	1730.8	1731.5
15°	1734.1	1731.3	1728.6	1725.8	1722.9	1717.7	1709.9	1702.1	1694.5	1686.7	1686.1
17.5°	1692.5	1688.5	1684.5	1680.4	1676.4	1669.7	1660.4	1651.1	1641.8	1632.4	1630.7
20°	1660.1	1656.1	1652.0	1648.0	1644.0	1636.7	1626.2	1615.6	1605.1	1594.5	1592.1
22.5°	1624.4	1619.8	1615.3	1610.8	1606.3	1598.3	1587.1	1575.8	1564.5	1553.2	1549.4
25°	1568.0	1562.4	1556.8	1551.3	1545.6	1536.5	1523.8	1511.1	1498.3	1485.6	1480.4
27.5°	1508.7	1501.8	1494.8	1487.7	1480.8	1470.5	1456.8	1443.3	1429.7	1416.0	1409.6
30°	1467.4	1459.7	1452.0	1444.2	1436.4	1425.2	1410.7	1396.0	1381.5	1367.0	1359.2
32.5°	1423.9	1415.1	1406.3	1397.7	1388.9	1377.0	1361.9	1346.9	1331.7	1316.7	1307.7
35°	1355.7	1345.8	1335.8	1326.0	1316.1	1303.3	1287.8	1272.3	1256.8	1241.2	1230.7
37.5°	1282.8	1272.6	1262.4	1252.1	1241.9	1228.2	1211.0	1193.9	1176.6	1159.4	1147.6
40°	1231.5	1221.2	1211.0	1200.7	1190.5	1176.6	1158.9	1141.1	1123.5	1105.8	1092.8
42.5°	1182.3	1171.6	1160.8	1150.1	1139.4	1124.8	1106.4	1087.9	1069.5	1051.1	1037.8
45°	1105.8	1094.4	1082.9	1071.4	1059.9	1044.8	1026.2	1007.6	989.0	970.4	955.2
47.5°	1026.8	1014.9	1003.1	991.3	979.4	963.8	944.4	925.0	905.6	886.4	870.6
50°	973.2	961.1	949.0	936.9	924.7	908.8	889.0	869.1	849.2	829.4	813.9
52.5°	918.5	906.6	894.7	882.9	871.0	855.0	834.6	814.3	793.9	773.6	757.8
55°	837.8	825.4	812.9	800.5	788.1	771.8	751.6	731.4	711.3	691.2	675.0
57.5°	757.9	745.0	732.1	719.1	706.3	689.8	670.0	650.2	630.3	610.5	594.1
60°	700.9	688.5	676.1	663.7	651.3	635.1	615.3	595.4	575.5	555.7	539.6
62.5°	649.5	636.6	623.7	610.8	597.9	581.3	560.9	540.6	520.2	499.9	484.9
65°	569.7	556.3	543.0	529.7	516.3	499.7	479.9	460.0	440.1	420.3	407.0
67.5°	486.8	473.9	461.2	448.4	435.6	420.0	401.5	383.1	364.7	346.3	334.8
70°	434.2	421.2	408.2	395.2	382.1	366.8	349.1	331.3	313.7	296.0	285.8
72.5°	378.4	366.6	354.8	343.1	331.2	317.0	300.3	283.6	266.9	250.2	241.5
75°	303.0	291.5	280.0	268.5	257.1	244.0	229.4	214.9	200.3	185.7	178.5
77.5°	226.5	216.7	207.0	197.2	187.5	176.7	164.9	153.2	141.4	129.6	125.4
80°	177.3	168.3	159.4	150.4	141.4	132.2	122.9	113.6	104.2	94.9	94.0
82.5°	134.9	126.6	118.4	110.1	101.9	95.0	89.8	84.4	79.1	73.7	73.0
85°	75.4	69.2	63.0	56.8	50.6	47.0	46.0	45.1	44.2	43.3	42.6
87.5°	26.6	25.3	24.1	22.9	21.6	21.2	21.4	21.7	22.0	22.3	22.5
90°	4.5	8.3	12.0	15.8	19.5	22.7	25.3	28.1	30.8	33.5	35.5
92.5°	32.6	36.9	41.1	45.3	49.7	52.7	54.6	56.6	58.4	60.3	61.5
95°	91.4	94.4	97.5	100.5	103.5	106.2	108.7	111.0	113.4	115.7	116.7
97.5°	159.6	162.0	164.4	166.9	169.4	172.0	174.7	177.4	180.3	183.0	184.2
100°	213.2	214.5	215.9	217.2	218.6	220.8	223.9	226.9	229.9	233.0	233.7
102.5°	269.2	269.7	270.3	270.8	271.4	273.1	275.8	278.6	281.3	284.2	285.1
105°	354.8	355.2	355.5	355.8	356.2	357.0	358.3	359.7	361.0	362.4	363.5
107.5°	444.6	445.0	445.5	445.9	446.3	446.6	446.8	447.0	447.2	447.4	448.3
110°	505.5	506.2	506.9	507.6	508.3	508.5	508.1	507.8	507.4	507.1	506.3



TEST NUMBER: P333094-840

CATALOG NUMBER: S124RDIW-S1020D1560U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	568.9	569.1	569.2	569.3	569.5	569.2	568.6	567.9	567.3	566.7	566.6
115°	663.9	663.9	663.9	663.9	663.9	663.6	662.9	662.2	661.6	660.9	660.6
117.5°	753.5	753.7	754.0	754.3	754.6	754.5	754.0	753.5	753.0	752.6	751.3
120°	813.1	814.5	815.9	817.2	818.5	818.7	817.7	816.7	815.7	814.7	812.9
122.5°	875.3	875.8	876.4	876.9	877.4	877.5	877.0	876.5	876.1	875.6	874.4
125°	966.9	966.9	966.9	966.9	966.9	966.7	966.4	966.0	965.7	965.4	964.7
127.5°	1050.1	1051.1	1052.1	1053.1	1054.1	1054.4	1053.8	1053.3	1052.8	1052.2	1051.5
130°	1108.5	1109.5	1110.5	1111.6	1112.6	1113.1	1113.1	1113.1	1113.1	1113.1	1112.5
132.5°	1168.2	1169.0	1169.7	1170.4	1171.2	1171.4	1171.1	1170.9	1170.6	1170.3	1169.7
135°	1247.1	1249.1	1251.1	1253.2	1255.3	1256.3	1256.3	1256.3	1256.3	1256.3	1255.6
137.5°	1333.0	1333.9	1334.8	1335.8	1336.8	1337.6	1338.1	1338.6	1339.2	1339.7	1338.8
140°	1390.3	1390.9	1391.6	1392.3	1392.9	1393.3	1393.3	1393.3	1393.3	1393.3	1392.9
142.5°	1442.6	1443.3	1444.0	1444.6	1445.3	1445.5	1445.2	1445.0	1444.7	1444.4	1444.4
145°	1515.1	1516.4	1517.8	1519.1	1520.6	1521.4	1521.7	1522.1	1522.4	1522.7	1522.4
147.5°	1587.0	1588.6	1590.2	1591.9	1593.5	1594.2	1593.9	1593.6	1593.4	1593.1	1592.8
150°	1630.8	1632.1	1633.6	1634.9	1636.3	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9
152.5°	1672.2	1673.0	1673.9	1674.7	1675.5	1676.1	1676.3	1676.6	1676.9	1677.1	1677.9
155°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.8	1735.4	1735.0	1734.7	1734.3	1735.8
157.5°	1789.5	1788.9	1788.3	1787.7	1787.1	1786.8	1786.7	1786.6	1786.6	1786.5	1787.5
160°	1821.2	1820.8	1820.5	1820.2	1819.8	1819.5	1819.2	1818.8	1818.5	1818.2	1819.2
162.5°	1850.4	1849.6	1848.7	1847.8	1846.8	1846.2	1845.9	1845.6	1845.2	1844.9	1846.7
165°	1889.7	1888.6	1887.6	1886.6	1885.6	1884.8	1884.1	1883.4	1882.8	1882.1	1884.1
167.5°	1919.9	1918.4	1917.0	1915.6	1914.2	1913.5	1913.6	1913.6	1913.7	1913.8	1915.8
170°	1936.9	1935.2	1933.5	1931.8	1930.2	1929.4	1929.8	1930.2	1930.5	1930.8	1932.8
172.5°	1949.0	1947.6	1946.2	1944.8	1943.4	1942.7	1942.8	1942.9	1942.9	1943.0	1945.3
175°	1965.8	1964.1	1962.5	1960.8	1959.0	1958.0	1957.7	1957.3	1957.0	1956.7	1959.0
177.5°	1971.3	1969.9	1968.6	1967.2	1965.9	1965.2	1965.2	1965.2	1965.2	1965.2	1967.1
180°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8



TEST NUMBER: P333094-840

CATALOG NUMBER: S124RDIW-S1020D1560U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5
2.5°	1816.6	1819.4	1822.1	1823.4	1823.1	1822.9	1822.6	1822.4
5°	1804.5	1807.7	1810.8	1812.0	1811.4	1810.8	1810.2	1809.6
7.5°	1780.6	1782.5	1784.5	1785.0	1784.0	1783.0	1782.0	1781.0
10°	1759.0	1760.2	1761.4	1761.4	1760.2	1759.0	1757.7	1756.5
12.5°	1732.2	1733.0	1733.7	1733.2	1731.5	1729.8	1728.1	1726.4
15°	1685.5	1684.8	1684.2	1682.7	1680.6	1678.4	1676.3	1674.1
17.5°	1629.0	1627.3	1625.6	1623.1	1619.7	1616.5	1613.2	1609.8
20°	1589.5	1587.1	1584.6	1581.3	1577.3	1573.3	1569.2	1565.2
22.5°	1545.7	1542.0	1538.3	1534.8	1531.5	1528.2	1524.9	1521.7
25°	1475.0	1469.8	1464.5	1460.3	1457.2	1454.1	1451.0	1447.9
27.5°	1403.0	1396.5	1390.0	1384.5	1380.1	1375.5	1371.1	1366.7
30°	1351.4	1343.6	1335.8	1329.5	1324.5	1319.6	1314.6	1309.7
32.5°	1298.7	1289.7	1280.7	1273.8	1269.1	1264.4	1259.7	1255.0
35°	1220.1	1209.6	1199.0	1191.0	1185.4	1179.8	1174.3	1168.6
37.5°	1135.9	1124.1	1112.3	1103.6	1098.0	1092.4	1086.8	1081.3
40°	1079.7	1066.7	1053.7	1044.4	1038.8	1033.2	1027.6	1022.1
42.5°	1024.5	1011.3	997.9	988.5	982.6	976.7	970.9	965.1
45°	940.0	924.7	909.6	899.2	893.6	888.0	882.4	876.9
47.5°	854.9	839.1	823.2	812.3	806.2	800.0	793.9	787.8
50°	798.3	782.8	767.3	756.6	750.7	744.8	738.9	733.1
52.5°	741.9	726.2	710.4	699.5	693.4	687.2	681.1	675.0
55°	658.8	642.8	626.6	615.6	609.7	603.8	597.9	592.0
57.5°	577.6	561.3	544.9	534.5	530.0	525.5	521.1	516.6
60°	523.4	507.3	491.2	480.6	475.6	470.7	465.7	460.8
62.5°	470.1	455.1	440.3	430.8	426.9	422.9	418.9	415.0
65°	393.5	380.2	366.9	358.4	354.7	350.9	347.2	343.5
67.5°	323.3	311.8	300.3	292.6	288.4	284.4	280.2	276.2
70°	275.5	265.3	255.1	248.3	245.3	242.2	239.0	236.0
72.5°	232.7	224.0	215.2	209.4	206.5	203.7	200.9	198.0
75°	171.5	164.3	157.1	152.7	150.8	149.0	147.0	145.2
77.5°	121.3	117.1	112.9	110.6	110.0	109.5	108.9	108.4
80°	93.1	92.2	91.2	90.6	90.3	90.0	89.7	89.4
82.5°	72.3	71.7	71.0	70.5	70.2	69.9	69.6	69.3
85°	42.0	41.4	40.8	40.5	40.5	40.5	40.5	40.5
87.5°	22.6	22.8	22.9	23.2	23.6	24.0	24.4	24.7
90°	37.6	39.6	41.6	43.0	43.6	44.3	45.0	45.6
92.5°	62.7	63.9	65.1	65.9	66.3	66.8	67.2	67.6
95°	117.8	118.8	119.8	120.3	120.3	120.3	120.3	120.3
97.5°	185.5	186.7	187.9	188.5	188.5	188.5	188.5	188.5
100°	234.3	235.0	235.7	236.0	236.0	236.0	236.0	236.0
102.5°	286.0	287.0	287.9	288.5	288.8	289.1	289.3	289.6
105°	364.5	365.5	366.5	367.5	368.5	369.5	370.5	371.5
107.5°	449.3	450.2	451.2	451.6	451.5	451.5	451.4	451.3
110°	505.7	505.0	504.3	504.5	505.5	506.5	507.6	508.6



TEST NUMBER: P333094-840

CATALOG NUMBER: S124RDIW-S1020D1560U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	566.4	566.3	566.2	566.2	566.4	566.6	566.8	567.0
115°	660.1	659.8	659.5	659.1	658.8	658.5	658.1	657.8
117.5°	750.2	749.1	747.9	747.0	746.3	745.7	745.0	744.3
120°	811.2	809.6	807.9	807.4	808.1	808.7	809.4	810.1
122.5°	873.2	872.1	871.0	869.8	868.6	867.4	866.2	864.9
125°	964.0	963.4	962.7	962.0	961.3	960.7	960.0	959.3
127.5°	1050.9	1050.2	1049.5	1048.8	1048.3	1047.8	1047.2	1046.7
130°	1111.8	1111.1	1110.3	1109.3	1108.0	1106.7	1105.3	1104.0
132.5°	1169.0	1168.3	1167.6	1167.0	1166.5	1166.0	1165.4	1164.9
135°	1254.9	1254.3	1253.5	1252.6	1251.6	1250.6	1249.6	1248.6
137.5°	1338.0	1337.1	1336.2	1335.8	1336.1	1336.3	1336.5	1336.7
140°	1392.6	1392.3	1391.9	1391.6	1391.3	1390.9	1390.6	1390.3
142.5°	1444.3	1444.2	1444.2	1444.1	1444.0	1444.0	1443.9	1443.8
145°	1522.1	1521.7	1521.4	1520.7	1519.6	1518.6	1517.6	1516.6
147.5°	1592.6	1592.3	1592.0	1591.6	1591.3	1591.0	1590.6	1590.3
150°	1636.9	1636.9	1636.9	1636.8	1636.4	1636.1	1635.8	1635.4
152.5°	1678.7	1679.5	1680.3	1680.3	1679.4	1678.6	1677.7	1676.8
155°	1737.1	1738.4	1739.8	1739.8	1738.4	1737.1	1735.8	1734.3
157.5°	1788.5	1789.5	1790.5	1790.4	1789.3	1788.2	1787.0	1785.8
160°	1820.2	1821.2	1822.2	1821.8	1820.2	1818.5	1816.7	1815.0
162.5°	1848.6	1850.4	1852.2	1852.3	1850.6	1849.0	1847.2	1845.5
165°	1886.1	1888.1	1890.2	1890.6	1889.2	1887.8	1886.4	1885.1
167.5°	1917.8	1919.9	1921.9	1921.9	1919.8	1917.6	1915.5	1913.4
170°	1934.9	1936.9	1938.9	1938.7	1936.4	1934.0	1931.7	1929.2
172.5°	1947.6	1949.8	1952.2	1952.2	1949.7	1947.4	1945.0	1942.7
175°	1961.5	1963.8	1966.2	1966.2	1963.8	1961.5	1959.0	1956.7
177.5°	1969.0	1970.9	1972.8	1972.7	1970.4	1968.3	1966.2	1964.0
180°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8

(END OF REPORT)