

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333406-927

Luminaire Tested: **S125DIW-S850D770U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333406-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S850D770U927-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5167.9 lumens
Efficiency: N/A
Efficacy: 114.8 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333406-927

CATALOG NUMBER: S125DIW-S850D770U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333406-927

CATALOG NUMBER: S125DIW-S850D770U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	94	91	87	91	88	84	81	75	73	70	63	61	60	52	51	50	45
2	90	83	77	72	83	77	72	67	66	62	59	56	53	50	46	44	43	38
3	82	73	66	60	76	68	61	56	58	53	49	49	46	43	41	39	36	33
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	32	28
5	69	58	50	44	64	54	47	41	46	41	37	40	35	32	33	30	28	24
6	64	52	44	38	59	48	41	36	42	36	32	36	31	28	30	27	24	21
7	59	47	39	33	55	44	37	32	38	32	28	33	28	25	28	24	22	19
8	55	42	35	29	51	40	33	28	35	29	25	30	25	22	25	22	19	17
9	51	39	31	26	47	36	30	25	32	26	22	27	23	20	23	20	17	15
10	48	36	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6259	6259	6259	6259
5°	7248	6280	5499	6280
10°	8433	6248	4818	6248
15°	9335	6202	4444	6202
20°	10449	6129	4144	6129
25°	12241	6047	3998	6047
30°	13221	5967	3871	5967
35°	10871	5815	3788	5815
40°	7727	5604	3697	5604
45°	5936	5320	3644	5320
50°	5067	4967	3636	4967
55°	4512	4622	3668	4622
60°	4070	4246	3761	4246
65°	3759	3865	3859	3865
70°	3418	3473	3914	3473
75°	3019	3059	3880	3059
80°	2540	2492	3552	2492
85°	2016	1793	2868	1793



TEST NUMBER: P333406-927

CATALOG NUMBER: S125DIW-S850D770U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.3	1.8
10°-20°	277.8	5.4
20°-30°	451.1	8.7
30°-40°	550.2	10.6
40°-50°	500.5	9.7
50°-60°	398.7	7.7
60°-70°	277.7	5.4
70°-80°	148.1	2.9
80°-90°	39.0	0.8
90°-100°	28.8	0.6
100°-110°	177.3	3.4
110°-120°	321.6	6.2
120°-130°	412.8	8.0
130°-140°	444.0	8.6
140°-150°	416.7	8.1
150°-160°	337.1	6.5
160°-170°	218.0	4.2
170°-180°	75.2	1.5
0°-30°	822.1	15.9
0°-40°	1372.3	26.6
0°-60°	2271.6	44.0
0°-90°	2736.3	52.9
90°-120°	527.8	10.2
90°-150°	1801.3	34.9
90°-180°	2432.0	47.1
0°-180°	5167.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	969	969	969	969	969	
5°	1118	969	848	969	1118	113
15°	1396	928	665	928	1396	400
25°	1718	849	561	849	1718	785
35°	1379	738	480	738	1379	844
45°	650	582	399	582	650	520
55°	401	410	326	410	401	361
65°	246	253	252	253	246	244
75°	121	123	156	123	121	130
85°	27	24	39	24	27	32
90°	14	1	14	1	14	7
95°	12	33	12	33	12	10
105°	174	172	174	172	174	158
115°	322	324	322	324	322	319
125°	461	461	461	461	461	410
135°	572	575	572	575	572	442
145°	664	666	664	666	664	415
155°	728	734	728	734	728	336
165°	770	774	770	774	770	217
175°	788	792	788	792	788	75
180°	792	792	792	792	792	



TEST NUMBER: P333406-927

CATALOG NUMBER: S125DIW-S850D770U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2
2.5°	1025.1	1023.7	1022.5	1019.8	1021.8	1016.2	1013.5	1008.9	1003.4	1001.4	999.1
5°	1118.0	1120.1	1122.1	1113.5	1114.4	1108.6	1095.4	1084.7	1076.1	1065.0	1057.2
7.5°	1229.9	1225.0	1224.6	1219.1	1209.4	1201.7	1187.9	1170.3	1153.3	1133.9	1117.8
10°	1285.9	1286.3	1282.5	1276.0	1265.7	1258.3	1240.2	1222.9	1202.0	1177.3	1159.6
12.5°	1328.0	1329.7	1325.0	1316.1	1311.1	1294.5	1280.3	1259.8	1234.9	1215.1	1188.2
15°	1396.1	1391.5	1388.3	1377.2	1368.6	1351.3	1328.6	1307.3	1280.1	1255.0	1229.9
17.5°	1461.7	1465.4	1459.2	1449.1	1422.3	1402.1	1371.7	1342.4	1308.7	1275.0	1245.1
20°	1520.4	1523.6	1514.2	1496.5	1464.4	1444.2	1404.3	1366.5	1327.4	1284.2	1251.3
22.5°	1593.4	1590.8	1578.0	1551.1	1523.3	1486.1	1442.8	1396.8	1347.8	1299.0	1255.3
25°	1717.8	1700.5	1692.7	1659.4	1622.8	1568.0	1508.8	1441.4	1380.5	1315.9	1260.0
27.5°	1786.7	1781.3	1772.6	1749.4	1710.9	1652.4	1582.5	1500.3	1414.4	1332.9	1259.7
30°	1772.9	1773.7	1774.6	1767.1	1742.5	1698.4	1629.0	1540.5	1438.4	1346.7	1262.0
32.5°	1650.5	1665.5	1679.7	1696.7	1703.6	1695.2	1651.6	1571.8	1466.8	1362.6	1260.7
35°	1378.8	1383.4	1429.8	1475.9	1538.4	1587.0	1619.5	1584.1	1495.6	1375.9	1259.1
37.5°	1075.1	1097.3	1129.5	1181.5	1271.8	1352.6	1456.5	1504.3	1475.8	1380.3	1256.2
40°	916.5	937.1	958.0	1011.1	1087.2	1185.1	1303.1	1403.9	1427.4	1366.5	1246.3
42.5°	794.1	810.3	833.6	873.5	937.2	1023.8	1136.6	1268.4	1349.4	1326.4	1225.7
45°	649.9	660.2	678.3	710.0	756.1	823.9	923.4	1067.5	1192.9	1234.5	1176.5
47.5°	556.3	556.2	570.3	592.2	625.4	683.1	756.7	869.5	1003.5	1102.6	1098.0
50°	504.3	502.2	513.3	532.3	558.6	596.8	667.2	757.2	886.1	998.3	1029.6
52.5°	459.5	459.8	466.6	480.6	502.6	535.4	587.9	669.1	779.1	894.4	953.2
55°	400.7	399.0	406.8	416.3	432.3	453.7	491.5	553.7	642.9	756.5	833.0
57.5°	346.7	351.2	354.3	360.9	374.2	388.6	420.5	466.0	536.9	634.3	715.2
60°	315.1	319.6	322.1	328.7	339.4	351.7	376.4	413.4	473.0	557.0	637.2
62.5°	286.8	290.3	291.1	297.1	305.8	317.8	337.2	368.3	415.4	488.9	567.4
65°	246.0	246.0	247.6	253.8	257.9	268.6	283.4	306.0	343.9	401.1	468.1
67.5°	206.7	208.7	208.2	211.0	214.8	223.0	233.6	252.3	280.4	322.1	375.7
70°	181.0	182.6	182.2	184.3	188.4	193.8	202.4	220.1	240.2	276.0	322.1
72.5°	158.0	158.6	157.6	160.3	162.7	167.4	177.1	186.5	205.3	235.5	273.4
75°	121.0	121.8	122.6	124.2	126.7	129.1	134.1	143.5	155.9	178.6	202.8
77.5°	90.6	89.1	91.1	90.9	92.2	94.1	98.5	103.5	113.6	127.9	146.7
80°	68.3	68.7	68.7	69.1	71.1	72.4	76.1	79.8	87.6	98.3	111.5
82.5°	49.8	50.9	50.3	51.0	52.8	53.6	55.7	58.7	63.3	71.7	81.2
85°	27.2	25.1	25.9	26.8	26.8	27.2	28.8	30.0	32.5	35.8	39.5
87.5°	10.7	11.3	11.6	11.5	11.7	11.6	12.8	12.7	13.5	14.4	15.5
90°	14.1	13.7	13.3	12.9	12.5	12.0	11.3	10.7	10.1	9.4	8.5
92.5°	13.2	13.0	12.8	12.6	12.4	12.0	11.3	10.7	10.1	9.4	8.6
95°	12.4	12.4	12.4	12.4	12.4	12.0	11.3	10.7	10.1	9.4	14.3
97.5°	12.4	12.4	12.4	12.4	12.4	14.2	17.8	21.5	25.2	28.9	38.7
100°	12.4	12.8	13.4	13.9	14.4	24.4	43.8	63.3	82.7	102.1	101.6
102.5°	73.8	82.7	91.6	100.4	109.3	115.6	119.3	122.9	126.7	130.3	130.0
105°	174.4	174.4	174.6	174.8	174.8	174.9	174.9	174.9	174.9	174.9	174.9
107.5°	219.8	220.1	220.5	220.9	221.3	221.5	221.5	221.5	221.4	221.4	221.2
110°	251.2	251.1	251.0	250.8	250.7	250.8	251.2	251.6	252.0	252.4	252.2



TEST NUMBER: P333406-927

CATALOG NUMBER: S125DIW-S850D770U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	279.4	279.6	279.8	280.0	280.1	280.4	281.0	281.5	281.9	282.5	282.3
115°	321.6	322.4	323.2	324.0	324.8	325.4	326.0	326.5	327.0	327.6	327.4
117.5°	366.8	367.1	367.4	367.7	368.1	368.6	369.3	369.9	370.7	371.3	370.8
120°	394.4	395.1	395.8	396.4	397.0	397.5	397.8	398.1	398.3	398.5	398.2
122.5°	420.7	421.5	422.2	423.0	423.7	424.3	424.5	424.8	425.1	425.3	425.2
125°	460.8	461.2	461.5	461.9	462.3	462.8	463.3	463.8	464.4	464.9	464.9
127.5°	494.5	495.4	496.4	497.3	498.4	499.0	499.2	499.6	499.8	500.1	500.2
130°	518.9	519.5	520.2	520.9	521.5	522.0	522.4	522.8	523.2	523.6	523.5
132.5°	541.5	542.1	542.7	543.4	544.1	544.4	544.5	544.5	544.6	544.7	545.0
135°	572.3	573.1	573.9	574.6	575.4	576.0	576.2	576.5	576.7	577.0	577.3
137.5°	603.3	604.0	604.7	605.3	606.0	606.3	606.3	606.3	606.2	606.1	606.3
140°	621.6	622.4	623.2	623.9	624.7	625.0	624.7	624.5	624.2	623.9	624.1
142.5°	639.0	639.8	640.6	641.4	642.1	642.5	642.5	642.4	642.3	642.3	642.1
145°	664.5	665.3	666.0	666.8	667.6	667.9	667.8	667.7	667.5	667.4	667.4
147.5°	685.5	686.4	687.4	688.3	689.2	689.6	689.4	689.3	689.1	689.0	688.8
150°	699.1	700.1	701.2	702.2	703.3	703.7	703.4	703.1	702.9	702.6	702.3
152.5°	711.8	712.7	713.7	714.5	715.5	715.9	715.6	715.3	715.1	714.8	714.5
155°	728.4	729.5	730.6	731.6	732.6	732.9	732.5	732.1	731.7	731.3	731.1
157.5°	742.4	743.5	744.5	745.5	746.6	746.9	746.5	746.1	745.7	745.2	745.2
160°	751.3	752.4	753.4	754.5	755.5	755.7	755.3	754.7	754.2	753.7	753.5
162.5°	759.3	760.5	761.6	762.8	763.9	764.1	763.3	762.6	761.9	761.2	761.0
165°	770.1	771.2	772.2	773.2	774.3	774.4	773.6	772.9	772.1	771.3	771.2
167.5°	777.6	778.8	780.0	781.2	782.4	782.4	781.5	780.5	779.6	778.7	778.6
170°	781.9	783.0	784.2	785.4	786.6	786.6	785.6	784.5	783.5	782.4	782.3
172.5°	784.7	785.8	787.0	788.2	789.3	789.5	788.5	787.6	786.6	785.8	785.5
175°	788.3	789.5	790.7	791.9	793.0	793.1	792.0	791.0	790.0	788.9	788.8
177.5°	790.4	791.2	792.1	792.9	793.8	793.8	793.1	792.3	791.6	790.9	790.8
180°	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9



TEST NUMBER: P333406-927

CATALOG NUMBER: S125DIW-S850D770U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2
2.5°	997.1	994.8	992.1	987.5	982.0	979.0	974.4	971.5	965.5	960.6	955.3
5°	1047.7	1037.0	1027.1	1014.4	1000.4	991.3	980.6	968.7	956.4	943.6	929.6
7.5°	1100.1	1081.2	1060.6	1038.5	1016.8	997.0	977.9	959.3	941.8	920.8	902.9
10°	1135.3	1111.4	1085.9	1055.9	1026.7	1001.2	975.3	952.7	929.6	905.0	883.1
12.5°	1170.5	1138.8	1102.7	1069.8	1034.6	1003.9	973.4	944.4	915.5	888.2	862.8
15°	1195.4	1167.4	1134.1	1087.2	1047.7	1005.4	965.0	927.6	892.6	862.2	830.1
17.5°	1211.7	1175.7	1140.0	1095.0	1043.1	995.8	950.1	907.3	867.8	829.3	798.4
20°	1214.7	1177.7	1140.3	1096.2	1043.1	988.9	943.3	891.8	849.5	809.5	771.7
22.5°	1213.7	1171.8	1131.0	1085.7	1034.0	984.0	928.8	876.3	830.4	791.1	751.6
25°	1204.4	1159.6	1108.6	1063.0	1011.9	958.9	902.9	848.6	801.7	756.9	717.8
27.5°	1196.7	1138.5	1080.8	1027.5	978.3	929.6	876.1	820.5	768.5	723.0	686.2
30°	1187.2	1123.4	1058.4	1002.8	952.3	905.0	854.4	800.1	745.8	701.3	661.9
32.5°	1178.6	1104.3	1035.7	975.3	921.6	875.7	829.0	777.4	724.1	679.0	639.4
35°	1162.1	1076.1	997.5	929.2	872.0	824.7	785.7	737.5	688.6	645.0	607.1
37.5°	1141.1	1039.0	954.7	883.1	820.5	770.6	734.3	697.3	650.3	608.3	574.1
40°	1124.6	1012.7	923.4	850.2	785.3	733.4	699.7	664.7	625.7	586.6	550.4
42.5°	1103.9	989.0	891.9	813.1	748.7	698.2	662.8	633.1	598.7	562.2	528.6
45°	1065.8	946.1	840.8	756.1	691.0	641.3	604.7	582.5	556.6	522.0	493.6
47.5°	1009.8	894.5	785.6	698.2	631.1	584.9	550.6	529.3	511.0	485.4	459.6
50°	960.0	856.0	745.8	658.9	591.9	545.4	513.8	494.4	478.8	459.1	437.3
52.5°	904.4	807.6	706.6	620.8	554.4	508.6	477.6	460.6	447.6	433.4	411.9
55°	816.1	733.9	640.1	558.6	497.3	452.5	425.3	410.5	399.8	389.1	376.0
57.5°	718.7	654.4	571.3	496.9	440.5	399.7	374.3	359.9	351.6	346.1	338.3
60°	650.3	595.2	523.6	455.7	400.7	364.5	339.8	328.7	321.7	317.1	311.4
62.5°	586.8	541.6	475.2	413.3	365.1	330.9	308.9	298.1	291.4	289.1	284.4
65°	493.2	458.3	403.5	352.1	311.0	281.8	263.2	252.9	248.8	246.4	246.8
67.5°	401.0	379.7	335.7	291.9	259.0	234.6	219.8	211.8	209.8	206.5	206.4
70°	344.7	328.7	291.7	253.4	224.2	205.3	192.1	183.9	181.8	180.1	179.7
72.5°	295.0	281.0	248.8	218.2	191.9	175.3	164.5	159.5	156.1	155.2	155.1
75°	221.7	213.9	188.4	164.1	146.0	134.5	127.1	122.6	120.1	119.7	120.1
77.5°	157.6	150.8	134.6	117.4	106.0	97.3	91.0	89.4	86.7	86.7	86.3
80°	118.4	113.9	103.7	90.1	80.6	73.2	69.9	67.0	66.2	65.0	66.2
82.5°	85.9	81.0	74.1	65.4	57.6	53.2	49.8	49.0	48.5	47.8	48.2
85°	42.4	42.8	38.7	32.1	28.8	26.3	24.2	24.2	23.8	23.4	23.8
87.5°	16.0	15.1	13.6	12.4	10.6	9.4	8.9	9.0	8.2	8.1	8.6
90°	7.6	6.7	5.7	4.8	3.7	2.7	1.7	0.6	1.7	2.7	3.7
92.5°	7.8	7.0	6.2	6.1	6.8	7.6	8.3	9.0	8.3	7.6	6.8
95°	19.3	24.2	29.2	31.9	32.3	32.6	33.0	33.4	33.0	32.6	32.3
97.5°	48.5	58.3	68.1	72.6	71.9	71.3	70.6	69.9	70.6	71.3	71.9
100°	101.1	100.6	100.1	99.6	99.2	98.8	98.4	98.0	98.4	98.8	99.2
102.5°	129.7	129.4	129.0	128.7	128.2	127.7	127.1	126.7	127.1	127.7	128.2
105°	174.9	174.9	174.9	174.7	174.1	173.6	173.1	172.5	173.1	173.6	174.1
107.5°	220.9	220.6	220.4	220.2	220.2	220.2	220.2	220.2	220.2	220.2	220.2
110°	251.9	251.6	251.4	251.2	251.2	251.2	251.2	251.2	251.2	251.2	251.2



TEST NUMBER: P333406-927

CATALOG NUMBER: S125DIW-S850D770U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	282.2	282.0	281.9	281.6	281.3	281.0	280.7	280.4	280.7	281.0	281.3
115°	327.3	327.2	327.0	326.6	326.0	325.3	324.6	324.0	324.6	325.3	326.0
117.5°	370.3	369.9	369.3	369.1	369.2	369.2	369.2	369.2	369.2	369.2	369.2
120°	397.8	397.4	397.0	396.9	397.0	397.1	397.3	397.4	397.3	397.1	397.0
122.5°	424.9	424.8	424.6	424.3	423.7	423.3	422.8	422.2	422.8	423.3	423.7
125°	464.9	464.9	464.9	464.5	463.5	462.6	461.7	460.8	461.7	462.6	463.5
127.5°	500.3	500.3	500.4	500.1	499.5	498.8	498.2	497.5	498.2	498.8	499.5
130°	523.3	523.2	523.1	522.7	522.0	521.3	520.7	520.1	520.7	521.3	522.0
132.5°	545.3	545.6	545.9	545.7	544.9	544.2	543.4	542.6	543.4	544.2	544.9
135°	577.5	577.8	578.1	577.8	577.0	576.2	575.4	574.6	575.4	576.2	577.0
137.5°	606.6	606.8	607.0	606.8	606.2	605.5	604.8	604.1	604.8	605.5	606.2
140°	624.2	624.3	624.5	624.4	624.2	623.9	623.6	623.4	623.6	623.9	624.2
142.5°	641.9	641.7	641.5	641.4	641.2	641.0	640.9	640.7	640.9	641.0	641.2
145°	667.4	667.4	667.4	667.3	667.0	666.8	666.5	666.2	666.5	666.8	667.0
147.5°	688.6	688.6	688.4	688.3	688.4	688.4	688.5	688.6	688.5	688.4	688.4
150°	702.1	701.8	701.6	701.6	701.8	702.1	702.3	702.6	702.3	702.1	701.8
152.5°	714.3	714.1	713.8	713.9	714.5	715.1	715.7	716.2	715.7	715.1	714.5
155°	730.9	730.6	730.3	730.6	731.3	732.1	732.9	733.7	732.9	732.1	731.3
157.5°	745.2	745.1	745.1	745.4	745.8	746.3	746.8	747.2	746.8	746.3	745.8
160°	753.4	753.3	753.1	753.5	754.2	755.0	755.8	756.6	755.8	755.0	754.2
162.5°	761.0	760.8	760.7	761.0	761.8	762.6	763.3	764.1	763.3	762.6	761.8
165°	771.0	770.9	770.8	771.1	771.9	772.7	773.4	774.2	773.4	772.7	771.9
167.5°	778.4	778.3	778.2	778.5	779.3	780.1	780.9	781.7	780.9	780.1	779.3
170°	782.2	782.0	781.9	782.3	783.2	784.1	785.1	786.0	785.1	784.1	783.2
172.5°	785.3	785.1	784.8	785.1	786.0	787.0	787.9	788.8	787.9	787.0	786.0
175°	788.6	788.5	788.4	788.7	789.5	790.3	791.1	791.9	791.1	790.3	789.5
177.5°	790.7	790.6	790.4	790.8	791.4	792.0	792.6	793.2	792.6	792.0	791.4
180°	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9



TEST NUMBER: P333406-927

CATALOG NUMBER: S125DIW-S850D770U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2
2.5°	952.4	948.7	945.8	939.2	935.6	930.7	926.7	931.0	926.4	928.4	925.3
5°	922.7	911.2	902.9	891.0	880.7	871.2	864.3	863.0	859.7	858.1	853.1
7.5°	886.9	872.5	858.4	842.8	829.6	816.2	807.6	800.6	795.9	789.7	785.5
10°	865.9	846.5	830.1	811.2	794.7	780.3	768.8	763.0	757.7	749.9	747.0
12.5°	839.9	819.9	799.8	779.6	763.8	747.7	737.8	729.1	725.5	716.6	715.7
15°	808.7	778.7	758.9	738.4	716.5	703.4	695.1	685.7	681.6	675.4	670.9
17.5°	771.5	744.7	720.0	698.7	680.0	668.9	658.7	652.2	645.2	641.1	633.7
20°	744.6	719.1	694.3	671.7	657.4	644.6	636.4	630.2	622.8	620.8	613.3
22.5°	721.8	693.7	670.0	651.0	635.3	620.9	612.0	607.8	602.7	596.4	594.8
25°	684.9	655.7	635.6	616.6	602.6	589.5	583.3	578.0	573.0	568.5	566.8
27.5°	653.0	626.9	602.9	585.8	573.7	561.7	556.2	549.7	546.1	542.5	538.1
30°	630.6	603.9	582.9	566.4	553.3	542.6	536.8	532.3	529.0	525.7	523.2
32.5°	607.5	582.8	562.4	546.4	533.2	525.1	520.0	516.8	513.2	509.2	506.1
35°	577.1	549.9	530.2	516.3	506.0	499.8	494.0	491.2	487.0	487.0	483.7
37.5°	542.8	519.4	501.9	489.2	480.0	474.4	468.2	466.2	463.6	461.8	460.7
40°	522.4	500.6	484.2	471.4	461.5	457.0	452.1	448.8	447.1	445.0	444.3
42.5°	501.4	480.5	464.8	453.0	444.4	440.5	435.9	433.6	430.3	427.6	427.1
45°	469.4	449.2	434.8	425.3	418.0	413.4	410.5	405.6	403.9	400.7	400.2
47.5°	438.9	419.6	405.5	397.8	391.3	387.5	383.0	378.1	376.2	374.5	374.4
50°	416.3	398.6	385.4	378.0	371.9	366.5	361.9	358.7	357.4	357.4	358.3
52.5°	393.2	378.2	367.0	358.0	352.1	346.4	342.2	340.2	338.3	340.3	341.8
55°	359.5	344.3	336.0	327.4	321.7	315.1	313.1	312.2	311.0	314.3	315.9
57.5°	323.8	313.1	303.5	294.9	289.8	286.0	283.2	282.7	284.9	286.5	291.9
60°	301.1	288.8	280.1	273.5	267.4	264.9	264.1	263.2	264.9	269.4	276.4
62.5°	276.1	266.1	256.7	251.8	247.3	243.2	243.0	243.5	246.8	252.0	259.0
65°	239.4	230.8	224.6	218.8	215.2	212.7	213.5	215.2	218.8	225.9	233.6
67.5°	202.2	196.2	190.7	186.0	182.4	182.4	183.3	185.8	190.1	198.2	205.3
70°	178.1	171.5	167.0	164.9	162.1	160.4	162.9	167.0	170.7	178.1	184.3
72.5°	154.1	148.5	145.0	143.5	142.4	141.0	141.8	146.2	151.3	158.7	165.9
75°	118.4	116.4	113.9	112.3	111.1	111.9	112.7	116.8	121.0	128.7	137.0
77.5°	86.4	84.3	82.9	82.5	81.8	82.1	84.5	87.5	91.6	97.3	103.5
80°	65.4	64.6	63.8	63.4	63.4	63.8	67.0	69.1	72.8	78.2	83.1
82.5°	47.6	47.1	47.0	46.9	47.2	47.3	49.3	52.0	55.1	59.1	63.4
85°	25.1	24.2	25.5	25.9	25.1	26.3	27.2	28.8	30.0	32.1	34.1
87.5°	9.2	10.1	9.9	10.4	10.6	11.4	11.2	12.7	13.5	14.3	14.0
90°	4.8	5.7	6.7	7.6	8.5	9.4	10.1	10.7	11.3	12.0	12.5
92.5°	6.1	6.2	7.0	7.8	8.6	9.4	10.1	10.7	11.3	12.0	12.4
95°	31.9	29.2	24.2	19.3	14.3	9.4	10.1	10.7	11.3	12.0	12.4
97.5°	72.6	68.1	58.3	48.5	38.7	28.9	25.2	21.5	17.8	14.2	12.4
100°	99.6	100.1	100.6	101.1	101.6	102.1	82.7	63.3	43.8	24.4	14.4
102.5°	128.7	129.0	129.4	129.7	130.0	130.3	126.7	122.9	119.3	115.6	109.3
105°	174.7	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.8
107.5°	220.2	220.4	220.6	220.9	221.2	221.4	221.4	221.5	221.5	221.5	221.3
110°	251.2	251.4	251.6	251.9	252.2	252.4	252.0	251.6	251.2	250.8	250.7



TEST NUMBER: P333406-927

CATALOG NUMBER: S125DIW-S850D770U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	281.6	281.9	282.0	282.2	282.3	282.5	281.9	281.5	281.0	280.4	280.1
115°	326.6	327.0	327.2	327.3	327.4	327.6	327.0	326.5	326.0	325.4	324.8
117.5°	369.1	369.3	369.9	370.3	370.8	371.3	370.7	369.9	369.3	368.6	368.1
120°	396.9	397.0	397.4	397.8	398.2	398.5	398.3	398.1	397.8	397.5	397.0
122.5°	424.3	424.6	424.8	424.9	425.2	425.3	425.1	424.8	424.5	424.3	423.7
125°	464.5	464.9	464.9	464.9	464.9	464.9	464.4	463.8	463.3	462.8	462.3
127.5°	500.1	500.4	500.3	500.3	500.2	500.1	499.8	499.6	499.2	499.0	498.4
130°	522.7	523.1	523.2	523.3	523.5	523.6	523.2	522.8	522.4	522.0	521.5
132.5°	545.7	545.9	545.6	545.3	545.0	544.7	544.6	544.5	544.5	544.4	544.1
135°	577.8	578.1	577.8	577.5	577.3	577.0	576.7	576.5	576.2	576.0	575.4
137.5°	606.8	607.0	606.8	606.6	606.3	606.1	606.2	606.3	606.3	606.3	606.0
140°	624.4	624.5	624.3	624.2	624.1	623.9	624.2	624.5	624.7	625.0	624.7
142.5°	641.4	641.5	641.7	641.9	642.1	642.3	642.3	642.4	642.5	642.5	642.1
145°	667.3	667.4	667.4	667.4	667.4	667.4	667.5	667.7	667.8	667.9	667.6
147.5°	688.3	688.4	688.6	688.6	688.8	689.0	689.1	689.3	689.4	689.6	689.2
150°	701.6	701.6	701.8	702.1	702.3	702.6	702.9	703.1	703.4	703.7	703.3
152.5°	713.9	713.8	714.1	714.3	714.5	714.8	715.1	715.3	715.6	715.9	715.5
155°	730.6	730.3	730.6	730.9	731.1	731.3	731.7	732.1	732.5	732.9	732.6
157.5°	745.4	745.1	745.1	745.2	745.2	745.2	745.7	746.1	746.5	746.9	746.6
160°	753.5	753.1	753.3	753.4	753.5	753.7	754.2	754.7	755.3	755.7	755.5
162.5°	761.0	760.7	760.8	761.0	761.0	761.2	761.9	762.6	763.3	764.1	763.9
165°	771.1	770.8	770.9	771.0	771.2	771.3	772.1	772.9	773.6	774.4	774.3
167.5°	778.5	778.2	778.3	778.4	778.6	778.7	779.6	780.5	781.5	782.4	782.4
170°	782.3	781.9	782.0	782.2	782.3	782.4	783.5	784.5	785.6	786.6	786.6
172.5°	785.1	784.8	785.1	785.3	785.5	785.8	786.6	787.6	788.5	789.5	789.3
175°	788.7	788.4	788.5	788.6	788.8	788.9	790.0	791.0	792.0	793.1	793.0
177.5°	790.8	790.4	790.6	790.7	790.8	790.9	791.6	792.3	793.1	793.8	793.8
180°	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9



TEST NUMBER: P333406-927

CATALOG NUMBER: S125DIW-S850D770U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2
2.5°	923.4	925.7	923.7	926.4	923.7	925.7	923.4	925.3	928.4	926.4	931.0
5°	851.0	847.4	849.9	848.2	849.9	847.4	851.0	853.1	858.1	859.7	863.0
7.5°	784.3	780.7	776.7	774.8	776.7	780.7	784.3	785.5	789.7	795.9	800.6
10°	742.5	737.9	737.5	734.7	737.5	737.9	742.5	747.0	749.9	757.7	763.0
12.5°	711.9	707.7	703.0	701.8	703.0	707.7	711.9	715.7	716.6	725.5	729.1
15°	668.4	665.1	662.3	664.7	662.3	665.1	668.4	670.9	675.4	681.6	685.7
17.5°	632.3	629.6	629.1	626.1	629.1	629.6	632.3	633.7	641.1	645.2	652.2
20°	609.6	607.5	608.4	603.0	608.4	607.5	609.6	613.3	620.8	622.8	630.2
22.5°	591.5	587.5	587.0	585.9	587.0	587.5	591.5	594.8	596.4	602.7	607.8
25°	563.2	561.1	559.0	561.1	559.0	561.1	563.2	566.8	568.5	573.0	578.0
27.5°	538.4	535.9	535.4	535.6	535.4	535.9	538.4	538.1	542.5	546.1	549.7
30°	523.2	519.1	519.5	519.1	519.5	519.1	523.2	523.2	525.7	529.0	532.3
32.5°	506.8	504.0	503.4	502.6	503.4	504.0	506.8	506.1	509.2	513.2	516.8
35°	482.5	482.5	480.5	480.5	480.5	482.5	482.5	483.7	487.0	487.0	491.2
37.5°	459.7	459.3	458.0	458.3	458.0	459.3	459.7	460.7	461.8	463.6	466.2
40°	442.6	442.2	440.9	438.5	440.9	442.2	442.6	444.3	445.0	447.1	448.8
42.5°	426.1	424.8	424.2	423.3	424.2	424.8	426.1	427.1	427.6	430.3	433.6
45°	400.2	400.2	399.4	399.0	399.4	400.2	400.2	400.2	400.7	403.9	405.6
47.5°	375.1	375.8	377.4	377.2	377.4	375.8	375.1	374.4	374.5	376.2	378.1
50°	359.9	360.4	361.6	361.9	361.6	360.4	359.9	358.3	357.4	357.4	358.7
52.5°	343.2	345.5	347.1	346.8	347.1	345.5	343.2	341.8	340.3	338.3	340.2
55°	319.6	322.5	325.3	325.8	325.3	322.5	319.6	315.9	314.3	311.0	312.2
57.5°	296.4	300.4	303.4	304.4	303.4	300.4	296.4	291.9	286.5	284.9	282.7
60°	280.5	285.9	289.6	291.2	289.6	285.9	280.5	276.4	269.4	264.9	263.2
62.5°	265.4	271.4	275.1	275.4	275.1	271.4	265.4	259.0	252.0	246.8	243.5
65°	240.7	246.8	250.1	252.5	250.1	246.8	240.7	233.6	225.9	218.8	215.2
67.5°	214.0	220.1	223.8	225.8	223.8	220.1	214.0	205.3	198.2	190.1	185.8
70°	194.6	200.7	205.7	207.3	205.7	200.7	194.6	184.3	178.1	170.7	167.0
72.5°	175.5	181.0	185.0	186.9	185.0	181.0	175.5	165.9	158.7	151.3	146.2
75°	142.4	149.7	153.4	155.5	153.4	149.7	142.4	137.0	128.7	121.0	116.8
77.5°	109.7	116.5	118.7	119.8	118.7	116.5	109.7	103.5	97.3	91.6	87.5
80°	88.0	92.1	95.0	95.5	95.0	92.1	88.0	83.1	78.2	72.8	69.1
82.5°	67.7	71.1	72.0	73.0	72.0	71.1	67.7	63.4	59.1	55.1	52.0
85°	37.0	38.7	39.1	38.7	39.1	38.7	37.0	34.1	32.1	30.0	28.8
87.5°	14.7	14.5	14.6	15.3	14.6	14.5	14.7	14.0	14.3	13.5	12.7
90°	12.9	13.3	13.7	14.1	13.7	13.3	12.9	12.5	12.0	11.3	10.7
92.5°	12.6	12.8	13.0	13.2	13.0	12.8	12.6	12.4	12.0	11.3	10.7
95°	12.4	12.4	12.4	12.4	12.4	12.4	12.4	12.4	12.0	11.3	10.7
97.5°	12.4	12.4	12.4	12.4	12.4	12.4	12.4	12.4	14.2	17.8	21.5
100°	13.9	13.4	12.8	12.4	12.8	13.4	13.9	14.4	24.4	43.8	63.3
102.5°	100.4	91.6	82.7	73.8	82.7	91.6	100.4	109.3	115.6	119.3	122.9
105°	174.8	174.6	174.4	174.4	174.4	174.6	174.8	174.8	174.9	174.9	174.9
107.5°	220.9	220.5	220.1	219.8	220.1	220.5	220.9	221.3	221.5	221.5	221.5
110°	250.8	251.0	251.1	251.2	251.1	251.0	250.8	250.7	250.8	251.2	251.6



TEST NUMBER: P333406-927

CATALOG NUMBER: S125DIW-S850D770U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	280.0	279.8	279.6	279.4	279.6	279.8	280.0	280.1	280.4	281.0	281.5
115°	324.0	323.2	322.4	321.6	322.4	323.2	324.0	324.8	325.4	326.0	326.5
117.5°	367.7	367.4	367.1	366.8	367.1	367.4	367.7	368.1	368.6	369.3	369.9
120°	396.4	395.8	395.1	394.4	395.1	395.8	396.4	397.0	397.5	397.8	398.1
122.5°	423.0	422.2	421.5	420.7	421.5	422.2	423.0	423.7	424.3	424.5	424.8
125°	461.9	461.5	461.2	460.8	461.2	461.5	461.9	462.3	462.8	463.3	463.8
127.5°	497.3	496.4	495.4	494.5	495.4	496.4	497.3	498.4	499.0	499.2	499.6
130°	520.9	520.2	519.5	518.9	519.5	520.2	520.9	521.5	522.0	522.4	522.8
132.5°	543.4	542.7	542.1	541.5	542.1	542.7	543.4	544.1	544.4	544.5	544.5
135°	574.6	573.9	573.1	572.3	573.1	573.9	574.6	575.4	576.0	576.2	576.5
137.5°	605.3	604.7	604.0	603.3	604.0	604.7	605.3	606.0	606.3	606.3	606.3
140°	623.9	623.2	622.4	621.6	622.4	623.2	623.9	624.7	625.0	624.7	624.5
142.5°	641.4	640.6	639.8	639.0	639.8	640.6	641.4	642.1	642.5	642.5	642.4
145°	666.8	666.0	665.3	664.5	665.3	666.0	666.8	667.6	667.9	667.8	667.7
147.5°	688.3	687.4	686.4	685.5	686.4	687.4	688.3	689.2	689.6	689.4	689.3
150°	702.2	701.2	700.1	699.1	700.1	701.2	702.2	703.3	703.7	703.4	703.1
152.5°	714.5	713.7	712.7	711.8	712.7	713.7	714.5	715.5	715.9	715.6	715.3
155°	731.6	730.6	729.5	728.4	729.5	730.6	731.6	732.6	732.9	732.5	732.1
157.5°	745.5	744.5	743.5	742.4	743.5	744.5	745.5	746.6	746.9	746.5	746.1
160°	754.5	753.4	752.4	751.3	752.4	753.4	754.5	755.5	755.7	755.3	754.7
162.5°	762.8	761.6	760.5	759.3	760.5	761.6	762.8	763.9	764.1	763.3	762.6
165°	773.2	772.2	771.2	770.1	771.2	772.2	773.2	774.3	774.4	773.6	772.9
167.5°	781.2	780.0	778.8	777.6	778.8	780.0	781.2	782.4	782.4	781.5	780.5
170°	785.4	784.2	783.0	781.9	783.0	784.2	785.4	786.6	786.6	785.6	784.5
172.5°	788.2	787.0	785.8	784.7	785.8	787.0	788.2	789.3	789.5	788.5	787.6
175°	791.9	790.7	789.5	788.3	789.5	790.7	791.9	793.0	793.1	792.0	791.0
177.5°	792.9	792.1	791.2	790.4	791.2	792.1	792.9	793.8	793.8	793.1	792.3
180°	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9



TEST NUMBER: P333406-927

CATALOG NUMBER: S125DIW-S850D770U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2
2.5°	926.7	930.7	935.6	939.2	945.8	948.7	952.4	955.3	960.6	965.5	971.5
5°	864.3	871.2	880.7	891.0	902.9	911.2	922.7	929.6	943.6	956.4	968.7
7.5°	807.6	816.2	829.6	842.8	858.4	872.5	886.9	902.9	920.8	941.8	959.3
10°	768.8	780.3	794.7	811.2	830.1	846.5	865.9	883.1	905.0	929.6	952.7
12.5°	737.8	747.7	763.8	779.6	799.8	819.9	839.9	862.8	888.2	915.5	944.4
15°	695.1	703.4	716.5	738.4	758.9	778.7	808.7	830.1	862.2	892.6	927.6
17.5°	658.7	668.9	680.0	698.7	720.0	744.7	771.5	798.4	829.3	867.8	907.3
20°	636.4	644.6	657.4	671.7	694.3	719.1	744.6	771.7	809.5	849.5	891.8
22.5°	612.0	620.9	635.3	651.0	670.0	693.7	721.8	751.6	791.1	830.4	876.3
25°	583.3	589.5	602.6	616.6	635.6	655.7	684.9	717.8	756.9	801.7	848.6
27.5°	556.2	561.7	573.7	585.8	602.9	626.9	653.0	686.2	723.0	768.5	820.5
30°	536.8	542.6	553.3	566.4	582.9	603.9	630.6	661.9	701.3	745.8	800.1
32.5°	520.0	525.1	533.2	546.4	562.4	582.8	607.5	639.4	679.0	724.1	777.4
35°	494.0	499.8	506.0	516.3	530.2	549.9	577.1	607.1	645.0	688.6	737.5
37.5°	468.2	474.4	480.0	489.2	501.9	519.4	542.8	574.1	608.3	650.3	697.3
40°	452.1	457.0	461.5	471.4	484.2	500.6	522.4	550.4	586.6	625.7	664.7
42.5°	435.9	440.5	444.4	453.0	464.8	480.5	501.4	528.6	562.2	598.7	633.1
45°	410.5	413.4	418.0	425.3	434.8	449.2	469.4	493.6	522.0	556.6	582.5
47.5°	383.0	387.5	391.3	397.8	405.5	419.6	438.9	459.6	485.4	511.0	529.3
50°	361.9	366.5	371.9	378.0	385.4	398.6	416.3	437.3	459.1	478.8	494.4
52.5°	342.2	346.4	352.1	358.0	367.0	378.2	393.2	411.9	433.4	447.6	460.6
55°	313.1	315.1	321.7	327.4	336.0	344.3	359.5	376.0	389.1	399.8	410.5
57.5°	283.2	286.0	289.8	294.9	303.5	313.1	323.8	338.3	346.1	351.6	359.9
60°	264.1	264.9	267.4	273.5	280.1	288.8	301.1	311.4	317.1	321.7	328.7
62.5°	243.0	243.2	247.3	251.8	256.7	266.1	276.1	284.4	289.1	291.4	298.1
65°	213.5	212.7	215.2	218.8	224.6	230.8	239.4	246.8	246.4	248.8	252.9
67.5°	183.3	182.4	182.4	186.0	190.7	196.2	202.2	206.4	206.5	209.8	211.8
70°	162.9	160.4	162.1	164.9	167.0	171.5	178.1	179.7	180.1	181.8	183.9
72.5°	141.8	141.0	142.4	143.5	145.0	148.5	154.1	155.1	155.2	156.1	159.5
75°	112.7	111.9	111.1	112.3	113.9	116.4	118.4	120.1	119.7	120.1	122.6
77.5°	84.5	82.1	81.8	82.5	82.9	84.3	86.4	86.3	86.7	86.7	89.4
80°	67.0	63.8	63.4	63.4	63.8	64.6	65.4	66.2	65.0	66.2	67.0
82.5°	49.3	47.3	47.2	46.9	47.0	47.1	47.6	48.2	47.8	48.5	49.0
85°	27.2	26.3	25.1	25.9	25.5	24.2	25.1	23.8	23.4	23.8	24.2
87.5°	11.2	11.4	10.6	10.4	9.9	10.1	9.2	8.6	8.1	8.2	9.0
90°	10.1	9.4	8.5	7.6	6.7	5.7	4.8	3.7	2.7	1.7	0.6
92.5°	10.1	9.4	8.6	7.8	7.0	6.2	6.1	6.8	7.6	8.3	9.0
95°	10.1	9.4	14.3	19.3	24.2	29.2	31.9	32.3	32.6	33.0	33.4
97.5°	25.2	28.9	38.7	48.5	58.3	68.1	72.6	71.9	71.3	70.6	69.9
100°	82.7	102.1	101.6	101.1	100.6	100.1	99.6	99.2	98.8	98.4	98.0
102.5°	126.7	130.3	130.0	129.7	129.4	129.0	128.7	128.2	127.7	127.1	126.7
105°	174.9	174.9	174.9	174.9	174.9	174.9	174.7	174.1	173.6	173.1	172.5
107.5°	221.4	221.4	221.2	220.9	220.6	220.4	220.2	220.2	220.2	220.2	220.2
110°	252.0	252.4	252.2	251.9	251.6	251.4	251.2	251.2	251.2	251.2	251.2



TEST NUMBER: P333406-927

CATALOG NUMBER: S125DIW-S850D770U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	281.9	282.5	282.3	282.2	282.0	281.9	281.6	281.3	281.0	280.7	280.4
115°	327.0	327.6	327.4	327.3	327.2	327.0	326.6	326.0	325.3	324.6	324.0
117.5°	370.7	371.3	370.8	370.3	369.9	369.3	369.1	369.2	369.2	369.2	369.2
120°	398.3	398.5	398.2	397.8	397.4	397.0	396.9	397.0	397.1	397.3	397.4
122.5°	425.1	425.3	425.2	424.9	424.8	424.6	424.3	423.7	423.3	422.8	422.2
125°	464.4	464.9	464.9	464.9	464.9	464.9	464.5	463.5	462.6	461.7	460.8
127.5°	499.8	500.1	500.2	500.3	500.3	500.4	500.1	499.5	498.8	498.2	497.5
130°	523.2	523.6	523.5	523.3	523.2	523.1	522.7	522.0	521.3	520.7	520.1
132.5°	544.6	544.7	545.0	545.3	545.6	545.9	545.7	544.9	544.2	543.4	542.6
135°	576.7	577.0	577.3	577.5	577.8	578.1	577.8	577.0	576.2	575.4	574.6
137.5°	606.2	606.1	606.3	606.6	606.8	607.0	606.8	606.2	605.5	604.8	604.1
140°	624.2	623.9	624.1	624.2	624.3	624.5	624.4	624.2	623.9	623.6	623.4
142.5°	642.3	642.3	642.1	641.9	641.7	641.5	641.4	641.2	641.0	640.9	640.7
145°	667.5	667.4	667.4	667.4	667.4	667.4	667.3	667.0	666.8	666.5	666.2
147.5°	689.1	689.0	688.8	688.6	688.6	688.4	688.3	688.4	688.4	688.5	688.6
150°	702.9	702.6	702.3	702.1	701.8	701.6	701.6	701.8	702.1	702.3	702.6
152.5°	715.1	714.8	714.5	714.3	714.1	713.8	713.9	714.5	715.1	715.7	716.2
155°	731.7	731.3	731.1	730.9	730.6	730.3	730.6	731.3	732.1	732.9	733.7
157.5°	745.7	745.2	745.2	745.2	745.1	745.1	745.4	745.8	746.3	746.8	747.2
160°	754.2	753.7	753.5	753.4	753.3	753.1	753.5	754.2	755.0	755.8	756.6
162.5°	761.9	761.2	761.0	761.0	760.8	760.7	761.0	761.8	762.6	763.3	764.1
165°	772.1	771.3	771.2	771.0	770.9	770.8	771.1	771.9	772.7	773.4	774.2
167.5°	779.6	778.7	778.6	778.4	778.3	778.2	778.5	779.3	780.1	780.9	781.7
170°	783.5	782.4	782.3	782.2	782.0	781.9	782.3	783.2	784.1	785.1	786.0
172.5°	786.6	785.8	785.5	785.3	785.1	784.8	785.1	786.0	787.0	787.9	788.8
175°	790.0	788.9	788.8	788.6	788.5	788.4	788.7	789.5	790.3	791.1	791.9
177.5°	791.6	790.9	790.8	790.7	790.6	790.4	790.8	791.4	792.0	792.6	793.2
180°	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9



TEST NUMBER: P333406-927

CATALOG NUMBER: S125DIW-S850D770U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2
2.5°	974.4	979.0	982.0	987.5	992.1	994.8	997.1	999.1	1001.4	1003.4	1008.9
5°	980.6	991.3	1000.4	1014.4	1027.1	1037.0	1047.7	1057.2	1065.0	1076.1	1084.7
7.5°	977.9	997.0	1016.8	1038.5	1060.6	1081.2	1100.1	1117.8	1133.9	1153.3	1170.3
10°	975.3	1001.2	1026.7	1055.9	1085.9	1111.4	1135.3	1159.6	1177.3	1202.0	1222.9
12.5°	973.4	1003.9	1034.6	1069.8	1102.7	1138.8	1170.5	1188.2	1215.1	1234.9	1259.8
15°	965.0	1005.4	1047.7	1087.2	1134.1	1167.4	1195.4	1229.9	1255.0	1280.1	1307.3
17.5°	950.1	995.8	1043.1	1095.0	1140.0	1175.7	1211.7	1245.1	1275.0	1308.7	1342.4
20°	943.3	988.9	1043.1	1096.2	1140.3	1177.7	1214.7	1251.3	1284.2	1327.4	1366.5
22.5°	928.8	984.0	1034.0	1085.7	1131.0	1171.8	1213.7	1255.3	1299.0	1347.8	1396.8
25°	902.9	958.9	1011.9	1063.0	1108.6	1159.6	1204.4	1260.0	1315.9	1380.5	1441.4
27.5°	876.1	929.6	978.3	1027.5	1080.8	1138.5	1196.7	1259.7	1332.9	1414.4	1500.3
30°	854.4	905.0	952.3	1002.8	1058.4	1123.4	1187.2	1262.0	1346.7	1438.4	1540.5
32.5°	829.0	875.7	921.6	975.3	1035.7	1104.3	1178.6	1260.7	1362.6	1466.8	1571.8
35°	785.7	824.7	872.0	929.2	997.5	1076.1	1162.1	1259.1	1375.9	1495.6	1584.1
37.5°	734.3	770.6	820.5	883.1	954.7	1039.0	1141.1	1256.2	1380.3	1475.8	1504.3
40°	699.7	733.4	785.3	850.2	923.4	1012.7	1124.6	1246.3	1366.5	1427.4	1403.9
42.5°	662.8	698.2	748.7	813.1	891.9	989.0	1103.9	1225.7	1326.4	1349.4	1268.4
45°	604.7	641.3	691.0	756.1	840.8	946.1	1065.8	1176.5	1234.5	1192.9	1067.5
47.5°	550.6	584.9	631.1	698.2	785.6	894.5	1009.8	1098.0	1102.6	1003.5	869.5
50°	513.8	545.4	591.9	658.9	745.8	856.0	960.0	1029.6	998.3	886.1	757.2
52.5°	477.6	508.6	554.4	620.8	706.6	807.6	904.4	953.2	894.4	779.1	669.1
55°	425.3	452.5	497.3	558.6	640.1	733.9	816.1	833.0	756.5	642.9	553.7
57.5°	374.3	399.7	440.5	496.9	571.3	654.4	718.7	715.2	634.3	536.9	466.0
60°	339.8	364.5	400.7	455.7	523.6	595.2	650.3	637.2	557.0	473.0	413.4
62.5°	308.9	330.9	365.1	413.3	475.2	541.6	586.8	567.4	488.9	415.4	368.3
65°	263.2	281.8	311.0	352.1	403.5	458.3	493.2	468.1	401.1	343.9	306.0
67.5°	219.8	234.6	259.0	291.9	335.7	379.7	401.0	375.7	322.1	280.4	252.3
70°	192.1	205.3	224.2	253.4	291.7	328.7	344.7	322.1	276.0	240.2	220.1
72.5°	164.5	175.3	191.9	218.2	248.8	281.0	295.0	273.4	235.5	205.3	186.5
75°	127.1	134.5	146.0	164.1	188.4	213.9	221.7	202.8	178.6	155.9	143.5
77.5°	91.0	97.3	106.0	117.4	134.6	150.8	157.6	146.7	127.9	113.6	103.5
80°	69.9	73.2	80.6	90.1	103.7	113.9	118.4	111.5	98.3	87.6	79.8
82.5°	49.8	53.2	57.6	65.4	74.1	81.0	85.9	81.2	71.7	63.3	58.7
85°	24.2	26.3	28.8	32.1	38.7	42.8	42.4	39.5	35.8	32.5	30.0
87.5°	8.9	9.4	10.6	12.4	13.6	15.1	16.0	15.5	14.4	13.5	12.7
90°	1.7	2.7	3.7	4.8	5.7	6.7	7.6	8.5	9.4	10.1	10.7
92.5°	8.3	7.6	6.8	6.1	6.2	7.0	7.8	8.6	9.4	10.1	10.7
95°	33.0	32.6	32.3	31.9	29.2	24.2	19.3	14.3	9.4	10.1	10.7
97.5°	70.6	71.3	71.9	72.6	68.1	58.3	48.5	38.7	28.9	25.2	21.5
100°	98.4	98.8	99.2	99.6	100.1	100.6	101.1	101.6	102.1	82.7	63.3
102.5°	127.1	127.7	128.2	128.7	129.0	129.4	129.7	130.0	130.3	126.7	122.9
105°	173.1	173.6	174.1	174.7	174.9	174.9	174.9	174.9	174.9	174.9	174.9
107.5°	220.2	220.2	220.2	220.2	220.4	220.6	220.9	221.2	221.4	221.4	221.5
110°	251.2	251.2	251.2	251.2	251.4	251.6	251.9	252.2	252.4	252.0	251.6



TEST NUMBER: P333406-927

CATALOG NUMBER: S125DIW-S850D770U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	280.7	281.0	281.3	281.6	281.9	282.0	282.2	282.3	282.5	281.9	281.5
115°	324.6	325.3	326.0	326.6	327.0	327.2	327.3	327.4	327.6	327.0	326.5
117.5°	369.2	369.2	369.2	369.1	369.3	369.9	370.3	370.8	371.3	370.7	369.9
120°	397.3	397.1	397.0	396.9	397.0	397.4	397.8	398.2	398.5	398.3	398.1
122.5°	422.8	423.3	423.7	424.3	424.6	424.8	424.9	425.2	425.3	425.1	424.8
125°	461.7	462.6	463.5	464.5	464.9	464.9	464.9	464.9	464.9	464.4	463.8
127.5°	498.2	498.8	499.5	500.1	500.4	500.3	500.3	500.2	500.1	499.8	499.6
130°	520.7	521.3	522.0	522.7	523.1	523.2	523.3	523.5	523.6	523.2	522.8
132.5°	543.4	544.2	544.9	545.7	545.9	545.6	545.3	545.0	544.7	544.6	544.5
135°	575.4	576.2	577.0	577.8	578.1	577.8	577.5	577.3	577.0	576.7	576.5
137.5°	604.8	605.5	606.2	606.8	607.0	606.8	606.6	606.3	606.1	606.2	606.3
140°	623.6	623.9	624.2	624.4	624.5	624.3	624.2	624.1	623.9	624.2	624.5
142.5°	640.9	641.0	641.2	641.4	641.5	641.7	641.9	642.1	642.3	642.3	642.4
145°	666.5	666.8	667.0	667.3	667.4	667.4	667.4	667.4	667.4	667.5	667.7
147.5°	688.5	688.4	688.4	688.3	688.4	688.6	688.6	688.8	689.0	689.1	689.3
150°	702.3	702.1	701.8	701.6	701.6	701.8	702.1	702.3	702.6	702.9	703.1
152.5°	715.7	715.1	714.5	713.9	713.8	714.1	714.3	714.5	714.8	715.1	715.3
155°	732.9	732.1	731.3	730.6	730.3	730.6	730.9	731.1	731.3	731.7	732.1
157.5°	746.8	746.3	745.8	745.4	745.1	745.1	745.2	745.2	745.2	745.7	746.1
160°	755.8	755.0	754.2	753.5	753.1	753.3	753.4	753.5	753.7	754.2	754.7
162.5°	763.3	762.6	761.8	761.0	760.7	760.8	761.0	761.0	761.2	761.9	762.6
165°	773.4	772.7	771.9	771.1	770.8	770.9	771.0	771.2	771.3	772.1	772.9
167.5°	780.9	780.1	779.3	778.5	778.2	778.3	778.4	778.6	778.7	779.6	780.5
170°	785.1	784.1	783.2	782.3	781.9	782.0	782.2	782.3	782.4	783.5	784.5
172.5°	787.9	787.0	786.0	785.1	784.8	785.1	785.3	785.5	785.8	786.6	787.6
175°	791.1	790.3	789.5	788.7	788.4	788.5	788.6	788.8	788.9	790.0	791.0
177.5°	792.6	792.0	791.4	790.8	790.4	790.6	790.7	790.8	790.9	791.6	792.3
180°	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9



TEST NUMBER: P333406-927

CATALOG NUMBER: S125DIW-S850D770U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	969.2	969.2	969.2	969.2	969.2	969.2	969.2
2.5°	1013.5	1016.2	1021.8	1019.8	1022.5	1023.7	1025.1
5°	1095.4	1108.6	1114.4	1113.5	1122.1	1120.1	1118.0
7.5°	1187.9	1201.7	1209.4	1219.1	1224.6	1225.0	1229.9
10°	1240.2	1258.3	1265.7	1276.0	1282.5	1286.3	1285.9
12.5°	1280.3	1294.5	1311.1	1316.1	1325.0	1329.7	1328.0
15°	1328.6	1351.3	1368.6	1377.2	1388.3	1391.5	1396.1
17.5°	1371.7	1402.1	1422.3	1449.1	1459.2	1465.4	1461.7
20°	1404.3	1444.2	1464.4	1496.5	1514.2	1523.6	1520.4
22.5°	1442.8	1486.1	1523.3	1551.1	1578.0	1590.8	1593.4
25°	1508.8	1568.0	1622.8	1659.4	1692.7	1700.5	1717.8
27.5°	1582.5	1652.4	1710.9	1749.4	1772.6	1781.3	1786.7
30°	1629.0	1698.4	1742.5	1767.1	1774.6	1773.7	1772.9
32.5°	1651.6	1695.2	1703.6	1696.7	1679.7	1665.5	1650.5
35°	1619.5	1587.0	1538.4	1475.9	1429.8	1383.4	1378.8
37.5°	1456.5	1352.6	1271.8	1181.5	1129.5	1097.3	1075.1
40°	1303.1	1185.1	1087.2	1011.1	958.0	937.1	916.5
42.5°	1136.6	1023.8	937.2	873.5	833.6	810.3	794.1
45°	923.4	823.9	756.1	710.0	678.3	660.2	649.9
47.5°	756.7	683.1	625.4	592.2	570.3	556.2	556.3
50°	667.2	596.8	558.6	532.3	513.3	502.2	504.3
52.5°	587.9	535.4	502.6	480.6	466.6	459.8	459.5
55°	491.5	453.7	432.3	416.3	406.8	399.0	400.7
57.5°	420.5	388.6	374.2	360.9	354.3	351.2	346.7
60°	376.4	351.7	339.4	328.7	322.1	319.6	315.1
62.5°	337.2	317.8	305.8	297.1	291.1	290.3	286.8
65°	283.4	268.6	257.9	253.8	247.6	246.0	246.0
67.5°	233.6	223.0	214.8	211.0	208.2	208.7	206.7
70°	202.4	193.8	188.4	184.3	182.2	182.6	181.0
72.5°	177.1	167.4	162.7	160.3	157.6	158.6	158.0
75°	134.1	129.1	126.7	124.2	122.6	121.8	121.0
77.5°	98.5	94.1	92.2	90.9	91.1	89.1	90.6
80°	76.1	72.4	71.1	69.1	68.7	68.7	68.3
82.5°	55.7	53.6	52.8	51.0	50.3	50.9	49.8
85°	28.8	27.2	26.8	26.8	25.9	25.1	27.2
87.5°	12.8	11.6	11.7	11.5	11.6	11.3	10.7
90°	11.3	12.0	12.5	12.9	13.3	13.7	14.1
92.5°	11.3	12.0	12.4	12.6	12.8	13.0	13.2
95°	11.3	12.0	12.4	12.4	12.4	12.4	12.4
97.5°	17.8	14.2	12.4	12.4	12.4	12.4	12.4
100°	43.8	24.4	14.4	13.9	13.4	12.8	12.4
102.5°	119.3	115.6	109.3	100.4	91.6	82.7	73.8
105°	174.9	174.9	174.8	174.8	174.6	174.4	174.4
107.5°	221.5	221.5	221.3	220.9	220.5	220.1	219.8
110°	251.2	250.8	250.7	250.8	251.0	251.1	251.2



TEST NUMBER: P333406-927

CATALOG NUMBER: S125DIW-S850D770U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	281.0	280.4	280.1	280.0	279.8	279.6	279.4
115°	326.0	325.4	324.8	324.0	323.2	322.4	321.6
117.5°	369.3	368.6	368.1	367.7	367.4	367.1	366.8
120°	397.8	397.5	397.0	396.4	395.8	395.1	394.4
122.5°	424.5	424.3	423.7	423.0	422.2	421.5	420.7
125°	463.3	462.8	462.3	461.9	461.5	461.2	460.8
127.5°	499.2	499.0	498.4	497.3	496.4	495.4	494.5
130°	522.4	522.0	521.5	520.9	520.2	519.5	518.9
132.5°	544.5	544.4	544.1	543.4	542.7	542.1	541.5
135°	576.2	576.0	575.4	574.6	573.9	573.1	572.3
137.5°	606.3	606.3	606.0	605.3	604.7	604.0	603.3
140°	624.7	625.0	624.7	623.9	623.2	622.4	621.6
142.5°	642.5	642.5	642.1	641.4	640.6	639.8	639.0
145°	667.8	667.9	667.6	666.8	666.0	665.3	664.5
147.5°	689.4	689.6	689.2	688.3	687.4	686.4	685.5
150°	703.4	703.7	703.3	702.2	701.2	700.1	699.1
152.5°	715.6	715.9	715.5	714.5	713.7	712.7	711.8
155°	732.5	732.9	732.6	731.6	730.6	729.5	728.4
157.5°	746.5	746.9	746.6	745.5	744.5	743.5	742.4
160°	755.3	755.7	755.5	754.5	753.4	752.4	751.3
162.5°	763.3	764.1	763.9	762.8	761.6	760.5	759.3
165°	773.6	774.4	774.3	773.2	772.2	771.2	770.1
167.5°	781.5	782.4	782.4	781.2	780.0	778.8	777.6
170°	785.6	786.6	786.6	785.4	784.2	783.0	781.9
172.5°	788.5	789.5	789.3	788.2	787.0	785.8	784.7
175°	792.0	793.1	793.0	791.9	790.7	789.5	788.3
177.5°	793.1	793.8	793.8	792.9	792.1	791.2	790.4
180°	791.9	791.9	791.9	791.9	791.9	791.9	791.9

(END OF REPORT)