

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333077-840

Luminaire Tested: **S124RDIW-S1020D470U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333077-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S1020D470U840-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 470 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6107.6 lumens  
Efficiency: N/A  
Efficacy: 132.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 46.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333077-840

CATALOG NUMBER: S124RDIW-S1020D470U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333077-840

CATALOG NUMBER: S124RDIW-S1020D470U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	74	74	74	69
1	102	98	94	91	97	93	89	86	83	80	78	74	72	70	66	64	63	59
2	94	86	80	75	88	82	76	72	73	69	65	65	62	59	58	56	54	50
3	86	76	69	63	81	72	66	60	65	60	55	58	54	51	52	49	46	43
4	79	68	60	54	74	64	57	51	58	52	48	52	47	44	47	43	40	37
5	72	61	52	46	68	58	50	45	52	46	41	47	42	38	42	38	35	32
6	67	55	46	40	63	52	44	39	47	41	36	43	38	34	38	34	31	28
7	62	49	41	36	58	47	40	35	43	37	32	39	34	30	35	31	28	25
8	58	45	37	32	54	43	36	31	39	33	29	36	31	27	32	28	25	23
9	54	41	34	29	51	40	33	28	36	30	26	33	28	24	30	26	23	21
10	50	38	31	26	48	36	30	25	33	28	24	31	26	22	28	24	21	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14721	14721	14721
5°	14755	14574	14665
10°	14662	14399	14399
15°	14493	14097	13992
20°	14262	13698	13447
25°	13967	13233	12897
30°	13679	12743	12209
35°	13361	12232	11517
40°	12978	11653	10771
45°	12625	11079	10011
50°	12223	10417	9207
55°	11792	9728	8332
60°	11317	8972	7440
65°	10883	8029	6562
70°	10249	6987	5570
75°	9451	5792	4529
80°	8243	4412	4156
85°	6984	4011	3751



TEST NUMBER: P333077-840

CATALOG NUMBER: S124RDIW-S1020D470U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	171.3	2.8
10°-20°	477.7	7.8
20°-30°	689.8	11.3
30°-40°	781.8	12.8
40°-50°	755.0	12.4
50°-60°	627.8	10.3
60°-70°	433.5	7.1
70°-80°	219.7	3.6
80°-90°	58.2	1.0
90°-100°	20.9	0.3
100°-110°	133.4	2.2
110°-120°	255.3	4.2
120°-130°	324.0	5.3
130°-140°	346.7	5.7
140°-150°	324.2	5.3
150°-160°	261.4	4.3
160°-170°	168.6	2.8
170°-180°	58.1	1.0
0°-30°	1338.7	21.9
0°-40°	2120.6	34.7
0°-60°	3503.4	57.4
0°-90°	4214.8	69.0
90°-120°	409.6	6.7
90°-150°	1404.6	23.0
90°-180°	1893.0	31.0
0°-180°	6107.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1824	1824	1824	1824	1824	
5°	1821	1814	1798	1811	1810	173
15°	1734	1720	1687	1683	1674	488
25°	1568	1541	1486	1462	1448	722
35°	1356	1310	1241	1195	1169	847
45°	1106	1052	970	904	877	852
55°	838	780	691	621	592	749
65°	570	508	420	363	344	562
75°	303	251	186	155	145	320
85°	75	49	43	41	40	85
90°	1	6	10	13	14	5
95°	25	10	10	13	13	32
105°	138	140	143	146	130	144
115°	257	258	258	259	259	253
125°	362	363	362	364	364	323
135°	448	448	450	451	452	345
145°	517	518	519	519	520	323
155°	567	567	566	568	567	261
165°	598	596	596	599	595	169
175°	612	609	610	613	608	58
180°	612	612	612	612	612	



TEST NUMBER: P333077-840

CATALOG NUMBER: S124RDIW-S1020D470U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5
2.5°	1828.0	1826.9	1825.9	1825.0	1824.0	1822.1	1819.4	1816.6	1813.9	1811.2	1813.9
5°	1820.7	1819.5	1818.3	1816.9	1815.7	1813.2	1809.6	1805.8	1802.1	1798.4	1801.5
7.5°	1804.2	1802.9	1801.6	1800.3	1799.0	1795.9	1791.1	1786.2	1781.4	1776.6	1778.6
10°	1788.6	1787.1	1785.4	1783.9	1782.4	1778.8	1773.2	1767.7	1762.0	1756.5	1757.7
12.5°	1768.5	1766.7	1764.8	1763.1	1761.3	1757.1	1750.5	1743.9	1737.4	1730.8	1731.5
15°	1734.1	1731.3	1728.6	1725.8	1722.9	1717.7	1709.9	1702.1	1694.5	1686.7	1686.1
17.5°	1692.5	1688.5	1684.5	1680.4	1676.4	1669.7	1660.4	1651.1	1641.8	1632.4	1630.7
20°	1660.1	1656.1	1652.0	1648.0	1644.0	1636.7	1626.2	1615.6	1605.1	1594.5	1592.1
22.5°	1624.4	1619.8	1615.3	1610.8	1606.3	1598.3	1587.1	1575.8	1564.5	1553.2	1549.4
25°	1568.0	1562.4	1556.8	1551.3	1545.6	1536.5	1523.8	1511.1	1498.3	1485.6	1480.4
27.5°	1508.7	1501.8	1494.8	1487.7	1480.8	1470.5	1456.8	1443.3	1429.7	1416.0	1409.6
30°	1467.4	1459.7	1452.0	1444.2	1436.4	1425.2	1410.7	1396.0	1381.5	1367.0	1359.2
32.5°	1423.9	1415.1	1406.3	1397.7	1388.9	1377.0	1361.9	1346.9	1331.7	1316.7	1307.7
35°	1355.7	1345.8	1335.8	1326.0	1316.1	1303.3	1287.8	1272.3	1256.8	1241.2	1230.7
37.5°	1282.8	1272.6	1262.4	1252.1	1241.9	1228.2	1211.0	1193.9	1176.6	1159.4	1147.6
40°	1231.5	1221.2	1211.0	1200.7	1190.5	1176.6	1158.9	1141.1	1123.5	1105.8	1092.8
42.5°	1182.3	1171.6	1160.8	1150.1	1139.4	1124.8	1106.4	1087.9	1069.5	1051.1	1037.8
45°	1105.8	1094.4	1082.9	1071.4	1059.9	1044.8	1026.2	1007.6	989.0	970.4	955.2
47.5°	1026.8	1014.9	1003.1	991.3	979.4	963.8	944.4	925.0	905.6	886.4	870.6
50°	973.2	961.1	949.0	936.9	924.7	908.8	889.0	869.1	849.2	829.4	813.9
52.5°	918.5	906.6	894.7	882.9	871.0	855.0	834.6	814.3	793.9	773.6	757.8
55°	837.8	825.4	812.9	800.5	788.1	771.8	751.6	731.4	711.3	691.2	675.0
57.5°	757.9	745.0	732.1	719.1	706.3	689.8	670.0	650.2	630.3	610.5	594.1
60°	700.9	688.5	676.1	663.7	651.3	635.1	615.3	595.4	575.5	555.7	539.6
62.5°	649.5	636.6	623.7	610.8	597.9	581.3	560.9	540.6	520.2	499.9	484.9
65°	569.7	556.3	543.0	529.7	516.3	499.7	479.9	460.0	440.1	420.3	407.0
67.5°	486.8	473.9	461.2	448.4	435.6	420.0	401.5	383.1	364.7	346.3	334.8
70°	434.2	421.2	408.2	395.2	382.1	366.8	349.1	331.3	313.7	296.0	285.8
72.5°	378.4	366.6	354.8	343.1	331.2	317.0	300.3	283.6	266.9	250.2	241.5
75°	303.0	291.5	280.0	268.5	257.1	244.0	229.4	214.9	200.3	185.7	178.5
77.5°	226.5	216.7	207.0	197.2	187.5	176.7	164.9	153.2	141.4	129.6	125.4
80°	177.3	168.3	159.4	150.4	141.4	132.2	122.9	113.6	104.2	94.9	94.0
82.5°	134.9	126.6	118.4	110.1	101.9	95.0	89.8	84.4	79.1	73.7	73.0
85°	75.4	69.2	63.0	56.8	50.6	47.0	46.0	45.1	44.2	43.3	42.6
87.5°	26.0	24.2	22.4	20.7	18.9	18.0	17.9	17.8	17.8	17.7	17.6
90°	1.4	2.5	3.6	4.7	5.9	6.8	7.7	8.5	9.3	10.1	10.7
92.5°	5.8	5.9	5.9	6.0	6.1	6.5	7.3	8.1	8.9	9.7	10.3
95°	25.1	21.7	18.3	14.8	11.3	9.7	9.8	9.9	10.0	10.1	10.7
97.5°	53.4	55.6	57.8	59.9	62.1	57.5	46.2	34.7	23.4	12.1	12.1
100°	75.0	76.9	78.8	80.6	82.4	76.2	62.2	48.2	34.1	20.1	18.4
102.5°	99.3	100.6	101.9	103.2	104.6	104.3	102.5	100.7	98.9	97.0	78.4
105°	137.7	138.4	139.0	139.6	140.2	140.8	141.3	141.8	142.3	142.8	143.7
107.5°	173.6	173.9	174.2	174.5	174.8	175.3	175.9	176.6	177.3	178.0	178.4
110°	197.7	198.0	198.3	198.6	198.9	199.3	200.0	200.7	201.3	201.9	202.1



TEST NUMBER: P333077-840

CATALOG NUMBER: S124RDIW-S1020D470U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	221.2	221.7	222.3	222.8	223.4	223.8	224.1	224.3	224.6	224.9	224.9
115°	257.2	257.5	257.8	258.1	258.4	258.5	258.4	258.3	258.2	258.1	258.3
117.5°	289.7	290.1	290.5	290.9	291.3	291.6	291.9	292.1	292.4	292.6	292.5
120°	311.6	312.0	312.5	312.9	313.3	313.5	313.4	313.3	313.2	313.1	313.3
122.5°	332.1	332.4	332.6	333.0	333.2	333.4	333.5	333.7	333.8	334.0	334.1
125°	361.5	361.9	362.3	362.7	363.1	363.2	363.0	362.8	362.6	362.4	362.7
127.5°	389.4	389.5	389.6	389.7	389.8	390.1	390.5	391.0	391.5	391.9	391.9
130°	407.3	407.4	407.6	407.7	407.8	408.0	408.3	408.6	408.9	409.2	409.3
132.5°	423.8	423.9	424.1	424.3	424.5	424.9	425.3	425.6	426.0	426.4	426.5
135°	448.5	448.4	448.3	448.2	448.1	448.3	448.7	449.1	449.5	449.9	450.1
137.5°	470.4	470.4	470.5	470.5	470.6	470.8	471.2	471.7	472.1	472.6	472.8
140°	484.6	484.8	485.0	485.2	485.4	485.6	485.8	486.1	486.4	486.6	486.9
142.5°	497.5	497.9	498.3	498.6	499.0	499.2	499.3	499.5	499.6	499.7	499.9
145°	517.2	517.5	517.8	518.1	518.4	518.6	518.6	518.6	518.6	518.6	518.7
147.5°	532.8	533.4	533.9	534.5	535.1	535.3	535.2	535.1	535.0	534.9	535.0
150°	544.2	544.6	545.0	545.4	545.8	545.9	545.8	545.7	545.6	545.5	545.5
152.5°	553.7	554.0	554.3	554.6	555.0	555.0	554.9	554.7	554.5	554.3	554.5
155°	567.0	567.1	567.2	567.3	567.4	567.3	567.0	566.7	566.4	566.1	566.5
157.5°	578.3	578.2	578.1	578.1	578.0	577.8	577.5	577.1	576.8	576.5	577.0
160°	584.9	584.6	584.3	584.0	583.7	583.5	583.4	583.3	583.2	583.1	583.7
162.5°	590.8	590.4	590.0	589.6	589.3	589.0	588.9	588.8	588.7	588.5	589.2
165°	598.1	597.6	597.1	596.6	596.1	595.9	595.9	595.9	595.9	595.9	596.7
167.5°	604.0	603.5	603.0	602.5	601.9	601.6	601.6	601.5	601.5	601.4	602.3
170°	607.3	606.7	606.1	605.5	604.9	604.6	604.7	604.8	604.9	605.0	605.8
172.5°	609.6	608.9	608.3	607.7	607.1	606.8	606.9	607.0	607.1	607.2	608.0
175°	611.9	611.3	610.7	610.1	609.5	609.3	609.4	609.5	609.6	609.7	610.6
177.5°	613.0	612.5	611.9	611.3	610.8	610.6	610.7	610.9	611.0	611.2	611.8
180°	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9



TEST NUMBER: P333077-840

CATALOG NUMBER: S124RDIW-S1020D470U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5
2.5°	1816.6	1819.4	1822.1	1823.4	1823.1	1822.9	1822.6	1822.4
5°	1804.5	1807.7	1810.8	1812.0	1811.4	1810.8	1810.2	1809.6
7.5°	1780.6	1782.5	1784.5	1785.0	1784.0	1783.0	1782.0	1781.0
10°	1759.0	1760.2	1761.4	1761.4	1760.2	1759.0	1757.7	1756.5
12.5°	1732.2	1733.0	1733.7	1733.2	1731.5	1729.8	1728.1	1726.4
15°	1685.5	1684.8	1684.2	1682.7	1680.6	1678.4	1676.3	1674.1
17.5°	1629.0	1627.3	1625.6	1623.1	1619.7	1616.5	1613.2	1609.8
20°	1589.5	1587.1	1584.6	1581.3	1577.3	1573.3	1569.2	1565.2
22.5°	1545.7	1542.0	1538.3	1534.8	1531.5	1528.2	1524.9	1521.7
25°	1475.0	1469.8	1464.5	1460.3	1457.2	1454.1	1451.0	1447.9
27.5°	1403.0	1396.5	1390.0	1384.5	1380.1	1375.5	1371.1	1366.7
30°	1351.4	1343.6	1335.8	1329.5	1324.5	1319.6	1314.6	1309.7
32.5°	1298.7	1289.7	1280.7	1273.8	1269.1	1264.4	1259.7	1255.0
35°	1220.1	1209.6	1199.0	1191.0	1185.4	1179.8	1174.3	1168.6
37.5°	1135.9	1124.1	1112.3	1103.6	1098.0	1092.4	1086.8	1081.3
40°	1079.7	1066.7	1053.7	1044.4	1038.8	1033.2	1027.6	1022.1
42.5°	1024.5	1011.3	997.9	988.5	982.6	976.7	970.9	965.1
45°	940.0	924.7	909.6	899.2	893.6	888.0	882.4	876.9
47.5°	854.9	839.1	823.2	812.3	806.2	800.0	793.9	787.8
50°	798.3	782.8	767.3	756.6	750.7	744.8	738.9	733.1
52.5°	741.9	726.2	710.4	699.5	693.4	687.2	681.1	675.0
55°	658.8	642.8	626.6	615.6	609.7	603.8	597.9	592.0
57.5°	577.6	561.3	544.9	534.5	530.0	525.5	521.1	516.6
60°	523.4	507.3	491.2	480.6	475.6	470.7	465.7	460.8
62.5°	470.1	455.1	440.3	430.8	426.9	422.9	418.9	415.0
65°	393.5	380.2	366.9	358.4	354.7	350.9	347.2	343.5
67.5°	323.3	311.8	300.3	292.6	288.4	284.4	280.2	276.2
70°	275.5	265.3	255.1	248.3	245.3	242.2	239.0	236.0
72.5°	232.7	224.0	215.2	209.4	206.5	203.7	200.9	198.0
75°	171.5	164.3	157.1	152.7	150.8	149.0	147.0	145.2
77.5°	121.3	117.1	112.9	110.6	110.0	109.5	108.9	108.4
80°	93.1	92.2	91.2	90.6	90.3	90.0	89.7	89.4
82.5°	72.3	71.7	71.0	70.5	70.2	69.9	69.6	69.3
85°	42.0	41.4	40.8	40.5	40.5	40.5	40.5	40.5
87.5°	17.4	17.3	17.2	17.3	17.5	17.8	18.1	18.4
90°	11.3	11.9	12.5	12.9	13.1	13.3	13.5	13.7
92.5°	10.9	11.5	12.1	12.4	12.5	12.5	12.6	12.6
95°	11.3	11.9	12.5	12.8	12.9	13.0	13.1	13.2
97.5°	12.2	12.2	12.3	12.4	12.5	12.6	12.7	12.8
100°	16.7	14.9	13.2	12.4	12.5	12.6	12.7	12.8
102.5°	59.7	41.1	22.4	13.1	13.1	13.1	13.1	13.2
105°	144.6	145.5	146.4	145.1	141.4	137.7	134.1	130.5
107.5°	178.9	179.4	179.9	180.3	180.7	181.0	181.4	181.8
110°	202.3	202.5	202.7	202.9	203.2	203.5	203.8	204.1





TEST NUMBER: P333077-840

CATALOG NUMBER: S124RDIW-S1020D470U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	224.8	224.8	224.7	224.9	225.3	225.7	226.1	226.4
115°	258.5	258.7	258.9	259.0	259.0	259.0	259.0	259.0
117.5°	292.5	292.5	292.4	292.4	292.3	292.3	292.3	292.2
120°	313.5	313.7	313.9	313.9	313.7	313.5	313.3	313.1
122.5°	334.2	334.3	334.4	334.4	334.2	334.0	333.8	333.6
125°	363.0	363.3	363.7	363.9	364.0	364.1	364.2	364.3
127.5°	391.8	391.7	391.7	391.6	391.5	391.4	391.4	391.3
130°	409.4	409.5	409.6	409.6	409.6	409.6	409.6	409.6
132.5°	426.6	426.7	426.8	426.8	426.7	426.7	426.6	426.5
135°	450.3	450.5	450.7	450.9	451.1	451.3	451.5	451.7
137.5°	473.0	473.2	473.5	473.5	473.5	473.4	473.4	473.3
140°	487.2	487.5	487.8	488.0	488.1	488.2	488.3	488.4
142.5°	500.1	500.4	500.6	500.7	500.7	500.8	500.8	500.8
145°	518.8	518.9	519.0	519.1	519.3	519.5	519.7	519.9
147.5°	535.1	535.1	535.2	535.3	535.4	535.5	535.6	535.7
150°	545.5	545.5	545.5	545.6	545.7	545.8	545.9	546.0
152.5°	554.6	554.8	555.0	555.0	555.0	554.9	554.8	554.8
155°	566.9	567.3	567.7	567.8	567.5	567.2	566.9	566.6
157.5°	577.5	578.0	578.6	578.6	578.0	577.5	577.0	576.5
160°	584.3	584.9	585.5	585.5	584.9	584.3	583.7	583.1
162.5°	589.8	590.4	591.0	591.0	590.3	589.6	588.9	588.2
165°	597.5	598.3	599.2	599.1	598.1	597.2	596.3	595.4
167.5°	603.2	604.1	605.0	604.9	603.9	602.9	601.9	600.9
170°	606.6	607.4	608.3	608.2	607.1	606.1	605.1	604.1
172.5°	608.8	609.7	610.5	610.4	609.3	608.1	607.0	605.9
175°	611.5	612.4	613.3	613.1	611.9	610.7	609.5	608.2
177.5°	612.5	613.1	613.8	613.6	612.7	611.7	610.7	609.8
180°	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9

(END OF REPORT)