

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333718-927

Luminaire Tested: **S125RDIW-S1090D1560U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333718-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1090D1560U927-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8288.4 lumens
Efficiency: N/A
Efficacy: 108.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333718-927

CATALOG NUMBER: S125RDIW-S1090D1560U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333718-927

CATALOG NUMBER: S125RDIW-S1090D1560U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	96	92	88	84	87	84	80	78	69	66	64	55	53	52	42	41	40	34
2	87	80	74	69	79	73	68	64	60	57	53	48	46	44	37	36	34	29
3	80	71	63	58	72	65	58	53	53	49	45	43	40	37	33	31	29	25
4	73	63	55	49	66	57	51	45	47	42	39	38	35	32	30	27	25	21
5	67	56	48	42	61	51	44	39	42	37	33	34	31	28	27	24	22	19
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	22	20	16
7	57	45	37	32	52	41	35	30	35	29	26	28	24	21	22	19	17	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	20	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9144	9144	9144
5°	9166	9061	9117
10°	9096	8977	8977
15°	8988	8795	8723
20°	8849	8541	8438
25°	8688	8292	8109
30°	8486	7999	7744
35°	8280	7698	7335
40°	8088	7384	6933
45°	7853	7033	6495
50°	7618	6650	6038
55°	7346	6286	5551
60°	7073	5842	5028
65°	6748	5327	4429
70°	6381	4685	3816
75°	5871	3950	3174
80°	5170	3102	2663
85°	4357	2534	2379



TEST NUMBER: P333718-927

CATALOG NUMBER: S125RDIW-S1090D1560U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.1	1.6
10°-20°	372.1	4.5
20°-30°	539.6	6.5
30°-40°	614.9	7.4
40°-50°	599.4	7.2
50°-60°	504.6	6.1
60°-70°	353.7	4.3
70°-80°	181.8	2.2
80°-90°	49.3	0.6
90°-100°	58.5	0.7
100°-110°	360.3	4.3
110°-120°	653.4	7.9
120°-130°	838.6	10.1
130°-140°	902.0	10.9
140°-150°	846.7	10.2
150°-160°	684.9	8.3
160°-170°	442.9	5.3
170°-180°	152.8	1.8
0°-30°	1044.8	12.6
0°-40°	1659.7	20.0
0°-60°	2763.6	33.3
0°-90°	3348.4	40.4
90°-120°	1072.2	12.9
90°-150°	3659.5	44.2
90°-180°	4940.0	59.6
0°-180°	8288.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1416	1416	1416	1416	1416	
5°	1414	1409	1398	1408	1406	134
15°	1344	1337	1315	1314	1305	379
25°	1219	1202	1164	1150	1138	561
35°	1050	1023	976	946	930	657
45°	860	827	770	729	711	663
55°	652	617	558	512	493	583
65°	442	404	349	307	290	437
75°	235	202	158	136	127	249
85°	59	40	34	33	32	66
90°	1	11	19	25	29	6
95°	68	62	19	25	25	87
105°	351	355	355	355	354	372
115°	658	664	665	661	654	652
125°	936	944	944	940	936	836
135°	1167	1174	1172	1170	1163	900
145°	1354	1356	1356	1357	1350	846
155°	1491	1484	1486	1489	1480	686
165°	1573	1566	1567	1573	1565	444
175°	1609	1602	1603	1611	1602	153
180°	1609	1609	1609	1609	1609	



TEST NUMBER: P333718-927

CATALOG NUMBER: S125RDIW-S1090D1560U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9
2.5°	1418.5	1417.9	1417.4	1416.7	1416.2	1415.0	1413.1	1411.2	1409.3	1407.4	1409.3
5°	1413.8	1412.9	1411.9	1411.0	1410.0	1408.2	1405.6	1403.0	1400.3	1397.7	1400.1
7.5°	1399.9	1399.0	1398.0	1397.2	1396.2	1394.2	1391.1	1388.0	1384.8	1381.7	1383.4
10°	1387.0	1386.3	1385.6	1384.9	1384.2	1382.2	1378.9	1375.5	1372.2	1368.9	1369.6
12.5°	1372.5	1371.6	1370.7	1369.8	1368.9	1366.2	1361.8	1357.2	1352.8	1348.3	1348.8
15°	1344.3	1342.8	1341.4	1340.0	1338.6	1335.4	1330.4	1325.4	1320.4	1315.4	1315.2
17.5°	1312.4	1310.2	1308.1	1305.8	1303.6	1299.4	1293.2	1286.9	1280.6	1274.3	1273.1
20°	1287.6	1285.2	1282.9	1280.5	1278.1	1273.1	1265.5	1257.9	1250.3	1242.7	1241.5
22.5°	1260.2	1257.8	1255.5	1253.1	1250.7	1245.5	1237.5	1229.5	1221.5	1213.5	1211.2
25°	1219.2	1215.6	1212.0	1208.5	1204.9	1198.7	1189.9	1181.1	1172.4	1163.6	1160.5
27.5°	1172.1	1167.8	1163.4	1159.1	1154.8	1148.0	1138.5	1129.1	1119.7	1110.2	1106.0
30°	1137.9	1133.4	1128.9	1124.3	1119.8	1112.5	1102.6	1092.6	1082.6	1072.6	1067.1
32.5°	1104.5	1099.2	1093.9	1088.7	1083.4	1075.7	1065.5	1055.3	1045.1	1035.0	1029.0
35°	1050.2	1044.5	1038.8	1033.1	1027.4	1019.1	1008.4	997.8	987.1	976.4	969.5
37.5°	996.9	990.0	983.0	976.1	969.2	960.2	949.1	938.1	927.1	916.1	907.8
40°	959.3	952.1	945.0	937.9	930.7	921.5	910.1	898.7	887.2	875.8	866.8
42.5°	919.9	912.6	905.3	897.9	890.7	881.1	869.3	857.5	845.7	833.9	825.3
45°	859.8	852.9	846.1	839.2	832.3	822.3	809.2	796.1	783.1	770.0	760.5
47.5°	797.6	790.3	783.0	775.8	768.5	758.3	745.1	731.9	718.7	705.6	695.8
50°	758.2	750.4	742.5	734.7	726.8	716.1	702.6	689.0	675.5	661.9	652.0
52.5°	715.4	707.4	699.3	691.3	683.3	672.9	660.1	647.3	634.5	621.8	611.0
55°	652.4	644.8	637.2	629.5	621.9	611.5	598.2	584.9	571.6	558.3	547.6
57.5°	588.6	580.5	572.4	564.2	556.1	545.7	532.8	520.0	507.2	494.3	483.9
60°	547.6	539.2	530.9	522.6	514.3	503.7	490.8	478.0	465.2	452.3	441.9
62.5°	503.9	496.0	488.1	480.1	472.1	461.7	448.7	435.6	422.6	409.6	399.9
65°	441.6	433.6	425.5	417.4	409.3	399.0	386.4	373.8	361.2	348.6	339.1
67.5°	379.9	371.8	363.7	355.6	347.5	337.5	325.3	313.3	301.3	289.1	280.5
70°	337.9	329.9	321.8	313.7	305.6	295.6	283.8	271.9	260.0	248.1	240.7
72.5°	296.9	289.0	281.1	273.2	265.3	255.8	244.7	233.5	222.4	211.4	204.5
75°	235.3	228.1	221.0	213.9	206.8	198.2	188.2	178.2	168.3	158.3	153.0
77.5°	174.1	168.4	162.7	157.0	151.3	144.4	136.5	128.5	120.5	112.5	108.8
80°	139.0	133.3	127.6	121.9	116.2	110.0	103.4	96.7	90.1	83.4	81.3
82.5°	104.8	99.7	94.5	89.4	84.3	79.5	74.9	70.3	65.8	61.2	60.2
85°	58.8	54.5	50.2	45.9	41.7	39.0	37.8	36.6	35.4	34.2	34.0
87.5°	19.9	19.0	18.1	17.2	16.3	15.9	16.1	16.3	16.5	16.6	17.0
90°	1.2	3.3	5.5	7.5	9.7	11.6	13.5	15.4	17.2	19.1	20.4
92.5°	18.4	16.9	15.4	13.9	12.4	12.5	14.2	15.8	17.4	19.1	20.4
95°	68.0	67.2	66.4	65.6	64.8	59.3	49.3	39.2	29.2	19.1	20.4
97.5°	141.9	143.3	144.7	146.2	147.7	138.4	118.4	98.5	78.6	58.7	51.2
100°	199.2	199.9	200.7	201.5	202.3	203.3	204.3	205.4	206.4	207.5	168.0
102.5°	257.4	258.3	259.4	260.4	261.3	262.2	262.8	263.5	264.1	264.7	257.3
105°	350.6	351.6	352.8	353.8	354.8	355.4	355.4	355.4	355.4	355.4	355.4
107.5°	447.4	447.4	447.4	447.4	447.4	447.7	448.2	448.8	449.3	449.8	449.9
110°	510.4	510.4	510.4	510.4	510.4	510.6	511.2	511.7	512.2	512.8	512.0



TEST NUMBER: P333718-927

CATALOG NUMBER: S125RDIW-S1090D1560U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	569.6	570.2	570.8	571.5	572.1	572.6	572.9	573.2	573.5	573.9	572.8
115°	658.3	659.6	660.9	662.3	663.5	664.3	664.6	664.9	665.2	665.4	664.3
117.5°	750.1	750.0	750.0	750.0	749.9	750.4	751.4	752.3	753.4	754.4	753.0
120°	807.3	807.1	806.8	806.5	806.3	806.5	807.3	808.1	808.9	809.7	809.2
122.5°	857.9	858.9	859.9	860.9	861.9	862.6	863.0	863.3	863.7	864.1	863.6
125°	936.1	937.9	939.8	941.7	943.6	944.4	944.4	944.4	944.4	944.4	943.4
127.5°	1010.7	1012.1	1013.4	1014.8	1016.1	1016.7	1016.5	1016.4	1016.2	1016.1	1015.4
130°	1056.5	1057.9	1059.2	1060.6	1061.8	1062.6	1063.0	1063.2	1063.4	1063.7	1063.0
132.5°	1102.3	1103.9	1105.4	1107.0	1108.5	1109.0	1108.4	1107.8	1107.2	1106.7	1106.5
135°	1167.4	1169.0	1170.7	1172.3	1173.9	1174.3	1173.9	1173.3	1172.7	1172.3	1171.7
137.5°	1227.3	1228.7	1230.1	1231.4	1232.9	1233.3	1232.8	1232.3	1231.8	1231.4	1231.5
140°	1266.5	1267.0	1267.5	1268.0	1268.6	1268.7	1268.4	1268.2	1267.9	1267.7	1268.2
142.5°	1301.7	1302.0	1302.3	1302.7	1303.0	1303.4	1303.8	1304.1	1304.5	1304.9	1305.0
145°	1353.5	1354.0	1354.6	1355.1	1355.7	1355.9	1355.9	1355.9	1355.9	1355.9	1356.1
147.5°	1398.8	1398.7	1398.6	1398.5	1398.4	1398.5	1398.8	1399.2	1399.5	1399.8	1400.1
150°	1427.4	1426.9	1426.4	1425.8	1425.3	1425.3	1425.8	1426.4	1426.9	1427.4	1428.0
152.5°	1455.1	1454.0	1452.8	1451.6	1450.4	1450.1	1450.6	1451.2	1451.8	1452.2	1452.8
155°	1490.6	1489.1	1487.5	1485.9	1484.3	1483.8	1484.3	1484.8	1485.3	1485.9	1486.7
157.5°	1518.1	1517.1	1516.2	1515.2	1514.3	1513.8	1513.9	1513.9	1513.9	1514.0	1514.9
160°	1537.2	1535.6	1534.0	1532.4	1530.8	1530.1	1530.4	1530.7	1530.9	1531.2	1532.2
162.5°	1552.4	1550.9	1549.3	1547.6	1546.0	1545.4	1545.6	1545.9	1546.2	1546.4	1547.9
165°	1573.0	1571.4	1569.7	1568.1	1566.5	1565.9	1566.1	1566.5	1566.7	1566.9	1568.5
167.5°	1588.2	1586.6	1584.9	1583.3	1581.6	1581.0	1581.2	1581.4	1581.8	1582.0	1583.9
170°	1596.8	1594.9	1593.1	1591.2	1589.4	1588.6	1588.8	1589.1	1589.4	1589.6	1591.7
172.5°	1602.5	1600.7	1598.8	1597.0	1595.1	1594.4	1594.9	1595.4	1595.9	1596.3	1598.2
175°	1608.7	1607.1	1605.5	1603.9	1602.3	1601.7	1602.0	1602.2	1602.5	1602.7	1604.9
177.5°	1611.5	1610.3	1609.0	1607.7	1606.5	1605.9	1606.1	1606.4	1606.5	1606.8	1608.3
180°	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7



TEST NUMBER: P333718-927

CATALOG NUMBER: S125RDIW-S1090D1560U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9
2.5°	1411.2	1413.1	1415.0	1415.8	1415.6	1415.5	1415.2	1415.1
5°	1402.5	1404.9	1407.2	1408.2	1407.7	1407.2	1406.8	1406.3
7.5°	1385.1	1386.7	1388.4	1388.9	1388.4	1387.9	1387.3	1386.8
10°	1370.3	1371.0	1371.7	1371.7	1371.0	1370.3	1369.6	1368.9
12.5°	1349.4	1349.9	1350.4	1350.1	1349.0	1348.0	1346.9	1345.8
15°	1314.9	1314.7	1314.5	1313.3	1311.1	1309.0	1306.9	1304.7
17.5°	1271.9	1270.7	1269.6	1268.1	1266.3	1264.6	1262.8	1261.1
20°	1240.3	1239.1	1237.9	1236.3	1234.1	1232.0	1229.9	1227.7
22.5°	1208.9	1206.6	1204.3	1202.2	1200.5	1198.7	1196.9	1195.2
25°	1157.4	1154.3	1151.2	1148.3	1145.7	1143.1	1140.5	1137.9
27.5°	1101.6	1097.3	1093.0	1089.6	1087.0	1084.5	1082.0	1079.5
30°	1061.7	1056.2	1050.8	1046.9	1044.8	1042.7	1040.5	1038.4
32.5°	1022.9	1016.8	1010.8	1006.5	1003.8	1001.1	998.3	995.6
35°	962.6	955.7	948.8	943.7	940.4	937.1	933.7	930.4
37.5°	899.5	891.3	883.0	877.3	874.0	870.8	867.5	864.3
40°	857.8	848.7	839.7	833.8	830.9	828.1	825.2	822.4
42.5°	816.7	807.9	799.3	792.9	788.7	784.6	780.4	776.2
45°	751.0	741.5	732.0	725.4	721.8	718.3	714.7	711.1
47.5°	686.0	676.2	666.5	659.6	655.6	651.6	647.8	643.8
50°	642.0	632.0	622.0	615.3	611.7	608.2	604.6	601.0
52.5°	600.3	589.5	578.8	571.6	568.1	564.5	560.9	557.4
55°	536.9	526.2	515.5	508.2	504.4	500.6	496.8	493.0
57.5°	473.4	463.0	452.5	445.5	442.2	438.8	435.4	432.1
60°	431.4	421.0	410.5	403.5	400.0	396.4	392.8	389.3
62.5°	390.2	380.5	370.8	364.2	360.6	357.0	353.5	349.9
65°	329.6	320.1	310.6	304.0	300.5	296.9	293.3	289.8
67.5°	271.8	263.1	254.4	248.6	245.7	242.9	240.0	237.2
70°	233.4	226.0	218.6	213.5	210.6	207.8	204.9	202.1
72.5°	197.7	190.9	184.1	179.7	177.8	175.9	174.0	172.1
75°	147.8	142.6	137.4	133.9	132.2	130.6	128.9	127.2
77.5°	105.2	101.6	97.8	95.4	94.2	92.9	91.7	90.5
80°	79.1	77.0	74.9	73.5	73.0	72.6	72.1	71.6
82.5°	59.2	58.1	57.2	56.6	56.2	55.9	55.7	55.4
85°	33.7	33.5	33.3	33.0	32.8	32.6	32.3	32.1
87.5°	17.2	17.4	17.7	17.8	17.8	17.7	17.7	17.7
90°	21.7	23.1	24.4	25.4	26.2	27.0	27.8	28.6
92.5°	21.7	23.1	24.4	25.2	25.6	26.0	26.4	26.7
95°	21.7	23.1	24.4	25.0	25.0	25.0	25.0	25.0
97.5°	43.7	36.3	28.8	25.0	25.0	25.0	25.0	25.0
100°	128.5	89.0	49.6	29.3	28.2	27.2	26.1	25.0
102.5°	249.8	242.3	234.9	222.1	204.1	186.1	168.0	150.0
105°	355.4	355.4	355.4	355.2	355.0	354.7	354.4	354.2
107.5°	450.0	450.0	450.0	449.6	448.9	448.1	447.3	446.5
110°	511.2	510.4	509.6	509.4	509.6	509.8	510.2	510.4



TEST NUMBER: P333718-927

CATALOG NUMBER: S125RDIW-S1090D1560U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	571.8	570.8	569.8	569.1	568.8	568.4	568.0	567.6
115°	663.3	662.3	661.2	659.9	658.3	656.6	655.1	653.5
117.5°	751.6	750.3	748.8	747.8	747.2	746.5	745.8	745.0
120°	808.7	808.1	807.6	806.7	805.3	804.0	802.7	801.4
122.5°	863.0	862.5	862.0	860.9	859.4	857.9	856.3	854.8
125°	942.4	941.3	940.2	939.3	938.5	937.7	936.9	936.1
127.5°	1014.9	1014.3	1013.7	1012.4	1010.4	1008.5	1006.5	1004.6
130°	1062.2	1061.4	1060.6	1059.5	1058.2	1056.9	1055.5	1054.2
132.5°	1106.4	1106.2	1106.0	1105.3	1104.0	1102.6	1101.3	1099.9
135°	1171.2	1170.7	1170.1	1169.0	1167.4	1165.9	1164.3	1162.7
137.5°	1231.6	1231.7	1231.8	1231.2	1229.8	1228.4	1227.0	1225.7
140°	1268.7	1269.2	1269.8	1269.2	1267.7	1266.1	1264.5	1262.9
142.5°	1305.0	1305.2	1305.3	1304.6	1302.9	1301.3	1299.7	1298.1
145°	1356.5	1356.7	1356.9	1356.3	1354.7	1353.1	1351.5	1350.0
147.5°	1400.4	1400.7	1401.1	1400.3	1398.4	1396.5	1394.6	1392.7
150°	1428.5	1429.0	1429.6	1428.8	1426.6	1424.5	1422.4	1420.3
152.5°	1453.3	1453.8	1454.4	1453.7	1451.8	1449.9	1448.0	1446.0
155°	1487.5	1488.3	1489.1	1488.4	1486.3	1484.2	1482.0	1479.9
157.5°	1515.7	1516.6	1517.4	1516.8	1514.7	1512.5	1510.4	1508.3
160°	1533.3	1534.4	1535.4	1534.9	1532.8	1530.7	1528.5	1526.5
162.5°	1549.4	1550.9	1552.4	1552.0	1549.7	1547.3	1545.0	1542.6
165°	1570.1	1571.8	1573.4	1573.0	1571.0	1568.8	1566.7	1564.6
167.5°	1585.8	1587.7	1589.6	1589.4	1587.0	1584.6	1582.2	1579.8
170°	1593.9	1596.0	1598.1	1598.0	1595.6	1593.2	1590.8	1588.4
172.5°	1600.1	1602.0	1603.9	1603.7	1601.3	1598.9	1596.6	1594.2
175°	1606.9	1609.1	1611.2	1611.1	1608.7	1606.3	1603.9	1601.6
177.5°	1609.8	1611.2	1612.7	1612.6	1610.9	1609.2	1607.5	1605.8
180°	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7

(END OF REPORT)