

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333109-840

Luminaire Tested: **S124RDIW-S1195D1340U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333109-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S1195D1340U840-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1340 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10288.1 lumens  
Efficiency: N/A  
Efficacy: 135.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 76.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333109-840

CATALOG NUMBER: S124RDIW-S1195D1340U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333109-840

CATALOG NUMBER: S124RDIW-S1195D1340U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40
2	89	82	76	71	82	75	70	66	63	60	56	53	50	48	42	41	39	34
3	81	72	65	59	74	67	60	55	56	52	48	47	43	40	38	35	33	29
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29	25
5	68	57	49	43	63	53	46	40	45	39	35	38	33	30	31	28	25	22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	22	20
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	25	22	20	17
8	54	42	34	29	50	39	32	28	34	28	24	28	24	21	23	20	18	16
9	50	38	31	26	46	36	29	25	31	25	22	26	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	17002	17002	17002
5°	17040	16832	16936
10°	16934	16629	16629
15°	16739	16280	16160
20°	16472	15821	15530
25°	16131	15284	14895
30°	15800	14716	14100
35°	15431	14128	13302
40°	14989	13460	12440
45°	14582	12795	11562
50°	14117	12031	10633
55°	13619	11234	9623
60°	13070	10362	8591
65°	12567	9270	7578
70°	11837	8068	6434
75°	10914	6691	5231
80°	9521	5100	4798
85°	8068	4631	4335



TEST NUMBER: P333109-840

CATALOG NUMBER: S124RDIW-S1195D1340U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	197.8	1.9
10°-20°	551.7	5.4
20°-30°	796.6	7.7
30°-40°	903.0	8.8
40°-50°	872.0	8.5
50°-60°	725.1	7.0
60°-70°	500.7	4.9
70°-80°	253.8	2.5
80°-90°	70.2	0.7
90°-100°	59.9	0.6
100°-110°	381.9	3.7
110°-120°	730.6	7.1
120°-130°	927.4	9.0
130°-140°	992.3	9.6
140°-150°	927.9	9.0
150°-160°	748.3	7.3
160°-170°	482.6	4.7
170°-180°	166.3	1.6
0°-30°	1546.1	15.0
0°-40°	2449.1	23.8
0°-60°	4046.2	39.3
0°-90°	4870.8	47.3
90°-120°	1172.4	11.4
90°-150°	4020.0	39.1
90°-180°	5417.0	52.7
0°-180°	10288.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2106	2106	2106	2106	2106	
5°	2103	2096	2077	2092	2090	199
15°	2003	1987	1948	1944	1934	564
25°	1811	1780	1716	1689	1672	834
35°	1566	1513	1434	1380	1350	978
45°	1277	1215	1121	1044	1013	984
55°	968	901	798	717	684	865
65°	658	587	485	419	397	649
75°	350	289	214	179	168	369
85°	87	56	50	47	47	98
90°	4	18	29	36	39	8
95°	72	30	29	36	38	93
105°	394	402	409	417	373	413
115°	736	740	739	741	741	724
125°	1035	1040	1037	1041	1043	924
135°	1284	1283	1288	1290	1293	989
145°	1480	1484	1484	1485	1488	925
155°	1623	1624	1620	1625	1622	748
165°	1712	1706	1706	1715	1704	484
175°	1751	1744	1745	1755	1741	167
180°	1751	1751	1751	1751	1751	



TEST NUMBER: P333109-840

CATALOG NUMBER: S124RDIW-S1195D1340U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0
2.5°	2111.1	2110.0	2108.9	2107.7	2106.6	2104.5	2101.3	2098.1	2095.0	2091.8	2095.0
5°	2102.7	2101.3	2099.9	2098.5	2097.1	2094.2	2089.9	2085.6	2081.3	2077.0	2080.5
7.5°	2083.8	2082.2	2080.7	2079.2	2077.7	2074.2	2068.6	2063.1	2057.4	2051.8	2054.2
10°	2065.7	2063.9	2062.1	2060.3	2058.5	2054.4	2048.0	2041.5	2035.1	2028.6	2030.0
12.5°	2042.5	2040.4	2038.3	2036.2	2034.2	2029.3	2021.7	2014.2	2006.5	1998.9	1999.8
15°	2002.8	1999.5	1996.4	1993.2	1989.9	1983.8	1974.9	1965.9	1956.9	1947.9	1947.2
17.5°	1954.8	1950.0	1945.4	1940.8	1936.1	1928.4	1917.6	1906.9	1896.1	1885.4	1883.4
20°	1917.3	1912.7	1908.0	1903.4	1898.7	1890.3	1878.1	1865.9	1853.7	1841.6	1838.7
22.5°	1876.0	1870.9	1865.6	1860.4	1855.1	1846.0	1832.9	1819.9	1806.9	1793.8	1789.5
25°	1810.9	1804.4	1798.0	1791.6	1785.1	1774.5	1759.9	1745.1	1730.5	1715.8	1709.7
27.5°	1742.5	1734.4	1726.4	1718.3	1710.1	1698.3	1682.5	1666.9	1651.1	1635.5	1627.9
30°	1694.9	1685.9	1676.9	1667.9	1659.0	1646.1	1629.2	1612.4	1595.6	1578.7	1569.7
32.5°	1644.5	1634.4	1624.3	1614.2	1604.1	1590.3	1572.9	1555.5	1538.0	1520.7	1510.3
35°	1565.8	1554.3	1542.9	1531.4	1519.9	1505.2	1487.3	1469.5	1451.5	1433.6	1421.4
37.5°	1481.7	1469.8	1457.9	1446.1	1434.3	1418.5	1398.7	1378.8	1359.0	1339.1	1325.4
40°	1422.3	1410.5	1398.7	1386.8	1374.9	1358.9	1338.5	1318.0	1297.6	1277.2	1262.1
42.5°	1365.5	1353.1	1340.7	1328.3	1316.0	1299.1	1277.8	1256.5	1235.3	1214.0	1198.6
45°	1277.2	1263.8	1250.6	1237.4	1224.2	1206.7	1185.3	1163.8	1142.3	1120.7	1103.2
47.5°	1185.9	1172.2	1158.5	1144.8	1131.1	1113.1	1090.8	1068.3	1046.0	1023.7	1005.4
50°	1124.0	1109.9	1096.0	1082.1	1068.0	1049.6	1026.6	1003.7	980.8	957.9	940.0
52.5°	1060.8	1047.0	1033.4	1019.7	1006.0	987.3	963.9	940.4	916.9	893.3	875.1
55°	967.6	953.2	938.9	924.5	910.2	891.4	868.1	844.9	821.5	798.2	779.6
57.5°	875.3	860.4	845.5	830.6	815.7	796.8	773.9	750.8	727.9	705.0	686.1
60°	809.5	795.2	780.8	766.5	752.1	733.6	710.6	687.7	664.7	641.8	623.2
62.5°	750.1	735.3	720.3	705.5	690.5	671.4	647.8	624.3	600.8	577.3	560.1
65°	657.9	642.5	627.1	611.7	596.3	577.1	554.2	531.3	508.4	485.3	470.0
67.5°	562.1	547.3	532.6	517.9	503.1	485.0	463.7	442.5	421.2	399.9	386.7
70°	501.5	486.5	471.4	456.4	441.3	423.5	403.1	382.7	362.3	341.8	330.0
72.5°	437.0	423.4	409.8	396.2	382.5	366.1	346.8	327.5	308.2	288.9	278.8
75°	349.9	336.7	323.4	310.1	296.9	281.9	265.0	248.1	231.4	214.5	206.2
77.5°	261.6	250.3	239.0	227.8	216.5	204.1	190.5	176.9	163.3	149.7	144.8
80°	204.8	194.4	184.0	173.6	163.2	152.7	141.9	131.2	120.4	109.7	108.6
82.5°	155.8	146.2	136.7	127.1	117.6	109.8	103.6	97.5	91.3	85.1	84.3
85°	87.1	79.9	72.7	65.5	58.4	54.3	53.2	52.1	51.1	50.0	49.3
87.5°	30.5	28.8	27.2	25.4	23.8	23.1	23.3	23.4	23.6	23.8	23.9
90°	3.9	7.2	10.3	13.5	16.8	19.5	21.8	24.1	26.5	28.8	30.6
92.5°	16.5	16.7	16.9	17.1	17.2	18.5	20.8	23.1	25.4	27.8	29.5
95°	72.0	62.1	52.2	42.3	32.4	27.7	28.0	28.3	28.5	28.8	30.6
97.5°	153.0	159.2	165.3	171.5	177.6	164.5	132.0	99.6	67.1	34.5	34.7
100°	214.8	220.0	225.3	230.6	235.8	218.3	178.1	137.9	97.8	57.7	52.7
102.5°	284.0	287.8	291.6	295.5	299.3	298.6	293.4	288.2	283.0	277.7	224.3
105°	394.3	396.0	397.8	399.5	401.2	402.8	404.3	405.8	407.2	408.7	411.3
107.5°	496.7	497.6	498.5	499.3	500.2	501.6	503.6	505.5	507.6	509.6	510.8
110°	565.8	566.7	567.6	568.5	569.4	570.7	572.4	574.1	575.9	577.6	578.2



TEST NUMBER: P333109-840

CATALOG NUMBER: S124RDIW-S1195D1340U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	632.9	634.5	636.1	637.6	639.2	640.4	641.3	642.1	642.9	643.7	643.6
115°	736.1	737.0	737.9	738.7	739.6	739.9	739.6	739.3	739.0	738.7	739.3
117.5°	829.1	830.3	831.4	832.6	833.7	834.7	835.4	836.0	836.6	837.3	837.2
120°	892.0	893.1	894.3	895.5	896.7	897.1	896.9	896.6	896.3	896.0	896.6
122.5°	950.7	951.4	952.1	952.8	953.5	954.0	954.4	954.8	955.2	955.6	956.0
125°	1034.8	1035.9	1037.1	1038.2	1039.5	1039.8	1039.2	1038.5	1037.9	1037.4	1038.2
127.5°	1114.4	1114.7	1115.0	1115.3	1115.6	1116.4	1117.7	1119.0	1120.4	1121.8	1121.6
130°	1165.8	1166.1	1166.4	1166.6	1166.9	1167.5	1168.4	1169.2	1170.1	1171.0	1171.3
132.5°	1212.9	1213.5	1214.0	1214.5	1215.0	1215.9	1217.0	1218.0	1219.1	1220.2	1220.5
135°	1283.6	1283.3	1283.0	1282.8	1282.5	1282.9	1284.0	1285.3	1286.5	1287.6	1288.2
137.5°	1346.3	1346.4	1346.5	1346.7	1346.8	1347.5	1348.7	1350.0	1351.3	1352.5	1353.2
140°	1387.2	1387.8	1388.3	1388.9	1389.5	1390.1	1390.6	1391.2	1391.8	1392.4	1393.2
142.5°	1423.8	1424.8	1425.9	1426.9	1428.1	1428.7	1429.1	1429.4	1429.8	1430.1	1430.8
145°	1480.2	1481.0	1481.9	1482.8	1483.6	1484.1	1484.1	1484.1	1484.1	1484.1	1484.4
147.5°	1524.9	1526.5	1528.2	1529.8	1531.5	1532.2	1531.9	1531.6	1531.3	1531.0	1531.2
150°	1557.4	1558.6	1559.7	1560.9	1562.1	1562.5	1562.3	1562.0	1561.7	1561.4	1561.4
152.5°	1584.7	1585.6	1586.5	1587.4	1588.4	1588.6	1588.1	1587.5	1587.0	1586.5	1587.0
155°	1623.0	1623.2	1623.5	1623.8	1624.1	1623.8	1623.0	1622.0	1621.1	1620.3	1621.4
157.5°	1655.2	1655.0	1654.8	1654.6	1654.5	1653.9	1652.8	1651.8	1650.9	1649.9	1651.4
160°	1674.0	1673.1	1672.2	1671.3	1670.5	1669.9	1669.6	1669.3	1669.0	1668.8	1670.5
162.5°	1690.7	1689.6	1688.6	1687.5	1686.4	1685.7	1685.4	1685.1	1684.8	1684.5	1686.2
165°	1712.0	1710.5	1709.1	1707.6	1706.2	1705.5	1705.5	1705.5	1705.5	1705.5	1707.8
167.5°	1728.8	1727.3	1725.8	1724.2	1722.7	1721.8	1721.7	1721.5	1721.3	1721.1	1723.7
170°	1738.2	1736.5	1734.6	1732.9	1731.2	1730.5	1730.7	1731.0	1731.3	1731.6	1733.9
172.5°	1744.4	1742.7	1741.0	1739.2	1737.5	1736.8	1737.1	1737.4	1737.6	1737.9	1740.2
175°	1751.3	1749.5	1747.8	1746.1	1744.2	1743.5	1743.8	1744.1	1744.4	1744.7	1747.4
177.5°	1754.4	1752.8	1751.1	1749.5	1747.9	1747.3	1747.8	1748.3	1748.7	1749.2	1751.0
180°	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3



TEST NUMBER: P333109-840

CATALOG NUMBER: S124RDIW-S1195D1340U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0
2.5°	2098.1	2101.3	2104.5	2105.9	2105.6	2105.3	2105.0	2104.8
5°	2084.2	2087.7	2091.3	2092.7	2092.0	2091.3	2090.6	2089.9
7.5°	2056.4	2058.7	2061.0	2061.5	2060.4	2059.3	2058.1	2057.0
10°	2031.4	2032.9	2034.4	2034.4	2032.9	2031.4	2030.0	2028.6
12.5°	2000.6	2001.6	2002.4	2001.8	1999.8	1997.8	1995.8	1993.8
15°	1946.5	1945.8	1945.1	1943.5	1941.0	1938.4	1936.0	1933.5
17.5°	1881.4	1879.4	1877.3	1874.5	1870.7	1866.8	1863.1	1859.3
20°	1835.8	1832.9	1830.1	1826.3	1821.7	1817.1	1812.3	1807.7
22.5°	1785.2	1780.9	1776.7	1772.6	1768.8	1764.9	1761.2	1757.4
25°	1703.5	1697.5	1691.4	1686.6	1682.9	1679.4	1675.8	1672.2
27.5°	1620.4	1612.9	1605.4	1599.0	1593.9	1588.7	1583.6	1578.4
30°	1560.7	1551.9	1542.9	1535.5	1529.7	1524.1	1518.3	1512.6
32.5°	1499.9	1489.4	1479.0	1471.2	1465.7	1460.3	1454.8	1449.4
35°	1409.2	1397.0	1384.8	1375.5	1369.1	1362.6	1356.1	1349.7
37.5°	1311.8	1298.2	1284.6	1274.6	1268.1	1261.6	1255.3	1248.8
40°	1247.1	1232.0	1217.0	1206.2	1199.7	1193.3	1186.9	1180.4
42.5°	1183.3	1167.9	1152.6	1141.6	1134.8	1128.1	1121.4	1114.6
45°	1085.6	1068.0	1050.5	1038.4	1032.1	1025.6	1019.2	1012.7
47.5°	987.2	969.1	950.9	938.2	931.1	924.0	916.9	909.8
50°	922.0	904.1	886.2	873.8	867.1	860.2	853.4	846.6
52.5°	857.0	838.8	820.5	807.9	800.8	793.8	786.6	779.5
55°	760.9	742.4	723.7	710.9	704.2	697.3	690.5	683.7
57.5°	667.2	648.2	629.3	617.3	612.2	606.9	601.8	596.6
60°	604.5	585.9	567.2	555.1	549.4	543.6	537.9	532.1
62.5°	542.9	525.7	508.5	497.6	493.0	488.5	483.8	479.3
65°	454.5	439.2	423.7	413.8	409.6	405.3	401.0	396.7
67.5°	373.4	360.1	346.9	337.9	333.2	328.4	323.7	318.9
70°	318.2	306.4	294.6	286.9	283.3	279.7	276.1	272.6
72.5°	268.7	258.6	248.5	241.9	238.5	235.3	232.0	228.6
75°	198.0	189.8	181.5	176.3	174.2	172.0	169.9	167.7
77.5°	140.1	135.2	130.5	127.7	127.0	126.4	125.8	125.1
80°	107.6	106.4	105.3	104.6	104.3	103.9	103.6	103.2
82.5°	83.6	82.8	82.0	81.4	81.1	80.7	80.4	80.0
85°	48.6	47.9	47.2	46.8	46.8	46.8	46.8	46.8
87.5°	23.9	24.0	24.0	24.3	24.7	25.1	25.5	26.0
90°	32.3	34.0	35.9	37.0	37.6	38.2	38.7	39.3
92.5°	31.3	33.0	34.7	35.6	35.9	36.0	36.1	36.2
95°	32.3	34.0	35.9	36.9	37.1	37.4	37.7	38.0
97.5°	34.9	35.1	35.2	35.5	35.9	36.1	36.4	36.7
100°	47.8	42.8	37.9	35.5	35.9	36.1	36.4	36.7
102.5°	171.0	117.5	64.1	37.5	37.6	37.6	37.7	37.8
105°	413.9	416.6	419.2	415.3	404.8	394.3	383.7	373.3
107.5°	512.1	513.4	514.6	515.8	516.9	518.1	519.2	520.3
110°	578.9	579.4	580.0	580.7	581.6	582.5	583.3	584.2





TEST NUMBER: P333109-840

CATALOG NUMBER: S124RDIW-S1195D1340U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	643.4	643.3	643.2	643.7	644.8	645.9	647.0	648.1
115°	739.9	740.5	741.0	741.3	741.3	741.3	741.3	741.3
117.5°	837.0	836.9	836.8	836.7	836.6	836.5	836.4	836.2
120°	897.1	897.7	898.3	898.3	897.7	897.1	896.6	896.0
122.5°	956.3	956.7	957.0	956.9	956.3	955.7	955.2	954.6
125°	1039.2	1040.1	1040.9	1041.5	1041.8	1042.1	1042.4	1042.7
127.5°	1121.5	1121.3	1121.1	1120.8	1120.6	1120.3	1120.1	1119.9
130°	1171.5	1171.8	1172.2	1172.4	1172.4	1172.4	1172.4	1172.4
132.5°	1220.8	1221.1	1221.4	1221.4	1221.2	1221.0	1220.7	1220.5
135°	1288.8	1289.3	1289.9	1290.5	1291.1	1291.6	1292.2	1292.8
137.5°	1353.8	1354.4	1355.1	1355.3	1355.1	1355.0	1354.8	1354.6
140°	1394.1	1395.0	1395.8	1396.4	1396.7	1397.0	1397.4	1397.7
142.5°	1431.4	1432.0	1432.7	1433.0	1433.1	1433.1	1433.2	1433.2
145°	1484.6	1484.9	1485.2	1485.7	1486.2	1486.8	1487.4	1488.0
147.5°	1531.5	1531.7	1531.9	1532.2	1532.5	1532.8	1533.0	1533.3
150°	1561.4	1561.4	1561.4	1561.5	1561.8	1562.1	1562.4	1562.7
152.5°	1587.4	1587.9	1588.3	1588.5	1588.3	1588.1	1588.0	1587.8
155°	1622.7	1623.8	1625.0	1625.1	1624.3	1623.4	1622.4	1621.6
157.5°	1652.9	1654.5	1656.0	1656.0	1654.5	1652.9	1651.4	1649.9
160°	1672.2	1674.0	1675.8	1675.8	1674.0	1672.2	1670.5	1668.8
162.5°	1688.0	1689.7	1691.4	1691.3	1689.4	1687.4	1685.4	1683.4
165°	1710.1	1712.4	1714.8	1714.5	1712.0	1709.4	1706.8	1704.1
167.5°	1726.3	1728.8	1731.4	1731.2	1728.3	1725.4	1722.5	1719.6
170°	1736.3	1738.6	1740.9	1740.6	1737.8	1734.8	1731.9	1729.0
172.5°	1742.5	1744.9	1747.3	1746.9	1743.6	1740.5	1737.4	1734.2
175°	1750.0	1752.6	1755.2	1754.7	1751.3	1747.8	1744.2	1740.8
177.5°	1752.9	1754.7	1756.7	1756.2	1753.3	1750.6	1747.8	1744.9
180°	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3

(END OF REPORT)