

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333706-927

Luminaire Tested: **S125RDIW-S1090D770U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333706-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S1090D770U927-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 770 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5778.3 lumens  
Efficiency: N/A  
Efficacy: 107.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 53.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333706-927

CATALOG NUMBER: S125RDIW-S1090D770U927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333706-927

CATALOG NUMBER: S125RDIW-S1090D770U927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63	58
1	100	96	92	88	93	89	86	83	77	75	73	66	65	63	56	55	54	49
2	91	84	78	72	85	78	73	68	68	64	61	59	56	53	50	48	46	42
3	83	74	67	61	77	69	63	57	60	55	51	52	48	45	44	42	39	36
4	76	66	58	52	71	61	54	49	54	48	44	47	42	39	40	37	34	31
5	70	59	50	44	65	55	48	42	48	42	38	42	37	34	36	33	30	27
6	65	53	44	39	60	49	42	37	44	38	33	38	33	30	33	29	26	24
7	60	48	40	34	56	45	38	32	40	34	29	35	30	26	30	26	24	21
8	56	43	36	30	52	41	34	29	36	30	26	32	27	24	28	24	21	19
9	52	40	32	27	48	37	31	26	33	28	24	29	25	21	26	22	19	17
10	49	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	17	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9144	9144	9144
5°	9166	9061	9117
10°	9096	8977	8977
15°	8988	8795	8723
20°	8849	8541	8438
25°	8688	8292	8109
30°	8486	7999	7744
35°	8280	7698	7335
40°	8088	7384	6933
45°	7853	7033	6495
50°	7618	6650	6038
55°	7346	6286	5551
60°	7073	5842	5028
65°	6748	5327	4429
70°	6381	4685	3816
75°	5871	3950	3174
80°	5170	3102	2663
85°	4357	2534	2379



TEST NUMBER: P333706-927

CATALOG NUMBER: S125RDIW-S1090D770U927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	133.1	2.3
10°-20°	372.1	6.4
20°-30°	539.6	9.3
30°-40°	614.9	10.6
40°-50°	599.4	10.4
50°-60°	504.6	8.7
60°-70°	353.7	6.1
70°-80°	181.8	3.1
80°-90°	47.6	0.8
90°-100°	28.8	0.5
100°-110°	177.3	3.1
110°-120°	321.6	5.6
120°-130°	412.8	7.1
130°-140°	444.0	7.7
140°-150°	416.7	7.2
150°-160°	337.1	5.8
160°-170°	218.0	3.8
170°-180°	75.2	1.3
0°-30°	1044.8	18.1
0°-40°	1659.7	28.7
0°-60°	2763.6	47.8
0°-90°	3346.7	57.9
90°-120°	527.8	9.1
90°-150°	1801.3	31.2
90°-180°	2432.0	42.1
0°-180°	5778.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1416	1416	1416	1416	1416	
5°	1414	1409	1398	1408	1406	134
15°	1344	1337	1315	1314	1305	379
25°	1219	1202	1164	1150	1138	561
35°	1050	1023	976	946	930	657
45°	860	827	770	729	711	663
55°	652	617	558	512	493	583
65°	442	404	349	307	290	437
75°	235	202	158	136	127	249
85°	59	40	34	33	32	66
90°	1	5	9	12	14	4
95°	33	31	9	12	12	43
105°	172	175	175	175	174	183
115°	324	327	328	325	322	321
125°	461	465	465	463	461	411
135°	575	578	577	576	572	443
145°	666	667	667	668	664	416
155°	734	730	731	733	728	338
165°	774	771	771	774	770	219
175°	792	789	789	793	788	75
180°	792	792	792	792	792	



TEST NUMBER: P333706-927

CATALOG NUMBER: S125RDIW-S1090D770U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9
2.5°	1418.5	1417.9	1417.4	1416.7	1416.2	1415.0	1413.1	1411.2	1409.3	1407.4	1409.3
5°	1413.8	1412.9	1411.9	1411.0	1410.0	1408.2	1405.6	1403.0	1400.3	1397.7	1400.1
7.5°	1399.9	1399.0	1398.0	1397.2	1396.2	1394.2	1391.1	1388.0	1384.8	1381.7	1383.4
10°	1387.0	1386.3	1385.6	1384.9	1384.2	1382.2	1378.9	1375.5	1372.2	1368.9	1369.6
12.5°	1372.5	1371.6	1370.7	1369.8	1368.9	1366.2	1361.8	1357.2	1352.8	1348.3	1348.8
15°	1344.3	1342.8	1341.4	1340.0	1338.6	1335.4	1330.4	1325.4	1320.4	1315.4	1315.2
17.5°	1312.4	1310.2	1308.1	1305.8	1303.6	1299.4	1293.2	1286.9	1280.6	1274.3	1273.1
20°	1287.6	1285.2	1282.9	1280.5	1278.1	1273.1	1265.5	1257.9	1250.3	1242.7	1241.5
22.5°	1260.2	1257.8	1255.5	1253.1	1250.7	1245.5	1237.5	1229.5	1221.5	1213.5	1211.2
25°	1219.2	1215.6	1212.0	1208.5	1204.9	1198.7	1189.9	1181.1	1172.4	1163.6	1160.5
27.5°	1172.1	1167.8	1163.4	1159.1	1154.8	1148.0	1138.5	1129.1	1119.7	1110.2	1106.0
30°	1137.9	1133.4	1128.9	1124.3	1119.8	1112.5	1102.6	1092.6	1082.6	1072.6	1067.1
32.5°	1104.5	1099.2	1093.9	1088.7	1083.4	1075.7	1065.5	1055.3	1045.1	1035.0	1029.0
35°	1050.2	1044.5	1038.8	1033.1	1027.4	1019.1	1008.4	997.8	987.1	976.4	969.5
37.5°	996.9	990.0	983.0	976.1	969.2	960.2	949.1	938.1	927.1	916.1	907.8
40°	959.3	952.1	945.0	937.9	930.7	921.5	910.1	898.7	887.2	875.8	866.8
42.5°	919.9	912.6	905.3	897.9	890.7	881.1	869.3	857.5	845.7	833.9	825.3
45°	859.8	852.9	846.1	839.2	832.3	822.3	809.2	796.1	783.1	770.0	760.5
47.5°	797.6	790.3	783.0	775.8	768.5	758.3	745.1	731.9	718.7	705.6	695.8
50°	758.2	750.4	742.5	734.7	726.8	716.1	702.6	689.0	675.5	661.9	652.0
52.5°	715.4	707.4	699.3	691.3	683.3	672.9	660.1	647.3	634.5	621.8	611.0
55°	652.4	644.8	637.2	629.5	621.9	611.5	598.2	584.9	571.6	558.3	547.6
57.5°	588.6	580.5	572.4	564.2	556.1	545.7	532.8	520.0	507.2	494.3	483.9
60°	547.6	539.2	530.9	522.6	514.3	503.7	490.8	478.0	465.2	452.3	441.9
62.5°	503.9	496.0	488.1	480.1	472.1	461.7	448.7	435.6	422.6	409.6	399.9
65°	441.6	433.6	425.5	417.4	409.3	399.0	386.4	373.8	361.2	348.6	339.1
67.5°	379.9	371.8	363.7	355.6	347.5	337.5	325.3	313.3	301.3	289.1	280.5
70°	337.9	329.9	321.8	313.7	305.6	295.6	283.8	271.9	260.0	248.1	240.7
72.5°	296.9	289.0	281.1	273.2	265.3	255.8	244.7	233.5	222.4	211.4	204.5
75°	235.3	228.1	221.0	213.9	206.8	198.2	188.2	178.2	168.3	158.3	153.0
77.5°	174.1	168.4	162.7	157.0	151.3	144.4	136.5	128.5	120.5	112.5	108.8
80°	139.0	133.3	127.6	121.9	116.2	110.0	103.4	96.7	90.1	83.4	81.3
82.5°	104.8	99.7	94.5	89.4	84.3	79.5	74.9	70.3	65.8	61.2	60.2
85°	58.8	54.5	50.2	45.9	41.7	39.0	37.8	36.6	35.4	34.2	34.0
87.5°	19.8	18.7	17.6	16.4	15.3	14.7	14.7	14.7	14.7	14.7	14.8
90°	0.6	1.7	2.7	3.7	4.8	5.7	6.7	7.6	8.5	9.4	10.1
92.5°	9.0	8.3	7.6	6.8	6.1	6.2	7.0	7.8	8.6	9.4	10.1
95°	33.4	33.0	32.6	32.3	31.9	29.2	24.2	19.3	14.3	9.4	10.1
97.5°	69.9	70.6	71.3	71.9	72.6	68.1	58.3	48.5	38.7	28.9	25.2
100°	98.0	98.4	98.8	99.2	99.6	100.1	100.6	101.1	101.6	102.1	82.7
102.5°	126.7	127.1	127.7	128.2	128.7	129.0	129.4	129.7	130.0	130.3	126.7
105°	172.5	173.1	173.6	174.1	174.7	174.9	174.9	174.9	174.9	174.9	174.9
107.5°	220.2	220.2	220.2	220.2	220.2	220.4	220.6	220.9	221.2	221.4	221.4
110°	251.2	251.2	251.2	251.2	251.2	251.4	251.6	251.9	252.2	252.4	252.0



TEST NUMBER: P333706-927

CATALOG NUMBER: S125RDIW-S1090D770U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	280.4	280.7	281.0	281.3	281.6	281.9	282.0	282.2	282.3	282.5	281.9
115°	324.0	324.6	325.3	326.0	326.6	327.0	327.2	327.3	327.4	327.6	327.0
117.5°	369.2	369.2	369.2	369.2	369.1	369.3	369.9	370.3	370.8	371.3	370.7
120°	397.4	397.3	397.1	397.0	396.9	397.0	397.4	397.8	398.2	398.5	398.3
122.5°	422.2	422.8	423.3	423.7	424.3	424.6	424.8	424.9	425.2	425.3	425.1
125°	460.8	461.7	462.6	463.5	464.5	464.9	464.9	464.9	464.9	464.9	464.4
127.5°	497.5	498.2	498.8	499.5	500.1	500.4	500.3	500.3	500.2	500.1	499.8
130°	520.1	520.7	521.3	522.0	522.7	523.1	523.2	523.3	523.5	523.6	523.2
132.5°	542.6	543.4	544.2	544.9	545.7	545.9	545.6	545.3	545.0	544.7	544.6
135°	574.6	575.4	576.2	577.0	577.8	578.1	577.8	577.5	577.3	577.0	576.7
137.5°	604.1	604.8	605.5	606.2	606.8	607.0	606.8	606.6	606.3	606.1	606.2
140°	623.4	623.6	623.9	624.2	624.4	624.5	624.3	624.2	624.1	623.9	624.2
142.5°	640.7	640.9	641.0	641.2	641.4	641.5	641.7	641.9	642.1	642.3	642.3
145°	666.2	666.5	666.8	667.0	667.3	667.4	667.4	667.4	667.4	667.4	667.5
147.5°	688.6	688.5	688.4	688.4	688.3	688.4	688.6	688.6	688.8	689.0	689.1
150°	702.6	702.3	702.1	701.8	701.6	701.6	701.8	702.1	702.3	702.6	702.9
152.5°	716.2	715.7	715.1	714.5	713.9	713.8	714.1	714.3	714.5	714.8	715.1
155°	733.7	732.9	732.1	731.3	730.6	730.3	730.6	730.9	731.1	731.3	731.7
157.5°	747.2	746.8	746.3	745.8	745.4	745.1	745.1	745.2	745.2	745.2	745.7
160°	756.6	755.8	755.0	754.2	753.5	753.1	753.3	753.4	753.5	753.7	754.2
162.5°	764.1	763.3	762.6	761.8	761.0	760.7	760.8	761.0	761.0	761.2	761.9
165°	774.2	773.4	772.7	771.9	771.1	770.8	770.9	771.0	771.2	771.3	772.1
167.5°	781.7	780.9	780.1	779.3	778.5	778.2	778.3	778.4	778.6	778.7	779.6
170°	786.0	785.1	784.1	783.2	782.3	781.9	782.0	782.2	782.3	782.4	783.5
172.5°	788.8	787.9	787.0	786.0	785.1	784.8	785.1	785.3	785.5	785.8	786.6
175°	791.9	791.1	790.3	789.5	788.7	788.4	788.5	788.6	788.8	788.9	790.0
177.5°	793.2	792.6	792.0	791.4	790.8	790.4	790.6	790.7	790.8	790.9	791.6
180°	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9



TEST NUMBER: P333706-927

CATALOG NUMBER: S125RDIW-S1090D770U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9
2.5°	1411.2	1413.1	1415.0	1415.8	1415.6	1415.5	1415.2	1415.1
5°	1402.5	1404.9	1407.2	1408.2	1407.7	1407.2	1406.8	1406.3
7.5°	1385.1	1386.7	1388.4	1388.9	1388.4	1387.9	1387.3	1386.8
10°	1370.3	1371.0	1371.7	1371.7	1371.0	1370.3	1369.6	1368.9
12.5°	1349.4	1349.9	1350.4	1350.1	1349.0	1348.0	1346.9	1345.8
15°	1314.9	1314.7	1314.5	1313.3	1311.1	1309.0	1306.9	1304.7
17.5°	1271.9	1270.7	1269.6	1268.1	1266.3	1264.6	1262.8	1261.1
20°	1240.3	1239.1	1237.9	1236.3	1234.1	1232.0	1229.9	1227.7
22.5°	1208.9	1206.6	1204.3	1202.2	1200.5	1198.7	1196.9	1195.2
25°	1157.4	1154.3	1151.2	1148.3	1145.7	1143.1	1140.5	1137.9
27.5°	1101.6	1097.3	1093.0	1089.6	1087.0	1084.5	1082.0	1079.5
30°	1061.7	1056.2	1050.8	1046.9	1044.8	1042.7	1040.5	1038.4
32.5°	1022.9	1016.8	1010.8	1006.5	1003.8	1001.1	998.3	995.6
35°	962.6	955.7	948.8	943.7	940.4	937.1	933.7	930.4
37.5°	899.5	891.3	883.0	877.3	874.0	870.8	867.5	864.3
40°	857.8	848.7	839.7	833.8	830.9	828.1	825.2	822.4
42.5°	816.7	807.9	799.3	792.9	788.7	784.6	780.4	776.2
45°	751.0	741.5	732.0	725.4	721.8	718.3	714.7	711.1
47.5°	686.0	676.2	666.5	659.6	655.6	651.6	647.8	643.8
50°	642.0	632.0	622.0	615.3	611.7	608.2	604.6	601.0
52.5°	600.3	589.5	578.8	571.6	568.1	564.5	560.9	557.4
55°	536.9	526.2	515.5	508.2	504.4	500.6	496.8	493.0
57.5°	473.4	463.0	452.5	445.5	442.2	438.8	435.4	432.1
60°	431.4	421.0	410.5	403.5	400.0	396.4	392.8	389.3
62.5°	390.2	380.5	370.8	364.2	360.6	357.0	353.5	349.9
65°	329.6	320.1	310.6	304.0	300.5	296.9	293.3	289.8
67.5°	271.8	263.1	254.4	248.6	245.7	242.9	240.0	237.2
70°	233.4	226.0	218.6	213.5	210.6	207.8	204.9	202.1
72.5°	197.7	190.9	184.1	179.7	177.8	175.9	174.0	172.1
75°	147.8	142.6	137.4	133.9	132.2	130.6	128.9	127.2
77.5°	105.2	101.6	97.8	95.4	94.2	92.9	91.7	90.5
80°	79.1	77.0	74.9	73.5	73.0	72.6	72.1	71.6
82.5°	59.2	58.1	57.2	56.6	56.2	55.9	55.7	55.4
85°	33.7	33.5	33.3	33.0	32.8	32.6	32.3	32.1
87.5°	15.0	15.1	15.2	15.2	15.1	15.1	14.9	14.8
90°	10.7	11.3	12.0	12.5	12.9	13.3	13.7	14.1
92.5°	10.7	11.3	12.0	12.4	12.6	12.8	13.0	13.2
95°	10.7	11.3	12.0	12.4	12.4	12.4	12.4	12.4
97.5°	21.5	17.8	14.2	12.4	12.4	12.4	12.4	12.4
100°	63.3	43.8	24.4	14.4	13.9	13.4	12.8	12.4
102.5°	122.9	119.3	115.6	109.3	100.4	91.6	82.7	73.8
105°	174.9	174.9	174.9	174.8	174.8	174.6	174.4	174.4
107.5°	221.5	221.5	221.5	221.3	220.9	220.5	220.1	219.8
110°	251.6	251.2	250.8	250.7	250.8	251.0	251.1	251.2





TEST NUMBER: P333706-927

CATALOG NUMBER: S125RDIW-S1090D770U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	281.5	281.0	280.4	280.1	280.0	279.8	279.6	279.4
115°	326.5	326.0	325.4	324.8	324.0	323.2	322.4	321.6
117.5°	369.9	369.3	368.6	368.1	367.7	367.4	367.1	366.8
120°	398.1	397.8	397.5	397.0	396.4	395.8	395.1	394.4
122.5°	424.8	424.5	424.3	423.7	423.0	422.2	421.5	420.7
125°	463.8	463.3	462.8	462.3	461.9	461.5	461.2	460.8
127.5°	499.6	499.2	499.0	498.4	497.3	496.4	495.4	494.5
130°	522.8	522.4	522.0	521.5	520.9	520.2	519.5	518.9
132.5°	544.5	544.5	544.4	544.1	543.4	542.7	542.1	541.5
135°	576.5	576.2	576.0	575.4	574.6	573.9	573.1	572.3
137.5°	606.3	606.3	606.3	606.0	605.3	604.7	604.0	603.3
140°	624.5	624.7	625.0	624.7	623.9	623.2	622.4	621.6
142.5°	642.4	642.5	642.5	642.1	641.4	640.6	639.8	639.0
145°	667.7	667.8	667.9	667.6	666.8	666.0	665.3	664.5
147.5°	689.3	689.4	689.6	689.2	688.3	687.4	686.4	685.5
150°	703.1	703.4	703.7	703.3	702.2	701.2	700.1	699.1
152.5°	715.3	715.6	715.9	715.5	714.5	713.7	712.7	711.8
155°	732.1	732.5	732.9	732.6	731.6	730.6	729.5	728.4
157.5°	746.1	746.5	746.9	746.6	745.5	744.5	743.5	742.4
160°	754.7	755.3	755.7	755.5	754.5	753.4	752.4	751.3
162.5°	762.6	763.3	764.1	763.9	762.8	761.6	760.5	759.3
165°	772.9	773.6	774.4	774.3	773.2	772.2	771.2	770.1
167.5°	780.5	781.5	782.4	782.4	781.2	780.0	778.8	777.6
170°	784.5	785.6	786.6	786.6	785.4	784.2	783.0	781.9
172.5°	787.6	788.5	789.5	789.3	788.2	787.0	785.8	784.7
175°	791.0	792.0	793.1	793.0	791.9	790.7	789.5	788.3
177.5°	792.3	793.1	793.8	793.8	792.9	792.1	791.2	790.4
180°	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9

(END OF REPORT)