

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333100-840

Luminaire Tested: **S124RDIW-S1195D770U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333100-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S1195D770U840-4F0-1E-UDD-A1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7750.2 lumens  
Efficiency: N/A  
Efficacy: 129.6 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 59.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333100-840

CATALOG NUMBER: S124RDIW-S1195D770U840-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333100-840

CATALOG NUMBER: S124RDIW-S1195D770U840-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	70	70	70	65
1	102	98	94	91	96	92	89	86	82	79	77	72	70	68	63	62	61	56
2	93	86	80	75	87	81	76	71	72	68	65	64	61	58	56	54	52	48
3	85	76	69	63	80	72	66	60	64	59	55	57	53	50	50	47	45	41
4	78	68	60	54	74	64	57	52	57	52	47	51	47	43	45	42	39	36
5	72	61	53	47	68	58	50	45	52	46	41	46	41	38	41	37	34	32
6	67	55	47	41	63	52	45	39	47	41	36	42	37	33	37	34	30	28
7	62	50	42	36	58	47	40	35	43	37	32	38	33	30	34	30	27	25
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	32	28	25	22
9	54	41	34	29	51	40	33	28	36	30	26	32	28	24	29	25	22	20
10	50	38	31	26	47	36	30	25	33	28	24	30	25	22	27	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	16156	16156	16156	16156
5°	18739	16204	14323	16204
10°	22168	16133	12782	16133
15°	25607	15984	10984	15984
20°	28511	15779	9933	15779
25°	29432	15577	9222	15577
30°	25765	15333	8793	15333
35°	20056	14970	8535	14970
40°	15039	14556	8395	14556
45°	11875	13891	8322	13891
50°	10025	13123	8081	13123
55°	8739	12279	7648	12279
60°	7863	11404	6770	11404
65°	6930	10457	5822	10457
70°	6243	9477	5254	9477
75°	5231	8400	4476	8400
80°	4421	7159	4198	7159
85°	3733	5604	3733	5604



TEST NUMBER: P333100-840

CATALOG NUMBER: S124RDIW-S1195D770U840-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	193.9	2.5
10°-20°	584.9	7.5
20°-30°	914.8	11.8
30°-40°	1017.0	13.1
40°-50°	902.3	11.6
50°-60°	703.1	9.1
60°-70°	460.3	5.9
70°-80°	226.4	2.9
80°-90°	58.8	0.8
90°-100°	63.9	0.8
100°-110°	189.3	2.4
110°-120°	321.4	4.1
120°-130°	423.8	5.5
130°-140°	475.9	6.1
140°-150°	467.7	6.0
150°-160°	393.4	5.1
160°-170°	261.7	3.4
170°-180°	91.6	1.2
0°-30°	1693.6	21.9
0°-40°	2710.6	35.0
0°-60°	4316.0	55.7
0°-90°	5061.5	65.3
90°-120°	574.6	7.4
90°-150°	1942.0	25.1
90°-180°	2689.0	34.7
0°-180°	7750.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	2001	2001	2001	2001	2001	
5°	2312	2000	1767	2000	2312	234
15°	3064	1912	1314	1912	3064	871
25°	3304	1749	1035	1749	3304	1466
35°	2035	1519	866	1519	2035	1276
45°	1040	1217	729	1217	1040	824
55°	621	872	543	872	621	565
65°	363	547	305	547	363	365
75°	168	269	144	269	168	185
85°	40	60	40	60	40	46
90°	22	2	22	2	22	13
95°	59	45	59	45	59	62
105°	183	175	183	175	183	193
115°	324	327	324	327	324	320
125°	472	476	472	476	472	421
135°	615	614	615	614	615	475
145°	746	746	746	746	746	467
155°	854	854	854	854	854	393
165°	928	930	928	930	928	261
175°	963	968	963	968	963	91
180°	969	969	969	969	969	



TEST NUMBER: P333100-840

CATALOG NUMBER: S124RDIW-S1195D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2
2.5°	2110.8	2116.7	2110.8	2110.2	2103.8	2101.8	2099.2	2090.8	2075.4	2066.4	2068.3
5°	2312.4	2332.6	2321.3	2319.7	2302.0	2284.2	2272.9	2247.2	2219.7	2201.2	2185.9
7.5°	2545.6	2557.2	2550.1	2538.8	2510.1	2493.9	2467.7	2433.7	2384.5	2346.9	2312.6
10°	2704.3	2713.9	2710.8	2689.8	2668.8	2626.1	2601.9	2554.4	2492.2	2443.1	2397.1
12.5°	2860.3	2870.7	2842.4	2843.3	2803.6	2770.0	2731.6	2671.7	2600.0	2536.6	2479.0
15°	3063.9	3051.0	3051.0	3034.8	2990.5	2943.8	2904.3	2841.4	2751.1	2675.2	2595.5
17.5°	3223.2	3227.7	3221.1	3183.1	3148.3	3099.9	3027.5	2954.1	2870.2	2768.4	2686.8
20°	3318.7	3318.7	3311.4	3285.6	3240.5	3188.9	3110.7	3030.8	2924.4	2822.0	2730.1
22.5°	3357.4	3359.9	3351.4	3330.1	3289.5	3239.1	3172.6	3091.5	2981.8	2866.5	2752.7
25°	3304.2	3319.5	3321.0	3315.5	3303.4	3272.7	3215.5	3132.4	3034.0	2909.1	2786.5
27.5°	3033.5	3052.9	3069.9	3097.8	3134.8	3154.2	3156.7	3114.5	3028.7	2908.4	2785.1
30°	2763.9	2780.1	2832.5	2901.0	2954.3	3002.6	3044.5	3055.9	3007.5	2899.4	2769.6
32.5°	2464.7	2486.6	2539.0	2612.7	2701.4	2783.3	2877.5	2925.5	2924.3	2859.4	2739.3
35°	2035.1	2051.2	2099.6	2177.0	2283.4	2405.2	2554.4	2670.4	2749.5	2743.8	2670.4
37.5°	1641.2	1659.5	1708.4	1772.5	1875.7	2026.5	2170.8	2330.8	2476.9	2559.0	2534.5
40°	1427.1	1427.9	1475.5	1541.7	1638.4	1769.8	1927.0	2104.4	2267.2	2400.3	2426.1
42.5°	1258.1	1258.3	1289.7	1361.0	1430.7	1554.4	1704.5	1880.6	2071.2	2224.8	2293.2
45°	1040.1	1047.3	1073.2	1115.9	1170.7	1275.6	1395.6	1559.3	1773.0	1955.2	2068.9
47.5°	880.8	891.4	907.9	942.7	986.4	1056.2	1155.6	1302.6	1476.4	1676.9	1838.7
50°	798.2	799.8	820.8	840.1	878.1	933.7	1020.8	1143.3	1302.9	1495.6	1675.5
52.5°	727.3	726.9	739.5	764.1	794.9	838.2	908.5	1020.1	1161.6	1334.4	1520.0
55°	620.9	624.9	634.5	653.9	677.3	707.9	763.6	847.4	958.7	1106.2	1274.8
57.5°	539.9	542.0	549.6	557.7	579.3	601.5	643.3	701.5	795.4	916.1	1073.2
60°	487.0	487.8	490.2	502.3	519.3	540.2	568.5	617.6	696.6	807.1	931.3
62.5°	435.4	436.9	440.6	449.4	462.5	477.0	506.5	546.0	611.5	705.8	817.7
65°	362.8	363.7	369.3	372.5	382.9	395.9	417.7	444.2	489.4	568.5	653.1
67.5°	303.2	303.2	303.5	307.8	315.1	323.7	336.7	358.0	392.0	440.6	515.2
70°	264.5	264.5	266.1	268.5	272.6	279.7	287.0	303.2	328.2	367.7	425.0
72.5°	228.3	228.9	230.6	231.1	233.2	239.1	244.5	254.8	273.4	303.2	349.4
75°	167.7	170.2	174.2	177.4	181.4	180.6	186.2	192.7	198.3	216.1	242.7
77.5°	124.8	123.5	124.0	126.7	127.2	128.1	132.1	137.0	141.3	149.7	159.2
80°	95.1	95.1	97.6	98.4	97.6	98.4	102.4	104.8	106.4	109.7	118.6
82.5°	71.9	73.2	72.4	73.2	73.7	74.5	77.9	78.4	80.0	81.3	85.0
85°	40.3	41.1	41.9	40.3	40.3	40.3	41.9	42.7	44.3	43.5	45.1
87.5°	18.7	18.0	18.6	18.5	19.1	18.3	18.8	19.8	18.4	18.8	18.5
90°	22.5	22.1	21.8	21.5	21.1	20.5	19.5	18.5	17.5	16.5	15.1
92.5°	33.3	33.1	32.9	32.7	32.5	32.1	31.5	30.9	30.3	29.7	28.8
95°	59.2	59.2	59.2	59.2	59.2	59.0	58.5	58.0	57.5	57.0	55.8
97.5°	92.8	92.8	92.8	92.8	92.8	92.5	91.9	91.3	90.7	90.1	88.8
100°	116.1	116.1	116.1	116.1	116.1	116.0	115.6	115.3	115.0	114.7	113.2
102.5°	142.6	142.4	142.3	142.2	142.0	141.7	141.3	140.8	140.4	139.9	138.5
105°	182.9	182.4	181.9	181.4	180.9	180.4	179.9	179.4	178.8	178.3	177.7
107.5°	222.2	222.2	222.3	222.3	222.3	222.1	221.6	221.2	220.7	220.3	220.2
110°	250.3	249.8	249.3	248.8	248.3	248.2	248.6	248.9	249.2	249.5	249.7



TEST NUMBER: P333100-840

CATALOG NUMBER: S124RDIW-S1195D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	279.1	279.0	278.9	278.8	278.7	278.7	278.7	278.8	278.9	278.9	279.2
115°	323.8	324.0	324.2	324.3	324.5	324.6	324.8	325.0	325.1	325.3	325.6
117.5°	366.4	366.7	367.0	367.4	367.7	368.1	368.7	369.3	369.8	370.4	370.6
120°	398.7	398.4	398.1	397.8	397.4	397.7	398.5	399.3	400.1	401.0	401.5
122.5°	425.8	426.4	426.9	427.5	428.1	428.7	429.3	429.8	430.4	431.0	431.2
125°	472.2	472.5	472.8	473.2	473.5	473.8	474.2	474.5	474.8	475.1	475.3
127.5°	515.2	515.4	515.7	516.0	516.2	516.5	516.9	517.3	517.6	518.0	518.2
130°	543.4	544.0	544.7	545.4	546.0	546.5	546.8	547.2	547.5	547.9	547.9
132.5°	573.4	573.6	573.9	574.2	574.4	574.7	575.1	575.4	575.7	576.0	576.2
135°	614.6	615.1	615.6	616.1	616.6	617.0	617.3	617.6	618.0	618.3	618.3
137.5°	657.9	657.8	657.7	657.6	657.5	657.7	658.1	658.5	658.9	659.4	659.1
140°	684.3	684.5	684.6	684.8	685.0	685.1	685.3	685.5	685.6	685.8	685.8
142.5°	710.6	710.7	710.7	710.7	710.8	710.8	710.8	710.9	710.9	710.9	711.1
145°	746.5	747.0	747.5	748.0	748.5	748.8	749.0	749.2	749.3	749.5	749.3
147.5°	782.7	782.9	783.2	783.3	783.5	783.6	783.8	783.9	784.0	784.2	784.3
150°	805.0	805.2	805.3	805.5	805.7	805.8	805.8	805.8	805.8	805.8	805.8
152.5°	825.4	825.8	826.3	826.7	827.1	827.1	826.7	826.3	825.9	825.5	825.4
155°	853.7	854.3	855.1	855.7	856.4	856.4	855.7	855.1	854.3	853.7	853.8
157.5°	879.0	879.6	880.2	880.7	881.3	881.3	880.8	880.3	879.8	879.3	879.4
160°	893.4	894.2	895.0	896.0	896.8	897.0	896.5	896.0	895.4	894.9	895.0
162.5°	908.4	909.3	910.1	910.9	911.7	911.7	910.8	909.9	909.0	908.1	908.3
165°	927.9	928.6	929.2	929.9	930.6	930.4	929.4	928.4	927.4	926.3	926.8
167.5°	941.8	942.9	943.9	944.9	945.9	945.9	944.9	944.0	943.0	942.0	941.9
170°	949.7	950.8	952.0	953.1	954.3	954.4	953.4	952.4	951.4	950.4	950.2
172.5°	956.2	957.4	958.6	959.7	960.9	960.9	959.8	958.7	957.6	956.3	956.3
175°	963.1	964.3	965.4	966.6	967.8	967.8	966.6	965.4	964.3	963.1	963.3
177.5°	966.7	967.8	968.9	969.9	971.0	971.1	970.1	969.2	968.3	967.3	967.3
180°	969.1	969.1	969.1	969.1	969.1	969.1	969.1	969.1	969.1	969.1	969.1



TEST NUMBER: P333100-840

CATALOG NUMBER: S124RDIW-S1195D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2
2.5°	2061.8	2052.9	2048.3	2038.0	2025.7	2019.2	2013.5	2005.1	1994.1	1982.5	1974.1
5°	2166.5	2147.2	2122.9	2094.0	2068.1	2043.2	2021.3	1999.6	1974.6	1948.8	1923.0
7.5°	2273.9	2235.8	2194.7	2147.2	2100.8	2058.8	2020.0	1983.0	1941.1	1903.5	1869.3
10°	2348.7	2297.1	2239.9	2179.4	2118.9	2066.5	2014.9	1968.1	1916.5	1870.6	1831.9
12.5°	2409.3	2348.7	2279.9	2204.5	2131.8	2068.4	2009.1	1948.1	1889.5	1839.7	1788.1
15°	2509.9	2426.9	2334.2	2243.9	2149.6	2063.3	1983.5	1912.5	1845.6	1775.4	1726.3
17.5°	2579.2	2480.6	2367.9	2259.4	2148.0	2046.2	1954.1	1869.7	1792.4	1720.8	1662.2
20°	2620.4	2511.5	2386.6	2263.2	2138.3	2029.4	1930.3	1836.7	1756.9	1679.5	1619.0
22.5°	2643.6	2523.1	2386.6	2257.5	2128.0	2010.0	1901.2	1803.8	1716.9	1639.5	1572.6
25°	2651.1	2522.0	2382.6	2234.2	2092.3	1967.3	1854.4	1748.8	1652.0	1574.7	1503.7
27.5°	2640.8	2488.8	2346.0	2193.7	2047.3	1915.6	1797.1	1686.1	1589.2	1506.1	1433.4
30°	2625.2	2462.4	2309.2	2151.2	2002.8	1876.2	1751.2	1644.9	1544.1	1457.7	1384.4
32.5°	2591.7	2430.1	2265.3	2103.4	1953.2	1822.7	1704.1	1597.1	1498.2	1410.1	1332.1
35°	2525.3	2361.6	2182.6	2016.5	1869.0	1733.5	1622.2	1519.0	1424.7	1330.4	1248.1
37.5°	2437.7	2270.5	2092.4	1910.6	1762.8	1635.0	1532.9	1436.0	1343.9	1257.8	1166.7
40°	2355.2	2202.8	2018.9	1838.4	1686.8	1563.4	1469.1	1381.2	1288.5	1203.0	1111.9
42.5°	2255.2	2125.4	1939.6	1758.4	1608.7	1489.9	1402.0	1316.1	1231.7	1148.8	1053.8
45°	2088.3	1989.9	1815.7	1641.6	1490.9	1373.1	1292.5	1216.7	1142.5	1063.5	974.0
47.5°	1897.0	1830.4	1680.1	1501.8	1362.3	1256.4	1178.5	1116.5	1053.8	974.8	896.3
50°	1764.1	1721.4	1576.3	1413.4	1280.4	1182.9	1103.0	1044.9	992.5	916.8	846.6
52.5°	1622.2	1599.5	1476.9	1321.2	1192.7	1097.0	1028.9	976.5	923.5	860.6	795.0
55°	1406.1	1418.3	1314.2	1179.6	1058.6	978.1	915.9	872.4	827.3	774.1	723.3
57.5°	1185.3	1229.4	1159.6	1041.4	928.1	853.5	806.8	770.1	732.3	688.1	644.7
60°	1053.0	1090.0	1050.6	946.5	847.4	778.1	734.6	706.3	668.4	628.1	595.0
62.5°	924.0	963.7	940.3	856.3	764.2	704.6	666.1	639.9	611.7	576.5	542.2
65°	761.9	787.7	776.5	718.4	653.1	602.3	566.8	547.4	521.7	495.8	465.2
67.5°	583.6	633.4	626.8	596.0	539.6	499.9	476.7	459.6	436.1	416.9	396.1
70°	479.8	525.7	524.9	499.9	469.3	432.1	416.1	401.5	380.5	362.0	345.1
72.5°	392.6	434.7	441.0	421.8	400.9	372.8	357.4	347.4	327.0	314.3	300.5
75°	275.0	305.6	313.7	313.7	304.0	289.4	275.8	269.3	254.8	243.5	235.4
77.5°	180.3	199.7	212.2	215.1	216.6	211.8	200.5	195.9	184.8	180.8	173.0
80°	127.3	140.3	154.8	159.7	163.7	162.1	157.2	154.0	143.5	139.5	136.2
82.5°	88.1	95.1	107.0	117.8	116.5	120.8	116.5	114.0	106.1	104.6	101.4
85°	45.9	46.8	48.4	55.6	59.7	61.3	62.1	60.5	58.1	58.1	52.4
87.5°	18.3	17.4	18.4	18.1	18.3	20.5	22.1	22.4	20.8	19.3	17.7
90°	13.8	12.5	11.2	9.6	7.8	6.0	4.0	2.2	4.0	6.0	7.8
92.5°	27.8	26.9	26.0	24.4	22.3	20.2	18.2	16.1	18.2	20.2	22.3
95°	54.6	53.4	52.3	51.0	49.5	48.0	46.5	44.9	46.5	48.0	49.5
97.5°	87.4	86.0	84.6	83.3	82.1	81.0	79.8	78.6	79.8	81.0	82.1
100°	111.7	110.2	108.7	107.6	106.9	106.2	105.6	104.9	105.6	106.2	106.9
102.5°	137.1	135.7	134.4	133.6	133.3	133.0	132.8	132.5	132.8	133.0	133.3
105°	177.0	176.4	175.7	175.3	175.1	175.0	174.8	174.6	174.8	175.0	175.1
107.5°	220.0	219.9	219.8	219.6	219.4	219.2	219.0	218.8	219.0	219.2	219.4
110°	249.9	250.0	250.2	250.1	249.8	249.5	249.1	248.8	249.1	249.5	249.8





TEST NUMBER: P333100-840

CATALOG NUMBER: S124RDIW-S1195D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	279.5	279.8	280.1	280.2	280.2	280.1	280.0	280.0	280.0	280.1	280.2
115°	326.0	326.3	326.6	326.8	326.8	326.8	326.8	326.8	326.8	326.8	326.8
117.5°	370.9	371.1	371.3	371.4	371.2	371.1	371.0	370.8	371.0	371.1	371.2
120°	402.0	402.5	402.9	402.9	402.2	401.5	400.9	400.2	400.9	401.5	402.2
122.5°	431.4	431.7	431.9	431.9	431.6	431.3	431.1	430.8	431.1	431.3	431.6
125°	475.5	475.6	475.8	475.9	475.9	475.9	475.9	475.9	475.9	475.9	475.9
127.5°	518.5	518.7	519.0	518.9	518.4	517.9	517.4	516.8	517.4	517.9	518.4
130°	547.9	547.9	547.9	547.6	547.1	546.6	546.1	545.6	546.1	546.6	547.1
132.5°	576.3	576.4	576.6	576.5	576.1	575.7	575.4	575.0	575.4	575.7	576.1
135°	618.3	618.3	618.3	617.8	616.8	615.8	614.8	613.9	614.8	615.8	616.8
137.5°	658.8	658.6	658.3	658.0	657.5	657.0	656.6	656.1	656.6	657.0	657.5
140°	685.8	685.8	685.8	685.6	685.3	685.0	684.6	684.3	684.6	685.0	685.3
142.5°	711.2	711.3	711.6	711.4	711.0	710.7	710.4	710.0	710.4	710.7	711.0
145°	749.2	749.0	748.8	748.4	747.8	747.1	746.4	745.8	746.4	747.1	747.8
147.5°	784.4	784.6	784.7	784.4	783.6	782.7	781.9	781.1	781.9	782.7	783.6
150°	805.8	805.8	805.8	805.4	804.8	804.1	803.3	802.7	803.3	804.1	804.8
152.5°	825.3	825.1	825.0	824.8	824.4	823.9	823.5	823.1	823.5	823.9	824.4
155°	854.0	854.1	854.3	854.4	854.4	854.4	854.4	854.4	854.4	854.4	854.4
157.5°	879.4	879.4	879.5	879.6	879.9	880.2	880.5	880.8	880.5	880.2	879.9
160°	895.2	895.4	895.5	895.8	896.0	896.1	896.3	896.5	896.3	896.1	896.0
162.5°	908.5	908.6	908.8	909.1	909.5	909.9	910.4	910.8	910.4	909.9	909.5
165°	927.1	927.4	927.8	928.2	928.7	929.2	929.7	930.2	929.7	929.2	928.7
167.5°	941.9	941.9	941.8	942.2	942.9	943.6	944.3	944.9	944.3	943.6	942.9
170°	950.1	949.9	949.7	950.1	950.9	951.7	952.5	953.4	952.5	951.7	950.9
172.5°	956.3	956.2	956.2	956.5	957.3	958.0	958.7	959.4	958.7	958.0	957.3
175°	963.4	963.6	963.8	964.3	965.1	965.9	966.7	967.7	966.7	965.9	965.1
177.5°	967.3	967.3	967.3	967.7	968.4	969.0	969.7	970.3	969.7	969.0	968.4
180°	969.1	969.1	969.1	969.1	969.1	969.1	969.1	969.1	969.1	969.1	969.1



TEST NUMBER: P333100-840

CATALOG NUMBER: S124RDIW-S1195D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2
2.5°	1965.1	1958.6	1950.3	1940.6	1928.9	1918.6	1914.1	1918.0	1920.0	1914.8	1914.1
5°	1905.2	1885.1	1869.0	1844.8	1825.4	1809.3	1798.1	1793.2	1794.8	1781.9	1778.7
7.5°	1838.1	1814.1	1787.7	1759.0	1732.2	1708.5	1696.1	1689.3	1675.7	1669.8	1660.0
10°	1794.8	1762.5	1736.8	1702.8	1672.2	1644.1	1630.3	1619.0	1605.3	1598.8	1585.2
12.5°	1750.3	1712.8	1684.5	1649.3	1618.0	1584.1	1570.9	1550.0	1528.5	1515.0	1497.4
15°	1687.6	1642.4	1607.7	1565.8	1528.7	1490.1	1455.3	1416.6	1402.1	1371.5	1353.7
17.5°	1614.2	1568.4	1525.5	1469.3	1412.0	1363.9	1327.0	1289.9	1267.7	1248.1	1239.1
20°	1565.8	1523.9	1464.2	1398.9	1335.2	1282.0	1252.1	1228.0	1203.8	1190.1	1180.4
22.5°	1520.0	1466.4	1397.1	1326.7	1262.9	1221.3	1196.1	1171.2	1151.5	1138.5	1125.6
25°	1443.3	1373.1	1299.7	1219.1	1175.6	1139.3	1111.9	1091.7	1079.6	1062.7	1056.2
27.5°	1364.4	1279.4	1198.5	1144.3	1098.9	1065.7	1041.9	1026.7	1011.4	1000.6	992.2
30°	1303.7	1217.5	1144.9	1093.3	1047.3	1020.0	1000.6	982.9	970.8	961.9	955.4
32.5°	1243.7	1157.5	1096.5	1041.1	1004.8	978.1	957.4	944.1	934.6	923.2	919.3
35°	1157.0	1080.5	1027.2	977.2	940.1	915.9	899.8	886.2	878.1	874.8	872.4
37.5°	1073.7	1010.9	953.7	912.7	879.7	860.6	841.6	834.9	829.3	823.5	826.2
40°	1020.8	961.9	911.1	867.6	840.9	820.0	808.7	800.6	795.8	795.8	795.8
42.5°	974.9	917.4	867.9	828.9	802.2	784.6	771.9	765.2	763.6	763.0	766.8
45°	903.8	850.6	800.6	768.4	745.8	728.1	720.8	715.2	715.2	718.4	719.2
47.5°	833.3	783.6	743.4	707.3	686.6	675.5	669.2	666.3	666.6	669.8	673.6
50°	790.1	740.9	701.5	669.2	649.8	639.3	633.7	632.2	633.7	633.7	639.3
52.5°	743.1	699.0	660.1	633.1	611.2	601.4	598.2	596.0	596.9	599.6	602.0
55°	674.1	634.5	597.4	571.7	555.5	549.1	541.8	542.6	541.0	542.6	542.6
57.5°	604.9	569.4	534.9	514.4	500.2	490.9	482.9	485.2	482.8	482.5	481.2
60°	560.4	521.7	494.2	475.7	459.6	451.5	444.2	445.9	443.4	441.8	438.6
62.5°	512.0	479.8	453.6	435.8	422.8	413.4	406.2	404.6	399.0	393.4	386.4
65°	441.8	415.3	391.8	375.0	362.8	355.6	349.9	345.1	333.0	320.1	313.7
67.5°	373.7	354.5	332.6	318.3	308.5	299.0	288.2	279.9	268.6	261.6	257.5
70°	329.7	311.2	292.7	278.9	268.5	259.6	247.5	241.9	233.8	230.6	226.6
72.5°	287.8	270.5	253.4	241.0	229.7	222.9	213.4	207.7	204.2	202.9	198.8
75°	224.2	210.5	197.5	186.2	177.4	172.6	168.5	164.5	162.9	155.6	151.6
77.5°	163.5	154.5	146.4	138.4	132.1	128.9	121.1	116.4	113.7	110.3	109.5
80°	127.3	121.0	112.9	108.1	99.2	95.9	92.7	91.9	91.1	90.3	89.5
82.5°	95.8	89.4	81.3	78.4	75.9	74.0	72.1	71.3	70.5	71.0	70.8
85°	48.4	45.1	45.1	44.3	43.5	42.7	41.9	41.9	41.1	41.9	41.1
87.5°	18.1	17.7	18.0	17.0	17.9	18.2	17.7	17.9	18.8	17.7	17.8
90°	9.6	11.2	12.5	13.8	15.1	16.5	17.5	18.5	19.5	20.5	21.1
92.5°	24.4	26.0	26.9	27.8	28.8	29.7	30.3	30.9	31.5	32.1	32.5
95°	51.0	52.3	53.4	54.6	55.8	57.0	57.5	58.0	58.5	59.0	59.2
97.5°	83.3	84.6	86.0	87.4	88.8	90.1	90.7	91.3	91.9	92.5	92.8
100°	107.6	108.7	110.2	111.7	113.2	114.7	115.0	115.3	115.6	116.0	116.1
102.5°	133.6	134.4	135.7	137.1	138.5	139.9	140.4	140.8	141.3	141.7	142.0
105°	175.3	175.7	176.4	177.0	177.7	178.3	178.8	179.4	179.9	180.4	180.9
107.5°	219.6	219.8	219.9	220.0	220.2	220.3	220.7	221.2	221.6	222.1	222.3
110°	250.1	250.2	250.0	249.9	249.7	249.5	249.2	248.9	248.6	248.2	248.3



TEST NUMBER: P333100-840

CATALOG NUMBER: S124RDIW-S1195D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	280.2	280.1	279.8	279.5	279.2	278.9	278.9	278.8	278.7	278.7	278.7
115°	326.8	326.6	326.3	326.0	325.6	325.3	325.1	325.0	324.8	324.6	324.5
117.5°	371.4	371.3	371.1	370.9	370.6	370.4	369.8	369.3	368.7	368.1	367.7
120°	402.9	402.9	402.5	402.0	401.5	401.0	400.1	399.3	398.5	397.7	397.4
122.5°	431.9	431.9	431.7	431.4	431.2	431.0	430.4	429.8	429.3	428.7	428.1
125°	475.9	475.8	475.6	475.5	475.3	475.1	474.8	474.5	474.2	473.8	473.5
127.5°	518.9	519.0	518.7	518.5	518.2	518.0	517.6	517.3	516.9	516.5	516.2
130°	547.6	547.9	547.9	547.9	547.9	547.9	547.5	547.2	546.8	546.5	546.0
132.5°	576.5	576.6	576.4	576.3	576.2	576.0	575.7	575.4	575.1	574.7	574.4
135°	617.8	618.3	618.3	618.3	618.3	618.3	618.0	617.6	617.3	617.0	616.6
137.5°	658.0	658.3	658.6	658.8	659.1	659.4	658.9	658.5	658.1	657.7	657.5
140°	685.6	685.8	685.8	685.8	685.8	685.8	685.6	685.5	685.3	685.1	685.0
142.5°	711.4	711.6	711.3	711.2	711.1	710.9	710.9	710.9	710.8	710.8	710.8
145°	748.4	748.8	749.0	749.2	749.3	749.5	749.3	749.2	749.0	748.8	748.5
147.5°	784.4	784.7	784.6	784.4	784.3	784.2	784.0	783.9	783.8	783.6	783.5
150°	805.4	805.8	805.8	805.8	805.8	805.8	805.8	805.8	805.8	805.8	805.7
152.5°	824.8	825.0	825.1	825.3	825.4	825.5	825.9	826.3	826.7	827.1	827.1
155°	854.4	854.3	854.1	854.0	853.8	853.7	854.3	855.1	855.7	856.4	856.4
157.5°	879.6	879.5	879.4	879.4	879.4	879.3	879.8	880.3	880.8	881.3	881.3
160°	895.8	895.5	895.4	895.2	895.0	894.9	895.4	896.0	896.5	897.0	896.8
162.5°	909.1	908.8	908.6	908.5	908.3	908.1	909.0	909.9	910.8	911.7	911.7
165°	928.2	927.8	927.4	927.1	926.8	926.3	927.4	928.4	929.4	930.4	930.6
167.5°	942.2	941.8	941.9	941.9	941.9	942.0	943.0	944.0	944.9	945.9	945.9
170°	950.1	949.7	949.9	950.1	950.2	950.4	951.4	952.4	953.4	954.4	954.3
172.5°	956.5	956.2	956.2	956.3	956.3	956.3	957.6	958.7	959.8	960.9	960.9
175°	964.3	963.8	963.6	963.4	963.3	963.1	964.3	965.4	966.6	967.8	967.8
177.5°	967.7	967.3	967.3	967.3	967.3	967.3	968.3	969.2	970.1	971.1	971.0
180°	969.1	969.1	969.1	969.1	969.1	969.1	969.1	969.1	969.1	969.1	969.1



TEST NUMBER: P333100-840

CATALOG NUMBER: S124RDIW-S1195D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2
2.5°	1910.3	1911.6	1907.0	1905.7	1907.0	1911.6	1910.3	1914.1	1914.8	1920.0	1918.0
5°	1772.2	1770.6	1766.6	1767.4	1766.6	1770.6	1772.2	1778.7	1781.9	1794.8	1793.2
7.5°	1654.2	1647.9	1649.6	1643.3	1649.6	1647.9	1654.2	1660.0	1669.8	1675.7	1689.3
10°	1582.0	1573.1	1565.8	1559.3	1565.8	1573.1	1582.0	1585.2	1598.8	1605.3	1619.0
12.5°	1483.3	1475.6	1465.8	1467.7	1465.8	1475.6	1483.3	1497.4	1515.0	1528.5	1550.0
15°	1343.2	1331.2	1311.8	1314.2	1311.8	1331.2	1343.2	1353.7	1371.5	1402.1	1416.6
17.5°	1224.8	1224.9	1216.1	1218.1	1216.1	1224.9	1224.8	1239.1	1248.1	1267.7	1289.9
20°	1163.5	1157.8	1158.6	1156.2	1158.6	1157.8	1163.5	1180.4	1190.1	1203.8	1228.0
22.5°	1120.8	1114.0	1108.3	1103.3	1108.3	1114.0	1120.8	1125.6	1138.5	1151.5	1171.2
25°	1048.9	1044.1	1036.9	1035.3	1036.9	1044.1	1048.9	1056.2	1062.7	1079.6	1091.7
27.5°	985.7	984.8	981.9	978.2	981.9	984.8	985.7	992.2	1000.6	1011.4	1026.7
30°	949.0	947.4	945.7	943.3	945.7	947.4	949.0	955.4	961.9	970.8	982.9
32.5°	916.1	915.1	913.5	913.7	913.5	915.1	916.1	919.3	923.2	934.6	944.1
35°	869.2	868.4	866.8	866.0	866.8	868.4	869.2	872.4	874.8	878.1	886.2
37.5°	825.4	827.4	826.5	826.3	826.5	827.4	825.4	826.2	823.5	829.3	834.9
40°	795.0	795.8	797.4	796.6	797.4	795.8	795.0	795.8	795.8	795.8	800.6
42.5°	769.8	770.0	772.2	769.5	772.2	770.0	769.8	766.8	763.0	763.6	765.2
45°	724.9	729.7	728.9	728.9	728.9	729.7	724.9	719.2	718.4	715.2	715.2
47.5°	675.7	679.8	681.0	680.9	681.0	679.8	675.7	673.6	669.8	666.6	666.3
50°	643.4	641.8	644.2	643.4	644.2	641.8	643.4	639.3	633.7	633.7	632.2
52.5°	604.1	604.4	604.2	603.4	604.2	604.4	604.1	602.0	599.6	596.9	596.0
55°	543.4	544.2	542.6	543.4	542.6	544.2	543.4	542.6	542.6	541.0	542.6
57.5°	477.7	473.7	475.3	473.4	475.3	473.7	477.7	481.2	482.5	482.8	485.2
60°	430.6	424.1	422.5	419.3	422.5	424.1	430.6	438.6	441.8	443.4	445.9
62.5°	377.7	373.1	367.7	370.2	367.7	373.1	377.7	386.4	393.4	399.0	404.6
65°	307.2	304.0	301.5	304.8	301.5	304.0	307.2	313.7	320.1	333.0	345.1
67.5°	254.3	252.6	252.6	251.0	252.6	252.6	254.3	257.5	261.6	268.6	279.9
70°	226.6	224.2	224.2	222.6	224.2	224.2	226.6	226.6	230.6	233.8	241.9
72.5°	198.1	195.8	196.4	195.4	196.4	195.8	198.1	198.8	202.9	204.2	207.7
75°	146.7	142.7	142.7	143.5	142.7	142.7	146.7	151.6	155.6	162.9	164.5
77.5°	109.5	108.7	109.8	108.4	109.8	108.7	109.5	109.5	110.3	113.7	116.4
80°	89.5	88.7	87.9	90.3	87.9	88.7	89.5	89.5	90.3	91.1	91.9
82.5°	69.5	69.4	69.2	72.2	69.2	69.4	69.5	70.8	71.0	70.5	71.3
85°	41.9	40.3	41.9	40.3	41.9	40.3	41.9	41.1	41.9	41.1	41.9
87.5°	19.1	18.6	18.0	18.7	18.0	18.6	19.1	17.8	17.7	18.8	17.9
90°	21.5	21.8	22.1	22.5	22.1	21.8	21.5	21.1	20.5	19.5	18.5
92.5°	32.7	32.9	33.1	33.3	33.1	32.9	32.7	32.5	32.1	31.5	30.9
95°	59.2	59.2	59.2	59.2	59.2	59.2	59.2	59.2	59.0	58.5	58.0
97.5°	92.8	92.8	92.8	92.8	92.8	92.8	92.8	92.8	92.5	91.9	91.3
100°	116.1	116.1	116.1	116.1	116.1	116.1	116.1	116.1	116.0	115.6	115.3
102.5°	142.2	142.3	142.4	142.6	142.4	142.3	142.2	142.0	141.7	141.3	140.8
105°	181.4	181.9	182.4	182.9	182.4	181.9	181.4	180.9	180.4	179.9	179.4
107.5°	222.3	222.3	222.2	222.2	222.2	222.3	222.3	222.3	222.1	221.6	221.2
110°	248.8	249.3	249.8	250.3	249.8	249.3	248.8	248.3	248.2	248.6	248.9



TEST NUMBER: P333100-840

CATALOG NUMBER: S124RDIW-S1195D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	278.8	278.9	279.0	279.1	279.0	278.9	278.8	278.7	278.7	278.7	278.8
115°	324.3	324.2	324.0	323.8	324.0	324.2	324.3	324.5	324.6	324.8	325.0
117.5°	367.4	367.0	366.7	366.4	366.7	367.0	367.4	367.7	368.1	368.7	369.3
120°	397.8	398.1	398.4	398.7	398.4	398.1	397.8	397.4	397.7	398.5	399.3
122.5°	427.5	426.9	426.4	425.8	426.4	426.9	427.5	428.1	428.7	429.3	429.8
125°	473.2	472.8	472.5	472.2	472.5	472.8	473.2	473.5	473.8	474.2	474.5
127.5°	516.0	515.7	515.4	515.2	515.4	515.7	516.0	516.2	516.5	516.9	517.3
130°	545.4	544.7	544.0	543.4	544.0	544.7	545.4	546.0	546.5	546.8	547.2
132.5°	574.2	573.9	573.6	573.4	573.6	573.9	574.2	574.4	574.7	575.1	575.4
135°	616.1	615.6	615.1	614.6	615.1	615.6	616.1	616.6	617.0	617.3	617.6
137.5°	657.6	657.7	657.8	657.9	657.8	657.7	657.6	657.5	657.7	658.1	658.5
140°	684.8	684.6	684.5	684.3	684.5	684.6	684.8	685.0	685.1	685.3	685.5
142.5°	710.7	710.7	710.7	710.6	710.7	710.7	710.7	710.8	710.8	710.8	710.9
145°	748.0	747.5	747.0	746.5	747.0	747.5	748.0	748.5	748.8	749.0	749.2
147.5°	783.3	783.2	782.9	782.7	782.9	783.2	783.3	783.5	783.6	783.8	783.9
150°	805.5	805.3	805.2	805.0	805.2	805.3	805.5	805.7	805.8	805.8	805.8
152.5°	826.7	826.3	825.8	825.4	825.8	826.3	826.7	827.1	827.1	826.7	826.3
155°	855.7	855.1	854.3	853.7	854.3	855.1	855.7	856.4	856.4	855.7	855.1
157.5°	880.7	880.2	879.6	879.0	879.6	880.2	880.7	881.3	881.3	880.8	880.3
160°	896.0	895.0	894.2	893.4	894.2	895.0	896.0	896.8	897.0	896.5	896.0
162.5°	910.9	910.1	909.3	908.4	909.3	910.1	910.9	911.7	911.7	910.8	909.9
165°	929.9	929.2	928.6	927.9	928.6	929.2	929.9	930.6	930.4	929.4	928.4
167.5°	944.9	943.9	942.9	941.8	942.9	943.9	944.9	945.9	945.9	944.9	944.0
170°	953.1	952.0	950.8	949.7	950.8	952.0	953.1	954.3	954.4	953.4	952.4
172.5°	959.7	958.6	957.4	956.2	957.4	958.6	959.7	960.9	960.9	959.8	958.7
175°	966.6	965.4	964.3	963.1	964.3	965.4	966.6	967.8	967.8	966.6	965.4
177.5°	969.9	968.9	967.8	966.7	967.8	968.9	969.9	971.0	971.1	970.1	969.2
180°	969.1	969.1	969.1	969.1	969.1	969.1	969.1	969.1	969.1	969.1	969.1



TEST NUMBER: P333100-840

CATALOG NUMBER: S124RDIW-S1195D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2
2.5°	1914.1	1918.6	1928.9	1940.6	1950.3	1958.6	1965.1	1974.1	1982.5	1994.1	2005.1
5°	1798.1	1809.3	1825.4	1844.8	1869.0	1885.1	1905.2	1923.0	1948.8	1974.6	1999.6
7.5°	1696.1	1708.5	1732.2	1759.0	1787.7	1814.1	1838.1	1869.3	1903.5	1941.1	1983.0
10°	1630.3	1644.1	1672.2	1702.8	1736.8	1762.5	1794.8	1831.9	1870.6	1916.5	1968.1
12.5°	1570.9	1584.1	1618.0	1649.3	1684.5	1712.8	1750.3	1788.1	1839.7	1889.5	1948.1
15°	1455.3	1490.1	1528.7	1565.8	1607.7	1642.4	1687.6	1726.3	1775.4	1845.6	1912.5
17.5°	1327.0	1363.9	1412.0	1469.3	1525.5	1568.4	1614.2	1662.2	1720.8	1792.4	1869.7
20°	1252.1	1282.0	1335.2	1398.9	1464.2	1523.9	1565.8	1619.0	1679.5	1756.9	1836.7
22.5°	1196.1	1221.3	1262.9	1326.7	1397.1	1466.4	1520.0	1572.6	1639.5	1716.9	1803.8
25°	1111.9	1139.3	1175.6	1219.1	1299.7	1373.1	1443.3	1503.7	1574.7	1652.0	1748.8
27.5°	1041.9	1065.7	1098.9	1144.3	1198.5	1279.4	1364.4	1433.4	1506.1	1589.2	1686.1
30°	1000.6	1020.0	1047.3	1093.3	1144.9	1217.5	1303.7	1384.4	1457.7	1544.1	1644.9
32.5°	957.4	978.1	1004.8	1041.1	1096.5	1157.5	1243.7	1332.1	1410.1	1498.2	1597.1
35°	899.8	915.9	940.1	977.2	1027.2	1080.5	1157.0	1248.1	1330.4	1424.7	1519.0
37.5°	841.6	860.6	879.7	912.7	953.7	1010.9	1073.7	1166.7	1257.8	1343.9	1436.0
40°	808.7	820.0	840.9	867.6	911.1	961.9	1020.8	1111.9	1203.0	1288.5	1381.2
42.5°	771.9	784.6	802.2	828.9	867.9	917.4	974.9	1053.8	1148.8	1231.7	1316.1
45°	720.8	728.1	745.8	768.4	800.6	850.6	903.8	974.0	1063.5	1142.5	1216.7
47.5°	669.2	675.5	686.6	707.3	743.4	783.6	833.3	896.3	974.8	1053.8	1116.5
50°	633.7	639.3	649.8	669.2	701.5	740.9	790.1	846.6	916.8	992.5	1044.9
52.5°	598.2	601.4	611.2	633.1	660.1	699.0	743.1	795.0	860.6	923.5	976.5
55°	541.8	549.1	555.5	571.7	597.4	634.5	674.1	723.3	774.1	827.3	872.4
57.5°	482.9	490.9	500.2	514.4	534.9	569.4	604.9	644.7	688.1	732.3	770.1
60°	444.2	451.5	459.6	475.7	494.2	521.7	560.4	595.0	628.1	668.4	706.3
62.5°	406.2	413.4	422.8	435.8	453.6	479.8	512.0	542.2	576.5	611.7	639.9
65°	349.9	355.6	362.8	375.0	391.8	415.3	441.8	465.2	495.8	521.7	547.4
67.5°	288.2	299.0	308.5	318.3	332.6	354.5	373.7	396.1	416.9	436.1	459.6
70°	247.5	259.6	268.5	278.9	292.7	311.2	329.7	345.1	362.0	380.5	401.5
72.5°	213.4	222.9	229.7	241.0	253.4	270.5	287.8	300.5	314.3	327.0	347.4
75°	168.5	172.6	177.4	186.2	197.5	210.5	224.2	235.4	243.5	254.8	269.3
77.5°	121.1	128.9	132.1	138.4	146.4	154.5	163.5	173.0	180.8	184.8	195.9
80°	92.7	95.9	99.2	108.1	112.9	121.0	127.3	136.2	139.5	143.5	154.0
82.5°	72.1	74.0	75.9	78.4	81.3	89.4	95.8	101.4	104.6	106.1	114.0
85°	41.9	42.7	43.5	44.3	45.1	45.1	48.4	52.4	58.1	58.1	60.5
87.5°	17.7	18.2	17.9	17.0	18.0	17.7	18.1	17.7	19.3	20.8	22.4
90°	17.5	16.5	15.1	13.8	12.5	11.2	9.6	7.8	6.0	4.0	2.2
92.5°	30.3	29.7	28.8	27.8	26.9	26.0	24.4	22.3	20.2	18.2	16.1
95°	57.5	57.0	55.8	54.6	53.4	52.3	51.0	49.5	48.0	46.5	44.9
97.5°	90.7	90.1	88.8	87.4	86.0	84.6	83.3	82.1	81.0	79.8	78.6
100°	115.0	114.7	113.2	111.7	110.2	108.7	107.6	106.9	106.2	105.6	104.9
102.5°	140.4	139.9	138.5	137.1	135.7	134.4	133.6	133.3	133.0	132.8	132.5
105°	178.8	178.3	177.7	177.0	176.4	175.7	175.3	175.1	175.0	174.8	174.6
107.5°	220.7	220.3	220.2	220.0	219.9	219.8	219.6	219.4	219.2	219.0	218.8
110°	249.2	249.5	249.7	249.9	250.0	250.2	250.1	249.8	249.5	249.1	248.8



TEST NUMBER: P333100-840

CATALOG NUMBER: S124RDIW-S1195D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	278.9	278.9	279.2	279.5	279.8	280.1	280.2	280.2	280.1	280.0	280.0
115°	325.1	325.3	325.6	326.0	326.3	326.6	326.8	326.8	326.8	326.8	326.8
117.5°	369.8	370.4	370.6	370.9	371.1	371.3	371.4	371.2	371.1	371.0	370.8
120°	400.1	401.0	401.5	402.0	402.5	402.9	402.9	402.2	401.5	400.9	400.2
122.5°	430.4	431.0	431.2	431.4	431.7	431.9	431.9	431.6	431.3	431.1	430.8
125°	474.8	475.1	475.3	475.5	475.6	475.8	475.9	475.9	475.9	475.9	475.9
127.5°	517.6	518.0	518.2	518.5	518.7	519.0	518.9	518.4	517.9	517.4	516.8
130°	547.5	547.9	547.9	547.9	547.9	547.9	547.6	547.1	546.6	546.1	545.6
132.5°	575.7	576.0	576.2	576.3	576.4	576.6	576.5	576.1	575.7	575.4	575.0
135°	618.0	618.3	618.3	618.3	618.3	618.3	617.8	616.8	615.8	614.8	613.9
137.5°	658.9	659.4	659.1	658.8	658.6	658.3	658.0	657.5	657.0	656.6	656.1
140°	685.6	685.8	685.8	685.8	685.8	685.8	685.6	685.3	685.0	684.6	684.3
142.5°	710.9	710.9	711.1	711.2	711.3	711.6	711.4	711.0	710.7	710.4	710.0
145°	749.3	749.5	749.3	749.2	749.0	748.8	748.4	747.8	747.1	746.4	745.8
147.5°	784.0	784.2	784.3	784.4	784.6	784.7	784.4	783.6	782.7	781.9	781.1
150°	805.8	805.8	805.8	805.8	805.8	805.8	805.4	804.8	804.1	803.3	802.7
152.5°	825.9	825.5	825.4	825.3	825.1	825.0	824.8	824.4	823.9	823.5	823.1
155°	854.3	853.7	853.8	854.0	854.1	854.3	854.4	854.4	854.4	854.4	854.4
157.5°	879.8	879.3	879.4	879.4	879.4	879.5	879.6	879.9	880.2	880.5	880.8
160°	895.4	894.9	895.0	895.2	895.4	895.5	895.8	896.0	896.1	896.3	896.5
162.5°	909.0	908.1	908.3	908.5	908.6	908.8	909.1	909.5	909.9	910.4	910.8
165°	927.4	926.3	926.8	927.1	927.4	927.8	928.2	928.7	929.2	929.7	930.2
167.5°	943.0	942.0	941.9	941.9	941.9	941.8	942.2	942.9	943.6	944.3	944.9
170°	951.4	950.4	950.2	950.1	949.9	949.7	950.1	950.9	951.7	952.5	953.4
172.5°	957.6	956.3	956.3	956.3	956.2	956.2	956.5	957.3	958.0	958.7	959.4
175°	964.3	963.1	963.3	963.4	963.6	963.8	964.3	965.1	965.9	966.7	967.7
177.5°	968.3	967.3	967.3	967.3	967.3	967.3	967.7	968.4	969.0	969.7	970.3
180°	969.1	969.1	969.1	969.1	969.1	969.1	969.1	969.1	969.1	969.1	969.1



TEST NUMBER: P333100-840

CATALOG NUMBER: S124RDIW-S1195D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2
2.5°	2013.5	2019.2	2025.7	2038.0	2048.3	2052.9	2061.8	2068.3	2066.4	2075.4	2090.8
5°	2021.3	2043.2	2068.1	2094.0	2122.9	2147.2	2166.5	2185.9	2201.2	2219.7	2247.2
7.5°	2020.0	2058.8	2100.8	2147.2	2194.7	2235.8	2273.9	2312.6	2346.9	2384.5	2433.7
10°	2014.9	2066.5	2118.9	2179.4	2239.9	2297.1	2348.7	2397.1	2443.1	2492.2	2554.4
12.5°	2009.1	2068.4	2131.8	2204.5	2279.9	2348.7	2409.3	2479.0	2536.6	2600.0	2671.7
15°	1983.5	2063.3	2149.6	2243.9	2334.2	2426.9	2509.9	2595.5	2675.2	2751.1	2841.4
17.5°	1954.1	2046.2	2148.0	2259.4	2367.9	2480.6	2579.2	2686.8	2768.4	2870.2	2954.1
20°	1930.3	2029.4	2138.3	2263.2	2386.6	2511.5	2620.4	2730.1	2822.0	2924.4	3030.8
22.5°	1901.2	2010.0	2128.0	2257.5	2386.6	2523.1	2643.6	2752.7	2866.5	2981.8	3091.5
25°	1854.4	1967.3	2092.3	2234.2	2382.6	2522.0	2651.1	2786.5	2909.1	3034.0	3132.4
27.5°	1797.1	1915.6	2047.3	2193.7	2346.0	2488.8	2640.8	2785.1	2908.4	3028.7	3114.5
30°	1751.2	1876.2	2002.8	2151.2	2309.2	2462.4	2625.2	2769.6	2899.4	3007.5	3055.9
32.5°	1704.1	1822.7	1953.2	2103.4	2265.3	2430.1	2591.7	2739.3	2859.4	2924.3	2925.5
35°	1622.2	1733.5	1869.0	2016.5	2182.6	2361.6	2525.3	2670.4	2743.8	2749.5	2670.4
37.5°	1532.9	1635.0	1762.8	1910.6	2092.4	2270.5	2437.7	2534.5	2559.0	2476.9	2330.8
40°	1469.1	1563.4	1686.8	1838.4	2018.9	2202.8	2355.2	2426.1	2400.3	2267.2	2104.4
42.5°	1402.0	1489.9	1608.7	1758.4	1939.6	2125.4	2255.2	2293.2	2224.8	2071.2	1880.6
45°	1292.5	1373.1	1490.9	1641.6	1815.7	1989.9	2088.3	2068.9	1955.2	1773.0	1559.3
47.5°	1178.5	1256.4	1362.3	1501.8	1680.1	1830.4	1897.0	1838.7	1676.9	1476.4	1302.6
50°	1103.0	1182.9	1280.4	1413.4	1576.3	1721.4	1764.1	1675.5	1495.6	1302.9	1143.3
52.5°	1028.9	1097.0	1192.7	1321.2	1476.9	1599.5	1622.2	1520.0	1334.4	1161.6	1020.1
55°	915.9	978.1	1058.6	1179.6	1314.2	1418.3	1406.1	1274.8	1106.2	958.7	847.4
57.5°	806.8	853.5	928.1	1041.4	1159.6	1229.4	1185.3	1073.2	916.1	795.4	701.5
60°	734.6	778.1	847.4	946.5	1050.6	1090.0	1053.0	931.3	807.1	696.6	617.6
62.5°	666.1	704.6	764.2	856.3	940.3	963.7	924.0	817.7	705.8	611.5	546.0
65°	566.8	602.3	653.1	718.4	776.5	787.7	761.9	653.1	568.5	489.4	444.2
67.5°	476.7	499.9	539.6	596.0	626.8	633.4	583.6	515.2	440.6	392.0	358.0
70°	416.1	432.1	469.3	499.9	524.9	525.7	479.8	425.0	367.7	328.2	303.2
72.5°	357.4	372.8	400.9	421.8	441.0	434.7	392.6	349.4	303.2	273.4	254.8
75°	275.8	289.4	304.0	313.7	313.7	305.6	275.0	242.7	216.1	198.3	192.7
77.5°	200.5	211.8	216.6	215.1	212.2	199.7	180.3	159.2	149.7	141.3	137.0
80°	157.2	162.1	163.7	159.7	154.8	140.3	127.3	118.6	109.7	106.4	104.8
82.5°	116.5	120.8	116.5	117.8	107.0	95.1	88.1	85.0	81.3	80.0	78.4
85°	62.1	61.3	59.7	55.6	48.4	46.8	45.9	45.1	43.5	44.3	42.7
87.5°	22.1	20.5	18.3	18.1	18.4	17.4	18.3	18.5	18.8	18.4	19.8
90°	4.0	6.0	7.8	9.6	11.2	12.5	13.8	15.1	16.5	17.5	18.5
92.5°	18.2	20.2	22.3	24.4	26.0	26.9	27.8	28.8	29.7	30.3	30.9
95°	46.5	48.0	49.5	51.0	52.3	53.4	54.6	55.8	57.0	57.5	58.0
97.5°	79.8	81.0	82.1	83.3	84.6	86.0	87.4	88.8	90.1	90.7	91.3
100°	105.6	106.2	106.9	107.6	108.7	110.2	111.7	113.2	114.7	115.0	115.3
102.5°	132.8	133.0	133.3	133.6	134.4	135.7	137.1	138.5	139.9	140.4	140.8
105°	174.8	175.0	175.1	175.3	175.7	176.4	177.0	177.7	178.3	178.8	179.4
107.5°	219.0	219.2	219.4	219.6	219.8	219.9	220.0	220.2	220.3	220.7	221.2
110°	249.1	249.5	249.8	250.1	250.2	250.0	249.9	249.7	249.5	249.2	248.9





TEST NUMBER: P333100-840

CATALOG NUMBER: S124RDIW-S1195D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	280.0	280.1	280.2	280.2	280.1	279.8	279.5	279.2	278.9	278.9	278.8
115°	326.8	326.8	326.8	326.8	326.6	326.3	326.0	325.6	325.3	325.1	325.0
117.5°	371.0	371.1	371.2	371.4	371.3	371.1	370.9	370.6	370.4	369.8	369.3
120°	400.9	401.5	402.2	402.9	402.9	402.5	402.0	401.5	401.0	400.1	399.3
122.5°	431.1	431.3	431.6	431.9	431.9	431.7	431.4	431.2	431.0	430.4	429.8
125°	475.9	475.9	475.9	475.9	475.8	475.6	475.5	475.3	475.1	474.8	474.5
127.5°	517.4	517.9	518.4	518.9	519.0	518.7	518.5	518.2	518.0	517.6	517.3
130°	546.1	546.6	547.1	547.6	547.9	547.9	547.9	547.9	547.9	547.5	547.2
132.5°	575.4	575.7	576.1	576.5	576.6	576.4	576.3	576.2	576.0	575.7	575.4
135°	614.8	615.8	616.8	617.8	618.3	618.3	618.3	618.3	618.3	618.0	617.6
137.5°	656.6	657.0	657.5	658.0	658.3	658.6	658.8	659.1	659.4	658.9	658.5
140°	684.6	685.0	685.3	685.6	685.8	685.8	685.8	685.8	685.8	685.6	685.5
142.5°	710.4	710.7	711.0	711.4	711.6	711.3	711.2	711.1	710.9	710.9	710.9
145°	746.4	747.1	747.8	748.4	748.8	749.0	749.2	749.3	749.5	749.3	749.2
147.5°	781.9	782.7	783.6	784.4	784.7	784.6	784.4	784.3	784.2	784.0	783.9
150°	803.3	804.1	804.8	805.4	805.8	805.8	805.8	805.8	805.8	805.8	805.8
152.5°	823.5	823.9	824.4	824.8	825.0	825.1	825.3	825.4	825.5	825.9	826.3
155°	854.4	854.4	854.4	854.4	854.3	854.1	854.0	853.8	853.7	854.3	855.1
157.5°	880.5	880.2	879.9	879.6	879.5	879.4	879.4	879.4	879.3	879.8	880.3
160°	896.3	896.1	896.0	895.8	895.5	895.4	895.2	895.0	894.9	895.4	896.0
162.5°	910.4	909.9	909.5	909.1	908.8	908.6	908.5	908.3	908.1	909.0	909.9
165°	929.7	929.2	928.7	928.2	927.8	927.4	927.1	926.8	926.3	927.4	928.4
167.5°	944.3	943.6	942.9	942.2	941.8	941.9	941.9	941.9	942.0	943.0	944.0
170°	952.5	951.7	950.9	950.1	949.7	949.9	950.1	950.2	950.4	951.4	952.4
172.5°	958.7	958.0	957.3	956.5	956.2	956.2	956.3	956.3	956.3	957.6	958.7
175°	966.7	965.9	965.1	964.3	963.8	963.6	963.4	963.3	963.1	964.3	965.4
177.5°	969.7	969.0	968.4	967.7	967.3	967.3	967.3	967.3	967.3	968.3	969.2
180°	969.1	969.1	969.1	969.1	969.1	969.1	969.1	969.1	969.1	969.1	969.1



TEST NUMBER: P333100-840

CATALOG NUMBER: S124RDIW-S1195D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2
2.5°	2099.2	2101.8	2103.8	2110.2	2110.8	2116.7	2110.8
5°	2272.9	2284.2	2302.0	2319.7	2321.3	2332.6	2312.4
7.5°	2467.7	2493.9	2510.1	2538.8	2550.1	2557.2	2545.6
10°	2601.9	2626.1	2668.8	2689.8	2710.8	2713.9	2704.3
12.5°	2731.6	2770.0	2803.6	2843.3	2842.4	2870.7	2860.3
15°	2904.3	2943.8	2990.5	3034.8	3051.0	3051.0	3063.9
17.5°	3027.5	3099.9	3148.3	3183.1	3221.1	3227.7	3223.2
20°	3110.7	3188.9	3240.5	3285.6	3311.4	3318.7	3318.7
22.5°	3172.6	3239.1	3289.5	3330.1	3351.4	3359.9	3357.4
25°	3215.5	3272.7	3303.4	3315.5	3321.0	3319.5	3304.2
27.5°	3156.7	3154.2	3134.8	3097.8	3069.9	3052.9	3033.5
30°	3044.5	3002.6	2954.3	2901.0	2832.5	2780.1	2763.9
32.5°	2877.5	2783.3	2701.4	2612.7	2539.0	2486.6	2464.7
35°	2554.4	2405.2	2283.4	2177.0	2099.6	2051.2	2035.1
37.5°	2170.8	2026.5	1875.7	1772.5	1708.4	1659.5	1641.2
40°	1927.0	1769.8	1638.4	1541.7	1475.5	1427.9	1427.1
42.5°	1704.5	1554.4	1430.7	1361.0	1289.7	1258.3	1258.1
45°	1395.6	1275.6	1170.7	1115.9	1073.2	1047.3	1040.1
47.5°	1155.6	1056.2	986.4	942.7	907.9	891.4	880.8
50°	1020.8	933.7	878.1	840.1	820.8	799.8	798.2
52.5°	908.5	838.2	794.9	764.1	739.5	726.9	727.3
55°	763.6	707.9	677.3	653.9	634.5	624.9	620.9
57.5°	643.3	601.5	579.3	557.7	549.6	542.0	539.9
60°	568.5	540.2	519.3	502.3	490.2	487.8	487.0
62.5°	506.5	477.0	462.5	449.4	440.6	436.9	435.4
65°	417.7	395.9	382.9	372.5	369.3	363.7	362.8
67.5°	336.7	323.7	315.1	307.8	303.5	303.2	303.2
70°	287.0	279.7	272.6	268.5	266.1	264.5	264.5
72.5°	244.5	239.1	233.2	231.1	230.6	228.9	228.3
75°	186.2	180.6	181.4	177.4	174.2	170.2	167.7
77.5°	132.1	128.1	127.2	126.7	124.0	123.5	124.8
80°	102.4	98.4	97.6	98.4	97.6	95.1	95.1
82.5°	77.9	74.5	73.7	73.2	72.4	73.2	71.9
85°	41.9	40.3	40.3	40.3	41.9	41.1	40.3
87.5°	18.8	18.3	19.1	18.5	18.6	18.0	18.7
90°	19.5	20.5	21.1	21.5	21.8	22.1	22.5
92.5°	31.5	32.1	32.5	32.7	32.9	33.1	33.3
95°	58.5	59.0	59.2	59.2	59.2	59.2	59.2
97.5°	91.9	92.5	92.8	92.8	92.8	92.8	92.8
100°	115.6	116.0	116.1	116.1	116.1	116.1	116.1
102.5°	141.3	141.7	142.0	142.2	142.3	142.4	142.6
105°	179.9	180.4	180.9	181.4	181.9	182.4	182.9
107.5°	221.6	222.1	222.3	222.3	222.3	222.2	222.2
110°	248.6	248.2	248.3	248.8	249.3	249.8	250.3



TEST NUMBER: P333100-840

CATALOG NUMBER: S124RDIW-S1195D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	278.7	278.7	278.7	278.8	278.9	279.0	279.1
115°	324.8	324.6	324.5	324.3	324.2	324.0	323.8
117.5°	368.7	368.1	367.7	367.4	367.0	366.7	366.4
120°	398.5	397.7	397.4	397.8	398.1	398.4	398.7
122.5°	429.3	428.7	428.1	427.5	426.9	426.4	425.8
125°	474.2	473.8	473.5	473.2	472.8	472.5	472.2
127.5°	516.9	516.5	516.2	516.0	515.7	515.4	515.2
130°	546.8	546.5	546.0	545.4	544.7	544.0	543.4
132.5°	575.1	574.7	574.4	574.2	573.9	573.6	573.4
135°	617.3	617.0	616.6	616.1	615.6	615.1	614.6
137.5°	658.1	657.7	657.5	657.6	657.7	657.8	657.9
140°	685.3	685.1	685.0	684.8	684.6	684.5	684.3
142.5°	710.8	710.8	710.8	710.7	710.7	710.7	710.6
145°	749.0	748.8	748.5	748.0	747.5	747.0	746.5
147.5°	783.8	783.6	783.5	783.3	783.2	782.9	782.7
150°	805.8	805.8	805.7	805.5	805.3	805.2	805.0
152.5°	826.7	827.1	827.1	826.7	826.3	825.8	825.4
155°	855.7	856.4	856.4	855.7	855.1	854.3	853.7
157.5°	880.8	881.3	881.3	880.7	880.2	879.6	879.0
160°	896.5	897.0	896.8	896.0	895.0	894.2	893.4
162.5°	910.8	911.7	911.7	910.9	910.1	909.3	908.4
165°	929.4	930.4	930.6	929.9	929.2	928.6	927.9
167.5°	944.9	945.9	945.9	944.9	943.9	942.9	941.8
170°	953.4	954.4	954.3	953.1	952.0	950.8	949.7
172.5°	959.8	960.9	960.9	959.7	958.6	957.4	956.2
175°	966.6	967.8	967.8	966.6	965.4	964.3	963.1
177.5°	970.1	971.1	971.0	969.9	968.9	967.8	966.7
180°	969.1	969.1	969.1	969.1	969.1	969.1	969.1

(END OF REPORT)