

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333728-927

Luminaire Tested: **S125RDIW-S1270D1050U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333728-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S1270D1050U927-4F0-1E-UDD-A  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1050 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7218.5 lumens  
Efficiency: N/A  
Efficacy: 107.1 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 67.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333728-927

CATALOG NUMBER: S125RDIW-S1270D1050U927-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333728-927

CATALOG NUMBER: S125RDIW-S1270D1050U927-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	51	46
2	91	83	78	72	84	78	73	68	67	63	60	57	54	52	48	46	44	40
3	83	74	67	61	77	69	62	57	59	55	51	51	47	44	43	40	38	34
4	76	65	58	52	70	61	54	49	53	48	43	45	41	38	38	35	33	29
5	70	58	50	45	65	55	48	42	48	42	38	41	37	33	35	31	29	26
6	64	53	45	39	60	49	42	37	43	37	33	37	33	29	31	28	26	23
7	60	48	40	34	55	45	38	32	39	33	29	34	29	26	29	25	23	20
8	55	43	36	30	51	41	34	29	36	30	26	31	26	23	26	23	20	18
9	52	39	32	27	48	37	30	26	33	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	28	23	30	25	21	26	22	19	23	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9715	9715	9715	9715
5°	11177	9728	8591	9728
10°	12821	9678	7581	9678
15°	13848	9579	6738	9579
20°	15270	9465	6222	9465
25°	17672	9311	5773	9311
30°	19231	9150	5480	9150
35°	16222	8964	5210	8964
40°	11328	8627	4977	8627
45°	8404	8173	4748	8173
50°	6701	7700	4554	7700
55°	5687	7113	4380	7113
60°	4914	6589	4100	6589
65°	4378	6021	3529	6021
70°	3846	5516	3218	5516
75°	3329	4776	3019	4776
80°	2525	4020	2525	4020
85°	2104	3157	2379	3157



TEST NUMBER: P333728-927

CATALOG NUMBER: S125RDIW-S1270D1050U927-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	144.3	2.0
10°-20°	422.7	5.9
20°-30°	670.3	9.3
30°-40°	808.3	11.2
40°-50°	721.8	10.0
50°-60°	553.6	7.7
60°-70°	359.7	5.0
70°-80°	174.9	2.4
80°-90°	44.0	0.6
90°-100°	39.3	0.5
100°-110°	242.1	3.4
110°-120°	439.0	6.1
120°-130°	563.4	7.8
130°-140°	606.0	8.4
140°-150°	568.8	7.9
150°-160°	460.1	6.4
160°-170°	297.6	4.1
170°-180°	102.6	1.4
0°-30°	1237.3	17.1
0°-40°	2045.6	28.3
0°-60°	3320.9	46.0
0°-90°	3899.6	54.0
90°-120°	720.3	10.0
90°-150°	2458.6	34.1
90°-180°	3319.0	46.0
0°-180°	7218.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1504	1504	1504	1504	1504	
5°	1724	1501	1325	1501	1724	172
15°	2071	1433	1008	1433	2071	593
25°	2480	1307	810	1307	2480	1139
35°	2058	1137	661	1137	2058	1243
45°	920	895	520	895	920	734
55°	505	632	389	632	505	458
65°	286	394	231	394	286	285
75°	133	191	121	191	133	142
85°	28	43	32	43	28	33
90°	19	1	19	1	19	10
95°	17	46	17	46	17	14
105°	238	236	238	236	238	215
115°	439	442	439	442	439	436
125°	629	629	629	629	629	559
135°	781	784	781	784	781	603
145°	907	909	907	909	907	567
155°	994	1002	994	1002	994	458
165°	1051	1057	1051	1057	1051	297
175°	1076	1081	1076	1081	1076	102
180°	1081	1081	1081	1081	1081	



TEST NUMBER: P333728-927

CATALOG NUMBER: S125RDIW-S1270D1050U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3
2.5°	1582.3	1581.4	1583.3	1577.9	1578.3	1569.9	1569.9	1563.5	1555.1	1548.7	1545.8
5°	1724.1	1725.4	1722.8	1713.6	1707.5	1698.2	1687.7	1669.1	1653.7	1638.9	1627.1
7.5°	1870.1	1871.0	1862.8	1860.0	1844.4	1833.0	1809.7	1784.5	1762.1	1733.8	1712.0
10°	1955.0	1954.5	1945.8	1939.0	1925.4	1908.1	1885.3	1855.6	1827.9	1797.0	1767.4
12.5°	2004.5	2002.9	2000.1	1991.9	1979.3	1964.0	1944.6	1915.4	1881.2	1847.4	1812.8
15°	2071.2	2066.8	2058.8	2048.3	2030.4	2012.5	1990.8	1964.9	1932.2	1893.9	1861.8
17.5°	2153.6	2153.8	2141.4	2126.9	2102.5	2070.9	2037.6	1995.7	1951.2	1909.1	1874.9
20°	2221.8	2219.9	2207.7	2179.2	2151.4	2111.9	2073.6	2022.4	1968.0	1913.0	1870.4
22.5°	2319.7	2314.8	2302.0	2264.7	2221.6	2170.7	2112.1	2049.5	1983.9	1921.4	1865.5
25°	2479.9	2476.2	2450.9	2407.7	2347.2	2268.7	2192.2	2106.3	2011.9	1929.8	1861.8
27.5°	2589.6	2585.5	2566.7	2530.9	2475.0	2392.5	2288.9	2174.1	2056.2	1943.2	1845.2
30°	2578.7	2588.0	2585.5	2568.9	2526.9	2452.8	2357.1	2228.0	2087.8	1955.0	1838.3
32.5°	2423.6	2431.9	2453.6	2486.3	2488.8	2459.2	2387.7	2268.5	2123.4	1972.4	1832.9
35°	2057.5	2068.7	2110.7	2176.8	2263.2	2335.4	2350.2	2286.1	2155.8	1993.4	1824.8
37.5°	1581.8	1642.6	1677.9	1747.5	1878.1	2011.0	2138.8	2185.9	2130.4	1984.7	1811.6
40°	1343.7	1358.5	1421.5	1499.9	1609.9	1748.2	1930.4	2061.9	2066.2	1964.9	1790.8
42.5°	1150.1	1168.9	1212.0	1274.7	1368.8	1507.1	1695.2	1868.8	1949.2	1910.6	1763.6
45°	920.1	934.3	965.8	1014.0	1086.2	1200.5	1362.2	1562.9	1722.3	1784.6	1690.8
47.5°	755.8	763.5	790.9	827.6	881.1	964.3	1089.6	1263.8	1454.8	1588.9	1575.7
50°	666.9	675.6	696.6	724.4	769.4	839.8	939.8	1085.0	1282.0	1445.6	1478.4
52.5°	597.8	604.9	618.0	644.3	681.5	735.6	816.3	947.6	1124.9	1298.9	1374.6
55°	505.1	510.1	520.5	535.4	565.1	604.0	673.7	764.5	907.8	1083.2	1194.3
57.5°	428.8	431.3	437.9	451.6	472.1	500.6	551.0	627.9	730.6	888.6	1011.2
60°	380.4	382.9	391.5	400.8	416.8	442.8	482.3	536.0	634.8	765.1	889.2
62.5°	341.8	343.3	347.1	356.3	370.4	390.4	421.5	465.3	543.9	658.4	775.6
65°	286.5	287.2	288.4	295.8	304.4	319.2	339.6	370.5	429.8	516.3	620.0
67.5°	233.5	234.2	238.6	241.2	250.3	258.0	270.0	293.6	335.3	393.6	474.3
70°	203.7	203.2	207.5	210.6	213.7	222.9	230.9	250.1	276.0	320.5	387.8
72.5°	176.1	174.5	176.3	177.4	181.6	187.8	195.9	207.6	227.6	258.3	309.7
75°	133.4	134.0	134.0	135.2	138.3	140.8	143.2	149.4	160.6	180.9	208.7
77.5°	93.6	92.6	95.2	95.6	97.4	100.1	102.3	104.7	109.3	117.7	132.1
80°	67.9	67.9	68.5	70.4	69.8	71.0	74.1	76.6	82.1	87.1	92.0
82.5°	52.1	51.7	52.2	52.6	52.5	53.7	54.8	55.3	57.4	59.9	63.4
85°	28.4	28.4	29.0	29.0	29.6	29.6	30.3	30.3	30.3	30.9	31.5
87.5°	14.7	14.1	13.5	13.4	13.8	14.7	13.9	13.3	13.2	12.9	13.2
90°	19.3	18.7	18.1	17.7	17.1	16.4	15.5	14.6	13.7	12.8	11.6
92.5°	18.0	17.7	17.4	17.2	17.0	16.4	15.5	14.6	13.7	12.8	11.7
95°	16.8	16.8	16.8	16.8	16.8	16.4	15.5	14.6	13.7	12.8	19.6
97.5°	16.8	16.8	16.8	16.8	16.8	19.3	24.3	29.4	34.4	39.5	52.8
100°	16.8	17.5	18.2	18.9	19.6	33.3	59.8	86.3	112.9	139.4	138.7
102.5°	100.8	112.9	125.0	137.1	149.2	157.8	162.8	167.8	172.9	177.8	177.4
105°	238.0	238.1	238.3	238.5	238.7	238.8	238.8	238.8	238.8	238.8	238.8
107.5°	300.0	300.5	301.0	301.6	302.1	302.4	302.3	302.3	302.2	302.2	301.8
110°	342.9	342.7	342.5	342.4	342.2	342.4	342.9	343.4	344.0	344.5	344.1



TEST NUMBER: P333728-927

CATALOG NUMBER: S125RDIW-S1270D1050U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	381.4	381.6	381.8	382.1	382.4	382.9	383.5	384.2	384.8	385.6	385.3
115°	439.0	440.1	441.2	442.3	443.3	444.2	444.9	445.6	446.3	447.0	446.9
117.5°	500.6	501.1	501.5	502.0	502.4	503.1	504.1	505.0	505.9	506.8	506.1
120°	538.4	539.3	540.2	541.1	541.9	542.6	543.0	543.3	543.7	544.0	543.4
122.5°	574.3	575.4	576.4	577.4	578.5	579.1	579.5	579.8	580.2	580.5	580.3
125°	628.9	629.5	630.0	630.6	631.1	631.7	632.4	633.1	633.8	634.5	634.5
127.5°	674.9	676.2	677.6	678.9	680.2	681.0	681.4	681.8	682.2	682.6	682.7
130°	708.3	709.2	710.0	710.9	711.8	712.5	713.0	713.6	714.2	714.6	714.5
132.5°	739.0	739.9	740.8	741.7	742.6	743.1	743.1	743.3	743.4	743.5	743.9
135°	781.2	782.2	783.3	784.3	785.4	786.2	786.5	786.9	787.2	787.6	787.9
137.5°	823.5	824.4	825.3	826.2	827.2	827.6	827.5	827.4	827.4	827.3	827.6
140°	848.4	849.5	850.6	851.7	852.7	853.1	852.7	852.4	852.0	851.7	851.8
142.5°	872.2	873.2	874.3	875.4	876.5	876.9	876.9	876.8	876.7	876.6	876.4
145°	907.0	908.0	909.1	910.1	911.2	911.6	911.5	911.3	911.2	910.9	910.9
147.5°	935.6	936.9	938.2	939.4	940.8	941.3	941.1	940.9	940.6	940.4	940.2
150°	954.2	955.6	957.0	958.5	959.9	960.4	960.1	959.7	959.4	959.0	958.7
152.5°	971.5	972.8	974.1	975.3	976.7	977.1	976.8	976.4	976.0	975.7	975.3
155°	994.3	995.7	997.1	998.5	1000.0	1000.4	999.9	999.3	998.8	998.3	997.9
157.5°	1013.4	1014.8	1016.2	1017.6	1019.1	1019.5	1018.9	1018.4	1017.8	1017.2	1017.2
160°	1025.6	1027.0	1028.4	1029.8	1031.2	1031.6	1030.9	1030.2	1029.4	1028.7	1028.6
162.5°	1036.4	1038.0	1039.6	1041.1	1042.7	1043.0	1042.0	1041.0	1040.0	1038.9	1038.8
165°	1051.1	1052.6	1054.0	1055.4	1056.9	1057.0	1056.0	1054.9	1053.8	1052.7	1052.6
167.5°	1061.4	1063.0	1064.6	1066.2	1067.9	1068.0	1066.7	1065.4	1064.1	1062.9	1062.7
170°	1067.1	1068.8	1070.4	1072.0	1073.6	1073.7	1072.3	1070.9	1069.4	1068.0	1067.8
172.5°	1071.0	1072.6	1074.2	1075.9	1077.4	1077.6	1076.3	1075.1	1073.7	1072.5	1072.1
175°	1076.0	1077.6	1079.2	1080.8	1082.4	1082.5	1081.1	1079.7	1078.2	1076.8	1076.7
177.5°	1078.9	1080.1	1081.2	1082.3	1083.5	1083.5	1082.5	1081.5	1080.5	1079.5	1079.3
180°	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8



TEST NUMBER: P333728-927

CATALOG NUMBER: S125RDIW-S1270D1050U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3
2.5°	1545.8	1542.3	1535.9	1529.9	1522.6	1516.2	1511.6	1506.3	1499.4	1491.0	1484.0
5°	1614.2	1600.6	1582.7	1567.3	1547.5	1532.1	1516.0	1500.6	1485.1	1465.4	1448.1
7.5°	1690.0	1662.0	1634.7	1600.4	1569.2	1541.4	1514.7	1487.7	1461.3	1433.2	1406.2
10°	1736.5	1702.5	1664.9	1621.6	1582.1	1544.4	1509.8	1475.8	1440.0	1408.6	1374.6
12.5°	1780.0	1736.1	1693.0	1638.4	1590.9	1544.9	1500.9	1458.6	1420.3	1379.4	1343.0
15°	1819.2	1776.0	1727.8	1661.1	1595.1	1539.4	1487.6	1432.7	1385.1	1339.4	1298.6
17.5°	1834.4	1789.1	1733.1	1669.0	1596.8	1526.9	1460.1	1399.8	1343.9	1290.6	1244.8
20°	1828.4	1784.6	1727.2	1666.0	1588.9	1516.0	1443.8	1377.1	1314.7	1258.5	1209.7
22.5°	1814.2	1768.8	1713.3	1648.8	1575.5	1498.3	1421.0	1349.9	1284.5	1226.4	1173.1
25°	1792.6	1730.9	1674.1	1611.1	1541.3	1464.7	1385.1	1306.6	1236.9	1177.6	1119.6
27.5°	1770.3	1693.2	1621.0	1558.4	1484.6	1416.3	1339.5	1259.1	1185.7	1125.4	1065.8
30°	1750.0	1663.6	1583.9	1512.9	1443.1	1378.3	1305.4	1227.0	1151.7	1089.3	1028.8
32.5°	1724.8	1632.9	1545.4	1463.5	1396.2	1331.9	1265.9	1191.0	1117.6	1053.2	991.7
35°	1693.2	1575.9	1480.8	1393.8	1319.0	1256.6	1197.4	1136.9	1063.3	996.6	936.8
37.5°	1651.7	1518.6	1408.6	1313.7	1234.9	1172.3	1125.5	1070.2	1003.1	939.2	883.7
40°	1626.5	1477.1	1356.7	1262.8	1180.0	1114.0	1070.2	1023.3	962.1	902.2	846.6
42.5°	1592.9	1439.1	1304.3	1206.5	1123.2	1059.6	1015.3	974.3	923.1	866.6	807.1
45°	1527.1	1365.3	1223.9	1119.0	1035.0	972.6	931.2	894.8	855.9	804.0	752.1
47.5°	1441.4	1288.4	1140.4	1025.8	943.6	885.7	845.5	816.7	788.9	744.8	694.4
50°	1372.8	1225.2	1080.6	969.5	881.8	826.9	789.2	766.4	741.0	700.8	658.9
52.5°	1291.7	1159.9	1018.4	904.8	822.0	770.6	734.4	711.5	690.6	657.9	617.9
55°	1164.0	1048.5	918.9	815.7	739.8	687.9	653.3	631.7	619.4	591.6	560.1
57.5°	1016.7	933.9	819.6	720.2	653.0	601.7	576.4	558.0	544.1	524.4	502.2
60°	913.9	855.9	753.4	658.9	597.1	548.3	525.5	510.1	497.1	480.5	463.1
62.5°	809.7	767.5	678.3	597.1	540.3	499.5	478.1	464.1	449.2	437.9	421.1
65°	670.0	632.3	570.6	507.0	454.5	421.8	406.3	394.0	384.7	372.3	360.6
67.5°	521.2	505.9	463.3	419.4	381.8	352.6	339.3	330.7	319.5	312.1	304.0
70°	429.8	422.4	392.1	363.1	327.9	308.2	295.8	292.1	278.5	271.1	265.5
72.5°	348.8	345.3	327.9	307.8	283.0	265.6	254.3	250.1	241.5	235.5	232.0
75°	239.0	240.2	237.1	224.2	214.9	203.7	193.9	191.4	185.3	180.3	177.2
77.5°	151.1	157.5	157.7	157.1	153.4	146.6	142.5	140.7	134.6	132.8	132.1
80°	103.8	110.5	116.7	116.1	114.9	113.0	110.0	108.1	105.0	103.1	101.9
82.5°	69.2	75.5	80.6	84.0	83.7	81.9	79.8	78.9	78.3	76.9	76.7
85°	32.7	34.0	35.8	40.2	43.3	43.8	43.3	42.6	40.7	41.4	42.0
87.5°	13.5	13.2	13.4	13.2	12.4	14.6	15.8	16.0	15.3	14.6	13.9
90°	10.3	9.1	7.8	6.5	5.1	3.6	2.2	0.8	2.2	3.6	5.1
92.5°	10.6	9.5	8.4	8.3	9.3	10.4	11.3	12.4	11.3	10.4	9.3
95°	26.4	33.1	39.8	43.6	44.0	44.6	45.2	45.6	45.2	44.6	44.0
97.5°	66.2	79.6	93.0	99.2	98.2	97.3	96.3	95.4	96.3	97.3	98.2
100°	138.0	137.3	136.6	135.9	135.4	134.8	134.4	133.8	134.4	134.8	135.4
102.5°	177.0	176.6	176.2	175.6	174.9	174.3	173.6	172.9	173.6	174.3	174.9
105°	238.8	238.8	238.8	238.4	237.7	236.9	236.2	235.5	236.2	236.9	237.7
107.5°	301.5	301.1	300.8	300.6	300.6	300.6	300.6	300.6	300.6	300.6	300.6
110°	343.8	343.4	343.1	342.9	342.9	342.9	342.9	342.9	342.9	342.9	342.9





TEST NUMBER: P333728-927

CATALOG NUMBER: S125RDIW-S1270D1050U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	385.1	384.9	384.7	384.4	383.9	383.5	383.1	382.6	383.1	383.5	383.9
115°	446.7	446.6	446.3	445.8	444.9	444.0	443.1	442.3	443.1	444.0	444.9
117.5°	505.5	504.8	504.1	503.8	503.8	503.9	503.9	504.0	503.9	503.9	503.8
120°	543.0	542.4	541.9	541.7	541.9	542.0	542.2	542.4	542.2	542.0	541.9
122.5°	580.0	579.8	579.6	579.1	578.4	577.7	577.0	576.4	577.0	577.7	578.4
125°	634.5	634.5	634.5	633.9	632.6	631.4	630.2	628.9	630.2	631.4	632.6
127.5°	682.9	682.9	683.0	682.6	681.8	680.9	680.0	679.1	680.0	680.9	681.8
130°	714.3	714.2	713.9	713.4	712.5	711.6	710.7	709.9	710.7	711.6	712.5
132.5°	744.3	744.7	745.0	744.7	743.7	742.7	741.6	740.6	741.6	742.7	743.7
135°	788.3	788.6	789.0	788.6	787.6	786.5	785.4	784.3	785.4	786.5	787.6
137.5°	828.0	828.3	828.6	828.3	827.4	826.4	825.5	824.6	825.5	826.4	827.4
140°	852.0	852.2	852.4	852.3	851.9	851.6	851.2	850.9	851.2	851.6	851.9
142.5°	876.2	875.9	875.7	875.4	875.2	875.0	874.8	874.6	874.8	875.0	875.2
145°	910.9	910.9	910.9	910.8	910.5	910.1	909.7	909.3	909.7	910.1	910.5
147.5°	940.0	939.8	939.6	939.5	939.6	939.7	939.8	939.8	939.8	939.7	939.6
150°	958.3	958.0	957.6	957.6	958.0	958.3	958.7	959.0	958.7	958.3	958.0
152.5°	975.0	974.6	974.3	974.5	975.3	976.0	976.8	977.6	976.8	976.0	975.3
155°	997.6	997.2	996.9	997.2	998.3	999.3	1000.4	1001.5	1000.4	999.3	998.3
157.5°	1017.1	1017.1	1017.1	1017.3	1018.0	1018.7	1019.3	1019.9	1019.3	1018.7	1018.0
160°	1028.4	1028.2	1028.0	1028.5	1029.5	1030.6	1031.7	1032.8	1031.7	1030.6	1029.5
162.5°	1038.6	1038.5	1038.2	1038.7	1039.8	1040.8	1042.0	1043.0	1042.0	1040.8	1039.8
165°	1052.4	1052.3	1052.0	1052.5	1053.6	1054.6	1055.7	1056.8	1055.7	1054.6	1053.6
167.5°	1062.5	1062.3	1062.2	1062.6	1063.7	1064.9	1066.0	1067.0	1066.0	1064.9	1063.7
170°	1067.6	1067.5	1067.3	1067.8	1069.1	1070.3	1071.6	1072.8	1071.6	1070.3	1069.1
172.5°	1071.8	1071.5	1071.2	1071.7	1072.9	1074.1	1075.4	1076.7	1075.4	1074.1	1072.9
175°	1076.4	1076.3	1076.1	1076.5	1077.6	1078.6	1079.7	1080.8	1079.7	1078.6	1077.6
177.5°	1079.3	1079.1	1079.0	1079.3	1080.1	1081.0	1081.9	1082.8	1081.9	1081.0	1080.1
180°	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8



TEST NUMBER: P333728-927

CATALOG NUMBER: S125RDIW-S1270D1050U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3
2.5°	1479.1	1472.2	1467.2	1457.3	1450.4	1447.5	1442.0	1440.5	1446.0	1442.0	1441.5
5°	1435.1	1417.2	1403.0	1388.8	1373.3	1363.5	1348.7	1346.2	1342.5	1336.9	1335.7
7.5°	1382.4	1359.1	1340.8	1317.3	1296.9	1280.5	1261.9	1253.2	1248.4	1241.2	1231.6
10°	1346.8	1319.0	1294.3	1270.8	1245.5	1225.2	1206.7	1192.4	1183.1	1174.5	1170.8
12.5°	1311.7	1283.4	1251.8	1223.4	1195.2	1172.3	1151.8	1142.6	1132.3	1122.1	1113.5
15°	1257.3	1219.6	1185.0	1152.3	1128.2	1103.5	1083.7	1070.2	1054.7	1050.4	1033.7
17.5°	1199.4	1162.5	1122.0	1087.6	1059.6	1032.5	1010.7	995.3	983.7	967.8	960.1
20°	1163.4	1119.6	1080.1	1048.5	1017.6	985.6	963.3	950.4	939.2	926.3	920.1
22.5°	1124.9	1082.0	1041.5	1004.6	973.2	941.6	925.7	912.4	899.7	887.7	879.6
25°	1068.3	1025.1	982.5	944.2	911.5	888.6	870.1	854.6	847.9	836.1	827.4
27.5°	1012.3	966.4	922.2	884.0	858.3	835.8	820.5	808.3	796.1	785.8	778.3
30°	976.3	929.4	881.2	851.0	823.8	802.2	785.4	773.7	764.5	755.2	749.6
32.5°	940.2	891.8	849.1	816.3	790.7	772.0	754.9	743.6	733.9	723.6	717.1
35°	882.4	833.1	798.4	766.4	741.0	723.7	712.0	695.9	687.9	680.5	673.7
37.5°	828.7	782.8	745.4	717.2	695.2	678.0	662.8	654.2	644.3	637.6	632.0
40°	789.2	747.2	713.2	683.6	667.6	648.4	634.2	623.1	615.7	607.0	600.9
42.5°	753.6	714.6	681.6	655.0	634.9	618.8	605.1	593.9	584.6	578.4	573.1
45°	703.4	664.5	632.3	607.6	589.1	573.7	559.4	553.9	541.5	534.2	531.7
47.5°	651.3	616.6	585.5	562.8	543.8	529.2	515.9	504.5	497.7	490.4	486.5
50°	616.3	583.0	553.9	531.7	513.2	497.1	484.7	477.4	468.1	461.3	456.4
52.5°	581.2	550.3	521.3	500.0	484.0	467.9	454.2	446.7	437.9	433.6	430.2
55°	531.1	498.4	473.6	452.7	435.9	421.1	408.2	400.8	395.2	390.9	389.7
57.5°	474.3	448.3	425.3	406.5	389.1	375.2	363.8	356.8	351.9	351.3	347.5
60°	437.2	413.8	392.8	372.3	357.5	344.6	334.7	326.7	321.7	321.1	319.9
62.5°	400.1	377.6	358.1	340.2	326.9	314.4	305.1	296.0	293.1	290.0	287.2
65°	345.2	324.8	308.8	294.5	280.4	269.8	260.6	255.0	248.3	244.5	237.7
67.5°	291.2	275.4	260.0	248.0	236.9	226.9	219.2	211.0	206.4	203.4	198.4
70°	255.6	243.3	227.8	214.9	206.3	198.2	192.0	182.8	179.7	177.2	174.8
72.5°	222.0	211.2	198.2	187.7	179.1	171.5	164.4	160.0	157.0	154.5	153.0
75°	174.8	164.3	153.1	145.8	139.6	133.4	129.7	126.6	125.3	124.8	122.2
77.5°	128.3	122.8	113.8	108.0	103.9	101.4	98.1	96.5	96.3	93.6	92.8
80°	98.2	95.1	87.7	85.2	82.1	79.7	77.8	74.7	71.6	70.4	68.5
82.5°	73.0	69.9	66.9	63.0	60.4	58.9	57.0	55.9	56.3	54.6	53.7
85°	38.9	35.8	34.6	34.0	32.7	34.0	33.4	32.7	32.1	31.5	32.1
87.5°	13.6	13.9	13.7	14.9	13.7	14.4	14.6	14.3	14.5	14.7	14.3
90°	6.5	7.8	9.1	10.3	11.6	12.8	13.7	14.6	15.5	16.4	17.1
92.5°	8.3	8.4	9.5	10.6	11.7	12.8	13.7	14.6	15.5	16.4	17.0
95°	43.6	39.8	33.1	26.4	19.6	12.8	13.7	14.6	15.5	16.4	16.8
97.5°	99.2	93.0	79.6	66.2	52.8	39.5	34.4	29.4	24.3	19.3	16.8
100°	135.9	136.6	137.3	138.0	138.7	139.4	112.9	86.3	59.8	33.3	19.6
102.5°	175.6	176.2	176.6	177.0	177.4	177.8	172.9	167.8	162.8	157.8	149.2
105°	238.4	238.8	238.8	238.8	238.8	238.8	238.8	238.8	238.8	238.8	238.7
107.5°	300.6	300.8	301.1	301.5	301.8	302.2	302.2	302.3	302.3	302.4	302.1
110°	342.9	343.1	343.4	343.8	344.1	344.5	344.0	343.4	342.9	342.4	342.2



TEST NUMBER: P333728-927

CATALOG NUMBER: S125RDIW-S1270D1050U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	384.4	384.7	384.9	385.1	385.3	385.6	384.8	384.2	383.5	382.9	382.4
115°	445.8	446.3	446.6	446.7	446.9	447.0	446.3	445.6	444.9	444.2	443.3
117.5°	503.8	504.1	504.8	505.5	506.1	506.8	505.9	505.0	504.1	503.1	502.4
120°	541.7	541.9	542.4	543.0	543.4	544.0	543.7	543.3	543.0	542.6	541.9
122.5°	579.1	579.6	579.8	580.0	580.3	580.5	580.2	579.8	579.5	579.1	578.5
125°	633.9	634.5	634.5	634.5	634.5	634.5	633.8	633.1	632.4	631.7	631.1
127.5°	682.6	683.0	682.9	682.9	682.7	682.6	682.2	681.8	681.4	681.0	680.2
130°	713.4	713.9	714.2	714.3	714.5	714.6	714.2	713.6	713.0	712.5	711.8
132.5°	744.7	745.0	744.7	744.3	743.9	743.5	743.4	743.3	743.1	743.1	742.6
135°	788.6	789.0	788.6	788.3	787.9	787.6	787.2	786.9	786.5	786.2	785.4
137.5°	828.3	828.6	828.3	828.0	827.6	827.3	827.4	827.4	827.5	827.6	827.2
140°	852.3	852.4	852.2	852.0	851.8	851.7	852.0	852.4	852.7	853.1	852.7
142.5°	875.4	875.7	875.9	876.2	876.4	876.6	876.7	876.8	876.9	876.9	876.5
145°	910.8	910.9	910.9	910.9	910.9	910.9	911.2	911.3	911.5	911.6	911.2
147.5°	939.5	939.6	939.8	940.0	940.2	940.4	940.6	940.9	941.1	941.3	940.8
150°	957.6	957.6	958.0	958.3	958.7	959.0	959.4	959.7	960.1	960.4	959.9
152.5°	974.5	974.3	974.6	975.0	975.3	975.7	976.0	976.4	976.8	977.1	976.7
155°	997.2	996.9	997.2	997.6	997.9	998.3	998.8	999.3	999.9	1000.4	1000.0
157.5°	1017.3	1017.1	1017.1	1017.1	1017.2	1017.2	1017.8	1018.4	1018.9	1019.5	1019.1
160°	1028.5	1028.0	1028.2	1028.4	1028.6	1028.7	1029.4	1030.2	1030.9	1031.6	1031.2
162.5°	1038.7	1038.2	1038.5	1038.6	1038.8	1038.9	1040.0	1041.0	1042.0	1043.0	1042.7
165°	1052.5	1052.0	1052.3	1052.4	1052.6	1052.7	1053.8	1054.9	1056.0	1057.0	1056.9
167.5°	1062.6	1062.2	1062.3	1062.5	1062.7	1062.9	1064.1	1065.4	1066.7	1068.0	1067.9
170°	1067.8	1067.3	1067.5	1067.6	1067.8	1068.0	1069.4	1070.9	1072.3	1073.7	1073.6
172.5°	1071.7	1071.2	1071.5	1071.8	1072.1	1072.5	1073.7	1075.1	1076.3	1077.6	1077.4
175°	1076.5	1076.1	1076.3	1076.4	1076.7	1076.8	1078.2	1079.7	1081.1	1082.5	1082.4
177.5°	1079.3	1079.0	1079.1	1079.3	1079.3	1079.5	1080.5	1081.5	1082.5	1083.5	1083.5
180°	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8



TEST NUMBER: P333728-927

CATALOG NUMBER: S125RDIW-S1270D1050U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3
2.5°	1441.1	1435.6	1434.1	1436.1	1434.1	1435.6	1441.1	1441.5	1442.0	1446.0	1440.5
5°	1329.5	1323.3	1326.4	1325.2	1326.4	1323.3	1329.5	1335.7	1336.9	1342.5	1346.2
7.5°	1231.4	1223.8	1215.6	1218.2	1215.6	1223.8	1231.4	1231.6	1241.2	1248.4	1253.2
10°	1162.8	1156.6	1152.9	1156.0	1152.9	1156.6	1162.8	1170.8	1174.5	1183.1	1192.4
12.5°	1105.0	1101.3	1098.0	1096.7	1098.0	1101.3	1105.0	1113.5	1122.1	1132.3	1142.6
15°	1026.3	1018.9	1015.8	1007.8	1015.8	1018.9	1026.3	1033.7	1050.4	1054.7	1070.2
17.5°	953.8	951.3	943.3	939.8	943.3	951.3	953.8	960.1	967.8	983.7	995.3
20°	910.9	908.4	900.3	905.3	900.3	908.4	910.9	920.1	926.3	939.2	950.4
22.5°	875.3	869.8	867.2	865.8	867.2	869.8	875.3	879.6	887.7	899.7	912.4
25°	825.0	817.0	813.9	810.2	813.9	817.0	825.0	827.4	836.1	847.9	854.6
27.5°	774.8	770.6	766.4	765.5	766.4	770.6	774.8	778.3	785.8	796.1	808.3
30°	742.3	737.9	734.8	734.8	734.8	737.9	742.3	749.6	755.2	764.5	773.7
32.5°	713.1	709.8	706.7	706.2	706.7	709.8	713.1	717.1	723.6	733.9	743.6
35°	670.7	665.7	664.5	660.8	664.5	665.7	670.7	673.7	680.5	687.9	695.9
37.5°	626.5	622.4	622.3	621.9	622.3	622.4	626.5	632.0	637.6	644.3	654.2
40°	598.3	595.2	594.7	590.3	594.7	595.2	598.3	600.9	607.0	615.7	623.1
42.5°	568.2	566.6	564.5	562.7	564.5	566.6	568.2	573.1	578.4	584.6	593.9
45°	527.4	523.0	523.0	519.9	523.0	523.0	527.4	531.7	534.2	541.5	553.9
47.5°	485.1	481.8	482.1	479.0	482.1	481.8	485.1	486.5	490.4	497.7	504.5
50°	456.9	455.1	454.5	453.3	454.5	455.1	456.9	456.4	461.3	468.1	477.4
52.5°	428.8	427.9	430.3	427.5	430.3	427.9	428.8	430.2	433.6	437.9	446.7
55°	390.9	389.0	392.8	389.0	392.8	389.0	390.9	389.7	390.9	395.2	400.8
57.5°	347.3	345.5	348.9	347.1	348.9	345.5	347.3	347.5	351.3	351.9	356.8
60°	318.6	315.0	316.8	317.4	316.8	315.0	318.6	319.9	321.1	321.7	326.7
62.5°	284.6	282.3	283.7	280.8	283.7	282.3	284.6	287.2	290.0	293.1	296.0
65°	236.5	234.6	232.2	230.9	232.2	234.6	236.5	237.7	244.5	248.3	255.0
67.5°	198.7	194.2	194.2	195.1	194.2	194.2	198.7	198.4	203.4	206.4	211.0
70°	171.0	171.0	170.4	170.4	170.4	171.0	171.0	174.8	177.2	179.7	182.8
72.5°	151.8	151.3	150.2	149.7	150.2	151.3	151.8	153.0	154.5	157.0	160.0
75°	122.2	122.9	121.7	121.0	121.7	122.9	122.2	122.2	124.8	125.3	126.6
77.5°	90.3	87.7	89.0	87.7	89.0	87.7	90.3	92.8	93.6	96.3	96.5
80°	68.5	67.9	69.8	67.9	69.8	67.9	68.5	68.5	70.4	71.6	74.7
82.5°	54.2	53.6	54.5	53.1	54.5	53.6	54.2	53.7	54.6	56.3	55.9
85°	32.7	32.1	31.5	32.1	31.5	32.1	32.7	32.1	31.5	32.1	32.7
87.5°	14.9	14.5	14.6	14.7	14.6	14.5	14.9	14.3	14.7	14.5	14.3
90°	17.7	18.1	18.7	19.3	18.7	18.1	17.7	17.1	16.4	15.5	14.6
92.5°	17.2	17.4	17.7	18.0	17.7	17.4	17.2	17.0	16.4	15.5	14.6
95°	16.8	16.8	16.8	16.8	16.8	16.8	16.8	16.8	16.4	15.5	14.6
97.5°	16.8	16.8	16.8	16.8	16.8	16.8	16.8	16.8	19.3	24.3	29.4
100°	18.9	18.2	17.5	16.8	17.5	18.2	18.9	19.6	33.3	59.8	86.3
102.5°	137.1	125.0	112.9	100.8	112.9	125.0	137.1	149.2	157.8	162.8	167.8
105°	238.5	238.3	238.1	238.0	238.1	238.3	238.5	238.7	238.8	238.8	238.8
107.5°	301.6	301.0	300.5	300.0	300.5	301.0	301.6	302.1	302.4	302.3	302.3
110°	342.4	342.5	342.7	342.9	342.7	342.5	342.4	342.2	342.4	342.9	343.4



TEST NUMBER: P333728-927

CATALOG NUMBER: S125RDIW-S1270D1050U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	382.1	381.8	381.6	381.4	381.6	381.8	382.1	382.4	382.9	383.5	384.2
115°	442.3	441.2	440.1	439.0	440.1	441.2	442.3	443.3	444.2	444.9	445.6
117.5°	502.0	501.5	501.1	500.6	501.1	501.5	502.0	502.4	503.1	504.1	505.0
120°	541.1	540.2	539.3	538.4	539.3	540.2	541.1	541.9	542.6	543.0	543.3
122.5°	577.4	576.4	575.4	574.3	575.4	576.4	577.4	578.5	579.1	579.5	579.8
125°	630.6	630.0	629.5	628.9	629.5	630.0	630.6	631.1	631.7	632.4	633.1
127.5°	678.9	677.6	676.2	674.9	676.2	677.6	678.9	680.2	681.0	681.4	681.8
130°	710.9	710.0	709.2	708.3	709.2	710.0	710.9	711.8	712.5	713.0	713.6
132.5°	741.7	740.8	739.9	739.0	739.9	740.8	741.7	742.6	743.1	743.1	743.3
135°	784.3	783.3	782.2	781.2	782.2	783.3	784.3	785.4	786.2	786.5	786.9
137.5°	826.2	825.3	824.4	823.5	824.4	825.3	826.2	827.2	827.6	827.5	827.4
140°	851.7	850.6	849.5	848.4	849.5	850.6	851.7	852.7	853.1	852.7	852.4
142.5°	875.4	874.3	873.2	872.2	873.2	874.3	875.4	876.5	876.9	876.9	876.8
145°	910.1	909.1	908.0	907.0	908.0	909.1	910.1	911.2	911.6	911.5	911.3
147.5°	939.4	938.2	936.9	935.6	936.9	938.2	939.4	940.8	941.3	941.1	940.9
150°	958.5	957.0	955.6	954.2	955.6	957.0	958.5	959.9	960.4	960.1	959.7
152.5°	975.3	974.1	972.8	971.5	972.8	974.1	975.3	976.7	977.1	976.8	976.4
155°	998.5	997.1	995.7	994.3	995.7	997.1	998.5	1000.0	1000.4	999.9	999.3
157.5°	1017.6	1016.2	1014.8	1013.4	1014.8	1016.2	1017.6	1019.1	1019.5	1018.9	1018.4
160°	1029.8	1028.4	1027.0	1025.6	1027.0	1028.4	1029.8	1031.2	1031.6	1030.9	1030.2
162.5°	1041.1	1039.6	1038.0	1036.4	1038.0	1039.6	1041.1	1042.7	1043.0	1042.0	1041.0
165°	1055.4	1054.0	1052.6	1051.1	1052.6	1054.0	1055.4	1056.9	1057.0	1056.0	1054.9
167.5°	1066.2	1064.6	1063.0	1061.4	1063.0	1064.6	1066.2	1067.9	1068.0	1066.7	1065.4
170°	1072.0	1070.4	1068.8	1067.1	1068.8	1070.4	1072.0	1073.6	1073.7	1072.3	1070.9
172.5°	1075.9	1074.2	1072.6	1071.0	1072.6	1074.2	1075.9	1077.4	1077.6	1076.3	1075.1
175°	1080.8	1079.2	1077.6	1076.0	1077.6	1079.2	1080.8	1082.4	1082.5	1081.1	1079.7
177.5°	1082.3	1081.2	1080.1	1078.9	1080.1	1081.2	1082.3	1083.5	1083.5	1082.5	1081.5
180°	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8



TEST NUMBER: P333728-927

CATALOG NUMBER: S125RDIW-S1270D1050U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3
2.5°	1442.0	1447.5	1450.4	1457.3	1467.2	1472.2	1479.1	1484.0	1491.0	1499.4	1506.3
5°	1348.7	1363.5	1373.3	1388.8	1403.0	1417.2	1435.1	1448.1	1465.4	1485.1	1500.6
7.5°	1261.9	1280.5	1296.9	1317.3	1340.8	1359.1	1382.4	1406.2	1433.2	1461.3	1487.7
10°	1206.7	1225.2	1245.5	1270.8	1294.3	1319.0	1346.8	1374.6	1408.6	1440.0	1475.8
12.5°	1151.8	1172.3	1195.2	1223.4	1251.8	1283.4	1311.7	1343.0	1379.4	1420.3	1458.6
15°	1083.7	1103.5	1128.2	1152.3	1185.0	1219.6	1257.3	1298.6	1339.4	1385.1	1432.7
17.5°	1010.7	1032.5	1059.6	1087.6	1122.0	1162.5	1199.4	1244.8	1290.6	1343.9	1399.8
20°	963.3	985.6	1017.6	1048.5	1080.1	1119.6	1163.4	1209.7	1258.5	1314.7	1377.1
22.5°	925.7	941.6	973.2	1004.6	1041.5	1082.0	1124.9	1173.1	1226.4	1284.5	1349.9
25°	870.1	888.6	911.5	944.2	982.5	1025.1	1068.3	1119.6	1177.6	1236.9	1306.6
27.5°	820.5	835.8	858.3	884.0	922.2	966.4	1012.3	1065.8	1125.4	1185.7	1259.1
30°	785.4	802.2	823.8	851.0	881.2	929.4	976.3	1028.8	1089.3	1151.7	1227.0
32.5°	754.9	772.0	790.7	816.3	849.1	891.8	940.2	991.7	1053.2	1117.6	1191.0
35°	712.0	723.7	741.0	766.4	798.4	833.1	882.4	936.8	996.6	1063.3	1136.9
37.5°	662.8	678.0	695.2	717.2	745.4	782.8	828.7	883.7	939.2	1003.1	1070.2
40°	634.2	648.4	667.6	683.6	713.2	747.2	789.2	846.6	902.2	962.1	1023.3
42.5°	605.1	618.8	634.9	655.0	681.6	714.6	753.6	807.1	866.6	923.1	974.3
45°	559.4	573.7	589.1	607.6	632.3	664.5	703.4	752.1	804.0	855.9	894.8
47.5°	515.9	529.2	543.8	562.8	585.5	616.6	651.3	694.4	744.8	788.9	816.7
50°	484.7	497.1	513.2	531.7	553.9	583.0	616.3	658.9	700.8	741.0	766.4
52.5°	454.2	467.9	484.0	500.0	521.3	550.3	581.2	617.9	657.9	690.6	711.5
55°	408.2	421.1	435.9	452.7	473.6	498.4	531.1	560.1	591.6	619.4	631.7
57.5°	363.8	375.2	389.1	406.5	425.3	448.3	474.3	502.2	524.4	544.1	558.0
60°	334.7	344.6	357.5	372.3	392.8	413.8	437.2	463.1	480.5	497.1	510.1
62.5°	305.1	314.4	326.9	340.2	358.1	377.6	400.1	421.1	437.9	449.2	464.1
65°	260.6	269.8	280.4	294.5	308.8	324.8	345.2	360.6	372.3	384.7	394.0
67.5°	219.2	226.9	236.9	248.0	260.0	275.4	291.2	304.0	312.1	319.5	330.7
70°	192.0	198.2	206.3	214.9	227.8	243.3	255.6	265.5	271.1	278.5	292.1
72.5°	164.4	171.5	179.1	187.7	198.2	211.2	222.0	232.0	235.5	241.5	250.1
75°	129.7	133.4	139.6	145.8	153.1	164.3	174.8	177.2	180.3	185.3	191.4
77.5°	98.1	101.4	103.9	108.0	113.8	122.8	128.3	132.1	132.8	134.6	140.7
80°	77.8	79.7	82.1	85.2	87.7	95.1	98.2	101.9	103.1	105.0	108.1
82.5°	57.0	58.9	60.4	63.0	66.9	69.9	73.0	76.7	76.9	78.3	78.9
85°	33.4	34.0	32.7	34.0	34.6	35.8	38.9	42.0	41.4	40.7	42.6
87.5°	14.6	14.4	13.7	14.9	13.7	13.9	13.6	13.9	14.6	15.3	16.0
90°	13.7	12.8	11.6	10.3	9.1	7.8	6.5	5.1	3.6	2.2	0.8
92.5°	13.7	12.8	11.7	10.6	9.5	8.4	8.3	9.3	10.4	11.3	12.4
95°	13.7	12.8	19.6	26.4	33.1	39.8	43.6	44.0	44.6	45.2	45.6
97.5°	34.4	39.5	52.8	66.2	79.6	93.0	99.2	98.2	97.3	96.3	95.4
100°	112.9	139.4	138.7	138.0	137.3	136.6	135.9	135.4	134.8	134.4	133.8
102.5°	172.9	177.8	177.4	177.0	176.6	176.2	175.6	174.9	174.3	173.6	172.9
105°	238.8	238.8	238.8	238.8	238.8	238.8	238.4	237.7	236.9	236.2	235.5
107.5°	302.2	302.2	301.8	301.5	301.1	300.8	300.6	300.6	300.6	300.6	300.6
110°	344.0	344.5	344.1	343.8	343.4	343.1	342.9	342.9	342.9	342.9	342.9



TEST NUMBER: P333728-927

CATALOG NUMBER: S125RDIW-S1270D1050U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	384.8	385.6	385.3	385.1	384.9	384.7	384.4	383.9	383.5	383.1	382.6
115°	446.3	447.0	446.9	446.7	446.6	446.3	445.8	444.9	444.0	443.1	442.3
117.5°	505.9	506.8	506.1	505.5	504.8	504.1	503.8	503.8	503.9	503.9	504.0
120°	543.7	544.0	543.4	543.0	542.4	541.9	541.7	541.9	542.0	542.2	542.4
122.5°	580.2	580.5	580.3	580.0	579.8	579.6	579.1	578.4	577.7	577.0	576.4
125°	633.8	634.5	634.5	634.5	634.5	634.5	633.9	632.6	631.4	630.2	628.9
127.5°	682.2	682.6	682.7	682.9	682.9	683.0	682.6	681.8	680.9	680.0	679.1
130°	714.2	714.6	714.5	714.3	714.2	713.9	713.4	712.5	711.6	710.7	709.9
132.5°	743.4	743.5	743.9	744.3	744.7	745.0	744.7	743.7	742.7	741.6	740.6
135°	787.2	787.6	787.9	788.3	788.6	789.0	788.6	787.6	786.5	785.4	784.3
137.5°	827.4	827.3	827.6	828.0	828.3	828.6	828.3	827.4	826.4	825.5	824.6
140°	852.0	851.7	851.8	852.0	852.2	852.4	852.3	851.9	851.6	851.2	850.9
142.5°	876.7	876.6	876.4	876.2	875.9	875.7	875.4	875.2	875.0	874.8	874.6
145°	911.2	910.9	910.9	910.9	910.9	910.9	910.8	910.5	910.1	909.7	909.3
147.5°	940.6	940.4	940.2	940.0	939.8	939.6	939.5	939.6	939.7	939.8	939.8
150°	959.4	959.0	958.7	958.3	958.0	957.6	957.6	958.0	958.3	958.7	959.0
152.5°	976.0	975.7	975.3	975.0	974.6	974.3	974.5	975.3	976.0	976.8	977.6
155°	998.8	998.3	997.9	997.6	997.2	996.9	997.2	998.3	999.3	1000.4	1001.5
157.5°	1017.8	1017.2	1017.2	1017.1	1017.1	1017.1	1017.3	1018.0	1018.7	1019.3	1019.9
160°	1029.4	1028.7	1028.6	1028.4	1028.2	1028.0	1028.5	1029.5	1030.6	1031.7	1032.8
162.5°	1040.0	1038.9	1038.8	1038.6	1038.5	1038.2	1038.7	1039.8	1040.8	1042.0	1043.0
165°	1053.8	1052.7	1052.6	1052.4	1052.3	1052.0	1052.5	1053.6	1054.6	1055.7	1056.8
167.5°	1064.1	1062.9	1062.7	1062.5	1062.3	1062.2	1062.6	1063.7	1064.9	1066.0	1067.0
170°	1069.4	1068.0	1067.8	1067.6	1067.5	1067.3	1067.8	1069.1	1070.3	1071.6	1072.8
172.5°	1073.7	1072.5	1072.1	1071.8	1071.5	1071.2	1071.7	1072.9	1074.1	1075.4	1076.7
175°	1078.2	1076.8	1076.7	1076.4	1076.3	1076.1	1076.5	1077.6	1078.6	1079.7	1080.8
177.5°	1080.5	1079.5	1079.3	1079.3	1079.1	1079.0	1079.3	1080.1	1081.0	1081.9	1082.8
180°	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8



TEST NUMBER: P333728-927

CATALOG NUMBER: S125RDIW-S1270D1050U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3
2.5°	1511.6	1516.2	1522.6	1529.9	1535.9	1542.3	1545.8	1545.8	1548.7	1555.1	1563.5
5°	1516.0	1532.1	1547.5	1567.3	1582.7	1600.6	1614.2	1627.1	1638.9	1653.7	1669.1
7.5°	1514.7	1541.4	1569.2	1600.4	1634.7	1662.0	1690.0	1712.0	1733.8	1762.1	1784.5
10°	1509.8	1544.4	1582.1	1621.6	1664.9	1702.5	1736.5	1767.4	1797.0	1827.9	1855.6
12.5°	1500.9	1544.9	1590.9	1638.4	1693.0	1736.1	1780.0	1812.8	1847.4	1881.2	1915.4
15°	1487.6	1539.4	1595.1	1661.1	1727.8	1776.0	1819.2	1861.8	1893.9	1932.2	1964.9
17.5°	1460.1	1526.9	1596.8	1669.0	1733.1	1789.1	1834.4	1874.9	1909.1	1951.2	1995.7
20°	1443.8	1516.0	1588.9	1666.0	1727.2	1784.6	1828.4	1870.4	1913.0	1968.0	2022.4
22.5°	1421.0	1498.3	1575.5	1648.8	1713.3	1768.8	1814.2	1865.5	1921.4	1983.9	2049.5
25°	1385.1	1464.7	1541.3	1611.1	1674.1	1730.9	1792.6	1861.8	1929.8	2011.9	2106.3
27.5°	1339.5	1416.3	1484.6	1558.4	1621.0	1693.2	1770.3	1845.2	1943.2	2056.2	2174.1
30°	1305.4	1378.3	1443.1	1512.9	1583.9	1663.6	1750.0	1838.3	1955.0	2087.8	2228.0
32.5°	1265.9	1331.9	1396.2	1463.5	1545.4	1632.9	1724.8	1832.9	1972.4	2123.4	2268.5
35°	1197.4	1256.6	1319.0	1393.8	1480.8	1575.9	1693.2	1824.8	1993.4	2155.8	2286.1
37.5°	1125.5	1172.3	1234.9	1313.7	1408.6	1518.6	1651.7	1811.6	1984.7	2130.4	2185.9
40°	1070.2	1114.0	1180.0	1262.8	1356.7	1477.1	1626.5	1790.8	1964.9	2066.2	2061.9
42.5°	1015.3	1059.6	1123.2	1206.5	1304.3	1439.1	1592.9	1763.6	1910.6	1949.2	1868.8
45°	931.2	972.6	1035.0	1119.0	1223.9	1365.3	1527.1	1690.8	1784.6	1722.3	1562.9
47.5°	845.5	885.7	943.6	1025.8	1140.4	1288.4	1441.4	1575.7	1588.9	1454.8	1263.8
50°	789.2	826.9	881.8	969.5	1080.6	1225.2	1372.8	1478.4	1445.6	1282.0	1085.0
52.5°	734.4	770.6	822.0	904.8	1018.4	1159.9	1291.7	1374.6	1298.9	1124.9	947.6
55°	653.3	687.9	739.8	815.7	918.9	1048.5	1164.0	1194.3	1083.2	907.8	764.5
57.5°	576.4	601.7	653.0	720.2	819.6	933.9	1016.7	1011.2	888.6	730.6	627.9
60°	525.5	548.3	597.1	658.9	753.4	855.9	913.9	889.2	765.1	634.8	536.0
62.5°	478.1	499.5	540.3	597.1	678.3	767.5	809.7	775.6	658.4	543.9	465.3
65°	406.3	421.8	454.5	507.0	570.6	632.3	670.0	620.0	516.3	429.8	370.5
67.5°	339.3	352.6	381.8	419.4	463.3	505.9	521.2	474.3	393.6	335.3	293.6
70°	295.8	308.2	327.9	363.1	392.1	422.4	429.8	387.8	320.5	276.0	250.1
72.5°	254.3	265.6	283.0	307.8	327.9	345.3	348.8	309.7	258.3	227.6	207.6
75°	193.9	203.7	214.9	224.2	237.1	240.2	239.0	208.7	180.9	160.6	149.4
77.5°	142.5	146.6	153.4	157.1	157.7	157.5	151.1	132.1	117.7	109.3	104.7
80°	110.0	113.0	114.9	116.1	116.7	110.5	103.8	92.0	87.1	82.1	76.6
82.5°	79.8	81.9	83.7	84.0	80.6	75.5	69.2	63.4	59.9	57.4	55.3
85°	43.3	43.8	43.3	40.2	35.8	34.0	32.7	31.5	30.9	30.3	30.3
87.5°	15.8	14.6	12.4	13.2	13.4	13.2	13.5	13.2	12.9	13.2	13.3
90°	2.2	3.6	5.1	6.5	7.8	9.1	10.3	11.6	12.8	13.7	14.6
92.5°	11.3	10.4	9.3	8.3	8.4	9.5	10.6	11.7	12.8	13.7	14.6
95°	45.2	44.6	44.0	43.6	39.8	33.1	26.4	19.6	12.8	13.7	14.6
97.5°	96.3	97.3	98.2	99.2	93.0	79.6	66.2	52.8	39.5	34.4	29.4
100°	134.4	134.8	135.4	135.9	136.6	137.3	138.0	138.7	139.4	112.9	86.3
102.5°	173.6	174.3	174.9	175.6	176.2	176.6	177.0	177.4	177.8	172.9	167.8
105°	236.2	236.9	237.7	238.4	238.8	238.8	238.8	238.8	238.8	238.8	238.8
107.5°	300.6	300.6	300.6	300.6	300.8	301.1	301.5	301.8	302.2	302.2	302.3
110°	342.9	342.9	342.9	342.9	343.1	343.4	343.8	344.1	344.5	344.0	343.4





TEST NUMBER: P333728-927

CATALOG NUMBER: S125RDIW-S1270D1050U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	383.1	383.5	383.9	384.4	384.7	384.9	385.1	385.3	385.6	384.8	384.2
115°	443.1	444.0	444.9	445.8	446.3	446.6	446.7	446.9	447.0	446.3	445.6
117.5°	503.9	503.9	503.8	503.8	504.1	504.8	505.5	506.1	506.8	505.9	505.0
120°	542.2	542.0	541.9	541.7	541.9	542.4	543.0	543.4	544.0	543.7	543.3
122.5°	577.0	577.7	578.4	579.1	579.6	579.8	580.0	580.3	580.5	580.2	579.8
125°	630.2	631.4	632.6	633.9	634.5	634.5	634.5	634.5	634.5	633.8	633.1
127.5°	680.0	680.9	681.8	682.6	683.0	682.9	682.9	682.7	682.6	682.2	681.8
130°	710.7	711.6	712.5	713.4	713.9	714.2	714.3	714.5	714.6	714.2	713.6
132.5°	741.6	742.7	743.7	744.7	745.0	744.7	744.3	743.9	743.5	743.4	743.3
135°	785.4	786.5	787.6	788.6	789.0	788.6	788.3	787.9	787.6	787.2	786.9
137.5°	825.5	826.4	827.4	828.3	828.6	828.3	828.0	827.6	827.3	827.4	827.4
140°	851.2	851.6	851.9	852.3	852.4	852.2	852.0	851.8	851.7	852.0	852.4
142.5°	874.8	875.0	875.2	875.4	875.7	875.9	876.2	876.4	876.6	876.7	876.8
145°	909.7	910.1	910.5	910.8	910.9	910.9	910.9	910.9	910.9	911.2	911.3
147.5°	939.8	939.7	939.6	939.5	939.6	939.8	940.0	940.2	940.4	940.6	940.9
150°	958.7	958.3	958.0	957.6	957.6	958.0	958.3	958.7	959.0	959.4	959.7
152.5°	976.8	976.0	975.3	974.5	974.3	974.6	975.0	975.3	975.7	976.0	976.4
155°	1000.4	999.3	998.3	997.2	996.9	997.2	997.6	997.9	998.3	998.8	999.3
157.5°	1019.3	1018.7	1018.0	1017.3	1017.1	1017.1	1017.1	1017.2	1017.2	1017.8	1018.4
160°	1031.7	1030.6	1029.5	1028.5	1028.0	1028.2	1028.4	1028.6	1028.7	1029.4	1030.2
162.5°	1042.0	1040.8	1039.8	1038.7	1038.2	1038.5	1038.6	1038.8	1038.9	1040.0	1041.0
165°	1055.7	1054.6	1053.6	1052.5	1052.0	1052.3	1052.4	1052.6	1052.7	1053.8	1054.9
167.5°	1066.0	1064.9	1063.7	1062.6	1062.2	1062.3	1062.5	1062.7	1062.9	1064.1	1065.4
170°	1071.6	1070.3	1069.1	1067.8	1067.3	1067.5	1067.6	1067.8	1068.0	1069.4	1070.9
172.5°	1075.4	1074.1	1072.9	1071.7	1071.2	1071.5	1071.8	1072.1	1072.5	1073.7	1075.1
175°	1079.7	1078.6	1077.6	1076.5	1076.1	1076.3	1076.4	1076.7	1076.8	1078.2	1079.7
177.5°	1081.9	1081.0	1080.1	1079.3	1079.0	1079.1	1079.3	1079.3	1079.5	1080.5	1081.5
180°	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8



TEST NUMBER: P333728-927

CATALOG NUMBER: S125RDIW-S1270D1050U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3
2.5°	1569.9	1569.9	1578.3	1577.9	1583.3	1581.4	1582.3
5°	1687.7	1698.2	1707.5	1713.6	1722.8	1725.4	1724.1
7.5°	1809.7	1833.0	1844.4	1860.0	1862.8	1871.0	1870.1
10°	1885.3	1908.1	1925.4	1939.0	1945.8	1954.5	1955.0
12.5°	1944.6	1964.0	1979.3	1991.9	2000.1	2002.9	2004.5
15°	1990.8	2012.5	2030.4	2048.3	2058.8	2066.8	2071.2
17.5°	2037.6	2070.9	2102.5	2126.9	2141.4	2153.8	2153.6
20°	2073.6	2111.9	2151.4	2179.2	2207.7	2219.9	2221.8
22.5°	2112.1	2170.7	2221.6	2264.7	2302.0	2314.8	2319.7
25°	2192.2	2268.7	2347.2	2407.7	2450.9	2476.2	2479.9
27.5°	2288.9	2392.5	2475.0	2530.9	2566.7	2585.5	2589.6
30°	2357.1	2452.8	2526.9	2568.9	2585.5	2588.0	2578.7
32.5°	2387.7	2459.2	2488.8	2486.3	2453.6	2431.9	2423.6
35°	2350.2	2335.4	2263.2	2176.8	2110.7	2068.7	2057.5
37.5°	2138.8	2011.0	1878.1	1747.5	1677.9	1642.6	1581.8
40°	1930.4	1748.2	1609.9	1499.9	1421.5	1358.5	1343.7
42.5°	1695.2	1507.1	1368.8	1274.7	1212.0	1168.9	1150.1
45°	1362.2	1200.5	1086.2	1014.0	965.8	934.3	920.1
47.5°	1089.6	964.3	881.1	827.6	790.9	763.5	755.8
50°	939.8	839.8	769.4	724.4	696.6	675.6	666.9
52.5°	816.3	735.6	681.5	644.3	618.0	604.9	597.8
55°	673.7	604.0	565.1	535.4	520.5	510.1	505.1
57.5°	551.0	500.6	472.1	451.6	437.9	431.3	428.8
60°	482.3	442.8	416.8	400.8	391.5	382.9	380.4
62.5°	421.5	390.4	370.4	356.3	347.1	343.3	341.8
65°	339.6	319.2	304.4	295.8	288.4	287.2	286.5
67.5°	270.0	258.0	250.3	241.2	238.6	234.2	233.5
70°	230.9	222.9	213.7	210.6	207.5	203.2	203.7
72.5°	195.9	187.8	181.6	177.4	176.3	174.5	176.1
75°	143.2	140.8	138.3	135.2	134.0	134.0	133.4
77.5°	102.3	100.1	97.4	95.6	95.2	92.6	93.6
80°	74.1	71.0	69.8	70.4	68.5	67.9	67.9
82.5°	54.8	53.7	52.5	52.6	52.2	51.7	52.1
85°	30.3	29.6	29.6	29.0	29.0	28.4	28.4
87.5°	13.9	14.7	13.8	13.4	13.5	14.1	14.7
90°	15.5	16.4	17.1	17.7	18.1	18.7	19.3
92.5°	15.5	16.4	17.0	17.2	17.4	17.7	18.0
95°	15.5	16.4	16.8	16.8	16.8	16.8	16.8
97.5°	24.3	19.3	16.8	16.8	16.8	16.8	16.8
100°	59.8	33.3	19.6	18.9	18.2	17.5	16.8
102.5°	162.8	157.8	149.2	137.1	125.0	112.9	100.8
105°	238.8	238.8	238.7	238.5	238.3	238.1	238.0
107.5°	302.3	302.4	302.1	301.6	301.0	300.5	300.0
110°	342.9	342.4	342.2	342.4	342.5	342.7	342.9



TEST NUMBER: P333728-927

CATALOG NUMBER: S125RDIW-S1270D1050U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	383.5	382.9	382.4	382.1	381.8	381.6	381.4
115°	444.9	444.2	443.3	442.3	441.2	440.1	439.0
117.5°	504.1	503.1	502.4	502.0	501.5	501.1	500.6
120°	543.0	542.6	541.9	541.1	540.2	539.3	538.4
122.5°	579.5	579.1	578.5	577.4	576.4	575.4	574.3
125°	632.4	631.7	631.1	630.6	630.0	629.5	628.9
127.5°	681.4	681.0	680.2	678.9	677.6	676.2	674.9
130°	713.0	712.5	711.8	710.9	710.0	709.2	708.3
132.5°	743.1	743.1	742.6	741.7	740.8	739.9	739.0
135°	786.5	786.2	785.4	784.3	783.3	782.2	781.2
137.5°	827.5	827.6	827.2	826.2	825.3	824.4	823.5
140°	852.7	853.1	852.7	851.7	850.6	849.5	848.4
142.5°	876.9	876.9	876.5	875.4	874.3	873.2	872.2
145°	911.5	911.6	911.2	910.1	909.1	908.0	907.0
147.5°	941.1	941.3	940.8	939.4	938.2	936.9	935.6
150°	960.1	960.4	959.9	958.5	957.0	955.6	954.2
152.5°	976.8	977.1	976.7	975.3	974.1	972.8	971.5
155°	999.9	1000.4	1000.0	998.5	997.1	995.7	994.3
157.5°	1018.9	1019.5	1019.1	1017.6	1016.2	1014.8	1013.4
160°	1030.9	1031.6	1031.2	1029.8	1028.4	1027.0	1025.6
162.5°	1042.0	1043.0	1042.7	1041.1	1039.6	1038.0	1036.4
165°	1056.0	1057.0	1056.9	1055.4	1054.0	1052.6	1051.1
167.5°	1066.7	1068.0	1067.9	1066.2	1064.6	1063.0	1061.4
170°	1072.3	1073.7	1073.6	1072.0	1070.4	1068.8	1067.1
172.5°	1076.3	1077.6	1077.4	1075.9	1074.2	1072.6	1071.0
175°	1081.1	1082.5	1082.4	1080.8	1079.2	1077.6	1076.0
177.5°	1082.5	1083.5	1083.5	1082.3	1081.2	1080.1	1078.9
180°	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8

(END OF REPORT)