

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333733-927

Luminaire Tested: **S125RDIW-S1270D1340U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333733-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S1270D1340U927-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7584.8 lumens  
Efficiency: N/A  
Efficacy: 99.5 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 76.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333733-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333733-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	99	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49	44
2	90	83	77	72	83	77	72	67	66	62	59	55	53	50	46	44	42	38
3	82	73	66	60	76	68	62	57	58	54	50	49	46	43	41	38	36	32
4	76	65	57	51	70	60	54	48	52	47	43	44	40	37	37	34	32	28
5	69	58	50	44	64	54	47	42	47	41	37	40	36	32	33	30	28	25
6	64	52	44	38	59	49	42	36	42	37	32	36	32	28	30	27	24	22
7	59	47	39	34	55	44	37	32	38	33	29	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	25	22	20	17
9	51	39	32	27	47	37	30	25	32	27	23	28	23	20	23	20	18	16
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	22	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9715	9715	9715	9715
5°	11177	9728	8591	9728
10°	12821	9678	7581	9678
15°	13848	9579	6738	9579
20°	15270	9465	6222	9465
25°	17672	9311	5773	9311
30°	19231	9150	5480	9150
35°	16222	8964	5210	8964
40°	11328	8627	4977	8627
45°	8404	8173	4748	8173
50°	6701	7700	4554	7700
55°	5687	7113	4380	7113
60°	4914	6589	4100	6589
65°	4378	6021	3529	6021
70°	3846	5516	3218	5516
75°	3329	4776	3019	4776
80°	2525	4020	2525	4020
85°	2104	3157	2379	3157



TEST NUMBER: P333733-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	144.3	1.9
10°-20°	422.7	5.6
20°-30°	670.3	8.8
30°-40°	808.3	10.7
40°-50°	721.8	9.5
50°-60°	553.6	7.3
60°-70°	359.7	4.7
70°-80°	174.9	2.3
80°-90°	44.6	0.6
90°-100°	88.4	1.2
100°-110°	261.2	3.4
110°-120°	442.4	5.8
120°-130°	582.2	7.7
130°-140°	652.3	8.6
140°-150°	639.3	8.4
150°-160°	537.0	7.1
160°-170°	357.0	4.7
170°-180°	124.9	1.6
0°-30°	1237.3	16.3
0°-40°	2045.6	27.0
0°-60°	3320.9	43.8
0°-90°	3900.2	51.4
90°-120°	792.0	10.4
90°-150°	2665.8	35.1
90°-180°	3685.0	48.6
0°-180°	7584.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1504	1504	1504	1504	1504	
5°	1724	1501	1325	1501	1724	172
15°	2071	1433	1008	1433	2071	593
25°	2480	1307	810	1307	2480	1139
35°	2058	1137	661	1137	2058	1243
45°	920	895	520	895	920	734
55°	505	632	389	632	505	458
65°	286	394	231	394	286	285
75°	133	191	121	191	133	142
85°	28	43	32	43	28	33
90°	25	1	25	1	25	16
95°	88	67	88	67	88	90
105°	255	234	255	234	255	270
115°	447	443	447	443	447	442
125°	650	646	650	646	650	581
135°	844	841	844	841	844	651
145°	1022	1018	1022	1018	1022	638
155°	1165	1165	1165	1165	1165	536
165°	1264	1267	1264	1267	1264	356
175°	1312	1317	1312	1317	1312	125
180°	1320	1320	1320	1320	1320	



TEST NUMBER: P333733-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3
2.5°	1582.3	1581.4	1583.3	1577.9	1578.3	1569.9	1569.9	1563.5	1555.1	1548.7	1545.8
5°	1724.1	1725.4	1722.8	1713.6	1707.5	1698.2	1687.7	1669.1	1653.7	1638.9	1627.1
7.5°	1870.1	1871.0	1862.8	1860.0	1844.4	1833.0	1809.7	1784.5	1762.1	1733.8	1712.0
10°	1955.0	1954.5	1945.8	1939.0	1925.4	1908.1	1885.3	1855.6	1827.9	1797.0	1767.4
12.5°	2004.5	2002.9	2000.1	1991.9	1979.3	1964.0	1944.6	1915.4	1881.2	1847.4	1812.8
15°	2071.2	2066.8	2058.8	2048.3	2030.4	2012.5	1990.8	1964.9	1932.2	1893.9	1861.8
17.5°	2153.6	2153.8	2141.4	2126.9	2102.5	2070.9	2037.6	1995.7	1951.2	1909.1	1874.9
20°	2221.8	2219.9	2207.7	2179.2	2151.4	2111.9	2073.6	2022.4	1968.0	1913.0	1870.4
22.5°	2319.7	2314.8	2302.0	2264.7	2221.6	2170.7	2112.1	2049.5	1983.9	1921.4	1865.5
25°	2479.9	2476.2	2450.9	2407.7	2347.2	2268.7	2192.2	2106.3	2011.9	1929.8	1861.8
27.5°	2589.6	2585.5	2566.7	2530.9	2475.0	2392.5	2288.9	2174.1	2056.2	1943.2	1845.2
30°	2578.7	2588.0	2585.5	2568.9	2526.9	2452.8	2357.1	2228.0	2087.8	1955.0	1838.3
32.5°	2423.6	2431.9	2453.6	2486.3	2488.8	2459.2	2387.7	2268.5	2123.4	1972.4	1832.9
35°	2057.5	2068.7	2110.7	2176.8	2263.2	2335.4	2350.2	2286.1	2155.8	1993.4	1824.8
37.5°	1581.8	1642.6	1677.9	1747.5	1878.1	2011.0	2138.8	2185.9	2130.4	1984.7	1811.6
40°	1343.7	1358.5	1421.5	1499.9	1609.9	1748.2	1930.4	2061.9	2066.2	1964.9	1790.8
42.5°	1150.1	1168.9	1212.0	1274.7	1368.8	1507.1	1695.2	1868.8	1949.2	1910.6	1763.6
45°	920.1	934.3	965.8	1014.0	1086.2	1200.5	1362.2	1562.9	1722.3	1784.6	1690.8
47.5°	755.8	763.5	790.9	827.6	881.1	964.3	1089.6	1263.8	1454.8	1588.9	1575.7
50°	666.9	675.6	696.6	724.4	769.4	839.8	939.8	1085.0	1282.0	1445.6	1478.4
52.5°	597.8	604.9	618.0	644.3	681.5	735.6	816.3	947.6	1124.9	1298.9	1374.6
55°	505.1	510.1	520.5	535.4	565.1	604.0	673.7	764.5	907.8	1083.2	1194.3
57.5°	428.8	431.3	437.9	451.6	472.1	500.6	551.0	627.9	730.6	888.6	1011.2
60°	380.4	382.9	391.5	400.8	416.8	442.8	482.3	536.0	634.8	765.1	889.2
62.5°	341.8	343.3	347.1	356.3	370.4	390.4	421.5	465.3	543.9	658.4	775.6
65°	286.5	287.2	288.4	295.8	304.4	319.2	339.6	370.5	429.8	516.3	620.0
67.5°	233.5	234.2	238.6	241.2	250.3	258.0	270.0	293.6	335.3	393.6	474.3
70°	203.7	203.2	207.5	210.6	213.7	222.9	230.9	250.1	276.0	320.5	387.8
72.5°	176.1	174.5	176.3	177.4	181.6	187.8	195.9	207.6	227.6	258.3	309.7
75°	133.4	134.0	134.0	135.2	138.3	140.8	143.2	149.4	160.6	180.9	208.7
77.5°	93.6	92.6	95.2	95.6	97.4	100.1	102.3	104.7	109.3	117.7	132.1
80°	67.9	67.9	68.5	70.4	69.8	71.0	74.1	76.6	82.1	87.1	92.0
82.5°	52.1	51.7	52.2	52.6	52.5	53.7	54.8	55.3	57.4	59.9	63.4
85°	28.4	28.4	29.0	29.0	29.6	29.6	30.3	30.3	30.3	30.9	31.5
87.5°	15.8	15.1	14.6	14.4	14.7	15.5	14.8	14.1	13.9	13.6	13.9
90°	24.6	24.0	23.3	22.6	21.9	21.0	19.9	18.7	17.6	16.5	14.8
92.5°	48.5	48.0	47.5	47.0	46.5	45.5	44.0	42.5	41.0	39.5	37.5
95°	88.4	87.9	87.5	87.0	86.5	85.6	83.9	82.3	80.7	79.1	76.8
97.5°	134.0	133.7	133.5	133.2	132.9	132.0	130.5	129.0	127.5	126.0	122.9
100°	168.5	168.1	167.6	167.2	166.7	165.4	163.3	161.4	159.3	157.2	154.2
102.5°	203.0	202.4	201.8	201.1	200.5	199.1	196.8	194.6	192.3	190.1	188.6
105°	254.8	254.1	253.5	252.8	252.1	251.0	249.7	248.3	247.0	245.6	244.2
107.5°	307.8	307.9	307.9	308.0	308.1	307.8	307.0	306.3	305.7	305.0	304.0
110°	347.3	347.5	347.8	348.0	348.2	348.0	347.3	346.7	345.9	345.2	344.6



TEST NUMBER: P333733-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	386.0	386.3	386.8	387.2	387.6	387.6	387.3	387.0	386.7	386.3	385.5
115°	447.0	447.3	447.4	447.7	447.9	448.1	448.4	448.6	448.9	449.1	448.6
117.5°	506.6	507.6	508.4	509.4	510.2	510.6	510.4	510.2	510.1	509.9	509.5
120°	547.7	548.6	549.5	550.4	551.4	551.8	551.8	551.8	551.8	551.8	551.6
122.5°	588.8	589.5	590.3	591.0	591.8	592.2	592.4	592.6	592.7	592.9	592.3
125°	650.5	650.7	650.9	651.2	651.4	651.7	652.2	652.6	653.1	653.6	653.3
127.5°	709.6	710.1	710.6	711.1	711.5	711.9	712.0	712.3	712.5	712.7	712.5
130°	749.1	749.6	750.0	750.5	750.9	751.3	751.5	751.7	751.9	752.2	751.7
132.5°	786.1	786.7	787.3	788.1	788.7	789.1	789.3	789.6	789.8	790.0	790.1
135°	843.7	844.5	845.5	846.4	847.3	847.8	847.8	847.8	847.8	847.8	847.6
137.5°	900.0	901.1	902.2	903.4	904.5	905.0	904.7	904.4	904.1	903.9	903.4
140°	936.1	937.3	938.4	939.5	940.7	941.0	940.6	940.2	939.7	939.2	938.5
142.5°	970.7	971.8	973.0	974.1	975.3	975.7	975.4	975.1	974.9	974.5	973.7
145°	1022.5	1023.1	1023.8	1024.5	1025.2	1025.6	1025.6	1025.6	1025.6	1025.6	1024.8
147.5°	1066.7	1068.2	1069.8	1071.3	1072.9	1073.3	1072.8	1072.2	1071.7	1071.2	1070.6
150°	1099.5	1099.9	1100.4	1100.9	1101.4	1101.6	1101.6	1101.6	1101.6	1101.6	1100.7
152.5°	1126.6	1127.4	1128.3	1129.1	1130.0	1130.0	1129.5	1128.9	1128.5	1127.9	1127.5
155°	1165.3	1166.4	1167.6	1168.7	1169.8	1170.0	1169.0	1168.2	1167.2	1166.3	1166.1
157.5°	1197.5	1199.0	1200.6	1202.1	1203.6	1203.9	1202.9	1202.1	1201.1	1200.2	1200.0
160°	1219.7	1220.9	1222.0	1223.2	1224.3	1224.4	1223.5	1222.6	1221.7	1220.8	1220.5
162.5°	1238.7	1240.0	1241.3	1242.6	1244.0	1244.0	1242.9	1241.9	1240.8	1239.7	1239.6
165°	1263.9	1265.3	1266.7	1268.0	1269.4	1269.6	1268.8	1267.8	1266.9	1266.0	1265.7
167.5°	1284.0	1285.5	1286.9	1288.3	1289.8	1289.8	1288.4	1287.1	1285.6	1284.3	1284.3
170°	1294.7	1296.3	1298.0	1299.6	1301.2	1301.2	1299.9	1298.5	1297.2	1295.8	1295.8
172.5°	1303.8	1305.2	1306.6	1308.1	1309.5	1309.5	1308.1	1306.8	1305.4	1304.0	1304.0
175°	1312.2	1313.8	1315.4	1317.0	1318.6	1318.7	1317.4	1316.0	1314.6	1313.3	1313.3
177.5°	1317.2	1318.4	1319.7	1321.0	1322.3	1322.4	1321.3	1320.2	1319.1	1318.0	1318.2
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5



TEST NUMBER: P333733-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3
2.5°	1545.8	1542.3	1535.9	1529.9	1522.6	1516.2	1511.6	1506.3	1499.4	1491.0	1484.0
5°	1614.2	1600.6	1582.7	1567.3	1547.5	1532.1	1516.0	1500.6	1485.1	1465.4	1448.1
7.5°	1690.0	1662.0	1634.7	1600.4	1569.2	1541.4	1514.7	1487.7	1461.3	1433.2	1406.2
10°	1736.5	1702.5	1664.9	1621.6	1582.1	1544.4	1509.8	1475.8	1440.0	1408.6	1374.6
12.5°	1780.0	1736.1	1693.0	1638.4	1590.9	1544.9	1500.9	1458.6	1420.3	1379.4	1343.0
15°	1819.2	1776.0	1727.8	1661.1	1595.1	1539.4	1487.6	1432.7	1385.1	1339.4	1298.6
17.5°	1834.4	1789.1	1733.1	1669.0	1596.8	1526.9	1460.1	1399.8	1343.9	1290.6	1244.8
20°	1828.4	1784.6	1727.2	1666.0	1588.9	1516.0	1443.8	1377.1	1314.7	1258.5	1209.7
22.5°	1814.2	1768.8	1713.3	1648.8	1575.5	1498.3	1421.0	1349.9	1284.5	1226.4	1173.1
25°	1792.6	1730.9	1674.1	1611.1	1541.3	1464.7	1385.1	1306.6	1236.9	1177.6	1119.6
27.5°	1770.3	1693.2	1621.0	1558.4	1484.6	1416.3	1339.5	1259.1	1185.7	1125.4	1065.8
30°	1750.0	1663.6	1583.9	1512.9	1443.1	1378.3	1305.4	1227.0	1151.7	1089.3	1028.8
32.5°	1724.8	1632.9	1545.4	1463.5	1396.2	1331.9	1265.9	1191.0	1117.6	1053.2	991.7
35°	1693.2	1575.9	1480.8	1393.8	1319.0	1256.6	1197.4	1136.9	1063.3	996.6	936.8
37.5°	1651.7	1518.6	1408.6	1313.7	1234.9	1172.3	1125.5	1070.2	1003.1	939.2	883.7
40°	1626.5	1477.1	1356.7	1262.8	1180.0	1114.0	1070.2	1023.3	962.1	902.2	846.6
42.5°	1592.9	1439.1	1304.3	1206.5	1123.2	1059.6	1015.3	974.3	923.1	866.6	807.1
45°	1527.1	1365.3	1223.9	1119.0	1035.0	972.6	931.2	894.8	855.9	804.0	752.1
47.5°	1441.4	1288.4	1140.4	1025.8	943.6	885.7	845.5	816.7	788.9	744.8	694.4
50°	1372.8	1225.2	1080.6	969.5	881.8	826.9	789.2	766.4	741.0	700.8	658.9
52.5°	1291.7	1159.9	1018.4	904.8	822.0	770.6	734.4	711.5	690.6	657.9	617.9
55°	1164.0	1048.5	918.9	815.7	739.8	687.9	653.3	631.7	619.4	591.6	560.1
57.5°	1016.7	933.9	819.6	720.2	653.0	601.7	576.4	558.0	544.1	524.4	502.2
60°	913.9	855.9	753.4	658.9	597.1	548.3	525.5	510.1	497.1	480.5	463.1
62.5°	809.7	767.5	678.3	597.1	540.3	499.5	478.1	464.1	449.2	437.9	421.1
65°	670.0	632.3	570.6	507.0	454.5	421.8	406.3	394.0	384.7	372.3	360.6
67.5°	521.2	505.9	463.3	419.4	381.8	352.6	339.3	330.7	319.5	312.1	304.0
70°	429.8	422.4	392.1	363.1	327.9	308.2	295.8	292.1	278.5	271.1	265.5
72.5°	348.8	345.3	327.9	307.8	283.0	265.6	254.3	250.1	241.5	235.5	232.0
75°	239.0	240.2	237.1	224.2	214.9	203.7	193.9	191.4	185.3	180.3	177.2
77.5°	151.1	157.5	157.7	157.1	153.4	146.6	142.5	140.7	134.6	132.8	132.1
80°	103.8	110.5	116.7	116.1	114.9	113.0	110.0	108.1	105.0	103.1	101.9
82.5°	69.2	75.5	80.6	84.0	83.7	81.9	79.8	78.9	78.3	76.9	76.7
85°	32.7	34.0	35.8	40.2	43.3	43.8	43.3	42.6	40.7	41.4	42.0
87.5°	14.0	13.7	13.9	13.5	12.7	14.7	15.9	16.0	15.4	14.7	14.2
90°	13.2	11.6	10.1	8.3	6.5	4.7	2.9	1.0	2.9	4.7	6.5
92.5°	35.6	33.6	31.6	29.9	28.7	27.4	26.1	24.9	26.1	27.4	28.7
95°	74.5	72.2	70.0	68.6	68.1	67.7	67.3	66.8	67.3	67.7	68.1
97.5°	119.7	116.5	113.4	111.7	111.5	111.4	111.1	111.0	111.1	111.4	111.5
100°	151.3	148.3	145.4	143.9	143.9	143.9	143.9	143.9	143.9	143.9	143.9
102.5°	187.1	185.6	184.1	182.8	182.0	181.0	180.1	179.2	180.1	181.0	182.0
105°	242.9	241.5	240.1	238.8	237.7	236.5	235.4	234.3	235.4	236.5	237.7
107.5°	302.9	301.8	300.8	299.7	298.6	297.4	296.3	295.1	296.3	297.4	298.6
110°	343.9	343.3	342.5	341.6	340.5	339.4	338.2	337.1	338.2	339.4	340.5





TEST NUMBER: P333733-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	384.6	383.7	382.9	382.1	381.6	381.0	380.4	379.8	380.4	381.0	381.6
115°	448.1	447.7	447.3	446.6	445.6	444.7	443.8	442.9	443.8	444.7	445.6
117.5°	509.1	508.7	508.3	507.9	507.4	507.0	506.6	506.2	506.6	507.0	507.4
120°	551.4	551.1	550.9	550.2	549.1	548.0	546.8	545.7	546.8	548.0	549.1
122.5°	591.8	591.1	590.6	590.0	589.6	589.2	588.8	588.4	588.8	589.2	589.6
125°	653.1	652.8	652.6	651.8	650.5	649.1	647.7	646.3	647.7	649.1	650.5
127.5°	712.2	711.9	711.6	711.1	710.3	709.6	708.8	708.0	708.8	709.6	710.3
130°	751.3	750.8	750.4	749.6	748.5	747.3	746.2	745.0	746.2	747.3	748.5
132.5°	790.2	790.3	790.4	789.5	787.6	785.8	783.9	782.0	783.9	785.8	787.6
135°	847.3	847.1	846.8	846.1	844.7	843.3	841.9	840.6	841.9	843.3	844.7
137.5°	902.9	902.4	901.8	900.9	899.6	898.3	897.0	895.6	897.0	898.3	899.6
140°	937.9	937.2	936.4	935.6	934.5	933.3	932.2	931.0	932.2	933.3	934.5
142.5°	972.8	971.9	971.1	970.2	969.2	968.3	967.3	966.4	967.3	968.3	969.2
145°	1024.1	1023.5	1022.8	1022.0	1021.0	1020.2	1019.2	1018.4	1019.2	1020.2	1021.0
147.5°	1070.1	1069.5	1069.0	1068.4	1067.9	1067.5	1066.9	1066.4	1066.9	1067.5	1067.9
150°	1099.8	1098.8	1097.9	1097.6	1097.8	1098.0	1098.3	1098.5	1098.3	1098.0	1097.8
152.5°	1127.1	1126.8	1126.4	1126.1	1125.8	1125.5	1125.1	1124.8	1125.1	1125.5	1125.8
155°	1165.9	1165.6	1165.4	1165.3	1165.3	1165.3	1165.3	1165.3	1165.3	1165.3	1165.3
157.5°	1199.8	1199.5	1199.3	1199.4	1199.9	1200.5	1200.9	1201.4	1200.9	1200.5	1199.9
160°	1220.4	1220.1	1219.9	1220.1	1220.8	1221.5	1222.2	1222.8	1222.2	1221.5	1220.8
162.5°	1239.6	1239.5	1239.5	1239.8	1240.2	1240.7	1241.3	1241.7	1241.3	1240.7	1240.2
165°	1265.5	1265.3	1265.1	1265.2	1265.7	1266.1	1266.5	1267.0	1266.5	1266.1	1265.7
167.5°	1284.3	1284.3	1284.3	1284.8	1285.6	1286.6	1287.5	1288.4	1287.5	1286.6	1285.6
170°	1295.8	1295.8	1295.8	1296.2	1297.2	1298.1	1299.0	1299.9	1299.0	1298.1	1297.2
172.5°	1304.0	1304.0	1304.0	1304.5	1305.4	1306.3	1307.2	1308.1	1307.2	1306.3	1305.4
175°	1313.3	1313.3	1313.3	1313.8	1314.6	1315.6	1316.4	1317.4	1316.4	1315.6	1314.6
177.5°	1318.3	1318.5	1318.7	1319.1	1319.9	1320.6	1321.4	1322.1	1321.4	1320.6	1319.9
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5



TEST NUMBER: P333733-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3
2.5°	1479.1	1472.2	1467.2	1457.3	1450.4	1447.5	1442.0	1440.5	1446.0	1442.0	1441.5
5°	1435.1	1417.2	1403.0	1388.8	1373.3	1363.5	1348.7	1346.2	1342.5	1336.9	1335.7
7.5°	1382.4	1359.1	1340.8	1317.3	1296.9	1280.5	1261.9	1253.2	1248.4	1241.2	1231.6
10°	1346.8	1319.0	1294.3	1270.8	1245.5	1225.2	1206.7	1192.4	1183.1	1174.5	1170.8
12.5°	1311.7	1283.4	1251.8	1223.4	1195.2	1172.3	1151.8	1142.6	1132.3	1122.1	1113.5
15°	1257.3	1219.6	1185.0	1152.3	1128.2	1103.5	1083.7	1070.2	1054.7	1050.4	1033.7
17.5°	1199.4	1162.5	1122.0	1087.6	1059.6	1032.5	1010.7	995.3	983.7	967.8	960.1
20°	1163.4	1119.6	1080.1	1048.5	1017.6	985.6	963.3	950.4	939.2	926.3	920.1
22.5°	1124.9	1082.0	1041.5	1004.6	973.2	941.6	925.7	912.4	899.7	887.7	879.6
25°	1068.3	1025.1	982.5	944.2	911.5	888.6	870.1	854.6	847.9	836.1	827.4
27.5°	1012.3	966.4	922.2	884.0	858.3	835.8	820.5	808.3	796.1	785.8	778.3
30°	976.3	929.4	881.2	851.0	823.8	802.2	785.4	773.7	764.5	755.2	749.6
32.5°	940.2	891.8	849.1	816.3	790.7	772.0	754.9	743.6	733.9	723.6	717.1
35°	882.4	833.1	798.4	766.4	741.0	723.7	712.0	695.9	687.9	680.5	673.7
37.5°	828.7	782.8	745.4	717.2	695.2	678.0	662.8	654.2	644.3	637.6	632.0
40°	789.2	747.2	713.2	683.6	667.6	648.4	634.2	623.1	615.7	607.0	600.9
42.5°	753.6	714.6	681.6	655.0	634.9	618.8	605.1	593.9	584.6	578.4	573.1
45°	703.4	664.5	632.3	607.6	589.1	573.7	559.4	553.9	541.5	534.2	531.7
47.5°	651.3	616.6	585.5	562.8	543.8	529.2	515.9	504.5	497.7	490.4	486.5
50°	616.3	583.0	553.9	531.7	513.2	497.1	484.7	477.4	468.1	461.3	456.4
52.5°	581.2	550.3	521.3	500.0	484.0	467.9	454.2	446.7	437.9	433.6	430.2
55°	531.1	498.4	473.6	452.7	435.9	421.1	408.2	400.8	395.2	390.9	389.7
57.5°	474.3	448.3	425.3	406.5	389.1	375.2	363.8	356.8	351.9	351.3	347.5
60°	437.2	413.8	392.8	372.3	357.5	344.6	334.7	326.7	321.7	321.1	319.9
62.5°	400.1	377.6	358.1	340.2	326.9	314.4	305.1	296.0	293.1	290.0	287.2
65°	345.2	324.8	308.8	294.5	280.4	269.8	260.6	255.0	248.3	244.5	237.7
67.5°	291.2	275.4	260.0	248.0	236.9	226.9	219.2	211.0	206.4	203.4	198.4
70°	255.6	243.3	227.8	214.9	206.3	198.2	192.0	182.8	179.7	177.2	174.8
72.5°	222.0	211.2	198.2	187.7	179.1	171.5	164.4	160.0	157.0	154.5	153.0
75°	174.8	164.3	153.1	145.8	139.6	133.4	129.7	126.6	125.3	124.8	122.2
77.5°	128.3	122.8	113.8	108.0	103.9	101.4	98.1	96.5	96.3	93.6	92.8
80°	98.2	95.1	87.7	85.2	82.1	79.7	77.8	74.7	71.6	70.4	68.5
82.5°	73.0	69.9	66.9	63.0	60.4	58.9	57.0	55.9	56.3	54.6	53.7
85°	38.9	35.8	34.6	34.0	32.7	34.0	33.4	32.7	32.1	31.5	32.1
87.5°	14.0	14.3	14.2	15.5	14.3	15.1	15.4	15.1	15.4	15.5	15.3
90°	8.3	10.1	11.6	13.2	14.8	16.5	17.6	18.7	19.9	21.0	21.9
92.5°	29.9	31.6	33.6	35.6	37.5	39.5	41.0	42.5	44.0	45.5	46.5
95°	68.6	70.0	72.2	74.5	76.8	79.1	80.7	82.3	83.9	85.6	86.5
97.5°	111.7	113.4	116.5	119.7	122.9	126.0	127.5	129.0	130.5	132.0	132.9
100°	143.9	145.4	148.3	151.3	154.2	157.2	159.3	161.4	163.3	165.4	166.7
102.5°	182.8	184.1	185.6	187.1	188.6	190.1	192.3	194.6	196.8	199.1	200.5
105°	238.8	240.1	241.5	242.9	244.2	245.6	247.0	248.3	249.7	251.0	252.1
107.5°	299.7	300.8	301.8	302.9	304.0	305.0	305.7	306.3	307.0	307.8	308.1
110°	341.6	342.5	343.3	343.9	344.6	345.2	345.9	346.7	347.3	348.0	348.2



TEST NUMBER: P333733-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	382.1	382.9	383.7	384.6	385.5	386.3	386.7	387.0	387.3	387.6	387.6
115°	446.6	447.3	447.7	448.1	448.6	449.1	448.9	448.6	448.4	448.1	447.9
117.5°	507.9	508.3	508.7	509.1	509.5	509.9	510.1	510.2	510.4	510.6	510.2
120°	550.2	550.9	551.1	551.4	551.6	551.8	551.8	551.8	551.8	551.8	551.4
122.5°	590.0	590.6	591.1	591.8	592.3	592.9	592.7	592.6	592.4	592.2	591.8
125°	651.8	652.6	652.8	653.1	653.3	653.6	653.1	652.6	652.2	651.7	651.4
127.5°	711.1	711.6	711.9	712.2	712.5	712.7	712.5	712.3	712.0	711.9	711.5
130°	749.6	750.4	750.8	751.3	751.7	752.2	751.9	751.7	751.5	751.3	750.9
132.5°	789.5	790.4	790.3	790.2	790.1	790.0	789.8	789.6	789.3	789.1	788.7
135°	846.1	846.8	847.1	847.3	847.6	847.8	847.8	847.8	847.8	847.8	847.3
137.5°	900.9	901.8	902.4	902.9	903.4	903.9	904.1	904.4	904.7	905.0	904.5
140°	935.6	936.4	937.2	937.9	938.5	939.2	939.7	940.2	940.6	941.0	940.7
142.5°	970.2	971.1	971.9	972.8	973.7	974.5	974.9	975.1	975.4	975.7	975.3
145°	1022.0	1022.8	1023.5	1024.1	1024.8	1025.6	1025.6	1025.6	1025.6	1025.6	1025.2
147.5°	1068.4	1069.0	1069.5	1070.1	1070.6	1071.2	1071.7	1072.2	1072.8	1073.3	1072.9
150°	1097.6	1097.9	1098.8	1099.8	1100.7	1101.6	1101.6	1101.6	1101.6	1101.6	1101.4
152.5°	1126.1	1126.4	1126.8	1127.1	1127.5	1127.9	1128.5	1128.9	1129.5	1130.0	1130.0
155°	1165.3	1165.4	1165.6	1165.9	1166.1	1166.3	1167.2	1168.2	1169.0	1170.0	1169.8
157.5°	1199.4	1199.3	1199.5	1199.8	1200.0	1200.2	1201.1	1202.1	1202.9	1203.9	1203.6
160°	1220.1	1219.9	1220.1	1220.4	1220.5	1220.8	1221.7	1222.6	1223.5	1224.4	1224.3
162.5°	1239.8	1239.5	1239.5	1239.6	1239.6	1239.7	1240.8	1241.9	1242.9	1244.0	1244.0
165°	1265.2	1265.1	1265.3	1265.5	1265.7	1266.0	1266.9	1267.8	1268.8	1269.6	1269.4
167.5°	1284.8	1284.3	1284.3	1284.3	1284.3	1284.3	1285.6	1287.1	1288.4	1289.8	1289.8
170°	1296.2	1295.8	1295.8	1295.8	1295.8	1295.8	1297.2	1298.5	1299.9	1301.2	1301.2
172.5°	1304.5	1304.0	1304.0	1304.0	1304.0	1304.0	1305.4	1306.8	1308.1	1309.5	1309.5
175°	1313.8	1313.3	1313.3	1313.3	1313.3	1313.3	1314.6	1316.0	1317.4	1318.7	1318.6
177.5°	1319.1	1318.7	1318.5	1318.3	1318.2	1318.0	1319.1	1320.2	1321.3	1322.4	1322.3
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5



TEST NUMBER: P333733-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3
2.5°	1441.1	1435.6	1434.1	1436.1	1434.1	1435.6	1441.1	1441.5	1442.0	1446.0	1440.5
5°	1329.5	1323.3	1326.4	1325.2	1326.4	1323.3	1329.5	1335.7	1336.9	1342.5	1346.2
7.5°	1231.4	1223.8	1215.6	1218.2	1215.6	1223.8	1231.4	1231.6	1241.2	1248.4	1253.2
10°	1162.8	1156.6	1152.9	1156.0	1152.9	1156.6	1162.8	1170.8	1174.5	1183.1	1192.4
12.5°	1105.0	1101.3	1098.0	1096.7	1098.0	1101.3	1105.0	1113.5	1122.1	1132.3	1142.6
15°	1026.3	1018.9	1015.8	1007.8	1015.8	1018.9	1026.3	1033.7	1050.4	1054.7	1070.2
17.5°	953.8	951.3	943.3	939.8	943.3	951.3	953.8	960.1	967.8	983.7	995.3
20°	910.9	908.4	900.3	905.3	900.3	908.4	910.9	920.1	926.3	939.2	950.4
22.5°	875.3	869.8	867.2	865.8	867.2	869.8	875.3	879.6	887.7	899.7	912.4
25°	825.0	817.0	813.9	810.2	813.9	817.0	825.0	827.4	836.1	847.9	854.6
27.5°	774.8	770.6	766.4	765.5	766.4	770.6	774.8	778.3	785.8	796.1	808.3
30°	742.3	737.9	734.8	734.8	734.8	737.9	742.3	749.6	755.2	764.5	773.7
32.5°	713.1	709.8	706.7	706.2	706.7	709.8	713.1	717.1	723.6	733.9	743.6
35°	670.7	665.7	664.5	660.8	664.5	665.7	670.7	673.7	680.5	687.9	695.9
37.5°	626.5	622.4	622.3	621.9	622.3	622.4	626.5	632.0	637.6	644.3	654.2
40°	598.3	595.2	594.7	590.3	594.7	595.2	598.3	600.9	607.0	615.7	623.1
42.5°	568.2	566.6	564.5	562.7	564.5	566.6	568.2	573.1	578.4	584.6	593.9
45°	527.4	523.0	523.0	519.9	523.0	523.0	527.4	531.7	534.2	541.5	553.9
47.5°	485.1	481.8	482.1	479.0	482.1	481.8	485.1	486.5	490.4	497.7	504.5
50°	456.9	455.1	454.5	453.3	454.5	455.1	456.9	456.4	461.3	468.1	477.4
52.5°	428.8	427.9	430.3	427.5	430.3	427.9	428.8	430.2	433.6	437.9	446.7
55°	390.9	389.0	392.8	389.0	392.8	389.0	390.9	389.7	390.9	395.2	400.8
57.5°	347.3	345.5	348.9	347.1	348.9	345.5	347.3	347.5	351.3	351.9	356.8
60°	318.6	315.0	316.8	317.4	316.8	315.0	318.6	319.9	321.1	321.7	326.7
62.5°	284.6	282.3	283.7	280.8	283.7	282.3	284.6	287.2	290.0	293.1	296.0
65°	236.5	234.6	232.2	230.9	232.2	234.6	236.5	237.7	244.5	248.3	255.0
67.5°	198.7	194.2	194.2	195.1	194.2	194.2	198.7	198.4	203.4	206.4	211.0
70°	171.0	171.0	170.4	170.4	170.4	171.0	171.0	174.8	177.2	179.7	182.8
72.5°	151.8	151.3	150.2	149.7	150.2	151.3	151.8	153.0	154.5	157.0	160.0
75°	122.2	122.9	121.7	121.0	121.7	122.9	122.2	122.2	124.8	125.3	126.6
77.5°	90.3	87.7	89.0	87.7	89.0	87.7	90.3	92.8	93.6	96.3	96.5
80°	68.5	67.9	69.8	67.9	69.8	67.9	68.5	68.5	70.4	71.6	74.7
82.5°	54.2	53.6	54.5	53.1	54.5	53.6	54.2	53.7	54.6	56.3	55.9
85°	32.7	32.1	31.5	32.1	31.5	32.1	32.7	32.1	31.5	32.1	32.7
87.5°	15.9	15.5	15.7	15.8	15.7	15.5	15.9	15.3	15.5	15.4	15.1
90°	22.6	23.3	24.0	24.6	24.0	23.3	22.6	21.9	21.0	19.9	18.7
92.5°	47.0	47.5	48.0	48.5	48.0	47.5	47.0	46.5	45.5	44.0	42.5
95°	87.0	87.5	87.9	88.4	87.9	87.5	87.0	86.5	85.6	83.9	82.3
97.5°	133.2	133.5	133.7	134.0	133.7	133.5	133.2	132.9	132.0	130.5	129.0
100°	167.2	167.6	168.1	168.5	168.1	167.6	167.2	166.7	165.4	163.3	161.4
102.5°	201.1	201.8	202.4	203.0	202.4	201.8	201.1	200.5	199.1	196.8	194.6
105°	252.8	253.5	254.1	254.8	254.1	253.5	252.8	252.1	251.0	249.7	248.3
107.5°	308.0	307.9	307.9	307.8	307.9	307.9	308.0	308.1	307.8	307.0	306.3
110°	348.0	347.8	347.5	347.3	347.5	347.8	348.0	348.2	348.0	347.3	346.7



TEST NUMBER: P333733-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	387.2	386.8	386.3	386.0	386.3	386.8	387.2	387.6	387.6	387.3	387.0
115°	447.7	447.4	447.3	447.0	447.3	447.4	447.7	447.9	448.1	448.4	448.6
117.5°	509.4	508.4	507.6	506.6	507.6	508.4	509.4	510.2	510.6	510.4	510.2
120°	550.4	549.5	548.6	547.7	548.6	549.5	550.4	551.4	551.8	551.8	551.8
122.5°	591.0	590.3	589.5	588.8	589.5	590.3	591.0	591.8	592.2	592.4	592.6
125°	651.2	650.9	650.7	650.5	650.7	650.9	651.2	651.4	651.7	652.2	652.6
127.5°	711.1	710.6	710.1	709.6	710.1	710.6	711.1	711.5	711.9	712.0	712.3
130°	750.5	750.0	749.6	749.1	749.6	750.0	750.5	750.9	751.3	751.5	751.7
132.5°	788.1	787.3	786.7	786.1	786.7	787.3	788.1	788.7	789.1	789.3	789.6
135°	846.4	845.5	844.5	843.7	844.5	845.5	846.4	847.3	847.8	847.8	847.8
137.5°	903.4	902.2	901.1	900.0	901.1	902.2	903.4	904.5	905.0	904.7	904.4
140°	939.5	938.4	937.3	936.1	937.3	938.4	939.5	940.7	941.0	940.6	940.2
142.5°	974.1	973.0	971.8	970.7	971.8	973.0	974.1	975.3	975.7	975.4	975.1
145°	1024.5	1023.8	1023.1	1022.5	1023.1	1023.8	1024.5	1025.2	1025.6	1025.6	1025.6
147.5°	1071.3	1069.8	1068.2	1066.7	1068.2	1069.8	1071.3	1072.9	1073.3	1072.8	1072.2
150°	1100.9	1100.4	1099.9	1099.5	1099.9	1100.4	1100.9	1101.4	1101.6	1101.6	1101.6
152.5°	1129.1	1128.3	1127.4	1126.6	1127.4	1128.3	1129.1	1130.0	1130.0	1129.5	1128.9
155°	1168.7	1167.6	1166.4	1165.3	1166.4	1167.6	1168.7	1169.8	1170.0	1169.0	1168.2
157.5°	1202.1	1200.6	1199.0	1197.5	1199.0	1200.6	1202.1	1203.6	1203.9	1202.9	1202.1
160°	1223.2	1222.0	1220.9	1219.7	1220.9	1222.0	1223.2	1224.3	1224.4	1223.5	1222.6
162.5°	1242.6	1241.3	1240.0	1238.7	1240.0	1241.3	1242.6	1244.0	1244.0	1242.9	1241.9
165°	1268.0	1266.7	1265.3	1263.9	1265.3	1266.7	1268.0	1269.4	1269.6	1268.8	1267.8
167.5°	1288.3	1286.9	1285.5	1284.0	1285.5	1286.9	1288.3	1289.8	1289.8	1288.4	1287.1
170°	1299.6	1298.0	1296.3	1294.7	1296.3	1298.0	1299.6	1301.2	1301.2	1299.9	1298.5
172.5°	1308.1	1306.6	1305.2	1303.8	1305.2	1306.6	1308.1	1309.5	1309.5	1308.1	1306.8
175°	1317.0	1315.4	1313.8	1312.2	1313.8	1315.4	1317.0	1318.6	1318.7	1317.4	1316.0
177.5°	1321.0	1319.7	1318.4	1317.2	1318.4	1319.7	1321.0	1322.3	1322.4	1321.3	1320.2
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5



TEST NUMBER: P333733-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3
2.5°	1442.0	1447.5	1450.4	1457.3	1467.2	1472.2	1479.1	1484.0	1491.0	1499.4	1506.3
5°	1348.7	1363.5	1373.3	1388.8	1403.0	1417.2	1435.1	1448.1	1465.4	1485.1	1500.6
7.5°	1261.9	1280.5	1296.9	1317.3	1340.8	1359.1	1382.4	1406.2	1433.2	1461.3	1487.7
10°	1206.7	1225.2	1245.5	1270.8	1294.3	1319.0	1346.8	1374.6	1408.6	1440.0	1475.8
12.5°	1151.8	1172.3	1195.2	1223.4	1251.8	1283.4	1311.7	1343.0	1379.4	1420.3	1458.6
15°	1083.7	1103.5	1128.2	1152.3	1185.0	1219.6	1257.3	1298.6	1339.4	1385.1	1432.7
17.5°	1010.7	1032.5	1059.6	1087.6	1122.0	1162.5	1199.4	1244.8	1290.6	1343.9	1399.8
20°	963.3	985.6	1017.6	1048.5	1080.1	1119.6	1163.4	1209.7	1258.5	1314.7	1377.1
22.5°	925.7	941.6	973.2	1004.6	1041.5	1082.0	1124.9	1173.1	1226.4	1284.5	1349.9
25°	870.1	888.6	911.5	944.2	982.5	1025.1	1068.3	1119.6	1177.6	1236.9	1306.6
27.5°	820.5	835.8	858.3	884.0	922.2	966.4	1012.3	1065.8	1125.4	1185.7	1259.1
30°	785.4	802.2	823.8	851.0	881.2	929.4	976.3	1028.8	1089.3	1151.7	1227.0
32.5°	754.9	772.0	790.7	816.3	849.1	891.8	940.2	991.7	1053.2	1117.6	1191.0
35°	712.0	723.7	741.0	766.4	798.4	833.1	882.4	936.8	996.6	1063.3	1136.9
37.5°	662.8	678.0	695.2	717.2	745.4	782.8	828.7	883.7	939.2	1003.1	1070.2
40°	634.2	648.4	667.6	683.6	713.2	747.2	789.2	846.6	902.2	962.1	1023.3
42.5°	605.1	618.8	634.9	655.0	681.6	714.6	753.6	807.1	866.6	923.1	974.3
45°	559.4	573.7	589.1	607.6	632.3	664.5	703.4	752.1	804.0	855.9	894.8
47.5°	515.9	529.2	543.8	562.8	585.5	616.6	651.3	694.4	744.8	788.9	816.7
50°	484.7	497.1	513.2	531.7	553.9	583.0	616.3	658.9	700.8	741.0	766.4
52.5°	454.2	467.9	484.0	500.0	521.3	550.3	581.2	617.9	657.9	690.6	711.5
55°	408.2	421.1	435.9	452.7	473.6	498.4	531.1	560.1	591.6	619.4	631.7
57.5°	363.8	375.2	389.1	406.5	425.3	448.3	474.3	502.2	524.4	544.1	558.0
60°	334.7	344.6	357.5	372.3	392.8	413.8	437.2	463.1	480.5	497.1	510.1
62.5°	305.1	314.4	326.9	340.2	358.1	377.6	400.1	421.1	437.9	449.2	464.1
65°	260.6	269.8	280.4	294.5	308.8	324.8	345.2	360.6	372.3	384.7	394.0
67.5°	219.2	226.9	236.9	248.0	260.0	275.4	291.2	304.0	312.1	319.5	330.7
70°	192.0	198.2	206.3	214.9	227.8	243.3	255.6	265.5	271.1	278.5	292.1
72.5°	164.4	171.5	179.1	187.7	198.2	211.2	222.0	232.0	235.5	241.5	250.1
75°	129.7	133.4	139.6	145.8	153.1	164.3	174.8	177.2	180.3	185.3	191.4
77.5°	98.1	101.4	103.9	108.0	113.8	122.8	128.3	132.1	132.8	134.6	140.7
80°	77.8	79.7	82.1	85.2	87.7	95.1	98.2	101.9	103.1	105.0	108.1
82.5°	57.0	58.9	60.4	63.0	66.9	69.9	73.0	76.7	76.9	78.3	78.9
85°	33.4	34.0	32.7	34.0	34.6	35.8	38.9	42.0	41.4	40.7	42.6
87.5°	15.4	15.1	14.3	15.5	14.2	14.3	14.0	14.2	14.7	15.4	16.0
90°	17.6	16.5	14.8	13.2	11.6	10.1	8.3	6.5	4.7	2.9	1.0
92.5°	41.0	39.5	37.5	35.6	33.6	31.6	29.9	28.7	27.4	26.1	24.9
95°	80.7	79.1	76.8	74.5	72.2	70.0	68.6	68.1	67.7	67.3	66.8
97.5°	127.5	126.0	122.9	119.7	116.5	113.4	111.7	111.5	111.4	111.1	111.0
100°	159.3	157.2	154.2	151.3	148.3	145.4	143.9	143.9	143.9	143.9	143.9
102.5°	192.3	190.1	188.6	187.1	185.6	184.1	182.8	182.0	181.0	180.1	179.2
105°	247.0	245.6	244.2	242.9	241.5	240.1	238.8	237.7	236.5	235.4	234.3
107.5°	305.7	305.0	304.0	302.9	301.8	300.8	299.7	298.6	297.4	296.3	295.1
110°	345.9	345.2	344.6	343.9	343.3	342.5	341.6	340.5	339.4	338.2	337.1



TEST NUMBER: P333733-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	386.7	386.3	385.5	384.6	383.7	382.9	382.1	381.6	381.0	380.4	379.8
115°	448.9	449.1	448.6	448.1	447.7	447.3	446.6	445.6	444.7	443.8	442.9
117.5°	510.1	509.9	509.5	509.1	508.7	508.3	507.9	507.4	507.0	506.6	506.2
120°	551.8	551.8	551.6	551.4	551.1	550.9	550.2	549.1	548.0	546.8	545.7
122.5°	592.7	592.9	592.3	591.8	591.1	590.6	590.0	589.6	589.2	588.8	588.4
125°	653.1	653.6	653.3	653.1	652.8	652.6	651.8	650.5	649.1	647.7	646.3
127.5°	712.5	712.7	712.5	712.2	711.9	711.6	711.1	710.3	709.6	708.8	708.0
130°	751.9	752.2	751.7	751.3	750.8	750.4	749.6	748.5	747.3	746.2	745.0
132.5°	789.8	790.0	790.1	790.2	790.3	790.4	789.5	787.6	785.8	783.9	782.0
135°	847.8	847.8	847.6	847.3	847.1	846.8	846.1	844.7	843.3	841.9	840.6
137.5°	904.1	903.9	903.4	902.9	902.4	901.8	900.9	899.6	898.3	897.0	895.6
140°	939.7	939.2	938.5	937.9	937.2	936.4	935.6	934.5	933.3	932.2	931.0
142.5°	974.9	974.5	973.7	972.8	971.9	971.1	970.2	969.2	968.3	967.3	966.4
145°	1025.6	1025.6	1024.8	1024.1	1023.5	1022.8	1022.0	1021.0	1020.2	1019.2	1018.4
147.5°	1071.7	1071.2	1070.6	1070.1	1069.5	1069.0	1068.4	1067.9	1067.5	1066.9	1066.4
150°	1101.6	1101.6	1100.7	1099.8	1098.8	1097.9	1097.6	1097.8	1098.0	1098.3	1098.5
152.5°	1128.5	1127.9	1127.5	1127.1	1126.8	1126.4	1126.1	1125.8	1125.5	1125.1	1124.8
155°	1167.2	1166.3	1166.1	1165.9	1165.6	1165.4	1165.3	1165.3	1165.3	1165.3	1165.3
157.5°	1201.1	1200.2	1200.0	1199.8	1199.5	1199.3	1199.4	1199.9	1200.5	1200.9	1201.4
160°	1221.7	1220.8	1220.5	1220.4	1220.1	1219.9	1220.1	1220.8	1221.5	1222.2	1222.8
162.5°	1240.8	1239.7	1239.6	1239.6	1239.5	1239.5	1239.8	1240.2	1240.7	1241.3	1241.7
165°	1266.9	1266.0	1265.7	1265.5	1265.3	1265.1	1265.2	1265.7	1266.1	1266.5	1267.0
167.5°	1285.6	1284.3	1284.3	1284.3	1284.3	1284.3	1284.8	1285.6	1286.6	1287.5	1288.4
170°	1297.2	1295.8	1295.8	1295.8	1295.8	1295.8	1296.2	1297.2	1298.1	1299.0	1299.9
172.5°	1305.4	1304.0	1304.0	1304.0	1304.0	1304.0	1304.5	1305.4	1306.3	1307.2	1308.1
175°	1314.6	1313.3	1313.3	1313.3	1313.3	1313.3	1313.8	1314.6	1315.6	1316.4	1317.4
177.5°	1319.1	1318.0	1318.2	1318.3	1318.5	1318.7	1319.1	1319.9	1320.6	1321.4	1322.1
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5



TEST NUMBER: P333733-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3
2.5°	1511.6	1516.2	1522.6	1529.9	1535.9	1542.3	1545.8	1545.8	1548.7	1555.1	1563.5
5°	1516.0	1532.1	1547.5	1567.3	1582.7	1600.6	1614.2	1627.1	1638.9	1653.7	1669.1
7.5°	1514.7	1541.4	1569.2	1600.4	1634.7	1662.0	1690.0	1712.0	1733.8	1762.1	1784.5
10°	1509.8	1544.4	1582.1	1621.6	1664.9	1702.5	1736.5	1767.4	1797.0	1827.9	1855.6
12.5°	1500.9	1544.9	1590.9	1638.4	1693.0	1736.1	1780.0	1812.8	1847.4	1881.2	1915.4
15°	1487.6	1539.4	1595.1	1661.1	1727.8	1776.0	1819.2	1861.8	1893.9	1932.2	1964.9
17.5°	1460.1	1526.9	1596.8	1669.0	1733.1	1789.1	1834.4	1874.9	1909.1	1951.2	1995.7
20°	1443.8	1516.0	1588.9	1666.0	1727.2	1784.6	1828.4	1870.4	1913.0	1968.0	2022.4
22.5°	1421.0	1498.3	1575.5	1648.8	1713.3	1768.8	1814.2	1865.5	1921.4	1983.9	2049.5
25°	1385.1	1464.7	1541.3	1611.1	1674.1	1730.9	1792.6	1861.8	1929.8	2011.9	2106.3
27.5°	1339.5	1416.3	1484.6	1558.4	1621.0	1693.2	1770.3	1845.2	1943.2	2056.2	2174.1
30°	1305.4	1378.3	1443.1	1512.9	1583.9	1663.6	1750.0	1838.3	1955.0	2087.8	2228.0
32.5°	1265.9	1331.9	1396.2	1463.5	1545.4	1632.9	1724.8	1832.9	1972.4	2123.4	2268.5
35°	1197.4	1256.6	1319.0	1393.8	1480.8	1575.9	1693.2	1824.8	1993.4	2155.8	2286.1
37.5°	1125.5	1172.3	1234.9	1313.7	1408.6	1518.6	1651.7	1811.6	1984.7	2130.4	2185.9
40°	1070.2	1114.0	1180.0	1262.8	1356.7	1477.1	1626.5	1790.8	1964.9	2066.2	2061.9
42.5°	1015.3	1059.6	1123.2	1206.5	1304.3	1439.1	1592.9	1763.6	1910.6	1949.2	1868.8
45°	931.2	972.6	1035.0	1119.0	1223.9	1365.3	1527.1	1690.8	1784.6	1722.3	1562.9
47.5°	845.5	885.7	943.6	1025.8	1140.4	1288.4	1441.4	1575.7	1588.9	1454.8	1263.8
50°	789.2	826.9	881.8	969.5	1080.6	1225.2	1372.8	1478.4	1445.6	1282.0	1085.0
52.5°	734.4	770.6	822.0	904.8	1018.4	1159.9	1291.7	1374.6	1298.9	1124.9	947.6
55°	653.3	687.9	739.8	815.7	918.9	1048.5	1164.0	1194.3	1083.2	907.8	764.5
57.5°	576.4	601.7	653.0	720.2	819.6	933.9	1016.7	1011.2	888.6	730.6	627.9
60°	525.5	548.3	597.1	658.9	753.4	855.9	913.9	889.2	765.1	634.8	536.0
62.5°	478.1	499.5	540.3	597.1	678.3	767.5	809.7	775.6	658.4	543.9	465.3
65°	406.3	421.8	454.5	507.0	570.6	632.3	670.0	620.0	516.3	429.8	370.5
67.5°	339.3	352.6	381.8	419.4	463.3	505.9	521.2	474.3	393.6	335.3	293.6
70°	295.8	308.2	327.9	363.1	392.1	422.4	429.8	387.8	320.5	276.0	250.1
72.5°	254.3	265.6	283.0	307.8	327.9	345.3	348.8	309.7	258.3	227.6	207.6
75°	193.9	203.7	214.9	224.2	237.1	240.2	239.0	208.7	180.9	160.6	149.4
77.5°	142.5	146.6	153.4	157.1	157.7	157.5	151.1	132.1	117.7	109.3	104.7
80°	110.0	113.0	114.9	116.1	116.7	110.5	103.8	92.0	87.1	82.1	76.6
82.5°	79.8	81.9	83.7	84.0	80.6	75.5	69.2	63.4	59.9	57.4	55.3
85°	43.3	43.8	43.3	40.2	35.8	34.0	32.7	31.5	30.9	30.3	30.3
87.5°	15.9	14.7	12.7	13.5	13.9	13.7	14.0	13.9	13.6	13.9	14.1
90°	2.9	4.7	6.5	8.3	10.1	11.6	13.2	14.8	16.5	17.6	18.7
92.5°	26.1	27.4	28.7	29.9	31.6	33.6	35.6	37.5	39.5	41.0	42.5
95°	67.3	67.7	68.1	68.6	70.0	72.2	74.5	76.8	79.1	80.7	82.3
97.5°	111.1	111.4	111.5	111.7	113.4	116.5	119.7	122.9	126.0	127.5	129.0
100°	143.9	143.9	143.9	143.9	145.4	148.3	151.3	154.2	157.2	159.3	161.4
102.5°	180.1	181.0	182.0	182.8	184.1	185.6	187.1	188.6	190.1	192.3	194.6
105°	235.4	236.5	237.7	238.8	240.1	241.5	242.9	244.2	245.6	247.0	248.3
107.5°	296.3	297.4	298.6	299.7	300.8	301.8	302.9	304.0	305.0	305.7	306.3
110°	338.2	339.4	340.5	341.6	342.5	343.3	343.9	344.6	345.2	345.9	346.7





TEST NUMBER: P333733-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	380.4	381.0	381.6	382.1	382.9	383.7	384.6	385.5	386.3	386.7	387.0
115°	443.8	444.7	445.6	446.6	447.3	447.7	448.1	448.6	449.1	448.9	448.6
117.5°	506.6	507.0	507.4	507.9	508.3	508.7	509.1	509.5	509.9	510.1	510.2
120°	546.8	548.0	549.1	550.2	550.9	551.1	551.4	551.6	551.8	551.8	551.8
122.5°	588.8	589.2	589.6	590.0	590.6	591.1	591.8	592.3	592.9	592.7	592.6
125°	647.7	649.1	650.5	651.8	652.6	652.8	653.1	653.3	653.6	653.1	652.6
127.5°	708.8	709.6	710.3	711.1	711.6	711.9	712.2	712.5	712.7	712.5	712.3
130°	746.2	747.3	748.5	749.6	750.4	750.8	751.3	751.7	752.2	751.9	751.7
132.5°	783.9	785.8	787.6	789.5	790.4	790.3	790.2	790.1	790.0	789.8	789.6
135°	841.9	843.3	844.7	846.1	846.8	847.1	847.3	847.6	847.8	847.8	847.8
137.5°	897.0	898.3	899.6	900.9	901.8	902.4	902.9	903.4	903.9	904.1	904.4
140°	932.2	933.3	934.5	935.6	936.4	937.2	937.9	938.5	939.2	939.7	940.2
142.5°	967.3	968.3	969.2	970.2	971.1	971.9	972.8	973.7	974.5	974.9	975.1
145°	1019.2	1020.2	1021.0	1022.0	1022.8	1023.5	1024.1	1024.8	1025.6	1025.6	1025.6
147.5°	1066.9	1067.5	1067.9	1068.4	1069.0	1069.5	1070.1	1070.6	1071.2	1071.7	1072.2
150°	1098.3	1098.0	1097.8	1097.6	1097.9	1098.8	1099.8	1100.7	1101.6	1101.6	1101.6
152.5°	1125.1	1125.5	1125.8	1126.1	1126.4	1126.8	1127.1	1127.5	1127.9	1128.5	1128.9
155°	1165.3	1165.3	1165.3	1165.3	1165.4	1165.6	1165.9	1166.1	1166.3	1167.2	1168.2
157.5°	1200.9	1200.5	1199.9	1199.4	1199.3	1199.5	1199.8	1200.0	1200.2	1201.1	1202.1
160°	1222.2	1221.5	1220.8	1220.1	1219.9	1220.1	1220.4	1220.5	1220.8	1221.7	1222.6
162.5°	1241.3	1240.7	1240.2	1239.8	1239.5	1239.5	1239.6	1239.6	1239.7	1240.8	1241.9
165°	1266.5	1266.1	1265.7	1265.2	1265.1	1265.3	1265.5	1265.7	1266.0	1266.9	1267.8
167.5°	1287.5	1286.6	1285.6	1284.8	1284.3	1284.3	1284.3	1284.3	1284.3	1285.6	1287.1
170°	1299.0	1298.1	1297.2	1296.2	1295.8	1295.8	1295.8	1295.8	1295.8	1297.2	1298.5
172.5°	1307.2	1306.3	1305.4	1304.5	1304.0	1304.0	1304.0	1304.0	1304.0	1305.4	1306.8
175°	1316.4	1315.6	1314.6	1313.8	1313.3	1313.3	1313.3	1313.3	1313.3	1314.6	1316.0
177.5°	1321.4	1320.6	1319.9	1319.1	1318.7	1318.5	1318.3	1318.2	1318.0	1319.1	1320.2
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5



TEST NUMBER: P333733-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3
2.5°	1569.9	1569.9	1578.3	1577.9	1583.3	1581.4	1582.3
5°	1687.7	1698.2	1707.5	1713.6	1722.8	1725.4	1724.1
7.5°	1809.7	1833.0	1844.4	1860.0	1862.8	1871.0	1870.1
10°	1885.3	1908.1	1925.4	1939.0	1945.8	1954.5	1955.0
12.5°	1944.6	1964.0	1979.3	1991.9	2000.1	2002.9	2004.5
15°	1990.8	2012.5	2030.4	2048.3	2058.8	2066.8	2071.2
17.5°	2037.6	2070.9	2102.5	2126.9	2141.4	2153.8	2153.6
20°	2073.6	2111.9	2151.4	2179.2	2207.7	2219.9	2221.8
22.5°	2112.1	2170.7	2221.6	2264.7	2302.0	2314.8	2319.7
25°	2192.2	2268.7	2347.2	2407.7	2450.9	2476.2	2479.9
27.5°	2288.9	2392.5	2475.0	2530.9	2566.7	2585.5	2589.6
30°	2357.1	2452.8	2526.9	2568.9	2585.5	2588.0	2578.7
32.5°	2387.7	2459.2	2488.8	2486.3	2453.6	2431.9	2423.6
35°	2350.2	2335.4	2263.2	2176.8	2110.7	2068.7	2057.5
37.5°	2138.8	2011.0	1878.1	1747.5	1677.9	1642.6	1581.8
40°	1930.4	1748.2	1609.9	1499.9	1421.5	1358.5	1343.7
42.5°	1695.2	1507.1	1368.8	1274.7	1212.0	1168.9	1150.1
45°	1362.2	1200.5	1086.2	1014.0	965.8	934.3	920.1
47.5°	1089.6	964.3	881.1	827.6	790.9	763.5	755.8
50°	939.8	839.8	769.4	724.4	696.6	675.6	666.9
52.5°	816.3	735.6	681.5	644.3	618.0	604.9	597.8
55°	673.7	604.0	565.1	535.4	520.5	510.1	505.1
57.5°	551.0	500.6	472.1	451.6	437.9	431.3	428.8
60°	482.3	442.8	416.8	400.8	391.5	382.9	380.4
62.5°	421.5	390.4	370.4	356.3	347.1	343.3	341.8
65°	339.6	319.2	304.4	295.8	288.4	287.2	286.5
67.5°	270.0	258.0	250.3	241.2	238.6	234.2	233.5
70°	230.9	222.9	213.7	210.6	207.5	203.2	203.7
72.5°	195.9	187.8	181.6	177.4	176.3	174.5	176.1
75°	143.2	140.8	138.3	135.2	134.0	134.0	133.4
77.5°	102.3	100.1	97.4	95.6	95.2	92.6	93.6
80°	74.1	71.0	69.8	70.4	68.5	67.9	67.9
82.5°	54.8	53.7	52.5	52.6	52.2	51.7	52.1
85°	30.3	29.6	29.6	29.0	29.0	28.4	28.4
87.5°	14.8	15.5	14.7	14.4	14.6	15.1	15.8
90°	19.9	21.0	21.9	22.6	23.3	24.0	24.6
92.5°	44.0	45.5	46.5	47.0	47.5	48.0	48.5
95°	83.9	85.6	86.5	87.0	87.5	87.9	88.4
97.5°	130.5	132.0	132.9	133.2	133.5	133.7	134.0
100°	163.3	165.4	166.7	167.2	167.6	168.1	168.5
102.5°	196.8	199.1	200.5	201.1	201.8	202.4	203.0
105°	249.7	251.0	252.1	252.8	253.5	254.1	254.8
107.5°	307.0	307.8	308.1	308.0	307.9	307.9	307.8
110°	347.3	348.0	348.2	348.0	347.8	347.5	347.3



TEST NUMBER: P333733-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	387.3	387.6	387.6	387.2	386.8	386.3	386.0
115°	448.4	448.1	447.9	447.7	447.4	447.3	447.0
117.5°	510.4	510.6	510.2	509.4	508.4	507.6	506.6
120°	551.8	551.8	551.4	550.4	549.5	548.6	547.7
122.5°	592.4	592.2	591.8	591.0	590.3	589.5	588.8
125°	652.2	651.7	651.4	651.2	650.9	650.7	650.5
127.5°	712.0	711.9	711.5	711.1	710.6	710.1	709.6
130°	751.5	751.3	750.9	750.5	750.0	749.6	749.1
132.5°	789.3	789.1	788.7	788.1	787.3	786.7	786.1
135°	847.8	847.8	847.3	846.4	845.5	844.5	843.7
137.5°	904.7	905.0	904.5	903.4	902.2	901.1	900.0
140°	940.6	941.0	940.7	939.5	938.4	937.3	936.1
142.5°	975.4	975.7	975.3	974.1	973.0	971.8	970.7
145°	1025.6	1025.6	1025.2	1024.5	1023.8	1023.1	1022.5
147.5°	1072.8	1073.3	1072.9	1071.3	1069.8	1068.2	1066.7
150°	1101.6	1101.6	1101.4	1100.9	1100.4	1099.9	1099.5
152.5°	1129.5	1130.0	1130.0	1129.1	1128.3	1127.4	1126.6
155°	1169.0	1170.0	1169.8	1168.7	1167.6	1166.4	1165.3
157.5°	1202.9	1203.9	1203.6	1202.1	1200.6	1199.0	1197.5
160°	1223.5	1224.4	1224.3	1223.2	1222.0	1220.9	1219.7
162.5°	1242.9	1244.0	1244.0	1242.6	1241.3	1240.0	1238.7
165°	1268.8	1269.6	1269.4	1268.0	1266.7	1265.3	1263.9
167.5°	1288.4	1289.8	1289.8	1288.3	1286.9	1285.5	1284.0
170°	1299.9	1301.2	1301.2	1299.6	1298.0	1296.3	1294.7
172.5°	1308.1	1309.5	1309.5	1308.1	1306.6	1305.2	1303.8
175°	1317.4	1318.7	1318.6	1317.0	1315.4	1313.8	1312.2
177.5°	1321.3	1322.4	1322.3	1321.0	1319.7	1318.4	1317.2
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5

(END OF REPORT)