

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333030-840

Luminaire Tested: **S124RDIW-S350D1340U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333030-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S350D1340U840-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6145.6 lumens  
Efficiency: N/A  
Efficacy: 131.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 46.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333030-840

CATALOG NUMBER: S124RDIW-S350D1340U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333030-840

CATALOG NUMBER: S124RDIW-S350D1340U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	49	49	49	32	32	32	24
1	92	88	84	81	82	78	75	72	60	58	56	44	42	41	28	28	27	20
2	84	77	71	66	74	68	64	60	53	50	47	38	36	35	25	24	23	17
3	76	68	61	55	68	60	54	50	47	43	39	34	31	29	22	21	20	15
4	70	60	52	47	62	53	47	42	41	37	33	30	27	25	20	18	17	13
5	64	53	45	40	57	47	41	36	37	32	29	27	24	22	18	16	15	11
6	59	47	40	34	52	43	36	31	33	28	25	24	21	19	16	14	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12	9
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10	8
9	47	35	28	23	41	32	25	21	25	20	17	19	15	13	13	11	9	7
10	44	32	25	21	39	29	23	19	23	18	15	17	14	12	12	10	8	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5040	5040	5040
5°	5051	4989	5020
10°	5019	4930	4930
15°	4962	4826	4790
20°	4883	4689	4603
25°	4782	4530	4415
30°	4683	4363	4180
35°	4574	4188	3943
40°	4443	3990	3687
45°	4322	3793	3427
50°	4185	3567	3152
55°	4037	3330	2853
60°	3873	3073	2546
65°	3725	2749	2245
70°	3510	2391	1907
75°	3235	1984	1550
80°	2822	1511	1423
85°	2399	1371	1278



TEST NUMBER: P333030-840

CATALOG NUMBER: S124RDIW-S350D1340U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	58.6	1.0
10°-20°	163.5	2.7
20°-30°	236.1	3.8
30°-40°	267.7	4.4
40°-50°	258.5	4.2
50°-60°	214.9	3.5
60°-70°	148.4	2.4
70°-80°	75.2	1.2
80°-90°	24.3	0.4
90°-100°	111.7	1.8
100°-110°	330.9	5.4
110°-120°	561.6	9.1
120°-130°	740.5	12.0
130°-140°	831.6	13.5
140°-150°	817.2	13.3
150°-160°	687.3	11.2
160°-170°	457.3	7.4
170°-180°	160.1	2.6
0°-30°	458.3	7.5
0°-40°	726.0	11.8
0°-60°	1199.4	19.5
0°-90°	1447.4	23.6
90°-120°	1004.2	16.3
90°-150°	3393.5	55.2
90°-180°	4698.0	76.4
0°-180°	6145.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	624	624	624	624	624	
5°	623	621	616	620	620	59
15°	594	589	577	576	573	167
25°	537	528	509	501	496	247
35°	464	448	425	409	400	290
45°	379	360	332	310	300	292
55°	287	267	237	213	203	256
65°	195	174	144	124	118	193
75°	104	86	64	53	50	110
85°	26	17	15	14	14	29
90°	4	18	29	36	39	6
95°	79	90	100	103	104	87
105°	305	307	312	316	320	324
115°	571	571	568	567	566	563
125°	832	832	830	828	825	741
135°	1073	1080	1080	1078	1074	830
145°	1303	1308	1310	1308	1304	815
155°	1493	1493	1492	1496	1492	687
165°	1625	1621	1619	1626	1621	458
175°	1691	1685	1683	1691	1683	160
180°	1693	1693	1693	1693	1693	



TEST NUMBER: P333030-840

CATALOG NUMBER: S124RDIW-S350D1340U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3
2.5°	625.8	625.4	625.1	624.8	624.4	623.8	622.9	622.0	621.0	620.1	621.0
5°	623.3	622.9	622.5	622.1	621.6	620.8	619.5	618.2	616.9	615.7	616.7
7.5°	617.6	617.2	616.8	616.3	615.9	614.8	613.2	611.5	609.9	608.2	608.8
10°	612.3	611.8	611.3	610.8	610.2	608.9	607.0	605.1	603.2	601.4	601.8
12.5°	605.4	604.8	604.2	603.6	603.0	601.6	599.3	597.0	594.8	592.5	592.8
15°	593.7	592.7	591.8	590.8	589.9	588.0	585.4	582.7	580.1	577.4	577.2
17.5°	579.5	578.0	576.6	575.3	573.9	571.6	568.5	565.2	562.1	558.9	558.3
20°	568.4	566.9	565.6	564.2	562.8	560.4	556.7	553.1	549.5	545.8	545.0
22.5°	556.1	554.5	553.0	551.5	549.9	547.1	543.3	539.5	535.6	531.7	530.5
25°	536.8	534.9	533.0	531.1	529.2	526.0	521.7	517.4	512.9	508.6	506.8
27.5°	516.5	514.1	511.7	509.4	507.0	503.4	498.8	494.1	489.5	484.8	482.5
30°	502.4	499.7	497.1	494.4	491.8	488.0	482.9	478.0	472.9	468.0	465.3
32.5°	487.5	484.4	481.5	478.5	475.4	471.4	466.3	461.1	456.0	450.8	447.7
35°	464.1	460.7	457.4	453.9	450.5	446.2	440.9	435.6	430.3	425.0	421.3
37.5°	439.2	435.7	432.2	428.7	425.2	420.5	414.5	408.7	402.8	397.0	392.9
40°	421.6	418.1	414.5	411.1	407.6	402.8	396.8	390.7	384.7	378.6	374.2
42.5°	404.8	401.1	397.4	393.7	390.1	385.1	378.8	372.4	366.2	359.8	355.3
45°	378.6	374.7	370.7	366.8	362.8	357.7	351.3	345.0	338.6	332.2	327.0
47.5°	351.5	347.5	343.5	339.3	335.3	329.9	323.4	316.7	310.0	303.5	298.0
50°	333.2	329.0	324.9	320.7	316.6	311.1	304.4	297.5	290.7	284.0	278.6
52.5°	314.5	310.3	306.3	302.3	298.2	292.7	285.7	278.7	271.8	264.8	259.4
55°	286.8	282.6	278.3	274.1	269.8	264.2	257.3	250.4	243.5	236.6	231.1
57.5°	259.4	255.0	250.6	246.2	241.8	236.2	229.3	222.6	215.8	208.9	203.4
60°	239.9	235.7	231.5	227.2	223.0	217.4	210.7	203.8	197.0	190.3	184.7
62.5°	222.4	217.9	213.5	209.1	204.7	199.0	192.1	185.1	178.1	171.2	166.0
65°	195.0	190.5	185.9	181.4	176.7	171.1	164.3	157.4	150.7	143.9	139.4
67.5°	166.6	162.3	157.8	153.5	149.2	143.8	137.4	131.2	124.8	118.6	114.6
70°	148.7	144.2	139.8	135.3	130.8	125.5	119.5	113.4	107.3	101.3	97.9
72.5°	129.6	125.5	121.5	117.4	113.4	108.6	102.8	97.0	91.4	85.6	82.7
75°	103.7	99.8	95.8	91.9	88.0	83.5	78.6	73.5	68.6	63.6	61.1
77.5°	77.6	74.2	70.9	67.6	64.2	60.5	56.5	52.4	48.4	44.3	42.9
80°	60.7	57.7	54.5	51.5	48.4	45.2	42.1	38.9	35.6	32.5	32.2
82.5°	46.2	43.3	40.5	37.7	34.8	32.5	30.7	28.9	27.1	25.2	25.0
85°	25.9	23.7	21.6	19.4	17.3	16.1	15.8	15.5	15.1	14.8	14.6
87.5°	9.6	9.5	9.5	9.5	9.4	9.6	10.0	10.4	10.7	11.1	11.4
90°	3.9	7.2	10.3	13.5	16.8	19.5	21.8	24.1	26.5	28.8	30.6
92.5°	28.1	31.7	35.3	39.0	42.7	45.3	47.0	48.6	50.2	51.9	52.9
95°	78.6	81.2	83.8	86.4	89.1	91.4	93.4	95.4	97.5	99.6	100.4
97.5°	137.2	139.4	141.5	143.5	145.6	147.8	150.3	152.7	155.0	157.4	158.4
100°	183.4	184.5	185.7	186.8	188.0	189.9	192.5	195.1	197.7	200.4	201.0
102.5°	231.6	232.1	232.5	233.0	233.4	234.8	237.2	239.6	242.0	244.4	245.2
105°	305.2	305.5	305.8	306.0	306.3	307.0	308.2	309.4	310.5	311.7	312.6
107.5°	382.4	382.7	383.1	383.4	383.8	384.1	384.3	384.5	384.7	384.8	385.6
110°	434.8	435.4	436.0	436.6	437.2	437.3	437.0	436.7	436.5	436.2	435.6



TEST NUMBER: P333030-840

CATALOG NUMBER: S124RDIW-S350D1340U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	489.3	489.4	489.5	489.7	489.8	489.6	489.1	488.5	488.0	487.5	487.4
115°	571.0	571.0	571.0	571.0	571.0	570.8	570.2	569.6	569.0	568.4	568.2
117.5°	648.0	648.2	648.5	648.7	648.9	648.8	648.4	648.0	647.6	647.2	646.2
120°	699.3	700.5	701.7	702.9	704.0	704.2	703.3	702.5	701.6	700.6	699.2
122.5°	752.8	753.3	753.8	754.2	754.7	754.7	754.3	753.9	753.5	753.1	752.0
125°	831.6	831.6	831.6	831.6	831.6	831.5	831.2	830.9	830.6	830.3	829.7
127.5°	903.1	904.0	904.9	905.7	906.7	906.9	906.4	905.9	905.4	904.9	904.4
130°	953.4	954.3	955.2	956.0	956.9	957.4	957.4	957.4	957.4	957.4	956.7
132.5°	1004.8	1005.4	1006.0	1006.7	1007.3	1007.5	1007.3	1007.0	1006.8	1006.6	1006.0
135°	1072.6	1074.4	1076.1	1077.8	1079.6	1080.5	1080.5	1080.5	1080.5	1080.5	1079.9
137.5°	1146.5	1147.3	1148.1	1148.9	1149.7	1150.4	1150.8	1151.3	1151.8	1152.3	1151.4
140°	1195.8	1196.3	1196.9	1197.5	1198.1	1198.3	1198.3	1198.3	1198.3	1198.3	1198.1
142.5°	1240.8	1241.3	1241.9	1242.5	1243.1	1243.2	1243.0	1242.8	1242.6	1242.3	1242.3
145°	1303.1	1304.3	1305.5	1306.7	1307.8	1308.5	1308.8	1309.1	1309.4	1309.7	1309.4
147.5°	1364.9	1366.3	1367.8	1369.2	1370.5	1371.1	1370.9	1370.7	1370.4	1370.2	1370.0
150°	1402.7	1403.8	1405.0	1406.1	1407.3	1407.9	1407.9	1407.9	1407.9	1407.9	1407.9
152.5°	1438.2	1439.0	1439.7	1440.4	1441.1	1441.6	1441.8	1442.0	1442.3	1442.5	1443.2
155°	1493.0	1493.0	1493.0	1493.0	1493.0	1492.9	1492.6	1492.3	1492.0	1491.8	1492.9
157.5°	1539.1	1538.6	1538.1	1537.5	1537.0	1536.7	1536.7	1536.6	1536.6	1536.5	1537.4
160°	1566.4	1566.1	1565.8	1565.5	1565.2	1564.9	1564.6	1564.4	1564.1	1563.8	1564.6
162.5°	1591.5	1590.7	1590.0	1589.2	1588.5	1588.0	1587.7	1587.4	1587.1	1586.8	1588.4
165°	1625.3	1624.5	1623.6	1622.7	1621.8	1621.1	1620.5	1619.9	1619.3	1618.7	1620.5
167.5°	1651.2	1650.0	1648.8	1647.6	1646.4	1645.8	1645.9	1645.9	1646.0	1646.0	1647.8
170°	1665.9	1664.5	1663.0	1661.5	1660.1	1659.5	1659.8	1660.1	1660.4	1660.6	1662.4
172.5°	1676.4	1675.2	1674.0	1672.7	1671.5	1670.9	1671.0	1671.0	1671.1	1671.1	1673.1
175°	1690.8	1689.3	1687.9	1686.5	1685.0	1684.1	1683.8	1683.5	1683.2	1682.9	1685.0
177.5°	1695.5	1694.4	1693.1	1692.0	1690.8	1690.3	1690.3	1690.3	1690.3	1690.3	1691.9
180°	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4



TEST NUMBER: P333030-840

CATALOG NUMBER: S124RDIW-S350D1340U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3
2.5°	622.0	622.9	623.8	624.2	624.1	624.1	624.0	623.9
5°	617.8	618.8	620.0	620.4	620.2	620.0	619.7	619.5
7.5°	609.6	610.3	611.0	611.1	610.8	610.5	610.1	609.8
10°	602.2	602.6	603.0	603.0	602.6	602.2	601.8	601.4
12.5°	593.0	593.3	593.6	593.4	592.8	592.2	591.6	591.0
15°	577.0	576.8	576.5	576.1	575.3	574.6	573.9	573.1
17.5°	557.6	557.1	556.5	555.6	554.5	553.4	552.3	551.2
20°	544.2	543.3	542.5	541.4	540.0	538.6	537.2	535.8
22.5°	529.2	527.9	526.6	525.4	524.3	523.2	522.1	520.9
25°	504.9	503.2	501.4	500.0	498.9	497.8	496.8	495.6
27.5°	480.3	478.1	475.8	474.0	472.4	470.9	469.4	467.9
30°	462.6	460.0	457.4	455.1	453.4	451.8	450.1	448.4
32.5°	444.6	441.5	438.5	436.1	434.4	432.8	431.2	429.6
35°	417.7	414.1	410.5	407.8	405.9	403.9	402.0	400.1
37.5°	388.9	384.9	380.8	377.8	375.9	374.0	372.0	370.1
40°	369.6	365.2	360.7	357.6	355.7	353.8	351.8	349.9
42.5°	350.7	346.2	341.6	338.4	336.4	334.4	332.3	330.4
45°	321.8	316.6	311.3	307.8	305.9	304.0	302.1	300.2
47.5°	292.7	287.2	281.9	278.1	276.0	273.9	271.8	269.7
50°	273.3	268.0	262.7	259.0	257.0	255.0	253.0	251.0
52.5°	254.0	248.6	243.3	239.4	237.4	235.3	233.2	231.1
55°	225.6	220.0	214.5	210.8	208.7	206.7	204.7	202.7
57.5°	197.7	192.2	186.5	183.0	181.5	180.0	178.3	176.8
60°	179.2	173.7	168.1	164.5	162.8	161.2	159.5	157.7
62.5°	161.0	155.8	150.8	147.5	146.1	144.8	143.4	142.1
65°	134.7	130.2	125.6	122.7	121.4	120.2	118.9	117.5
67.5°	110.7	106.7	102.8	100.2	98.8	97.4	95.9	94.5
70°	94.3	90.8	87.4	85.0	83.9	82.9	81.8	80.8
72.5°	79.7	76.6	73.7	71.7	70.7	69.8	68.8	67.8
75°	58.7	56.2	53.8	52.3	51.6	51.0	50.4	49.7
77.5°	41.5	40.1	38.7	37.9	37.7	37.5	37.3	37.1
80°	31.9	31.5	31.2	31.0	30.9	30.8	30.7	30.6
82.5°	24.7	24.5	24.3	24.1	24.0	23.9	23.8	23.7
85°	14.4	14.1	13.9	13.8	13.8	13.8	13.8	13.8
87.5°	11.6	11.9	12.2	12.4	12.6	12.8	13.0	13.2
90°	32.3	34.0	35.7	37.0	37.6	38.2	38.7	39.3
92.5°	53.9	55.0	56.0	56.8	57.1	57.5	57.8	58.2
95°	101.3	102.2	103.0	103.5	103.5	103.5	103.5	103.5
97.5°	159.6	160.6	161.6	162.2	162.2	162.2	162.2	162.2
100°	201.6	202.2	202.7	203.0	203.0	203.0	203.0	203.0
102.5°	246.0	246.8	247.6	248.1	248.4	248.6	248.8	249.1
105°	313.5	314.4	315.2	316.1	316.9	317.8	318.7	319.5
107.5°	386.4	387.2	388.1	388.4	388.4	388.3	388.3	388.2
110°	434.9	434.3	433.8	433.9	434.8	435.7	436.6	437.5





TEST NUMBER: P333030-840

CATALOG NUMBER: S124RDIW-S350D1340U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	487.3	487.2	487.0	487.1	487.2	487.4	487.6	487.8
115°	567.8	567.5	567.2	566.9	566.6	566.3	566.0	565.8
117.5°	645.3	644.3	643.3	642.5	641.9	641.4	640.8	640.2
120°	697.8	696.3	694.9	694.4	695.0	695.6	696.2	696.7
122.5°	751.0	750.1	749.1	748.1	747.0	746.0	745.0	743.9
125°	829.2	828.6	828.0	827.4	826.9	826.3	825.7	825.1
127.5°	903.8	903.2	902.6	902.1	901.7	901.2	900.7	900.3
130°	956.2	955.6	955.0	954.2	953.0	951.8	950.7	949.5
132.5°	1005.4	1004.9	1004.3	1003.8	1003.3	1002.8	1002.4	1001.9
135°	1079.3	1078.7	1078.1	1077.4	1076.5	1075.7	1074.8	1073.9
137.5°	1150.7	1150.0	1149.2	1148.9	1149.1	1149.3	1149.4	1149.6
140°	1197.8	1197.5	1197.2	1196.9	1196.6	1196.3	1196.0	1195.8
142.5°	1242.2	1242.2	1242.1	1242.0	1242.0	1241.9	1241.9	1241.8
145°	1309.1	1308.8	1308.5	1308.0	1307.1	1306.2	1305.4	1304.4
147.5°	1369.7	1369.5	1369.3	1369.0	1368.7	1368.4	1368.2	1367.9
150°	1407.9	1407.9	1407.9	1407.8	1407.4	1407.1	1406.8	1406.6
152.5°	1443.9	1444.6	1445.3	1445.2	1444.5	1443.7	1443.0	1442.2
155°	1494.1	1495.2	1496.4	1496.4	1495.2	1494.1	1492.9	1491.8
157.5°	1538.2	1539.1	1540.0	1539.9	1538.9	1537.9	1537.0	1536.0
160°	1565.5	1566.4	1567.2	1566.9	1565.5	1564.1	1562.6	1561.2
162.5°	1589.9	1591.5	1593.1	1593.2	1591.6	1590.2	1588.8	1587.3
165°	1622.2	1624.0	1625.8	1626.1	1624.9	1623.7	1622.6	1621.3
167.5°	1649.5	1651.2	1652.9	1652.9	1651.1	1649.3	1647.6	1645.8
170°	1664.2	1665.9	1667.7	1667.5	1665.5	1663.4	1661.4	1659.4
172.5°	1675.1	1677.1	1679.1	1679.0	1677.0	1675.0	1672.9	1670.9
175°	1687.0	1689.0	1691.1	1691.1	1689.0	1687.0	1685.0	1682.9
177.5°	1693.5	1695.2	1696.8	1696.7	1694.9	1692.9	1691.1	1689.2
180°	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4

(END OF REPORT)