

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333032-840

Luminaire Tested: **S124RDIW-S350D1560U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333032-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S350D1560U840-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6967.8 lumens
Efficiency: N/A
Efficacy: 130.5 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333032-840

CATALOG NUMBER: S124RDIW-S350D1560U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - · 90°-270° - · - · 135°-315°



TEST NUMBER: P333032-840

CATALOG NUMBER: S124RDIW-S350D1560U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	68	68	68	48	48	48	30	30	30	22
1	92	88	84	81	81	78	75	72	59	57	56	42	41	40	27	26	26	19
2	84	77	71	66	74	68	63	59	52	49	46	37	35	34	24	23	22	16
3	76	67	61	55	67	60	54	50	46	42	39	33	31	29	21	20	19	14
4	70	60	52	47	62	53	47	42	41	37	33	30	27	25	19	18	16	12
5	64	53	45	40	56	47	41	36	37	32	29	27	24	21	17	16	14	10
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	16	14	13	9
7	54	43	35	30	48	38	32	27	30	25	22	22	19	16	14	13	11	8
8	50	39	31	26	44	35	28	24	27	22	19	20	17	15	13	11	10	7
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9	7
10	43	32	25	21	38	29	23	19	23	18	15	17	14	12	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4789	4789	4789	4789
5°	5555	4803	4246	4803
10°	6571	4782	3789	4782
15°	7590	4738	3256	4738
20°	8451	4677	2944	4677
25°	8725	4618	2734	4618
30°	7637	4545	2606	4545
35°	5945	4438	2530	4438
40°	4458	4314	2488	4314
45°	3520	4117	2466	4117
50°	2972	3890	2396	3890
55°	2590	3640	2267	3640
60°	2330	3379	2007	3379
65°	2055	3100	1727	3100
70°	1851	2811	1555	2811
75°	1550	2489	1326	2489
80°	1311	2120	1246	2120
85°	1102	1667	1102	1667



TEST NUMBER: P333032-840

CATALOG NUMBER: S124RDIW-S350D1560U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.5	0.8
10°-20°	173.4	2.5
20°-30°	271.2	3.9
30°-40°	301.5	4.3
40°-50°	267.5	3.8
50°-60°	208.4	3.0
60°-70°	136.5	2.0
70°-80°	67.1	1.0
80°-90°	22.4	0.3
90°-100°	129.9	1.9
100°-110°	384.7	5.5
110°-120°	652.9	9.4
120°-130°	861.0	12.4
130°-140°	966.9	13.9
140°-150°	950.1	13.6
150°-160°	799.1	11.5
160°-170°	531.7	7.6
170°-180°	186.2	2.7
0°-30°	502.0	7.2
0°-40°	803.5	11.5
0°-60°	1279.4	18.4
0°-90°	1505.3	21.6
90°-120°	1167.5	16.8
90°-150°	3945.5	56.6
90°-180°	5463.0	78.4
0°-180°	6967.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	593	593	593	593	593	
5°	686	593	524	593	686	69
15°	908	567	390	567	908	258
25°	980	518	307	518	980	435
35°	603	450	257	450	603	378
45°	308	361	216	361	308	244
55°	184	259	161	259	184	167
65°	108	162	90	162	108	108
75°	50	80	42	80	50	55
85°	12	18	12	18	12	15
90°	46	4	46	4	46	24
95°	120	91	120	91	120	125
105°	372	355	372	355	372	392
115°	658	664	658	664	658	650
125°	959	967	959	967	959	856
135°	1249	1247	1249	1247	1249	964
145°	1517	1515	1517	1515	1517	949
155°	1734	1736	1734	1736	1734	798
165°	1885	1890	1885	1890	1885	531
175°	1957	1966	1957	1966	1957	186
180°	1969	1969	1969	1969	1969	



TEST NUMBER: P333032-840

CATALOG NUMBER: S124RDIW-S350D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2
2.5°	625.7	627.4	625.7	625.5	623.6	623.0	622.3	619.8	615.2	612.5	613.1
5°	685.5	691.5	688.1	687.6	682.4	677.1	673.8	666.1	657.9	652.5	647.9
7.5°	754.6	758.0	755.9	752.6	744.1	739.2	731.4	721.4	706.8	695.7	685.5
10°	801.6	804.5	803.5	797.3	791.1	778.4	771.2	757.2	738.7	724.2	710.5
12.5°	847.9	850.9	842.5	842.8	831.0	821.0	809.7	791.9	770.7	751.9	734.9
15°	908.2	904.3	904.3	899.6	886.5	872.6	860.9	842.2	815.5	793.0	769.3
17.5°	955.4	956.7	954.8	943.5	933.2	918.9	897.4	875.7	850.8	820.6	796.5
20°	983.7	983.7	981.6	973.9	960.6	945.2	922.1	898.4	866.9	836.5	809.3
22.5°	995.2	995.9	993.4	987.1	975.1	960.2	940.4	916.4	883.8	849.7	816.0
25°	979.5	984.0	984.4	982.8	979.2	970.1	953.1	928.6	899.4	862.3	826.0
27.5°	899.2	904.9	910.0	918.3	929.3	934.9	935.7	923.2	897.8	862.1	825.6
30°	819.3	824.0	839.6	859.9	875.7	890.0	902.5	905.8	891.5	859.5	821.0
32.5°	730.5	737.1	752.7	774.5	800.7	825.1	852.9	867.2	866.8	847.6	812.0
35°	603.2	608.0	622.4	645.3	676.8	713.0	757.2	791.5	815.0	813.3	791.5
37.5°	486.6	491.9	506.3	525.4	556.0	600.7	643.5	690.9	734.2	758.5	751.2
40°	423.0	423.2	437.4	457.0	485.6	524.6	571.2	623.8	672.1	711.6	719.1
42.5°	372.9	372.9	382.3	403.4	424.0	460.7	505.2	557.4	614.0	659.5	679.7
45°	308.3	310.4	318.1	330.7	347.0	378.1	413.7	462.2	525.5	579.6	613.3
47.5°	261.1	264.3	269.1	279.4	292.4	313.1	342.5	386.2	437.7	497.1	545.0
50°	236.6	237.1	243.3	249.0	260.2	276.8	302.6	338.9	386.3	443.3	496.7
52.5°	215.6	215.5	219.2	226.5	235.6	248.4	269.3	302.4	344.4	395.6	450.6
55°	184.0	185.2	188.1	193.8	200.8	209.8	226.3	251.2	284.2	327.9	377.9
57.5°	160.1	160.7	162.9	165.3	171.7	178.3	190.7	207.9	235.7	271.6	318.1
60°	144.3	144.6	145.3	148.9	153.9	160.2	168.5	183.1	206.5	239.2	276.1
62.5°	129.1	129.5	130.6	133.2	137.1	141.4	150.2	161.9	181.3	209.2	242.4
65°	107.6	107.8	109.5	110.4	113.5	117.3	123.8	131.7	145.1	168.5	193.6
67.5°	89.9	89.9	90.0	91.3	93.4	95.9	99.8	106.1	116.2	130.6	152.7
70°	78.4	78.4	78.9	79.6	80.8	82.9	85.1	89.9	97.3	109.0	125.9
72.5°	67.7	67.9	68.4	68.5	69.1	70.9	72.5	75.5	81.0	89.9	103.6
75°	49.7	50.4	51.6	52.6	53.8	53.5	55.2	57.2	58.8	64.0	71.9
77.5°	37.0	36.7	36.8	37.6	37.7	38.0	39.2	40.6	41.9	44.3	47.2
80°	28.2	28.2	28.9	29.2	28.9	29.2	30.4	31.1	31.5	32.5	35.1
82.5°	21.3	21.7	21.5	21.7	21.8	22.1	23.1	23.2	23.7	24.1	25.1
85°	11.9	12.2	12.4	11.9	11.9	11.9	12.4	12.6	13.1	12.9	13.4
87.5°	13.3	13.0	13.0	12.9	13.0	12.5	12.3	12.3	11.5	11.3	10.7
90°	45.6	45.0	44.3	43.6	43.0	41.6	39.6	37.6	35.5	33.5	30.8
92.5°	67.6	67.2	66.8	66.3	65.9	65.1	63.9	62.7	61.5	60.3	58.4
95°	120.3	120.3	120.3	120.3	120.3	119.8	118.8	117.8	116.7	115.7	113.4
97.5°	188.5	188.5	188.5	188.5	188.5	187.9	186.7	185.5	184.2	183.0	180.3
100°	236.0	236.0	236.0	236.0	236.0	235.7	235.0	234.3	233.7	233.0	229.9
102.5°	289.6	289.3	289.1	288.8	288.5	287.9	287.0	286.0	285.1	284.2	281.3
105°	371.5	370.5	369.5	368.5	367.5	366.5	365.5	364.5	363.5	362.4	361.0
107.5°	451.3	451.4	451.5	451.5	451.6	451.2	450.2	449.3	448.3	447.4	447.2
110°	508.6	507.6	506.5	505.5	504.5	504.3	505.0	505.7	506.3	507.1	507.4



TEST NUMBER: P333032-840

CATALOG NUMBER: S124RDIW-S350D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	567.0	566.8	566.6	566.4	566.2	566.2	566.3	566.4	566.6	566.7	567.3
115°	657.8	658.1	658.5	658.8	659.1	659.5	659.8	660.1	660.6	660.9	661.6
117.5°	744.3	745.0	745.7	746.3	747.0	747.9	749.1	750.2	751.3	752.6	753.0
120°	810.1	809.4	808.7	808.1	807.4	807.9	809.6	811.2	812.9	814.7	815.7
122.5°	864.9	866.2	867.4	868.6	869.8	871.0	872.1	873.2	874.4	875.6	876.1
125°	959.3	960.0	960.7	961.3	962.0	962.7	963.4	964.0	964.7	965.4	965.7
127.5°	1046.7	1047.2	1047.8	1048.3	1048.8	1049.5	1050.2	1050.9	1051.5	1052.2	1052.8
130°	1104.0	1105.3	1106.7	1108.0	1109.3	1110.3	1111.1	1111.8	1112.5	1113.1	1113.1
132.5°	1164.9	1165.4	1166.0	1166.5	1167.0	1167.6	1168.3	1169.0	1169.7	1170.3	1170.6
135°	1248.6	1249.6	1250.6	1251.6	1252.6	1253.5	1254.3	1254.9	1255.6	1256.3	1256.3
137.5°	1336.7	1336.5	1336.3	1336.1	1335.8	1336.2	1337.1	1338.0	1338.8	1339.7	1339.2
140°	1390.3	1390.6	1390.9	1391.3	1391.6	1391.9	1392.3	1392.6	1392.9	1393.3	1393.3
142.5°	1443.8	1443.9	1444.0	1444.0	1444.1	1444.2	1444.2	1444.3	1444.4	1444.4	1444.7
145°	1516.6	1517.6	1518.6	1519.6	1520.7	1521.4	1521.7	1522.1	1522.4	1522.7	1522.4
147.5°	1590.3	1590.6	1591.0	1591.3	1591.6	1592.0	1592.3	1592.6	1592.8	1593.1	1593.4
150°	1635.4	1635.8	1636.1	1636.4	1636.8	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9
152.5°	1676.8	1677.7	1678.6	1679.4	1680.3	1680.3	1679.5	1678.7	1677.9	1677.1	1676.9
155°	1734.3	1735.8	1737.1	1738.4	1739.8	1739.8	1738.4	1737.1	1735.8	1734.3	1734.7
157.5°	1785.8	1787.0	1788.2	1789.3	1790.4	1790.5	1789.5	1788.5	1787.5	1786.5	1786.6
160°	1815.0	1816.7	1818.5	1820.2	1821.8	1822.2	1821.2	1820.2	1819.2	1818.2	1818.5
162.5°	1845.5	1847.2	1849.0	1850.6	1852.3	1852.2	1850.4	1848.6	1846.7	1844.9	1845.2
165°	1885.1	1886.4	1887.8	1889.2	1890.6	1890.2	1888.1	1886.1	1884.1	1882.1	1882.8
167.5°	1913.4	1915.5	1917.6	1919.8	1921.9	1921.9	1919.9	1917.8	1915.8	1913.8	1913.7
170°	1929.2	1931.7	1934.0	1936.4	1938.7	1938.9	1936.9	1934.9	1932.8	1930.8	1930.5
172.5°	1942.7	1945.0	1947.4	1949.7	1952.2	1952.2	1949.8	1947.6	1945.3	1943.0	1942.9
175°	1956.7	1959.0	1961.5	1963.8	1966.2	1966.2	1963.8	1961.5	1959.0	1956.7	1957.0
177.5°	1964.0	1966.2	1968.3	1970.4	1972.7	1972.8	1970.9	1969.0	1967.1	1965.2	1965.2
180°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8



TEST NUMBER: P333032-840

CATALOG NUMBER: S124RDIW-S350D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2
2.5°	611.2	608.5	607.1	604.1	600.5	598.5	596.8	594.3	591.1	587.6	585.2
5°	642.2	636.4	629.2	620.7	613.1	605.6	599.2	592.7	585.3	577.6	570.1
7.5°	674.0	662.8	650.6	636.4	622.8	610.3	598.7	587.8	575.4	564.2	554.1
10°	696.2	681.0	664.0	646.0	628.1	612.6	597.2	583.4	568.2	554.5	543.0
12.5°	714.2	696.2	675.8	653.5	631.9	613.1	595.5	577.4	560.1	545.3	530.0
15°	744.0	719.4	692.0	665.1	637.2	611.6	587.9	566.9	547.0	526.2	511.7
17.5°	764.6	735.3	701.9	669.7	636.7	606.5	579.3	554.2	531.3	510.1	492.7
20°	776.8	744.5	707.4	670.9	633.8	601.6	572.2	544.4	520.8	497.9	479.9
22.5°	783.7	747.9	707.4	669.1	630.8	595.8	563.6	534.7	509.0	485.9	466.2
25°	785.9	747.6	706.3	662.3	620.3	583.2	549.7	518.4	489.7	466.8	445.8
27.5°	782.7	737.7	695.4	650.3	606.8	567.8	532.7	499.8	471.1	446.5	424.9
30°	778.2	729.9	684.5	637.6	593.7	556.1	519.1	487.6	457.7	432.1	410.4
32.5°	768.2	720.3	671.5	623.5	579.0	540.3	505.1	473.4	444.1	418.0	394.9
35°	748.5	700.0	647.0	597.7	554.0	513.8	480.9	450.3	422.3	394.4	370.0
37.5°	722.6	673.1	620.3	566.3	522.5	484.6	454.4	425.7	398.4	372.8	345.9
40°	698.1	653.0	598.4	544.9	500.0	463.4	435.5	409.4	381.9	356.6	329.6
42.5°	668.5	630.1	574.9	521.2	476.9	441.6	415.6	390.1	365.1	340.5	312.4
45°	619.0	589.9	538.3	486.7	441.9	407.0	383.1	360.6	338.7	315.3	288.7
47.5°	562.3	542.6	498.1	445.1	403.8	372.4	349.3	330.9	312.4	288.9	265.7
50°	522.9	510.3	467.3	419.0	379.5	350.6	327.0	309.7	294.2	271.8	251.0
52.5°	480.9	474.1	437.8	391.6	353.6	325.2	305.0	289.5	273.8	255.1	235.7
55°	416.8	420.4	389.6	349.6	313.8	289.9	271.6	258.6	245.2	229.4	214.4
57.5°	351.3	364.5	343.8	308.7	275.1	253.0	239.1	228.3	217.0	204.0	191.1
60°	312.1	323.2	311.4	280.5	251.2	230.7	217.7	209.3	198.1	186.2	176.4
62.5°	273.9	285.7	278.7	253.8	226.5	208.8	197.4	189.7	181.3	170.9	160.7
65°	225.9	233.5	230.1	213.0	193.6	178.5	168.0	162.3	154.6	147.0	137.9
67.5°	173.0	187.7	185.8	176.6	160.0	148.1	141.3	136.2	129.3	123.6	117.4
70°	142.2	155.8	155.6	148.1	139.1	128.2	123.3	119.1	112.8	107.3	102.3
72.5°	116.4	128.9	130.8	125.0	118.9	110.5	105.9	103.0	96.9	93.2	89.1
75°	81.5	90.6	93.0	93.0	90.1	85.8	81.7	79.8	75.5	72.2	69.8
77.5°	53.4	59.2	62.9	63.7	64.2	62.7	59.4	58.1	54.7	53.6	51.3
80°	37.8	41.6	45.8	47.4	48.5	48.1	46.7	45.6	42.5	41.3	40.4
82.5°	26.1	28.2	31.7	34.9	34.5	35.9	34.5	33.8	31.4	31.0	30.1
85°	13.6	13.8	14.3	16.5	17.7	18.2	18.4	18.0	17.2	17.2	15.6
87.5°	10.2	9.5	9.3	8.7	8.1	8.2	8.0	7.4	7.6	7.8	7.9
90°	28.1	25.3	22.7	19.5	15.8	12.0	8.3	4.5	8.3	12.0	15.8
92.5°	56.6	54.6	52.7	49.7	45.3	41.1	36.9	32.6	36.9	41.1	45.3
95°	111.0	108.7	106.2	103.5	100.5	97.5	94.4	91.4	94.4	97.5	100.5
97.5°	177.4	174.7	172.0	169.4	166.9	164.4	162.0	159.6	162.0	164.4	166.9
100°	226.9	223.9	220.8	218.6	217.2	215.9	214.5	213.2	214.5	215.9	217.2
102.5°	278.6	275.8	273.1	271.4	270.8	270.3	269.7	269.2	269.7	270.3	270.8
105°	359.7	358.3	357.0	356.2	355.8	355.5	355.2	354.8	355.2	355.5	355.8
107.5°	447.0	446.8	446.6	446.3	445.9	445.5	445.0	444.6	445.0	445.5	445.9
110°	507.8	508.1	508.5	508.3	507.6	506.9	506.2	505.5	506.2	506.9	507.6



TEST NUMBER: P333032-840

CATALOG NUMBER: S124RDIW-S350D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	567.9	568.6	569.2	569.5	569.3	569.2	569.1	568.9	569.1	569.2	569.3
115°	662.2	662.9	663.6	663.9	663.9	663.9	663.9	663.9	663.9	663.9	663.9
117.5°	753.5	754.0	754.5	754.6	754.3	754.0	753.7	753.5	753.7	754.0	754.3
120°	816.7	817.7	818.7	818.5	817.2	815.9	814.5	813.1	814.5	815.9	817.2
122.5°	876.5	877.0	877.5	877.4	876.9	876.4	875.8	875.3	875.8	876.4	876.9
125°	966.0	966.4	966.7	966.9	966.9	966.9	966.9	966.9	966.9	966.9	966.9
127.5°	1053.3	1053.8	1054.4	1054.1	1053.1	1052.1	1051.1	1050.1	1051.1	1052.1	1053.1
130°	1113.1	1113.1	1113.1	1112.6	1111.6	1110.5	1109.5	1108.5	1109.5	1110.5	1111.6
132.5°	1170.9	1171.1	1171.4	1171.2	1170.4	1169.7	1169.0	1168.2	1169.0	1169.7	1170.4
135°	1256.3	1256.3	1256.3	1255.3	1253.2	1251.1	1249.1	1247.1	1249.1	1251.1	1253.2
137.5°	1338.6	1338.1	1337.6	1336.8	1335.8	1334.8	1333.9	1333.0	1333.9	1334.8	1335.8
140°	1393.3	1393.3	1393.3	1392.9	1392.3	1391.6	1390.9	1390.3	1390.9	1391.6	1392.3
142.5°	1445.0	1445.2	1445.5	1445.3	1444.6	1444.0	1443.3	1442.6	1443.3	1444.0	1444.6
145°	1522.1	1521.7	1521.4	1520.6	1519.1	1517.8	1516.4	1515.1	1516.4	1517.8	1519.1
147.5°	1593.6	1593.9	1594.2	1593.5	1591.9	1590.2	1588.6	1587.0	1588.6	1590.2	1591.9
150°	1636.9	1636.9	1636.9	1636.3	1634.9	1633.6	1632.1	1630.8	1632.1	1633.6	1634.9
152.5°	1676.6	1676.3	1676.1	1675.5	1674.7	1673.9	1673.0	1672.2	1673.0	1673.9	1674.7
155°	1735.0	1735.4	1735.8	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9
157.5°	1786.6	1786.7	1786.8	1787.1	1787.7	1788.3	1788.9	1789.5	1788.9	1788.3	1787.7
160°	1818.8	1819.2	1819.5	1819.8	1820.2	1820.5	1820.8	1821.2	1820.8	1820.5	1820.2
162.5°	1845.6	1845.9	1846.2	1846.8	1847.8	1848.7	1849.6	1850.4	1849.6	1848.7	1847.8
165°	1883.4	1884.1	1884.8	1885.6	1886.6	1887.6	1888.6	1889.7	1888.6	1887.6	1886.6
167.5°	1913.6	1913.6	1913.5	1914.2	1915.6	1917.0	1918.4	1919.9	1918.4	1917.0	1915.6
170°	1930.2	1929.8	1929.4	1930.2	1931.8	1933.5	1935.2	1936.9	1935.2	1933.5	1931.8
172.5°	1942.9	1942.8	1942.7	1943.4	1944.8	1946.2	1947.6	1949.0	1947.6	1946.2	1944.8
175°	1957.3	1957.7	1958.0	1959.0	1960.8	1962.5	1964.1	1965.8	1964.1	1962.5	1960.8
177.5°	1965.2	1965.2	1965.2	1965.9	1967.2	1968.6	1969.9	1971.3	1969.9	1968.6	1967.2
180°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8



TEST NUMBER: P333032-840

CATALOG NUMBER: S124RDIW-S350D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2
2.5°	582.5	580.6	578.1	575.2	571.8	568.8	567.3	568.6	569.2	567.5	567.3
5°	564.7	558.8	554.0	546.8	541.1	536.3	533.0	531.5	532.0	528.2	527.3
7.5°	544.8	537.8	529.9	521.4	513.5	506.4	502.8	500.8	496.7	494.9	492.0
10°	532.0	522.5	514.8	504.7	495.6	487.4	483.2	479.9	475.8	473.9	469.9
12.5°	518.9	507.8	499.3	488.9	479.6	469.6	465.6	459.5	453.1	449.1	443.8
15°	500.2	486.9	476.6	464.1	453.1	441.7	431.4	419.9	415.7	406.6	401.3
17.5°	478.5	464.9	452.2	435.6	418.6	404.2	393.3	382.3	375.8	370.0	367.3
20°	464.1	451.7	434.0	414.7	395.8	380.0	371.1	364.0	356.8	352.7	349.9
22.5°	450.6	434.6	414.1	393.2	374.4	362.0	354.6	347.2	341.3	337.5	333.7
25°	427.8	407.0	385.3	361.3	348.5	337.7	329.6	323.6	320.0	315.0	313.1
27.5°	404.5	379.2	355.3	339.2	325.8	315.9	308.8	304.4	299.8	296.6	294.1
30°	386.5	360.9	339.4	324.1	310.4	302.4	296.6	291.3	287.7	285.1	283.3
32.5°	368.7	343.2	325.1	308.6	297.8	289.9	283.8	279.8	277.0	273.7	272.5
35°	343.0	320.2	304.5	289.6	278.7	271.6	266.7	262.7	260.2	259.3	258.6
37.5°	318.2	299.6	282.7	270.5	260.7	255.1	249.4	247.4	245.8	244.1	244.9
40°	302.6	285.1	270.0	257.2	249.2	243.1	239.7	237.3	235.9	235.9	235.9
42.5°	289.0	272.0	257.2	245.7	237.8	232.6	228.8	226.8	226.3	226.1	227.3
45°	267.9	252.2	237.3	227.7	221.1	215.8	213.7	212.0	212.0	213.0	213.2
47.5°	247.0	232.3	220.4	209.6	203.5	200.3	198.3	197.5	197.6	198.5	199.7
50°	234.2	219.6	207.9	198.3	192.7	189.6	187.8	187.3	187.8	187.8	189.6
52.5°	220.3	207.2	195.7	187.6	181.2	178.2	177.3	176.6	176.9	177.7	178.4
55°	199.9	188.1	177.1	169.5	164.7	162.8	160.6	160.9	160.4	160.9	160.9
57.5°	179.3	168.7	158.5	152.5	148.2	145.5	143.2	143.8	143.1	143.0	142.6
60°	166.1	154.6	146.5	141.0	136.2	133.8	131.7	132.2	131.5	131.0	130.0
62.5°	151.8	142.2	134.4	129.2	125.3	122.6	120.4	120.0	118.3	116.6	114.5
65°	131.0	123.1	116.1	111.2	107.6	105.4	103.7	102.3	98.7	94.9	93.0
67.5°	110.8	105.0	98.6	94.3	91.4	88.7	85.4	83.0	79.7	77.6	76.3
70°	97.8	92.3	86.7	82.7	79.6	77.0	73.4	71.7	69.3	68.4	67.2
72.5°	85.3	80.2	75.1	71.4	68.2	66.0	63.2	61.6	60.5	60.1	59.0
75°	66.4	62.4	58.6	55.2	52.6	51.1	50.0	48.8	48.3	46.2	44.9
77.5°	48.5	45.7	43.4	41.0	39.2	38.2	35.9	34.5	33.7	32.7	32.4
80°	37.8	35.9	33.4	32.0	29.4	28.5	27.5	27.3	27.0	26.8	26.6
82.5°	28.4	26.5	24.1	23.2	22.5	21.9	21.4	21.1	20.9	21.0	21.0
85°	14.3	13.4	13.4	13.1	12.9	12.6	12.4	12.4	12.2	12.4	12.2
87.5°	8.7	9.1	9.7	9.8	10.6	11.1	11.3	11.7	12.3	12.3	12.6
90°	19.5	22.7	25.3	28.1	30.8	33.5	35.5	37.6	39.6	41.6	43.0
92.5°	49.7	52.7	54.6	56.6	58.4	60.3	61.5	62.7	63.9	65.1	65.9
95°	103.5	106.2	108.7	111.0	113.4	115.7	116.7	117.8	118.8	119.8	120.3
97.5°	169.4	172.0	174.7	177.4	180.3	183.0	184.2	185.5	186.7	187.9	188.5
100°	218.6	220.8	223.9	226.9	229.9	233.0	233.7	234.3	235.0	235.7	236.0
102.5°	271.4	273.1	275.8	278.6	281.3	284.2	285.1	286.0	287.0	287.9	288.5
105°	356.2	357.0	358.3	359.7	361.0	362.4	363.5	364.5	365.5	366.5	367.5
107.5°	446.3	446.6	446.8	447.0	447.2	447.4	448.3	449.3	450.2	451.2	451.6
110°	508.3	508.5	508.1	507.8	507.4	507.1	506.3	505.7	505.0	504.3	504.5



TEST NUMBER: P333032-840

CATALOG NUMBER: S124RDIW-S350D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	569.5	569.2	568.6	567.9	567.3	566.7	566.6	566.4	566.3	566.2	566.2
115°	663.9	663.6	662.9	662.2	661.6	660.9	660.6	660.1	659.8	659.5	659.1
117.5°	754.6	754.5	754.0	753.5	753.0	752.6	751.3	750.2	749.1	747.9	747.0
120°	818.5	818.7	817.7	816.7	815.7	814.7	812.9	811.2	809.6	807.9	807.4
122.5°	877.4	877.5	877.0	876.5	876.1	875.6	874.4	873.2	872.1	871.0	869.8
125°	966.9	966.7	966.4	966.0	965.7	965.4	964.7	964.0	963.4	962.7	962.0
127.5°	1054.1	1054.4	1053.8	1053.3	1052.8	1052.2	1051.5	1050.9	1050.2	1049.5	1048.8
130°	1112.6	1113.1	1113.1	1113.1	1113.1	1113.1	1112.5	1111.8	1111.1	1110.3	1109.3
132.5°	1171.2	1171.4	1171.1	1170.9	1170.6	1170.3	1169.7	1169.0	1168.3	1167.6	1167.0
135°	1255.3	1256.3	1256.3	1256.3	1256.3	1256.3	1255.6	1254.9	1254.3	1253.5	1252.6
137.5°	1336.8	1337.6	1338.1	1338.6	1339.2	1339.7	1338.8	1338.0	1337.1	1336.2	1335.8
140°	1392.9	1393.3	1393.3	1393.3	1393.3	1393.3	1392.9	1392.6	1392.3	1391.9	1391.6
142.5°	1445.3	1445.5	1445.2	1445.0	1444.7	1444.4	1444.4	1444.3	1444.2	1444.2	1444.1
145°	1520.6	1521.4	1521.7	1522.1	1522.4	1522.7	1522.4	1522.1	1521.7	1521.4	1520.7
147.5°	1593.5	1594.2	1593.9	1593.6	1593.4	1593.1	1592.8	1592.6	1592.3	1592.0	1591.6
150°	1636.3	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9	1636.8
152.5°	1675.5	1676.1	1676.3	1676.6	1676.9	1677.1	1677.9	1678.7	1679.5	1680.3	1680.3
155°	1735.9	1735.8	1735.4	1735.0	1734.7	1734.3	1735.8	1737.1	1738.4	1739.8	1739.8
157.5°	1787.1	1786.8	1786.7	1786.6	1786.6	1786.5	1787.5	1788.5	1789.5	1790.5	1790.4
160°	1819.8	1819.5	1819.2	1818.8	1818.5	1818.2	1819.2	1820.2	1821.2	1822.2	1821.8
162.5°	1846.8	1846.2	1845.9	1845.6	1845.2	1844.9	1846.7	1848.6	1850.4	1852.2	1852.3
165°	1885.6	1884.8	1884.1	1883.4	1882.8	1882.1	1884.1	1886.1	1888.1	1890.2	1890.6
167.5°	1914.2	1913.5	1913.6	1913.6	1913.7	1913.8	1915.8	1917.8	1919.9	1921.9	1921.9
170°	1930.2	1929.4	1929.8	1930.2	1930.5	1930.8	1932.8	1934.9	1936.9	1938.9	1938.7
172.5°	1943.4	1942.7	1942.8	1942.9	1942.9	1943.0	1945.3	1947.6	1949.8	1952.2	1952.2
175°	1959.0	1958.0	1957.7	1957.3	1957.0	1956.7	1959.0	1961.5	1963.8	1966.2	1966.2
177.5°	1965.9	1965.2	1965.2	1965.2	1965.2	1965.2	1967.1	1969.0	1970.9	1972.8	1972.7
180°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8



TEST NUMBER: P333032-840

CATALOG NUMBER: S124RDIW-S350D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2
2.5°	566.2	566.6	565.3	564.9	565.3	566.6	566.2	567.3	567.5	569.2	568.6
5°	525.3	524.8	523.6	523.9	523.6	524.8	525.3	527.3	528.2	532.0	531.5
7.5°	490.3	488.5	489.0	487.1	489.0	488.5	490.3	492.0	494.9	496.7	500.8
10°	468.9	466.3	464.1	462.2	464.1	466.3	468.9	469.9	473.9	475.8	479.9
12.5°	439.7	437.4	434.5	435.0	434.5	437.4	439.7	443.8	449.1	453.1	459.5
15°	398.2	394.6	388.9	389.6	388.9	394.6	398.2	401.3	406.6	415.7	419.9
17.5°	363.0	363.0	360.4	361.1	360.4	363.0	363.0	367.3	370.0	375.8	382.3
20°	344.9	343.3	343.5	342.7	343.5	343.3	344.9	349.9	352.7	356.8	364.0
22.5°	332.2	330.2	328.5	327.1	328.5	330.2	332.2	333.7	337.5	341.3	347.2
25°	310.9	309.5	307.4	306.9	307.4	309.5	310.9	313.1	315.0	320.0	323.6
27.5°	292.2	292.0	291.0	289.9	291.0	292.0	292.2	294.1	296.6	299.8	304.4
30°	281.3	280.8	280.3	279.6	280.3	280.8	281.3	283.3	285.1	287.7	291.3
32.5°	271.6	271.2	270.7	270.8	270.7	271.2	271.6	272.5	273.7	277.0	279.8
35°	257.6	257.4	256.9	256.7	256.9	257.4	257.6	258.6	259.3	260.2	262.7
37.5°	244.7	245.3	245.0	244.9	245.0	245.3	244.7	244.9	244.1	245.8	247.4
40°	235.7	235.9	236.4	236.1	236.4	235.9	235.7	235.9	235.9	235.9	237.3
42.5°	228.2	228.2	228.9	228.1	228.9	228.2	228.2	227.3	226.1	226.3	226.8
45°	214.9	216.3	216.0	216.0	216.0	216.3	214.9	213.2	213.0	212.0	212.0
47.5°	200.3	201.6	201.9	201.8	201.9	201.6	200.3	199.7	198.5	197.6	197.5
50°	190.8	190.3	191.0	190.8	191.0	190.3	190.8	189.6	187.8	187.8	187.3
52.5°	179.0	179.2	179.2	178.8	179.2	179.2	179.0	178.4	177.7	176.9	176.6
55°	161.1	161.4	160.9	161.1	160.9	161.4	161.1	160.9	160.9	160.4	160.9
57.5°	141.6	140.5	140.9	140.4	140.9	140.5	141.6	142.6	143.0	143.1	143.8
60°	127.6	125.7	125.2	124.3	125.2	125.7	127.6	130.0	131.0	131.5	132.2
62.5°	112.0	110.6	109.0	109.8	109.0	110.6	112.0	114.5	116.6	118.3	120.0
65°	91.1	90.1	89.4	90.4	89.4	90.1	91.1	93.0	94.9	98.7	102.3
67.5°	75.3	74.8	74.8	74.4	74.8	74.8	75.3	76.3	77.6	79.7	83.0
70°	67.2	66.4	66.4	65.9	66.4	66.4	67.2	67.2	68.4	69.3	71.7
72.5°	58.8	58.1	58.3	58.0	58.3	58.1	58.8	59.0	60.1	60.5	61.6
75°	43.5	42.3	42.3	42.5	42.3	42.3	43.5	44.9	46.2	48.3	48.8
77.5°	32.4	32.2	32.5	32.1	32.5	32.2	32.4	32.4	32.7	33.7	34.5
80°	26.6	26.3	26.1	26.8	26.1	26.3	26.6	26.6	26.8	27.0	27.3
82.5°	20.6	20.6	20.5	21.4	20.5	20.6	20.6	21.0	21.0	20.9	21.1
85°	12.4	11.9	12.4	11.9	12.4	11.9	12.4	12.2	12.4	12.2	12.4
87.5°	13.1	13.0	13.0	13.3	13.0	13.0	13.1	12.6	12.3	12.3	11.7
90°	43.6	44.3	45.0	45.6	45.0	44.3	43.6	43.0	41.6	39.6	37.6
92.5°	66.3	66.8	67.2	67.6	67.2	66.8	66.3	65.9	65.1	63.9	62.7
95°	120.3	120.3	120.3	120.3	120.3	120.3	120.3	120.3	119.8	118.8	117.8
97.5°	188.5	188.5	188.5	188.5	188.5	188.5	188.5	188.5	187.9	186.7	185.5
100°	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0	235.7	235.0	234.3
102.5°	288.8	289.1	289.3	289.6	289.3	289.1	288.8	288.5	287.9	287.0	286.0
105°	368.5	369.5	370.5	371.5	370.5	369.5	368.5	367.5	366.5	365.5	364.5
107.5°	451.5	451.5	451.4	451.3	451.4	451.5	451.5	451.6	451.2	450.2	449.3
110°	505.5	506.5	507.6	508.6	507.6	506.5	505.5	504.5	504.3	505.0	505.7



TEST NUMBER: P333032-840

CATALOG NUMBER: S124RDIW-S350D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	566.4	566.6	566.8	567.0	566.8	566.6	566.4	566.2	566.2	566.3	566.4
115°	658.8	658.5	658.1	657.8	658.1	658.5	658.8	659.1	659.5	659.8	660.1
117.5°	746.3	745.7	745.0	744.3	745.0	745.7	746.3	747.0	747.9	749.1	750.2
120°	808.1	808.7	809.4	810.1	809.4	808.7	808.1	807.4	807.9	809.6	811.2
122.5°	868.6	867.4	866.2	864.9	866.2	867.4	868.6	869.8	871.0	872.1	873.2
125°	961.3	960.7	960.0	959.3	960.0	960.7	961.3	962.0	962.7	963.4	964.0
127.5°	1048.3	1047.8	1047.2	1046.7	1047.2	1047.8	1048.3	1048.8	1049.5	1050.2	1050.9
130°	1108.0	1106.7	1105.3	1104.0	1105.3	1106.7	1108.0	1109.3	1110.3	1111.1	1111.8
132.5°	1166.5	1166.0	1165.4	1164.9	1165.4	1166.0	1166.5	1167.0	1167.6	1168.3	1169.0
135°	1251.6	1250.6	1249.6	1248.6	1249.6	1250.6	1251.6	1252.6	1253.5	1254.3	1254.9
137.5°	1336.1	1336.3	1336.5	1336.7	1336.5	1336.3	1336.1	1335.8	1336.2	1337.1	1338.0
140°	1391.3	1390.9	1390.6	1390.3	1390.6	1390.9	1391.3	1391.6	1391.9	1392.3	1392.6
142.5°	1444.0	1444.0	1443.9	1443.8	1443.9	1444.0	1444.0	1444.1	1444.2	1444.2	1444.3
145°	1519.6	1518.6	1517.6	1516.6	1517.6	1518.6	1519.6	1520.7	1521.4	1521.7	1522.1
147.5°	1591.3	1591.0	1590.6	1590.3	1590.6	1591.0	1591.3	1591.6	1592.0	1592.3	1592.6
150°	1636.4	1636.1	1635.8	1635.4	1635.8	1636.1	1636.4	1636.8	1636.9	1636.9	1636.9
152.5°	1679.4	1678.6	1677.7	1676.8	1677.7	1678.6	1679.4	1680.3	1680.3	1679.5	1678.7
155°	1738.4	1737.1	1735.8	1734.3	1735.8	1737.1	1738.4	1739.8	1739.8	1738.4	1737.1
157.5°	1789.3	1788.2	1787.0	1785.8	1787.0	1788.2	1789.3	1790.4	1790.5	1789.5	1788.5
160°	1820.2	1818.5	1816.7	1815.0	1816.7	1818.5	1820.2	1821.8	1822.2	1821.2	1820.2
162.5°	1850.6	1849.0	1847.2	1845.5	1847.2	1849.0	1850.6	1852.3	1852.2	1850.4	1848.6
165°	1889.2	1887.8	1886.4	1885.1	1886.4	1887.8	1889.2	1890.6	1890.2	1888.1	1886.1
167.5°	1919.8	1917.6	1915.5	1913.4	1915.5	1917.6	1919.8	1921.9	1921.9	1919.9	1917.8
170°	1936.4	1934.0	1931.7	1929.2	1931.7	1934.0	1936.4	1938.7	1938.9	1936.9	1934.9
172.5°	1949.7	1947.4	1945.0	1942.7	1945.0	1947.4	1949.7	1952.2	1952.2	1949.8	1947.6
175°	1963.8	1961.5	1959.0	1956.7	1959.0	1961.5	1963.8	1966.2	1966.2	1963.8	1961.5
177.5°	1970.4	1968.3	1966.2	1964.0	1966.2	1968.3	1970.4	1972.7	1972.8	1970.9	1969.0
180°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8



TEST NUMBER: P333032-840

CATALOG NUMBER: S124RDIW-S350D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2
2.5°	567.3	568.8	571.8	575.2	578.1	580.6	582.5	585.2	587.6	591.1	594.3
5°	533.0	536.3	541.1	546.8	554.0	558.8	564.7	570.1	577.6	585.3	592.7
7.5°	502.8	506.4	513.5	521.4	529.9	537.8	544.8	554.1	564.2	575.4	587.8
10°	483.2	487.4	495.6	504.7	514.8	522.5	532.0	543.0	554.5	568.2	583.4
12.5°	465.6	469.6	479.6	488.9	499.3	507.8	518.9	530.0	545.3	560.1	577.4
15°	431.4	441.7	453.1	464.1	476.6	486.9	500.2	511.7	526.2	547.0	566.9
17.5°	393.3	404.2	418.6	435.6	452.2	464.9	478.5	492.7	510.1	531.3	554.2
20°	371.1	380.0	395.8	414.7	434.0	451.7	464.1	479.9	497.9	520.8	544.4
22.5°	354.6	362.0	374.4	393.2	414.1	434.6	450.6	466.2	485.9	509.0	534.7
25°	329.6	337.7	348.5	361.3	385.3	407.0	427.8	445.8	466.8	489.7	518.4
27.5°	308.8	315.9	325.8	339.2	355.3	379.2	404.5	424.9	446.5	471.1	499.8
30°	296.6	302.4	310.4	324.1	339.4	360.9	386.5	410.4	432.1	457.7	487.6
32.5°	283.8	289.9	297.8	308.6	325.1	343.2	368.7	394.9	418.0	444.1	473.4
35°	266.7	271.6	278.7	289.6	304.5	320.2	343.0	370.0	394.4	422.3	450.3
37.5°	249.4	255.1	260.7	270.5	282.7	299.6	318.2	345.9	372.8	398.4	425.7
40°	239.7	243.1	249.2	257.2	270.0	285.1	302.6	329.6	356.6	381.9	409.4
42.5°	228.8	232.6	237.8	245.7	257.2	272.0	289.0	312.4	340.5	365.1	390.1
45°	213.7	215.8	221.1	227.7	237.3	252.2	267.9	288.7	315.3	338.7	360.6
47.5°	198.3	200.3	203.5	209.6	220.4	232.3	247.0	265.7	288.9	312.4	330.9
50°	187.8	189.6	192.7	198.3	207.9	219.6	234.2	251.0	271.8	294.2	309.7
52.5°	177.3	178.2	181.2	187.6	195.7	207.2	220.3	235.7	255.1	273.8	289.5
55°	160.6	162.8	164.7	169.5	177.1	188.1	199.9	214.4	229.4	245.2	258.6
57.5°	143.2	145.5	148.2	152.5	158.5	168.7	179.3	191.1	204.0	217.0	228.3
60°	131.7	133.8	136.2	141.0	146.5	154.6	166.1	176.4	186.2	198.1	209.3
62.5°	120.4	122.6	125.3	129.2	134.4	142.2	151.8	160.7	170.9	181.3	189.7
65°	103.7	105.4	107.6	111.2	116.1	123.1	131.0	137.9	147.0	154.6	162.3
67.5°	85.4	88.7	91.4	94.3	98.6	105.0	110.8	117.4	123.6	129.3	136.2
70°	73.4	77.0	79.6	82.7	86.7	92.3	97.8	102.3	107.3	112.8	119.1
72.5°	63.2	66.0	68.2	71.4	75.1	80.2	85.3	89.1	93.2	96.9	103.0
75°	50.0	51.1	52.6	55.2	58.6	62.4	66.4	69.8	72.2	75.5	79.8
77.5°	35.9	38.2	39.2	41.0	43.4	45.7	48.5	51.3	53.6	54.7	58.1
80°	27.5	28.5	29.4	32.0	33.4	35.9	37.8	40.4	41.3	42.5	45.6
82.5°	21.4	21.9	22.5	23.2	24.1	26.5	28.4	30.1	31.0	31.4	33.8
85°	12.4	12.6	12.9	13.1	13.4	13.4	14.3	15.6	17.2	17.2	18.0
87.5°	11.3	11.1	10.6	9.8	9.7	9.1	8.7	7.9	7.8	7.6	7.4
90°	35.5	33.5	30.8	28.1	25.3	22.7	19.5	15.8	12.0	8.3	4.5
92.5°	61.5	60.3	58.4	56.6	54.6	52.7	49.7	45.3	41.1	36.9	32.6
95°	116.7	115.7	113.4	111.0	108.7	106.2	103.5	100.5	97.5	94.4	91.4
97.5°	184.2	183.0	180.3	177.4	174.7	172.0	169.4	166.9	164.4	162.0	159.6
100°	233.7	233.0	229.9	226.9	223.9	220.8	218.6	217.2	215.9	214.5	213.2
102.5°	285.1	284.2	281.3	278.6	275.8	273.1	271.4	270.8	270.3	269.7	269.2
105°	363.5	362.4	361.0	359.7	358.3	357.0	356.2	355.8	355.5	355.2	354.8
107.5°	448.3	447.4	447.2	447.0	446.8	446.6	446.3	445.9	445.5	445.0	444.6
110°	506.3	507.1	507.4	507.8	508.1	508.5	508.3	507.6	506.9	506.2	505.5



TEST NUMBER: P333032-840

CATALOG NUMBER: S124RDIW-S350D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	566.6	566.7	567.3	567.9	568.6	569.2	569.5	569.3	569.2	569.1	568.9
115°	660.6	660.9	661.6	662.2	662.9	663.6	663.9	663.9	663.9	663.9	663.9
117.5°	751.3	752.6	753.0	753.5	754.0	754.5	754.6	754.3	754.0	753.7	753.5
120°	812.9	814.7	815.7	816.7	817.7	818.7	818.5	817.2	815.9	814.5	813.1
122.5°	874.4	875.6	876.1	876.5	877.0	877.5	877.4	876.9	876.4	875.8	875.3
125°	964.7	965.4	965.7	966.0	966.4	966.7	966.9	966.9	966.9	966.9	966.9
127.5°	1051.5	1052.2	1052.8	1053.3	1053.8	1054.4	1054.1	1053.1	1052.1	1051.1	1050.1
130°	1112.5	1113.1	1113.1	1113.1	1113.1	1113.1	1112.6	1111.6	1110.5	1109.5	1108.5
132.5°	1169.7	1170.3	1170.6	1170.9	1171.1	1171.4	1171.2	1170.4	1169.7	1169.0	1168.2
135°	1255.6	1256.3	1256.3	1256.3	1256.3	1256.3	1255.3	1253.2	1251.1	1249.1	1247.1
137.5°	1338.8	1339.7	1339.2	1338.6	1338.1	1337.6	1336.8	1335.8	1334.8	1333.9	1333.0
140°	1392.9	1393.3	1393.3	1393.3	1393.3	1393.3	1392.9	1392.3	1391.6	1390.9	1390.3
142.5°	1444.4	1444.4	1444.7	1445.0	1445.2	1445.5	1445.3	1444.6	1444.0	1443.3	1442.6
145°	1522.4	1522.7	1522.4	1522.1	1521.7	1521.4	1520.6	1519.1	1517.8	1516.4	1515.1
147.5°	1592.8	1593.1	1593.4	1593.6	1593.9	1594.2	1593.5	1591.9	1590.2	1588.6	1587.0
150°	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9	1636.3	1634.9	1633.6	1632.1	1630.8
152.5°	1677.9	1677.1	1676.9	1676.6	1676.3	1676.1	1675.5	1674.7	1673.9	1673.0	1672.2
155°	1735.8	1734.3	1734.7	1735.0	1735.4	1735.8	1735.9	1735.9	1735.9	1735.9	1735.9
157.5°	1787.5	1786.5	1786.6	1786.6	1786.7	1786.8	1787.1	1787.7	1788.3	1788.9	1789.5
160°	1819.2	1818.2	1818.5	1818.8	1819.2	1819.5	1819.8	1820.2	1820.5	1820.8	1821.2
162.5°	1846.7	1844.9	1845.2	1845.6	1845.9	1846.2	1846.8	1847.8	1848.7	1849.6	1850.4
165°	1884.1	1882.1	1882.8	1883.4	1884.1	1884.8	1885.6	1886.6	1887.6	1888.6	1889.7
167.5°	1915.8	1913.8	1913.7	1913.6	1913.6	1913.5	1914.2	1915.6	1917.0	1918.4	1919.9
170°	1932.8	1930.8	1930.5	1930.2	1929.8	1929.4	1930.2	1931.8	1933.5	1935.2	1936.9
172.5°	1945.3	1943.0	1942.9	1942.9	1942.8	1942.7	1943.4	1944.8	1946.2	1947.6	1949.0
175°	1959.0	1956.7	1957.0	1957.3	1957.7	1958.0	1959.0	1960.8	1962.5	1964.1	1965.8
177.5°	1967.1	1965.2	1965.2	1965.2	1965.2	1965.2	1965.9	1967.2	1968.6	1969.9	1971.3
180°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8



TEST NUMBER: P333032-840

CATALOG NUMBER: S124RDIW-S350D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2
2.5°	596.8	598.5	600.5	604.1	607.1	608.5	611.2	613.1	612.5	615.2	619.8
5°	599.2	605.6	613.1	620.7	629.2	636.4	642.2	647.9	652.5	657.9	666.1
7.5°	598.7	610.3	622.8	636.4	650.6	662.8	674.0	685.5	695.7	706.8	721.4
10°	597.2	612.6	628.1	646.0	664.0	681.0	696.2	710.5	724.2	738.7	757.2
12.5°	595.5	613.1	631.9	653.5	675.8	696.2	714.2	734.9	751.9	770.7	791.9
15°	587.9	611.6	637.2	665.1	692.0	719.4	744.0	769.3	793.0	815.5	842.2
17.5°	579.3	606.5	636.7	669.7	701.9	735.3	764.6	796.5	820.6	850.8	875.7
20°	572.2	601.6	633.8	670.9	707.4	744.5	776.8	809.3	836.5	866.9	898.4
22.5°	563.6	595.8	630.8	669.1	707.4	747.9	783.7	816.0	849.7	883.8	916.4
25°	549.7	583.2	620.3	662.3	706.3	747.6	785.9	826.0	862.3	899.4	928.6
27.5°	532.7	567.8	606.8	650.3	695.4	737.7	782.7	825.6	862.1	897.8	923.2
30°	519.1	556.1	593.7	637.6	684.5	729.9	778.2	821.0	859.5	891.5	905.8
32.5°	505.1	540.3	579.0	623.5	671.5	720.3	768.2	812.0	847.6	866.8	867.2
35°	480.9	513.8	554.0	597.7	647.0	700.0	748.5	791.5	813.3	815.0	791.5
37.5°	454.4	484.6	522.5	566.3	620.3	673.1	722.6	751.2	758.5	734.2	690.9
40°	435.5	463.4	500.0	544.9	598.4	653.0	698.1	719.1	711.6	672.1	623.8
42.5°	415.6	441.6	476.9	521.2	574.9	630.1	668.5	679.7	659.5	614.0	557.4
45°	383.1	407.0	441.9	486.7	538.3	589.9	619.0	613.3	579.6	525.5	462.2
47.5°	349.3	372.4	403.8	445.1	498.1	542.6	562.3	545.0	497.1	437.7	386.2
50°	327.0	350.6	379.5	419.0	467.3	510.3	522.9	496.7	443.3	386.3	338.9
52.5°	305.0	325.2	353.6	391.6	437.8	474.1	480.9	450.6	395.6	344.4	302.4
55°	271.6	289.9	313.8	349.6	389.6	420.4	416.8	377.9	327.9	284.2	251.2
57.5°	239.1	253.0	275.1	308.7	343.8	364.5	351.3	318.1	271.6	235.7	207.9
60°	217.7	230.7	251.2	280.5	311.4	323.2	312.1	276.1	239.2	206.5	183.1
62.5°	197.4	208.8	226.5	253.8	278.7	285.7	273.9	242.4	209.2	181.3	161.9
65°	168.0	178.5	193.6	213.0	230.1	233.5	225.9	193.6	168.5	145.1	131.7
67.5°	141.3	148.1	160.0	176.6	185.8	187.7	173.0	152.7	130.6	116.2	106.1
70°	123.3	128.2	139.1	148.1	155.6	155.8	142.2	125.9	109.0	97.3	89.9
72.5°	105.9	110.5	118.9	125.0	130.8	128.9	116.4	103.6	89.9	81.0	75.5
75°	81.7	85.8	90.1	93.0	93.0	90.6	81.5	71.9	64.0	58.8	57.2
77.5°	59.4	62.7	64.2	63.7	62.9	59.2	53.4	47.2	44.3	41.9	40.6
80°	46.7	48.1	48.5	47.4	45.8	41.6	37.8	35.1	32.5	31.5	31.1
82.5°	34.5	35.9	34.5	34.9	31.7	28.2	26.1	25.1	24.1	23.7	23.2
85°	18.4	18.2	17.7	16.5	14.3	13.8	13.6	13.4	12.9	13.1	12.6
87.5°	8.0	8.2	8.1	8.7	9.3	9.5	10.2	10.7	11.3	11.5	12.3
90°	8.3	12.0	15.8	19.5	22.7	25.3	28.1	30.8	33.5	35.5	37.6
92.5°	36.9	41.1	45.3	49.7	52.7	54.6	56.6	58.4	60.3	61.5	62.7
95°	94.4	97.5	100.5	103.5	106.2	108.7	111.0	113.4	115.7	116.7	117.8
97.5°	162.0	164.4	166.9	169.4	172.0	174.7	177.4	180.3	183.0	184.2	185.5
100°	214.5	215.9	217.2	218.6	220.8	223.9	226.9	229.9	233.0	233.7	234.3
102.5°	269.7	270.3	270.8	271.4	273.1	275.8	278.6	281.3	284.2	285.1	286.0
105°	355.2	355.5	355.8	356.2	357.0	358.3	359.7	361.0	362.4	363.5	364.5
107.5°	445.0	445.5	445.9	446.3	446.6	446.8	447.0	447.2	447.4	448.3	449.3
110°	506.2	506.9	507.6	508.3	508.5	508.1	507.8	507.4	507.1	506.3	505.7



TEST NUMBER: P333032-840

CATALOG NUMBER: S124RDIW-S350D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	569.1	569.2	569.3	569.5	569.2	568.6	567.9	567.3	566.7	566.6	566.4
115°	663.9	663.9	663.9	663.9	663.6	662.9	662.2	661.6	660.9	660.6	660.1
117.5°	753.7	754.0	754.3	754.6	754.5	754.0	753.5	753.0	752.6	751.3	750.2
120°	814.5	815.9	817.2	818.5	818.7	817.7	816.7	815.7	814.7	812.9	811.2
122.5°	875.8	876.4	876.9	877.4	877.5	877.0	876.5	876.1	875.6	874.4	873.2
125°	966.9	966.9	966.9	966.9	966.7	966.4	966.0	965.7	965.4	964.7	964.0
127.5°	1051.1	1052.1	1053.1	1054.1	1054.4	1053.8	1053.3	1052.8	1052.2	1051.5	1050.9
130°	1109.5	1110.5	1111.6	1112.6	1113.1	1113.1	1113.1	1113.1	1113.1	1112.5	1111.8
132.5°	1169.0	1169.7	1170.4	1171.2	1171.4	1171.1	1170.9	1170.6	1170.3	1169.7	1169.0
135°	1249.1	1251.1	1253.2	1255.3	1256.3	1256.3	1256.3	1256.3	1256.3	1255.6	1254.9
137.5°	1333.9	1334.8	1335.8	1336.8	1337.6	1338.1	1338.6	1339.2	1339.7	1338.8	1338.0
140°	1390.9	1391.6	1392.3	1392.9	1393.3	1393.3	1393.3	1393.3	1393.3	1392.9	1392.6
142.5°	1443.3	1444.0	1444.6	1445.3	1445.5	1445.2	1445.0	1444.7	1444.4	1444.4	1444.3
145°	1516.4	1517.8	1519.1	1520.6	1521.4	1521.7	1522.1	1522.4	1522.7	1522.4	1522.1
147.5°	1588.6	1590.2	1591.9	1593.5	1594.2	1593.9	1593.6	1593.4	1593.1	1592.8	1592.6
150°	1632.1	1633.6	1634.9	1636.3	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9
152.5°	1673.0	1673.9	1674.7	1675.5	1676.1	1676.3	1676.6	1676.9	1677.1	1677.9	1678.7
155°	1735.9	1735.9	1735.9	1735.9	1735.8	1735.4	1735.0	1734.7	1734.3	1735.8	1737.1
157.5°	1788.9	1788.3	1787.7	1787.1	1786.8	1786.7	1786.6	1786.6	1786.5	1787.5	1788.5
160°	1820.8	1820.5	1820.2	1819.8	1819.5	1819.2	1818.8	1818.5	1818.2	1819.2	1820.2
162.5°	1849.6	1848.7	1847.8	1846.8	1846.2	1845.9	1845.6	1845.2	1844.9	1846.7	1848.6
165°	1888.6	1887.6	1886.6	1885.6	1884.8	1884.1	1883.4	1882.8	1882.1	1884.1	1886.1
167.5°	1918.4	1917.0	1915.6	1914.2	1913.5	1913.6	1913.6	1913.7	1913.8	1915.8	1917.8
170°	1935.2	1933.5	1931.8	1930.2	1929.4	1929.8	1930.2	1930.5	1930.8	1932.8	1934.9
172.5°	1947.6	1946.2	1944.8	1943.4	1942.7	1942.8	1942.9	1942.9	1943.0	1945.3	1947.6
175°	1964.1	1962.5	1960.8	1959.0	1958.0	1957.7	1957.3	1957.0	1956.7	1959.0	1961.5
177.5°	1969.9	1968.6	1967.2	1965.9	1965.2	1965.2	1965.2	1965.2	1965.2	1967.1	1969.0
180°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8



TEST NUMBER: P333032-840

CATALOG NUMBER: S124RDIW-S350D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	593.2	593.2	593.2	593.2	593.2	593.2	593.2
2.5°	622.3	623.0	623.6	625.5	625.7	627.4	625.7
5°	673.8	677.1	682.4	687.6	688.1	691.5	685.5
7.5°	731.4	739.2	744.1	752.6	755.9	758.0	754.6
10°	771.2	778.4	791.1	797.3	803.5	804.5	801.6
12.5°	809.7	821.0	831.0	842.8	842.5	850.9	847.9
15°	860.9	872.6	886.5	899.6	904.3	904.3	908.2
17.5°	897.4	918.9	933.2	943.5	954.8	956.7	955.4
20°	922.1	945.2	960.6	973.9	981.6	983.7	983.7
22.5°	940.4	960.2	975.1	987.1	993.4	995.9	995.2
25°	953.1	970.1	979.2	982.8	984.4	984.0	979.5
27.5°	935.7	934.9	929.3	918.3	910.0	904.9	899.2
30°	902.5	890.0	875.7	859.9	839.6	824.0	819.3
32.5°	852.9	825.1	800.7	774.5	752.7	737.1	730.5
35°	757.2	713.0	676.8	645.3	622.4	608.0	603.2
37.5°	643.5	600.7	556.0	525.4	506.3	491.9	486.6
40°	571.2	524.6	485.6	457.0	437.4	423.2	423.0
42.5°	505.2	460.7	424.0	403.4	382.3	372.9	372.9
45°	413.7	378.1	347.0	330.7	318.1	310.4	308.3
47.5°	342.5	313.1	292.4	279.4	269.1	264.3	261.1
50°	302.6	276.8	260.2	249.0	243.3	237.1	236.6
52.5°	269.3	248.4	235.6	226.5	219.2	215.5	215.6
55°	226.3	209.8	200.8	193.8	188.1	185.2	184.0
57.5°	190.7	178.3	171.7	165.3	162.9	160.7	160.1
60°	168.5	160.2	153.9	148.9	145.3	144.6	144.3
62.5°	150.2	141.4	137.1	133.2	130.6	129.5	129.1
65°	123.8	117.3	113.5	110.4	109.5	107.8	107.6
67.5°	99.8	95.9	93.4	91.3	90.0	89.9	89.9
70°	85.1	82.9	80.8	79.6	78.9	78.4	78.4
72.5°	72.5	70.9	69.1	68.5	68.4	67.9	67.7
75°	55.2	53.5	53.8	52.6	51.6	50.4	49.7
77.5°	39.2	38.0	37.7	37.6	36.8	36.7	37.0
80°	30.4	29.2	28.9	29.2	28.9	28.2	28.2
82.5°	23.1	22.1	21.8	21.7	21.5	21.7	21.3
85°	12.4	11.9	11.9	11.9	12.4	12.2	11.9
87.5°	12.3	12.5	13.0	12.9	13.0	13.0	13.3
90°	39.6	41.6	43.0	43.6	44.3	45.0	45.6
92.5°	63.9	65.1	65.9	66.3	66.8	67.2	67.6
95°	118.8	119.8	120.3	120.3	120.3	120.3	120.3
97.5°	186.7	187.9	188.5	188.5	188.5	188.5	188.5
100°	235.0	235.7	236.0	236.0	236.0	236.0	236.0
102.5°	287.0	287.9	288.5	288.8	289.1	289.3	289.6
105°	365.5	366.5	367.5	368.5	369.5	370.5	371.5
107.5°	450.2	451.2	451.6	451.5	451.5	451.4	451.3
110°	505.0	504.3	504.5	505.5	506.5	507.6	508.6



TEST NUMBER: P333032-840

CATALOG NUMBER: S124RDIW-S350D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	566.3	566.2	566.2	566.4	566.6	566.8	567.0
115°	659.8	659.5	659.1	658.8	658.5	658.1	657.8
117.5°	749.1	747.9	747.0	746.3	745.7	745.0	744.3
120°	809.6	807.9	807.4	808.1	808.7	809.4	810.1
122.5°	872.1	871.0	869.8	868.6	867.4	866.2	864.9
125°	963.4	962.7	962.0	961.3	960.7	960.0	959.3
127.5°	1050.2	1049.5	1048.8	1048.3	1047.8	1047.2	1046.7
130°	1111.1	1110.3	1109.3	1108.0	1106.7	1105.3	1104.0
132.5°	1168.3	1167.6	1167.0	1166.5	1166.0	1165.4	1164.9
135°	1254.3	1253.5	1252.6	1251.6	1250.6	1249.6	1248.6
137.5°	1337.1	1336.2	1335.8	1336.1	1336.3	1336.5	1336.7
140°	1392.3	1391.9	1391.6	1391.3	1390.9	1390.6	1390.3
142.5°	1444.2	1444.2	1444.1	1444.0	1444.0	1443.9	1443.8
145°	1521.7	1521.4	1520.7	1519.6	1518.6	1517.6	1516.6
147.5°	1592.3	1592.0	1591.6	1591.3	1591.0	1590.6	1590.3
150°	1636.9	1636.9	1636.8	1636.4	1636.1	1635.8	1635.4
152.5°	1679.5	1680.3	1680.3	1679.4	1678.6	1677.7	1676.8
155°	1738.4	1739.8	1739.8	1738.4	1737.1	1735.8	1734.3
157.5°	1789.5	1790.5	1790.4	1789.3	1788.2	1787.0	1785.8
160°	1821.2	1822.2	1821.8	1820.2	1818.5	1816.7	1815.0
162.5°	1850.4	1852.2	1852.3	1850.6	1849.0	1847.2	1845.5
165°	1888.1	1890.2	1890.6	1889.2	1887.8	1886.4	1885.1
167.5°	1919.9	1921.9	1921.9	1919.8	1917.6	1915.5	1913.4
170°	1936.9	1938.9	1938.7	1936.4	1934.0	1931.7	1929.2
172.5°	1949.8	1952.2	1952.2	1949.7	1947.4	1945.0	1942.7
175°	1963.8	1966.2	1966.2	1963.8	1961.5	1959.0	1956.7
177.5°	1970.9	1972.8	1972.7	1970.4	1968.3	1966.2	1964.0
180°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8

(END OF REPORT)