

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333739-927

Luminaire Tested: **S125RDIW-S1270D1560U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333739-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1270D1560U927-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8150.6 lumens
Efficiency: N/A
Efficacy: 98.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333739-927

CATALOG NUMBER: S125RDIW-S1270D1560U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333739-927

CATALOG NUMBER: S125RDIW-S1270D1560U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40
2	89	82	76	71	81	75	70	66	63	60	56	52	50	47	42	41	39	34
3	81	72	65	59	74	66	60	55	56	51	48	47	43	40	38	35	33	29
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29	25
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	31	28	25	22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22	19
7	58	46	38	33	53	43	36	31	37	31	27	31	27	23	25	22	20	17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	18	16	14
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10561	10561	10561
5°	10585	10466	10529
10°	10506	10368	10368
15°	10380	10158	10075
20°	10221	9864	9745
25°	10033	9576	9365
30°	9801	9238	8944
35°	9563	8891	8472
40°	9340	8528	8008
45°	9070	8122	7501
50°	8799	7681	6974
55°	8483	7260	6411
60°	8169	6748	5807
65°	7795	6154	5115
70°	7370	5410	4409
75°	6780	4561	3666
80°	5973	3582	3080
85°	5039	2927	2749



TEST NUMBER: P333739-927

CATALOG NUMBER: S125RDIW-S1270D1560U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.8	1.9
10°-20°	429.7	5.3
20°-30°	623.1	7.6
30°-40°	710.2	8.7
40°-50°	692.3	8.5
50°-60°	582.7	7.1
60°-70°	408.5	5.0
70°-80°	210.0	2.6
80°-90°	56.4	0.7
90°-100°	102.8	1.3
100°-110°	303.6	3.7
110°-120°	514.3	6.3
120°-130°	676.9	8.3
130°-140°	758.4	9.3
140°-150°	743.3	9.1
150°-160°	624.3	7.7
160°-170°	415.0	5.1
170°-180°	145.2	1.8
0°-30°	1206.6	14.8
0°-40°	1916.8	23.5
0°-60°	3191.8	39.2
0°-90°	3866.6	47.4
90°-120°	920.8	11.3
90°-150°	3099.4	38.0
90°-180°	4284.0	52.6
0°-180°	8150.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1635	1635	1635	1635	1635	
5°	1633	1627	1614	1626	1624	155
15°	1552	1544	1519	1517	1507	437
25°	1408	1388	1344	1328	1314	648
35°	1213	1182	1128	1093	1074	759
45°	993	955	889	842	821	766
55°	753	712	645	591	569	674
65°	510	467	403	355	335	505
75°	272	234	183	157	147	288
85°	68	47	40	38	37	76
90°	1	11	19	25	29	7
95°	78	81	92	100	103	83
105°	272	278	286	292	296	291
115°	515	520	522	521	520	509
125°	752	758	760	758	756	673
135°	977	984	986	985	981	753
145°	1184	1189	1192	1192	1189	740
155°	1355	1355	1356	1360	1355	624
165°	1473	1471	1472	1476	1470	415
175°	1532	1527	1527	1533	1526	145
180°	1535	1535	1535	1535	1535	



TEST NUMBER: P333739-927

CATALOG NUMBER: S125RDIW-S1270D1560U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3
2.5°	1638.2	1637.6	1636.9	1636.3	1635.6	1634.2	1632.0	1629.8	1627.6	1625.4	1627.6
5°	1632.8	1631.7	1630.6	1629.5	1628.4	1626.4	1623.3	1620.3	1617.3	1614.3	1617.0
7.5°	1616.8	1615.7	1614.7	1613.6	1612.6	1610.3	1606.6	1603.0	1599.4	1595.8	1597.7
10°	1602.0	1601.1	1600.3	1599.5	1598.6	1596.3	1592.4	1588.6	1584.8	1581.0	1581.8
12.5°	1585.2	1584.1	1583.0	1582.0	1581.0	1577.9	1572.7	1567.6	1562.3	1557.2	1557.8
15°	1552.5	1550.9	1549.3	1547.6	1545.9	1542.2	1536.4	1530.7	1525.0	1519.2	1518.9
17.5°	1515.7	1513.2	1510.7	1508.2	1505.6	1500.7	1493.5	1486.2	1479.0	1471.7	1470.4
20°	1487.1	1484.3	1481.5	1478.8	1476.1	1470.3	1461.6	1452.8	1444.0	1435.2	1433.8
22.5°	1455.5	1452.7	1449.9	1447.2	1444.5	1438.5	1429.3	1420.1	1410.8	1401.6	1398.9
25°	1408.0	1403.9	1399.8	1395.7	1391.5	1384.4	1374.3	1364.1	1353.9	1343.8	1340.2
27.5°	1353.7	1348.7	1343.7	1338.7	1333.7	1325.8	1314.9	1304.0	1293.2	1282.3	1277.3
30°	1314.2	1308.9	1303.7	1298.5	1293.3	1284.9	1273.4	1261.9	1250.3	1238.8	1232.5
32.5°	1275.7	1269.6	1263.5	1257.4	1251.3	1242.3	1230.6	1218.9	1207.0	1195.3	1188.4
35°	1212.9	1206.3	1199.7	1193.1	1186.5	1177.0	1164.7	1152.4	1140.0	1127.7	1119.7
37.5°	1151.4	1143.4	1135.4	1127.4	1119.3	1108.9	1096.2	1083.5	1070.7	1058.0	1048.5
40°	1107.9	1099.6	1091.4	1083.2	1075.0	1064.2	1051.1	1037.9	1024.7	1011.5	1001.2
42.5°	1062.5	1054.0	1045.5	1037.0	1028.6	1017.6	1004.0	990.4	976.8	963.1	953.2
45°	993.0	985.1	977.1	969.2	961.2	949.7	934.5	919.5	904.4	889.3	878.3
47.5°	921.1	912.8	904.4	896.0	887.6	875.8	860.5	845.3	830.1	814.9	803.6
50°	875.7	866.6	857.5	848.5	839.5	827.1	811.4	795.8	780.1	764.5	753.0
52.5°	826.2	817.0	807.7	798.4	789.2	777.1	762.4	747.7	732.8	718.1	705.7
55°	753.4	744.7	735.9	727.1	718.3	706.2	690.9	675.5	660.1	644.8	632.4
57.5°	679.8	670.4	661.0	651.6	642.2	630.2	615.4	600.5	585.7	570.8	558.8
60°	632.4	622.7	613.1	603.6	594.0	581.7	566.9	552.1	537.3	522.4	510.4
62.5°	582.0	572.8	563.6	554.4	545.3	533.2	518.2	503.1	488.1	473.0	461.8
65°	510.1	500.7	491.5	482.1	472.8	460.8	446.3	431.7	417.2	402.7	391.7
67.5°	438.7	429.4	420.0	410.7	401.4	389.8	375.8	361.9	347.9	334.0	323.9
70°	390.3	381.0	371.6	362.3	353.0	341.4	327.7	314.0	300.2	286.5	278.1
72.5°	342.9	333.7	324.6	315.5	306.4	295.4	282.6	269.7	256.9	244.1	236.2
75°	271.7	263.5	255.2	247.0	238.8	228.9	217.4	205.9	194.3	182.8	176.7
77.5°	201.1	194.5	187.9	181.3	174.8	166.8	157.6	148.4	139.2	129.9	125.7
80°	160.6	154.0	147.4	140.8	134.2	127.1	119.4	111.7	104.0	96.3	93.9
82.5°	121.0	115.1	109.2	103.2	97.4	91.7	86.4	81.2	75.9	70.7	69.5
85°	68.0	63.0	58.1	53.1	48.2	45.0	43.6	42.3	40.9	39.5	39.2
87.5°	23.0	21.9	20.8	19.6	18.5	18.1	18.2	18.4	18.5	18.6	18.9
90°	1.2	3.3	5.5	7.6	9.7	11.6	13.5	15.4	17.3	19.1	20.4
92.5°	28.9	30.4	31.9	33.4	34.9	36.8	39.1	41.3	43.6	45.9	47.6
95°	77.6	78.2	78.7	79.2	79.8	81.4	84.1	86.7	89.4	92.0	93.9
97.5°	129.0	129.2	129.4	129.7	129.9	131.8	135.5	139.2	142.8	146.5	148.2
100°	167.2	167.2	167.2	167.2	167.2	169.0	172.5	175.9	179.4	182.8	185.2
102.5°	208.3	209.5	210.5	211.5	212.6	214.0	215.8	217.5	219.3	221.0	223.6
105°	272.4	273.7	275.0	276.4	277.7	279.2	280.7	282.3	283.9	285.6	287.2
107.5°	343.1	344.4	345.8	347.1	348.4	349.7	350.9	352.1	353.4	354.6	355.4
110°	391.9	393.2	394.5	395.9	397.2	398.2	399.0	399.8	400.6	401.4	402.2



TEST NUMBER: P333739-927

CATALOG NUMBER: S125RDIW-S1270D1560U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	441.6	442.3	443.0	443.6	444.3	445.2	446.2	447.2	448.2	449.2	449.6
115°	514.9	516.0	517.1	518.1	519.2	520.0	520.5	521.0	521.6	522.1	521.8
117.5°	588.5	589.0	589.5	589.9	590.4	590.9	591.4	591.8	592.3	592.9	593.0
120°	634.4	635.7	637.1	638.4	639.7	640.5	640.8	641.0	641.3	641.6	641.6
122.5°	684.1	684.6	685.1	685.6	686.0	686.6	687.3	688.0	688.6	689.4	689.1
125°	751.5	753.0	754.7	756.3	757.9	758.8	759.1	759.3	759.6	759.9	759.3
127.5°	823.2	824.1	825.0	825.9	826.8	827.4	827.8	828.1	828.4	828.7	828.4
130°	866.2	867.5	868.9	870.1	871.5	872.4	873.0	873.5	874.0	874.6	874.3
132.5°	909.2	911.4	913.5	915.8	917.9	918.9	918.9	918.7	918.6	918.5	918.2
135°	977.3	978.9	980.5	982.1	983.7	984.6	984.8	985.2	985.4	985.6	985.6
137.5°	1041.3	1042.9	1044.4	1045.9	1047.5	1048.5	1049.2	1049.7	1050.3	1050.9	1051.2
140°	1082.4	1083.8	1085.1	1086.4	1087.7	1088.8	1089.6	1090.4	1091.2	1092.0	1092.5
142.5°	1123.6	1124.7	1125.8	1126.9	1128.0	1129.0	1130.0	1131.1	1132.1	1133.1	1133.4
145°	1184.0	1185.0	1186.1	1187.2	1188.3	1189.1	1189.9	1190.7	1191.5	1192.3	1192.3
147.5°	1239.9	1240.5	1241.0	1241.7	1242.2	1242.9	1243.5	1244.1	1244.8	1245.4	1246.0
150°	1277.2	1276.9	1276.7	1276.4	1276.1	1276.5	1277.6	1278.7	1279.7	1280.8	1280.8
152.5°	1307.7	1308.1	1308.5	1308.8	1309.2	1309.6	1310.1	1310.5	1310.9	1311.4	1312.0
155°	1354.9	1354.9	1354.9	1354.9	1354.9	1354.9	1355.3	1355.5	1355.7	1356.1	1357.1
157.5°	1396.9	1396.3	1395.7	1395.1	1394.6	1394.4	1394.6	1395.0	1395.2	1395.4	1396.5
160°	1421.7	1420.9	1420.1	1419.4	1418.6	1418.3	1418.6	1418.8	1419.1	1419.4	1420.4
162.5°	1443.8	1443.1	1442.6	1442.0	1441.4	1441.1	1441.1	1441.2	1441.3	1441.3	1442.6
165°	1473.1	1472.6	1472.0	1471.6	1471.0	1470.8	1471.2	1471.4	1471.6	1472.0	1473.0
167.5°	1497.9	1496.9	1495.9	1494.8	1493.7	1493.2	1493.2	1493.2	1493.2	1493.2	1494.8
170°	1511.3	1510.3	1509.2	1508.2	1507.1	1506.6	1506.6	1506.6	1506.6	1506.6	1508.2
172.5°	1520.9	1519.9	1518.8	1517.7	1516.6	1516.2	1516.2	1516.2	1516.2	1516.2	1517.7
175°	1531.7	1530.6	1529.5	1528.4	1527.4	1526.9	1526.9	1526.9	1526.9	1526.9	1528.4
177.5°	1537.2	1536.3	1535.5	1534.6	1533.7	1533.2	1533.0	1532.8	1532.6	1532.4	1533.7
180°	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2



TEST NUMBER: P333739-927

CATALOG NUMBER: S125RDIW-S1270D1560U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3
2.5°	1629.8	1632.0	1634.2	1635.1	1635.0	1634.7	1634.5	1634.3
5°	1619.8	1622.5	1625.2	1626.4	1625.8	1625.2	1624.7	1624.1
7.5°	1599.6	1601.6	1603.5	1604.1	1603.5	1602.9	1602.3	1601.7
10°	1582.5	1583.4	1584.2	1584.2	1583.4	1582.5	1581.8	1581.0
12.5°	1558.5	1559.0	1559.6	1559.3	1558.1	1556.8	1555.5	1554.3
15°	1518.6	1518.4	1518.1	1516.7	1514.3	1511.8	1509.3	1506.8
17.5°	1469.0	1467.6	1466.3	1464.6	1462.5	1460.5	1458.5	1456.4
20°	1432.4	1431.1	1429.7	1427.8	1425.3	1422.8	1420.4	1417.9
22.5°	1396.2	1393.5	1390.8	1388.5	1386.5	1384.4	1382.4	1380.4
25°	1336.6	1333.1	1329.5	1326.2	1323.2	1320.2	1317.2	1314.2
27.5°	1272.3	1267.3	1262.3	1258.4	1255.5	1252.5	1249.6	1246.7
30°	1226.2	1219.9	1213.5	1209.2	1206.7	1204.2	1201.7	1199.3
32.5°	1181.4	1174.4	1167.4	1162.4	1159.3	1156.1	1153.0	1149.9
35°	1111.7	1103.7	1095.8	1089.9	1086.1	1082.2	1078.4	1074.5
37.5°	1038.9	1029.4	1019.8	1013.1	1009.4	1005.7	1002.0	998.2
40°	990.7	980.2	969.9	963.0	959.6	956.4	953.1	949.8
42.5°	943.2	933.2	923.2	915.8	910.9	906.1	901.3	896.4
45°	867.3	856.3	845.3	837.8	833.7	829.6	825.5	821.3
47.5°	792.3	781.0	769.7	761.8	757.2	752.7	748.1	743.5
50°	741.5	729.9	718.4	710.6	706.5	702.3	698.2	694.1
52.5°	693.2	680.9	668.4	660.2	656.1	652.0	647.8	643.7
55°	620.0	607.7	595.3	586.9	582.6	578.1	573.8	569.4
57.5°	546.7	534.6	522.5	514.6	510.6	506.8	502.9	499.0
60°	498.3	486.2	474.1	466.0	461.9	457.8	453.7	449.6
62.5°	450.7	439.4	428.3	420.6	416.5	412.3	408.2	404.1
65°	380.7	369.7	358.7	351.2	347.1	342.9	338.8	334.7
67.5°	313.9	303.8	293.8	287.1	283.8	280.5	277.3	273.9
70°	269.5	261.0	252.5	246.6	243.3	240.0	236.7	233.5
72.5°	228.4	220.5	212.6	207.6	205.4	203.3	201.1	198.8
75°	170.7	164.7	158.7	154.6	152.7	150.8	148.9	146.9
77.5°	121.4	117.2	113.0	110.2	108.8	107.3	105.9	104.5
80°	91.4	89.0	86.4	84.9	84.4	83.8	83.3	82.8
82.5°	68.4	67.2	66.1	65.3	65.0	64.6	64.3	64.0
85°	39.0	38.7	38.4	38.2	37.9	37.6	37.3	37.1
87.5°	19.2	19.4	19.7	19.8	19.7	19.7	19.6	19.6
90°	21.8	23.1	24.4	25.5	26.3	27.1	27.9	28.7
92.5°	49.4	51.1	52.9	54.0	54.7	55.2	55.8	56.4
95°	95.7	97.6	99.4	100.6	101.2	101.7	102.2	102.7
97.5°	150.0	151.7	153.4	154.6	154.9	155.2	155.5	155.8
100°	187.6	190.0	192.3	193.8	194.3	194.9	195.4	195.9
102.5°	226.2	228.9	231.4	233.1	233.9	234.6	235.4	236.1
105°	288.8	290.3	291.9	293.1	293.9	294.7	295.5	296.3
107.5°	356.2	357.0	357.7	358.1	358.1	358.1	358.0	357.9
110°	403.1	403.9	404.6	404.9	404.6	404.3	404.1	403.9



TEST NUMBER: P333739-927

CATALOG NUMBER: S125RDIW-S1270D1560U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	450.0	450.4	450.7	450.7	450.2	449.7	449.2	448.8
115°	521.6	521.3	521.0	520.8	520.5	520.2	520.0	519.8
117.5°	593.3	593.5	593.7	593.3	592.2	591.1	590.1	589.0
120°	641.6	641.6	641.6	641.0	640.0	638.9	637.9	636.8
122.5°	689.0	688.7	688.5	688.0	687.1	686.3	685.4	684.6
125°	758.8	758.3	757.7	757.3	757.1	756.8	756.5	756.3
127.5°	828.1	827.9	827.6	827.2	826.6	826.2	825.6	825.1
130°	874.0	873.8	873.5	873.1	872.6	872.0	871.5	871.0
132.5°	918.0	917.7	917.4	917.0	916.2	915.4	914.7	913.9
135°	985.6	985.6	985.6	985.2	984.0	983.0	981.9	980.9
137.5°	1051.5	1051.9	1052.2	1051.7	1050.4	1049.0	1047.7	1046.3
140°	1093.1	1093.6	1094.1	1093.7	1092.4	1091.1	1089.7	1088.4
142.5°	1133.7	1134.0	1134.4	1133.9	1132.5	1131.2	1129.9	1128.5
145°	1192.3	1192.3	1192.3	1191.9	1191.1	1190.3	1189.5	1188.7
147.5°	1246.7	1247.3	1247.9	1247.4	1245.5	1243.7	1242.0	1240.2
150°	1280.8	1280.8	1280.8	1280.5	1279.9	1279.5	1278.9	1278.3
152.5°	1312.6	1313.3	1313.9	1313.8	1312.8	1311.9	1310.9	1310.0
155°	1358.1	1359.2	1360.3	1360.2	1358.8	1357.5	1356.1	1354.9
157.5°	1397.6	1398.7	1399.7	1399.4	1397.6	1395.8	1394.1	1392.3
160°	1421.5	1422.5	1423.6	1423.5	1422.1	1420.8	1419.5	1418.2
162.5°	1443.9	1445.2	1446.4	1446.3	1444.8	1443.2	1441.7	1440.1
165°	1474.0	1475.1	1476.2	1475.9	1474.3	1472.7	1471.2	1469.5
167.5°	1496.4	1497.9	1499.5	1499.5	1497.9	1496.3	1494.6	1492.9
170°	1509.7	1511.3	1512.9	1512.8	1510.9	1509.1	1507.2	1505.4
172.5°	1519.3	1520.9	1522.5	1522.5	1520.8	1519.2	1517.5	1515.9
175°	1530.1	1531.7	1533.3	1533.1	1531.3	1529.4	1527.6	1525.7
177.5°	1534.9	1536.2	1537.5	1537.4	1535.9	1534.4	1532.9	1531.4
180°	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2

(END OF REPORT)