

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333033-840

Luminaire Tested: **S124RDIW-S350D1560U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333033-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S350D1560U840-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1560 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7746.6 lumens  
Efficiency: N/A  
Efficacy: 145.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 53.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333033-840

CATALOG NUMBER: S124RDIW-S350D1560U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333033-840

CATALOG NUMBER: S124RDIW-S350D1560U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	88	88	88	88	66	66	66	46	46	46	27	27	27	19
1	91	87	83	80	80	77	74	71	58	56	54	40	39	38	24	24	23	16
2	83	76	70	65	73	67	62	58	51	47	45	35	34	32	21	20	20	13
3	75	67	60	54	66	59	53	49	45	41	38	31	29	27	19	18	17	12
4	69	59	51	46	61	52	46	41	40	35	32	28	25	23	17	16	15	10
5	63	52	45	39	55	46	40	35	35	31	27	25	22	20	15	14	13	9
6	58	47	39	34	51	42	35	30	32	27	24	23	20	17	14	12	11	8
7	54	42	34	29	47	37	31	26	29	24	21	20	17	15	13	11	10	7
8	50	38	31	26	44	34	28	23	26	21	18	19	16	14	12	10	9	6
9	46	34	27	23	40	31	25	20	24	19	16	17	14	12	11	9	8	6
10	43	31	25	20	38	28	22	18	22	17	14	16	13	11	10	8	7	5

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5040	5040	5040
5°	5051	4989	5020
10°	5019	4930	4930
15°	4962	4826	4790
20°	4883	4689	4603
25°	4782	4530	4415
30°	4683	4363	4180
35°	4574	4188	3943
40°	4443	3990	3687
45°	4322	3793	3427
50°	4185	3567	3152
55°	4037	3330	2853
60°	3873	3073	2546
65°	3725	2749	2245
70°	3510	2391	1907
75°	3235	1984	1550
80°	2822	1511	1423
85°	2399	1371	1278



TEST NUMBER: P333033-840

CATALOG NUMBER: S124RDIW-S350D1560U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	58.6	0.8
10°-20°	163.5	2.1
20°-30°	236.1	3.0
30°-40°	267.7	3.5
40°-50°	258.5	3.3
50°-60°	214.9	2.8
60°-70°	148.4	1.9
70°-80°	75.2	1.0
80°-90°	25.2	0.3
90°-100°	69.6	0.9
100°-110°	444.0	5.7
110°-120°	849.4	11.0
120°-130°	1078.3	13.9
130°-140°	1153.7	14.9
140°-150°	1078.8	13.9
150°-160°	870.0	11.2
160°-170°	561.1	7.2
170°-180°	193.4	2.5
0°-30°	458.3	5.9
0°-40°	726.0	9.4
0°-60°	1199.4	15.5
0°-90°	1448.2	18.7
90°-120°	1363.1	17.6
90°-150°	4673.9	60.3
90°-180°	6298.0	81.3
0°-180°	7746.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	624	624	624	624	624	
5°	623	621	616	620	620	59
15°	594	589	577	576	573	167
25°	537	528	509	501	496	247
35°	464	448	425	409	400	290
45°	379	360	332	310	300	292
55°	287	267	237	213	203	256
65°	195	174	144	124	118	193
75°	104	86	64	53	50	110
85°	26	17	15	14	14	29
90°	4	21	34	42	46	5
95°	84	35	34	42	44	108
105°	458	468	475	485	434	480
115°	856	860	859	862	862	842
125°	1203	1209	1206	1211	1212	1074
135°	1492	1491	1497	1500	1503	1149
145°	1721	1725	1726	1727	1730	1075
155°	1887	1888	1884	1889	1885	870
165°	1990	1983	1983	1994	1981	562
175°	2036	2028	2028	2040	2024	194
180°	2036	2036	2036	2036	2036	



TEST NUMBER: P333033-840

CATALOG NUMBER: S124RDIW-S350D1560U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3
2.5°	625.8	625.4	625.1	624.8	624.4	623.8	622.9	622.0	621.0	620.1	621.0
5°	623.3	622.9	622.5	622.1	621.6	620.8	619.5	618.2	616.9	615.7	616.7
7.5°	617.6	617.2	616.8	616.3	615.9	614.8	613.2	611.5	609.9	608.2	608.8
10°	612.3	611.8	611.3	610.8	610.2	608.9	607.0	605.1	603.2	601.4	601.8
12.5°	605.4	604.8	604.2	603.6	603.0	601.6	599.3	597.0	594.8	592.5	592.8
15°	593.7	592.7	591.8	590.8	589.9	588.0	585.4	582.7	580.1	577.4	577.2
17.5°	579.5	578.0	576.6	575.3	573.9	571.6	568.5	565.2	562.1	558.9	558.3
20°	568.4	566.9	565.6	564.2	562.8	560.4	556.7	553.1	549.5	545.8	545.0
22.5°	556.1	554.5	553.0	551.5	549.9	547.1	543.3	539.5	535.6	531.7	530.5
25°	536.8	534.9	533.0	531.1	529.2	526.0	521.7	517.4	512.9	508.6	506.8
27.5°	516.5	514.1	511.7	509.4	507.0	503.4	498.8	494.1	489.5	484.8	482.5
30°	502.4	499.7	497.1	494.4	491.8	488.0	482.9	478.0	472.9	468.0	465.3
32.5°	487.5	484.4	481.5	478.5	475.4	471.4	466.3	461.1	456.0	450.8	447.7
35°	464.1	460.7	457.4	453.9	450.5	446.2	440.9	435.6	430.3	425.0	421.3
37.5°	439.2	435.7	432.2	428.7	425.2	420.5	414.5	408.7	402.8	397.0	392.9
40°	421.6	418.1	414.5	411.1	407.6	402.8	396.8	390.7	384.7	378.6	374.2
42.5°	404.8	401.1	397.4	393.7	390.1	385.1	378.8	372.4	366.2	359.8	355.3
45°	378.6	374.7	370.7	366.8	362.8	357.7	351.3	345.0	338.6	332.2	327.0
47.5°	351.5	347.5	343.5	339.3	335.3	329.9	323.4	316.7	310.0	303.5	298.0
50°	333.2	329.0	324.9	320.7	316.6	311.1	304.4	297.5	290.7	284.0	278.6
52.5°	314.5	310.3	306.3	302.3	298.2	292.7	285.7	278.7	271.8	264.8	259.4
55°	286.8	282.6	278.3	274.1	269.8	264.2	257.3	250.4	243.5	236.6	231.1
57.5°	259.4	255.0	250.6	246.2	241.8	236.2	229.3	222.6	215.8	208.9	203.4
60°	239.9	235.7	231.5	227.2	223.0	217.4	210.7	203.8	197.0	190.3	184.7
62.5°	222.4	217.9	213.5	209.1	204.7	199.0	192.1	185.1	178.1	171.2	166.0
65°	195.0	190.5	185.9	181.4	176.7	171.1	164.3	157.4	150.7	143.9	139.4
67.5°	166.6	162.3	157.8	153.5	149.2	143.8	137.4	131.2	124.8	118.6	114.6
70°	148.7	144.2	139.8	135.3	130.8	125.5	119.5	113.4	107.3	101.3	97.9
72.5°	129.6	125.5	121.5	117.4	113.4	108.6	102.8	97.0	91.4	85.6	82.7
75°	103.7	99.8	95.8	91.9	88.0	83.5	78.6	73.5	68.6	63.6	61.1
77.5°	77.6	74.2	70.9	67.6	64.2	60.5	56.5	52.4	48.4	44.3	42.9
80°	60.7	57.7	54.5	51.5	48.4	45.2	42.1	38.9	35.6	32.5	32.2
82.5°	46.2	43.3	40.5	37.7	34.8	32.5	30.7	28.9	27.1	25.2	25.0
85°	25.9	23.7	21.6	19.4	17.3	16.1	15.8	15.5	15.1	14.8	14.6
87.5°	9.7	9.8	9.8	9.9	10.0	10.2	10.7	11.1	11.6	12.0	12.4
90°	4.5	8.3	12.0	15.8	19.5	22.7	25.3	28.1	30.8	33.5	35.5
92.5°	19.2	19.4	19.6	19.8	20.0	21.4	24.1	26.9	29.6	32.3	34.3
95°	83.7	72.2	60.8	49.3	37.8	32.1	32.5	32.8	33.1	33.5	35.5
97.5°	177.8	185.0	192.2	199.4	206.6	191.3	153.5	115.7	78.0	40.2	40.4
100°	249.7	255.9	262.0	268.0	274.1	253.8	207.1	160.4	113.7	67.1	61.3
102.5°	330.1	334.7	339.1	343.6	348.0	347.2	341.1	335.1	328.9	322.9	260.7
105°	458.4	460.4	462.4	464.5	466.6	468.4	470.1	471.8	473.4	475.1	478.2
107.5°	577.4	578.6	579.6	580.6	581.6	583.2	585.5	587.8	590.1	592.4	593.9
110°	657.9	658.9	659.9	661.0	662.0	663.5	665.5	667.5	669.5	671.6	672.3



TEST NUMBER: P333033-840

CATALOG NUMBER: S124RDIW-S350D1560U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	735.9	737.7	739.5	741.3	743.2	744.6	745.5	746.5	747.4	748.4	748.2
115°	855.9	856.9	857.9	858.9	859.9	860.3	859.9	859.6	859.3	858.9	859.6
117.5°	964.0	965.3	966.7	968.1	969.5	970.5	971.2	972.0	972.7	973.4	973.3
120°	1037.1	1038.4	1039.9	1041.2	1042.5	1043.0	1042.7	1042.4	1042.0	1041.7	1042.4
122.5°	1105.3	1106.1	1106.9	1107.7	1108.6	1109.2	1109.7	1110.1	1110.6	1111.2	1111.6
125°	1203.2	1204.5	1205.8	1207.2	1208.5	1208.8	1208.2	1207.5	1206.8	1206.2	1207.2
127.5°	1295.7	1296.1	1296.4	1296.7	1297.1	1298.0	1299.6	1301.1	1302.6	1304.2	1304.0
130°	1355.4	1355.7	1356.0	1356.5	1356.8	1357.5	1358.5	1359.5	1360.5	1361.5	1361.8
132.5°	1410.2	1410.8	1411.5	1412.1	1412.7	1413.6	1414.9	1416.1	1417.4	1418.8	1419.1
135°	1492.5	1492.1	1491.8	1491.5	1491.1	1491.6	1493.0	1494.3	1495.7	1497.0	1497.7
137.5°	1565.3	1565.4	1565.5	1565.7	1565.8	1566.6	1568.1	1569.6	1571.0	1572.6	1573.3
140°	1612.8	1613.5	1614.2	1614.8	1615.5	1616.2	1616.8	1617.5	1618.2	1618.8	1619.9
142.5°	1655.4	1656.6	1657.9	1659.1	1660.3	1661.1	1661.5	1661.9	1662.3	1662.7	1663.4
145°	1720.9	1721.9	1722.9	1723.9	1725.0	1725.5	1725.5	1725.5	1725.5	1725.5	1725.8
147.5°	1773.0	1774.8	1776.8	1778.7	1780.6	1781.3	1781.0	1780.7	1780.3	1780.0	1780.3
150°	1810.8	1812.1	1813.4	1814.8	1816.1	1816.6	1816.3	1816.0	1815.6	1815.3	1815.3
152.5°	1842.4	1843.5	1844.6	1845.6	1846.7	1847.0	1846.3	1845.7	1845.1	1844.5	1845.1
155°	1886.9	1887.2	1887.5	1887.9	1888.2	1887.9	1886.9	1885.9	1884.9	1883.8	1885.2
157.5°	1924.4	1924.2	1924.0	1923.8	1923.6	1922.9	1921.7	1920.6	1919.5	1918.2	1920.1
160°	1946.3	1945.3	1944.3	1943.3	1942.3	1941.6	1941.2	1940.9	1940.6	1940.2	1942.3
162.5°	1965.8	1964.5	1963.2	1962.0	1960.7	1959.8	1959.4	1959.1	1958.8	1958.4	1960.5
165°	1990.4	1988.7	1987.1	1985.4	1983.7	1982.9	1982.9	1982.9	1982.9	1982.9	1985.5
167.5°	2009.9	2008.2	2006.4	2004.7	2002.9	2002.0	2001.8	2001.6	2001.4	2001.1	2004.1
170°	2020.9	2018.9	2016.8	2014.8	2012.8	2012.0	2012.3	2012.7	2013.0	2013.3	2016.0
172.5°	2028.2	2026.2	2024.2	2022.2	2020.1	2019.2	2019.6	2019.9	2020.2	2020.6	2023.3
175°	2036.1	2034.1	2032.1	2030.0	2028.0	2027.2	2027.5	2027.8	2028.2	2028.5	2031.5
177.5°	2039.8	2037.9	2036.0	2034.1	2032.3	2031.5	2032.1	2032.7	2033.2	2033.7	2035.9
180°	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1



TEST NUMBER: P333033-840

CATALOG NUMBER: S124RDIW-S350D1560U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3
2.5°	622.0	622.9	623.8	624.2	624.1	624.1	624.0	623.9
5°	617.8	618.8	620.0	620.4	620.2	620.0	619.7	619.5
7.5°	609.6	610.3	611.0	611.1	610.8	610.5	610.1	609.8
10°	602.2	602.6	603.0	603.0	602.6	602.2	601.8	601.4
12.5°	593.0	593.3	593.6	593.4	592.8	592.2	591.6	591.0
15°	577.0	576.8	576.5	576.1	575.3	574.6	573.9	573.1
17.5°	557.6	557.1	556.5	555.6	554.5	553.4	552.3	551.2
20°	544.2	543.3	542.5	541.4	540.0	538.6	537.2	535.8
22.5°	529.2	527.9	526.6	525.4	524.3	523.2	522.1	520.9
25°	504.9	503.2	501.4	500.0	498.9	497.8	496.8	495.6
27.5°	480.3	478.1	475.8	474.0	472.4	470.9	469.4	467.9
30°	462.6	460.0	457.4	455.1	453.4	451.8	450.1	448.4
32.5°	444.6	441.5	438.5	436.1	434.4	432.8	431.2	429.6
35°	417.7	414.1	410.5	407.8	405.9	403.9	402.0	400.1
37.5°	388.9	384.9	380.8	377.8	375.9	374.0	372.0	370.1
40°	369.6	365.2	360.7	357.6	355.7	353.8	351.8	349.9
42.5°	350.7	346.2	341.6	338.4	336.4	334.4	332.3	330.4
45°	321.8	316.6	311.3	307.8	305.9	304.0	302.1	300.2
47.5°	292.7	287.2	281.9	278.1	276.0	273.9	271.8	269.7
50°	273.3	268.0	262.7	259.0	257.0	255.0	253.0	251.0
52.5°	254.0	248.6	243.3	239.4	237.4	235.3	233.2	231.1
55°	225.6	220.0	214.5	210.8	208.7	206.7	204.7	202.7
57.5°	197.7	192.2	186.5	183.0	181.5	180.0	178.3	176.8
60°	179.2	173.7	168.1	164.5	162.8	161.2	159.5	157.7
62.5°	161.0	155.8	150.8	147.5	146.1	144.8	143.4	142.1
65°	134.7	130.2	125.6	122.7	121.4	120.2	118.9	117.5
67.5°	110.7	106.7	102.8	100.2	98.8	97.4	95.9	94.5
70°	94.3	90.8	87.4	85.0	83.9	82.9	81.8	80.8
72.5°	79.7	76.6	73.7	71.7	70.7	69.8	68.8	67.8
75°	58.7	56.2	53.8	52.3	51.6	51.0	50.4	49.7
77.5°	41.5	40.1	38.7	37.9	37.7	37.5	37.3	37.1
80°	31.9	31.5	31.2	31.0	30.9	30.8	30.7	30.6
82.5°	24.7	24.5	24.3	24.1	24.0	23.9	23.8	23.7
85°	14.4	14.1	13.9	13.8	13.8	13.8	13.8	13.8
87.5°	12.7	13.0	13.3	13.6	13.8	14.0	14.2	14.4
90°	37.6	39.6	41.6	43.0	43.6	44.3	45.0	45.6
92.5°	36.4	38.4	40.4	41.5	41.6	41.8	41.9	42.0
95°	37.6	39.6	41.6	42.8	43.1	43.5	43.8	44.1
97.5°	40.6	40.8	41.0	41.3	41.6	42.0	42.3	42.6
100°	55.5	49.8	44.0	41.3	41.6	42.0	42.3	42.6
102.5°	198.7	136.6	74.6	43.6	43.6	43.7	43.8	43.8
105°	481.2	484.3	487.4	482.7	470.6	458.4	446.3	434.0
107.5°	595.4	596.9	598.3	599.8	601.1	602.3	603.6	604.9
110°	673.0	673.7	674.3	675.2	676.2	677.2	678.2	679.2





TEST NUMBER: P333033-840

CATALOG NUMBER: S124RDIW-S350D1560U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	748.1	747.9	747.8	748.4	749.7	750.9	752.2	753.6
115°	860.3	860.9	861.6	862.0	862.0	862.0	862.0	862.0
117.5°	973.2	973.0	972.9	972.8	972.6	972.5	972.4	972.2
120°	1043.0	1043.7	1044.4	1044.4	1043.7	1043.0	1042.4	1041.7
122.5°	1112.0	1112.4	1112.8	1112.6	1112.0	1111.3	1110.5	1109.9
125°	1208.2	1209.2	1210.2	1210.9	1211.2	1211.5	1211.9	1212.2
127.5°	1303.8	1303.6	1303.4	1303.1	1302.9	1302.6	1302.3	1302.1
130°	1362.2	1362.5	1362.8	1363.0	1363.0	1363.0	1363.0	1363.0
132.5°	1419.5	1419.8	1420.1	1420.2	1419.9	1419.6	1419.4	1419.1
135°	1498.3	1499.0	1499.8	1500.5	1501.1	1501.8	1502.5	1503.1
137.5°	1574.1	1574.8	1575.6	1575.8	1575.6	1575.4	1575.2	1575.0
140°	1620.9	1621.9	1623.0	1623.6	1624.0	1624.3	1624.6	1625.0
142.5°	1664.3	1665.0	1665.7	1666.1	1666.2	1666.3	1666.3	1666.4
145°	1726.2	1726.5	1726.8	1727.4	1728.0	1728.7	1729.4	1730.0
147.5°	1780.5	1780.8	1781.1	1781.4	1781.7	1782.0	1782.4	1782.7
150°	1815.3	1815.3	1815.3	1815.5	1815.8	1816.1	1816.5	1816.8
152.5°	1845.6	1846.1	1846.7	1846.8	1846.6	1846.4	1846.2	1846.0
155°	1886.5	1887.9	1889.3	1889.5	1888.4	1887.4	1886.4	1885.4
157.5°	1921.8	1923.6	1925.3	1925.3	1923.6	1921.8	1920.1	1918.2
160°	1944.3	1946.3	1948.3	1948.3	1946.3	1944.3	1942.3	1940.2
162.5°	1962.6	1964.6	1966.6	1966.4	1964.2	1961.9	1959.5	1957.2
165°	1988.2	1990.9	1993.7	1993.5	1990.4	1987.4	1984.4	1981.4
167.5°	2007.1	2010.0	2013.1	2012.9	2009.4	2006.1	2002.7	1999.3
170°	2018.7	2021.4	2024.2	2023.8	2020.4	2017.0	2013.7	2010.2
172.5°	2026.0	2028.7	2031.4	2030.9	2027.3	2023.7	2020.0	2016.3
175°	2034.6	2037.7	2040.7	2040.2	2036.1	2032.1	2028.0	2024.0
177.5°	2038.0	2040.2	2042.4	2041.8	2038.6	2035.3	2032.1	2028.8
180°	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1

(END OF REPORT)