

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333659-927

Luminaire Tested: **S125RDIW-S375D1560U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333659-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S375D1560U927-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5432.5 lumens
Efficiency: N/A
Efficacy: 101.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333659-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333659-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	30	30	30	21
1	91	87	84	80	81	77	74	72	59	57	55	42	41	40	26	26	25	18
2	83	76	70	66	73	68	63	59	52	48	46	37	35	33	23	22	21	15
3	76	67	60	55	67	60	54	49	46	42	38	33	30	28	21	19	18	13
4	69	59	52	46	61	53	46	42	40	36	33	29	26	24	18	17	16	11
5	64	53	45	39	56	47	40	35	36	32	28	26	23	21	17	15	14	10
6	58	47	39	34	52	42	35	31	32	28	24	23	20	18	15	13	12	9
7	54	42	35	29	48	38	31	27	29	25	21	21	18	16	14	12	11	8
8	50	38	31	26	44	34	28	23	27	22	19	19	16	14	13	11	10	7
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	6
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3130	3130	3130
5°	3138	3102	3121
10°	3114	3074	3074
15°	3077	3011	2986
20°	3030	2924	2889
25°	2974	2838	2776
30°	2905	2738	2651
35°	2834	2636	2511
40°	2769	2528	2373
45°	2689	2408	2223
50°	2608	2277	2067
55°	2514	2152	1901
60°	2421	2001	1721
65°	2311	1825	1516
70°	2185	1603	1307
75°	2011	1352	1088
80°	1770	1060	915
85°	1489	867	815



TEST NUMBER: P333659-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.6	0.8
10°-20°	127.4	2.3
20°-30°	184.7	3.4
30°-40°	210.5	3.9
40°-50°	205.2	3.8
50°-60°	172.7	3.2
60°-70°	121.1	2.2
70°-80°	62.2	1.1
80°-90°	19.1	0.4
90°-100°	102.8	1.9
100°-110°	303.6	5.6
110°-120°	514.3	9.5
120°-130°	676.9	12.5
130°-140°	758.4	14.0
140°-150°	743.3	13.7
150°-160°	624.3	11.5
160°-170°	415.0	7.6
170°-180°	145.2	2.7
0°-30°	357.7	6.6
0°-40°	568.2	10.5
0°-60°	946.1	17.4
0°-90°	1148.5	21.1
90°-120°	920.8	16.9
90°-150°	3099.4	57.1
90°-180°	4284.0	78.9
0°-180°	5432.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	485	485	485	485	485	
5°	484	482	478	482	481	46
15°	460	458	450	450	447	130
25°	417	411	398	394	390	192
35°	360	350	334	324	318	225
45°	294	283	264	249	243	227
55°	223	211	191	175	169	200
65°	151	138	119	105	99	150
75°	81	69	54	46	44	85
85°	20	14	12	11	11	23
90°	1	11	19	25	29	5
95°	78	81	92	100	103	83
105°	272	278	286	292	296	291
115°	515	520	522	521	520	509
125°	752	758	760	758	756	673
135°	977	984	986	985	981	753
145°	1184	1189	1192	1192	1189	740
155°	1355	1355	1356	1360	1355	624
165°	1473	1471	1472	1476	1470	415
175°	1532	1527	1527	1533	1526	145
180°	1535	1535	1535	1535	1535	



TEST NUMBER: P333659-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	485.6	485.4	485.2	485.1	484.8	484.4	483.8	483.1	482.4	481.8	482.4
5°	484.0	483.7	483.4	483.0	482.7	482.1	481.2	480.3	479.4	478.5	479.3
7.5°	479.3	479.0	478.6	478.3	478.0	477.3	476.3	475.2	474.1	473.0	473.6
10°	474.8	474.6	474.4	474.1	473.9	473.2	472.1	470.9	469.8	468.7	468.9
12.5°	469.8	469.5	469.3	469.0	468.7	467.7	466.2	464.7	463.1	461.6	461.8
15°	460.2	459.7	459.2	458.8	458.3	457.2	455.4	453.8	452.0	450.4	450.3
17.5°	449.3	448.5	447.8	447.0	446.3	444.9	442.7	440.5	438.4	436.3	435.9
20°	440.8	440.0	439.2	438.4	437.5	435.9	433.2	430.6	428.0	425.4	425.0
22.5°	431.4	430.6	429.8	429.0	428.2	426.4	423.7	421.0	418.2	415.5	414.7
25°	417.4	416.1	414.9	413.7	412.5	410.4	407.3	404.3	401.3	398.3	397.3
27.5°	401.2	399.8	398.3	396.8	395.3	393.0	389.8	386.5	383.3	380.1	378.6
30°	389.5	388.0	386.4	384.9	383.3	380.9	377.5	374.1	370.7	367.2	365.4
32.5°	378.1	376.3	374.5	372.7	370.9	368.3	364.8	361.3	357.8	354.3	352.3
35°	359.5	357.6	355.6	353.6	351.7	348.9	345.2	341.6	337.9	334.3	331.9
37.5°	341.3	338.9	336.5	334.1	331.8	328.7	325.0	321.2	317.4	313.6	310.8
40°	328.4	326.0	323.5	321.1	318.6	315.4	311.6	307.7	303.7	299.8	296.8
42.5°	314.9	312.4	309.9	307.4	304.9	301.7	297.6	293.6	289.5	285.5	282.6
45°	294.4	292.0	289.6	287.2	284.9	281.5	277.0	272.6	268.1	263.6	260.3
47.5°	273.1	270.5	268.1	265.5	263.1	259.6	255.1	250.6	246.1	241.5	238.2
50°	259.6	256.9	254.2	251.5	248.8	245.2	240.5	235.9	231.2	226.6	223.2
52.5°	244.9	242.2	239.4	236.7	233.9	230.4	226.0	221.6	217.2	212.9	209.2
55°	223.3	220.7	218.1	215.6	212.9	209.4	204.8	200.2	195.7	191.1	187.4
57.5°	201.5	198.8	195.9	193.1	190.4	186.8	182.4	178.0	173.6	169.2	165.6
60°	187.4	184.6	181.7	178.9	176.0	172.5	168.0	163.7	159.2	154.9	151.3
62.5°	172.5	169.8	167.1	164.4	161.6	158.0	153.6	149.2	144.7	140.2	136.9
65°	151.2	148.5	145.7	142.9	140.1	136.6	132.3	128.0	123.7	119.4	116.1
67.5°	130.1	127.3	124.5	121.8	119.0	115.5	111.4	107.3	103.1	99.0	96.0
70°	115.7	113.0	110.2	107.4	104.6	101.2	97.1	93.1	89.0	84.9	82.4
72.5°	101.6	98.9	96.3	93.6	90.9	87.5	83.7	79.9	76.1	72.3	70.0
75°	80.6	78.1	75.7	73.2	70.8	67.9	64.4	61.0	57.6	54.2	52.4
77.5°	59.6	57.7	55.7	53.7	51.8	49.4	46.7	44.0	41.3	38.5	37.2
80°	47.6	45.6	43.7	41.7	39.8	37.7	35.4	33.1	30.8	28.5	27.8
82.5°	35.9	34.1	32.4	30.6	28.8	27.2	25.7	24.1	22.5	20.9	20.6
85°	20.1	18.7	17.2	15.8	14.3	13.3	12.9	12.5	12.1	11.7	11.6
87.5°	7.0	7.0	6.9	6.9	6.8	7.0	7.3	7.6	7.9	8.2	8.5
90°	1.2	3.3	5.5	7.6	9.7	11.6	13.5	15.4	17.3	19.1	20.4
92.5°	28.9	30.4	31.9	33.4	34.9	36.8	39.1	41.3	43.6	45.9	47.6
95°	77.6	78.2	78.7	79.2	79.8	81.4	84.1	86.7	89.4	92.0	93.9
97.5°	129.0	129.2	129.4	129.7	129.9	131.8	135.5	139.2	142.8	146.5	148.2
100°	167.2	167.2	167.2	167.2	167.2	169.0	172.5	175.9	179.4	182.8	185.2
102.5°	208.3	209.5	210.5	211.5	212.6	214.0	215.8	217.5	219.3	221.0	223.6
105°	272.4	273.7	275.0	276.4	277.7	279.2	280.7	282.3	283.9	285.6	287.2
107.5°	343.1	344.4	345.8	347.1	348.4	349.7	350.9	352.1	353.4	354.6	355.4
110°	391.9	393.2	394.5	395.9	397.2	398.2	399.0	399.8	400.6	401.4	402.2



TEST NUMBER: P333659-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	441.6	442.3	443.0	443.6	444.3	445.2	446.2	447.2	448.2	449.2	449.6
115°	514.9	516.0	517.1	518.1	519.2	520.0	520.5	521.0	521.6	522.1	521.8
117.5°	588.5	589.0	589.5	589.9	590.4	590.9	591.4	591.8	592.3	592.9	593.0
120°	634.4	635.7	637.1	638.4	639.7	640.5	640.8	641.0	641.3	641.6	641.6
122.5°	684.1	684.6	685.1	685.6	686.0	686.6	687.3	688.0	688.6	689.4	689.1
125°	751.5	753.0	754.7	756.3	757.9	758.8	759.1	759.3	759.6	759.9	759.3
127.5°	823.2	824.1	825.0	825.9	826.8	827.4	827.8	828.1	828.4	828.7	828.4
130°	866.2	867.5	868.9	870.1	871.5	872.4	873.0	873.5	874.0	874.6	874.3
132.5°	909.2	911.4	913.5	915.8	917.9	918.9	918.9	918.7	918.6	918.5	918.2
135°	977.3	978.9	980.5	982.1	983.7	984.6	984.8	985.2	985.4	985.6	985.6
137.5°	1041.3	1042.9	1044.4	1045.9	1047.5	1048.5	1049.2	1049.7	1050.3	1050.9	1051.2
140°	1082.4	1083.8	1085.1	1086.4	1087.7	1088.8	1089.6	1090.4	1091.2	1092.0	1092.5
142.5°	1123.6	1124.7	1125.8	1126.9	1128.0	1129.0	1130.0	1131.1	1132.1	1133.1	1133.4
145°	1184.0	1185.0	1186.1	1187.2	1188.3	1189.1	1189.9	1190.7	1191.5	1192.3	1192.3
147.5°	1239.9	1240.5	1241.0	1241.7	1242.2	1242.9	1243.5	1244.1	1244.8	1245.4	1246.0
150°	1277.2	1276.9	1276.7	1276.4	1276.1	1276.5	1277.6	1278.7	1279.7	1280.8	1280.8
152.5°	1307.7	1308.1	1308.5	1308.8	1309.2	1309.6	1310.1	1310.5	1310.9	1311.4	1312.0
155°	1354.9	1354.9	1354.9	1354.9	1354.9	1354.9	1355.3	1355.5	1355.7	1356.1	1357.1
157.5°	1396.9	1396.3	1395.7	1395.1	1394.6	1394.4	1394.6	1395.0	1395.2	1395.4	1396.5
160°	1421.7	1420.9	1420.1	1419.4	1418.6	1418.3	1418.6	1418.8	1419.1	1419.4	1420.4
162.5°	1443.8	1443.1	1442.6	1442.0	1441.4	1441.1	1441.1	1441.2	1441.3	1441.3	1442.6
165°	1473.1	1472.6	1472.0	1471.6	1471.0	1470.8	1471.2	1471.4	1471.6	1472.0	1473.0
167.5°	1497.9	1496.9	1495.9	1494.8	1493.7	1493.2	1493.2	1493.2	1493.2	1493.2	1494.8
170°	1511.3	1510.3	1509.2	1508.2	1507.1	1506.6	1506.6	1506.6	1506.6	1506.6	1508.2
172.5°	1520.9	1519.9	1518.8	1517.7	1516.6	1516.2	1516.2	1516.2	1516.2	1516.2	1517.7
175°	1531.7	1530.6	1529.5	1528.4	1527.4	1526.9	1526.9	1526.9	1526.9	1526.9	1528.4
177.5°	1537.2	1536.3	1535.5	1534.6	1533.7	1533.2	1533.0	1532.8	1532.6	1532.4	1533.7
180°	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2



TEST NUMBER: P333659-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	483.1	483.8	484.4	484.7	484.7	484.6	484.5	484.4
5°	480.1	480.9	481.7	482.1	482.0	481.7	481.6	481.4
7.5°	474.1	474.8	475.3	475.5	475.3	475.2	475.0	474.8
10°	469.1	469.4	469.6	469.6	469.4	469.1	468.9	468.7
12.5°	461.9	462.2	462.3	462.2	461.8	461.4	461.1	460.7
15°	450.1	450.0	450.0	449.6	448.9	448.1	447.4	446.6
17.5°	435.5	435.1	434.7	434.1	433.6	432.9	432.3	431.7
20°	424.6	424.2	423.8	423.3	422.5	421.8	421.0	420.3
22.5°	413.8	413.0	412.3	411.5	411.0	410.4	409.8	409.2
25°	396.2	395.1	394.1	393.2	392.2	391.3	390.5	389.5
27.5°	377.2	375.7	374.1	373.0	372.2	371.3	370.4	369.6
30°	363.5	361.6	359.7	358.5	357.7	357.0	356.2	355.5
32.5°	350.2	348.2	346.0	344.6	343.6	342.7	341.7	340.9
35°	329.5	327.2	324.8	323.1	321.9	320.8	319.6	318.5
37.5°	307.9	305.1	302.3	300.3	299.2	298.1	297.0	295.9
40°	293.7	290.6	287.5	285.4	284.5	283.5	282.5	281.5
42.5°	279.6	276.6	273.6	271.5	270.1	268.5	267.1	265.7
45°	257.1	253.8	250.6	248.3	247.2	245.9	244.7	243.4
47.5°	234.9	231.5	228.1	225.8	224.4	223.1	221.7	220.4
50°	219.8	216.3	212.9	210.6	209.5	208.2	207.0	205.7
52.5°	205.5	201.8	198.1	195.7	194.5	193.3	192.0	190.8
55°	183.8	180.1	176.5	174.0	172.7	171.3	170.1	168.8
57.5°	162.1	158.5	154.9	152.5	151.4	150.2	149.1	147.9
60°	147.7	144.1	140.5	138.2	136.9	135.7	134.5	133.2
62.5°	133.6	130.2	126.9	124.7	123.4	122.2	121.0	119.8
65°	112.8	109.6	106.3	104.1	102.9	101.6	100.4	99.2
67.5°	93.0	90.1	87.1	85.1	84.1	83.2	82.1	81.2
70°	79.9	77.4	74.9	73.1	72.1	71.1	70.2	69.2
72.5°	67.7	65.4	63.1	61.6	60.9	60.3	59.6	58.9
75°	50.6	48.8	47.1	45.9	45.3	44.7	44.1	43.6
77.5°	36.0	34.8	33.5	32.6	32.2	31.8	31.4	31.0
80°	27.1	26.4	25.7	25.2	25.0	24.9	24.7	24.6
82.5°	20.3	19.9	19.6	19.3	19.3	19.2	19.1	18.9
85°	11.6	11.5	11.4	11.3	11.2	11.2	11.1	11.0
87.5°	8.7	9.0	9.3	9.4	9.6	9.7	9.7	9.8
90°	21.8	23.1	24.4	25.5	26.3	27.1	27.9	28.7
92.5°	49.4	51.1	52.9	54.0	54.7	55.2	55.8	56.4
95°	95.7	97.6	99.4	100.6	101.2	101.7	102.2	102.7
97.5°	150.0	151.7	153.4	154.6	154.9	155.2	155.5	155.8
100°	187.6	190.0	192.3	193.8	194.3	194.9	195.4	195.9
102.5°	226.2	228.9	231.4	233.1	233.9	234.6	235.4	236.1
105°	288.8	290.3	291.9	293.1	293.9	294.7	295.5	296.3
107.5°	356.2	357.0	357.7	358.1	358.1	358.1	358.0	357.9
110°	403.1	403.9	404.6	404.9	404.6	404.3	404.1	403.9



TEST NUMBER: P333659-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	450.0	450.4	450.7	450.7	450.2	449.7	449.2	448.8
115°	521.6	521.3	521.0	520.8	520.5	520.2	520.0	519.8
117.5°	593.3	593.5	593.7	593.3	592.2	591.1	590.1	589.0
120°	641.6	641.6	641.6	641.0	640.0	638.9	637.9	636.8
122.5°	689.0	688.7	688.5	688.0	687.1	686.3	685.4	684.6
125°	758.8	758.3	757.7	757.3	757.1	756.8	756.5	756.3
127.5°	828.1	827.9	827.6	827.2	826.6	826.2	825.6	825.1
130°	874.0	873.8	873.5	873.1	872.6	872.0	871.5	871.0
132.5°	918.0	917.7	917.4	917.0	916.2	915.4	914.7	913.9
135°	985.6	985.6	985.6	985.2	984.0	983.0	981.9	980.9
137.5°	1051.5	1051.9	1052.2	1051.7	1050.4	1049.0	1047.7	1046.3
140°	1093.1	1093.6	1094.1	1093.7	1092.4	1091.1	1089.7	1088.4
142.5°	1133.7	1134.0	1134.4	1133.9	1132.5	1131.2	1129.9	1128.5
145°	1192.3	1192.3	1192.3	1191.9	1191.1	1190.3	1189.5	1188.7
147.5°	1246.7	1247.3	1247.9	1247.4	1245.5	1243.7	1242.0	1240.2
150°	1280.8	1280.8	1280.8	1280.5	1279.9	1279.5	1278.9	1278.3
152.5°	1312.6	1313.3	1313.9	1313.8	1312.8	1311.9	1310.9	1310.0
155°	1358.1	1359.2	1360.3	1360.2	1358.8	1357.5	1356.1	1354.9
157.5°	1397.6	1398.7	1399.7	1399.4	1397.6	1395.8	1394.1	1392.3
160°	1421.5	1422.5	1423.6	1423.5	1422.1	1420.8	1419.5	1418.2
162.5°	1443.9	1445.2	1446.4	1446.3	1444.8	1443.2	1441.7	1440.1
165°	1474.0	1475.1	1476.2	1475.9	1474.3	1472.7	1471.2	1469.5
167.5°	1496.4	1497.9	1499.5	1499.5	1497.9	1496.3	1494.6	1492.9
170°	1509.7	1511.3	1512.9	1512.8	1510.9	1509.1	1507.2	1505.4
172.5°	1519.3	1520.9	1522.5	1522.5	1520.8	1519.2	1517.5	1515.9
175°	1530.1	1531.7	1533.3	1533.1	1531.3	1529.4	1527.6	1525.7
177.5°	1534.9	1536.2	1537.5	1537.4	1535.9	1534.4	1532.9	1531.4
180°	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2

(END OF REPORT)