

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333642-927

Luminaire Tested: **S125RDIW-S375D470U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333642-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S375D470U927-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2630.8 lumens
Efficiency: N/A
Efficacy: 114.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 23
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333642-927

CATALOG NUMBER: S125RDIW-S375D470U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333642-927

CATALOG NUMBER: S125RDIW-S375D470U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44
1	97	92	89	85	88	85	81	78	70	68	66	57	55	54	45	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	40	38	36	31
3	80	71	64	58	73	65	59	54	55	50	46	44	41	39	35	33	31	27
4	74	63	55	49	67	58	51	46	49	43	39	40	36	33	32	29	27	23
5	68	56	48	42	62	52	45	40	43	38	34	36	32	29	28	26	24	20
6	62	50	42	37	57	47	40	34	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	24	21	18	16
8	53	41	34	28	49	38	31	27	32	27	23	27	23	20	22	19	17	14
9	50	38	30	25	45	35	28	24	30	25	21	25	21	18	20	17	15	13
10	46	35	27	23	43	32	26	21	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3130	3130	3130
5°	3138	3102	3121
10°	3114	3074	3074
15°	3077	3011	2986
20°	3030	2924	2889
25°	2974	2838	2776
30°	2905	2738	2651
35°	2834	2636	2511
40°	2769	2528	2373
45°	2689	2408	2223
50°	2608	2277	2067
55°	2514	2152	1901
60°	2421	2001	1721
65°	2311	1825	1516
70°	2185	1603	1307
75°	2011	1352	1088
80°	1770	1060	915
85°	1489	867	815



TEST NUMBER: P333642-927

CATALOG NUMBER: S125RDIW-S375D470U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.6	1.7
10°-20°	127.4	4.8
20°-30°	184.7	7.0
30°-40°	210.5	8.0
40°-50°	205.2	7.8
50°-60°	172.7	6.6
60°-70°	121.1	4.6
70°-80°	62.2	2.4
80°-90°	16.7	0.6
90°-100°	17.6	0.7
100°-110°	108.3	4.1
110°-120°	196.4	7.5
120°-130°	252.0	9.6
130°-140°	271.1	10.3
140°-150°	254.4	9.7
150°-160°	205.8	7.8
160°-170°	133.1	5.1
170°-180°	45.9	1.7
0°-30°	357.7	13.6
0°-40°	568.2	21.6
0°-60°	946.1	36.0
0°-90°	1146.2	43.6
90°-120°	322.2	12.2
90°-150°	1099.7	41.8
90°-180°	1485.0	56.4
0°-180°	2630.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	485	485	485	485	485	
5°	484	482	478	482	481	46
15°	460	458	450	450	447	130
25°	417	411	398	394	390	192
35°	360	350	334	324	318	225
45°	294	283	264	249	243	227
55°	223	211	191	175	169	200
65°	151	138	119	105	99	150
75°	81	69	54	46	44	85
85°	20	14	12	11	11	23
90°	0	3	6	8	9	2
95°	20	19	6	7	8	26
105°	105	107	107	107	106	112
115°	198	200	200	198	196	196
125°	281	284	284	282	281	251
135°	351	353	352	351	349	270
145°	407	407	408	408	406	254
155°	448	446	447	447	445	206
165°	473	471	471	473	470	133
175°	484	481	482	484	481	46
180°	484	484	484	484	484	



TEST NUMBER: P333642-927

CATALOG NUMBER: S125RDIW-S375D470U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	485.6	485.4	485.2	485.1	484.8	484.4	483.8	483.1	482.4	481.8	482.4
5°	484.0	483.7	483.4	483.0	482.7	482.1	481.2	480.3	479.4	478.5	479.3
7.5°	479.3	479.0	478.6	478.3	478.0	477.3	476.3	475.2	474.1	473.0	473.6
10°	474.8	474.6	474.4	474.1	473.9	473.2	472.1	470.9	469.8	468.7	468.9
12.5°	469.8	469.5	469.3	469.0	468.7	467.7	466.2	464.7	463.1	461.6	461.8
15°	460.2	459.7	459.2	458.8	458.3	457.2	455.4	453.8	452.0	450.4	450.3
17.5°	449.3	448.5	447.8	447.0	446.3	444.9	442.7	440.5	438.4	436.3	435.9
20°	440.8	440.0	439.2	438.4	437.5	435.9	433.2	430.6	428.0	425.4	425.0
22.5°	431.4	430.6	429.8	429.0	428.2	426.4	423.7	421.0	418.2	415.5	414.7
25°	417.4	416.1	414.9	413.7	412.5	410.4	407.3	404.3	401.3	398.3	397.3
27.5°	401.2	399.8	398.3	396.8	395.3	393.0	389.8	386.5	383.3	380.1	378.6
30°	389.5	388.0	386.4	384.9	383.3	380.9	377.5	374.1	370.7	367.2	365.4
32.5°	378.1	376.3	374.5	372.7	370.9	368.3	364.8	361.3	357.8	354.3	352.3
35°	359.5	357.6	355.6	353.6	351.7	348.9	345.2	341.6	337.9	334.3	331.9
37.5°	341.3	338.9	336.5	334.1	331.8	328.7	325.0	321.2	317.4	313.6	310.8
40°	328.4	326.0	323.5	321.1	318.6	315.4	311.6	307.7	303.7	299.8	296.8
42.5°	314.9	312.4	309.9	307.4	304.9	301.7	297.6	293.6	289.5	285.5	282.6
45°	294.4	292.0	289.6	287.2	284.9	281.5	277.0	272.6	268.1	263.6	260.3
47.5°	273.1	270.5	268.1	265.5	263.1	259.6	255.1	250.6	246.1	241.5	238.2
50°	259.6	256.9	254.2	251.5	248.8	245.2	240.5	235.9	231.2	226.6	223.2
52.5°	244.9	242.2	239.4	236.7	233.9	230.4	226.0	221.6	217.2	212.9	209.2
55°	223.3	220.7	218.1	215.6	212.9	209.4	204.8	200.2	195.7	191.1	187.4
57.5°	201.5	198.8	195.9	193.1	190.4	186.8	182.4	178.0	173.6	169.2	165.6
60°	187.4	184.6	181.7	178.9	176.0	172.5	168.0	163.7	159.2	154.9	151.3
62.5°	172.5	169.8	167.1	164.4	161.6	158.0	153.6	149.2	144.7	140.2	136.9
65°	151.2	148.5	145.7	142.9	140.1	136.6	132.3	128.0	123.7	119.4	116.1
67.5°	130.1	127.3	124.5	121.8	119.0	115.5	111.4	107.3	103.1	99.0	96.0
70°	115.7	113.0	110.2	107.4	104.6	101.2	97.1	93.1	89.0	84.9	82.4
72.5°	101.6	98.9	96.3	93.6	90.9	87.5	83.7	79.9	76.1	72.3	70.0
75°	80.6	78.1	75.7	73.2	70.8	67.9	64.4	61.0	57.6	54.2	52.4
77.5°	59.6	57.7	55.7	53.7	51.8	49.4	46.7	44.0	41.3	38.5	37.2
80°	47.6	45.6	43.7	41.7	39.8	37.7	35.4	33.1	30.8	28.5	27.8
82.5°	35.9	34.1	32.4	30.6	28.8	27.2	25.7	24.1	22.5	20.9	20.6
85°	20.1	18.7	17.2	15.8	14.3	13.3	12.9	12.5	12.1	11.7	11.6
87.5°	6.8	6.5	6.2	5.9	5.5	5.4	5.4	5.5	5.5	5.5	5.6
90°	0.4	1.0	1.7	2.3	2.9	3.5	4.0	4.6	5.1	5.7	6.1
92.5°	5.5	5.1	4.6	4.2	3.7	3.7	4.3	4.8	5.2	5.7	6.1
95°	20.4	20.2	20.0	19.7	19.5	17.8	14.8	11.8	8.8	5.7	6.1
97.5°	42.6	43.1	43.5	44.0	44.4	41.6	35.6	29.6	23.6	17.7	15.4
100°	59.8	60.1	60.4	60.6	60.8	61.1	61.4	61.7	62.0	62.3	50.5
102.5°	77.3	77.6	78.0	78.3	78.6	78.8	79.0	79.1	79.4	79.5	77.3
105°	105.4	105.7	106.0	106.3	106.6	106.8	106.8	106.8	106.8	106.8	106.8
107.5°	134.4	134.4	134.4	134.4	134.4	134.5	134.7	134.8	135.0	135.1	135.2
110°	153.4	153.4	153.4	153.4	153.4	153.4	153.6	153.8	153.9	154.1	153.8



TEST NUMBER: P333642-927

CATALOG NUMBER: S125RDIW-S375D470U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	171.2	171.3	171.5	171.7	171.9	172.1	172.1	172.3	172.4	172.5	172.1
115°	197.8	198.2	198.6	199.0	199.4	199.6	199.7	199.8	199.9	199.9	199.6
117.5°	225.5	225.4	225.4	225.4	225.4	225.5	225.8	226.1	226.4	226.7	226.3
120°	242.6	242.6	242.5	242.4	242.3	242.4	242.6	242.9	243.1	243.4	243.2
122.5°	257.9	258.1	258.4	258.7	259.0	259.2	259.4	259.4	259.6	259.7	259.5
125°	281.3	281.9	282.4	283.0	283.5	283.8	283.8	283.8	283.8	283.8	283.5
127.5°	303.7	304.2	304.6	305.0	305.4	305.5	305.5	305.5	305.4	305.3	305.1
130°	317.5	317.9	318.3	318.7	319.1	319.3	319.4	319.5	319.6	319.6	319.4
132.5°	331.3	331.8	332.2	332.6	333.1	333.3	333.1	333.0	332.7	332.6	332.6
135°	350.9	351.3	351.8	352.3	352.8	352.9	352.8	352.6	352.4	352.3	352.1
137.5°	368.8	369.2	369.6	370.1	370.5	370.7	370.5	370.3	370.2	370.0	370.1
140°	380.6	380.7	380.9	381.0	381.2	381.3	381.2	381.1	381.0	381.0	381.1
142.5°	391.2	391.3	391.4	391.5	391.6	391.7	391.8	391.9	392.1	392.1	392.1
145°	406.8	406.9	407.1	407.3	407.4	407.5	407.5	407.5	407.5	407.5	407.6
147.5°	420.4	420.3	420.3	420.3	420.3	420.3	420.4	420.5	420.6	420.6	420.7
150°	429.0	428.8	428.6	428.5	428.3	428.3	428.5	428.6	428.8	429.0	429.1
152.5°	437.3	437.0	436.6	436.3	435.9	435.8	435.9	436.1	436.3	436.4	436.6
155°	448.0	447.5	447.0	446.6	446.1	445.9	446.1	446.2	446.4	446.6	446.8
157.5°	456.2	455.9	455.7	455.3	455.0	455.0	455.0	455.0	455.0	455.0	455.3
160°	461.9	461.4	461.0	460.5	460.0	459.9	459.9	460.0	460.1	460.2	460.5
162.5°	466.5	466.0	465.6	465.1	464.6	464.5	464.5	464.6	464.7	464.8	465.2
165°	472.7	472.2	471.7	471.3	470.8	470.6	470.6	470.7	470.8	470.9	471.3
167.5°	477.3	476.8	476.3	475.8	475.3	475.1	475.2	475.2	475.3	475.4	476.0
170°	479.9	479.3	478.7	478.2	477.6	477.4	477.4	477.5	477.6	477.7	478.3
172.5°	481.6	481.0	480.5	479.9	479.3	479.2	479.3	479.4	479.6	479.7	480.3
175°	483.5	483.0	482.5	482.0	481.6	481.3	481.4	481.5	481.6	481.6	482.3
177.5°	484.3	483.9	483.5	483.2	482.8	482.6	482.7	482.8	482.8	482.9	483.3
180°	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5



TEST NUMBER: P333642-927

CATALOG NUMBER: S125RDIW-S375D470U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	483.1	483.8	484.4	484.7	484.7	484.6	484.5	484.4
5°	480.1	480.9	481.7	482.1	482.0	481.7	481.6	481.4
7.5°	474.1	474.8	475.3	475.5	475.3	475.2	475.0	474.8
10°	469.1	469.4	469.6	469.6	469.4	469.1	468.9	468.7
12.5°	461.9	462.2	462.3	462.2	461.8	461.4	461.1	460.7
15°	450.1	450.0	450.0	449.6	448.9	448.1	447.4	446.6
17.5°	435.5	435.1	434.7	434.1	433.6	432.9	432.3	431.7
20°	424.6	424.2	423.8	423.3	422.5	421.8	421.0	420.3
22.5°	413.8	413.0	412.3	411.5	411.0	410.4	409.8	409.2
25°	396.2	395.1	394.1	393.2	392.2	391.3	390.5	389.5
27.5°	377.2	375.7	374.1	373.0	372.2	371.3	370.4	369.6
30°	363.5	361.6	359.7	358.5	357.7	357.0	356.2	355.5
32.5°	350.2	348.2	346.0	344.6	343.6	342.7	341.7	340.9
35°	329.5	327.2	324.8	323.1	321.9	320.8	319.6	318.5
37.5°	307.9	305.1	302.3	300.3	299.2	298.1	297.0	295.9
40°	293.7	290.6	287.5	285.4	284.5	283.5	282.5	281.5
42.5°	279.6	276.6	273.6	271.5	270.1	268.5	267.1	265.7
45°	257.1	253.8	250.6	248.3	247.2	245.9	244.7	243.4
47.5°	234.9	231.5	228.1	225.8	224.4	223.1	221.7	220.4
50°	219.8	216.3	212.9	210.6	209.5	208.2	207.0	205.7
52.5°	205.5	201.8	198.1	195.7	194.5	193.3	192.0	190.8
55°	183.8	180.1	176.5	174.0	172.7	171.3	170.1	168.8
57.5°	162.1	158.5	154.9	152.5	151.4	150.2	149.1	147.9
60°	147.7	144.1	140.5	138.2	136.9	135.7	134.5	133.2
62.5°	133.6	130.2	126.9	124.7	123.4	122.2	121.0	119.8
65°	112.8	109.6	106.3	104.1	102.9	101.6	100.4	99.2
67.5°	93.0	90.1	87.1	85.1	84.1	83.2	82.1	81.2
70°	79.9	77.4	74.9	73.1	72.1	71.1	70.2	69.2
72.5°	67.7	65.4	63.1	61.6	60.9	60.3	59.6	58.9
75°	50.6	48.8	47.1	45.9	45.3	44.7	44.1	43.6
77.5°	36.0	34.8	33.5	32.6	32.2	31.8	31.4	31.0
80°	27.1	26.4	25.7	25.2	25.0	24.9	24.7	24.6
82.5°	20.3	19.9	19.6	19.3	19.3	19.2	19.1	18.9
85°	11.6	11.5	11.4	11.3	11.2	11.2	11.1	11.0
87.5°	5.7	5.8	5.9	5.9	5.9	5.9	5.9	5.8
90°	6.5	6.9	7.3	7.7	7.9	8.2	8.4	8.6
92.5°	6.5	6.9	7.3	7.6	7.7	7.8	7.9	8.0
95°	6.5	6.9	7.3	7.5	7.5	7.5	7.5	7.5
97.5°	13.2	10.9	8.6	7.5	7.5	7.5	7.5	7.5
100°	38.7	26.8	14.9	8.8	8.5	8.2	7.8	7.5
102.5°	75.1	72.8	70.6	66.8	61.3	55.9	50.5	45.1
105°	106.8	106.8	106.8	106.8	106.7	106.6	106.5	106.5
107.5°	135.2	135.2	135.2	135.1	134.9	134.7	134.4	134.2
110°	153.6	153.4	153.1	153.0	153.1	153.2	153.3	153.4



TEST NUMBER: P333642-927

CATALOG NUMBER: S125RDIW-S375D470U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	171.8	171.5	171.3	171.0	171.0	170.8	170.7	170.6
115°	199.3	199.0	198.7	198.3	197.8	197.3	196.9	196.4
117.5°	225.9	225.5	225.1	224.7	224.5	224.3	224.1	223.9
120°	243.0	242.9	242.7	242.4	242.0	241.6	241.2	240.8
122.5°	259.4	259.2	259.0	258.7	258.3	257.8	257.4	256.9
125°	283.2	282.9	282.6	282.3	282.0	281.8	281.5	281.3
127.5°	305.0	304.8	304.7	304.3	303.6	303.1	302.5	301.9
130°	319.2	318.9	318.7	318.4	318.0	317.6	317.2	316.8
132.5°	332.5	332.4	332.4	332.2	331.8	331.4	331.0	330.6
135°	352.0	351.8	351.6	351.3	350.9	350.4	349.9	349.4
137.5°	370.1	370.2	370.2	370.0	369.6	369.2	368.8	368.4
140°	381.3	381.4	381.6	381.4	381.0	380.5	380.0	379.5
142.5°	392.2	392.2	392.3	392.1	391.6	391.1	390.6	390.1
145°	407.7	407.7	407.8	407.6	407.1	406.6	406.2	405.7
147.5°	420.9	421.0	421.0	420.8	420.3	419.7	419.1	418.5
150°	429.3	429.4	429.6	429.4	428.7	428.1	427.5	426.8
152.5°	436.7	436.9	437.0	436.9	436.3	435.7	435.1	434.6
155°	447.0	447.3	447.5	447.3	446.6	446.0	445.4	444.7
157.5°	455.5	455.7	456.0	455.8	455.2	454.6	453.9	453.3
160°	460.8	461.1	461.4	461.3	460.7	460.0	459.4	458.8
162.5°	465.6	466.1	466.5	466.4	465.7	465.0	464.3	463.6
165°	471.9	472.4	472.9	472.8	472.1	471.4	470.8	470.2
167.5°	476.6	477.1	477.7	477.7	476.9	476.2	475.5	474.8
170°	479.0	479.7	480.3	480.2	479.5	478.8	478.1	477.4
172.5°	480.9	481.4	482.0	482.0	481.3	480.5	479.8	479.1
175°	482.9	483.5	484.2	484.2	483.5	482.8	482.0	481.3
177.5°	483.8	484.2	484.7	484.7	484.1	483.6	483.1	482.6
180°	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5

(END OF REPORT)